thermoscientific



Two-dimensional HPLC determination of water-soluble vitamins in a nutritional drink

Authors

Dai Zhenyu, Chen Jing, Xu Qun, and Jeffrey Rohrer, Thermo Fisher Scientific, Shanghai, People's Republic of China;

Keywords

Food Analysis, Food Quality, Two-Dimensional HPLC, Acclaim PolarAdvantage Column, Acclaim 120 C18 Column, Hypersil GOLD Phenyl Column

Goal

To develop an efficient high-performance liquid chromatography (HPLC) method for simple and sensitive determination of water-soluble vitamins in a complex multivitamin/mineral drink. Target analytes are B group vitamins, including thiamine (V_{B1}), riboflavin (V_{B2}), nicotinamide (V_{B3}), pantothenic acid (VB_5), pyridoxine (V_{B6}), biotin (V_{B7}), and cyanocobalamin (V_{B12}), and ascorbic acid (V_c).

Introduction

Vitamins are a well-known group of compounds that are essential for human health. They can be classified into two main groups: water- and fat-soluble. With the exception of V_{B6} and V_{B12} , water-soluble vitamins are not stored in the body. Thus, if one's dietary vitamin intake is insufficient, a vitamin supplement should be added to the diet.

The vitamin supplement can be in tablet form, a clear vitamin-enhanced functional drink, vitamin-enhanced milk, or a nontransparent multivitamin/ mineral nutritional drink with additions of other substances (e.g., fruit extracts) that make it more complex than clear products. To ensure that these products contain the labeled amounts of vitamins, a number of reliable quality control assays are available.^{1,2} For a vitamin tablet or a clear functional drink, the analysis is relatively simple and a routine HPLC method (e.g., a C18 column with UV detection) is satisfactory for quantifying the vitamins.³



Some samples, however, have too many additional components to allow a routine HPLC vitaminquantification method. Vitamin-enhanced milk and a nontransparent multivitamin/mineral nutritional drink referred to as a multivitamin nutritional drink throughout the rest of this study—are two such samples. In addition to vitamins, these samples may also supply amino acids, minerals, coenzyme Q10, the compounds contained in grape extracts, and more. These additional compounds interfere with the separation of vitamins, making quantification difficult. Therefore, a simple and sensitive two-dimensional HPLC (2D-HPLC) method is needed to quantify vitamins in these complex samples.

Equipment and Software

- The Thermo Scientific[™] UltiMate[™] 3000 Dual-Gradient Rapid Separation (RS) LC system was used, which includes:
- Thermo Scientific[™] UltiMate[™] 3000 Series SRD-3600 Integrated Solvent and Degasser Rack | (P/N 5035.9230)
- Thermo Scientific[™] UltiMate[™] 3000 DPG-3600RS Dual-Gradient RS Pump (P/N 5040.0066)
- Thermo Scientific[™] UltiMate[™] 3000 WPS-3000TRS Thermostatted Split-Loop Autosampler (P/N 5840.0020)
- Thermo Scientific[™] UltiMate[™] 3000 TCC-3000RS Rapid Separation Thermostatted Column Compartment (P/N 5730.000) with 2p-6p valves
- Thermo Scientific[™] UltiMate[™] 3000 DAD-3000RS Diode Array Detector (P/N 5082.0020), equipped with analytical flow cell, 13 μL, SST (P/N 6082.0100)
- Mixer for 800 µL Mixing Volume (P/N 6040.5750)
- Thermo Scientific[™] Chromeleon[™] Chromatography Data System (CDS) software version 7.1 or higher
- Thermo Scientific[™] Orion[™] 2-Star pH Benchtop Meter

Reagents and Standards

- Deionized (DI) water, 18.2 MΩ.cm resistivity
- Acetonitrile (CH₃CN) for HPLC (Fisher Scientific P/N AC610010040)
- Potassium Phosphate Monobasic (KH₂PO₄) (Fisher Scientific P/N P286-1)
- o-Phosphoric Acid (H₃PO₄), 85%, (Fisher Scientific P/N A260-500)
- Products from the National Institute for the Control of Pharmaceutical and Biological Products, Beijing, China:
 V_{B1}, V_{B2}, V_{B3}, V_{B5}, V_{B6}, V_{B7}, V_{B12}, V_C

Preparation of Standard Solutions

To prepare water-soluble vitamin standards of V_{B1}, V_{B3}, V_{B5}, V_{B6}, V_{B7}, V_{B12}, and V_C, weigh 10 mg of the vitamin powder and add DI water to 10 mL in a volumetric flask to make stock solutions of 1.0 mg/mL for each vitamin. Make a fresh preparation of V_C daily, due to its limited stability. Also, because of the limited solubility of V_{B2} in water, decrease the concentration of the V_{B2} stock solution to 0.03 mg/mL. Weigh 3 mg of V_{B2} into 100 mL DI water to address the solubility issue. If a 10 mL volumetric flask was used, 0.3 mg of V_{B2} would have to be weighed, but that would exceed the precision range of the balance.

Add 500 μ L of V_{B2} stock solution, 100 μ L each of V_{B5} and V_{B7} stock solutions, and 50 μ L each of V_{B1}, V_{B3}, V_{B6}, V_{B12}, and V_c stock solutions to a 1 mL sample vial. Bring the final volume to 1 mL by adding 50 μ L of DI water to make the mixed stock standard solution. In this mixed stock standard solution, the concentration of V_{B2} will be 15 μ g/mL, the concentrations of V_{B5} and V_{B7} will be 100 μ g/mL, and the concentration of the other vitamins will be 50 μ g/mL.

| Mixed Working Standard Solution | | | 2 | 3 | 4 | 5 | 6 |
|-------------------------------------------------------------------------|--------------------------------------------------|------|------|-----|-----|-----|-----|
| Volume of Mixed Stock Standard Solution for a 10 mL Preparation (mL) | | | 0.1 | 0.2 | 1.0 | 2.0 | 10 |
| Concentration of Each Vitamin (mg/L) | V _{B2} | 0.03 | 0.15 | 0.3 | 1.5 | 3.0 | 15 |
| | V_{B5}, V_{B7} | 0.2 | 1.0 | 2.0 | 10 | 20 | 100 |
| | $\rm V_{B1}, V_{B3}, V_{B6}, V_{B12}, V_{C}$ | 0.1 | 0.5 | 1.0 | 5.0 | 10 | 50 |

Table 1. Preparation of mixed working standard solutions of water-soluble vitamins.

Table 2. Labeled values of the multivitamin nutritional drink.

| Ingredient | Amount Per Serving* | Ingredient | Amount Per Serving | |
|-----------------------------------|------------------------|------------------------------------------|-----------------------|--|
| Total Carbohydrate | 9 g | Zinc (as gluconate) | 15 mg | |
| Vitamin A | 10000 IU** | Selenium (as L-selenium methione) | 100 mcg | |
| Vitamin C | 1000 mg | Copper (as gluconate) | 1 mg | |
| Vitamin D3 | 200 IU | Manganese (as gluconate) | 5 mg | |
| Vitamin E | 200 IU | Chromium (as amino acid chelate) | 200 mcg | |
| Vitamin K1 | 300 mcg | Potassium (as citrate) | 100 mg | |
| Vitamin B1 | 30 mg | Choline (as bitartrate) | 30 mg | |
| Vitamin B2 | 30 mg | Inositol | 30 mg | |
| Vitamin B3 | 30 mg | Boron (as amino acid chelate) | 1 mg | |
| Vitamin B5 | 150 mg | Amino Acid Complex (proprietary formula) | 125 mg | |
| Vitamin B6 | 30 mg | Grape Seed Extract | 25 mg | |
| Vitamin B7 | 300 mcg | Coenzyme Q-10 | 5 mg | |
| Vitamin B12 | 500 mcg | Dimethyl Glycine | 25 mg | |
| Folate | 400 mcg | Paba | 30 mg | |
| Calcium | 600 mg | Citrus Bioflavonoids | 13 mg | |
| Phosphorus | 80 mg | Glucolactone | 150 mg | |
| Iron (as gluconate) | 4 mg | Plant-Derived Minerals | 600 mg | |
| Magnesium (as citrate, gluconate) | 300 mg | | | |

* Serving size: 28.4 mL **International units (IU), mass depending on substance potency

For the preparation of mixed working standard solutions for calibration, add the appropriate volume of the mixed stock standard solution into 10 mL glass vials and bring to 10 mL with DI water. See Table 1 for details.

Sample Preparation

A multivitamin nutritional drink supplemented with V_{B1} , V_{B2} , V_{B3} , V_{B5} , V_{B6} , V_{B7} , V_{B12} , and V_{C} was provided by a customer. The drink also contained some fat-soluble vitamins, minerals, amino acid complex, grape seed extract, coenzyme Q10, and other ingredients added to meet daily nutritional needs. Table 2 lists the sample components.

Dilute the drink sample with DI water if necessary and filter through a 0.45 μ m filter. To determine if the sample needs to be diluted, compare the labeled values to the calibration ranges in this study. Store the sample in a brown bottle at 4 °C before analysis.

Conditions

| First Dimensi | on |
|---------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Columns: | For water-soluble vitamins except for V _{B12} , Thermo Scientific [™] Acclaim [™] PolarAdvantage [™] (PA), 5 µm Analytical, 4.6 × 250 mm (P/N 061321) |
| | For V _{B12} , Thermo Scientific™ Hypersil GOLD™ Phenyl Analytical HPLC, 5 μm, 4.6 × 150 mm (P/N 25905-154630) |
| Mobile Phase: | A. 25 mM phosphate buffer (dissolve \sim 3.4 g KH ₂ PO ₄ in 1 L water and adjust the pH to 3.0 with H ₃ PO ₄) B. CH ₃ CN |
| Gradient: | See Table 3 |
| Flow Rate: | 0.8 mL/min |
| Inj. Volume: | 10 μL |
| Temperature: | 25 °C |
| Detection: | UV, absorbance at 210 and 254 nm |
| Second Dime | nsion |
| Column: | Acclaim 120 C18, 5 μm Analytical, 4.6 × 150 mm (P/N 059148) |
| Mobile Phase: | Same as used in the First Dimension |
| Flow Rate: | 0.8 mL/min |
| Temperature: | 25 °C |
| Detection: | UV absorbance at 210, 245, 268, and 291 nm |
| | |

These conditions apply to Figures 3 through 7.

Table 3. Gradient program and valve switching.

| First Dimension (Right Pump) | | | Valve Switching | | | Second Dimension (Left Pump) | | | | |
|------------------------------|------------------------------|-----------------------------------------------|-----------------------------|---------------|----------------------------|------------------------------|---------------|------------------------------|-----------------------------------------------|-----------------------------|
| Time (min) | Flow Rate (mL/ min) | % A (25 mM Phosphate Buffer, pH 3.0) | % B (CH ₃ CN) | Time (min) | Right Valve Position | Left Valve Position | Time (min) | Flow Rate (mL/ min) | % A (25 mM Phosphate Buffer, pH 3.0) | % B (CH ₃ CN) |
| 0 | 0.8 | 100 | 0 | 0 | 6_1 | 1_2 | 0 | 0.8 | 100 | 0 |
| 5 | 0.8 | 100 | 0 | 3.94 | 1_2 | 6_1 | 14 | 0.8 | 100 | 0 |
| 12.5 | 0.8 | 65.0 | 35.0 | 4.3 | 6_1 | 1_2 | 23.5 | 0.8 | 50 | 50 |
| 13.0 | 0.8 | 20.0 | 80.0 | 5.32 | 1_2 | 6_1 | 24 | 0.8 | 100 | 0 |
| 21.0 | 0.8 | 20.0 | 80.0 | 5.89 | 6_1 | 1_2 | 30 | 0.8 | 100 | 0 |
| 21.5 | 0.8 | 100 | 0 | 7.8 | 1_2 | 1_2 | — | — | — | — |
| 30 | 0.8 | 100 | 0 | 8.35 | 6_1 | 6_1 | — | — | — | — |
| — | — | — | — | 13.12 | 1_2 | 1_2 | — | — | — | — |
| — | — | — | — | 13.28 | 6_1 | 6_1 | — | — | — | — |
| — | — | — | — | 14.61 | 1_2 | 1_2 | — | — | — | — |
| — | — | — | — | 14.82 | 6_1 | 6_1 | — | — | — | — |
| _ | _ | — | _ | 15.42 | 1_2 | 1_2 | _ | — | _ | _ |
| — | — | — | — | 15.60 | 6_1 | 6_1 | — | — | — | — |
| — | — | — | — | 15.97 | 1_2 | 1_2 | — | — | — | — |
| — | — | — | — | 16.12 | 6_1 | 6_1 | — | — | — | — |
| — | — | — | — | 28.5 | 6_1 | 1_2 | _ | _ | _ | — |

Results and Discussion Conventional HPLC Method for the Determination of Vitamins

Currently, there is no U.S. Pharmacopeia (USP) method for the separation of a mixture containing all eight watersoluble vitamins. A USP method for individual vitamins is complicated (i.e., sodium perchlorate, phosphoric acid, dimethyl sulfoxide, acetonitrile, and water are needed for biotin determination) and involves an ion-pairing agent to retain hydrophilic vitamins.⁴ Due to the irreversible impact of the ion-pairing agent on column performance, extensive research was conducted to search for methods without ion-pairing agents and with the use of a simpler mobile phase.

Recently, acidic or neutral phosphate buffer/organic solvent mobile phases have been used to separate vitamins in an extract of a multivitamin tablet and in vitamin-enhanced functional drinks that are less complex than the one investigated here.¹ For complex samples, such as certain multivitamin nutritional drinks, the additional supplements can interfere with vitamin separation and, ultimately, their detection by UV absorbance. Figure 1 shows that the use of a typical HPLC method for a multi-vitamin nutritional drink results in the water-soluble vitamin peaks being hard or even impossible to quantify due to the large number of

| Column: Mobile Phase: | Acclaim PA1, 5 μ m Analytical, 4.6 × 250 mm A. 25 mM phosphate buffer (dissolve ~3.4 g KH ₂ PO ₄ in 1 L water and adjust pH to 3.0 with H ₃ PO ₄) | | | | | |
|----------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|--|
| Gradient: | B. CH ₃ CN CH ₃ CN, 0–5 min, 0%; 12.5 min, 35%; 13–21 min, | | | | | |
| Flow Rate: Inj. Volume: Temperature: Detection: Samples: | 80%; 21.5–30 min, 0% 0.8 mL/min 10 μL 25 °C UV absorbance at 210 nm A. Standard mixture B. Multivitamin nutritional drink | | | | | |
| Peaks: | $ \begin{array}{llllllllllllllllllllllllllllllllllll$ | | | | | |
| 500- | | | | | | |
| mAU B | | | | | | |
| 0 A | | | | | | |
| -50 <mark>0</mark> | 5 10 15 20 25 Minutes | | | | | |

Figure 1. A standard mixture (A) and a multivitamin nutritional drink sample (B) using a conventional HPLC method.

UV-absorbing interfering peaks. Obviously, Peaks 1–3 cannot be quantified. Peaks 5–8 can be detected in the sample, but due to all the additional peaks, the vitamin peaks cannot be precisely quantified. Comparison of the UV spectra of the standard and the sample confirmed that Peaks 5–8 were not pure enough for quantification.

The 2D-HPLC Method

Two-dimensional HPLC has been used to achieve efficient separation of complex samples. Not only do two columns with different chemistries provide additional separation power, but the use of heart-cutting technology in on-line 2D-HPLC also simplifies the separation in the second dimension. The work shown here uses 2D chromatography to determine watersoluble vitamins in a complex sample.

Figure 2 shows the configuration of the 2D-HPLC system used for this study. After simple sample preparation (filter the sample, then dilute with DI water if necessary), inject the sample into the first dimension and partially separate it using an Acclaim PA column. The in-line UV detector determines where the water-soluble vitamins elute. An injection of the mixed standard determines the start and end times for each vitamin peak. Use these values to switch the valves.




Figure 2. Configuration of the 2D-HPLC system.

Switch the right valve to the 1_2 position to individually transfer the vitamin peaks to the flow path of the second column. For early eluting vitamin peaks, switch the left valve to the 1_6 position so that these vitamin fractions are directly transferred to the second column. For late eluting vitamin peaks, switch the left valve to the 1_2 position to put the 750 µL mixer in line. In this

configuration, the water mobile phase in the second dimension will dilute the acetonitrile from the firstdimension mobile phase. This enables the seconddimension column to trap the vitamin peaks.

Note: When the right valve is switched to the 1_2 position, UV Detector 1 will be connected between the two columns. However, the backpressure of the second-dimension column may exceed the pressure limit of the UV Detector 1 flow cell. Thus, choose the proper particle size and length of the second-dimension column to keep the backpressure below the pressure limit of the flow cell. The pressure limit command in the instrument method can also be set to stop the flow in any situation when backpressure may become too high.

Development of the 2D-HPLC Method Valve switching

To achieve optimal resolution and peak shape in 2D-HPLC applications, the critical part of method development is the transfer of first-dimension peaks to the second-dimension column. Ideally, the firstdimension mobile phase being cut and transferred with target peaks to the second dimension will be same as the second-dimension mobile phase at the time of transfer. But in reality, the two mobile phases usually will have different concentrations of acetonitrile or other organic solvent.

Figure 3, Chromatogram A shows that Peaks 5, 7, and 8 disappear when they are directly transferred to the second dimension. Obviously, the late eluting peaks from the first column are contained in too high a concentration of acetonitrile to be retained on the second column. The traditional approach to this problem is to provide water to dilute the acetonitrile in the transferred fraction with a tertiary pump so the fraction can be retained on the trap column ahead of the second column.⁵ However, the need for an additional pump limits this application.

Thermo Scientific Application Note (AN) 1023 demonstrated an alternative way to solve this problem.⁶ Briefly, a 750 μ L mixer was configured in line before the eluted fraction was transferred to the second dimension. Then the peak mobile phase was mixed extensively with the second-dimension starting mobile phase (water phase) before the second-dimension separation.

In this study, the authors initially applied the AN 1023 approach for all target peaks. It worked well for late eluting peaks, which had high concentrations of acetonitrile, but the early eluting peaks broadened (Figure 3, Chromatogram B). After conducting additional experiments, the authors discovered that early eluting vitamin peaks broadened due to their physiochemical characteristics. These peaks cannot be trapped at the head of the second column, even with a 100% water mobile phase. Thus, the configuration was modified so that early eluting peaks are directly transferred to the second column, whereas late eluting peaks are transferred into the 750 μ L mixer before the second column. Figure 3, Chromatogram C shows that the final configuration works well for all eight watersoluble vitamins.




Figure 4. A standard mixture (A) and a multivitamin nutritional drink sample (B) using an Acclaim PA column in the first dimension.




Figure 5. A $\rm V_{_{B12}}$ standard (A) and a multivitamin nutritional drink sample (B) using a Hypersil GOLD Phenyl column in the first dimension.

Detection: UV absorbance at 210 nm Valve Position: See Table 3

Configurations: A. 750 μL mixer always off-line (i.e. Figure 2: Left valve position 1-6) B. 750 μL mixer always in-line (i.e. Figure 2: Left valve position 1-2) C. 750 μL mixer off-line for Peaks 1–3, in-line for Peaks 4–8




Figure 3. Second-dimension analysis of the standard mixture with three different configurations.

Choice of wavelength for the UV detector

Vitamins B_1 , B_2 , B_6 , and C were detected at 245, 268, 291, and 245 nm, respectively, which are the wavelengths of maximum UV absorbance for each. Vitamin B_3 was detected at 268 nm, which is close to its maximum UV absorbance. The maximum UV absorbance wavelengths of V_{B5} and V_{B7} are below 200 nm; to minimize noise, both were detected at 210 nm. Vitamin B_{12} was detected with the 245 nm channel. If desired, a fifth channel of 361 nm can be configured to detect V_{B12} at its absorbance maximum.

Column choice and its impact on separation

Several combinations of columns were tested. Previous work suggested that good choices for most watersoluble vitamins are an Acclaim PA column used as the first-dimension column and an Acclaim 120 C18 column used as the second-dimension column.⁷ Most watersoluble vitamins can be separated with good resolution using this column combination, but V_{B12} coelutes with an

Table 4. Reproducibility of retention time and peak area for water-soluble vitamins.

| Water-Soluble Vitamin | Retention Time RSD | Peak Area RSD |
|--------------------------|-----------------------|------------------|
| V _{B1} | 0.05% | 1.08 |
| V _{B2} | 0.02% | 0.32 |
| V _{B3} | 0.11% | 0.62 |
| V _{B5} | 0.03% | 0.36 |
| V _{B6} | 0.03% | 0.45 |
| V _{B7} | 0.02% | 0.87 |
| V _{B12} | 0.02% | 0.48 |
| V _c | 0.1% | 3.44 |

Table 5. Calibration data and MDLs for the water-soluble vitamins.

impurity in the drink sample, making quantification of $\rm V_{\rm B12}$ impossible.

The authors searched for another column to use for the first dimension. The Hypersil GOLD Phenyl column worked well for this purpose. Figure 4 shows that $\rm V_{B12}$ was not detected at 245 nm when an Acclaim PA




Figure 6. Chromatogram overlays of eight consecutive injections of a mixture of water-soluble vitamin standards.

| Water-Soluble Vitamin | Detection Wavelength (nm) | Range (µg/mL) | Regression Equation | r | MDL (µg/mL) |
|--------------------------|---------------------------------|------------------|---------------------|--------|----------------|
| V _{B1} | 245 | 0.5–10 | A=0.1755c-0.1080 | 0.9978 | 0.30 |
| V _{B3} | 268 | 0.5–50 | A=0.2385c+0.0276 | 0.9999 | 0.23 |
| V_{B6} | 291 | 0.5–50 | A=0.2918c+0.1237 | 0.9999 | 0.18 |
| V _{B5} | 210 | 1.0–100 | A=0.0462c+0.0161 | 0.9999 | 0.26 |
| V _{B12} | 245 | 0.5–50 | A=0.1026c+0.0153 | 0.9999 | 0.20 |
| V _{B2} | 268 | 0.15–15 | A=0.9618c-0.0423 | 0.9995 | 0.03 |
| V _{B7} | 210 | 2.0-100 | A=0.0101c | 0.9994 | 1.5 |
| V _c | 245 | _ | _ | _ | _ |

Due to working standard instability, Vitamin C calibration and quantification were not provided.

column was used in the first dimension. However, when the Hypersil GOLD Phenyl column was used in the first dimension, V_{B12} was detected (Figure 5). The authenticity of the V_{B12} peak was confirmed by its UV spectrum.

Reproducibility, Linearity, and Detection Limits

Prior to sample analysis, reproducibility was estimated by making eight replicate injections of water-soluble vitamins. The RSDs for retention time and peak area are shown in Table 4. An overlay of the eight injections is shown in Figure 6.




Figure 7. Second dimension of multivitamin nutritional drink sample (100-fold dilution).

Calibration linearity for the water-soluble vitamins was investigated by making three replicate injections of a mixed standard prepared at five or six different concentrations. The external standard method was used to calculate the calibration curve and quantify these compounds in samples. Table 5 reports the data from the calibration as calculated by Chromeleon CDS software. The authors found linear calibration curves for each vitamin over the ranges evaluated. The singlesided Student's *t* test method was used for estimating method detection limits (MDL) for a 99% confidence level. These data are reported in Table 5.

Sample Analysis

Vitamins B_7 and B_{12} were not detected in the multivitamin nutritional drink, possibly due to their low concentration in the sample. Vitamin B_3 was surprisingly not detected. Vitamin B_3 was fully recovered when spiked into the sample at its labeled value; therefore, the method is capable of determining V_{B3} . The other water-soluble vitamins were detected close to their labeled values.

Although V_c in the working standard solutions is quite unstable, its presence in the multivitamin nutritional drink appeared to be relatively stable. As shown in Figure 7, V_c is a major peak in the sample chromatogram. Good recoveries of water-soluble vitamins in the spiked sample (Table 6) provided

Table 6. Analysis results of water-soluble vitamins in the multivitamin nutritional drink sample.

| Analyte | Labeled (mg/mL)* | Detected (µg/mL) | Added (μg/mL) | Found (µg/mL) | Recovery (%) |
|------------------|---------------------|---------------------|------------------|------------------|-----------------|
| V _{B1} | 1 | 1.03 | 1 | 1.98 | 95 |
| V _{B3} | 1 | ND | 1 | 0.96 | 96 |
| V_{B6} | 1 | 1.1 | 1 | 2.2 | 110 |
| V _{B5} | 5 | 4.51 | 2 | 6.03 | 76 |
| V _{B12} | 0.015 | ND | 1 | 0.83 | 83 |
| V _{B2} | 1 | 1.03 | 0.3 | 1.34 | 103 |
| V _{B7} | 0.01 | ND | 2 | 2.30 | 115 |
| V _c | 35 | Detected | — | — | _ |

*The sample is diluted 1000 times before analysis; thus, 1 mg/mL will be detected as 1 μ g/mL. Due to working standard instability, Vitamin C was not quantified. ND = not detected.

another positive indicator of method accuracy. This 2D-HPLC method greatly simplifies the seconddimension chromatogram, as shown in Figure 7.

Conclusion

Two-dimensional HPLC simplifies the determination of the vitamin content of a multivitamin nutritional drink, a complex sample. Analysis of this complex sample requires only off-line filtration because the remainder of the sample preparation is automated by the UltiMate 3000 Dual-Gradient HPLC system and Chromeleon CDS software. The application was successful for determination of the B group vitamins in the presence of other nutritional additives.

The method was not able to quantify Vitamin C, although detected.

References

- Moreno, P.; Salvado, V. Determination of Eight Water- and Fat-Soluble Vitamins in Multivitamin Pharmaceutical Formulations by High-Performance Liquid Chromatography. J. Chromatogr., A 2000, 870, 207–215.
- Perveen, S.; Yasmin, A; Khan, K.M. Quantitative Simultaneous Estimation of Water Soluble Vitamins, Riboflavin, Pyridoxine, Cyanocobalamin and Folic Acid in Nutraceutical Products by HPLC. The Open Analytical Chemistry Journal 2009, 3, 1–5.
- 3. Thermo Fisher Scientific Application Note 252: HPLC Assay of Water-Soluble Vitamins, Fat-Soluble Vitamins, and a Preservative in Dry Syrup Multivitamin Formulation
- 4. Vitamins/Dietary Supplements, The U.S. Pharmacopeia 35, NF 30, Washington, DC, 2008, pp 1592–1605.
- Thermo Fisher Scientific Application Note 287: Two-Dimensional HPLC Combined with On-Line SPE for Determination of Sudan Dyes I–IV in Chili Oil. Sunnyvale, CA, 2011. [Online] <u>https://tools.thermofisher.com/content/sfs/brochures/111142-AN287-HPLC-Sudan-Dyes-Chili-Oil-21Sept2011-LPN2919.pdf</u>
- 6. Thermo Fisher Scientific Application Note AN72597: Determination of Sudan Dyes I–IV in Curry Paste. Sunnyvale, CA, 2012.
- 7. Thermo Fisher Scientific Technical Note 72488: Determination of Water- and Fat-Soluble Vitamins by HPLC. Sunnyvale, CA, 2010.

Find out more at thermofisher.com/ultimate3000

Thermo Fisher s c | e N T | F | C

©2017 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries. This information is presented as an example of the capabilities of Thermo Fisher Scientific products. It is not intended to encourage use of these products in any manners that might infringe the intellectual property rights of others. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representatives for details. **AN70755-EN 1217S**