Application Note: ANCCSCETHERBS

Separation of Eighteen Pesticides Using Accucore RP-MS HPLC Column

Derek Hillbeck, Thermo Fisher Scientific, Runcorn, Cheshire, UK

Key Words

- Accucore
- Core Enhanced
 Technology
- Pesticides
- Herbicides
- Triazines
- Phenylurea
- Environment

Abstract

This application shows the use of the Thermo Scientific Accucore RP-MS column for the separation of 18 pesticides. A 15 minute analysis time is demonstrated, with baseline resolution between all components. By operating at higher flow rates and backpressures a reduction in overall analysis time with little loss in column efficiency can be achieved.

Introduction

Environmental monitoring of chemicals used in the production of food is becoming more widespread due to the increased use of pesticides and the inevitable leaching from soil into water sources. European regulation DIN38-407 F12 covers the determination of 17 common pesticides in water, other legislation specifies different groups of pesticides. Typically methods have been carried out on long columns with extended run times in order to fully resolve the target analytes. New methods based on Accucore[™] HPLC columns for the separation of these pesticides allow more rapid analysis with improved chromatographic resolution between components.

Accucore HPLC columns use Core Enhanced TechnologyTM to facilitate fast and high efficiency separations. The 2.6 µm diameter particles are not totally porous, but rather have a solid core and a porous outer layer. The optimised phase bonding creates a series of high coverage, robust phases. Accucore RP-MS uses an optimized alkyl chain length for more effective coverage of the silica surface. This coverage results in a significant reduction in secondary interactions and thus highly efficient peaks with very low tailing. The tightly controlled 2.6 µm diameter of Accucore particles results in much lower backpressures than typically seen with sub-2 µm materials.



Experimental Details

Chemicals and Reagents

Pesticide mix 18 obtained from Neochema (Bodenheim/Manz, Germany) containing the following pesticides at 10 µg/mL in acetonitrile: atrazine, desethylatrazine, metoxuron, hexazinone, simazine, cyanazine, methabenzthiazuron, chlorotoluron, monolinuron, diuron, isoproturon, metopromuron, metazachlor, sebuthylazin, propazine, terbuthylazine, linuron, metolachlor

Part Number

06/17
626/17

Sample Handling Equipment	Part Number
NSC Mass Spec Certified 2 mL clear vial	MSCERT4000-34W
with blue bonded PTFE silicone cap	

Sample Preparation

An aliquot of the 18 pesticide mixture was diluted with an equal volume of water and then loaded into an autosampler vial.

Separation Conditions		Part Number	
Instrumentation:	Thermo Scientific Accela UHPLC system		
Column:	Accucore RP-MS 2.6 µm 150 x 2.1 mm	m, 17626-152130	
Mobile phase:	A: water	B: acetonitrile	

Experiments were conducted at seven different flow rates with gradients scaled to deliver equal column volumes per gradient section. Data from three flow rates presented.

Flow rate	400 µL/min	700 µL/min	1000 µL/min	
%B	Minutes			
20	0.00	0.00	0.00	
40	11.50	6.60	4.70	
80	15.00	8.60	6.00	
80	16.50	9.40	6.60	
20	17.25	9.90	6.90	
20	22.50	15.00	11.00	



Column temperature:	50 °C
Injection details:	2 µL partial loop
Injection wash solvent:	80:20 (v/v) water/acetonitrile
UV detector wavelength:	230 nm
Backpressure:	240 bar at 400 μL/min, 420 bar at 700 μL/min, 610 bar at 1000 μL/min

Results

The analysis was carried out on an Accucore RP-MS 2.6 μ m 150 x 2.1 mm HPLC column. As shown in Figure 1, all eighteen pesticides eluted between 2 and 15 minutes with baseline resolution when using a flow rate of 400 μ L/min. Of particular note is the separation achieved between diuron and isoproturon which have always been difficult compounds to fully resolve. Over seven replicate injections there was very little deviation in retention time for any of these molecules (Table 1) and the peak shapes are symmetrical.




Figure 1: Example chromatography – analysis of eighteen pesticide mixture at 400 $\mu L/\text{min}$

1. desethylatrazine 2. metoxuron 3. hexazinone 4. simazine 5. cyanazine

6. methabenzthiazuron 7. Chlorotoluron 8. Atrazine 9. monolinuron

10. diuron 11. isoproturon 12. metobromuron 13. metazachlor

14. sebuthylazin15. propazine 16. terbuthylazine 17. linuron 18. metolachlor

Standard	Peak	Retention time (minutes)		
	Number	mean	SD	%CV
desethylatrazine	1	2.29	0.01	0.3%
metoxuron	2	3.78	0.01	0.2%
hexazinone	3	4.21	0.01	0.1%
simazine	4	4.62	0.01	0.1%
cyanazine	5	5.02	0.01	0.1%
methabenzthiazuron	6	6.40	0.01	0.1%
chlorotoluron	7	6.80	0.01	0.1%
atrazine	8	7.35	0.01	0.1%
monolinuron	9	7.57	0.01	0.1%
diuron	10	7.94	0.01	0.1%
isoproturon	11	8.13	0.01	0.1%
metobromuron	12	8.46	0.01	0.1%
metazachlor	13	9.45	0.01	0.1%
sebuthylazin	14	10.16	0.01	0.1%
propazine	15	10.49	0.01	0.1%
terbuthylazine	16	11.30	0.01	0.1%
linuron	17	11.51	0.01	0.1%
metolachlor	18	14.19	0.00	0.0%

Table 1: Retention data of pesticide standards from seven replicate injections

The Core Enhanced Technology within Accucore columns provides opportunities to exploit the wide efficiency range of these columns. By increasing the flow rate it is possible to reduce overall analysis time with only a small deterioration in column efficiency.




Figure 2: Example chromatography – analysis of eighteen pesticide mixture at 400, 700 and 1000 $\mu L/\text{min}$

Standard	Peak	Flow rate (µL/min)		
	Number	400	700	1000
desethylatrazine	1	-	-	-
metoxuron	2	19.8	18.0	15.3
hexazinone	3	5.3	5.0	4.2
simazine	4	4.5	3.5	2.5
cyanazine	5	4.5	4.0	3.3
methabenzthiazuron	6	14.2	13.1	11.0
chlorotoluron	7	4.0	3.5	2.6
atrazine	8	5.2	4.4	3.3
monolinuron	9	1.9	1.8	1.5
diuron	10	3.3	3.4	3.0
isoproturon	11	1.9	1.6	1.2
metobromuron	12	2.8	2.4	1.8
metazachlor	13	8.4	7.6	6.2
sebuthylazin	14	5.7	4.9	3.8
propazine	15	2.8	2.5	1.9
terbuthylazine	16	6.6	6.2	5.1
linuron	17	1.6	1.6	1.3
metolachlor	18	26.2	24.5	20.0

Table 2: Peak resolution values from analysis of eighteen pesticide mixture at 400, 700 and 1000 $\mu L/min$ (taken from named peak to previous peak)

Conclusions

The use of an Accucore RP-MS column allowed the complete separation of eighteen pesticides in less than 15 minutes and at standard HPLC backpressures. If equipment compatible with higher backpressure is available, further gains can be made through reduced analysis time with little loss in column efficiency. Accucore RP-MS columns are therefore an excellent choice for the analysis of pesticides, allowing good sample throughput and analysis on both conventional and higher pressure HPLC systems.

In addition to these offices, Thermo Fisher Scientific maintains a network of representative organizations throughout the world.

North America USA and Canada +1 800 332 3331

Europe France +33 (0)1 60 92 48 34 Germany +49 (0) 2423 9431 -20

United Kingdom +44 1928 534110

Asia Japan +81 3 5826 1615

China +86-21-68654588 or +86-10-84193588 800-810-5118

India +91-22-6742 9494

Thermo Fisher Scientific Australia Pty Ltd 1300 735 292 (free call domostic)

Thermo Fisher Scientific New Zealand Ltd 0800 933 966 (free call domestic)

All Other Enquiries +44 (0) 1928 534 050

Technical Support

North America 800 332 3331 Outside North America

www.thermoscientific.com/chromatography

© 2012 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representative for details.

