



Advanced shaking solutions

for Thermo Scientific™ Cytomat™ 2 automated incubators and storage systems

The Thermo Scientific™ Cytomat™ Tower Shaker is the only solution that provides true orbital shaking. It is ideal for applications requiring sample agitation and cells that need to be kept in suspension.

Key Applications


- Cell Culture (Mammalian)
- Microbial Culture
- Genomics
- Luminex (ELISA, Biomarkers)

Markets

- Drug Discovery
- Life Science Research
- Diagnostics

The synchronized dual magnetic drive system (located at the bottom and top) ensures consistent shaking amplitude across all microplates without having any influence of load, position or number of plates.

The graph below shows optimum bacterial growth with the dual magnetic drive system across all plates (blue line; standard deviation 2.7%). In comparison, the technology with only bottom drive shaking reveals inconsistent actual growth (standard deviation 10.1%).





Unique features

- Easy 3 step setup of Tower Shaker
install/secure by lock screw to the ceiling/plug-in for communication
- Active microplate clamp mechanism secures plate and lid separately;
no abrasions of the microplates during shaking
- Mix and match standard and Tower Shaker stacker for maximum
flexibility for assay adoption
- Inductive wear-free driving mechanism allows for no particle
emission or belts to change
- Superior shaking technology with individual speed settings of each
Tower Shaker from 100-1200 rpm with oscillating amplitude of
2 mm (3 mm option available) offers a wide range of application
setups

Cytomat Order Numbers

Product	Part No.
Cytomat 2C450-LIN ToS, 230V	50122537
Cytomat 2C450-LIN ToS, 120V	50124892
Cytomat 2C470-LIN ToS, 230V	upon request
Cytomat 2C470-LIN ToS, 120V	50126933
Cytomat 2 Hotel, ToS, 100-230V	50111434

Shaking Options

(100-1200 rpm, orbital shaking with a max. load of 850 g per position)

Product	Part No.
Tower Shaker P23 16 microplate capacity, 1 mm amplitude (2 mm oscillation amplitude)	50107700
Tower Shaker P27 13 microplate capacity, 1 mm amplitude (2 mm oscillation amplitude)	50122160
Tower Shaker P50 7 microplate capacity, 1 mm amplitude (2 mm oscillation amplitude)	50118421
Tower Shaker P23, 3 mm Customized, 16 microplate capacity, 1.5 mm amplitude (3 mm oscillation amplitude)	50129388
Tower Shaker P27, 3 mm Customized, 13 microplate capacity, 1.5 mm amplitude (3 mm oscillation amplitude)	50138322
Tower Shaker P33 Customized, 11 microplate capacity, 1 mm amplitude (2 mm oscillation amplitude)	50127680
Tower Shaker P40 Customized, 9 microplate capacity, 1 mm amplitude (2 mm oscillation amplitude)	50133660
Tower Shaker P60 Customized, 6 microplate capacity, 1 mm amplitude (2 mm oscillation amplitude)	50126934

Options for Cytomat Shaker 2 C450/C470-LIN ToS

Product	Part No.	
O ₂ Control	O ₂ control to minimize oxygen level with N ₂ supply, 1-21 Vol%	50137130
GT	Gate top (seen from robot side)	50144992
DL	Door left hinged	50137140
CU	Inner chamber made of copper	50137139
UB	Under Bench version Ask your sales representative for further details	upon request

Accessories for Cytomat Shaker ToS

(Please specify 2 pieces of the stacker options)

Product	Part No.	
BCR C2	1D-Barcode reader on handler of PSS	50123106
Transfer Station	Transfer station for C2, with sensor for plate detection	50070711
90° Transfer Station	90° CW (Clockwise) - turnable transfer station for C2, with sensor for plate detection	50074585
90° Transfer Station	90° CCW (Counter Clockwise) - turnable transfer station for C2, with sensor for plate detection	50125928
Swap Station	180° turnable transfer station with two positions for C2, with two sensors for plate detection	50072392
Plate Lift	Plate Lift for Under Bench version Ask your sales representative for further details	upon request
Linear Station 300	300 mm linear moving transfer station, with sensor for plate detection	50075523
Linear Station 400	400 mm linear moving transfer station, with sensor for plate detection	50079463
Linear Station 500	500 mm linear moving transfer station, with sensor for plate detection	50079742

thermoscientific.com/CytomatSeries

© 2015 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries.

North America Sales +1 203 449 2355
 North America Office +1 905 332 2000
 Europe, Middle East, Africa +49 6184 90 6476
 China +86 800 810 5118
 Japan 0120 753 670
 Australia +61 8 8208 8200

FLYER-LA-ToS-01/05

Thermo
SCIENTIFIC

A Thermo Fisher Scientific Brand