


Vials and well plates portfolio



SureSTART LC vials and well plates

Recommended for Vanquish HPLC and UHPLC systems


There's a SureSTART vial, cap, well plate, and mat for every Vanquish application and budget

Options include:

- Innovative Thermo Scientific™ SureStop™ technology vials and Thermo Scientific™ AVCS™ technology caps that provide the tightest seal available from screw thread caps and vials, to ensure you get the best results from your samples
- A variety of volume sizes: for standard and low volume
- Clear and amber (for light sensitive analytes)



Click to learn more about product quality and performance:

 [Thermo Scientific™ SureSTART™ products—Assured quality and performance](#)

- Thermo Scientific SureSTART, SureStop, and AVCS technology

Need to make your consumables budget go further?

Discover the flexible options available to you within the Thermo Scientific SureSTART collection.


- Thermo Scientific SureSTART products—the power to extend your consumables budget

Thermo Scientific™ Vanquish™ Core HPLC systems,
Thermo Scientific™ Vanquish™ Flex UHPLC systems,
Thermo Scientific™ Vanquish™ Horizon UHPLC systems, and
Thermo Scientific™ Vanquish™ Duo systems for dual LC



Product type	Product description	100/Pack	10 × 100/Pack
Kit	Certified kit	6PCK578W	—
	2 mL clear screw glass vial (9 mm short thread) with SureStop technology and write-on patch	6PSV9-1PSS	—
	Blue screw cap (9 mm) (PP: white silicone/red PTFE septa: 1 mm thickness) with AVCS technology	6ASC9ST1	—
Vials	2 mL clear screw glass vial (9 mm short thread) with SureStop technology and write-on patch	6PSV9-1PSS	6PSV9-1PSST
	2 mL amber screw glass vial (9 mm short thread), with SureStop technology and write-on patch	6PSV9-2PSS	6PSV9-2PSST
	0.3 mL clear screw glass vial with fixed insert (9 mm short thread), with write-on patch	6PSV9-03FIVP	6PSV9-03FIVPT
	0.3 mL amber screw glass vial with fixed insert (9 mm short thread), with write-on patch	6PSV9-03FIVAP	6PSV9-03FIVAPT
Caps	Red screw cap (9 mm) (PP: white silicone/red PTFE septa: 1.0 mm thickness) with AVCS technology	6ASC9ST1R	6ASC9ST1RT
	Blue screw cap (9 mm) (PP: blue silicone/clear PTFE soft septa: 1.0 mm thickness) with AVCS technology	6PSC9ST101	—

Product type	Product description	Cat. no.
96-well plate and mat	Thermo Scientific™ WebSeal™ 96-well non-coated, V-bottom plastic microplate (100 µL), barcoded. 50/Pack	60180-P210B
	WebSeal 96-well, V-shape round well microplate: (220 µL), barcoded. 100/Pack	60180-P207B
	WebSeal nonsterile mats , silicone, well shape: round, flat base (For use with the P/N 60180-P210B well plate). 50/Pack	60180-M210
	WebSeal nonsterile mats , clear silicone, well shape: round, flat base with step and preslit. (For use with the P/N 60180-P207B well plate). 5/Pack	60180-M113



Thermo Scientific™ Vanquish™ Neo UHPLC system



Product type	Product description	100/Pack	10 x 100/Pack
Kit	Convenience kit	6PK1655	—
	0.2 mL amber screw TPX vial (9 mm short thread) with fixed conical-shaped glass insert	60180-1655	—
	Bonded black screw cap (9 mm) (PP: white silicone/red PTFE septa: 1 mm thickness)	6PSC9STB1	—
Vials	0.2 mL amber screw TPX vial (9 mm short thread) with fixed conical-shaped glass insert	60180-1655	—
	1.5 mL clear screw glass vial (9 mm short thread), total recovery	6PSV9-TR1	6PRV11-TR1T
	1.7 mL clear screw glass vial (9 mm short thread), inner v-bottom high recovery	6PSV9-V1	6PSV9-V1T
	0.4 mL clear screw polypropylene vial (9 mm short thread), with fixed conical-shaped insert	6ESV9-04PP	6ESV9-04PPCT
	1.7 mL clear snap glass vial, silanized (11 mm wide opening), inner v-bottom, high recovery	6PRV11-S1V	—
	0.8 mL clear polypropylene snap vial (11 mm wide opening), with fixed conical-shaped insert	6ERV11-08PPC	6ERV11-08PPCT
Inserts and holders	0.2 mL clear gold grade glass conical insert	—	6PME02CG
	2 mL clear screw glass insert holder (9 mm short thread), with write-on patch	CHSV9-10P	CHSV9-10PT
Caps	Bonded black screw cap (9 mm) (PP: white silicone/red PTFE septa: 1.0 mm thickness)	6PSC9STB1	6PSC9STB1T
	Blue snap cap (11 mm) (PE: white silicone/red polyimide septa: 1.0 mm thickness)	6ARC11SPI1	—

Product type	Product description	Size	Cat. no.
96-well plates	Thermo Scientific™ WebSeal™ 96-well microtiter plate , 5.6 mm round diameter, total V-bottom, Level 2 (100 µL), polypropylene, barcoded	50/Pack	60180-P210B
	Thermo Scientific™ WebSeal™ 96-well mid-height plate , 7 mm round diameter, U-bottom, Level 2 (1.0 mL), polypropylene, barcoded	50/Pack	60180-P201B
	Thermo Scientific™ WebSeal™ Plate+ 96-well mid-height plate , 7 mm round diameter, U-bottom, Level 3 (1.0 mL), glass coated polypropylene, barcoded	10/Pack	60180-P343B
	Thermo Scientific™ WebSeal™ Plate+ 96-well microtiter plate , 7 mm round diameter, V-bottom, Level 3 (350 µL), glass coated polypropylene, barcoded	10/Pack	60180-P332B
96 mats and tape	Thermo Scientific™ WebSeal™ mat , 96 round well, 5.6 mm diameter, clear silicone, flat base, cross, for 60180-P210B	50/Pack	60180-M210
	Thermo Scientific™ WebSeal™ mat , 96 round well, 7 mm diameter, clear silicone, flat base, thinned penetration line	50/Pack	60180-M187
	Thermo Scientific™ WebSeal™ sealing tape , with 3 layer no adhesive at cavity area	25/Pack 100/Pack	60180-M176 60180-M146
384-well plate and mat	Thermo Scientific™ WebSeal™ plate+ 384-well microtiter plate , V-bottom, Level 3 (125 µL), glass coated polypropylene, barcoded	10/Pack	60180-P340B
	Thermo Scientific™ WebSeal™ 384-well sealing mat , square, flat base, pre-slit, Level 1	5/Pack	60180-M150

Learn more at thermofisher.com/surestart

thermo scientific