

# Thermo Scientific Vanquish – Diode Array Detector HL

Better separations, more results, easier interaction

Thermo Scientific™ Vanquish™ UHPLC system is designed to offer:

- **Better separations** with the power of the system to unveil more compounds than ever before
- **More results** with throughput, speed and sample capacity to boost workflow productivity
- **Easier interaction** to make the system a joy to work with

The Vanquish UHPLC system is designed as an integrated UHPLC system, where the detector measures the analytes with more sensitivity.

Vanquish Diode Array Detector



## Taking Detection to a New Level

The LightPipe™ technology of the Vanquish Diode Array Detector (DAD) provides you with an unmatched detection experience. This DAD achieves the best signal-to-noise performance through the combination of lowest baseline noise, a very long light path, and minimum peak dispersion. The ultra-wide dynamic range of the detector is ideal for simultaneous detection of highly concentrated main compounds and impurities down to trace levels. Interfering refractive index and thermal effects are reduced to a minimum for less baseline drift and therefore more reliable peak integration. A thoughtful design and a wide range of usability features optimize the interaction with the detector for maximum effectiveness and ease-of-use.

- Acquire data at up to 200 Hz using up to 10 absorption channels and one 3D field for best support of ultrafast separations
- Benefit from outstanding sensitivity with low-dispersion 10 mm and 60 mm flow cells and a wide linearity range to comply with most demanding applications
- Optimize sensitivity, linearity, and spectral resolution of your application with four programmable optical slit widths from 1 nm to 8 nm
- Lowest baseline drift gives you best quantitation reproducibility – achieved through optimized fused-silica LightPipe flow cells and an effective thermal control
- Enjoy intuitive user interaction, convenient flow cell and lamp usage tracking, and the integrated wavelength validation through holmium oxide filter

**Thermo**  
SCIENTIFIC

## PRODUCT SPECIFICATIONS

Specification	Value
Optical Design	Single-beam, reverse-optics design with concave holographic grating. High Numerical Aperture (NA) achromatic optics. 1024 element photodiode array.
Maximum Data Collection Rate	200 Hz (including 3D acquisition) (under Thermo Scientific™ Dionex™ Chromeleon™ Chromatography Data System 7.2 SR1 control or higher)
Wavelength Range	190–680 nm
Noise	<±3 µAU at 230 nm (standard flow cell, bandwidth: 4 nm, slit width: 4 nm; time constant: 2 s)
Drift	<0.5 mAU/hour at 230 nm
Linearity	<5% at 2.0 AU (typically <5% at 2.5 AU)
Slit Width	Settable: 1 nm, 2 nm, 4 nm, 8 nm
Spectral Bandwidth	Pixel resolution: 0.5 nm (average); Optical resolution: 1 nm (FWHM with 1 nm slit width)
Light Source	Deuterium lamp
Number of Signal Channels	10 + 3D field
Flow Cell Volumes	Standard flow cell: 2 µL (illuminated), 0.8 µL (dispersion) High sensitivity flow cell: 13 µL (illuminated), 4.0 µL (dispersion)
Flow Cell Pressure Limit	6 MPa (60 bar, 870 psi)
Wavelength Accuracy	±1 nm
Wavelength Repeatability	±0.1 nm
Wavelength Calibration	Internal calibration with D-alpha line of the deuterium lamp
Wavelength Validation	Internal validation with holmium oxide filter
Biocompatible	Yes, pH range 2–12, buffer and/or chloride concentration up to 1 mol/L
PC Connection	USB 2.0; 3-port-HUB to connect further Vanquish modules
Safety Features	Power-up diagnostics of optics, cooling fans, motors and electronics. Leak detection and safe leak handling.
GLP	Predictive Performance functions: lamp age and ignitions, lamp intensity degradation, leak detection, service monitoring period. All system parameters logged in the Chromeleon Chromatography Data System Audit Trail.
Environmental Conditions	5–35 °C; 20–80% RH (non condensing)
Power Requirements	100–240 V AC, 50/60 Hz, max. 150 W/255 VA
Dimensions (h × w × d)	160 mm × 420 mm × 620 mm (6.3 × 16.5 × 24.4 in.)
Weight	17 kg (37.5 lbs)

## ORDERING INFORMATION

Description	Part Number
Vanquish Diode Array Detector HL	VH-D10-A
Accessories	
LightPipe flow cell, 10 mm, standard	6083.0100
LightPipe flow cell, 60 mm, high sensitivity	6083.0200
LightPipe diagnostic cell	6083.0300
Deuterium lamp for Vanquish DAD HL	6083.1110

To order in the U.S., call 1-800-346-6390, or contact the Thermo Fisher Scientific office nearest you. Outside the U.S., order through your local Thermo Fisher Scientific office or distributor. Refer to the following part numbers.

[www.thermofisher.com/chromatography](http://www.thermofisher.com/chromatography)

©2016 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries. This information is presented as an example of the capabilities of Thermo Fisher Scientific products. It is not intended to encourage use of these products in any manners that might infringe the intellectual property rights of others. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representative for details.

<b>Africa</b> +43 1 333 50 34 0	<b>Denmark</b> +45 70 23 62 60	<b>Japan</b> +81 6 6885 1213	<b>Russia/CIS</b> +43 1 333 50 34 0
<b>Australia</b> +61 3 9757 4300	<b>Europe-Other</b> +43 1 333 50 34 0	<b>Korea</b> +82 2 3420 8600	<b>Singapore</b> +65 6289 1190
<b>Austria</b> +43 810 282 206	<b>Finland</b> +358 9 3291 0200	<b>Latin America</b> +1 561 688 8700	<b>Sweden</b> +46 8 556 468 00
<b>Belgium</b> +32 53 73 42 41	<b>France</b> +33 1 60 92 48 00	<b>Middle East</b> +43 1 333 50 34 0	<b>Switzerland</b> +41 61 716 77 00
<b>Brazil</b> +55 11 3731 5140	<b>Germany</b> +49 6103 408 1014	<b>Netherlands</b> +31 76 579 55 55	<b>Taiwan</b> +886 2 8751 6655
<b>Canada</b> +1 800 530 8447	<b>India</b> +91 22 6742 9494	<b>New Zealand</b> +64 9 980 6700	<b>UK/Ireland</b> +44 1442 233555
<b>China</b> 800 810 5118 (free call domestic) 400 650 5118	<b>Italy</b> +39 02 950 591	<b>Norway</b> +46 8 556 468 00	<b>USA</b> +1 800 532 4752

**Thermo**  
SCIENTIFIC

A Thermo Fisher Scientific Brand