


More capabilities. New possibilities.

Trade in Any Brand HPLC for a New Thermo Scientific™ UltiMate™ or Vanquish™ System



The versatile and modular range of Thermo Scientific UHPLC systems are designed to make UHPLC accessible to all users, all laboratories, and for all analytes.

- Thermo Scientific™ Dionex™ Viper™ fitting— a fingertight fitting system that provides the best possible chromatographic performance by design
- Thermo Scientific™ Dionex™ Chromeleon™ 7.2 Chromatography Data System software – our next generation chromatography data system that offers a unique combination of intelligent functionality and operational simplicity
- Wide range of detectors, including the unique Thermo Scientific™ Dionex™ Corona™ Veo™ Charged Aerosol Detector

For a limited time we are offering owners of any brand HPLC to join the Thermo Scientific UHPLC community. Our attractive trade-in program provides a generous discount making it easy to exchange your existing system by any Thermo Scientific UHPLC instrument of your choice.

Interested to find out more about this offer?

**Reach out to your local Thermo Scientific Representative,
call us at +46 8 556 468 00 or +45 70 23 62 60,
or send an email to analyze.se@thermofisher.com.**

Thermo
SCIENTIFIC

More capabilities. New possibilities.

Trade in Any Brand HPLC for a New Thermo Scientific UHPLC System

UHPLC Trade-In System Options

System Type	Pumps	Samplers	Column Compartments	Detectors
UltiMate 3000 Entry Level System (UV-Vis max pressure 620 bar, max flow 10 mL/min)	<ul style="list-style-type: none"> Isocratic pump Quaternary pump 	Autosampler with integrated column compartment		<ul style="list-style-type: none"> UV-Vis Diode Array Fluorescence Refractive Index Electrochemical
UltiMate 3000 Standard System (max pressure 620 bar, max flow 10 mL/min)	<ul style="list-style-type: none"> Quaternary pump Binary pump Dual gradient pump 	Well plate sampler with optional tray cooling	Column compartment for up to 6 × 25 cm columns with optional 2 switching valves	<ul style="list-style-type: none"> UV-Vis Diode Array Fluorescence Refractive Index Electrochemical Charged Aerosol (CAD)
UltiMate 3000 RSLC System (max pressure 1000 bar, max flow 8 mL/min)				
UltiMate 3000 RSLCnano System (max pressure 800 bar, flows from 20 nL/min to 50 µL/min)	<ul style="list-style-type: none"> Binary pump (analytical) Ternary pump (loading) 	Well plate sampler with optional tray cooling and advanced fractionation options	Integrated column compartment and up to 2 switching valves	<ul style="list-style-type: none"> UV-Vis with 3 nL flow cell
Vanquish System (max pressure 1500 bar, max flow 5 mL/min) Fully biocompatible	<ul style="list-style-type: none"> Binary pump 	Well plate sampler, 4-40 °C. Charger module for up to 23 well plates	Integrated column compartments, 5-120 °C. Forced and still air thermostating	<ul style="list-style-type: none"> Diode Array with LightPipe technology Fluorescence Charged Aerosol (CAD)
Vanquish Flex System (max pressure 1000 bar, max flow 8 mL/min) Fully biocompatible	<ul style="list-style-type: none"> Quaternary pump 	Well plate sampler, 4-40 °C. Charger module for up to 23 well plates	Integrated column compartments, 5-120 °C. Forced and still air thermostating	<ul style="list-style-type: none"> Diode Array with LightPipe technology Fluorescence Charged Aerosol (CAD)

**This promotional offer ends December 31, 2015. Local restrictions may apply.
Model name, serial number and date of retire need to be provided.**

Thermo Fisher Scientific offers a range of **financing and leasing options for UHPLC instruments**, so you can choose the solution matching your financial and analytical requirements best. Please contact us to discuss these financing and leasing options in more details.

**Interested to find out more about this offer?
Reach out to your local Thermo Scientific Representative,
call us at +46 8 556 468 00 or +45 70 23 62 60,
or send an email to analyze.se@thermofisher.com.**

©2015 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representative for details.

Thermo
SCIENTIFIC

A Thermo Fisher Scientific Brand