# A New GC–ICP–MS Method for Compound Specific Determination of Brominated Flame Retardants

Antonella Guzzonatoa\*, Hans-Juergen Schlueter<sup>b</sup>, Heinz Mehlmann<sup>b</sup>, Dirk Krumweide<sup>b</sup>, Shona McSheehy Ducos<sup>b</sup>, Stuart Harrad<sup>a</sup> <sup>a</sup>School of Geography, Earth & Environmental Sciences, University of Birmingham, Birmingham, B15 2TT, UK; <sup>b</sup>Thermo Fisher Scientific, Hanna-Kunath Str. 11, 28199, Bremen, Germany

## **Overview**

**Purpose:** Develop a simultaneous, accurate and precise method for compound specific brominated flame retardant (BFR) quantification for PBDE congeners 28 to 209 without debromination.

**Methods:** A Thermo Scientific<sup>™</sup> Trace<sup>™</sup> 1310 Gas Chromatograph (GC) was interfaced with a Thermo Scientific <sup>™</sup> iCAP<sup>™</sup> Q ICP-MS to analyze PBDE technical mixes and WEEE material.

**Results:** BFR technical mixes and polymeric solid reference material extracts were successfully characterized and their detailed relative compositions compared to those reported in the literature.

## Introduction

Polybrominated diphenyl ethers (PDBEs) are brominated flame retardants (BFRs), which are commonly found in electrical and electronic equipment (EEE) and household textiles for flame retardancy purposes. Due to the ubiquitous use and poor recycling practices, these substances are now found in consumer goods that do not require flame retardancy, such as kitchen utensils, children's toys and food contact materials.

The three most important commercial BFR mixtures, c-pentaBDE, c-octaBDE and c-decaBDE, cover the vast majority of the market: the c-decaBDE mixture was the most produced accounting for 83.3% of the global market demand. In plastic materials commonly associated with EEE and recycled materials, these BFRs are not covalently bonded to the polymer chains. As a result, they may leach into the environment and due to their toxicity and tendency to bio-accumulate, pose a significant risk to the natural environment and human health. Furthermore, the toxicity of the BFR varies based on the number of Br atoms. Therefore, it is important to differentiate between BFRs with different levels of bromination. Consequently, the RoHS Directive 2011/65/EU, effective since 2013, dictates that PBBs and PBDEs (classes covering the most largely used additive BFRs, including deca-BDE) concentrations should be a maximum of 0.1 weight % in homogeneous material.

Simultaneously measuring the concentration of flame retardants containing different numbers of Br atoms rapidly and at high sensitivity and precision has hitherto been problematic. This is because higher brominated compounds (nona- and deca-BDE) are more labile and tend to debrominate into less brominated congeners (usually by losing two Br atoms at a time). To accommodate this, two GC columns are often used to cover the entire spectrum of possible PBDEs, a longer one (15 to 30 m) to achieve separation between the many lower brominated BDEs and a shorter one (6 m) to detect higher brominated compounds without decomposing them [Stapleton, 2006.]. This is time consuming and complex. Therefore a method based on ICP-MS detection was developed with a goal to accurately and rapidly quantify BFRs in plastic materials and subsequently consumer products.

# **Methods**


#### Samples and sample preparation

Technical mixes, penta-BDE (Bromkal 70-5DE; penta DE-71), octa-BDE (Bromkal 79-8DE) and deca-BDE (Saytex 102E) (Cambridge Isotope Laboratories), were used to determine if the method presented here maintained the relative ratio of compounds across the chromatogram (Fig. 1a and 1b). A solid standard (ERM EC591, Institute for Reference Materials and Measurements) of polypropylene matrix was used to account for the matrix effect of real sample material (i.e. polymeric matrix in the inlet system), which was cold-solvent quiescently extracted and analyzed.



#### GC-ICP-MS

A Thermo Scientific Trace 1310 GC was interfaced to a Thermo Scientific iCAP Q ICP–MS. Sample introduction was via a Thermo Scientific™ TriPlus™ autosampler. Simultaneous analysis of PBDEs from congener 28 to congener 209 was undertaken during the same chromatographic run.



## Results

#### Calibration

Calibration curves (Fig. 2a and 2b) for each congener of the standard mix were developed by diluting the standard with nonane to create six calibration levels (2.5 ng/mL to 100 ng/mL). The correlation coefficient for each congener was  $R^{2}$ >0.99. A calibration curve was obtained using the ERM EC591 Solid Reference Material extracts in order to evaluate the matrix effect on the linearity of the data: the linearity was optimal for each measured congener ( $R^{2}$ >0.99; Fig. 2b).





FIGURE 2a. Calibration curve for PBDEs standard mixture

FIGURE 2b. Calibration curve for PBDEs in a ERM EC591 solid reference material extract



GC Column	DB5MS capillary column 0.25 mm I, 0.1 µm film
	thickness, 15m length (J&W Scientific, Aglient)
Injection mode and liner	PTV Splitless with Silicosteel
Injection temperature	100°C
Injection volume	1µl
Carrier flow (He)	3 to 4.5 ml/min
Make up gas flow (Ar)	950 ml/min
Interface temperature	270°C
Initial temperature	100°C
Initial time	2 min
Ramp rate	15°C min <sup>-1</sup> ; 8°C min <sup>-1</sup> ; 25°C min <sup>-1</sup>
Final temperature	280°C
Final time	4 min
Forward power	1400 W
Isotopes and dwell times	<sup>79</sup> Br is 100 ms; <sup>81</sup> Br is 80 ms
Transient acc. time	1200 secs

# improved chromatographic method that eliminates debromination

## Conclusion

- The calculated LOD for this technique is 1.8 pg of analyte on-column (comparable to GC/LR-ECNI-MS [Eljarrat et al, 2002]). At least a ten-fold improvement is to be expected when coupling the GC to a sector field ICP-MS instrument. However, congeners peaks were measurable down to a 0.65 pg of on-column analyte. (Fig 3)
- By virtually eliminating the decomposition of higher brominated compounds into the lower brominated ones, quantification of the complete range of congeners was possible.
- Thanks to the programmed flow, chromatographic run times are reduced and by employing just one GC column, the number of analysis per sample is halved (Table 1).

## References

Eljarrat et al, 2002 . J Mass Spectrom 37: 76-84

Stapleton, 2006. Anal Bioanal Chem 386: 807-817

## Acknowledgements

The research leading to these results has received funding from the People Programme (Marie Curie Actions) of the European Union's Seventh Framework Programme FP7/2007-2013/ under grant agreement n° 606857







#### www.thermofisher.com

©2016 Thermo Fisher Scientific Inc. All rights reserved. ERM European Reference Materials is a trademark of the European commission. The University of Birmingham is a trademark of the University of Birmingham. All other trademarks are the property of Thermo Fisher Scientific and its subsidiaries. This information is presented as an example of the capabilities of Thermo Fisher Scientific products. It is not intended to encourage use of these products in any manners that might infringe the intellectual property rights of others. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representative for details. First presented at the Winter Conference on Plasma Spectrochemistry, Tucson, AZ. January 2016

 
 Africa
 +43 1 333 50 34 0

 Australia
 +61 3 9757 4300

 Austria
 +43 810 282 206

 Belgium
 +32 53 73 42 41

 Canada
 +1 800 530 8447

 China
 800 810 5118 (free call domestic) 400 650 5118

 PN43313-EN 0216S
 Denmark +45 70 23 62 60 Europe-Other +43 1 333 50 34 0 Finland +358 10 3292 200 France +33 1 60 92 48 00 Germany +49 6103 408 1014 India +91 22 6742 9494 Italy +39 02 950 591 Japan +81 45 453 9100 Korea +82 2 3420 8600 Latin America +1 561 688 8700 Middle East +43 1 333 50 34 0 Netherlands +31 76 579 55 55 New Zealand +64 9 980 6700 Norway +46 8 556 468 00 Russia/CIS +43 1 333 50 34 0 Singapore +65 6289 1190 Spain +34 914 845 965 Sweden +46 8 556 468 00 Switzerland +41 61 716 77 00 UK +44 1442 233555 USA +1 800 532 4752

