

Accreditation



The Deutsche Akkreditierungsstelle attests with this **Accreditation Certificate** that the testing laboratory

Oxoid Deutschland GmbH
Am Lippeglacis 4-8, 46483 Wesel

meets the requirements according to DIN EN ISO/IEC 17025:2018 for the conformity assessment activities listed in the annex to this certificate. This includes additional existing legal and normative requirements for the testing laboratory, including those in relevant sectoral schemes, provided they are explicitly confirmed in the annex to this certificate.

The management system requirements of DIN EN ISO/IEC 17025 are written in the language relevant to the operations of testing laboratories and they conform to the principles of DIN EN ISO 9001.

This accreditation was issued in accordance with Art. 5 Para. 1 Sentence 2 of Regulation (EC) 765/2008, after an accreditation procedure was carried out in compliance with the minimum requirements of DIN EN ISO/IEC 17011 and on the basis of a review and decision of the appointed accreditation committees.

This accreditation certificate only applies in connection with the notices of 14.11.2024 with accreditation number D-PL-20190-01.

It consists of this cover sheet, the reverse side of the cover sheet and the following annex with a total of 3 pages.

Registration number of the accreditation certificate: **D-PL-20190-01-00**

Berlin, 14.11.2024

Barbara Tyralla
Head of Technical Unit

Translation issued:
13.05.2025



Barbara Tyralla
Head of Technical Unit

The certificate together with the annex reflects the status as indicated by the date of issue. The current status of any given scope of accreditation can be found in the directory of accredited bodies maintained by Deutsche Akkreditierungsstelle GmbH (www.dakks.de).

This document is a translation. The definitive version is the original German accreditation certificate.

See notes overleaf

Deutsche Akkreditierungsstelle GmbH

Office Berlin
Spittelmarkt 10
10117 Berlin

Office Frankfurt am Main
Europa-Allee 52
60327 Frankfurt am Main

Office Braunschweig
Bundesallee 100
38116 Braunschweig

The Deutsche Akkreditierungsstelle GmbH (DAkKS) is the entrusted national accreditation body of the Federal Republic of Germany according to § 8 section 1 AkkStelleG in conjunction with § 1 section 1 AkkStelleGBV. DAkKS is designated as the national accreditation authority by Germany according to Art. 4 Para. 4 of Regulation (EC) 765/2008 and clause 4.7 of DIN EN ISO/IEC 17000.

Pursuant to Art. 11 section 2 of Regulation (EC) 765/2008, the accreditation certificate shall be recognised as equivalent by the national authorities within the scope of this Regulation as well as by the WTO member states that have committed themselves in bilateral or multilateral mutual agreements to recognise the certificates of accreditation bodies that are members of ILAC or IAF as equivalent.

DAkKS is a signatory to the multilateral agreements for mutual recognition of the European co-operation for Accreditation (EA), International Accreditation Forum (IAF) and International Laboratory Accreditation Co-operation (ILAC).

The up-to-date state of membership can be retrieved from the following websites:

EA: www.european-accreditation.org

ILAC: www.ilac.org

IAF: www.iaf.nu

Deutsche Akkreditierungsstelle

Annex to the accreditation certificate D-PL-20190-01-00 according to DIN EN ISO/IEC 17025:2018

Valid from: 14.11.2024

Date of issue: 14.11.2024

Holder of accreditation certificate:

**Oxoid Deutschland GmbH
Am Lippeglacis 4-8, 46483 Wesel**

with the location

**Oxoid Deutschland GmbH
Am Lippeglacis 4-8, 46483 Wesel**

The testing laboratory meets the requirements of DIN EN ISO/IEC 17025:2018 to carry out the conformity assessment activities listed in this annex. The testing laboratory meets additional legal and normative requirements, if applicable, including those in relevant sectoral schemes, provided that these are explicitly confirmed below.

The management system requirements of DIN EN ISO/IEC 17025 are written in the language relevant to the operations of testing laboratories and they conform to the principles of DIN EN ISO 9001.

Microbiological analysis of culture media in the area of food, feed, water and healthcare

Flexible Scope of Accreditation:

The testing laboratory is permitted to use standardised or equivalent test methods listed here with different issue dates without being required to prior inform and obtain approval from DAkkS (flexibilization according to category A).

The testing laboratory has an up-to-date list of all test methods within the flexible scope of accreditation. The list is publicly available on the website of the testing laboratory.

This certificate annex is only valid together with the written accreditation certificate and reflects the status as indicated by the date of issue. The current status of any given scope of accreditation can be found in the directory of accredited bodies maintained by Deutsche Akkreditierungsstelle GmbH at <https://www.dakks.de>.

Annex to the accreditation certificate D-PL-20190-01-00

1 Culture media in the area of food, feed, water and healthcare

1.1 Microbiological analysis

DIN EN ISO 11133 Microbiology of food, animal feed and water – Preparation, production,
2020-10 storage and performance testing of culture media
 (Here also culture media in the area of healthcare)

MA-003 Testing of culture media for microbial purity
2021-03

MA-004 Quantitative methods for performance testing of solid culture media
2021-03

MA-005 Qualitative methods for performance testing of solid culture media
2021-03

MA-006 Quantitative testing of solid culture media using membrane filtration
2021-03

MA-007 Methods for performance testing of liquid culture media
2021-03

MA-008 Methods for performance testing of diluents
2021-03

MA-009 Determination of the specificity of culture media
2021-03

1.2 Visual, physical, physico-chemical and chemical analysis

MA-001 Visual inspection of culture media
2021-03

MA-002 pH measurement of culture media
2021-03

MA-010 Fill weight and fill format control
2021-03

Valid from: 14.11.2024

Date of issue: 14.11.2024

Page 2 of 3

This document is a translation. The definitive version is the original German annex to the accreditation certificate.

Annex to the accreditation certificate D-PL-20190-01-00

Abbreviations used:

DIN	Deutsches Institut für Normung e.V. (German Institute for Standardization)
EN	European standard
IEC	International Electrotechnical Commission
ISO	International Organization for Standardization
MA-xxx	In-house method of the Oxid Deutschland GmbH testing laboratory

Valid from: 14.11.2024

Date of issue: 14.11.2024

Page 3 of 3

This document is a translation. The definitive version is the original German annex to the accreditation certificate.

Dok.: AO 5.3-01 Rev. 03 Stand: 14.11.2024 		Leistungsangebot (D-PL-20190-01-00)	Flexible Akkreditierung: Dem Prüflaboratorium ist, ohne das es einer vorherigen Information und Zustimmung der DAkkS bedarf, die Anwendung der hier aufgeführten genormten oder ihnen gleichzusetzenden Prüfverfahren mit unterschiedlichen Ausgabeständen gestattet. Das Prüflaboratorium verfügt über eine aktuelle Liste aller Prüfverfahren im flexiblen Akkreditierungsbereich.						
Prüfnorm gemäß Akkreditierung:	Ausgabest and (JJJJ-MM)	Titel des Prüfverfahrens:	flex. Akkreditiert der Kat.: A / B / C	zugehörige Methoden-anweisung:	Verifizierung / Validierung durchgeführt am:	Verifizierung / Validierung durchgeführt durch:	Gültigkeit der neuen Mothodenanweisung ab:	Aufnahme ins Leistungsverzeichnis mit Veröffentlichung	Anpassung der aktuellen Prüfnorm im LIMS am:
Nährmedien im Bereich Lebensmittel, Futtermittel, Wasser und Gesundheitsversorgung									
1 Mikrobiologische Untersuchungen									
DIN EN ISO 11133	2020-10	Mikrobiologie von Lebensmitteln, Futtermitteln und Wasser - Vorbereitung, Herstellung, Lagerung und Leistungsprüfung von Nährmedien <i>(hier auch Nährmedien im Bereich Gesundheitsversorgung)</i>	A	MA 1 bis 10	2/25/2021	Thurau	2/25/2021	2/25/2021	2/25/2021
MA-003	2021-03	Prüfung von Nährmedien auf mikrobielle Reinhei	A	MA 3	2/25/2021	Thurau	2/25/2021	2/25/2021	2/25/2021
MA-004	2021-03	Quantitative Verfahren zur Leistungsprüfung von festen Nährmedie	A	MA 4	2/25/2021	Thurau	2/25/2021	2/25/2021	2/25/2021
MA-005	2021-03	Qualitative Verfahren zur Leistungsprüfung von festen Nährmedien	A	MA 5	2/25/2021	Thurau	2/25/2021	2/25/2021	2/25/2021
MA-006	2021-03	Quantitative Prüfung von festen Nährmedien mittels Membranfiltration	A	MA 6	2/25/2021	Thurau	2/25/2021	2/25/2021	2/25/2021
MA-007	2021-03	Verfahren zur Leistungsprüfung von flüssigen Nährmedien	A	MA 7	2/25/2021	Thurau	2/25/2021	2/25/2021	2/25/2021
MA-008	2021-03	Verfahren zur Leistungsprüfung von Verdünnungsmitteln	A	MA 8	2/25/2021	Thurau	2/25/2021	2/25/2021	2/25/2021
MA-009	2021-03	Bestimmung der Spezifität von Nährmedien	A	MA 9	2/25/2021	Thurau	2/25/2021	2/25/2021	2/25/2021
2 Visuelle, physikalische, physikalisch-chemische und chemisch Untersuchungen									
MA-001	2021-03	Visuelle Prüfung von Nährmedien	A	MA 1	2/25/2021	Thurau	2/25/2021	2/25/2021	2/25/2021
MA-002	2021-03	pH-Messung von Nährmedien	A	MA 2	2/25/2021	Thurau	2/25/2021	2/25/2021	2/25/2021
MA-010	2021-03	Füllgewichts- und Füllformatkontrolle	A	MA 10	2/25/2021	Thurau	2/25/2021	2/25/2021	2/25/2021
verwendete Abkürzungen: DIN Deutsches Institut für Normung e.V. EN Europäische Norm IEC International Electrotechnical Commission – Internationale Elektrotechnische Kommission ISO International Organization for Standardization – Internationale Organisation für Normung MA-xxx Hausverfahren des Prüflaboratoriums der Oxoid Deutschland GmbH									