

# HPLC solvents, mobile phase blends and additives

Achieve maximum performance in your HPLC analysis

HPLC Grade Chemicals	Pack sizes	Catalog numbers	
1-Propanol, HPLC Grade, 99% min	1 L, 4 x 1 L	<a href="#">022932.K2</a>	<a href="#">022932.M1</a>
Acetic acid, ammonium salt, HPLC Grade, 98+%,	250 g, 500 g	<a href="#">219992500</a>	<a href="#">219990500</a>
Acetone, HPLC Grade, 99.5+%	1 L, 2.5 L	<a href="#">268310010</a>	<a href="#">268310025</a>
Acetonitrile, HPLC Grade, 99.8%	1 L, 2.5 L	<a href="#">268270010</a>	<a href="#">268270025</a>
Acetonitrile, HPLC far UV/gradient Grade, 99.9+%	1 L, 2.5 L	<a href="#">H33387.AU</a>	<a href="#">H33387.OF</a>
Ammonium hydroxide, HPLC Grade, 35% soln in Water	100 mL	<a href="#">460801000</a>	
Isopropanol, HPLC Grade, 99.5%	1 L, 2.5 L	<a href="#">383910010</a>	<a href="#">383910025</a>
Methanol, HPLC Grade, 99.8%	1 L, 2.5 L	<a href="#">268280010</a>	<a href="#">268280025</a>
Tetrahydrofuran, HPLC Grade, 99.8%, unstabilized	1 L, 2.5 L	<a href="#">268370010</a>	<a href="#">268370025</a>
Trifluoroacetic acid, HPLC Grade, 99.5+%	100 mL, 4 x 100 mL	<a href="#">044630.AE</a>	<a href="#">044630.5Y</a>
Water, HPLC Grade, 1 L and 2.5 L	1 L, 2.5 L	<a href="#">389390010</a>	<a href="#">389390025</a>

## LC-MS & UHPLC-MS solvents, mobile phase blends, additives & kits

LC-MS & UHPLC-MS Solvents and Mobile Phase Solutions	Pack sizes	Catalog numbers	
Acetonitrile, LC-MS Grade, 99.8%	1 L, 4 x 1 L	<a href="#">51101</a>	<a href="#">85188</a>
Acetonitrile + 0.1% formic acid (FA) (V/V), LC-MS Grade	1 L, 4 x 1 L	<a href="#">85174</a>	<a href="#">85175</a>
Methanol, LC-MS Grade, 99.8%	1 L, 4 x 1 L	<a href="#">047192.K2</a>	<a href="#">047192.M1</a>
Water, LC-MS Grade	1 L, 4 L	<a href="#">047146.K7</a>	<a href="#">047146.Y0</a>
Water + 0.1% Formic acid (FA) (V/V), LC-MS Grade	1 L, 4 x 1 L	<a href="#">85170</a>	<a href="#">85171</a>
Acetonitrile, UHPLC-MS grade	1 L, 6 x 1 L	<a href="#">A9561</a>	<a href="#">A9561CS</a>
Methanol, UHPLC-MS grade	1 L, 6 x 1 L	<a href="#">A4581</a>	<a href="#">A4581CS</a>
Water, Optima UHPLC-MS grade	1 L, 6 x 1 L	<a href="#">W81</a>	<a href="#">W81CS</a>

LC-MS Reagents	Pack sizes	Catalog numbers	
Formic acid, LC-MS Grade, 99+%,	10 x 1 mL ampoules, 50 mL	<a href="#">28905</a>	<a href="#">85178</a>
Heptafluorobutyric acid, HPLC Grade	10 x 1 mL ampoules	<a href="#">53104</a>	
Trifluoroacetic acid (TFA), LC-MS Grade	50 mL	<a href="#">85183</a>	

ChromaCare LC-MS Flush Solutions			
LC-MS Flush Solution	<a href="#">T111101000</a>	Biologics Flush Solution	<a href="#">MB1241</a>

UHPLC-MS Installation Kits	
UHPLCMS INSTALLATION KIT Thermo Scientific	<a href="#">UHPLCMSKIT</a>

 Need more chemicals? Visit [Thermo Scientific Chemicals](#)

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third party data or information associated with the product. Products are for research and development use only. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use. © 2023 Thermo Fisher Scientific Inc. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified. **05\_2023**