


|             |                       |       |   |
|-------------|-----------------------|-------|---|
| CATALOG NO. | NOM. CAPACITY ( GAL ) |       |   |
| 005305-     | 1 1/4                 | 2 1/8 | 5 |

| MATERIALS        |              |              |              |
|------------------|--------------|--------------|--------------|
| SIZE CODE....:   | -0609        | -0910        | -1212        |
| CHAMBER.....:    | PC           | PEI          | PEI          |
| VACUUM PLATE:    | PP ( WHITE ) | PC ( WHITE ) | PC ( WHITE ) |
| GASKET( S )....: | NEOPRENE     |              |              |
| ADAPTER.....:    | HDPE         |              |              |

|                                          |            |            |           |            |             |            |
|------------------------------------------|------------|------------|-----------|------------|-------------|------------|
| SIZE CODE.....:                          | -0609      |            | -0910     |            | -1212       |            |
| CHAMBER                                  |            |            |           |            |             |            |
| NOM. WEIGHT<br>( gms ).....:             | 685        |            | 1000      |            | 2030        |            |
|                                          | INCHES     | MM         | INCHES    | MM         | INCHES      | MM         |
| J ( I.D. ).....:                         | 6.42 ±0.08 | 163.1 ±2.0 | 8.49 ±.09 | 215.6 ±2.3 | 11.72 ±0.10 | 297.7 ±2.5 |
| K ( O.D. ).....:                         | 6.68 ±0.08 | 169.7 ±2.0 | 8.72 ±.09 | 221.5 ±2.3 | 11.97 ±0.10 | 304.0 ±2.5 |
| L ( HT. ).....:                          | 9.4 ±0.1   | 239 ±3     | 10.0 ±0.1 | 254 ±3     | 12.0 ±0.1   | 305 ±3     |
| W.T.( <sup>NOM.</sup><br>VALL THK )....: | 0.15       | 3.8        | 0.12      | 3.0        | 0.17        | 4.3        |
| PLATE                                    |            |            |           |            |             |            |
| NOM. WEIGHT<br>( gms ).....:             | 330        |            | 900       |            | 900         |            |
|                                          | INCHES     | MM         | INCHES    | MM         | INCHES      | MM         |
| A ( DIA ).....:                          | 8.3        | 211        | 13.5      | 343        | 13.5        | 343        |
| B ( DIA ).....:                          | 6.31       | 160.3      | 12.80     | 325.1      | 12.80       | 325.1      |
| C ( DIA ).....:                          | N/A        | N/A        | 11.52     | 292.6      | 11.52       | 292.6      |
| D ( DIA ).....:                          | N/A        | N/A        | 8.32      | 211.3      | 8.32        | 211.3      |
| E ( DIA ).....:                          | N/A        | N/A        | 6.31      | 160.3      | 6.31        | 160.3      |
| F .....                                  | 0.10       | 2.5        | 0.10      | 2.5        | 0.10        | 2.5        |
| G .....                                  | 1.07       | 27.2       | 1.07      | 27.2       | 1.07        | 27.2       |
| H .....                                  | 9.8        | 249        | 14.2      | 361        | 14.2        | 361        |

NOTES:

- ALL DIMENSIONS ARE NOMINAL AND IN INCHES AND MILLIMETERS UNLESS OTHERWISE NOTED.
- THIS IS NOT A PRODUCTION DRAWING, BUT IS FOR INFORMATIONAL PURPOSES ONLY, AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



SPECS ON BACK

NOT TO SCALE

CONFIDENTIAL

THIS PRODUCT SPECIFICATION SHEET CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION AND IS TO BE USED ONLY FOR THE EXPRESSED PURPOSES AGREED UPON BY AN AUTHORIZED OFFICER OF THERMO FISHER SCIENTIFIC.

**ThermoFisher**  
**SCIENTIFIC**

Thermo Fisher Scientific  
75 Panorama Creek Drive  
Rochester, NY 14625-2385, USA

|      |     |       |        |                  |              |
|------|-----|-------|--------|------------------|--------------|
| MADE | MCC | APP'D | PVC    | PSS-00-5305-XXXX | REV.<br>0396 |
| CK'D | PVC |       | 4/5/96 |                  |              |

DESCRIPTION:

VACUUM CHAMBERS