



Technical Data Sheet

Thermo Scientific Ultra-Low Temperature Upright Freezer

Revision-3

Thermo Fisher Scientific, Asheville, North Carolina

Specifications	Model Number																													
	Thermo Scientific TSU600V																													
Application, Rating and Electrical Data	Application, Rating and Electrical Data																													
Application	Storage of General (non-flammable) Laboratory Materials																													
Storage Volume	815 liters / 28.8 cu. ft., 600 Standard 2" Boxes																													
Temperature Rating	-50°C to -85°C @ 32 °C(90°F) Ambient																													
Electrical Power	230V, 50 Hz, 1 Phase																													
Instrument Rated Current	9.5 FLA																													
Building Supply Rating	20.0A dedicated grounded circuit. Protected by circuit breaker rated for inductive loads																													
Power Plug/Power Cord Length	CEE 7/7, 10 Feet or 3.0 Meters																													
Agency Listings	CE																													
Application Environment	Indoor Use Only; Non-Corrosive, Non-Flammable, Non-Explosive, Good Air Ventilation, 15C - 32C (59F - 90F)																													
Cooling Water Condition	N/A																													
Lifetime of Product	10 years																													
Refrigeration Configuration	Refrigeration Configuration																													
Refrigeration System	Industrial-Rated Two Stage Cascade System																													
Compressor / Number	1 HP Hermetic Compressor for Low Temperature Application / 2																													
Condenser Type/Number	Enhanced Finned-Tube and Forced-Air Cooled / 1																													
Expansion Device	Capillary Tube On Both Cascade Stages																													
Evaporator Type	Cold Wall With Enhanced Heat Transfer Treatment																													
Defrost Method	Manual Defrost																													
Refrigerant Charge/Flammability	CFC/HCFC-Free Environmentally Safe Refrigerant Mixtures / Non-Flammable in both stages																													
Controller/Electrical System Configuration and Features	Controller/Electrical System Configuration and Features																													
Controller Level	Eye Level																													
Power Switch	On-Off with Circuit Breaker																													
Controller Type	Microprocessor Control with Touch Screen Input and Display. Includes USB System Data Retrieval																													
Setpoint Security	Yes																													
Compressor Safe Guard	High Temperature Warning/Current and Temperature Protection/Logic Protection																													
Control Sensor	Single RTD (1000 ohm Platinum RTD)																													
RS232/Remote Alarm Terminals	RS485/4-20mA output																													
Adjustable Warm/Cold Alarms	Fully Adjustable																													
Auto-Voltage Safeguard	Buck/Boost System																													
Dimensions and Construction	Dimensions and Construction																													
Interior Dimensions (H x D x W)	1.30 x 0.72 x 0.87 m (51.2 x 28.3 x 34.4 in.)																													
Exterior Dimensions (H x D x W)	1.98 x 0.96 x 1.11 m (78.0 x 37.6 x 43.6 in.)																													
Insulation	High R-value Vacuum Insulation Panels and High Density Water-Blown Polyurethane Foam																													
Perimeter Heater	Silicone-Based High Performance Seal Gasket with Electrical Door Perimeter Heater																													
Shelves / Capacity	3 or 4 Stainless Steel Shelves Adjustable In 1" Increments. Max. Cap. per Shelf: 110 kg (245 lbs.)																													
All-Direction Casters	Standard with Locks																													
Ship Weight	Approximately 388 kg (854 lbs.)																													
Other Options	LN2 or CO2 Back Up System, HID Controlled Access, SMS Text, Chart Recorder, 4 or 5 Inner Doors																													
Typical Performance Characteristics in Normal Ambient Condition	Typical Performance Characteristics in Normal Ambient Condition																													
 <p style="font-size: small;">25C Ambient (18768-H-X) — PD — WU</p>	 <p style="font-size: small;">25C Ambient (18768-H-X) — Avg — Max — Min</p>	<p>Performance Data Summary (Typical Average Values)</p> <table style="font-size: x-small; border-collapse: collapse;"> <tr><td>Avg. Cabinet Temp. at -80C Setpoint, High Performance (C):</td><td style="text-align: right;">-79.5</td></tr> <tr><td>Peak Variation From -80C Setpoint, High Performance (C):</td><td style="text-align: right;">+4.9 / -2.9</td></tr> <tr><td>Peak Variation From -80C Setpoint, Energy Saving (C):</td><td style="text-align: right;">+9.6 / -0.8</td></tr> <tr><td>Stability, -80C Setpoint, High Performance (C):</td><td style="text-align: right;">2.5</td></tr> <tr><td>Uniformity, -80C Setpoint, High Performance (C):</td><td style="text-align: right;">5.2</td></tr> <tr><td>1 Min. Door Open Recovery to -75C Avg. Cabinet Temp. (min):</td><td style="text-align: right;">33</td></tr> <tr><td>Cycle Rate, -80C Setpoint, High Performance (on/off, min/min):</td><td style="text-align: right;">19/12</td></tr> <tr><td>Duty Cycle, -80C Setpoint, High Performance (%):</td><td style="text-align: right;">62</td></tr> <tr><td>Energy Consumption, -80C Setpoint, High Performance (kWh/day):</td><td style="text-align: right;">21.3</td></tr> <tr><td>Heat Rejection, -80C Setpoint, High Performance (BTU/hr):</td><td style="text-align: right;">3028</td></tr> <tr><td>Energy Consumption, -80C Setpoint, Energy Saving (kWh/day):</td><td style="text-align: right;">17.7</td></tr> <tr><td>Heat Rejection, -80C Setpoint, Energy Saving (BTU/hr):</td><td style="text-align: right;">2516</td></tr> <tr><td>Pulldown Time to -80C Average Cabinet Temp. (hours)</td><td style="text-align: right;">7.9</td></tr> <tr><td>Warmup Time, From Average Cabinet Temp. of -80C to -50C (min):</td><td style="text-align: right;">257</td></tr> </table>	Avg. Cabinet Temp. at -80C Setpoint, High Performance (C):	-79.5	Peak Variation From -80C Setpoint, High Performance (C):	+4.9 / -2.9	Peak Variation From -80C Setpoint, Energy Saving (C):	+9.6 / -0.8	Stability, -80C Setpoint, High Performance (C):	2.5	Uniformity, -80C Setpoint, High Performance (C):	5.2	1 Min. Door Open Recovery to -75C Avg. Cabinet Temp. (min):	33	Cycle Rate, -80C Setpoint, High Performance (on/off, min/min):	19/12	Duty Cycle, -80C Setpoint, High Performance (%):	62	Energy Consumption, -80C Setpoint, High Performance (kWh/day):	21.3	Heat Rejection, -80C Setpoint, High Performance (BTU/hr):	3028	Energy Consumption, -80C Setpoint, Energy Saving (kWh/day):	17.7	Heat Rejection, -80C Setpoint, Energy Saving (BTU/hr):	2516	Pulldown Time to -80C Average Cabinet Temp. (hours)	7.9	Warmup Time, From Average Cabinet Temp. of -80C to -50C (min):	257
Avg. Cabinet Temp. at -80C Setpoint, High Performance (C):	-79.5																													
Peak Variation From -80C Setpoint, High Performance (C):	+4.9 / -2.9																													
Peak Variation From -80C Setpoint, Energy Saving (C):	+9.6 / -0.8																													
Stability, -80C Setpoint, High Performance (C):	2.5																													
Uniformity, -80C Setpoint, High Performance (C):	5.2																													
1 Min. Door Open Recovery to -75C Avg. Cabinet Temp. (min):	33																													
Cycle Rate, -80C Setpoint, High Performance (on/off, min/min):	19/12																													
Duty Cycle, -80C Setpoint, High Performance (%):	62																													
Energy Consumption, -80C Setpoint, High Performance (kWh/day):	21.3																													
Heat Rejection, -80C Setpoint, High Performance (BTU/hr):	3028																													
Energy Consumption, -80C Setpoint, Energy Saving (kWh/day):	17.7																													
Heat Rejection, -80C Setpoint, Energy Saving (BTU/hr):	2516																													
Pulldown Time to -80C Average Cabinet Temp. (hours)	7.9																													
Warmup Time, From Average Cabinet Temp. of -80C to -50C (min):	257																													
<p>1) Performance is nominal and individual units may vary. 2) Freezer performance will differ due to product amount, product size and operating conditions. 3) Continuous product enhancements may, without notice, result in amendments or omissions to this specification. Thermo Scientific cannot accept responsibility for damage, injury, loss or expenses resulting from misapplication of the information herein.</p>																														

