



## Biological safety cabinets

# Where innovation meets experience

## 1500 Series A2 Biological Safety Cabinet

Redefine excellence in your lab with the Thermo Scientific™ 1500 Series Class II, Type A2 Biological Safety Cabinet, offering advanced protection, exceptional user comfort and convenience.

### Features include:

- Made in the USA
- Real-time airflow compensation with Thermo Scientific™ SmartFlow™ Plus technology
- Thermo Scientific™ DAVE™ (Digital Airflow Verification) Plus System validates protection by monitoring airflow velocities, which detect and alert to any changes
- User-friendly 7 in. touchscreen interface
- New window mechanism with haptic feedback for correct sash window height
- SmartClean front window design to improve access to the work area for easy cleaning
- Programmable UV light enables pre-scheduled sterilization
- New ergonomic accessories for added comfort
- Stainless-steel, SmartCoat-painted interior



## Specifications and ordering information

### Thermo Scientific 1500 Series Class II, Type A2 Biological Safety Cabinets

Cabinet with manual adjustable stand, UV and armrests

Cat. No.	1523A2	1575A2	1577A2
Size	3 ft.	4 ft.	6 ft.
Window opening	10 in.	10 in.	10 in.
Interior material	Stainless steel	Stainless steel	Stainless steel
Voltage/frequency	120V/60Hz	120V/60Hz	120V/60Hz
Exterior dimensions (W x H x D)	39.4 x 61.8 x 31.5 in.	51.2 x 61.8 x 31.5 in.	74.8 x 61.8 x 31.5 in.

 Learn more at [thermofisher.com/1500a2-usa](https://thermofisher.com/1500a2-usa)

**For Laboratory Use. It is the customer's responsibility to ensure that the performance of the product is suitable for customers' specific use or application.** © 2025 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified. **STUDIO 24-3484 0125**

**thermo** scientific