



INNOVATOR INSIGHT

G-Rex bioreactors incubated in Heracell™ Vios™ CR CO₂ Incubators help prevent cross contamination and bacterial contamination in cell and gene modified cell therapy production

Mary Kay Bates, Dan Fick, Jürgen Schneider, Dan Welch,
Josh Ludwig, and Lindsey Low

Abstract: for cell and gene modified cell therapy (GMCT) manufacturing, a robust contamination control strategy (CCS) is necessary to ensure compliance with current good manufacturing practices (cGMP). A successful CCS helps ensure safety, purity, efficacy, and quality of a cell therapy product. Cell therapy manufacturers should implement closed systems (CS) wherever possible and employ equipment that maintains a stable, clean environment with advanced monitoring. We show that CS G-Rex® bioreactors combined with Thermo Scientific™ Heracell™ Vios™ CR carbon dioxide (CO₂) incubators enable simplified parallel processing capabilities and significantly reduced contamination risks in a highly efficient production. Producing T cells, NK cells and others in a CS G-Rex bioreactor (Wilson Wolf Manufacturing, LLC) reduces the risk of contamination. The G-Rex approach eliminates most manual handling, a leading source of contamination. G-Rex bioreactors include weldable tubing for simple CS sterile connections and do not require interventions for feeding. Importantly, CS G-Rex bioreactors feature a validated sterile fluid path that reliably maintains integrity throughout manufacturing as shown by microbial ingress testing based on

ASTM E-3251. The bioreactors withstand full immersion in a challenge media solution containing bacteria for at least 14 days. G-Rex bioreactors also passed Viral Penetration testing based on ASTM Method F1671, demonstrating suitability for use in CAR-T and other CGT applications requiring use of virus. Heracell Vios CR CO₂ Incubators provide recovery of all parameters in 10 minutes or less, and uniformity of ± 0.3 °C per DIN 12880, which defines how incubators and other laboratory heating equipment should be measured. These parameters are maintained even when performing high volume production with ten G-Rex 500M-CS bioreactors simultaneously. Thermo Scientific™ CultiMaxx™ shelving maximizes production capacity per footprint. Incubating multiple G-Rex bioreactors in a single chamber means the incubator must offer proven contamination control features, to protect individual donor/patient product, if applicable. An on-demand cycle delivers 12-log sterility assurance level (SAL). In-chamber HEPA filtration generates air cleanliness in the chamber equal to ISO Class 5. Data show the Heracell Vios CR CO₂ incubators are certified for use in ISO Class 5, GMP Grade A/B cleanrooms. Together, G-Rex bioreactors incubated in Heracell Vios CR CO₂ incubators offer a high yield, parallel processing method with reduced contamination risk in a highly efficient footprint enabling robust CCS in a cGMP environment.

Cell & Gene Therapy Insights 2024; 10(4), 594–607

DOI: 10.18609/cgti.2024.072

MATERIALS AND METHODS

G-Rex microbial ingress test

Tests were performed by a third-party test lab, Wuxi AppTec (Atlanta GA USA) in accordance with ASTM E-3251 [1]. Briefly, a 1×10^6 CFU (colony forming unit) challenge solution was prepared using *Brevundimonas diminuta*. The test sample G-Rex bioreactors were aseptically filled with Nutrient Broth Media through each of the tubing lines, including the sample port, the reduction lines, and the harvest lines to sufficiently wet all internal surfaces. 5,000 mL of Nutrient Broth Media was introduced into each test sample G-Rex bioreactor. 12 L of challenge solution was filled into a lined container (Figure 1A). The G-Rex bioreactors were weighted to ensure full immersion in the challenge solution during the entire 14-day incubation test period (Figure 1B). The vent filter was unclamped and in an upright position to ensure that it did not make contact with the challenge solution.

To confirm no growth, the test bioreactors were carefully removed from the challenge

solution and placed inside a new sterile bag. The bioreactors were then gently swirled to mix the contents, and a 1.0 mL aliquot of Nutrient Broth was removed and added to a 10 cm Petri dish in triplicate per bioreactor and incubated 2–3 days then counted. For positive controls, the *B. diminuta* challenge solution was incubated in parallel with the samples, and growth was confirmed.


G-Rex membrane viral penetration test

Viral penetration testing was performed by a third-party test lab (Nelson Laboratories, Salt Lake City, UT, USA) according to their internal protocols. Tests were performed on the G-Rex membrane material according to ASTM F16712 [2]. Briefly, a challenge suspension was prepared using bacteriophage Phi-X174 maintained at a concentration of at least 1.0×10^6 /mL. A total of 32 test articles (G-Rex membrane material) were prepared by loading each test article membrane into a test apparatus as shown in Figure 2.

The bolts around the test frame were torqued to create a perimeter seal. Each test

FIGURE 1

G-Rex bioreactors immersed for the microbial ingress test.



(A) Loading the bioreactors: 12 L of challenge solution were filled into the lined container and the bioreactor completely immersed except the vent filter. (B) During the test: the bioreactors were weighted to ensure full immersion for the complete 14-day test.

reservoir containing the filter sample was then filled with 60 mL of PhiX174 bacteriophage challenge suspension and pressured to 2.0 psig (~103 mm Hg) for 1 minute. Air pressure was then vented, and the test articles were allowed to sit for 54 minutes with no applied pressure while the surface of the membranes was observed for liquid penetration. As confirmation, an assay titer was performed for each test article in addition to positive and negative controls. For this test, the observed side of the membranes was rinsed with a sterile medium and assayed for the presence of Phi-X174 bacteriophage.

CO₂ incubator temperature uniformity mapping

Validated type K, Class 2 nickel chromium-nickel (NiCr-Ni) thermocouple temperature probes (Gantner, Germany) were placed in 27 locations in the incubator chamber, with 9 equidistant probes on each of three shelves, placed according to DIN 12880 [3]. The thermocouples were used in conjunction with a TV A4-32 MG data logger system (Gantner). The temperature was set to 37 °C, the humidity reservoir was filled to the maximum 3 L

and the humidity was set to maximum (93% or higher). The incubator operated at these conditions undisturbed for 12 hours before commencing the test measurement. Each measurement had a 10-second duration and the test continued for 22 hours, in an ambient temperature of 22.8 °C. Uniformity equals the difference between the highest and lowest recorded temperatures.

CO₂ incubator recovery tests

For temperature, the tests were performed similarly to the uniformity mapping, except the incubator 'low humidity' setting was used and a validated PT100 temperature probe (KMP, Germany) was placed in the center of the center shelf. 10 G-Rex 500M-CS bioreactors were each filled with 5 L of water pre-heated to 37 °C. Both the inner and outer doors of the incubator were opened for 60 seconds, then closed. Recovery is defined as returning to 98% of the set value.

For CO₂ gas recovery testing, the incubator was set to the most commonly used concentration of 5%, temperature was set to 37 °C, and the 'low humidity' setting was used, which reduces humidity to 90%. CO₂

FIGURE 2

Membrane viral penetration test set-up.



The test membrane was loaded into the test apparatus, then the bolts tightened to seal the perimeter. The test reservoir was filled with the bacteriophage challenge suspension and pressurized. Following the venting, the membrane surface was visually inspected for liquid penetration. Then each test reservoir was tested for the bacteriophage.

was measured using a GMM221 infrared sensor (Vaisala, Finland) used without the protective cover and placed in the center of the middle shelf between the 4 G-Rex bioreactors (10 G-Rex vessels total in the incubator chamber). Recovery is defined as returning to 98% of the set value.

For humidity, the 'low humidity' setting was used. Humidity was measured using a FHAD 462 relative humidity (RH) sensor (AHLBORN, Germany) positioned in the center of the middle shelf between the 4 G-Rex bioreactors (10 total in the incubator chamber). Recovery is defined as returning to 98% of the set value.

HEPA filtration tests

Tests were performed in a room at 22 °C, 50% RH. Ambient particles greater than or equal to 0.5 µm were counted, and an average of 4,269,400 particles/m³ was recorded (ISO Class 8) [4]. The incubator chamber and glass door were wiped with 70% ethanol to remove any surface residual particles. A calibrated particle counter, ACS Plus 328 (KM Optoelectronic GmbH, Germany) was used with an airflow setting of 1.0 cubic

foot per minute (cfm). Particles were generated to boost to ISO Class 8–9 levels using an aerosol generator, CFG290 LMT (Topaz GmbH, Germany). The sample tubing for the particle counter was located in the center of the empty chamber and the return air located in the top left rear of the chamber. The return air velocity was set to 2.1 m/sec. The test sample tubing and the return air tubing were run through the access port in the left upper rear wall. The space around the tubing was sealed, and the incubator water drain was sealed inside the chamber to ensure no passive air. A new HEPA filter was installed in the incubator chamber according to the user manual. Samples were collected for 30 seconds and purge time was 2 seconds between samples. Particles of 0.5 µm and larger were counted. The particle counter was operated in 'Automatic' mode for a minimum of 10 minutes.

Cleanroom compatibility tests

Tests were performed by an industry specialist, TÜV SÜD (Munich, Germany). Briefly, working in an ISO Class 4 cleanroom, the entire incubator was manually wiped and analyzed for surface particle shedding. The entire incubator exterior was then sampled using a particle counter to determine the areas of highest emission. This area was then sampled for 100 minutes with a sample taken every minute during the approximately 12-hour sterilization cycle at 180 °C. Particles of 0.5 µm and larger were counted.

RESULTS

Closed-System G-Rex Bioreactors prevent bacterial contamination and viral penetration

G-Rex Bioreactor validations enable fully closed system manufacturing

G-Rex CS Bioreactor validations include Shipping Simulation (ASTM D 4169)

[5], Environmental Conditioning (ISTA Procedure 3A) [6], Accelerated and Real-Time Shelf-Life Studies (3 year per Q10 Theory principles and ASTM F 1980-16) [7], and Sterilization Validation (Sterile Fluid Path) per Method VDMAX25 ANSI/AAMI/ISO 11137 [8] 10⁶ SAL Dose Substantiation and Max Dose validations. This validation testing supports the shelf life and sterile fluid path claims listed on G-Rex Certificates of Compliance. G-Rex is manufactured by Wilson Wolf Manufacturing LLC, in accordance with cGMP, and is 100% leak tested prior to release. To further substantiate G-Rex CS and sterile fluid path integrity claims during use, third-party microbial ingress testing, and viral penetration testing were performed.

Incubating multiple G-Rex bioreactors simultaneously in Heracell Vios CR CO₂ incubators represents minimal risk due to in-chamber protections

Heracell Vios CR CO₂ incubators offer proven contamination control

Based on a history of incubation innovation, Heracell Vios CR CO₂ incubators are the first-to-market certified cleanroom compatible CO₂ incubators [9]. In this way, the Heracell Vios CR models protect the cleanroom environment as an extension of the proven protection for cells incubated in the incubator chamber. This in-chamber protection includes a HEPA filtration system to capture airborne viable and non-viable particles, a 180 °C 12-log sterilization cycle which has been proven effective by a third-party test lab [10]. Humidity is provided by a covered, protected water reservoir which is easily drained and fully opened for easy cleaning and disinfection. All interior surfaces are electropolished to reduce microscopic structures where microorganisms could attach and to provide enhanced chemical resistance. The exterior casing is sealed, brushed stainless

steel with ingress protection (IP) 54 rated electronics. A unique Active Particle Control system captures particles that would otherwise be emitted to the cleanroom.

Microbial ingress testing verifies sterile fluid path integrity after rigorous microbial challenge

For microbial ingress testing, a very small bacterium, *B. diminuta*, is considered an ideal challenge. *B. diminuta* is a highly motile, gram-negative bacterium. Due to its small size (0.3–0.6 µm), it is the preferred indicator organism for testing filter integrity and pore size.

As described in the 'Methods' section, three test G-Rex bioreactors, three negative control bioreactors, and three positive control bioreactors were prepared. All bioreactors were immersed in the challenge solution and placed in an incubator for 14 days. After incubation, the bioreactors were examined for the presence or absence of bacterial growth. All three test bioreactors showed no bacterial growth after 14 days of incubation under test conditions.

After the completion of the 14-day test, no growth was observed in the nutrient broth tested from the test bioreactors (Table 1), confirming the results of the microbial ingress testing, and verifying sterile fluid path integrity despite full immersion in the bacterial challenge solution.

Similar microbial ingress testing has been performed according to the protocol described above for all available sterile Closed System G-Rex models resulting in no growth in any of the test bioreactors. These results confirm that the G-Rex bioreactors are a closed system.

Membrane viral penetration testing confirms non-porous membrane structure and no viral penetration

G-Rex bioreactors include a highly gas-permeable membrane comprised of thin

▶ **TABLE 1**

Microbial tests show no growth.

	Replicate 1	Replicate 2	Replicate 3
Test bioreactor: pre-subculture	No growth	No growth	No growth
Test bioreactor: post-subculture	No growth	No growth	No growth
Positive control	Growth	Growth	Growth
Negative control	No growth	No growth	No growth
Growth promotion	Growth	Growth	Growth

None of the tested bioreactors showed any growth, indicating that they passed the microbial ingress test challenge and demonstrating that the G-Rex bioreactors operate as a closed system.

▶ **TABLE 2**

Viral penetration tests show no penetration.

Test article number	Pre-challenge concentration (PFU/mL)	Post-challenge concentration (PFU/mL)	Assay titer (PFU/mL)	Visual penetration	Test result
1–32	2.5×10^8	3.0×10^8	$<1^a$	None seen	PASS
Negative control	2.5×10^8	3.0×10^8	$<1^a$	None seen	Acceptable
Positive control	2.5×10^8	3.0×10^8	TNTC ^{1b}	Yes	Acceptable

No bacteriophage was found in any of the 32 test samples, providing further evidence that the G-Rex bioreactors are a closed system.

^aA value of <1 plaque forming unit (PFU)/mL is reported for assay plates showing no plaques.

^bTNTC = PFUs were too numerous to count.

silicone rubber. According to Fick’s law of diffusion [11], gas molecules diffuse through the non-porous membrane’s molecular structure into the liquid medium inside the bioreactor. The oxygen consumption rate of cells at the bottom of a typical non gas permeable cell culture vessel such as a T flask easily exceeds the diffusion rate of oxygen through the overlying culture medium [12]. With the G-Rex bioreactor, gas diffusion through the membrane surface at the bottom of the bioreactor negates reliance on oxygen diffusion at the gas-liquid interface above the medium inside the bioreactor for sufficient oxygen delivery to cells. Unconstrained by height, enough media can be present in the device at onset of culture to eliminate the need for medium exchanges.

The membrane material at the bottom of the bioreactor was tested for viral penetration according to ASTM F1671 (Figure 2). This test method is intended to evaluate

blood-borne pathogens of major concern, including hepatitis B virus, hepatitis C virus, and human immunodeficiency virus. The Phi-X174 bacteriophage has the following attributes: it is a non-enveloped 15–27 nm virus with an icosahedral or nearly spherical morphology, excellent environmental stability, a limit of detection which approaches a single virus particle, and it grows rapidly.


As shown in Table 2, all 32 test articles passed viral penetration testing, no liquid penetration was observed, and no (<1) plaque-forming units (PFU/mL) were reported for each test sample matching the negative control assays and confirming no viral penetration of the membrane.

These test results support closed-system G-Rex bioreactors in cell therapy and GMCT manufacturing processes in low-cost and lower-grade cleanrooms. Additionally, G-Rex bioreactors are structured with sufficient wall heights to contain medium

at unconventional volumes. The G-Rex structure also ensures the medium surface remains at a uniform distance of 10 cm above the gas-permeable cell growth surface. Together, these structural elements allow immune cells to expand from a minimum cell density per square centimeter of gas-permeable cell growth surface area to a maximum cell density per square centimeter of gas permeable cell growth surface area without medium change. An optimal ratio of 10 mL of medium per square centimeter of cell growth surface area eliminates all interventions during expansion, including medium exchanges or cytokine spikes, further reducing contamination risks and simplifying cell manufacturing processes [13].





CultiMaxx shelving increases G-Rex capacity without compromising incubator performance


CultiMaxx Shelving is specifically designed to increase the incubator chamber capacity from 4 to 10 G-Rex 500M-CS units. Like the rest of the chamber, these shelves are electropolished to increase cleanability and reduce areas where microorganisms could attach. Due to the modified shelving configuration, we wanted to determine effects on environmental uniformity throughout the incubator chamber, because reactive T cells and NK cells are demonstrably affected by culturing conditions [14]. For the G-Rex specialized CultiMaxx shelving, Heracell™ Vios™ CR incubator shelves have been extended and the lowest shelf sits lower in the incubator chamber compared to the standard shelving. Conceivably these changes could negatively affect the uniformity of culturing conditions. When testing the new shelving in an empty Heracell VIOS incubator at 27 points according to DIN 12880, results show that the uniformity specification of $\pm 0.3^\circ\text{C}$ is maintained (Figure 3), similar to the standard shelving (results not shown).



Conditions recover quickly following a long door opening, even with 10 G-Rex bioreactors in the chamber simultaneously

Especially for primary patient immune cells, it is important that cultured cells spend their maximum time at their ideal conditions [14]. Because incubator recovery to set conditions following a door opening could be affected by size, type, and placement of large culture vessels, we tested recovery of each parameter following a sixty second door opening with ten filled G-Rex 500M-CS in place in the incubator chamber. Results show that all parameters recover quickly (see Figures 4–6). Recovery is similar to the 10-minute or less performance specification for the standard Heracell Vios





CR incubator, which is based on a 30-second door opening (results not shown). We have defined recovery as 98% of the set value.

Vios CR incubator protects cells with proven contamination control technologies


Many CO₂ incubators today offer features to help limit contamination inside. However, there is a wide range of efficacy of these technologies. For cell therapy manufacturing, proven technologies should be employed.

HEPA filtration

It is a common misconception that HEPA filtration only captures particles 0.3 µm or larger. This stems from the Most Penetrating Particle Size (MPPS) classification. Different physical processes are involved including impaction, interception and diffusion [15]

such that for an H13 HEPA filter, the MPPS is 99.97% efficient at particles of 0.3 µm but as shown in **Figure 7**, smaller and larger particles are captured with higher efficiency approaching 100%.

A HEPA filtration system is driven by a circulating fan. Thermo Scientific™ THRIVE™ Active Airflow system works with the H13 HEPA filter to clean the air over time, as a dilution, where the entire chamber air volume is passed through the HEPA filter every 60 seconds. We wanted to ensure that the Heracell Vios 250i CR CO₂ incubator chamber reaches ISO Class 5 cleanroom conditions in 5 minutes after a 30 second door opening. Normal indoor room air is ISO Class 8–9. ISO Class 8 = 3.5 × 10⁶ particles of 0.5 µm or larger per cubic meter of air. A Grade B cleanroom is equal to ISO Class 5 when at rest, ISO Class 7 in operation. These tests were conducted in an ISO Class 7 room at 23 °C. Particles were injected in the chamber to




equal approximately ISO Class 8–9. Samples were taken according to ISO 14644-1 [4,16]. The results show that conditions inside the chamber reach ISO Class 5 conditions in about 5 minutes and continue to get cleaner over time (**Figure 8**). This system helps to protect cultures from any microorganisms which could enter the incubator when the doors are opened.

Cleanroom compatibility certification

An estimated 70% of particulates in a cleanroom come from the staff, and an estimated 15% comes from the process equipment [17]. As that process equipment is heated, more particles are shed into the air. For this reason, a CO₂ incubator with a high temperature sterilization cycle represents a greater risk and should be certified for use in a cleanroom. Heracell Vios CR CO₂ incubators include an exhaust filtration system that protects the



cleanroom even during sterilization. They are certified by an industry specialist to be compatible with EU Grade A/B, ISO Class 5 cleanrooms [8]. As shown in **Figure 9**, the particles sized 0.5 µm or larger given off during the 12-hour (720 minutes) sterilization cycle fall below ISO Class 5, which has a limit of 3,520 particles/m³ sized 0.5 µm or larger.



During normal operation at 37 °C, the incubator is also certified for use in ISO Class 5 conditions.

Closed system G-Rex bioreactors in combination with Heracell Vios CR CO₂ incubators enable simplified and efficient cGMP cell therapy manufacturing

The results of this testing tangibly demonstrate the possibility of high-throughput parallel processing of cell and gene-modified cell therapies. The modular approach is easily automated and scaled in a highly efficient facility layout. Without intervention, G-Rex bioreactors regularly achieve 40 million cells per square centimeter of gas-permeable cell growth surface area [18]. Each G-Rex 500M-CS can produce 20 billion cells, and each Heracell Vios CR CO₂ Incubator can hold 10 G-Rex 500M-CS (Figure 10). Thus, when the incubators are stacked, up to 400 billion cells can be produced in just over 3 square feet of floor space. This predictability enables repeatable, robust, and low-risk cell production for large-scale allogeneic and/or autologous processes. A scalable, low-cost, and high-throughput manufacturing facility layout is now possible.

Production set-up can occur in a small cleanroom, which houses upstream cellular processing equipment and reagents for high throughput closed system cell production set-up (i.e., apheresis wash, media fill, activation, etc.) and closed system inoculation of G-Rex bioreactors, followed by transfer of G-Rex bioreactors to a separate incubation room, which houses numerous incubators for parallel expansion processes with no risk of bacterial or cross-contamination (Figure 11).

Upon completion of the expansion phase, closed system G-Rex bioreactors can be removed from the incubators and moved to a cleanroom dedicated to downstream processing. The downstream cleanroom houses downstream cell processing equipment and reagents for cell harvest, final formulation, and fill processes. The resulting facility will produce significantly more doses in a smaller space than conventional facility designs. In addition, this combination has already been demonstrated in a fully automated system [19].

CONCLUSIONS

- G-Rex bioreactors are shown to operate as a closed system using multiple tests including microbial ingress testing and viral penetration testing.
- Heracell Vios CR CO₂ incubators are shown to retain their specified uniformity and recovery specifications even when filled with 10 G-Rex CS bioreactors. They also protect cells with ISO Class 5 conditions inside the chamber, and are certified for use in ISO Class 5, EU GMP Grade A/B cleanrooms environments.
- Heracell Vios CR CO₂ incubators with CultiMaxx shelving can hold up to 10 G-Rex 500M-CS bioreactors, producing up to 400 billion cells in a small footprint. G-Rex bioreactors in combination with Heracell Vios CR incubators enable novel facility design for high-throughput and easily automated cell therapy manufacturing.

REFERENCES

1. ASTM International. ASTM E-3251-20. Standard Test Method For Microbial Ingress Testing On Single-Use Systems Test Method for Microbial Ingress Testing On Single-Use Systems 2023.
2. ASTM International. ASTM F1671/F1671M-22. Standard Test Method For Resistance Of Materials Used In Protective Clothing To Penetration By Blood-Borne Pathogens Using Phi-X174 Bacteriophage Penetration As A Test System 2022.
3. Deutsches Institut für Normung. DIN 12880 Electrical Laboratory Devices—Heating Ovens And Incubators 2007.
4. International Organization for Standardization (ISO). ISO 14644-1: Clean Rooms And Associated Controlled Environments 2015.
5. ASTM Standard Practice for Performance Testing of Shipping Containers and Systems.
6. ISTA Packaged-Products for Parcel Delivery System Shipment 70 kg (50 lb) or Less.
7. ASTM Standard Guide for Accelerated Aging of Sterile Barrier Systems and Medical Devices.
8. ISO Sterilization of Health Care Products—Radiation.
9. Wronski K, Bates MK, Phillips P, *et al.* Compliance testing demonstrates a CO₂ incubator merits certification for use in Grade A/B environments. Thermo Fisher Scientific EXT5075 0423 (2021).
10. Thermo Fisher Scientific. Thermo Scientific Steri-Run sterilization cycle proves total sterilization. ANC02STERIRUN 0215 (2015).
11. Place TI, Domann FE, Case AJ. Limitations of oxygen delivery to cells in culture: an under-appreciated problem in basic and translational research. *Free Radic. Biol. Med.* 2017; 113, 311–22.
12. Bajgain P, Mucharla R, Wilson J, *et al.* Optimizing the production of suspension cells using the G-Rex ‘M’ series. *Mol. Ther. Methods Clin. Dev.* 2014; 1, 14015.
13. Garcia-Aponte OF, Herwig C, Kozma B. Lymphocyte expansion in bioreactors: upgrading adoptive cell therapy. *J. Biol. Eng.* 2021; 15, 13.
14. Bates MK. Consider all CO₂ incubator parameters for best cell growth. LABO 56–59 (2014).
15. Lindley WG. Filter Pore Size And Aerosol Sample Collection. In: *NIOSH Manual of Analytical Methods (NMAM)*, 5th Edition. 2016; Department of Health and Human Services, Centers for Disease Control and Prevention, National Institute for Occupational Safety and Health.
16. European Commission. The Rules Governing Medicinal Products In The European Union. Volume 4: Eu Guidelines For Good Manufacturing Practice For Medicinal Products For Human And Veterinary Use. Annex 1 Manufacture of Sterile Medicinal Products (2013).
17. Clarke D, Stanton J, Powers D, *et al.* Managing particulates in cell therapy: guidance for best practice. *Cytotherapy* 2016; 18(9), 1063–76.
18. Gagliardi C, Khalil M, Foster AE. Streamlined production of genetically modified T cells with activation, transduction and expansion in closed-system G-Rex bioreactors. *Cytotherapy* 2019; 21(12), 1246–57.
19. Melocchi A, Schmittlein B, John AL, *et al.* Development of a robotic cluster for automated and scalable cell therapy manufacturing. *Cytotherapy* 2024; In press.

AFFILIATIONS

Mary Kay Bates

Senior Global Applications Scientist,
Thermo Fisher Scientific,
Waltham, MA, USA

Dan Fick

Director of Quality,
Wilson Wolf Manufacturing LLC,
St Paul, MN, USA

Jürgen Schneider

R&D System Engineer,
Thermo Fisher Scientific,
Waltham, MA, USA

Dan Welch

Director of Product Development,
Wilson Wolf Manufacturing LLC,
St Paul, MN, USA

Josh Ludwig

Global Commercial Director,
ScaleReady USA LLC,
St Paul, MN, USA

Lindsey Low

Senior Global Product Manager,
Thermo Fisher Scientific,
Waltham, MA, USA



AUTHORSHIP & CONFLICT OF INTEREST

Contributions: The named authors take responsibility for the integrity of the work as a whole, and have given their approval for this version to be published.

Acknowledgements: None.

Disclosure and potential conflicts of interest: Welch D and Fick D are employees of Wilson Wolf Manufacturing LLC. Ludwig J is an employee of ScaleReady USA LLC.

Funding declaration: The authors received no financial support for the research, authorship and/or publication of this article.

ARTICLE & COPYRIGHT INFORMATION

Copyright: Published by *Cell & Gene Therapy Insights* under Creative Commons License Deed CC BY NC ND 4.0 which allows anyone to copy, distribute, and transmit the article provided it is properly attributed in the manner specified below. No commercial use without permission.

Attribution: Copyright © Thermo Fisher Scientific. Published by *Cell & Gene Therapy Insights* under Creative Commons License Deed CC BY NC ND 4.0.

Article source: Invited; externally peer reviewed.

Submitted for peer review: Mar 7, 2024; **Revised manuscript received:** May 16, 2024;

Publication date: Jun 12, 2024.



G-Rex® Bioreactor Simple. Proven.



The GOLD standard -
used in approved
CAR-T therapies globally.