



Pipetting

Samco transfer pipettes

Precisely what you need

Yesterday, today, and tomorrow

Thermo Scientific™ Samco™ transfer pipettes have provided outstanding performance and reliability for over 40 years.

Design

- Grips easily with latex gloves—no slipping
- Clear, graduated markings
- Fine-tip accuracy
- Packaging materials greatly reduce airborne mold spores from entering testing areas

Repeatable results

- Inert, nontoxic polyethylene
- Manufactured without mold-release agents that could interfere with test results

Reliability

- On-site tool room able to provide custom-made transfer pipettes
- Precision-cut tips deliver a uniform drop size
- Controlled processes produce a uniform bulb with uncompromised integrity
- ISO 13485:2016– and ISO 9001:2015–certified facilities
- QSR (cGMP)–compliant facilities

Application guide

Life science applications

Top 9 pipettes:
9, 19, 21, 26, 30, 31, 32, 33, 34

Cells in flasks and tubes— large volume, long pipettes

| | |
|---|--------|
| Subculturing, harvesting, sampling 15, 50, 100 mL tubes and flasks | 33, 34 |
| Remove supernatant and media from cell cultures | 33, 34 |
| Wash cells | 33, 34 |
| Post-centrifugation to remove all cell layers | 33, 34 |

Isolating cells—large aperture pipette

| | |
|--|---------------|
| Prevent cells from getting stripped when removed or transferred | 9, 10, 26, 27 |
| Triturate cells | 9, 10, 26, 27 |
| Isolate platelets from blood and wash | 9, 10, 26, 27 |

Technique control—narrow stem, exact volume, and fine tips

| | |
|--|-----------------------|
| Loading gels | 19, 21, 30, 31, 35–45 |
| PCR work | 19, 21, 30, 31 |
| DNA sample removal | 19, 21, 30, 31 |
| Feed hybridomas | 19, 21, 30, 31, 35–45 |
| Protein assays | 19, 21, 30, 31, 35–45 |
| Lipid extractions | 19, 21, 30, 31, 35–45 |
| Atomic absorption spectroscopy-reagent prep | 19, 21, 30, 31, 35–45 |
| Dropwise additions to culture plates | 19, 21, 30, 31 |

Eliminate steps—large bulb, narrow stem, SEDI-PET pipettes

| | |
|--|----------------|
| Reaction chamber | 16, 30, 31, 32 |
| Storage ampule | 16, 30, 31, 32 |
| Portable aliquoting | 16, 30, 31, 32 |
| Pre-mix, collect, heat-seal, freeze, store, or incubate and dispense: | 16, 30, 31, 32 |
| - Reagents buffer solutions | |
| - Protozoa, nematode larvae, marine eggs, seeds | |
| - Anti-serum urine | |

Industrial, research, and testing applications

Top 13 pipettes:
5, 11, 13, 15, 16, 17, 19, 20, 21, 27, 32, 33, 34

Chromatography

Sample preparation for: LC, GC, HPLC, TLC

| | |
|---|----------------------------|
| Using 1 mL auto-sampler vials | 11, 12, 19, 20, 21, 22, 31 |
| Using 2 mL auto-sampler vials | 13, 21 |
| Layering in columns / transfers in columns | 33, 34 |
| Loading gels | 19, 22 |

Viscous liquid samples and transfers

| | |
|---------------------|---------------|
| Creams | 9, 10, 26, 27 |
| Oils | 9, 10, 26, 27 |
| Perfumes | 9, 26, 27 |
| Beverages | 9, 10, 26, 27 |
| Industrial slurries | 9, 10, 26, 27 |
| Food | 9, 10, 26, 27 |

Field testing

| | |
|---------------------------------|--------|
| Water sampling | 31, 34 |
| Pre-filled with KCl and buffers | 31, 34 |

pH meter maintenance

| | |
|--|----|
| Adding acids or bases | 11 |
| Remove and replace electrode fill solutions | 17 |

Spectrophotometry cuvettes

| | |
|--|----|
| Reaches bottom of semi-microcuvettes; will not scratch expensive glass or quartz cells | 32 |
|--|----|

Reagent handling

| | |
|----------------------|------------------------|
| Portable ampule | 31, 32 |
| Spreading and mixing | 24, 25, 26 |
| Slide tests | 13, 14, 15, 16, 17, 25 |

Research applications

Top 13 pipettes:
8, 9, 15, 16, 17, 20, 24, 25, 26, 31, 32, 33, 34

Blood banking

| | |
|--|-------------------------------|
| Rapid transfers (3.5 cc in one squeeze) | 3, 4, 6, 7, 8, 10, 14, 15, 16 |
| Narrow barrel fits tubes and donor bag tubing | 3, 4, 6, 7, 8, 10, 14, 15, 16 |
| Controlled drop size | 7, 8, 15 |
| Calibrated transfers | 7, 8, 15 |

Remove, dispense small volumes

| | |
|--|-----------------------------|
| Remove and separate serum and blood | 17, 20, and other fine tips |
| Dispense small drops - Small samples - Load hemocytometers | 17, 20, and other fine tips |
| Transfer in and out of multi-well plates | 17, 20, and other fine tips |

Sedimentation and storage

| | |
|---|--------------------------|
| Sedimentation | 29, 31 |
| Access to Wintrobe tubes | 31 |
| Fill, heat-seal, and store or aliquot reagents, anti-serum, urine, etc. | 2, 6, 13, 16, 27, 31, 32 |

Bottle sampling

| | |
|-----------------|--------|
| Culture bottles | 33, 34 |
|-----------------|--------|

Slides

| | |
|-------------------------|------------|
| Smear samples | 24, 25, 26 |
| Mix and spread reagents | 24, 25, 26 |

Funnels/filters/scoops

| | |
|------------------------------------|-------|
| Cut bulb in half and insert filter | 9, 27 |
| Cut bulb at angle for scoop | 9, 27 |


General purpose transfer pipettes

- Low-affinity surface reduces cell loss or protein binding
- Ideal for tissue culture, blood culture, and urine analysis
- Single-piece tool eliminates the need for plugging, packaging, and autoclaving while reducing cross-contamination

General purpose and Thermo Scientific™ B/B-Pet™ pipettes

| Key | Product description | Length (cm) | Stem diameter (mm) | Overall capacity (mL) | Bulb draw (mL) | Drops per mL | Quantity per pack | Quantity per case | Sterile pipettes | | Cat. No. |
|-----|------------------------------|-------------|--------------------|-----------------------|----------------|--------------|-------------------|-------------------|----------------------|-------------|----------|
| | | | | | | | | | Individually wrapped | 20 per pack | |
| 1 | General Purpose Standard | 15.6 | 7.9 | 7.7 | 3.0 | 21 | 500 | 5,000 | 202-1S | 202-20S-4 | 202 |
| 2 | General Purpose Large Bulb | 15.1 | 6.1 | 8.6 | 4.7 | 21 | 400 | 4,000 | 204-1S | 204-20S | 204 |
| 3 | General Purpose Small Bulb | 12.7 | 2.5 | 13.7 | 7.4 | 24 | 500 | 5,000 | * | * | 325-11 |
| 4 | General Extra Small Bulb | 7.2 | 3.3 | 0.6 | 0.3 | * | 500 | 4,000 | * | * | 281NL |
| 5 | General Purpose 3" | 8.7 | 4.8 | 1.8 | 0.9 | 26 | 500 | 4,000 | 273-1S | 273-20S | 273 |
| 6 | General Purpose 4" | 10.3 | 2.5 | 3.1 | 2.2 | 22 | 400 | 4,000 | * | * | 334-11 |
| 7 | General Purpose 5" | 12.9 | 6.6 | 7.5 | 2.8 | 24 | 400 | 4,000 | 335-1S | 335-20S | 335 |
| 8 | General Purpose 6" | 15.4 | 6.6 | 4.9 | 1.8 | 24 | 500 | 5,000 | 336-1S | 336-20S | 336 |
| 8 | 62 µL Large Aperture Pipette | 13.7 | 6.1 | 9.5 | 6.2 | 20 | 250 | 2,500 | 691-1S | 691-20S | 691 |
| 10 | General Purpose Beral | 14.5 | 2.8 | 5.5 | 2.4 | 22 | 500 | 5,000 | * | * | B75-100 |

* Not standard; sterile product available upon request.




Graduated transfer pipettes

- Can be frozen in liquid nitrogen or heat-sealed for storage
- Graduation marks allow multiple allocations in a single draw
- Accurately measure more than one volume, with graduation marks in intervals of 0.1 mL, 0.25 mL, or 1 mL available

Graduated pipettes

| Key | Product description | Length (cm) | Stem diameter (mm) | Overall capacity (mL) | Bulb draw (mL) | Drops per mL | Quantity per pack | Quantity per case | Sterile pipettes | | Cat. No. |
|-----|---------------------------|-------------|--------------------|-----------------------|----------------|--------------|-------------------|-------------------|----------------------|-------------|----------|
| | | | | | | | | | Individually wrapped | 20 per pack | |
| 11 | Graduated 1 mL Small Bulb | 14.0 | 4.7 | 3.9 | 2.1 | 25 | 500 | 5,000 | 212-1S-4 | 212-20S | 212 |
| 12 | Graduated 1 mL Large Bulb | 15.5 | 4.6 | 5.8 | 3.5 | 25 | 500 | 5,000 | 222-1S-4 | 222-20S-4 | 222 |
| 13 | Graduated 3 mL Large Bulb | 15.5 | 7.9 | 7.7 | 3.2 | 21 | 500 | 5,000 | 225-1S | 225-20S-4 | 225 |
| 14 | Graduated 1 mL Large Bulb | 15.2 | 2.8 | 5.8 | 4.3 | 20 | 500 | 5,000 | * | * | 718 |
| 15 | Graduated 2 mL | 15.2 | 7.1 | 4.6 | 1.8 | 25 | 500 | 5,000 | 274-1S | 274-20S | 274 |
| 16 | Graduated 5 mL Large Bulb | 21.7 | 3.0 | 13.7 | 7.4 | 19 | 250 | 2,500 | 728NL-1S | 728NL-20S | 728NL |
| 17 | Graduated 0.3 mL | 11.6 | 3.0 | 1.5 | 0.8 | 22 | 500 | 4,000 | 282-1S-4 | 282-20S | 282 |

* Not standard; sterile product available upon request.




Thermo Scientific™ Samco™ Fine Tip Transfer Pipettes

- Precise dispensing of small drops
- Elongated tips allow greater control when using small-volume containers
- Ideal for loading gels, PCR work, and sample removal

Fine tip pipettes

| Key | Product description | Length (cm) | Stem diameter (mm) | Overall capacity (mL) | Bulb draw (mL) | Drops per mL | Quantity per pack | Quantity per case | Sterile pipettes | | Cat. No. |
|-----------|------------------------------|-------------|--------------------|-----------------------|----------------|--------------|-------------------|-------------------|----------------------|-------------|----------|
| | | | | | | | | | Individually wrapped | 20 per pack | |
| 18 | Fine Tip Standard | 14.7 | 4.6 | 5.8 | 3.3 | 53 | 500 | 5,000 | 232-1S | 232-20S | 232 |
| 19 | Fine Tip Large Bulb | 14.7 | 6.1 | 8.9 | 4.8 | 45 | 400 | 4,000 | 234-1S-4 | 234-20S | 234 |
| 20 | Extended Fine Tip Small Bulb | 10.4 | 3.0 | 1.7 | 1.0 | 48 | 400 | 3,200 | 231-1S | 231-20S | 231 |
| 21 | Extended Fine Tip Large Bulb | 15.3 | 3.0 | 5.4 | 3.1 | 50 | 250 | 2,000 | 235-1S | 233-20S | 233 |
| 22 | Extended Fine Tip Standard | 15.7 | 4.6 | 5.8 | 3.7 | 50 | 500 | 5,000 | 235-1S | 235-20S | 235 |
| 23 | Fine Tip Small | 5.1 | 1.2 | 1.6 | 1.0 | 34 | 500 | 4,000 | — | — | 243 |



Special purpose

- **Thermo Scientific™ Padl-Pet™ transfer pipettes** have a fin on top of the squeeze bulb, ideal for smearing, mixing, and spreading reagents after dispensing liquids
- **Slurry transfer pipettes** have a tip diameter that is double the size of the standard transfer pipettes, ideal for viscous liquids
- **Narrow stem pipettes** can be bent to access narrow openings and small tube diameters
- **Extra long pipettes** are ideal for reaching into large bottles and containers

Special purpose and Padl-Pet pipettes

| Key | Product description | Length (cm) | Stem diameter (mm) | Overall capacity (mL) | Bulb draw (mL) | Drops per mL | Quantity per pack | Quantity per case | Sterile pipettes | | Cat. No. |
|-----|-------------------------------|-------------|--------------------|-----------------------|----------------|--------------|-------------------|-------------------|----------------------|-------------|----------|
| | | | | | | | | | Individually wrapped | 20 per pack | |
| 24 | Padl-Pet 25 µL Drop Size | 13.1 | 3.8 | 1.0 | 0.2 | — | 500 | 4,000 | * | * | 292 |
| 25 | Padl-Pet 30 µL Drop Size | 13.0 | 3.8 | 1.0 | 0.2 | — | 500 | 4,000 | * | * | 293 |
| 26 | Padl-Pet 50 µL Drop Size | 12.4 | 3.6 | 0.8 | 0.2 | — | 500 | 4,000 | * | * | 295 |
| 27 | Samco Slurry Transfer Pipette | 13.2 | 5.1 | 7.5 | 3.3 | 13 | 450 | 4,500 | * | * | 993 |


Narrow stem Thermo Scientific™ SEDI-PET™ and Q-Pet™ pipettes

| Key | Product description | Length (cm) | Stem diameter (mm) | Overall capacity (mL) | Bulb draw (mL) | Drops per mL | Quantity per pack | Quantity per case | Sterile pipettes | | Cat. No. |
|-----|--------------------------------|-------------|--------------------|-----------------------|----------------|--------------|-------------------|-------------------|----------------------|-------------|----------|
| | | | | | | | | | Individually wrapped | 20 per pack | |
| 28 | SEDI-PET Short Stem | 6.4 | 2.5 | 1.3 | 0.8 | 26 | 500 | 4,000 | 241-1S | 241-20S | 241 |
| 29 | SEDI-PET Short Stem Large Bulb | 8.5 | 2.5 | 4.3 | 3.1 | 24 | 500 | 5,000 | 242-1S | 242-20S | 242 |
| 30 | SEDI-PET Standard | 15.5 | 2.5 | 4.5 | 3.3 | 26 | 500 | 5,000 | 251-1S | 251-20S | 251 |
| 31 | SEDI-PET Large Bulb | 15.5 | 3.0 | 15.3 | 11.6 | 19 | 250 | 2,500 | 252-1S | 252-20S | 252 |
| 32 | Q-Pet Transfer Pipette | 15.5 | 8.0 | 6.9 | 3.2 | 31 | 500 | 5,000 | 694-1S | * | 694 |

Extra long pipettes

| Key | Product description | Length (cm) | Stem diameter (mm) | Overall capacity (mL) | Bulb draw (mL) | Drops per mL | Quantity per pack | Quantity per case | Sterile pipettes | | Cat. No. |
|-----|---------------------|-------------|--------------------|-----------------------|----------------|--------------|-------------------|-------------------|----------------------|-------------|----------|
| | | | | | | | | | Individually wrapped | 20 per pack | |
| 33 | Extra Long 9" | 22.5 | 5.0 | 5.6 | 2.3 | 25 | 400 | 4,000 | 262-1S | 262-20S | 262 |
| 34 | Extra Long 12" | 30.0 | 8.6 | 24.1 | 10.7 | 20 | 100 | 1,000 | 263-1S | 263-20S | 263 |

* Not standard; sterile product available upon request.




Exact Volume** pipettes

- Polyethylene
- Useful for small samples or dispensing reagents
- Ideal for home and point-of-care (POC) testing with validated applications
- OEM applications
- Custom design options available to meet your exact specifications

Exact Volume** pipettes

| Key | Product description | Length (cm) | Stem diameter (mm) | Dispense volume (mL) | Quantity per pack | Quantity per case | Cat. No. |
|-----|---------------------|-------------|--------------------|----------------------|-------------------|-------------------|----------|
| 35 | Exact Volume** | 10.6 | 3.8 | 400 | 500 | 5,000 | 967NL |
| 36 | Exact Volume** | 10.2 | 3.0 | 250 | 500 | 5,000 | 191NL |
| 37 | Exact Volume** | 8.89 | 3.0 | 200 | 500 | 5,000 | 941NL |
| 38 | Exact Volume** | 9.5 | 3.6 | 300 | 500 | 5,000 | 966NL |
| 39 | Exact Volume** | 8.0 | 3.0 | 150 | 500 | 5,000 | 788NL |
| 40 | Exact Volume** | 8.3 | 2.5 | 100 | 500 | 5,000 | 787NL |
| 41 | Exact Volume** | 7.5 | 2.5 | 80 | 500 | 5,000 | 786NL |
| 42 | Exact Volume** | 6.5 | 2.5 | 60 | 500 | 5,000 | 785NL |
| 43 | Exact Volume** | 5.9 | 2.5 | 50 | 500 | 5,000 | 930NL |
| 44 | Exact Volume** | 5.9 | 2.3 | 40 | 500 | 5,000 | 784NL |
| 45 | Exact Volume** | 5.3 | 2.0 | 20 | 500 | 5,000 | 783NL |

** Exact Volume is the name of this group of transfer pipettes. These conveniently dispense a precise volume within a tolerance range.





Capillary transfer pipettes

- Rapid, automatic fill with no bubbles
- Suited for collecting and dispensing microliter-scale liquid samples
- No anticoagulants or bulky plungers are required because collection and dispensing occurs within seconds
- For horizontal use only

Capillary transfer pipettes

| Key | Product description | Stem length (cm) | Stem diameter (mm) | Dispense volume (mL) | Quantity per pack | Quantity per case | Cat. No. |
|-----|--|------------------|--------------------|----------------------|-------------------|-------------------|----------|
| 46 | Samco Capillary Transfer Pipette, 50 μ L | 3.87 | 2.34 | 50 | 500 | 5,000 | 1029-100 |
| 47 | Samco Capillary Transfer Pipette, 25 μ L | 2.26 | 2.34 | 25 | 500 | 5,000 | 1028-100 |





Learn more at thermofisher.com/transferpipettes

thermo scientific

This product is intended for General Laboratory Use. It is the customer's responsibility to ensure that the performance of the product is suitable for customers' specific use or application. © 2015–2022 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified. COL35241 1022