Thermo Scientific FH 62 C14 Continuous Particulate Monitor

Continuous, real-time measurement

The Thermo Scientific™ FH 62 C14
Continuous Particulate Monitor
measures the mass concentration of
suspended particulate matter (e.g., PM
Coarse, PM10, PM2.5, PM1 and TSP)
and by use of beta attenuation.

- Continuous, real-time measurement by a C14 monitor
- Radon gas activity measurement eliminates interference of natural airborne radioactivity
- Control and data exchange over two serial interfaces possible
- Storage of half-hour average concentrations over a whole year
- Insensitive to vibration and diurnal temperature





In addition, the ambient radioactive influence of natural Radon (Rn-222) gas is measured as a refinement step toward better sensitivity at lower ambient particulate concentrations.

The particulate sample collection area of the FH 62 C14 monitor is located between both the C14 source and the proportional detector.

While ambient particulate matter is being deposited onto a filter tape sample spot, the dynamic filter loading is measured continuously by the attenuation of the C14 source beta rays. As a result, a continuous, real-time measurement of airborne particulate is provided. It is not necessary to move the filter spot from the sample position to the detector position for zero and mass determination.

Additional features of the FH 62 C14 monitor include:

- User selectable reporting of mass concentration based on standard or actual flow rate
- processor-controlled calibration of all sensors.



Thermo Scientific FH 62 C14 Continuous Particulate Monitor

Measuring Principle	Continuous and simultaneous particulate collection through beta ray attenuation
Source	Carbonium-14 (C14) < 3.7MBq (<100μCi)
Ranges	0 to 5,000μg/m3 or 0 to 10,000μg/m3
Minimum detection limit	<1 μg/m3 (24-hour average); <4 μg/m3 (1-hour average)
Precision of two monitors	± 2 μg/m3 (24-hour)
Resolution	± 1 μg/m3 (instantaneous)
Correlation coefficiant	R > 0.98
Measurement cycle	Single filter spot in position for 24 hours (default); user selectable 30-minutes to 24 hours
Data averages	Each full 1/2, and 24 hour values automatically stored; each full 1/2, 1, 3 and 24 hour
Air flow rate	1 m3/h (16.67 lpm) measured across an internal subsonic orifice; user selectable from 0 to 20 lpm
Sample Flow Rate	0.6 liters/min.
Operating temperature	-22 to 140°F (-30 to 60°C)
Output	Serial interface RS 232 Analog output: 4-20mA or 0-10V output of concentration (µg/m3)
Power Requirements	Instrument: 100-240V, 50/60Hz, 330W max., 15W without pump or heater Pump: 100-110/100-120V, 50/60Hz or 220/240V, 50/60Hz, 100W
Dimensions	Instrument: 19" (W) x 12.25" (H) x 13" (D) / 483mm (W) x 311mm (H) x 330mm (D) Pump: 8.25" (W) x 8.75" (H) x 4.25" (D) / 210mm (W) x 222mm (H) x 108mm (D)
Weight	Instrument: 50 lbs (22.5 kg) / Pump: 18 lbs (8.16 kg)
Approvals and Certifications	Approved to meet U.S. EPA Equivalent PM10 Method (EQPM-1102-150) and the CARB California Approved Sampler (CAS) for PM10 and PM2.5

Additional Information

Optional Accessories

- · Adjustable tube heaters
- Analog I/O expansion board
- TSP or PM10 Inlets
- Mass & Flow Rate calibration Kkits
- WINS Impactor, Sharp-Cut Cyclone & Very Sharp-Cut Cyclone for PM2.5

To maintain optimal product performance, you need immediate access to experts worldwide, as well as priority status when your air quality equipment needs repair or replacement. We offer comprehensive, flexible support solutions for all phases of the product life cycle. Through predictable, fixed-cost pricing, our services help protect the return on investment and total cost of ownership of your Thermo Scientific products.

For more information, visit our website at thermoscientific.com/air

© 2013 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representative for details.

This product is manufactured in a plant whose quality management system is ISO 9001 certified.

USA

27 Forge Parkway Franklin, MA 02038 Ph: (866) 282-0430 Fax: (508) 520-1460 customerservice.aqi@thermofisher.com

India

C/327, TTC Industrial Area MIDC Pawane New Mumbai 400 705, India Ph: +91 22 4157 8800 india@thermofisher.com

China

+Units 702-715, 7th Floor Tower West, Yonghe Beijing, China 100007 +86 10 84193588 info.eid.china@thermofisher.com

Europe

Takkebijsters 1 Breda Netherlands 4801EB +31 765795641 info.aq.breda@thermofisher.com

