

<u>Data Sheet</u> GeneChip® Tomato Genome Array

The GeneChip® Tomato Genome Array is designed specifically to monitor gene expression in tomato (Solanum lycopersicum, formerly Lycopersicon esculentum). The comprehensive array consists of more than 10,000 S. lycopersicum probe sets to interrogate more than 9,200 S. lycopersicum transcripts. The Tomato Genome Array is particularly useful for agricultural researchers studying tomato genetics.

This array was created in collaboration with leading tomato researchers through the Affymetrix GeneChip® Consortia Program and was designed based on content from UniGene and GenBank® mRNAs.

Applications

Tomato is an important food crop worldwide. Many research programs utilize genomic approaches to aid selective breeding programs to identify the underlying genetic mechanisms that are important for high crop yield, resistance to diseases and insects, and response to environmental factors that influence the productive growing areas for tomato plants. The Tomato Genome Array is a tool that enables researchers to elucidate these complex genetic traits in the tomato plant to determine how crop production can be improved.

Array profile

The GeneChip Tomato Genome Array is a 169-format, 11 µm array design and contains 11 probe pairs per probe set. The sequence information for this array was selected from public data sources including UniGene and GenBank mRNAs.

The array contains more than 10,000 S. lycopersicum probe sets to monitor gene expression for more than 9,200 S. lycopersicum genes.

Instrument/software requirements

- GeneChip® Scanner 3000
- Affymetrix® GeneChip® Command Console® Software (AGCC)

Specifications

Number of probe sets	10,038 tomato probe sets + 11 tomato control probe sets	
Number of transcripts	9,254 tomato transcripts + 10 tomato control transcripts	
UniGene clusters	~4,600 tomato UniGene 3' clusters ~3,400 tomato non-UniGene clusters	
Number of arrays in set	One	
Array format	169	
Feature size	11 μm	
Oligonucleotide probe length	25-mer	
Probe pairs per sequence	11	
Hybridization controls	bioB, bioC, bioD from Escherichia coli and cre from P1 bacteriophage	
Poly-A controls	dap, lys, phe, thr, trp from Bacillus subtilis	
Housekeeping/control genes	beta-actin, elongation factor 1, GAPDH Test3 controls: 17S rRNA, 25S rRNA, glutathione S-transferase, phytochrome B2, ubiquitin	
Detection sensitivity	1:100,000*	

^{*}As measured by detection in comparative analysis between a complex target containing spiked control transcriptions and a complex target with no spikes.



Ordering information

Part number	Description	
GeneChip® Tomato Genome Array		
900737	Contains 2 arrays	
900738	Contains 6 arrays	
900739	Contains 30 arrays	

Supporting products

Part number	Description
GeneChip® 3' IVT Express Kit	
901228	10 reactions
901229	30 reactions

Affymetrix, Inc. Tel: +1-888-362-2447 Affymetrix UK Ltd. Tel: +44-(0)-1628-552550 Affymetrix Japan K.K. Tel: +81-(0)3-6430-4020 Panomics Products Tel: +1-877-PANOMICS www.panomics.com • USB Products Tel: +1-800-321-9322 www.usb.affymetrix.com

www.affymetrix.com Please visit our website for international distributor contact information.

For Research Use Only. Not for use in diagnostic procedures.