



Mouse IL-10 Antibody Bead Kit

INFORMATION SHEET

Catalog #: LMC0101 Description: Mouse IL-10 Lot:* 408775

*Note: A letter at the end of the lot number signifies an additional packaging of this same lot.

Intended Use

This reagent set comprises the analyte specific components for the measurement of mouse IL-10 in serum, plasma, or tissue culture supernatant. The assay may be run alone or in combination with other Antibody Bead Kits from Invitrogen. Buffer reagents needed to complete the reaction are sold separately under Catalog #LMB0001. These reagents are intended for use in the **Luminex® 100™ or 200™ System** only. **This kit is configured for research use only and is not to be used in diagnostic procedures.**

Reagents Provided

1. Antibody Bead Concentrate (10x):

Catalog #: LM0092 Description: Rat x Ms IL-10 Lot: 408778 Size: 0.25 mL-100 tests

Bead Region: 9

Form: 0.25 mL 10x bead concentrate solution in storage buffer. Contains 7.5 mM sodium azide as preservative.

Storage: **Light-sensitive material.** Store at 2 to 8°C in the dark, until the expiration date indicated on the kit.

2. Biotinylated Antibody Concentrate (10x):

Catalog #: BN0092 Description: Rat x Ms IL-10 biotin Lot: 408779 Size: 1 mL-100 tests

Form: 1 mL of a 10x stock of Biotinylated Antibody Concentrate in Biotin Diluent. Contains 15 mM sodium azide as preservative. Concentration of antibody is matched to this lot of beads. Do not mix lots of Coated Beads and Detection Antibody.

Storage: Store at 2 to 8°C until the expiration date indicated on the kit.

3. Ms Th1/Th2 Standard (IL-2, IL-4, IL-5, IL-10, IL-12, IFN-γ) (2 vials):

Catalog #: SM002 Description: Rec. Ms Th1/Th2 Std. Lot: 310669 Size: Single use

Form: Lyophilized. The proteins in this standard have been calibrated against the mass of highly purified recombinants. See the Product Insert included in the Buffer Reagent Kit for further information.

Storage: Store at 2 to 8°C. Use within 1 hour after reconstitution. Discard immediately after use.

Concentration of Reconstituted Standards**:

IL-2 (2,624 pg/mL)	IL-4 (13,900 pg/mL)
IFN-γ (4,750 pg/mL)	IL-5 (6,620 pg/mL)
IL-10 (13,940 pg/mL)	IL-12 (13,700 pg/mL)

****Important note: The concentrations of reconstituted standards are lot-specific. Please verify all concentration values entered in data analysis software.**

Reconstitution: Reconstitute with 1 mL Assay Diluent when measuring IL-10 in serum or plasma samples. For other sample types, such as tissue culture supernatants, reconstitute the standard in 1 mL of a solution consisting of 50% Assay Diluent + 50% sample matrix. Allow standard to rehydrate for approximately 10 minutes before further dilution.

Recommended Starting Concentration for Standard Curve: Upon reconstitution, the starting concentration of standards is the value cited above. Make serial 1:3 dilutions in Assay Diluent (serum/plasma samples) or other appropriate matrix. Use 100 µL per assay. If establishing a Multiplex Assay, this same standard can be used to measure the other related cytokines cited above in a Multiplex Assay format. See the Product Insert included in the Buffer Reagent Kit for further information.

This product is for research use only. Not for use in diagnostic procedures.

www.invitrogen.com

Invitrogen Corporation • 542 Flynn Rd • Camarillo • CA 93012 • Tel: 800.955.6288 • E-mail: techsupport@invitrogen.com

PILMC0101 (Rev 09/08)

(Page 1 of 2) DCC-08-1089/1288



Important Licensing Information - These products may be covered by one or more Limited Use Label Licenses (see the Invitrogen Catalog or our website, www.invitrogen.com). By use of these products you accept the terms and conditions of all applicable Limited Use Label Licenses. Unless otherwise indicated, these products are for research use only and are not intended for human or animal diagnostic, therapeutic or commercial use.

Mouse IL-10 Antibody Bead Kit

INFORMATION SHEET

Performance Characteristics

Analytical Sensitivity: The minimum detectable dose of Ms IL-10 is <15 pg/mL. This was determined by adding two standard deviations to the mean FI obtained when the zero standard was assayed 30 times.



Typical Standard Curve

Specificity: Buffered solutions of a panel of substances at 10 or 20 ng/mL were assayed with the Invitrogen Mouse IL-10 Antibody Bead kit. The following substances were tested and all were found to have no cross-reactivity: mouse IL-1 β , IL-2, IL-3, IL-4, IL-5, IL-6, GM-CSF, IFN- γ , MCP-1, TNF- α ; rat IL-2, IL-4, IFN- γ .

Precision:

	Intra-assay	Inter-assay
Mean (pg/mL)	6750	6950
SD	420	450
%CV	6.2	6.5

Linearity: Mouse serum and tissue culture medium containing 10% fetal calf serum were spiked with mouse IL-10 and serially diluted in Assay Diluent and a solution consisting of 50% Assay Diluent and 50% tissue culture medium containing 10% fetal calf serum, respectively, over the range of the assay. Linear regression analysis of samples versus the expected concentrations yielded a correlation coefficient of 0.99 for both serum and tissue culture.

Recovery: Mouse serum averaged 87% (range: 79% to 93%). Mouse EDTA plasma averaged 110% (range: 103% to 123%); citrate plasma averaged 95% (range: 90% to 106%). Tissue culture medium containing 10% fetal calf serum averaged 100% (range: 95% to 105%).

Correlation to ELISA: A correlation coefficient of 0.95 was calculated when values for tissue culture samples, obtained with the Mouse IL-10 Antibody Bead Kit, were compared to the Invitrogen ELISA for Mouse IL-10 (cat.# KMC0101, KMC0102). Mouse IL-10 Antibody Bead Kit \times 2.2 = Mouse IL-10 ELISA. Correlation of results obtained with the Mouse IL-10 Antibody Bead Kit to one's own system should be determined to arrive at an appropriate multiplication factor.

By purchasing this Kit, which contains fluorescently labeled microsphere beads authorized by Luminex® Corporation ("Luminex®"), you, the customer, acquire the right under Luminex's patent rights to use this Kit or any portion of this Kit, including without limitation the microsphere beads contained herein, only with Luminex's laser based fluorescent analytical test instrumentation marketed under the name Luminex® 100™ or 200™. This product is covered by one or more of the following U.S. patents: 6,046,807.

This product is for research use only. Not for use in diagnostic procedures.

www.invitrogen.com

Invitrogen Corporation • 542 Flynn Rd • Camarillo • CA 93012 • Tel: 800.955.6288 • E-mail: techsupport@invitrogen.com

PILMC0101 (Rev 09/08)

(Page 2 of 2) DCC-08-1089/1288

Important Licensing Information - These products may be covered by one or more Limited Use Label Licenses (see the Invitrogen Catalog or our website, www.invitrogen.com). By use of these products you accept the terms and conditions of all applicable Limited Use Label Licenses. Unless otherwise indicated, these products are for research use only and are not intended for human or animal diagnostic, therapeutic or commercial use.