

# PureLink™ Microbiome DNA Purification Kit

Purification of high-quality microbial and host DNA from stool samples

Catalog Number A29790

Pub. No. MAN0014266 Rev. A.0

**WARNING!** Read the Safety Data Sheets (SDSs) and follow the handling instructions. Wear appropriate protective eyewear, clothing, and gloves. Safety Data Sheets (SDSs) are available from [thermofisher.com/support](http://thermofisher.com/support).

## Product description

The Invitrogen™ PureLink™ Microbiome DNA Purification Kit enables fast purification of high-quality microbial and host DNA from a wide variety of sample types. The kit uses proven PureLink™ spin-column technology for robust yields of purified DNA that is ready for downstream PCR, sequencing, or other applications.

Typical DNA recovery is 5–25 µg from 0.2 g of human stool or 0.1 g of mouse or rat stool.

## Procedure overview

This guide describes purification of microbial and host DNA from stool samples. (For purification of host DNA from stool samples, refer to Pub. no. MAN0014334.) In this procedure, the microorganisms are efficiently lysed by a combination of heat, chemical, and mechanical disruption with specialized beads. Inhibitors are eliminated by precipitation using a proprietary cleanup buffer. The sample is then applied to a PureLink™ spin column, and the DNA that is bound to the column undergoes a single wash step before elution.

## Kit contents

**Table 1** PureLink™ Microbiome DNA Purification Kit (Cat. no. A29790, 50 reactions)

| Component                                    | Quantity | Storage      |
|----------------------------------------------|----------|--------------|
| S1—Lysis Buffer                              | 40 mL    | 15°C to 30°C |
| S2—Lysis Enhancer                            | 5 mL     |              |
| S3—Cleanup Buffer                            | 12.5 mL  |              |
| S4—Binding Buffer                            | 45 mL    |              |
| S5—Wash Buffer Concentrate <sup>[1]</sup>    | 13 mL    |              |
| S6—Elution Buffer                            | 5 mL     |              |
| PureLink™ Spin Columns with Collection Tubes | 50       |              |

| Component                  | Quantity | Storage      |
|----------------------------|----------|--------------|
| PureLink™ Collection Tubes | 100      | 15°C to 30°C |
| Bead Tubes <sup>[2]</sup>  | 50       |              |

<sup>[1]</sup> Add 13 mL of 96–100% ethanol before use. See “Before you begin” on page 2.

<sup>[2]</sup> Ships separately.

## Required materials

Unless otherwise indicated, all materials are available through [thermofisher.com](http://thermofisher.com). MLS: Fisher Scientific ([www.fisherscientific.com](http://www.fisherscientific.com)) or other major laboratory supplier.

**Table 2** Required materials not included with the kit

| Item                                                                                                  | Source                                     |
|-------------------------------------------------------------------------------------------------------|--------------------------------------------|
| Heat block, dry bath, or water bath, 65°C                                                             | MLS                                        |
| (Optional) For dry bath, Lab Armor™ Beads                                                             | Cat. no. A12543                            |
| Microcentrifuge capable of 14,000 × g                                                                 | MLS                                        |
| Vortex mixers, 2 <sup>[1]</sup>                                                                       | MLS                                        |
| For vortex bead homogenization: hands-free adapter for vortex mixer, with horizontal tube orientation | Fisher Scientific NC0070788 <sup>[2]</sup> |
| (Optional; alternative to vortex bead homogenization) Bead mill homogenizer                           | Omni 19-040, or equivalent                 |
| Adjustable pipettors, 100–1000 µL                                                                     | MLS                                        |
| Microcentrifuge tubes, DNase-free, 1.5 mL or 2.0 mL                                                   | MLS                                        |
| Ethanol, 96–100%                                                                                      | MLS                                        |


<sup>[1]</sup> For vortex bead homogenization: we recommend using two mixers, one dedicated to the hands-free adapter.

<sup>[2]</sup> Cat. no. AM10024 (not available for sale) can also be used.

**Table 3** Additional materials required for stool samples

| Item                        | Source                                      |
|-----------------------------|---------------------------------------------|
| Corning™ Microspatula #3013 | Fisher Scientific 14-245-102, or equivalent |
| Laboratory scale            | MLS                                         |

## Workflow



## Important procedural guidelines

### Sample input requirements and handling

- Collect stool samples according to your laboratory guidelines and experimental needs.
- Depending on the size of the feces, mix stool samples thoroughly to create a homogenous sample before weighing and transferring a portion to the Bead Tube. Thorough mixing is important for detection of certain microorganisms that concentrate in fecal material adjacent to the intestinal wall or around food debris.

The Corning™ Microspatula is recommended because it is sturdy enough for sample mixing, and it fits the opening of the Bead Tube.

- Recommended input amount:

| Source                                 | Amount <sup>[1]</sup> |
|----------------------------------------|-----------------------|
| Human or other medium to large animals | 0.2±0.05 g            |
| Rodent or other small animals          | 0.1±0.05 g            |

<sup>[1]</sup> Do not exceed 0.25 g.

- Ensure that samples are mixed thoroughly with S1—Lysis Buffer and S2—Lysis Enhancer to create a homogenous sample.

One way to ensure thorough mixing is to vortex the tube with the cap down.

## Alternatives to the optimized procedure

- This procedure is optimized for homogenization by bead beating on the vortex mixer with horizontal agitation. This is a cost-effective method for recovery of high-quality microbial DNA. Ensure that the vortex adapter enables horizontal agitation; adapters with a vertical tube orientation may not agitate adequately.

**Note:** Balance the vortex adapter to ensure proper movement of the adapter and optimal homogenization.

If you use a bead mill homogenizer, follow the manufacturer's instructions to optimize sample disruption.

- This procedure is optimized for centrifugations at 14,000 × g. The PureLink™ Spin Columns with Collection Tubes can withstand up to 16,000 × g.

If your microcentrifuge is not capable of 14,000 × g, adjust the centrifugation times to ensure that all of the sample passes through the column.

## Options for elution

- The DNA can be eluted from the column with 50–200 μL of S6—Elution Buffer, to optimize the concentration of the recovered DNA.
- Two sequential elution steps with S6—Elution Buffer might increase the yield slightly. For example, for a total elution volume of 100 μL, either:
  - Perform two sequential elution steps with 50 μL of S6—Elution Buffer, or
  - Perform the first elution step with 100 μL of S6—Elution Buffer, then apply the flow-through (containing the eluted DNA) to the same column and repeat for a second elution.
- If desired, perform the final elution spin into nuclease-free 1.5-mL microcentrifuge tubes, instead of the collection tubes supplied with the kit, which do not have caps. Position the cap of the microcentrifuge tubes opposite the direction of rotation.

## Before you begin

### Before first use of the kit: prepare S5—Wash Buffer

Add 13 mL of 96–100% ethanol to S5—Wash Buffer Concentrate, mix well, and store at room temperature.

### Before each use of the kit

If precipitate is visible in S1—Lysis Buffer or S4—Binding Buffer, warm the buffers at 37°C for 5 minutes and shake well to dissolve the precipitate.

## Methods

Perform the procedure at room temperature (20–25°C), unless otherwise indicated.

### 1 Prepare the lysate

- a. Add sample and S1—Lysis Buffer to the Bead Tube, according to the sample source.

| Source                                 | Sample     | S1—Lysis Buffer <sup>[1]</sup> |
|----------------------------------------|------------|--------------------------------|
| Human or other medium to large animals | 0.2±0.05 g | 600 µL                         |
| Rodent or other small animal           | 0.1±0.05 g | 700 µL                         |

<sup>[1]</sup> Adjust the volume of S1—Lysis Buffer to bring the total mixture to ~800 µL.

- b. Cap securely, then vortex.  
Ensure that the sample is thoroughly dispersed in the liquid.
- c. Add 100 µL of S2—Lysis Enhancer, cap securely, and vortex briefly.
- d. Incubate at 65°C for 10 minutes.
- e. Homogenize by bead beating for 10 minutes at maximum speed on the vortex mixer.  
Use the hands-free adapter and horizontal agitation.
- f. Centrifuge at 14,000 × g for 5 minutes.
- g. Transfer up to 400 µL of the supernatant to a clean microcentrifuge tube.

---

**IMPORTANT!** A layer of debris may be present on top of the bead pellet. Avoid transfer of this debris with the supernatant.

---

- h. Add 250 µL of S3—Cleanup Buffer, and vortex immediately.  
Vortex immediately to ensure even dispersion of S3—Cleanup Buffer and uniform precipitation of inhibitors.
- i. Centrifuge at 14,000 × g for 2 minutes.
- j. Transfer up to 500 µL of the supernatant to a clean microcentrifuge tube, avoiding the pellet and any debris.

### 2 Bind the DNA to the column

- a. Add 900 µL of S4—Binding Buffer, and vortex briefly.
- b. Load 700 µL of the sample mixture onto a spin column-tube assembly, and centrifuge at 14,000 × g for 1 minute.
- c. Discard the flow-through, and repeat step 2b with the remaining sample mixture.  
Ensure that the entire sample mixture has passed into the collection tube by inspecting the column. If sample remains in the column, centrifuge again at 14,000 × g for 1 minute.

### 3 Wash and elute the DNA

- a. Place the spin column in a clean collection tube, add 500 µL of S5—Wash Buffer, then centrifuge the spin column-tube assembly at 14,000 × g for 1 minute.
- b. Discard the flow-through, then centrifuge the spin column-tube assembly at 14,000 × g for 30 seconds.  
The second centrifugation optimizes removal of S5—Wash Buffer, which could interfere with downstream applications.
- c. Place the spin column in a clean tube, add 100 µL of S6—Elution Buffer, then incubate at room temperature for 1 minute.
- d. Centrifuge the spin column-tube assembly at 14,000 × g for 1 minute, then discard the column.  
The purified DNA is in the tube.

### 3 Wash and elute the DNA *(continued)*

The DNA is ready for immediate use. Alternatively, store the purified DNA:

- At 4°C for up to 1 week.
- At -20°C for long-term storage.

## Troubleshooting

| Observation                                          | Possible cause                                                                                                  | Recommended action                                                                                                                                                                                                      |
|------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| There is less than 400 µL of supernatant after lysis | For some samples, it can be difficult to withdraw 400 µL of supernatant at step 1g, while avoiding debris.      | If <250 µL of supernatant is transferred, add S1—Lysis Buffer to the transferred supernatant to bring the volume to 400 µL.                                                                                             |
|                                                      | Stools from some grass-eating animals (for example, horse) may have a larger debris field over the bead pellet. | It is acceptable to penetrate the debris layer in these cases, to maximize lysate recovery. If <250 µL of supernatant is transferred, add S1—Lysis Buffer to the transferred supernatant to bring the volume to 400 µL. |
| Low yield                                            | Inefficient lysis.                                                                                              | Heat samples at 95°C for 5–10 minutes instead of at 65°C for 10 minutes.<br>Heat at 95°C for 5–10 minutes, and bead beat for a longer time or using a higher power setting.                                             |
|                                                      | Low levels of DNA in the sample.                                                                                | Repeat the purification with more starting material.<br>Do not exceed 0.25 g.                                                                                                                                           |
|                                                      | For some challenging samples, too much starting material can result in low yield.                               | Repeat the purification with less starting material, and increase the volume of S1—Lysis Buffer so that the total volume of sample/S1—Lysis Buffer is 800 µL.                                                           |
| Inhibition of PCR or other downstream reactions      | Presence of inhibitors in the recovered DNA.                                                                    | Dilute the DNA 10- to 100-fold for PCR.                                                                                                                                                                                 |
|                                                      |                                                                                                                 | After addition of S3—Cleanup Buffer, incubate the sample for 10 minutes on ice.                                                                                                                                         |
|                                                      |                                                                                                                 | Repeat the purification with less starting material. Increase the volume of S1—Lysis Buffer so that the total volume of sample/S1—Lysis Buffer is 800 µL.                                                               |

## Documentation and support

### Revision history MAN0014266 (English)

| Revision | Date           | Description   |
|----------|----------------|---------------|
| A.0      | September 2015 | New document. |

### Limited product warranty

Life Technologies Corporation and/or its affiliate(s) warrant their products as set forth in the Life Technologies' General Terms and Conditions of Sale found on Life Technologies' website at [www.thermofisher.com/us/en/home/global/terms-and-conditions.html](http://www.thermofisher.com/us/en/home/global/terms-and-conditions.html). If you have any questions, please contact Life Technologies at [www.thermofisher.com/support](http://www.thermofisher.com/support).

The information in this guide is subject to change without notice.

#### DISCLAIMER

TO THE EXTENT ALLOWED BY LAW, LIFE TECHNOLOGIES AND/OR ITS AFFILIATE(S) WILL NOT BE LIABLE FOR SPECIAL, INCIDENTAL, INDIRECT, PUNITIVE, MULTIPLE, OR CONSEQUENTIAL DAMAGES IN CONNECTION WITH OR ARISING FROM THIS DOCUMENT, INCLUDING YOUR USE OF IT.

Important Licensing Information: These products may be covered by one or more Limited Use Label Licenses. By use of these products, you accept the terms and conditions of all applicable Limited Use Label Licenses.

©2015 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified.

For support visit [thermofisher.com/support](http://thermofisher.com/support) or email [techsupport@lifetech.com](mailto:techsupport@lifetech.com)

thermofisher.com