invitrogen



Gather Your Materials





Multichannel Pipette (200 µL)



Qubit Assay



Qubit Flex Tube Strips Qubit Flex Reservoir (10 mL)

Limited Product Warranty

Life Technologies Corporation and/or its affiliate(s) warrant their products as set forth in the Life Technologies' General Terms and Conditions of Sale found on Life Technologies' website at www.thermofisher.com/us/en/home/global/terms-and-conditions.html. If you have any questions, please contact Life Technologies at www.thermofisher.com/support.

The information in this document is subject to change without notice

DISCLAIMER: TO THE EXTENT ALLOWED BY LAW, THERMO FISHER SCIENTIFIC AND/OR ITS AFFILIATE(S) WILL NOT BE LIABLE FOR SPECIAL, INCIDENTAL, INDIRECT, PUNITIVE, MULTIPLE OR CONSEQUENTIAL DAMAGES IN CONNECTION WITH OR ARISING FROM THIS DOCUMENT, INCLUDING YOUR USE OF IT.

Important Licensing Information: These products may be covered by one or more Limited Use Label Licenses. By use of these products, you accept the terms and conditions of all applicable Limited Use Label Licenses.

Manufacturer: Life Technologies Holdings Pte Ltd | Block 33 | Marsiling Industrial Estate Road 3 | #07-06, Singapore 739256

Find out more at thermofisher.com/qubit

For Research Use Only. Not for use in diagnostic procedures. © 2019 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified.

Thermo Fisher SCIENTIFIC

1 Before You Begin



Select **Calculators** from the Qubit Flex home screen.

These two calculators will help you prepare your assays.

۲	Assay Ra	ange Calculator	í			
Enter sample volume used: dsDNA HS						
	Range	Sample Concentration				
	Extended low	0.02 - < 0.04				
	Core	0.04 - 20				
	Extended high					
0.04 - 20						
		Done				


Use the **Assay Range Calculator** to show how the assay range changes based on the sample volume used (1-20 µL). Tap (i) to view range details.

Core range = High accuracy Extended range = Moderate accuracy



Use the **Reagent Calculator** to determine the amount of working solution to prepare.


One sample = One tube of the tube strip **One standard =** All 8 tubes of the tube strip **Overage =** 3 extra tubes



Vortex all tubes for 2-3 seconds, check for bubbles, then incubate for 2 minutes (15 minutes for protein) at room temperature

3 Read Standards & Run Samples

4 Analyze the Results



Open circles on graph = Standards Blue = Samples in core range Orange = Samples in extended range Red = Samples outside of range

•)	Molarity	С	alcula	ıtor		
	Desire	d units:		ıg∕µL	to	nM	
	Molecular weight:			660 g/mol			
	Auto-populate DNA length						
	Sample	Concentratio	on	Leng		Molarity (nM)	
		4.93		50	0	14.9	
		4.89		50	0	14.8	
		4.89		50	0	14.8	
		4.87		50	0	14.8	
		ort C			Ca	llculate	

Use the **Molarity Calculator** to convert values to molarity based on nucleic acid length.

(Normalization Calculator							
	Final Cor	ncentration: 2 ng/µL	Final Volume: 10 µL					
	Sample	Add sample	Add buffer (بالد)					
		2.3	7.7					
		2.2	7.8					
		2.3						
		2.2	7.8	>				
		2.2	7.8					
		2.3						
		2.2	7.8					
Page 1 of 3								
	Ex	port	Done					

Use the **Normalization Calculator** to determine how to dilute the samples to the same concentration.

2 Prepare the Assay