### thermo scientific



Quantitative imaging and multi-technique surface analysis



## **Designed** for performance

The Thermo Scientific<sup>™</sup> ESCALAB<sup>™</sup> QXi XPS (X-ray Photoelectron Spectroscopy) Microprobe is the latest development in the highly successful ESCALAB product line. The ESCALAB QXi XPS Microprobe is an expandable, optimized, multi-technique platform with unparalleled flexibility and configurability. Cutting-edge technology, driven by intuitive software and hardware, leads to world-class results and productivity. System control, data acquisition, processing and reporting are seamlessly integrated by the powerful Thermo Scientific Avantage<sup>™</sup> Data System.



### Leading analytical performance

- Quantitative spectral imaging
- Fast parallel imaging
- Signature-free detector
- Best-in-class energy resolution
- Microfocused monochromator
- Compositional image analysis
- Auto-tuning, high-flux ion profiling source
- Turn-key charge compensation

### **Streamlined operation**

- Advanced automation
- Selection of analysis area and angular resolution
- Automatic gas handling and vacuum control
- Automated Sample Exchange (optional)
- Calibration on demand
- Energy Scale and transmission function
- Ion gun alignment and beam focusing
- Point-and-click sample navigation and analysis setup
  - Live view of analysis position
- High-intensity illumination

### Flexibility by design

- ISS and REELS as standard
- Preploc chamber as standard
- Automated UPS option
- Field emission electron source option for AES/SEM/EDS
- IPES (on request)
- Optional preparation accessories include:
  - Fracture Stage
  - Specimen heating/cooling
  - Sputter cleaning ion gun
  - High-pressure gas cell (on request)

## Versatile tool for surface analysis

### Large area spectroscopy (LAXPS)

The combination of high-efficiency lenses and detectors ensures the highest sensitivity for large area spectroscopy applications. Acquire high-resolution spectra in seconds.

- Maximum chemical detectability
- Six-channel electron multipliers for maximum dynamic range
- Twin crystal monochromator for maximum X-ray flux

### Small area spectroscopy (SAXPS)

The ESCALAB QXi XPS Microprobe provides fast and precise small area analysis.

- Small feature analysis from greater than 900  $\mu m$  to less than 5  $\mu m$
- Software-enabled feature selection via real-time iris and image control

### Fast parallel imaging (XPI)

Parallel imaging produces rapid, high-resolution XPS chemical images.

- Less than 3 µm chemical imaging resolution
- Signature-free detection system
- Imaging of both large and small features
- Single-input lens and analyzer for imaging and spectroscopy
- Collection of image stacks for quantitative chemica state imaging
- PCA for composition image analysis

### **Energy resolution**

Excellent energy resolution is achieved with the combination of advanced analyzer design and a twin-crystal microfocusing X-ray monochromator.

- Identification and quantification of individual chemical states
- Resolution of overlapping peaks and subtle differences in surface chemistry

### **Insulator analysis**

Insulating samples are easily analyzed using state-of-the-art charge compensation.

- Automated analysis of insulators
- Excellent performance under all analysis conditions

### **Depth profiling**

The advanced ion gun provides high current density even at low beam energy. Auto-tuning of the ion gun ensures optimum crater quality and profiling speed.

- Azimuthal and off-axis sample rotation during profiling
- Full computer control of the ion gun operation modes
- Automated gas handling for etch rate repeatability



### **Angle resolved XPS**

Particles

Matrix

292 290 288 286 284

Binding Energy (eV)

294

- Software-controlled angular resolution ensures
  optimum repeatability
- Eucentric tilt for constant analysis position regardless of sample thickness
- Direct mechanical drive ensures accuracy and precision of tilt position
- Integrated suite of ARXPS processing tools, including Max-Ent (profile reconstruction) and multilayer thickness calculator

### **Automated Sample Exchange option**

- Software-controlled switching of sample holders into analysis chamber
- Sample holder image capture for navigation and definition of analysis points





Spectroscopic imaging of contaminant particles in a fluoropolymer matrix.

Additional techniques

Configuration details

About us

# Additional techniques

### Standard

### Reflection electron energy loss spectroscopy (REELS)

Complementary electronic, structural, and phase information can be provided using the ESCALAB QXi XPS Microprobe's in-lens electron source.

- Hydrogen identification and quantification for polymers and other materials
- Narrow energy spread and an energy range of 0 to 1,000 eV

### Ion scattering spectroscopy (ISS)

Reversible polarity lens and analyzer power supplies make ISS a standard feature.

• Channel electron multipliers provide maximum dynamic range while avoiding image detector damage

### Optional

### Auger electron spectroscopy (AES, SEM, SAM)

The ESCALAB QXi XPS Microprobe can be configured with a Schottky field emission source.

- Auger analysis at very high spatial resolution, 95 nm spot size at 5 nA
- Multiple channel electron multiplier detector essential for high count rates

### Ultra-violet photoelectron spectroscopy

Rapid, high-resolution UPS measurements are possible with the high-flux UV lamp option.

- Excellent electronics stability and low-energy performance required for work-function measurements
- Mu-metal analysis chamber provides optimum magnetic shielding





## thermo scientific

# Configuration details

### **Electron analyzer**

- Double-focusing full 180° spherical sector analyzer
- Magnetic and multi-element electrostatic input lenses
- Motorized, computer-controlled irises to define lateral and angular resolution

### **Detection system**

- Channel electron multipliers—For applications that need high dynamic range: LAXPS, REELS, AES, ISS
- Image Detector-Two-dimensional detector based on a pair of channel plates and having true pulsecounting capability

### Microfocused monochromated X-ray source

- 0.5-meter Rowland circle
- Microfocused electron gun
- Multi-position aluminum anode
- Optional silver anode
- Two toroidal quartz crystals

### Flood qun

- Charge compensation
- Electron imaging
- REFLS

### Ion source

- Depth profiling
- Sample cleaning
- ISS operating mode

### Sample navigation and manipulation

- Point-and-shoot sample navigation and analysis setup
- Live optical view of sample and analysis markers
- Automated 5-axis sample manipulator
- Heating and cooling enabled<sup>1</sup>
- Azimuthal rotation<sup>2</sup>
- Optional automated sample exchange system

### **Avantage Data System**

- Full digital instrument control
- Advanced acquisition, processing, and reporting package
- Recipe mode, from acquisition to report
- Auto analysis function available

### Twin-anode, non-monochromated XPS option

- Dual-anode (MgKa/AlKa) X-ray source
- Other anodes available (e.g., Ag, Zr, etc.)

### Thermo Scientific MAGCIS<sup>™</sup> option (monatomic and gas cluster ion source)

- Dual-mode ion source
- Cluster mode for profiling "soft" materials such as polymers and gentle cleaning of samples prior to XPS
- Monatomic mode for standard ion gun operation

### **UV** photoelectron

### spectroscopy (UPS) option

- High-intensity UV lamp
- Automated noble-gas admission system

### 95 nm AES/SEM/SAM electron gun option

- Schottky type field emission source
- Dedicated source ion pump
- Optional EDS detector
- System vibration isolation
- Charge compensation for insulating samples

### Notes

1. Sample heating requires the use of one of the optional heated sample holders.

2. Sample rotation requires the use of the rotation sample holder.

### Find out more at thermofisher.com/escalab



For research use only. Not for use in diagnostic procedures. For current certifications, visit thermofisher.com/certifications © 2021 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified. BR0138-EN-11-2021

## SEM detector

## About Thermo Fisher Scientific

We are the world leader in serving science. Our mission is to enable our customers to make the world healthier, cleaner and safer.



Step ahead. Step beyond. Duration 1.33

Our innovative solutions for 3D electron microscopy, spectroscopy, and microanalysis help materials science researchers advance their sample characterization to gain deeper insight into materials using the latest advances in analytical instruments. Our multiscale, multimodal solutions provide the additive manufacturing industry with imaging and characterization of powders and parts at nano- to atomic-level resolution.

Our TEMs, DualBeam<sup>™</sup> FIB/SEMs, surface analysis systems, and comprehensive portfolio of SEMs, combined with software suites, take customers from questions to usable data by combining high-resolution imaging with physical, chemical, elemental, mechanical, and electrical analysis across scales and modes through the broadest sample types.



### **Financial and Leasing Services**

At Thermo Fisher Scientific, we will not let budgetary constraints stand between you and your next great discovery.

We are your one-stop partner for the best laboratory products and analytical technologies available, plus the unique financing options you need to accelerate success in science or industry.

Cost-effective financing designed for each individual customer is key to any successful capital equipment solution.

We understand not just your advanced technology and application requirements, but the business challenges you face when financing your critical equipment assets. For decades, we have worked closely with businesses, hospitals, universities, and municipalities to provide flexible financing terms to support their successful operations.

If you are looking for off-balance sheet financing, accelerated ROI, technology protection, or cash flow management, our innovative financing options can help meet your company's budgetary needs and bottom-line goals.

We also offer instrument maintenance and training services.

Explore equipment leasing and financing options