

Thermo Fisher Scientific hereby certifies that the product identified below is inspected and released according to the requirements of product and quality specifications as maintained in our quality management system which is compliant to ISO 13485:2003 (BSI Certificate Number: FM 653694) in the USA.



Barry Srolis  
Sr. Quality Manager

The following information represents Product Certification for: Item#: **642014-0360**

Certificate issued: **03/22/2017**

Description: **2 Liter Basic Wash Bottle**

Lot#: **1198915**

Manufactured: **03/14/2017**

| Part Number | Description              | Common Name | DMF# | Cytotoxicity | USP Class VI | FDA Compliance - 21 CFR  |
|-------------|--------------------------|-------------|------|--------------|--------------|--------------------------|
| 1-1465-85P  | Bottle, Basic Wash       |             |      |              |              |                          |
| 8-0043-07   | Resin, Purell PE GF 4750 | RESIN, HDPE | 5654 | N/A          | N/A          | 177.1520(a)(3)(i)(c)3.2a |

If N/A appears in any of the columns above it means the information is not available. Any item listed as "COMPONENT PART" will show blank in the DMF#, Cytotoxicity, USP Class VI, and FDA Compliance Information columns.

If the word "PASSED" appears in the USP Class VI column next to the resin listing, this material has passed USP Class VI requirements, latest Volume, as part of our initial test approval protocol.

If the word "PASSED" appears in the Cytotoxicity column next to the resin listing, this material was tested and shown to be non-cytotoxic as part of our initial test approval protocol, using either mouse fibroblast L929 cells or the more sensitive human diploid lung cell lines WI-38 or MRC-5.

This lot meets current product drawing B-1-1465-85 and leak test specifications.  
Data is available upon request.

Thermo Fisher Scientific certifies this product meets the following dimensional requirements:

Overall Height 9.449in + /-0.079 (240mm + /-2)  
Overall Width 3.150in + 0.039/-0.059 (80mm + 1/-1.50)  
Overall Length 5.787in + /-0.059 (147mm + /-1.50)  
Major Thread Diameter 1.102in + 0.000/-0.020 (28mm + 0/-0.5)  
Inner Mouth Diameter 0.740in + 0.004/-0.008 (18.8mm + 0.1/-0.2)  
Overall Neck Height 0.787in + /-0.016 (20mm + /-0.4)  
Radius Wall Thickness Min 0.020in (Min 0.5mm)  
Bottle Wall Thickness Min 0.028in (Min 0.7mm)  
Part Weight 165 + /-5g