



Gas detection and occupational safety

Hazard reduction

For a safer workplace

Hazard reduction

Thermo Fisher Scientific offers a full range of gas detection and environmental monitoring solutions, to help keep workers safe in their workplace and to monitor the impact of gas, dust and noise on the environment. Our product range provides the key equipment for gas detection and environmental monitoring, including portable and fixed gas detectors, area-gas monitors, lone worker monitors, noise dosimeters, sound level meters, particulate monitors and samplers and SCBA equipment. To complement our monitoring solutions, Thermo Fisher Scientific can provide on-site or workshop calibration/service for your equipment, in order to ensure reliability and compliance.

The products showcased in this brochure are only a small sample of our full range. Please contact us for more information.

Contents

Portable gas detection	4
Safe worker single gas detectors	5
Safe worker four-gas detectors	6
Safe worker four, five and six-gas detectors, with integral pump	8
Docking stations for portable gas detectors	9
Indoor ambient air monitoring	9
Wastewater odour/gas loggers	10
Area gas detectors	10
Gas detector fleet management	11
<hr/>	
Lone worker safety	12
Lone worker safety	13
<hr/>	
Fixed gas detection	14
Fixed gas detection	15
Industrial Infra-red flammable gas detectors	15
Light industry/commercial gas detectors	16
Industrial ultrasonic gas leak detectors	16
Industrial gas detectors	16
Hi-tech/low range gas detection	18
Controllers	19
Hazardous area communications	20
Calibration gas	20
Cylinders and regulators	20
<hr/>	
Occupational hygiene	21
Dust and vibration monitoring/logging	22
Real-time particulate monitoring	23
Boundary monitoring of noise, dust, vibration, VOC	23
Noise and sound monitoring	24
<hr/>	
Other hazard reduction and safety products	25
Self-contained breathing apparatus	26
<hr/>	
Environmental monitoring solutions	27
We've got your back	28
<hr/>	



Gas detection



Portable gas detection

Designed to monitor a wide variety of toxic and combustible gases, such as methane, hydrogen sulphide, carbon monoxide, carbon dioxide and oxygen deficiency.

Safe worker single gas detectors



Honeywell BW Solo

Next-generation wireless (Bluetooth), datalogging, single-button, single gas detector with a wide range of toxic gas models. Intelligent 1-Series Sensor for most monitored gases, with smaller size, faster response, 5-year life and 3-year warranty. Easy sensor replacement, in the field, with no tools.

Honeywell BW Clip

Always-ON no-maintenance single-gas detector, delivering continuous detection of H₂S, SO₂, O₂ or CO, with no need for calibration, sensor or battery replacement or battery charging. Available in standard and Real Time display versions and with 2 or 3 year operation.



MSA Altair 2X

Serviceable, rugged single or dual gas detector for H₂S, CO, NO₂, NH₃, Cl₂, SO₂, H₂S+CO, CO+NO₂, or SO₂+H₂S, with 3-year device warranty and up to 3-year battery life.

Blackline G6

Serviceable, cloud-connected single gas detector for H₂S, SO₂, O₂ or CO. Offers GPS location technology, over-the-air configuration and up to 1-year battery life.



Honeywell RAE ToxiRAE Pro

Wireless, single gas detector for VOCs, O₂, Toxic, CO₂ and combustible gases. Includes Man Down Alarm with real-time remote wireless notification. Replaceable sensor, filter, and Li-ion battery.

Blackline G7c/G7x

Cloud-connected cellular or satellite, this single-gas detector provides easy access to historical/compliance data and in-field sensor cartridge replacement. Optional real-time monitoring to include man-down, SOS alerts and text/voice communication.



Safe worker four-gas detectors



Honeywell BW GasAlertMicroClip

XL and X3 Rugged, IP68, serviceable, continuous monitor of 1 to 4 gas hazards (H2S, CO, O2 and LEL). 2-years warranty for XL; 3-years for X3 and typically 5-years sensor life. Replacable sensor, rechargeable battery. Connected Worker.

Honeywell BW Clip4

Always-ON, IP68 4-gas detector of H2S, CO, O2 and LEL, with a 2-year continuous runtime and Real Time display. Does not require battery charging, or sensor or battery replacement. Daily full self-test and non-compliance indication.



Honeywell Icon/Icon+

Wireless (Bluetooth) 4-gas detector with simple ICON display. 2-month battery runtime and Always-ON option. 2-year warranty fixed life (Icon) or 3-year warranty serviceable (Icon+).

Honeywell Flex4/Flex5

Serviceable, wireless (Bluetooth) 4 or 5-gas detector, with real-time display and up to 15 sensors to choose from. 2-month battery runtime, 3-year warranty.



MSA Altair 4XR

Rugged 4-gas detector with 4 or 5-year warranty and man-down alerts. Long-life, fast XCell Sensor Technology with end-of-life indicator.

MSA Altair io4

Rugged 4-gas detector with cellular connectivity for real-time visibility. IP68 and drop tested from 25ft. Long-life, fast XCell Sensor Technology with end-of-life indicator.



Safe worker four-gas detectors



Blackline G7c/G7x

Cloud-connected cellular or satellite, this four-gas detector provides easy access to historical/compliance data and in-field sensor cartridge replacement. Optional real-time monitoring to include man-down, SOS alerts and text/voice communication.

Honeywell RAE MicroRAE

Wireless, four gas detector for H₂S, CO, O₂, LEL and HCN. Includes man-down Alarm with real-time remote wireless notification. Options for Bluetooth, GPS, 900MHz.



Safe worker four, five and six-gas detectors, with integral pump



Honeywell BW Ultra

Next-generation, ultra-rugged, five gas detector with a wide range of toxic gas models and with integrated sample pump for up to 23m draw. Intelligent 1-Series Sensor for most monitored gases, with smaller size, faster response. Bluetooth for Connected Worker.

Honeywell BW GasAlertMax XT II

Serviceable, continuous monitor of 1 to 4 gas hazards (H₂S, CO, O₂ and LEL), with integrated pump for remote sampling. Quick-connect tubing system secures the sampling hose in place, for easy change of tubing (up to 23m). 2-year warranty on replaceable sensors.



Blackline G7c/G7x

Cloud-connected cellular or satellite, this four/five gas detector provides easy access to historical/compliance data and in-field sensor cartridge replacement. Optional real-time monitoring to include man-down, SOS alerts and text/voice communication.

MSA Altair 5X

Rugged 6-gas detector with integral pump, Bluetooth connectivity, 3-year warranty and man-down alerts. Long-life, fast XCell Sensor Technology with end-of-life indicator.



Honeywell RAE MultiRAE

Wireless, pumped gas detector for up to six gases including VOCs, PID, CO₂-IR and over 15 more gases. Includes man-down Alarm with real-time remote wireless notification. Options for Wi-Fi, Bluetooth, 900MHz.

Docking stations for portable gas detectors



Honeywell BW IntelliDoX

Smart docking system with upto 5 independent modules for automated instrument management of BW Solo, BW Ultra, BW Clip, BW Clip4 and GasAlertMicroClip gas detectors. Fast Bump-test avoids gas wastage; data transfer via USB or Ethernet.

Blackline G7 Dock

Calibrating and bump testing G7c and G7x devices is easy with Blackline's G7 Dock. See the real-time compliance status of all G7 equipment via the Blackline Live monitoring account.



MSA Galaxy GX2

Docking system for Altair series of gas detectors. Test up to 10 gas detectors, simultaneously. Auto-detection of calibration gas ensures the correct settings and that you don't run out of gas.

Honeywell RAE AutoRAE2

Simplify bump testing and calibration of your RAE gas monitors with the AutoRAE2. Deploy as a single, stand-alone unit to calibrate one instrument at a time, or networked to support up to 10 units.



Indoor ambient air monitoring



Honeywell Transmission Risk Air Monitor (HTRAM)

A cost-effective monitor for use in schools, offices, lunchrooms, that alerts users when conditions are present that may increase the risk of exposure to airborne viral transmission in an indoor area. Monitors CO₂, humidity and temperature, coupled with human activity settings, to alerts the user to adverse conditions.

Wastewater odour/gas loggers



OdaLog G20

The next generation of IECEx certified portable gas loggers, now with Smart Sensor technology for predictive maintenance and health indication and with a long deployment period of up to 90 days.

OdaLog G20 RTX

The next generation of IECEx certified portable gas loggers, with integrated 4G Modem for remote data access, Smart Sensor technology for predictive maintenance and health indication and with a long deployment period of up to 90 days.



Area gas detectors



Honeywell BW RigRat

Transportable Local Area Gas Monitor, for temporary/shutdown, confined space and situational monitoring and for perimeter monitoring with “chained” devices. Mains, battery or solar power options, upto six gas sensors, bluetooth access, weatherproof and IECEx Zone 0 rated, options for noise and meteorological monitoring, Wifi and radio.

Blackline G7 EXO

Cloud connected, transportable Local Area Gas Monitor, for temporary/shutdown, confined space and situational monitoring, with SOS-latch, integrated cellular communications and two-way voice calling to a live monitoring team. Mains, battery or solar power options, upto 5 gas sensors, weatherproof and IECEx Zone 0 rated. Optional satellite communications.



Gas detector fleet management



Honeywell Safety Suite

Honeywell Safety Suite software is designed to enhance worker safety, while providing the tools for Honeywell gas detector compliance and fleet management. Maintain and track your fleet of devices and monitors workers' exposure to gas in real time.

MSA Safety_io

Cloud software service and real-time alert system for managing your MSA portable gas detection fleet, with daily e-mail notification of fleet status, reports for calibrations, detector records and alarms.



Blackline Live Portal

With the Blackline Live web-portal the safety status of every team member is visible at a glance using Blackline Live's real-time maps. Historical data and compliance data may be accessed for the Blackline G6 single gas detector, the G7 single/multi-gas detector and the G7 EXO area monitor, all wirelessly.



Hazard reduction



Lone worker safety

Work alone solutions for every industry. We provide innovative solutions to support lone workers, evacuation management, and your environmental gas detection needs.

Lone worker safety





Blackline G7c and G7x

Always-connected cellular or satellite wireless lone worker monitor, with fall-detection, no-motion detection, missed check-in detection, and SOS emergency trigger. Communication via text, voice or push-to-talk. Combine with upto 5 gas sensors to provide full lone worker safety.

Blackline Live Monitoring

The Blackline Live web-portal provides full indication of a remote worker's G7 safety status, 24/7. On receipt of an alert, monitoring personnel follow their protocol to contact the worker, by text or voice, logged and date stamped. Gas sensors wirelessly communicate compliance and usage data also to the portal.





Gas detection



Fixed gas detection

Innovative technologies designed to monitor a wide variety of toxic and combustible gases found throughout the Petrochemical, Wastewater, Power Generation, Mineral Processing, Metal Smelting and Manufacturing industries

Fixed gas detection

Industrial Infra-red flammable gas detectors



Honeywell Searchline Excel Edge and Plus

The latest in infra-red open-path hydrocarbon gas detection, up to 330m. Bluetooth enabled for smart-device interrogation, HALO-LED indication and integral I/O for analog, relay, HART and Modbus outputs.

Honeywell Searchline Excel

World renowned infra-red open-path hydrocarbon gas detector, for use in potentially explosive atmospheres. Pathlength upto 200m, for wide area coverage, with very high speed of response, to provide earliest warning.



Honeywell Searchpoint Optima Plus

Market leading infra-red point hydrocarbon gas detector, for use in potentially explosive atmospheres. Fastest speed of response and fail-to-safe operation, suitable for oil and gas platforms, terminals, refineries.

Honeywell Optima Excel Local Display

Smart junction box for the Searchpoint Optima Plus and Searchline Excel infrared detectors for flammable hydrocarbons. Features worldwide hazardous approvals, Bluetooth connectivity to smart device, and tri-colour display.



Light industry/commercial gas detectors



Honeywell Sensepoint XCL

Bluetooth enabled single-gas detector monitoring toxic and combustible gases and oxygen, in commercial and light industry - boiler rooms, fuel stations, car-parks, labs, breweries. Easily commissioned via a smart device or Touchpoint Plus controller.

Industrial ultrasonic gas leak detectors



Honeywell Searchzone Sonik

Acoustic ultrasonic gas leak detector complementing Honeywell's established portfolio of gas detection devices. Reliable gas leak detection even in the harshest weather, with Bluetooth connectivity for commissioning.

Industrial gas detectors



Honeywell Sensepoint XCD

All-in-one flammable, toxic and oxygen gas sensor and explosion-proof transmitter, for potentially explosive atmospheres. Transmitter features a tri-colour display for viewing status from a distance. RFD and RTD versions for other hazardous classes.

Honeywell Sensepoint XRL

Bluetooth enabled single-gas detector monitoring toxic and combustible gases and oxygen, in outdoor and hazardous areas. Easily commissioned via a smart device or Touchpoint Plus controller.



Industrial gas detectors



Honeywell Series 3000 MkII and MkIII

2-wire loop powered toxic and oxygen gas sensor and transmitter for the protection of personnel in potentially explosive atmospheres.

Honeywell XNX Universal Transmitter

Universal transmitter compatible with all Honeywell Gas Detection technologies. Satisfies Class 1/Class 2 intrinsically safe, explosion-proof requirements in oil, chemical, wastewater and other industries.



Honeywell Sensepoint

Certified flammable, toxic and oxygen gas detectors, suitable for potentially explosive atmospheres. High quality, low cost solution.

Honeywell RAEGuard 2 PID

Photoionisation detector (PID) measuring a broad range of volatile organic compounds (VOC), in potentially explosive atmosphere of paint/solvent industry, refineries, power petro-chem.



Hi-tech/low range gas detection



Honeywell Midas

Single gas sensor/transmitter for monitoring up to 35 toxic, ambient and flammable gases in such as light industry, laboratories, wastewater plants.

Honeywell SPM Flex

Using Chemcassette tape technology, simply snap in the appropriate tape and operate as a fixed or portable unit. Detects ultra-sensitive gases including hydrides, mineral acids, amines, oxidizers and more, down to ppb levels. Portable for emergency response, suspect leaks.



Controllers



Honeywell Unipoint

Simple DIN rail mounted controller offering integrators a flexible and low- cost solution to incorporate flammable, toxic or oxygen gas detection into their control systems.

Honeywell Touchpoint Plus

An easily configurable, wall-mounted control system that supports up to 16 gas detection channels. Numerous output options - 4-20mA, relay, Modbus.



Honeywell Touchpoint Pro

Complete centralized safety system, cabinet or rack mounted, monitoring up to 64 detection channels. Numerous inputs, outputs and relay modules, Modbus, Ethernet, web-server interface.

Hazardous area communications



We offer a comprehensive range of certified Manual Alarm Call Points, Alarm Beacons and Sounders for use in potentially explosive atmospheres and extreme environmental conditions.

Calibration gas

Routine testing and calibration of gas detection equipment with quality test gas is critical to the accuracy and reliability of your instruments. We offer a comprehensive range of specialty test gases and regulators suitable for response testing and calibration of fixed and portable gas detection instruments.



Cylinders

Our test gases come in a variety of sizes ranging from 34 litres through to 116 litres.

Regulators

We offer a variety of gas pressures regulators with various pressure ranges.





Hazard reduction



Occupational hygiene

We offer a range of dust and noise monitoring solutions that enhance the long term health and quality of life for workers in high risk occupational sectors

Dust and vibration monitoring/logging



Casella Apex2 IS

Personal sampling pump for monitoring worker's exposure to dusts, fumes, gases and vapours. Ergonomic design, with long battery life, high back pressure and motion detection, to show the pump has been worn. Intrinsically safe and with wireless option to allow access to the device without disturbing the wearer.

Casella VAPex

Personal low flow sampling pump specifically for monitoring of gasses and vapours in working environments. Ergonomic design, with long battery life, high back pressure along with motion detection, to show the pump has been worn. Intrinsically safe and wireless for easy control and data access.



Casella Vortex3

Ideal for area sampling for airborne contaminants such as Asbestos and other hazardous materials, Vortex3 is the latest generation of static, high flow rate sampling pumps.

Casella Flow Detective

An all-in-one airflow calibrator, suitable for all types of air sampling pumps and other applications for flows up to 5L/min. Wireless connection to smart-device, for calibration reports an control and to allow wireless closed-loop calibration of Apex2 and VAPex pumps.



Real-time particulate monitoring



Casella MicrodustPro

A real-time hand-held, data logging instrument for the detection of airborne dusts, fumes and aerosols. Ideal for walk-through surveys. Data log of 500 measurement, with USB access.

Casella Dust-Detective

Area and Boundary dust monitor, comprising a ruggedised enclosure holding a Microdust Pro real time dust monitor together with an Apex2 personal air sampling pump. Provides upto 13hrs of Gravimetric and real-time dust data.



Boundary monitoring of noise, dust, vibration, VOC



Casella Guardian2

Monitoring station for reporting of noise, dust and vibration. Options include a VOC sensor, for remediation of a site contaminated with petroleum based products, windspeed sensor, solar power. Web-hosted data access, email and text alerts.

Noise and sound monitoring



Casella dBadge2 IS

Wearable personal noise dosimeter, intrinsically safe and unobtrusive. Features an in-built motion detector and wireless connectivity for start/stop control. Pro and Plus models include voice-notes recording.

Casella 24X Series

Entry level sound level meters, ideal for occupational noise measurements. Rugged, 2-button operation, with models for logging and USB data access.



Casella 63X Series

Versatile sound level meters, ideal for both occupational and environmental noise measurements. Features level triggered events, octave and 1/3 octave measurement, voice-notes and audio recording. USB connectivity for data access.



Hazard reduction



Other hazard reduction and safety products

We offer a range of equipment to compliment our gas detection and occupational safety solutions.

Self-contained breathing apparatus



MSA Safety SCBA Platform

The MSA M1 SCBA Platform is an advanced, ergonomic, and modular SCBA system which was designed and developed side-by-side with firefighters. Choices range from a basic “work” model to a “professional” model with advanced harness and pneumatics.



Environmental monitoring solutions

Supporting your priority to protect your people and your site

Environmental monitoring is critical to protect your employee's safety

Further to our dynamic hazard reduction product offering, we have extensive product solutions to support environmental monitoring. With current safety standards the high level of regulatory compliance is a critical focus for any work site. The priority of both employee and community safety is paramount. The products we have on offer have been curated and developed to bring you leading technologies that support user friendly approaches to minimise environmental impact. Our strategic partner brands provide years of trusted experience across the environmental industries, with providing new ways of thinking and working to support the end user.

Our featured offerings include:

- Water analysis
- Air quality analysis
- Soil analysis
- Environmental contaminant analysis
- Environmental sample containers and accessories



Service and calibration

We've got your back

Let our service and calibration experts support your important work

Thermo Fisher Scientific, your true industry service partner

Thermo Fisher Scientific is your industrial partner, focused on helping you to improve process efficiency and minimise unplanned downtime.

We offer technologically advanced monitoring and measurement instrumentation to enable plants in power, mining, municipal, food and beverage, and more, to improve production efficiency, improve the lifecycle of their existing assets, and ensure environmental compliance. This is backed by our NATA calibration and service support capabilities.

We have service centres in Melbourne, Sydney, Brisbane, Perth and Auckland and offer on-site calibration services that guarantee a convenient servicing location as well as minimising equipment downtime and a cost-effective solution for all your calibration requirements.

Our factory trained technical service team is equipped with the global knowledge and tools to support your organisation when instruments require repair, service and calibration. They're factory trained to ensure we can offer a guarantee on our workmanship with anything we do as well as only using genuine parts to maximise your instrument uptime. Why risk using anyone else when Thermo Fisher stand behind everything we do.

In many cases, we can offer a maintenance agreement to minimise the financial impact on your business by giving you greater working capital increasing your cashflow; talk to us today to find out how we can tailor a service solution to meet your business needs.

Learn more at thermofisher.com/hazardreduction