

Alfa Aesar

The background of the advertisement features a complex, futuristic design. It includes a large, blue, wireframe structure that resembles a DNA double helix or a molecular model, set against a light blue and white background with a grid of dots. The overall aesthetic is clean, modern, and scientific.

Bio

Chemicals for Life

Including:

Amino Acids and Derivatives

Buffers

Click Chemistry Reagents

Electrophoresis Reagents

Signal Transduction Reagents

Western Blot and ELISA Reagents

...and much more

Introducing Alfa Aesar Bio

Alfa Aesar is pleased to introduce the latest addition to its complete range of over 46,000 products.

The new biochemical product range adds over 4,000 products to the existing offering, providing a more complete selection for all of your research needs.

With a wide and continuously growing variety of materials for biological research including electrophoresis reagents, enzymes, signal transduction reagents and much more, Alfa Aesar now truly offers one stop chemical shopping combined with unparalleled customer service.

Visit www.alfa.com for the latest news and product availability


Alfa Aesar



Table of Contents

| | |
|--------------------------------------|-----------|
| Table of Contents | I |
| Key to Chemical Listings | II |
| How to Order | III |
| General Information | IV |
| Terms of Sale | V |
| Product Information | VI |
| Product Safety - MSDS | VIII |
| Bulk and Specialty Capabilities | IX |
| Alfa Aesar Product Lines | X |
| Periodic Table | XII |
| Abbreviations and Codes | 1 |
| PRODUCT CATEGORY INDEX | 3 |
| ACS Reagents | 3 |
| Amino Acids and Derivatives | 5 |
| Antibiotics | 9 |
| Antibodies | 11 |
| Apoptosis Reagents | 12 |
| Buffers | 14 |
| Carbohydrates and Derivatives | 23 |
| Cell Culture Reagents | 25 |
| Chiral Compounds | 27 |
| Click Chemistry Reagents | 29 |
| Electrophoresis Reagents | 30 |
| Enzymes | 38 |
| Growth Factors | 40 |
| Natural Products | 41 |
| Nucleosides and Nucleotides | 43 |
| Peptides | 47 |
| Signal Transduction Reagents | 51 |
| Solvents, Acids and Bases | 62 |
| Stains, Dyes and Indicators | 63 |
| Vitamins | 66 |
| Western Blot and ELISA Reagents | 67 |
| ALPHABETICAL CHEMICAL LISTING | 69 |

Key to Chemical Listings

| | | | |
|-----------|--|-----------|-----------------|
| 1 | 2 | 7 | 4 |
| J62011 | A-7 hydrochloride [N-(10-Aminodecyl)-5-chloro-1-naphthalenesulfonamide hydrochloride] [79127-24-5], C ₂₀ H ₂₆ ClN ₂ O ₂ S·HCl, F.W. 433.44, Solid | | 25mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 12 | |
| | Application(s): Calmodulin antagonist | | |
| 5 | Abamectin, 97+% [Avermectin B1] [71751-41-2], C ₄₈ H ₇₂ O ₁₄ , F.W. 873.10, Powder, m.p. 150-155°, Merck 14,2, UN2811, MDL MFCD01769550 | | 1g 5g 25g |
| | H:H300-H400-H332, P:P261-P301+P310-P321-P304+P340+P501a | 8 | 9 |
| | Application(s): Interacts with GABA receptors to cause chloride channel activation | 14 | |
| 6 | Abietic acid, tech. 75% Δ [514-10-3], C ₂₀ H ₃₀ O ₂ , F.W. 302.45, Merck 14,7, EINECS 208-178-3, BRN 2221451, MDL MFCD03423567, 1 | 3 | 25g 100g |
| 11 | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 10 | |
| |  | 13 | |

- | | |
|---|---|
| 1 Stock number | 9 UN Dangerous Goods number |
| 2 Product name and grade | 10 Denotes substance is listed in Toxic Substance Control Act (TSCA) inventory |
| 3 Sensitivity symbol (see abbreviations index) | 11 Globally Harmonized System (GHS) Pictograms |
| 4 Unit size | 12 Precautionary and Hazard Codes |
| 5 Alternative name(s) | 13 Chemical structure |
| 6 Chemical Abstract Service (CAS) number | 14 EINECS (European Inventory of Existing Chemical Substances) Number |
| 7 Molecular formula | |
| 8 Physical form | |

F.W. Formula weight

m.p. Melting point

b.p. Boiling point

f.p. Flash point

d. Density in g/ml

n_D^{20} Refractive index

$[\alpha]_D^{20}$ Optical rotation

Merck Merck Index Number

BRN Beilstein Registry number

Fieser Fieser's Reagents reference

RTECS Registry of Toxic Effects of

Chemical Substances reference

MDL MDL number

How to Order

TELEPHONE

Please have the following information available when placing an order:

- Your customer number (if applicable).
- Billing and shipping addresses.
- Product stock number, size, and quantity for each item you wish to order.
- Your purchase order number or government/corporate credit card number and expiration date.

INTERNET

www.alfa.com

Our web catalogue features up-to-date prices and a user-friendly e-commerce system.

EMAIL

info@alfa.com

for catalogue product orders and general inquiries

tech@alfa.com

for technical inquiries

specialquotes@alfa.com

for bulk and specialty inquiries

We do not require a confirming purchase order. If you choose to send one, please mark it clearly, "CONFIRMING ORDER" to avoid possible duplication. There is no minimum order. We welcome all orders, regardless of size.

Alfa Aesar is ISO 9001 and ISO 14001 Certified



General Information

ORDERING

Customer Service Representatives are available weekdays to assist you. When you call to place an order, we will work with you to learn your specific needs. There is no minimum order. All orders are accepted, regardless of size.

PRICING

Most current pricing may be found at our website: www.alfa.com. In cases where the selling price has changed significantly, we will contact you prior to filling your web, email or faxed order.

SHIPPING

Whenever possible, we will ship products by the method specified on your order.

TECHNICAL SERVICE

At your request, we will furnish technical assistance and information with respect to our products. Our Technical Service Representatives are trained in specific product lines to answer your questions regarding applications, specifications, product properties and handling.



MATERIAL SAFETY DATA SHEETS

Each product ordered is automatically accompanied by a Material Safety Data Sheet (MSDS) if applicable. If one is not immediately available, a copy will be sent via mail as soon as possible. If an MSDS is needed prior to shipment of a product please visit our MSDS website at www.alfa.com.

RETURN SHIPMENTS

Some materials are not returnable. Returned shipments cannot be accepted unless prior arrangements have been made.

TERMS OF SALE

Full details of Terms and Conditions are listed on our website (www.alfa.com). For health and safety reasons, we shall not supply chemicals to private individuals or deliver to residential addresses. Orders will be accepted from legitimate business customers only.

NEW CUSTOMERS

We welcome new customers and setting up an account with Alfa Aesar is easy. Just call your local sales office and a customer service representative will assist you.



Product Information

HOW TO FIND A PRODUCT

BY PRODUCT CATEGORY

All chemicals are listed by category in the application index at the beginning of the catalogue.

ALPHABETICALLY

All chemicals are listed in alphabetical order in the main section.

ELECTRONIC FORMATS

Online at www.alfa.com you can search by description, stock number, CAS number, MDL number, and competitor matching stock number. There are also tools for substructure search, alphabetical index, pure element search and a labware search. MSDS and Certificate of Analysis searches are also offered.

SPECIFICATIONS

Alfa Aesar quality control chemists employ a variety of analytical methods consistent with the diversity of the product range. Products are tested according to our current specifications, available on request.

PRODUCT GRADES

The purity determined for an individual product can vary slightly from lot to lot. The percentage grade figures shown in the catalogue represent typical purity values, defined as shown. Similarly, catalogue figures for physical data, such as melting point, boiling point or refractive index, are typical values, and may not form part of the product specification.

Where possible, products are assigned one of the grades shown here, based on the assays of different lots determined by the method defined on the product specification.

For these grades, the following tolerances apply:

| Grade | Assay Range |
|--------------|--------------------|
| 99+% | >99.0% |
| 99% | >98.5% |
| 98+% | >98.0% |
| 98% | >97.5% |
| 97+% | >97.0% |
| 97% | >96.0% |
| 96.0% | >95.0% |
| 95.0% | >94.0% |
| 94% | >92.5% |
| 90+% | >90.0% |
| Tech. 90% | >88.0% |
| Tech. 85% | >83.0% |

Other numerical grades may apply to specific products. While we make every effort to maintain the grades shown in the catalogue, we also reserve the right to amend product grades and specifications up or down as dictated by stock availability. If you require confirmation of any product grade, or wish to know the actual purity for material we hold in stock, contact our Technical Service department. For bulk orders we can also supply you with a certificate of analysis with full analytical results for the particular lot number you have purchased.

PRODUCT USE AND HAZARDOUS INFORMATION

Chemicals listed in this catalogue are only for use in research and development laboratories or chemical manufacturing facilities. All products listed in this catalogue should be handled only by properly trained personnel. Please refer to the terms and conditions of sale on our website for further use limitations and hazard information.



STORAGE CONDITIONS

Product listings include sensitivity symbols that indicate recommended storage and handling conditions.

△ **Air Sensitive**

The product can react with air, oxygen, or carbon dioxide. It should be stored in an inert atmosphere in a tightly sealed container.

▣ **Moisture Sensitive**

The product can react chemically with water. It should be protected from humidity by storing under an inert atmosphere in a tightly sealed container.

■ **Hygroscopic**

The product can absorb water from the atmosphere. It should be protected from humidity by storing under an inert atmosphere in a tightly sealed container.

▲ **Light Sensitive**

The product may deteriorate if exposed to strong light. It should be stored in the dark or in a light-proof container.

■ **Packaged Under Argon**

Products we package under argon are particularly sensitive to air and/or moisture, and especially if the product can react with nitrogen.

Product Safety - MSDS

MATERIAL SAFETY DATA SHEETS FROM ALFA AESAR

Please consult risk and safety codes and the Material Safety Data Sheet (MSDS) before ordering. You can obtain MSDS online at www.alfa.com or on request.

- Transportation data from DOT, IATA, IMDG and ADR/AID
- Canadian DSL and NDSL lists
- European country specific OELs

TO OBTAIN AN MSDS

Go to www.alfa.com

Call your regional sales office

Send an email to tech@alfa.com

PRECAUTIONARY AND HAZARD CODES


The catalogue displays Precautionary and Hazard Codes for all products where applicable. A full listing of Precautionary and Hazard Phrases is listed in the back of this catalogue.

SPECIAL HANDLING

Items requiring special handling are listed in the catalogue with a notation to that effect.

ENVIRONMENTAL, HEALTH AND SAFETY CONTACT DETAILS

For product handling or safety inquiries, or in case of emergency, please contact your local sales office.



Bulk & Specialty Capabilities

The expert technical and commercial personnel in our Bulk and Specialty Sales group can aid in your search for the ideal bulk, special or custom manufactured product.

MANUFACTURING

Alfa Aesar's combined resources bring you a broader range of unique building blocks and other novel compounds. Over 100 production chemists employ a variety of techniques in the development of new products, many of which are otherwise unavailable commercially.

Alfa Aesar's production operations offer a single source for fine chemicals, from research to pilot scale.

CUSTOMER SERVICE

Our dedicated scientific and commercial teams offer full service from production to delivery. Most products are stocked in catalogue pack sizes and the majority are available from stock in semi-bulk and bulk quantities as well. All specialty and bulk products are shipped with a batch specific certificate of analysis and material safety data sheet. Because we understand that specific packaging is often important, we offer custom packaging and labeling to meet your requirements.



Additional Product Lines

Alfa Aesar brands represent the finest in novel and specialized organic and inorganic compounds, metals and standards.

ACTIVE DRY™

Active Dry™ anhydrous solvents feature the alkali metal silica gel system (Na-SG-I), an efficient drying agent and impurity remover for solvents and anionic polymerization processes. Each solvent includes an Active Dry™ pouch immersed in the solvent to ensure dryness, and is sealed using our exclusive ChemSeal™ septum caps.

CHEMSEAL™

A range of air, oxygen and moisture sensitive products is offered in ChemSeal packaging. The ChemSeal system employs a resealable septum through which a volumetric quantity of the reagent can be withdrawn without exposure to oxygen or moisture.

FIBRECAT™

FibreCat precious metal catalysts are anchored to a series of functionalized fibres, creating a combination of selectivity and ease of handling and separation.

PREMION®

Premion is Alfa Aesar's trademarked name for high purity precious metal compounds and pure elements. The minimum purity for Premion pure elements is 99.99% (metals basis).

Premion pure elements include the following metals: Platinum (Pt), Palladium (Pd), Rhodium (Rh), Iridium (Ir), Ruthenium (Ru), Osmium (Os), Silver (Ag), and Gold (Au). The minimum purity for Premion compounds is 99.95% (metals basis). They include the compounds of the elements listed above. All Premion products automatically come with a batch-specific Certificate of Analysis.

PREMION

HIGH PURITY PRECIOUS METALS

PURATRONIC®

Puratronic high purity base metals and salts are the leading choice of pharmaceutical and electronic companies as the basic building blocks for many research and development processes. Alfa Aesar ensures the quality and purity of each Puratronic product during manufacturing. Each Puratronic compound has a minimum purity of 99.99% (many exceed 99.999%) and a lot specific Certificate of Analysis is shipped with each item.

PURATRONIC®
HIGH PURITY RESEARCH
CHEMICALS & MATERIALS

REACTON®

Recognized as a benchmark for high purity rare earths, the REacton brand line encompasses the entire Lanthanide series (excluding promethium) along with scandium and yttrium. REacton rare earths feature extremely low impurity levels and exacting Certificates of Analysis are issued with each REacton product.

REacton®

Rare Earth Metals
and Compounds

SPECURE®

Specpure is the trade name for Alfa Aesar's analytical standard solutions. Specpure standards are produced using the highest quality raw materials and ASTM Type 1 deionized water for the greatest calibration accuracy possible. All Specpure standards are shipped with a batch-specific Certificate of Analysis. Specpure atomic absorption standard solution concentrations are accurate to $\pm 1.0\%$ and plasma solutions to $\pm 0.3\%$.

Specpure®

PRODUCTS FOR THE ANALYTICAL CHEMIST

SPECTROFLUX®

Spectroflux is Alfa Aesar's brand of lithium borate based fluxes prepared for daily use in a variety of analytical methods. A range of fluxes is available for use in methods such as X-ray emission spectrometers, atomic absorption spectrometers, spectrophotometers, polarographs, ion selective electrodes, ICP or classical analytical techniques. Regardless of the method chosen, Spectroflux analytical fluxes offer the benefits of speed and analytical precision.

SPECTROFlux®

ULTRA DRY ANHYDROUS MATERIALS

Alfa Aesar provides a comprehensive line of ultra dry materials, the first choice for air and moisture sensitive applications. Ultra dry compounds are manufactured under exacting conditions to ensure that oxygen and water impurities are in the parts per million range. Only high purity starting materials are used in the manufacturing process, which produces results in overall purities of 99.9% to 99.999%. All ultra dry salts are ampouled under argon, and most are available in -10 mesh beads and powder form.

ULTRA Dry™

Anhydrous Materials

VACPURE™

Evaporation processes and other exacting applications require ultra purity. The new Vacpure system is a specially engineered sealing/packaging process for a range of high purity metals. The Vacpure system ensures that oxygen, moisture and other impurities are extracted from the packaging before sealing, maintaining the purity of the enclosed material.

Vacpure®

Alfa Aesar


Visit Our Website at
www.alfa.com

1E VIA

1K

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|---------------------------------|---------------------------------|-------------------------------|----------------------------------|-----------------------------------|-------------------------------|--------------------------------------|----------------------------------|------------------------------------|---------------------------------|----------------------------------|-----------------------------------|---------------------------------|-----------------------------------|----------------------------------|--------------------------------|---------------------------------|-----------------------------------|----------------------------------|--------------------------------|---------------------------------|--------------------------------------|--------------------------------|-----------------------------------|-----------------------------------|-----------------------------------|--------------------------------|-----------------------------------|------------------------------------|-------------------------------------|----------------------------------|------------------------------------|---------------------------------|--------------------------------|--------------------------------|---------------------------------|---------------------------------|-------------------------------|----------------------------------|--------------------------------|----------------------------------|-----------------------------------|----------------------------------|--------------------------------|----------------------------------|--------------------------------|---------------------------------|--------------------------------|---------------------------------|----------------------------|--------------------------------|------------------------------|------------------------------|---------------------------|
| 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | 19 | 20 | 21 | 22 | 23 | 24 | 25 | 26 | 27 | 28 | 29 | 30 | 31 | 32 | 33 | 34 | 35 | 36 | | | | | | | | | | | | | | | | | | |
| H 1.00794 Hydrogen | He 4.002602 Helium | Li 6.941 Lithium | Be 9.0122 Beryllium | B 10.811 Boron | C 12.011 Carbon | N 14.007 Nitrogen | O 15.999 Oxygen | F 18.998 Fluorine | Ne 20.180 Neon | Na 22.990 Sodium | Mg 24.305 Magnesium | Al 26.982 Aluminum | Si 28.086 Silicon | P 30.974 Phosphorus | S 32.06 Sulfur | Cl 35.45 Chlorine | Ar 39.948 Argon | K 39.098 Potassium | Ca 40.078 Calcium | Sc 44.956 Scandium | Ti 47.88 Titanium | V 50.942 Vanadium | Cr 52.00 Chromium | Mn 54.938 Manganese | Fe 55.845 Iron | Ni 58.693 Nickel | Cu 63.546 Copper | Zn 65.38 Zinc | Ga 69.723 Gallium | Ge 72.630 Germanium | As 74.922 Arsenic | Se 78.96 Selenium | Br 79.904 Bromine | Kr 83.798 Krypton | Rb 85.468 Rubidium | Sr 87.62 Strontium | Y 88.906 Yttrium | Zr 91.224 Zirconium | Nb 92.906 Niobium | Mo 95.94 Molybdenum | Tc 98.906 Technetium | Ru 101.07 Ruthenium | Rh 101.07 Rhodium | Pd 106.36 Palladium | Ag 107.868 Silver | Cd 112.411 Cadmium | Hg 200.59 Mercury | Tl 204.38 Thallium | Pb 207.2 Lead | Bi 208.98 Bismuth | Po 209 Polonium | At 210 Astatine | Rn 222 Radon |
| Fr 223 Francium | Ra 226 Radium | Ac 227 Actinium | Lr 260 Lawrencium | La 138.905 Lanthanum | Ce 140.12 Cerium | Pr 140.908 Praseodymium | Nd 144.24 Neodymium | Pm 144.913 Promethium | Sm 150.36 Samarium | Eu 151.964 Europium | Gd 157.25 Gadolinium | Tb 158.925 Terbium | Dy 162.50 Dysprosium | Ho 164.930 Holmium | Er 167.259 Erbium | Tm 168.930 Thulium | Yb 173.054 Ytterbium | Lu 174.967 Lutetium | U 238.029 Uranium | Th 232.038 Thorium | Pa 231.036 Protactinium | U 238.029 Uranium | Np 237.048 Neptunium | Pu 244.064 Plutonium | Am 243.061 Americium | Cm 247.070 Curium | Bk 247.070 Berkelium | Cf 251.08 Californium | Es 252.083 Einsteinium | Fm 257.10 Fermium | Md 288.10 Mendelevium | No 289.10 Nobelium | Lr 260 Lawrencium | | | | | | | | | | | | | | | | | | | | |

Periodic Table of Elements



- Physical State**
- Solid
 - Liquid
 - Gas
- Natural**
- Natural
 - Radioactive
 - Artificial

ISO 9001:2008
 ISO 14001:2004
 BS OHSAS 18001:2007
 Certified

Abbreviations and Codes

The following abbreviations are used throughout our listing of products.

| | | | |
|---------|--|------------------------------|--|
| Å | Angstrom | N | Normality of solution |
| AAS | Atomic absorption spectrometry | n _D ²⁰ | Refractive index for the sodium D line at 20 °C (or temperature indicated) |
| ACS | Chemicals meeting the specifications outlined by the American Chemical Society | nm | Nanometer |
| AES | Atomic emission spectrometry | NEW! | New product |
| APS | Average particle size | NMR | Nuclear magnetic resonance |
| anhy | Anhydrous | OD | Outer diameter |
| approx. | Approximately | oz | Ounce |
| aq. | Aqueous | optical gr. | Suitable for optical applications |
| Atm | Atmospheres | pc(s) | Piece(s) |
| b.p. | Boiling point in °C at 760mm pressure, unless otherwise specified | pH | Value taken to represent the acidity or alkalinity of an aqueous solution |
| (c) | Contained weight of active material | POR | Price on request |
| °C | Celsius | ppb | Parts per billion |
| ca | Circa | ppm | Parts per million |
| cc | Cubic centimeter | prec. | Precipitated |
| cm | Centimeter | Primary Standard | Analytical reagent of exceptional purity, for standardizing volumetric solutions and preparing reference standards |
| cont. | Contained | P.T. | Passes test |
| cP | Centipoise | PTFE | Poly(tetrafluoroethylene) |
| cS | Centistoke | Purified | A grade of higher quality than technical, often used where there are no official standards |
| d. | Density | P.V. | Pore volume |
| dec. | Decomposes | Reagent | Reagent grade |
| dia. | Diameter | REM | Rare earth metal |
| ea. | Each | (REO) | Rare earth oxide base - content of specific rare earth element in comparison to total rare earths present |
| ee | Enantiomeric excess | S.A. | Surface area |
| eV | Electron volt | soln. | Solution |
| °F | Fahrenheit | Sp.Gr. | Specific gravity |
| f.p. | Flash point | Sp.Rot. | Specific rotation |
| FSSS | Fisher sub-sieve sizer | stab. | Stabilized |
| F.W. | Formula weight | subl. | Sublimes |
| g | Gram | Tc | Critical temperature |
| g/l | Grams per liter (gas density) | tech. | Technical grade |
| GC | Gas chromatography | TLC | Thin-layer chromatography |
| GLC | Suitable for use in gas liquid chromatography | TSCA | Toxic Substance Control Act |
| HPLC | High-performance liquid chromatography | UN | Hazardous material transportation identification number |
| ICP | Inductively Coupled Plasma | λ | Wavelength in nanometers |
| ID | Inner diameter | wt | Weight |
| in | Inch | w/w | Weight/weight |
| incl | Includes | w/v | Weight/volume |
| IR | Infrared | XRD | X-ray diffraction |
| J/mol·K | Joule(s) per mole Kelvin | △ | Air sensitive |
| kg | Kilogram | ▣ | Moisture sensitive |
| L or l | Liter | ■ | Hygroscopic |
| lb | Pound | ▲ | Light sensitive |
| μ | Micro | ≈ | Approximately |
| μg | Microgram | > | Greater than |
| μm | Micrometer (micron) | ≥ | Greater than or equal to |
| m | Meter | < | Less than |
| M | Molarity of solution | ≤ | Less than or equal to |
| max | Maximum | [] | Numbers in brackets after the chemical description indicate the Chemical Abstract Service Registry Number |
| meq | Milliequivalent | - mesh # | 90% particles pass through screen having a given mesh size |
| Merck | The Merck Index | + mesh # | 90% particles are retained by a screen having a given mesh size |
| mg | Milligram | t | Denotes substance is listed in Toxic Substance Control Act (TSCA) inventory |
| micron | Micrometer | | |
| min. | Minimum | | |
| ml | Milliliter | | |
| mm | Millimeter | | |
| mmol | Millimole | | |
| Mn | Number averaged molecular weight | | |
| mol | Mole | | |
| m.p. | Melting point | | |
| M.W. | Molecular weight | | |
| Mw | Weighted averaged molecular weight | | |
| Mw/Mn | Monodispersity value | | |
| (N) | Nematic phase of a liquid crystal | | |

ACS Reagents

ACS reagents are high purity reagents for laboratory use. These reagents meet the specifications of the American Chemical Society (ACS) Committee on Analytical Reagents. These specifications are listed in the Tenth Edition of Reagent Chemicals: Specifications and Procedures.

| Description | Stock # | Page # |
|---|---------|--------|
| Acetic acid, glacial, ACS, 99.7+% | 36289 | 70 |
| Acetone, ACS, 99.5+% | 30698 | 71 |
| Amidosulfonic acid, ACS, 99.3-100.3% (Assay dried basis) | 33233 | 91 |
| Ammonium chloride, ACS, 99.5% min | 40193 | 101 |
| Ammonium dihydrogen phosphate, ACS, 98.0% min | 11598 | 101 |
| Ammonium hydrogen phosphate, ACS, 98.0% min | 11597 | 101 |
| Ammonium hydroxide, ACS, 28.0-30.0% NH ₃ | 33285 | 101 |
| Ammonium iron(III) sulfate dodecahydrate, ACS, 98.5-102.0% | 39391 | 101 |
| Ammonium iron(II) sulfate hexahydrate, ACS, 98.5-101.5% | 13448 | 101 |
| Ammonium sulfate, ACS, 99.0% min | 11566 | 102 |
| Barium chloride dihydrate, ACS | 12310 | 117 |
| Barium hydroxide octahydrate, ACS, 98+% | 14499 | 117 |
| Bromocresol Green, ACS | J65225 | 136 |
| Bromocresol Green sodium salt, ACS | J64284 | 136 |
| Bromophenol Blue, ACS | 32641 | 137 |
| Calcium carbonate, ACS, 99.0% min | 33295 | 143 |
| Calcium chloride dihydrate, ACS, 99.0-105.0% | 33296 | 143 |
| Calcium chloride, anhydrous, ACS, 96.0% min | 89866 | 143 |
| Cerium(IV) ammonium nitrate, ACS, 98.5% min | 33254 | 151 |
| Chloroacetic acid, ACS, 99+% | 41724 | 154 |
| Chloroform, ACS, 99.8+% | 32614 | 156 |
| Citric acid monohydrate, ACS, 99.0-102.0% | 36665 | 164 |
| Citric acid, anhydrous, ACS, 99.5+% | 36664 | 164 |
| Cobalt(II) chloride hexahydrate, ACS, 98.0-102.0% | 36554 | 166 |
| Crystal Violet, ACS, 90+% | 22866 | 170 |
| Dimethyl sulfoxide, ACS, 99.9% min | 36480 | 197 |
| Ethylenediaminetetraacetic acid disodium salt dihydrate, ACS, 99.0-101.0% | 33312 | 216 |
| Formaldehyde, 37% in aq. soln., ACS, 36.5-38.0%, stab. with 10-15% methanol | 33314 | 227 |
| Formic acid, ACS, 96+% | 36617 | 228 |
| Hexamethylenetetramine, ACS, 99+% | 36462 | 244 |
| Hydrazine sulfate, ACS, 99.0% min | 40120 | 247 |
| 8-Hydroxyquinoline, ACS | 41272 | 251 |
| Iron(III) chloride hexahydrate, ACS, 97.0-102.0% | 12497 | 259 |
| Lead(II) nitrate, ACS, 99.0% min | 14243 | 268 |
| Lithium carbonate, ACS, 99.0% min | 36225 | 271 |
| Lithium chloride, ACS, 99% min | 36217 | 272 |
| Lithium sulfate monohydrate, ACS, 99.0% min | 36216 | 272 |
| Magnesium sulfate heptahydrate, ACS, 98.0-102.0% | 11596 | 275 |
| Manganese(II) chloride tetrahydrate, ACS, 98.0-101.0% | 36526 | 277 |
| N-(1-Naphthyl)ethylenediamine dihydrochloride, ACS | J63214 | 298 |
| Nickel(II) sulfate hexahydrate, ACS, 98.0% min | 36336 | 301 |
| Nitilotriacetic acid, ACS, 98.0% min | 36515 | 303 |
| Orthophosphoric acid, 85% w/w aq. soln., ACS | 33266 | 309 |
| Oxalic acid dihydrate, ACS, 99.5-102.5% | 33262 | 310 |
| Phenol, ACS, 99+%, stab. | 33213 | 314 |
| Potassium chloride, ACS, 99.0-100.5% | 11595 | 326 |
| Potassium dihydrogen phosphate, ACS, 99.0% min | 11594 | 326 |
| Potassium hydrogen phosphate, ACS, 98.0% min | 11593 | 326 |
| Potassium hydroxide, ACS, 85% min, K ₂ CO ₃ 2.0% max | 13451 | 327 |
| Potassium sulfate, ACS, 99.0% min | 14311 | 328 |
| Potassium thiocyanate, ACS, 98.5% min | 14318 | 328 |
| Sodium acetate, anhydrous, ACS, 99.0% min | 11554 | 343 |
| Sodium acetate trihydrate, ACS, 99.0%-100.5% | 11553 | 343 |
| Sodium carbonate, anhydrous, ACS, 99.5% min | 11552 | 344 |
| Sodium carbonate, ACS primary standard, 99.95-100.05% (dried basis) | 33377 | 344 |
| Sodium dihydrogen phosphate monohydrate, ACS, 98.0-102.0% | 11591 | 345 |

| Description | Stock # | Page # |
|--|---------|--------|
| Sodium hydrogen carbonate, ACS, 99.7-100.3% | 14707 | 346 |
| Sodium hydrogen phosphate heptahydrate, ACS, 98.0-102.0% | 11592 | 346 |
| Sodium sulfate, ACS, 99.0% min | 11560 | 349 |
| Sodium tungsten oxide dihydrate, ACS, 99.0-101.0% | 36489 | 349 |
| Starch, soluble, ACS (for iodometry) | 36703 | 352 |
| 5-Sulfosalicylic acid dihydrate, ACS, 99+% | 43144 | 356 |
| Thymol Blue sodium salt, ACS | 42785 | 369 |
| Trisodium citrate dihydrate, ACS, 99.0% min | 36439 | 382 |
| Zinc chloride, ACS, 97% | 12307 | 396 |
| Zinc sulfate heptahydrate, ACS, 99.0-103.0% | 33399 | 396 |

Amino Acids and Derivatives

Amino acids are the building blocks of peptides and proteins. All amino acids contain a carboxylic acid group, an amine group, and a side-chain that varies for each amino acid. These side-chains differ in polarity and pH, and are important to both protein structure and function.

| Description | Stock # | Page # |
|---|---------|--------|
| N-Acetyl-DL-alanine, 97+% | L10329 | 71 |
| N-Acetyl-L-alanine, 96% | L11811 | 71 |
| N-Acetyl-L-glutamic acid, 99% | B23621 | 73 |
| N- α -Acetyl-L-glutamine, 99% | L06780 | 73 |
| N-Acetylglycine, 99% | B21887 | 73 |
| DL-N-Acetylhomocysteine thiolactone, 99% | B22741 | 73 |
| N-Acetyl-L-leucine, 99% | L13926 | 73 |
| N-Acetyl-DL-methionine, 99% | B21866 | 74 |
| N-Acetyl-L-phenylalanine, 99% | B23812 | 74 |
| N-Acetyl-L-proline, 99% | L14300 | 74 |
| N-Acetyl-L-tyrosine, 99% | A17307 | 75 |
| β -Alanine, 98% | A16665 | 82 |
| DL-Alanine, 99% | A12230 | 82 |
| D-Alanine, 99% | A10231 | 82 |
| L-Alanine, 99% | A15804 | 82 |
| 2-Allyl-N-Fmoc-L-glycine, 95% | H52177 | 89 |
| 4-Aminobenzoic acid, 99% | A12673 | 92 |
| 4-Aminobenzoic acid sodium salt, 99% | J63428 | 92 |
| 4-Amino-N-Boc-L-phenylalanine, 95% | H51980 | 92 |
| 4-Aminobutyric acid, 99+% | J61307 | 92 |
| 6-Aminohexanoic acid, 99% | A14719 | 95 |
| 2-Amino-5-hydroxybenzoic acid, 98% | L08256 | 95 |
| 2-Aminoisobutyric acid, 99% | A13021 | 96 |
| DL-Arginine, 98% | A17520 | 109 |
| D-Arginine, 98% | A16137 | 109 |
| L-Arginine, 98+% | A15738 | 109 |
| DL-Arginine monohydrochloride monohydrate, 98+% | A10758 | 109 |
| DL-Arginine hydrochloride | J61420 | 109 |
| D-Arginine monohydrochloride, 99% | A16222 | 109 |
| L-Arginine monohydrochloride, 98+% | A14730 | 109 |
| L-(+)-Asparagine, 99% | B21473 | 110 |
| DL-Asparagine monohydrate, 98% | B20273 | 110 |
| D-(-)-Asparagine monohydrate, 99% | B24556 | 111 |
| L-(+)-Asparagine monohydrate, 98+% | A15012 | 111 |
| DL-Aspartic acid, 98+% | A13646 | 111 |
| D-Aspartic acid, 99% | B21184 | 111 |
| L-Aspartic acid, 98+% | A13520 | 111 |
| L-Aspartic acid 4-benzyl ester, 98% | L08956 | 111 |
| L-Aspartic acid monosodium salt monohydrate, 99% | B22321 | 111 |
| N-Benzyloxycarbonyl-D-alaninol, 98% | B22372 | 122 |
| N-Benzyloxycarbonyl-L-alaninol | H27066 | 123 |
| N-Boc- β -alanine, 99% | B22522 | 129 |
| N-Boc-D-alanine, 98+% | B22706 | 129 |
| N-Boc-L-alanine, 98+% | A16018 | 129 |
| N-Boc- γ -aminobutyric acid, 98+% | B22407 | 129 |
| (S)-4-(Boc-amino)-2-(Fmoc-amino)butyric acid, 95% | H51990 | 129 |
| (S)-3-(Boc-amino)-5-methylhexanoic acid, 95% | H52173 | 129 |
| (S)-3-(Boc-amino)-4-phenylbutyric acid, 95% | H52174 | 129 |
| N(α)-Boc-L-asparagine, 98+% | A16019 | 129 |
| N-Boc-L-aspartic acid, 98+% | L08498 | 130 |
| N-Boc-L-aspartic acid 1-benzyl ester, 99% | B22314 | 130 |
| N-Boc-L-aspartic acid 4-benzyl ester, 98% | B21758 | 130 |
| N-Boc-O-benzyl-D-serine, 99% | B22666 | 130 |
| N-Boc-O-benzyl-L-threonine, 99% | B21677 | 130 |
| N-Boc-O-benzyl-L-tyrosine, 98% | B23455 | 130 |
| N-Boc-4-bromo-L-phenylalanine, 98% | H51969 | 130 |
| N-Boc-3-chloro-L-phenylalanine, 95% | H52015 | 130 |
| N-Boc-4-chloro-D-phenylalanine, 95% | H52181 | 130 |

| Description | Stock # | Page # |
|--|---------|--------|
| N(α)-Boc-N(ϵ),N(ϵ)-dimethyl-L-lysine, 97% | H52437 | 130 |
| N-Boc-O-ethyl-L-serine, 97% | H52781 | 130 |
| N-Boc-3-fluoro-D-phenylalanine, 98% | H51963 | 130 |
| N-Boc-3-fluoro-L-phenylalanine, 95% | H51988 | 130 |
| N(ω)-Boc-N(β)-Fmoc-L- β -homolysine, 95% | H52189 | 130 |
| N(ϵ)-Boc-N(α)-Fmoc-D-lysine, 98% | H28301 | 130 |
| N-Boc-D-glutamic acid 1-benzyl ester, 99% | B21944 | 130 |
| N-Boc-L- β -glutamic acid 5-benzyl ester, 95% | H52191 | 131 |
| N-Boc-L-glutamic acid 5-tert-butyl ester, 99% | B22322 | 131 |
| N(α)-Boc-D-glutamine, 98+% | L08536 | 131 |
| N(α)-Boc-L-glutamine, 98+% | L08604 | 131 |
| N-Boc-glycine, 98+% | A11579 | 131 |
| N(α)-Boc-D-histidine, 98+% | L08810 | 131 |
| N(α)-Boc-L-histidine, 98+% | B22042 | 131 |
| N-Boc-4-iodo-L-phenylalanine, 98% | H51960 | 131 |
| N-Boc-D-leucine hydrate, 98+% | L09124 | 131 |
| N(ϵ)-Boc-L-lysine, 97% | B21738 | 131 |
| N-Boc-L-tert-leucine, 98% | H51136 | 133 |
| N-Boc-D-methionine, 98+% | L09207 | 131 |
| N-Boc-L-methionine, 98+% | L08366 | 131 |
| N-Boc-4-methoxy-D-phenylalanine, 95% | H52082 | 131 |
| N-Boc-N-methyl-L-alanine, 98% | H31317 | 131 |
| N-Boc-4-methyl-L-phenylalanine, 95% | H51983 | 132 |
| N-Boc-2-methyl-D-serine, 97% | H52787 | 132 |
| N-Boc-2-methyl-L-serine, 97% | H52570 | 132 |
| N-Boc-3-nitro-L-phenylalanine, 95% | H52058 | 132 |
| N-Boc-4-nitro-L-phenylalanine, 95% | H51986 | 132 |
| N-Boc-L-norvaline, 98+% | L08615 | 132 |
| N-Boc-D-phenylalanine, 98% | L08722 | 132 |
| N-Boc-L-phenylalanine, 99% | A16017 | 132 |
| N-Boc-D-phenylglycine, 99% | L18540 | 132 |
| N-Boc-L-phenylglycine, 99% | L18541 | 132 |
| N-Boc-D-proline, 98+% | L08826 | 132 |
| N-Boc-L-proline, 99% | A13744 | 132 |
| N-Boc-L-prolinol, 98+% | L09885 | 132 |
| N-Boc-2-propargyl-L-glycine, 95% | H52128 | 132 |
| N-Boc-D-serine, 98+% | L08904 | 132 |
| N-Boc-L-serine, 98% (dry wt.), may cont. up to 10% water | A16224 | 132 |
| N-Boc-L-threonine, 98+% | L09111 | 133 |
| N-Boc-trans-4-hydroxy-L-proline, 97% | H27110 | 131 |
| N(α)-Boc-D-tryptophan, 97% | L09214 | 133 |
| N(α)-Boc-L-tryptophan, 98+% | A16023 | 133 |
| N-Boc-L-tyrosine, 98+% | A10810 | 133 |
| N-Boc-L-tyrosine methyl ester, 99% | B22164 | 133 |
| N-Boc-D-valine, 98+% | L09193 | 133 |
| N-Boc-L-valine, 98+% | A16007 | 133 |
| 4-Bromo-N-Fmoc-L-phenylalanine, 95% | H51978 | 137 |
| O-tert-Butyl-N-Fmoc-L- β -homoserine, 95% | H52065 | 141 |
| O-tert-Butyl-N-Fmoc-L- β -homotyrosine, 95% | H52192 | 141 |
| L-Carnitine, 99+% | A17618 | 148 |
| 4-Chloro-D-phenylalanine, 95% | H51982 | 158 |
| L-Citrulline, 98% | A13316 | 165 |
| D-Cycloserine, 98+% | A18000 | 172 |
| Cystamine dihydrochloride, 97+% | B22873 | 172 |
| DL-Cysteine, 96% | H56126 | 172 |
| L-Cysteine, 98+% | A10435 | 172 |
| D-Cysteine hydrochloride monohydrate, 99% | H27107 | 173 |
| L-Cysteine hydrochloride monohydrate, 99% | A10389 | 173 |
| L-Cysteine hydrochloride, anhydrous, 98% | L06328 | 173 |
| DL-Cystine | J63564 | 173 |
| D-Cystine, 98% | L13772 | 173 |
| L-Cystine, 99% | A13762 | 173 |
| L-Cystine dihydrochloride, 99% | J62292 | 173 |
| L-Cystine disodium salt monohydrate, 98+% | J63071 | 173 |
| L-Cystine disodium salt, 98+% | J62310 | 173 |
| N(α)-Ethoxycarbonyl-L-asparagine, 97% | L09327 | 214 |

| Description | Stock # | Page # |
|--|---------|--------|
| 4-Fluoro-N-Fmoc-L-phenylalanine, 95% | H51972 | 224 |
| N-Fmoc-L-alanine monohydrate, 98% | B21107 | 225 |
| 4-(Fmoc-amino)benzoic acid, 97% | H52828 | 225 |
| L-3-(Fmoc-amino)-N-trityladipic acid 6-amide, 95% | H52195 | 225 |
| N(α)-Fmoc-L-asparagine, 98% | B21008 | 225 |
| N-Fmoc-L- β -glutamic acid 5-tert-butyl ester, 95% | H52190 | 225 |
| N-Fmoc-glycine, 98% | B21050 | 225 |
| N-Fmoc-L- β -homoalanine, 95% | H52178 | 225 |
| N-Fmoc-L- β -homoglutamic acid 6-tert-butyl ester, 95% | H52188 | 225 |
| N-Fmoc-L- β -homoleucine, 95% | H51976 | 225 |
| N-Fmoc-L- β -homoproline, 95% | H52060 | 225 |
| N-Fmoc-L- β -homovaline, 95% | H52182 | 225 |
| trans-N-Fmoc-4-hydroxy-L-proline, 97% | H52740 | 226 |
| N-Fmoc-L-isoleucine, 98% | B21154 | 226 |
| N-Fmoc-D-leucine, 98% | H29041 | 226 |
| N-Fmoc-L-leucine, 98% | B21040 | 226 |
| N-Fmoc-L-methionine, 98+% | B21220 | 226 |
| N-Fmoc-4-methoxy-L-phenylalanine, 95% | H52117 | 226 |
| N-Fmoc-4-nitro-L-phenylalanine, 98% | H51962 | 226 |
| N-Fmoc-L-norleucine, 98% | B22475 | 226 |
| N-Fmoc-D-phenylalanine, 98% | B21689 | 226 |
| N-Fmoc-L-phenylalanine, 98+% | B21210 | 226 |
| N-Fmoc-D-proline, 98+%, may cont. up to ca 5% water | H28500 | 226 |
| N-Fmoc-L-proline, 98% | B21081 | 226 |
| N-Fmoc-L-propargylglycine, 95% | H52171 | 226 |
| N-Fmoc-3-(4-pyridyl)-D-alanine, 95% | H52193 | 226 |
| N-Fmoc-3-(4-pyridyl)-L-alanine, 95% | H52172 | 226 |
| N-Fmoc-L-serine, 97+% | B21079 | 226 |
| (S)-N-Fmoc-1,2,3,4-tetrahydroisoquinoline-3-carboxylic acid, 95% | H51975 | 227 |
| N-Fmoc-S-trityl-L-cysteine, 95% | H27363 | 227 |
| N(α)-Fmoc-D-tryptophan, 98% | B22022 | 227 |
| N(α)-Fmoc-L-tryptophan, 98% | B21130 | 227 |
| N-Fmoc-L-valine, 98% | B21030 | 227 |
| D-Glutamic acid, 99+% | A14191 | 234 |
| L-Glutamic acid, 99+% | A15031 | 234 |
| DL-Glutamic acid monohydrate, 99% | A17719 | 234 |
| L-Glutamic acid monosodium salt | J63424 | 234 |
| L-Glutamic acid hydrochloride, 99% | A12505 | 234 |
| L-Glutamic acid 5-methyl ester, 99% | B24859 | 235 |
| D-Glutamine, 99+% | J60784 | 235 |
| L-Glutamine, 99+% | J61560 | 235 |
| γ -L-Glutamyl-4-nitroanilide, 98+% | A14442 | 235 |
| Glycine, ACS, 98.5+% | 43497 | 236 |
| Glycine, 99.5+% | 36435 | 237 |
| Glycine anhydride, 99% | A18822 | 237 |
| Histamine | J61727 | 245 |
| Histamine dihydrochloride, 98+% | L09198 | 245 |
| Histamine diphosphate, 99+% | J61088 | 245 |
| D-Histidine, 99% | B21027 | 245 |
| L-Histidine, 98+% | A10413 | 245 |
| DL-Histidine monohydrochloride monohydrate, 99% | A16165 | 246 |
| L-Histidine monohydrochloride monohydrate, 99% | A17627 | 246 |
| DL- β -Homoproline hydrochloride, 97% | H31749 | 246 |
| D-(-)-4-Hydroxyphenylglycine, 98+% | L07190 | 251 |
| DL-5-Hydroxytryptophan, 99% | A12237 | 252 |
| L-5-Hydroxytryptophan hydrate, 98% | A13954 | 252 |
| D-Isoleucine, 98% | H27488 | 260 |
| DL-Isoleucine, 99% | A17521 | 260 |
| L-Isoleucine, 99% | A13699 | 260 |
| D-Leucine, 99% | A14842 | 268 |
| L-Leucine, 99% | A12311 | 268 |
| DL-Leucine, 99% | A10590 | 268 |
| L-Leucinol, 97% | B23745 | 268 |
| L-Lysine, 98% | J62225 | 273 |
| DL-Lysine monohydrochloride, 99% | A11066 | 273 |
| D-Lysine monohydrochloride, 98% | L07710 | 273 |

| Description | Stock # | Page # |
|--|---------|--------|
| L-Lysine monohydrochloride, 99+% | A16249 | 273 |
| L-Lysine monohydrochloride, Cell Culture Reagent | J62099 | 273 |
| L-Lysine methyl ester dihydrochloride, 99% | A18157 | 273 |
| DL-Methionine, 99% | A11457 | 283 |
| D-Methionine, 99% | B21213 | 284 |
| L-Methionine, 98+% | A10318 | 284 |
| L-Methionine, Cell Culture Reagent | J61904 | 284 |
| DL-Methionine sulfone, 98% | B25094 | 284 |
| L-Methionine sulfone, 99+% | A17027 | 284 |
| DL-Methionine sulfoxide, 98+% | A18081 | 284 |
| L-Methionine sulfoxide | J62873 | 284 |
| N-Methyl-L-arginine | J62431 | 286 |
| N-Methyl-D-aspartic acid, 98+% | J61361 | 286 |
| (R)-(-)- α -Methylhistamine dihydrochloride | J61636 | 288 |
| α -Methyl-DL-histidine dihydrochloride, 99% | J60865 | 288 |
| D-(-)-Norleucine, 99% | L08257 | 304 |
| L-(+)-Norleucine, 99% | L03913 | 305 |
| DL-Norvaline, 98% | A15900 | 305 |
| D-Norvaline, 99% | B23444 | 305 |
| L-Norvaline, 99% | L08658 | 305 |
| DL-Ornithine monohydrochloride, 99% | A18173 | 308 |
| D-Ornithine hydrochloride, 98+% | L00793 | 308 |
| L-Ornithine hydrochloride, 99% | A12111 | 309 |
| DL-Phenylalanine, 99% | A10132 | 315 |
| D-Phenylalanine, 99% | A10572 | 315 |
| L-Phenylalanine, 99% | A13238 | 315 |
| D-Phenylalaninol, 98% | L09697 | 316 |
| L-Phenylalaninol, 98% | A11586 | 316 |
| D-(-)-2-Phenylglycine, 99% | A15669 | 317 |
| L-(+)-2-Phenylglycine, 98+% | A19360 | 317 |
| N-Phenylglycine, 97% | A14182 | 317 |
| Sarcosine, 98% | A14594 | 340 |
| Sarcosine hydrochloride, 99% | B25536 | 340 |
| DL-Serine, 99% | A15184 | 341 |
| D-Serine, 99% | A11353 | 341 |
| L-Serine, 99% | A11179 | 341 |
| L-Serine, Cell Culture Reagent | J62187 | 341 |
| Serotonin hydrochloride, 99% | B21263 | 342 |
| Taurine, 99% | A12403 | 359 |
| DL-Threonine, 99% | A10606 | 368 |
| D-Threonine, 99% | B21177 | 368 |
| L-Threonine, 98+% | A16851 | 368 |
| N-Tritylglycine, 97% | L09095 | 383 |
| DL-Tryptophan, 99% | L05936 | 384 |
| D-Tryptophan, 99% | A18426 | 384 |
| L-Tryptophan, 99% | A10230 | 384 |
| Tryptophol, 97% | L02555 | 385 |
| L-Tyrosine disodium salt dihydrate, 99% | J61770 | 386 |
| DL-Valine, 99% | A16756 | 390 |
| D-Valine, 98+% | A18894 | 390 |
| L-Valine, 99% | A12720 | 390 |

Antibiotics

Antibiotics are molecules that either kill or prevent the growth of microorganisms. The term antibiotic is frequently used interchangeably with the word antibacterial, but antiviral, antifungal and antineoplastic compounds are also classified as antibiotics. Antibiotics work by a number of different actions including inhibition or regulation of cell wall synthesis, nucleic acid metabolism, and protein synthesis.

| Description | Stock # | Page # |
|--|---------|--------|
| Actinomycin D | J60148 | 78 |
| Amikacin | J60849 | 91 |
| Amikacin disulfate | J63862 | 91 |
| 7-Aminocephalosporanic acid, 98% (dry wt.), may cont. up to 2% water | A10530 | 92 |
| 7-Aminodesacetoxycephalosporanic acid, 98% | L03417 | 93 |
| Amoxicillin trihydrate | J61290 | 102 |
| Amphotericin B, <i>Streptomyces nodosus</i> | J61491 | 103 |
| Ampicillin | J60977 | 103 |
| Antibiotic A23187, 99+% | J63020 | 105 |
| Apramycin, 98+% | J63874 | 108 |
| Aztreonam | J62887 | 116 |
| Bacitracin | J62432 | 116 |
| Bafilomycin A1 | J61835 | 116 |
| Bleomycin sulfate | J60727 | 128 |
| Carbenicillin disodium salt | J61949 | 147 |
| Cefotaxime sodium salt | J62690 | 151 |
| Cephalexin hydrate, 97+% | J63172 | 151 |
| Chloramphenicol, 99+% | B20841 | 154 |
| Chlortetracycline hydrochloride | J60095 | 160 |
| Ciprofloxacin, 98% | J61317 | 163 |
| Clindamycin hydrochloride monohydrate | J61409 | 165 |
| Clindamycin phosphate | J63387 | 165 |
| Colistin sulfate | J60915 | 167 |
| Cyclosporin A, 99+% | J63191 | 172 |
| Danofloxacin | J62904 | 175 |
| Daunorubicin hydrochloride | J60224 | 175 |
| Demeclocycline hydrochloride | J63102 | 176 |
| Dicloxacillin sodium salt | J61581 | 186 |
| Dihydrostreptomycin sesquisulfate | J60495 | 191 |
| Doxycycline hyclate | J60579 | 202 |
| Doxycycline hydrochloride | J60422 | 202 |
| Enoxacin | J61912 | 207 |
| Enrofloxacin | J60023 | 207 |
| Epirubicin hydrochloride | J60411 | 209 |
| Erythromycin, Cell Culture Grade | J62279 | 210 |
| G418 disulfate, 50mg/ml solution | J63871 | 229 |
| Geldanamycin, 99+% | J63397 | 231 |
| Gentamycin sulfate, 600 I.U./mg | J62834 | 231 |
| Hygromycin B | J60681 | 252 |
| Isonicotinic acid hydrazide, 98+% | A10583 | 261 |
| Ivermectin | J62777 | 262 |
| Josamycin, 98+% | J62245 | 262 |
| Kanamycin monosulfate | J61272 | 262 |
| Leptomycin B, 99+%, 1mM soln. in ethanol | J63784 | 268 |
| Lincomycin hydrochloride | J61251 | 270 |
| Monensin sodium salt, 90-95.5% | J61669 | 294 |
| Neomycin sulfate hydrate | J61499 | 299 |
| 5-Nitro-2-furaldehyde semicarbazone, 98+% | A18593 | 304 |
| Nitrofurantoin, 98% | B24079 | 304 |
| Norfloxacin | J62652 | 304 |
| Novobiocin sodium salt | J60928 | 305 |
| Nystatin | J62486 | 305 |
| Ofloxacin | J62080 | 306 |
| Oligomycin | J61898 | 307 |
| Oligomycin A, 99+% | J60211 | 307 |
| Oxytetracycline, 98+% | J62427 | 310 |

Antibiotics

| Description | Stock # | Page # |
|--|---------|--------|
| Paromomycin sulfate | J61274 | 312 |
| Penicillin G potassium salt | J63901 | 313 |
| Penicillin G sodium salt | J63032 | 313 |
| Penicillin V potassium salt | J62442 | 313 |
| Polymixin B sulfate | J63074 | 325 |
| Puromycin, 98+% | J60175 | 331 |
| Puromycin dihydrochloride, 99+% | J61278 | 331 |
| Rapamycin, 99+% | J62473 | 335 |
| Rifampin, Molecular Biology Grade | J60836 | 338 |
| Rifamycin SV sodium, 98+% | J63095 | 338 |
| Spectinomycin dihydrochloride pentahydrate, Cell Culture Grade | J61820 | 350 |
| Streptomycin sulfate, Cell Culture Reagent | J61299 | 352 |
| Streptozotocin, 97+% | J61601 | 352 |
| Sulfacetamide, 98% | A19836 | 355 |
| Sulfamerazine, 98+% | L04194 | 355 |
| Tetracycline | J61714 | 361 |
| Thiamphenicol | J63575 | 366 |
| Thiostrepton, Streptomyces laurentii, 90+% | J62332 | 368 |
| Tobramycin sulfate | J62995 | 370 |
| Tunicamycin, 95% | J62217 | 385 |
| Tylosin tartrate, 98+% | J62633 | 386 |
| Valinomycin, 90+% | J62312 | 390 |
| Vancomycin hydrochloride, Molecular Biology Grade | J62790 | 390 |

Antibodies

An antibody is a large Y-shaped protein that is used by the immune system to identify and neutralize foreign objects such as bacteria and viruses. Using a binding mechanism, an antibody can tag a microbe or an infected cell for attack by other parts of the immune system, or can neutralize its target directly. Alfa Aesar offers antibodies to the cytoskeletal proteins, growth & attachment factors, lipoproteins, hormones and keratinocyte differentiation markers are also offered. Most of the antibodies are provided lyophilized or in buffer containing 0.02% sodium azide.

| Description | Stock # | Page # |
|--|---------|--------|
| Anti-Apo[a] antibody, from goat | J64642 | 105 |
| Anti-Fibroblast Growth Factor, basic, from rabbit | J65053 | 105 |
| Anti-cyclic AMP antibody | J64001 | 105 |
| Anti-cyclic AMP antibody, preconjugated | J64263 | 105 |
| Anti-cyclic GMP antibody | J64025 | 105 |
| Anti-cyclic GMP antibody, preconjugated | J64514 | 105 |
| Anti-Cytokeratin antibody, from rabbit, whole serum | J65649 | 105 |
| Anti-EGF antibody, from rabbit | J65390 | 105 |
| Anti-EGF antibody, from rabbit | J65464 | 105 |
| Anti-EGF antibody, from rabbit, whole serum | J64008 | 105 |
| Anti-EGF antibody, from rabbit, whole serum | J65866 | 105 |
| Anti-Fibronectin, antibody, from rabbit | J64158 | 106 |
| Anti-Fibronectin antibody, from rabbit | J65644 | 106 |
| Anti-Fibronectin antibody, from rabbit, whole serum | J64763 | 106 |
| Anti-GFAP antibody, from rabbit | J64334 | 106 |
| Anti-Goat IgG, from donkey | J64177 | 106 |
| Anti-Involucrin antibody kit | J65602 | 106 |
| Anti-Laminin antibody, from rabbit | J65295 | 106 |
| Anti-LDL antibody, from rabbit | J64398 | 106 |
| Anti-Lysozyme antibody, from mouse | J65202 | 106 |
| Anti-Mouse IgG-Peroxidase, from goat | J64787 | 106 |
| Anti-Myosin (Smooth Muscle) antibody, from rabbit | J64817 | 106 |
| Anti-Myosin antibody, from rabbit | J64913 | 106 |
| Anti-Nerve Growth Factor antibody, from rabbit | J64696 | 106 |
| Anti-Osteocalcin antibody, from goat, whole serum | J65216 | 106 |
| Anti-Osteocalcin antibody, from goat, whole serum, RIA Grade | J64663 | 106 |
| Anti-Osteocalcin antibody, from rabbit, whole serum | J64503 | 107 |
| Anti-Osteocalcin antibody, from rabbit, whole serum | J65982 | 107 |
| Anti-Platelet Derived Growth Factor-BB antibody, from sheep | J64286 | 107 |
| Anti-Rabbit IgG, from goat | J64160 | 107 |
| Anti-Rabbit IgG-FITC from goat | J64967 | 107 |
| Anti-Rabbit IgG-Peroxidase, from goat | J64155 | 107 |
| Anti-Rabbit IgG-TRITC, from goat | J65031 | 107 |
| Anti-Sheep IgG, from donkey | J65931 | 107 |
| Anti-Tamm Horsfall Glycoprotein antibody, from rabbit | J65429 | 107 |
| Anti-Transglutaminase Type I antibody | J65575 | 107 |
| Anti-Myosin IIA (non muscle) antibody, from rabbit | J65418 | 106 |

Apoptosis Reagents

Apoptosis is a highly regulated programmed cell death. It is a critical part of normal cell development, immunity and wound repair. Abnormalities in apoptosis can lead to a variety of pathologies including cancer and neurodegenerative disease. At least three major pathways are known to initiate apoptosis and the choice of the correct apoptosis reagent depends on which of these pathways you desire to activate. This list contains reagents that are commonly used in apoptosis protocols.

| Description | Stock # | Page # |
|--|---------|--------|
| Acemetacin | J63583 | 69 |
| Acivicin, 98+% | J63105 | 76 |
| Acridine Orange, dye content 55-65% | L13159 | 76 |
| Actinomycin D | J60148 | 78 |
| Alendronate sodium trihydrate, 97% | J61397 | 88 |
| Alloxan monohydrate, 98% | A15324 | 89 |
| 6-Aminonicotinamide, 99% | L06692 | 98 |
| Amiodarone hydrochloride | J60456 | 100 |
| Anisomycin, 97+% | J62964 | 104 |
| Antimycin A | J63522 | 106 |
| Aphidicolin | J60236 | 107 |
| Arvanil, 98% | J62812 | 110 |
| Bambuterol hydrochloride, 98+% | J60424 | 117 |
| Benzamidine hydrochloride, 99% | J62823 | 119 |
| Benzylphosphonic acid, 97% | A13850 | 123 |
| Berberine chloride | J62311 | 123 |
| Bezafibrate, 98+% | J61412 | 124 |
| Brefeldin A, 99% | J62340 | 135 |
| Calyculin A, 98+% | J61952 | 144 |
| Camptothecin | J62523 | 145 |
| Chelerythrine chloride, 99+% | J62906 | 153 |
| Chenodeoxycholic acid | J60364 | 153 |
| Chlorambucil, 98% | J61964 | 154 |
| Clofibrate, 95+% | J60342 | 165 |
| Clomiphene citrate | J63663 | 165 |
| Colchicine, 98+% | J61072 | 167 |
| Concanavalin A | J61221 | 167 |
| Cyclophosphamide monohydrate, 97+% | L11508 | 172 |
| Cyclosporin A, 99+% | J63191 | 172 |
| Cyproconazole | J63142 | 172 |
| Dacarbazine | J61023 | 174 |
| Danazol | J62200 | 175 |
| Daunorubicin hydrochloride | J60224 | 175 |
| N,N'-Diacetyl-1,6-diaminohexane, 98+% | B22771 | 182 |
| 4',7-Dihydroxyisoflavone, 98+% | J63763 | 192 |
| Diosmin | J62073 | 198 |
| Docetaxel | J60174 | 201 |
| Doxorubicin hydrochloride | J64000 | 202 |
| Doxycycline hydrochloride | J60422 | 202 |
| Ebselen | J63190 | 204 |
| Ecdysterone | J63091 | 204 |
| Ellagic acid hydrate, 97%, may cont. up to 12% water | A15722 | 205 |
| Enalapril | J60750 | 206 |
| Enalaprilat | J63392 | 206 |
| (-)-Epicatechin | J61218 | 208 |
| (-)-Epicatechin gallate | J60814 | 208 |
| (-)-Epigallocatechin | J61630 | 209 |
| Epirubicin hydrochloride | J60411 | 209 |
| Etoposide | J63651 | 217 |
| Evodiamine | J62771 | 218 |
| Farnesol, mixture of isomers, 96% | A19316 | 218 |
| Haloperidol | J61688 | 241 |
| Harmol | J61135 | 241 |
| Honokiol, 98+% | J63434 | 246 |

| Description | Stock # | Page # |
|--|---------|--------|
| Hypericin, 98% | H26425 | 253 |
| Imiquimod, 99% | J63990 | 255 |
| Irinotecan hydrochloride | J60743 | 259 |
| Kaempferol, 98+% | J60373 | 262 |
| Margaritoxin, 99+% | J61103 | 278 |
| Melatonin, 99+% | J62452 | 279 |
| Mevastatin, 98% | J61357 | 291 |
| Mitomycin C | J63193 | 292 |
| Monensin sodium salt, 90-95.5% | J61669 | 294 |
| Nifedipine, 98% | J62811 | 302 |
| Nimesulide | J63699 | 303 |
| Orlistat, 98% | J62999 | 308 |
| Phenylethyl 3,4-dihydroxycinnamate, 99+% | J61386 | 316 |
| Prostratin, 99+% | J60971 | 329 |
| Resiniferatoxin, 99+% | J62458 | 336 |
| SB 202190, 99+% | J60950 | 340 |
| SB 203580, 99% | J61482 | 341 |
| D-erythro-Sphingosine, 99+% | J63584 | 351 |
| Sulindac | J61772 | 356 |
| Sulindac sulfide | J62104 | 356 |
| Suramin hexasodium salt, 98+% | J61707 | 356 |
| Tamoxifen, 98+% | J63509 | 357 |
| Temsirolimus, 99+% | J63654 | 360 |
| 3',4',5,7-Tetrahydroxyflavone, 97% | L14186 | 363 |
| Ticlopidine hydrochloride | J63971 | 370 |
| Toremifene, 98+% | J63803 | 371 |
| Tozasertib, 99+% | J63232 | 372 |
| 4',5,7-Trihydroxyflavone, 97% | L15041 | 377 |
| Vargatef, 99+% | J63082 | 391 |
| Vinblastine sulfate, 98% | J63598 | 392 |
| Vincristine sulfate, 98+% | J60907 | 392 |

Buffers

Buffers are aqueous solutions of weak acids and their conjugate bases or weak bases and their conjugate acids. Buffers show little change in pH when small amounts of strong acids and bases are added. Buffer solutions are used as a means of keeping pH at a nearly constant value. The pH plays an important role in many biochemical processes and can affect internal and external environments of living tissue. Living organisms have developed mechanisms to maintain a normal pH for each cell or organ system. Buffer solutions are often necessary to maintain the correct pH for enzymes and proteins, as many proteins require very precise conditions to function properly.

| Description | Stock # | Page # |
|--|---------|--------|
| ACES, 99% | A11553 | 69 |
| ACES, 0.5M buffer soln., pH 6.0 | J61761 | 69 |
| ACES, 0.5M buffer soln., pH 6.5 | J60366 | 70 |
| ACES, 0.5M buffer soln., pH 7.0 | J60755 | 70 |
| ACES, 0.5M buffer soln., pH 7.5 | J61011 | 70 |
| Acetate, 1M buffer soln., pH, 3.0 | J63876 | 70 |
| Acetate, 1M buffer soln., pH, 3.5 | J60340 | 70 |
| Acetate, 1M buffer soln., pH, 4.0 | J60104 | 70 |
| Acetate, 1M buffer soln., pH, 5.0 | J60964 | 70 |
| Acetate, 1M buffer soln., pH, 5.5 | J61033 | 70 |
| ADA, 98+% | A15267 | 78 |
| ADA, 0.2M buffer soln., pH 6.0 | J60054 | 78 |
| ADA, 0.2M buffer soln., pH 6.5 | J61259 | 78 |
| ADA, 0.2M buffer soln., pH 7.0 | J61176 | 78 |
| ADA, 0.2M buffer soln., pH 7.5 | J62424 | 78 |
| Alkaline Phosphatase Buffer-1 (5X) | J62907 | 89 |
| Alkaline running buffer soln. | J63170 | 89 |
| 2-Amino-2-ethyl-1,3-propanediol, 97% | B24509 | 94 |
| 2-Amino-2-methyl-1,3-propanediol, 99+% | J63144 | 97 |
| AMP, 0.2M buffer soln., pH 9.0 | J62043 | 102 |
| AMP, 0.2M buffer soln., pH 9.5 | J63988 | 102 |
| AMP, 0.2M buffer soln., pH 10.0 | J63290 | 102 |
| AMP, 0.2M buffer soln., pH 10.5 | J62474 | 102 |
| AMPD, 0.2M buffer soln., pH 7.5 | J60276 | 102 |
| AMPD, 0.2M buffer soln., pH 8.9 | J61377 | 102 |
| AMPD, 0.2M buffer soln., pH 9.5 | J60916 | 102 |
| AMPSO, 98+% | J62378 | 103 |
| AMPSO, 0.2M buffer soln., pH 8.0 | J61467 | 103 |
| AMPSO, 0.2M buffer soln., pH 8.5 | J61238 | 103 |
| AMPSO, 0.2M buffer soln., pH 9.0 | J62328 | 103 |
| AMPSO, 0.2M buffer soln., pH 9.5 | J63354 | 103 |
| BES, 99% | A16092 | 123 |
| BES, 0.5M buffer soln., pH 6.0 | J60058 | 123 |
| BES, 0.5M buffer soln., pH 6.5 | J60624 | 123 |
| BES, 0.5M buffer soln., pH 7.0 | J60061 | 123 |
| BES, 0.5M buffer soln., pH 7.5 | J63168 | 123 |
| BES-buffered saline (2X) | J61955 | 123 |
| Bicarbonate, 1M buffer soln., pH 8.0 | J63491 | 124 |
| Bicarbonate, 1M buffer soln., pH 8.5 | J60092 | 124 |
| Bicarbonate, 1M buffer soln., pH 9.0 | J60116 | 124 |
| BICINE, 99% | A14957 | 124 |
| BICINE, 0.5M buffer soln., pH 7.5 | J60494 | 124 |
| BICINE, 0.5M buffer soln., pH 8.0 | J63924 | 124 |
| BICINE, 0.5M buffer soln., pH 8.5 | J61632 | 124 |
| BICINE, 0.5M buffer soln., pH 9.0 | J62838 | 124 |
| 2,2-Bis(hydroxymethyl)-2,2',2"-nitrilotriethanol, 98+% | B22515 | 127 |
| BIS-TRIS, 0.5M buffer soln., pH 6.0 | J62928 | 127 |
| BIS-TRIS, 0.5M buffer soln., pH 6.5 | J63036 | 127 |
| BIS-TRIS, 0.5M buffer soln., pH 7.0 | J60656 | 127 |
| BIS-TRIS, 0.5M buffer soln., pH 7.5 | J62177 | 127 |
| 1,3-Bis[tris(hydroxymethyl)methylamino]propane, 98+% | 43496 | 128 |
| BIS-TRIS propane, 0.2M buffer soln., pH 7.0 | J63555 | 128 |
| BIS-TRIS propane, 0.2M buffer soln., pH 7.5 | J61292 | 128 |

| Description | Stock # | Page # |
|---|---------|--------|
| BIS-TRIS propane, 0.2M buffer soln., pH 8.0 | J62831 | 128 |
| BIS-TRIS propane, 0.2M buffer soln., pH 8.5 | J62012 | 128 |
| BIS-TRIS propane, 0.2M buffer soln., pH 9.0 | J63943 | 128 |
| BIS-TRIS propane, 0.5M buffer soln., pH 6.5 | J62354 | 128 |
| Borate, 0.5M buffer soln., pH 8.5 | J60803 | 133 |
| Borate, 0.5M buffer soln., pH 9.0 | J62125 | 134 |
| Borate, 0.5M buffer soln., pH 9.5 | J62154 | 134 |
| Borate-buffered saline (5X) | J60979 | 134 |
| CABS, 0.2M buffer soln., pH 10.5 | J61832 | 141 |
| CAPS, 99% | A17037 | 145 |
| CAPS, 0.5M buffer soln., pH 9.0 | J63749 | 145 |
| CAPS, 0.5M buffer soln., pH 9.0 | J60022 | 145 |
| CAPS, 0.5M buffer soln., pH 9.5 | J60776 | 145 |
| CAPS, 0.5M buffer soln., pH 10.0 | J60569 | 146 |
| CAPS, 0.5M buffer soln., pH 10.5 | J62446 | 146 |
| CAPS, 0.5M buffer soln., pH 11.0 | J63138 | 146 |
| CAPSO, 98% | B21305 | 146 |
| CAPSO, 0.2M buffer soln., pH 8.5 | J60973 | 146 |
| CAPSO, 0.2M buffer soln., pH 9.0 | J61126 | 146 |
| CAPSO, 0.2M buffer soln., pH 9.5 | J63242 | 146 |
| CAPSO sodium salt, 98% | B25202 | 146 |
| Carbonate, 0.5M buffer soln., pH 9.0 | J63899 | 147 |
| Carbonate, 0.5M buffer soln., pH 9.4 | J61064 | 147 |
| Carbonate, 0.5M buffer soln., pH 9.5 | J63658 | 147 |
| Carbonate, 0.5M buffer soln., pH 9.6 | J62610 | 147 |
| Carbonate, 0.5M buffer soln., pH 10.0 | J61229 | 147 |
| Carbonate-buffered saline (5X), pH 9.0 | J61396 | 147 |
| Carbonate-buffered saline (5X), pH 9.5 | J63928 | 147 |
| CHAPS lysis buffer | J60580 | 152 |
| CHAPS lysis buffer (2X) | J60812 | 152 |
| CHES, 99% | A18047 | 153 |
| CHES, 0.5M buffer soln, pH 8.5 | J61492 | 153 |
| CHES, 0.5M buffer soln, pH 9.0 | J63670 | 153 |
| CHES, 0.5M buffer soln, pH 9.5 | J62333 | 153 |
| CHES, 0.5M buffer soln, pH 10.0 | J63419 | 153 |
| Citrate, 0.5M buffer soln., pH 2.5 | J63008 | 164 |
| Citrate, 0.5M buffer soln., pH 3.0 | J61391 | 164 |
| Citrate, 0.5M buffer soln., pH 3.5 | J61690 | 164 |
| Citrate, 0.5M buffer soln., pH 4.0 | J61249 | 164 |
| Citrate, 0.5M buffer soln., pH 4.5 | J60024 | 164 |
| Citrate, 0.5M buffer soln., pH 5.0 | J60125 | 164 |
| Citrate, 0.5M buffer soln., pH 5.5 | J60754 | 164 |
| Citrate, 0.5M buffer soln., pH 6.0 | J63950 | 164 |
| Citrate, 0.5M buffer soln., pH 8.0 | J60919 | 164 |
| Citrate-buffered saline (20X) | J63666 | 164 |
| Dialysis tubing wash buffer (5X) | J61029 | 182 |
| DIPSO, 0.2M buffer soln., pH 7.0 | J62498 | 199 |
| DIPSO, 0.2M buffer soln., pH 7.5 | J63097 | 199 |
| DIPSO, 0.2M buffer soln., pH 8.0 | J61388 | 199 |
| DIPSO, 0.2M buffer soln., pH 8.5 | J62629 | 199 |
| E. coli lysis buffer | J63402 | 204 |
| E. coli lysis buffer-II | J62613 | 204 |
| E. coli sample buffer | J63289 | 204 |
| Enzyme storage buffer in PBS and glycerol, autoclaved | J63115 | 208 |
| Enzyme storage buffer in TBS and glycerol, autoclaved | J63264 | 208 |
| EPPS, 0.2M buffer soln., pH 7.0 | J61538 | 209 |
| EPPS, 0.2M buffer soln., pH 7.5 | J60511 | 209 |
| EPPS, 0.2M buffer soln., pH 8.0 | J61296 | 209 |
| EPPS, 0.2M buffer soln., pH 8.5 | J61476 | 209 |
| Factor XA protease digestion buffer | J63878 | 218 |
| FSB buffer | J60262 | 228 |
| Gelatin veronal buffer (GVB), 5mM barbital | J63358 | 230 |
| Gelatin veronal buffer (GVB), 10mM barbital | J62828 | 231 |
| Gelatin veronal buffer with EDTA (GVBE), 5mM barbital | J63725 | 231 |
| Gelatin veronal buffer with EDTA (GVBE), 10mM barbital | J61085 | 231 |
| Gelatin veronal buffer with Mg and EDTA (GVBMG), 5mM barbital | J61909 | 231 |

| Description | Stock # | Page # |
|--|---------|--------|
| Gelatin veronal buffer with Mg and EDTA (GVBMG), 10mM barbital | J60686 | 231 |
| Gelatin veronal buffer with Mg and Ca (GVB++), 5mM barbital | J61165 | 231 |
| Gelatin veronal buffer with Mg and Ca (GVB++), 10mM barbital | J61744 | 231 |
| Glucose gelatin veronal buffer (GGVB) | J60385 | 233 |
| Glucose gelatin veronal buffer with EDTA (GGVB) | J61846 | 233 |
| Glucose veronal buffer (GVB) | J63656 | 234 |
| Glucose veronal buffer with EDTA (GVB) | J60787 | 234 |
| Glycine, 0.2M buffer soln., pH 2.5 | J61855 | 236 |
| Glycine, 0.2M buffer soln., pH 3.0 | J62527 | 236 |
| Glycine, 0.2M buffer soln., pH 3.5 | J60154 | 236 |
| Glycylglycine, 0.2M buffer soln., pH 7.5 | J60282 | 237 |
| Glycylglycine, 0.2M buffer soln., pH 8.0 | J62920 | 237 |
| Glycylglycine, 0.2M buffer soln., pH 8.5 | J60717 | 237 |
| Glycylglycine, 0.2M buffer soln., pH 9.0 | J62591 | 237 |
| Glycylglycine, 99% | A10523 | 237 |
| GTE buffer | J62597 | 239 |
| HEPES, 99% | A14777 | 242 |
| HEPES hemisodium salt | J61830 | 242 |
| HEPES, 0.5M buffer soln., pH 6.5 | J60463 | 242 |
| HEPES, 0.5M buffer soln., pH 7.0 | J60064 | 242 |
| HEPES, 0.5M buffer soln., pH 7.5 | J61275 | 242 |
| HEPES, 0.5M buffer soln., pH 7.6 | J61047 | 242 |
| HEPES, 0.5M buffer soln., pH 8.0 | J63002 | 242 |
| HEPES, 0.5M buffer soln., pH 8.5 | J63218 | 242 |
| HEPES, 0.5M buffer soln., pH 9.0 | J63614 | 242 |
| HEPES, 1.0M buffer soln., pH 6.5 | J61017 | 242 |
| HEPES, 1.0M buffer soln., pH 7.0 | J62688 | 243 |
| HEPES, 1.0M buffer soln., pH 7.5 | J60712 | 243 |
| HEPES sodium salt, 99% | A16516 | 242 |
| HEPES, 1.0M buffer soln., pH 8.0 | J63578 | 243 |
| HEPES, 1.0M buffer soln., pH 8.5 | J61360 | 243 |
| HEPES, 1.0M buffer soln., pH 9.0 | J60440 | 243 |
| HEPES-buffered saline, pH 6.5 (5X) | J61239 | 243 |
| HEPES-buffered saline, pH 7.0 (2X for transfection) | J62623 | 243 |
| HEPES-buffered saline, pH 7.0 (5X) | J60753 | 243 |
| HEPES lysis buffer with NP-40 | J62915 | 243 |
| HEPES lysis buffer with NP-40 (2X) | J63867 | 243 |
| HEPES lysis buffer with Triton® X-100 | J63860 | 243 |
| HEPES lysis buffer with Triton® X-100 (2X) | J62809 | 243 |
| HEPES protein extraction buffer (5X) | J63297 | 243 |
| HEPES-Triton® X-100 extraction buffer | J63043 | 243 |
| HEPPSO, 0.2M buffer soln., pH 7.0 | J63877 | 243 |
| HEPPSO, 0.2M buffer soln., pH 7.5 | J61640 | 243 |
| HEPPSO, 0.2M buffer soln., pH 8.0 | J62529 | 243 |
| HEPPSO, 0.2M buffer soln., pH 8.5 | J60760 | 243 |
| Imidazole, 0.5M buffer soln., pH 6.0 | J61956 | 254 |
| Imidazole, 0.5M buffer soln., pH 6.5 | J62207 | 254 |
| Imidazole, 0.5M buffer soln., pH 7.0 | J62593 | 254 |
| Imidazole, 0.5M buffer soln., pH 7.5 | J63496 | 254 |
| Imidazole-buffered saline (5X) | J63887 | 254 |
| Kinase buffer I (5X) | J61967 | 263 |
| Kinase buffer II (5X) | J60269 | 263 |
| Kinase buffer III (5X) | J61566 | 264 |
| Kinase buffer IV (5X) | J63665 | 264 |
| Kinase buffer V (5X) | J62045 | 264 |
| Kinase Storage Buffer | J63719 | 264 |
| Lysis buffer, pH 8.0 | J63892 | 273 |
| Lysis buffer, 0.5% Tween 20, pH 8.0 | J61792 | 273 |
| Maleate, 0.2M buffer soln., pH 5.0 | J60582 | 275 |
| Maleate, 0.2M buffer soln., pH 5.5 | J62049 | 275 |
| Maleate, 0.2M buffer soln., pH 6.0 | J62035 | 275 |
| Maleate, 0.2M buffer soln., pH 6.5 | J61156 | 275 |
| Maleate, 0.2M buffer soln., pH 7.0 | J61297 | 275 |
| MES, 0.2M buffer soln., pH 5.5 | J63257 | 282 |
| MES, 0.2M buffer soln., pH 6.0 | J60930 | 282 |
| MES, 0.5M buffer soln., pH 5.0 | J62081 | 282 |

| Description | Stock # | Page # |
|---|---------|--------|
| MES, 0.5M buffer soln., pH 5.5 | J62534 | 282 |
| MES, 0.5M buffer soln., pH 6.0 | J62574 | 282 |
| MES, 0.5M buffer soln., pH 6.5 | J63778 | 282 |
| MES, 0.5M buffer soln., pH 7.0 | J63089 | 282 |
| MES, 0.5M buffer soln., pH 7.5 | J63706 | 282 |
| MES, 0.5M buffer soln., pH 8.0 | J61665 | 282 |
| MES, 0.5M buffer soln., pH 8.5 | J63944 | 282 |
| MES, 0.5M buffer soln., pH 9.0 | J60031 | 282 |
| MES, 1.0M buffer soln., pH 5.0 | J61960 | 282 |
| MES, 1.0M buffer soln., pH 5.5 | J63341 | 282 |
| MES, 1.0M buffer soln., pH 6.0 | J60763 | 282 |
| MES, 1.0M buffer soln., pH 6.5 | J61587 | 282 |
| MES, 1.0M buffer soln., pH 7.0 | J62231 | 282 |
| MES, 1.0M buffer soln., pH 7.5 | J62752 | 282 |
| MES, 1.0M buffer soln., pH 8.0 | J61556 | 282 |
| MES, 1.0M buffer soln., pH 8.5 | J62720 | 283 |
| MES, 1.0M buffer soln., pH 9.0 | J61656 | 283 |
| MES monohydrate, 98% | A16104 | 283 |
| MES hydrate, 99+% | H56472 | 283 |
| MES-buffered saline (5X), pH 6.5 | J61979 | 283 |
| MES-buffered saline (5X), pH 7.0 | J61938 | 283 |
| MES lysis buffer with NP-40 | J63411 | 283 |
| MES lysis buffer with NP-40 (2X) | J60244 | 283 |
| MES lysis buffer with Triton® X-100 | J62693 | 283 |
| MES lysis buffer with Triton® X-100 (2X) | J63169 | 283 |
| MNE buffer, pH 6.5 | J60690 | 292 |
| MOBS, 0.2M buffer soln., pH 7.0 | J61416 | 292 |
| MOBS, 0.2M buffer soln., pH 7.5 | J63519 | 293 |
| MOBS, 0.2M buffer soln., pH 8.0 | J63594 | 293 |
| MOBS, 0.2M buffer soln., pH 8.5 | J62203 | 293 |
| MOPS, 99% | A12914 | 294 |
| MOPS, 0.5M buffer soln., pH 5.5 | J62477 | 294 |
| MOPS, 0.5M buffer soln., pH 6.0 | J62476 | 294 |
| MOPS, 0.5M buffer soln., pH 6.5 | J63369 | 294 |
| MOPS, 0.5M buffer soln., pH 7.0 | J60328 | 294 |
| MOPS, 0.5M buffer soln., pH 7.5 | J62839 | 294 |
| MOPS, 0.5M buffer soln., pH 8.0 | J61236 | 294 |
| MOPS, 0.5M buffer soln., pH 8.5 | J62368 | 295 |
| MOPS, 0.5M buffer soln., pH 9.0 | J60922 | 295 |
| MOPS, 1.0M buffer soln., pH 5.5 | J62261 | 295 |
| MOPS, 1.0M buffer soln., pH 6.0 | J62840 | 295 |
| MOPS, 1.0M buffer soln., pH 6.5 | J61797 | 295 |
| MOPS, 1.0M buffer soln., pH 7.0 | J61821 | 295 |
| MOPS, 1.0M buffer soln., pH 7.5 | J61843 | 295 |
| MOPS, 1.0M buffer soln., pH 8.0 | J61958 | 295 |
| MOPS, 1.0M buffer soln., pH 8.5 | J62682 | 295 |
| MOPS, 1.0M buffer soln., pH 9.0 | J60097 | 295 |
| MOPS-buffered saline (5X), pH 7.0 | J63986 | 295 |
| MOPS-buffered saline (5X), pH 7.2 | J60490 | 295 |
| MOPS-buffered saline (5X), pH 7.5 | J61616 | 295 |
| MOPS-EDTA-sodium acetate buffer (MESA) | J60184 | 295 |
| MOPSO, 0.2M buffer soln., pH 6.0 | J60993 | 295 |
| MOPSO, 0.2M buffer soln., pH 6.5 | J61833 | 295 |
| MOPSO, 0.2M buffer soln., pH 7.0 | J61469 | 295 |
| MOPSO, 0.2M buffer soln., pH 7.5 | J60464 | 295 |
| Nitrocellulose stripping buffer (10X) | J62541 | 303 |
| NP-40 lysis buffer | J60766 | 305 |
| NP-40 lysis buffer (2X) | J62805 | 305 |
| NP-40 lysis buffer, high salt | J61428 | 305 |
| NP-40 lysis buffer, low salt | J60902 | 305 |
| NP-40 lysis buffer with glycerol (2X) | J60143 | 305 |
| NP-40 permeating solution in PBS (10X) | J60838 | 305 |
| NP-40 permeating solution in TBS (10X) | J62410 | 305 |
| Nylon membrane stripping buffer (10X) | J62974 | 305 |
| Polyethylene glycol-lithium acetate soln. | J62213 | 324 |
| Phosphatase buffer 1 (5X) | J62267 | 319 |

| Description | Stock # | Page # |
|--|---------|--------|
| Phosphate, 0.2M buffer soln., pH 4.4 | J60467 | 319 |
| Phosphate, 0.2M buffer soln., pH 6.8 | J60325 | 319 |
| Phosphate, 0.2M buffer soln., pH 7.0 | J60669 | 319 |
| Phosphate, 0.2M buffer soln., pH 7.2 | J62899 | 319 |
| Phosphate, 0.2M buffer soln., pH 7.4 | J60380 | 319 |
| Phosphate, 0.2M buffer soln., pH 7.5 | J61324 | 319 |
| Phosphate, 0.2M buffer soln., pH 7.6 | J61870 | 319 |
| Phosphate, 0.2M buffer soln., pH 8.0 | J60480 | 319 |
| Phosphate, 0.2M buffer soln., pH 8.5 | J61925 | 319 |
| Phosphate, 0.2M buffer soln., pH 9.0 | J63581 | 320 |
| Phosphate, 0.2M buffer soln., pH 9.5 | J60819 | 320 |
| Phosphate, 0.5M buffer soln., pH 6.5 | J60845 | 320 |
| Phosphate, 0.5M buffer soln., pH 7.0 | J62749 | 320 |
| Phosphate, 0.5M buffer soln., pH 7.2 | J63974 | 320 |
| Phosphate, 0.5M buffer soln., pH 7.4 | J60785 | 320 |
| Phosphate, 0.5M buffer soln., pH 7.5 | J63349 | 320 |
| Phosphate, 0.5M buffer soln., pH 7.6 | J60197 | 320 |
| Phosphate, 0.5M buffer soln., pH 8.0 | J61722 | 320 |
| Phosphate, 0.5M buffer soln., pH 8.5 | J61086 | 320 |
| Phosphate, 0.5M buffer soln., pH 9.0 | J62345 | 320 |
| Phosphate, 0.5M buffer soln., pH 9.5 | J62025 | 320 |
| Phosphate buffered RIPA | J62694 | 320 |
| Phosphate buffered RIPA (2X) | J60780 | 320 |
| Phosphate buffered RIPA with glycerol (2X) | J62939 | 320 |
| Phosphate-buffered saline (PBS, 10X), pH 7.4 | J62036 | 320 |
| Phosphate-buffered saline (PBS, 10X), pH 7.4, for Western blot | J60801 | 320 |
| Phosphate-buffered saline (PBS, 10X), pH 7.6 | J62692 | 320 |
| Phosphate-buffered saline (PBS, 10X), RNase free | J62851 | 320 |
| Phosphate-buffered saline (DPBS, 10X), Dulbecco's formula | J61917 | 320 |
| Phosphate-buffered saline (PBS, 1X), sterile | J61196 | 320 |
| Phosphate-buffered saline (PBS, 5X), with EDTA | J60893 | 320 |
| Phosphate-buffered saline (PBS, 10X), no potassium | J60465 | 321 |
| Phosphate-Citrate Buffer (5X) | J62982 | 321 |
| PIPES, 98% | A16090 | 322 |
| PIPES monosodium salt hydrate, 99% | B21835 | 322 |
| PIPES, 0.5M buffer soln., pH 5.5 | J60891 | 322 |
| PIPES, 0.5M buffer soln., pH 6.0 | J62224 | 322 |
| PIPES, 0.5M buffer soln., pH 6.5 | J61224 | 322 |
| PIPES, 0.5M buffer soln., pH 6.8 | J61786 | 322 |
| PIPES, 0.5M buffer soln., pH 7.0 | J63234 | 322 |
| PIPES, 0.5M buffer soln., pH 7.5 | J63617 | 322 |
| PIPES, 0.5M buffer soln., pH 8.0 | J61406 | 322 |
| PIPES, 1.0M buffer soln., pH 6.0 | J60611 | 322 |
| PIPES, 1.0M buffer soln., pH 6.5 | J60659 | 322 |
| PIPES, 1.0M buffer soln., pH 6.8 | J60300 | 322 |
| PIPES, 1.0M buffer soln., pH 7.0 | J62195 | 322 |
| PIPES, 1.0M buffer soln., pH 7.5 | J62494 | 322 |
| PIPES, 1.0M buffer soln., pH 8.0 | J60618 | 322 |
| PIPES-buffered saline (5X), pH 6.5 | J63152 | 322 |
| PIPES-buffered saline (5X), pH 6.8 | J60947 | 322 |
| PIPES-buffered saline (5X), pH 7.0 | J63543 | 322 |
| PIPES lysis buffer with NP-40 | J62278 | 322 |
| PIPES lysis buffer with NP-40 (2X) | J60568 | 322 |
| PIPES lysis buffer with Triton® X-100 | J62360 | 322 |
| PIPES lysis buffer with Triton® X-100 (2X) | J62068 | 323 |
| POPSO, 0.2M buffer soln., pH 7.0 | J63333 | 326 |
| POPSO, 0.2M buffer soln., pH 7.5 | J60869 | 326 |
| POPSO, 0.2M buffer soln., pH 8.0 | J60085 | 326 |
| POPSO, 0.2M buffer soln., pH 8.5 | J60623 | 326 |
| Potassium acetate, 1M aq. soln., pH 7.5 | J62817 | 326 |
| Potassium acetate, 1M aq. soln., pH 7.5, RNase free | J60832 | 326 |
| Potassium acetate, 8M aq. soln., RNase free | J62856 | 326 |
| Potassium phosphate, 0.2M buffer soln., pH 7.0 | J61261 | 327 |
| Potassium phosphate, 0.2M buffer soln., pH 7.2 | J60664 | 327 |
| Potassium phosphate, 0.2M buffer soln., pH 7.4 | J62397 | 327 |
| Potassium phosphate, 0.2M buffer soln., pH 7.5 | J62239 | 327 |

| Description | Stock # | Page # |
|--|---------|--------|
| Potassium phosphate, 0.2M buffer soln., pH 7.6 | J63128 | 327 |
| Potassium phosphate, 0.2M buffer soln., pH 8.0 | J60851 | 327 |
| Potassium phosphate, 0.5M buffer soln., pH 7.0 | J60584 | 327 |
| Potassium phosphate, 0.5M buffer soln., pH 7.2 | J60326 | 327 |
| Potassium phosphate, 0.5M buffer soln., pH 7.4 | J61413 | 327 |
| Potassium phosphate, 0.5M buffer soln., pH 7.5 | J61553 | 327 |
| Potassium phosphate, 0.5M buffer soln., pH 7.6 | J63189 | 327 |
| RBC lysis buffer for human | J62990 | 335 |
| RBC lysis buffer for mouse | J62150 | 335 |
| RIPA buffer | J63306 | 338 |
| RIPA buffer (2X) | J63324 | 338 |
| RIPA buffer (5X) | J62524 | 338 |
| RIPA buffer with EDTA | J61529 | 338 |
| RIPA buffer with EDTA + EGTA | J60645 | 338 |
| RIPA buffer with EGTA | J61951 | 338 |
| RIPA with glycerol (2X) | J61734 | 338 |
| RIPA buffer with Triton® X-100 (1X) | J62725 | 338 |
| RIPA buffer with Triton® X-100 (2X) | J60488 | 338 |
| RIPA buffer with Triton® X-100 (5X) | J62885 | 338 |
| RIPA buffer with Triton® X-100 + 10% glycerol (2X) | J60423 | 338 |
| RIPA buffer-2 | J62189 | 338 |
| RIPA buffer-2 (2X) | J60629 | 338 |
| SM buffer, pH 7.5 | J61367 | 342 |
| Sodium acetate, 1M aq. soln., pH 4.5, RNase free | J63669 | 342 |
| Sodium acetate, 3M aq. soln., pH 4.5, autoclaved | J61288 | 343 |
| Sodium acetate, 3M aq. soln., pH 5.2, autoclaved | J63560 | 343 |
| Sodium acetate, 3M aq. soln., pH 5.2, RNase free | J61928 | 343 |
| Sodium acetate, 3M aq. soln., pH 7.0, autoclaved | J60899 | 343 |
| Sodium acetate, 3M aq. soln., pH 7.0, RNase free | J61934 | 343 |
| Sodium bicarbonate, 1M buffer soln., pH 8.0 | J62495 | 343 |
| Sodium bicarbonate, 1M buffer soln., pH 8.5 | J60408 | 344 |
| Sodium bicarbonate, 1M buffer soln., pH 9.0 | J60066 | 344 |
| Sodium bicarbonate, 1M buffer soln., pH 9.4 | J62808 | 344 |
| Sodium bicarbonate, 1M buffer soln., pH 10.0 | J63025 | 344 |
| Sodium borate, 0.5M buffer soln., pH 8.0 | J60068 | 344 |
| Sodium borate, 0.5M buffer soln., pH 8.5 | J62902 | 344 |
| Sodium borate, 0.5M buffer soln., pH 9.0 | J63637 | 344 |
| Sodium cacodylate, 0.1M buffer soln., pH 6.5 | J60367 | 344 |
| Sodium cacodylate, 0.1M buffer soln., pH 6.8 | J62202 | 344 |
| Sodium cacodylate, 0.1M buffer soln., pH 7.0 | J60344 | 344 |
| Sodium citrate, 0.5M buffer soln., pH 5.0 | J62918 | 345 |
| Sodium citrate, 0.5M buffer soln., pH 5.5 | J63199 | 345 |
| Sodium citrate, 0.5M buffer soln., pH 6.0 | J61815 | 345 |
| Sodium citrate, 0.5M buffer soln., pH 6.5 | J63888 | 345 |
| Sodium hydroxide and β-mercaptoethanol buffer | J60415 | 347 |
| Sodium phosphate, 0.2M buffer soln., pH 7.0 | J63482 | 347 |
| Sodium phosphate, 0.2M buffer soln., pH 7.2 | J63816 | 347 |
| Sodium phosphate, 0.2M buffer soln., pH 7.4 | J62152 | 347 |
| Sodium phosphate, 0.2M buffer soln., pH 7.5 | J62041 | 348 |
| Sodium phosphate, 0.2M buffer soln., pH 7.6 | J62815 | 348 |
| Sodium phosphate, 0.2M buffer soln., pH 8.0 | J62733 | 348 |
| Sodium phosphate, 0.2M buffer soln., pH 8.5 | J61372 | 348 |
| Sodium phosphate, 0.2M buffer soln., pH 9.0 | J60565 | 348 |
| Sodium phosphate, 0.2M buffer soln., pH 9.5 | J63159 | 348 |
| Sodium phosphate, 0.5M buffer soln., pH 7.0 | J63791 | 348 |
| Sodium phosphate, 0.5M buffer soln., pH 7.5 | J61561 | 348 |
| Sodium phosphate, 0.5M buffer soln., pH 7.6 | J60158 | 348 |
| Sodium phosphate, 0.5M buffer soln., pH 8.0 | J60825 | 348 |
| Sodium phosphate, 0.5M buffer soln., pH 8.5 | J61151 | 348 |
| Sodium phosphate, 0.5M buffer soln., pH 9.0 | J60651 | 348 |
| Sodium phosphate, 0.5M buffer soln., pH 9.5 | J61456 | 348 |
| Sodium pyrophosphate, 200mM buffer soln. | J62052 | 348 |
| SSC buffer (20X) | J60839 | 351 |
| SSC (20X), RNase free | J60561 | 351 |
| SSPE (20X) | J61214 | 351 |
| SSPE (20X), RNase free | J60783 | 351 |

| Description | Stock # | Page # |
|--|---------|--------|
| STE buffer soln. | J60265 | 352 |
| STET | J60563 | 352 |
| SU buffer, SDS + Urea | J61534 | 353 |
| Succinate, 0.2M buffer soln., pH 4.0 | J63619 | 353 |
| Succinate, 0.2M buffer soln., pH 4.5 | J63881 | 353 |
| Succinate, 0.2M buffer soln., pH 5.0 | J63863 | 353 |
| Succinate, 0.2M buffer soln., pH 5.5 | J61100 | 353 |
| Succinate, 0.2M buffer soln., pH 6.0 | J61853 | 353 |
| Succinate, 0.2M buffer soln., pH 6.5 | J62078 | 353 |
| Sucrose, 80%, in MNE buffer, MES + NaCl + EDTA | J60720 | 355 |
| Sucrose gelatin veronal buffer (SGVB), pH 7.2 | J63979 | 355 |
| Sucrose gelatin veronal buffer with EDTA (SGVBE), pH 7.2 | J62587 | 355 |
| TAE (10X), TRIS + acetate + EDTA | J63677 | 357 |
| TAE (50X), TRIS + acetate + EDTA | J63931 | 357 |
| TAPS, 99% | A17754 | 358 |
| TAPS, 0.2M buffer soln., pH 8.0 | J60322 | 358 |
| TAPS, 0.2M buffer soln., pH 8.5 | J63268 | 358 |
| TAPS sodium salt, 98% | J61189 | 358 |
| TB Solution-I | J62568 | 359 |
| TB Solution-II | J60028 | 359 |
| TB Solution-III | J63410 | 359 |
| TB Solution-IV | J63318 | 359 |
| TBE (5X), TRIS + borate + EDTA | J63487 | 359 |
| TBE (10X), TRIS + borate + EDTA | J62449 | 359 |
| TBE sample buffer (6X) | J60357 | 359 |
| TBE running buffer (10X) | J62788 | 359 |
| TBE urea sample buffer (2X) | J60186 | 359 |
| TE buffer, (20X), pH 7.4, autoclaved | J60738 | 359 |
| TE buffer, (20X), pH 7.6, autoclaved | J61110 | 359 |
| TE buffer, (20X), pH 8.0, autoclaved | J62388 | 359 |
| TE buffer, pH 7.4, RNase free | J60234 | 359 |
| TE buffer, pH 7.6, RNase free | J62285 | 359 |
| TE buffer, pH 8.1, RNase free | J62745 | 360 |
| TEA, 0.2M buffer soln., pH 7.0 | J61546 | 360 |
| TEA, 0.2M buffer soln., pH 7.5 | J61319 | 360 |
| TEA, 0.2M buffer soln., pH 8.0 | J63793 | 360 |
| TEA, 0.2M buffer soln., pH 8.5 | J61668 | 360 |
| TES, 0.2M buffer soln., pH 7.0 | J63379 | 360 |
| TES, 0.2M buffer soln., pH 7.5 | J61350 | 360 |
| TES, 0.2M buffer soln., pH 8.0 | J61889 | 360 |
| TES, 99% | B21819 | 360 |
| TES sodium salt | J62706 | 361 |
| Thrombin buffer, pH 8.0 | J63240 | 368 |
| TM media, TRIS + MgSO ₄ .7H ₂ O | J63355 | 370 |
| TN buffer soln. | J63985 | 370 |
| TNT buffer soln. | J60622 | 370 |
| TPE (10X), TRIS + phosphate + EDTA | J60233 | 372 |
| Transfer or electro blotting buffer (10X), pH 8.5 | J63037 | 373 |
| Transformation buffer-1, pH 7.5 | J63244 | 373 |
| Transformation buffer-2, pH 7.5 | J63293 | 373 |
| Tricine, 98+% | A14695 | 375 |
| Tricine, 0.5M buffer soln., pH 6.5 | J60107 | 375 |
| Tricine, 0.5M buffer soln., pH 7.0 | J62234 | 375 |
| Tricine, 0.5M buffer soln., pH 7.5 | J62672 | 375 |
| Tricine, 0.5M buffer soln., pH 8.0 | J62983 | 375 |
| Tricine, 0.5M buffer soln., pH 8.5 | J63108 | 375 |
| Tricine, 0.5M buffer soln., pH 9.0 | J63880 | 375 |
| Tricine-buffered saline (5X), pH 7.0 | J60811 | 375 |
| Tricine-buffered saline (5X), pH 7.5 | J63294 | 375 |
| Tricine-buffered saline (5X), pH 8.0 | J60745 | 375 |
| TRIS, 0.5M buffer soln., pH 6.5 | J61787 | 379 |
| TRIS, 0.5M buffer soln., pH 6.8 | J63735 | 379 |
| TRIS, 0.5M buffer soln., pH 7.0 | J61213 | 379 |
| TRIS, 0.5M buffer soln., pH 7.2 | J61009 | 379 |
| TRIS, 0.5M buffer soln., pH 7.4 | J62778 | 379 |
| TRIS, 0.5M buffer soln., pH 7.5 | J61141 | 379 |

| Description | Stock # | Page # |
|---|---------|--------|
| TRIS, 0.5M buffer soln., pH 7.6 | J62736 | 379 |
| TRIS, 0.5M buffer soln., pH 7.8 | J61944 | 379 |
| TRIS, 0.5M buffer soln., pH 8.0 | J62552 | 379 |
| TRIS, 0.5M buffer soln., pH 8.2 | J62944 | 379 |
| TRIS, 0.5M buffer soln., pH 8.4 | J61537 | 379 |
| TRIS, 0.5M buffer soln., pH 8.5 | J62131 | 379 |
| TRIS, 0.5M buffer soln., pH 8.6 | J62287 | 379 |
| TRIS, 0.5M buffer soln., pH 8.8 | J61144 | 380 |
| TRIS, 0.5M buffer soln., pH 9.0 | J62551 | 380 |
| TRIS, 0.5M buffer soln., pH 9.5 | J63134 | 380 |
| TRIS, 1.0M buffer soln., pH 6.5 | J60381 | 380 |
| TRIS, 1.0M buffer soln., pH 6.5, 0.2 micron filtered | J62264 | 380 |
| TRIS, 1.0M buffer soln., pH 6.8 | J63831 | 380 |
| TRIS, 1.0M buffer soln., pH 7.0 | J62657 | 380 |
| TRIS, 1.0M buffer soln., pH 7.0, 0.2 micron filtered | J60822 | 380 |
| TRIS, 1.0M buffer soln., pH 7.2 | J62186 | 380 |
| TRIS, 1.0M buffer soln., pH 7.4 | J60202 | 380 |
| TRIS, 1.0M buffer soln., pH 7.5 | J60636 | 380 |
| TRIS, 1.0M buffer soln., pH 7.5, 0.2 micron filtered | J62993 | 380 |
| TRIS, 1.0M buffer soln., pH 7.6 | J61036 | 380 |
| TRIS, 1.0M buffer soln., pH 7.8 | J61579 | 380 |
| TRIS, 1.0M buffer soln., pH 8.0 | J62726 | 380 |
| TRIS, 1.0M buffer soln., pH 8.0, 0.2 micron filtered | J61429 | 380 |
| TRIS, 1.0M buffer soln., pH 8.2 | J61798 | 380 |
| TRIS, 1.0M buffer soln., pH 8.4 | J62577 | 380 |
| TRIS, 1.0M buffer soln., pH 8.5, 0.2 micron filtered | J61038 | 380 |
| TRIS, 1.0M buffer soln., pH 8.6 | J61066 | 380 |
| TRIS, 1.0M buffer soln., pH 8.8 | J60452 | 380 |
| TRIS, 1.0M buffer soln., pH 9.0 | J62085 | 380 |
| TRIS, 1.0M buffer soln., pH 9.0, 0.2 micron filtered | J60707 | 380 |
| TRIS, 1.0M buffer soln., pH 9.5 | J62084 | 381 |
| TRIS-acetate-SDS running buffer (10X), pH 8.3 | J62560 | 381 |
| TRIS-buffered saline (TBS, 20X) pH 7.4 | J60877 | 381 |
| TRIS-buffered saline (TBS, 10X, high salt) pH 7.4 | J62664 | 381 |
| TRIS-buffered saline (TBS, 10X, low salt) pH 8.0 | J60102 | 381 |
| TRIS-buffered saline (TBS, 10X) pH 7.4, for Western blot | J62938 | 381 |
| TRIS-buffered saline (TBS, 10X) pH 7.4 | J60764 | 381 |
| TRIS-buffered saline (TBS, 10X) pH 7.6 | J62662 | 381 |
| TRIS-buffered saline (TBS, 10X) pH 8.0 | J62780 | 381 |
| TRIS-buffered saline (TBS, 5X), with EDTA | J63692 | 381 |
| TRIS-buffered saline (TBS, 10X), with 1% Triton® X-100 | J62533 | 381 |
| TRIS-buffered saline (TBS, 10X), with 0.5% Tween 20 | J60448 | 381 |
| TRIS-buffered saline (TBS, 20X), with 0.5% Tween 20 | J63682 | 381 |
| TRIS-buffered saline (TBS, 10X), with 1% Tween 20 | J62955 | 381 |
| TRIS-buffered saline (TBS, 20X), with 1% Tween 20 | J60497 | 381 |
| TRIS-CAPS buffer (10X) | J61339 | 381 |
| TRIS-glycine-native running buffer (10X), pH 8.5 | J62914 | 381 |
| TRIS-glycine-SDS running buffer (10X), pH 8.3 | J61006 | 381 |
| TRIS-glycine native sample buffer (4X), pH 8.6 | J61864 | 381 |
| TRIS-HEPES-native running buffer (10X), pH 8.0 | J62737 | 382 |
| TRIS-HEPES-SDS running buffer (10X), pH 8.0 | J61789 | 382 |
| TRIS-Tricine-SDS kit (10X) | J63948 | 383 |
| TRIS-Tricine-SDS running buffer (10X), anode buffer, pH 8.9 | J63375 | 383 |
| TRIS-Tricine-SDS running buffer (10X), cathode buffer, pH 8.3 | J60992 | 383 |
| Tris(hydroxymethyl)aminomethane, Molecular Biology Grade, 99.9% | J61062 | 382 |
| Tris(hydroxymethyl)aminomethane hydrochloride, 1M stock soln, pH 8.0 | J63636 | 382 |
| Tris(hydroxymethyl)aminomethane hydrochloride, 1M soln., pH 7.4, RNase free | J62848 | 382 |
| Tris(hydroxymethyl)aminomethane hydrochloride, 1M soln., pH 8.0, RNase free | J60080 | 382 |
| Triton® X-100 lysis buffer, pH 7.4 | J62289 | 383 |
| Triton® X-100 lysis buffer (2X), pH 7.4 | J63653 | 383 |
| Triton® X-100 lysis buffer-2, pH 8.0 | J62526 | 383 |
| Triton® X-100 lysis buffer with glycerol (2X), pH 7.4 | J63866 | 383 |
| TSS (Transformation & Storage Soln.), pH 6.5 | J62318 | 385 |
| Tween 20 blocking buffer, 1% in PBS (10X) | J61544 | 385 |
| Veronal-buffered saline (VBS), 5mM buffer soln., pH 7.0 | J61371 | 391 |
| Veronal-buffered saline (VBS), 10mM buffer soln., pH 7.0 | J61611 | 391 |

| Description | Stock # | Page # |
|---|---------|--------|
| Veronal-buffered saline (VBS), 10mM buffer soln., pH 7.4 | J63779 | 391 |
| Veronal-buffered saline with MG + CA (VBS++), 5mM buffer soln., pH 7.2 | J60003 | 391 |
| Veronal-buffered saline with MG + CA (VBS++), 10mM buffer soln., pH 7.2 | J63853 | 391 |
| Veronal-buffered saline with EDTA (VBSE), 5mM buffer soln., pH 7.2 | J62759 | 391 |
| Veronal-buffered saline with EDTA (VBSE), 10mM buffer soln., pH 7.2 | J63338 | 391 |
| Veronal-buffered saline with MG + EGTA (VBSMG), 5mM buffer soln., pH 7.2 | J60535 | 392 |
| Veronal-buffered saline with MG + EGTA (VBSMG), 10mM buffer soln., pH 7.2 | J63417 | 392 |
| Wash buffer, pH 8.0 | J61918 | 393 |
| Wash buffer, 1.0% Triton® X-100, pH 8.0 | J60428 | 393 |
| Wash buffer, 0.5% Tween 20, pH 8.0 | J60165 | 393 |
| Yeast lysis solution for DNA isolation | J61459 | 395 |
| Zymogram developing buffer (10X), pH 7.45 | J61375 | 397 |
| Zymogram renaturation buffer (10X) | J63137 | 397 |
| Zymogram sample buffer, pH 6.6 | J62774 | 397 |

Carbohydrates and Derivatives

Carbohydrates consist of only carbon, hydrogen and oxygen. This class of molecules includes all sugars and starches, and plays many important roles in living systems. Their major function is the storage and transport of energy. This list includes sugars, sugar alcohols and oligosaccharides.

| Description | Stock # | Page # |
|---|---------|--------|
| N-Acetyl-D-glucosamine, 98+% | A13047 | 73 |
| N-Acetyl-D-mannosamine monohydrate, 99% | L11167 | 74 |
| Adonitol, 99% | L03253 | 80 |
| D-Amygdalin, 98% | J61472 | 103 |
| D-Amygdalin hydrate, 96% | L12731 | 103 |
| DL-Arabinose, 98+% | L09895 | 108 |
| D-(-)-Arabinose, 99% | A10357 | 108 |
| L-(-)-Arabinose, 99% | A11921 | 108 |
| D-(+)-Arabitol, 99% | A17801 | 108 |
| L-(-)-Arabitol, 98% | A13103 | 109 |
| Arbutin, 98+% | L14945 | 109 |
| D-(+)-Cellobiose, 98+% | A14553 | 151 |
| D-Cellobiose octaacetate | L08780 | 151 |
| Cellulose, microcrystalline | A17730 | 151 |
| Chitin | J61206 | 153 |
| α -Chloralose, 98+%, β anomer ca 15% | A11492 | 153 |
| 2-Deoxy-D-glucose, 98% | L07338 | 178 |
| (+)-1-Deoxymannojirimycin hydrochloride | J61277 | 179 |
| (+)-1-Deoxynojirimycin | J62602 | 179 |
| 2-Deoxy-D-ribose, 99% | A11990 | 180 |
| Dextran, MW ca 6,000 | J62775 | 181 |
| Dextran, MW ca 20,000 | J61216 | 181 |
| Dextran, MW ca 40,000 | J63690 | 181 |
| Dextran, MW ca 75,000 | J60989 | 181 |
| Dextran, MW ca 500,000 | J63702 | 181 |
| Dextran, MW ca 150,000 | J63789 | 181 |
| Dextran, MW ca 250,000 | J60200 | 181 |
| Dextran sulfate sodium salt solution, 50% w/v aq. soln. | J60938 | 181 |
| Dextran sulfate sodium salt, MW ca 8,000 | J62101 | 181 |
| Dextran sulfate sodium salt, MW ca 40,000 | J63606 | 181 |
| Dextran sulfate sodium salt, MW ca >500,000 | J62787 | 181 |
| Dextrin, precipitated by alcohol | A15717 | 181 |
| Dulcitol, 97% | A18402 | 202 |
| Dulcitol, 99% | J63206 | 202 |
| meso-Erythritol, 99% | A15813 | 210 |
| D-Erythrose, syrup, ca 70% w/v, >75% dry wt. basis | B21093 | 210 |
| D-Fructose, 99% | A17718 | 228 |
| D-(+)-Fucose, 99% | A18234 | 228 |
| L-(-)-Fucose, 99% | A16789 | 228 |
| D-Galactosamine hydrochloride, 98% | L07462 | 229 |
| D-(+)-Galactose, 98% | A12813 | 229 |
| L-(-)-Galactose, 98% | B21448 | 229 |
| D-(+)-Glucono-1,5-lactone, 99% | A13105 | 233 |
| D-Glucosamine hydrochloride, 98+% | A15532 | 233 |
| β -D-Glucosamine pentaacetate, 96% | L09020 | 233 |
| D-(+)-Glucose, anhydrous, 99% | A16828 | 233 |
| D-(+)-Glucose monohydrate, 99% | A11090 | 233 |
| D-Glucuronic acid, 98+% | L14350 | 234 |
| D-Glucurono-6,3-lactone, 99% | A15861 | 234 |
| 1-Hexadecanol, 98% | A11180 | 244 |
| Hydantoin, 99% | A12486 | 247 |
| myo-Inositol, 98+% | A13586 | 257 |
| Inulin | A18425 | 257 |
| Invert sugar | J60273 | 257 |
| Isomaltose | J60884 | 261 |
| Lactulose, 99% | J60160 | 265 |
| Lanolin | A16902 | 266 |

| Description | Stock # | Page # |
|--------------------------------------|---------|--------|
| D-(+)-Maltose monohydrate, 95% | A16266 | 277 |
| D-Mannitol, 99% | A14030 | 277 |
| D-Mannitol, ACS | 33342 | 277 |
| D-(+)-Mannose, 99% | A10842 | 277 |
| L-(-)-Mannose, 99% | A17722 | 277 |
| D-(+)-Melezitose hydrate, 99% | B22209 | 279 |
| α -D-(+)-Melibiose | J60439 | 279 |
| Methyl cellulose, viscosity 15 cPs | 45490 | 286 |
| Methyl cellulose, viscosity 400 cPs | 43147 | 286 |
| Methyl cellulose, viscosity 1600 cPs | 43146 | 286 |
| Methyl cellulose, viscosity 8000 cPs | 43483 | 286 |
| Methyl cellulose, viscosity 4000 cPs | 36718 | 286 |
| N-Methyl-D-glucamine, 99% | L14282 | 288 |
| Palatinose hydrate, 98+% | J60091 | 311 |
| Pectin Citrus | J61021 | 312 |
| Phloroglucinol, anhydrous, 98% | B25502 | 318 |
| D-(+)-Raffinose pentahydrate, 99% | A18313 | 335 |
| Resorcinol, 99% | A13080 | 336 |
| Resorcinol, ACS, 99.0-100.5% | 36248 | 336 |
| L-(+)-Rhamnose monohydrate, 99% | A16166 | 336 |
| D-(-)-Ribose, 98% | A17894 | 338 |
| L-(+)-Ribose, 99% | B21117 | 338 |
| Saponin | A18820 | 340 |
| Sodium D-gluconate, 97% | A10464 | 346 |
| D-Sorbitol, 98% | 36404 | 350 |
| D-Sorbose, 98% | B21208 | 350 |
| Sucrose, 99% | A15583 | 354 |
| Sucrose, ACS | 36508 | 354 |
| D-Tagatose, 99% | B21192 | 357 |
| 5-Thio-D-glucose, 97+% | J63621 | 367 |
| D-(+)-Trehalose dihydrate, 99% | A19434 | 374 |
| D-Turanose, 98% | B21224 | 385 |
| Xylitol, 99% | A16944 | 394 |
| D-(+)-Xylose, 98+% | A10643 | 394 |
| L-(-)-Xylose, 99% | B21622 | 395 |

Cell Culture Reagents

Cell culture reagents are high purity products suitable for use in cell culture applications. Cell culture reagents include cell culture media, laboratory preparations, biological extracts and sterile reagents.

| Description | Stock # | Page # |
|---|---------|--------|
| Agar, plant cell culture tested | H26724 | 81 |
| β-Alanine, Cell Culture Reagent | J63435 | 82 |
| L-Alanine, Cell Culture Reagent | J60279 | 82 |
| Apolipoprotein A-I, human plasma 95% | J64506 | 108 |
| Apolipoprotein A-II, human plasma, 95% | J64658 | 108 |
| L-Asparagine monohydrate, Cell Culture Reagent | J62869 | 111 |
| Calcium chloride, 100mM aq. soln., sterile | J62905 | 143 |
| L-Cysteine, Cell Culture Reagent | J63745 | 173 |
| L-Cystine, Cell Culture Reagent | J61651 | 173 |
| L-Cystine dihydrochloride, Cell Culture Reagent | J63717 | 173 |
| Dil-Lipoprotein, high density, human plasma | J65503 | 194 |
| Dil-Lipoprotein, low density, acetylated, human plasma | J65597 | 193 |
| Dil-Lipoprotein, low density, human plasma | J65330 | 193 |
| Dil-Lipoprotein, low density, oxidized, human plasma | J64164 | 194 |
| Dil-Lipoprotein, very low density, human plasma | J65568 | 193 |
| DiO-Lipoprotein, low density, acetylated, human plasma | J64029 | 198 |
| DiO-Lipoprotein, low density, human plasma | J64267 | 198 |
| Erythromycin, Cell Culture Grade | J62279 | 210 |
| Ethylenediaminetetraacetic acid, Cell Culture Reagent | J62948 | 215 |
| Fibronectin, human, 95% | J64560 | 220 |
| Fibronectin, rat, 95% | J64390 | 220 |
| Fibronectin, stabilized soln., bovine | J65696 | 220 |
| Fibronectin, stabilized soln., human | J64738 | 220 |
| Fibronectin, stabilized soln., rat | J65555 | 220 |
| Folic acid, Cell Culture Reagent | J62937 | 227 |
| Giemsa Stain | B21172 | 232 |
| D-(+)-Glucose, 1M aq. soln., sterile | J60067 | 233 |
| L-Glutamine, Cell Culture Reagent | J60573 | 235 |
| Glycerol, Cell Culture Grade | J62399 | 235 |
| Glycine, 99.5+%, Cell Culture Reagent | J62407 | 237 |
| Goat Serum | J64301 | 238 |
| L-Histidine, Cell Culture Reagent | J63065 | 246 |
| L-Histidine monohydrochloride monohydrate, Cell Culture Reagent | J61465 | 246 |
| Hybridoma Cell Growth Supplement | J64856 | 247 |
| D-myo-Inositol, Cell Culture Grade | J62886 | 257 |
| L-Isoleucine, Cell Culture Reagent | J63045 | 260 |
| Kanamycin monosulfate, Cell Culture Grade | J60668 | 262 |
| L-Leucine, Cell Culture Reagent | J62824 | 268 |
| Lipoprotein(a), human plasma, 99% | J64606 | 271 |
| Lipoprotein Deficient Serum, bovine | J65182 | 271 |
| Lipoprotein Deficient Serum, human | J65516 | 271 |
| Lipoprotein, high density, human plasma, 99% | J64903 | 271 |
| Lipoprotein, low density, acetylated, human plasma, 99% | J65029 | 271 |
| Lipoprotein, low density, carbamylated, human plasma, 99% | J64426 | 271 |
| Lipoprotein, low density, human plasma, 99% | J65039 | 271 |
| Lipoprotein, low density, oxidized, human plasma, 99% | J65591 | 271 |
| Lipoprotein, low density, oxidized, human plasma, Hi-TBAR, 99% | J65261 | 271 |
| Lipoprotein, low density, oxidized, human plasma, Low-TBAR, 99% | J64223 | 271 |
| Lipoprotein, very low density, human plasma, 99% | J65642 | 271 |
| L-Lysine monohydrochloride, Cell Culture Reagent | J62099 | 273 |
| Magnesium chloride hexahydrate, Cell Culture Reagent | J62575 | 274 |
| Magnesium chloride, 1M aq. soln., sterile | J61014 | 274 |
| Magnesium sulfate, 1M aq. soln., sterile | J61030 | 274 |
| Magnesium sulfate heptahydrate, Cell Culture Reagent | J61839 | 275 |
| L-Methionine, Cell Culture Reagent | J61904 | 284 |
| L-Ornithine hydrochloride, Cell Culture Reagent | J60241 | 309 |
| L-Phenylalanine, Cell Culture Reagent | J63925 | 316 |
| Phosphate-buffered saline (PBS, 1X), sterile | J61196 | 320 |

Cell Culture Reagents

| Description | Stock # | Page # |
|--|---------|--------|
| Platelet-Poor Plasma Derived Serum, bovine | J64483 | 323 |
| Poly-D-lysine hydrobromide | J65578 | 324 |
| Polymixin B sulfate, Cell Culture Reagent | J61763 | 325 |
| Potassium chloride, 1M aq. soln., autoclaved | J60105 | 326 |
| Pyridoxamine dihydrochloride, Cell Culture Reagent | J62679 | 332 |
| Rabbit Serum | J65195 | 335 |
| L-Serine, Cell Culture Reagent | J62187 | 341 |
| Sodium chloride, 5M aq. soln., pH 8.0, autoclaved | J61807 | 344 |
| Sodium pyruvate, Cell Culture Grade | J61840 | 348 |
| Spectinomycin dihydrochloride pentahydrate, Cell Culture Grade | J61820 | 350 |
| Streptomycin sulfate, Cell Culture Reagent | J61299 | 352 |
| Taurine, Cell Culture Grade | J62308 | 359 |
| L-Threonine, Cell Culture Reagent | J63709 | 368 |
| Trypan Blue, dye content >60% | A18600 | 384 |
| L-Tryptophan, Cell Culture Reagent | J62508 | 384 |
| L-Tyrosine, Cell Culture Reagent | J63511 | 386 |
| L-Valine, Cell Culture Reagent | J62943 | 390 |

Chiral Compounds

Chiral compounds lack an internal plane of symmetry and thus have non-superimposable mirror images. Many biologically active molecules are chiral, including amino acids, DNA, and sugars. Chiral molecules are often useful in drug design and synthesis. This list includes chiral reagents with biological activity. It also includes chiral building blocks useful for drug design.

| Description | Stock # | Page # |
|---|---------|--------|
| (R)-(-)-2-Aminobutane, 99% | L03889 | 92 |
| (S)-(+)-2-Aminobutane, 98% | L10069 | 92 |
| (2S)-2-Aminobutyramide | J62670 | 92 |
| (1R,2S)-(-)-2-Amino-1,2-diphenylethanol, 99% | H27607 | 93 |
| (1S,2R)-(+)-2-Amino-1,2-diphenylethanol, 99% | H27834 | 93 |
| (R)-(+)-1-Amino-2-(methoxymethyl)pyrrolidine | J60524 | 96 |
| (S)-(-)-1-Amino-2-(methoxymethyl)pyrrolidine | J61723 | 96 |
| (S)-(+)-2-(Aminomethyl)pyrrolidine | J60492 | 97 |
| (R)-(-)-1-Amino-2-propanol, 98% | L14101 | 99 |
| (S)-(+)-1-Amino-2-propanol, 98% | L14102 | 99 |
| (R)-(-)-2-Amino-1-propanol, 98% | L11030 | 99 |
| (S)-(+)-2-Amino-1-propanol, 98% | B24916 | 99 |
| (S)-(-)-1-Benzyl-3-hydroxypyrrolidine, 99%, ee 99% | L19497 | 122 |
| (R)-1-Benzyl-3-pyrrolidinol | J61031 | 123 |
| (R)-(-)-2-Butanol, 98+% | L13983 | 140 |
| (S)-(+)-2-Butanol, 98+% | L14164 | 140 |
| (1S)-(-)-Camphor, 98% | B23469 | 144 |
| (+)-Dehydroabietylamine hydrochloride | J63123 | 176 |
| (1S,2S)-(+)-1,2-Diaminocyclohexane, 98% | L14072 | 182 |
| (S)-(+)-2,2-Dimethylcyclopropanecarboxamide | J61050 | 196 |
| α,α -Diphenyl-N-methyl-D-prolinol, 97%, ee 99+% | L19398 | 198 |
| α,α -Diphenyl-N-methyl-L-prolinol, 97%, ee 99+% | L19399 | 198 |
| (R)-(+)-2-(Diphenylmethyl)pyrrolidine | J61001 | 198 |
| (R)-1,1-Diphenyl-2-propanol | J63641 | 199 |
| (S)-1,1-Diphenyl-2-propanol | J63320 | 199 |
| Ethyl (R)-4-bromo-3-hydroxybutyrate | J60862 | 214 |
| Ethyl (S)-4-bromo-3-hydroxybutyrate | J62782 | 214 |
| Ethyl (R)-(-)-3-hydroxybutyrate | J63400 | 216 |
| Ethyl (S)-(-)-3-hydroxybutyrate | J63184 | 216 |
| (R)-2-Heptanol | J61806 | 243 |
| (S)-(+)-2-Heptanol, 98% | 33795 | 243 |
| (S)-(+)-2-Hexanol, 98% | L10401 | 245 |
| (R)-2-(1-Hydroxyethyl)pyridine | J62548 | 249 |
| (S)-2-(1-Hydroxyethyl)pyridine | J60980 | 249 |
| (S)-(+)-5-(Hydroxymethyl)-2-pyrrolidinone, 98% | L18359 | 250 |
| (R)-(-)-5-(Hydroxymethyl)-2-pyrrolidinone, 99% | L18358 | 250 |
| (R)-(+)-3-Hydroxypyrrolidine, 99%, ee 99% | L19499 | 251 |
| (S)-(-)-3-Hydroxypyrrolidine, 99%, ee 99% | L19498 | 251 |
| (R)-1-Methoxy-2-propanol | J63467 | 285 |
| (S)-1-Methoxy-2-propanol | J62757 | 285 |
| (R)-2-(Methylenemethoxy)propane-1,2-diol | J61773 | 287 |
| (S)-2-(Methylenemethoxy)propane-1,2-diol | J62190 | 287 |
| (R)-(-)-4-Methyl-2-pentanol, 99% | L18881 | 289 |
| (S)-(+)-4-Methyl-2-pentanol, 99% | L18882 | 289 |
| (R)-(-)-2-Octanol, 99% | L11502 | 306 |
| (S)-(+)-2-Octanol, 99% | L12425 | 306 |
| (S)-1-Octen-3-ol | J60071 | 306 |
| (R)-3,3,4,4,4-Pentafluorobutanol | J61700 | 313 |
| (S)-3,3,4,4,4-Pentafluorobutanol | J60988 | 313 |
| (R)-(-)-2-Pentanol, 97% | J63298 | 313 |
| (S)-(+)-2-Pentanol, 97% | L09314 | 313 |
| D-Phenylalaninol, 98% | L09697 | 316 |
| L-Phenylalaninol, 98% | A11586 | 316 |
| (R)-(+)-1-Phenylethanol, ChiPros® 99%, ee 97+% | L19296 | 316 |
| (S)-(-)-1-Phenylethanol, 99% | B21188 | 316 |
| (R)-(-)-2-Phenylglycinol, 98% | A19030 | 317 |
| (S)-(+)-2-Phenylglycinol, 98+% | L13265 | 317 |
| (R)-(+)-1-Phenyl-1-propanol, 99% | L05681 | 318 |
| (S)-(-)-1-Phenyl-1-propanol, 99% | L06608 | 318 |

| Description | Stock # | Page # |
|--|---------|--------|
| (R)-(+)-2-Phenyl-1-propanol, 98+% | L13999 | 318 |
| (S)-(-)-2-Phenyl-1-propanol, 98+% | L13988 | 318 |
| (R)-2-Phenylpropionamide | J61693 | 318 |
| (S)-2-Phenylpropionamide | J60150 | 318 |
| (R)-(+)-1-Phenylpropylamine, ChiPros® 99+%, ee 98% | L16319 | 318 |
| (S)-(-)-1-Phenylpropylamine, ChiPros® 99+%, ee 99% | L16320 | 318 |
| (R)-(-)-Prolinol, 98+% | L11109 | 329 |
| (S)-(+)-Prolinol, 98% | L09779 | 329 |
| (R)-Tetrahydrofuran-2-carboxamide | J62007 | 363 |
| (S)-Tetrahydrofuran-2-carboxamide | J60420 | 363 |
| (R)-(-)-Tetrahydrofurfuryl alcohol, 98+% | L19044 | 363 |
| (S)-(+)-Tetrahydrofurfuryl alcohol | J62573 | 363 |
| D-(-)-Valinol, 98% | L14166 | 390 |
| L-(+)-Valinol, 97% | L11300 | 390 |

Click Chemistry Reagents

Click chemistry is a newer approach to synthesis that makes use of simple, rapid and reliable reactions. It has several benefits over other synthesis approaches such as being orthogonal to conventional methods and occurring under relatively mild conditions. These reactions also proceed with high, almost quantitative, yields. These benefits have made click chemistry reactions a popular method of introducing labels and other tags to biomolecules. The most popular click chemistry reaction is the Huisgen 1,3-dipolar cycloaddition of alkynes to azides, which is generally carried out with catalysis by copper (I), or by introduction of an azide to a strain-promoted cyclooctyne.

| Description | Stock # | Page # |
|--|---------|--------|
| Acetylene-PEG4-biotin conjugate | J65577 | 72 |
| Acetylene-PEG4-carboxyrhodamine 6G conjugate | J65593 | 72 |
| Acetylene-PEG4-carboxyrhodamine 110 conjugate | J64892 | 72 |
| Acetylene-PEG4-carboxytetramethylrhodamine 110 conjugate | J64523 | 72 |
| Acetylene-PEG4-maleimide | J64859 | 72 |
| Acetylene-PEG4-sulforhodamine B conjugate | J64948 | 72 |
| Acetylene-PEG4-sulforhodamine 101 conjugate | J65924 | 72 |
| 1-Amino-11-azido-3,6,9-trioxaundecane | J64308 | 91 |
| 1-Amino-3,6,9,12-tetraoxapentadec-14-yne | J64527 | 100 |
| Azadibenzocyclooctyne acid | J64549 | 113 |
| Azadibenzocyclooctyne-amine | J65637 | 113 |
| Azadibenzocyclooctyne-Biotin conjugate | J65472 | 113 |
| Azadibenzocyclooctyne-maleimide | J65377 | 113 |
| Azadibenzocyclooctyne-PEG4-NHS ester | J65223 | 114 |
| Azadibenzocyclooctyne-PEG4-phosphoramidite | J65570 | 114 |
| Azadibenzocyclooctyne-NHS ester | J65981 | 113 |
| Azadibenzocyclooctyne-PEG, MW 5,000 | J64977 | 113 |
| Azadibenzocyclooctyne-PEG, MW 10,000 | J65322 | 113 |
| Azadibenzocyclooctyne-PEG, MW 20,000 | J65953 | 113 |
| Azadibenzocyclooctyne-PEG4-acid | J65338 | 113 |
| Azadibenzocyclooctyne-PEG4-alcohol | J64617 | 113 |
| Azadibenzocyclooctyne-PEG4 amine | J65301 | 113 |
| Azadibenzocyclooctyne-PEG4 biotin conjugate | J65737 | 113 |
| Azadibenzocyclooctyne-PEG4-maleimide | J65673 | 114 |
| Azadibenzocyclooctyne-PEG12 biotin conjugate | J65780 | 114 |
| Azadibenzocyclooctyne-SETA 650 | J64040 | 114 |
| Azadibenzocyclooctyne-S-S-NHS ester | J65628 | 114 |
| Azadibenzocyclooctyne-S-S-PEG3-biotin conjugate | J64256 | 114 |
| Azadibenzocyclooctyne-sulfo-biotin conjugate | J64671 | 114 |
| Azido-PEG(3+3)-S-S-biotin conjugate | J64574 | 115 |
| Azido-PEG12-biotin conjugate | J65147 | 115 |
| Azido-PEG3-biotin conjugate | J64996 | 115 |
| Azido-PEG3-carboxyrhodamine 110 conjugate | J65107 | 115 |
| Azido-PEG3-carboxyrhodamine 6G conjugate | J64906 | 115 |
| Azido-PEG3-carboxytetramethylrhodamine 110 conjugate | J64510 | 115 |
| Azido-PEG3-maleimide kit | J65984 | 115 |
| Azido-PEG3-S-S-NHS ester | J64895 | 115 |
| Azido-PEG3-sulfo-biotin conjugate | J65598 | 115 |
| Azido-PEG3-sulforhodamine 101 conjugate | J65476 | 115 |
| Azido-PEG3-sulforhodamine B conjugate | J65529 | 115 |
| 3-Azido-1-propylamine | J65668 | 115 |
| 15-Azido-4,7,10,13-tetraoxapentadecanoic acid | J64030 | 116 |
| 1,11-Diazido-3,6,9-trioxaundecane | J64863 | 184 |
| N-Succinimidyl 15-azido-4,7,10,13-tetraoxapentadecanoate | J64834 | 354 |
| N-Succinimidyl 3-(propargyloxy)propionate | J64496 | 354 |
| N-Succinimidyl 4,7,10,13-tetraoxahexadec-15-ynoate | J64902 | 354 |

Electrophoresis Reagents

Gel electrophoresis is a technique used to separate DNA, RNA and proteins. When an electric current is applied to these molecules in a gel matrix, they can be separated based on their sizes, shapes and net charges. Agarose gels, because of their larger pore size, are used for the separation of large macromolecules such as nucleic acids, large proteins and protein complexes. Polyacrylamide gels are used to separate most proteins and small oligonucleotides that require a small gel pore size for retardation. This list includes reagents that can be used for agarose and polyacrylamide gel electrophoresis

| Description | Stock # | Page # |
|--|---------|--------|
| Acridine Orange, dye content 55-65% | L13159 | 76 |
| Acrylamide, 30% soln, bisacrylamide free | J62100 | 76 |
| Acrylamide, 40% soln, bisacrylamide free | J62480 | 77 |
| Acrylamide, electrophoresis grade, 99+% | L15075 | 77 |
| Acrylamide/Bisacrylamide 19:1, 30% soln | J60126 | 77 |
| Acrylamide/Bisacrylamide 19:1, 40% soln | J60909 | 77 |
| Acrylamide/Bisacrylamide 19:1, powder | J60486 | 77 |
| Acrylamide/Bisacrylamide 29:1, 30% soln | J63279 | 77 |
| Acrylamide/Bisacrylamide 29:1, 40% soln | J63079 | 77 |
| Acrylamide/Bisacrylamide 29:1, powder | J60824 | 77 |
| Acrylamide/Bisacrylamide 37.5:1, 30% soln | J61505 | 77 |
| Acrylamide/Bisacrylamide 37.5:1, 40% soln | J60868 | 77 |
| Acrylamide/Bisacrylamide 37.5:1, powder | J61220 | 77 |
| Acrylamide/Bisacrylamide 39:1, 30% soln | J60412 | 77 |
| Acrylamide/Bisacrylamide 39:1, 40% soln | J63323 | 77 |
| Agarose, high EEO | J60299 | 81 |
| Agarose, high melting temperature, high resolution | J62714 | 81 |
| Agarose, high melting temperature, medium resolution | J61123 | 81 |
| Agarose D1-LE, molecular biology grade | H26855 | 81 |
| Agarose gel loading dye (6X), alkaline | J62157 | 81 |
| Agarose gel loading dye (6X), Ficoll based | J62800 | 81 |
| Agarose gel loading dye (6X), glycerol based | J63869 | 81 |
| Agarose gel loading dye (6X), glycerol based, bromophenol free | J63429 | 81 |
| Agarose gel loading dye (6X) glycerol based, Xylene Cyanol FF free | J60933 | 81 |
| Agarose gel loading dye (6X), sucrose based | J60333 | 81 |
| Alcian Blue 8GX | J60122 | 85 |
| Alkaline running buffer soln. | J63170 | 89 |
| Amido Black 10B | A11374 | 91 |
| 2-Amino-2-methyl-1-propanol, 95%, may cont. ca 5% water | A17814 | 97 |
| Ammonium chloride, ACS, 99.5% min | 40193 | 101 |
| Ammonium chloride, 99.5% min | 12361 | 101 |
| Ammonium peroxydisulfate, 98% | A10533 | 101 |
| Ammonium peroxydisulfate, Electrophoresis Grade | J61856 | 102 |
| Ammonium sulfate, ACS, 99.0% min | 11566 | 102 |
| Ammonium sulfate, 99.95% (metals basis) | 89363 | 102 |
| Bathocuproin sulfonate disodium salt hydrate, 97% | B22550 | 118 |
| N,N'-Bis(acryloyl)cystamine, 98% | 44132 | 126 |
| bis-Benzimide H-33342 trihydrochloride trihydrate, 98% | J62134 | 126 |
| Boric acid, ACS, 99.5% min | 33253 | 134 |
| Brilliant Blue G, ultrapure | 43318 | 135 |
| Bromophenol Blue sodium salt | A16899 | 137 |
| Cesium chloride, 99.9% (metals basis) | 10018 | 152 |
| CHAPS, 98+% | B21927 | 152 |
| N,N'-Diallyl-L-tartardiamide, 99% | A12195 | 182 |
| N,N'-(1,2-Dihydroxyethylene)bisacrylamide, 97% | L19211 | 192 |
| Dimethylsuberimidate dihydrochloride | 43244 | 197 |
| Dimethyl sulfoxide, ACS, 99.9% min | 36480 | 197 |
| 1,4-Dithioerythritol, 99% | A10138 | 200 |
| 1,4-Dithio-DL-threitol, 99% | A15797 | 200 |
| DNA marker, broad range | J62291 | 200 |
| DNA marker, high range, 1,000 Base Pair Ladder | J63178 | 200 |
| DNA marker, low range, 250 Base Pair Ladder | J63973 | 200 |

| Description | Stock # | Page # |
|---|---------|--------|
| Ethidium bromide soln., 0.625mg/ml | J62029 | 214 |
| Ethidium bromide soln., 10mg/ml | J62282 | 214 |
| Ethidium bromide, 98% (dry wt.) | L07482 | 214 |
| Ethidium bromide de-staining bags | J62931 | 214 |
| Ethylenediaminetetraacetic acid, 99% | A10713 | 215 |
| Ethylenediaminetetraacetic acid, ACS, 99.4+% | 11931 | 215 |
| Ethylenediaminetetraacetic acid, Cell Culture Reagent | J62948 | 215 |
| Ethylenediaminetetraacetic acid disodium salt dihydrate, ACS, 99.0-101.0% | 33312 | 216 |
| Fast Green FCF | A16520 | 219 |
| Ficoll® 400 | B22095 | 221 |
| Formamide, ACS, 99.5+% | 14835 | 227 |
| Glycine, 99% | A13816 | 237 |
| Guanidine hydrochloride, 98% | A13543 | 239 |
| Guanidine hydrochloride, 99+% | J60786 | 239 |
| Guanine, 98% | A12024 | 240 |
| HEPES hemisodium salt | J61830 | 242 |
| HEPES sodium salt, 99% | A16516 | 242 |
| IEF Anode buffer (50X) | J63303 | 253 |
| IEF Cathode buffer (10X) with lysine | J61903 | 253 |
| IEF Cathode buffer (10X) with lysine and arginine | J62204 | 253 |
| IEF Sample buffer (2X) pH 3-10 with lysine and arginine | J62241 | 253 |
| IEF Sample buffer (4X) pH 3-7 with lysine | J63633 | 253 |
| India Ink | J61007 | 255 |
| Laemmli SDS sample buffer, non-reducing (4X) | J63615 | 265 |
| Laemmli SDS sample buffer, non-reducing (6X) | J60660 | 265 |
| Laemmli SDS sample buffer, reducing (4X) | J60015 | 265 |
| Laemmli SDS sample buffer, reducing (6X) | J61337 | 265 |
| Laemmli SDS sample buffer with pyronin Y, non-reducing (4X) | J61716 | 265 |
| Laemmli SDS sample buffer with pyronin Y, reducing (4X) | J62115 | 266 |
| N-Lauroylsarcosine sodium salt, 95% | J60040 | 266 |
| LDS-sample buffer (4X), non-reducing | J61894 | 267 |
| LDS-sample buffer (4X), reducing | J61942 | 267 |
| Lithium dodecylsulfate, 99+% | 39328 | 272 |
| 2-Mercaptoethanol, 98+% | A15890 | 281 |
| MES-SDS running buffer (20X) | J62138 | 283 |
| N,N'-Methylenebisacrylamide, 2% soln. | J63265 | 287 |
| N,N'-Methylenebisacrylamide, 99+% | 43701 | 287 |
| Methylene Blue, high purity, biological stain | A18174 | 287 |
| Methylene Blue trihydrate | J60823 | 287 |
| Methyl Green, zinc chloride | J61509 | 288 |
| MOPS-SDS running buffer (20X) | J62847 | 295 |
| n-Octyl-β-D-glucopyranoside | L13259 | 306 |
| n-Octyl-β-D-thioglucopyranoside, 98+% | J61028 | 306 |
| Orange G, Electrophoresis Grade | J62743 | 308 |
| Orange G loading dye (6X), glycerol based | J60562 | 308 |
| Orange G/blue dye (6X) | J62098 | 308 |
| Orange G/blue loading dye (6X) | J61877 | 308 |
| Phenol:Chloroform:Isoamyl alcohol 25:24:1, Ready-to-use saturated aq. soln., pH 5.2, with alkaline buffer | J62336 | 314 |
| Phenol:Chloroform:Isoamyl alcohol 25:24:1, Ready-to-use saturated aq. soln., pH 6.7, with alkaline buffer | J60331 | 314 |
| Phenol:Chloroform 1:1, Ready-to-use soln., pH 6.7, with alkaline buffer | J63452 | 314 |
| Polyethyleneimine, M.W. 60,000, 50% w/w aq. soln. | J61270 | 324 |
| Polyethyleneimine, branched, M.W. 70,000, 30% w/v aq. soln. | 40529 | 324 |
| Polysorbate 20 | L15029 | 325 |
| Polysorbate 80 | L13315 | 325 |
| Ponceau S, 0.2% v/v soln. in 5% acetic acid | J63139 | 325 |
| Ponceau S, Electrophoresis Grade | J60744 | 325 |
| Potassium peroxydisulfate, ACS, 99.0% min | 13145 | 327 |
| Proteinase K, Tritirachium album limber | J62051 | 331 |
| Proteinase K, Ready-to-use soln. | J63710 | 331 |
| Pyronin Y | J61068 | 332 |
| Pyronin Y, 0.2% w/v aq. soln. | J60505 | 332 |
| Rapid stain G-250 | J61347 | 335 |
| Rapid stain R-250 | J61969 | 335 |
| Riboflavin, 98% | A11764 | 337 |

Electrophoresis Reagents

| Description | Stock # | Page # |
|--|---------|--------|
| Riboflavin-5'-phosphate sodium salt dihydrate | A14545 | 337 |
| RNA sample loading buffer | J62832 | 339 |
| RNA sample loading buffer (6X) | J62468 | 339 |
| RNA sample loading buffer, no ethidium bromide | J61937 | 339 |
| Separating or resolving buffer (4X) | J60181 | 341 |
| Sodium n-dodecyl sulfate, 99% (dry wt.), water <1.5% | A11183 | 346 |
| Stacking buffer (4X) | J63450 | 351 |
| Stains-All, 95% | J62630 | 351 |
| 5-Sulfosalicylic acid dihydrate, ACS, 99+% | 43144 | 356 |
| TAE (10X), TRIS + acetate + EDTA | J63677 | 357 |
| TAE (50X), TRIS + acetate + EDTA | J63931 | 357 |
| TBE sample buffer (6X) | J60357 | 359 |
| TBE running buffer (10X) | J62788 | 359 |
| TBE urea sample buffer (2X) | J60186 | 359 |
| N,N,N',N'-Tetramethylethylenediamine, 99% | A12536 | 364 |
| N,N,N',N'-Tetramethylethylenediamine, Electrophoresis Grade | J63734 | 365 |
| Transfer or electro blotting buffer (10X), pH 8.5 | J63037 | 373 |
| Tricine-SDS Sample Buffer (2X), non-reducing | J62677 | 375 |
| Tricine-SDS Sample Buffer (2X), reducing | J61042 | 375 |
| TRIS-CAPS buffer (10X) | J61339 | 381 |
| TRIS-glycine-native running buffer (10X), pH 8.5 | J62914 | 381 |
| TRIS-glycine-SDS running buffer (10X), pH 8.3 | J61006 | 381 |
| TRIS-glycine native sample buffer (4X), pH 8.6 | J61864 | 381 |
| TRIS-HEPES-native running buffer (10X), pH 8.0 | J62737 | 382 |
| TRIS-HEPES-SDS running buffer (10X), pH 8.0 | J61789 | 382 |
| TRIS-Tricine-SDS kit (10X) | J63948 | 383 |
| TRIS-Tricine-SDS running buffer (10X), anode buffer, pH 8.9 | J63375 | 383 |
| TRIS-Tricine-SDS running buffer (10X), cathode buffer, pH 8.3 | J60992 | 383 |
| Tris(hydroxymethyl)aminomethane, ACS, 99.8-100.1% (Assay, dried basis) | 31801 | 382 |
| Tris(hydroxymethyl)aminomethane, Electrophoresis Grade, 99.5% | J61016 | 382 |
| Tris(hydroxymethyl)aminomethane, Electrophoresis Grade, 99.9% | J62569 | 382 |
| Tris(hydroxymethyl)aminomethane hydrochloride, 99+% | A11379 | 382 |
| Urea, 98+% | A12360 | 388 |
| Urea, ACS, 99.0-100.5% | 36428 | 388 |
| Water, RNase, DNase-free | J60610 | 393 |
| Xylenecyanol FF, dye content 70% | B21530 | 394 |
| Zymogram developing buffer (10X), pH 7.45 | J61375 | 397 |
| Zymogram renaturation buffer (10X) | J63137 | 397 |
| Zymogram sample buffer, pH 6.6 | J62774 | 397 |

Electrophoresis Reagents - Buffers

The buffer system in electrophoresis controls the pH of the gel, acting to prevent damage to sample molecules and controlling the ionization state of the molecules. Electrophoresis buffers also provide ions that carry the electric current through the gel matrix. Common electrophoresis buffers include TAE buffer for agarose gel electrophoresis and Tris-glycine for PAGE.

| Description | Stock # | Page # |
|---|---------|--------|
| Alkaline running buffer soln. | J63170 | 89 |
| 2-Amino-2-methyl-1-propanol, 95%, may cont. ca 5% water | A17814 | 97 |
| Citric acid, 99+% | A10395 | 164 |
| Ethylenediaminetetraacetic acid, 99% | A10713 | 215 |
| Ethylenediaminetetraacetic acid, ACS, 99.4+% | 11931 | 215 |
| Ethylenediaminetetraacetic acid disodium salt dihydrate, ACS, 99.0-101.0% | 33312 | 216 |
| HEPES hemisodium salt | J61830 | 242 |
| HEPES sodium salt, 99% | A16516 | 242 |
| IEF Anode buffer (50X) | J63303 | 253 |
| IEF Cathode buffer (10X) with lysine | J61903 | 253 |
| IEF Cathode buffer (10X) with lysine and arginine | J62204 | 253 |
| IEF Sample buffer (2X) pH 3-10 with lysine and arginine | J62241 | 253 |
| IEF Sample buffer (4X) pH 3-7 with lysine | J63633 | 253 |
| Laemmli SDS sample buffer, non-reducing (4X) | J63615 | 265 |
| Laemmli SDS sample buffer, reducing (4X) | J60015 | 265 |
| Laemmli SDS sample buffer with pyronin Y, non-reducing (4X) | J61716 | 265 |
| Laemmli SDS sample buffer with pyronin Y, reducing (4X) | J62115 | 266 |
| LDS-sample buffer (4X), non-reducing | J61894 | 267 |
| LDS-sample buffer (4X), reducing | J61942 | 267 |
| MES-SDS running buffer (20X) | J62138 | 283 |
| MOPS-SDS running buffer (20X) | J62847 | 295 |
| Separating or resolving buffer (4X) | J60181 | 341 |
| Stacking buffer (4X) | J63450 | 351 |
| TAE (10X), TRIS + acetate + EDTA | J63677 | 357 |
| TAE (50X), TRIS + acetate + EDTA | J63931 | 357 |
| TBE sample buffer (6X) | J60357 | 359 |
| TBE running buffer (10X) | J62788 | 359 |
| TBE urea sample buffer (2X) | J60186 | 359 |
| Transfer or electro blotting buffer (10X), pH 8.5 | J63037 | 373 |
| Tricine-SDS Sample Buffer (2X), non-reducing | J62677 | 375 |
| Tricine-SDS Sample Buffer (2X), reducing | J61042 | 375 |
| TRIS-CAPS buffer (10X) | J61339 | 381 |
| TRIS-glycine-native running buffer (10X), pH 8.5 | J62914 | 381 |
| TRIS-glycine-SDS running buffer (10X), pH 8.3 | J61006 | 381 |
| TRIS-glycine native sample buffer (4X), pH 8.6 | J61864 | 381 |
| TRIS-HEPES-native running buffer (10X), pH 8.0 | J62737 | 382 |
| TRIS-HEPES-SDS running buffer (10X), pH 8.0 | J61789 | 382 |
| TRIS-Tricine-SDS kit (10X) | J63948 | 383 |
| TRIS-Tricine-SDS running buffer (10X), anode buffer, pH 8.9 | J63375 | 383 |
| TRIS-Tricine-SDS running buffer (10X), cathode buffer, pH 8.3 | J60992 | 383 |
| Tris(hydroxymethyl)aminomethane, ACS, 99.8-100.1% (Assay, dried basis) | 31801 | 382 |
| Tris(hydroxymethyl)aminomethane, Electrophoresis Grade, 99.5% | J61016 | 382 |
| Tris(hydroxymethyl)aminomethane, Electrophoresis Grade, 99.9% | J62569 | 382 |
| Tris(hydroxymethyl)aminomethane hydrochloride, 99+% | A11379 | 382 |
| Zymogram developing buffer (10X), pH 7.45 | J61375 | 397 |
| Zymogram renaturation buffer (10X) | J63137 | 397 |
| Zymogram sample buffer, pH 6.6 | J62774 | 397 |

Electrophoresis Reagents - Co-monomers

Polyacrylamide gels are formed by the polymerization of acrylamide monomer in aqueous solution in the presence of small amounts of a bifunctional crosslinker. In most cases the cross linker is N, N'-methylenebisacrylamide, but others such as N, N'-bis(acryloyl)cystamine and N, N'-diallyl-L-tartardiamide are sometimes used. Crosslinking of these co-monomers produces a three-dimensional mesh-like gel matrix that enables the purification of macromolecules. This list includes acrylamide, bisacrylamide, and premixed mixtures for PAGE gel casting.

| Description | Stock # | Page # |
|--|---------|--------|
| Acrylamide, 30% soln, bisacrylamide free | J62100 | 76 |
| Acrylamide, 40% soln, bisacrylamide free | J62480 | 77 |
| Acrylamide, electrophoresis grade, 99+% | L15075 | 77 |
| Acrylamide/Bisacrylamide 19:1, 30% soln | J60126 | 77 |
| Acrylamide/Bisacrylamide 19:1, 40% soln | J60909 | 77 |
| Acrylamide/Bisacrylamide 19:1, powder | J60486 | 77 |
| Acrylamide/Bisacrylamide 29:1, 30% soln | J63279 | 77 |
| Acrylamide/Bisacrylamide 29:1, 40% soln | J63079 | 77 |
| Acrylamide/Bisacrylamide 29:1, powder | J60824 | 77 |
| Acrylamide/Bisacrylamide 37.5:1, 30% soln | J61505 | 77 |
| Acrylamide/Bisacrylamide 37.5:1, 40% soln | J60868 | 77 |
| Acrylamide/Bisacrylamide 37.5:1, powder | J61220 | 77 |
| Acrylamide/Bisacrylamide 39:1, 30% soln | J60412 | 77 |
| Acrylamide/Bisacrylamide 39:1, 40% soln | J63323 | 77 |
| N,N'-Bis(acryloyl)cystamine, 98% | 44132 | 126 |
| N,N'-Diallyl-L-tartardiamide, 99% | A12195 | 182 |
| 1,4-Diacryloylpiperazine, 97% | L15694 | 182 |
| N,N'-(1,2-Dihydroxyethylene)bisacrylamide, 97% | L19211 | 192 |
| N,N'-Methylenebisacrylamide, 2% soln. | J63265 | 287 |
| N,N'-Methylenebisacrylamide, 99+% | 43701 | 287 |

Electrophoresis Reagents - Initiators of Polymerization

Crosslinking in polyacrylamide gels is achieved by the addition of a catalyst. The most common system of catalytic initiation involves the production of free oxygen radicals by ammonium persulfate in the presence of the tertiary aliphatic amine N,N,N',N'-tetramethylethylenediamine (TEMED). Initiation can also be achieved by a photochemical process where a very small amount of riboflavin is added in the presence of TEMED; however, gelation may take longer with this method.

| Description | Stock # | Page # |
|---|---------|--------|
| Ammonium peroxydisulfate, 98% | A10533 | 101 |
| Ammonium peroxydisulfate, Electrophoresis Grade | J61856 | 102 |
| Potassium peroxydisulfate, ACS, 99.0% min | 13145 | 327 |
| Riboflavin, 98% | A11764 | 337 |
| Riboflavin-5'-phosphate sodium salt dihydrate | A14545 | 337 |
| N,N,N',N'-Tetramethylethylenediamine, 99% | A12536 | 364 |
| N,N,N',N'-Tetramethylethylenediamine, Electrophoresis Grade | J63734 | 365 |

Electrophoresis Reagents - Protein Purification

These items can be used to isolate and purify proteins that have been separated by PAGE.

| Description | Stock # | Page # |
|---|---------|--------|
| Ammonium chloride, 99.5% min | 12361 | 101 |
| Ammonium sulfate, 99.95% (metals basis) | 89363 | 102 |
| Boric acid, ACS, 99.5% min | 33253 | 134 |
| Cesium chloride, 99.9% (metals basis) | 10018 | 152 |
| Cesium chloride, 99.999+% (metals basis) | 89188 | 152 |
| Cesium hydroxide hydrate, 99.9% (metals basis) | 13233 | 152 |
| Cesium nitrate, 99.8% (metals basis) | 12884 | 152 |
| CHAPS, 98+% | B21927 | 152 |
| Chloroform, HPLC Grade, 99.5+% min | 22920 | 156 |
| Chloroform, HPLC Grade, 99.5+% min, stab. with amylene | 43685 | 156 |
| Chloroform, Spectrophotometric Grade, 99.5+% | 32442 | 156 |
| Chloroform, ethanol-free, 99+%, stab. with ca 50 ppm amylene | L14759 | 156 |
| Dimethylsuberimidate dihydrochloride | 43244 | 197 |
| Dimethyl sulfoxide, ACS, 99.9% min | 36480 | 197 |
| 1,4-Dithioerythritol, 99% | A10138 | 200 |
| 1,4-Dithio-DL-threitol, 99% | A15797 | 200 |
| Ethidium bromide soln., 10mg/ml | J62282 | 214 |
| Ethidium bromide, 98% (dry wt.) | L07482 | 214 |
| Ethidium bromide de-staining bags | J62931 | 214 |
| Formamide, ACS, 99.5+% | 14835 | 227 |
| (1-Hexadecyl)trimethylammonium bromide, 98% | A15235 | 244 |
| N-Lauroylsarcosine sodium salt, 95% | J60040 | 266 |
| 2-Mercaptoethanol, 98+% | A15890 | 281 |
| n-Octyl-β-D-thioglucopyranoside, 98+% | J61028 | 306 |
| Phenol:Chloroform:Isoamyl alcohol 25:24:1, Ready-to-use saturated aq. soln., pH 5.2, with alkaline buffer | J62336 | 314 |
| Phenol:Chloroform:Isoamyl alcohol 25:24:1, Ready-to-use saturated aq. soln., pH 6.7, with alkaline buffer | J60331 | 314 |
| Phenol:Chloroform 1:1, Ready-to-use soln., pH 6.7, with alkaline buffer | J63452 | 314 |
| Polyethyleneimine, M.W. 60,000, 50% w/w aq. soln. | J61270 | 324 |
| Polysorbate 20 | L15029 | 325 |
| Polysorbate 80 | L13315 | 325 |
| Proteinase K, Ready-to-use soln. | J63710 | 331 |
| Sodium n-dodecyl sulfate, 99% (dry wt.), water <1.5% | A11183 | 346 |
| 5-Sulfosalicylic acid dihydrate, ACS, 99+% | 43144 | 356 |
| Urea, 98+% | A12360 | 388 |
| Water, RNase, DNase-free | J60610 | 393 |

Electrophoresis Reagents - Stains

Stains bind non-specifically to peptides, proteins and oligonucleotides and are used to visualize their location within the gel matrices. The most common dye for DNA or RNA staining is ethidium bromide while Brilliant Blue is traditionally used for protein staining.

| Description | Stock # | Page # |
|--|---------|--------|
| Acridine Orange, dye content 55-65% | L13159 | 76 |
| Alcian Blue 8GX | J60122 | 85 |
| Amido Black 10B | A11374 | 91 |
| Bathocuproin sulfonate disodium salt hydrate, 97% | B22550 | 118 |
| bis-Benzimide H-33342 trihydrochloride trihydrate, 98% | J62134 | 126 |
| Brilliant Blue G soln., Ready-to-Use | J63797 | 135 |
| Brilliant Blue R | J64297 | 135 |
| Brilliant Blue R soln., Ready-to-Use | J61384 | 135 |
| Bromophenol Blue sodium salt | A16899 | 137 |
| Ethidium bromide soln., 0.625mg/ml | J62029 | 214 |
| Fast Green FCF | A16520 | 219 |
| India Ink | J61007 | 255 |
| Methyl Green, zinc chloride | J61509 | 288 |
| Orange G, Electrophoresis Grade | J62743 | 308 |
| Ponceau S, Electrophoresis Grade | J60744 | 325 |
| Pyronin Y | J61068 | 332 |
| Rapid stain R-250 | J61969 | 335 |
| Stains-All, 95% | J62630 | 351 |
| Xylenecyanol FF, dye content 70% | B21530 | 394 |

Enzymes

Enzymes are proteins that catalyze biochemical reactions on specific substrates. Enzymes serve a wide variety of functions inside living organisms and play important roles in cell cycle regulation and metabolism.

| Description | Stock # | Page # |
|---|---------|--------|
| Alcohol dehydrogenase kit - 12 variants (A1 through A12) | J64628 | 85 |
| Alcohol dehydrogenase kit - 35 variants (A1 through A35) | J64194 | 85 |
| Alcohol dehydrogenase, yeast | J65869 | 85 |
| R1-Alcohol Dehydrogenase | 45391 | 87 |
| R2-Alcohol Dehydrogenase | 45393 | 87 |
| S1-Alcohol Dehydrogenase | 45392 | 87 |
| S2-Alcohol Dehydrogenase | 45394 | 87 |
| S3-Alcohol Dehydrogenase | 45395 | 87 |
| S4-Alcohol Dehydrogenase | 45397 | 87 |
| S5-Alcohol Dehydrogenase | 45399 | 87 |
| S6-Alcohol Dehydrogenase | 45401 | 87 |
| Aldehyde Dehydrogenase Kit - 5 variants (AD1 through AD5) | J64713 | 87 |
| Aldehyde Reductase Kit - 10 variants (AR1-AR10) | J65717 | 88 |
| Alkaline Phosphatase, calf intestine, EIA Grade | J61037 | 89 |
| Cathepsin G, 95% | J61280 | 150 |
| Cellulase, chromatographically purified, T. reesei | J64019 | 151 |
| Clostripain, Clostridium histolyticum | J61362 | 166 |
| Cofactor Recycling Enzymes Kit - 8 variants | J64535 | 166 |
| Collagenase, Type I, Clostridium histolyticum | J62406 | 167 |
| Deoxyribonuclease I, bovine pancreas | J62229 | 179 |
| Deoxyribonuclease II, porcine spleen | J63389 | 179 |
| DNA Polymerase I Large (Klenow Fragment) | J65056 | 106 |
| Elastase, porcine pancreas | J61874 | 205 |
| Ene Reductase Kit - 8 variants (ENR1 through ENR8) | J64291 | 206 |
| Esterase Kit - 50 variants (E1 through E50) | J65256 | 211 |
| Esterase Kit - 30 variants (E1 through E30) | J64957 | 210 |
| Ficin, fig tree latex | J60136 | 221 |
| Formate Dehydrogenase | J65016 | 227 |
| Glucose Dehydrogenase variant B | J65832 | 233 |
| Glucose-6-phosphate dehydrogenase, Leuconostoc mesenteroides | J60117 | 234 |
| Glucose-6-phosphate dehydrogenase, yeast | J61181 | 234 |
| Glutamic oxalacetic transaminase, porcine heart | J60044 | 235 |
| Glutamic pyruvic transaminase, porcine heart | J62109 | 235 |
| Hexokinase, yeast | J63795 | 245 |
| Isocitrate Dehydrogenase | J65073 | 260 |
| Lactate dehydrogenase, rabbit muscle | J63220 | 265 |
| Lipase, from porcine pancreas | J62903 | 270 |
| Lipase Kit - 12 variants (L1 through L12) | J64732 | 270 |
| Lysozyme, chicken egg white | J60701 | 274 |
| Malic decarboxylase variant A | J65970 | 276 |
| Malic decarboxylase variant B | J64878 | 276 |
| Neuraminidase, Clostridium perfringens | J63259 | 300 |
| Pancreatin, porcine pancreas | J62162 | 311 |
| Papain, Carica Papaya Latex | J61875 | 311 |
| Pectinase, Aspergillus niger | J63408 | 312 |
| Pepsin, porcine stomach | J61679 | 313 |
| Peroxidase, horseradish | J60026 | 314 |
| Phenylalanine Dehydrogenase | J64524 | 316 |
| Proteinase K, Tritirachium album limber | J62051 | 331 |
| Proteinase K, Ready-to-use soln. | J63710 | 331 |
| Pyruvate Kinase, rabbit muscle | J61373 | 333 |
| Reverse Transcriptase, Avian Myeloblastosis Virus in phosphate buffer | J65829 | 336 |
| Reverse Transcriptase, murine, Moloney Murine Leukemia Virus | J60167 | 336 |
| Ribonuclease, bovine pancreas | J62952 | 337 |
| Ribonuclease A, bovine pancreas, purified | J61996 | 337 |
| Ribonuclease B, bovine pancreas | J62334 | 337 |
| Ribonuclease T1, Aspergillus oryzae in 2.8M ammonium sulfate | J61644 | 337 |
| SP6 RNA Polymerase in Tris buffer | J65792 | 350 |
| SP6 RNA Polymerase in potassium phosphate buffer | J65573 | 350 |

| Description | Stock # | Page # |
|---|---------|--------|
| Superoxide Dismutase, bovine erythrocytes | J63003 | 356 |
| T4 DNA Ligase, 99+%, in 10mM Tris HCl and 50mM NaCl | J65133 | 357 |
| T4 DNA Ligase, in 20mM Tris HCl and 50mM KCl | J65312 | 357 |
| T4 Polynucleotide Kinase | J65162 | 372 |
| T7 RNA Polymerase, in 20mM potassium phosphate and 10mM DTT | J65896 | 357 |
| Taq DNA Polymerase | J64594 | 358 |
| Transaminase Kit - 12 variants (TA1 through TA12) | J64941 | 372 |
| Transaminase Kit - 20 variants (TA1 through TA20) | J64306 | 372 |
| Trypsin, bovine pancreas | J63688 | 384 |
| Trypsin 1:250, porcine pancreas | J63993 | 384 |
| Trypsin, porcine pancreas | J60402 | 384 |
| Urease, Jack Beans | J61455 | 388 |
| Uricase, Candida utilis | J60875 | 389 |
| Urokinase, human urine | J60553 | 389 |
| Yeast Lytic Enzyme, Arthrobacter luteus | J63195 | 395 |

Growth Factors

Growth factors are naturally occurring substances which stimulate cellular growth, proliferation and cellular differentiation. Growth factors are important for regulating cellular processes and act as signaling molecules between cells. Our extensive product line includes receptor-grade, aseptically packaged GFs and AFs. These are highly purified proteins that have been membrane filtered, aseptically filled and lyophilized.

| Description | Stock # | Page # |
|---|---------|--------|
| Bovine Pituitary Extract | J64417 | 134 |
| Endothelial Cell Growth Supplement, bovine hypothalamus | J64516 | 206 |
| Epidermal Growth Factor, human, 99% | J64012 | 208 |
| Epidermal Growth Factor, mouse submaxillary gland, 99% | J65329 | 209 |
| Epidermal Growth Factor, rat, 99% | J64798 | 209 |
| Fibroblast Growth Factor, acidic, bovine, 90% | J65635 | 220 |
| Fibroblast Growth Factor, acidic, human, 95% | J64035 | 220 |
| Fibroblast Growth Factor, basic, bovine, 95% | J65713 | 220 |
| Fibroblast Growth Factor, basic, human, 95% | J64811 | 220 |
| Insulin-like Growth Factor-I, human, 97% | J64081 | 257 |
| Insulin-like Growth Factor-II, human, 97% | J65170 | 257 |
| Nerve Growth Factor 2.5S, mouse submaxillary gland, 95% | J64864 | 300 |
| Platelet-Derived Growth Factor-AA, human, Receptor Grade, 97% | J64463 | 323 |
| Platelet-Derived Growth Factor-BB, human, Receptor Grade, 97% | J64812 | 323 |
| Transforming Growth Factor- α , human, 98% | J64478 | 373 |
| Transforming Growth Factor- β 1, human platelets, 97% | J65773 | 373 |
| Transforming Growth Factor- β 1, human platelets, carrier free, 97% | J65044 | 374 |
| Transforming Growth Factor- β 1, human platelets, lyophilized with BSA, 97% | J65173 | 374 |
| Vascular Endothelial Cell Growth Factor, 98% | J64375 | 391 |

Natural Products

Natural products are chemical compounds that are synthesized in organisms. These compounds often play an important role in the development of medicinal compounds. Our list of natural products include steroids, terpenes, glycosides, and several alkaloids among other biochemicals.

| Description | Stock # | Page # |
|---|---------|--------|
| Acacia, Total ash <4% | 36499 | 69 |
| Agar powder | A10752 | 81 |
| Alginic acid | A17582 | 89 |
| Alginic acid sodium salt, low viscosity | B25266 | 89 |
| Alginic acid sodium salt, high viscosity | J61887 | 89 |
| Alginic acid sodium salt, very low viscosity | A18565 | 89 |
| Allantoin, 98% | A15571 | 89 |
| Aloin | J62153 | 90 |
| Ammonium L-(+)-tartrate, 98% | 17658 | 102 |
| Anthrone, ACS | 30739 | 105 |
| Bilirubin, 97% | A17522 | 125 |
| Carrageenan, iota type | J60603 | 148 |
| Casein, tech. | A13707 | 148 |
| Casein Peptone | H26557 | 149 |
| Catechol, 99% | A10164 | 150 |
| Chenodeoxycholic acid | J60364 | 153 |
| Cholesterol, 95% | A11470 | 161 |
| Cholic acid sodium salt | J62050 | 161 |
| (-)-Cinchonidine, 99% (total base), may cont. up to 5% quinine | A18796 | 163 |
| (+)-Cinchonine, 98+%, cont. up to 3% quinidine/dihydroquinidine and 3% quinine/dihydroquinine | A17523 | 163 |
| 1,8-Cineole, 99% | A12269 | 163 |
| Collagen, bovine achilles tendon | J60218 | 167 |
| Croton oil | J62367 | 169 |
| Curcumin, 95% (total curcuminoid content), from Turmeric rhizome | B21573 | 170 |
| Cytochrome C, equine heart, 90+% | J62122 | 174 |
| Dehydrocholic acid, 99% | A19666 | 176 |
| Deoxycholic acid, 99% | B20061 | 177 |
| Deoxycholic acid sodium salt | J62288 | 177 |
| Deoxyribonucleic acid, salmon testes | J60840 | 179 |
| 5,7-Dihydroxyflavone, 98% | L14178 | 192 |
| Diosmin | J62073 | 198 |
| Elaidic acid, 98% | A14832 | 205 |
| Erythrina Christagalli Agglutinin (ECA) | J60146 | 210 |
| Farnesyl acetate, mixture of isomers, 96% | A19778 | 218 |
| Fetuin I, fetal bovine serum | J60437 | 220 |
| Fibrinogen, bovine | J63276 | 220 |
| Fibronectin, bovine plasma | J62380 | 220 |
| Filter aid, Celite® Standard Super-cel | B21983 | 221 |
| Gellan Gum | J63423 | 231 |
| Geranyl acetate, 98% | A19864 | 231 |
| Glycerol tributurate, 98% | A11830 | 236 |
| Hematin, 97% | A18518 | 241 |
| Hematoporphyrin dihydrochloride | A18579 | 241 |
| Hemin (porcine), 98+% | A11165 | 242 |
| Hemoglobin, bovine | J63838 | 242 |
| Heparin sodium salt, from porcine intestinal mucosa, IU>=100/mg | A16198 | 242 |
| Hesperidin, 98+% | J62126 | 244 |
| Hyaluronic acid, bovine vitreous humor | J60566 | 247 |
| Hydrocortisone, 98% | A16292 | 248 |
| Hydroquinone, 99% | A11411 | 248 |
| Insulin, from porcine pancreas, 98+% | J61321 | 257 |
| Intrinsic Factor | J61698 | 257 |
| Karaya Gum | J61844 | 262 |
| Kojic acid, 99% | A10760 | 264 |
| Lactalbumin hydrolysate | J63215 | 264 |
| Lecithin, 60%, egg | J60576 | 268 |
| Lecithin, 90%, soybean | J61675 | 268 |
| Magnesium silicate monohydrate (Talc) | 40318 | 274 |
| Meat Peptone | H26694 | 278 |

| Description | Stock # | Page # |
|---|---------|--------|
| Melatonin, 99+% | J62452 | 279 |
| Mucin, bovine submaxillary gland | J63859 | 296 |
| Myricetin, 98% | J60450 | 296 |
| (+)-Nootkatone, crystalline, 98+% | A19166 | 304 |
| D-Pinitol, 95% | H56648 | 321 |
| Safflower oil, Carthamus tinctorius | J63982 | 339 |
| Sodium cholate hydrate, 99% | A17074 | 345 |
| Sodium DL-lactate, 60% w/w aq. soln. | 41529 | 347 |
| Sodium taurocholate hydrate, 97% | A18346 | 349 |
| Soybean oil | J61399 | 350 |
| α -Terpineol, 96% | 16285 | 360 |
| Thrombin, bovine plasma | J63383 | 368 |
| Tragacanth powder | A18502 | 372 |
| Transferrin (Apo), bovine plasma, 98+% | J61626 | 373 |
| Transferrin (Holo), bovine plasma, 98+% | J61046 | 373 |
| Ursodeoxycholic acid, 99% | B20490 | 389 |
| Wheat Germ Oil | J63969 | 393 |
| Yeast extract | J60287 | 395 |
| 2X YT Microbial medium | J63227 | 395 |

Nucleosides and Nucleotides

Nucleotides and nucleosides are the building blocks of RNA and DNA and are derived from nitrogenous bases. These nitrogenous bases are either purines (adenine and guanine) or pyrimidines (cytosine, uracil, and thymine). Nucleosides consist of a purine or pyrimidine base linked to a pentose sugar. Nucleotides consist of nucleosides with one or more phosphate groups.

| Description | Stock # | Page # |
|--|---------|--------|
| N4-Acetyl-5'-O-(4,4'-dimethoxytrityl)-2'-fluoro-2'-deoxycytidine, 98% | J65262 | 72 |
| N4-Acetyl-5'-O-(4,4'-dimethoxytrityl)-2'-fluoro-2'-deoxycytidine-3'-CE-phosphoramidite, 98% | J65064 | 72 |
| N4-Acetyl-5'-O-(4,4'-dimethoxytrityl)-2'-O-methylcytidine, 98% | J65490 | 72 |
| N4-Acetyl-5'-O-(4,4'-dimethoxytrityl)-2'-O-methylcytidine-3'-CE-phosphoramidite | J65996 | 72 |
| N4-Acetyl-2'-fluoro-2'-deoxycytidine, 98% | J65915 | 72 |
| N4-Acetyl-2'-O-methylcytidine, 98% | J65560 | 74 |
| Adenine, 99% | A14906 | 78 |
| Adenine hydrochloride, 98+%, cont. up to ca 5% water | A17622 | 78 |
| Adenine sulfate, 98+% | A16964 | 78 |
| Adenosine, 99% | A10781 | 78 |
| Adenosine-2',3'-cyclic monophosphate sodium salt, 98% | J60558 | 78 |
| Adenosine-3',5'-cyclic monophosphate sodium salt, 99% | J62174 | 79 |
| Adenosine-5'-diphosphate monopotassium salt dihydrate, 99% | J60672 | 79 |
| Adenosine-5'-diphosphate disodium salt, 97% (dry wt.), water 7% max. | L14029 | 79 |
| Adenosine-5'- diphosphate trilithium salt, 98% | J64497 | 79 |
| Adenosine-5'-monophosphate disodium salt | J61643 | 79 |
| Adenosine-3',5'-monophosphoric acid, 98% | J60936 | 79 |
| Adenosine-5'-triphosphate disodium salt hydrate, 98% | J61125 | 79 |
| 2-Amino-6-chloropurine, 99% | A18195 | 92 |
| 2-Amino-2'-deoxyadenosine, 99% | J64266 | 93 |
| 2'-Amino-2'-deoxyadenosine, 98% | J65532 | 93 |
| 2'-Amino-2'-deoxyguanosine, 98% | J64650 | 93 |
| 2'-Amino-2'-deoxyinosine, 98% | J65374 | 93 |
| 2'-Amino-2'-deoxyuridine, 98% | J65923 | 93 |
| 3'-Amino-2',3'-dideoxyadenosine, 99% | J65090 | 93 |
| 3'-Amino-2',3'-dideoxyguanosine, 99% | J65326 | 93 |
| 3'-Amino-2',3'-dideoxyinosine, 99% | J64758 | 93 |
| 3'-Amino-2',3'-dideoxythymidine, 99% | J64342 | 93 |
| 2-Amino-2'-fluoro-2'-deoxyadenosine, 99% | J65741 | 94 |
| Aminoguanidine hydrogen carbonate, 98+% | B24696 | 94 |
| 4-Aminoimidazole-5-carboxamide hydrochloride, 98% | B24012 | 95 |
| 2-Amino-2'-O-methyladenosine, 99% | J65334 | 96 |
| 6-Aminonicotinamide, 99% | L06692 | 98 |
| 3-Aminopyrazine-2-carboxylic acid, 98+% | B23707 | 99 |
| 2-Aminopyrimidine, 98% | B24594 | 99 |
| 5-Aminouracil, 97% | L04452 | 100 |
| 6-Aminouracil, 98% | L03332 | 100 |
| 9-β-D-Arabinofuranosyladenine, 99% | J65076 | 108 |
| 9-β-D-Arabinofuranosyladenine-5'-monophosphate, 99% | J65653 | 108 |
| 9-β-D-Arabinofuranosyl-2-fluoro-adenine-5'-monophosphate, 99% | J65154 | 108 |
| 1-β-D-Arabinofuranosyluracil, 99% | J64147 | 108 |
| 5-Azacytosine, 98% (dry wt.), may cont. up to ca 7% water | A13410 | 112 |
| 7-Azaindole, 98% | L07983 | 114 |
| 6-Azathymine, 98% | L06762 | 114 |
| 6-Azauracil, 98% | A14389 | 114 |
| 6-Azauridine | J61309 | 114 |
| 2'-Azido-2'-deoxyuridine, 98% | J64387 | 115 |
| Benzimidazole, 99% | A12763 | 119 |
| N-Benzoylaminopurine, 99% | L08292 | 121 |
| N ₆ -Benzoyl-2'-deoxyadenosine, 98% | J64175 | 121 |
| N ₆ -Benzoyl-5'-O-(4,4'-dimethoxytrityl)-2'-fluoro-2'-deoxyadenosine, 98% | J65402 | 121 |
| N ₆ -Benzoyl-5'-O-(4,4'-dimethoxytrityl)-2'-fluoro-2'-deoxyadenosine-3'-CE-phosphoramidite, 98% | J64064 | 121 |
| N ₄ -Benzoyl-5'-O-(4,4'-dimethoxytrityl)-2'-fluoro-2'-deoxycytidine, 98% | J64614 | 121 |
| N ₄ -Benzoyl-5'-O-(4,4'-dimethoxytrityl)-2'-fluoro-2'-deoxycytidine-3'-CE-phosphoramidite, 98% | J64259 | 121 |

| Description | Stock # | Page # |
|---|---------|--------|
| N ₆ -Benzoyl-5'-O-(4,4'-dimethoxytrityl)-2'-O-methyladenosine, 98% | J65098 | 121 |
| N ₆ -Benzoyl-5'-O-(4,4'-dimethoxytrityl)-2'-O-methyladenosine-3'-CE-phosphoramidite, 98% | J65669 | 121 |
| N ₄ -Benzoyl-5'-O-(4,4'-dimethoxytrityl)-2'-O-methylcytidine, 98% | J65169 | 121 |
| N ₄ -Benzoyl-5'-O-(4,4'-dimethoxytrityl)-2'-O-methylcytidine-3'-CE-phosphoramidite, 98% | J65701 | 121 |
| N ₆ -Benzoyl-2'-fluoro-2'-deoxyadenosine, 98% | J64345 | 121 |
| N ₄ -Benzoyl-2'-fluoro-2'-deoxycytidine, 98% | J65736 | 121 |
| N ₆ -Benzoyl-2'-O-methyladenosine, 98% | J65475 | 122 |
| N ₄ -Benzoyl-2'-O-methylcytidine, 98% | J64474 | 122 |
| 6-Benzyladenine, 99% | A14678 | 122 |
| 8-Bromoadenosine, 98% | L03544 | 136 |
| 8-Bromo-2'-deoxyadenosine, 99% | J65357 | 136 |
| 5-Bromo-2'-deoxycytidine, 99% | J65456 | 136 |
| 8-Bromo-2'-deoxyguanosine, 99% | J64723 | 136 |
| 2'-Bromo-2'-deoxyuridine, 98% | J64704 | 137 |
| 5-Bromo-2'-deoxyuridine-5'-monophosphate sodium salt, 98% | J64219 | 137 |
| 8-Bromoguanosine | J63940 | 137 |
| 5-Bromouracil, 98+% | A14799 | 138 |
| 5-Bromouridine, 98% | A18507 | 138 |
| 2-Chloro-2'-arabino-fluoro-2'-deoxyadenosine, 99+% | J60927 | 155 |
| 6-Chloropurine, 99% | A11202 | 159 |
| 6-Chloropurine 2'-deoxyriboside, 97% | J64871 | 159 |
| 2-Chloropyrimidine, 98% | A15394 | 159 |
| 8-Chlorotheophylline, 99% | A12408 | 160 |
| 5-Chlorouracil, 98% | A11084 | 160 |
| 6-Chlorouracil, 98+% | L01875 | 160 |
| Citrazinic acid, 97% | A15461 | 164 |
| Creatinine hydrochloride, 99+% | J61755 | 169 |
| Cyclocytidine hydrochloride, 98+% | J63845 | 171 |
| Cytidine, 99% | A10261 | 173 |
| Cytidine-5'-diphosphate disodium salt, 98% | J64234 | 174 |
| Cytidine-5'-monophosphate disodium salt, 99+% | J63376 | 174 |
| Cytidine-5'-triphosphate disodium salt, 98+% | J62238 | 174 |
| Cytosine, 98+% | A14731 | 174 |
| 2'-Deoxyadenosine, 99% | J63886 | 177 |
| 2'-Deoxyadenosine-5'-diphosphate trisodium salt, 98% | J65307 | 177 |
| 2'-Deoxyadenosine-5'-triphosphate disodium salt, 97% | J65542 | 177 |
| 2'-Deoxycytidine | J63062 | 177 |
| 2'-Deoxycytidine-5'-diphosphate trisodium salt, 98% | J65408 | 178 |
| 2'-Deoxyguanosine | J60741 | 178 |
| 2'-Deoxyguanosine-5'-triphosphate trisodium salt, 97% | J65179 | 178 |
| 2'-Deoxyinosine | J61411 | 178 |
| 2'-Deoxyinosine-5'-monophosphate disodium salt, 99% | J64271 | 179 |
| 2'-Deoxyinosine-5'-triphosphate trisodium salt, 98% | J64174 | 179 |
| 2-Deoxy-D-ribose, 99% | A11990 | 180 |
| 2'-Deoxythymidine-5'-diphosphate trisodium salt, 98% | J64938 | 180 |
| 2'-Deoxyuridine, 99% | A16026 | 180 |
| 2,2'-Diamino-2'-deoxyadenosine, 98% | J65748 | 183 |
| 2,3'-Diamino-2',3'-dideoxyadenosine, 99% | J65237 | 183 |
| 2,4-Dichloropyrimidine, 98+% | A15131 | 186 |
| 4,6-Dichloropyrimidine, 98% | L13212 | 186 |
| 2',3'-Dideoxycytidine, 98+% | L10619 | 187 |
| 5,6-Dihydro-5-methyluracil, 98+% | L01996 | 191 |
| 5,6-Dihydrouracil, 99% | L01918 | 191 |
| 4,6-Dihydroxypyrimidine, 98% | A15688 | 193 |
| 5'-O-(4,4'-Dimethoxytrityl)-2'-deoxyinosine, 98% | J65136 | 194 |
| 5'-O-(4,4'-Dimethoxytrityl)-2'-deoxyinosine-3'-CE-phosphoramidite, 98% | J64050 | 194 |
| 5'-O-(4,4'-Dimethoxytrityl)-2'-deoxyuridine, 98% | J65960 | 194 |
| 5'-O-(4,4'-Dimethoxytrityl)-2'-deoxyuridine-3'-CE-phosphoramidite, 98% | J65478 | 195 |
| 5'-O-(4,4'-Dimethoxytrityl)-N ₂ -dimethylformamidinyl-2'-fluoro-2'-deoxyguanosine, 98% | J65936 | 195 |
| 5'-O-(4,4'-Dimethoxytrityl)-N ₂ -dimethylformamidinyl-2'-fluoro-2'-deoxyguanosine-3'-CE-phosphoramidite, 98% | J65536 | 195 |
| 5'-O-(4,4'-Dimethoxytrityl)-N ₂ -dimethylformamidinyl-2'-O-methylguanosine, 98% | J65794 | 195 |
| 5'-O-(4,4'-Dimethoxytrityl)-N ₂ -dimethylformamidinyl-2'-O-methylguanosine-3'-CE-phosphoramidite, 98% | J65699 | 195 |

| Description | Stock # | Page # |
|---|---------|--------|
| 5'-O-(4,4'-Dimethoxytrityl)-2'-fluoro-2'-deoxyinosine, 98% | J65008 | 195 |
| 5'-O-(4,4'-Dimethoxytrityl)-2'-fluoro-2'-deoxyuridine, 98% | J64217 | 195 |
| 5'-O-(4,4'-Dimethoxytrityl)-2'-fluoro-2'-deoxyuridine-3'-CE-phosphoramidite, 98% | J65350 | 195 |
| 5'-O-(4,4'-Dimethoxytrityl)-2'-fluoro-N ₂ -isobutyryl-2'-deoxyguanosine, 98% | J64232 | 195 |
| 5'-O-(4,4'-Dimethoxytrityl)-2'-fluoro-N ₂ -isobutyryl-2'-deoxyguanosine-3'-CE-phosphoramidite, 98% | J65817 | 195 |
| 5'-O-(4,4'-Dimethoxytrityl)-N ₂ -isobutyryl-2'-O-methylguanosine, 98% | J65583 | 195 |
| 5'-O-(4,4'-Dimethoxytrityl)-N ₂ -isobutyryl-2'-O-methylguanosine-3'-CE-phosphoramidite, 98% | J65100 | 195 |
| 5'-O-(4,4'-Dimethoxytrityl)-N ₆ -methyl-2'-deoxyadenosine, 98% | J65498 | 195 |
| 5'-O-(4,4'-Dimethoxytrityl)-2'-O-methylinosine, 98% | J64825 | 195 |
| 5'-O-(4,4'-Dimethoxytrityl)-2'-O-methyluridine, 98% | J64880 | 195 |
| 5'-O-(4,4'-Dimethoxytrityl)-2'-O-methyluridine-3'-CE-phosphoramidite, 98% | J65508 | 195 |
| 1,1-Dimethylbiguanide hydrochloride | J63361 | 196 |
| N ₂ -Dimethylformamidinyl-2'-O-methylguanosine, 98% | J64577 | 197 |
| 1,3-Dimethyluracil, 99% | L19664 | 197 |
| 2-Fluoro-9-β-D-arabinofuranosyladenine, 98% | J65562 | 223 |
| 5-Fluorocytidine, 98% | J60908 | 223 |
| 5-Fluorocytosine, 98+% | L16496 | 223 |
| 2'-Fluoro-2'-deoxyadenosine, 99% | J65441 | 223 |
| 2'-Fluoro-2'-deoxycytidine, 99% | J65632 | 223 |
| 2'-Fluoro-2'-deoxyguanosine, 99% | J64055 | 223 |
| 2'-Fluoro-2'-deoxyinosine, 99% | J65208 | 223 |
| 2'-Fluoro-2'-deoxyuridine, 99% | J65948 | 224 |
| 5-Fluoro-2'-deoxyuridine, 98+% | L16497 | 224 |
| 2'-Fluoro-N ₂ -isobutyryl-2'-deoxyguanosine, 98% | J65608 | 224 |
| 5-Fluorouracil, 99% | A13456 | 224 |
| 5-Fluorouridine, 97% | J62083 | 224 |
| Guanidine thiocyanate, 99% | B21250 | 239 |
| Guanosine, 98+% | A11328 | 240 |
| Guanosine-5'-diphosphate disodium salt | J61646 | 240 |
| Guanosine-5'-triphosphate disodium salt | J61414 | 240 |
| Hydroxyguanidine sulfate | J61354 | 249 |
| Hypoxanthine, 99% | A11481 | 253 |
| Inosine, 98+% | A14459 | 256 |
| Inosine-5'-diphosphate disodium salt, 95% | J65397 | 256 |
| Inosine-5'-monophosphate disodium salt hydrate | J61959 | 256 |
| Inosine-5'-triphosphate trisodium salt, 96% | J65670 | 256 |
| 5-Iodocytidine, 99% | J64698 | 258 |
| 5-Iodo-2'-deoxycytidine, 99% | J61356 | 258 |
| (+)-5-Iodo-2'-deoxyuridine, 98% | A11542 | 258 |
| 5-Iodouridine, 96% | J62259 | 259 |
| N ₂ -Isobutyryl-2'-O-methylguanosine, 98% | J65249 | 260 |
| Isocytosine, 99% | H54228 | 260 |
| 2-Mercaptobenzothiazole, 97% | A14086 | 280 |
| 2-Mercaptoimidazole, 98+% | L01346 | 281 |
| 6-Mercaptopurine monohydrate, 98% | A12197 | 281 |
| Mercaptosuccinic acid, 98% | B23301 | 281 |
| 2'-O-Methyladenosine, 99% | J64922 | 285 |
| 2'-O-Methylcytidine, 99% | J65528 | 287 |
| 5-Methylcytosine, 97% | 43492 | 287 |
| N ₆ -Methyl-2'-deoxyadenosine, 99% | J64961 | 287 |
| 5-Methyl-2'-deoxycytidine, 99% | J65209 | 287 |
| Methylguanidine hydrochloride, 98% | J60033 | 288 |
| 2'-O-Methylguanosine, 99% | J65770 | 288 |
| 2'-O-Methylinosine, 99% | J64748 | 288 |
| 6-(Methylthio)purine, 97% | L01836 | 290 |
| 6-Methyl-2-thiouracil, 98% | A17982 | 290 |
| 6-Methyluracil, 97% | B24191 | 291 |
| 2'-O-Methyluridine, 99% | J64897 | 291 |
| β-Nicotinamide adenine dinucleotide, 98+% | J62337 | 301 |
| β-Nicotinamide adenine dinucleotide phosphate monosodium salt | 44126 | 301 |
| β-Nicotinamide adenine dinucleotide phosphate disodium salt, 97% | J62556 | 301 |
| β-Nicotinamide adenine dinucleotide phosphate reduced tetrasodium salt, 95% | J62089 | 302 |
| β-Nicotinamide adenine dinucleotide reduced disodium salt trihydrate, 98% | J61461 | 302 |
| Purine, 98% | J60999 | 331 |

| Description | Stock # | Page # |
|--|---------|--------|
| 4(3H)-Pyrimidone, 98+% | A10859 | 332 |
| Ribonucleic acid from Baker's yeast | J61215 | 337 |
| Theobromine, 99% | A11861 | 365 |
| Theophylline | J60203 | 366 |
| 6-Thioguanine, 98% | B21280 | 367 |
| Thionicotinamide, 98% | A11144 | 367 |
| 2-Thiouracil, 98% | A18119 | 368 |
| 4-Thiouridine, 98+% | J60679 | 368 |
| Thymidine, 99% | A11493 | 369 |
| Thymidine-5'-monophosphate disodium salt | J60747 | 369 |
| Thymine, 97% | A15879 | 369 |
| L-Thyroxine, 98% | J62606 | 370 |
| 3,3',5'-Triiodo-L-thyronine sodium salt | J63312 | 378 |
| Uracil, 99+% | A15570 | 388 |
| Uridine, 99% | A15227 | 389 |
| Uridine-5'-diphosphate disodium salt, 98% | J64329 | 389 |
| Uridine-5'-diphosphate sodium salt, 98+% | J60141 | 389 |
| Uridine-5'-monophosphate disodium salt, 99% | A18601 | 389 |
| Uridine-5'-triphosphate trisodium salt, 98+% | J63427 | 389 |
| Xanthine, 99% | A11077 | 393 |

Peptides

Peptides are chains of less than 100 amino acids. They are key regulators of many biological functions including hormone release and various neurological processes. We offer a variety of peptides for biological research, including several opioid and neuropeptides.

| Description | Stock # | Page # |
|--|---------|--------|
| Acetyl-Adrenocorticotrophic Hormone (1-14) | J64039 | 71 |
| Acetyl α -Endorphin | J64680 | 72 |
| Acetyl-[Lys0,Nle3]- γ 2-Melanocyte Stimulating Hormone, amide | J65515 | 73 |
| Adjuvant Peptide | J62385 | 80 |
| Adrenocorticotrophic Hormone (1-4) | J61985 | 80 |
| Adrenocorticotrophic Hormone (1-10) | J63084 | 80 |
| Adrenocorticotrophic Hormone (1-13) | J61247 | 80 |
| Adrenocorticotrophic Hormone (1-14) | J60060 | 80 |
| Adrenocorticotrophic Hormone (1-39), guinea pig | J65775 | 80 |
| Adrenocorticotrophic Hormone (12-39), rat | J64495 | 80 |
| Adrenocorticotrophic Hormone (34-39) | J64410 | 80 |
| Tyr-Adrenocorticotrophic Hormone (4-9) | J65314 | 80 |
| Tyr-Adrenocorticotrophic Hormone (4-10) | J64183 | 80 |
| Amastatin hydrochloride, 98+% | J62932 | 90 |
| Angiotensin, (rat or canine) | J61129 | 104 |
| Angiotensin I (human) | J62102 | 104 |
| Angiotensin II (human) | J60866 | 104 |
| Angiotensin III (human) | J61756 | 104 |
| Angiotensin Converting Enzyme Inhibitor | J63143 | 104 |
| Angiotensin Converting Enzyme Substrate | J61332 | 104 |
| Anorexigenic Peptide | J63107 | 104 |
| Apamin | J60961 | 107 |
| Aspartame, 98% | J61523 | 111 |
| Autocamtide 2 | J65067 | 112 |
| Bombesin | J63514 | 133 |
| Borate, 0.5M buffer soln., pH 8.0 | J63742 | 133 |
| Bradykinin | J63131 | 134 |
| Bradykinin (1-3) | J61719 | 134 |
| Bradykinin (1-5) | J63233 | 134 |
| Bradykinin acetate salt | J60345 | 134 |
| Lys-Bradykinin acetate salt | J61171 | 135 |
| Met-Lys-Bradykinin | J61532 | 135 |
| Brain Derived Acidic Fibroblast Growth Factor (102-111) | J65458 | 135 |
| Buccalin | J60655 | 139 |
| Busulfan, 98% | J61348 | 140 |
| Calcineurin Autoinhibitory Fragment | J64047 | 142 |
| Calcitonin, chicken | J61049 | 142 |
| Calcitonin, eel | J63006 | 142 |
| Calcitonin, human, 97+% | J63192 | 142 |
| Calcitonin, porcine | J64341 | 142 |
| Calcitonin, rat | J61231 | 142 |
| Calcitonin, salmon | J63531 | 142 |
| Calcitonin (8-32), salmon | J64415 | 143 |
| Calcitonin Gene Related Peptide, human | J65667 | 143 |
| Calcitonin Gene Related Peptide (8-37), human | J65912 | 143 |
| Calcitonin Gene Related Peptide II, human | J64037 | 143 |
| [Tyr0] Calcitonin Gene Related Peptide II, human | J65250 | 143 |
| Calcium-Like Peptide | J60926 | 143 |
| Calpain Inhibitor I, 95+% | J61766 | 144 |
| Calpain Inhibitor II, 95+% | J62491 | 144 |
| Calpain Inhibitor III, 95+% | J62919 | 144 |
| MG 132 | J63250 | 291 |
| Calpain Substrate I | J63222 | 144 |
| Calphostin C, 99+% | J60647 | 144 |
| β -Casomorphin, bovine | J62791 | 149 |
| β -Casomorphin, human, 95+% | J62271 | 149 |
| Cathepsin G Substrate, 98+% | J63798 | 150 |
| DAGO | J60431 | 174 |

| Description | Stock # | Page # |
|--|---------|--------|
| Delicious Peptide, bovine | J63678 | 176 |
| Delta Sleep-Inducing Peptide | J63334 | 176 |
| Deltorphin I | J60952 | 176 |
| Deltorphin II | J62286 | 176 |
| Dermorphin | J62019 | 180 |
| Diprotin A | J60369 | 199 |
| Diprotin B | J63321 | 199 |
| Dynorphin A (1-6), porcine | J62646 | 202 |
| Dynorphin A (1-7), porcine | J63897 | 203 |
| Dynorphin A (1-8), porcine | J64636 | 203 |
| Dynorphin A (1-9), porcine | J64418 | 203 |
| Dynorphin A (1-13), porcine | J64015 | 203 |
| Dynorphin A (1-13) amide, porcine | J64409 | 203 |
| Dynorphin A (1-17), porcine | J65394 | 203 |
| Dynorphin A (2-17), porcine | J64002 | 203 |
| Dynorphin A (2-17) amide, porcine | J65159 | 203 |
| Dynorphin A (3-17), porcine | J65126 | 203 |
| Dynorphin A (6-17), porcine | J65986 | 203 |
| Dynorphin A (13-17), porcine | J64991 | 203 |
| [Phe7] Dynorphin A (1-7), porcine | J65474 | 203 |
| Dynorphin A amide, porcine | J65622 | 203 |
| Dynorphin B, porcine | J64089 | 203 |
| Dynorphin B (1-9), porcine | J64774 | 203 |
| Dynorphin B 29, porcine | J64335 | 203 |
| Elastase Substrate V | J60093 | 205 |
| Eledoisin | J60596 | 205 |
| Eledoisin Related Peptide | J62110 | 205 |
| α -Endorphin, human | J63462 | 206 |
| α -Endorphin, human | J62140 | 206 |
| β -Endorphin, camel | J61230 | 206 |
| β -Endorphin, human | J62374 | 206 |
| β -Endorphin, rat | J62875 | 206 |
| [Des-Tyr1]- β -Endorphin, human | J64685 | 206 |
| Endotoxin Inhibitor | J63502 | 206 |
| Endotoxin Substrate | J62862 | 206 |
| (Ala ²)-Leu-Enkephalin | J63207 | 207 |
| (D-Ala ³)-Leu-Enkephalin | J61859 | 207 |
| (Des-Tyr ¹)-Leu-Enkephalin | J60677 | 207 |
| Leu-Enkephalin | J61408 | 207 |
| (Des-Tyr ¹)-Met-Enkephalin | J61684 | 207 |
| Met-Enkephalin | J61154 | 207 |
| Eosinophilotactic Tetrapeptide (AGSE) | J62018 | 208 |
| Eosinophilotactic Tetrapeptide (VGDE) | J61884 | 208 |
| Eosinophilotactic Tetrapeptide (VGSE) | J61494 | 208 |
| Epidermal Growth Factor Receptor Peptide (985-996) | J64705 | 209 |
| Experimental Allergic Encephalitogenic Peptide, human | J61478 | 218 |
| Extracellular Death Factor trifluoroacetate salt | J61052 | 218 |
| Fibrinogen-Binding Inhibitor Peptide | J60863 | 220 |
| Fibrinogen-Binding Peptide | J61540 | 220 |
| Fibrinolysis Inhibiting Factor | J60967 | 220 |
| Fibroblast Growth Factor Basic Fragment (1-24), bovine | J65662 | 220 |
| GAP 26 | J64547 | 230 |
| GAP 27 | J64109 | 230 |
| Ghrelin, human | J64943 | 232 |
| Ghrelin, rat | J64669 | 232 |
| Ghrelin, Ser(palmitoyl), rat | J64299 | 232 |
| (Des-octanoyl)-Ghrelin, human | J65946 | 232 |
| Ginseng Tetrapeptide | J63101 | 232 |
| Glucagon (1-29), human | J60827 | 233 |
| Glucagon (19-29), human | J63443 | 233 |
| [Ser8] Glucagon Like Peptide-1 (7-36) amide, human | J64460 | 233 |
| Glucagon Like Peptide-2 (1-33), human | J65432 | 233 |
| Glycylglycylglycine, 99% | A13778 | 237 |
| GMAP (16-41) amide | J64666 | 238 |
| GMAP (25-41) amide | J64644 | 238 |

| Description | Stock # | Page # |
|---|---------|--------|
| Growth Hormone Pro-Releasing Factor, human | J65580 | 238 |
| Growth Hormone Releasing Factor (GRF) (1-29) amide, human | J61111 | 238 |
| Growth Hormone Releasing Factor (GRF) (1-40), human | J61784 | 238 |
| Growth Hormone Releasing Factor (GRF) (1-44), human | J62895 | 238 |
| Guanylin, human | J64285 | 240 |
| Guanylin, rat, mouse | J65417 | 240 |
| Hamburger Pentapeptide | J60543 | 241 |
| Helodermin | J65734 | 241 |
| Helospectin II | J65020 | 241 |
| Hemokinin 1, human | J65288 | 242 |
| Heparin Binding Peptide | J60443 | 242 |
| Histatin 5 | J64792 | 245 |
| Hypercalcemia Malignancy Factor (1-34) amide, human | J65234 | 252 |
| Hypercalcemia Malignancy Factor (7-34), amide, human | J64361 | 252 |
| Hypercalcemia Malignancy Factor (1-34), human | J65499 | 252 |
| Inactivation Gate Peptide | J60062 | 255 |
| Indolicidin | J65215 | 256 |
| Insulin B (22-25) | J61170 | 257 |
| β -Interleukin-I (163-171), human | J65928 | 257 |
| β -Interleukin II (44-56) | J65203 | 257 |
| Kassinin, 96% | J60353 | 263 |
| Katacalcin | J65495 | 263 |
| Kemptide | J60591 | 263 |
| Kentsin | J61809 | 263 |
| Kinetensin | J63865 | 264 |
| Kisspeptin-10 | J65487 | 264 |
| Kisspeptin-13 | J64054 | 264 |
| Kyotorphin | J63771 | 264 |
| Laminin (925-933) | J64340 | 266 |
| Laminin (929-933) | J64127 | 266 |
| Laminin A Chain (2091-2108) | J65640 | 266 |
| Laminin Pentapeptide amide | J64356 | 266 |
| Leupeptin hemisulfate | J61188 | 269 |
| Leuprolide | J62147 | 269 |
| Leuprolide, human, synthetic | J62967 | 269 |
| Levitide, 96% | J62880 | 269 |
| LH-RH (4-10) | J64141 | 269 |
| LH-RH free acid | J64883 | 269 |
| LH-RH, human | J65645 | 269 |
| LH-RH, salmon | J64173 | 269 |
| [Gln ₆] LH-RH, chicken | J65648 | 269 |
| [Hyp ₉] LH-RH | J65994 | 269 |
| [D-Trp ₆] LH-RH amide | J65530 | 269 |
| [D-Trp ₆] LH-RH ethylamide | J64762 | 269 |
| Litorin | J60177 | 272 |
| Liver Cell Growth Factor | J60485 | 272 |
| Liver Cell Growth Factor acetate salt | J64233 | 272 |
| Lys-Bradykinin | J62067 | 273 |
| Macrophage Inhibitory Peptide | J63844 | 274 |
| Magainin I | J60301 | 274 |
| Magainin II | J61172 | 274 |
| Malantide | J62283 | 275 |
| Mast Cell Degranulating Peptide | J63412 | 278 |
| Mast Cell Degranulating Peptide HR-1 | J63655 | 278 |
| Mast Cell Degranulating Peptide HR-2 | J60447 | 278 |
| Mastoparan | J61662 | 278 |
| Mastoparan X | J61173 | 278 |
| [Met 210] Melanocyte Protein PMEL 17 (209-217), human, mouse | J64424 | 279 |
| α -Melanocyte Stimulating Hormone amide | J64310 | 279 |
| α -Melanocyte Stimulating Hormone free acid | J64142 | 279 |
| β -Melanocyte Stimulating Hormone, human | J65192 | 279 |
| [D-Trp ₈] γ -Melanocyte Stimulating Hormone | J65088 | 279 |
| Melanocyte-Stimulating Hormone-Release Inhibiting Factor, synthetic | J60045 | 279 |
| Melanotan II | J65115 | 279 |
| Molluscan Cardioexcitatory Neuropeptide | J62389 | 294 |

| Description | Stock # | Page # |
|---|---------|--------|
| α -Neo-Endorphin (1-7) | J65680 | 299 |
| [Met5, Lys6] α -Neo-Endorphin (1-6) | J65819 | 299 |
| [Met5, Lys6,7] α -Neo-Endorphin (1-7) | J64851 | 299 |
| Neuromedin N | J63747 | 300 |
| Neurotensin | J63359 | 300 |
| Neurotensin (1-6) | J62461 | 300 |
| Neurotensin (1-8) | J62253 | 300 |
| Neurotensin (1-11) | J63799 | 300 |
| Neurotensin (8-13) | J61112 | 300 |
| Opiorphin | J62709 | 308 |
| Orexin A, human | J65378 | 308 |
| Orexin B, canine | J65811 | 308 |
| Orexin B, human | J65110 | 308 |
| Orexin B, mouse, rat | J65275 | 308 |
| [Ala ¹¹ , D-Leu ⁵] Orexin B, human | J64476 | 308 |
| Osteocalcin (1-49), human | J65012 | 309 |
| Osteocalcin (7-19), human | J65386 | 309 |
| Osteocalcin (45-49), human | J65959 | 309 |
| Oxytocin, 96% | J63421 | 311 |
| L-Phenylalanyl-L-phenylalanine | J60043 | 316 |
| L-Phenylalanyl-L-proline | J60063 | 316 |
| Physalaemin | J62647 | 321 |
| Proctolin | J60532 | 328 |
| Protein Kinase C Substrate | J61622 | 331 |
| Protein Kinase Inhibitor | J61687 | 331 |
| Ranatensin, 96% | J61334 | 335 |
| Rigin, 96% | J63099 | 338 |
| Substance P | J63489 | 353 |
| Substance P free acid | J61828 | 353 |
| Substance P (1-4) | J62756 | 353 |
| Substance P (1-7), 96% | J60018 | 353 |
| Substance P (4-11) | J61891 | 353 |
| Substance P (6-11) | J63228 | 353 |
| Syntide 2, 96% | J62843 | 357 |
| Thymopentin, 99+% | J61431 | 369 |
| Thyrotropin-Releasing Hormone | J62120 | 370 |
| Tocinoic acid, 96% | J62846 | 370 |
| Tuftsins, 96% | J63904 | 385 |
| Uroguanylin, human | J65601 | 389 |
| Vapreotide | J61096 | 391 |
| Vasoactive Intestinal Peptide, human, porcine, rat | J63980 | 391 |
| Vasopressin, 98+% | J61248 | 391 |
| Xenopsin | J61481 | 394 |

Signal Transduction Reagents

Signal transduction involves the binding of extracellular signaling molecules and ligands to cell-surface receptors. This binding event leads to changes in the cell's biochemistry, cytoskeletal structure or gene transcription. This list includes some common ligands involved in cell signaling pathways.

| Description | Stock # | Page # |
|--|---------|--------|
| Acebutolol hydrochloride | J63790 | 69 |
| L-Adrenaline, 98+% | L04911 | 80 |
| Alaproclate hydrochloride, 96% | J62741 | 82 |
| 9-Aminoacridine hydrochloride hydrate, 99% | B24356 | 91 |
| Bexarotene, 99+% | J63701 | 124 |
| Bromhexine hydrochloride, 98+% | J63451 | 135 |
| Colcemid, 98+% | J63900 | 167 |
| Colchicine, 98+% | J61072 | 167 |
| Cytochalasin A | J60280 | 174 |
| Dicyclomine hydrochloride | J61422 | 187 |
| 3,4-Dihydroxyphenylacetic acid, 98+% | A15893 | 193 |
| 3,4-Dihydroxy-DL-phenylalanine, 98% | 41535 | 193 |
| 3,4-Dihydroxy-L-phenylalanine, 98+% | A11311 | 193 |
| (-)-Epigallocatechin gallate | J61745 | 209 |
| Forskolin, 98+% | J63292 | 228 |
| 1-n-Hexyltheobromine, 98+% | L13597 | 245 |
| 5-Hydroxyindole-3-acetic acid, 98% | J61435 | 249 |
| 6-Hydroxynicotinic acid, 98% | A15802 | 250 |
| 4-Hydroxy-TEMPO, free radical, 98+% | A12497 | 252 |
| 2-Mercaptoethane sulfonic acid sodium salt, 96% | J63989 | 281 |
| 2-Mercaptoethylamine hydrochloride, 98+% | A14377 | 281 |
| 2-Mercapto-1-methylimidazole, 98% | A13094 | 281 |
| N ω -Methyl-L-arginine acetate, 99+% | J60890 | 286 |
| N-Methyldeoxynojirimycin | J60509 | 287 |
| 1-(1-Naphthyl)piperazine hydrochloride | J62097 | 298 |
| Nefazodone hydrochloride, 98+% | J62793 | 299 |
| L-Noradrenaline, 98% | L08087 | 304 |
| (\pm)-Octopamine hydrochloride, 99% | J61281 | 306 |
| 1H-[1,2,4]Oxadiazolo[4,3-a]-quinoxalin-1-one, 99+% | J62250 | 310 |
| D-(-)-Penicillamine, 99% | A11446 | 313 |
| Phenylbutazone, 98% | L03449 | 316 |
| 1-Pyrrolidinecarbodithioic acid ammonium salt, 98% | B23731 | 333 |
| Rapamycin, 99+% | J62473 | 335 |
| Serotonin hydrochloride, 99% | B21263 | 342 |
| (-)-Shikimic acid, 98% | L04848 | 342 |
| Sulindac | J61772 | 356 |
| Tacrine hydrochloride hydrate, 98+% | J60070 | 357 |
| Tamm Horsfall Glycoprotein, human, 99% | J64893 | 357 |
| Thalidomide | J60271 | 365 |
| (\pm)-Thalidomide, 99+% | J62266 | 365 |
| DL-Thioctic acid, 98% | L04711 | 366 |
| Tolmetin sodium salt dihydrate, 98+% | J62663 | 371 |
| Triamcinolone acetonide, 98+% | J63548 | 374 |
| Trimethoprim | J63053 | 378 |
| Valethamate bromide, 99% | J62622 | 390 |
| Vincamine, 98% | J60545 | 392 |

Signal Transduction Reagents - Agonists

Agonists bind to receptors and elicit a biological response. This list includes both natural ligands for receptors as well as synthetic agonists.

| Description | Stock # | Page # |
|---|---------|--------|
| O-Acetyl-L-carnitine hydrochloride | J61536 | 71 |
| S-Acetylthiocholine iodide, 98% | A16802 | 75 |
| (±)-Anabasine, tech. 85% | L12089 | 103 |
| Arvanil, 98% | J62812 | 110 |
| (±)-Baclofen, 99+% | J62768 | 116 |
| Bisacodyl, 98+% | J61997 | 126 |
| Bryostatin 1 | J63848 | 139 |
| Bryostatin 2 | J61551 | 139 |
| Buspirone hydrochloride | J60476 | 140 |
| Calcium-Like Peptide | J60926 | 143 |
| Capsaicin | J62865 | 146 |
| Carbachol, 99% | L06674 | 146 |
| Carbamazepine, 98% | J62590 | 146 |
| CGS 12066B dimaleate, 98+% | J63801 | 152 |
| CGS 21680 hydrochloride, 99+% | J60793 | 152 |
| 2-Chloroadenosine | J63810 | 155 |
| 1-(3-Chlorophenyl)biguanide hydrochloride, 97% | B20355 | 158 |
| 1-(4-Chlorophenyl)piperazine, 97% | J60278 | 158 |
| 1-(3-Chlorophenyl)piperazine monohydrochloride, 97% | A14057 | 158 |
| Cimaterol | J60650 | 163 |
| Clonidine hydrochloride, 98+% | J63707 | 166 |
| Cloprostenol sodium salt | J60577 | 166 |
| Deltorphan I | J60952 | 176 |
| Deltorphan II | J62286 | 176 |
| Dermorphin | J62019 | 180 |
| 1,10-Diaminodecane, 98% | J63821 | 183 |
| 2,6-Diisopropylphenol, 97% | L06841 | 193 |
| Dimaprit dihydrochloride | J61079 | 194 |
| Dobutamine hydrochloride | J61333 | 201 |
| Domoic acid | J61608 | 201 |
| Dynorphin A (1-7), porcine | J63897 | 203 |
| 5'-N-Ethylcarboxamidoadenosine | J60405 | 215 |
| Evodiamine | J62771 | 218 |
| (±)-7-Hydroxy-2-di-n-propylaminotetralin hydrobromide | J61065 | 248 |
| Ibotenic acid hydrate, 98+% | J60748 | 253 |
| Imetit dihydrobromide, 98% | J62346 | 254 |
| Ingenol 3-angelate, 99% | J60601 | 256 |
| 2-Iodomelatonin, 98+% | J61498 | 258 |
| Isoguvacine hydrochloride, 99% | J63243 | 260 |
| Isonipecotic acid, 98% | A11795 | 261 |
| DL-Isoproterenol hydrochloride, 99% | J61788 | 261 |
| Isosorbide mononitrate, 98+% | J63674 | 261 |
| Lofexidine hydrochloride, 98+% | J63960 | 272 |
| DL-Menthol, 98+% | A18098 | 280 |
| D-Menthol, 99% | L06102 | 280 |
| L-Menthol, 99% | A10474 | 280 |
| N-Methyl dopamine hydrochloride, 98+% | J60306 | 287 |
| Mezerein, Daphne mezereum | J62440 | 291 |
| Morphiceptin acetate | J61987 | 296 |
| Muscimol, 99+% | J61720 | 296 |
| 2-(1-Naphthylmethyl)-2-imidazoline nitrate, 99% | L12617 | 298 |
| Nicergoline | J63295 | 301 |
| (S)-(-)-Nicotine, 99% | A12398 | 302 |
| DL-Nornicotine, 98% | L10809 | 305 |
| Phorbol 12-myristate 13-acetate, 99+% | J63916 | 319 |
| Pyridine-2,3-dicarboxylic acid, 99% | A11414 | 332 |
| Pyrilamine maleate | J63247 | 332 |
| Quipazine dimaleate, 99+% | J61933 | 334 |
| (+)-Quisqualic acid, 99+% | J61591 | 334 |

| Description | Stock # | Page # |
|-----------------------------------|---------|--------|
| Salbutamol, 99% | J63741 | 339 |
| Spermidine trihydrochloride, 99+% | J61595 | 351 |
| Spermine, 97% | L19562 | 351 |
| Spermine tetrahydrochloride, 99% | J63060 | 351 |
| Tulobuterol | J63975 | 385 |
| Xylazine | J61430 | 394 |
| Zolmitriptan | J60616 | 397 |

Signal Transduction Reagents - Antagonists

Antagonists are receptor ligands that block or dampen agonist responses upon binding. Antagonists do not provoke any biological effects on their own but prevent actions from agonists.

| Description | Stock # | Page # |
|---|---------|--------|
| 3-Acetylpyridine, 98% | A14246 | 74 |
| 1-Aminocyclobutanecarboxylic acid hydrochloride | J63873 | 92 |
| Arcaïne sulfate salt | J63277 | 109 |
| Astemizole, 99+% | J60339 | 111 |
| (R,S)-Atenolol | J61199 | 111 |
| Benzotropine mesylate | J61954 | 120 |
| 2-Benzyl-2-imidazoline hydrochloride, 99% | B21764 | 122 |
| Candesartan, 98% | J62818 | 145 |
| Canrenic acid potassium salt, 98+% | J61394 | 145 |
| Canrenone, 98% | J60238 | 145 |
| Capsazepine, 99+% | J63055 | 146 |
| Cetirizine dihydrochloride, 99+% | J63549 | 152 |
| CGS 15943, 99+% | J61313 | 152 |
| 5-Chloroindole-2-carboxylic acid, 98% | A18626 | 157 |
| 7-Chlorokynurenic acid, 99+% | J61359 | 157 |
| Chloropyramine hydrochloride | J60350 | 159 |
| Cimetidine, 98+% | J62825 | 163 |
| Cinanserin hydrochloride, 99+% | J63370 | 163 |
| Clobenpropit dihydrobromide, 99+% | J60807 | 165 |
| Clozapine, 98+% | J61583 | 166 |
| Conessine, 97% | J62617 | 167 |
| 6-Cyano-7-nitroquinoxaline-2,3-dione, 99+% | J63472 | 170 |
| 8-Cyclopentyl-1,3-dimethylxanthine | J61565 | 172 |
| Dextromethorphan hydrobromide | J61732 | 181 |
| Dibucaine hydrochloride | J62804 | 184 |
| 5,7-Dichlorokynurenic acid | J61138 | 186 |
| Dihydroergocristine methanesulfonate | J60638 | 190 |
| Dihydroergotamine methanesulfonate | J63840 | 190 |
| Dimenhydrinate | J63718 | 194 |
| 6,7-Dinitroquinoxaline-2,3-dione | J60911 | 198 |
| Diphenhydramine hydrochloride, 99% | A10136 | 198 |
| 4-Diphenylacetoxymethylpiperidine methiodide | J62298 | 198 |
| 1,3-Dipropyl-8-phenylxanthine | J63554 | 199 |
| Doxepin hydrochloride | J62579 | 201 |
| Dyphylline | J63167 | 203 |
| Ebastine | J63088 | 204 |
| Famotidine, 98+% | J63165 | 218 |
| Fexofenadine hydrochloride | J63262 | 220 |
| Flumazenil, 98% | J62537 | 222 |
| Fluphenazine, 98+% | J61179 | 225 |
| Ginkgolide A | J62384 | 232 |
| Ginkgolide B | J60646 | 232 |
| Hexamethonium bromide, 98+% | J60466 | 244 |
| 4-Hydroxyquinoline-2-carboxylic acid hydrate, 98% | A12602 | 251 |
| 2-Hydroxysaclofen | J63588 | 251 |
| Ifenprodil hemitartrate, 99% | J60932 | 253 |
| Imidazole-4-acetic acid monohydrochloride, 97% | B22473 | 254 |
| Ipratropium bromide, 99% | J60453 | 259 |
| Ketanserin tartrate, 98+% | J62798 | 263 |
| Ketotifen fumarate, 99% | J63708 | 263 |
| Loratadine, 98+% | J60190 | 272 |
| Lorglumide sodium salt, 98+% | J61713 | 272 |
| Luzindole, 97% | J61915 | 273 |
| Mecamylamine hydrochloride | J60257 | 278 |
| Memantine hydrochloride | J63830 | 280 |
| Methotrexate | J63075 | 284 |
| Metoclopramide hydrochloride monohydrate | J61545 | 291 |
| Metoprolol tartrate, 98+% | J61920 | 291 |
| Mianserin hydrochloride | J61570 | 291 |

| Description | Stock # | Page # |
|--|---------|--------|
| Naftopidil, 98+% | J60311 | 297 |
| Nalidixic acid sodium salt | J63550 | 297 |
| Naloxone hydrochloride, 98% | J60013 | 297 |
| Naltrexone hydrochloride | J60590 | 297 |
| α -Naphthoflavone, 97% | A18542 | 297 |
| β -Naphthoflavone, 98+% | A18543 | 297 |
| Phenoxybenzamine hydrochloride | J61900 | 315 |
| 4 α -Phorbol 12-myristate 13-acetate, 99% | J61099 | 319 |
| Pirenzepine dihydrochloride, 99% | J62252 | 323 |
| Prazosin hydrochloride | J61712 | 328 |
| Ranitidine hydrochloride, 99% | B22260 | 335 |
| Rauwolscine hydrochloride, 99% | J63198 | 335 |
| Saclofen, 99+% | J63345 | 339 |
| Sotalol hydrochloride, 98% | J63772 | 350 |
| Tamsulosin hydrochloride, 98+% | J61999 | 357 |
| Telmisartan, 99% | J61441 | 360 |
| Terazosin hydrochloride, 99+% | J62055 | 360 |
| Terfenadine | J61936 | 360 |
| 6,7,8,9-Tetrahydro-5H-benzocycloheptene-5-ol-4-ylidene acetic acid | J63941 | 362 |
| Thioridazine hydrochloride | J60895 | 367 |
| 3-Tropanyl-3,5-dichlorobenzoate, 99+% | J62583 | 383 |
| 3-Tropanylindole-3-carboxylate hydrochloride | J62807 | 383 |
| Tropicamide, 99+% | J61132 | 383 |
| D-Tubocurarine chloride | J60222 | 385 |
| Urapidil hydrochloride, 98+% | J63219 | 388 |
| Yohimbine hydrochloride, 98+% | J60185 | 395 |

Signal Transduction Reagents - Ca, Na, K Channel Blockers

Calcium, sodium and potassium channels are pore-forming proteins that regulate the flow of ions across cell membranes. They play key roles in many biological processes, but are especially important in neurotransmission. They are also involved in biological activities that involve rapid changes in cells, such as muscle contraction and T-cell activation. Items in this list block or inhibit action by these channel proteins.

| Description | Stock # | Page # |
|---|---------|--------|
| Aconitine, 98% | J62056 | 76 |
| 1-Adamantanamine hydrochloride, 99% | A12699 | 78 |
| Alamethicin | J63829 | 82 |
| Ambroxol hydrochloride, 99% | J63712 | 91 |
| Amiloride hydrochloride dihydrate | J62168 | 91 |
| N-(6-Aminoethyl)-5-chloro-1-naphthalenesulfonamide hydrochloride | J63012 | 95 |
| 4-Aminopyridine, 99+% | J61470 | 99 |
| Amlodipine, 97+% | J62242 | 100 |
| Aniracetam | J61661 | 104 |
| Anthracene-9-carboxylic acid, 98+% | A14049 | 105 |
| Antibiotic A23187, 99+% | J63020 | 105 |
| Apamin | J60961 | 107 |
| BAPTA, 97% | A13190 | 117 |
| (±)-Bay K 8644 | J61480 | 118 |
| Bifonazole, 99% | J63253 | 125 |
| Bumetanide, 98+% | J62302 | 139 |
| Bupivacaine | J62742 | 139 |
| Calmidazolium chloride | J63270 | 143 |
| Calmodulin, bovine testes | J60231 | 144 |
| Clofilium tosylate, 97+% | J63552 | 165 |
| Clotrimazole | J63895 | 166 |
| Cyclopiazonic acid, 99+% | J61594 | 172 |
| Dantrolene sodium salt | J60887 | 175 |
| 2,5-Di-tert-butylhydroquinone, 98+% | A14606 | 185 |
| 2-Diethylaminoethyl 4-aminobenzoate hydrochloride, 99% | A17485 | 188 |
| 8-(Diethylamino)octyl 3,4,5-trimethoxybenzoate hydrochloride, 97% | J62528 | 188 |
| (+)-cis-Diltiazem hydrochloride | J63245 | 194 |
| Dizocilpine maleate, 99+% | J63917 | 200 |
| Ebselen | J63190 | 204 |
| Ethacrynic acid | J63684 | 213 |
| Felodipine | J61195 | 219 |
| Fendiline hydrochloride | J63254 | 219 |
| Flecainide acetate, 98% | J63527 | 221 |
| Flunarizine dihydrochloride, 99+% | J62969 | 222 |
| Furosemide, 97+% | J61457 | 229 |
| Glimepiride | J62032 | 232 |
| Glipizide | J63398 | 232 |
| Glybenzcyclamide, 99% | B21459 | 235 |
| HDBA, 98+% | J60507 | 241 |
| 5-Hydroxydecanoic acid sodium salt, 98% | J61434 | 248 |
| Ibutilide hemifumarate salt, 99% | H56358 | 253 |
| Indapamide | J63846 | 255 |
| Ionomycin, 98% | J62448 | 259 |
| Isradipine, 98+% | J63920 | 261 |
| KN-62 | J62444 | 264 |
| Lansoprazole, 98+% | J62008 | 266 |
| Lidocaine hydrochloride monohydrate, 98% | J63035 | 269 |
| Lidocaine N-ethyl bromide, 99+% | J60678 | 270 |
| Loperamide hydrochloride, 98+% | J60168 | 272 |
| Manidipine | J63305 | 277 |
| 5-(N-Methyl-N-isobutyl)amiloride, 98+% | J63667 | 288 |
| Minoxidil | J61803 | 292 |
| Monensin sodium salt, 90-95.5% | J61669 | 294 |
| Nicardipine hydrochloride, 98+% | J61269 | 301 |
| Nicorandil, 98+% | J60879 | 301 |
| Nifedipine, 98% | J62811 | 302 |

| Description | Stock # | Page # |
|---------------------------------------|---------|--------|
| Niflumic acid, 99+% | J60489 | 302 |
| Nigericin sodium salt, 98+% | J61349 | 302 |
| Nimodipine, 98+% | J61287 | 303 |
| Nitrendipine | J60841 | 303 |
| Ouabain octahydrate, 98% | J60724 | 310 |
| Paxilline, 97+% | J61341 | 312 |
| PCO-400 | J60502 | 312 |
| Phenothiazine, 98+% | A12517 | 315 |
| (+)-Quinidine | A12559 | 333 |
| Quinidine sulfate dihydrate, 98+% | J60426 | 334 |
| Quinine hemisulfate monohydrate, 99% | A17036 | 334 |
| SKF-96365 hydrochloride, 99+% | J60937 | 342 |
| Sodium butyrate, 98+% | A11079 | 344 |
| Sodium oxalate, 99% | A11648 | 347 |
| Spironolactone | J60119 | 351 |
| L-Tetrahydropalmatine | J63911 | 363 |
| Tetrahydropalmatine, 98% | J63328 | 363 |
| Thapsigargin, 95% | J62866 | 365 |
| Tolbutamide, 98% | B21698 | 371 |
| Tolfenamic acid, 99+% | J61256 | 371 |
| TRAM 34 | J60019 | 372 |
| 2,4,7-Triamino-6-phenylpteridine, 98% | B20044 | 374 |
| 1,2,4-Triazole, 99% | A11597 | 374 |
| (±)-Verapamil hydrochloride, 99+% | J61535 | 391 |
| Veratridine, 97+% | J62324 | 391 |
| Vinpocetine, 98% | J61000 | 392 |

Signal Transduction Reagents - Inhibitors

Inhibitors bind to enzymes and decrease their activity. Many drugs are enzyme inhibitors as they can cause a range of biological actions including correcting metabolic imbalances or inducing cell death.

| Description | Stock # | Page # |
|--|---------|--------|
| A-3 hydrochloride | J62760 | 69 |
| A-7 hydrochloride | J62011 | 69 |
| Acarbose, 95% | J61737 | 69 |
| Aceclofenac, 99% | J60355 | 69 |
| Acemetacin | J63583 | 69 |
| Acetohydroxamic acid, 98% | L01569 | 70 |
| N-Acetyl-D-sphingosine, 98% | J60534 | 74 |
| Acivicin, 98+% | J63105 | 76 |
| Actin, from rabbit muscle | J61490 | 77 |
| AG-879, 99% | J62625 | 81 |
| 3-Aminobenzamide, 98% | A10793 | 91 |
| 1-Aminobenzotriazole, 98% | J63610 | 92 |
| DL-Aminoglutethimide, 99% | J62182 | 94 |
| trans-4-(Aminomethyl)cyclohexanecarboxylic acid, 97% | B21742 | 97 |
| Aminophylline, anhydrous, 98% | J60705 | 98 |
| Amrinone, 98% | J62655 | 103 |
| Anisomycin, 97+% | J62964 | 104 |
| Antazoline hydrochloride, 98% | J62511 | 104 |
| Aphidicolin | J60236 | 107 |
| Azathioprine | J62314 | 114 |
| Benazepril hydrochloride, 98% | J61093 | 118 |
| Benzydamine hydrochloride | J61180 | 122 |
| Bisindolylmaleimide 1 | J63401 | 127 |
| Bortezomib, 99% | J60378 | 134 |
| Bromo-7-nitroindazole, 98+% | J63480 | 137 |
| Brompheniramine | J63922 | 138 |
| Buccalin | J60655 | 139 |
| Bupropion hydrochloride, 99% | J61105 | 140 |
| Busulfan, 98% | J61348 | 140 |
| Calpain Inhibitor I, 95+% | J61766 | 144 |
| Calpain Inhibitor II, 95+% | J62491 | 144 |
| Calphostin C, 99+% | J60647 | 144 |
| Camptothecin | J62523 | 145 |
| Canertinib, 99+% | J63403 | 145 |
| Cantharidin, 98% | J61801 | 145 |
| Captopril | J63593 | 146 |
| Carboxy-PTIO potassium salt, 98+% | J61316 | 148 |
| Castanospermine, 99% | J61071 | 150 |
| Chelerythrine chloride, 99+% | J62906 | 153 |
| Chicago Sky Blue 6B | A14242 | 153 |
| Chlorogenic acid | J60457 | 157 |
| Chlorpheniramine maleate, 99% | B25238 | 160 |
| Chromomycin A3, 98% | J62927 | 161 |
| Chymostatin | J63275 | 162 |
| Cilostazol, 98% | J62301 | 163 |
| Clomipramine hydrochloride | J62485 | 165 |
| (±)-Clopidogrel hydrogen sulfate, 98+% | H56409 | 166 |
| Curcumin, 95% (total curcuminoid content), from Turmeric rhizome | B21573 | 170 |
| Cyclophamine, 99+% | J61528 | 172 |
| Dasatinib | J60621 | 175 |
| (+)-1-Deoxymannojirimycin hydrochloride | J61277 | 179 |
| (+)-1-Deoxyojirimycin | J62602 | 179 |
| (R)-(-)-Deprenyl hydrochloride | J61286 | 180 |
| 3,5-Diamino-1,2,4-triazole, 98+% | B22775 | 183 |
| Diclofenac sodium salt | J62609 | 186 |
| DL-erythro-Dihydrosphingosine | J62103 | 191 |
| 3,4-Dihydroxycinnamic acid, predominantly trans, 99% | A15950 | 192 |
| 6,7-Dihydroxycoumarin, 98+% | A15393 | 192 |

| Description | Stock # | Page # |
|---|---------|--------|
| 1,3-Dihydroxynaphthalene, 98% | A17739 | 192 |
| 3,4-Dihydroxy-L-phenylalanine, 98+% | A11311 | 193 |
| Dilazep dihydrochloride | J62459 | 193 |
| Diphenyleiiodonium chloride | J64838 | 198 |
| Dipyridamole | J63329 | 199 |
| Domperidone | J63681 | 201 |
| Dovitinib | J61776 | 201 |
| Doxofylline | J60575 | 201 |
| 5,8,11,14-Eicosatetraynoic acid | J61624 | 204 |
| cis-5,8,11-Eicosatrienoic acid | J63870 | 204 |
| 5,8,11,-Eicosatriynoic acid | J60414 | 204 |
| Ellagic acid hydrate, 97%, may cont. up to 12% water | A15722 | 205 |
| Emodin | J61600 | 205 |
| Enalapril | J60750 | 206 |
| Enalaprilat | J63392 | 206 |
| Endothall | J60948 | 206 |
| (R,S)-Equol | J61383 | 209 |
| Erbstatin analog | J61612 | 209 |
| Erlotinib hydrochloride | J61633 | 210 |
| Esculin sesquihydrate | J63114 | 210 |
| Eserine | J61477 | 210 |
| Etidronate disodium | J62381 | 217 |
| Etoposide | J63651 | 217 |
| Fasudil, 98+% | J63525 | 219 |
| Fenvalerate, 99% | J63562 | 219 |
| Finasteride | J63454 | 221 |
| Fluconazole, 99% | J62015 | 221 |
| Flufenamic acid, 97% | B23583 | 222 |
| 2-Fluoro- α -methyl-4-biphenylacetic acid, 99% | B22603 | 224 |
| Fluoxetine hydrochloride, 99% | J61197 | 224 |
| Furazolidone, 98% | B20834 | 229 |
| Furegrelate sodium salt, 99+% | J61378 | 229 |
| Galanthamine hydrobromide | J62482 | 229 |
| GBR 12783 dihydrochloride | J63405 | 230 |
| GBR 12909 dihydrochloride | J60684 | 230 |
| GBR 12935 dihydrochloride | J62991 | 230 |
| Geldanamycin, 99+% | J63397 | 231 |
| Guvacine hydrochloride, 99+% | J61083 | 240 |
| H-7 dihydrochloride | J61697 | 240 |
| H-9 dihydrochloride | J63638 | 240 |
| Haloenol Lactone Suicide Substrate, 98+% | J63728 | 240 |
| Harmaline, 98+% | J61699 | 241 |
| Harmine, 98+% | L19068 | 241 |
| Harmol | J61135 | 241 |
| 1,2,3,4,5,6-Hexabromocyclohexane | J60853 | 244 |
| 1-Hydrazinophthalazine hydrochloride, 98% | B22995 | 247 |
| Hydrochlorothiazide, 98% | B22093 | 247 |
| 4-Hydroxybenzylidenemalononitrile, 98% | L04651 | 248 |
| (Hydroxy-2-naphthylmethyl)phosphonic acid, 98% | J63913 | 250 |
| 4-Hydroxy-1H-pyrazolo[3,4-d]pyrimidine, 98% | A16974 | 251 |
| Hydroxytacrine maleate salt | J60680 | 252 |
| Hypericin, 98% | H26425 | 253 |
| Ibandronate sodium, 98+% | J62443 | 253 |
| Iminodiacetic acid, 98+% | A11510 | 254 |
| Imipramine hydrochloride | J63723 | 255 |
| Indatraline hydrochloride, 99% | J61485 | 255 |
| Indomethacin, 99+% | J63255 | 256 |
| Irinotecan hydrochloride | J60743 | 259 |
| 4-Isobutyl- α -methylphenylacetic acid, 99% | B20989 | 260 |
| K252c, 99% | J63090 | 262 |
| Ketoconazole, 98+% | J63367 | 263 |
| Ketoprofen | J62702 | 263 |
| Lapatinib, 99+% | J62299 | 266 |
| Leptomycin B, 99+%, 1mM soln. in ethanol | J63784 | 268 |
| Lestaurtinib, 99+% | J60602 | 268 |
| Lovastatin, 97% | H52792 | 273 |

| Description | Stock # | Page # |
|--|---------|--------|
| Maprotiline hydrochloride, 99% | J62321 | 277 |
| Masitinib, 99+% | J62588 | 278 |
| Meclofenamic acid sodium salt, 99+% | J60484 | 279 |
| Mefenamic acid, 98% | J62705 | 279 |
| Meloxicam | J60635 | 280 |
| (S)-(+)-2-(6-Methoxy-2-naphthyl)propionic acid, 99% | L09855 | 285 |
| Methyl caffeate | J63786 | 286 |
| Midostaurin | J62917 | 291 |
| Milrinone, 98+% | J62659 | 292 |
| Nabumetone | J63072 | 296 |
| Naproxen sodium, 98% | J63103 | 298 |
| Neostigmine bromide | J62300 | 299 |
| Nilotinib, 99+% | J62578 | 303 |
| Nipecotinic acid, 98% | B24723 | 303 |
| Nordihydroguaiaretic acid, 97% | L03149 | 304 |
| Olomoucine, 98% | J60388 | 307 |
| Omeprazole, 98% | J62860 | 307 |
| Orlistat, 98% | J62999 | 308 |
| Oxonic acid potassium salt | J60400 | 310 |
| Pazopanib, 99+% | J62470 | 312 |
| Phosphodiesterase Inhibitor (IBMX) | J64598 | 321 |
| Piroxicam | J63239 | 323 |
| Proadifen hydrochloride | J63833 | 328 |
| (±)-Propranolol hydrochloride, 99% | H26645 | 329 |
| Quinapril hydrochloride, 98% | J61913 | 333 |
| Sarcosine, 98% | A14594 | 340 |
| SB 203580, 99% | J61482 | 341 |
| Sorafenib, 99+% | J62984 | 349 |
| D-erythro-Sphingosine, 99+% | J63584 | 351 |
| Tacrolimus, 99+% | J63571 | 357 |
| Tandutinib, 99% | J62004 | 358 |
| Tetraethylthiuram disulfide, 97% | B20721 | 362 |
| Tioconazole, 98+% | J60459 | 370 |
| Tozasertib, 99+% | J63232 | 372 |
| Trazodone hydrochloride | J63070 | 374 |
| Trequinsin hydrochloride, 98+% | J63999 | 374 |
| Tricyclodecan-9-yl xanthogenate potassium salt, 98+% | J63015 | 376 |
| Triflumuron, 98+% | J63112 | 376 |
| 1-(2-Trifluoromethylphenyl)imidazole, 98+% | L10465 | 377 |
| 1,8,9-Trihydroxyanthracene, 97% | B20303 | 377 |
| 4',5,7-Trihydroxyflavone, 97% | L15041 | 377 |
| Trypsin inhibitor, chicken egg whites | J63927 | 384 |
| Trypsin inhibitor, soybeans | J60982 | 384 |
| Tyrphostin A9, 99% | J63058 | 386 |
| Tyrphostin A23, 99% | J60308 | 386 |
| Tyrphostin A25, 99+% | J62936 | 386 |
| Tyrphostin A46, 99% | J60482 | 386 |
| Tyrphostin B7, 95%, cis + trans | J63126 | 387 |
| Tyrphostin B42, 99+% | J61715 | 387 |
| Tyrphostin B46, 98+% | J61704 | 387 |
| U0126, 99+% | J61246 | 387 |
| U-73122, 99+% | J62898 | 387 |
| U-73343, 98% | J62719 | 387 |
| Wortmannin, Penicillium funiculosum, 99+% | J63983 | 393 |
| Zaprinast, 98+% | J63326 | 395 |

Signal Transduction Reagents - Protease Inhibitors

During protein expression proteases can begin degrading protein samples as soon as cells or tissues are lysed, decreasing the protein yield and quality. In order to preserve the activity and nature of proteins, solutions are usually treated with a mixture of protease inhibitors during cell lysis. We offer a number of protease inhibitors to prevent protein sample degradation by the most common proteases.

| Description | Stock # | Page # |
|---|---------|--------|
| 4-(2-Aminoethyl)benzenesulfonyl fluoride hydrochloride, 97% | H26473 | 94 |
| Antipain | J60011 | 107 |
| Antipain dihydrochloride, 99+% | J63680 | 107 |
| Aprotinin, from bovine lung | J63039 | 108 |
| Bestatin | J61106 | 124 |
| Calpain Inhibitor III, 95+% | J62919 | 144 |
| Calpeptin, 98+% | J60481 | 144 |
| Camostat mesylate, 98% | J62362 | 144 |
| Cystatin, 95% | J62240 | 172 |
| E-64 | J62933 | 203 |
| Elastatinal | J61120 | 205 |
| Genistin, 99+% | J63445 | 231 |
| MG 132 | J63250 | 291 |
| Okadaic acid, 98% | J60155 | 307 |
| Pepstatin A, 98% | J60237 | 314 |
| Phenylethyl 3,4-dihydroxycinnamate, 99+% | J61386 | 316 |
| Phosphatase Inhibitor Cocktail I | J63907 | 319 |
| Phosphatase Inhibitor Cocktail II | J61022 | 319 |
| Protease Inhibitor Cocktail, for general use | J61852 | 330 |
| Protease Inhibitor Cocktail, for mammalian cells | J61473 | 330 |
| Quercetin dihydrate, 97% | A15807 | 333 |
| Staurosporine, 99+% | J62837 | 352 |
| Tamoxifen, 98+% | J63509 | 357 |
| α -Toluenesulfonyl fluoride, 99% | B22146 | 371 |
| N- α -(p-Toluenesulfonyl)-DL-lysine chloromethyl ketone hydrochloride, 98% | J63959 | 371 |
| N- α -(p-Toluenesulfonyl)-L-lysine chloromethyl ketone hydrochloride | J60120 | 371 |
| 4',5,7-Trihydroxyisoflavone, 99+% | J63241 | 377 |

Solvents, Acids and Bases

Solvents are used to dissolve other chemicals. For biological applications, water is the most commonly used solvent; however, some procedures require the use of other solvents like DMSO, DMF or acetonitrile. Acids and bases can be used to adjust the pH of biological samples. Alfa Aesar offers a variety of solvents, acids and bases to meet your research needs.

| Description | Stock # | Page # |
|--|---------|--------|
| Acetic acid, glacial, ACS, 99.7+% | 36289 | 70 |
| Acetone, ACS, 99.5+% | 30698 | 71 |
| Acetonitrile, ACS, 99.5+% | 36423 | 71 |
| Acetyl chloride, 99+% | 43262 | 71 |
| Ammonium dihydrogen phosphate, ACS, 98.0% min | 11598 | 101 |
| Ammonium hydrogen phosphate, ACS, 98.0% min | 11597 | 101 |
| Ammonium hydroxide, ACS, 28.0-30.0% NH ₃ | 33285 | 101 |
| Chloroacetic acid, 99% | A11482 | 154 |
| Chlorosulfonic acid, typically 99% | 87977 | 159 |
| Decahydronaphthalene, cis + trans, 98% | A13883 | 175 |
| 1,2-Dichloroethane, ACS, 99+% | 39121 | 185 |
| Dichloromethane, 99+%, stab. with ca. 50ppm 2-methyl-2-butene | L13089 | 186 |
| 2,6-Dichlorophenol, 99% | A14411 | 186 |
| Diethylene glycol, 99% | A14728 | 189 |
| Diethylene glycol diethyl ether, 99% | A17478 | 189 |
| Diethylene glycol diethyl ether, HPLC Grade, 99+% | 43464 | 189 |
| Diethylene glycol dimethyl ether, 99%, stab. with 100ppm BHT | A13397 | 189 |
| Diethylene glycol monoethyl ether acetate, 99% | L13446 | 189 |
| Diethylene glycol monoethyl ether, 98% | A14670 | 189 |
| 2,3-Dihydrofuran, 98+% | B20575 | 190 |
| N,N-Dimethylformamide, ACS, 99.8+% | 39117 | 197 |
| Dimethyl sulfoxide, ACS, 99.9% min | 36480 | 197 |
| Formic acid, ACS, 96+% | 36617 | 228 |
| Formic acid, 97% | A13285 | 228 |
| Glycerol, ultrapure, HPLC Grade | 38988 | 236 |
| Glyoxylic acid, 50% w/w aq. soln. | B25149 | 238 |
| Hydrochloric acid, ACS, HCl 36.5-38.0% | 33257 | 247 |
| Hydrochloric acid, 1.0N Standardized Solution | 35640 | 247 |
| 1-Methyl-2-pyrrolidinone, Biograde, 99.5% | 44063 | 290 |
| Methanol, Biograde, 99.8+% | 44571 | 283 |
| Nitric acid, 1.0N Standardized Solution | 35624 | 303 |
| Orthophosphoric acid, 85% w/w aq. soln., ACS | 33266 | 309 |
| Potassium chloride, ACS, 99.0-100.5% | 11595 | 326 |
| Potassium dihydrogen phosphate, ACS, 99.0% min | 11594 | 326 |
| Potassium hydrogen phosphate, ACS, 98.0% min | 11593 | 326 |
| Potassium hydroxide, ACS, 85% min, K ₂ CO ₃ 2.0% max | 13451 | 327 |
| Potassium sulfate, ACS, 99.0% min | 14311 | 328 |
| Sodium chloride, ACS, 99.0% min | 12314 | 345 |
| Sodium hydrogen phosphate, anhydrous, ACS, 99.0% min | 13437 | 346 |
| Sodium hydroxide, 10N aq. soln. | J63736 | 346 |
| Sodium hydroxide (low chloride), ACS, 97.0% min | 13455 | 346 |
| Tetraethylene glycol, 99% | B23880 | 362 |
| Tetrahydrofuran, Biograde, 99.8%, unstab. | 44505 | 363 |
| Tetrahydrofuran, Spectrophotometric Grade, 99.7+%, unstab. | 32468 | 363 |
| 2,2,2-Trifluoroethanol, 99+% | A10788 | 376 |

Stains, Dyes and Indicators

Dyes, stains and indicators are all integral tools in the laboratory. Stains can be used in microbiological assays as well as in histology. Indicators are useful for measuring or setting pH of solutions. Fluorescent dyes are used extensively to label macromolecules in fluorescent microscopy and purification techniques.

| Description | Stock # | Page # |
|---|---------|--------|
| Acid Fuchsin sodium salt | B22222 | 76 |
| Acridine, 98+% | L01657 | 76 |
| Acridine hydrochloride | J62634 | 76 |
| Acriflavine hydrochloride | J60048 | 76 |
| Alizarin, 94% | A14404 | 89 |
| Alizarin Yellow R sodium salt | 38707 | 89 |
| Amido Black 10B, 0.2% v/v soln. in 5% acetic acid | J61978 | 91 |
| 2-Aminofluorene, 98% | B22769 | 94 |
| 7-Amino-4-methylcoumarin, 98% | A15017 | 97 |
| Arsenazo III free acid | J63031 | 110 |
| Auramine O, 80% dye content | J60343 | 112 |
| Azocarmine G | A12507 | 116 |
| Azure I | A17508 | 116 |
| Azure II | A11777 | 116 |
| Azure A | J61346 | 116 |
| Basic Fuchsin | A12952 | 117 |
| Bathocuproin, 98% | B22841 | 117 |
| Bathocuproin sulfonate disodium salt hydrate, 97% | B22550 | 118 |
| Bathophenanthroline, 98+% | A14258 | 118 |
| Bismarck Brown Y | A16674 | 127 |
| Biuret, 97% | L00812 | 128 |
| Blue Tetrazolium chloride | A12502 | 129 |
| Bradford Dye Reagent, ready to use | J61522 | 134 |
| Brilliant Blue G soln., Ready-to-Use | J63797 | 135 |
| Brilliant Blue R soln., Ready-to-Use | J61384 | 135 |
| Brilliant Green | A12801 | 135 |
| Bromocresol Green sodium salt, 0.04% w/v aq. soln. | 38696 | 136 |
| Bromocresol Purple sodium salt, 0.04% w/v aq. soln. | 38700 | 136 |
| Bromophenol Blue, ACS | 32641 | 137 |
| Bromophenol Blue sodium salt, 0.04% w/v aq. soln. | 38693 | 137 |
| Bromothymol Blue sodium salt, 0.04% w/v aq. soln. | 38701 | 138 |
| Calcein sodium salt, ca 2-3 Na | L10255 | 142 |
| 5(6)-Carboxyfluorescein, mixture of isomers, 97% | L13439 | 148 |
| Chicago Sky Blue 6B | A14242 | 153 |
| Chlorazol Black E | A13259 | 154 |
| 4-Chloro-7-nitrobenzofurazan, 99% | A14165 | 157 |
| 2-Chloro-4-nitrophenol, 97% | B21561 | 157 |
| Chlorophenol Red | B21623 | 157 |
| Chlorophenol Red sodium salt | L10364 | 158 |
| Chlorophenol Red sodium salt, 0.04% w/v aq. soln. | 38699 | 158 |
| Congo Red, indicator grade | B24310 | 168 |
| o-Cresolphthalein | A12899 | 169 |
| o-Cresolphthalein complexone, indicator grade | L03859 | 169 |
| m-Cresol Purple | B24338 | 169 |
| m-Cresol Purple sodium salt, 0.04% w/v aq. soln. | 38691 | 169 |
| m-Cresol Purple sodium salt | A18025 | 169 |
| Cresol Red sodium salt | B21361 | 169 |
| Crystal Violet | B21932 | 170 |
| Dansyl amide, 98% | A11449 | 175 |
| Dansyl chloride, 97+% | A13828 | 175 |
| 3,3'-Diaminobenzidine, tablets | J60972 | 182 |
| 3,3'-Diaminobenzidine tetrahydrochloride hydrate | J62216 | 182 |
| o-Dianisidine, 98+% | A17150 | 184 |
| o-Dianisidine dihydrochloride, 99% | A17175 | 184 |
| 2,6-Dichloroindophenol sodium salt hydrate | A10107 | 185 |
| 3,5-Dihydroxytoluene, 99% | L18567 | 193 |
| 2,9-Dimethyl-1,10-phenanthroline hemihydrate, 98+% | A11398 | 197 |

Stains, Dyes and Indicators

| Description | Stock # | Page # |
|---|---------|--------|
| 2,9-Dimethyl-1,10-phenanthroline, 98% | J63698 | 197 |
| Direct Red 80 | B21693 | 199 |
| Eosin B | A17377 | 208 |
| Eosin Yellowish | B24535 | 208 |
| Eriochrome® Blue Black B | J63396 | 210 |
| Erioglaucine sodium salt | J61780 | 210 |
| Erythrosin B | A14180 | 210 |
| Erythrosin B, spirit soluble | J62619 | 210 |
| 7-Ethoxyresorufin | J62987 | 214 |
| Ethyl Orange sodium salt | J62863 | 217 |
| Ethyl Red | J63446 | 217 |
| Ethyl Violet | J63951 | 217 |
| Evans Blue | A16774 | 218 |
| Fast Blue BB base | J62456 | 218 |
| Fast Blue BB salt | L09704 | 218 |
| Fast Garnet GBC base | J60574 | 218 |
| Field's Stain A | A18577 | 221 |
| Field's Stain B | A18578 | 221 |
| Fluo 3-AM | J63388 | 222 |
| Fluorescamine | 43749 | 222 |
| Fluorescein, 90+% | L13251 | 222 |
| Fluorescein amine isomer I, 96% | J62175 | 222 |
| Fluorescein amine isomer II, 95% | J60609 | 223 |
| Fluorescein diacetate, 97% | B24466 | 223 |
| Fluorescein disodium salt | J61549 | 223 |
| Fluorescein isothiocyanate, isomer 1, 95% | L09319 | 223 |
| FURA 2 pentasodium salt | J63686 | 229 |
| FURA 2-AM | J62728 | 229 |
| Giemsa Stain | B21172 | 232 |
| Hematoxylin hydrate, 96% (dry wt.), water ca 6% | A12431 | 242 |
| India Ink | J61007 | 255 |
| Indigo carmine | A16052 | 255 |
| Iodonitrotetrazolium violet, 95% | B22301 | 258 |
| Janus Green B | A17391 | 262 |
| Jenner's Stain | J61077 | 262 |
| Kiton Red S | A14769 | 264 |
| Leishman Stain | A11644 | 268 |
| Light Green SF Yellowish | B23330 | 270 |
| Malachite Green oxalate | A16186 | 275 |
| Metanil Yellow | A17527 | 283 |
| 7-Methoxycoumarin-4-acetic acid, 99% | J62475 | 284 |
| Methyl Orange, 0.1% w/v aq. soln. | 38695 | 289 |
| Methyl Orange | A17604 | 289 |
| Methyl Red, 0.1% w/v solution in ethanol | 38698 | 290 |
| Methyl Red, ACS | 36682 | 290 |
| Methyl Red hydrochloride, ACS | 36668 | 290 |
| Methyl Red sodium salt, ACS | 36667 | 290 |
| Naphthol Green B | A18268 | 298 |
| Naphthol Yellow S | B20872 | 298 |
| Neutral Red, 1% aq. solution, Ready-to-use | J61379 | 300 |
| Neutral Red, ACS | J62643 | 300 |
| Nigrosin water soluble | A18147 | 302 |
| Nigrosin, alcohol soluble | J61186 | 302 |
| Nile Blue A | A17174 | 302 |
| Ninhydrin, ACS reagent | 43846 | 303 |
| Nitrazine Yellow | J60281 | 303 |
| Nitro Blue Tetrazolium chloride, 99% | J60230 | 303 |
| Oil Red O | A12989 | 307 |
| Orcein, for analysis | B20294 | 308 |
| Phenolphthalein, 98% | A17135 | 314 |
| Phenolphthalein, ACS | 38705 | 314 |
| Phenolphthalein, 1% w/v in alcohol | 38704 | 315 |
| Phenol Red, ACS | 16294 | 315 |
| Phenol Red sodium salt, 0.02% w/v aq. soln. | 38702 | 315 |
| Ponceau S, 0.2% v/v soln. in 5% acetic acid | J63139 | 325 |
| Pyronin Y, 0.2% w/v aq. soln. | J60505 | 332 |

| Description | Stock # | Page # |
|--|---------|--------|
| Quin 2 | J61919 | 333 |
| Rapid stain G-250 | J61347 | 335 |
| Rapid stain R-250 | J61969 | 335 |
| Resazurin sodium salt | B21187 | 335 |
| Rhodamine 6G | J62315 | 337 |
| Rhodamine B | A13572 | 337 |
| Rhodanile Blue | A13622 | 337 |
| Safranin O | B21674 | 339 |
| Solvent Blue 38 | A15395 | 349 |
| Stains-All, 96% | H32127 | 352 |
| Sudan II | A17613 | 355 |
| Sudan III | A18318 | 355 |
| Sudan IV | A12181 | 355 |
| Sudan Black B | J62268 | 355 |
| Sulfonazo III tetrasodium salt | A10486 | 356 |
| Sulforhodamine 101 acid chloride | J60581 | 356 |
| Tartrazine | A17682 | 358 |
| Tetrabromophenol Blue | B20123 | 361 |
| 5(6)-Tetramethylrhodamine isothiocyanate | J62258 | 365 |
| Thiazolyl Blue tetrazolium bromide, 98% | L11939 | 366 |
| Thioflavine T, tech. 75% | J61043 | 367 |
| Thymol Blue | B21370 | 369 |
| Thymol Blue, ACS | 16272 | 369 |
| Thymol Blue sodium salt, 0.04% w/v aq. soln. | 38692 | 369 |
| Thymolphthalein, 0.05% w/v solution in ethanol | 38706 | 369 |
| Thymolphthalein, ACS | 16245 | 369 |
| 2,3,5-Triphenyl-2H-tetrazolium chloride, 98% | A10870 | 379 |
| Trypan Blue, dye content >60% | A18600 | 384 |
| Wright's Stain | A17903 | 393 |
| XTT sodium salt | J61726 | 394 |
| Xylenol Blue | A17457 | 394 |
| Xylidyl Blue I sodium salt | L10863 | 394 |

Vitamins

Vitamins are organic compounds required as nutrients by organisms. Organisms do not synthesize sufficient amounts of vitamins and must obtain them through their diet. Vitamins have diverse biochemical functions. Some vitamins, like vitamin D, have hormone-like functions as regulators of mineral metabolism while others, like vitamin E, function as antioxidants. Others still, like members of the B family of vitamins, function as precursors for enzyme cofactors that help enzymes work as catalysts in metabolism.


| Description | Stock # | Page # |
|--|---------|--------|
| L-(+)-Ascorbic acid, ACS, 99+% | 36237 | 110 |
| L-Ascorbic acid sodium salt, 99% | A17759 | 110 |
| L-Ascorbic acid 6-palmitate, 99% | 32791 | 110 |
| D-(+)-Biotin, 98+% | A14207 | 125 |
| (+)-Biotin N-hydroxysuccinimide ester, 98% | 44771 | 125 |
| Calciferol | J61610 | 142 |
| Calciferol, 98% | J62163 | 142 |
| Citric acid, anhydrous, ACS, 99.5+% | 36664 | 164 |
| Flavin adenine dinucleotide disodium salt hydrate, 94% (dry wt.), water <10% | A14495 | 221 |
| Folic acid, crystalline | J60833 | 227 |
| Methylcobalamin hydrate, 99% | A11176 | 286 |
| 2-Methyl-1,4-naphthoquinone, 98% | A13593 | 289 |
| Nicotinamide, 99% | A15970 | 301 |
| Nicotinic acid, 99% | A12683 | 302 |
| D-Panthenol, 98+% | A18499 | 311 |
| D-Pantothenic acid calcium salt hydrate, 98% | A16609 | 311 |
| Pyridoxal-5-phosphate monohydrate, 98% | A12323 | 332 |
| Pyridoxamine dihydrochloride, Cell Culture Reagent | J62679 | 332 |
| 9-cis-Retinoic acid | J62219 | 336 |
| 13-cis-Retinoic acid | J61666 | 336 |
| Retinoic acid, 98% | 44540 | 336 |
| Retinol, 98%, synthetic | J62079 | 336 |
| Riboflavin, 98% | A11764 | 337 |
| Thiamine hydrochloride, 99% (dry wt.), may cont. up to 5% water | A19560 | 366 |
| Thiamine nitrate | J60014 | 366 |
| Thiamine pyrophosphate chloride, 98% | J61483 | 366 |
| DL- α -Tocopherol, 97+% | A17039 | 370 |
| Vitamin A acetate in gelatin, powder, 500,000 I.U./g | A16237 | 392 |
| Vitamin A palmitate, 98+% | J63022 | 392 |
| Vitamin B12, 98+% (dry wt basis) | A14894 | 392 |
| Vitamin D3, 99% | B22524 | 392 |
| Vitamin E acetate, 97% | A14505 | 393 |
| Vitamin K ₁ | L10575 | 393 |









Western Blot and ELISA Reagents














ELISA and Western blotting are common techniques for protein detection and quantification. ELISA is a plate-based assay while Western blots are performed on a membrane surface after transfer from a gel. In both techniques enzyme-linked antibodies are usually used to detect immobilized proteins. This list includes blocking, transfer and wash buffers that are frequently used in ELISA or Western blots. It also includes stains for Western blots and substrates for ELISA.

| Description | Stock # | Page # |
|--|---------|--------|
| Alkaline Phosphatase, calf intestine, EIA Grade | J61037 | 89 |
| 3-Amino-9-ethylcarbazole, 95% | B22529 | 94 |
| Anti-Osteocalcin antibody, RIA Grade | J64638 | 107 |
| BLOTTO | J61417 | 128 |
| BLOTTO in PBS | J60296 | 128 |
| BLOTTO in PBS, with 0.02% sodium azide | J60166 | 128 |
| BLOTTO antifoam in PBS | J63851 | 128 |
| BLOTTO antifoam in PBS, with 0.02% sodium azide | J61888 | 128 |
| BLOTTO in TBS | J63238 | 128 |
| BLOTTO in TBS, with 0.02% sodium azide | J62235 | 128 |
| BLOTTO antifoam in TBS | J62031 | 128 |
| BLOTTO antifoam in TBS, with 0.02% sodium azide | J63891 | 129 |
| BLOTTO and Tween 20 in PBS | J61880 | 129 |
| BLOTTO and Tween 20 in PBS, with 0.02% sodium azide | J62304 | 129 |
| BLOTTO and Tween 20 in TBS | J62341 | 129 |
| BLOTTO and Tween 20 in TBS, with 0.02% sodium azide | J63026 | 129 |
| BSA blocking buffer, 3% in PBS | J61655 | 139 |
| BSA blocking buffer, 3% in PBS, with 0.02% sodium azide | J60473 | 139 |
| BSA blocking buffer, 3% in PBS, with 0.05% Tween-20 | J61116 | 139 |
| BSA blocking buffer, 3% in TBS | J61119 | 139 |
| BSA blocking buffer, 3% in TBS, with 0.05% Tween-20 | J62554 | 139 |
| BSA blocking buffer, 5% in PBS | J61089 | 139 |
| BSA blocking buffer, 5% in PBS, with 0.05% Tween-20 | J63711 | 139 |
| BSA blocking buffer, 5% in TBS | J62637 | 139 |
| BSA blocking buffer, 5% in TBS, with 0.02% sodium azide | J62305 | 139 |
| BSA blocking buffer, 5% in TBS, with 0.05% Tween-20 | J60098 | 139 |
| Casein blocking buffer, 3% in PBS | J60289 | 149 |
| Casein blocking buffer, 3% in PBS, with 0.02% sodium azide | J63453 | 149 |
| Casein blocking buffer, 3% in TBS | J61298 | 149 |
| Casein blocking buffer, 3% in TBS, with 0.02% sodium azide | J62935 | 149 |
| Cyclic AMP Enzyme Immunoassay Kit | J65001 | 171 |
| Cyclic GMP Enzyme Immunoassay Kit | J65422 | 171 |
| 3,3'-Diaminobenzidine, tablets | J60972 | 182 |
| 3,3'-Diaminobenzidine tetrahydrochloride hydrate | J62216 | 182 |
| Human Epidermal Growth Factor Enzyme Immunoassay Kit | J65512 | 247 |
| FCS blocking buffer in PBS | J63160 | 219 |
| FCS blocking buffer in TBS | J61327 | 219 |
| Fibronectin, human, Enzyme Immunoassay Kit | J64057 | 221 |
| Gelatin blocking buffer, 1% in PBS | J62755 | 230 |
| Gelatin blocking buffer, 1% in PBS, with 0.02% sodium azide | J63104 | 230 |
| Gelatin blocking buffer, 1% in TBS | J62966 | 230 |
| Gelatin blocking buffer, 1% in TBS, with 0.02% sodium azide | J60805 | 230 |
| Gelatin and Tween 20 in PBS | J60939 | 230 |
| Gelatin and Tween 20 in PBS, with 0.02% sodium azide | J62479 | 230 |
| Gelatin and Tween 20 in TBS | J62272 | 230 |
| Gelatin and Tween 20 in TBS, with 0.02% sodium azide | J61671 | 230 |
| Horse serum | J61851 | 246 |
| Involucrin, human, Enzyme Immunoassay Kit | J64994 | 257 |
| Lysozyme, human, Enzyme Immunoassay Kit | J64986 | 266 |
| Osteocalcin, rat, 99.9% | J64231 | 309 |
| Osteocalcin, human, intact, Enzyme Immunoassay Kit | J64816 | 309 |
| Osteocalcin, human, mid-tact, Enzyme Immunoassay Kit | J64764 | 309 |
| Osteocalcin, rat, Enzyme Immunoassay Kit | J65214 | 309 |
| Osteocalcin, mouse, Enzyme Immunoassay Kit | J64239 | 309 |
| Peroxidase, horseradish | J60026 | 314 |
| Phosphate-buffered saline (PBS, 10X), pH 7.4, for Western blot | J60801 | 320 |







| Description | Stock # | Page # |
|---|---------|--------|
| Semi dry blot transfer buffer (10X) | J63664 | 341 |
| Stripping buffer (4X) | J60925 | 352 |
| Stripping buffer-2 (4X) | J62023 | 353 |
| Stripping buffer-3 (4X) | J60810 | 353 |
| 3,3',5,5'-Tetramethylbenzidine, 98% | A13868 | 364 |
| 3,3',5,5'-Tetramethylbenzidine dihydrochloride hydrate, 99+% | J60332 | 364 |
| 3,3',5,5'-Tetramethylbenzidine aq. soln. | J60808 | 364 |
| 3,3',5,5'-Tetramethylbenzidine soln., Ready-to-Use, high sensitivity | J61325 | 364 |
| 3,3',5,5'-Tetramethylbenzidine soln., Ready-to-Use, precipitating, standard sensitivity | J60461 | 364 |
| TRIS-buffered saline (TBS, 10X), with 0.5% Tween 20 | J60448 | 381 |
| TRIS-buffered saline (TBS, 20X), with 0.5% Tween 20 | J63682 | 381 |
| TRIS-buffered saline (TBS, 10X), with 1% Tween 20 | J62955 | 381 |
| TRIS-buffered saline (TBS, 20X), with 1% Tween 20 | J60497 | 381 |
| Tween 20 blocking buffer, 1% in PBS (10X) | J61544 | 385 |
| Tween 20 blocking buffer, 0.5% in PBS (10X) | J60304 | 385 |
| Tween 20 washing buffer, 1% in PBS (10X) | J63314 | 385 |
| Tween 20 washing buffer, 0.5% in PBS (10X) | J63596 | 385 |
| Tween 20 washing buffer, 1% in PBS (20X) | J61419 | 385 |
| Tween 20 washing buffer, 0.5% in PBS (20X) | J62844 | 385 |

| Stock # | Description | Size |
|---------|--|---------------------|
| J65650 | 10058-F4 [5-[(4-Ethylphenyl)methylene]-2-thioxo-4-thiazolidinone, c-Myc Inhibitor] [403811-55-2], C ₁₂ H ₁₁ NOS ₂ , F.W. 249.35, Solid, MDL MFCD00758517 ! H:H319-H317, P:P261-P280-P305+P351+P338-P302+P352-P321-P501 | 10mg |
| J62760 | A-3 hydrochloride [N-(2-Aminoethyl)-5-chloronaphthalene-1-sulfonamide hydrochloride] [78957-85-4], C ₁₂ H ₁₃ ClN ₂ O ₂ S HCl, F.W. 321.22, Solid, MDL MFCD0077311 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): A protein kinase inhibitor | 25mg |
| J62011 | A-7 hydrochloride [N-(10-Aminodecyl)-5-chloro-1-naphthalenesulfonamide hydrochloride] [79127-24-5], C ₂₀ H ₂₉ ClN ₂ O ₂ S HCl, F.W. 433.44, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): Calmodulin antagonist | 25mg |
| J60039 | Abamectin, 97+% [Avermectin B1] [71751-41-2], C ₄₈ H ₇₂ O ₁₄ , F.W. 873.10, Powder, m.p. 150-155°, Merck 14,2, UN2811, RTECS CL1203000, MDL MFCD01769550 ! H:H300-H400-H332, P:P261-P301+P310-P321-P304+P340-P405-P501a Application(s): Interacts with GABA receptors to cause chloride channel activation | 1g 5g |
| L13770 | Abietic acid, tech. 75% △ [514-10-3], C ₂₀ H ₃₀ O ₂ , F.W. 302.45, Merck 14,7, EINECS 208-178-3, RTECS TP8580000, BRN 2221451, MDL MFCD03423567, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Useful precursor for synthesis of various natural products including diterpenes and steroids. Review: <i>Sci. Pharm.</i> , 53, 173 (1985). | 25g 100g |
| |  | |
| | ABT , see 1-Aminobenzotriazole, 98%, J63610, p. 92 9-AC , see Anthracene-9-carboxylic acid, A14049, p. 105 7-ACA , see 7-Aminocephalosporanic acid, A10530, p. 92 | |
| 36499 | Acacia, Total ash <4% [Gum Arabic] [9000-01-5], -100 Mesh Powder, d. 1.35-1.49, Merck 14,14, EINECS 232-519-5, MDL MFCD00081264, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): Mixture of polysaccharides and glycoproteins used in the food industry as a stabilizer | 500g 2kg |
| J61737 | Acarbose, 95% [Bay-g 5421] [56180-94-0], C ₂₅ H ₄₃ NO ₁₈ , F.W. 645.61, Powder, Merck 14,18, EINECS 260-030-7, MDL MFCD00869592 Application(s): A reversible α-glucosidase inhibitor | 1g 2g 5g |
| | ACBC , see 1-Aminocyclobutane carboxylic acid hydrochloride, J63873, p. 92 | |
| J63790 | Acebutolol hydrochloride [34381-68-5], C ₁₈ H ₂₈ N ₂ O ₄ ·HCl, F.W. 372.89, White to off-white powder, m.p. 141-143°, Merck 14,19, EINECS 251-980-3, RTECS ES5235000, MDL MFCD00078860 ! H:H302-H312-H332, P:P261-P280-P302+P352-P304+P340-P322-P501 Application(s): Cardioselective β-adrenergic blocker | 1g 5g 10g |
| J60355 | Aceclofenac, 99% [89796-99-6], C ₁₈ H ₁₉ Cl ₂ NO ₄ , F.W. 354.18, Powder, m.p. 149-153°, Merck 14,22, UN2811, RTECS CY1577900, MDL MFCD00864296 ! H:H301-H400-H410-H319, P:P280-P301+P310-P305+P351+P338-P321-P405-P501a Application(s): A non-steroidal, anti-inflammatory drug (NSAID) with potent inhibitory activity in several models of inflammation | 5g 25g 100g |
| J63583 | Acemetacin [53164-05-9], C ₂₁ H ₁₈ ClNO ₆ , F.W. 415.83, Powder, m.p. 149-153°, Merck 14,27, UN2811, EINECS 258-403-4, RTECS NL3521400, MDL MFCD00151473 ! H:H300-H310-H330, P:P301+P310-P304+P340-P320-P330-P361-P405-P501a Application(s): A potent inhibitor of COX-2 found to have anti-tumor activity in the colon | 2g 10g |
| A11553 | ACES, 99% [N-(2-Acetamido)-2-aminoethanesulfonic acid, N-(Carbamoylmethyl)taurine] [7365-82-4], H ₂ NCOCH ₂ NHCH ₂ CH ₂ SO ₃ H, F.W. 182.20, m.p. ca 275° dec., Merck 14,36, EINECS 230-908-4, BRN 2253770, MDL MFCD00008030, † Biological buffer, pK _a = 6.9 at 20°: <i>Biochemistry</i> , 5, 467 (1966). Application(s): Good's buffers | 25g 100g 500g |
| J61761 | ACES, 0.5M buffer soln., pH 6.0 [7365-82-4], Liquid, † | 100ml 250ml |





| Stock # | Description | Size |
|---------|---|---------------------------------|
| J60366 | ACES, 0.5M buffer soln., pH 6.5 [7365-82-4], Liquid, † | 100ml 250ml |
| J60755 | ACES, 0.5M buffer soln., pH 7.0 [7365-82-4], Liquid, † | 100ml 250ml |
| J61011 | ACES, 0.5M buffer soln., pH 7.5 [7365-82-4], Liquid, † | 100ml 250ml |
| A12589 | Acetamide, 99% ■ [60-35-5], CH_3CONH_2 , F.W. 59.07, m.p. 76-81°, b.p. 220-222°, d. 1.159, Merck 14,43, Fieser 1,3, EINECS 200-473-5, RTECS AB4025000, BRN 1071207, MDL MFCD00008023, †  H: H351, P: P280h Useful additive for brominations of acid-sensitive compounds in non-polar solvents since it forms a stable, insoluble 1:1 complex with HBr: <i>Chem. Ber.</i> , 82 , 275 (1949). For amidocarbonylation in the presence of carbon monoxide and hydrogen in a route to phenylalanine, see Benzyl chloride, A12481 . | 250g 1kg 5kg |
| | Acetamidoacetic acid , see N-Acetylglycine, B21887, p. 73 N-(2-Acetamido)-2-aminoethanesulfonic acid , see ACES, A11553, p. 69 2-Acetamido-2-deoxy-1,3,4,6-tetra-O-acetyl-β-D-glucopyranose , see β-D-Glucosamine pentaacetate, L09020, p. 233 5-Acetamido-3,5-dideoxy-D-glycero-D-galactononulosonic acid , see N-(-)-Acetyneuraminic acid, L13950, p. 74 N-(2-Acetamido)iminodiacetic acid , see ADA, A15267, p. 78 | |
| A11240 | 4-Acetamidophenol, 98% [Acetaminophen, 4'-Hydroxyacetanilide] [103-90-2], $\text{C}_9\text{H}_9\text{NO}_2$, F.W. 151.17, m.p. 168-172°, d. 1.293, Merck 14,47, EINECS 203-157-5, RTECS AE4200000, BRN 2208089, MDL MFCD00002328, †  H: H302-H412, P: P273-P264-P270-P301+P312-P330-P501a  | 250g 500g 1kg 5kg |
| | Application(s): Cyclooxygenase inhibitor and widely used analgesic 5-Acetamido-1,3,4-thiadiazole-2-sulfonamide , see Acetazolamide, L07562, p. 70 Acetaminophen , see 4-Acetamidophenol, A11240, p. 70 | |
| J63876 | Acetate, 1M buffer soln., pH, 3.0 [127-09-3], Liquid, † | 250ml 500ml |
| J60340 | Acetate, 1M buffer soln., pH, 3.5 [127-09-3], Liquid, † | 250ml 500ml |
| J60104 | Acetate, 1M buffer soln., pH, 4.0 [127-09-3], Liquid, † | 250ml 500ml |
| J60964 | Acetate, 1M buffer soln., pH, 5.0 [127-09-3], Liquid, † | 250ml 500ml |
| J61033 | Acetate, 1M buffer soln., pH, 5.5 [127-09-3], Liquid, † | 250ml 500ml |
| L07562 | Acetazolamide, 99% [5-Acetamido-1,3,4-thiadiazole-2-sulfonamide] [59-66-5], $\text{C}_8\text{H}_{10}\text{N}_4\text{O}_3\text{S}_2$, F.W. 222.25, m.p. ca 255° dec., Merck 14,53, EINECS 200-440-5, RTECS AC8225000, BRN 212994, MDL MFCD00003105, †  H: H360, P: P281-P201-P202-P308+P313-P405-P501a  | 5g 25g |
| | Application(s): Carbonic anhydrase inhibitor; increases cerebral blood flow | |
| 36289 | Acetic acid, glacial, ACS, 99.7+% [64-19-7], $\text{CH}_3\text{CO}_2\text{H}$, F.W. 60.05, Liquid, m.p. 16.6°, b.p. 118.1°, f.p. 40°(104°F), d. 1.049, n_D^{20} 1.3721, Merck 14,55, Fieser 2,5 5,3 7,1 8,1 19,1 21,1, UN2789, EINECS 200-580-7, MDL MFCD00036152, † Maximum level of impurities: Color (APHA) 10, Dilution Test P.T., Evaporation Residue 0.001%, $(\text{CH}_3\text{CO})_2\text{O}$ 0.01%, Cl 1ppm, SO_4 1ppm, Heavy Metals (as Pb) 0.5ppm, Fe 0.2ppm, Substances reducing dichromate P.T., Substances reducing permanganate P.T., Titrationl  H: H314-H226, P: P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a | 100ml 500ml 2L 4x500ml |
| | Acetic acid cholesteryl ester , see Cholesteryl acetate, A15052, p. 161 Acetic chloride , see Acetyl chloride, 43262, p. 71 Acetic phenylhydrazide , see N-Acetyl-N'-phenylhydrazine, A14446, p. 74 | |
| L01569 | Acetohydroxamic acid, 98% ■ [546-88-3], $\text{C}_2\text{H}_5\text{NO}_2$, F.W. 75.07, m.p. 86-90°, Merck 14,63, Fieser 13,2, EINECS 208-913-8, RTECS AK8157000, BRN 1739019, MDL MFCD00009994  H: H360, P: P281-P201-P202-P308+P313-P405-P501a  | 1g 5g 25g |
| | Application(s): Urease inhibitor | |

| Stock # | Description | Size |
|---------|--|---|
| 30698 | Acetone, ACS, 99.5+% [67-64-1], CH ₃ COCH ₃ , F.W. 58.08, Liquid, m.p. -94°, b.p. 56°, f.p. -17°(1°F), d. 0.791, n _D ²⁰ 1.3590, Merck 14,66, Fieser 2,13 3,4 6,9, UN1090, EINECS 200-662-2, RTECS AL3150000, BRN 635680, MDL MFCD00008765, † Maximum level of impurities: Color (APHA) 10, Evaporation residue 0.001%, Solubility in water P.T., Titratable acid 0.0003meq/g, Titratable base 0.0006meq/g, Aldehyde as (HCHO) 0.002%, Isopropyl alcohol 0.05%, Methanolan 0.05%, Substances reducing permangan | 10ml 500ml 1L 4L 4x1L |
| |   H:H225-H319-EUH066-H336, P:P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a | |
| 36423 | Acetonitrile, ACS, 99.5+% [Methyl cyanide] [75-05-8], CH ₃ CN, F.W. 41.05, Liquid, m.p. -48° to -45°, b.p. 80-82°, f.p. 5°(41°F), d. 0.786, n _D ²⁰ 1.3440, Merck 14,70, Fieser 2,13 15,1 18,2 19,1, UN1648, EINECS 200-835-2, RTECS AL7700000, BRN 741857, MDL MFCD00001878, † Maximum level of impurities: Color (APHA) 10, Evaporation residue 0.005%, Titratable acid 8µeq/g, Titratable base 0.6µeq/g, H ₂ O 0.3% | 500ml 1L 4L 4x1L 4x4L |
| |   H:H225-H302-H312-H332-H319, P:P210-P241-P303+P361+P353-P305+P351+P338-P302+P352-P501a | |
| | 2-Acetoxybenzoic acid , see O-Acetylsalicylic acid, A12488, p. 74 3-Acetoxyindole , see 3-Indoxyl acetate, L04932, p. 256 (R)-3-Acetoxy-4-(trimethylammonio)butyrate hydrochloride , see O-Acetyl-L-carnitine chloride, J61536, p. 71 Aceturic acid , see N-Acetylglycine, B21887, p. 73 | |
| J64039 | Acetyl-Adrenocorticotrophic Hormone (1-14) [Acetyl-ACTH (1-14), Ac-Ser-Tyr-Ser-Met-Glu-His-Phe-Arg-Trp-Gly-Lys-Pro-Val-Gly] C ₂₀ H ₁₁₁ N ₂₁ O ₂₁ S, F.W. 1722.92, Solid | 5mg |
| L10329 | N-Acetyl-DL-alanine, 97+% [Ac-DL-Ala-OH] [1115-69-1], C ₆ H ₉ NO ₃ , F.W. 131.13, m.p. 135-139°, EINECS 214-229-0, BRN 774333, MDL MFCD00037238 |  5g 25g |
| L11811 | N-Acetyl-L-alanine, 96% [Ac-Ala-OH] [97-69-8], C ₆ H ₉ NO ₃ , F.W. 131.13, m.p. 122-128°, [α] _D ²⁰ -64° (c=2 in water), EINECS 202-602-0, BRN 1722932, MDL MFCD00063132 |  1g 5g |
| J64106 | N-Acetyl-Arg-Glu-Lys-Arg-7-amido-4-trifluoromethylcoumarin [Ac-REK-R-AFC, Ac-Arg-Glu-Lys-Arg-AFC] C ₃₅ H ₅₁ F ₃ N ₁₅ O ₉ , F.W. 840.80, Solid | 10mg |
| J65204 | N-Acetyl-Asp-Glu-Val-Asp-al  [Ac-Asp-Glu-Val-Asp-CHO, Ac-DEVD-CHO] [169332-60-9], C ₂₀ H ₃₀ N ₄ O ₁₁ , F.W. 502.47, Powder, RTECS EK7643000, MDL MFCD00671412 | 1mg 5mg |
| J64134 | N-Acetyl-Asp-Glu-Val-Asp-7-amido-4-trifluoromethylcoumarin [Ac-DEVD-AFC] [201608-14-2], C ₃₀ H ₃₄ F ₃ N ₅ O ₁₃ , F.W. 729.61, Powder, MDL MFCD01310970 | 10mg |
| J65878 | N-Acetyl-Asp-Glu-Val-Asp p-nitroanilide [Ac-DEVD-pNA] [189950-66-1], C ₂₆ H ₃₄ N ₄ O ₁₃ , F.W. 638.58, Powder, MDL MFCD00792707 | 25mg |
| | Acetylbenzoylconine , see Aconitine, 98%, J60023, p. 207 N-Acetyl-2-benzyltryptamine , see Luzindole, 97%, J61915, p. 273 | |
| J61536 | O-Acetyl-L-carnitine hydrochloride [(R)-3-Acetoxy-4-(trimethylammonio)butyrate hydrochloride, L-Carnitine acetyl ester hydrochloride] [5080-50-2], C ₈ H ₁₇ NO ₄ ·HCl, F.W. 239.70, White powder, Merck 14,84, BRN 4340103, MDL MFCD00082230  H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): Weak cholinergic agonist | 5g 25g |
| | Acetyl ceramide , see N-Acetyl-D-sphingosine, 98%, J60534, p. 74 | |
| 43262 | Acetyl chloride, 99+%  [Ethanoyl chloride, Acetic chloride] [75-36-5], CH ₃ COCl, F.W. 78.50, Liquid, m.p. -112°, b.p. 50-52°, f.p. 4°(39°F), d. 1.104, n _D ²⁰ 1.3890, Merck 14,85, UN1717, EINECS 200-865-6, RTECS AO6390000, BRN 605303, MDL MFCD00000719, †   H:H225-H314-EUH014, P:P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a | 50ml 250ml 1L |
| L02168 | Acetylcholine chloride, 98+%  [2-Acetoxy-N,N,N-trimethylethanium chloride, 2-Acetyloxy-N,N,N-trimethylethanium chloride] [60-31-1], CH ₃ CO ₂ CH ₂ CH ₂ N(CH ₃) ₃ Cl, F.W. 181.66, m.p. 149-152°, Merck 14,87, EINECS 200-468-8, RTECS FZ9800000, BRN 3571875, MDL MFCD00011698, †  H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): Endogenous neurotransmitter at cholinergic synapses (Acetylcyclopentadienyl)cyclopentadienyliiron , see 1-Acetylferrocene, A13078, p. 72 | 25g 100g |

| Stock # | Description | Size |
|---------|--|---------------------------|
| A15409 | N-Acetyl-L-cysteine, 98+% [616-91-1], C ₃ H ₇ NO ₂ S, F.W. 163.20, m.p. 108-111°, [α] _D ²⁰ +5.3° (c=2 in water), Merck 14,88, Fieser 21,2, EINECS 210-498-3, RTECS HA1660000, BRN 1724426, MDL MFCD00004880, † Catalyzes the addition of ammonia to nitriles to form amidines in high yield: <i>Tetrahedron Lett.</i> , 40, 7067 (1999). | 25g |
| | | 100g |
| | | 500g |
| | Application(s): A mucolytic agent for isolation of mycobacteria from sputum | |
| J65262 | N4-Acetyl-5'-O-(4,4'-dimethoxytrityl)-2'-fluoro-2'-deoxycytidine, 98% [N4-Acetyl-2'-deoxy-5'-O-DMT-2'fluorocytidine, 2'-Fluoro-5'-O-DMT-N4-acetylcytidine] C ₃₂ H ₃₂ FN ₃ O ₇ , F.W. 589.61, Powder | 1g 5g |
| J65064 | N4-Acetyl-5'-O-(4,4'-dimethoxytrityl)-2'-fluoro-2'-deoxycytidine-3'-CE-phosphoramidite, 98% C ₄₁ H ₄₉ FN ₃ O ₈ P, F.W. 789.83, Powder ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| J65490 | N4-Acetyl-5'-O-(4,4'-dimethoxytrityl)-2'-O-methylcytidine, 98% C ₃₃ H ₃₅ N ₃ O ₈ , F.W. 601.64, Powder | 1g |
| J65996 | N4-Acetyl-5'-O-(4,4'-dimethoxytrityl)-2'-O-methylcytidine-3'-CE-phosphoramidite C ₄₂ H ₅₂ N ₃ O ₉ P, F.W. 801.86, Powder ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| J64680 | Acetyl α-Endorphin [Ac-Tyr-Gly-Gly-Phe-Met-Thr-Ser-Glu-Lys-Ser-Gln-Thr-Pro-Leu-Val-Thr] C ₇₉ H ₁₂₂ N ₁₈ O ₂₇ S, F.W. 1787.98, Solid | 1mg |
| J65577 | Acetylene-PEG4-biotin conjugate [15-[(R)-(+)-Biotinylamino]-4,7,10,13-tetraoxapentadec-1-yne] C ₂₁ H ₃₅ N ₃ O ₆ S, F.W. 457.59, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 25mg 100mg |
| J65593 | Acetylene-PEG4-carboxyrhodamine 6G conjugate [Acetylene-Fluor 525] C ₃₈ H ₄₆ N ₃ O ₆ , F.W. 672.79, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5mg |
| J64892 | Acetylene-PEG4-carboxyrhodamine 110 conjugate [Acetylene-Fluor 488] C ₂₂ H ₃₄ N ₃ O ₆ , F.W. 588.63, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5mg 25mg |
| J64523 | Acetylene-PEG4-carboxytetramethylrhodamine 110 conjugate [Acetylene-Fluor 545] C ₃₆ H ₄₂ N ₃ O ₆ , F.W. 644.73, Amorphous solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5mg 25mg |
| J64859 | Acetylene-PEG4-maleimide [3-(N-maleimidyl)-N-(3,6,9,12-tetraoxapentadec-14-yn-1-yl)propionamide] C ₂₀ H ₃₀ N ₂ O ₈ , F.W. 426.46, Viscous liquid or solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 25mg 100mg 500mg |
| J65924 | Acetylene-PEG4-sulforhodamine 101 conjugate [Acetylene-Fluor 585] C ₄₂ H ₅₀ N ₃ O ₁₀ S ₂ , F.W. 820.99, Amorphous solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5mg |
| J64948 | Acetylene-PEG4-sulforhodamine B conjugate [Acetylene-Fluor 568] C ₃₈ H ₅₀ N ₃ O ₁₁ S ₂ , F.W. 772.98, Amorphous solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5mg |
| A13078 | 1-Acetylferrocene, 97% [(Acetylcyclopentadienyl)cyclopentadienyliron, Ferrocenyl methyl ketone] [1271-55-2], C ₁₂ H ₁₂ FeO, F.W. 228.07, m.p. 79-86°, b.p. 160-163°/4mm, UN3467, EINECS 215-043-2, RTECS OB3700000, MDL MFCD00001432, †  ! H:H300+H311, P:P301+P310+P361+P302+P352-P321-P405-P501a A procedure for the conversion of methyl ketones to terminal acetylenes is exemplified by reaction with POC ₂ - DMF to give (2-formyl-1-chlorovinyl)ferrocene which, by elimination with NaOH, affords ethynylferrocene: <i>J. Organomet. Chem.</i> , 6, 173 (1966); <i>Org. Synth. Coll.</i> , 9, 411 (1998). | 5g 25g 100g 250g |
| J65915 | N4-Acetyl-2'-fluoro-2'-deoxycytidine, 98% C ₁₁ H ₁₄ FN ₃ O ₅ , F.W. 287.24, Powder | 1g |

| Stock # | Description | Size |
|---------|---|--|
| A13047 | N-Acetyl-D-glucosamine, 98+% ■ [7512-17-6], C ₈ H ₁₅ NO ₆ , F.W. 221.21, m.p. 213° dec., [α] _D ²⁰ +42° (c=2 in water), Merck 14,4458, EINECS 231-368-2, BRN 1727589, MDL MFCD00136044, † |  10g |
| | | 50g |
| | | 100g |
| B23621 | N-Acetyl-L-glutamic acid, 99% [Ac-Glu-OH] [1188-37-3], C ₇ H ₁₁ NO ₅ , F.W. 189.17, m.p. 194-199°, [α] _D ²⁰ -16.5° (c=1 in water), EINECS 214-708-4, RTECS LZ9725000, BRN 1727473, MDL MFCD00002802, † |  25g 100g |
| L06780 | N-α-Acetyl-L-glutamine, 99% [Ac-Gln-OH] [2490-97-3], C ₇ H ₁₂ N ₂ O ₅ , F.W. 188.18, m.p. ca 206° dec., [α] _D ²⁰ -12° (c=3 in water), Merck 14,25, EINECS 219-647-7, BRN 1727471, MDL MFCD00038159, † |  50g 250g |
| | | |
| B21887 | N-Acetylglycine, 99% [Acetamidooacetic acid, Aceturic acid] [543-24-8], CH ₂ CONHCH ₂ CO ₂ H, F.W. 117.10, m.p. ca 210° dec., Merck 14,80, EINECS 208-839-6, BRN 774114, MDL MFCD00004275, † | 100g |
| | | 500g |
| | | 2.5kg |
| J65657 | N-Acetyl-L-histidine monohydrate [Ac-His-OH] [39145-52-3], C ₈ H ₁₁ N ₃ O ₃ ·H ₂ O, F.W. 215.21 (197.09anhy), Powder, m.p. 163°, MDL MFCD00149320 | 1g |
| | | 5g |
| | | 25g |
| B22741 | DL-N-Acetylhomocysteine thiolactone, 99% [1195-16-0], C ₆ H ₉ NO ₃ S, F.W. 159.21, m.p. 109-111°, EINECS 214-793-8, RTECS AC8680000, MDL MFCD00005480, † |  5g 25g 100g |
| | | |
| | 3-Acetyl-4-hydroxy-6-methyl-2-pyrone sodium salt, see Sodium dehydroacetate, B21060, p. 345 | |
| J65828 | N-Acetyl-Ile-Glu-Pro-Asp-7-amino-4-trifluoromethylcoumarin [Ac-IEPD-AFC] C ₃₂ H ₃₈ N ₅ O ₁₁ F ₃ , F.W. 725.66, Powder, MDL MFCD03452821 | 10mg |
| J65683 | N-Acetyl-Ile-Glu-Thr-Asp-7-amido-4-trifluoromethylcoumarin [Ac-IGTD-AFC, Ac-Ile-Glu-Thr-Asp-AFC] C ₃₁ H ₃₈ F ₃ N ₅ O ₁₂ , F.W. 729.60, Solid | 10mg |
| J64258 | N-Acetyl-Ile-Glu-Thr-Asp-7-amino-4-trifluoromethyl coumarin [Ac-IETD-AFC] C ₃₁ H ₃₈ F ₃ N ₅ O ₁₂ , F.W. 729.65, Lyophilized powder | 5mg |
| L00137 | 1-Acetylimidazole, 98% ■ [2466-76-4], C ₄ H ₅ N ₂ O, F.W. 110.12, m.p. 98-104°, EINECS 219-577-7, RTECS NI3400000, BRN 108425, MDL MFCD00005287, † ! H: H315-H319-H335, P: P261-P305+P351-P338-P302+P352-P321-P405-P501a Mild acylating agent. Reactivity can be enhanced by quaternization with, e.g. benzyl bromide: <i>Chem. Pharm. Bull.</i> , 30 , 4242 (1982). Acylation of nitromethane salts leads to acylnitro compounds: <i>Synthesis</i> , 478 (1978). Application(s): Acetylates hydroxyl group of tyrosyl residues |  5g 25g 100g |
| | | |
| | | |
| | N-Acetyl-2-iodo-5-methoxytryptamine , see 2-Iodomelatonin, 98+%, J61498, p. 258 | |
| L13926 | N-Acetyl-L-leucine, 99% [Ac-Leu-OH] [1188-21-2], C ₈ H ₁₅ NO ₃ , F.W. 173.21, m.p. 177-179°, [α] _D ²⁰ -23° (c=5 in ethanol), EINECS 214-706-3, BRN 1724849, MDL MFCD00065131, † |  5g 25g |
| | | |
| J65269 | N-Acetyl-Leu-Glu-Glu-Asp-7-amido-4-trifluoromethylcoumarin [Ac-LEED-AFC] C ₃₂ H ₃₈ F ₃ N ₅ O ₁₃ , F.W. 757.66, Powder, MDL MFCD03452816 | 5mg |
| J64911 | N-Acetyl-Leu-Gly-His-Asp-7-amino-4-trifluoromethylcoumarin [Ac-LEHD-AFC] C ₃₃ H ₃₈ F ₃ N ₇ O ₁₁ , F.W. 765.69, Solid, MDL MFCD01862610 | 5mg |
| J65083 | N(α)-Acetyl-L-lysine, 99% [Ac-L-Lys-OH] [1946-82-3], C ₉ H ₁₆ N ₂ O ₃ , F.W. 188.20, Powder, m.p. 256-258° dec., EINECS 217-747-5, MDL MFCD00008233 | 1g |
| | | 5g |
| J64139 | N(ε)-Acetyl-L-lysine, 99% [L-Lys(Ac)-OH] [692-04-6], C ₉ H ₁₆ N ₂ O ₃ , F.W. 188.20, Powder, m.p. 250° dec., EINECS 211-725-9, MDL MFCD00002639 | 1g |
| | | 5g |
| J65515 | Acetyl-[Lys0,Nle3]-γ2-Melanocyte Stimulating Hormone, amide [Ac-Lys-Tyr-Val-Nle-Gly-His-Phe-Arg-Trp-Asp-Arg-Phe-Gly-NH ₂ , Acetyl-(Lys0,Nle3)-g2-MSH, amide] [237761-41-0], C ₈₃ H ₁₁₆ N ₂₄ O ₁₇ , F.W. 1721.96, Solid | 0.5mg 1mg |

| Stock # | Description | Size |
|---------|---|-----------------------|
| J64841 | N-Acetyl-Lys-Pro-Arg-7-amino-4-trifluoromethylcoumarin [Ac-KPR-AFC] C ₂₉ H ₃₉ F ₃ N ₃ O ₆ , F.W. 652.66, Solid, MDL MFCD03452898 | 10mg 25mg |
| L11167 | N-Acetyl-D-mannosamine monohydrate, 99% [7772-94-3], C ₈ H ₁₅ NO ₆ ·H ₂ O, F.W. 239.24 (221.22anhy), m.p. ca 130° dec., [α] _D ²⁰ +10.5° (c=1 in water), BRN 1346524, MDL MFCD00149493, † | 250mg 1g 5g |
| B21866 | N-Acetyl-DL-methionine, 99% [Ac-DL-Met-OH] [1115-47-5], C ₇ H ₁₃ NO ₃ S, F.W. 191.25, m.p. 113-117°, Merck 14,96, EINECS 214-224-3, RTECS PD0500000, BRN 1725554, MDL MFCD00008681, † | 50g 250g 1kg |
| | N-Acetyl-5-methoxytryptamine , see Melatonin, 99+%, J62452, p. 279 | |
| J65560 | N4-Acetyl-2'-O-methylcytidine, 98% C ₁₂ H ₁₇ N ₃ O ₆ , F.W. 299.28, Powder | 1g |
| | N-Acetylmuramly-L-alanyl-D-isoglutamine , see Adjuvant Peptide, J62385, p. 80 | |
| L13950 | N-(-)-Acetylneuraminic acid, 97% △ [5-Acetamido-3,5-dideoxy-D-glycero-D-galactononulosonic acid, NANA] [131-48-6], C ₁₁ H ₁₉ NO ₈ , F.W. 309.28, m.p. ca 185° dec., [α] _D ²⁰ -32° (c=1 in water), Merck 14,8484, EINECS 205-023-1, BRN 1716283, MDL MFCD00006620, † | 25mg 100mg |
| | 2-Acetyloxy-N,N,N-trimethylethanium chloride , see Acetylcholine chloride, L02168, p. 71 | |
| B23812 | N-Acetyl-L-phenylalanine, 99% [Ac-Phe-OH] [2018-61-3], C ₁₁ H ₁₃ NO ₃ , F.W. 207.23, m.p. 166-170°, [α] _D ²⁰ +40° (c=1 in methanol), EINECS 217-959-8, MDL MFCD00063158, † | 1g 5g 25g |
| A14446 | N-Acetyl-N'-phenylhydrazide, 98% [Acetic phenylhydrazide, 2-Phenylacetohydrazide] [114-83-0], C ₈ H ₉ NHNHCOCH ₃ , F.W. 150.18, m.p. 128-131°, UN2811, EINECS 204-055-3, RTECS AJ2900000, BRN 742880, MDL MFCD00008672, † | 25g 100g 500g |
| | H:H301-H315-H319-H335, P:P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a | |
| L14300 | N-Acetyl-L-proline, 99% [Ac-Pro-OH] [68-95-1], C ₅ H ₉ NO ₃ , F.W. 157.18, m.p. 117-118°, [α] _D ²⁰ -116° (c=1 in water), EINECS 200-698-9, BRN 83200, MDL MFCD00020837 | 1g 5g |
| A12688 | 2-Acetylpyridine, 98% [Methyl 2-pyridyl ketone] [1122-62-9], C ₇ H ₇ NO, F.W. 121.14, m.p. 8-10°, b.p. 189-190°, f.p. 76° (169°F), d. 1.082, n _D ²⁰ 1.5235, EINECS 214-355-6, RTECS OB5310000, BRN 107759, MDL MFCD00006303, † | 25g 100g 500g |
| | ! H:H315-H319, P:P280g-P305+P351+P338 | |
| A14246 | 3-Acetylpyridine, 98% [Methyl 3-pyridyl ketone] [350-03-8], C ₇ H ₇ NO, F.W. 121.14, m.p. 12-13°, b.p. 218-220°, f.p. 104° (219°F), d. 1.106, n _D ²⁰ 1.5350, Merck 14,6116, UN2810, EINECS 206-496-7, RTECS OB5425000, BRN 107751, MDL MFCD00006396, † | 25g 100g 500g |
| | H:H301-H315-H319, P:P280h-P305+P351+P338-P309-P310 | |
| A12488 | O-Acetylsalicylic acid, 99% [2-Acetoxybenzoic acid] [50-78-2], C ₉ H ₈ O ₄ , F.W. 180.15, m.p. 136-140°, f.p. 250° (482°F), d. 1.400, Merck 14,851, EINECS 200-064-1, RTECS VO0700000, BRN 779271, MDL MFCD00002430, † | 100g 500g 2.5kg |
| | H:H301-H315-H319-H335, P:P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a | |
| J64933 | O-Acetyl-L-serine hydrochloride [L-Ser(Ac)-OH] [66638-22-0], C ₅ H ₉ NO ₄ ·HCl, F.W. 183.59, Powder, MDL MFCD00060169 | 1g 5g |
| | Application(s): Substrate for cysteine synthase and β-substituted alanine synthase in higher plants | |
| J60534 | N-Acetyl-D-sphingosine, 98% [Acetyl ceramide, C2-Ceramide] [3102-57-6], C ₂₀ H ₃₉ NO ₃ , F.W. 341.53, Powder, m.p. 77-78°, MDL MFCD00153903 | 1mg 5mg 10mg |
| | Application(s): Inhibits cell proliferation and induces monocytic differentiation of HL-60 cells. Activates protein phosphatases | |

| Stock # | Description | Size |
|---------------|--|--|
| A16802 | S-Acetylthiocholine iodide, 98% ▲ ■ [1866-15-5], $\text{CH}_3\text{COSCH}_2\text{CH}_2\text{N}(\text{CH}_3)_3\text{I}$, F.W. 289.18, m.p. 205-209°, UN2811, EINECS 217-474-1, RTECS FZ9865000, BRN 3916578, MDL MFCD00011819, †  H: H301-H312-H315-H319-H335, P: P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a | 1g 5g 25g |
| J64597 | (R)-2-Acetylthio-3-phenylpropionic acid [D-2-Thioacetyl-3-phenylpropionic Acid] [57359-76-9], $\text{C}_{11}\text{H}_{12}\text{O}_3\text{S}$, F.W. 224.28, Oil  H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | 250mg 500mg |
| J65409 | (S)-2-Acetylthio-3-phenylpropionic acid [(S)- α -(Acetylthio)benzenepropanoic acid] [76932-17-7], $\text{C}_{11}\text{H}_{12}\text{O}_3\text{S}$, F.W. 224.28, Powder  H: H302-H318-H317, P: P261-P280-P305+P351+P338-P302+P352-P321-P501 | 1g 5g |
| J64780 | N-Acetyl-Trp-Glu-His-Asp-7-amido-4-trifluoromethylcoumarin [Ac-WEHD-AFC] $\text{C}_{38}\text{H}_{37}\text{F}_3\text{N}_5\text{O}_{11}$, F.W. 838.74, Powder, MDL MFCD01862607 | 1mg 5mg |
| J65062 | N-Acetyl-Trp-Val-Ala-Asp-7-amido-4-methylcoumarin ▲ ▽ [Ac-WVAD-AMC] $\text{C}_{35}\text{H}_{40}\text{N}_5\text{O}_8$, F.W. 688.73, Lyophilized powder | 5mg |
| J64096 | N-Acetyl-L-tryptophan, 99% [Ac-L-Trp-OH] [1218-34-4], $\text{C}_{13}\text{H}_{14}\text{N}_2\text{O}_3$, F.W. 246.30, Powder, m.p. 186°, EINECS 214-935-9, RTECS YN6160000, MDL MFCD00065976, † | 5g 25g 100g |
| J65646 | N-Acetyl-Tyr-Glu-Val-Asp-7-amido-4-methylcoumarin ▲ [Ac-YEVD-AMC, Caspase 1 (ICE) Substrate 1M fluorogenic] $\text{C}_{35}\text{H}_{41}\text{N}_5\text{O}_{12}$, F.W. 723.72, Powder | 5mg |
| A17307 | N-Acetyl-L-tyrosine, 99% [Ac-Tyr-OH] [537-55-3], $\text{C}_{11}\text{H}_{13}\text{NO}_4$, F.W. 223.23, m.p. 150-151°, $[\alpha]_D^{20} +58^\circ$ (c=5 in ethanol), EINECS 208-671-3, BRN 2697172, MDL MFCD00037190, † |  10g 50g 250g |
| J65213 | N-Acetyl-Tyr-Val-Ala-Asp-7-amido-4-trifluoromethylcoumarin [Ac-YVAD-AFC] $\text{C}_{33}\text{H}_{36}\text{N}_5\text{O}_{10}\text{F}_3$, F.W. 719.66, Powder | 10mg |
| J64931 | N-Acetyl-Tyr-Val-Ala-Asp-p-nitroanilide [Ac-YVAD-pNA] $\text{C}_{29}\text{H}_{36}\text{N}_6\text{O}_{10}$, F.W. 628.63, Powder | 25mg |
| J65806 | N-Acetyl-Val-Asp-Val-Ala-Asp-7-amido-4-trifluoromethylcoumarin [Ac-VDVAD-AFC] $\text{C}_{33}\text{H}_{41}\text{N}_6\text{O}_{12}\text{F}_3$, F.W. 770.71, Powder, MDL MFCD04037014 | 5mg |
| J65299 | N-Acetyl-Val-Asp-Val-Ala-Asp-p-nitroanilide [Ac-VDVAD-pNA, Caspase-2 substrate (chromogenic)] $\text{C}_{29}\text{H}_{41}\text{N}_7\text{O}_{12}$, F.W. 679.67, Lyophilized powder | 25mg |
| J65277 | N-Acetyl-Val-Glu-Ile-Asp-al [Ac-VEID-CHO, Ac-Val-Glu-Ile-Asp-CHO] $\text{C}_{22}\text{H}_{36}\text{N}_4\text{O}_9$, F.W. 500.54, Lyophilized powder, MDL MFCD01318861 | 5mg |
| J65287 | N-Acetyl-Val-Glu-Ile-Asp-7-amido-4-trifluoromethylcoumarin [Ac-VEID-AFC] $\text{C}_{32}\text{H}_{40}\text{N}_5\text{O}_{11}\text{F}_3$, F.W. 727.68, Powder, MDL MFCD01318833 | 10mg |
| J64992 | N-Acetyl-Val-Glu-Ile-Asp-p-nitroanilide [Ac-VEID-pNA] [189684-54-6], $\text{C}_{28}\text{H}_{40}\text{N}_6\text{O}_{11}$, F.W. 636.65, Lyophilized solid | 25mg |














ACIA, see Acivicin, 98+%, J63105, p. 76

Acid Black 1, see Amido Black 10B, A11374, p. 91








Acid Black 2, see Nigrosin water soluble, A18147, p. 302




Acid Blue 9, see Erioglaucine sodium salt, J61780, p. 210

Acid Blue 147, see Xylenecyanol FF, B21530, p. 394

| Stock # | Description | Size |
|---------------|---|---------------------|
| B22222 | Acid Fuchsin sodium salt [Acid Violet 19, C.I. 42685] [3244-88-0], C ₂₀ H ₇ N ₃ Na ₃ O ₆ S ₃ , F.W. 585.53, Merck 14,107, EINECS 221-816-5, RTECS DD4737000, BRN 4111656, MDL MFCD00013286, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 25g 100g 500g |
| |  | |
| | Acid Green 1 , see Naphthol Green B, A18268, p. 298 Acid Green 5 , see Light Green SF Yellowish, B23330, p. 270 Acid Orange 10 , see Orange G, Electrophoresis Grade, J62743, p. 308 Acid Red 51 , see Erythrosin B, certified, A14180, p. 210 Acid Red 87 , see Eosin Yellowish, B24535, p. 208 Acid Violet 19 , see Acid Fuchsin sodium salt, B22222, p. 76 Acid Yellow 1 , see Naphthol Yellow S, B20872, p. 298 Acid Yellow 23 , see Tartrazine, A17682, p. 358 Acid Yellow 73 , see Fluorescein disodium salt, J61549, p. 223 | |
| J63105 | Acivicin, 98+% [ACIA] [42228-92-2], C ₈ H ₇ ClN ₂ O ₃ , F.W. 178.57, Solid, m.p. 209-211°, UN2811, RTECS NY2103000, MDL MFCD00058450  H:H301, P:P264-P270-P301+P310-P321-P405-P501a | 10mg 25mg |
| | Application(s): Inhibits glutamine amidotransferases in purine and pyrimidine synthetic pathways. Tumor growth inhibitor | |
| A16010 | cis-Aconitic acid, tech. 90% ■ [(1Z)-Propene-1,2,3-tricarboxylic acid] [585-84-2], C ₆ H ₆ O ₆ , F.W. 174.11, m.p. 115-120°, EINECS 209-561-1, MDL MFCD00063184, † ! H:H315-H319-H335, P:P280g-P305+P351+P338 | 1g 5g 25g |
| |  | |
| B20087 | trans-Aconitic acid, 98% [1,2,3-Propenetricarboxylic acid] [4023-65-8], C ₆ H ₆ O ₆ , F.W. 174.11, m.p. ca 190° dec., Merck 14,117, EINECS 223-688-6, RTECS UD2380000, MDL MFCD00002721, † ! H:H315-H319-H335, P:P280g-P305+P351+P338 | 25g 100g 500g |
| |  | |
| J62056 | Aconitine, 98% [Acetylbenzoylaconine] [302-27-2], C ₃₄ H ₄₇ NO ₁₁ , F.W. 645.75, Crystalline powder, m.p. 194-202°, Merck 14,118, UN1544, EINECS 206-121-7, RTECS AR5960000, BRN 74608, MDL MFCD00082375  H:H300-H330, P:P301+P310-P304+P340-P320-P330-P405-P501a | 50mg 250mg |
| | Application(s): Opens tetrodotoxin-sensitive sodium channels. Useful for creating models of cardiac arrhythmia | |
| L01657 | Acridine, 98+% [260-94-6], C ₁₃ H ₉ N, F.W. 179.22, m.p. 107-111°, b.p. 346°, d. 1.005, Merck 14,122, UN2713, EINECS 205-971-6, RTECS AR7175000, BRN 120200, MDL MFCD00005025, †  !  H:H318-H302-H312-H332-H335-H315-H411, P:P280-P273-P305+P351+P338-P337+P313 | 5g 25g |
| |  | |
| J62634 | Acridine hydrochloride [17784-47-3], C ₁₃ H ₉ ClN, F.W. 215.68, Powder, EINECS 241-762-6, RTECS AR9322000, BRN 3697519, MDL MFCD00035149 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| | Application(s): Acid fast bacillus stain | |
| L13159 | Acridine Orange, dye content 55-65% ■ [3,6-Bis(dimethylamino)acridine hydrochloride zinc chloride double salt, C.I. 46005] [10127-02-3], C ₁₇ H ₂₀ Cl ₂ N ₂ Zn, F.W. 438.10, EINECS 233-353-6, RTECS AR7600000, BRN 3734978, MDL MFCD00081043  H:H341, P:P281-P201-P202-P308+P313-P405-P501a Biological stain. | 5g 25g |
| |  | |
| | Application(s): Fluorescent stain for proteins. An RNA polymerase inhibitor | |
| J60048 | Acriflavine hydrochloride [3,6-Diamino-10-methylacridinium chloride hydrochloride, Euflavine] [8063-24-9], Powder, Merck 14,123, UN3077, BRN 6265525, MDL MFCD00069039  !  H:H318-H302-H411, P:P280-P273-P305+P351+P338-P310-P301+P312-P501a | 10g 25g |
| | Application(s): An intercalating dye | |
| J62100 | Acrylamide, 30% soln, bisacrylamide free [79-06-1], Liquid, Merck 14,129, UN3426, EINECS 201-173-7, BRN 605349, MDL MFCD00008032, †  ! H:H340-H350-H372-H361f-H302-H312-H315-H319-H317, P:P260-P305+P351+P338-P302+P352-P321-P405-P501a | 500ml 1L |

| Stock # | Description | Size |
|---------|--|---------------------|
| J62480 | Acrylamide, 40% soln, bisacrylamide free [79-06-1], Liquid, Merck 14,129, UN3426, EINECS 201-173-7, BRN 605349, MDL MFCD00008032, † ☠ ! H:H340-H350-H372-H361f-H302-H312-H315-H319-H317, P:P260-P305+P351+P338-P302+P352-P321-P405-P501a | 500ml 1L |
| L15075 | Acrylamide, electrophoresis grade, 99+% ▲ ■ [Propenamide] [79-06-1], CH ₂ =CHCONH ₂ , F.W. 71.08, m.p. 82-85°, b.p. 125°/25mm, f.p. 138°(280°F), d. 1.322, Merck 14,129, UN2074, EINECS 201-173-7, RTECS AS3325000, BRN 605349, MDL MFCD00008032, † ☠ H:H301-H340-H350-H372-H361f-H312-H332-H315-H319-H317, P:P260-P301+P310-P305+P351+P338-P302+P352-P405-P501a | 25g 100g 500g |
| J60126 | Acrylamide/Bisacrylamide 19:1, 30% soln Liquid, UN3426, † ☠ ! H:H340-H350-H372-H361f-H302-H312-H315-H319-H317, P:P260-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): Premixed solution for preparing protein PAGE gels | 500ml 1L |
| J60909 | Acrylamide/Bisacrylamide 19:1, 40% soln Liquid, UN3426, † ☠ ! H:H340-H350-H372-H361f-H302-H312-H315-H319-H317, P:P260-P305+P351+P338-P302+P352-P321-P405-P501a | 500ml 1L |
| J60486 | Acrylamide/Bisacrylamide 19:1, powder Powder, UN2074, † ☠ H:H301-H340-H350-H372-H361f-H312-H332-H315-H319-H317, P:P260-P301+P310-P305+P351+P338-P302+P352-P405-P501a Application(s): Premixed powder for preparing protein PAGE gels | 100g 500g |
| J63279 | Acrylamide/Bisacrylamide 29:1, 30% soln Liquid, UN3426, † ☠ ! H:H340-H350-H372-H361f-H302-H312-H315-H319-H317, P:P260-P305+P351+P338-P302+P352-P321-P405-P501a | 500ml 1L |
| J63079 | Acrylamide/Bisacrylamide 29:1, 40% soln Liquid, UN3426, † ☠ ! H:H340-H350-H372-H361f-H302-H312-H315-H319-H317, P:P260-P305+P351+P338-P302+P352-P321-P405-P501a | 500ml 1L |
| J60824 | Acrylamide/Bisacrylamide 29:1, powder Powder, UN2074, † ☠ H:H301-H340-H350-H372-H361f-H312-H332-H315-H319-H317, P:P260-P301+P310-P305+P351+P338-P302+P352-P405-P501a Application(s): Premixed powder for preparing protein DNA gels | 100g 500g |
| J61505 | Acrylamide/Bisacrylamide 37.5:1, 30% soln Liquid, UN3426, † ☠ ! H:H340-H350-H372-H361f-H302-H312-H315-H319-H317, P:P260-P305+P351+P338-P302+P352-P321-P405-P501a | 500ml 1L |
| J60868 | Acrylamide/Bisacrylamide 37.5:1, 40% soln Liquid, UN3426, † ☠ ! H:H340-H350-H372-H361f-H302-H312-H315-H319-H317, P:P260-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): Premixed solution for preparing nucleic acid PAGE gels | 500ml 1L |
| J61220 | Acrylamide/Bisacrylamide 37.5:1, powder Powder, UN2074 ☠ H:H301-H340-H350-H372-H361f-H312-H332-H315-H319-H317, P:P260-P301+P310-P305+P351+P338-P302+P352-P405-P501a Application(s): Premixed powder for preparing nucleic acid PAGE gels | 100g 500g |
| J60412 | Acrylamide/Bisacrylamide 39:1, 30% soln Liquid, UN3426, † ☠ ! H:H340-H350-H372-H361f-H302-H312-H315-H319-H317, P:P260-P305+P351+P338-P302+P352-P321-P405-P501a | 500ml 1L |
| J63323 | Acrylamide/Bisacrylamide 39:1, 40% soln Liquid, UN3426, † ☠ ! H:H340-H350-H372-H361f-H302-H312-H315-H319-H317, P:P260-P305+P351+P338-P302+P352-P321-P405-P501a | 500ml 1L |
| | ACTH [1-10] , see Adrenocorticotrophic Hormone 1-10 (ACTH 1-10), J63084, p. 80 ACTH [1-13] , see Adrenocorticotrophic Hormone 1-13 (ACTH 1-13), J61247, p. 80 ACTH [1-14] , see Adrenocorticotrophic Hormone 1-14 (ACTH 1-14), J60060, p. 80 ACTH [1-4] Peptide , see Adrenocorticotrophic Hormone 1-4 (ACTH 1-4), J61985, p. 80 | |
| J61490 | Actin, from rabbit muscle [51005-14-2], Solution, MDL MFCD00130338 Application(s): Used in cell transport studies, and inhibits deoxyribonuclease I Actinomycin C1 , see Actinomycin D, J60148, p. 78 | 1mg |






| Stock # | Description | Size |
|--|--|--|
| J60148 | Actinomycin D [Dactinomycin, Actinomycin C1] [50-76-0], C ₂₆ H ₃₆ N ₁₀ O ₁₀ , F.W. 1255.40, Powder, m.p. 251-253°, Merck 14,2800, UN3462, EINECS 200-063-6, RTECS AU1575000, BRN 605235, MDL MFCD00005033  H: H300-H360-H351, P: P281-P301+P310-P321-P308+P313-P405-P501a | 5mg |
| Application(s): Inhibits nucleic acid synthesis and potently induces apoptosis | | |
| J64144 | Acycloguanosine, 98% [9-(2-Hydroxyethoxymethyl)guanine, Acyclovir] [59277-89-3], C ₈ H ₁₄ N ₆ O ₃ , F.W. 225.20, Powder, m.p. 256-260°, Merck 14,146, EINECS 261-685-1, RTECS UP0791400, MDL MFCD00057880 | 1g 5g 25g |
| Application(s): Inhibits cytomegalovirus replication; induces apoptosis | | |
| Acyl-neuraminyl hydrolase, see Neuraminidase, Clostridium perfringens, J63259, p. 300 | | |
| A15267 | ADA, 98+% [N-(2-Acetamido)iminodiacetic acid] [26239-55-4], H ₂ NCOCH ₂ N(CH ₂ CO ₂ H) ₂ , F.W. 190.16, m.p. ca 218° dec., Merck 14,147, EINECS 247-530-0, BRN 1787181, MDL MFCD00008031, † Biological buffer, pK _a = 6.9 at 20°: <i>Biochemistry</i> , 5, 467 (1966). | 25g 100g 500g |
| J60054 | ADA, 0.2M buffer soln., pH 6.0 [7415-22-7], Liquid | 100ml 250ml |
| J61259 | ADA, 0.2M buffer soln., pH 6.5 [7415-22-7], Liquid | 100ml 250ml |
| J61176 | ADA, 0.2M buffer soln., pH 7.0 [7415-22-7], Liquid | 100ml 250ml |
| J62424 | ADA, 0.2M buffer soln., pH 7.5 [7415-22-7], Liquid | 100ml 250ml |
| A12699 | 1-Adamantanamine hydrochloride, 99% [Amantadine hydrochloride, 1-Aminoadamantane hydrochloride] [665-66-7], C ₁₀ H ₁₇ N·HCl, F.W. 187.71, m.p. 360°, Merck 14,374, EINECS 211-560-2, RTECS AU4375000, BRN 4198854, MDL MFCD00074723, †  H: H361-H302, P: P281-P264-P301+P312-P308+P313-P405-P501a |  25g 100g 500g |
| Application(s): Antiviral drug that inhibits ion channels of influenza and disrupts T-cell development | | |
| 7-ADCA, see 7-Aminodesacetoxycephalosporanic acid, L03417, p. 93 | | |
| A14906 | Adenine, 99% [6-Aminopurine] [73-24-5], C ₅ H ₄ N ₆ , F.W. 135.13, m.p. >360° dec., Merck 14,152, UN2811, EINECS 200-796-1, RTECS AU6125000, BRN 5777, MDL MFCD00041790, † ! H: H302, P: P264-P270-P301+P312-P330-P501a |  25g 50g 250g 500g |
| Adenine deoxyriboside, see 2'-Deoxyadenosine, 99%, J63886, p. 177 | | |
| Adenine hemisulfate, see Adenine sulfate, A16964, p. 78 | | |
| A17622 | Adenine hydrochloride, 98+% , cont. up to ca 5% water [6-Aminopurine hydrochloride] [2922-28-3], C ₅ H ₅ N ₅ ·HCl, F.W. 171.59, m.p. ca 290° dec., EINECS 220-867-0, BRN 4009585, MDL MFCD00150864, † ! H: H302, P: P264-P270-P301+P312-P330-P501a |  5g 100g |
| A16964 | Adenine sulfate, 98+% ■ [Adenine hemisulfate, 6-Aminopurine sulfate] [321-30-2], C ₁₀ H ₁₀ N ₁₀ ·H ₂ SO ₄ , F.W. 368.34, m.p. ca 210° dec., Merck 14,152, EINECS 206-286-5, RTECS AU7140000, BRN 3820263, MDL MFCD00213655, † ! H: H302, P: P280h |  10g 50g |
| A10781 | Adenosine, 99% [58-61-7], C ₁₀ H ₁₃ N ₅ O ₄ , F.W. 267.25, m.p. 234-237°, [α] _D ²⁰ -70° (c=2 in 5% NaOH), Merck 14,153, EINECS 200-389-9, RTECS AU7175000, BRN 93029, MDL MFCD00005752, † |  10g 50g 250g |
| J60558 | Adenosine-2',3'-cyclic monophosphate sodium salt, 98% [37063-35-7], C ₁₀ H ₁₁ N ₅ NaO ₆ P, F.W. 351.19, Powder, m.p. 241-243°, EINECS 253-328-3, MDL MFCD00005757 | 100mg 250mg 500mg |


| Stock # | Description | Size |
|---------|---|--------------------|
| J62174 | Adenosine-3',5'-cyclic monophosphate sodium salt, 99% [3',5'-Cyclic AMP.Na] [37839-81-9], C ₁₀ H ₁₁ N ₅ NaO ₆ P, F.W. 351.19, Crystalline powder, BRN 54612, MDL MFCD00069736 | 250mg 1g 5g |
| | Adenosine 3',5'-cyclophosphate , see Adenosine-3',5'-monophosphoric acid free acid, 98%, J60936, p. 79 | |
| J60672 | Adenosine-5'-diphosphate monopotassium salt dihydrate, 99% [5'-ADP-K] [72696-48-1], C ₁₀ H ₁₄ KN ₅ O ₁₀ P ₂ ·2H ₂ O, F.W. 501.33 (465.29anhy), Crystalline powder, MDL MFCD00066472 | 1g 5g |
| L14029 | Adenosine-5'-diphosphate disodium salt, 97% (dry wt.), water 7% max. [5'-ADP-Na2] [16178-48-6], C ₁₀ H ₁₃ N ₅ Na ₂ O ₁₀ P ₂ , F.W. 471.17, [α] _D ²⁰ -30° (c=0.5 in 0.5M Na ₂ HPO ₄), EINECS 240-314-7, BRN 3645656, MDL MFCD00066635, † | 250mg 1g |
| |  | |
| J64497 | Adenosine-5'- diphosphate trilitium salt, 98% [5'-ADP] [31008-64-7], C ₁₀ H ₁₂ N ₅ O ₁₀ P ₂ Li ₃ , F.W. 445.00, Powder, MDL MFCD00065469 | 1g 5g 25g |
| J61643 | Adenosine-5'-monophosphate disodium salt [5'AMP.Na] [4578-31-8], C ₁₀ H ₁₂ N ₅ NaO ₇ P, F.W. 391.20, Powder, Merck 14,158, EINECS 224-961-2, RTECS AU7481600, BRN 3586732, MDL MFCD00065023 | 5g 25g 100g |
| J60936 | Adenosine-3',5'-monophosphoric acid, 98% [3',5'-Cyclic AMP, Adenosine 3',5'-cyclophosphate] [60-92-4], C ₁₀ H ₁₂ N ₅ O ₆ P, F.W. 329.21, Crystalline powder, m.p. 260° dec., Merck 14,2708, EINECS 200-492-9, RTECS AU7357600, BRN 52645, MDL MFCD00005845, † | 1g 5g |
| L14051 | Adenosine-5'-monophosphoric acid, 99% (dry wt.), water <6% [Adenylic acid, 5'-AMP] [61-19-8], C ₁₀ H ₁₄ N ₅ O ₆ P, F.W. 347.22, m.p. ca 190° dec., [α] _D ²⁰ -47° (c=2 in 2% NaOH), Merck 14,158, EINECS 200-500-0, RTECS AU7480500, BRN 5205540, MDL MFCD00149360, † | 1g 5g |
| |  | |
| J61125 | Adenosine-5'-triphosphate disodium salt hydrate, 98% ▲ ■ [ATP disodium salt hydrate] [34369-07-8], C ₁₀ H ₁₄ N ₅ Na ₂ O ₁₃ P ₃ , F.W. 551.15, Powder, Merck 14,155, EINECS 213-579-1, † H: H303, P: P312 | 5g 10g 25g |
| J60336 | Adenosine-5'-triphosphate disodium salt hydrate, ultrapure, 98% ▲ ■ [ATP disodium salt hydrate] [34369-07-8], C ₁₀ H ₁₄ N ₅ Na ₂ P ₃ ·xH ₂ O, F.W. 605.19 (551.15anhy), Powder, Merck 14,155, EINECS 213-579-1, † H: H303, P: P312 | 25g 100g |
| L14522 | Adenosine-5'-triphosphate disodium salt hydrate, 99+%, water <10% [5'-ATP-Na2] [34369-07-8], C ₁₀ H ₁₄ N ₅ Na ₂ O ₁₃ P ₃ ·xH ₂ O, F.W. 551.15(anhy), [α] _D ²⁰ -19° (c=3 in water), Merck 14,155, EINECS 213-579-1, RTECS AU7417000, BRN 3585462, MDL MFCD00150755, † H: H303, P: P312 | 1g 5g |
| |  | |
| | Adenylic acid , see Adenosine-5'-monophosphoric acid, L14051, p. 79 | |
| J64042 | Adenylyl Cyclase Type V Inhibitor, NKY80 ▲ [NKY80, 2-Amino-7-(furan-2-yl)-7,8-dihydroquinazolin-5(6H)-one] [299442-43-6], C ₁₂ H ₁₁ N ₃ O ₂ , F.W. 229.23, Powder, MDL MFCD02026323 ! H: H302, P: P264-P270-P301+P312-P330-P501 | 5mg |
| A13705 | Adipic acid, 99% [Butane-1,4-dicarboxylic acid, Hexanedioic acid] [124-04-9], HOOC(CH ₂) ₄ COOH, F.W. 146.14, m.p. 151-155°, b.p. ca 205°/3mm, f.p. 196°(384°F), d. 1.360, Merck 14,162, Fieser 1,15, EINECS 204-673-3, RTECS AU8400000, BRN 1209788, MDL MFCD00004420, † ! H: H319 | 1kg 5kg 25kg |
| | Adipic acid dimethyl ester , see Dimethyl adipate, B21174, p. 196 | |

| Stock # | Description | Size |
|---------|--|---------------------|
| A13168 | Adipoyl chloride, 98% <input checked="" type="checkbox"/> [1,4-Butanedicarbonyl chloride, Hexanedioyl dichloride] [111-50-2], ClCO(CH ₂) ₄ COCl, F.W. 183.03, b.p. 105-107°/2mm, f.p. >110°(230°F), d. 1.255, n _D ²⁰ 1.4705, UN3265, EINECS 203-876-4, BRN 507709, MDL MFCD00000759, † | 25g 100g 500g |
| J62385 | Adjuvant Peptide [N-Acetylmuramyl-L-alanyl-D-isoglutamine, Muramyl dipeptide] [53678-77-6], C ₁₉ H ₃₂ N ₂ O ₁₁ ·xH ₂ O, F.W. 492.48(anhy), Powder, Merck 14,6305, EINECS 258-696-9, RTECS MA2275260, BRN 4220745, MDL MFCD00077638 Application(s): Used in immunization to replace more complex proteins. Inhibits the HIV replication in CD4+ H9 lymphocytes | 1mg 5mg |
| L03253 | Adonitol, 99% <input checked="" type="checkbox"/> [Ribitol] [488-81-3], C ₅ H ₁₂ O ₅ , F.W. 152.15, m.p. 102-104°, Merck 14,168, EINECS 207-685-7, RTECS VJ0800000, BRN 1720524, MDL MFCD00064291, † | 5g 25g |
| | 5'-ADP-K , see Adenosine-5'-diphosphate monopotassium salt, 99%, J60672, p. 79 5'-ADP-Na2 , see Adenosine-5'-diphosphate disodium salt, L14029, p. 79 | |
| L04911 | L-Adrenaline, 98+% <input checked="" type="checkbox"/> <input checked="" type="checkbox"/> [L-Epinephrine] [51-43-4], C ₉ H ₁₃ NO ₃ , F.W. 183.20, m.p. 216-219°, [α] _D ²⁰ -52° (c=1 in 0.6N HCl), Merck 14,3619, UN2811, EINECS 200-098-7, RTECS DO2625000, BRN 2368277, MDL MFCD00002204, † | 5g 25g |
| J63005 | DL-Adrenaline <input checked="" type="checkbox"/> [DL-Epinephrine, 3,4-Dihydroxy-a-(methylaminomethyl)benzyl alcohol] [329-65-7], (HO) ₂ C ₆ H ₃ CH(CH ₂ NHCH ₃)OH, F.W. 183.20, Powder, m.p. 197° dec., Merck 14,3619, UN2811, EINECS 206-347-6, RTECS DO2975000, MDL MFCD00063027 Application(s): A hormone and neurotransmitter | 1g 5g 25g |
| J64615 | β-Adrenergic Receptor Kinase1 Inhibitor <input checked="" type="checkbox"/> [β-ARK1 Inhibitor, GRK2 Inhibitor] [24269-96-3], C ₁₂ H ₉ NO ₆ , F.W. 263.20, Powder | 5mg |
| J61985 | Adrenocorticotrophic Hormone (1-4) [ACTH [1-4] Peptide, H-Ser-Tyr-Ser-Met-OH] [19405-50-6], C ₂₀ H ₃₀ N ₄ O ₆ S, F.W. 486.55, Powder | 1mg 2mg 5mg |
| J63084 | Adrenocorticotrophic Hormone (1-10) [ACTH [1-10], Ser-Tyr-Ser-Met-Glu-His-Phe-Arg-Trp-Gly] [2791-05-1], C ₅₉ H ₇₈ N ₁₆ O ₁₆ S ₁ , F.W. 1299.40, Powder | 1mg 5mg |
| J61247 | Adrenocorticotrophic Hormone (1-13) [ACTH [1-13], H-Ser-Tyr-Ser-Met-Glu-His-Phe-Arg-Trp-Gly-Lys-Pro-Val-OH] [22006-64-0], C ₇₃ H ₁₀₈ N ₂₀ O ₁₉ S, F.W. 1623.85, Powder | 0.5mg 1mg 5mg |
| J60060 | Adrenocorticotrophic Hormone (1-14) [ACTH [1-14], H-Ser-Tyr-Ser-Met-Glu-His-Phe-Arg-Trp-Gly-Lys-Pro-Val-Gly-OH] [25696-21-3], C ₇₇ H ₁₀₈ N ₂₁ O ₂₀ S, F.W. 1680.90, Powder | 1mg 2mg 5mg |
| J65775 | Adrenocorticotrophic Hormone (1-39), guinea pig [ACTH (1-39), guinea pig] [111524-36-8], C ₂₀₈ H ₃₀₈ N ₅₆ O ₅₈ S, F.W. 4529.04, Solid | 1mg |
| J64495 | Adrenocorticotrophic Hormone (12-39), rat [ACTH (12-39), rat, Pro-Val-Gly-Lys-Lys-Arg-Arg-Pro-Val-Lys-Val-Tyr-Pro-Asn-Val-Ala-Glu-Asn-Glu-Ser-Ala-Glu-Ala-Phe-Pro-Leu-Glu-Phe] C ₁₄₅ H ₂₂₇ N ₃₉ O ₄₁ , F.W. 3172.58, Solid | 1mg |
| J64410 | Adrenocorticotrophic Hormone (34-39) [ACTH (34-39), Ala-Phe-Pro-Leu-Glu-Phe] C ₃₇ H ₅₀ N ₆ O ₉ , F.W. 722.83, Solid | 10mg 25mg |
| J65314 | Tyr-Adrenocorticotrophic Hormone (4-9) [Tyr-ACTH (4-9), Tyr-Met-Glu-His-Phe-Arg-Trp] [129813-57-6], C ₅₁ H ₆₈ N ₁₃ O ₁₁ S, F.W. 1068.2, Solid, MDL MFCD00133037 | 1mg 5mg |
| J64183 | Tyr-Adrenocorticotrophic Hormone (4-10) [Tyr-ACTH (4-10), Tyr-Met-Glu-His-Phe-Arg-Trp-Gly] [131374-17-9], C ₅₃ H ₆₈ N ₁₄ O ₁₂ S, F.W. 1125.26, Solid | 1mg 5mg |

AEBSF, see 4-(2-Aminoethyl)benzenesulfonyl fluoride hydrochloride, H26473, p. 94

| Stock # | Description | Size |
|---------|---|-----------------------|
| | Aerosporin , see Polymixin B sulfate, J63074, p. 325 AET , see S-(2-Aminoethyl)isothioureia dihydrobromide, L14232, p. 94 | |
| J62625 | AG-879, 99% [Tyrphostin AG 879, α -Cyano-(3,5-di-t-butyl-4-hydroxy)thiocinnamide] [148741-30-4], C ₁₈ H ₂₄ N ₂ O ₅ , F.W. 316.50, Solid, MDL MFCD00236450 | 5mg 25mg |
| | Application(s): Inhibits the tyrosine kinase activity of the nerve growth factor receptor (TrkA; pp140trk) and heregulin receptor erbB-2 (HER-2) | |
| | AG-1749 , see Lansoprazole, 98+%, J62008, p. 266 | |
| A10752 | Agar powder [9002-18-0], (C ₁₂ H ₁₈ O ₉) _x , Merck 14,184, EINECS 232-658-1, RTECS AW7950000, MDL MFCD00081288, † For gel preparation. | 100g 500g 2.5kg |
| H26724 | Agar, plant cell culture tested ■ ■ [9002-18-0], Merck 14,184, EINECS 232-658-1, RTECS AW7950000, MDL MFCD00081288, † | 100g 500g 2.5kg |
| J60299 | Agarose, high EEO [9012-36-6], Powder, EINECS 232-731-8, MDL MFCD00081294, † | 50g 100g 250g |
| | Application(s): For electrophoresis of serum proteins, immuno electrophoresis and counter immuno electrophoresis | |
| J62714 | Agarose, high melting temperature, high resolution [9012-36-6], Powder, EINECS 232-731-8, MDL MFCD00081294, † | 25g 100g |
| | Application(s): For resolution of small fragments | |
| J61123 | Agarose, high melting temperature, medium resolution [9012-36-6], Powder, EINECS 232-731-8, MDL MFCD00081294, † | 25g 100g 500g |
| | Application(s): For standard DNA applications | |
| H32601 | Agarose beads 4% B [9012-36-6], b.p. 100°, f.p. 38°(100°F), d. 1.040, UN1170, MDL MFCD00081294, † 🔥 H:H226, P:P210-P241-P280-P240-P303+P361+P353-P501a | 1L |
| H32305 | Agarose beads 4% B-CL (Cross-linked) [61970-08-9], b.p. 100°, f.p. 38°(100°F), d. 1.040, UN1170, MDL MFCD00081294 🔥 H:H226, P:P210-P241-P280-P240-P303+P361+P353-P501a | 1L |
| H32491 | Agarose beads 6% B [9012-36-6], b.p. 100°, f.p. 38°(100°F), d. 1.040, UN1170, MDL MFCD00081294, † 🔥 H:H226, P:P210-P241-P280-P240-P303+P361+P353-P501a | 1L |
| H32568 | Agarose beads 6% B-CL (Cross-linked) [62610-50-8], b.p. 100°, f.p. 38°(100°F), d. 1.040, UN1170, MDL MFCD00081294 🔥 H:H226, P:P210-P241-P280-P240-P303+P361+P353-P501a | 1L |
| H26855 | Agarose D1-LE, molecular biology grade ■ [9012-36-6], EINECS 232-731-8, MDL MFCD00081294, † A general-purpose agarose for molecular biology applications. It has a low electroendosmosis(EEO) and high electrophoresis mobility. Suitable for analytical and preparative nucleic acid electrophoresis, blotting and protein electrophoresis. | 25g 100g 500g |
| J62157 | Agarose gel loading dye (6X), alkaline Liquid, Note: 300mM sodium hydroxide, 6mM EDTA, 0.25% bromocresol green, 0.25% xylene cyanol FF and 18% Ficoll | 10ml 25ml |
| J62800 | Agarose gel loading dye (6X), Ficoll based Viscous liquid, Note: 0.25% bromophenol blue, 0.25% xylene cyanol FF and 15% Ficoll in water, † | 10ml 25ml |
| J63869 | Agarose gel loading dye (6X), glycerol based Liquid, Note: 0.25% bromophenol blue, 0.25% xylene cyanol FF and 40% glycerol, † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 25ml 50ml |
| J60933 | Agarose gel loading dye (6X) glycerol based, Xylene Cyanol FF free Liquid, Note: No Xylene cyanol FF. Contains 0.25% bromophenol blue, 30% glycerol., † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 25ml 50ml |
| J63429 | Agarose gel loading dye (6X), glycerol based, bromophenol free Liquid, Note: No Bromophenol blue. Contains 0.25% xylene cyanol FF and 30% glycerol. | 25ml 50ml |
| J60333 | Agarose gel loading dye (6X), sucrose based Liquid, Note: 0.25% Bromophenol blue, 0.25% xylene cyanol FF, 40% sSucrose (w/v)., † | 25ml 50ml |

| Stock # | Description | Size |
|---------|--|--|
| H26417 | Agarose LM, low melt, for recovery of samples after separation ■ ■ [9012-36-6], EINECS 232-731-8, MDL MFCD00081294, † Low melting temperature agarose which has a high resolving capacity for DNA fragments smaller than 1000 bp, especially PCR products ranging from 200-800 bp. Ideal for preparative electrophoresis. | 5g 25g 100g |
| A16693 | Agarose ME, for electrophoresis of macromolecules [9012-36-6], EINECS 232-731-8, MDL MFCD00081294, Note: Gel point 36°, † | 5g 25g |
| H26738 | Agarose MS8, molecular sieve grade, for small DNA fragments ■ ■ [9012-36-6], EINECS 232-731-8, MDL MFCD00081294, † For molecular screening that improves resolution of small DNA fragments and polymerase chain reaction (PCR) products. Enhanced visibility and high gel strength. | 25g 100g |
| J65119 | Akt Inhibitor X ▲ ■ [10-(4-(N-Diethylamino)butyl)-2-chlorophenoxazine hydrochloride, 4-(2-Chloro-10H-phenoxazin-10-yl)-N,N-diethylbutan-1-amine hydrochloride] [925681-41-0], C ₂₆ H ₂₅ ClN ₂ O.HCl, F.W. 381.34, Powder ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5mg |
| | H-β-Ala-OH , see β-Alanine, Cell Culture Reagent, J63435, p. 82 H-Ala-OH , see L-Alanine, Cell Culture Reagent, J60279, p. 82 | |
| J63829 | Alamethicin [U-22324] [59588-86-2], C ₂₂ H ₁₅₀ N ₂₂ O ₂₅ , F.W. 1964.40, Powder, m.p. 267-270°, UN3462, RTECS AY1900000  H:H301, P:P264-P270-P301+P310-P321-P405-P501a | 1mg 5mg |
| | Application(s): A channel-forming ionophore that activates membrane enzymes | |
| A16665 | β-Alanine, 98% [H-β-Ala-OH, 3-Aminopropionic acid] [107-95-9], H ₂ NCH ₂ CH ₂ CO ₂ H, F.W. 89.09, m.p. ca 205° dec., d. 1.437, Merck 14,205, Fieser 1,16 5,6 6, 10 17,3, EINECS 203-536-5, RTECS UA2369200, BRN 906793, MDL MFCD00008200, † Effective catalyst for the Knoevenagel condensation, for example of ethyl cyanoacetate with 2-butanone: <i>Org. Synth. Coll.</i> , 4 , 93 (1963), and of malononitrile with various substrates, where stronger bases would cause self-condensation of the nitrile: <i>J. Org. Chem.</i> , 38 , 1512 (1973); <i>Synthesis</i> , 669 (1974). | 250g 1kg 5kg |
| J63435 | β-Alanine, Cell Culture Reagent [H-β-Ala-OH, 3-Aminopropionic acid] [107-95-9], H ₂ NCH ₂ CH ₂ CO ₂ H, F.W. 89.09, Powder, m.p. ca 205° dec., d. 1.437, Merck 14,205, EINECS 203-536-5, RTECS UA2369200, BRN 906793, MDL MFCD00008200, † | 250g 500g 1kg |
| A12230 | DL-Alanine, 99% [H-DL-Ala-OH, DL-2-Aminopropionic acid] [302-72-7], C ₃ H ₇ NO ₂ , F.W. 89.09, m.p. ca 292° dec., d. 1.42, Merck 14,204, EINECS 206-126-4, RTECS AY2980000, BRN 635807, MDL MFCD00064408, † |  250g 1kg 5kg |
| A10231 | D-Alanine, 99% [H-D-Ala-OH, D-2-Aminopropionic acid] [338-69-2], C ₃ H ₇ NO ₂ , F.W. 89.09, m.p. ca 295° dec., [α] _D ²⁰ -14° (c=5 in 5N HCl), Merck 14,204, EINECS 206-418-1, BRN 1720249, MDL MFCD00008077, † |  5g 25g 100g |
| A15804 | L-Alanine, 99% [H-Ala-OH, L-2-Aminopropionic acid] [56-41-7], C ₃ H ₇ NO ₂ , F.W. 89.09, m.p. ca 295° dec., d. 1.432, [α] _D ²⁰ +14° (c=5 in 5N HCl), Merck 14,204, Fieser 17,2, EINECS 200-273-8, RTECS AY2990000, BRN 1720248, MDL MFCD00064410, † α-Amino acids can be converted to the corresponding α-chloro acids with a high degree of retention of configuration, by diazotization in the presence of HCl: <i>J. Am. Chem. Soc.</i> , 76 , 6054 (1954). The intermediate is thought to be a rigid oxiranone which prevents racemization. For an improved technique and list of examples, see: <i>Org. Synth. Coll.</i> , 8 , 119 (1993): |  25g 100g 500g |
| |  | |
| J60279 | L-Alanine, Cell Culture Reagent [H-Ala-OH, L-2-Aminopropionic acid] [56-41-7], C ₃ H ₇ NO ₂ , F.W. 89.09, Powder, m.p. ca 295° dec., Merck 14,204, EINECS 200-273-8, RTECS AY2990000, BRN 1720248, MDL MFCD00064410, † | 50g 100g 500g |
| | DL-Alanine 2-(4-chlorophenyl)-1,1-dimethylethyl ester hydrochloride , see Alaproclate hydrochloride, 96%, J62741, p. 82 L-Alanine: 2-oxoglutarate aminotransferase , see Glutamic pyruvic transaminase, porcine heart, J62109, p. 235 D-Alaninol , see (R)-(-)-2-Amino-1-propanol, L11030, p. 99 L-Alaninol , see (S)-(+)-2-Amino-1-propanol, B24916, p. 99 | |
| J62741 | Alaproclate hydrochloride, 96% [DL-Alanine 2-(4-chlorophenyl)-1,1-dimethylethyl ester hydrochloride] [60719-83-7], C ₁₃ H ₁₈ ClNO ₂ ·HCl, F.W. 292.21, Crystalline powder, RTECS AY4397300, MDL MFCD00153761 ! H:H302-H312-H332, P:P261-P280-P302+P352-P304+P340-P322-P501 | 25mg |
| | Application(s): Powerful, selective serotonin uptake inhibitor | |

| Stock # | Description | Size |
|---------|--|------|
| H25925 | Albendazole, 98+% [Methyl 5-n-propylthio-2-benzimidazolecarbamate] [54965-21-8], C ₁₂ H ₁₅ N ₃ O ₂ S, F.W. 265.34, m.p. 208-210°, Merck 14,210, EINECS 259-414-7, MDL MFCD00083232 | 10g |
| |  | 50g |
| | ↓ ! H:H360-H302, P:P281-P264-P301+P312-P308+P313-P405-P501a | 100g |
| J65097 | Albumin, Bovine, Cohn Fraction V, 98%, Cell Culture Grade, Low Endotoxin [Bovine serum albumin, BSA] [9048-46-8], Lyophilized powder, EINECS 232-936-2, MDL MFCD00130384, † | 10g |
| | | 50g |
| | | 100g |
| | | 250g |
| J64682 | Albumin, Bovine, Cohn Fraction V, 98%, Fatty Acid Free, pH 5.2 [Bovine serum albumin, BSA] [9048-46-8], Lyophilized powder, EINECS 232-936-2, MDL MFCD00130384, † | 1kg |
| | | 50g |
| | | 100g |
| | | 250g |
| J64944 | Albumin, Bovine, Cohn Fraction V, 98%, Fatty Acid Free, pH 7.0 [Bovine serum albumin, BSA] [9048-46-8], Lyophilized powder, EINECS 232-936-2, MDL MFCD00130384, † | 500g |
| | | 1kg |
| | | 50g |
| | | 100g |
| J65973 | Albumin, Bovine, Cohn Fraction V, 98%, Immunoassay Grade, protease and enzyme-free, pH 5.2 [Bovine serum albumin, BSA] [9048-46-8], Lyophilized powder, EINECS 232-936-2, MDL MFCD00130384, † | 250g |
| | | 500g |
| | | 1kg |
| | | 50g |
| J65731 | Albumin, Bovine, Cohn Fraction V, 98%, Immunoassay Grade, protease and enzyme-free, pH 7.0 [Bovine serum albumin, BSA] [9048-46-8], Lyophilized powder, EINECS 232-936-2, MDL MFCD00130384, † | 100g |
| | | 250g |
| | | 500g |
| | | 1kg |
| J65525 | Albumin, Bovine, Cohn Fraction V, 98%, Low Fatty Acid, pH 5.2 [Bovine serum albumin, BSA] [9048-46-8], Lyophilized powder, EINECS 232-936-2, MDL MFCD00130384, † | 50g |
| | | 100g |
| | | 250g |
| | | 500g |
| J65969 | Albumin, Bovine, Cohn Fraction V, 98%, Low Fatty Acid, pH 7.0 [Bovine serum albumin, BSA] [9048-46-8], Lyophilized powder, EINECS 232-936-2, MDL MFCD00130384, † | 1kg |
| | | 50g |
| | | 100g |
| | | 250g |
| J65399 | Albumin, Bovine, Cohn Fraction V, Reagent Grade, pH 5.2 [Bovine serum albumin, BSA] [9048-46-8], Lyophilized powder, EINECS 232-936-2, MDL MFCD00130384, † | 500g |
| | | 1kg |
| | | 50g |
| | | 100g |
| J65966 | Albumin, Bovine, Cohn Fraction V, Reagent Grade, pH 7.0 [Bovine serum albumin, BSA] [9048-46-8], Lyophilized powder, EINECS 232-936-2, MDL MFCD00130384, † | 250g |
| | | 500g |
| | | 1kg |
| | | 50g |
| J64100 | Albumin, Bovine, Fraction V, 98%, Reagent Grade, pH 7.0 [Bovine serum albumin, BSA] [9048-46-8], Lyophilized powder, EINECS 232-936-2, MDL MFCD00130384, † | 100g |
| | | 50g |
| | | 100g |
| | | 250g |
| | | 500g |
| | | 1kg |

| Stock # | Description | Size |
|---------|---|-------|
| J65855 | Albumin, Bovine, Fraction V, 96%, Standard Grade, pH 5.2 [Bovine serum albumin, BSA] [9048-46-8], Lyophilized powder, EINECS 232-936-2, MDL MFCD00130384, † | 10g |
| | | 50g |
| | | 100g |
| | | 250g |
| | | 1kg |
| J64655 | Albumin, Bovine, Fraction V, 97%, Standard Grade, pH 7.0 [Bovine serum albumin, BSA] [9048-46-8], Lyophilized powder, EINECS 232-936-2, MDL MFCD00130384, † | 10g |
| | | 50g |
| | | 100g |
| | | 250g |
| | | 1kg |
| J65788 | Albumin, Bovine, Fraction V, 96%, Standard Grade, New Zealand origin, pH 7.0 [Bovine serum albumin, BSA] [9048-46-8], Lyophilized powder, EINECS 232-936-2, MDL MFCD00130384, † | 10g |
| | | 50g |
| | | 100g |
| | | 250g |
| | | 1kg |
| J65833 | Albumin, Bovine, Fraction V, 30% soln., Standard Grade, no preservative [Bovine serum albumin solution, BSA solution] [9048-46-8], Liquid, EINECS 232-936-2, MDL MFCD00130384, † | 100ml |
| | | 500ml |
| | | 1L |
| J65569 | Albumin, Bovine, Fraction V, 30% soln., Standard Grade, with azide as preservative [Bovine serum albumin solution, BSA solution] [9048-46-8], Liquid, EINECS 232-936-2, MDL MFCD00130384, † ! H:H302, P:P264-P270-P301+P312-P330-P501 | 100ml |
| | | 500ml |
| | | 1L |
| J65042 | Albumin, Bovine, Fraction V, 35% soln., Reagent Grade, Fatty Acid Free, no preservative [Bovine serum albumin solution, BSA solution] [9048-46-8], Liquid, EINECS 232-936-2, MDL MFCD00130384, † | 100ml |
| | | 500ml |
| | | 1L |
| J64728 | Albumin, Bovine, Fraction V, 35% soln., Reagent Grade, Fatty Acid Free, with azide as preservative [Bovine serum albumin solution, BSA solution] [9048-46-8], Liquid, EINECS 232-936-2, MDL MFCD00130384, † ! H:H302, P:P264-P270-P301+P312-P330-P501 | 100ml |
| | | 500ml |
| | | 1L |
| J64248 | Albumin, Bovine, Fraction V, 35% soln., Cell Culture Grade, no preservative [Bovine serum albumin solution, BSA solution] [9048-46-8], Liquid, EINECS 232-936-2, MDL MFCD00130384, † | 50ml |
| | | 100ml |
| J64101 | Albumin, Bovine, Fraction V, 35% soln., Cell Culture Grade, with azide as preservative [Bovine serum albumin solution, BSA solution] [9048-46-8], Liquid, EINECS 232-936-2, MDL MFCD00130384, † ! H:H302, P:P264-P270-P301+P312-P330-P501 | 50ml |
| | | 100ml |
| J65030 | Albumin, Bovine, Low Endotoxin, Cell Culture Grade, Chromatographically purified [Bovine Serum Albumin, BSA] [9048-46-8], F.W. 66kDa, Powder, EINECS 232-936-2, MDL MFCD00130384, † | 10g |
| | | 25g |
| | | 50g |
| | | 100g |
| J65400 | Albumin, Bovine, Low Fatty Acid, Chromatographically purified [Bovine Serum Albumin, BSA] [9048-46-8], F.W. 66kDa, Powder, EINECS 232-936-2, MDL MFCD00130384, † Application(s): Suitable for immunoassays. Reduced fatty acid content minimizes non-specific binding of antibodies | 10g |
| | | 25g |
| | | 50g |
| | | 100g |
| J65470 | Albumin, Bovine, Low IgG, Chromatographically purified [Bovine Serum Albumin, BSA] [9048-46-8], F.W. 66kDa, Powder, EINECS 232-936-2, MDL MFCD00130384, † Application(s): For immunoassays that require low IgG so as not to interfere with antibody-antigen binding | 10g |
| | | 25g |
| | | 50g |
| | | 100g |
| J64912 | Albumin, Bovine, Protease-free, Chromatographically purified [Bovine Serum Albumin, BSA] [9048-46-8], F.W. 66kDa, Powder, EINECS 232-936-2, MDL MFCD00130384, † Application(s): Suitable for immunoassay applications where protease activity would be undesirable | 25g |
| | | 100g |
| | | 500g |
| J65189 | Albumin, Bovine, RIA Grade, Chromatographically purified [Bovine Serum Albumin, BSA] [9048-46-8], F.W. 66kDa, Powder, EINECS 232-936-2, MDL MFCD00130384, † Application(s): For standard use in radioimmunoassays | 10g |
| | | 50g |
| | | 100g |

| Stock # | Description | Size |
|---------|---|--------------|
| J64777 | Albumin, Bovine, Standard Grade, Chromatographically purified | 10g |
| | [Bovine Serum Albumin, BSA] | 50g |
| | [9048-46-8], F.W. 66kDa, Powder, EINECS 232-936-2, MDL MFCD00130384, † | 100g |
| | Application(s): Suitable for standard protein research applications | 500g |
| J64752 | Albumin, Bovine plasma, crystalline, 98% | 5g |
| | [Bovine Serum Albumin, BSA] | 10g |
| | [9048-46-8], Powder, EINECS 232-936-2, MDL MFCD00130384, † | |
| | Application(s): For lipid solubilization; also a blocking agent in Western blots | |
| A16951 | Albumin, ex egg, 80% | 50g |
| | [9006-59-1], EINECS 232-692-7, MDL MFCD00804580, † | 250g |
| | Albuterol , see Salbutamol, 99%, J63741, p. 339 | |
| | Albuterol sulfate , see Salbutamol sulfate, A18544, p. 339 | |
| | AICA , see 5-Amino-4-imidazolecarboxamide hydrochloride, B24012, p. 95 | |
| J60122 | Alcian Blue 8GX | 10g |
| | [Ingrain blue 1, C.I. 74240] | 25g |
| | [33864-99-2], C ₃₈ H ₈₈ Cl ₂ CuN ₁₆ S ₄ , F.W. 1298.88, Powder, m.p. 148°, EINECS 251-705-7, MDL MFCD00010720, | 100g |
| | Note: Certified by the Biological Stain Commission, † | |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| J65869 | Alcohol dehydrogenase, yeast | 30kilounits |
| | [ADH, Alcohol: NAD ⁺ oxidoreductase] | 150kilounits |
| | [9031-72-5], Lyophilized powder, EINECS 232-870-4, RTECS SZ5999500, MDL MFCD00081305, | |
| | Note: from Baker's yeast, † | |
| | Application(s): Catalyzes the oxidation of alcohol and the reduction of aldehydes | |
| J64628 | Alcohol dehydrogenase kit - 12 variants (A1 through A12) | 1each |
| | [EC 1.1.1.1] | |
| | Lyophilized powder, Note: Contains 100mg of each variant | |
| | Application(s): Catalyzes stereoselective reduction of ketones to produce enantiomerically pure alcohols | |
| J64194 | Alcohol dehydrogenase kit - 35 variants (A1 through A35) | 1each |
| | [EC 1.1.1.1] | |
| | Lyophilized powder, Note: Contains 100mg of each variant | |
| | ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | |
| | Application(s): Catalyzes stereoselective reduction of ketones to produce enantiomerically pure alcohols | |
| J65760 | Alcohol Dehydrogenase A1 | 250mg |
| | [EC 1.1.1.1] | 500mg |
| | [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 1g |
| J65907 | Alcohol Dehydrogenase A2 | 250mg |
| | [EC 1.1.1.1] | 500mg |
| | [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 1g |
| J65344 | Alcohol Dehydrogenase A3 | 250mg |
| | [EC 1.1.1.1] | 500mg |
| | [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 1g |
| J64009 | Alcohol Dehydrogenase A4 | 250mg |
| | [EC 1.1.1.1] | 500mg |
| | [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 1g |
| J65129 | Alcohol Dehydrogenase A5 | 250mg |
| | [EC 1.1.1.1] | 500mg |
| | [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 1g |
| J64820 | Alcohol Dehydrogenase A6 | 250mg |
| | [EC 1.1.1.1] | 500mg |
| | [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 1g |
| J64660 | Alcohol Dehydrogenase A7 | 250mg |
| | [EC 1.1.1.1] | 500mg |
| | [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 1g |
| J64842 | Alcohol Dehydrogenase A8 | 250mg |
| | [EC 1.1.1.1] | 500mg |
| | [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 1g |
| J64213 | Alcohol Dehydrogenase A9 | 250mg |
| | [EC 1.1.1.1] | 500mg |
| | [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 1g |

| Stock # | Description | Size |
|---------|---|----------------------|
| J65285 | Alcohol Dehydrogenase A10 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg 500mg 1g |
| J65660 | Alcohol Dehydrogenase A11 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg 500mg 1g |
| J64939 | Alcohol Dehydrogenase A12 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg 500mg 1g |
| J65084 | Alcohol Dehydrogenase A13 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg 500mg 1g |
| J64220 | Alcohol Dehydrogenase A14 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg 500mg 1g |
| J65514 | Alcohol Dehydrogenase A15 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg 500mg 1g |
| J64185 | Alcohol Dehydrogenase A16 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg 500mg 1g |
| J66000 | Alcohol Dehydrogenase A17 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg 500mg 1g |
| J65821 | Alcohol Dehydrogenase A18 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg 500mg 1g |
| J64662 | Alcohol Dehydrogenase A19 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg 500mg 1g |
| J64564 | Alcohol Dehydrogenase A20 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg 500mg 1g |
| J64491 | Alcohol Dehydrogenase A21 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg 500mg 1g |
| J64145 | Alcohol Dehydrogenase A22 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg 500mg 1g |
| J65454 | Alcohol Dehydrogenase A23 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg 500mg 1g |
| J65139 | Alcohol Dehydrogenase A24 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg 500mg 1g |
| J65992 | Alcohol Dehydrogenase A25 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg 500mg 1g |
| J65124 | Alcohol Dehydrogenase A26 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg 500mg 1g |
| J65951 | Alcohol Dehydrogenase A27 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg 500mg 1g |
| J64317 | Alcohol Dehydrogenase A28 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg 500mg 1g |




| Stock # | Description | Size |
|---|--|------------|
| J64321 | Alcohol Dehydrogenase A29 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg |
| | | 500mg |
| | | 1g |
| J65989 | Alcohol Dehydrogenase A30 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg |
| | | 500mg |
| | | 1g |
| J65743 | Alcohol Dehydrogenase A31 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg |
| | | 500mg |
| | | 1g |
| J65451 | Alcohol Dehydrogenase A32 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg |
| | | 500mg |
| | | 1g |
| J65860 | Alcohol Dehydrogenase A33 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg |
| | | 500mg |
| | | 1g |
| J65190 | Alcohol Dehydrogenase A34 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg |
| | | 500mg |
| | | 1g |
| J64886 | Alcohol Dehydrogenase A35 [EC 1.1.1.1] [9031-72-5], Lyophilized powder, EINECS 232-870-4 | 250mg |
| | | 500mg |
| | | 1g |
| J64450 | Alcohol Dehydrogenase A36 Lyophilized powder, Note: Component in the Cofactor Recycling Enzymes Kit, item J64535 | 250mg |
| | | 500mg |
| | | 1g |
| 45391 | R1-Alcohol Dehydrogenase MDL MFCD00081305 | 1kilounit |
| | | 5kilounits |
| Application(s): Synthesis of enantiometrically pure alcohols with (R)-configuration. Very broad substrate specificity: aliphatic, cyclic and aromatic ketones, diketones and keto acid esters | | |
| 45393 | R2-Alcohol Dehydrogenase [9028-12-0], Powder, MDL MFCD00081305 | 1kilounit |
| | | 5kilounits |
| Application(s): Synthesis of enantiomerically pure alcohols with (R)-configuration. Very broad substrate specificity: aliphatic, cyclic and aromatic ketones and diketones | | |
| 45392 | S1-Alcohol Dehydrogenase [9031-72-5], Powder, EINECS 232-870-4, MDL MFCD00081305 | 1kilounit |
| | | 5kilounits |
| Application(s): Synthesis of enantiomerically pure alcohols with (S)-configuration. High activity to α -diketones, shortchain aliphatic ketones and aliphatic keto acid esters | | |
| 45394 | S2-Alcohol Dehydrogenase [9031-72-5], Powder, EINECS 232-870-4, MDL MFCD00081305 | 1kilounit |
| | | 5kilounits |
| Application(s): Synthesis of enantiomerically pure alcohols with (S)-configuration. High activity to ketones with bulky side chains, such as acetophenones, ring-halogenated acetophenones or pinacolone | | |
| 45395 | S3-Alcohol Dehydrogenase [9031-72-5], Powder, EINECS 232-870-4, MDL MFCD00081305 | 1kilounit |
| | | 5kilounits |
| Application(s): Synthesis of enantiomerically pure aromatic alcohols with (S)-configuration. High activity to ketones with bulk side chains such as acetophenones, ring-halogenated acetophenones or pinacolone | | |
| 45397 | S4-Alcohol Dehydrogenase [9031-72-5], Powder, EINECS 232-870-4, MDL MFCD00081305 | 1kilounit |
| | | 5kilounits |
| Application(s): Synthesis of enantiomerically pure alcohols with (S)-configuration. Broad substrate specificity that includes linear and cyclic ketones and acetaldehyde | | |
| 45399 | S5-Alcohol Dehydrogenase MDL MFCD00081305 | 1kilounit |
| | | 5kilounits |
| Application(s): Enzymic catalysis in organic solvents | | |
| 45401 | S6-Alcohol Dehydrogenase [9031-72-5], Powder, EINECS 232-870-4, MDL MFCD00081305, † | 1kilounit |
| | | 5kilounits |
| Application(s): Synthesis of enantiomerically pure alcohols with (S)-configuration. High activity to ketones with bulk side chains such as acetophenones, ring-halogenated acetophenones or pinacolone | | |
| J64713 | Aldehyde Dehydrogenase Kit - 5 variants (AD1 through AD5) [EC 1.2.1.3] Lyophilized powder, Note: Contains 100mg of each variant | 1each |
| | | |
| Application(s): Catalyzes the oxidation of aldehydes to the corresponding carboxylic acids with NAD ⁺ /NADP ⁺ as cofactor | | |







| Stock # | Description | Size |
|---------|--|----------------------|
| J65968 | Aldehyde Dehydrogenase AD1 [EC 1.2.1.3] Lyophilized powder | 250mg 500mg 1g |
| J65229 | Aldehyde Dehydrogenase AD2 [EC 1.2.1.3] Lyophilized powder | 250mg 500mg 1g |
| J64511 | Aldehyde Dehydrogenase AD3 [EC 1.2.1.3] Lyophilized powder | 250mg 500mg 1g |
| J65123 | Aldehyde Dehydrogenase AD4 [EC 1.2.1.3] Lyophilized powder | 250mg 500mg 1g |
| J64097 | Aldehyde Dehydrogenase AD5 [EC 1.2.1.3] Lyophilized powder | 250mg 500mg 1g |
| J65717 | Aldehyde Reductase Kit - 10 variants (AR1-AR10) Lyophilized powder, Note: Contains 100mg of each variant Application(s): Catalyzes the reduction of aldehydes to the corresponding primary alcohols with NADH/NADPH as cofactor | 1each |
| J64832 | Aldehyde Reductase AR1 Lyophilized powder | 250mg 500mg 1g |
| J64744 | Aldehyde Reductase AR2 Lyophilized powder | 250mg 500mg 1g |
| J64714 | Aldehyde Reductase AR3 Lyophilized powder | 250mg 500mg 1g |
| J64367 | Aldehyde Reductase AR4 Lyophilized powder | 250mg 500mg 1g |
| J65435 | Aldehyde Reductase AR5 Lyophilized powder | 250mg 500mg 1g |
| J65614 | Aldehyde Reductase AR6 Lyophilized powder | 250mg 500mg 1g |
| J65548 | Aldehyde Reductase AR7 Lyophilized powder | 250mg 500mg 1g |
| J65082 | Aldehyde Reductase AR8 Lyophilized powder | 250mg 500mg 1g |
| J65242 | Aldehyde Reductase AR9 Lyophilized powder | 250mg 500mg 1g |
| J65021 | Aldehyde Reductase AR10 Lyophilized powder | 250mg 500mg 1g |
| J61397 | Alendronate sodium trihydrate, 97% [MK-217] [121268-17-5], C ₄ H ₁₂ NaNO ₇ P ₂ ·3H ₂ O, F.W. 325.12 (271.08anhy), Solid, Merck 14,229, RTECS SZ6523500, MDL MFCD01748233 ! H:H302, P:P264-P270-P301+P312-P330-P501a Application(s): Inhibits CD45 protein tyrosine phosphatase and farnesyl diphosphate synthase; induces apoptosis | 5g |
| | Algin , see Alginic acid sodium salt, high viscosity, J61887, p. 89 | |




| Stock # | Description | Size |
|--|---|-----------------------------------|
| A17582 | Alginate acid ■ [Polymannuronic acid] [9005-32-7], m.p. >300°, Merck 14,242, EINECS 232-680-1, RTECS AZ5775000, MDL MFCD00081309, Note: Insoluble in water, † | 100g 500g 2.5kg |
| Application(s): A straight chain, hydrophilic, colloidal polyuronic acid | | |
| B25266 | Alginate acid sodium salt, low viscosity ■ [Algin, Polymannuronic acid sodium salt] [9005-38-3], Merck 14,241, RTECS AZ5820000, MDL MFCD00081310, † | 50g 100g 250g 500g |
| Application(s): A gelling polysaccharide extracted from giant brown seaweed, useful in viscosity studies | | |
| J61887 | Alginate acid sodium salt, high viscosity [Algin, Sodium alginate] [9005-38-3], Powder, Merck 14,241, MDL MFCD00081310, † | 100g 250g 1kg |
| Application(s): A gelling polysaccharide extracted from giant brown seaweed, useful in viscosity studies | | |
| A18565 | Alginate acid sodium salt, very low viscosity ■ [Algin, Polymannuronic acid sodium salt] [9005-38-3], Merck 14,241, MDL MFCD00081310, † | 100g 500g 2.5kg |
| Aliquat® 100 , see Tetra-n-butylammonium bromide, A10249, p. 361 | | |
| A14404 | Alizarin, 94% [1,2-Dihydroxyanthraquinone] [72-48-0], C ₁₄ H ₈ O ₄ , F.W. 240.21, m.p. 286-290°, b.p. ca 430° subl., Merck 14,251, EINECS 200-782-5, RTECS CB6580000, BRN 1914037, MDL MFCD00001201, † ! H: H319, P: P280-P264-P305+P351+P338-P337+P313 Acid-base indicator: pH 5.8 - 7.2, 11.0 - 13.0. | 100g 500g 2.5kg |
| 42040 | Alizarin Red S sodium salt [3,4-Dihydroxy-9,10-dioxo-2-anthracenesulfonic acid sodium salt, C.I. 58005] [130-22-3], C ₁₅ H ₈ O ₅ Na, F.W. 342.27, Powder, Merck 14,8573, EINECS 204-981-8, RTECS CB1095300, BRN 4117090, MDL MFCD00013049, Note: Transition interval: pH 4.6 (yellow) to pH 6.0 (red), † | 5g 25g |
| 38707 | Alizarin Yellow R sodium salt [Mordant Yellow 3R, 5-(4-Nitrophenylazo)salicylic acid sodium salt] [1718-34-9], C ₁₅ H ₈ N ₃ NaO ₅ , F.W. 309.22, Powder, Merck 14,255, EINECS 217-002-4, RTECS DH2528600, BRN 962365, MDL MFCD00067121, † Note: Transition interval: pH 10.1 (yellow) to pH 12.1 (orange), † ! H: H302, P: P280F | 10g 25g |
| J61037 | Alkaline Phosphatase, calf intestine, EIA Grade [EC 3.1.3.1, CIAP] [9001-78-9], Liquid, 140 kDa, EINECS 232-631-4, MDL MFCD00131849, Note: Minimum 3,000 units per mg protein. One unit hydrolyzes 1 micromole of p-nitrophenol phosphate per minute at 37 degrees and pH 9.8, † | 1mg 5mg |
| Application(s): Used to dephosphorylate proteins; also used to dephosphorylate the 5' termini of DNA or RNA to prevent self ligation | | |
| J62907 | Alkaline Phosphatase Buffer-1 (5X) Liquid, Note: Contains 200mM Tris, 200mM NaCl, and 40mM magnesium chloride at pH 9.5, † | 100ml 250ml |
| J63170 | Alkaline running buffer soln. Liquid, Note: Contains 0.5M NaOH and 50mM EDTA, † | 250ml 500ml |
| Alkylbenzyltrimethylammonium chloride , see Benzalkonium chloride, 41339, p. 119 | | |
| A15571 | Allantoin, 98% [5-Ureidohydantoin] [97-59-6], C ₄ H ₆ N ₂ O ₃ , F.W. 158.12, m.p. ca 230° dec., Merck 14,258, EINECS 202-592-8, RTECS YT1600000, BRN 102364, MDL MFCD00005260, † | 250g 1kg 5kg |
| Allantoxanic acid potassium salt , see Oxonic acid potassium salt, J60400, p. 310 | | |
| ALLM , see Calpain Inhibitor II, 95+%, J62491, p. 144 | | |
| ALLN , see Calpain Inhibitor I, 95+%, J61766, p. 144 | | |
| Allopurinol , see 4-Hydroxypyrazolo[3,4-d]pyrimidine, A16974, p. 251 | | |
| A15324 | Alloxan monohydrate, 98% △ [Mesoxalylurea monohydrate, 2,4,5,6(1H,3H)-Pyrimidinetetrone] [2244-11-3], C ₄ H ₂ N ₂ O ₄ ·H ₂ O, F.W. 160.09 (142.07anhy), m.p. ca 260° dec., Merck 14,282, EINECS 200-062-0, RTECS UW0492000, BRN 5309394, MDL MFCD00149399, † | 25g 50g 100g 250g 1kg |
| Application(s): Cytotoxic compound that causes oxidative base damage to nuclear DNA | | |
| H52177 | 2-Allyl-N-Fmoc-L-glycine, 95% [Fmoc-allyl-Gly-OH] [146549-21-5], C ₂₀ H ₁₉ NO ₄ , F.W. 337.37, BRN 5884047, MDL MFCD01311749 | 250mg 1g 5g |







| Stock # | Description | Size |
|---------|--|---------------------|
| | 4-Allylguaiacol , see Eugenol, A14332, p. 217 | |
| | 4-Allyl-2-methoxyphenol , see Eugenol, A14332, p. 217 | |
| J62153 | Aloin [Barbaloin, 1,8-Dihydroxy-10-(β-D-glucopyranosyl)-3-(hydroxymethyl)-9(10H)-anthracenone] [1415-73-2], C ₂₁ H ₂₂ O ₉ , F.W. 418.40, Powder, EINECS 215-808-0, RTECS LZ6520000, BRN 6077558, MDL MFCD00151160 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10g 25g 50g |
| | Application(s): Aloe exudant, used as a stimulant-laxative | |
| J61582 | Aluminum chloride, 0.5M aq. soln. [7784-13-6], AlCl ₃ , F.W. 133.34, Liquid, UN2581, † H:H314, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 50ml 100ml |
| 46200 | Aluminum oxide, for Bio-Mass Cleanup [1344-28-1], Al ₂ O ₃ , F.W. 101.96, 50-150 Micron APS Powder, m.p. 2045°, b.p. 2980°, n _D ²⁰ 1.765, Merck 14,356, EINECS 215-691-6, MDL MFCD00003424, † | 250g 1kg |
| J65155 | AM 580 [4-[(5,6,7,8-Tetrahydro-5,5,8,8-tetramethyl-2-naphthalenyl)carboxamido]benzoic acid] [102121-60-8], C ₂₂ H ₂₅ NO ₃ , F.W. 351.44, Crystalline solid, RTECS DH6834890, MDL MFCD00673916 | 10mg |
| | Amantadine hydrochloride , see 1-Adamantanamine hydrochloride, A12699, p. 78 | |
| J62932 | Amastatin hydrochloride, 98+% [[[2S,3R]-3-Amino-2-hydroxy-5-methylhexanoyl]-Val-Val-Asp-OH] [100938-10-1], C ₂₁ H ₃₈ N ₄ O ₆ ·HCl, F.W. 511.01, Powder, BRN 8888370, MDL MFCD00150636 | 1mg 5mg |
| | Application(s): Inhibitor for aminopeptidase A and leucine aminopeptidase | |
| L14285 | Amberlite® IR-120(H), ion exchange resin [78922-04-0], d. 1.2800, Merck 14,382, Fieser 1,511 4,266 5,355 6,302 9,256, MDL MFCD00132707 H:H318, P:P280i-P305+P351+P338-P310 Strongly acidic gel-type cation-exchange resin, 8% crosslinked, H ⁺ form. Catalyst for preparation of enol ethers or ketals from ketones: <i>Synthesis</i> , 348 (1974), and for selective ketalization of diketo steroids: <i>J. Chem. Soc. Perkin 1</i> , 2376 (1974). See also Amberlyst® 15(H), 89079 , p. 90. | 250g 500g 1kg |
| 42253 | Amberlite® IRA-67, ion exchange resin [80747-90-6], Merck 14,382, MDL MFCD00145567, Note: Acrylic-DVB; Weakly basic gel type resin | 250g 1kg 5kg |
| 17246 | Amberlite® IRA-400(Cl), ion exchange resin [9002-24-8], Styrene-DVB; Strongly basic gel type resin, Merck 14,382, MDL MFCD00132708, † Strongly-basic gel-type anion-exchange resin, Cl ⁻ form. In the hydroxide form, is a catalyst for preparation of esters from carboxylic acids and alkyl iodides: <i>Synthesis</i> , 723 (1975), and has also been used as a low-cost, recyclable alternative to silver oxide for the preparation of quaternary ammonium hydroxides: <i>Org. Synth. Coll.</i> , 6, 550 (1988). | 100g 500g 2kg |
| L19567 | Amberlite® IRA-900(Cl), ion exchange resin [9050-97-9], Merck 14,382, MDL MFCD00132712 Macroreticular strongly basic ionic exchange resin, Cl ⁻ form. | 250g 1kg |
| 44079 | Amberlyst® 15(H), wet, ion exchange resin ■ [39389-20-3], Styrene-DVB; Strongly acidic macroreticular resin, Beads, Fieser 5,355 6,302 9,256 11,276 13,152 15,178 18,194, MDL MFCD00145841, † | 250g 1kg 5kg |
| 89079 | Amberlyst® 15(H), ion exchange resin [39389-20-3], Styrene-DVB; Strongly acidic macroreticular resin, Pale brown beads, Fieser 5,355 6,302 9,256 11,276 13,152 15,178 18,194, MDL MFCD00145841, † Amberlyst is a registered trademark of Rohm and Haas Co. Macroreticular strongly acidic cation-exchange resin, H ⁺ form, suitable for non-aqueous applications. Useful catalyst for a variety of reactions, for example: Formation of THP ethers: <i>Synthesis</i> , 618 (1979). Protection of alcohols as <i>tert</i> -butyl ethers: <i>Tetrahedron Lett.</i> , 29, 2951 (1988). Protection of aldehydes as dithioacetals: <i>Synth. Commun.</i> , 19, 2383 (1989). Esterification of acids with methanol: <i>Synth. Commun.</i> , 18, 847 (1988). Cleavage of acetals: <i>Synthesis</i> , 1021 (1984); <i>J. Am. Chem. Soc.</i> , 117, 10143 (1995). Regeneration of carbonyl compounds from hydrazones: <i>J. Chem. Soc., Perkin 1</i> , 2563 (1988). For use in the Fischer indole synthesis, see: <i>Heterocycles</i> , 22, 1211 (1984); <i>J. Chem. Soc., Perkin 1</i> , 1319 (1990). | 50g 250g 1kg |
| A17956 | Amberlyst® A-21, ion exchange resin [9049-93-8], Fieser 18,194 21,237, MDL MFCD00145842 Macroreticular weakly basic anion-exchange resin, free base, suitable for non-aqueous applications. Effective catalyst for the Michael addition of nitroalkanes to methyl acrylate: <i>Synthesis</i> , 711 (1987), and also for the cleavage of 2-nitrocycloalkanones: <i>Synthesis</i> , 355 (1992). Promotes the Henry (nitro-aldol) reaction of aldehydes with nitroalkanes giving superior results to conventional conditions: <i>Liebigs Ann. Chem.</i> , 1235 (1994); <i>J. Org. Chem.</i> , 59, 5466 (1994); <i>Tetrahedron</i> , 52, 1677 (1996). Useful heterogeneous catalyst for conversion of carbonyl compounds to oximes with hydroxylamine hydrochloride: <i>Chem. Lett.</i> , 475 (1997). | 250g 1kg |






| Stock # | Description | Size |
|---------|--|-----------------------|
| J63712 | Ambroxol hydrochloride, 99% [18683-91-5], C ₁₅ H ₁₉ Br ₂ N ₂ O·HCl, F.W. 414.57, Powder, Merck 14,386, EINECS 242-500-3, RTECS GV8423000, MDL MFCD00078932 | 5g |
| | Application(s): Sodium channel blocker. Metabolite of bromhexine | |
| | N-Amidino-3,5-diamino-6-chloropyrazine-2-carboxamide hydrochloride , see Amiloride hydrochloride, J62168, p. 91 | |
| | N-Amidinosarcosine monohydrate , see Creatine monohydrate, B25009, p. 168 | |
| J61978 | Amido Black 10B, 0.2% v/v soln. in 5% acetic acid [Acid black 1, C.I. 20470] [1064-48-8], C ₂₂ H ₁₄ N ₆ Na ₂ O ₉ S ₂ , F.W. 616.49, Liquid, BRN 5374263, MDL MFCD00004017, † H:EUH210 | 500ml 1L |
| A11374 | Amido Black 10B ■ [C.I. 20470, Naphthalene Black 10B] [1064-48-8], C ₂₂ H ₁₄ N ₆ Na ₂ O ₉ S ₂ , F.W. 616.49, EINECS 213-903-1, RTECS QJ6196000, BRN 5374263, MDL MFCD00004017, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 25g 100g |
| 33233 | Amidosulfonic acid, ACS, 99.3-100.3% (Assay dried basis) [Sulfamic acid] [5329-14-6], H ₂ NSO ₃ H, F.W. 97.09, Crystalline, m.p. ca 205° dec., d. 2.12, Merck 14,8921, Fieser 1,1117 20,353, UN2967, EINECS 226-218-8, RTECS W05950000, MDL MFCD00011603, † Maximum level of impurities: Insoluble matter 0.01%, Residue after ignition 0.01%, Cl 0.001%, SO ₂ 0.05%, Heavy Metals (as Pb) 0.001%, Fe 5ppm ! H:H315-H319-H412, P:P280-P305+P351+P338-P302+P352-P321-P362-P501a | 100g 500g |
| | Amidotrizoic acid , see Diatrizoic acid, J63444, p. 184 | |
| J60849 | Amikacin [N1-[(S)-(-)-4-Amino-2-hydroxybutyl]kanamycin A] [37517-28-5], C ₂₂ H ₄₃ N ₅ O ₁₃ , F.W. 585.61, Crystalline powder, m.p. 203°, Merck 14,405, EINECS 253-538-5, RTECS WK1955000, BRN 1445422, MDL MFCD00883675 | 1g 5g 25g |
| | Application(s): An aminoglycoside antibiotic derived from Kanamycin A | |
| J63862 | Amikacin disulfate [39831-55-5], C ₂₂ H ₄₃ N ₅ O ₁₃ ·2H ₂ SO ₄ , F.W. 781.77, Powder, m.p. 220-230°, Merck 14,405, EINECS 254-648-6, RTECS WK1961200, BRN 6172633, MDL MFCD00167475, Note: Potency: 674-786 micrograms per mg | 25g 100g |
| | Application(s): An aminoglycoside antibiotic derived from Kanamycin A | |
| J62168 | Amiloride hydrochloride dihydrate [N-Amidino-3,5-diamino-6-chloropyrazine-2-carboxamide hydrochloride] [2016-88-8], C ₈ H ₈ ClN ₂ O·2H ₂ O, F.W. 266.09, Powder, m.p. >240°, Merck 14,406, UN2811, EINECS 217-958-2, RTECS UQ2275500, MDL MFCD00058197 ☠ H:H301, P:P264-P270-P301+P310-P321-P405-P501a | 1g 5g |
| | Application(s): Sodium channel blocker | |
| | Aminoacetic acid , see Glycine, 99.5+%, Cell Culture Reagent, J62407, p. 237 | |
| B24356 | 9-Aminoacridine hydrochloride hydrate, 99% [9-Acridinamine hydrochloride hydrate] [52417-22-8], C ₁₅ H ₁₀ N ₂ ·HCl·xH ₂ O, F.W. 230.69(anhy), m.p. >300°, UN2811, EINECS 205-145-5, RTECS AR7350000, MDL MFCD00150071, † ☠ H:H301-H341, P:P280h-P309-P310 | 5g 25g |
| | Application(s): A mutagen and DNA modifier | |
| | 1-Aminoadamantane hydrochloride , see 1-Adamantanamine hydrochloride, A12699, p. 78 | |
| | L-2-Amino-4-(2-aminophenyl)-4-oxobutanoic acid , see L-Kynurenine, J60199, p. 264 | |
| A13846 | 4-Aminoantipyrine, 97% [4-Amino-2,3-dimethyl-1-phenyl-3-pyrazolin-5-one, 4-Aminophenazone] [83-07-8], C ₁₁ H ₁₃ N ₃ O, F.W. 203.25, m.p. 106-110°, Merck 14,591, EINECS 201-452-3, RTECS CD2480000, BRN 181635, MDL MFCD00003145, † ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 100g 500g 2.5kg |
| | Application(s): Endogenous poly-ADP-ribosyltransferase inhibitor | |
| J64308 | 1-Amino-11-azido-3,6,9-trioxaundecane [Azido-PEG3-amine] [134179-38-7], C ₈ H ₁₈ N ₃ O ₃ , F.W. 218.26, Viscous liquid, UN2735, MDL MFCD00269874 ☠ H:H314, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501 | 25mg 100mg |
| A10793 | 3-Aminobenzamide, 98% [3544-24-9], C ₇ H ₈ N ₂ O, F.W. 136.15, m.p. 111-115°, EINECS 222-586-9, RTECS CU8992000, BRN 2802373, MDL MFCD00007989 ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 5g 25g |
| | Application(s): Endogenous poly-ADP-ribosyltransferase inhibitor | |
| | 5-Aminobenzene-1,3-dicarboxylic acid , see 5-Aminoisophthalic acid, A15074, p. 96 | |
| | 4-Aminobenzenesulfonamide , see Sulfanilamide, A13001, p. 355 | |
| | N-(4-Aminobenzenesulfonyl)acetamide , see Sulfacetamide, A19836, p. 355 | |














| Stock # | Description | Size |
|---------|---|---|
| A12673 | 4-Aminobenzoic acid, 99% ▲ △ [H-4-Abz-OH, PABA] [150-13-0], C ₇ H ₇ NO ₂ , F.W. 137.14, m.p. ca 187° dec., d. 1.374, Merck 14,423, Fieser 2,24, EINECS 205-753-0, RTECS DG1400000, BRN 471605, MDL MFCD00007894, † ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a |  50g 250g 1kg |
| | 4-Aminobenzoic acid ethyl ester , see Ethyl 4-aminobenzoate, A12754, p. 214 | |
| J63428 | 4-Aminobenzoic acid sodium salt, 99% [PABA, Sodium 4-aminobenzoate] [555-06-6], C ₇ H ₆ NNaO ₂ , F.W. 159.12, Powder, m.p. >300°, EINECS 209-080-3, RTECS DG2975000, MDL MFCD00064395, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 25g 100g 250g |
| | Application(s): Pharmaceutical intermediate | |
| J63610 | 1-Aminobenzotriazole, 98% [1-Benzotriazolamine, ABT] [1614-12-6], C ₆ H ₆ N ₄ , F.W. 134.14, Powder, m.p. 81-84°, BRN 607843, MDL MFCD00132902 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 250mg 1g 5g |
| | Application(s): Suicide inhibitor of cytochrome P450 and chloroperoxidase | |
| | N-(4-Aminobenzoyl)glycine , see 4-Aminohippuric acid, A13786, p. 95 | |
| | 5-Amino-(3,4'-bipyridin)-6(1H)-one , see Amrinone, 98%, J62655, p. 103 | |
| H51980 | 4-Amino-N-Boc-L-phenylalanine, 95% [Boc-Phe(4-NH ₂)-OH] [55533-24-9], C ₁₇ H ₂₀ N ₂ O ₄ , F.W. 280.32, m.p. 124-126°, MDL MFCD00038139 |  250mg 1g 5g |
| | 2-Amino-8-bromo-6-hydroxypurine riboside , see 8-Bromoguanosine, J63940, p. 137 | |
| L03889 | (R)-(-)-2-Aminobutane, 99% △ [(R)-(-)-2-Butylamine, (R)-(-)-1-Methylpropylamine] [13250-12-9], C ₄ H ₁₁ N, F.W. 73.14, b.p. 63°, f.p. -19°(-2°F), d. 0.722, n _D ²⁰ 1.3930, [α] _D ²⁰ -7.5° (neat), Merck 14,1544, UN2733, EINECS 236-232-6, BRN 1718760, MDL MFCD00064416 ! H:H225-H314-H400-H302-H332, P:P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a |  250mg 1g 5g |
| L10069 | (S)-(+)-2-Aminobutane, 98% △ [(S)-(+)-2-Butylamine, (S)-(+)-1-Methylpropylamine] [513-49-5], C ₄ H ₁₁ N, F.W. 73.14, b.p. 63°, f.p. -19°(-2°F), d. 0.722, n _D ²⁰ 1.3930, [α] _D ²⁰ +7.5° (neat), Merck 14,1544, UN2733, EINECS 208-164-7, RTECS EO3327000, BRN 1718760, MDL MFCD00064417, † ! H:H225-H314-H400-H302-H332, P:P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a |  250mg 1g 5g |
| J62670 | (2S)-2-Aminobutyramide [143164-46-9], C ₄ H ₁₀ N ₂ O, F.W. 102.14, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | Call |
| | Application(s): For synthesis of optically active products | |
| J61307 | 4-Aminobutyric acid, 99+% [γ-Aminobutyric acid, GABA] [56-12-2], H ₂ N(CH ₂) ₃ CO ₂ H, F.W. 103.12, Powder, m.p. ca 195° dec., Merck 14,430, EINECS 200-258-6, RTECS ES6300000, BRN 906818, MDL MFCD00008226, † | 10g |
| | γ-Aminobutyric acid, see 4-Aminobutyric acid, 99+%, J61307, p. 92 | |
| | ε-Aminocaproic acid, see 6-Aminocaproic acid, A14719, p. 95 | |
| | 6-Aminocaproic acid, see 6-Aminohexanoic acid, A14719, p. 95 | |
| A10530 | 7-Aminocephalosporanic acid, 98% (dry wt.), may cont. up to 2% water [7-ACA] [957-68-6], C ₁₀ H ₁₂ N ₂ O ₅ S, F.W. 272.28, m.p. >300°, Merck 14,434, EINECS 213-485-0, BRN 622638, MDL MFCD00005177 ! H:H334-H317, P:P285-P261-P280-P302+P352-P321-P501a |  1g 5g 25g |
| | (R)-2-Amino-3-(4-chlorophenyl)propionic acid , see 4-Chloro-D-phenylalanine, H51982, p. 158 | |
| A18195 | 2-Amino-6-chloropurine, 99% [6-Chloroguanine] [10310-21-1], C ₅ H ₄ ClN ₅ , F.W. 169.57, m.p. >300°, EINECS 233-686-7, RTECS UO7502000, BRN 9626, MDL MFCD00075252 |  1g 5g 25g |
| J64468 | 2-Amino-6-chloropurine riboside, 95% [6-Chloroguanine riboside] [2004-07-1], C ₁₀ H ₁₂ ClN ₅ O ₄ , F.W. 301.69, Powder, m.p. 165-167°, EINECS 217-905-3, MDL MFCD00005735 | 1g 5g |
| | 6-Amino-2-chloropurine riboside , see 2-Chloroadenosine, J63810, p. 155 | |
| J63873 | 1-Aminocyclobutanecarboxylic acid hydrochloride [ACBC hydrochloride] [98071-16-0], C ₅ H ₈ NO ₂ HCl, F.W. 151.63, Powder, RTECS GU1336000, MDL MFCD000661068 ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g 5g |
| | Application(s): NMDA receptor antagonist acting at the glycine site | |

| Stock # | Description | Size |
|---------|--|-------------------|
| | Aminocyclohexane , see Cyclohexylamine, A15851, p. 171 | |
| J65118 | 1-Amino-1-cyclopropanecarboxylic acid, 99% [ACPC] [22059-21-8], C ₄ H ₇ NO ₂ , F.W. 101.11, Crystalline powder, m.p. 229-231°, RTECS GZ1110000, BRN 2076413, MDL MFCD00009944 | 250mg 1g |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): A NMDA glutamate receptor agonist at glycine site | |
| | N-(10-Aminodecyl)-5-chloro-1-naphthalenesulfonamide hydrochloride , see A-7 hydrochloride, J62011, p. 69 | |
| J64266 | 2-Amino-2'-deoxyadenosine, 99% [2,6-Diaminopurine 2'-deoxyriboside, 9-(2-Deoxy-β-D-ribofuranosyl)-2,6-diaminopurine] [4546-70-7], C ₁₀ H ₁₄ N ₆ O ₅ , F.W. 266.26, Powder, RTECS UO7523300 | 1g 5g 25g |
| J65532 | 2'-Amino-2'-deoxyadenosine, 98% [10414-81-0], C ₁₀ H ₁₄ N ₆ O ₅ , F.W. 266.26, Powder | 1g |
| J64650 | 2'-Amino-2'-deoxyguanosine, 98% [9-(2-Amino-2-deoxy-β-D-ribofuranosyl)guanine] [60966-26-9], C ₁₀ H ₁₄ N ₆ O ₅ , F.W. 282.26, Powder, RTECS MF8752000 | 1g |
| | ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J65374 | 2'-Amino-2'-deoxyinosine, 98% [9-(2-Amino-2-deoxy-β-D-ribofuranosyl)hypoxanthine] [75763-51-8], C ₁₀ H ₁₃ N ₅ O ₅ , F.W. 267.24, Powder | 1g |
| J65923 | 2'-Amino-2'-deoxyuridine, 98% [26889-39-4], C ₉ H ₁₃ N ₃ O ₅ , F.W. 243.22, Powder | 1g |
| L03417 | 7-Aminodesacetoxycephalosporanic acid, 98% [7-ADCA] [22252-43-3], C ₈ H ₁₀ N ₂ O ₃ S, F.W. 214.24, m.p. ca 234° dec., EINECS 247-654-5, BRN 5273616, MDL MFCD00151456 | 250mg 1g 5g |
| |  | |
| J65090 | 3'-Amino-2',3'-dideoxyadenosine, 99% [9-(3-Amino-2,3-dideoxy-β-D-erythro-pentafuranosyl)adenine, 9-(3-Amino-2,3-dideoxy-β-D-ribofuranosyl)-hypoxanthine] [7403-25-0], C ₁₀ H ₁₄ N ₆ O ₂ , F.W. 250.26, Powder | 1g |
| J65326 | 3'-Amino-2',3'-dideoxyguanosine, 99% [9-(3-Amino-2,3-dideoxy-β-D-ribofuranosyl)guanine] [66323-49-7], C ₁₀ H ₁₄ N ₆ O ₃ , F.W. 266.26, Powder | 1g |
| | ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J64758 | 3'-Amino-2',3'-dideoxyinosine, 99% C ₁₀ H ₁₃ N ₅ O ₃ , F.W. 251.24, Powder, MDL MFCD10566669 | 1g |
| J64342 | 3'-Amino-2',3'-dideoxythymidine, 99% [52450-18-7], C ₁₀ H ₁₅ N ₃ O ₄ , F.W. 241.24, Powder, MDL MFCD00038057 | 1g |
| | 4'-Amino-2',5'-diethoxybenzanilide , see Fast Blue BB base, J62456, p. 218 | |
| | 4-Amino-2,6-dihydropyrimidine , see 6-Aminouracil, L03332, p. 100 | |
| | 5-Amino-2,4-dihydropyrimidine , see 5-Aminouracil, L04452, p. 100 | |
| | 4-Amino-2,3-dimethyl-1-phenyl-3-pyrazolin-5-one , see 4-Aminoantipyrine, A13846, p. 91 | |
| H27607 | (1R,2S)-(-)-2-Amino-1,2-diphenylethanol, 99% [23190-16-1], C ₁₄ H ₁₅ NO, F.W. 213.28, m.p. 141-143°, MDL MFCD00074960 | 1g 5g |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| H27834 | (1S,2R)-(+)-2-Amino-1,2-diphenylethanol, 99% [23364-44-5], C ₁₄ H ₁₅ NO, F.W. 213.28, m.p. 141-143°, MDL MFCD00074959 | 1g 5g |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| |  | |
| |  | |
| | Aminodiphenylmethane , see Benzhydramine, B24303, p. 119 | |
| B25121 | 12-Aminododecanoic acid, 96% [12-Aminolauroic acid] [693-57-2], H ₂ N(CH ₂) ₁₁ CO ₂ H, F.W. 215.34, m.p. 185-187°, EINECS 211-754-7, MDL MFCD00008153, † | 1g 5g 25g |
| | 2-Aminoethanesulfonic acid , see Taurine, A12403, p. 359 | |
| | Aminoethanethiol hydrochloride , see 2-Mercaptoethylamine hydrochloride, A14377, p. 281 | |

| Stock # | Description | | Size |
|---------|--|--|-----------------------|
| H26473 | 4-(2-Aminoethyl)benzenesulfonyl fluoride hydrochloride, 97% ■ [AEBSF] [30827-99-7], C ₈ H ₁₀ FNO ₂ S·HCl, F.W. 239.69, m.p. ca 184° dec., UN3261, BRN 7604627, MDL MFCD00132962 ⚠ H: H314, P: P260+P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a Irreversible serine protease inhibitor: <i>Thromb. Res.</i> , 2 , 343 (1973); <i>Acta Biol. Med. Ger.</i> , 39 , 355 (1980). |  | 250mg 1g |
| B22529 | 3-Amino-9-ethylcarbazole, 95% [132-32-1], C ₁₄ H ₁₄ N ₂ , F.W. 210.28, m.p. 98-100°, EINECS 205-055-7, RTECS FE3590000, MDL MFCD00004964, † ⚠ H: H350, P: P281-P201-P202-P308+P313-P405-P501a |  | 25g 100g |
| | Application(s): A covalent binding serine protease inhibitor | | |
| | N-(2-Aminoethyl)-5-chloronaphthalene-1-sulfonamide hydrochloride , see A-3 hydrochloride, J62760, p. 69 3-(2-Aminoethyl)-5-hydroxyindole hydrochloride , see Serotonin hydrochloride, B21263, p. 342 N-(2-Aminoethyl)-5-isoquinolinesulfonamide hydrochloride , see H-9 dihydrochloride, J63638, p. 240 | | |
| L14232 | S-(2-Aminoethyl)isothiourea dihydrobromide, 98% [AET, S-(2-Aminoethyl)isothiuronium bromide dihydrobromide] [56-10-0], C ₃ H ₈ N ₂ S 2HBr, F.W. 281.02, m.p. 190-192°, Merck 14 , 178, EINECS 200-257-0, RTECS UM0175000, BRN 3911163, MDL MFCD00037011, † ! H: H302, P: P280f Radioprotective agent. |  | 5g 25g |
| | S-(2-Aminoethyl)isothiuronium bromide dihydrobromide, see S-(2-Aminoethyl)isothiourea dihydrobromide, L14232, p. 94 4-(2-Aminoethyl)phenol, see Tyramine, 98+%, J60990, p. 386 | | |
| B24509 | 2-Amino-2-ethyl-1,3-propanediol, 97% ■ [1,1-Bis(hydroxymethyl)propylamine] [115-70-8], C ₅ H ₁₃ NO ₂ , F.W. 119.16, b.p. 152-153°/10mm, f.p. >110°(230°F), d. 1.099, n _D ²⁰ 1.490, Merck 14 , 439, EINECS 204-101-2, MDL MFCD00004680, † ! H: H315-H319, P: P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 |  | 100g 500g |
| B22769 | 2-Aminofluorene, 98% [2-Fluorenamine, 2-Fluorenylamine] [153-78-6], C ₁₃ H ₁₁ N, F.W. 181.24, m.p. 126-130°, EINECS 205-817-8, RTECS LL5075000, BRN 1945861, MDL MFCD00001125 ⚠ H: H341-H351, P: P281-P201-P202-P308+P313-P405-P501a |  | 1g 5g 25g |
| | 5-Aminofluorescein, see Fluorescein amine isomer I, 96%, J62175, p. 222 6-Aminofluorescein, see Fluorescein amine isomer II, 95%, J60609, p. 223 | | |
| J65741 | 2-Amino-2'-fluoro-2'-deoxyadenosine, 99% [9-(2-Deoxy-2-fluoro-β-D-ribofuranosyl)-2,6-diaminopurine, 2,6-Diaminopurine 2'-fluoro-2'-deoxyriboside] [134444-47-6], C ₁₀ H ₁₃ FN ₅ O ₃ , F.W. 284.25, Powder | | 1g |
| | D-2-Aminoglutaric acid, see D-Glutamine, 99+%, J60784, p. 235 DL-2-Aminoglutaric acid monohydrate, see DL-Glutamic acid monohydrate, A17719, p. 234 D-2-Aminoglutaric acid, see D-Glutamic acid, A14191, p. 234 L-2-Aminoglutaric acid, see L-Glutamic acid, A15031, p. 234 L-2-Aminoglutaric acid hydrochloride, see L-Glutamic acid hydrochloride, A12505, p. 234 | | |
| J62182 | DL-Aminogluthethimide, 99% [(±)-3-(4-Aminophenyl)-3-ethyl-2,6-piperidinedione] [125-84-8], C ₁₃ H ₁₆ N ₂ O ₂ , F.W. 232.28, Powder, m.p. 152-154°, Merck 14 , 440, EINECS 204-756-4, RTECS MA4026950, MDL MFCD00010122 ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | | 1g 5g 25g |
| | Application(s): Adrenocortical suppressant which also inhibits conversion of androgens to estrogens by the aromatase enzyme system | | |
| B24696 | Aminoguanidine hydrogen carbonate, 98+% [2582-30-1], CH ₅ N ₄ H ₂ CO ₃ , F.W. 136.11, m.p. ca 170° dec., d. 1.600, UN3077, EINECS 219-956-7, RTECS FG1772000, BRN 3569869, MDL MFCD00012949, † ! ⚠ H: H317-H411, P: P261-P280-P302+P352-P321-P363-P501a |  | 100g 500g 2.5kg |
| H55363 | 1-Amino-4-guanidinobutane sulfate salt, 97% [2482-00-0], H ₂ N(CH ₂) ₃ NHC(=NH)NH ₂ ·H ₂ SO ₄ , F.W. 228.27, Merck 14 , 188, EINECS 219-617-3, RTECS ME8413000, BRN 3918807, MDL MFCD00013109 | | 250mg 1g 5g |
| | D-2-Amino-5-guanidinopentanoic acid, see D-Arginine, A16137, p. 109 L-2-Amino-5-guanidinopentanoic acid, see L-Arginine, A15738, p. 109 DL-2-Amino-5-guanidinopentanoic acid monohydrochloride monohydrate, see DL-Arginine monohydrochloride monohydrate, A10758, p. 109 L-2-Amino-5-guanidinopentanoic acid hydrochloride, see L-Arginine monohydrochloride, A14730, p. 109 (R)-(-)-2-Aminohexanoic acid, see D-(-)-Norleucine, L08257, p. 304 (S)-(+)-2-Aminohexanoic acid, see L-(+)-Norleucine, L03913, p. 305 | | |






| Stock # | Description | Size | |
|---------|---|---|-------------|
| A14719 | 6-Aminohexanoic acid, 99% [ε-Aminocaproic acid, EACA] [60-32-2], H ₂ N(CH ₂) ₅ CO ₂ H, F.W. 131.18, m.p. 210-212°, Merck 14,432, EINECS 200-469-3, RTECS MO6300000, BRN 906872, MDL MFCD00008238, † Has been recommended as a reagent for the extraction of aldehydes from reaction mixtures, giving better recovery than bisulfite: <i>Chem. Pharm. Bull.</i> , 28 , 1917 (1980). | 100g 500g 2.5kg | |
| | J63012 | N-(6-Aminoethyl)-5-chloro-1-naphthalenesulfonamide hydrochloride [W-7 hydrochloride] [61714-27-0], C ₁₀ H ₂₁ ClO ₂ N ₂ S·HCl, F.W. 377.33, Powder, m.p. 217-220°, BRN 6030174 Application(s): Calmodulin antagonist | 100mg |
| | A13786 | 4-Aminohippuric acid, 97% [N-(4-Aminobenzoyl)glycine] [61-78-9], C ₈ H ₁₀ N ₂ O ₃ , F.W. 194.19, m.p. ca 200° dec., Merck 14,442, EINECS 200-518-9, BRN 1213676, MDL MFCD00007890, †  | 25g 100g |
| | Application(s): Useful in kidney function testing (2S,3R)-2-Amino-3-hydroxybutyric acid , see L-Threonine, Cell Culture Reagent, J63709, p. 368 | | |
| L08256 | 2-Amino-5-hydroxybenzoic acid, 98% [5-Hydroxyanthranilic acid] [394-31-0], C ₇ H ₇ NO ₃ , F.W. 153.14, m.p. ca 248° dec., BRN 2803663, MDL MFCD00007870  | 5g 25g | |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | | |
| | 4-Amino-2-hydroxybenzoic acid , see 4-Aminosalicylic acid, B23289, p. 99 (+/-)-2-Amino-3-hydroxybutyric acid , see DL-Threonine, A10606, p. 368 (2R,3S)-2-Amino-3-hydroxybutyric acid , see D-Threonine, B21177, p. 368 (2S,3R)-2-Amino-3-hydroxybutyric acid , see L-Threonine, A16851, p. 368 | | |
| J65145 | 4-Amino-3-hydroxybutyric acid [DL-γ-Amino-β-hydroxybutyric acid] [924-49-2], C ₆ H ₉ NO ₃ , F.W. 119.12, Powder, m.p. 223° dec., Merck 14,444, EINECS 213-106-9, RTECS ES7015000, BRN 1721708, MDL MFCD00008141, †  | 5g 25g 100g | |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | | |
| | Application(s): Reduces uptake of iodine by the thyroid glands in animals. Antispasmodic | | |
| | N1-[(S)-(-)-4-Amino-2-hydroxybutyryl]kanamycin A , see Amikacin, J60849, p. 91 DL-2-Amino-3-[3-(5-hydroxyindole)]propionic acid , see DL-5-Hydroxytryptophan, A12237, p. 252 L-2-Amino-3-[3-(5-hydroxyindole)]propionic acid , see L-5-Hydroxytryptophan hydrate, A13954, p. 252 α-Amino-3-hydroxy-5-isoxazoleacetic acid , see Ibotenic acid, 98+%, J60748, p. 253 2-Amino-2-hydroxymethyl-1,3-propanediol hydrochloride , see Tris(hydroxymethyl)aminomethane hydrochloride, A11379, p. 382 2-Amino-5-[1-hydroxy-2-[(1-methylethyl)amino]ethyl]benzonitrile , see Cimaterol, J60650, p. 163 [(2S,3R)-3-Amino-2-hydroxy-5-methylhexanoyl]-Val-Val-Asp-OH , see Amastatin hydrochloride, 98+%, J62932, p. 90 | | |
| J65847 | (S)-α-Amino-3-hydroxy-5-methyl-4-isoxazolepropionic acid ■ [(S)-2-Amino-3-(3-hydroxy-5-methylisoxazol-4-yl)propanoic acid] [83643-88-3], C ₇ H ₁₀ N ₂ O ₄ , F.W. 186.16, Powder, MDL MFCD00672630 | 5mg | |
| J64884 | Amino-3-hydroxy-5-methylisoxazole-4-propionic acid [(±)-α-Amino-3-hydroxy-5-methylisoxazole-4-propionic acid, (RS)-AMPA] [74341-63-2], C ₇ H ₁₀ N ₂ O ₄ , F.W. 186.17, Powder, MDL MFCD00213388 Application(s): Selective quisqualate agonist | 10mg | |
| | N-[(2S,3R)-3-Amino-2-hydroxy-1-oxo-4-phenylbutanoyl]-L-leucine , see Bestatin, J61106, p. 124 (R)-(-)-α-Amino-(4-hydroxyphenyl)acetic acid , see D-(-)-4-Hydroxyphenylglycine, L07190, p. 251 (+/-)-2-Amino-3-hydroxypropionic acid , see DL-Serine, A15184, p. 341 (R)-2-Amino-3-hydroxypropionic acid , see D-Serine, A11353, p. 341 (S)-2-Amino-3-hydroxypropionic acid , see L-Serine, A11179, p. 341 2-Amino-6-hydroxypurine , see Guanine, A12024, p. 240 2-Amino-4-hydroxypyrimidine , see Isocytosine, H54228, p. 260 4-Amino-2-hydroxypyrimidine , see Cytosine, A14731, p. 174 | | |
| B24012 | 4-Aminoimidazole-5-carboxamide hydrochloride, 98% ■ [AICAI] [72-40-2], C ₄ H ₆ N ₄ O·HCl, F.W. 162.58, m.p. ca 270° dec., EINECS 200-778-3, RTECS NI3911000, BRN 3701645, MDL MFCD00012704, † Starting material for synthesis of the antitumour agent temozolomide. A synthetic pathway employing Ethyl isocyanatoacetate , L10609, avoids the use of the highly toxic methyl isocyanate: <i>J. Chem. Soc., Perkin 1</i> , 2783 (1995). | 1g 5g 25g | |
| |  | | |
| J64720 | 5-Aminoimidazole-4-carboxamide 1-β-D-ribofuranoside, 98% [Acadesine, AICAR] [2627-69-2], C ₈ H ₁₄ N ₄ O ₅ , F.W. 258.23, Powder, m.p. 214-215°, EINECS 220-097-5, MDL MFCD00869751, †  | 50mg 200mg | |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | | |
| | Application(s): Activator of AMP-activated protein kinase (AMPK) L-2-Amino-3-(4-imidazolyl)propionic acid , see L-Histidine, Cell Culture Reagent, J63065, p. 246 L-2-Amino-3-(4-imidazolyl)propionic acid monohydrochloride monohydrate , see L-Histidine monohydrochloride monohydrate, Cell Culture Reagent, J61465, p. 246 (+/-)-2-Amino-3-(3-indolyl)propionic acid , see DL-Tryptophan, L05936, p. 384 (R)-2-Amino-3-(3-indolyl)propionic acid , see D-Tryptophan, A18426, p. 384 | | |

| Stock # | Description | Size |
|---------|--|---|
| | (S)-2-Amino-3-(3-indolyl)propionic acid, see L-Tryptophan, A10230, p. 384 2-Amino-4-(5-indolyl)-1,1,3-tricyanobuta-1,3-diene, see Tyrphostin B7, 95%, cis + trans, J63126, p. 387 | |
| A19838 | 2-Amino-5-iodobenzoic acid, 98% ▲ <i>[5-Iodoanthranilic acid]</i> [5326-47-6], C ₈ H ₆ INO ₂ , F.W. 263.03, m.p. ca 220° dec., EINECS 226-205-7, RTECS DG2802000, BRN 639029, MDL MFCD00007849, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a |  5g 25g |
| A13021 | 2-Aminoisobutyric acid, 99% <i>[H-Aib-OH, 2-Methylalanine]</i> [62-57-7], C ₅ H ₉ NO ₂ , F.W. 103.12, m.p. >300°, Merck 14,445, EINECS 200-544-0, RTECS AY7000000, BRN 506496, MDL MFCD00008049, † |  25g 100g 250g |
| A15074 | 5-Aminoisophthalic acid, 95% <i>[5-Aminobenzene-1,3-dicarboxylic acid]</i> [99-31-0], C ₈ H ₇ NO ₄ , F.W. 181.15, m.p. >300°, EINECS 202-748-5, BRN 2805628, MDL MFCD00002522, † ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a |  50g 250g |
| | DL-2-Aminoisovaleric acid, see DL-Valine, A16756, p. 390 D-2-Aminoisovaleric acid, see D-Valine, A18894, p. 390 L-2-Aminoisovaleric acid, see L-Valine, A12720, p. 390 (R)-(+)-4-Amino-3-isoxazolidinone, see D-Cycloserine, A18000, p. 172 5-Amino-4-ketovaleric acid hydrochloride, see 5-Aminolevulinic acid hydrochloride, A16942, p. 96 12-Aminolauric acid, see 12-Aminododecanoic acid, B25121, p. 93 | |
| A16942 | 5-Aminolevulinic acid hydrochloride, 99% ■ <i>[5-Amino-4-ketovaleric acid hydrochloride]</i> [5451-09-2], C ₇ H ₁₀ NO ₂ ·HCl, F.W. 167.59, m.p. ca 156 dec., Merck 14,446, EINECS 226-679-5, RTECS OI1640000, BRN 3690651, MDL MFCD00012869 |  100mg 500mg 2g |
| | 2-Amino-3-mercapto-3-methylbutanoic acid, see DL-Penicillamine, B24710, p. 313 DL-2-Amino-3-mercaptopropionic acid, see DL-Cysteine, H56126, p. 172 L-2-Amino-3-mercaptopropionic acid, see L-Cysteine, Cell Culture Reagent, J63745, p. 173 D-2-Amino-3-mercaptopropionic acid hydrochloride monohydrate, see D-Cysteine hydrochloride monohydrate, H27107, p. 173 2-Amino-6-mercaptapurine, see 6-Thioguanine, B21280, p. 367 | |
| J64244 | 2-Amino-3-methoxybenzoic acid <i>[3-Methoxyanthranilic acid]</i> [3177-80-8], C ₉ H ₉ NO ₃ , F.W. 167.16, Powder, m.p. 169-170°, MDL MFCD00075178 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5g 10g 25g |
| J64485 | 2'-Amino-3'-methoxyflavone, 99% <i>[PD 98059, 2-(2-Amino-3-methoxyphenyl)-4H-1-benzopyran-4-one]</i> [167869-21-8], C ₁₆ H ₁₃ NO ₃ , F.W. 267.28, Powder, MDL MFCD00671789 ! H:H302, P:P264-P270-P301+P312-P330-P501 Application(s): A MAP kinase inhibitor | 5mg 10mg 25mg |
| J60524 | (R)-(+)-1-Amino-2-(methoxymethyl)pyrrolidine <i>[RAMP]</i> [72748-99-3], C ₆ H ₁₄ N ₂ O, F.W. 130.19, Liquid, b.p. 186-187°, f.p. 71°(160°F), d. 0.978, n _D ²⁰ 1.464, BRN 4229866, MDL MFCD00010622 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): For synthesis of optically active products | Call |
| J61723 | (S)-(-)-1-Amino-2-(methoxymethyl)pyrrolidine <i>[SAMP]</i> [59983-39-0], C ₆ H ₁₄ N ₂ O, F.W. 130.19, Liquid, b.p. 42°, f.p. 71°(160°F), d. 0.97, n _D ²⁰ 1.465, BRN 1523794, MDL MFCD00064485 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): For synthesis of optically active products | Call |
| J65334 | 2-Amino-2'-O-methyladenosine, 99% <i>[2,6-Diamino-9-(2'-O-methyl-β-D-ribofuranosyl)purine, 2,6-Diaminopurine 2'-O-methylriboside]</i> [80791-87-3], C ₁₁ H ₁₆ N ₆ O ₄ , F.W. 296.28, Powder | 1g |
| B24230 | 2-Amino-3-methylbenzoic acid, 98% <i>[2-Amino-m-toluic acid, 3-Methylanthranilic acid]</i> [4389-45-1], C ₉ H ₉ NO ₂ , F.W. 151.16, m.p. 174-177°, EINECS 224-505-2, BRN 2359694, MDL MFCD00007745 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a |  1g 5g |
| | (R)-(-)-2-Amino-3-methyl-1-butanol, see D-(-)-Valinol, L14166, p. 390 (S)-(+)-2-Amino-3-methyl-1-butanol, see L-(-)-Valinol, L11300, p. 390 (+)-2-Amino-3-methylbutyric acid, see DL-Valine, A16756, p. 390 (R)-(-)-2-Amino-3-methylbutyric acid, see D-Valine, A18894, p. 390 (S)-(+)-2-Amino-3-methylbutyric acid, see L-Valine, A12720, p. 390 β-(Aminomethyl)-4-chlorobenzenethanesulfonic acid, see Saclofen, 99+%, J63345, p. 339 | |

| Stock # | Description | Size |
|---------------|--|---|
| A15017 | 7-Amino-4-methylcoumarin, 98% [Coumarin 120] [26093-31-2], C ₁₁ H ₉ NO ₂ , F.W. 175.19, m.p. 225-228°, EINECS 247-454-8, BRN 142231, MDL MFCD0006868, † ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250mg 1g 5g |
| |  | |
| B21742 | trans-4-(Aminomethyl)cyclohexanecarboxylic acid, 97% [1197-18-8], C ₈ H ₁₅ NO ₂ , F.W. 157.21, m.p. >300°, Merck 14,9569, EINECS 214-818-2, RTECS GU8400000, BRN 2207452, MDL MFCD00001466 ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 10g 50g 250g |
| |  | |
| | Application(s): Inhibits plasmin-induced fibrinolysis | |
| | α-(Aminomethyl)-4-hydroxybenzyl alcohol hydrochloride, see (+/-)-Octopamine hydrochloride, 99%, J61281, p. 360 4-(Aminomethyl)-5-hydroxy-6-methyl-3-pyridinemethanol dihydrochloride, see Pyridoxamine dihydrochloride, Cell Culture Reagent, J62679, p. 332 2-Amino-1-methyl-2-imidazolin-4-one, see Creatinine hydrochloride, 99+%, J61755, p. 169 (+/-)-2-Amino-3-methylpentanoic acid, see DL-Isoleucine, A17521, p. 260 (2R,3R)-2-Amino-3-methylpentanoic acid, see D-Isoleucine, H27488, p. 260 (2S,3S)-2-Amino-3-methylpentanoic acid, see L-Isoleucine, Cell Culture Reagent, J63045, p. 260 (±)-2-Amino-4-methylpentanoic acid, see DL-Leucine, A10590, p. 268 (R)-2-Amino-4-methylpentanoic acid, see D-Leucine, A14842, p. 268 (S)-2-Amino-4-methylpentanoic acid, see L-Leucine, A12311, p. 268 (S)-2-Amino-4-methylpentanol, see L-Leucinol, B23745, p. 268 | |
| J63144 | 2-Amino-2-methyl-1,3-propanediol, 99+% [Ammediol, AMPD] [124-68-5], (HOCH ₂) ₂ C(NH ₂)CH ₃ , F.W. 105.14, Powder, m.p. 100-110°, b.p. 151°/10mm, Merck 14,448, EINECS 204-100-7, RTECS TY2975000, BRN 635708, MDL MFCD0004678, † ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 25g 100g 250g |
| | Application(s): A useful biological buffer | |
| A17814 | 2-Amino-2-methyl-1-propanol, 95%, may cont. ca 5% water [AMP, Isobutanolamine] [124-68-5], C ₄ H ₁₁ NO, F.W. 89.14, m.p. 24-28°, b.p. 164-166°, f.p. 67°(152°F), d. 0.934, n _D ²⁰ 1.4455, Merck 14,449, Fieser 1,37 3,14 6,20, EINECS 204-709-8, RTECS UA5950000, BRN 505979, MDL MFCD0008051, † ! H: H315-H319-H412, P: P280g-P273-P305+P351+P338-P337+P313 Buffer and phosphate acceptor in assay of phosphatases: <i>Methods of Enzymatic Analysis</i> , 3rd ed., H. U. Bergmeyer, Ed., Verlag Chemie, Weinheim (1984), vol. 4, p76. Precursor of 2-substituted-4,4-dimethyl-2-oxazoline derivatives of carboxylic acids: <i>J. Org. Chem.</i> , 39 , 2787 (1974), developed by Meyers. The oxazoline, which is readily formed with the acid chloride and thionyl chloride, is stable to base, organometallic reagents, etc., but readily cleaved by dilute acid. For further information on the reactivity of these derivatives, see 2,4,4-Trimethyl-2-oxazoline, L00181 . 2-Aryl-4,4-dimethyl-2-oxazolines are activated towards ortho-lithiation: <i>J. Org. Chem.</i> , 40 , 3058 (1975). Methoxy- or fluoro-substituents in the ortho-position are readily substituted by organolithiums or Grignards, providing a versatile route to biaryls: <i>J. Am. Chem. Soc.</i> , 97 , 7383 (1975). For examples, see: <i>Org. Synth. Coll.</i> , 9 , 258 (1998). The oxazoline can also be converted to an aldehyde by methylation and borohydride reduction. | 100ml 500ml 2.5L |
| |  | |
| |  | |
| | For reviews of the use of oxazolines in synthesis, see: <i>Angew. Chem. Int. Ed.</i> , 15 , 270 (1976); <i>Tetrahedron</i> , 41 , 837 (1985); 50 , 2297 (1994). | |
| J60492 | (S)-(+)-2-(Aminomethyl)pyrrolidine △ [69500-64-7], C ₅ H ₁₁ N ₂ , F.W. 96.14, Liquid, b.p. 65°/10mm, f.p. 47°(117°F), d. 0.933, n _D ²⁰ 1.482, UN2734, MDL MFCD00191745 ! H: H314-H226, P: P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a | Call |
| | Application(s): For synthesis of optically active products (±)-2-Amino-4-(methylthio)butyric acid, see DL-Methionine, A11457, p. 283 (R)-2-Amino-4-(methylthio)butyric acid, see D-Methionine, B21213, p. 284 (S)-2-Amino-4-(methylthio)butyric acid, see L-Methionine, Cell Culture Reagent, J61904, p. 284 | |
| L03099 | 5-Aminonaphthalene-2-sulfonic acid, 97% [1,6-Cleve's Acid, 1-Naphthylamine-6-sulfonic acid] [119-79-9], C ₁₀ H ₇ NO ₂ S, F.W. 223.25, m.p. >300°, Merck 14,2350, EINECS 204-351-2, RTECS QK1285000, BRN 1819887, MDL MFCD00004030, † | 5g 25g |
| |  | |
| J65304 | 8-Aminonaphthalene-2-sulfonic acid, 95% [1-Naphthylamine-7-sulfonic acid, Cleves acid-1,7] [119-28-8], C ₁₀ H ₇ NO ₂ S, F.W. 223.25, Powder, m.p. >300°, Merck 142,351, UN2585, EINECS 204-311-4, BRN 2115629, MDL MFCD00004032, † ! H: H314, P: P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 25g 100g |
| |  | |




| Stock # | Description | Size |
|---------|--|-----------------------|
| J64358 | 4-Amino-1,8-naphthalimide, 97% [6-Aminobenzo[de]isoquinoline-1,3-dione] [1742-95-6], C ₁₂ H ₈ N ₂ O, F.W. 212.2, Solid, m.p. >360°, d. 1.105, EINECS 217-110-1, RTECS DE4081000, MDL MFCD00006921, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 100mg 1g |
| L06692 | 6-Aminonicotinamide, 99% [6-Aminopyridine-3-carboxamide] [329-89-5], C ₆ H ₇ N ₃ O, F.W. 137.14, m.p. 246-248°, EINECS 206-349-7, RTECS US4550000, BRN 116042, MDL MFCD00006327  ! H:H360, P:P281-P201-P202-P308+P313-P405-P501a | 1g 5g |
| | Application(s): Induces apoptosis in tumor cells | |
| | (2R*,3S*)-(+)-2-Amino-octadecane-1,3-diol, see DL-erythro-Dihydrosphingosine, J62103, p. 191 trans-D-erythro-2-Amino-4-octadecene-1,3-diol, see D-erythro-Sphingosine, 99+%, J63584, p. 351 trans-D-erythro-2-Amino-4-octadecene-1,3-diol hydrochloride, see D-erythro-Sphingosine hydrochloride, H52427, p. 351 (S)-2-Aminopentanedioic acid, see L-Glutamic acid monosodium salt, J63424, p. 234 (±)-2-Aminopentanoic acid, see DL-Norvaline, A15900, p. 305 (R)-2-Aminopentanoic acid, see D-Norvaline, B23444, p. 305 (S)-2-Aminopentanoic acid, see L-Norvaline, L08658, p. 305 4-Aminophenazone, see 4-Aminoantipyrine, A13846, p. 91 D-(-)-α-Aminophenylacetic acid, see D-(-)-2-Phenylglycine, A15669, p. 317 (S)-(+)-α-Aminophenylacetic acid, see L-(+)-2-Phenylglycine, A19360, p. 317 | |
| J65331 | 4-Amino-DL-phenylalanine [DL-Phe(4-NH2)-OH] [2922-41-0], C ₉ H ₁₂ N ₂ O ₂ , F.W. 180.2, Powder, EINECS 220-869-1, MDL MFCD00007917 | 1g 5g |
| | (R)-(-)-2-Amino-2-phenylethanol, see (R)-(-)-2-Phenylglycinol, A19030, p. 317 (S)-(+)-2-Amino-2-phenylethanol, see (S)-(+)-2-Phenylglycinol, L13265, p. 317 (+)-3-(4-Aminophenyl)-3-ethyl-2,6-piperidinedione, see DL-Aminoglutethimide, 99%, J62182, p. 94 | |
| J65814 | 4-Aminophenyl phosphate monosodium salt hydrate, 97% [Monosodium 4-aminophenyl phosphate hydrate] [52331-30-3], C ₆ H ₇ NNaO ₄ P.xH ₂ O, F.W. 211.09(anhy), Crystalline solid | 10mg 50mg 100mg |
| | Application(s): Substrate for the electrochemical measurement of alkaline phosphatase | |
| | (R)-(+)-1-Amino-1-phenylpropane, see (R)-(+)-1-Phenylpropylamine, L16319, p. 318 (S)-(-)-1-Amino-1-phenylpropane, see (S)-(-)-1-Phenylpropylamine, L16320, p. 318 (R)-(+)-2-Amino-3-phenyl-1-propanol, see D-Phenylalaninol, L09697, p. 316 (S)-(-)-2-Amino-3-phenyl-1-propanol, see L-Phenylalaninol, A11586, p. 316 (+)-2-Amino-3-phenylpropionic acid, see DL-Phenylalanine, A10132, p. 315 (R)-2-Amino-3-phenylpropionic acid, see D-Phenylalanine, A10572, p. 315 (S)-2-Amino-3-phenylpropionic acid, see L-Phenylalanine, A13238, p. 315 N-(4-Aminophenylsulfonyl)acetamide, see Sulfacetamide, A19836, p. 355 | |
| J64075 | (S)-(+)-2-Amino-4-phosphonobutyric acid, 99% ▲ [L-AP-4] [23052-81-5], C ₆ H ₁₀ NO ₅ P, F.W. 183.1, Powder, MDL MFCD00083244 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1mg 10mg |
| | Application(s): A NMDA agonist | |
| J64210 | (±)-2-Amino-5-phosphonopentanoic acid, 99% ▲ [DL-AP5, DL-2-Amino-5-phosphonovaleric acid] [76326-31-3], C ₈ H ₁₂ NO ₅ P, F.W. 197.13, Powder, BRN 2446389, MDL MFCD00010515 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10mg 50mg |
| | Application(s): A potent NMDA antagonist | |
| J64887 | (R)-(-)-2-Amino-5-phosphonopentanoic acid, 99% ▲ [D-AP5, D-2-Amino-5-phosphonovaleric acid] [79055-68-8], C ₈ H ₁₂ NO ₅ P, F.W. 197.13, Powder, RTECS RD2513000, MDL MFCD00078839 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1mg 10mg |
| | Application(s): A competitive NMDA antagonist | |
| J64921 | 4-Aminophthalhydrazide, 98% △ [6-Amino-2,3-dihydro-1,4-phthalazinedione, Isoluminol] [3682-14-2], C ₈ H ₇ N ₃ O ₂ , F.W. 177.16, Powder, m.p. 300°, BRN 164804, MDL MFCD00010560 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g 5g |
| | Application(s): A chemiluminescent molecule | |
| J60705 | Aminophylline, anhydrous, 98% [3,7-Dihydro-1,3-dimethylpurine-2,6-dione, complex with 1,2-ethanediamine (2:1), Theophylline hemi(ethyl-enediamine) complex] [317-34-0], C ₁₂ H ₁₆ N ₄ O ₂ .0.5C ₂ H ₆ N ₂ , F.W. 210.21, Powder, m.p. 269-274°, Merck 14,465, UN2811, EINECS 206-264-5, RTECS XH5600000, MDL MFCD00013221, † ! H:H301, P:P264-P270-P301+P310-P321-P405-P501a | 25g 100g 500g |
| | Application(s): A non-selective phosphodiesterase inhibitor | |



| Stock # | Description | Size |
|---------|--|----------------------|
| L14101 | (R)-(-)-1-Amino-2-propanol, 98% Δ ■ [(R)-(-)-Isopropanolamine] [2799-16-8], C ₃ H ₉ NO, F.W. 75.11, m.p. 24-26°, b.p. 160°, f.p. 71°(159°F), d. 0.960, n _D ²⁰ 1.4482, [α] _D ²⁰ -18° (c=1.8 in water), UN3259, EINECS 220-532-9, RTECS UA5775000, BRN 1718869, MDL MFCD00064428  | 250mg 1g 5g |
| | ! H:H314-H312, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a For an extensive review of the use of 1,2-amino alcohols as chiral auxiliaries in asymmetric synthesis, see: <i>Chem. Rev.</i> , 96 , 835 (1996). | |
| L14102 | (S)-(+)-1-Amino-2-propanol, 98% Δ ■ [(S)-(+)-Isopropanolamine] [2799-17-9], C ₃ H ₉ NO, F.W. 75.11, m.p. 24-26°, b.p. 160°, f.p. 71°(159°F), d. 0.960, n _D ²⁰ 1.4490, [α] _D ²⁰ +18.5° (c=1.8 in water), UN3259, EINECS 220-533-4, RTECS UA5775000, BRN 1718868, MDL MFCD00064429  | 250mg 1g |
| | ! H:H314-H312, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | |
| L11030 | (R)-(-)-2-Amino-1-propanol, 98% Δ ■ [H-D-Ala-ol, D-Alaninol] [35320-23-1], C ₃ H ₇ NO, F.W. 75.11, b.p. 174-176°, f.p. 83°(181°F), d. 0.965, n _D ²⁰ 1.4493, [α] _D ²⁰ -22° (c=2 in ethanol), UN2735, EINECS 220-533-4, RTECS UA5775000, BRN 1718866, MDL MFCD00064413  | 1g 5g 25g |
| | ! H:H314, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | |
| B24916 | (S)-(+)-2-Amino-1-propanol, 98% Δ ■ [H-Ala-ol, L-Alaninol] [2749-11-3], C ₃ H ₇ NO, F.W. 75.11, b.p. 174-176°, f.p. 83°(181°F), d. 0.965, n _D ²⁰ 1.4498, [α] _D ²⁰ +22° (c=2 in ethanol), UN2735, EINECS 220-388-7, BRN 1718865, MDL MFCD00064412  | 1g 5g 25g |
| | ! H:H314, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | |
| | 3-Aminopropionic acid , see β-Alanine, Cell Culture Reagent, J63435, p. 82 DL-2-Aminopropionic acid , see DL-Alanine, A12230, p. 82 D-2-Aminopropionic acid , see D-Alanine, A10231, p. 82 L-2-Aminopropionic acid , see L-Alanine, Cell Culture Reagent, J60279, p. 82 N-(3-Aminopropyl)-1,4-butanediamine trihydrochloride , see Spermidine trihydrochloride, 99+%, J61595, p. 351 N-(3-Aminopropyl)-1,4-diaminobutane , see Spermidine, A19096, p. 350 | |
| J64782 | 1-(4-Amino-2-n-propyl-5-pyrimidinylmethyl)-2-methylpyridinium chloride [Amprolium hydrochloride] [137-88-2], C ₁₁ H ₁₅ N ₅ Cl.HCl, F.W. 315.24, Powder, EINECS 205-307-5, RTECS TJ565000, BRN 4118699, MDL MFCD00078831 | 25g 100g |
| | Application(s): A thiamine analogue; blocks thiamine uptake and prevents carbohydrate synthesis | |
| J64919 | 2-Aminopurine, 98% [452-06-2], C ₄ H ₄ N ₆ , F.W. 135.13, Powder, m.p. 280-282°, EINECS 207-197-4, RTECS UO7475000, MDL MFCD00005566  | 250mg 500mg 1g |
| | ! H:H302, P:P264-P270-P301+P312-P330-P501 | |
| | Application(s): A protein kinase R inhibitor | |
| | 6-Aminopurine , see Adenine, A14906, p. 78 6-Aminopurine hydrochloride , see Adenine hydrochloride, A17622, p. 78 6-Aminopurine sulfate , see Adenine sulfate, A16964, p. 78 2-Amino-6-purinethiol , see 6-Thioguanine, B21280, p. 367 | |
| B23707 | 3-Aminopyrazine-2-carboxylic acid, 98+% [5424-01-1], C ₄ H ₅ N ₃ O ₂ , F.W. 139.11, m.p. 204-206° dec., EINECS 226-558-7, BRN 124835, MDL MFCD00006141  | 1g 5g 25g |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| J61470 | 4-Aminopyridine, 99+% [Fampridine, 4-Pyridinamine] [504-24-5], C ₅ H ₆ N ₂ , F.W. 94.12, Crystalline powder, m.p. 157-161°, b.p. 273-274°, f.p. 164°(327°F), d. 1.26, Merck 14,3933, UN2671, EINECS 207-987-9, RTECS US1750000, BRN 105782, MDL MFCD00006439, †  | 25g 100g |
| | ! H:H300-H311-H315-H319-H335-H411, P:P280h-P273-P270-P301+P310-P305+P351+P338-P302+P352 | |
| | Application(s): A potassium channel blocker | |
| | 6-Aminopyridine-3-carboxamide , see 6-Aminonicotinamide, L06692, p. 98 | |
| B24594 | 2-Aminopyrimidine, 98% [2-Pyrimidinamine] [109-12-6], C ₄ H ₅ N ₃ , F.W. 95.11, m.p. 123-127°, b.p. 159°/186mm, EINECS 203-648-4, RTECS UV6326000, BRN 107014, MDL MFCD00006089, †  | 100g 500g |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| B23289 | 4-Aminosalicylic acid, 98+% [4-Amino-2-hydroxybenzoic acid] [65-49-6], C ₇ H ₇ NO ₃ , F.W. 153.14, m.p. ca 135-145° dec., Merck 14,477, EINECS 200-613-5, RTECS VO1225000, BRN 473071, MDL MFCD00007789, †  | 100g 500g |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | DL-2-Aminosuccinamic acid monohydrate , see DL-Asparagine monohydrate, B20273, p. 110 L-2-Aminosuccinamic acid monohydrate , see L-(+)-Asparagine monohydrate, A15012, p. 111 | |



| Stock # | Description | Size |
|---------|---|--|
| | DL-Aminosuccinic acid , see DL-Aspartic acid, A13646, p. 111 D-Aminosuccinic acid , see D-Aspartic acid, B21184, p. 111 L-Aminosuccinic acid , see L-Aspartic acid, A13520, p. 111 (S)-2-Aminosuccinic acid 4-amide , see L-Asparagine monohydrate, Cell Culture Reagent, J62869, p. 111 3-(Aminosulfonyl)-5-(butylamino)-4-phenoxybenzoic acid , see Bumetanide, 98+%, J62302, p. 139 9-Amino-1,2,3,4-tetrahydroacridine hydrochloride , see Tacrine hydrochloride hydrate, 98+%, J60070, p. 357 9-Amino-1,2,3,4-tetrahydro-1-acridinol (2Z)-2-butenedioate , see Hydroxytacrine maleate salt, J60680, p. 252 | |
| J64527 | 1-Amino-3,6,9,12-tetraoxapentadec-14-yne [Acetylene-PEG4-amine] C ₁₁ H ₂₁ NO ₄ , F.W. 231.29, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 100mg 500mg |
| | 2-Amino-m-toluic acid , see 2-Amino-3-methylbenzoic acid, B24230, p. 96 2-Amino-1,3,5-triazin-2(1H)-one , see 5-Azacytosine, A13410, p. 112 4-Aminouracil , see 6-Aminouracil, L03332, p. 100 | |
| L04452 | 5-Aminouracil, 97% [5-Amino-2,4-dihydroxypyrimidine] [932-52-5], C ₄ H ₅ N ₃ O ₂ , F.W. 127.10, m.p. >300°, EINECS 213-252-3, RTECS YQ8740000, BRN 127250, MDL MFCD00006025, † ! H:H302, P:P264-P270-P301+P312-P330-P501a Condensation with crotonaldehyde gives 2,4-dioxo-6-methylpyrido[3,2-d]pyrimidine: <i>J. Chem. Soc. (C)</i> , 1745 (1967). An improved procedure has been used in synthesis of inhibitors of human thymidylate synthase: <i>J. Med. Chem.</i> , 27 , 1710 (1984), and of dihydrofolate reductases: <i>J. Med. Chem.</i> , 39 , 1836 (1996):  | 5g 25g  |
| | Review of the use of uracils as starting materials in heterocyclic synthesis: <i>Adv. Heterocycl. Chem.</i> , 55 , 130 (1992). | |
| L03332 | 6-Aminouracil, 98% [4-Amino-2,6-dihydroxypyrimidine, 4-Aminouracil] [873-83-6], C ₄ H ₅ N ₃ O ₂ , F.W. 127.10, m.p. 360°, EINECS 212-854-3, RTECS YQ8750000, BRN 120491, MDL MFCD00006071, † ! H:H302, P:P280f Silylation promotes regioselective alkylation at the 3-nitrogen: <i>Tetrahedron Lett.</i> , 32 , 6539 (1991). The products are intermediates in a versatile synthesis of xanthines: <i>Synthesis</i> , 1295 (1995):  | 100g 500g  |
| | L-(+)-2-Amino-5-ureidoveraleric acid , see L-Citrulline, A13316, p. 165 DL-2-Aminovaleric acid , see DL-Norvaline, A15900, p. 305 D-2-Aminovaleric acid , see D-Norvaline, B23444, p. 305 L-2-Aminovaleric acid , see L-Norvaline, L08658, p. 305 | |
| J60456 | Amiodarone hydrochloride [2-n-Butyl-3-benzofuranyl [4-[2-(diethylamino)ethoxy]-3,5-diiodophenyl] ketone hydrochloride] [19774-82-4], C ₂₈ H ₂₉ I ₂ NO ₂ ·HCl, F.W. 681.77, Powder, m.p. 156°, Merck 14,482, EINECS 243-293-2, RTECS OB1361000, MDL MFCD00069204 ! H:H302-H312-H332, P:P261-P280-P302+P352-P304+P340-P322-P501 | 1g 5g 25g |
| | Application(s): A non-selective ion channel blocker; also an antiarrhythmic agent | |
| J62242 | Amlodipine, 97+% [UK-48340] [88150-42-9], C ₂₀ H ₂₅ ClN ₂ O ₅ , F.W. 408.88, Crystalline powder, m.p. 134-136°, Merck 14,491, UN2811  H:H301-H318-H373-H400-H410, P:P260-P301+P310-P305+P351+P338-P321-P405-P501a | 1g 5g 10g |
| | Application(s): A calcium channel antagonist with potent antioxidant activity | |
| J62164 | Amlodipine besylate, 98+% [111470-99-6], C ₂₀ H ₂₅ ClN ₂ O ₅ ·C ₆ H ₅ SO ₃ H, F.W. 567.05, Solid, m.p. 195-204°, Merck 14,491, RTECS US7967700, MDL MFCD00887594 ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g 5g 25g |
| | Application(s): An L-type calcium channel antagonist with potent antioxidant activity | |
| | Ammediol , see 2-Amino-2-methyl-1,3-propanediol, 99+%, J63144, p. 97 | |
| J60688 | Ammonium acetate, 5M aq. soln. [631-61-8], CH ₃ COONH ₄ , F.W. 77.08, Liquid, † | 250ml 500ml |
| J62046 | Ammonium chloride, 0.5M aq. soln. [12125-02-9], NH ₄ Cl, F.W. 53.49, Liquid, † ! H:H302-H319, P:P280-P264-P305+P351+P338-P301+P312-P337+P313-P501 | 50ml 100ml |

| Stock # | Description | Size |
|---------|--|----------------------|
| 12361 | Ammonium chloride, 99.5% min ■ [12125-02-9], NH ₄ Cl, F.W. 53.49, Granular, m.p. 340° subl., d. ≈1.53, n _D ²⁰ 1.642, Merck 14,509, Solubility: Soluble in water, methanol, ethanol. Insoluble in acetone, ether, ethyl acetate., EINECS 235-186-4, RTECS BP4550000, MDL MFCD00011420, † ! H:H302-H319, P:P280-P264-P305+P351+P338-P301+P312-P337+P313-P501a | 500g 2kg |
| | Application(s): As a flux in galvanizing steel sheet, in batteries, to clean soldering irons, analytical lab reagent, in washing powders, electroplating, lustering cotton | |
| 40193 | Ammonium chloride, ACS, 99.5% min ■ [12125-02-9], NH ₄ Cl, F.W. 53.49, Crystalline, m.p. 340° subl., d. ≈1.53, n _D ²⁰ 1.642, Merck 14,509, EINECS 235-186-4, RTECS BP4550000, MDL MFCD00011420, † Maximum level of impurities: Insoluble matter 0.005%, Residue after ignition 0.01%, PO ₄ 2ppm, SO ₄ 0.002%, Ca 0.001%, Mg 5ppm, Heavy Metals (as Pb) 5ppm, Fe 2ppm, pH of a 5% solution 4.5-5.5 at 25° ! H:H302-H319, P:P280-P264-P305+P351+P338-P301+P312-P337+P313-P501a | 1kg 5kg |
| 87777 | Ammonium diamminetetrahydroxychromate(III) monohydrate, ACS, 93.0% min [Reinecke salt, Ammonium reineckate] [13573-16-5], NH ₄ [Cr(NH ₃) ₂ (SCN) ₂].H ₂ O, F.W. 354.44 (336.42anhy), Powder, Merck 14,8128, Solubility: Insoluble in dilute hydrochloric acid. Moderately soluble in water. Soluble in alcohol, UN3077, EINECS 237-003-3, MDL MFCD00066638, † Maximum level of impurities: Insoluble in dilute hydrochloric acid ≤ 0.05%, Sensitivity P.T. ! H:H400-H410-H302-EUH032-H312-H332, P:P261-P280-P302+P352-P304+P340-P322-P501a | 25g 100g |
| | Application(s): Used to precipitate primary and secondary amines as their ammonium salts | |
| 11598 | Ammonium dihydrogen phosphate, ACS, 98.0% min [mono-Ammonium phosphate, Ammonium phosphate, monobasic] [7722-76-1], NH ₄ H ₂ PO ₄ , F.W. 115.03, Crystalline, m.p. 190°, d. 1.803, Merck 14,543, Solubility: Freely soluble in water. Slightly soluble in alcohol. Insoluble in acetone, EINECS 231-764-5, MDL MFCD0003396, † Maximum level of impurities: Insoluble matter 0.005%, pH of a 5% solution 3.8-4.4 at 25°, Cl 5ppm, NO ₃ 0.001%, SO ₄ 0.01%, Heavy metals (as Pb) 5ppm, Fe 0.001%, Ca 0.001%, Mg 0.0005%, K 0.005%, Na 0.005%. ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 500g 2kg |
| | Application(s): Preparation of baking powder with sodium bicarbonate, in fermentation | |
| | Ammonium ferric sulfate , see Ammonium iron(III) sulfate dodecahydrate, 39391, p. 101 | |
| 11597 | Ammonium hydrogen phosphate, ACS, 98.0% min [Diammonium hydrogen phosphate, Phosphoric acid diammonium salt] [7783-28-0], (NH ₄) ₂ HPO ₄ , F.W. 132.06, Crystalline, m.p. 155° dec., d. 1.619, Merck 14,542, EINECS 231-987-8, MDL MFCD00010891, † Maximum level of impurities: Insoluble matter 0.005%, pH of a 5% solution 7.7-8.1 at 25°, Cl 0.001%, NO ₃ 0.003, SO ₄ 0.01%, Heavy metals (as Pb) 0.001%, Fe 0.001%, Ca 0.001%, Mg 0.0005%, K 0.005%, Na 0.005% ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250g 1kg |
| 33285 | Ammonium hydroxide, ACS, 28.0-30.0% NH₃ [1336-21-6], NH ₄ OH, F.W. 35.05, Liquid, d. 0.90, Merck 14,494, UN2672, EINECS 215-647-6, MDL MFCD00066650, † Maximum level of impurities: Residue after ignition 0.002%, CO ₂ 0.002%, Cl 0.5ppm, PO ₄ 2ppm, NO ₃ 2ppm, Sulfate (SO ₄) 2ppm, Fe 0.2ppm, Substances reducing permanganate P.T., Heavy Metals (as Pb) 0.5ppm ! H:H314-H400, P:P280-P273-P305+P351+P338-P309-P310 | 250g 1kg 5x1kg |
| 39391 | Ammonium iron(III) sulfate dodecahydrate, ACS, 98.5-102.0% [Ammonium ferric sulfate, Ferric ammonium sulfate] [7783-83-7], NH ₄ Fe(SO ₄) ₂ ·12H ₂ O, F.W. 482.19 (266.07anhy), Broken Crystals, m.p. 39-41°, d. 1.71, Merck 14,521, Solubility: Freely soluble in water. Insoluble in alcohol, MDL MFCD00150004, † Maximum level of impurities: Insoluble matter 0.01%, Cl 0.001%, NO ₃ 0.01%, Ca 0.01%, Mg 0.005%, K 0.005%, Na 0.02%, Cu 0.003%, Ferrous iron (Fe ⁺²) P.T. (limit about 0.001%), Zn 0.003% Application(s): In dyeing and printing textiles, as analytical lab reagent | 500g 2.5kg |
| 13448 | Ammonium iron(II) sulfate hexahydrate, ACS, 98.5-101.5% ▲ △ [Iron(II) ammonium sulfate, Ferrous ammonium sulfate] [7783-85-9], (NH ₄) ₂ Fe(SO ₄) ₂ ·6H ₂ O, F.W. 392.13 (284.04anhy), Crystalline, m.p. ca 100° dec., d. 1.864, Merck 14,521, Solubility: Soluble in water. Insoluble in alcohol, EINECS 233-382-4, RTECS BR6500000, MDL MFCD00150530, † Maximum level of impurities: Insoluble matter 0.01%, PO ₄ 0.003%, Ca 0.005%, Cu 0.003%, Mg 0.002%, Ferric ion (Fe ⁺³) 0.01%, Mn 0.01%, K 0.002%, Na 0.02%, Zn 0.003% ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 500g 2kg |
| | Application(s): Polymerization catalyst, photography | |
| A10533 | Ammonium peroxydisulfate, 98% ■ [Ammonium persulfate] [7727-54-0], (NH ₄) ₂ S ₂ O ₈ , F.W. 228.19, m.p. 120° dec., f.p. None, d. 1.982, n _D ²⁰ 1.50, Merck 14,541, Fieser 1,952 3,238 5,5 6,20 12,33 18,24, UN1444, EINECS 231-786-5, RTECS SE0350000, MDL MFCD0003390, † Note: Aqueous solution decomposes slowly at room temperature, † ! H:H334-H272-H302-H335-H315-H319-H317, P:P221-P210-P285-P305+P351+P338-P405-P501a In combination with AgNO ₃ and Cu(OAc) ₂ , promotes a carbamoyl radical process for the conversion of oxalic acid monoamides to isocyanates: <i>J. Org. Chem.</i> , 60 , 5430 (1995). | 500g 1kg 5kg |

| Stock # | Description | Size |
|---------|--|-------|
| J61856 | Ammonium peroxydisulfate, Electrophoresis Grade ▣ [Ammonium persulfate] [7727-54-0], (NH ₄) ₂ S ₂ O ₈ , F.W. 228.20, Powder, m.p. 120° dec., f.p. None, d. 1.982, n _D ²⁰ 1.5, Merck 14,541, UN1444, EINECS 231-786-5, RTECS SE0350000, MDL MFCD00003390, † | 25g |
| | | 100g |
| | Ammonium persulfate , see Ammonium peroxydisulfate, Electrophoresis Grade, J61856, p. 102 Ammonium purpurate , see Murexide, A17540, p. 296 Ammonium pyrrolidinedithiocarbamate , see 1-Pyrrolidinedithiocarbamic acid ammonium salt, B23731, p. 333 Ammonium reineckate , see Ammonium diamminetetraethiocyanatochromate(III) monohydrate, 87777, p. 101 | |
| J60368 | Ammonium sulfate, 0.5M aq. soln. [7783-20-2], (NH ₄) ₂ SO ₄ , F.W. 132.14, Liquid, † H:H303, P:P312 | 50ml |
| | | 100ml |
| J61620 | Ammonium sulfate, saturated soln. [7783-20-2], (NH ₄) ₂ SO ₄ , F.W. 132.14, Liquid, EINECS 231-984-1, † | 50ml |
| 11566 | Ammonium sulfate, ACS, 99.0% min [7783-20-2], (NH ₄) ₂ SO ₄ , F.W. 132.14, Granular, m.p. ca 280° dec., d. 1.769, Merck 14,555, Solubility: Soluble in water. Insoluble in alcohol and acetone, EINECS 231-984-1, RTECS BS4500000, MDL MFCD00003391, † Maximum level of impurities: Insoluble matter 0.005%. Residue after ignition 0.005%, pH of a 5% solution 5.0-6.0 at 25°, Cl 5ppm, NO ₃ 0.001%, PO ₄ 5ppm, Heavy Metals (as Pb) 5ppm, Fe 5ppm H:H303, P:P312 | 100g |
| | | 500g |
| | 2kg | |
| | 10kg | |
| | Application(s): In galvanizing steel, manufacturing of ammonia alum and sulfuric acid | |
| 89363 | Ammonium sulfate, 99.95% (metals basis) [7783-20-2], (NH ₄) ₂ SO ₄ , F.W. 132.14, Crystalline, m.p. ca 280° dec., d. 1.769, Merck 14,555, EINECS 231-984-1, RTECS BS4500000, MDL MFCD00003391, † H:H303, P:P312 | 100g |
| | | 500g |
| | 2kg | |
| J64419 | Ammonium sulfate, ultrapure, 99+% [7783-20-2], (NH ₄) ₂ SO ₄ , F.W. 132.14, Crystalline, m.p. ca 280° dec., d. 1.769, Merck 14,555, EINECS 231-984-1, RTECS BS4500000, MDL MFCD00003391, † | 100g |
| | | 500g |
| | 2kg | |
| 17658 | Ammonium L-(+)-tartrate, 98% ■ [L-(+)-Tartaric acid diammonium salt, Ammonium tartrate, dibasic] [3164-29-2], C ₄ H ₁₂ N ₂ O ₆ , F.W. 184.15, Crystalline, d. 1.6, Solubility: Soluble in water, alcohol, EINECS 221-618-9, RTECS WW8050000, BRN 6120352, MDL MFCD00013073, † H:H412, P:P273-P501a | 50g |
| | | 250g |
| | 1kg | |
| | | |
| | Ammonium tartrate, dibasic , see Ammonium L-(+)-tartrate, 17658, p. 102 Ammonium tetrathiocyanatodiammine chromate(III) , see Ammonium diamminetetraethiocyanatochromate(III) monohydrate, 87777, p. 101 AMN107 , see Nilotinib, 99+%, J62578, p. 303 Amosyt , see Dimenhydrinate, J63718, p. 194 | |
| J61290 | Amoxicillin trihydrate [61336-70-7], C ₁₆ H ₁₉ N ₅ O ₆ S 3H ₂ O, F.W. 419.45 (365.40anhy), Powder, Merck 14,577, EINECS 243-003-8, RTECS XH8310000, BRN 7507120, MDL MFCD00072029 | 10g |
| | | 25g |
| | H:H334-H317, P:P285-P261-P280-P302+P352-P321-P501a | |
| | Application(s): A semi-synthetic antibiotic similar to penicillin | |
| | AMP , see 2-Amino-2-methyl-1-propanol, A17814, p. 97 5'-AMP , see Adenosine-5'-monophosphoric acid monohydrate, L14051, p. 79 | |
| J62043 | AMP, 0.2M buffer soln., pH 9.0 [4958-39-8], Liquid | 100ml |
| | | 250ml |
| J63988 | AMP, 0.2M buffer soln., pH 9.5 [4958-39-8], Liquid | 100ml |
| | | 250ml |
| J63290 | AMP, 0.2M buffer soln., pH 10.0 [4958-39-8], Liquid | 100ml |
| | | 250ml |
| J62474 | AMP, 0.2M buffer soln., pH 10.5 [4958-39-8], Liquid | 100ml |
| | | 250ml |
| | 5'-AMP.2Na , see Adenosine-5'-monophosphate disodium salt, J61643, p. 79 AMPD , see 2-Amino-2-methyl-1,3-propanediol, 99+%, J63144, p. 97 | |
| J60276 | AMPD, 0.2M buffer soln., pH 7.5 [115-69-5], Liquid, † | 100ml |
| | | 250ml |
| J61377 | AMPD, 0.2M buffer soln., pH 8.9 [115-69-5], Liquid, † | 100ml |
| | | 250ml |
| J60916 | AMPD, 0.2M buffer soln., pH 9.5 [115-69-5], Liquid, † | 100ml |
| | | 250ml |




| Stock # | Description | Size |
|---------|---|---------------------|
| J61491 | Amphotericin B, Streptomyces nodosus [1397-89-3], C ₄₇ H ₇₃ NO ₁₇ , F.W. 924.10, Powder, Merck 14,585, EINECS 215-742-2, RTECS BU2625000, BRN 78342, MDL MFCD0087763 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 100mg 1g 5g |
| J60977 | Ampicillin [69-53-4], C ₁₆ H ₁₉ N ₃ O ₅ S, F.W. 349.40, Powder, m.p. 208° dec., Merck 14,586, EINECS 200-709-7, RTECS XH8350000, BRN 1090925, MDL MFCD00005175 ! H:H334-H335-H315-H319-H317, P:P285-P305+P351+P338-P302+P352-P321-P405-P501a | 5g 25g |
| J63807 | Ampicillin sodium salt [69-52-3], C ₁₆ H ₁₈ N ₃ NaO ₅ S, F.W. 371.39, Powder, m.p. 215°, Merck 14,586, EINECS 200-708-1, RTECS XH8400000, BRN 4119211, MDL MFCD00064313 ! H:H334-H317, P:P285-P261-P280-P302+P352-P321-P501a | 1g 5g 10g |
| J62378 | AMPSO, 98+% [N-(1,1-Dimethyl-2-hydroxyethyl)-3-amino-2-hydroxypropanesulfonic acid] [68399-79-1], C ₇ H ₁₇ NO ₅ S, F.W. 227.28, Crystals, m.p. 215-225°, EINECS 269-991-7, BRN 5929916, MDL MFCD00041777, † Application(s): Useful as a buffer | 25g 100g |
| J61467 | AMPSO, 0.2M buffer soln., pH 8.0 [102029-60-7], Liquid | 100ml 250ml |
| J61238 | AMPSO, 0.2M buffer soln., pH 8.5 [102029-60-7], Liquid | 100ml 250ml |
| J62328 | AMPSO, 0.2M buffer soln., pH 9.0 [102029-60-7], Liquid | 100ml 250ml |
| J63354 | AMPSO, 0.2M buffer soln., pH 9.5 [102029-60-7], Liquid | 100ml 250ml |
| J62655 | Amrinone, 98% [5-Amino-(3,4'-bipyridin)-6(1H)-one] [60719-84-8], C ₁₀ H ₈ N ₂ O, F.W. 187.20, Crystals, m.p. 294-297° dec, Merck 14,592, UN2811, EINECS 262-390-0, RTECS DW2500000, MDL MFCD00083228 ! H:H301, P:P264-P270-P301+P310-P321-P405-P501a Application(s): Phosphodiesterase III inhibitor and inhibits platelet aggregation | 250mg 1g |
| J61472 | D-Amygdalin, 98% [D-Mandelonitrile-β-D-glucosido-6-β-D-glucoside] [29883-15-6], C ₂₀ H ₂₇ NO ₁₁ , F.W. 457.44, Powder, m.p. 210-215°, Merck 14,597, EINECS 249-925-3, RTECS OO8450000, BRN 66856, MDL MFCD00006598 ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): A benzylic glycoside that has been used as an antineoplastic agent | 1g 5g 25g |
| L12731 | D-Amygdalin hydrate, 96% [D-Mandelonitrile-β-D-glucosido-6-β-D-glucoside] [29883-15-6], C ₂₀ H ₂₇ NO ₁₁ ·xH ₂ O, F.W. 457.44(anhly), m.p. 215-220°, [α] _D ²⁰ -38° (c=1.2 in water), Merck 14,597, EINECS 249-925-3, RTECS OO8450000, BRN 66856, MDL MFCD00006598 ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): A benzylic glycoside that has been used as an antineoplastic agent | 2g 10g |
| |  | |
| L12089 | (±)-Anabasin, tech. 85% [Neonicotinic, 2-(3-Pyridyl)piperidine] [13078-04-1], C ₁₀ H ₁₄ N ₂ , F.W. 162.24, m.p. ca 9°, b.p. 270-272°, f.p. 93°(199°F), d. 1.046, n _D ²⁰ 1.5440, Merck 14,619, UN3140, RTECS BV4375000, BRN 82639, MDL MFCD00006370 ! H:H300-H310-H411, P:P301+P310-P361-P302+P350-P321-P405-P501a | 25mg 100mg |
| |  | |
| | Anafranil hydrochloride , see Clomipramine hydrochloride, J62485, p. 165 Ancitabine hydrochloride , see Cyclocytidine hydrochloride, 98+%, J63845, p. 171 | |
| A13482 | trans-Anethole, 98+% ▲ [(E)-1-Methoxy-4-propenylbenzene, trans-4-Propenylanisole] [4180-23-8], C ₁₀ H ₁₂ O, F.W. 148.21, m.p. 20-23°, b.p. 232-235°, f.p. 96°(205°F), d. 0.991, n _D ²⁰ 1.5610, Merck 14,643, EINECS 224-052-0, RTECS BZ9275000, BRN 774229, MDL MFCD00009284, † H:H227, P:P210-P280-P370+P378a-P403+P235-P501a Application(s): Inhibits lung and forestomach carcinogenesis | 25g 100g 500g |
| |  | |
| | Aneurine hydrochloride , see Thiamine hydrochloride, A19560, p. 366 Aneurinepyrophosphoric acid , see Thiamine pyrophosphate chloride, 98%, J61483, p. 366 | |









| Stock # | Description | Size |
|---------|--|-----------------------|
| J61129 | Angiotensin, (rat or canine) [H-Asp-Arg-Val-Tyr-Ile-His-Pro-OH] C ₄₁ H ₆₂ N ₁₂ O ₁₁ , F.W. 899.03, Powder | 5mg |
| J62102 | Angiotensin I (human) [Hypertensin I, H-Asp-Arg-Val-Tyr-Ile-His-Pro-Phe-His-Leu-OH] [484-42-4], C ₆₂ H ₈₉ N ₁₇ O ₁₄ , F.W. 1296.50, Powder, MDL MFCD00133091 | 5mg 10mg 25mg |
| J60866 | Angiotensin II (human) [H-Asp-Arg-Val-Tyr-Ile-His-Pro-Phe-OH acetate salt] [4474-91-3], C ₅₀ H ₇₇ N ₁₃ O ₁₂ , F.W. 1046.19, Powder, RTECS BW2165000 | 5mg 10mg 25mg |
| J61756 | Angiotensin III (human) [H-Arg-Val-Tyr-Ile-His-Pro-Phe-OH] [12687-51-3], C ₄₈ H ₆₈ N ₁₂ O ₉ , F.W. 931.10, Powder, BRN 8385695, MDL MFCD00133094 | 5mg 25mg |
| J63143 | Angiotensin Converting Enzyme Inhibitor [H-pGlu-Trp-Pro-Arg-Pro-Gln-Ile-Pro-Pro-OH] [35115-60-7], C ₅₃ H ₇₆ N ₁₄ O ₁₂ , F.W. 1101.30, Powder, MDL MFCD00076208 | 5mg |
| J61332 | Angiotensin Converting Enzyme Substrate [Bz-Phe-Ala-Pro-OH] [69677-91-4], C ₂₄ H ₂₇ N ₅ O ₅ , F.W. 437.50, Powder | 5mg |
| A13024 | Aniline hydrochloride, 99% ■ [142-04-1], C ₆ H ₇ N HCl, F.W. 129.59, m.p. 196-200°, b.p. 245°, f.p. 193° (379°F), d. 1.221, Merck 14,659, UN1548, EINECS 205-519-8, RTECS CY0875000, BRN 3593823, MDL MFCD00012958, †  H:H301-H311-H331-H372-H341-H351-H318-H400-H317, P:P280-P273-P305+P351+P338-P361-P304+P340-P309+P311 A convenient method has been described for generating aryl isocyanates from aniline hydrochlorides and oxalyl chloride, via thermolysis of the intermediate oxamic chloride: <i>Tetrahedron Lett.</i> , 45 , 4769 (2004). | 100g 500g 2.5kg |
| J65332 | 8-Anilinoanthracene-1-sulfonic acid, 95% [N-Phenyl peri acid, ANS] [82-76-8], C ₁₆ H ₁₃ NO ₃ S, F.W. 299.34, Powder, m.p. 215-217°, Merck 14,661, EINECS 201-438-7, BRN 1843887, MDL MFCD00003998, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): Fluorescent probe for proteins on polyacrylamide gels | 5g 25g 100g |
| J65538 | 8-Anilinoanthracene-1-sulfonic acid ammonium salt, 98% ▲ ▴ ■ [1,8-ANS NH ₄ , Ammonium 8-anilino-1-naphthalenesulfonate] [28836-03-5], C ₁₆ H ₁₃ NO ₃ S.NH ₃ , F.W. 316.37, Crystalline powder, m.p. 242-244°, EINECS 249-265-6, BRN 3581235, MDL MFCD00012560, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): Fluorescent probe for proteins on polyacrylamide gels | 5g 25g 100g |
| J61661 | Aniracetam [1-(4-Methoxybenzoyl)-2-pyrrolidinone] [72432-10-1], C ₁₂ H ₁₃ NO ₃ , F.W. 219.24, Powder, Merck 14,662, RTECS UY5781900, MDL MFCD00153767 Application(s): AMPA receptor potentiator. Slows the rate of ion-channel closing | 1g |
| J62964 | Anisomycin, 97+% [(2R,3S,4S)-2-(4-Methoxybenzyl)-3,4-pyrrolidinediol-3-acetate, Flagecidin] [22862-76-6], C ₁₈ H ₁₉ NO ₇ , F.W. 265.31, Powder, m.p. 140-141°, Merck 14,670, UN3462, EINECS 245-269-7, RTECS BZ9800000, BRN 20705, MDL MFCD00077650  H:H301, P:P264-P270-P301+P310-P321-P405-P501a Application(s): A protein synthesis inhibitor. Causes apoptosis of PC12 Cells | 10mg 50mg |
| J63107 | Anorexigenic Peptide [pGlu-His-Gly-OH] [69275-10-1], C ₁₃ H ₁₇ N ₅ O ₅ , F.W. 323.40, Powder, MDL MFCD00079240 Application(s): An appetite-suppressing peptide | 1mg 2mg |
| J62511 | Antazoline hydrochloride, 98% [2-(N-Benzylanilinomethyl)-2-imidazoline hydrochloride] [2508-72-7], C ₁₇ H ₁₉ N ₃ HCl, F.W. 301.82, Powder, m.p. 237-241°, Merck 14,680, EINECS 219-719-8, RTECS NJ2150000, MDL MFCD00058145 ! H:H302-H312-H332-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): Imidazoline binding site ligand and an antihistamine | 25g |








| Stock # | Description | Size |
|--|--|--|
| A14049 | Anthracene-9-carboxylic acid, 98+% [9-Anthroic acid] [723-62-6], C ₁₄ H ₁₀ O ₂ , F.W. 222.24, m.p. ca 218° dec., EINECS 211-964-9, RTECS CB8764000, BRN 1875336, MDL MFCD00001257, † ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a |  10g 50g 250g |
| Application(s): Chloride ion transport inhibitor | | |
| β-Anthraniloyl-L-alanine, see L-Kynurenine, J60199, p. 264 | | |
| 9-Anthroic acid, see 9-Anthracenecarboxylic acid, A14049, p. 105 | | |
| 30739 | Anthrone, ACS ▲ [90-44-8], C ₁₄ H ₁₀ O, F.W. 194.23, Crystalline, m.p. 155-158°, Merck 14,691 , EINECS 201-994-0, RTECS CB8925500, BRN 1910173, MDL MFCD00001187, † Maximum level of impurities: Melting point no more than a 5° range including 156°, Sensitivity to carbohydrates P.T., Absorbance of reagent solution P.T., Solubility in ethyl acetate P.T. ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a |  25g 100g |
| Application(s): Used for determination of carbohydrates | | |
| J64642 | Anti-Apo[a] antibody, from goat | 1ml |
| J65053 | Anti-Fibroblast Growth Factor, basic, from rabbit Note: Source: Rabbit IgG | 0.5mg |
| Application(s): Suitable for immunohistochemical applications, inhibition and Western blotting. | | |
| J63020 | Antibiotic A23187, 99+% [Calcimycin, Calcium ionophore A23187] [52665-69-7], C ₂₈ H ₃₇ N ₃ O ₈ , F.W. 523.62, Powder, Merck 14,1639 , EINECS 258-084-1, RTECS DM4676000, BRN 1096801, MDL MFCD00151202 ! H: H302-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 10mg 50mg |
| Application(s): An antibiotic and calcium ionophore | | |
| Antibiotic AM-2282, see Staurosporine, 99+%, J62837, p. 352 | | |
| Antibiotic K178 sodium salt, see Nigericin sodium salt, 98+%, J61349, p. 302 | | |
| Antibiotic S 7481F1, see Cyclosporin A, 99+%, J63191, p. 172 | | |
| J60749 | Antibody & Antigen purification buffers Liquid, Note: Contains 1L of 1M Tris-HCl (pH 8.0) and 500 ml of 100mM Glycine (pH 2.5), † | 1kit |
| Application(s): Buffers for immunoaffinity purification of antibodies. | | |
| J63014 | Antibody purification on protein A column Liquid, Note: This kit contains: 1L of 1M Tris-HCl (pH 8.0) and 500ml of 100mM Glycine (pH 3.0)., † | 1kit |
| Application(s): Buffers to be used when performing antibody purification using immobilized Protein A. | | |
| J64001 | Anti-cyclic AMP antibody Note: Source: Rabbit | 100tubes 1000tubes |
| Application(s): Unconjugated antibody. Suitable for radioimmunoassays. | | |
| J64263 | Anti-cyclic AMP antibody, preconjgated Note: Source: Rabbit | 100tubes |
| Application(s): Preconjgated antibody. Suitable for radioimmunoassays. | | |
| J64025 | Anti-cyclic GMP antibody Note: Source: Rabbit | 100tubes 1000tubes |
| Application(s): Unconjugated antibody. Suitable for radioimmunoassays. | | |
| J64514 | Anti-cyclic GMP antibody, preconjgated Note: Source: Rabbit | 100tubes |
| Application(s): Preconjgated antibody. Suitable for radioimmunoassays. | | |
| J65649 | Anti-Cytokeratin antibody, from rabbit, whole serum Note: Source: Rabbit; Species reactivity: Vertebrates | 1ml |
| Application(s): Suitable for immunohistochemical applications and Western blotting. A whole serum preparation | | |
| J65390 | Anti-EGF antibody, from rabbit Note: Source: Rabbit; Species reactivity: rat | 500tubes |
| Application(s): Suitable for radioimmunoassays. A component in Rat EGF Assay kit. | | |
| J65464 | Anti-EGF antibody, from rabbit Note: Source: Rabbit; Species reactivity: mouse | 100microliters |
| Application(s): Suitable for radioimmunoassays, double immunodiffusion and inhibition. A whole serum preparation | | |
| J64008 | Anti-EGF antibody, from rabbit, whole serum Note: Source: Rabbit; Species reactivity: human | 0.5ml |
| Application(s): Affinity purified. Suitable for immunohistochemical applications. A whole serum preparation. | | |
| J65866 | Anti-EGF antibody, from rabbit, whole serum Note: Source: Rabbit; Species reactivity: rat | 1each |
| Application(s): Suitable for immunohistochemical applications, inhibition, and western blotting. A whole serum preparation | | |








| Stock # | Description | Size |
|---------|---|---------------|
| J65056 | DNA Polymerase I Large (Klenow Fragment) [9012-90-2], F.W. 68kDa, Liquid, EINECS 232-741-2, † Application(s): Has 5' to 3' polymerase activity as well as 3' to 5' exonuclease activity. For generating complementary strands of cDNA | 500units |
| J64158 | Anti-Fibronectin, antibody, from rabbit Note: Source: Rabbit; Species reactivity: human Application(s): Affinity purified. | 100micrograms |
| J65644 | Anti-Fibronectin antibody, from rabbit Note: Source: Rabbit IgG; Species reactivity: mouse Application(s): Affinity purified. Suitable for immunohistochemical applications and Western blotting | 0.5ml |
| J64763 | Anti-Fibronectin antibody, from rabbit, whole serum Note: Source: Rabbit; Species reactivity: human Application(s): Suitable for immunohistochemical applications and double immunodiffusion studies. A whole serum preparation. | 1ml |
| J64334 | Anti-GFAP antibody, from rabbit Note: Source: Rabbit Application(s): Suitable for immunohistochemical applications and Western blotting | 0.5ml |
| J64177 | Anti-Goat IgG, from donkey Note: Source: Donkey Application(s): Precipitating Antibody | 5ml |
| J65602 | Anti-Involucrin antibody kit Note: Source: Rabbit; Species reactivity: human Application(s): Suitable for immunohistochemical applications. | 1kit |
| J65295 | Anti-Laminin antibody, from rabbit Note: Source: Rabbit IgG Application(s): Suitable for immunohistochemical applications, ELISA and Western blotting. Adsorbed | 0.5ml |
| J64398 | Anti-LDL antibody, from rabbit Note: Affinity purified | 1ml |
| J65202 | Anti-Lysozyme antibody, from mouse Note: Source: Mouse IgG1; Species reactivity: human Application(s): Monoclonal antibody. Suitable for immunohistochemical applications, Western blotting, ELISA, and inhibition studies. | 1each |
| J64787 | Anti-Mouse IgG-Peroxidase, from goat Note: Source: Goat Application(s): Adsorbed. Suitable for enzyme immunoassays, immunohistochemistry and Western blotting. | 1mg |
| J63522 | Antimycin A ▲ [1397-94-0], C ₂₈ H ₄₀ N ₂ O ₉ , F.W. 548.63, Powder, m.p. 149-150°, Merck 14,714, UN3462, RTECS CD0350000, MDL MFCD01779723, Note: Isolated from Streptomyces sp.  H: H300, P: P264-P270-P301+P310-P321-P405-P501a | 5mg 10mg |
| J64817 | Anti-Myosin (Smooth Muscle) antibody, from rabbit Note: Source: Rabbit IgG. Species reactivity: vertebrates. Application(s): Suitable for immunohistochemical applications, Western blotting and immunoprecipitation studies. | 0.5ml |
| J64913 | Anti-Myosin antibody, from rabbit Note: Source: Rabbit IgG. Species reactivity: vertebrates. Reacts with smooth and non-muscle myosin. Application(s): Suitable for immunohistochemical applications, Western blotting and immunoprecipitation studies. | 0.5ml |
| J65418 | Anti-Myosin IIA (non muscle) antibody, from rabbit Note: Source: Rabbit. Species reactivity: vertebrates. Application(s): Suitable for immunohistochemical applications, Western blots, and immunoprecipitations. | 0.5ml |
| J64696 | Anti-Nerve Growth Factor antibody, from rabbit Note: Source: Rabbit Application(s): Adsorbed. Suitable for immunohistochemical applications, Western blotting and inhibition studies. | 0.5ml |
| J65216 | Anti-Osteocalcin antibody, from goat, whole serum Note: Source: Goat; Species reactivity: mouse Application(s): Suitable for immunohistochemical applications. Lyophilized from whole serum | 0.25ml |
| J64663 | Anti-Osteocalcin antibody, from goat, whole serum, RIA Grade Note: Source: Goat; Species reactivity: mouse Application(s): Suitable for radioimmunoassays. A whole serum preparation | 500each |






| Stock # | Description | Size |
|---------|---|--------------------|
| J64503 | Anti-Osteocalcin antibody, from rabbit, whole serum Note: Source: Rabbit; Species reactivity: bovine Application(s): Suitable for immunohistochemical applications. Lyophilized from whole serum. | 0.5ml |
| J65982 | Anti-Osteocalcin antibody, from rabbit, whole serum Note: Source: Rabbit; Species reactivity: human Application(s): Suitable for immunohistochemical applications. Lyophilized from whole serum | 0.5ml |
| J64638 | Anti-Osteocalcin antibody, RIA Grade Note: Species reactivity: rat | 500each |
| J60011 | Antipain [[/S)-1-Carboxy-2-phenyl-ethyl]-carbamoyl-Arg-Val-Arg-aldehyde] [37691-11-5], C ₂₇ H ₄₄ N ₁₀ O ₆ , F.W. 604.70, Powder, EINECS 253-631-0, RTECS YV9350700, BRN 6837629, MDL MFCD00135959 ! H:H302, P:P264-P270-P301+P312-P330-P501a Application(s): A natural protease inhibitor for trypsin, papain and cathepsins A and B | 50mg |
| J63680 | Antipain dihydrochloride, 99+% [37682-72-7], C ₂₇ H ₄₄ N ₁₀ O ₆ ·2HCl, F.W. 677.60, Powder, RTECS YV9350800, MDL MFCD00135957 Application(s): A natural protease inhibitor for trypsin, papain and cathepsins A and B | 5mg |
| J64286 | Anti-Platelet Derived Growth Factor-BB antibody, from sheep Note: Source: Sheep IgG Application(s): Neutralizing Antibody. Suitable for use in ELISA. | 0.5mg |
| J64160 | Anti-Rabbit IgG, from goat Note: Source: Goat Application(s): Precipitating Antibody | 5ml |
| J64967 | Anti-Rabbit IgG-FITC from goat Note: Source: Goat Application(s): A monospecific IgG suitable for immunohistochemical applications. | 1ml |
| J64155 | Anti-Rabbit IgG-Peroxidase, from goat Note: Source: Goat Application(s): Affinity purified. Suitable for immunohistochemical applications and Western blotting | 1ml |
| J65031 | Anti-Rabbit IgG-TRITC, from goat Note: Source: Goat Application(s): Adsorbed. Suitable for immunohistochemical applications. | 1ml |
| J64717 | Antireproductive tripeptide [Bovine Pineal Antireproductive Tripeptide, H-Thr-Ser-Lys-OH acetate salt] [71730-64-8], C ₁₃ H ₂₆ N ₄ O ₆ , F.W. 334.37, Powder | 10mg 25mg |
| J65931 | Anti-Sheep IgG, from donkey Note: Source: Donkey Application(s): Precipitating Antibody | 5ml |
| J65429 | Anti-Tamm Horsfall Glycoprotein antibody, from rabbit [Anti-UMOD, Anti-Uromodulin antibody] | 0.5ml |
| J65575 | Anti-Transglutaminase Type I antibody Note: Source: Mouse IgG2a; Species reactivity: human Application(s): Monoclonal antibody. Suitable for immunohistochemical applications, ELISA and immunoprecipitation. | 0.5ml |
| J60961 | Apamin [H-Cys-Asn-Cys-Lys-Ala-Pro-Glu-Thr-Ala-Leu-Cys-Ala-Arg- Arg-Cys-Gln-Gln-His-NH ₂ (Cys1-Cys11, Cys3-Cys15)] [24345-16-2], C ₇₀ H ₁₃₁ N ₅ O ₂₄ S ₄ , F.W. 2027.37, Powder, Merck 14,725, EINECS 246-182-7, RTECS CD6899900, MDL MFCD00167944 Application(s): Neurotoxic peptide isolated from honeybee venom. Blocks calcium-activated potassium channels APC , see Aphidicolin, J60236, p. 107 APDC , see 1-Pyrrolidinedicarbothioic acid ammonium salt, B23731, p. 333 | 0.5mg |
| J60236 | Aphidicolin [APC] [38966-21-1], C ₂₀ H ₃₀ O ₄ , F.W. 338.48, Crystalline powder, m.p. 224°, Merck 14,727, RTECS PB9185000, BRN 4689958, MDL MFCD00083214 Application(s): A DNA polymerase inhibitor. Blocks the cell cycle at the early S-phase Apigenin , see 4',5,7-Trihydroxyflavone, L15041, p. 377 | 1mg 5mg 10mg |
| J60630 | Apoferitin, from horse spleen [9013-31-4], Freeze-dried powder, MDL MFCD00081365 Application(s): Gel filtration molecular weight marker | 100mg |

| Stock # | Description | Size |
|---|---|--|
| J64506 | Apolipoprotein A-I, human plasma 95% [Apo A-I] | 1mg |
| J64658 | Apolipoprotein A-II, human plasma, 95% [Apo A-II] | 1mg |
| J65320 | Apoptosis Activator 2 ▲ [1-[(3,4-Dichlorophenyl)methyl]-1H-indole-2,3-dione] [79183-19-0], C ₁₅ H ₉ Cl ₂ NO ₂ , F.W. 306.14, Powder | 5mg 25mg |
| J65987 | Apoptosis Inhibitor II, Ns3694 [4-Chloro-2-[3-(3-trifluoromethyl-phenyl)-ureido]benzoic acid] [426834-38-0], C ₁₅ H ₁₀ ClF ₃ N ₂ O ₃ , F.W. 358.70, Powder, MDL MFCD00249000 | 10mg 50mg |
| J65477 | APP Gamma Secretase Inhibitor ▲ [3-5 Difluorophenacetyl-Ala-S-phenylglycine-methylester] C ₂₀ H ₂₀ F ₂ N ₂ O ₄ , F.W. 390.38, Lyophilized powder | 5mg |
| J63874 | Apramycin, 98+% [D-Streptomine] [37321-09-8], C ₂₇ H ₄₁ N ₅ O ₁₁ , F.W. 539.60, Powder, b.p. 823°, f.p. 451.6°(845°F), d. 1.56, Merck 14,752, EINECS 253-460-1 | 1g 5g |
| Application(s): Potent inhibitor of protein synthesis in bacteria | | |
| J63039 | Aprotinin, from bovine lung [9087-70-1], C ₂₈₄ H ₄₃₂ N ₆₄ O ₇₉ S ₂ , F.W. 6511.52, Powder, Merck 14,757, EINECS 232-994-9, RTECS YN5080000, MDL MFCD00130541 | 10mg 25mg 100mg |
| ! H:H302, P:P264-P270-P301+P312-P330-P501a | | |
| Application(s): A potent protease inhibitor | | |
| J65076 | 9-β-D-Arabinofuranosyladenine, 99% [Vidarabine, Ara-A] [5536-17-4], C ₁₀ H ₁₃ N ₅ O ₄ , F.W. 267.24, Powder, Merck 14,9976, EINECS 226-893-9, RTECS AU6200000, BRN 624881, MDL MFCD00065471, † | 1g 5g 25g |
| 🔓 H:H361, P:P281-P201-P202-P308+P313-P405-P501 | | |
| J65653 | 9-β-D-Arabinofuranosyladenine-5'-monophosphate, 99% [Vidarabine monophosphate] [29984-33-6], C ₁₀ H ₁₄ N ₅ O ₇ P, F.W. 347.22, Powder, EINECS 249-990-8, RTECS AU6204000, MDL MFCD00069723 | 1g 5g |
| ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | | |
| J65154 | 9-β-D-Arabinofuranosyl-2-fluoroadenine-5'-monophosphate, 99% [Fludarabine monophosphate, 2-F-ara-AMP] [75607-67-9], C ₁₀ H ₁₃ FN ₅ O ₇ P, F.W. 365.21, Powder, RTECS UO7440900, MDL MFCD00866418 | 1g |
| ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | | |
| J64147 | 1-β-D-Arabinofuranosyluracil, 99% [Ara-U, Arauridine] [3083-77-0], C ₈ H ₁₂ N ₂ O ₆ , F.W. 244.20, Powder, EINECS 221-386-9, RTECS YQ8818000, BRN 28749, MDL MFCD00065998 | 1g 5g 25g |
| L09895 | DL-Arabinose, 98+% [147-81-9], C ₅ H ₁₀ O ₅ , F.W. 150.13, m.p. 158-160°, Merck 14,761, EINECS 205-699-8, BRN 1723086, MDL MFCD00135867, † | 10g 50g |
| A10357 | D-(-)-Arabinose, 99% [10323-20-3], C ₅ H ₁₀ O ₅ , F.W. 150.13, m.p. 154-158°, [α] _D ²⁰ -104° (c=10 in water, 24h), EINECS 233-708-5, BRN 1723079, MDL MFCD00135608, † Chiral building block. For use in the synthesis of a chiral quinuclidine-3,5-diol, see: <i>J. Chem. Soc., Perkin 1</i> , 1065 (1989). | 10g 50g 250g |
| | |  |
| A11921 | L-(+)-Arabinose, 99% [87-72-9], C ₅ H ₁₀ O ₅ , F.W. 150.13, m.p. 155-160°, [α] _D ²⁰ +104° (c=10 in water, 24h), Merck 14,761, EINECS 201-767-6, BRN 1723085, MDL MFCD00067709, † | 50g 250g |
| | |  |
| A17801 | D-(+)-Arabitol, 99% [488-82-4], C ₅ H ₁₂ O ₅ , F.W. 152.15, m.p. 100-104°, [α] _D ²⁰ +11° (c=5 in 8% borax solution), Merck 14,762, EINECS 207-686-2, BRN 1720520, MDL MFCD00004709, † | 5g 25g |
| | |  |







| Stock # | Description | Size |
|---------|--|---|
| A13103 | L-(-)-Arabitol, 98% ■ [7643-75-6], C ₆ H ₁₂ O ₆ , F.W. 152.15, m.p. 98-103°, [α] _D ²⁰ -11° (c=5 in 8% borax soln), Merck 14,762, EINECS 231-582-6, BRN 1720521, MDL MFCD00064290, † |  5g |
| | | 25g |
| | | 100g |
| | D-Araboascorbic acid , see D-(-)-Isoascorbic acid, 36366, p. 260 | |
| L14945 | Arbutin, 98+% △ ■ [Hydroquinone-glucose, 4-Hydroxyphenyl-β-D-glucopyranoside] [497-76-7], C ₁₂ H ₁₆ O ₇ , F.W. 272.26, m.p. 196-200°, [α] _D ²⁰ -65° (c=2 in water), Merck 14,773, EINECS 207-850-3, RTECS CE8863000, BRN 89673, MDL MFCD00016915 |  1g |
| | | 5g |
| J63277 | Arcaine sulfate salt [1,4-Diguandidinobutane sulfate salt] [14923-17-2], C ₈ H ₁₈ N ₆ H ₂ SO ₄ , F.W. 270.30, White powder, RTECS MF6550000, MDL MFCD00050545 | 1g |
| | | 2.5g |
| | | 5g |
| | Application(s): An NMDA antagonist and a nitric oxide synthase inhibitor | |
| J65468 | Arg-Gly-Asp [Arginyl-glycyl-aspartic acid, RGD] [99896-85-2], C ₁₂ H ₂₂ N ₆ O ₆ , F.W. 346.34, Powder, MDL MFCD00057952 | 1mg |
| | | 5mg |
| | Application(s): Fragment from cell-attachment domain of fibronectin; a cell-attachment peptide | |
| J64877 | Arg-Gly-Asp-Ser [RGDS, Arginyl-glycyl-aspartyl-serine] [91037-65-9], C ₁₈ H ₂₇ N ₇ O ₈ , F.W. 433.42, Powder, MDL MFCD00076452 | 5mg |
| | | |
| | Application(s): Supports fibroblast attachment | |
| A17520 | DL-Arginine, 98% △ [7200-25-1], C ₆ H ₁₄ N ₄ O ₂ , F.W. 174.20, m.p. ca 230° dec., EINECS 230-571-3, BRN 1725411, MDL MFCD00063117, † |  5g |
| | | 25g |
| A16137 | D-Arginine, 98% △ [D-2-Amino-5-guanidinopentanoic acid, H-D-Arg-OH] [157-06-2], C ₆ H ₁₄ N ₄ O ₂ , F.W. 174.20, m.p. ca 235°, EINECS 205-866-5, RTECS CF1934220, BRN 1725412, MDL MFCD00063116, † |  1g |
| | | 5g |
| | | ! H: H319, P: P280-P264-P305+P351+P338-P337+P313 |
| A15738 | L-Arginine, 98+% △ [L-2-Amino-5-guanidinopentanoic acid, H-Arg-OH] [74-79-3], C ₆ H ₁₄ N ₄ O ₂ , F.W. 174.20, m.p. 226° dec., [α] _D ²⁰ +26° (c=1.6 in 6N HCl), Merck 14,780, EINECS 200-811-1, RTECS CF1934200, BRN 1725413, MDL MFCD00002635, † |  25g |
| | | 100g |
| | | 500g |
| | | 2.5kg |
| | ! H: H319, P: P280-P264-P305+P351+P338-P337+P313 | |
| A10758 | DL-Arginine monohydrochloride monohydrate, 98+% [DL-2-Amino-5-guanidinopentanoic acid monohydrochloride monohydrate, H-DL-Arg-OH.HCl] [332360-01-7], C ₈ H ₁₈ N ₄ O ₂ .HCl.H ₂ O, F.W. 228.69 (210.67anhy), EINECS 250-903-0, BRN 4158960, MDL MFCD00151031, † |  5g |
| | | 25g |
| J61420 | DL-Arginine hydrochloride [32042-43-6], C ₆ H ₁₄ N ₄ O ₂ .HCl, F.W. 210.67, Powder, EINECS 250-903-0, MDL MFCD00064549 | 5g |
| | | 25g |
| | Application(s): Substrate for nitric oxide synthase; induces insulin release by a nitric oxide-dependent mechanism | |
| A16222 | D-Arginine monohydrochloride, 99% ■ [627-75-8], C ₆ H ₁₄ N ₄ O ₂ .HCl, F.W. 210.67, m.p. 216-218°, EINECS 211-010-1, RTECS CF1995000, BRN 5773432, MDL MFCD00012620, † |  1g |
| | | 5g |
| | | 25g |
| A14730 | L-Arginine monohydrochloride, 98+% ■ [L-2-Amino-5-guanidinopentanoic acid hydrochloride, H-Arg-OH.HCl] [1119-34-2], C ₆ H ₁₄ N ₄ O ₂ .HCl, F.W. 210.67, m.p. 216° dec., d. 1.42, [α] _D ²⁰ +22° (c=5 in 5N HCl), Merck 14,780, EINECS 214-275-1, RTECS CF1995500, BRN 3631658, MDL MFCD00064550, † |  100g |
| | | 500g |
| | | 2.5kg |
| | | |
| | Arlace® 83 , see Sorbitan sesquioleate, J62648, p. 350 | |
| J64151 | ARP 100 [N-Hydroxy-2-(N-isopropoxy-[1,1'-biphenyl]-4-yl)sulfonamido]acetamide] [704888-90-4], C ₁₇ H ₂₀ N ₂ O ₅ S, F.W. 364.42, Solid | 5mg |
| | | ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 |
| | Arpamy , see (+/-)-Verapamil hydrochloride, 99+%, J61535, p. 391 | |

| Stock # | Description | Size |
|---------------|---|-----------------------|
| A11838 | Arsenazo III disodium salt [3,6-Bis(2,2'-arsonophenylazo)-4,5-dihydroxy-2,7-naphthalenedisulfonic acid disodium salt] [62337-00-2], C ₂₂ H ₁₆ As ₂ N ₄ Na ₂ O ₇ S ₂ , F.W. 820.34, m.p. >320°, UN3465, EINECS 263-516-7, MDL MFCD00003936  H.H301-H331-H400-H410, P.P261-P301+P310-P321-P304+P340-P405-P501a | 1g 5g 25g |
| J63031 | Arsenazo III free acid [1668-00-4], (HO) ₂ C ₁₀ H ₆ (SO ₃ H) ₂ (N=NC ₆ H ₄ AsO ₂ H ₂) ₂ , F.W. 776.37, Powder, UN3465, EINECS 216-788-6, BRN 5717957, MDL MFCD00036695  H.H301-H331-H400-H410, P.P261-P301+P310-P321-P304+P340-P405-P501a Application(s): Suitable for determination of micromolar amounts of calcium | 5g 25g |
| J65406 | Artemisinin, 99% [Arteannuin, Qinghaosu] [63968-64-9], C ₁₅ H ₂₂ O ₅ , F.W. 282.33, Powder to crystals, m.p. 156-157°, Merck 14,817, RTECS KD4170000, MDL MFCD00081057 Application(s): Natural anti-malarial compound | 1g 5g |
| | L-Arterenol , see L-Noradrenaline, L08087, p. 304 | |
| J62812 | Arvanil, 98% [128007-31-8], C ₂₈ H ₄₁ NO ₃ , F.W. 439.64, Liquid, RTECS JX3845000, MDL MFCD01752675, Note: Supplied as a 50mg/ml solution in ethanol Application(s): Cannabinoid and vanilloid receptor agonist. Induces apoptosis through a caspase-8 pathway | 5mg 10mg 50mg |
| J64218 | AS 19 [(2S)-N,N-Dimethyl-5-(1,3,5-trimethyl-1H-pyrazol-4-yl)-1,2,3,4-tetrahydronaphthalen-2-amine] C ₁₈ H ₂₅ N ₃ , F.W. 283.41, Oil | 10mg |
| J65125 | α-Asarone ▲ [trans-1,2,4-Trimethoxy-5-(1-propenyl)benzene, Ile-Leu-Pro-Trp-Lys-Trp-Pro-Trp-Trp-Pro-Trp-Arg-Arg-NH2] [2883-98-9], (CH ₃) ₃ C ₆ H ₂ CH=CHCH ₃ , F.W. 208.25, Powder, m.p. 57-61°, b.p. 296°, EINECS 220-743-6, RTECS DC2975000, BRN 1910606, MDL MFCD00064457 | 1g 5g |
| J65782 | Ascorbate oxidase, from Cucurbita sp. [EC 1.10.3.3] [9029-44-1], Lyophilized powder, EINECS 232-852-6, MDL MFCD00130560 | 1kilounit |
| 11188 | L-(+)-Ascorbic acid, 98+% [Vitamin C] [50-81-7], C ₆ H ₈ O ₆ , F.W. 176.12, Powder, m.p. ca 191° dec., d. 1.65, Merck 14,830, EINECS 200-066-2, RTECS CI7650000, BRN 84272, MDL MFCD00064328, †  | 100g 500g 2kg |
| 36237 | L-(+)-Ascorbic acid, ACS, 99+% [Vitamin C] [50-81-7], C ₆ H ₈ O ₆ , F.W. 176.12, Powder, m.p. ca 191° dec., d. 1.65, Merck 14,830, EINECS 200-066-2, RTECS CI7650000, BRN 84272, MDL MFCD00064328, † Maximum level of impurities: Specific rotation [α] _D ²⁵ +21.0 ±0.5°, Residue after ignition 0.1%, Heavy Metals (as Pb) 0.002%, Fe 0.001% | 25g 100g 500g |
| A17759 | L-Ascorbic acid sodium salt, 99% [Vitamin C sodium salt] [134-03-2], C ₆ H ₇ NaO ₆ , F.W. 198.11, m.p. ca 220°, Merck 14,830, EINECS 205-126-1, RTECS CI7671000, BRN 3767246, MDL MFCD00082340, †  | 100g 500g |
| 32791 | L-Ascorbic acid 6-palmitate, 99% [137-66-6], C ₂₈ H ₃₈ O ₇ , F.W. 414.52, Crystalline, m.p. 113-114°, EINECS 205-305-4, MDL MFCD00005377, †  | 25g 100g 500g |
| | Asparaginase , see Aspartame, 98%, J61523, p. 111 | |
| B21473 | L-(+)-Asparagine, 99% ■ [70-47-3], C ₄ H ₈ N ₂ O ₃ , F.W. 132.12, m.p. 234-236° dec., Merck 14,837, EINECS 200-735-9, BRN 1723527, MDL MFCD00064401, †  | 100g 500g 2.5kg |
| B20273 | DL-Asparagine monohydrate, 98% [DL-2-Aminosuccinamic acid monohydrate, H-DL-Asn.H ₂ O] [3130-87-8], C ₄ H ₈ N ₂ O ₃ ·H ₂ O, F.W. 150.14 (132.12anhy), m.p. ca 220° dec., EINECS 221-521-1, BRN 6234992, MDL MFCD00151039, †  | 100g 500g |


| Stock # | Description | Size |
|---|---|---|
| B24556 | D-(-)-Asparagine monohydrate, 99% [5794-24-1], C ₄ H ₈ N ₂ O ₃ ·H ₂ O, F.W. 150.14 (132.12anhy), m.p. 274-276° dec., Merck 14,837, MDL MFCD00149558 |  25g |
| | | 100g |
| A15012 | L-(+)-Asparagine monohydrate, 98+% [L-2-Aminosuccinamic acid monohydrate, H-Asn-OH.H2O] [5794-13-8], C ₄ H ₈ N ₂ O ₃ ·H ₂ O, F.W. 150.14 (132.12anhy), m.p. ca 245° dec., d. 1.543, [α] _D ²⁰ +31° (c=5 in 5N HCl), Merck 14,837, EINECS 200-735-9, BRN 5767869, MDL MFCD00151038, † Starting material for synthesis of β-amino acids: <i>Arch. Pharm.</i> , 324, 551 (1991) |  100g |
| | | 500g |
| | | 2.5kg |
| J62869 | L-Asparagine monohydrate, Cell Culture Reagent [(S)-2-Aminosuccinic acid 4-amide, L-Aspartic acid 4-amide] [5794-13-8], C ₄ H ₈ N ₂ O ₃ ·H ₂ O, F.W. 150.14 (132.12anhy), White to off-white, m.p. 215-217°, EINECS 200-735-9, BRN 1723527, MDL MFCD00151038, † | 100g |
| | | 500g |
| | | 1kg |
| Aspartate aminotransferase , see Glutamic oxalacetic transaminase, porcine heart, J60044, p. 235 | | |
| L-Aspartate: 2-oxoglutarate aminotransferase , see Glutamic oxalacetic transaminase, porcine heart, J60044, p. 235 | | |
| A13646 | DL-Aspartic acid, 98+% [DL-Aminosuccinic acid, H-DL-Asp-OH] [617-45-8], C ₄ H ₇ NO ₄ , F.W. 133.10, m.p. >300° dec., EINECS 210-513-3, RTECS CI9097800, BRN 774618, MDL MFCD00063083, † |  100g |
| | | 500g |
| | | 2.5kg |
| B21184 | D-Aspartic acid, 99% [D-Aminosuccinic acid, H-D-Asp-OH] [1783-96-6], C ₄ H ₇ NO ₄ , F.W. 133.10, m.p. >300° dec., d. 1.66, [α] _D ²⁰ -25° (c=1 in 1N HCl), Merck 14,840, EINECS 217-234-6, RTECS CI9097500, BRN 1723529, MDL MFCD00063081 |  5g |
| | | 25g |
| | | 100g |
| A13520 | L-Aspartic acid, 98+% [L-Aminosuccinic acid, H-Asp-OH] [56-84-8], C ₄ H ₇ NO ₄ , F.W. 133.10, m.p. >300° dec., d. 1.66, [α] _D ²⁰ +25° (c=2 in 5N HCl), Merck 14,840, EINECS 200-291-6, RTECS CI9098500, BRN 1723530, MDL MFCD00002616, † Readily forms β-lactam derivatives which are valuable intermediates for the synthesis of a variety of products, including thienamycin: <i>J. Am. Chem. Soc.</i> , 102, 6163 (1980); <i>Tetrahedron Lett.</i> , 23, 2293 (1982). |  100g |
| | | 250g |
| | | 500g |
| | | 1kg |
| | | 5kg |
| L-Aspartic acid 4-amide , see L-Asparagine monohydrate, Cell Culture Reagent, J62869, p. 111 | | |
| L08956 | L-Aspartic acid 4-benzyl ester, 98% [H-Asp(OBz)-OH, β-Benzyl L-aspartate] [2177-63-1], C ₁₁ H ₁₃ NO ₄ , F.W. 223.23, m.p. ca 220° dec., [α] _D ²⁰ +27.5° (c=1 in 1N HCl), EINECS 218-541-8, BRN 1983183, MDL MFCD00037208 |  1g |
| | | 5g |
| | | 25g |
| J65983 | L-Aspartic acid dimethyl ester hydrochloride, 99% [L-Asp(OMe)-Ome.HCl, Dimethyl L-aspartate hydrochloride] [32213-95-9], C ₈ H ₁₁ NO ₄ ·HCl, F.W. 197.62, Powder, m.p. 115-117°, EINECS 250-957-4, MDL MFCD00038878 | 5g |
| | | 25g |
| B22321 | L-Aspartic acid monosodium salt monohydrate, 99% [Sodium L-aspartate monohydrate] [323194-76-9], C ₄ H ₈ NNaO ₃ ·H ₂ O, F.W. 173.11 (155.10anhy), EINECS 223-264-0, MDL MFCD00152960 |  100g |
| | | 500g |
| J61523 | Aspartame, 98% [Asp-Phe methyl ester, Asp-Phe-OMe, Asparaginase] [22839-47-0], HOOCCH ₂ CH(NH ₂)CONHCH(CH ₂ C ₆ H ₅)COOCH ₃ , F.W. 294.30, Powder, m.p. 243-245°, Merck 14,839, EINECS 245-261-3, RTECS WM3407000, BRN 2223850, MDL MFCD00002724, † | 5g |
| | | 25g |
| | | 100g |
| Application(s): A non-nutritive sweetener and dipeptide ester about 160 times sweeter than sucrose | | |
| J60339 | Astemizole, 99+% [1-(4-Fluorobenzyl)-2-(1-[4-methoxyphenethyl]piperidin-4-yl)aminobenzimidazole, Hismanal] [68844-77-9], C ₂₈ H ₃₁ FN ₃ O, F.W. 458.57, Powder, m.p. 149-150°, Merck 14,856, EINECS 272-441-9, RTECS DD8968000, MDL MFCD00153919 | 50mg |
| | | ! |
| H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | | |
| Application(s): Selective histamine H1 receptor antagonist | | |
| J61199 | (R,S)-Atenolol [29122-68-7], C ₁₄ H ₂₂ N ₂ O ₃ , F.W. 266.34, Powder, m.p. 163°, Merck 14,859, EINECS 249-451-7, RTECS AC3600000, MDL MFCD00057645 | 1g |
| | | |
| Application(s): Cardioselective β-adrenergic blocker. An antihypertensive | | |
| ATP disodium salt , see Adenosine-5'-triphosphate disodium salt, 98%, J61125, p. 79 | | |
| ATP disodium salt trihydrate , see Adenosine-5'-triphosphate disodium salt trihydrate, 98%, J60336, p. 79 | | |
| 5'-ATP-Na₂ , see Adenosine-5'-triphosphate disodium salt hydrate, L14522, p. 79 | | |
| J64988 | Atrial Natriuretic Peptide (1-28), rat [88898-17-3], C ₁₂₈ H ₂₀₅ N ₄₅ O ₃₅ S ₂ , F.W. 3062.41, Powder | 0.5mg |
| | | 1mg |
| J65178 | Atrial Natriuretic Peptide (4-24), frog [118691-44-4], C ₉₃ H ₁₅₀ N ₃₄ O ₂₇ S ₃ , F.W. 2272.59, Powder, MDL MFCD00076224 | 0.5mg |
| | | 1mg |

| Stock # | Description | Size |
|--|---|-------------------|
| A10236 | Atropine sulfate monohydrate, 98+% ▲ [5908-99-6], C ₂₃ H ₃₄ N ₂ O ₆ ·H ₂ SO ₄ ·H ₂ O, F.W. 694.84 (676.82anhy), m.p. 187-192°, Merck 14.875, UN1544, EINECS 200-104-8, RTECS CK2455000, BRN 6109275, MDL MFCD00074815, †  H:H300-H330, P:P301+P310-P304+P340-P320-P330-P405-P501a | 10g 50g |
| Application(s): Antagonist at muscarinic receptors; also a bronchodilator | | |
| J60343 | Auramine O, 80% dye content [C.I. 41000] [2465-27-2], C ₁₇ H ₂₁ N ₃ ·HCl, F.W. 303.84, Powder, m.p. 250° dec., UN2811, EINECS 219-567-2, RTECS BY3675000, BRN 4030061, MDL MFCD00012484, †  H:H311-H351-H302, P:P280-P281-P361-P302+P352-P405-P501a | 25g 50g |
| Application(s): Fluorescent stain for acid-resistant bacteria in sputum | | |
| Aureomycin , see Chlorotetracycline hydrochloride, J60095, p. 160 | | |
| J65997 | Aurora Kinase/Cdk Inhibitor ▲ [4-(5-Amino-1-(2,6-difluorobenzoyl)-1H-[1,2,4]triazolo-3-ylamino)-benzenesulfonamide] [443797-96-4], C ₁₅ H ₁₂ F ₂ N ₆ O ₃ S·CH ₃ CN, F.W. 435.41, Powder ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5mg |
| A15905 | Aurintricarboxylic acid [4431-00-9], C ₂₂ H ₁₄ O ₉ , F.W. 422.35, m.p. >300°, EINECS 224-628-1, RTECS GU4790000, BRN 2228904, MDL MFCD00011663, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 5g 25g 100g |
| Application(s): Inhibits protein-nucleic acid interactions | | |
| J65067 | Autocamtide 2 [Lys-Lys-Ala-Leu-Arg-Arg-Gln-Glu-Thr-Val-Asp-Ala-Leu] C ₆₅ H ₁₁₈ N ₂₂ O ₂₀ , F.W. 1527.76, Solid | 0.5mg 1mg |
| J64813 | Autophagy Inhibitor, 3-MA [3-Methyladenine, 6-Amino-3-methylpurine] [5142-23-4], C ₆ H ₇ N ₅ , F.W. 149.15, Solid, EINECS 225-908-6, RTECS AU6520000, BRN 14,6087, MDL MFCD00010531 | 25mg 50mg |
| Auxit , see Bromhexine hydrochloride, 98+%, J63451, p. 135 | | |
| Avermectin B1 , see Abamectin, 97+%, J60039, p. 69 | | |
| J64972 | Avidin, from egg [1405-69-2], Lyophilized powder, EINECS 215-783-6, RTECS CL1590000, MDL MFCD00130572 | 10mg |
| Application(s): Has extremely strong affinity for biotin | | |
| AVP peptide , see Vasopressin, 98+%, J61248, p. 391 | | |
| AY-22989 , see Rapamycin, 99+%, J62473, p. 335 | | |
| J65079 | AY 9944 dihydrochloride ■ [1,4-Bis(2-chlorobenzylaminomethyl)cyclohexane dihydrochloride, trans-N,N-Bis[2-chlorophenylmethyl]-1,4-cyclohexanedime thanamine dihydrochloride] [366-93-8], C ₂₂ H ₂₈ Cl ₂ N ₂ ·2HCl, F.W. 464.30, Solid, UN2811, RTECS GU7025000  H:H301-H360, P:P281-P301+P310-P321-P308+P313-P405-P501 | 10mg 50mg |
| H26082 | O-(7-Aza-1H-benzotriazol-1-yl)-N,N,N',N'-tetramethyluronium hexafluorophosphate, 99% ▽ [HATU, 1-[Bis(dimethylamino)methylene]-1H-1,2,3-triazolo[4,5-b]pyridinium 1-oxide hexafluorophosphate] [148893-10-1], C ₁₀ H ₁₅ F ₆ N ₆ OP, F.W. 380.23, m.p. ca 185° dec., MDL MFCD00274639 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 1g 5g 25g |
| 1-Azabicyclo[2.2.2]octan-3-ol , see 3-Quinuclidinol, B21503, p. 334 | | |
| 1-Azabicyclo[2.2.2]octan-3-one hydrochloride , see 3-Quinuclidinone hydrochloride, A13320, p. 334 | | |
| J64159 | 5-Azacytidine, 98% [4-Amino-1-(β-D-ribofuranosyl)-1,3,5-triazin-2(1H)-one, Ladakamycin] [320-67-2], C ₇ H ₁₀ N ₄ O ₅ , F.W. 244.2, Powder, m.p. 226-232° dec., Merck 14,890, EINECS 206-280-2, RTECS XZ3017500, BRN 620461, MDL MFCD00006539 !  H:H302-H340-H350, P:P281-P264-P301+P312-P308+P313-P405-P501 | 1g 5g |
| Application(s): Causes DNA demethylation or hemi-demethylation; a powerful mutagen | | |
| A13410 | 5-Azacytosine, 98% (dry wt.), may cont. up to ca 7% water [4-Amino-1,3,5-triazin-2(1H)-one] [931-86-2], C ₄ H ₄ N ₄ O, F.W. 112.09, m.p. >300°, EINECS 213-242-9, RTECS XZ2854300, BRN 116378, MDL MFCD00149402 ! H:H302, P:P264-P270-P301+P312-P330-P501a | 5g 25g |
|  | | |




| Stock # | Description | Size |
|---------|--|-------|
| J65513 | 5-Aza-2'-deoxycytidine, 98% [2'-Deoxy-5-azacytidine, 4-Amino-1-(2-deoxy-β-D-ribofuranosyl)-1,3,5-triazin-2(1H)-one] [2353-33-5], C ₈ H ₁₂ N ₄ O ₄ , F.W. 228.21, Powder, Merck 14,2853, EINECS 219-089-4, RTECS XZ3012000, BRN 617982, MDL MFCD00043011 | 100mg |
| | | 250mg |
| | ! H:H302-H315-H319-H341-H360-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J64549 | Azadibenzocyclooctyne acid [ADIBO-acid] C ₂₁ H ₁₉ NO ₃ , F.W. 333.38, Solid | 25mg |
| | | 100mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): Simplest amine reactive reagent for introducing a dibenzylcyclooctyne to available amine functionality | |
| J65637 | Azadibenzocyclooctyne-amine [ADIBO-amine] [1255942-06-3], C ₁₈ H ₁₆ N ₂ O, F.W. 276.33, Solid | 25mg |
| | | 100mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): A carbonyl reactive reagent used to incorporate DBCO into organic compounds, surfaces or particles | |
| J65472 | Azadibenzocyclooctyne-Biotin conjugate [ADIBO-Biotin conjugate] C ₂₈ H ₃₀ N ₄ O ₃ S, F.W. 502.63, Solid | 10mg |
| | | 25mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J65377 | Azadibenzocyclooctyne-maleimide [ADIBO-maleimide] C ₂₅ H ₂₁ N ₃ O ₄ , F.W. 427.45, Solid | 25mg |
| | | 100mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J65981 | Azadibenzocyclooctyne-NHS ester  [ADIBO-NHS ester] C ₂₅ H ₂₂ N ₂ O ₅ , F.W. 430.45, Solid | 25mg |
| | | 100mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): Unique and simple NHS ester allows DBCO incorporation into amine-containing molecules | |
| J64977 | Azadibenzocyclooctyne-PEG, MW 5,000 [ADIBO-PEG, MW 5,000] F.W. 5kDa, Solid | 100mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J65322 | Azadibenzocyclooctyne-PEG, MW 10,000 [ADIBO-PEG, MW 10,000] F.W. 10kDa, Solid | 100mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J65953 | Azadibenzocyclooctyne-PEG, MW 20,000 [ADIBO-PEG 20,000] F.W. 20 kDa, Solid | 100mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J65338 | Azadibenzocyclooctyne-PEG4-acid [ADIBO-PEG4-acid] C ₃₂ H ₄₀ NO ₈ , F.W. 566.66, Viscous liquid or solid | 10mg |
| | | 25mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): Amine reactive reagent for introducing a dibenzylcyclooctyne to available amine functionality. PEG4 spacer enhances water solubility and reduces or eliminates aggregation and precipitation when labeling biological materials | |
| J64617 | Azadibenzocyclooctyne-PEG4-alcohol [ADIBO-PEG4-alcohol] C ₂₉ H ₃₆ N ₂ O ₇ , F.W. 524.61, Viscous liquid or solid | 25mg |
| | | 100mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): DBCO-containing reagent with PEG4 spacer and alcohol terminus | |
| J65301 | Azadibenzocyclooctyne-PEG4 amine [ADIBO-PEG4-amine] [1255942-08-5], C ₂₈ H ₃₇ N ₃ O ₆ , F.W. 523.62, Viscous liquid | 10mg |
| | | 25mg |
| | | 100mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): A carbonyl reactive reagent with a PEG4 spacer. PEG4 spaces increases water solubility and accessibility of the DBCO moiety | |
| J65737 | Azadibenzocyclooctyne-PEG4 biotin conjugate [ADIBO-PEG4-biotin conjugate] C ₃₈ H ₅₁ N ₅ O ₅ S, F.W. 749.92, Solid | 10mg |
| | | 25mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | 100mg | |

| Stock # | Description | Size |
|---------|--|--|
| J65673 | Azadibenzocyclooctyne-PEG4-maleimide [ADIBO-PEG4-maleimide] C ₂₈ H ₄₂ N ₄ O ₉ , F.W. 674.74, Viscous liquid | 10mg 25mg 100mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J65223 | Azadibenzocyclooctyne-PEG4-NHS ester  [ADIBO-PEG4-NHS ester] C ₂₈ H ₄₃ N ₅ O ₁₁ , F.W. 693.74, Viscous liquid or solid | 10mg 25mg 100mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J65570 | Azadibenzocyclooctyne-PEG4-phosphoramidite [ADIBO-PEG4-phosphoramidite] C ₂₈ H ₅₃ N ₅ O ₇ P, F.W. 708.82, Viscous liquid or solid | 25mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J65780 | Azadibenzocyclooctyne-PEG12 biotin conjugate [ADIBO-PEG12-biotin conjugate] C ₅₅ H ₈₃ N ₅ O ₁₆ S, F.W. 1102.34, Solid | 10mg 25mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J64040 | Azadibenzocyclooctyne-SETA 650 [ADIBO-SETA 650] F.W. 1173.36, Solid | 0.5mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J65628 | Azadibenzocyclooctyne-S-S-NHS ester [ADIBO-S-S-NHS ester] C ₂₈ H ₂₇ N ₅ O ₈ S ₂ , F.W. 565.65, Solid | 25mg 100mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J64256 | Azadibenzocyclooctyne-S-S-PEG3-biotin conjugate [ADIBO-S-S-PEG3-biotin conjugate] C ₄₂ H ₅₆ N ₆ O ₈ S ₃ , F.W. 869.12, Solid | 10mg 25mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J64671 | Azadibenzocyclooctyne-sulfo-biotin conjugate [ADIBO-sulfo-biotin conjugate] C ₂₇ H ₅₀ N ₆ O ₈ S ₂ , F.W. 652.76, Solid | 10mg 25mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| L07983 | 7-Azaindole, 98% [1 <i>H</i> -Pyrrolo[2,3- <i>b</i>]pyridine] [271-63-6], C ₇ H ₆ N ₂ , F.W. 118.14, m.p. 103-107°, b.p. 270°, EINECS 205-981-0, RTECS UY8710000, BRN 109667, MDL MFCD00005606 Glycosylation at the pyrrole nitrogen has been carried out under phase-transfer conditions to give nucleoside analogues: <i>Heterocycles</i> , 29 , 795 (1989). For a review of the chemistry of azaindoles, see: <i>Russ. Chem. Rev.</i> , 49 , 428 (1980). |  1g 5g 25g |
| J62314 | Azathioprine [446-86-6], C ₉ H ₇ N ₃ O ₂ S, F.W. 277.26, Crystalline powder, Merck 14,902 , EINECS 207-175-4, RTECS UO8925000, MDL MFCD00069203 | 1g 5g 10g |
| | !  H:H302-H315-H319-H350-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): An immunosuppressant. A purine synthesis inhibitor which inhibits the proliferation of cells | |
| L06762 | 6-Azathymine, 98% [6-Methyl-1,2,4-triazine-3,5(2 <i>H</i> ,4 <i>H</i>)-dione] [932-53-6], C ₄ H ₅ N ₃ O ₂ , F.W. 127.10, m.p. 211-215°, Merck 14,903 , EINECS 213-253-9, RTECS XY8050000, BRN 126863, MDL MFCD00006457 |  5g 25g |
| A14389 | 6-Azaauracil, 98% [1,2,4-Triazine-3,5(2 <i>H</i> ,4 <i>H</i>)-dione] [461-89-2], C ₃ H ₃ N ₃ O ₂ , F.W. 113.08, m.p. 274-282°, EINECS 207-318-0, RTECS XY7700000, BRN 116472, MDL MFCD00006456, † |  5g 25g |
| | ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | 6-Azaauracil riboside , see 6-Azauridine, J61309, p. 114 | |
| J61309 | 6-Azauridine [6-Azaauracil riboside, 2-β- <i>D</i> -Ribofuranosyl-1,2,4-triazine-3,5(2 <i>H</i> ,4 <i>H</i>)-dione] [54-25-1], C ₈ H ₁₁ N ₅ O ₆ , F.W. 245.19, Powder, m.p. 160-161°, Merck 14,904 , EINECS 200-199-6, RTECS XY8575000, MDL MFCD00006472 | 1g 5g |
| | !  H:H302-H312-H332-H351, P:P261-P280-P281-P302+P352-P405-P501 | |




| Stock # | Description | Size |
|---------|---|-----------------------|
| 36308 | Azelaic acid, 98% [Nonanedioic acid] [123-99-9], HOOC(CH ₂) ₇ COOH, F.W. 188.22, Crystalline, m.p. ca 102°, b.p. 286°/100mm, f.p. 215°(419°F), d. 1.225, Merck 14,905, EINECS 204-669-1, RTECS CM1980000, BRN 1101094, MDL MFCD00004432, f | 25g 100g 5x100g |
| J65127 | 3'-Azido-3'-deoxythymidine, 98% ▲ ■ [AZT, Zidovudine] [30516-87-1], C ₁₀ H ₁₃ N ₅ O ₅ , F.W. 267.24, Powder, m.p. 113-115°, Merck 14,10123, RTECS XP207200, BRN 3595791, MDL MFCD00006536 ↓ H:H351, P:P281-P201-P202-P308+P313-P405-P501 Application(s): Anti-viral agent | 1g 5g 25g |
| J64387 | 2'-Azido-2'-deoxyuridine, 98% [N3-dU] [26929-65-7], C ₉ H ₁₁ N ₅ O ₅ , F.W. 269.21, Powder, m.p. 149-153°, EINECS 248-113-6, BRN 4204828, MDL MFCD00043045 | 500mg |
| J64574 | Azido-PEG(3+3)-S-S-biotin conjugate C ₃₃₂ H ₅₈₈ N ₆ O ₁₁ S ₃ , F.W. 811.05, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10mg 25mg |
| J65147 | Azido-PEG12-biotin conjugate [35-[(R)-(+)-Biotinylamino]-1-azido-3,6,9,12,15,18,21,24,27,30,33-undecaaxapentatriacontane] C ₃₆₁ H ₆₄₁ N ₆ O ₁₃ S, F.W. 796.96, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 25mg 100mg |
| J64996 | Azido-PEG3-biotin conjugate [11-[(R)-(+)-Biotinylamino]-1-azido-3,6,9-trioxaundecane] C ₁₈₁ H ₃₂₁ N ₆ O ₅ S, F.W. 444.55, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 25mg 100mg |
| J65107 | Azido-PEG3-carboxyrhodamine 110 conjugate [Azide-Fluor 488] C ₂₈₁ H ₃₁₁ N ₆ O ₇ , F.W. 575.59, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5mg 25mg |
| J64906 | Azido-PEG3-carboxyrhodamine 6G conjugate [Azide-Fluor 525] C ₃₃₅ H ₄₃₅ N ₆ O ₇ , F.W. 659.75, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5mg |
| J64510 | Azido-PEG3-carboxytetramethylrhodamine 110 conjugate [Azide-Fluor 545] C ₃₃₃ H ₃₉₃ N ₆ O ₇ , F.W. 631.70, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5mg 25mg |
| J65984 | Azido-PEG3-maleimide kit [N-(11-Azido-3,6,9-trioxaundecyl)-3-(N-maleimidyl)pro pionamide] C ₁₅₁ H ₂₃₁ N ₅ O ₈ , F.W. 369.37, Solid, Note: Kit contains two components: a) 1.1 eq. of solution of azido-PEG4-amine in DMSO; b) 1.0 eq. of maleimide-NHS ester as a solid. ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 25mg 100mg |
| J64895 | Azido-PEG3-S-S-NHS ester C ₁₈₁ H ₂₉₁ N ₅ O ₈ S ₂ , F.W. 507.58, Viscous liquid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10mg 25mg 100mg |
| J65598 | Azido-PEG3-sulfo-biotin conjugate C ₂₁₁ H ₃₆₁ N ₇ O ₉ S ₂ , F.W. 594.67, Amorphous solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 25mg 100mg |
| J65476 | Azido-PEG3-sulforhodamine 101 conjugate [Azide-Fluor 585] C ₂₉₁ H ₄₇₁ N ₆ O ₉ S ₂ , F.W. 807.96, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5mg 25mg |
| J65529 | Azido-PEG3-sulforhodamine B conjugate [Azide-Fluor 588] C ₃₃₅ H ₄₇₁ N ₆ O ₉ S ₂ , F.W. 759.91, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5mg |
| J65668 | 3-Azido-1-propylamine [1-Azido-3-aminopropane] [88192-19-2], C ₃ H ₈ N ₄ , F.W. 100.12, Liquid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 100mg 1g |

| Stock # | Description | Size |
|---------|---|--------------------|
| J64030 | 15-Azido-4,7,10,13-tetraoxapentadecanoic acid [Azido-PEG4-acid] C ₁₁ H ₂₁ N ₃ O ₆ , F.W. 291.30, Liquid | 25mg 100mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J65535 | 2,2'-Azino-bis(3-ethylbenzothiazoline-6-sulfonic acid) diam monium salt, 98% ▲ [ABTS diammonium salt] [30931-67-0], C ₁₈ H ₂₄ N ₄ O ₆ S ₄ , F.W. 548.68, Powder, EINECS 250-396-6, RTECS DL7002000, BRN 7329461, MDL MFCD00010404 | 1g 5g |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): Chromogenic substrate for peroxidase assays | |
| J64865 | 1,1'-Azobis(N,N-dimethylformamide), 95% [Diamide, TMAD] [10465-78-8], (CH ₃) ₂ NCON=NCON(CH ₃) ₂ , F.W. 172.19, Powder, m.p. 112°, EINECS 233-951-7, RTECS LQ1041000, BRN 1910409, MDL MFCD00008318 | 1g 5g |
| | Azo Black , see Chlorazol Black E, A13259, p. 154 | |
| A12507 | Azocarmine G [C.I. 50085] [25641-18-3], C ₂₈ H ₁₈ N ₄ NaO ₆ S ₂ , F.W. 579.58, EINECS 247-157-3, MDL MFCD00042002, † | 5g 25g |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| |  | |
| J62887 | Aztreonam [78110-38-0], C ₁₃ H ₁₇ N ₄ O ₆ S ₂ , F.W. 435.43, Powder, m.p. 227° dec., Merck 14,925, EINECS 278-839-9, RTECS UA2451400, MDL MFCD00072145 | 1g 5g |
| | Application(s): Synthetic monocyclic β-lactam antibiotic. Inhibits cell wall synthesis in gram-negative bacteria | |
| A17508 | Azure I [C.I. 52010, Methylene Azure] [531-55-5], C ₁₆ H ₁₆ ClN ₃ S, F.W. 305.83, m.p. ca 205° dec., Merck 14,6058, EINECS 208-511-2, RTECS SO5550000, BRN 3922630, MDL MFCD00011935 | 5g 25g 100g |
| | ! H:H341, P:P281-P201-P202-P308+P313-P405-P501a | |
| | Application(s): For differentiating cellular RNA and DNA in plant tissues | |
| A11777 | Azure II [37247-10-2], MDL MFCD00080716, Note: Mixture containing equal amounts of Azure I and Methylene Blue | 10g 50g |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| J61346 | Azure A [C.I. 52005] [531-53-3], C ₁₆ H ₁₄ ClN ₃ S, F.W. 291.80, Powder, m.p. 290° dec., Merck 14,927, EINECS 208-510-7, RTECS SP5660000, BRN 3922287, MDL MFCD00012112, † | 25g 100g |
| | Application(s): For staining cell granules and tissues | |
| J64515 | Azure C [C.I. 52002, 3-Amino-7-methylaminophenothiazin-5-ium chloride] [531-57-7], C ₁₃ H ₁₂ ClN ₃ S, F.W. 277.78, Powder, EINECS 208-512-8, BRN 4060661, MDL MFCD00067677 | 1g 5g |
| | BAC , see N,N'-Bis(acryloyl)cystamine, 44132, p. 126 | |
| | Baccidal , see Norfloxacin, J62652, p. 304 | |
| J62432 | Bacitracin [1405-87-4], C ₈₈ H ₁₀₃ N ₁₇ O ₁₆ S, F.W. 1421.60, Powder, m.p. 222°, Merck 14,934, EINECS 215-786-2, RTECS CP0175000, MDL MFCD00062640, † | 5g 25g |
| | H:H303, P:P312 | |
| | Application(s): Inhibits cell wall synthesis in Gram-positive bacteria | |
| J62768 | (±)-Baclofen, 99+% [(R,S)-Baclofen] [1134-47-0], C ₁₀ H ₁₂ ClNO ₂ , F.W. 213.66, Powder, Merck 14,937, UN2811, EINECS 214-486-9, RTECS MW5084200, MDL MFCD00055143 | 1g |
| | ! H:H301-H334-H360-H315-H319-H317-H335, P:P285-P301+P310-P305+P351+P338-P302+P352-P405-P501a | |
| | Application(s): Selective GABA-b receptor agonist | |
| | (R,S)-Baclofen , see (+/-)-Baclofen, 99+%, J62768, p. 116 | |
| | Bactidan , see Enoxacin, J61912, p. 207 | |
| J61835 | Bafilomycin A1 [88899-55-2], C ₃₅ H ₅₈ O ₉ , F.W. 622.83, Oil, RTECS RN9781000, BRN 4730700, MDL MFCD06795130 | 1mg 5mg 10mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Application(s): Specific, potent inhibitor of vacuolar ATPases | |
| | BAL , see 2,3-Dimercaptopropanol, L03953, p. 194 | |
| | Balsam Canada , see Canada balsam, A16289, p. 145 | |






| Stock # | Description | Size |
|---|---|--------------------|
| J60424 | Bambuterol hydrochloride, 98+% [KWD-2183] [81732-46-9], C ₁₈ H ₂₉ N ₃ O ₅ ·HCl, F.W. 403.91, Powder, Merck 14,953, MDL MFCD03427293 | 500mg 1g |
| Application(s): β-adrenoceptor agonist. Inhibits plasma cholinesterase during metabolism | | |
| J65901 | Bandrowski's Base [20048-27-5], C ₁₈ H ₁₈ N ₆ , F.W. 318.40, Powder, RTECS GU4805000, BRN 2395527, MDL MFCD00210781 | 1g 5g |
| ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | | |
| A13190 | BAPTA, 97% [1,2-Bis(2-aminophenoxy)ethane-N,N,N',N'-tetraacetic acid] [85233-19-8], C ₂₈ H ₂₈ N ₄ O ₁₀ , F.W. 476.44, m.p. ca 174° dec., Merck 14,957, RTECS MC0423000, MDL MFCD00036255 | 1g 5g 25g |
| ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | | |
| Application(s): Acts as a calcium chelator | | |
| Barbaloin , see Aloin, J62153, p. 90 | | |
| 12310 | Barium chloride dihydrate, ACS [10326-27-9], BaCl ₂ ·2H ₂ O, F.W. 244.28 (208.25anhy), Crystalline, m.p. 113° -2H ₂ O, d. 3.097, Merck 14,971, Solubility: Very soluble in water. Soluble in methanol. Insoluble in ethanol, acetone, ethyl acetate, UN1564, EINECS 233-788-1, RTECS CQ8751000, MDL MFCD00149154, † | 500g 2kg |
| Maximum level of impurities: Insoluble matter 0.005%, Oxidizing substances (as NO ₂) 0.005%, K 0.0025%, Na 0.005%, Ca 0.05%, Heavy Metals (as Pb) 5ppm, Fe 2ppm, Sr 0.1%, Loss on drying at 150° 14.0-16.0%, pH of a 5% solution 5.2-8.2 at 25% | | |
| H:H301-H332, P:P261-P301+P310-P321-P304+P340-P405-P501a | | |
| 14499 | Barium hydroxide octahydrate, ACS, 98+% ▲ ■ [12230-71-6], Ba(OH) ₂ ·8H ₂ O, F.W. 315.48 (171.36anhy), Crystalline, m.p. 78°, d. 2.18, Merck 14,977, Fieser 12,38 18,28 19,18, Solubility: Soluble in water, methanol. Slightly soluble in ethanol. Practically insoluble in acetone, UN3262, EINECS 241-234-5, RTECS CQ9200000, MDL MFCD00149152, † | 250g 1kg |
| Maximum level of impurities: Carbonate (as BaCO ₃) 2.0%, Insoluble in dilute hydrochloric acid 0.01%, Cl 0.001%, S P.T. (limit about 0.001%), K 0.01%, Na 0.01%, Ca 0.05%, Heavy Metals (as Pb) 5ppm, Fe 0.001%, Sr 0.8% | | |
| ! H:H314-H302-H332, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | | |
| Application(s): Used in manufacture of alkali, glass; in synthetic rubber vulcanization, alkalizing agent in water softening, boiler scale remedy, softening water | | |
| 12194 | Barium nitrate, ACS, 99+% ■ [10022-31-8], Ba(NO ₃) ₂ , F.W. 261.35, Crystalline, m.p. 592° dec., d. 3.24, Merck 14,983, Solubility: Freely soluble in water. Slightly soluble in alcohol and acetone, UN1446, EINECS 233-020-5, MDL MFCD00003442, † | 50g 500g 2kg |
| Maximum level of impurities: Insoluble matter 0.01%, pH as a 5% solution 5.0-8.0 at 25°, Cl 5ppm, K 0.005%, Na 0.005%, Ca 0.05%, Heavy Metals (as Pb) 5ppm, Fe 2ppm, Sr 0.1% | | |
| ! H:H302-H332, P:P261-P264-P304+P340-P301+P312-P312-P501a | | |
| 13989 | Barium sulfate, 97% [7727-43-7], BaSO ₄ , F.W. 233.40, 1-4 Micron Powder, m.p. 1580° dec., d. 4.5, Merck 14,994, Solubility: Insoluble in water, dilute acids, alcohol. Soluble in hot, concentrated H ₂ SO ₄ , EINECS 231-784-4, MDL MFCD00003455, † | 100g 1kg 5kg |
| Basic Blue 9 , see Methylene Blue | | |
| Basic Blue 12 , see Nile Blue A, A17174, p. 302 | | |
| A12952 | Basic Fuchsin [C.I. 42510, <i>Fuchsin basic</i>] [632-99-5], C ₂₀ H ₂₀ ClN ₃ , F.W. 337.86, m.p. 268-270° dec., Merck 14,5652, Solubility: Soluble in water, EINECS 211-189-6, RTECS CX9850000, BRN 4166684, MDL MFCD00012569, † | 5g 25g 100g |
| ! H:H351-H302, P:P281-P264-P301+P312-P308+P313-P405-P501a | | |
| Application(s): Biological stain for distinguishing coli and aerogene bacteria | | |
| Basic Green 1 , see Brilliant Green, A12801, p. 135 | | |
| Basic Red 1 , see Rhodamine 6G, J62315, p. 337 | | |
| Basic Red 5 , see Neutral Red, ACS, J62643, p. 300 | | |
| Basic Red 5 , see Neutral Red, J63054, p. 300 | | |
| Basic Red 5 , see Neutral Red, 1% aq. solution, Ready-to-use, J61379, p. 300 | | |
| Basic Violet 3 , see Crystal Violet, B21932, p. 170 | | |
| Basic Violet 4 , see Ethyl Violet, J63951, p. 217 | | |
| Basic Violet 10 , see Rhodamine B, A13572, p. 337 | | |
| Basic Violet 14 , see Basic Fuchsin, A12952, p. 117 | | |
| Basic Yellow 1 , see Thioflavine T, tech. 75%, J61043, p. 367 | | |
| B22841 | Bathocuproin, 98% [2,9-Dimethyl-4,7-diphenyl-1,10-phenanthroline] [4733-39-5], C ₂₆ H ₂₀ N ₂ , F.W. 360.46, m.p. 279-285°, EINECS 225-240-5, BRN 306714, MDL MFCD00004972, † | 1g 5g |
| Reagent for the determination of copper: <i>Anal. Chem.</i> , 25, 510 (1953). | | |
| Bathocuproin sulfonate , see Bathocuproin sulfonate disodium salt hydrate, B22550, p. 118 | | |





| Stock # | Description | Size |
|---------|---|---------------------------|
| B22550 | Bathocuproin sulfonate disodium salt hydrate, 97% [Bathocuproin sulfonate, 2,9-Dimethyl-4,7-diphenyl-1,10-phenanthroline disulfonic acid disodium salt] [52698-84-7], C ₂₈ H ₁₈ N ₂ Na ₂ O ₄ S ₂ ·xH ₂ O, F.W. 564.55(anhy), m.p. >300°, EINECS 258-111-7, BRN 9033637, MDL MFCD03012947, † Reagent for copper: <i>Clin. Chim. Acta</i> , 3, 328 (1958). | 250mg 1g 5g |
| | Application(s): Used as a stain for proteins in polyacrylamide gels; for determination of iron and copper; and uric acid by automated procedures | |
| A14258 | Bathophenanthroline, 98+% [4,7-Diphenyl-1,10-phenanthroline] [1662-01-7], C ₂₄ H ₁₆ N ₂ , F.W. 332.41, m.p. 218-222°, EINECS 216-767-1, RTECS SF8427000, BRN 261048, MDL MFCD00004976, † Reagent for iron. | 1g 5g 25g |
| | Application(s): For colorimetric iron determinations | |
| J64257 | Bax Channel Blocker ■ [1-(3,6-Dibromo-9H-carbazol-9-yl)-3-(piperazin-1-yl)propan-2-ol bis(trifluoroacetate) salt] [335165-69-0], C ₁₈ H ₂₁ Br ₂ N ₅ O ₂ CF ₃ CO ₂ H, F.W. 695.24, Powder H: H341, P: P281-P201-P202-P308+P313-P405-P501 | 10mg |
| | BAY 43-9006 , see Sorafenib, 99+%, J62984, p. 349 Bay-g 5421 , see Acarbose, 95%, J61737, p. 69 | |
| J61480 | (±)-Bay K 8644 [71145-03-4], C ₁₈ H ₁₅ F ₃ N ₂ O ₄ , F.W. 356.30, Powder, MDL MFCD00036697 | 1mg 5mg |
| | Application(s): An active L-type, voltage-gated calcium channel agonist BCA , see Bicinchoninic acid disodium salt, 44247, p. 124 | |
| J63283 | BCA protein assay kit Liquid, Note: Solution A: Bicinchoninic acid and tartrate in an alkaline carbonate buffer Solution B: 4% copper sulfate | 1kit |
| | Application(s): Contains two separate solutions for 500 estimations of proteins | |
| J64464 | Bcl-2 Inhibitor ▲ [2,9-Dimethoxy-11,12-dihydrodibenzo[c,g]1,2-diazocine 5,6-dioxide, 5,5'-Dimethoxy-2,2'-dinitrosobenzyl] [383860-03-5], C ₁₈ H ₁₈ N ₂ O ₄ , F.W. 300.30, Solid | 5mg |
| J65675 | Bcl-2 Inhibitor II, YC137 ▲ [2-Methoxycarbonylamino-4-methylsulfanyl-butylric acid, YC137] [810659-53-1], C ₂₄ H ₂₇ N ₃ O ₆ S ₂ , F.W. 511.57, Solid | 5mg |
| A12850 | Behenic acid, tech. 85% [Docosanoic acid] [112-85-6], CH ₃ (CH ₂) ₂₀ CO ₂ H, F.W. 340.60, m.p. 74-78°, b.p. 306°/60mm, Merck 14,1023, EINECS 204-010-8, BRN 1792887, MDL MFCD00002807, † ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 50g 250g 1kg 5kg |
| | Bemesetron , see 3-Tropanyl-3,5-dichlorobenzoate, 99+%, J62583, p. 383 | |
| J61093 | Benazepril hydrochloride, 98% [86541-74-4], C ₂₄ H ₂₈ N ₂ O ₅ ·HCl, F.W. 460.95, Crystalline powder, m.p. 148-149°, Merck 14,1031, RTECS CX7065000, MDL MFCD00895734 | 25mg 100mg |
| | Application(s): An angiotensin converting enzyme (ACE) inhibitor that reduces blood pressure | |
| J64581 | Benserazide hydrochloride ▲ [DL-Serine 2-(2,3,4-trihydroxybenzyl)hydrazide hydrochloride] [14919-77-8], C ₉ H ₁₃ N ₂ O ₅ ·HCl, F.W. 293.70, Powder, m.p. 146-148°, Merck 14,1050, EINECS 238-991-9, RTECS VT9632300, MDL MFCD00078571 ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g 5g |
| A15795 | Bentonite, sodium form [Sodium bentonite] [1302-78-9], Merck 14,1055, EINECS 215-108-5, MDL MFCD00130611, Note: Forms a colloidal suspension in water, † ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 500g 2.5kg |
| | Application(s): Suspending agent, gel binder, filler in ceramics, catalyst support | |
| B20760 | Benzalkonium chloride, 50% w/w aq. soln. [63449-41-2], f.p. None, d. 0.99, Merck 14,1059, UN1760, EINECS 264-151-6, RTECS BO3151000, BRN 4062599, MDL MFCD00145757, † H: H301-H314-H400-H312, P: P260-P301+P310-P303+P361+P353-P305+P351+P338-P405-P501a | 500ml 2.5L |
| | Application(s): Cationic surface active agent | |





| Stock # | Description | Size |
|--|--|-----------------------|
| 41339 | Benzalkonium chloride [Alkylbenzyltrimethylammonium chloride] [63449-41-2], C ₉ H ₉ CH ₂ N(CH ₃) ₃ Cl, Semi-solid/solid, R=C ₉ H ₁₇ , to C ₁₈ H ₃₇ , Merck 14,1059, Solubility: Soluble in water, UN2923, EINECS 264-151-6, MDL MFCD00145757, † ! H: H314-H400-H302-H312, P: P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 25g 100g 500g |
| Application(s): Cationic surface active agent | | |
| A16002 | Benzamidine hydrochloride hydrate, 98%, water ca 10-14% ■ [206752-36-5], C ₇ H ₈ N ₄ ·HCl·xH ₂ O, F.W. 156.62, Powder or beads, m.p. 82-85°, Fieser 6.27, EINECS 216-795-4, RTECS CV6260000, BRN 3594959, MDL MFCD00066285, † ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 5g 25g 100g |
| Application(s): A proteolytic inhibitor and apoptosis reagent | | |
| J62823 | Benzamidine hydrochloride, 99% [1670-14-0], C ₇ H ₈ N ₄ ·HCl, F.W. 156.62, Powder or beads, m.p. 80-85°, EINECS 216-795-4, RTECS CV6260000, BRN 3594959, MDL MFCD00013025, † ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 5g 10g |
| Application(s): Reversible inhibitor of trypsin, trypsin-like proteins and serine proteases | | |
| 4-Benzamido-2,5-diethoxybenzene diazonium chloride hemi zinc salt , see Fast Blue BB salt, L09704, p. 218 Benzeno-1,2-dicarboxylic acid di-n-butylester , see Di-n-butyl phthalate, A13257, p. 185 1,2-Benzenediol , see Catechol, A10164, p. 150 1,3-Benzenediol , see Resorcinol, 36248, p. 336 1,4-Benzenediol , see Hydroquinone, A11411, p. 248 Benzene hexabromide , see 1,2,3,4,5,6-Hexabromocyclohexane, J60853, p. 244 | | |
| A16148 | Benzenesulfonic acid, 94% ■ [98-11-3], C ₆ H ₅ O ₃ S, F.W. 158.18, m.p. ca 45-50°, f.p. >110° (230°F), d. 1.32, Merck 14,1070, UN2585, EINECS 202-638-7, RTECS DB4200000, BRN 742513, MDL MFCD00011689, † ! H: H314-H302, P: P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 100g 500g 2.5kg |
| Application(s): Acid catalyst for direct esterification of amino acids and peptides | | |
| A17491 | 1,2,3-Benzenetricarboxylic acid dihydrate, 99% [Hemimellitic acid dihydrate] [36362-97-7], C ₆ H ₃ O ₆ ·2H ₂ O, F.W. 246.19 (210.14anhy), m.p. ca 191° dec., EINECS 209-317-0, BRN 2214816, MDL MFCD00149097 ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 5g 10g 25g |
| 1,3,5-Benzenetriol, anhydrous , see Phloroglucinol, B25502, p. 318 | | |
| B24303 | Benzhydrylamine, 97% △ [Aminodiphenylmethane] [91-00-9], (C ₆ H ₅) ₂ CHNH ₂ , F.W. 183.25, m.p. 11-13°, b.p. 294-296°, f.p. >110° (230°F), d. 1.064, n _D ²⁰ 1.5950, Merck 14,1076, Solubility: Slightly soluble in water, UN2735, EINECS 202-032-2, RTECS DA4407300, BRN 776434, MDL MFCD00008059 ! H: H314-H302, P: P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 5g 25g 100g |
| A12763 | Benzimidazole, 99% [51-17-2], C ₇ H ₆ N ₂ , F.W. 118.14, m.p. 170-174°, b.p. 360°, Merck 14,1081, EINECS 200-081-4, RTECS DD5425000, BRN 109682, MDL MFCD00005585, † H: H303, P: P312 | 50g 250g 1kg |
| 1,2-Benzisothiazol-3(2H)-one 1,1-dioxide sodium salt hydrate , see o-Benzoic sulfimide sodium salt hydrate, A15530, p. 119 Benzocaine , see Ethyl 4-aminobenzoate, A12754, p. 214 5,6-Benzoflavone , see β-Naphthoflavone, A18543, p. 297 7,8-Benzoflavone , see α-Naphthoflavone, A18542, p. 297 | | |
| 36230 | Benzoic acid, ACS, 99.5% min [65-85-0], C ₇ H ₆ O ₂ , F.W. 122.12, Crystalline, m.p. 121-124°, b.p. 249°, f.p. 121° (250°F), d. 1.32, Merck 14,1091, Fieser 1.49, EINECS 200-618-2, RTECS DG0875000, BRN 636131, MDL MFCD00002398, † Maximum level of impurities: Freezing point 122°-123°, Residue after ignition 0.005%, Insoluble in methanol 0.005%, Chlorine compounds (as Cl) 0.005%, Sulfur compounds (as S) 0.002%, Heavy Metals (as Pb) 5ppm, Substances reducing permanganate P.T. ! H: H302-H319-H335, P: P280f-P305+P351+P338 | 25g 100g 500g |
| Benzoic acid benzyl ester , see Benzyl benzoate, L03258, p. 122 | | |
| B23938 | o-Benzoic sulfimide, 98+% [Saccharin, 1,2-Benzothiazol-3(2H)-one 1,1-dioxide] [81-07-2], C ₇ H ₅ NO ₃ S, F.W. 183.18, m.p. 227-230°, d. 0.828, Merck 14,8311, EINECS 201-321-0, RTECS DE4200000, BRN 6888, MDL MFCD00005866, † | 100g 500g 2.5kg |
| Application(s): An artificial sweetener which is an inhibitor for phosphotransferase activity | | |
| A15530 | o-Benzoic sulfimide sodium salt hydrate, 99% [1,2-Benzisothiazol-3(2H)-one 1,1-dioxide sodium salt hydrate, Saccharin sodium hydrate] [82385-42-0], C ₇ H ₄ NNaO ₃ S·xH ₂ O, F.W. 241.21 (205.18anhy), m.p. >300°, Merck 14,8312, EINECS 204-886-1, RTECS DE4550000, BRN 3599229, MDL MFCD00151213, † Effective catalyst for the silylation of a wide range of functional groups by Hexamethyl-disilazane , A15139: <i>J. Org. Chem.</i> , 47, 3966 (1982). | 250g 1kg 5kg |



| Stock # | Description | Size |
|---------|--|--------------------|
| A10188 | Benzoin, 99% <i>[2-Hydroxy-2-phenylacetophenone]</i> [119-53-9], C ₁₄ H ₁₂ O ₂ , F.W. 212.25, m.p. 131-136°, b.p. 334-344°, f.p. 181°(357°F), d. 1.310, Merck 14,1093 , Fieser 6,34 , EINECS 204-331-3, RTECS DI1590000, BRN 391839, MDL MFCD00004496, † Exclusive C-alkylation occurs with an alkyl bromide and NaOH in DMSO: <i>Liebigs Ann. Chem.</i> , 735 , 56 (1970). Borohydride reduction and periodate cleavage of the product lead to a useful synthesis of aryl ketones, with benzoin functioning as a benzoyl anion equivalent: <i>Synthesis</i> , 268 (1975): <div style="text-align: center;">  </div> | 250g 1kg 5kg |
| A10739 | Benzophenone, 99% <i>[Diphenyl ketone]</i> [119-61-9], C ₁₄ H ₁₀ O, F.W. 182.22, m.p. 47-50°, b.p. 305°, f.p. 138°(280°F), d. 1.111, Merck 14,1098 , UN3077, EINECS 204-337-6, RTECS DI9950000, BRN 1238185, MDL MFCD00003076, † H:H400-H410, P:P273-P391-P501a For a review of the use of benzophenone as a triplet-sensitizer in photochemistry, see: <i>Synthesis</i> , 249 (1981). <div style="text-align: center;">  </div> | 250g 1kg 5kg |
| J64901 | Benzopurpurin 4B <i>[C.I. 23500, Direct Red 2]</i> [992-59-6], C ₂₀ H ₁₂ N ₆ Na ₂ O ₆ S ₂ , F.W. 724.73, Powder, Merck 14,1011 , EINECS 213-594-3, RTECS QK1765000, MDL MFCD00012410, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 25g 100g |
| | 1-Benzopyran-2-one , see Coumarin, A15336, p. 168 Benzothiazole-2-thiol , see 2-Mercaptobenzothiazole, A14086, p. 280 1,2-Benzothiazol-3(2H)-one 1,1-dioxide , see o-Benzoic sulfimide, B23938, p. 119 1-Benzotriazolamine , see 1-Aminobenzotriazole, 98%, J63610, p. 92 | |
| A15423 | 1H-Benzotriazole, 99% [95-14-7], C ₆ H ₄ N ₄ , F.W. 119.13, m.p. 96-99°, b.p. 204°/15mm, f.p. 212°(413°F), d. 1.360, Merck 14,1108 , Fieser 13,262 19,20 20,21 21,24 , EINECS 202-394-1, RTECS DM1225000, BRN 112133, MDL MFCD00005699, † ! H:H302-H332-H319-H412, P:P280H-P273-P305+P351+P338 The combination with thionyl chloride (1:1), dissolved in DCM, is a useful and convenient reagent for conversion of alcohols and carboxylic acids to the alkyl or acyl chlorides: <i>Synlett</i> , 1763 (1999). For reviews of Katritzky's extensive work on benzotriazoles as versatile synthetic intermediates, see: <i>Tetrahedron</i> , 47 , 2683 (1991); <i>Chem. Soc. Rev.</i> , 363 (1994) <i>Synthesis</i> , 445 (1994); 1315 (1995). For use in the synthesis of indolo[2,3-b]quinolines, see 2-Chloroquinoline , B23443. <div style="text-align: center;">  </div> | 50g 250g 1kg |
| B23597 | O-(1H-Benzotriazol-1-yl)-N,N,N',N'-tetramethyluronium hexafluorophosphate, 98% <i>[HBTU]</i> [94790-37-1], C ₁₁ H ₁₆ F ₆ N ₆ OP, F.W. 379.25, m.p. ca 200° dec., EINECS 423-020-5, BRN 7328329, MDL MFCD00075445 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Peptide coupling reagent giving high yields with minimal racemization: <i>Synthesis</i> , 572 (1984). <div style="text-align: center;">  </div> | 5g 25g 100g |
| L13470 | O-(1H-Benzotriazol-1-yl)-N,N,N',N'-tetramethyluronium tetrafluoroborate, 99% <i>[TBTU]</i> [125700-67-6], C ₁₁ H ₁₆ BF ₄ N ₆ O, F.W. 321.08, m.p. 195-198° dec., EINECS 423-040-4, BRN 7066325, MDL MFCD00077413 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Peptide coupling reagent, suited to solid-phase peptide synthesis: <i>Tetrahedron Lett.</i> , 30 , 1927 (1989). Of several coupling methods tried in the synthesis of the marine sponge cycloheptapeptide stylopeptide 1, the combination of TBTU and N-ethyl-diisopropylamine in DCM gave the best results: <i>J. Org. Chem.</i> , 61 , 2322 (1996). Reagent for cleavage of THP, silyl, and 4,4-dimethoxytrityl (Dmt) ethers. Selective cleavage of THP ethers in the presence of TBDMS can also be achieved: <i>Synlett</i> , 709 (1999). <div style="text-align: center;">  </div> | 1g 5g 25g |
| J61954 | Benzotropine mesylate <i>[Benzotropine methanesulfonate, Benzotropine hydrobromidum]</i> [132-17-2], C ₂₁ H ₂₅ NO ₃ S ₂ , F.W. 403.54, Solid, UN2811, EINECS 205-048-8, RTECS YM3150000, MDL MFCD00074784 H:H301-H311-H330, P:P301+P310-P304+P340-P320-P330-P361-P405-P501a Application(s): Muscarinic receptor antagonist | 100mg 1g 5g |





| Stock # | Description | Size | |
|---------|--|---|-----------------|
| A14537 | Benzoylacetone, 98+% [1-Phenyl-1,3-butanedione] [93-91-4], C ₁₀ H ₁₀ O ₂ , F.W. 162.19, m.p. 55-60°, b.p. 260-262°, d. 1.090, EINECS 202-286-4, RTECS EK3540200, BRN 742413, MDL MFCD00008786, † Dimetallated derivatives react with electrophiles preferentially at the terminal position; e.g. arylation by 2-chloroquinoline: <i>J. Org. Chem.</i> , 37 , 3199 (1972); <i>J. Am. Chem. Soc.</i> , 97 , 374 (1975). Reaction with aromatic esters gives 1,3-diaryl-1,3,5-pentanetriones, which can be cyclized with acid to γ-pyrones: <i>Org. Synth. Coll.</i> , 5 , 718, 721 (1973): |  | 50g |
| | | 250g | |
| | | 1kg | |
| |  | | |
| J64915 | N-α-Benzoyl-L-arginine p-nitroanilide hydrochloride [Bz-L-Arg-pNA.HCl] [21653-40-7], C ₁₈ H ₂₂ N ₆ O ₆ .HCl, F.W. 434.90, Powder, m.p. 223°, EINECS 244-505-6, BRN 4081878, MDL MFCD00063682 | 100mg 250mg 500mg | |
| L08292 | N-Benzoylaminopurine, 99% [N-Benzoyladenine] [4005-49-6], C ₁₂ H ₉ N ₅ O, F.W. 239.23, m.p. 241-244°, BRN 20585, MDL MFCD00037927 |  | 1g 5g 25g |
| A15179 | Benzoylcholine chloride, 99% ■ [(2-Benzoyloxyethyl)trimethylammonium chloride] [2964-09-2], C ₈ H ₉ CO ₂ CH ₂ CH ₂ N(CH ₃) ₃ .Cl, F.W. 243.73, m.p. 205-208°, EINECS 221-000-9, RTECS GA0830000, BRN 3919727, MDL MFCD00011786 | 10g 50g 250g | |
| J65790 | N₄-Benzoylcytidine, 99% [13089-48-0], C ₁₆ H ₁₇ N ₃ O ₆ , F.W. 347.32, Crystalline powder, m.p. 230-234° dec., MDL MFCD00010572 | 5g 10g 25g | |
| J64175 | N₆-Benzoyl-2'-deoxyadenosine, 98% C ₁₇ H ₁₇ N ₅ O ₄ , F.W. 355.35, Powder | 5g | |
| J65402 | N₆-Benzoyl-5'-O-(4,4'-dimethoxytrityl)-2'-fluoro-2'-deoxyadenosine, 98% C ₃₈ H ₃₄ FN ₅ O ₆ , F.W. 675.70, Powder | 1g | |
| J64064 | N₆-Benzoyl-5'-O-(4,4'-dimethoxytrityl)-2'-fluoro-2'-deoxyadenosine-3'-CE-phosphoramidite, 98% C ₄₇ H ₅₁ FN ₅ O ₇ P, F.W. 875.92, Powder ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g | |
| J64614 | N₄-Benzoyl-5'-O-(4,4'-dimethoxytrityl)-2'-fluoro-2'-deoxycytidine, 98% C ₃₇ H ₃₄ FN ₃ O ₇ , F.W. 651.68, Powder | 100mg 1g | |
| J64259 | N₄-Benzoyl-5'-O-(4,4'-dimethoxytrityl)-2'-fluoro-2'-deoxycytidine-3'-CE-phosphoramidite, 98% C ₄₆ H ₅₁ FN ₅ O ₈ P, F.W. 851.90, Powder ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g | |
| J65098 | N₆-Benzoyl-5'-O-(4,4'-dimethoxytrityl)-2'-O-methyladenosine, 98% C ₃₉ H ₃₇ N ₅ O ₇ , F.W. 687.74, Powder | 1g | |
| J65669 | N₆-Benzoyl-5'-O-(4,4'-dimethoxytrityl)-2'-O-methyladenosine-3'-CE-phosphoramidite, 98% C ₄₈ H ₅₄ N ₇ O ₈ P, F.W. 887.96, Powder ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g | |
| J65169 | N₄-Benzoyl-5'-O-(4,4'-dimethoxytrityl)-2'-O-methylcytidine, 98% C ₃₈ H ₃₇ N ₃ O ₈ , F.W. 663.71, Powder | 1g | |
| J65701 | N₄-Benzoyl-5'-O-(4,4'-dimethoxytrityl)-2'-O-methylcytidine-3'-CE-phosphoramidite, 98% C ₄₇ H ₅₁ N ₅ O ₈ P, F.W. 361.35, Powder ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g | |
| J64345 | N₆-Benzoyl-2'-fluoro-2'-deoxyadenosine, 98% [305808-19-9], C ₁₇ H ₁₆ FN ₅ O ₄ , F.W. 373.34, Powder, MDL MFCD00149575 | 1g | |
| J65736 | N₄-Benzoyl-2'-fluoro-2'-deoxycytidine, 98% C ₁₆ H ₁₆ FN ₃ O ₅ , F.W. 349.31, Powder | 1g | |
| | N-Benzoyladenine , see N-Benzoylaminopurine, L08292, p. 121 | | |
| | N-Benzoylglycine , see Hippuric acid, A12690, p. 245 | | |

| Stock # | Description | Size |
|--|---|----------------------|
| J65492 | N₂-Benzoylguanosine [3676-72-0], C ₁₇ H ₁₇ N ₅ O ₆ , F.W. 387.35, Powder, m.p. 250-252°, MDL MFCD00057045 | 500mg 1g 2g |
| J65475 | N₆-Benzoyl-2'-O-methyladenosine, 98% C ₁₈ H ₁₉ N ₅ O ₅ , F.W. 385.37, Powder | 1g |
| J64474 | N₄-Benzoyl-2'-O-methylcytidine, 98% C ₁₇ H ₁₉ N ₅ O ₆ , F.W. 361.35, Powder | 1g |
| (2-[3-Benzoylphenyl]propionic acid), see Ketoprofen, J62702, p. 263 4'-N-Benzoylstaurosporine, see Midostaurin, J62917, p. 291 | | |
| J64910 | N-Benzyl-p-toluenesulphonamide ▲ [BTS, 4-Methyl-N-(phenylmethyl)benzenesulfonamide] [1576-37-0], C ₁₄ H ₁₅ NO ₂ S, F.W. 261.34, Crystalline powder, m.p. 115°, RTECS XT5490000 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5mg 10mg |
| Benzotropine methanesulfonate , see Benzotropine mesylate, J61954, p. 120 Benzotropine methanesulfonate , see Benzotropine mesylate, J61954, p. 120 | | |
| J61180 | Benzylamine hydrochloride [132-69-4], C ₉ H ₁₂ N ₂ O·HCl, F.W. 345.87, Crystalline powder, m.p. 156-161°, Merck 14 , 1122, EINECS 205-076-0, RTECS NK7875000, MDL MFCD00078957 ! H:H302-H312-H332-H319, P:P261-P280-P305+P315+P338-P302+P352-P304+P340-P501 | 5g 25g |
| Application(s): Nonsteroidal analgesic and anti-inflammatory compound. A prostaglandin synthase inhibitor | | |
| A14678 | 6-Benzyladenine, 99% [6-Benzylaminopurine] [1214-39-7], C ₁₂ H ₁₁ N ₅ , F.W. 225.26, m.p. 229-233°, EINECS 214-927-5, RTECS AU6252200, BRN 19406, MDL MFCD00005572, † ! H:H302, P:P280F-P330 | 1g 5g 25g |
| Application(s): Inhibitor of respiratory kinase in plants. Increases post-harvest life of green vegetables | | |
| 6-Benzylaminopurine , see 6-Benzyladenine, A14678, p. 122 2-(N-Benzylanilinomethyl)-2-imidazole hydrochloride , see Antazoline hydrochloride, 98%, J62511, p. 104 β-Benzyl L-aspartate , see L-Aspartic acid 4-benzyl ester, L08956, p. 111 | | |
| L03258 | Benzyl benzoate, 99+% [Benzoic acid benzyl ester] [120-51-4], C ₁₄ H ₁₂ CO ₂ ·CH ₂ C ₆ H ₅ , F.W. 212.25, m.p. 18-20°, b.p. 323-324°, f.p. 147°(296°F), d. 1.112, n _D ²⁰ 1.5680, Merck 14 , 1127, UN3082, EINECS 204-402-9, RTECS DG4200000, BRN 2049280, MDL MFCD00003075, † !  H:H302-H411, P:P273-P264-P270-P301+P312-P330-P501a | 250g 1kg 2.5kg |
| N-Benzyl-2-(3,4-dihydroxybenzylidene)cyanacetamide , see Tyrphostin B42, 99+%, J61715, p. 387 | | |
| J63465 | Benzylidimethyl-n-tetradecylammonium chloride hydrate, 98% [n-Tetradecylbenzylidimethylammonium chloride hydrate, Myristyltrimethylammonium chloride hydrate] [139-08-2], C ₂₃ H ₄₂ ClN·xH ₂ O, F.W. 368.05(anhy), White powder, Merck 14 , 1059, UN3261, EINECS 205-352-0, RTECS BO7150000, BRN 4062599, MDL MFCD00011771, †  ! H:H314-H400-H302-H312, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 25g |
| Application(s): Phase transfer catalyst | | |
| L19497 | (S)-(-)-1-Benzyl-3-hydroxypyrrolidine, 99%, ee 99% [(S)-(-)-1-Benzyl-3-pyrrolidinol] [101385-90-4], C ₁₁ H ₁₅ NO, F.W. 177.25, b.p. 116°/0.9mm, f.p. 148°(298°F), d. 1.070, n _D ²⁰ 1.5480, [α] _D ²⁰ -3.7° (c=5 in methanol), EINECS 212-273-5, BRN 4982831, MDL MFCD00075485 ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 Product of Toray Industries, Inc. | 1g 5g |
| Application(s): For synthesis of optically active products | | |
| 2-(Benzylidene)acetophenone , see trans-Chalcone, A14734, p. 152 | | |
| B21764 | 2-Benzyl-2-imidazole hydrochloride, 99% [Tolazoline hydrochloride] [59-97-2], C ₁₀ H ₁₂ N ₂ ·HCl, F.W. 196.68, m.p. 174-176°, Merck 14 , 9506, EINECS 200-447-3, MDL MFCD00012693, † ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 25g 100g |
| Application(s): An α adrenergic blocking agent | | |
| A16856 | 4-Benzylxyaniline hydrochloride, 98% [51388-20-6], C ₁₃ H ₁₃ NO·HCl, F.W. 235.72, m.p. ca 225° dec., EINECS 257-170-6, RTECS BW7615000, BRN 3633307, MDL MFCD00012995 | 25g 100g |
| 4-Benzylxybenzyl alcohol, polymer supported , see Wang resin, L17028, p. 393 | | |
| B22372 | N-Benzylloxycarbonyl-D-alaninol, 98% [(2R)-N-Benzylloxycarbonylamino-1-propanol, N-Cbz-D-Alaninol] [61425-27-2], C ₁₁ H ₁₅ NO ₃ , F.W. 209.25, m.p. 82-84°, MDL MFCD00672531 | 1g 5g 25g |


| Stock # | Description | Size |
|---------|---|---|
| H27066 | N-Benzoyloxycarbonyl-L-alaninol [(S)-(2-Hydroxy-1-methylethyl)carbamic acid benzyl ester, Z-Ala-ol] [66674-16-6], C ₁₁ H ₁₅ NO ₃ , F.W. 209.25, MDL MFCD00672530 |  1g 5g |
| | (2R)-N-Benzoyloxycarbonylamino-1-propanol, see N-Benzoyloxycarbonyl-D-alaninol, B22372, p. 122 N-Benzoyloxycarbonyl-L-leucyl-norleucinal, see Calpeptin, 98+%, J60481, p. 144 (2-Benzoyloxyethyl)trimethylammonium chloride, see Benzoylcholine chloride, A15179, p. 121 | |
| J65150 | 5-Benzoyloxygramine, 99% [5-Benzoyloxy-3-(dimethylaminomethyl)indole] [1453-97-0], C ₁₈ H ₂₀ N ₂ O, F.W. 280.37, Powder, m.p. 139°, EINECS 215-927-8, MDL MFCD00005631 ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| | Benzylpenicillin potassium salt , see Penicillin G potassium salt, J63901, p. 313 Benzylpenicillin sodium salt , see Penicillin G sodium salt, J63032, p. 313 | |
| A13850 | Benzylphosphonic acid, 97% [Phenylmethanephosphonic acid, α-Toluenephosphonic acid] [6881-57-8], C ₈ H ₉ CH ₂ PO ₃ H ₂ , F.W. 172.11, m.p. 166-172°, UN3261, BRN 2519318, MDL MFCD00039519, † H: H314, P: P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 1g 5g 25g |
| | Application(s): Structural mimic of phosphotyrosine | |
| J61031 | (R)-1-Benzyl-3-pyrrolidinol [101930-07-8], C ₁₁ H ₁₅ NO, F.W. 177.24, Liquid, b.p. 116°/0.9mm, f.p. 113°(235°F), d. 1.07, n _D ²⁰ 1.548, MDL MFCD00075484 ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | Call |
| | Application(s): For synthesis of optically active products | |
| 41717 | Benzyltrimethylammonium hydroxide, 20% w/w aq. soln. [100-85-6], C ₉ H ₁₃ CH ₂ N(CH ₃) ₃ OH, F.W. 167.25, Liquid, UN3267, EINECS 202-895-5, MDL MFCD00008281, † H: H314, P: P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 50ml 250ml 1L |
| A14927 | Benzyltrimethylammonium hydroxide, 40% w/w in methanol △ [Triton B] [100-85-6], C ₉ H ₁₃ CH ₂ N(CH ₃) ₃ OH, F.W. 167.25, b.p. 65°, f.p. 15°(59°F), d. 0.920, n _D ²⁰ 1.4250, Fieser 1, 1252 5, 29 8, 36, UN2924, EINECS 202-895-5, RTECS BO8575000, BRN 3917256, MDL MFCD00008281, † H: H224-H301-H311-H330-H370-H314, P: P301+P310-P303+P361+P353-P304+P340-P305+P351+P338-P320-P330-P361-P405-P501a Triton® is a registered trademark of Rohm and Haas Co. Useful base catalyst or reagent for many reactions. For use in the Michael addition of nitro-compounds to α,β-unsaturated esters, see: <i>Org. Synth. Coll.</i> , 4, 652 (1963). For C-methylation of 2-Methylcyclohexane-1,3-dione , A11218 , see: <i>Org. Synth. Coll.</i> , 8, 312 (1993). | 100ml 500ml 2.5L |
| J62311 | Berberine chloride [C.I. 75160, Natural Yellow 18] [633-65-8], C ₂₀ H ₁₈ ClNO ₄ , F.W. 371.82, Powder, EINECS 211-195-9, BRN 3836585, MDL MFCD00011939, † | 5g |
| | Application(s): Apoptosis inhibitor. Increases P-glycoprotein expression in hepatoma cells. Stain for heparin in mast cells | |
| L03807 | Berberine chloride hydrate, 97%, water <17% ▲ [141433-60-5], C ₂₀ H ₁₈ ClNO ₄ ·xH ₂ O, F.W. 371.82(anhyd), m.p. ca 200° dec., Merck 14, 1154, EINECS 211-195-9, RTECS DR9866400, BRN 3836585, MDL MFCD00149998, † | 5g 25g |
| | Application(s): Antiprotozoal and antidiarrheal agent. Apoptosis inhibitor | |
| A16092 | BES, 99% [N,N-Bis(2-hydroxyethyl)-2-aminoethanesulfonic acid] [10191-18-1], C ₈ H ₁₅ NO ₃ S, F.W. 213.25, m.p. 153-157°, Solubility: Soluble in water, EINECS 233-465-5, RTECS KI7363500, BRN 1781572, MDL MFCD00007533, † ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a Biological buffer, pK _a 7.15 at 20°C: <i>Biochemistry</i> , 5, 467 (1966). |  25g 100g 500g |
| J60058 | BES, 0.5M buffer soln., pH 4.0 [66992-27-6], Liquid | 100ml 250ml |
| J60624 | BES, 0.5M buffer soln., pH 6.5 [66992-27-6], Liquid | 100ml 250ml |
| J60061 | BES, 0.5M buffer soln., pH 7.0 [66992-27-6], Liquid | 100ml 250ml |
| J63168 | BES, 0.5M buffer soln., pH 7.5 [66992-27-6], Liquid | 100ml 250ml |
| J61955 | BES-buffered saline (2X) [66992-27-6], Liquid, Note: Contains 10.7 g/L BES, 16 g/L NaCl, 0.27g/L sodium phosphate, pH 6.96 | 250ml 500ml |

| Stock # | Description | Size |
|--|---|-----------------------|
| J64052 | BES sodium salt [<i>N,N</i> -Bis(2-hydroxyethyl)-2-aminoethanesulfonic acid sodium salt] [66992-27-6], C ₈ H ₁₄ NNaO ₃ S, F.W. 235.23, Powder, MDL MFCD00067425 | 25g 100g |
| J61106 | Bestatin [Ubenimex, <i>N</i> -[(2 <i>S</i> ,3 <i>R</i>)-3-Amino-2-hydroxy-1-oxo-4-phenylbutanoyl]-L-leucine] [58970-76-6], C ₁₈ H ₂₅ N ₂ O ₄ , F.W. 308.37, Powder, m.p. 233-236°, Merck 14,9842, EINECS 261-529-2, RTECS OH2915000, MDL MFCD00083262 | 25mg 50mg 250mg |
| Application(s): Aminopeptidase B inhibitor. Also inhibits leucine aminopeptidase | | |
| J60384 | Bestatin hydrochloride, 99+% [65391-42-6], C ₁₈ H ₂₄ N ₂ O ₄ ·HCl, F.W. 344.87, Powder, m.p. 216-218°, BRN 4628066, MDL MFCD00058004 | 5mg 25mg |
| Application(s): Aminopeptidase B inhibitor. Also inhibits leucine aminopeptidase | | |
| A16122 | Betaine hydrochloride, 99% [[Carboxymethyl]trimethylammonium chloride] [590-46-5], (CH ₃) ₃ NCH ₂ CO ₂ HCl, F.W. 153.61, m.p. ca 240° dec., Merck 14,1179, EINECS 209-683-1, RTECS BP3136000, BRN 3916181, MDL MFCD00011903, † | 250g 1kg 5kg |
| ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | | |
| Application(s): An organic osmolyte | | |
| J65919 | Bethanechol chloride, 98% [Carbamy]-β-methylcholine chloride] [590-63-6], C ₇ H ₁₀ ClN ₂ O ₂ , F.W. 196.68, Crystalline powder, m.p. 187-190°, EINECS 209-686-8, RTECS BR5425000, MDL MFCD00055224, † | 1g 5g |
| J63701 | Bexarotene, 99+% [LGD-1069, Targretin] [153559-49-0], C ₂₀ H ₂₈ O ₂ , F.W. 348.48, Powder, m.p. 220-225°, Merck 14,1194, Solubility: Soluble in DMSO and ethanol, RTECS DH6834830 | 100mg 300mg |
| ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | | |
| Application(s): Synthetic retinoid analog with specific affinity for the retinoid X receptor | | |
| J61412 | Bezafibrate, 98+% [41859-67-0], C ₁₈ H ₂₀ ClNO ₂ , F.W. 361.82, Powder, m.p. 183-186°, Merck 14,1195, EINECS 255-567-9, RTECS UE8755000, MDL MFCD00078970 | 500mg 1g 5g |
| ! H:H302, P:P264-P270-P301+P312-P330-P501a | | |
| Application(s): A peroxisome proliferator-activated receptor agonist and hypolipidemic agent | | |
| BHA, see 2(3)-tert-Butyl-4-methoxyphenol, B23530, p. 141 BHT, see 2,6-Di-tert-butyl-4-methylphenol, A16863, p. 185 BIBF 1120, see Vargatef, 99+%, J63082, p. 391 BIBR 277, see Telmisartan, 99%, J61441, p. 360 | | |
| J63491 | Bicarbonate, 1M buffer soln., pH 8.0 [144-55-8], Liquid, † | 250ml 500ml |
| J60092 | Bicarbonate, 1M buffer soln., pH 8.5 [144-55-8], Liquid, † | 250ml 500ml |
| J60116 | Bicarbonate, 1M buffer soln., pH 9.0 [144-55-8], Liquid, † | 250ml 500ml |
| 44247 | Bicinchoninic acid disodium salt [BCA, 2,2'-Biquinoline-4,4'-dicarboxylic acid disodium salt] [979-88-4], C ₂₀ H ₁₀ N ₂ O ₄ Na ₂ , F.W. 388.29, Powder/chunks, MDL MFCD00037500, † | 2g 10g |
| ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | | |
| Application(s): For determination of Cu and protein assays | | |
| A14957 | BICINE, 99% [<i>N,N</i> -Bis(2-hydroxyethyl)glycine] [150-25-4], C ₆ H ₁₂ N ₂ O ₄ , F.W. 163.17, m.p. ca 191° dec., Merck 14,1201, Solubility: Soluble in water, EINECS 205-755-1, RTECS MB9700000, BRN 1769362, MDL MFCD00004295, † Biological buffer, pK _a = 8.35 at 20° : <i>Biochemistry</i> , 5, 467 (1966). | 50g 250g 1kg |
| Application(s): Good's buffers | | |
| J60494 | BICINE, 0.5M buffer soln., pH 7.5 [150-25-4], Liquid, † | 100ml 250ml |
| J63924 | BICINE, 0.5M buffer soln., pH 8.0 [150-25-4], Liquid, † | 100ml 250ml |
| J61632 | BICINE, 0.5M buffer soln., pH 8.5 [150-25-4], Liquid, † | 100ml 250ml |
| J62838 | BICINE, 0.5M buffer soln., pH 9.0 [150-25-4], Liquid, † | 100ml 250ml |



























| Stock # | Description | Size |
|--|---|------------------------|
| J65603 | Biebrich Scarlet sodium salt [C.I. 26905, Acid Red 66] [4196-99-0], C ₂₂ H ₁₄ N ₂ Na ₂ O ₆ S ₂ , F.W. 556.49, Powder, m.p. 181-188°, f.p. 300°(572°F), EINECS 224-084-5, BRN 3883900, MDL MFCD00003891, † | 25g 100g |
| J63253 | Bifonazole, 99% [Mycosporan, 1-(α ,4-Diphenylbenzyl)imidazole] [60628-96-8], C ₂₂ H ₁₈ N ₂ , F.W. 310.39, Powder, m.p. 142°, Merck 14,1213, EINECS 262-336-6, RTECS NI3517000, MDL MFCD00865567 ! H:H302, P:P264-P270-P301+P312-P330-P501 | 1g 5g 25g |
| Application(s): Inhibits synthesis of ergosterol in dermatophytes. Calmodulin antagonist | | |
| J64631 | BigCHAP ■ [N,N-Bis(3-D-gluconamidopropyl)cholamide] [86303-22-2], C ₄₂ H ₇₅ N ₃ O ₁₆ , F.W. 878.07, Powder, m.p. 136-145°, MDL MFCD00082541 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250mg 1g 5g |
| A17522 | Bilirubin, 97% ▲ [635-65-4], C ₃₀ H ₃₆ N ₄ O ₆ , F.W. 584.68, Merck 14,1218, EINECS 211-239-7, RTECS DU3038000, BRN 74376, MDL MFCD00005499, † | 1g 5g 25g |
|  | | |
| J65226 | Biliverdin hydrochloride ▲ [55482-27-4], C ₃₃ H ₃₅ ClN ₄ O ₆ , F.W. 619.12, Powder, RTECS DU3033000, MDL MFCD08669554 | 100mg 250mg |
| A14207 | D-(+)-Biotin, 98+% ▲ [Vitamin H] [58-85-5], C ₁₀ H ₁₆ N ₂ O ₃ S, F.W. 244.32, m.p. 224-226°, [α] _D ²⁰ +91° (c=1 in 0.1N NaOH), Merck 14,1231, EINECS 200-399-3, RTECS XJ9088200, BRN 86838, MDL MFCD00005541, † | 1g 5g 10g 25g |
| Application(s): Essential vitamin that is important for amino acid and energy metabolism | | |
| 44771 | (+)-Biotin N-hydroxysuccinimide ester, 98% [Biotin-NHS, N-Hydroxysuccinidobiotin] [35013-72-0], C ₁₄ H ₁₉ N ₃ O ₅ S, F.W. 341.40, Powder, MDL MFCD00078531 | 50mg 250mg 1g |
| Application(s): In coupling reactions to amino acids, peptides and proteins through primary amines | | |
|  | | |
| Biotin-NHS, see (+)-Biotin N-hydroxysuccinimide ester, 44771, p. 125 | | |
| J64477 | Biotin-Phe-Ala-fluoromethyl ketone [Biotin-FA-FMK, Biotin-Phe-Ala-FMK] C ₂₇ H ₃₈ FN ₃ O ₇ S, F.W. 593.67, Powder | 5mg |
| J65533 | Biotin-Val-Ala-Asp(OMe)-fluoromethyl ketone [Biotin-VAD-FMK, Biotin-VAD(OMe)-FMK] C ₃₀ H ₄₀ FN ₃ O ₈ S, F.W. 672.81, Powder | 1mg |
| J64265 | Biotinyl-Ala-Ser-Thr-DL-Asp-fluoromethyl ketone [Biotinyl-ASTD-FMK] C ₂₈ H ₃₈ FN ₃ O ₁₀ S, F.W. 634.67, Powder | 1mg |
| A10265 | Biphenyl, 99% [Diphenyl, Phenylbenzene] [92-52-4], C ₁₂ H ₁₀ , F.W. 154.21, m.p. 69-72°, b.p. 254-255°, f.p. 113°(235°F), d. 0.990, Merck 14,3314, Solubility: Soluble in alcohol and ether, UN3077, EINECS 202-163-5, RTECS DU8050000, BRN 1634058, MDL MFCD00003054, † ! H:H400-H410-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a For use in combination with Li metal for the generation of activated Ca metal, see: <i>Org. Synth. Coll.</i> , 9, 9 (1998). | 250g 1kg 5kg |
|  | | |
| A13956 | Biphenyl-4-carbonyl chloride, 98% ■ [4-Phenylbenzoyl chloride] [14002-51-8], C ₁₃ H ₉ ClO, F.W. 216.67, m.p. 110-115°, b.p. 160°/2mm, Fieser 4,376 7,282, UN3261, EINECS 237-804-8, BRN 472842, MDL MFCD00000692, † ! H:H314, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a Protection of the OH group of a non-crystalline prostaglandin intermediate, in the presence of pyridine, enabled isolation as the crystalline 4-phenylbenzoate ester: <i>J. Am. Chem. Soc.</i> , 93, 1491 (1971). For protection of 3-azido-2,3-dideoxypentoses in a short AZT synthesis, see: <i>Synthesis</i> , 451 (1991). Again, the solid nature of these intermediates facilitates isolation. Protection of amines as their crystalline 4-phenylbenzamides has also been recommended. These amides can be cleaved with sodium amalgam: <i>Tetrahedron Lett.</i> , 3853 (1976). | 10g 50g 250g |
|  | | |

| Stock # | Description | Size |
|---------------|--|---------------------|
| | Biphenyl-2-ol , see 2-Phenylphenol, A10592, p. 317 | |
| A15782 | 2,2'-Bipyridine, 99+% [2,2'-Bipyridyl, 2,2'-Dipyridyl] [366-18-7], C ₁₀ H ₈ N ₂ , F.W. 156.19, m.p. 70°, b.p. 272-273°, f.p. 121°(249°F), Merck 14,3347, UN2811, EINECS 206-674-4, RTECS DW1750000, BRN 113089, MDL MFCD00006212, † | 25g 100g 500g |
| |  H:H301-H311, P:P301+P310-P361-P302+P352-P321-P405-P501a Reagent for iron. Chelating ligand. For use as an alternative to phosphines in Heck type reactions, see: <i>Synlett</i> , 871 (1992). Complex with Chromium(VI) oxide , 12522, has been used in a mild selective oxidation of alcohols to aldehydes and ketones: <i>Acta Chem. Scand.</i> , 25, 1125 (1971). | |
| | Application(s): Reagent for iron determinations | |
| | 2,2'-Bipyridyl , see 2,2'-Bipyridine, A15782, p. 126 | |
| A10907 | 2,2'-Biquinoline, 98+% [Cuproin, 2,2'-Diquinolinyl] [119-91-5], C ₁₈ H ₈ N ₂ , F.W. 256.31, m.p. 193-196°, EINECS 204-357-5, BRN 187259, MDL MFCD00006740, † | 1g 5g 25g |
| |  H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Reagent for spectrophotometric determination of Cu: <i>Analyst</i> , 83, 299 (1958). Indicator for titration of organolithium reagents, giving yellow-green charge-transfer complexes. | |
| | 2,2'-Biquinoline-4,4'-dicarboxylic acid disodium salt , see Bicinchoninic acid disodium salt, 44247, p. 124 | |
| B21457 | α-Bisabolol, 96% △ [515-69-5], C ₁₅ H ₂₆ O, F.W. 222.37, f.p. 135°(275°F), d. 0.93, n _D ²⁰ 1.4950, Merck 14,1241, EINECS 208-205-9, RTECS MJ9685000, BRN 5733954, MDL MFCD03846910, † | 10g 50g |
| |  | |
| J61997 | Bisacodyl, 98+% [603-50-9], C ₂₂ H ₁₈ NO ₄ , F.W. 361.40, Crystalline powder, Merck 14,1242, EINECS 210-044-4, RTECS SM8750000, MDL MFCD00038039, † | 10g 25g |
| | Application(s): A diphenolic laxative that stimulates adenyl cyclase activity | |
| | Bis-acrylamide , see N,N'-Methylenebisacrylamide, 43701, p. 287 | |
| | 1,2-Bis(acrylamido)ethylene glycol , see N,N'-(1,2-Dihydroxyethylene)bisacrylamide, L19211, p. 192 | |
| 44132 | N,N'-Bis(acryloyl)cystamine, 98% [BAC] [60984-57-8], (CH ₂ =CHC(O)NHCH ₂ CH ₂ S) ₂ , F.W. 260.37, Powder, Packaged under argon, m.p. 123-124°, EINECS 262-546-8, MDL MFCD00036225 | 1g 5g 25g |
| |  H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Application(s): Used as a reversible cross-linker for polyacrylamide gels | |
| | 1,4-Bis(acryloyl)piperazine , see 1,4-Diacryloylpiperazine, L15694, p. 182 | |
| | Bis(2-aminoethyl) disulfide dihydrochloride , see Cystamine dihydrochloride, B22873, p. 172 | |
| | 1,2-Bis(2-aminophenoxy)ethane-N,N,N',N'-tetraacetic acid , see BAPTA, A13190, p. 117 | |
| | N,N'-Bis(3-aminopropyl)-1,4-butanediamine tetrahydrochloride , see Spermine tetrahydrochloride, 99%, J63060, p. 351 | |
| | 3,6-Bis(2,2'-arsonophenylazo)-4,5-dihydroxy-2,7-naphthalenedisulfonic acid disodium salt , see Arsenazo III disodium salt, A11838, p. 110 | |
| J62134 | bis-Benzimide H-33342 trihydrochloride trihydrate, 98% [Hoechst 33342®] [23491-52-3], C ₂₇ H ₂₈ N ₄ O ₃ ·3HCl·3H ₂ O, F.W. 615.99 (561.94anhy), Powder, EINECS 245-691-1, RTECS SM1140500, BRN 4088183, MDL MFCD00012679 | 50mg 100mg |
| |  H:H302-H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P501 | |
| | Application(s): Stain for identifying specific chromosome banding patterns | |
| | Bis[N,N-bis(carboxymethyl)aminomethyl]fluorescein sodium salt , see Calcein sodium salt, L10255, p. 142 | |
| J64065 | 1,3-Bis(4-bromophenyl)-5-phenyl-2,4-imidazolidinedione [1,3-Bis(4-bromophenyl)-5-phenylimidazolidine-2,4-dione] [878533-35-8], C ₂₁ H ₁₄ Br ₂ N ₂ O ₂ , F.W. 486.16, Solid | 50mg |
| | N,N-Bis(carboxymethyl)glycine , see Nitrotriacetic acid, 36515, p. 303 | |
| | Bis(3-carboxy-4-nitrophenyl) disulfide , see 5,5'-Dithiobis(2-nitrobenzoic acid), A14331, p. 200 | |
| A13118 | Bis(2-chloroethyl)amine hydrochloride, 98% [821-48-7], C ₄ H ₈ Cl ₂ N·HCl, F.W. 178.49, m.p. 211-215°, UN2923, EINECS 212-479-5, RTECS IA1225000, BRN 3550356, MDL MFCD00012515, † | 50g 250g 1kg |
| |  H:H331-H314-H341-H302-H317, P:P280-P262-P305+P351+P338-P309-P310 | |
| | 4-(4-[Bis(2-chloroethyl)amino]phenyl)butyric acid , see Chlorambucil, 98%, J61964, p. 154 | |
| | Bis(2-chloroethyl)phosphoramidic cyclic propanolamide ester , see Cyclophosphamide monohydrate, L11508, p. 172 | |
| | Bis(cyclopentadienyl)iron , see Ferrocene, 87202, p. 219 | |
| | 1,4-Bis(3,4-dihydroxyphenyl)-2,3-dimethylbutane , see Nordihydroguaiaretic acid, L03149, p. 304 | |
| | 3,6-Bis(dimethylamino)acridine hydrochloride zinc chloride double salt , see Acridine Orange, L13159, p. 76 | |
| | 1,2-Bis(dimethylamino)ethane , see N,N,N',N'-Tetramethylethylenediamine, A12536, p. 364 | |

















| Stock # | Description | Size |
|---------------|--|--|
| | 1-[Bis(dimethylamino)methylene]-1H-1,2,3-triazolo[4,5-b]pyridinium 1-oxide hexafluorophosphate , see O-(7-Aza-1H-benzotriazol-1-yl)-N,N,N',N'-tetramethyluronium hexafluorophosphate, H26082, p. 112 | |
| | Bis(2-ethoxyethyl) ether , see Diethylene glycol diethyl ether, A17478, p. 189 | |
| | 1-(2-[Bis(4-fluorophenyl)methoxy]ethyl)-4-(3-phenylpropyl)piperazine dihydrochloride , see GBR 12909 dihydrochloride, J60684, p. 230 | |
| | 1-[Bis(4-fluorophenyl)methyl]-4-(3-phenyl-2-propenyl)piperazine dihydrochloride , see Flunarizine dihydrochloride, 99+%, J62969, p. 222 | |
| | 2,2'-Bis(8-formyl-1,6,7-trihydroxy-5-isopropyl-3-methylnaphthalene) , see Gossypol, 98+%, J63767, p. 238 | |
| | N,N-Bis(2-hydroxyethyl)-2-aminoethanesulfonic acid , see BES, A16092, p. 123 | |
| | Bis(2-hydroxyethyl)aminotris(hydroxymethyl)methane , see 2,2-Bis(hydroxymethyl)-2,2',2''-nitrilotriethanol, B22515, p. 127 | |
| | Bis(2-hydroxyethyl) ether , see Diethylene glycol, A14728, p. 189 | |
| | N,N-Bis(2-hydroxyethyl)glycine , see BICINE, A14957, p. 124 | |
| | Bis(2-hydroxyethyl) sulfide , see 2,2'-Thiodiethanol, A17002, p. 367 | |
| | 1,7-Bis(4-hydroxy-3-methoxyphenyl)-1,6-heptadiene-3,5-dione , see Curcumin, B21573, p. 170 | |
| B22515 | 2,2-Bis(hydroxymethyl)-2,2',2''-nitrilotriethanol, 98+% [Bis(2-hydroxyethyl)aminotris(hydroxymethyl)methane, Bis-TRIS] [6976-37-0], (HOCH ₂) ₃ CN(CH ₂ CH ₂ OH) ₂ , F.W. 209.24, m.p. 102-105°, EINECS 230-237-7, BRN 2205275, MDL MFCD0002853, † | 25g 100g 500g |
| | ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a Buffer: pH range 5.5 - 8.0. | |
| | Application(s): Good's buffers | |
| | 1,1-Bis(hydroxymethyl)propylamine , see 2-Amino-2-ethyl-1,3-propanediol, B24509, p. 94 | |
| | meso-3,4-Bis(4-hydroxyphenyl)hexane , see Hexestrol, 98+%, J60889, p. 245 | |
| J63401 | Bisindolylmaleimide 1 [GF 109203X] [133052-90-1], C ₂₅ H ₂₄ N ₄ O ₂ , F.W. 412.48, Crystalline powder, MDL MFCD00236428 | 5mg 25mg |
| | Application(s): Very potent and selective inhibitor of protein kinase C | |
| J64757 | Bismarck Brown R [C.I. 21010, Basic Brown 4] [5421-66-9], C ₂₁ H ₂₄ N ₈ , F.W. 461.40, Powder, m.p. 222°dec., EINECS 226-541-4, BRN 1829673, MDL MFCD00036386, † | 25g 100g |
| A16674 | Bismarck Brown Y [C.I. 21000] [10114-58-6], C ₁₈ H ₁₈ N ₈ ·2HCl, F.W. 419.32, Merck 14, 1253, Solubility: Soluble in water, EINECS 233-314-3, MDL MFCD00012977, † | 25g 100g |
| | Application(s): Plasma stain for mucins, cartilage and goblet cells | |
| | Bis(2-methoxyethyl) ether , see Diethylene glycol dimethyl ether, A13397, p. 189 | |
| | 2,3-Bis(2-methoxy-4-nitro-5-sulfophenyl)-2H-tetrazolium-5-carboxanilide inner salt , see XTT sodium salt, J61726, p. 394 | |
| L00183 | N,O-Bis(trimethylsilyl)acetamide, 95% ▀ [BSA] [10416-59-8], C ₈ H ₂₂ NOSi ₂ , F.W. 203.43, m.p. -24°, b.p. 71-73°/35mm, f.p. 42° (107°F), d. 0.829, n _D ²⁰ 1.4170, Fieser 1,61 2,30 3,23 18,57 20,50 21,62, UN2920, EINECS 233-892-7, RTECS AK3000000, BRN 1306669, MDL MFCD0008270, † | 5g 25g 100g |
| | ! H: H314-H226-H302-EUH014, P: P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a Powerful silylation reagent for a wide range of functional groups under mild conditions. Reviews: <i>J. Prakt. Chem./Chem. Ztg.</i> , 337 , 332 (1995); <i>Synthesis</i> , 357 (1998). Unlike halosilanes, silylated amides often need no added base catalysts. For an example of use without added solvent or catalyst for the silylation of a tertiary α-hydroxy ketone, see: <i>Org. Synth. Coll.</i> , 7 , 381 (1990). Silylating power can be increased in polar solvents such as DMF or acetonitrile, or by addition of acidic catalysts, often TMS chloride, or an acid such as TFA or HCl. O-Silylation in the presence of TBAF (0.02 equiv.) occurs under very mild conditions: <i>Tetrahedron Lett.</i> , 35 , 8409 (1994). BSA catalyzes the acylation of acylphosphoranes with activated derivatives of carboxylic acids. Subsequent ozonolysis, or oxidation with singlet oxygen or dimethyldioxirane, provides a route to 1,2,3-triketones: <i>J. Org. Chem.</i> , 54 , 2785 (1989); 60 , 8231 (1995): | |
| |  | |
| | Bis-tris , see 2,2-Bis(hydroxymethyl)-2,2',2''-nitrilotriethanol, B22515, p. 127 | |
| J62928 | BIS-TRIS, 0.5M buffer soln., pH 6.0 [6976-37-0], Liquid, † | 100ml 250ml |
| J63036 | BIS-TRIS, 0.5M buffer soln., pH 6.5 [6976-37-0], Liquid, † | 100ml 250ml |
| J60656 | BIS-TRIS, 0.5M buffer soln., pH 7.0 [6976-37-0], Liquid, † | 100ml 250ml |
| J62177 | BIS-TRIS, 0.5M buffer soln., pH 7.5 [6976-37-0], Liquid, † | 100ml 250ml |








| Stock # | Description | Size |
|---------|---|---------------------|
| 43496 | 1,3-Bis[tris(hydroxymethyl)methylamino]propane, 98+% [Bis-Tris Propane] [64431-96-5], CH ₃ [CH ₂ NHC(CH ₂ OH) ₃] ₃ , F.W. 282.34, Powder, m.p. 168-170°, EINECS 264-899-3, MDL MFCD00004689, Note: pKa ₁ =6.8, useful pH range 6.3-9.5 | 25g 100g 500g |
| | Bis-tris propane, see 1,3-Bis[tris(hydroxymethyl)methylamino]propane, 43496, p. 128 | |
| J63555 | BIS-TRIS propane, 0.2M buffer soln., pH 7.0 [64431-96-5], Liquid | 100ml 250ml |
| J61292 | BIS-TRIS propane, 0.2M buffer soln., pH 7.5 [64431-96-5], Liquid | 100ml 250ml |
| J62831 | BIS-TRIS propane, 0.2M buffer soln., pH 8.0 [64431-96-5], Liquid | 100ml 250ml |
| J62012 | BIS-TRIS propane, 0.2M buffer soln., pH 8.5 [64431-96-5], Liquid | 100ml 250ml |
| J63943 | BIS-TRIS propane, 0.2M buffer soln., pH 9.0 [64431-96-5], Liquid | 100ml 250ml |
| J62354 | BIS-TRIS propane, 0.5M buffer soln., pH 6.5 [64431-96-5], Liquid | 100ml 250ml |
| | Bitrex® Macfarlan Smith, A Johnson Matthey Co., see Denatonium benzoate, J61048, p. 176 | |
| L00812 | Biuret, 97% [Carbamylurea] [108-19-0], H ₂ NCONHCONH ₂ , F.W. 103.08, m.p. ca 189° dec., d. 1.46, Merck 14,1309, EINECS 203-559-0, BRN 1703510, MDL MFCD00007946, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 100g 500g |
| J61883 | Blasticidin S hydrochloride, 98+%, 10mg/ml in 1M HEPES buffer soln. [3513-03-9], C ₁₇ H ₂₆ N ₈ O ₅ ·HCl, F.W. 458.90, Liquid, Merck 14,1316, UN2810, MDL MFCD02091640 ! H:H302, P:P264-P270-P301+P312-P330-P501a Application(s): Inhibits protein synthesis and induces apoptosis | 20mg 100mg |
| J60727 | Bleomycin sulfate [9041-93-4], Powder, Merck 14,1318, EINECS 232-925-2, RTECS EC5991990, MDL MFCD00070310 ☠ H:H340-H351, P:P281-P201-P202-P308+P313-P405-P501a Application(s): A glycopeptide antibiotic. Inhibits DNA synthesis and causes breaks in DNA strands | 25mg 100mg |
| J61417 | BLOTTO Liquid, Note: 5% non-fat dried milk, 0.02% sodium azide. Application(s): Blocking reagent for immunohistochemistry experiments. | 500ml 1L |
| J60296 | BLOTTO in PBS Liquid, Note: Contains 5% nonfat dry milk in PBS. Application(s): Blocking reagent for immunohistochemistry experiments | 250ml 500ml |
| J60166 | BLOTTO in PBS, with 0.02% sodium azide Liquid, Note: 5% nonfat dry milk, 0.02% Sodium azide in PBS Application(s): Blocks non-specific binding site for antibodies on the membrane | 250ml 500ml |
| J63851 | BLOTTO antifoam in PBS Liquid, Note: Contains 5% nonfat dry milk and 0.01% Antifoam A in PBS Application(s): Blocking buffer for immunohistochemistry experiments | 250ml 500ml |
| J61888 | BLOTTO antifoam in PBS, with 0.02% sodium azide Liquid, Note: 5% nonfat dry milk, 0.01% Antifoam A, and 0.02% azide in PBS. Application(s): Blocking reagent for immunohistochemistry experiments | 250ml 500ml |
| J63238 | BLOTTO in TBS Liquid, Note: 5% nonfat dry milk in TBS Application(s): Blocks non-specific binding site for antibodies on the membrane | 250ml 500ml |
| J62235 | BLOTTO in TBS, with 0.02% sodium azide Liquid, Note: 5% nonfat dry milk and 0.02% sodium azide in TBS Application(s): Blocking reagent in immunohistochemistry experiments | 250ml 500ml |
| J62031 | BLOTTO antifoam in TBS Liquid, Note: Contains 5% nonfat dry milk and 0.01% Antifoam A in TBS Application(s): Blocks non-specific binding site for antibodies on the membrane | 250ml 500ml |








| Stock # | Description | Size |
|---------|--|---|
| J63891 | BLOTTO antifoam in TBS, with 0.02% sodium azide Liquid, Note: Contains 5% nonfat dry milk, 0.01% Antifoam A and 0.02% azide in TBS. Application(s): Blocking reagent for immunological procedures. | 250ml 500ml |
| J61880 | BLOTTO and Tween 20 in PBS Liquid, Note: Contains 5% nonfat dry milk and 0.05% Tween-20 in PBS Application(s): Blocking reagent in immunohistochemistry experiments | 250ml 500ml |
| J62304 | BLOTTO and Tween 20 in PBS, with 0.02% sodium azide Liquid, Note: This buffer contains 5% nonfat dry milk, 0.05% Tween-20 and 0.02% sodium azide in PBS Application(s): Blocking reagent for immunohistochemistry experiments | 250ml 500ml |
| J62341 | BLOTTO and Tween 20 in TBS Liquid, Note: 5% nonfat dry milk and 0.05% Tween-20 in TBS Application(s): Blocks non-specific binding site for antibodies on the membrane | 500ml 1L |
| J63026 | BLOTTO and Tween 20 in TBS, with 0.02% sodium azide Liquid, Note: This product contains 5% nonfat dry milk, 0.05% Tween-20 and 0.02% sodium azide in TBS Application(s): Blocking reagent for immunohistochemistry experiments | 500ml 1L |
| A12502 | Blue Tetrazolium chloride [BTC, Tetrazolium Blue chloride] [1871-22-3], C ₁₀ H ₂₀ Cl ₂ N ₄ O ₂ , F.W. 727.66, m.p. ca 255° dec., Merck 14,9244, Fieser 1,61 15.43, EINECS 217-488-8, BRN 3894077, MDL MFCD00040933, † Reagent for identification of reducing sugars. For use in the oxidation of steroids, see: <i>J. Chem. Soc., Chem. Commun.</i> , 2687 (1988). |  2Cl ⁻ 1g 5g 25g |
| | BK , see Bradykinin, J63131, p. 134 BMV-13754 , see Nefazodone hydrochloride, 98+%, J62793, p. 299 BMS-354825 , see Dasatinib, J60621, p. 175 BN-52021 , see Ginkgolide B, J60646, p. 232 | |
| B22522 | N-Boc-β-alanine, 99% [Boc-β-Ala-OH, N-tert-Butoxycarbonyl-β-alanine] [3303-84-2], (CH ₃) ₃ CO ₂ CNHCH ₂ CH ₂ CO ₂ H, F.W. 189.21, m.p. 73-76°, EINECS 221-979-2, MDL MFCD00037291 |  2.5g 10g |
| B22706 | N-Boc-D-alanine, 98+% [Boc-D-Ala-OH, N-(tert-Butoxycarbonyl)-D-alanine] [7764-95-6], C ₈ H ₁₅ NO ₄ , F.W. 189.21, m.p. 81-84°, [α] _D ²⁰ +26° (c=2 in acetic acid), BRN 2048396, MDL MFCD00063123 |  5g 25g |
| A16018 | N-Boc-L-alanine, 98+% [Boc-Ala-OH, N-(tert-Butoxycarbonyl)-L-alanine] [15761-38-3], C ₈ H ₁₅ NO ₄ , F.W. 189.21, m.p. 80-84°, [α] _D ²⁰ -26° (c=2 in acetic acid), EINECS 239-847-8, BRN 1726365, MDL MFCD00037225, † |  5g 25g |
| B22407 | N-Boc-γ-aminobutyric acid, 98+% [N-tert-Butoxycarbonyl-γ-aminobutyric acid] [57294-38-9], (CH ₃) ₃ COCONH(CH ₂) ₃ CO ₂ H, F.W. 203.2, m.p. 57-60°, MDL MFCD00037313 | 1g 5g |
| | (S)-2-(Boc-amino)-6-(dimethylamino)hexanoic acid, see N(a)-Boc-N(e),N(e)-dimethyl-L-lysine, H52437, p. 130 (S)-2-(Boc-amino)-3,3-dimethylbutyric acid, see N-Boc-L-tert-leucine, H51136, p. 133 (S)-2-(Boc-amino)-3-ethoxypropionic acid, see N-Boc-O-ethyl-L-serine, H52781, p. 130 | |
| H51990 | (S)-4-(Boc-amino)-2-(Fmoc-amino)butyric acid, 95% [Fmoc-Dab(Boc)-OH, Nγ-Boc-Nα-Fmoc-L-2,4-diaminobutyric acid] [125238-99-5], C ₂₄ H ₂₈ N ₂ O ₆ , F.W. 440.50, BRN 6250328, MDL MFCD00151941 |  250mg 1g 5g |
| | (S)-7-(Boc-amino)-3-(Fmoc-amino)heptanoic acid, see N-Boc-Nβ-Fmoc-L-β-homolysine, H52189, p. 130 (R)-3-(Boc-amino)-3-(4-methoxyphenyl)propionic acid, see N-Boc-4-methoxy-D-phenylalanine, H52082, p. 131 | |
| H52173 | (S)-3-(Boc-amino)-5-methylhexanoic acid, 95% [N-Boc-L-β-homoleucine, Boc-β-Homoleu-OH] [132549-43-0], C ₁₂ H ₂₃ NO ₄ , F.W. 245.32, m.p. 53-55°, BRN 4251252, MDL MFCD02101665 |  250mg 1g |
| H52174 | (S)-3-(Boc-amino)-4-phenylbutyric acid, 95% [N-Boc-L-β-homophenylalanine, Boc-β-Homophe-OH] [51871-62-6], C ₁₅ H ₂₁ NO ₄ , F.W. 279.34, m.p. 101-107°, BRN 3060457, MDL MFCD01076271 |  250mg 1g |
| | Boc anhydride , see Di-tert-butyl dicarbonate, A14708, p. 184 | |
| A16019 | N(α)-Boc-L-asparagine, 98+% [Boc-Asn-OH, N(α)-tert-Butoxycarbonyl-L-asparagine] [7536-55-2], C ₈ H ₁₆ N ₂ O ₆ , F.W. 232.24, m.p. ca 170° dec., [α] _D ²⁰ -7.3° (c=2 in DMF), EINECS 231-405-2, BRN 1977963, MDL MFCD00038152, † |  5g 25g |


| Stock # | Description | Size |
|---------|---|---|
| L08498 | N-Boc-L-aspartic acid, 98+% [Boc-Asp-OH, <i>N</i> -(<i>tert</i> -Butoxycarbonyl)-L-aspartic acid] [13726-67-5], C ₈ H ₁₅ NO ₆ , F.W. 233.23, m.p. 115°, [α] _D ²⁰ -5.5° (c=1 in methanol), EINECS 237-294-7, BRN 1913973, MDL MFCD00037279 |  1g 5g |
| B22314 | N-Boc-L-aspartic acid 1-benzyl ester, 99% [Boc-Asp-OBzl, <i>N</i> -(<i>tert</i> -Butoxycarbonyl)-L-aspartic acid 1-benzyl ester] [30925-18-9], C ₁₆ H ₂₁ NO ₆ , F.W. 323.35, m.p. 95-97°, MDL MFCD00065563 |  1g 5g |
| B21758 | N-Boc-L-aspartic acid 4-benzyl ester, 98% [Boc-Asp(OBzl)-OH, <i>N</i> -(<i>tert</i> -Butoxycarbonyl)-L-aspartic acid 4-benzyl ester] [7536-58-5], C ₁₆ H ₂₁ NO ₆ , F.W. 323.35, m.p. 110-112°, EINECS 231-406-8, MDL MFCD00065564, † |  1g 5g |
| J65812 | N-Boc-L-aspartic acid 4-methyl ester fluoromethyl ketone [Boc-D-FMK, Boc-Asp(OMe)-FMK] [187389-53-3], C ₁₁ H ₁₈ FNO ₅ , F.W. 263.26, Powder, MDL MFCD03453073 | 5mg |
| B22666 | N-Boc-O-benzyl-D-serine, 99% [Boc-D-Ser(Bzl)-OH, <i>N</i> -(<i>tert</i> -Butoxycarbonyl)-O-benzyl-D-serine] [47173-80-8], C ₁₅ H ₂₁ NO ₅ , F.W. 295.31, m.p. 60-63°, MDL MFCD00038248 |  1g 5g |
| B21677 | N-Boc-O-benzyl-L-threonine, 99% [Boc-Thr(Bzl)-OH, <i>N</i> -(<i>tert</i> -Butoxycarbonyl)-O-benzyl-L-threonine] [15260-10-3], C ₁₆ H ₂₃ NO ₅ , F.W. 309.36, m.p. 115-116°, EINECS 239-304-5, MDL MFCD00066062, † |  1g 5g |
| B23455 | N-Boc-O-benzyl-L-tyrosine, 98% [Boc-Tyr(Bzl)-OH, <i>N</i> -(<i>tert</i> -Butoxycarbonyl)-O-benzyl-L-tyrosine] [2130-96-3], C ₂₁ H ₂₅ NO ₅ , F.W. 371.43, m.p. 108-110°, EINECS 218-349-4, MDL MFCD00065597 |  1g 5g 25g |
| H51969 | N-Boc-4-bromo-L-phenylalanine, 98% [Boc-Phe(4-Br)-OH] [62129-39-9], C ₁₆ H ₁₈ BrNO ₃ , F.W. 344.20, m.p. 118-120°, MDL MFCD00237571 |  1g 5g |
| H52015 | N-Boc-3-chloro-L-phenylalanine, 95% [Boc-Phe(3-Cl)-OH] [114873-03-9], C ₁₆ H ₁₆ ClNO ₃ , F.W. 299.75, MDL MFCD00672515 |  250mg 1g 5g |
| H52181 | N-Boc-4-chloro-D-phenylalanine, 95% [Boc-D-Phe(4-Cl)-OH] [57292-44-1], C ₁₆ H ₁₆ ClNO ₃ , F.W. 299.75, m.p. 110°, BRN 5381988, MDL MFCD00076978 |  250mg 1g 5g |
| H52437 | N(α)-Boc-N(ε),N(ε)-dimethyl-L-lysine, 97% [(<i>S</i>)-2-(Boc-amino)-6-(dimethylamino)hexanoic acid, <i>N</i> (α)- <i>tert</i> -Butoxycarbonyl-N(ε),N(ε)-dimethyl-L-lysine] [65671-53-6], C ₁₃ H ₂₆ N ₂ O ₄ , F.W. 274.36 |  250mg 1g |
| H52781 | N-Boc-O-ethyl-L-serine, 97% [(<i>S</i>)-2-(Boc-amino)-3-ethoxypropionic acid, <i>N</i> -(<i>tert</i> -Butoxycarbonyl)-O-ethyl-L-serine] [104839-00-1], C ₁₆ H ₁₉ NO ₅ , F.W. 233.26 |  250mg 1g |
| H51963 | N-Boc-3-fluoro-D-phenylalanine, 98% [Boc-D-Phe(3-F)-OH] [114873-11-9], C ₁₄ H ₁₆ FNO ₃ , F.W. 283.30, m.p. 75-79°, MDL MFCD00672523 |  1g 5g |
| H51988 | N-Boc-3-fluoro-L-phenylalanine, 95% [Boc-Phe(3-F)-OH] [114873-01-7], C ₁₄ H ₁₆ FNO ₃ , F.W. 283.30, m.p. 75-80°, BRN 5347375, MDL MFCD00672522 |  250mg 1g 5g |
| H52189 | N(ω)-Boc-N(β)-Fmoc-L-β-homolysine, 95% [(<i>S</i>)-7-(Boc-amino)-3-(Fmoc-amino)heptanoic acid, Fmoc-β-Homolys(Boc)-OH] [203854-47-1], C ₂₇ H ₃₄ N ₂ O ₆ , F.W. 482.58, BRN 8022293, MDL MFCD01863054 |  250mg 1g |
| H28301 | N(ε)-Boc-N(α)-Fmoc-D-lysine, 98% [N(ε)-(<i>tert</i> -Butoxycarbonyl)-N(α)-9-fluorenylmethoxycarbonyl-D-lysine, Fmoc-D-Lys(Boc)-OH] [92122-45-7], C ₂₆ H ₃₂ N ₂ O ₆ , F.W. 468.54, m.p. 135-139°, [α] _D ²⁰ +11° (c=1 in DMF), MDL MFCD00065660 |  1g 5g |
| B21944 | N-Boc-D-glutamic acid 1-benzyl ester, 99% [Boc-D-Glu-OBzl, <i>N</i> -(<i>tert</i> -Butoxycarbonyl)-D-glutamic acid 1-benzyl ester] [34404-30-3], C ₁₇ H ₂₃ NO ₆ , F.W. 337.37, MDL MFCD00038266 |  1g 5g |




| Stock # | Description | Size |
|--|---|-------------------|
| H52191 | N-Boc-L-β-glutamic acid 5-benzyl ester, 95% [N-Boc-L-β-homoaspartic acid 5-benzyl ester, Boc-β-Glu(OBzl)-OH] [254101-10-5], C ₁₇ H ₂₃ NO ₆ , F.W. 337.37, BRN 8430789, MDL MFCD01862861 | 250mg 1g |
| B22322 | N-Boc-L-glutamic acid 5-tert-butyl ester, 99% [Boc-Glu(OtBu)-OH, N-tert-Butoxycarbonyl-L-glutamic acid 4-tert-butyl ester] [13726-84-6], C ₁₄ H ₂₅ NO ₆ , F.W. 303.36, m.p. 110-112°, MDL MFCD00038257 | 1g 5g |
| L08536 | N(α)-Boc-D-glutamine, 98+% [Boc-D-Gln-OH, N(α)-tert-Butoxycarbonyl-D-glutamine] [61348-28-5], C ₁₆ H ₁₈ N ₂ O ₅ , F.W. 246.26, m.p. 117-119°, [α] _D ²⁰ +3.5° (c=2 in ethanol), BRN 1981311, MDL MFCD00038158 | 250mg 1g |
| L08604 | N(α)-Boc-L-glutamine, 98+% [Boc-Gln-OH, N(α)-tert-Butoxycarbonyl-L-glutamine] [13726-85-7], C ₁₆ H ₁₈ N ₂ O ₅ , F.W. 246.26, m.p. 118-120°, [α] _D ²⁰ -3.5° (c=2 in ethanol), EINECS 237-296-8, BRN 2127805, MDL MFCD00065571, † | 5g 25g |
| A11579 | N-Boc-glycine, 98+% [Boc-Gly-OH, N-(tert-Butoxycarbonyl)glycine] [4530-20-5], (CH ₃) ₃ COCONHCH ₂ CO ₂ H, F.W. 175.18, m.p. 87-90°, EINECS 224-864-5, BRN 1101514, MDL MFCD00002690, † ▲ H: H318, P: P280-P305+P351+P338-P310 | 5g 25g 100g |
| L08810 | N(α)-Boc-D-histidine, 98+% [Boc-D-His-OH, N(α)-tert-Butoxycarbonyl-D-histidine] [50654-94-9], C ₁₁ H ₁₁ N ₃ O ₅ , F.W. 255.27, m.p. ca 197° dec., [α] _D ²⁰ -26° (c=1 in methanol), BRN 4196575, MDL MFCD00037851 | 250mg 1g |
| B22042 | N(α)-Boc-L-histidine, 98+% [Boc-His-OH, N(α)-tert-Butoxycarbonyl-L-histidine] [17791-52-5], C ₁₁ H ₁₁ N ₃ O ₅ , F.W. 255.27, m.p. ca 198° dec., [α] _D ²⁰ +26° (c=1 in methanol), EINECS 241-768-9, BRN 755289, MDL MFCD00065576 | 1g 5g |
| N-Boc-L-β-homoaspartic acid 5-benzyl ester , see N-Boc-L-▲-glutamic acid 5-benzyl ester, H52191, p. 131 | | |
| N-Boc-L-β-homoleucine , see (S)-3-(Boc-amino)-5-methylhexanoic acid, H52173, p. 129 | | |
| H27110 | N-Boc-trans-4-hydroxy-L-proline, 97% [Boc-Hyp-OH, 1-tert-Butoxycarbonyl-(2S,4R)-4-hydroxyproline-2-carboxylic acid] [13726-69-7], C ₁₀ H ₁₇ NO ₅ , F.W. 231.25, m.p. 123-127°, MDL MFCD00053370 | 1g 5g 25g |
| H51960 | N-Boc-4-iodo-L-phenylalanine, 98% ▲ [Boc-Phe(4-I)-OH] [62129-44-6], C ₁₄ H ₁₅ INO ₄ , F.W. 391.21, m.p. 150° dec., BRN 4503851, MDL MFCD00037119 | 5g 25g |
| L09124 | N-Boc-D-leucine hydrate, 98+% [Boc-D-Leu-OH.H ₂ O, N-(tert-Butoxycarbonyl)-D-leucine] [16937-99-8], C ₁₁ H ₂₁ NO ₄ .xH ₂ O, F.W. 231.30(anhy), m.p. 80-84°, [α] _D ²⁰ +25° (c=2 in acetic acid), BRN 2331060, MDL MFCD00065583 | 1g 5g |
| B21738 | N(ε)-Boc-L-lysine, 97% [N(ε)-Boc-L-lysine, H-Lys(Boc)-OH] [2418-95-3], C ₁₁ H ₂₂ N ₂ O ₅ , F.W. 246.31, m.p. ca 250° dec., BRN 4252546, MDL MFCD00037221 | 1g 5g |
| L09207 | N-Boc-D-methionine, 98+% [Boc-D-Met-OH, N-(tert-Butoxycarbonyl)-D-methionine] [5241-66-7], C ₁₀ H ₁₉ NO ₄ .S, F.W. 249.32, m.p. 47-50°, [α] _D ²⁰ +29° (c=1 in methanol), EINECS 226-043-7, BRN 4294122, MDL MFCD00038256 | 1g 5g |
| L08366 | N-Boc-L-methionine, 98+% [Boc-Met-OH, N-(tert-Butoxycarbonyl)-L-methionine] [2488-15-5], C ₁₀ H ₁₉ NO ₄ .S, F.W. 249.32, m.p. 48-51°, [α] _D ²⁰ -22° (c=1 in methanol), EINECS 219-639-3, BRN 1727869, MDL MFCD00065586 | 1g 5g |
| H52082 | N-Boc-4-methoxy-D-phenylalanine, 95% [(R)-3-(Boc-amino)-3-(4-methoxyphenyl)propionic acid, Boc-D-Tyr(Me)-OH] [68856-96-2], C ₁₅ H ₂₁ NO ₅ , F.W. 295.33 | 250mg 1g 5g |
| H31317 | N-Boc-N-methyl-L-alanine, 98% [Boc-N-Me-Ala-OH, N-tert-Butoxycarbonyl-N-methyl-L-alanine] [16948-16-6], C ₉ H ₁₇ NO ₄ , F.W. 203.24, m.p. 88-92°, [α] _D ²⁰ -31° (c=1 in ethanol), MDL MFCD00037242 | 1g 5g |

| Stock # | Description | | Size |
|---------|---|--|--------------------------|
| H51983 | N-Boc-4-methyl-L-phenylalanine, 95% [Boc-Phe(4-Me)-OH] [80102-26-7], C ₁₆ H ₁₉ NO ₄ , F.W. 279.34, m.p. 84-88°, BRN 5381557, MDL MFCD01317027 |  | 250mg 1g 5g |
| H52787 | N-Boc-2-methyl-D-serine, 97% [84311-18-2], C ₉ H ₁₇ NO ₅ , F.W. 219.24 |  | 250mg 1g |
| H52570 | N-Boc-2-methyl-L-serine, 97% [84311-19-3], C ₉ H ₁₇ NO ₅ , F.W. 219.24 |  | 250mg 1g |
| H52058 | N-Boc-3-nitro-L-phenylalanine, 95% [Boc-Phe(3-NO2)-OH] [131980-29-5], C ₁₄ H ₁₃ N ₂ O ₆ , F.W. 310.31, MDL MFCD01317033 |  | 250mg 1g 5g |
| H51986 | N-Boc-4-nitro-L-phenylalanine, 95% [Boc-Phe(4-NO2)-OH] [33305-77-0], C ₁₆ H ₁₃ N ₂ O ₆ , F.W. 310.31, EINECS 251-450-1, BRN 2820671, MDL MFCD00038128 |  | 250mg 1g 5g |
| L08615 | N-Boc-L-norvaline, 98+% [Boc-Nva-OH, N-(tert-Butoxycarbonyl)-L-norvaline] [53308-95-5], C ₁₀ H ₁₉ NO ₄ , F.W. 217.28, m.p. 43-47°, [α] _D ²⁰ -15° (c=2 in methanol), BRN 3607582, MDL MFCD00037268 |  | 250mg 1g |
| L08722 | N-Boc-D-phenylalanine, 98% [Boc-D-Phe-OH, N-(tert-Butoxycarbonyl)-D-phenylalanine] [18942-49-9], C ₁₉ H ₁₉ NO ₄ , F.W. 265.31, m.p. 85-88°, [α] _D ²⁰ -24° (c=1 in ethanol), BRN 3593396, MDL MFCD00063149 |  | 1g 5g |
| A16017 | N-Boc-L-phenylalanine, 99% [Boc-Phe-OH, N-(tert-Butoxycarbonyl)-L-phenylalanine] [13734-34-4], C ₁₉ H ₁₉ NO ₄ , F.W. 265.31, m.p. 84-88°, [α] _D ²⁰ +25° (c=1 in ethanol), EINECS 237-305-5, BRN 2219729, MDL MFCD00002663, † |  | 5g 25g |
| L18540 | N-Boc-D-phenylglycine, 99% [Boc-D-Phg-OH, N-(tert-Butoxycarbonyl)-D-phenylglycine] [33125-05-2], C ₁₈ H ₁₇ NO ₄ , F.W. 251.28, m.p. 90-92°, [α] _D ²⁰ -144° (c=1 in ethanol), BRN 3033982, MDL MFCD00062043 Reagent of choice for assignment of absolute configuration of chiral primary amines by ¹ H NMR, giving better results than Mosher's acid ((R)-(+)-α-Methoxy-α-(trifluoromethyl)phenylacetic acid, B22968): J. Org. Chem., 64, 4669 (1999). |  | 1g 5g |
| L18541 | N-Boc-L-phenylglycine, 99% [Boc-Phg-OH, N-(tert-Butoxycarbonyl)-L-phenylglycine] [2900-27-8], C ₁₈ H ₁₇ NO ₄ , F.W. 251.28, m.p. 88-90°, [α] _D ²⁰ +144° (c=1 in ethanol), BRN 3592362, MDL MFCD00065588 |  | 1g 5g |
| L08826 | N-Boc-D-proline, 98+% [Boc-D-Pro-OH, N-(tert-Butoxycarbonyl)-D-proline] [37784-17-1], C ₁₀ H ₁₇ NO ₄ , F.W. 215.25, m.p. 133-135°, [α] _D ²⁰ +61° (c=1 in acetic acid), BRN 479316, MDL MFCD00063226 |  | 1g 5g |
| A13744 | N-Boc-L-proline, 99% [Boc-Pro-OH, N-(tert-Butoxycarbonyl)-L-proline] [15761-39-4], C ₁₀ H ₁₇ NO ₄ , F.W. 215.25, m.p. 132-136°, [α] _D ²⁰ -61° (c=1 in acetic acid), EINECS 239-848-3, BRN 15828, MDL MFCD00037324, † |  | 5g 25g |
| L09885 | N-Boc-L-prolinol, 98+% [Boc-Pro-ol, N-(tert-Butoxycarbonyl)-L-prolinol] [69610-40-8], C ₁₀ H ₁₉ NO ₄ , F.W. 201.27, m.p. 59-62°, [α] _D ²⁰ -54° (c=5 in methanol), BRN 3542667, MDL MFCD00066232 |  | 250mg 1g 5g 25g |
| H52128 | N-Boc-2-propargyl-L-glycine, 95% [63039-48-5], C ₁₀ H ₁₃ NO ₄ , F.W. 213.23, MDL MFCD01320855 |  | 250mg 1g |
| L08904 | N-Boc-D-serine, 98+% [Boc-D-Ser-OH, N-(tert-Butoxycarbonyl)-D-serine] [6368-20-3], C ₈ H ₁₅ NO ₅ , F.W. 205.21, m.p. 88-91°, [α] _D ²⁰ +3.5° (c=2 in acetic acid), BRN 1874714, MDL MFCD00063142 |  | 1g 5g |
| A16224 | N-Boc-L-serine, 98% (dry wt.), may cont. up to 10% water [Boc-Ser-OH, N-(tert-Butoxycarbonyl)-L-serine] [3262-72-4], C ₈ H ₁₅ NO ₅ , F.W. 205.21, m.p. 90-91° dec., [α] _D ²⁰ -3.5° (c=2 in acetic acid), EINECS 221-867-3, BRN 2212252, MDL MFCD00037243 |  | 1g 5g 25g |





| Stock # | Description | Size |
|--|---|---|
| H51136 | N-Boc-L-tert-leucine, 98% [<i>N</i> -tert-Butoxycarbonyl-L-leucine, <i>Boc-Tle-OH</i>] [62965-35-9], C ₁₁ H ₂₁ NO ₄ , F.W. 231.29, m.p. 118-121°, MDL MFCD00065574 |  1g |
| | | 5g |
| | | 25g |
| L09111 | N-Boc-L-threonine, 98+% [<i>Boc-Thr-OH</i> , <i>N</i> -(tert-Butoxycarbonyl)-L-threonine] [2592-18-9], C ₈ H ₁₇ NO ₄ , F.W. 219.24, m.p. 77-81°, [α] _D ²⁰ -8.5° (c=1 in acetic acid), EINECS 219-987-6, BRN 2331474, MDL MFCD00065946 |  1g |
| | | 5g |
| H51965 | (R)-N-Boc-1,2,3,4-tetrahydroisoquinoline-3-carboxylic acid, 98% [<i>N</i> -Boc-D-Tic] [115962-35-1], C ₁₅ H ₁₉ NO ₄ , F.W. 277.32, MDL MFCD00143818 ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a |  1g |
| | | 5g |
| L09214 | N(α)-Boc-D-tryptophan, 97% [<i>Boc-D-Trp-OH</i> , <i>N</i> (α)-tert-Butoxycarbonyl-D-tryptophan] [5241-64-5], C ₁₆ H ₂₀ N ₂ O ₄ , F.W. 304.35, m.p. ca 138° dec., [α] _D ²⁰ +21° (c=1 in acetic acid), EINECS 226-042-1, BRN 4237334, MDL MFCD00037944 |  1g |
| | | 5g |
| A16023 | N(α)-Boc-L-tryptophan, 98+% [<i>Boc-Trp-OH</i> , <i>N</i> (α)-tert-Butoxycarbonyl-L-tryptophan] [13139-14-5], C ₁₆ H ₂₀ N ₂ O ₄ , F.W. 304.35, m.p. ca 138° dec., [α] _D ²⁰ -19.5° (c=1 in DMF), EINECS 236-072-7, BRN 39677, MDL MFCD00065595, † |  5g |
| | | 25g |
| A10810 | N-Boc-L-tyrosine, 98+% [<i>Boc-Tyr-OH</i> , <i>N</i> -(tert-Butoxycarbonyl)-L-tyrosine] [3978-80-1], C ₁₄ H ₁₉ NO ₄ , F.W. 281.31, m.p. 141° dec., [α] _D ²⁰ +37° (c=1 in dioxan), EINECS 223-613-7, BRN 2816406, MDL MFCD00037179 ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a |  1g |
| | | 5g |
| B22164 | N-Boc-L-tyrosine methyl ester, 99% [<i>N</i> -tert-Butoxycarbonyl-L-tyrosine methyl ester, <i>Boc-Tyr-OMe</i>] [4326-36-7], C ₁₅ H ₂₁ NO ₄ , F.W. 295.34, m.p. 105-108°, MDL MFCD00191181 |  5g |
| | | 25g |
| J64264 | Boc-Val-Ile[(S)-4-amino-2,2-difluoro-3-oxo-pentanoyl]-Val-Ile-OME [<i>N</i> -Boc-V-Ile[(S)-4-Amino-2,2-Difluoro-3-Oxo-Pentanoyl]-V-I-OMe] C ₃₃ H ₅₇ F ₂ N ₅ O ₈ , F.W. 705.83, Powder | 100g |
| L09193 | N-Boc-D-valine, 98+% [<i>Boc-D-Val-OH</i> , <i>N</i> -(tert-Butoxycarbonyl)-D-valine] [22838-58-0], C ₁₀ H ₁₉ NO ₄ , F.W. 217.27, m.p. 76-80°, [α] _D ²⁰ +6.3° (c=1 in acetic acid), BRN 2050408, MDL MFCD00038282 |  1g |
| | | 5g |
| A16007 | N-Boc-L-valine, 98+% [<i>Boc-L-Val-OH</i> , <i>N</i> -(tert-Butoxycarbonyl)-L-valine] [13734-41-3], C ₁₀ H ₁₉ NO ₄ , F.W. 217.27, m.p. 77-80°, [α] _D ²⁰ -7.5° (c=1 in acetic acid), EINECS 237-307-6, BRN 1711290, MDL MFCD00065605, † |  5g |
| | | 25g |
| J64508 | Bolton-Hunter Reagent [<i>N</i> -Succinimidyl-3-(4-hydroxyphenyl)propionate, <i>Rudinger reagent</i>] [34071-95-9], C ₁₇ H ₁₉ NO ₅ , F.W. 263.25, Powder, m.p. 132-133°, EINECS 251-818-1, BRN 1545011, MDL MFCD00005515 ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| | | 5g |
| J63514 | Bombesin [<i>Glp-Gln-Arg-Leu-Gly-Asn-Gln-Trp-Ala-Val-Gly-His-Leu-Met-NH2</i>] [31362-50-2], C ₇₁ H ₁₁₀ N ₂₀ O ₁₈ S, F.W. 1619.90, Powder, Merck 14,1329, RTECS BD3480000, MDL MFCD00167514 ⚠ H: H341, P: P281-P201-P202-P308+P313-P405-P501 | 1mg |
| | | 5mg |
| Application(s): Gut tetradecapeptide with the ability to stimulate release of various hormones | | |
| 3-BOPH HCl, see 1-(3-tert-Butoxyphenyl)homopiperazine monohydrochloride, H51752, p. 140 | | |
| 4-BOPH HCl, see 1-(4-tert-Butoxyphenyl)homopiperazine monohydrochloride, H51687, p. 141 | | |
| Boric acid, see Boric acid, 33253, p. 134 | | |
| J63742 | Borate, 0.5M buffer soln., pH 8.0 [1330-43-4], Liquid, † ⚠ H: H360FD, P: P281-P201-P202-P308+P313-P405-P501a | 250ml |
| | | 500ml |
| J60803 | Borate, 0.5M buffer soln., pH 8.5 [1330-43-4], Liquid, † ⚠ H: H360FD, P: P281-P201-P202-P308+P313-P405-P501a | 250ml |
| | | 500ml |









| Stock # | Description | Size |
|---|--|---------------------|
| J62125 | Borate, 0.5M buffer soln., pH 9.0 [1330-43-4], Liquid, †  H:H360FD, P:P281-P201-P202-P308+P313-P405-P501a | 250ml 500ml |
| J62154 | Borate, 0.5M buffer soln., pH 9.5 [1330-43-4], Liquid, †  H:H360, P:P281-P201-P202-P308+P313-P405-P501 | 500ml 1L |
| J60979 | Borate-buffered saline (5X) [1330-43-4], Liquid, Note: 125mM sodium borate, 750mM sodium chloride, pH 7.0, †  ! H:H360, P:P281-P201-P202-P308+P313-P405-P501 | 250ml 500ml |
| Borax , see Sodium tetraborate decahydrate, 40114, p. 349 | | |
| 33253 | Boric acid, ACS, 99.5% min [<i>Boracic acid, Orthoboric acid</i>] [10043-35-3], H ₃ BO ₃ , F.W. 61.83, Granular, m.p. ca 185° dec., f.p. None, d. 1.435, Merck 14 , 1336, Fieser 1,63 2,32 3,29 4,41 5,48 9,59 11,70, Solubility: Soluble in water (1 gram in 18ml cold or 4ml boiling water). Solubility in water is increased by addition of HCl, citric or tartaric acid, EINECS 233-139-2, RTECS ED4550000, BRN 1697939, MDL MFCD00011337, † Maximum level of impurities: Insoluble in methanol 0.005%, Nonvolatile with methanol 0.5%, Cl 0.001%, PO ₄ 0.001%, SO ₄ 0.01%, Ca 0.005%, Heavy Metals (as Pb) 0.001%, Fe 0.001%  H:H360FD, P:P201-P308+P313 | 500g 2kg |
| Application(s): In hardening steel, preservatives, manufacturing of cements, porcelain, enamels, glass, borates, artificial gems, in nickeling baths, painting, photography | | |
| A16624 | Boric acid, 98% [<i>Boracic acid, Orthoboric acid</i>] [10043-35-3], H ₃ BO ₃ , F.W. 61.83, m.p. ca 185° dec., f.p. None, d. 1.435, Merck 14 , 1336, Fieser 1,63 2,32 3,29 4,41 5,48 9,59 11,70, EINECS 233-139-2, RTECS ED4550000, BRN 1697939, MDL MFCD00011337, †  H:H360FD, P:P201-P308+P313 | 1kg 5kg |
| DL-2-Bornanone, see (±)-Camphor, A10936, p. 144 L-2-Bornanone, see (1S)-(-)-Camphor, B23469, p. 144 | | |
| J60378 | Bortezomib, 99% [<i>MG-341</i>] [179324-69-7], C ₁₉ H ₂₅ BN ₂ O ₄ , F.W. 384.24, Powder, m.p. 139-143°, Merck 14 , 1351, UN3249, RTECS ED7771666  H:H301-H311-H330-H372, P:P301+P310-P304+P340-P320-P330-P361-P405-P501a | 5mg 10mg 25mg |
| Application(s): A potent, highly selective and reversible inhibitor of the 20S proteasome | | |
| J62631 | Bovine Gamma Globulin, 1mg/ml [9007-83-4], Liquid | 25ml 50ml |
| J64417 | Bovine Pituitary Extract [<i>BPE</i>] Note: Receptor Grade. Suitable for cell culture. Supplied partially purified as an aseptically lyophilized powder. | 50mg 10x50mg |
| J60205 | Bovine Serum Albumin, 1mg/ml [9048-46-8], Liquid, EINECS 232-936-2, † | 25ml 50ml |
| 4-BPHP 2HCl, see 1-(4-tert-Butylphenyl)homopiperazine dihydrochloride, H51702, p. 141 | | |
| J61522 | Bradford Dye Reagent, ready to use Liquid, UN1760  H:H314-H318-H371, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 500ml 1L |
| J63131 | Bradykinin [<i>Arg-Pro-Pro-Gly-Phe-Ser-Pro-Phe-Arg-OH, BK</i>] [58-82-2], C ₅₀ H ₇₃ N ₁₅ O ₁₁ , F.W. 1060.23, Powder, Merck 14 , 1359, EINECS 200-398-8, RTECS EE1530000 Application(s): An endogenous vasodilator peptide | 10mg |
| J61719 | Bradykinin (1-3) [<i>H-Arg-Pro-Pro-OH</i>] C ₁₈ H ₂₈ N ₆ O ₄ , F.W. 368.40, Powder Application(s): Biologically active fragment of bradykinin | 5mg |
| J63233 | Bradykinin (1-5) [<i>H-Arg-Pro-Pro-Gly-Phe-OH</i>] C ₂₇ H ₄₀ N ₈ O ₆ , F.W. 572.67, Powder, MDL MFCD00076260 Application(s): Biologically active fragment of bradykinin | 5mg 25mg |
| J60345 | Bradykinin acetate salt [<i>Arg-Pro-Pro-Gly-Phe-Ser-Pro-Phe-Arg-OH</i>] [6846-03-3], C ₅₀ H ₇₃ N ₁₅ O ₁₁ ·C ₂ H ₄ O ₂ , F.W. 1120.21, Powder, MDL MFCD06763566 | 25mg 100mg |






| Stock # | Description | Size |
|---|---|----------------------|
| J61171 | Lys-Bradykinin acetate salt [Kallidin, Lys-Arg-Pro-Pro-Gly-Phe-Ser-Pro-Phe-Arg] [342-10-9], C ₅₆ H ₈₅ N ₁₇ O ₁₂ , F.W. 1188.40, Powder, Merck 14,5278, EINECS 206-438-0 | 5mg 25mg |
| Application(s): Endogenous bradykinin receptor agonist | | |
| J61532 | Met-Lys-Bradykinin [Met-Lys-Arg-Pro-Pro-Gly-Phe-Ser-Pro-Phe-Arg] [550-19-6], C ₆₁ H ₈₄ N ₁₈ O ₁₃ S ₁ , F.W. 1319.60, Powder | 5mg 25mg |
| J65458 | Brain Derived Acidic Fibroblast Growth Factor (102-111) [His-Ala-Glu-Lys-His-Trp-Phe-Val-Gly-Leu] C ₅₈ H ₈₂ N ₁₆ O ₁₃ , F.W. 1223.38, Solid | 1mg |
| J64990 | Brassinin [Methyl ((1H-indol-3-yl)methyl)carbamodithioate] [105748-59-2], C ₁₁ H ₁₂ N ₂ S ₂ , F.W. 236.36, Powder, m.p. 142-144° | 100mg |
| J62340 | Brefeldin A, 99% [20350-15-6], C ₁₈ H ₂₄ O ₄ , F.W. 280.36, Crystalline powder, m.p. 201-205°, Merck 14,1369, RTECS GY8410000, BRN 25191, MDL MFCD00083258 ! H:302, P:264-P270-P301+P312-P330-P501a | 10mg 25mg 50mg |
| Application(s): Inhibits protein transport from the endoplasmic reticulum to Golgi apparatus. Brefeldin A mediated apoptosis has been observed in human tumor cells | | |
| Brij® 35, see Brij® L23, A15809, p. 135 | | |
| A15809 | Brij® L23 [Brij® 35, Tricosaethylene glycol mono-n-dodecyl ether] [9002-92-0], C ₂₅ H ₄₈ (CH ₂) ₁₀ CH ₂ (OCH ₂ CH ₂) ₂₃ OH, F.W. 1199.57, m.p. ca 35-40°, EINECS 500-002-6, RTECS JR5990000, MDL MFCD00080891, † ! H:302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250g 1kg 5kg |
| Non-ionic surfactant. Detergent for ion chromatography. Solubilizing agent for membrane proteins. | | |
| Application(s): For use in Stein-Moore chromatography | | |
| 43318 | Brilliant Blue G, ultrapure [Coomassie Brilliant Blue G 250, C.I. 42655] [6104-58-1], C ₄₇ H ₄₈ N ₃ NaO ₇ S ₂ , F.W. 854.04, Powder, EINECS 228-058-4, MDL MFCD00078482, Note: E(m) (595nm, H ₂ O) >36,300, † | 2g 10g 50g |
| Application(s): Protein staining following gel electrophoresis | | |
| J63797 | Brilliant Blue G soln., Ready-to-Use [Coomassie Brilliant Blue G, C.I. 42655] [6104-58-1], C ₄₇ H ₄₈ N ₃ NaO ₇ S ₂ , F.W. 854.04, Liquid, UN1992, EINECS 228-058-4, BRN 5230822, Note: This solution contains 30% methanol, 5% acetic acid, 0.2% Brilliant Blue G., † ☠ ☢ ☣ ☤ H:311-H331-H370-H226, P:P210-P241-P303+P361+P353-P361-P405-P501a | 500ml 1L |
| J64297 | Brilliant Blue R [Coomassie Brilliant Blue R, C.I. 42660] [6104-59-2], C ₄₈ H ₄₄ N ₃ NaO ₇ S ₂ , F.W. 825.97, Crystalline powder, EINECS 228-060-5, BRN 5718025, MDL MFCD00041762, † | 50g |
| J61384 | Brilliant Blue R soln., Ready-to-Use [Coomassie Brilliant Blue R, C.I. 42660] [6104-59-2], C ₄₈ H ₄₄ N ₃ NaO ₇ S ₂ , F.W. 825.97, Liquid, UN1992, EINECS 228-060-5, BRN 5718025, † ☠ ☢ ☣ ☤ H:311-H331-H370-H226, P:P210-P241-P303+P361+P353-P361-P405-P501a | 500ml 1L |
| A12801 | Brilliant Green [Basic Green 1, C.I. 42040] [633-03-4], C ₂₇ H ₃₄ N ₂ O ₃ S, F.W. 482.65, m.p. 210° dec., Merck 14,1374, EINECS 211-190-1, RTECS BP6825000, BRN 3901207, MDL MFCD00011880, † ! H:302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 25g 100g |
|  | | |
| J63451 | Bromhexine hydrochloride, 98+% [Auxit] [611-75-6], C ₁₄ H ₁₈ BrN ₂ ·HCl, F.W. 412.60, Powder, m.p. 240-244°, Merck 14,1391, EINECS 210-280-8, RTECS XS9950000, BRN 4848376, MDL MFCD00056626 | 100g 500g |
| Application(s): A mucolytic agent | | |
| J65582 | 8-Bromoadenine [6-Amino-8-bromopurine] [6974-78-3], C ₅ H ₄ BrN ₆ , F.W. 214.03, Powder, m.p. >250°, EINECS 230-225-1, RTECS UO7410000, MDL MFCD00082518 | 100mg 500mg 1g |





| Stock # | Description | Size |
|---------|--|---------------------------|
| L03544 | 8-Bromoadenosine, 98% \triangle [2946-39-6], C ₁₀ H ₁₂ BrN ₆ O ₄ , F.W. 346.15, m.p. ca 211° dec., [α] _D ²⁰ -33° (c=1 in 1N HCl), EINECS 220-959-0, BRN 627737, MDL MFCD00005733 Adenosine binding inhibitor. | 250mg 1g |
| |  | |
| J64469 | 8-Bromoadenosine-3',5'-cyclic monophosphate ■ [8-Br-cAMP] [23583-48-4], C ₁₀ H ₁₁ BrN ₆ O ₈ P, F.W. 408.11, Powder, m.p. 254°, EINECS 245-760-6, MDL MFCD00075580 | 50mg 100mg 250mg |
| B25681 | 3-Bromobenzenesulfonamide, 97% [89599-01-9], C ₆ H ₄ BrNO ₂ S, F.W. 236.09, m.p. 154-158°, MDL MFCD00084903 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 1g 5g |
| |  | |
| J60151 | 5-Bromo-4-chloro-3-indolyl-α-D-galactoside [X-α-Gal] [107021-38-5], C ₁₄ H ₁₅ BrClNO ₆ , F.W. 408.63, Powder, MDL MFCD00063780 ! H:H302-H332, P:P261-P264-P304+P340-P301+P312-P312-P501a | 250mg 1g |
| | Application(s): Substrate for β-galactosidase | |
| B21034 | 5-Bromo-4-chloro-3-indolyl-β-D-galactopyranoside, 98+% ▲▲ [X-gal] [7240-90-6], C ₁₄ H ₁₅ BrClNO ₆ , F.W. 408.64, m.p. ca 236° dec., [α] _D ²⁰ -60° (c=1 in 50% DMF), EINECS 230-640-8, BRN 1402009, MDL MFCD00005666 | 10mg 50mg 250mg |
| | Application(s): Substrate for β-galactosidase | |
| |  | |
| J65677 | 5-Bromo-4-chloro-3-indolyl β-D-glucoside, 99% [5-Bromo-4-chloro-3-indolyl β-D-glucopyranoside, X-Glucoside] [15548-60-4], C ₁₄ H ₁₅ BrClNO ₆ , F.W. 408.63, Powder, EINECS 239-603-0, BRN 1552603, MDL MFCD00063690 | 500mg 1g 5g |
| J64360 | 5-Bromo-4-chloro-3-indolyl β-D-glucuronide sodium salt, 99% ▲ [BC-Indicator, X-Glucuronide] [129541-41-9], C ₁₄ H ₁₂ BrClNNaO ₇ , F.W. 444.59, Powder, MDL MFCD00135782 | 250mg 1g |
| J64451 | 5-Bromo-4-chloro-3-indolyl phosphate disodium salt, 98% ▲▲ [X-Phosphate disodium salt] [102185-33-1], C ₈ H ₄ BrClNNa ₂ O ₄ P, F.W. 370.43, Powder, MDL MFCD00036757 | 250mg 1g |
| J65225 | Bromocresol Green, ACS [76-60-8], C ₂₁ H ₁₄ Br ₂ O ₅ S, F.W. 698.04, Powder, m.p. 225° dec., Merck 14,1386, EINECS 200-972-8, BRN 372527, MDL MFCD00005874, † | 5g 25g |
| 38696 | Bromocresol Green sodium salt, 0.04% w/v aq. soln. [Bromocresol Green, water soluble] [62625-32-5], C ₂₁ H ₁₃ Br ₂ NaO ₅ S, F.W. 720.01, Liquid, MDL MFCD00148898, Note: Transition interval: pH 3.8 (yellow) to pH 5.4 (blue), † | 100ml 500ml |
| J64284 | Bromocresol Green sodium salt, ACS [Bromocresol Green, water soluble] [62625-32-5], C ₂₁ H ₁₃ Br ₂ NaO ₅ S, F.W. 720.02, Crystalline powder, m.p. 230° dec., Merck 14,1386, EINECS 263-657-4, MDL MFCD00148898, † | 5g 25g |
| 38700 | Bromocresol Purple sodium salt, 0.04% w/v aq. soln. [Bromocresol Purple, water soluble] [62625-30-3], C ₂₁ H ₁₅ Br ₂ NaO ₅ S, F.W. 562.22, Liquid, MDL MFCD00148896, Note: Transition interval: pH 5.2 (yellow-green) to pH 6.8 (purple), † | 100ml 500ml 6x100ml |
| J65357 | 8-Bromo-2'-deoxyadenosine, 99% [8-Bromo-2'-deoxy-D-adenosine] [14985-44-5], C ₁₀ H ₁₃ FN ₆ O ₃ , F.W. 284.25, Powder, MDL MFCD01630970 ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| J65456 | 5-Bromo-2'-deoxycytidine, 99% [1022-79-3], C ₉ H ₁₁ BrN ₃ O ₃ , F.W. 307.10, Powder, EINECS 213-824-2, RTECS HA3705000, MDL MFCD00047496 | 1g |
| J64723 | 8-Bromo-2'-deoxyguanosine, 99% [13389-03-2], C ₁₀ H ₁₂ BrN ₅ O ₄ , F.W. 346.14, Powder ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |






| Stock # | Description | Size |
|--|---|---------------------------|
| J64704 | 2'-Bromo-2'-deoxyuridine, 98% [72218-68-9], C ₉ H ₁₁ BrN ₂ O ₅ , F.W. 307.10, Powder | 500mg |
| J64219 | 5-Bromo-2'-deoxyuridine-5'-monophosphate sodium salt, 98% [5-BrdUMP] [51432-32-7], C ₉ H ₁₂ BrNNa ₂ O ₈ P, F.W. 419.05, Powder, MDL MFCD00057406 ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| Bromoenoilactone , see Haloenoil Lactone Suicide Substrate, 98+%, J63728, p. 240 Bromofluorescein , see Eosin Yellowish, B24535, p. 208 | | |
| H54587 | 4-Bromo-7-fluoroindole, 95% [883500-66-1], C ₈ H ₅ BrFN, F.W. 214.04 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250mg 1g 5g |
| H51978 | 4-Bromo-N-Fmoc-L-phenylalanine, 95% [Fmoc-Phe(4-Br)-OH] [198561-04-5], C ₂₄ H ₂₀ BrNO ₄ , F.W. 466.33, m.p. 165-168°, MDL MFCD00273460 | 250mg 1g 5g |
| J63940 | 8-Bromoguanosine [2-Amino-8-bromo-6-hydroxypurine riboside] [4016-63-1], C ₁₀ H ₁₂ BrN ₅ O ₅ , F.W. 362.14, Powder, EINECS 223-677-6, MDL MFCD00037985 | 5g |
| L02992 | 8-Bromoguanosine hydrate, 97% [332359-99-6], C ₁₀ H ₁₂ BrN ₅ O ₅ ·xH ₂ O, F.W. 362.14(anhy), m.p. >300°, [α] _D ²⁰ -30° (c=2 in DMSO/water, 1:1), EINECS 223-677-6, BRN 578725, MDL MFCD00150531 | 1g 5g 25g |
| (R)-4-Bromo-3-hydroxybutyric acid ethyl ester , see Ethyl (R)-4-bromo-3-hydroxybutyrate, J60862, p. 214 (S)-4-Bromo-3-hydroxybutyric acid ethyl ester , see Ethyl (S)-4-bromo-3-hydroxybutyrate, J62782, p. 214 | | |
| J65978 | 5-Bromo-3-indolyl β-D-galactopyranoside, 98+% [Bluo-Gal] [97753-82-7], C ₁₄ H ₁₆ BrNO ₆ , F.W. 374.18, Powder, MDL MFCD00063691 | 100mg 1g |
| Application(s): α-Galactosidase substrate for Lac-gene detection systems | | |
| J64131 | 3-Bromo-3-methyl-2-(2-nitrophenylthio)-3H-indole , see BNPS-Skatole, J61050, p. 196 6-Bromo-2-naphthyl β-D-glucopyranoside [Br-Nap-β-D-Glc] [15548-61-5], C ₁₈ H ₁₇ BrO ₆ , F.W. 385.12, Powder, EINECS 239-604-6, MDL MFCD00063007 | 1g 5g |
| Application(s): Chromogenic substrate for β-glucosidase | | |
| J65443 | 5-Bromonicotinic acid 10-methoxy-1,6-dimethylergoline-8-methyl ester , see Nicergoline, J63295, p. 301 5-Bromo-5-nitro-1,3-dioxane, 98% [30007-47-7], C ₆ H ₈ BrNO ₄ , F.W. 212.00, Powder, m.p. 58-61°, EINECS 250-001-7, RTECS JG9650000, MDL MFCD00101855, † ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5g 25g |
| Application(s): Reactive against both gram-positive and gram-negative bacteria. Less toxic than sodium azide | | |
| J63480 | Bromo-7-nitroindazole, 98+% [74209-34-0], C ₇ H ₄ BrN ₃ O ₂ , F.W. 242.00, Powder, MDL MFCD00159910 | 5mg 25mg 50mg |
| Application(s): Inhibitor of nitric oxide synthase (NOS) | | |
| 32641 | Bromophenol Blue, ACS [115-39-9], C ₁₃ H ₁₀ Br ₂ O ₃ S, F.W. 669.98, Crystalline, m.p. 270° dec., Merck 14,1444, Solubility: Freely soluble in NaOH, EINECS 204-086-2, RTECS SJ7453000, BRN 61698, MDL MFCD00005875, † Specifications: Clarity of solution P.T., Visual transition interval pH 3.0 (yellow) to pH 4.6 (blue) | 1g 5g 25g |
| A16899 | Bromophenol Blue sodium salt [Bromophenol Blue, water soluble] [34725-61-6], C ₁₃ H ₉ Br ₂ NaO ₃ S, F.W. 691.96, m.p. >300°, Merck 14,1444, EINECS 252-170-2, MDL MFCD00013793, † Acid-base indicator: pH 3.0 - 4.6 | 10g 50g |
| Application(s): Tracking dye for alkaline and neutral buffer systems, for nucleic acid staining | | |
| 38693 | Bromophenol Blue sodium salt, 0.04% w/v aq. soln. [34725-61-6], C ₁₃ H ₉ Br ₂ NaO ₃ S, F.W. 691.96, Liquid, Merck 14,1444, MDL MFCD00013793, Note: Transition interval: pH 3.0 (yellow) to pH 4.6 (blue), † | 100ml 500ml 6x100ml |
| Bromophenol Blue, water soluble , see Bromophenol Blue sodium salt, A16899, p. 137 | | |





| Stock # | Description | Size |
|---------|---|--|
| A15922 | N-Bromosuccinimide, 99% ▲ [NBS] [128-08-5], C ₄ H ₅ BrNO ₂ , F.W. 177.99, m.p. 175-180° dec., d. 2.098, Merck 14,1438 , Fieser 1,78 12,79 13,49 14,57 15,50 16,49 18,65 19,50 20,58 21,72 , UN3261, EINECS 204-877-2, BRN 113916, MDL MFCD00005510, †  | 250g 1kg 5kg |
| | <p>  Source of free-radical or positive bromine. For examples of radical benzylic bromination (Wohl-Ziegler), see: <i>Org. Synth. Coll.</i>, 4, 921 (1963); 5, 145, 329, 825 (1973). The use of the ozone depleting solvent CCl₄ has been avoided by the use of the ionic liquid 1-n-Butyl-3-methylimidazolium hexafluorophosphate, L19086: <i>Synlett</i>, 702 (2003). Cleavage of carbohydrate benzyl ethers: <i>J. Org. Chem.</i>, 55, 378 (1990), and of benzyl esters: <i>Synlett</i>, 219 (1994), occur under mild conditions; the benzyl group is converted to benzaldehyde. For allylic bromination, see e.g.: <i>Org. Synth. Coll.</i>, 4, 108 (1963); 9, 112, 191 (1998) review: <i>Chem. Rev.</i>, 43, 271 (1948). For free-radical α-bromination of a Boc glycine ester, see: <i>Org. Synth. Coll.</i>, 9, 526 (1998). Both aliphatic and aromatic aldehydes are converted to acyl bromides under free-radical conditions: <i>Tetrahedron Lett.</i>, 3809 (1979); <i>Synlett</i>, 347 (1990); <i>Tetrahedron Lett.</i>, 31, 7237 (1990). In acetonitrile, NBS is a mild and regioselective nuclear brominating agent for activated aromatics such as methoxybenzenes and naphthalenes: <i>J. Org. Chem.</i>, 60, 5328 (1995). Deactivated aromatics, e.g. nitroarenes and benzotrifluorides, can be <i>m</i>-brominated under mild conditions in good yield with NBS in TFA, in the presence of H₂SO₄: <i>Synlett</i>, 1245 (1999). In the presence of a phosphine or phosphite, converts alcohols to alkyl bromides with inversion: <i>Tetrahedron Lett.</i>, 3937 (1973). For a review of this and related reactions, see: <i>Org. React.</i>, 29, 1 (1983). Alkenes undergo <i>trans</i>-addition reactions with NBS in combination with a nucleophile. For examples, see: <i>Org. Synth. Coll.</i>, 6, 184, 560 (1988). With alcohols, bromohydrin ethers are formed. For use in the synthesis of cyclopropenone, see: <i>Org. Synth. Coll.</i>, 6, 361 (1988):  </p> | |
| | <p> In the presence of DBU in MeOH, amides rearrange to amines in good yields, providing a mild and efficient alternative to the classical Hofmann halogen/ caustic alkali conditions: <i>J. Org. Chem.</i>, 62, 7495 (1997). Examples of the use of NBS as a mild, selective oxidizing agent: Sulfides to sulfoxides: <i>J. Org. Chem.</i>, 37, 3976 (1968). Oximes to nitrile oxides: <i>J. Org. Chem.</i>, 37, 436 (1968). Secondary alcohol in the presence of primary: <i>Tetrahedron Lett.</i>, 2745 (1979). (In DMSO): Alkynes to α-diketones: <i>Can. J. Chem.</i>, 49, 1099 (1979). (Free radical): Aldehydes to acyl bromides or amides: <i>Tetrahedron Lett.</i>, 31, 7237 (1990). Benzyl silyl ethers to aldehydes: <i>Synlett</i>, 345 (1990). Aldehydes to esters: <i>Synlett</i>, 347 (1990). For use as a mild catalyst in acetalization reactions, see Triethyl orthoformate, A13587. For a brief feature on uses in synthesis, see: <i>Synlett</i>, 498 (2006). See also 1,3-Dibromo-5,5-dimethylhydantoin, A15510. </p> | |
| | <p>Application(s): Allylic bromination reagent. Cleaves peptides at tryptophyl residues</p> | |
| 38701 | Bromothymol Blue sodium salt, 0.04% w/v aq. soln. [34722-90-2], C ₂₇ H ₂₇ Br ₂ NaO ₃ S, F.W. 646.38, Liquid, MDL MFCD00077263, Note: Transition interval: pH 6.0 (yellow) to pH 7.6 (blue), † | 100ml 500ml 6x100ml |
| A14799 | 5-Bromouracil, 98+% [51-20-7], C ₄ H ₃ BrN ₂ O ₂ , F.W. 190.99, m.p. ca 310° dec., Merck 14,1440 , EINECS 200-084-0, RTECS YQ9060000, BRN 127176, MDL MFCD00006017, †  | 5g 25g 100g |
| A18507 | 5-Bromouridine, 98% [957-75-5], C ₉ H ₁₁ BrN ₂ O ₆ , F.W. 323.10, m.p. 191-193°, EINECS 213-486-6, MDL MFCD00006528  | 250mg |
| J63922 | Brompheniramine [86-22-6], C ₁₆ H ₁₈ BrN ₂ , F.W. 319.24, Powder, Merck 14,1443 , EINECS 201-657-8, † | 10mg 25mg 100mg |
| | <p>Application(s): An antihistamine and also an inhibitor of serotonin reuptake</p> | |
| J61178 | Brucine [10,11-Dimethoxystrychnine] [357-57-3], C ₂₃ H ₂₈ N ₂ O ₄ , F.W. 394.47, Powder, m.p. 175-178° dec., Merck 14,1455 , UN1570, EINECS 206-614-7, RTECS EH8925000, BRN 63046, MDL MFCD00005942, †  | 5g 25g 100g |
| A16251 | Brucine dihydrate, 98% [5892-11-5], C ₂₃ H ₂₈ N ₂ O ₄ ·2H ₂ O, F.W. 430.50 (394.47anhy), m.p. 176-178°, UN1570, MDL MFCD00149384, †  | 10g 50g |
| | <p>  Resolving agent for chiral acids. Application(s): Resolving agent </p> | |

| Stock # | Description | Size |
|---------|---|------------------------------|
| 36249 | Brucine sulfate heptahydrate, ACS [60583-39-3], (C ₂₈ H ₂₆ N ₂ O ₄) ₂ ·H ₂ SO ₄ ·7H ₂ O, F.W. 1013.15 (887.03anhy). Powder, m.p. 180° dec., Merck 14,1455, UN2811, EINECS 225-432-9, MDL MFCD00150159, † Maximum level of impurities: Clarity of solution P.T., Loss on drying at 105° 13.0%, Residue after ignition 0.1%, Sensitivity to nitrate P.T.   H:H300-H330-H412, P:P301+P310-P304+P340-P320-P330-P405-P501a | 25g |
| | Application(s): Resolving agent | |
| | Bryamycin , see Thiostrepton, Streptomyces laurentii, 98%, J62332, p. 368 | |
| J63848 | Bryostatin 1 [83314-01-6], C ₄₇ H ₆₆ O ₁₇ , F.W. 905.03, Solid, m.p. 230-235°, Merck 14,1457, RTECS EH9455000, MDL MFCD00893832 | 10micrograms 25micrograms |
| | Application(s): Binds to and activates protein kinase C | |
| J61551 | Bryostatin 2 [NSC 339554] [87745-28-6], C ₄₅ H ₆₆ O ₁₆ , F.W. 863.00, Solid | 10micrograms 25micrograms |
| | Application(s): A macrocyclic lactone with anti-tumor properties. Binds to and activates protein kinase C | |
| | Butylated hydroxytoluene , see 2,6-Di-tert-butyl-4-methylphenol, A16863, p. 185 BSA , see N,O-Bis(trimethylsilyl)acetamide, L00183, p. 127 | |
| J61655 | BSA blocking buffer, 3% in PBS Liquid, Note: 3% Bovine serum albumin in PBS, pH 7.4, † | 250ml 500ml |
| J60473 | BSA blocking buffer, 3% in PBS, with 0.02% sodium azide Liquid, Note: 3% Bovine serum albumin in PBS with 0.02% sodium azide, † | 250ml 500ml |
| J61116 | BSA blocking buffer, 3% in PBS, with 0.05% Tween-20 Liquid, Note: 3% Bovine serum albumin in PBS, with 0.05% Tween 20, pH 7.4, † | 250ml 500ml |
| J61119 | BSA blocking buffer, 3% in TBS Liquid, Note: 3% Bovine serum albumin in Tris-buffered saline, pH 7.4, †  H:H360, P:P281-P201-P202-P308+P313-P405-P501 | 250ml 500ml |
| J62554 | BSA blocking buffer, 3% in TBS, with 0.05% Tween-20 Liquid, Note: 3% Bovine serum album in TBS, with 0.05% Tween 20, pH 7.4, † | 250ml 500ml |
| J61089 | BSA blocking buffer, 5% in PBS Liquid, Note: 5% Bovine serum albumin in Phosphate-buffered saline, pH 7.4, † | 250ml 500ml |
| J63711 | BSA blocking buffer, 5% in PBS, with 0.05% Tween-20 Liquid, Note: 5% Bovine serum albumin in phosphate-buffered saline, 0.05% Tween-20, pH 7.4, † | 250ml 500ml |
| J62637 | BSA blocking buffer, 5% in TBS Liquid, Note: 5% Bovine serum albumin in Tris-buffered saline, pH 7.4, † | 250ml 500ml |
| J62305 | BSA blocking buffer, 5% in TBS, with 0.02% sodium azide Liquid, Note: 5% Bovine serum albumin in TBS, with 0.02% azide, pH 7.4, †  H:H360, P:P281-P201-P202-P308+P313-P405-P501 | 250ml 500ml |
| J60098 | BSA blocking buffer, 5% in TBS, with 0.05% Tween-20 Liquid, Note: 5% Bovine serum albumin in Tris-buffered saline, 0.05% Tween-20, pH 7.4, † | 250ml 500ml |
| | BTC , see Blue Tetrazolium chloride, A12502, p. 129 | |
| J60655 | Buccalin [Buccalin A, Gly-Met-Asp-Ser-Leu-Ala-Phe-Ser-Gly-Gly-Leu-NH2] [116844-51-0], C ₄₅ H ₇₂ N ₁₂ O ₁₅ S ₁ , F.W. 1053.50, Powder | 1mg 5mg |
| | Application(s): A modulatory neuropeptide involved in regulation of acetylcholine release | |
| | Buccalin A , see Buccalin, J60655, p. 139 | |
| J62302 | Bumetanide, 98+% [3-(Aminosulfonyl)-5-(butylamino)-4-phenoxybenzoic acid] [28395-03-1], C ₁₇ H ₂₀ N ₂ O ₅ S, F.W. 364.40, Solid, m.p. 230-231°, Merck 14,1484, EINECS 249-004-6, RTECS DG4910000, MDL MFCD00078949 | 1g 5g |
| | Application(s): Inhibitor of the sodium-potassium-chloride cotransporter | |
| J62742 | Bupivacaine [38396-39-3], C ₁₈ H ₂₈ N ₂ O, F.W. 288.43, Crystalline powder, m.p. 106-110°, UN2811, EINECS 253-911-2, †  H:H300-H310-H330, P:P301+P310-P304+P340-P320-P330-P361-P405-P501a | 1g 5g 25g |
| | Application(s): Sodium channel blocker | |






| Stock # | Description | Size |
|---------|---|-----------------------|
| J62835 | Bupivacaine hydrochloride, 98+% [Marcaïne, Carbostesin] [18010-40-7], C ₂₀ H ₂₈ N ₂ O·HCl, F.W. 324.89, White powder, m.p. 255-259°, Merck 14,1495, UN2811, EINECS 241-917-8, RTECS TK6125000, MDL MFCD00078956 | 1g 5g 25g |
| |  H: H300+H310+H330, P: P301+P310+P304+P340+P320+P330+P361+P405+P501 | |
| | Application(s): Inhibits TREK-1 channels and depolarizes the cell membrane | |
| J61105 | Bupropion hydrochloride, 99% [1-(3-Chlorophenyl)-2-((1,1-dimethylethyl)amino)-1-propanone hydrochloride] [31677-93-7], C ₁₅ H ₁₈ ClNO·HCl, F.W. 276.20, Powder, m.p. 233-234°, Merck 14,1499, EINECS 250-759-9, RTECS UG8858000, MDL MFCD00055209 | 1g 5g |
| |  H: H302, P: P264+P270+P301+P312+P330+P501 | |
| | Application(s): A selective inhibitor of dopamine uptake | |
| J60476 | Buspirone hydrochloride [33386-08-2], C ₁₈ H ₂₁ N ₂ O ₂ ·HCl, F.W. 421.96, White to off-white powder, Merck 14,1504, UN2811, EINECS 251-489-4, RTECS CL9915000, MDL MFCD00078569 | 1g 5g 25g |
| |  H: H301+H315+H319+H335, P: P301+P310+P305+P351+P338+P302+P352+P321+P405+P501 | |
| | Application(s): A 5-HT-1A serotonin receptor agonist. Affects dopaminergic, serotonergic and noradrenergic pathways | |
| J61348 | Busulfan, 98% [1,4-Butanediol dimethanesulfonate] [55-98-1], CH ₃ SO ₂ O(CH ₂) ₂ OSO ₂ CH ₃ , F.W. 246.29, Crystalline powder, Merck 14,1505, UN2811, EINECS 200-250-2, RTECS EK1750000, BRN 1791786, MDL MFCD00007562 | 5g 25g 100g |
| |  H: H300+H310+H330+H350, P: P301+P310+P304+P340+P320+P330+P361+P405+P501 | |
| | Application(s): A cell cycle non-specific alkylating antineoplastic agent 1,4-Butanediamine , see 1,4-Diaminobutane, B21316, p. 182 1,4-Butanediamine dihydrochloride , see 1,4-Diaminobutane dihydrochloride, A18312, p. 182 1,4-Butanedicarbonyl chloride , see Adipoyl chloride, A13168, p. 80 Butane-1,4-dicarboxylic acid , see Adipic acid, A13705, p. 79 Butanedioic acid , see Succinic acid, 33272, p. 353 Butanedioic anhydride , see Succinic anhydride, A12245, p. 354 1,4-Butanediol dimethanesulfonate , see Busulfan, 98%, J61348, p. 140 | |
| A14339 | 2,3-Butanedione monoxime, 99% ■ [Diacetyl monoxime] [57-71-6], C ₄ H ₇ NO ₂ , F.W. 101.11, m.p. 74-77°, b.p. 185-186°, EINECS 200-348-5, RTECS EK3150000, BRN 605582, MDL MFCD00002116, † Reagent for colorimetric determination of urea: <i>Anal. Biochem.</i> , 97 , 421 (1979). Reagent for Co, Ni, Pd and Re: <i>Talanta</i> , 26 , 425 (1979). Formation of the silyl enol ether (1-aza-3-siloxy-1,3-butadiene), followed by hetero Diels-Alder reaction with Dimethyl acetylenedicarboxylate , A11437 , affords a highly-functionalized pyridine: <i>Tetrahedron</i> , 62 , 5454 (2006). | 100g 500g 2.5kg |
| | Application(s): For determination of urea | |
| | Butanimide , see Succinimide, A13503, p. 354 | |
| L13983 | (R)-(-)-2-Butanol, 98+% [(R)-(-)- <i>sec</i> -Butyl alcohol] [14898-79-4], C ₄ H ₁₀ O, F.W. 74.12, b.p. 99-100°, f.p. 26°(79°F), d. 0.806, n _D ²⁰ 1.3980, [α] _D ²⁰ -15° (c=10 in methanol), Merck 14,1541, UN1120, EINECS 238-967-8, BRN 1718764, MDL MFCD00064280, † | 1g 5g |
| |  H: H226+H319+H335+H336, P: P262+P233+P301+P310+P305+P351+P338+P315+P403 | |
| | Application(s): For synthesis of optically active products | |
| L14164 | (S)-(+)-2-Butanol, 98+% [(S)-(+)- <i>sec</i> -Butyl alcohol] [4221-99-2], C ₄ H ₁₀ O, F.W. 74.12, b.p. 99-100°, f.p. 26°(79°F), d. 0.806, n _D ²⁰ 1.3980, [α] _D ²⁰ +13.5° (c=10 in methanol), Merck 14,1541, UN1120, EINECS 224-168-1, BRN 1718763, MDL MFCD00064281 | 1g 5g |
| |  H: H226+H319+H335+H336, P: P262+P233+P301+P310+P305+P351+P338+P315+P403 | |
| | Application(s): For synthesis of optically active products cis-2-Butenedioic acid , see Maleic acid, A14596, p. 275 trans-2-Butenedioic acid , see Fumaric acid, A10976, p. 228 cis-Butenedioic anhydride , see Maleic anhydride, A12178, p. 275 N-tert-Butoxycarbonyl products , see Boc, B22706, p. 129 1-tert-Butoxycarbonyl-(2S,4R)-4-hydroxypyrrolidine-2-carboxylic acid , see N-Boc-trans-4-hydroxy-L-proline, H27110, p. 131 N-tert-Butoxycarbonyl-L-leucine , see N-Boc-L-tert-leucine, H51136, p. 133 2-Butoxy-N-(2-diethylaminoethyl)-4-quinolinecarboxamide hydrochloride , see Dibucaine hydrochloride, J62804, p. 184 | |
| H51752 | 1-(3-tert-Butoxyphenyl)homopiperazine monohydrochloride, 98% [3-BOPH·HCl] [934992-04-8], C ₁₅ H ₂₄ N ₂ O·HCl, F.W. 284.83, m.p. 143-147°, MDL MFCD16172200, Note: Sold in collaboration with Tosoh Organic Chemical Co., Ltd. | 500mg |
| |  | |

| Stock # | Description | Size |
|---------|--|------------------------|
| H51687 | 1-(4-tert-Butoxyphenyl)homopiperazine monohydrochloride, 98% [4-BOPH HCl] [934991-96-5], C ₁₅ H ₂₃ N ₂ O·HCl, F.W. 284.83, m.p. 197-201°, MDL MFCD16251545, Note: Sold in collaboration with Tosoh Organic Chemical Co., Ltd. | 500mg |
| |  | |
| | 1-(4-Butoxyphenyl)-3-(1-piperidinyl)-1-propanone , see Dyclonine hydrochloride, J61330, p. 202 (R)-(-)-sec-Butyl alcohol , see (R)-(-)-2-Butanol, L13983, p. 140 (S)-(+)-sec-Butyl alcohol , see (S)-(+)-2-Butanol, L14164, p. 140 (R)-(-)-2-Butylamine , see (R)-(-)-2-Aminobutane, L03889, p. 92 (S)-(+)-2-Butylamine , see (S)-(+)-2-Aminobutane, L10069, p. 92 α-[(tert-Butylamino)methyl]-4-hydroxy-1,3-benzenedimethanol sulfate , see Salbutamol sulfate, A18544, p. 339 Butylated hydroxyanisole , see 2(3)-tert-Butyl-4-methoxyphenol, B23530, p. 141 2-n-Butyl-3-benzofuranyl [4-[2-(diethylamino)ethoxy]-3,5-diiodophenyl] ketone hydrochloride , see Amiodarone hydrochloride, J60456, p. 100 4-Butyl-1,2-diphenyl-3,5-pyrazolidinedione , see Phenylbutazone, L03449, p. 316 | |
| H52065 | O-tert-Butyl-N-Fmoc-L-β-homoserine, 95% [Fmoc-β-Homoser(tBu)-OH] [203854-51-7], C ₂₅ H ₂₇ NO ₅ , F.W. 397.47, m.p. 96-98°, BRN 8014825, MDL MFCD01862865 | 250mg 1g |
| |  | |
| H52192 | O-tert-Butyl-N-Fmoc-L-β-homotyrosine, 95% [Fmoc-β-Homoty(tBu)-OH] [219967-69-8], C ₂₉ H ₃₁ NO ₅ , F.W. 473.57, BRN 8236890, MDL MFCD01862862 | 250mg 1g |
| |  | |
| B23530 | 2(3)-tert-Butyl-4-methoxyphenol, 96% ▲ [BHA, Butylated hydroxyanisole] [25013-16-5], C ₁₁ H ₁₆ O ₂ , F.W. 180.25, m.p. 55-65°, Merck 14,1547, EINECS 246-563-8, MDL MFCD01779059, † | 50g 250g 1kg |
| |  | |
| | ⚠ ! H:H351-H302, P:P281-P264-P301+P312-P308+P313-P405-P501a | |
| | Application(s): Antioxidant | |
| H51702 | 1-(4-tert-Butylphenyl)homopiperazine dihydrochloride, 98% [4-BPHP 2HCl] [934992-03-7], C ₁₅ H ₂₃ N ₂ ·2HCl, F.W. 305.30, m.p. 240-244°, MDL MFCD08436124, Note: Sold in collaboration with Tosoh Organic Chemical Co., Ltd. | 500mg |
| |  | |
| | ! H:H315-H319-H335, P:P280g-P305+P351+P338 | |
| | Application(s): Useful intermediate for synthesis | |
| | n-Butyl phenyl ketone , see Valerophenone, A10525, p. 390 1-n-Butyl-3-(p-tolylsulfonyl)urea , see Tolbutamide, B21698, p. 371 | |
| L13189 | Butyric acid, 99+% [107-92-6], CH ₃ (CH ₂) ₃ COOH, F.W. 88.11, m.p. -8°, b.p. 162-164°, f.p. 69°(156°F), d. 0.964, n _D ²⁰ 1.3980, Merck 14,1593, UN2820, EINECS 203-532-3, RTECS ES5425000, BRN 906770, MDL MFCD00002814, † | 100ml 500ml 2.5L |
| | ⚠ ⚠ H:H311-H314, P:P260-P303+P361+P353-P305+P351+P338-P361-P405-P501a | |
| J64844 | (4S)-3-Butyryl-4-benzyl-2-oxazolidinone [UIC-1017, Cell Sheet Migration Inhibitor, Negative Control] [112459-79-7], C ₁₄ H ₁₇ NO ₃ , F.W. 247.29, Powder | 5mg |
| J64391 | Butyrylcholine chloride, 98+% ■ [(2-Hydroxyethyl)trimethylammoniumchloride butyrate] [2963-78-2], C ₈ H ₂₀ ClNO ₂ , F.W. 209.71, Powder, EINECS 220-999-9, MDL MFCD00011844 | 50g 100g |
| A12622 | S-Butyrylthiocholine iodide, 98% ▲ ■ [1866-16-6], CH ₃ CH ₂ CH ₂ COSCH ₂ CH ₂ N(CH ₃) ₃ I, F.W. 317.23, m.p. 172-176°, EINECS 217-475-7, BRN 3729509, MDL MFCD00011845, † | 5g 25g |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | C2-Ceramide , see N-Acetyl-D-sphingosine, 98%, J60534, p. 74 | |
| J61832 | CABS, 0.2M buffer soln., pH 10.5 [161308-34-5], Liquid | 100ml 250ml |
| A18139 | Cacodylic acid sodium salt trihydrate [Sodium cacodylate trihydrate, Dimethylarsinic acid sodium salt trihydrate] [6131-99-3], (CH ₃) ₂ AsO ₂ Na·3H ₂ O, F.W. 214.03 (159.98anhy), Merck 14,8595, UN1688, EINECS 204-708-2, RTECS CH7700000, BRN 3702348, MDL MFCD00149079, † | 25g 100g 500g |
| | ⚠ ⚠ H:H301-H331-H400-H410, P:P261-P301+P310-P321-P304+P340-P405-P501a | |
| | Application(s): An integral component of terminal deoxynucleotidyl transferase buffer. | |
| | Cadavarine , see 1,5-Diaminopentane, B23039, p. 183 2-CADO , see 2-Chloroadenosine, J63810, p. 155 | |


| Stock # | Description | Size |
|---------|--|---------------------|
| J64396 | Caerulein, non-sulfated [Pyr-Gln-Asp-Tyr-Thr-Gly-Trp-Met-Asp-Phe-NH] [20994-83-6], C ₅₈ H ₇₃ N ₁₃ O ₁₈ S, F.W. 1272.36, Powder | 1mg |
| | Application(s): Stimulates smooth muscle and increases digestive secretions | |
| J64320 | Caerulein, sulfated [Glp-Gln-Asp-Tyr(SO ₃ H)-Thr-Gly-Trp-Met-Asp-Phe-NH ₂ , Ceruletide] [17650-98-5], C ₅₈ H ₇₃ N ₁₃ O ₂₁ S ₂ , F.W. 1352.40, Powder, BRN 5422487, MDL MFCD00076478 | 0.5mg 1mg |
| | Application(s): Stimulates smooth muscle and increases digestive secretions | |
| J65355 | Cafestol [469-83-0], C ₂₀ H ₂₈ O ₃ , F.W. 316.44, Powder, m.p. 156-158°, d. 1.23, Merck 14,1634, RTECS PB9185090 | 50mg 100mg |
| | Application(s): Natural extract from coffee beans which induces glutathione S-transferase | |
| | Caffeic acid , see 3,4-Dihydroxycinnamic acid, A15950, p. 192 Caffeic acid methyl ester , see Methyl caffeate, J63786, p. 286 | |
| A10431 | Caffeine, 99% [3,7-Dihydro-1,3,7-trimethyl-1H-purine-2,6-dione, 1,3,7-Trimethylxanthine] [58-08-2], C ₈ H ₁₀ N ₄ O ₂ , F.W. 194.19, m.p. 234-236°, d. 1.230, Merck 14,1636, Solubility: Soluble in pyrrrole, THF-H ₂ O mixture, ethyl acetate, UN1544, EINECS 200-362-1, RTECS EV6475000, BRN 17705, MDL MFCD00005758, † ! H:H302, P:P264-P270-P301+P312-P330-P501a | 100g 250g 1kg |
| | Application(s): Has inhibitory action against lung and colon tumorigenses, and virus induction | |
| L10255 | Calcein sodium salt, ca 2-3 Na [Bis[N,N-bis(carboxymethyl)aminomethyl]fluorescein sodium salt, Fluorexon] [108750-13-6], C ₃₀ H ₂₆ N ₂ Na ₂ O ₁₃ , F.W. 666.51, MDL MFCD00005049 Reagent for complexometric determination of Ca and Mg: <i>Analyst</i> , 82, 284 (1957); 83, 188 (1958). | 5g 25g |
| | Application(s): Indicator for the determination of calcium in biological systems | |
| J61610 | Calciferol [Ergocalciferol, Vitamin D ₂] [50-14-6], C ₂₈ H ₄₄ O, F.W. 396.65, Powder, m.p. 114-118°, Merck 14,10018, UN2811, EINECS 200-014-9, RTECS KE1050000, BRN 1916682, MDL MFCD00166988, † ☞ H:H300-H311-H372, P:P260-P301+P310-P361-P302+P352-P405-P501a | 1g 5g 10g |
| J62163 | Calciferol, 98% [Ergocalciferol, Vitamin D ₂] [50-14-6], C ₂₈ H ₄₄ O, F.W. 396.66, Powder, m.p. 118-119°, Merck 14,10018, UN2811, EINECS 200-014-9, RTECS KE1050000, BRN 1916682, MDL MFCD00166988, † ☞ H:H301-H311-H330-H372, P:P301+P310-P304+P340-P320-P330-P361-P405-P501a | 1g 5g 25g |
| | Calcimycin , see Antibiotic A23187, 99+%, J63020, p. 105 | |
| J64047 | Calcineurin Autoinhibitory Fragment [Ile-Thr-Ser-Phe-Glu-Glu-Ala-Lys-Gly-Leu-Asp-Arg-Ile-Asn-Glu-Arg-Met-Pro-Pro-Arg-Arg-Asp-Ala-Met-Pro] C ₁₂₄ H ₂₀₅ N ₃₉ O ₃₉ S ₂ , F.W. 2930.31, Solid | 0.5mg 1mg |
| J61049 | Calcitonin, chicken C ₁₄₅ H ₂₄₀ N ₄₂ O ₄₆ S ₂ , F.W. 3371.89, Powder, Merck 14,1643 | 0.5mg |
| | Application(s): A peptide hormone produced by thyroid cells, shown to inhibit osteoclasts activity | |
| J63006 | Calcitonin, eel [57014-02-5], C ₁₄₈ H ₂₄₁ N ₄₃ O ₄₇ S ₂ , F.W. 3414.94, Powder, Merck 14,1643, MDL MFCD00133858 | 1mg |
| | Application(s): A peptide hormone | |
| J63192 | Calcitonin, human, 97+% [Calcitonin M, Human C carcinoma] [21215-62-3], C ₁₄₅ H ₂₃₈ N ₄₀ O ₄₅ S ₃ , F.W. 3417.90, Powder, Merck 14,1643, EINECS 244-276-2, RTECS XP3560000, MDL MFCD00167520 | 0.5mg 1mg |
| | Application(s): Decreases blood calcium and phosphate due to inhibition of resorption by osteoblasts and osteocytes. A carrier peptide that can be used to internalize fusion proteins | |
| J64341 | Calcitonin, porcine C ₁₅₉ H ₂₃₂ N ₄₅ O ₄₅ S ₃ , F.W. 3604.01, Solid, EINECS 235-585-3, RTECS XP3561000 | 0.5mg 1mg |
| J61231 | Calcitonin, rat [11118-25-5], C ₁₄₈ H ₂₂₈ N ₄₀ O ₄₆ S ₂ , F.W. 3399.90, Powder, Merck 14,1643, MDL MFCD00133857 | 0.5mg |
| | Application(s): A peptide hormone | |
| J63531 | Calcitonin, salmon [47931-85-1], C ₁₄₅ H ₂₄₀ N ₄₄ O ₄₆ S ₂ , F.W. 3417.90, Powder, Merck 14,1643, EINECS 256-342-8, RTECS EV8000000, MDL MFCD00133859 | 0.5mg |
| | Application(s): A peptide hormone | |











| Stock # | Description | Size |
|---------|---|--------------------|
| J64415 | Calcitonin (8-32), salmon [Val-Leu-Gly-Lys-Leu-Ser-Gln-Glu-Leu-His-Lys-Leu-Gln-Thr-Tyr-Pro-Arg-Thr-Asn-Thr-Gly-Ser-Gly-Thr-Pro-NH2] [155069-90-2], C ₁₁₉ H ₁₉₈ N ₃₆ O ₃₇ , F.W. 2725.06, Solid | 0.5mg 1mg |
| J65667 | Calcitonin Gene Related Peptide, human [CGRP, human] [90954-53-3], C ₁₆₃ H ₂₈₇ N ₅₁ O ₄₉ S ₂ , F.W. 3789.3, Solid, MDL MFCD00285485 | 0.5mg 1mg |
| J65912 | Calcitonin Gene Related Peptide (8-37), human [α-CGRP (8-37), human] [119911-68-1], C ₁₃₉ H ₂₃₀ N ₄₄ O ₃₈ , F.W. 3125.58, Powder, MDL MFCD00133153 | 0.5mg 1mg |
| J64037 | Calcitonin Gene Related Peptide II, human [98824-26-1], C ₁₆₂ H ₂₆₇ N ₅₁ O ₄₈ S ₃ , F.W. 3793.35, Solid | 0.5mg |
| J65250 | [Tyr0] Calcitonin Gene Related Peptide II, human C ₁₇₁ H ₂₇₈ N ₅₂ O ₅₀ S ₃ , F.W. 3956.52, Solid | 0.5mg 1mg |
| | Calcitonin M , see Calcitonin, human, 97+%, J63192, p. 142 | |
| 12365 | Calcium carbonate, 98% [471-34-1], CaCO ₃ , F.W. 100.09, Powder, m.p. 800° dec., d. 2.930, n _D ²⁰ 1.6583, Merck 14,1657, Solubility: Practically insoluble in water. Soluble in diluted acids, EINECS 207-439-9, RTECS FF9335000, MDL MFCD00010906, † | 500g 2kg |
| | Application(s): Manufacture of paint, rubber, plastics, etc. In food, cosmetics, and pharmaceuticals. As soil conditioner, neutralizer of surface waters, and as an industrial acid neutralizer | |
| 33295 | Calcium carbonate, ACS, 99.0% min [471-34-1], CaCO ₃ , F.W. 100.09, Powder, m.p. 800° dec., d. 2.930, n _D ²⁰ 1.6583, Merck 14,1657, EINECS 207-439-9, RTECS FF9335000, MDL MFCD00010906, † Maximum level of impurities: Insoluble in dilute hydrochloric acid 0.01%, Cl 0.001%, F 0.0015%, SO ₄ 0.01%, NH ₄ 0.003%, Heavy Metals (as Pb) 0.001%, Fe 0.003%, Ba 0.01%, Mg 0.02%, K 0.01%, Na 0.1%, Sr 0.1% | 100g 500g |
| J62905 | Calcium chloride, 100mM aq. soln., sterile [10043-52-4], CaCl ₂ , F.W. 110.99, Liquid, † ! H:H302, P:P264-P270-P301+P312-P330-P501a | 500ml 1L |
| J63122 | Calcium chloride, 1M aq. soln. [10043-52-4], CaCl ₂ , F.W. 110.99, Liquid, MDL MFCD00010903, † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 50ml 100ml |
| 33296 | Calcium chloride dihydrate, ACS, 99.0-105.0% ■ [10035-04-8], CaCl ₂ ·2H ₂ O, F.W. 147.02 (110.99anhy), Powder, d. 0.835, Merck 14,1659, EINECS 233-140-8, MDL MFCD00149613, † Maximum level of impurities: Insoluble matter 0.01%, pH of a 5% solution 4.5-8.5 at 25°, Oxidizing substances (as NO ₃) 0.003%, SO ₄ 0.01%, NH ₄ 0.005%, Ba 0.005%, Heavy Metals (as Pb) 5ppm, Fe 0.001%, Mg 0.005%, K 0.01%, Na 0.02%, Sr 0.1% ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 500g 2kg |
| 89866 | Calcium chloride, anhydrous, ACS, 96.0% min ■ [10043-52-4], CaCl ₂ , F.W. 110.99, Powder, Packaged under argon, m.p. 782°, b.p. >1600°, Merck 14,1659, EINECS 233-140-8, RTECS EV9800000, MDL MFCD00010903, Note: d ₂₅ ²⁵ 2.15, † Maximum level of impurities: Titratable base 0.006meq/g ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 50g 250g |
| | Application(s): Typical ionic halide, often used as a desiccant | |
| | Calcium ionophore A23187 , see Antibiotic A23187, 99+%, J63020, p. 105 | |
| J60926 | Calcium-Like Peptide [Val-Ala-Ile-Thr-Val-Leu-Val-Lys, CALP1] [145224-99-3], C ₄₀ H ₇₅ N ₉ O ₁₀ , F.W. 827.09, Powder | 1mg 5mg |
| | Application(s): Cell-permeable calmodulin agonist | |
| | Calcium D-pantothenate hydrate , see D-Pantothenic acid calcium salt hydrate, A16609, p. 311 | |
| | Calcium phosphate hydroxide , see Hydroxylapatite, high resolution, J61818, p. 250 | |
| | Calcium phosphate hydroxide , see Hydroxylapatite, fast flow, J60076, p. 249 | |
| 89836 | Calcium phosphate (pyro), 96% min [Calcium pyrophosphate] [7790-76-3], Ca ₂ P ₂ O ₇ , F.W. 254.10, Powder, m.p. 1230°, d. 3.09, EINECS 232-221-5, MDL MFCD00015983, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250g 1kg 5kg |
| | Calcium pyrophosphate , see Calcium phosphate (pyro), 89836, p. 143 | |
| J63270 | Calmidazolium chloride [57265-65-3], C ₃₁ H ₂₃ Cl ₂ N ₂ O, F.W. 687.71, Solid, MDL MFCD00077679 | 10mg |
| | Application(s): Inhibits the calcium-calmodulin dependent phosphodiesterase | |



| Stock # | Description | Size |
|---------|---|-------------------------------|
| J60231 | Calmodulin, bovine testes [77107-46-1], Lyophilized powder, 16.680 kDa, Merck 14,1719, MDL MFCD00131869 | 1mg 2.5mg |
| | Application(s): Activates cyclic phosphodiesterase CALP1 , see Calcium-Like Peptide, J60926, p. 143 | |
| J61766 | Calpain Inhibitor I, 95+% [Ac-LLnL-CHO, ALLN] [110044-82-1], C ₂₀ H ₃₇ N ₅ O ₄ , F.W. 383.53, Powder, BRN 7656053, MDL MFCD00065505 | 5mg 25mg |
| | Application(s): An inhibitor of both Calpain I and II | |
| J62491 | Calpain Inhibitor II, 95+% [N-Ac-Leu-Leu-Methioninal, ALLM] [136632-32-1], C ₁₉ H ₃₅ N ₅ O ₄ S, F.W. 401.60, Powder, BRN 7693643, MDL MFCD00065506 | 5mg 25mg |
| | Application(s): An inhibitor of calpains I and II | |
| J62919 | Calpain Inhibitor III, 95+% [MDL, Z-Val-Phe-CHO] [88191-84-8], C ₁₈ H ₃₃ N ₅ O ₄ S, F.W. 401.60, Powder, MDL MFCD00798796 | 25mg |
| | Application(s): Inhibits calpain proteolysis | |
| J65052 | Calpain Inhibitor IV ▲ [Z-Leu-Leu-Tyr-fluoromethyl ketone, Z-LLY-FMK] C ₂₈ H ₄₀ FN ₃ O ₆ , F.W. 557.65, Powder | 1mg |
| J65826 | Calpain Inhibitor X ▲ [Z-Leu-α-aminobutyric acid-CONHC2H5, Z-Leu-Abu-CONHC2H5] C ₂₁ H ₃₁ N ₅ O ₅ , F.W. 405.50, Solid | 1mg 5mg |
| J65991 | Calpain Inhibitor XI [Z-Leu-α-aminobutyric acid-CONH(CH2)3-morpholine, Z-L-Abu-CONH(CH2)3-morpholine] C ₂₈ H ₄₀ N ₄ O ₆ , F.W. 504.60, Solid | 1mg 5mg |
| J64751 | Calpain Inhibitor XII [Z-L-Nva-CONH-CH2-2-Py] C ₂₈ H ₃₄ N ₄ O ₅ , F.W. 482.60, Solid | 1mg 5mg |
| J63222 | Calpain Substrate I [Suc-Leu-Tyr-AMC] [94367-20-1], C ₂₈ H ₃₃ N ₃ O ₈ , F.W. 551.59, Powder, MDL MFCD00057900 | 50mg 100mg 250mg |
| | Application(s): Fluorogenic substrate for both calpains I and II | |
| J60481 | Calpeptin, 98+% [N-Benzoyloxycarbonyl-L-leucyl-norleucinal, Z-Leu-norleucinal] [117591-20-5], C ₂₀ H ₃₀ N ₂ O ₄ , F.W. 362.50, Powder, MDL MFCD00155623 | 10mg 50mg |
| | Application(s): Inhibitor of the calcium-dependent protease calpain and cathepsin L | |
| J60647 | Calphostin C, 99+% [UCN-1028c] [121263-19-2], C ₄₄ H ₃₈ O ₁₄ , F.W. 790.76, Powder, MDL MFCD00133155 | 100micrograms |
| | Application(s): Potent inhibitor of protein kinase C | |
| J61952 | Calyculin A, 98+% [101932-71-2], C ₂₆ H ₃₁ N ₅ O ₁₅ P, F.W. 1009.17, Solid, Merck 14,1724, UN3462, BRN 4903216, MDL MFCD06795864 | 100micrograms |
| |  H:H301-H311-H330-H315, P:P301+P310-P304+P340-P320-P330-P361-P405-P501a | |
| | Application(s): Very potent inhibitor (Ki = ca. 0.1 nM) with high specificity for the PP-1 and PP-2 classes of protein serine/threonine phosphatase | |
| J62362 | Camostat mesylate, 98% [59721-29-8], C ₂₀ H ₂₂ N ₄ O ₅ .CH ₃ SO ₃ H, F.W. 494.52, Powder, m.p. 150-155°, Merck 14,1728, MDL MFCD00941410 | 25mg 100mg 500mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): An orally active synthetic serine protease inhibitor | |
| A10936 | (±)-Camphor, 96% [DL-2-Bornanone] [76-22-2], C ₁₅ H ₁₈ O, F.W. 152.24, m.p. 172-176°, b.p. 204°, f.p. 64° (147°F), d. 0.992, Merck 14,1732, Solubility: Soluble in alcohols, ether, chloroform, benzene, UN2717, EINECS 200-945-0, RTECS EX1225000, BRN 1907611, MDL MFCD00074738, † | 100g 500g 2.5kg 10kg |
| |  | |
| |  ! H:H228-H315-H319, P:P210-P280g-P305+P351+P338 | |
| B23469 | (1S)-(-)-Camphor, 98% [L-2-Bornanone] [464-48-2], C ₁₅ H ₁₆ O, F.W. 152.24, m.p. 175-180°, b.p. 204°, f.p. 65° (149°F), d. 0.990, [α] _D ²⁰ -43° (c=10 in ethanol), Merck 14,1732, UN2717, EINECS 207-354-7, RTECS EX1250000, BRN 4291747, MDL MFCD00064148, † | 5g 25g 100g |
| |  | |
| |  ! H:H228-H315-H319, P:P210-P280g-P305+P351+P338 | |

| Stock # | Description | Size |
|---------|---|-----------------------|
| J62523 | Camptothecin [(S)-(+)-Camptothecin] [7689-03-4], C ₂₀ H ₁₈ N ₂ O ₄ , F.W. 348.35, Powder, m.p. 260° dec., Merck 14,1735, UN1544, RTECS UQ492000, BRN 631069, MDL MFCD00081076 | 250mg 1g 5g |
| | ⚠ H: H301, P: P264-P270-P301+P310-P321-P405-P501a Application(s): Cytotoxic antitumor agent that inhibits topoisomerase I (S)-(+)-Camptothecin , see Camptothecin, J62523, p. 145 | |
| A16289 | Canada balsam, natural filtered [Balsam Canada] [8007-47-4], f.p. 43° (109°F), d. 0.99, n _D ²⁰ 1.5230, Merck 14,946, UN1993, EINECS 232-362-2, RTECS CP2352500, MDL MFCD00132800, † | 25g 100g 500g |
| | 🔥 H: H226, P: P210-P241-P280-P240-P303+P361+P353-P501a For microscopy. Application(s): Mounting medium for microscopy | |
| J62818 | Candesartan, 98% [Celaxetil] [139481-59-7], C ₂₄ H ₂₀ N ₆ O ₅ , F.W. 440.45, Powder, m.p. 183-185°, Merck 14,1739, MDL MFCD00081076 | 100mg 1g |
| | ⚠ H: H302-H312-H332-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): Angiotensin II receptor antagonist | |
| J63403 | Canertinib, 99+% [CI-1033] [267243-28-7], C ₂₄ H ₂₅ ClFN ₃ O ₃ , F.W. 485.94, Solid, Merck 14,1744 | 25mg 100mg |
| | ⚠ H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): An irreversible pan-HER tyrosine kinase inhibitor | |
| J63750 | Canertinib dihydrochloride salt, 99+% [CI-1033, PD-183805] [289499-45-2], C ₂₄ H ₂₅ ClFN ₃ O ₃ ·2HCl, F.W. 558.86, Powder, Merck 14,1744, RTECS UC6316110, MDL MFCD09954112 | 25mg 50mg 100mg |
| | ⚠ H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): An irreversible pan-HER tyrosine kinase inhibitor | |
| J61394 | Cannabiscetin , see Myricetin, 98%, J60450, p. 296 | |
| | Canrenoic acid potassium salt, 98+% [2181-04-6], C ₂₂ H ₃₀ KO ₄ , F.W. 396.58, Powder, Merck 14,1750, EINECS 218-554-9, RTECS TU3500000, MDL MFCD05662375 | 1g 5g 25g |
| | ⚠ H: H302, P: P264-P270-P301+P312-P330-P501a | |
| J60238 | Canrenone, 98% [976-71-6], C ₂₂ H ₃₂ O ₃ , F.W. 340.46, Solid, m.p. 149-151°, Merck 14,1752, EINECS 213-554-5 | 1g 5g 25g |
| | Application(s): Inhibits aldosterone biosynthesis and blocks ouabain effects | |
| J61801 | Cantharidin, 98% [56-25-7], C ₁₀ H ₁₂ O ₄ , F.W. 196.20, Powder, m.p. 215-217°, Merck 14,1752, UN2811, EINECS 200-263-3, RTECS RN8575000, MDL MFCD00134968, † | 100mg |
| | ⚠ H: H300-H315-H319-H335, P: P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): Inhibitor of protein phosphatase 2A | |
| | Capric aldehyde , see Decanal, A11656, p. 176 Caproamide , see Hexanoamide, H25929, p. 244 Caprylic acid methyl ester , see Methyl caprylate, A10991, p. 289 | |
| A17037 | CAPS, 99% [3-Cyclohexylamino-1-propanesulfonic acid] [1135-40-6], C ₈ H ₁₉ NO ₃ S, F.W. 221.32, m.p. 324°, Merck 14,1767, EINECS 214-492-1, RTECS TZ6395000, BRN 2835588, MDL MFCD00003837, † | 25g 100g 500g |
| | ⚠ H: H302-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a Buffer, pKa = 10.40 at 20°. <i>Biochemistry</i> , 5, 467 (1966). | |
| J63749 | CAPS, 0.5M buffer soln., pH 9.0 [1135-40-6], Liquid, † | 250ml 500ml |
| | ⚠ H: H302, P: P264-P270-P301+P312-P330-P501a | |
| J60022 | CAPS, 0.5M buffer soln., pH 9.0 [1135-40-6], Liquid, † | 250ml 500ml |
| | ⚠ H: H302, P: P264-P270-P301+P312-P330-P501a | |
| J60776 | CAPS, 0.5M buffer soln., pH 9.5 [1135-40-6], Liquid, † | 100ml 250ml |
| | ⚠ H: H302, P: P264-P270-P301+P312-P330-P501a | |






| Stock # | Description | Size |
|--|--|---|
| J60569 | CAPS, 0.5M buffer soln., pH 10.0 [1135-40-6], Liquid, † | 250ml 500ml |
| J62446 | CAPS, 0.5M buffer soln., pH 10.5 [1135-40-6], Liquid, † ! H:H302, P:P264-P270-P301+P312-P330-P501a | 250ml 500ml |
| J63138 | CAPS, 0.5M buffer soln., pH 11.0 [1135-40-6], Liquid, † ! H:H302, P:P264-P270-P301+P312-P330-P501a | 250ml 500ml |
| J62865 | Capsaicin [8-Methyl-N-vanillyl-trans-6-nonenamide, (E)-Capsaicin] [404-86-4], C ₁₈ H ₂₇ NO ₃ , F.W. 305.41, Solid, m.p. 56-58°, b.p. 210-220°, f.p. 113°(235°F), Merck 14,1768, UN2811, EINECS 206-969-8, RTECS RA8530000, BRN 2816484, MDL MFCD00017259, † ☠ H:H300-H311, P:P301+P310-P361-P302+P352-P321-P405-P501a | 1g 5g |
| Application(s): Prototypic vanilloid receptor agonist. Reversibly inhibits aggregation of platelets (E)-Capsaicin, see Capsaicin, J62865, p. 146 | | |
| J63055 | Capsazepine, 99+% [138977-28-3], C ₁₉ H ₂₁ ClN ₂ O ₂ S, F.W. 376.90, Powder, m.p. 159-161°, MDL MFCD00153778 | 10mg 50mg |
| Application(s): A competitive antagonist for capsaicin and resiniferatoxin | | |
| B21305 | CAPSO, 98% ■ [3-Cyclohexylamino-2-hydroxy-1-propanesulfonic acid] [73463-39-5], C ₉ H ₁₉ NO ₃ S, F.W. 237.32, m.p. 270-274°, MDL MFCD00041778 |  25g 100g 500g |
| J60973 | CAPSO, 0.2M buffer soln., pH 8.5 [102601-34-3], Liquid | 100ml 250ml |
| J61126 | CAPSO, 0.2M buffer soln., pH 9.0 [102601-34-3], Liquid | 100ml 250ml |
| J63242 | CAPSO, 0.2M buffer soln., pH 9.5 [102601-34-3], Liquid | 100ml 250ml |
| B25202 | CAPSO sodium salt, 98% ■ [3-Cyclohexylamino-2-hydroxy-1-propanesulfonic acid sodium salt] [102601-34-3], C ₉ H ₁₉ NaO ₃ S, F.W. 259.30, MDL MFCD00070063 |  25g 100g 500g |
| J63593 | Captopril [N-[(S)-3-Mercapto-2-methylpropionyl]-L-proline] [62571-86-2], C ₉ H ₁₅ NO ₃ S, F.W. 217.29, Powder, m.p. 104-108°, Merck 14,1774, EINECS 263-607-1, RTECS UY0550000, BRN 477887, MDL MFCD00168073 ☠ ! H:H361-H317, P:P261-P280-P302+P352-P321-P405-P501a | 1g 5g 25g |
| Application(s): Orally active inhibitor of angiotensin-converting enzyme | | |
| L06674 | Carbachol, 99% ■ [Carbamoylcholine chloride] [51-83-2], H ₂ NCO ₂ CH ₂ CH ₂ N(CH ₃) ₃ Cl, F.W. 182.65, m.p. ca 210° dec., Merck 14,1779, UN2811, EINECS 200-127-3, RTECS GA0875000, BRN 3917459, MDL MFCD00012011, † ☠ H:H301, P:P264-P270-P301+P310-P321-P405-P501a | 5g 25g |
| Application(s): Cholinergic agonist | | |
| J60284 | Carbadox, 98+% [6804-07-5], C ₁₁ H ₁₆ N ₄ O ₄ , F.W. 262.22, Solid, m.p. 239-240°, f.p. 18°(64°F), Merck 14,1780, UN1325, RTECS FE2779000, MDL MFCD00057293 ☠ ☠ ! H:H228-H350-H302, P:P210-P241-P280-P281-P405-P501a | 25g 100g |
| Application(s): Quinoxaline derivative. A broad spectrum antibiotic agent | | |
| J62590 | Carbamazepine, 98% [5H-Dibenz[b,f]azepine-5-carboxamide] [298-46-4], C ₁₅ H ₁₂ N ₂ O, F.W. 236.27, Powder, m.p. 189-192°, Merck 14,1781, EINECS 206-062-7, RTECS HN8225000, MDL MFCD00005073 ☠ ! H:H334-H302-H317, P:P285-P261-P280-P302+P352-P321-P501a | 25g 100g |
| Application(s): Cytochrome P450 3A4 inducing anti-epileptic drug; ligand for the GABA-A receptor benzodiazepine modulatory site | | |
| Carbamide, see Urea, 36428, p. 388 Carbomethioic acid, see Tolnaftate, J61834, p. 371 Carbamoylcholine chloride, see Carbachol, L06674, p. 146 N-(Carbamoylmethyl)taurine, see ACES, A11553, p. 69 Carbamyliurea, see Biuret, L00812, p. 128 | | |

| Stock # | Description | Size |
|---|--|---------------------|
| A11448 | Carbazole, 95% [86-74-8], C ₁₂ H ₉ N, F.W. 167.21, m.p. 240-246°, b.p. 354-356°, f.p. 220°(428°F), d. 1.150, Merck 14, 1790, UN3077, EINECS 201-696-0, RTECS FE3150000, BRN 3956, MDL MFCD00004960, †   H:H351-H400-H410, P:P281-P273-P308+P313-P391-P405-P501a | 50g 100g 500g |
| J61949 | Carbenicillin disodium salt [4800-94-6], C ₁₇ H ₁₆ N ₂ Na ₂ O ₆ S, F.W. 422.36, Powder, Merck 14, 1792, EINECS 225-360-8, RTECS ON9105000, BRN 5722128, MDL MFCD00077683  H:H334-H317, P:P285-P261-P280-P302+P352-P321-P501a | 1g 5g 25g |
| Application(s): Water-soluble antibiotic effective against gram-negative bacteria | | |
| J63714 | Carbenoxolone disodium salt, 97+% [7421-40-1], C ₂₂ H ₂₈ Na ₂ O ₇ , F.W. 614.70, Solid, Merck 14, 1793, EINECS 231-044-0, RTECS RK0250000, MDL MFCD00079043 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g 5g |
| Application(s): A triterpenoid chemopreventive agent | | |
| J64446 | Carbetapentane citrate [Pentoxifyverine citrate, 2-[2-(Diethylamino)ethoxy]ethyl 1-phenylcyclopentane-1-carboxylate citrate] [23142-01-0], C ₂₈ H ₃₁ NO ₃ ·C ₆ H ₈ O ₇ , F.W. 633.70, Powder, EINECS 245-449-5, RTECS GY3500000, MDL MFCD00055697 ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 50mg 1g |
| N(α)-Carbethoxy-L-asparagine, see N(α)-Ethoxycarbonyl-L-asparagine, L09327, p. 214 Carbimazole, see Ethyl 3-methyl-2-thioimidazole-1-carboxylate, L08218, p. 217 | | |
| L16334 | Carbon, activated, Norit ROW 0.8mm pellets, steam activated [7440-44-0], EINECS 231-153-3, MDL MFCD00133992, † Extruded carbon with large pore volume and pore size distribution, suitable for decolorization, deodorisation and purification applications. | 100g 500g 2kg |
| Application(s): Decolorizing carbon | | |
| L11860 | Carbon powder, activated, Norit GSX, steam activated, acid washed [7440-44-0], UN1362, EINECS 231-153-3, RTECS FF5250100, MDL MFCD00133992, †  H:H228-H252, P:P210-P241-P280-P235+P410-P240-P420 High purity grade with high internal surface area, suitable for decolorization, purification and catalyst carrier applications. | 100g 500g 2kg |
| Application(s): Decolorizing carbon | | |
| J63899 | Carbonate, 0.5M buffer soln., pH 9.0 [497-19-8], Liquid, † H:H303, P:P312 | 250ml 500ml |
| J61064 | Carbonate, 0.5M buffer soln., pH 9.4 [497-19-8], Liquid, † H:H303, P:P312 | 250ml 500ml |
| J63658 | Carbonate, 0.5M buffer soln., pH 9.5 [497-19-8], Liquid, † H:H303, P:P312 | 250ml 500ml |
| J62610 | Carbonate, 0.5M buffer soln., pH 9.6 [497-19-8], Liquid, † H:H303, P:P312 | 250ml 500ml |
| J61229 | Carbonate, 0.5M buffer soln., pH 10.0 [497-19-8], Liquid, † H:H303, P:P312 | 250ml 500ml |
| J61396 | Carbonate-buffered saline (5X), pH 9.0 [497-19-8], Liquid, Note: 125mM sodium carbonate, 750mM sodium chloride, pH 9.0, † H:H303, P:P312 | 250ml 500ml |
| J63928 | Carbonate-buffered saline (5X), pH 9.5 [497-19-8], Liquid, Note: 125mM sodium carbonate, 750mM sodium chloride, pH 9.5, † H:H303, P:P312 | 250ml 500ml |
| N-(Nα-Carbonyl-Cpd-X-Phe-al)-Phe, see Chymostatin, J63275, p. 162 | | |
| A14688 | 1,1'-Carbonyldiimidazole, 97%  [CDI] [530-62-1], C ₇ H ₆ N ₂ O, F.W. 162.15, m.p. 116-120°, Merck 14, 1819, Fieser 1,114 5.97 6.97 8.77 9.96 12,106 13.66 16.64 18.85 21.90, UN3263, EINECS 208-488-9, BRN 6826, MDL MFCD00005286, †  H:H314-H302, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 10g 50g 250g |



| Stock # | Description | Size |
|---------------|--|---|
| | <p>Reagent for peptide coupling via the acylimidazolide: <i>Liebigs Ann. Chem.</i>, 609, 75 (1957); <i>J. Am. Chem. Soc.</i>, 80, 4423 (1958); 82, 4596 (1960); <i>J. Org. Chem.</i>, 27, 2094 (1962).</p> <p>One-pot esterification of a carboxylic acid with t-BuOH occurs in the presence of DBU: <i>Synthesis</i>, 833 (1982). The reactivity of acyl imidazolides can be increased by N-alkylation: <i>Chem. Pharm. Bull.</i>, 32, 5044 (1984).</p> <p>Acylimidazolides can also be reduced to aldehydes by DIBAL-H. This reaction has been applied to N-protected amino acids: <i>J. Chem. Soc., Chem. Commun.</i>, 79 (1979).</p> <p>Dehydrates aldioximes, including chiral oximes, to nitriles in high yield: <i>J. Chem. Soc., Chem. Commun.</i>, 628 (1973); <i>Synth. Commun.</i>, 12, 25 (1982). Ketoximes can be converted to amides by the spontaneous Beckmann rearrangement of imidazolium salts: <i>Chem. Pharm. Bull.</i>, 32, 2560 (1984):</p> $ \begin{array}{c} \text{R}'' \\ \\ \text{R}'-\text{C}=\text{N}-\text{OH} \\ \text{ii) } \text{CH}_2=\text{CH}-\text{CH}_2-\text{Br} \end{array} \xrightarrow[\text{ii) } \text{CH}_2=\text{CH}-\text{CH}_2-\text{Br}]{\text{i) CDI} } \left[\begin{array}{c} \text{R}'' \\ \\ \text{R}'-\text{C}=\text{N}-\text{O}-\text{C}(=\text{O})-\text{N}(\text{CH}_2\text{CH}_2\text{CH}_2\text{Br})_2 \end{array} \right] \longrightarrow \begin{array}{c} \text{O} \\ \\ \text{R}'-\text{C}-\text{NHR}' \end{array} \quad 80\text{-}98\% $ <p>β-Hydroxy amino acids are dehydrated to dehydroamino acids: <i>Synthesis</i>, 968 (1982). α,β-Dihydroxyketones are converted to α-diketones: <i>Synth. Commun.</i>, 23, 2219 (1993).</p> | |
| | Application(s): Peptide coupling reagent | |
| J60433 | <p>Carboplatin <i>[1,1-Cyclobutanedicarboxylatodiammineplatinum(II), cis-Diammine(1,1-cyclobutanedicarboxylato) platinum]</i> [41575-94-4], [C₄H₈(CO₂)₂]Pt(NH₃)₂, F.W. 371.25, Powder, Merck 14,1822, EINECS 255-446-0, RTECS TP2300000, MDL MFCD00070464</p> <p>⚠ ! H: H334-H340-H360-H302-H312-H332-H317, P: P285-P261-P302+P352-P321-P405-P501a</p> | <p>1g 5g</p> |
| | Application(s): An antitumor agent | |
| | <p>Carbostesin, see Bupivacaine hydrochloride, 98+%, J62835, p. 140 Carbowax[®], see Polyethylene glycol 12,000, 42635, p. 324 4(5)-Carboxyfluorescein, see 5(6)-Carboxyfluorescein, L13439, p. 148</p> | |
| L13439 | <p>5(6)-Carboxyfluorescein, mixture of isomers, 97% <i>[4(5)-Carboxyfluorescein]</i> [72088-94-9], C₂₁H₁₂O₇, F.W. 376.32, m.p. ca 300°, EINECS 276-331-1, MDL MFCD00151081, †</p> <p>Used as a probe of intracellular pH: <i>Anal. Biochem.</i>, 156, 202 (1986)</p> | <p>250mg 1g</p>  |
| | <p>(Carboxymethyl)trimethylammonium chloride, see Betaine hydrochloride, A16122, p. 124 3-Carboxy-4-nitrophenyl disulfide, see 5,5'-Dithiobis(2-nitrobenzoic acid), A14331, p. 200</p> | |
| J65311 | <p>Carboxypeptidase Y from yeast <i>[Serine carboxypeptidase, E.C. 3.4.16.1]</i> [9046-67-7], Lyophilized powder, EINECS 232-934-1, MDL MFCD00130723</p> <p>! ⚠ H: H315-H319-H334-H335, P: P285-P305+P351+P338-P302+P352-P321-P405-P501</p> | <p>1mg 5mg 10mg</p> |
| | Application(s): For C-terminal sequencing of proteins. Also for C-terminal modification of proteins and peptides | |
| J61316 | <p>Carboxy-PTIO potassium salt, 98+% [148819-94-7], C₁₄H₁₆KN₂O₄, F.W. 315.38, Solid, MDL MFCD00216153</p> | <p>10mg 50mg</p> |
| | Application(s): Stable, water-soluble free radical that reacts with nitric oxide to inhibit NO synthase | |
| A17618 | <p>L-Carnitine, 99+% ■ <i>[(R)-(-)-3-Hydroxy-4-(trimethylammonio)butyrate, Vitamin B7]</i> [541-15-1], C₇H₁₅NO₃, F.W. 161.20, m.p. ca 190° dec., Merck 14,1849, EINECS 208-768-0, RTECS BP2980000, BRN 4292315, MDL MFCD00038747</p> | <p>10g 50g 250g</p>  |
| | <p>L-Carnitine acetyl ester hydrochloride, see O-Acetyl-L-carnitine chloride, 98%, J61536, p. 71 Carrageen, see Carrageenan, iota type, J60603, p. 148</p> | |
| J60603 | <p>Carrageenan, iota type <i>[Carrageenan gum, Carrageen]</i> [9062-07-1], Powder, EINECS 232-949-3, MDL MFCD00151512</p> | <p>100g 250g</p> |
| | Application(s): Forms soft gels in the presence of calcium ions | |
| | Carrageenan gum , see Carrageenan, iota type, J60603, p. 148 | |
| A13707 | <p>Casein, tech. ■ [9000-71-9], m.p. ca 280° dec., Merck 14,1883, EINECS 232-555-1, RTECS FI3519500, MDL MFCD00081481, †</p> | <p>500g 2.5kg 10kg</p> |
| | Application(s): Natural protein source, typically isolated from bovine milk | |
| J64482 | <p>Casein, high nitrogen, 95% ■ [9000-71-9], Powder, m.p. ca 280° dec., EINECS 232-555-1, RTECS FI3519420, †</p> | <p>500g 1kg</p> |
| J64214 | <p>Casein, Hammarsten Grade ■ <i>[Casein, Hammerstein Grade]</i> [9000-71-9], Powder, EINECS 232-555-1, RTECS FI3519420, †</p> | <p>100g</p> |
| J65590 | <p>Casein sodium salt <i>[Sodium caseinate]</i> [9005-46-3], Powder, RTECS FI3540000, MDL MFCD00130736, †</p> | <p>500g 1kg 5kg</p> |


| Stock # | Description | Size |
|---------|---|----------------|
| J60289 | Casein blocking buffer, 3% in PBS Liquid, Note: 3% Casein in phosphate-buffered saline, pH 7.4 Application(s): For Western Blots and ELISA | 250ml 500ml |
| J63453 | Casein blocking buffer, 3% in PBS, with 0.02% sodium azide Liquid, Note: 3% Casein in PBS with 0.02% sodium azide Application(s): For Western Blots and ELISA | 250ml 500ml |
| J61298 | Casein blocking buffer, 3% in TBS Liquid, Note: 3% Casein in Tris-buffered saline, pH 7.4 | 250ml 500ml |
| J62935 | Casein blocking buffer, 3% in TBS, with 0.02% sodium azide Liquid, Note: 3% Casein in TBS with 0.02% sodium azide Application(s): For Western Blots and ELISA | 250ml 500ml |
| J64565 | Casein hydrolysate enzymatic [Casamino acids] [65072-00-6], Powder, EINECS 265-363-1, RTECS FI3519450, † | 100g 500g |
| J64362 | Casein Kinase II Inhibitor III [CKII Inhibitor, TBCA] [934358-00-6], C ₉ H ₁₁ Br ₂ O ₂ , F.W. 463.74, Powder ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5mg |
| H26557 | Casein Peptone ■ [Peptones, casein] [91079-40-2], EINECS 293-428-4, MDL MFCD00131829 Application(s): Peptone is used in nutrient media for growing bacteria and fungi | 100g 500g |
| J62791 | β-Casomorphin, bovine [72122-62-4], C ₄₁ H ₅₅ N ₇ O ₉ , F.W. 789.93, Powder Application(s): A synthetic peptide with opioid activity which has first been isolated from an enzymatic casein digest | 5mg 25mg |
| J62271 | β-Casomorphin, human, 95+% [H-Tyr-Pro-Phe-Val-Glu-Pro-Ile-OH] [102029-74-3], C ₄₄ H ₆₁ N ₇ O ₁₁ , F.W. 864.01, Powder, MDL MFCD00076324 Application(s): An opioid peptide ▲-Casomorphin (1-4) amide (bovine), see Morpheceptin acetate, J61987, p. 296 | 5mg 25mg |
| J64407 | Caspase-1 Inhibitor I ■ [Ac-YVAD-CHO, Ac-Tyr-Val-Ala-Asp-CHO] [143313-51-3], C ₂₃ H ₃₂ N ₄ O ₈ , F.W. 492.52, Powder | 1mg 5mg |
| J64226 | Caspase-1 Inhibitor II [Ac-YVAD-CMK, IL-1β Converting Enzyme (ICE) Inhibitor II] [178603-78-6], C ₂₄ H ₃₃ ClN ₄ O ₈ , F.W. 540.99, Powder, RTECS AY3079566 | 5mg |
| J64583 | Caspase-1 Inhibitor IV [ICE Inhibitor IV, Ac-YVAD-AOM] [154674-81-4], C ₃₃ H ₄₂ N ₄ O ₁₀ , F.W. 654.71, Powder | 1mg |
| J64442 | Caspase-3 Inhibitor III [Ac-DEVD-CMK, Ac-Asp-Glu-Val-Asp-CMK] C ₂₁ H ₃₁ ClN ₄ O ₁₁ , F.W. 550.94, Powder | 1mg 5mg |
| J64801 | Caspase-3/7 Inhibitor ▲ [5-[(S)-(+)-2-(Methoxymethyl)pyrrolidino]sulfonylsatin] C ₁₄ H ₁₆ N ₂ O ₅ , F.W. 324.35, Powder | 1mg |
| J64729 | Caspase-9 Inhibitor I ■ [Z-Leu-Glu(OMe)-His-Asp(OMe)-fluoromethyl ketone, Z-LE(OMe)HD(OMe)-FMK] C ₃₂ H ₄₃ FN ₆ O ₁₀ , F.W. 690.71, Powder | 1mg |
| J65501 | Caspase-9 Inhibitor III [Ac-LEHD-CMK] [403848-57-7], C ₂₄ H ₃₅ ClN ₄ O ₉ , F.W. 587.02, Powder | 1mg 5mg |
| J65218 | Caspase-1 Substrate III, Fluorogenic ■ [N-Acetyl-Tyr-Val-Ala-Asp-7-amido-4-methylcoumarin, Ac-YVAD-AMC] [149231-65-2], C ₃₃ H ₃₉ N ₅ O ₁₀ , F.W. 665.69, Powder, MDL MFCD00171369 | 5mg |
| J65867 | Caspase-3 Substrate II, Fluorogenic ■ [N-Acetyl-Asp-Glu-Val-Asp-7-amido-4-methylcoumarin, Ac-DEVD-AMC] [169332-61-0], C ₃₀ H ₃₇ N ₅ O ₁₃ , F.W. 675.64, Powder, MDL MFCD00671411 | 5mg |

















| Stock # | Description | Size |
|--|---|--------------------|
| J61071 | Castanospermine, 99% [(1 <i>S</i> ,6 <i>S</i> ,7 <i>R</i> ,8 <i>R</i> ,8 <i>aR</i>)-1,6,7,8-Tetrahydroxyoctahydroindolizidine] [79831-76-8], C ₈ H ₁₅ N ₃ O ₄ , F.W. 189.21, Solid, m.p. 213-217°, Merck 14 ,1896, BRN 3588654, MDL MFCD00017555 ! H:H302-H312-H332, P:P261-P280-P302+P352-P304+P340-P322-P501a | 100mg 500mg |
| Application(s): Potent α and β -glucosidase inhibitor. | | |
| J64793 | (+)-Catechin, 98% ▲ [3,3',4',5',7-Pentahydroxyflavan] [154-23-4], C ₁₅ H ₁₄ O ₆ , F.W. 290.27, Powder, EINECS 205-825-1, RTECS DJ3450000, MDL MFCD00075649 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10mg 25mg |
| A10164 | Catechol, 99% [1,2-Dihydroxybenzene, Pyrocatechol] [120-80-9], C ₆ H ₆ O ₂ , F.W. 110.11, m.p. 104-107°, b.p. 245-246°, f.p. 127°(260°F), d. 1.370, Merck 14 ,7999, UN2811, EINECS 204-427-5, RTECS UX1050000, BRN 471401, MDL MFCD00002188, t  ! H:H301-H311-H315-H319, P:P301+P310-P305+P351+P338-P361-P302+P352-P405-P501a Ring-opening with O ₂ in the presence of CuCl, pyridine and methanol gives the monoester of cis,cis-muconic acid: <i>Org. Synth. Coll.</i> , 8 , 490 (1993). In the presence of catechol, carboxylic acids are reduced to alcohols by NaBH ₄ : <i>Tetrahedron</i> , 48 , 371 (1992). For an example of the use of catechol in the synthesis of crown ethers, see: <i>Org. Synth. Coll.</i> , 6 , 395 (1988). | 250g 1kg 5kg |
| Catechol monomethyl ether, see 2-Methoxyphenol, A16319, p. 285 | | |
| J65308 | Cathepsin B₁, Human Liver, 95% [EC 3.4.22.1] [9047-22-7], F.W. 27.5kDa, Liquid, RTECS FI5725000, MDL MFCD00130748 | 25micrograms |
| J61280 | Cathepsin G, 95% [EC 3.4.21.20] [107200-92-0], Powder, Merck 14 ,1905, MDL MFCD00130750, Note: Minimum 2 units per mg protein. One unit is defined as the amount of enzyme that will hydrolyze 1.0 micromole of Suc-AAPF-pNA per minute at 25 degrees and pH 7.5 | 100milliunits |
| Application(s): Enzyme that degrades collagen and proteoglycans | | |
| J65347 | Cathepsin B Inhibitor III [CA-074, [L-3-trans-(Propylcarbamoyl)oxirane-2-carbonyl]-L-isoleucyl-L-proline] [134448-10-5], C ₁₈ H ₂₉ N ₃ O ₆ , F.W. 383.44, Powder, MDL MFCD00797531 | 1mg 10mg |
| J64737 | Cathepsin B Inhibitor IV [CA-074 ME, (L-3-trans-(Propylcarbamoyl)oxirane-2-carbonyl)-L-isoleucyl-L-proline methyl ester] [147859-80-1], C ₁₉ H ₃₁ N ₃ O ₆ , F.W. 397.46, Powder, MDL MFCD03452890 | 1mg 10mg |
| J65957 | Cathepsin G Inhibitor I ▲ [429676-93-7], C ₃₆ H ₃₃ N ₂ O ₆ P, F.W. 620.60, Solid | 1mg 10mg |
| J63798 | Cathepsin G Substrate, 98+% [N-Methoxysuccinyl-Ala-Ala-Pro-Met p-nitroanilide, MeOSuc-Ala-Ala-Pro-Met-pNA] [70967-91-8], C ₂₇ H ₃₈ N ₆ O ₈ S, F.W. 622.69, Powder | 25mg |
| Application(s): Suc-Ala-Ala-Pro-Phe-pNA. Colorimetric substrate for chymotrypsin, human leukocyte cathepsin G, and peptidyl prolyl isomerase | | |
| J64082 | Cathepsin K Substrate (fluorogenic) [Z-Leu-Arg-7-amido-4-methylcoumarin, Z-LR-AMC] C ₂₃ H ₃₈ N ₆ O ₆ , F.W. 578.65, Solid | 10mg 25mg |
| J64690 | Cdc2-Like Kinase Inhibitor, TG003 ▲ [Clk Inhibitor, TG003] [300801-52-9], C ₁₃ H ₁₅ N ₃ O ₂ S, F.W. 249.33, Solid, MDL MFCD00624584 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5mg 50mg |
| CDI, see N,N'-Carbonyldiimidazole, A14688, p. 147 | | |
| J64252 | Cefaclor [Panoral, (R)-3-Chloro-7-((S)-2-amino-2-phenylacetamido)-3-cephem-4-carboxylic acid] [53994-73-3], C ₁₅ H ₁₄ ClN ₂ O ₄ S, F.W. 367.81, Powder, Merck 14 ,1912, EINECS 258-909-5, RTECS XI0363000, BRN 8176092, MDL MFCD00151471 ! H:H334-H317, P:P285-P261-P280-P302+P352-P321-P501a | 1g 10g |
| J65274 | Cefazolin sodium salt ▲ [Cefamedin] [27164-46-1], C ₁₄ H ₁₄ N ₆ NaO ₄ S ₃ , F.W. 476.49, Powder, m.p. 170-172°, Merck 14 ,1917, EINECS 248-278-4, RTECS XI0390000, BRN 3585038, MDL MFCD00056883 ! H:H334-H317, P:P285-P261-P280-P302+P352-P321-P501a | 1g 5g |

| Stock # | Description | Size |
|---------|---|-------|
| J65185 | Cefoperazone sodium salt | 1g |
| | [Cefobid sodium salt, Cefazone sodium salt] [62893-20-3], C ₂₆ H ₂₆ N ₃ NaO ₆ S ₂ , F.W. 667.65, Powder, Merck 14,1930, EINECS 263-751-5, RTECS XI0374000, BRN 4902135, MDL MFCD07793331 | 5g |
| | ⚠ H:3334-H317, P:P285-P261-P280-P302+P352-P321-P501 | 25g |
| J62690 | Cefotaxime sodium salt | 1g |
| | [64485-93-4], C ₁₆ H ₁₆ N ₃ NaO ₆ S ₂ , F.W. 477.40, Powder, Merck 14,1933, EINECS 264-915-9, RTECS XI0250000, BRN 5711411, MDL MFCD00079073 | 5g |
| | ⚠ H:3334-H317, P:P285-P261-P280-P302+P352-P321-P501a | 25g |
| | Celixel , see Candesartan, 99%, J62818, p. 145 | |
| J65943 | Celiprolol hydrochloride [NSC 324509, Corliprol] [57470-78-7], C ₂₀ H ₃₄ ClN ₃ O ₄ , F.W. 415.95, Crystalline solid, EINECS 260-752-2, RTECS YR6560000 | 10mg |
| | Celite [®] , see Filter aid, L14552, p. 221 | |
| A14553 | D-(+)-Cellobiose, 98+% [4-O-β-Glucopyranosyl-D-glucose] [528-50-7], C ₁₂ H ₂₂ O ₁₁ , F.W. 342.30, m.p. 234° dec., [α] _D ²⁰ +34° (c=10 in water, 15h), Merck 14,1961, EINECS 208-436-5, BRN 93795, MDL MFCD00136034, † | 5g |
| |  | 25g |
| | | 100g |
| L08780 | D-Cellobiose octaacetate [4-O-β-Glucopyranosyl-D-glucose octaacetate] [5346-90-7], C ₂₈ H ₃₈ O ₁₉ , F.W. 678.59, m.p. 224-231°, [α] _D ²⁰ +40° (c=1 in chloroform), Merck 14,1961, EINECS 226-304-5, BRN 79280, MDL MFCD00009600 | 5g |
| |  | 25g |
| | | |
| | Cellosolve [®] , see 2-Ethoxyethanol, A16100, p. 214 | |
| J64019 | Cellulose, chromatographically purified, T. reesei [EC 3.2.1.4, 1,4-(1,3;1,4)-β-D-Glucan-4-glucanohydrolase] [9012-54-8], Lyophilized powder, EINECS 232-734-4, RTECS FJ5375000, † | 250mg |
| | Application(s): Converts crystalline, amorphous, and chemically-derived celluloses quantitatively to glucose | 1g |
| | | |
| A17730 | Cellulose, microcrystalline [9004-34-6], Merck 14,1965, EINECS 232-674-9, MDL MFCD00081512, † | 500g |
| | ⚠ H:3335, P:P261-P304+P340-P312-P405+P403+P233-P501a | 2.5kg |
| | | 10kg |
| J64196 | Centrophoxine hydrochloride, 98% [Meclufenoxate hydrochloride, 2-[2-(Dimethylamino)ethyl] 2-(4-chlorophenoxy)acetate hydrochloride] [3685-84-5], C ₁₂ H ₁₆ ClNO ₃ ·HCl, F.W. 294.17, Powder, m.p. 135-145°, EINECS 222-975-3, RTECS AG0440000, MDL MFCD00012533 | 5g |
| | Application(s): Ester of dimethylethanolamine and 4-chlorophenoxyacetic acid; activates acetylcholinesterase activity in hippocampus of aged rats | 25g |
| | | 100g |
| J63172 | Cephalexin hydrate, 97+% [15686-71-2], C ₁₆ H ₁₇ N ₃ O ₅ ·xH ₂ O, F.W. 347.39(anhy), Powder, Merck 14,1974, EINECS 239-773-6, RTECS XI0350000, BRN 965503, MDL MFCD00167148 | 5g |
| | ⚠ H:3334-H317, P:P285-P261-P280-P302+P352-P321-P501a | 25g |
| | Application(s): Colorimetric substrate for chymotrypsin, human leukocyte cathepsin G, and peptidyl prolyl isomerase | |
| J65607 | Cephalothin sodium salt [7-(2-Thienylacetamido)cephalosporanic acid sodium salt, Cephalotin sodium salt] [58-71-9], C ₁₆ H ₁₅ N ₃ NaO ₆ S ₂ , F.W. 418.42, Powder, Merck 14,1982, EINECS 200-394-6, RTECS XI038830, BRN 4120706, MDL MFCD00072025 | 1g |
| | ⚠ H:3334-H317, P:P285-P261-P280-P302+P352-P321-P501 | 5g |
| | | |
| 33254 | Cerium(IV) ammonium nitrate, ACS, 98.5% min [16774-21-3], (NH ₄) ₂ Ce(NO ₃) ₆ , F.W. 548.23, Granular, Merck 14,1992, Fieser 1,120 13,67 14,74 15,70 16,66 17,68 18,85 19,67 20,73 21,90, Solubility: Soluble in water and alcohol, UN1477, EINECS 240-827-6, MDL MFCD00151121, † | 100g |
| | Maximum level of impurities: Insoluble in dilute sulfuric acid 0.05%, Cl 0.01%, PO ₄ 0.02%, Fe 0.005% | 500g |
| | ⚠ H:272-H315-H319-H335, P:P221-P210-P305+P351+P338-P302+P352-P405-P501a | 2kg |
| | Application(s): Analytical chemistry, as an oxidant for organic compounds, as a polymerization catalyst for olefins, and as a scavenger in the manufacture of azides | |


| Stock # | Description | Size |
|---------------|---|---------------------|
| J64538 | Cerulenin, 98% [(2 <i>R</i> ,3 <i>S</i> , <i>E</i> , <i>E</i>)-2,3-Epoxy-4-oxo-7,10-dodecadienamido] [17397-89-6], C ₂₂ H ₃₇ NO ₃ , F.W. 223.27, Powder, Merck 14,2004, EINECS 241-424-8, RTECS JR1670000, BRN 4140423, MDL MFCD00077686 ! H:H302, P:P264-P270-P301+P312-P330-P501 | 5mg 10mg |
| 10018 | Cesium chloride, 99.9% (metals basis) ■ [7647-17-8], CsCl, F.W. 168.36, Crystalline, m.p. 646°, b.p. 1303°, d. 3.99, n _D ²⁰ 1.6418, Merck 14,2011, EINECS 231-600-2, RTECS FK9625000, MDL MFCD00010955, † Application(s): For density gradient work to separate and purify proteins | 25g 100g |
| J65950 | Cesium chloride, ultrapure, 99.9% (metals basis) ■ [7647-17-8], CsCl, F.W. 168.36, Crystalline, m.p. 646°, b.p. 1303°, d. 3.99, n _D ²⁰ 1.6418, Merck 14,2011, EINECS 231-600-2, RTECS FK9625000, MDL MFCD00010955, † | 25g 100g |
| 89188 | Cesium chloride, 99.999+% (metals basis) ■ [7647-17-8], CsCl, F.W. 168.36, Powder, m.p. 646°, b.p. 1303°, d. 3.99, n _D ²⁰ 1.6418, Merck 14,2011, EINECS 231-600-2, RTECS FK9625000, MDL MFCD00010955, † | 10g 50g |
| 13233 | Cesium hydroxide hydrate, 99.9% (metals basis) △ ■ [12260-45-6], CsOH·xH ₂ O (15-20% H ₂ O), F.W. 149.91(anhy), Crystalline, Merck 14,2013, Fieser 21,96, UN2682, EINECS 244-344-1, MDL MFCD00010964, † ! H:H314-H302, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 5g 25g 100g |
| 12884 | Cesium nitrate, 99.8% (metals basis) ■ [7789-18-6], CsNO ₃ , F.W. 194.91, Crystalline, m.p. 414°, b.p. dec., d. 3.68, n _D ²⁰ 1.55, Merck 14,2015, Solubility: Soluble in 5 parts cold and 0.5 parts boiling water. Soluble in acetone. Slightly soluble in alcohol, UN1451, EINECS 232-146-8, MDL MFCD00010963, † H:H272, P:P221-P210-P220-P280-P370+P378a-P501a Application(s): Preparation of Cs compounds | 50g 250g |
| J63549 | Cetirizine dihydrochloride, 99+% [83881-52-1], C ₂₁ H ₂₅ ClN ₂ O ₂ ·2HCl, F.W. 461.82, Solid, Merck 14,2022, RTECS AG0980000, MDL MFCD00941428 ! H:H302, P:P264-P270-P301+P312-P330-P501 Application(s): Histamine H-1 receptor antagonist. Inhibits activation of eosinophils and neutrophils | 5g 10g 25g |
| | Cetrimonium bromide , see (1-Hexadecyl)trimethylammonium bromide, A15235, p. 244 Cetyl alcohol , see 1-Hexadecanol, A11180, p. 244 Cetylpyridinium chloride monohydrate , see (1-Hexadecyl)pyridinium chloride monohydrate, A13499, p. 244 Cetyltrimethylammonium bromide , see (1-Hexadecyl)trimethylammonium bromide, A15235, p. 244 | |
| J63801 | CGS 12066B dimaleate, 98+% [109028-10-6], C ₁₇ H ₁₇ F ₃ N ₄ ·2(C ₄ H ₄ O ₄), F.W. 566.49, Solid, m.p. 126-127° Application(s): 5-HT-1B full agonist | 10mg 50mg |
| J61313 | CGS 15943, 99+% [9-Chloro-2-(2-furanyl)-[1,2,4]triazolo[1,5-c]quinazolin-5-amine] [104615-18-1], C ₁₅ H ₈ ClN ₄ O, F.W. 285.69, Solid, MDL MFCD01529897 Application(s): Potent adenosine receptor antagonist | 10mg 50mg |
| J60793 | CGS 21680 hydrochloride, 99+% [124182-57-6], C ₂₃ H ₂₉ N ₇ O ₆ ·HCl, F.W. 535.98, Solid, MDL MFCD11045878 Application(s): A-2A Adenosine receptor agonist | 5mg 10mg 50mg |
| A14734 | trans-Chalcone, 97% [2-(Benzylidene)acetophenone, 1,3-Diphenyl-2-propen-1-one] [614-47-1], C ₁₅ H ₁₂ O, F.W. 208.26, m.p. 55-57°, b.p. 208°/25mm, Merck 14,2037, EINECS 210-383-8, RTECS UD5576750, BRN 509985, MDL MFCD00003082, † ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): Inhibits lung and forestomach carcinogenesis | 100g 500g |
| B21927 | CHAPS, 98+% ■ [3-[(3-Cholamidopropyl)dimethylammonio]-1-propanesulfonate] [75621-03-3], C ₂₆ H ₅₉ N ₃ O ₇ S, F.W. 614.88, m.p. 156-158° dec., MDL MFCD00012116 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): Buffer; zwitterionic nondenaturing detergent for solubilizing membrane proteins | 1g 5g 25g |
| J60580 | CHAPS lysis buffer Liquid, Note: Contains 50mM Tris-HCl (pH 7.4), 110mM NaCl, 5mM EDTA and 1% CHAPS Application(s): For cell lysis and protein extraction | 50ml 100ml |
| J60812 | CHAPS lysis buffer (2X) Liquid, Note: Contains 100mM Tris-HCl (pH 7.4), 220mM NaCl, 10mM EDTA and 2% CHAPS | 25ml 50ml |













| Stock # | Description | Size |
|--|--|---------------------|
| J62906 | Chelerythrine chloride, 99+% [Toddaline] [3895-92-9], C ₂₂ H ₁₈ CINO ₄ , F.W. 383.82, Solid, Merck 14,2051, EINECS 223-444-9, RTECS FL9200000, MDL MFCD00060717 ! H:H302-H312-H332-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5mg 10mg 25mg |
| Application(s): A natural benzophenanthridine alkaloid. Inhibits protein kinase C. Induces apoptosis in leukemia cells | | |
| L00782 | Chelidamic acid hydrate, 95% [1,4-Dihydro-4-oxo-2,6-pyridinedicarboxylic acid hydrate, 4-Hydroxypyridine-2,6-dicarboxylic acid hydrate] [138-60-3], C ₇ H ₅ NO ₅ ·xH ₂ O, F.W. 183.12(anhy), m.p. ca 260° dec., EINECS 205-335-8, MDL MFCD00066478 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 1g 5g |
|  | | |
| J65184 | Chemotactic Peptide [N-Formyl-Met-Leu-Phe, fMLP] [59880-97-6], C ₂₁ H ₃₁ N ₃ O ₅ S, F.W. 437.55, Lyophilized powder, RTECS SQ7342000, BRN 2315783, MDL MFCD00036780 | 25mg |
| J60364 | Chenodeoxycholic acid [474-25-9], C ₂₄ H ₄₀ O ₄ , F.W. 392.57, Needle crystals, m.p. 164-168°, Merck 14,2054, EINECS 207-481-8, RTECS FZ1980000, BRN 3219887, MDL MFCD00064142 ! H:H361, P:P281-P201-P202-P308+P313-P405-P501a | 5g 25g |
| Application(s): Bile acid that induces apoptosis through protein kinase C signaling pathways | | |
| A18047 | CHES, 99% ■ [2-(Cyclohexylamino)ethanesulfonic acid] [103-47-9], C ₈ H ₁₇ NO ₃ S, F.W. 207.29, m.p. >300°, Merck 14,2055, EINECS 203-115-6, BRN 2967601, MDL MFCD00003835, † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 Biological buffer, pKa = 9.3 at 20°: <i>Biochemistry</i> , 5, 467 (1966). | 25g 100g 500g |
| Application(s): Zwitterionic buffer useful in pH range 8.6 to 10.0 | | |
| J61492 | CHES, 0.5M buffer soln, pH 8.5 [103-47-9], Liquid, † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 100ml 250ml |
| J63670 | CHES, 0.5M buffer soln, pH 9.0 [103-47-9], Liquid, † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 100ml 250ml |
| J62333 | CHES, 0.5M buffer soln, pH 9.5 [103-47-9], Liquid, † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 100ml 250ml |
| J63419 | CHES, 0.5M buffer soln, pH 10.0 [103-47-9], Liquid, † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 100ml 250ml |
| A14242 | Chicago Sky Blue 6B [C.I. 24410, Direct Blue 1] [2610-05-1], C ₂₄ H ₂₄ N ₆ Na ₄ O ₁₆ S ₄ , F.W. 992.79, EINECS 220-026-8, RTECS QJ6430000, MDL MFCD00004020, † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 25g 100g 500g |
| Application(s): Inhibits L-glutamate uptake | | |
| CHIR-258 , see Dovitinib, J61776, p. 201 | | |
| J61206 | Chitin [1398-61-4], C ₁₀ H ₁₉ NO ₅ , F.W. 233.26, Powder, Merck 14,2065, EINECS 215-744-3, MDL MFCD00466914, † | 100g 500g |
| Application(s): A long-chain polymer of a N-acetylglucosamine | | |
| J64143 | Chitosan, 85% deacetylated [Poly(D-glucosamine), Deacetylated chitin] [9012-76-4], Powder, RTECS FM6300000, MDL MFCD00161512, † | 50g 250g 500g |
| A11492 | α-Chloralose, 98+%, β anomer ca 15% [1,2-O-(2,2,2-Trichloroethylidene)-α-D-glucofuranose] [15879-93-3], C ₆ H ₁₁ Cl ₃ O ₅ , F.W. 309.53, m.p. 180-184°, [α] _D ²⁰ +19° (c=2 in ethanol), Merck 14,2072, EINECS 240-016-7, RTECS FM9450000, BRN 85418, MDL MFCD00005542, † ! H:H302-H332, P:P261-P264-P304+P340-P301+P312-P312-P501a | 25g 100g |
| Application(s): Used as sedative and anesthetic in lab animals | | |




| Stock # | Description | Size |
|---------------|--|-----------------------------------|
| J61964 | Chlorambucil, 98% [4-(4-[Bis(2-chloroethyl)amino]phenyl)butyric acid] [305-03-3], C ₁₈ H ₁₉ Cl ₂ NO ₂ , F.W. 304.21, Powder, m.p. 66-67°, Merck 14,2073, UN2811, EINECS 206-162-0, RTECS ES7525000, BRN 999011, MDL MFCD00021783  H:H301+H350-H315-H319-H335, P:P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a | 5g 25g |
| | Application(s): Alkylates DNA; induces apoptosis in chronic lymphocytic leukemia cells | |
| 42374 | Chloramine-T trihydrate, ACS, 98.0-103.0%  [7080-50-4], CH ₃ C ₆ H ₄ SO ₂ N(Cl)Na·3H ₂ O, F.W. 281.69 (227.67anhy), Crystalline, m.p. 167-170°, f.p. 192° (377°F), Merck 14,2075, Fieser 4,75 7,58 8,83 9,101 10,85 11,118 13,70 15,79 20,103 21,125, UN3263, EINECS 204-854-7, RTECS XT5616800, BRN 3924168, MDL MFCD00149066, † Maximum level of impurities: pH of a 5% solution 8.0-10.0 @25°, Suitable for determination of bromide P.T., Clarity of aqueous solution, P.T., Insoluble in alcohol 1.5%  H:H334-H314-H302, P:P260-P280-P303+P361+P353-P305+P351+P338-P310-P420g | 100g 500g |
| | Application(s): Reagent for selective oxidation of methionine | |
| B20841 | Chloramphenicol, 99+% [Chloromycetin] [56-75-7], C ₁₁ H ₁₂ Cl ₂ N ₂ O ₅ , F.W. 323.14, m.p. 149-152°, [α] _D ²⁰ +19° (c=6 in ethanol), Merck 14,2077, EINECS 200-287-4, RTECS AB6825000, BRN 2225532, MDL MFCD00078159, †  H:H350-H361, P:P281-P201-P202-P308+P313-P405-P501a  | 25g 100g |
| | Application(s): Inhibitor of translation on the 50S subunit at the peptidyltransferase step | |
| A10493 | Chloranilic acid, 98+% [2,5-Dichloro-3,6-dihydroxy-1,4-benzoquinone] [87-88-7], C ₆ H ₂ Cl ₂ O ₄ , F.W. 208.99, m.p. >300° dec., Merck 14,2079, EINECS 201-780-7, RTECS DK4005000, BRN 1875040, MDL MFCD00001596, †  H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Reagent for determination of Ca, Sr, Zr and Mo.  | 25g 100g 500g |
| | Application(s): Reagent for determination of Ca, Sr, Zr and Mo. | |
| A13259 | Chlorazol Black E [Azo Black, C.I. 30235] [1937-37-7], C ₂₃ H ₁₂ N ₄ Na ₂ O ₂ S ₂ , F.W. 781.73, EINECS 217-710-3, RTECS QJ6160000, MDL MFCD00066363, †  H:H350-H361d, P:P281-P201-P202-P308+P313-P405-P501a  | 10g 50g |
| | Application(s): Antiseptic and disinfectant agent | |
| 41385 | Chlorhexidine digluconate, 20% w/v aq. soln., non-sterile [18472-51-0], C ₂₂ H ₃₀ Cl ₂ N ₁₀ ·2C ₆ H ₁₂ O ₇ , F.W. 897.76, Liquid, d. 1.06, EINECS 242-354-0, MDL MFCD00083599, †  H:H302, P:P264-P270-P301+P312-P330-P501  | 25ml 100ml 500ml 4x500ml |
| | Application(s): Skeletal muscle relaxant | |
| J62934 | Chlormezanone, 98+% [80-77-3], C ₁₁ H ₁₂ ClNO ₂ S, F.W. 273.74, Powder, m.p. 114°, Merck 14,2106, EINECS 201-307-4, RTECS XJ1050000, MDL MFCD00143951  H:H302, P:P264-P270-P301+P312-P330-P501 | 5g 25g |
| | Application(s): Skeletal muscle relaxant | |
| A11482 | Chloroacetic acid, 99%  [Monochloroacetic acid] [79-11-8], ClCH ₂ CO ₂ H, F.W. 94.50, m.p. 60-63°, b.p. 189°, f.p. 126° (258°F), d. 1.404, Merck 14,2112, Solubility: Soluble in water, alcohols, benzene, chloroform, ether, UN1751, EINECS 201-178-4, RTECS AF8575000, BRN 605438, MDL MFCD00002683, †  H:H301+H311-H331-H314-H400, P:P301+P310-P303+P361+P353-P305+P351+P338-P361-P405-P501a A convenient one-pot alternative to the Knoevenagel or Horner-Wadsworth-Emmons reactions for the synthesis of α-unsubstituted cinnamic acids involves the reaction of chloroacetic acid with dimethyl phosphite in the presence of sodium methoxide, and treatment of the resulting phosphonoacetate salt with a benzaldehyde: <i>J. Org. Chem.</i> , 46 , 2514 (1981):  | 250g 1kg |
| | Application(s): Reagent for the synthesis of α-unsubstituted cinnamic acids | |
| 41724 | Chloroacetic acid, ACS, 99+% [79-11-8], ClCH ₂ CO ₂ H, F.W. 94.50, Crystalline, m.p. 60-63°, b.p. 189°, f.p. 126° (258°F), d. 1.404, Merck 14,2112, UN1751, EINECS 201-178-4, RTECS AF8575000, BRN 605438, MDL MFCD00002683, † Maximum level of impurities: Insoluble matter 0.01%, Residue after ignition 0.02%, Carbonyl compounds (as acetone) 0.02%, Other carbonyl compounds 0.01%, Cl 0.01%, SO ₄ 0.02%, Heavy Metals (as Pb) 0.001%, Fe 0.002%, Substances darkened by sulfuric acid P.T.  H:H301+H311-H331-H314-H400, P:P301+P310-P303+P361+P353-P305+P351+P338-P361-P405-P501a | 100g 500g 4x500g |







| Stock # | Description | Size |
|---------------|--|--------------|
| A15846 | Chloroacetyl chloride, 98% | 25ml |
| | [79-04-9], ClCH ₂ COCl, F.W. 112.94, m.p. -22°, b.p. 105-106°, d. 1.417, n _D ²⁰ 1.4530, Merck 14,2067 , Fieser 1,130 250ml | |
| | [146-77-0], C ₂ H ₃ ClO, F.W. 98.96, m.p. -117.6, RTECS AO6475000, BRN 6054399, MDL MFCD00000725, † 500ml | |
| | H:H301-EUH029-H311-H331-H372-H314-H400-EUH014, P:P301+P310-P303+P361+P353-P305+P351+P338-P361-P405-P501a Reagent for the protection of amines as their chloroacetamides. The protecting group can be removed by reaction with thiourea derivatives, forming 2-thiazolidin-4-ones as by-products: <i>J. Am. Chem. Soc.</i> , 90 , 4508 (1968); <i>Gazz. Chim. Ital.</i> , 98 , 1261 (1968). Side reactions can be minimized by using Piperidine-1-thiocarboxamide, L12445 , as the thiourea: <i>Angew. Chem. Int. Ed.</i> , 10 , 75 (1971). Also used for the protection of alcohols as their chloroacetates: <i>Tetrahedron Lett.</i> , 251 (1979). They are hydrolyzed very readily in the presence of many other ester functions: <i>J. Am. Chem. Soc.</i> , 86 , 118 (194); <i>J. Chem. Soc., Perkin 1</i> , 934 (1975); or can be cleaved with thiourea: <i>Tetrahedron Lett.</i> , 251 (1979), ethylenediamine, or mercaptoethylamine: <i>J. Org. Chem.</i> , 35 , 1940 (1970). | 2.5L |
| J63810 | 2-Chloroadenosine [2-CADO, 6-Amino-2-chloropurine riboside] [146-77-0], C ₁₀ H ₁₂ ClN ₅ O ₄ , F.W. 301.69, Powder, EINECS 205-678-3, BRN 43957, MDL MFCD00005734 1g | 250mg |
| | H:H302, P:P264-P270-P301+P312-P330-P501 | |
| | Application(s): A selective A1-adenosine receptor agonist. Induces apoptosis | |
| J60927 | 2-Chloro-2'-arabino-fluoro-2'-deoxyadenosine, 99+% [Clotarabine] | 50mg |
| | [123318-82-1], C ₁₀ H ₁₁ ClFN ₅ O ₅ , F.W. 303.68, Powder, Merck 14,2372 , UN2811, RTECS UD7473000, MDL MFCD00871077 100mg | |
| | H:H301, P:P264-P270-P301+P310-P321-P405-P501a 250mg | |
| | Application(s): A purine nucleoside anti-metabolite. Toxic to nondividing lymphocytes and monocytes | |
| A10832 | 2-Chlorobenzoic acid, 98+% [118-91-2], C ₇ H ₅ ClO ₂ , F.W. 156.57, m.p. 138-142°, b.p. 284-286°, f.p. 173°(343°F), d. 1.544, Merck 14,2124 , EINECS 204-285-4, RTECS DG4976000, BRN 907340, MDL MFCD00002412, † | 250g |
| | H:H319-H335, P:P305+P351+P338 The Ullmann-Goldberg reaction with anilines to give diarylamines can be carried out with Cu powder in water: <i>Synth. Commun.</i> , 23 , 1447 (1993). The reaction in DMF has been shown to be greatly accelerated by ultrasonic irradiation: <i>Synth. Commun.</i> , 19 , 2077 (1989). Ullmann-Goldberg reaction with phenols to give diaryl ethers gives improved results with pyridine as a co-catalyst: <i>Synth. Commun.</i> , 25 , 1077 (1995). | 1kg |
| | | 5kg |
| | | |
| A15135 | 4-Chlorobenzoic acid, 98+% [74-11-3], C ₇ H ₅ ClO ₂ , F.W. 156.57, m.p. 239-243°, b.p. 275°, f.p. 238°(460°F), d. 1.54, Merck 14,2125 , EINECS 200-805-9, RTECS DG4976010, BRN 907196, MDL MFCD00002531, † | 250g |
| | H:H302-H315-H319-H335, P:P280h-P305+P351+P338 | 1kg |
| | | |
| | | |
| | 5-Chloro-2-benzoxazinone , see 5-Chloro-2(3H)-benzoxazolone, B24507, p. 155 | |
| B24507 | 5-Chloro-2(3H)-benzoxazolone, 99% [5-Chloro-2-benzoxazinone, Chloroxazolone] | 50g |
| | [95-25-0], C ₇ H ₅ ClN ₂ O ₂ , F.W. 169.57, m.p. 189-192°, Merck 14,2194 , EINECS 202-403-9, MDL MFCD00005717, † | 250g |
| | H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a 1kg | |
| | | |
| | 1-(4-Chlorobenzoyl)-5-methoxy-2-methyl-1H-indole-3-acetic acid , see Indomethacin, 99+%, J63255, p. 256 | |
| | N-4-Chlorobenzyl-N',N'-dimethyl-N-(2-pyridyl)ethylenediamine , see Chloropyramine hydrochloride, J60350, p. 159 | |
| | 5-(2-Chlorobenzyl)-4,5,6,7-tetrahydrothieno[3,2-c]pyridine hydrochloride , see Ticlopidine hydrochloride, J63971, p. 370 | |
| | 3-Chloro-10,11-dihydro-N,N-dimethyl-5H-dibenz[b,f]azepine-5-propanamine hydrochloride , see Clomipramine hydrochloride, J62485, p. 165 | |
| | 5-Chloro-2,4-dihydropyrimidine , see 5-Chlorouracil, A11084, p. 160 | |
| | 6-Chloro-2,4-dihydropyrimidine , see 6-Chlorouracil, L01875, p. 160 | |
| B21964 | 4-Chloro-3,5-dimethylphenol, 98+% [4-Chloro-3,5-xyleneol, PCMX] | 100g |
| | [88-04-0], C ₈ H ₇ ClO, F.W. 156.61, m.p. 112-116°, b.p. ca 246°, f.p. 138°(280°F), Merck 14,2176 , EINECS 201-793-8, RTECS ZE6850000, BRN 1862539, MDL MFCD00002324, † | 500g |
| | H:H315-H319-H317, P:P261-P280-P305+P351+P338-P302+P352-P321-P501a | |
| | | |
| | 8-Chloro-1,3-dimethyl-2,6-purinedione , see 8-Chlorotheophylline, A12408, p. 160 | |
| A13774 | 1-Chloro-2,4-dinitrobenzene, 98% [2,4-Dinitrochlorobenzene] | 100g |
| | [97-00-7], C ₆ H ₃ ClN ₂ O ₄ , F.W. 202.55, m.p. 48-52°, b.p. 314-316°, f.p. 186°(366°F), d. 1.700, Merck 14,2136 , UN3441, EINECS 202-551-4, RTECS CZ0525000, BRN 613161, MDL MFCD00007075, † | 500g |
| | H:H301-H311-H331-H373-H400-H410, P:P260-P301+P310-P361-P302+P352-P405-P501a 2.5kg | |
| | The doubly-activated chloro-substituent is readily displaced by nucleophiles, e.g.: Ammonium acetate to give 2,4-dinitroaniline: <i>Org. Synth. Coll.</i> , 2 , 221 (1943); or with ammonia gas in toluene in the presence of TBAB which improves the solubility of ammonia in the organic medium and accelerates the reaction: <i>J. Chem. Soc., Chem. Commun.</i> , 1267 (1987). Benzyl mercaptan to give the thioether: <i>Org. Synth. Coll.</i> , 5 , 474 (1973). Iodide ion to give 2,4-dinitro-1-iodobenzene: <i>Org. Synth. Coll.</i> , 5 , 478 (1973). Nitrite in toluene (phase-transfer) to give 1,2,4-trinitrobenzene (caution!): <i>J. Org. Chem.</i> , 56 , 4967 (1991). | |

| Stock # | Description | Size | | | | | | | | | | | | |
|---------|---|--------------------------|------|------|------|-----|-----|---|------|------|------|------|------|--|
| | 2-(4-[(1Z)-4-Chloro-1,2-diphenyl-1-butenyl]phenoxy)-N,N-dimethylethanamine , see Toremfifene, 98+%, J63803, p. 371 | | | | | | | | | | | | | |
| | (±)-1-Chloro-2,3-epoxypropane , see (±)-Epichlorohydrin, A15823, p. 208 | | | | | | | | | | | | | |
| J65111 | 7-(2-Chloroethyl)theophylline, 97% [1,3-Dimethyl-7-(β-chloroethyl)xanthine] [5878-61-5], C ₉ H ₁₁ ClN ₂ O ₂ , F.W. 242.66, Powder, m.p. 122-127°, EINECS 227-553-2, RTECS XH5090000, MDL MFCD00005760 | 1g 5g | | | | | | | | | | | | |
| B21209 | 1-Chloro-2-fluorobenzene, 98+% [2-Chlorofluorobenzene] [348-51-6], C ₆ H ₄ ClF, F.W. 130.55, m.p. -43°, b.p. 137-138°, f.p. 31° (87°F), d. 1.242, n _D ²⁰ 1.5010, UN1993, EINECS 206-476-8, BRN 1855301, MDL MFCD00000533, †  H:H226-H332-H315-H319-H335, P:P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a Benzynes precursor, compare 1-Bromo-2-fluorobenzene, A10635 . Lithiation at low temperatures with n-BuLi occurs ortho to F; subsequent reaction with electrophiles provides access to mixed dihalo derivatives such as 3-chloro-2-fluorobenzoic acid: <i>Tetrahedron Lett.</i> , 36 , 881 (1995). Improved yields are obtained by the use of the superbasic combination of n-BuLi and KO-t-Bu: <i>Tetrahedron Lett.</i> , 37 , 6551 (1996). | 25g 100g 500g | | | | | | | | | | | | |
| 32614 | Chloroform, ACS, 99.8+% [Trichloromethane] [67-66-3], CHCl ₃ , F.W. 119.38, Liquid, m.p. -63°, b.p. 60.5-61.5°, d. 1.492, n _D ²⁰ 1.4460, Merck 14,2141, Fieser 1,29 3,140 4,22 5,28 8,92 12,517 15,84, UN1888, EINECS 200-663-8, RTECS FS9100000, BRN 1731042, MDL MFCD00000826, † Maximum level of impurities: Color (APHA) 10, Residue after evaporation 0.001%, Acetone and aldehyde P.T. (limit about 0.005% as (CH ₃) ₂ CO), Acid and chlorine P.T., Free chlorine (Cl) P.T., Pb 0.05ppm, Substances darkened by sulfuric acid P.T. H:H351-H373-H302-H315, P:P260-P280-P302+P352-P321-P405-P501a | 1L 4L 4x4L | | | | | | | | | | | | |
| 22920 | Chloroform, HPLC Grade, 99.5+% min [67-66-3], CHCl ₃ , F.W. 119.38, Liquid, m.p. -63°, b.p. 60.5-61.5°, d. 1.492, n _D ²⁰ 1.4460, Merck 14,2141, Fieser 1,29 3,140 4,22 5,28 8,92 12,517 15,84, UN1888, EINECS 200-663-8, RTECS FS9100000, BRN 1731042, MDL MFCD00000826, Note: Filtered through 0.2μ filters., † Maximum level of impurities: Evaporation residue 3ppm, Chlorinated pesticides 5ppt, H ₂ O 0.03% H:H351-H373-H302-H315, P:P260-P280-P302+P352-P321-P405-P501a UV absorption - 1cm cell vs H₂O | 1L 4L 4x1L | | | | | | | | | | | | |
| | <table border="1"> <thead> <tr> <th>λ(nm)</th> <th>290</th> <th>270</th> <th>260</th> <th>255</th> <th>245</th> </tr> </thead> <tbody> <tr> <td>A</td> <td>0.01</td> <td>0.02</td> <td>0.05</td> <td>0.15</td> <td>1.00</td> </tr> </tbody> </table> | λ(nm) | 290 | 270 | 260 | 255 | 245 | A | 0.01 | 0.02 | 0.05 | 0.15 | 1.00 | |
| λ(nm) | 290 | 270 | 260 | 255 | 245 | | | | | | | | | |
| A | 0.01 | 0.02 | 0.05 | 0.15 | 1.00 | | | | | | | | | |
| 43685 | Chloroform, HPLC Grade, 99.5+% min, stab. with amylene [67-66-3], CHCl ₃ , F.W. 119.38, Liquid, m.p. -63°, b.p. 60.5-61.5°, d. 1.492, n _D ²⁰ 1.4460, Merck 14,2141, Fieser 1,29 3,140 4,22 5,28 8,92 12,517 15,84, UN1888, EINECS 200-663-8, RTECS FS9100000, BRN 1731042, MDL MFCD00000826, † H:H351-H373-H302-H315, P:P260-P280-P302+P352-P321-P405-P501a UV absorption - 1cm cell vs H₂O | 1L 4L 4x1L 4x4L | | | | | | | | | | | | |
| | <table border="1"> <thead> <tr> <th>λ(nm)</th> <th>290</th> <th>270</th> <th>260</th> <th>255</th> <th>245</th> </tr> </thead> <tbody> <tr> <td>A</td> <td>0.01</td> <td>0.02</td> <td>0.05</td> <td>0.15</td> <td>1.00</td> </tr> </tbody> </table> | λ(nm) | 290 | 270 | 260 | 255 | 245 | A | 0.01 | 0.02 | 0.05 | 0.15 | 1.00 | |
| λ(nm) | 290 | 270 | 260 | 255 | 245 | | | | | | | | | |
| A | 0.01 | 0.02 | 0.05 | 0.15 | 1.00 | | | | | | | | | |
| 32442 | Chloroform, Spectrophotometric Grade, 99.5+% [67-66-3], CHCl ₃ , F.W. 119.38, Liquid, m.p. -63°, b.p. 60.5-61.5°, d. 1.492, n _D ²⁰ 1.4460, Merck 14,2141, Fieser 1,29 3,140 4,22 5,28 8,92 12,517 15,84, UN1888, EINECS 200-663-8, RTECS FS9100000, BRN 1731042, MDL MFCD00000826, Note: Meets ACS Spectrophotometric Requirements. Filtered through 0.2μ filters., † Maximum level of impurities: Evaporation residue 3ppm, Chlorinated pesticides 5ppt, H ₂ O 0.04% H:H351-H373-H302-H315, P:P260-P280-P302+P352-P321-P405-P501a UV absorption - 1cm cell vs H₂O | 1L 4L 4x1L | | | | | | | | | | | | |
| | <table border="1"> <thead> <tr> <th>λ(nm)</th> <th>290</th> <th>270</th> <th>260</th> <th>255</th> <th>245</th> </tr> </thead> <tbody> <tr> <td>A</td> <td>0.01</td> <td>0.02</td> <td>0.05</td> <td>0.15</td> <td>1.00</td> </tr> </tbody> </table> | λ(nm) | 290 | 270 | 260 | 255 | 245 | A | 0.01 | 0.02 | 0.05 | 0.15 | 1.00 | |
| λ(nm) | 290 | 270 | 260 | 255 | 245 | | | | | | | | | |
| A | 0.01 | 0.02 | 0.05 | 0.15 | 1.00 | | | | | | | | | |
| L14759 | Chloroform, ethanol-free, 99+%, stab. with ca 50 ppm amylene [Trichloromethane] [67-66-3], CHCl ₃ , F.W. 119.38, m.p. -63°, b.p. 60.5-61.5°, d. 1.492, n _D ²⁰ 1.4460, Merck 14,2141, Fieser 1,29 3,140 4,22 5,28 8,92 12,517 15,84, UN1888, EINECS 200-663-8, RTECS FS9100000, BRN 1731042, MDL MFCD00000826, † H:H351-H373-H302-H315, P:P260-P280-P302+P352-P321-P405-P501a | 500ml 1L 2.5L | | | | | | | | | | | | |
| | Chloroformic acid 9-fluorenylmethyl ester , see 9-Fluorenylmethyl chloroformate, A11683, p. 222 9-Chloro-2-(2-furanyl)-[1,2,4]triazolo[1,5-c]quinazolin-5-amine , see CGS 15943, 99+%, J61313, p. 152 4-Chloro-N-furfuryl-5-sulfamoylanthranilic acid , see Furosemide, 97+%, J61457, p. 229 | | | | | | | | | | | | | |






| Stock # | Description | Size |
|---------|--|--------------------|
| B21962 | Chlorogenic acid hemihydrate, 97% [6001-76-9], C ₁₆ H ₁₈ O ₉ ·0.5H ₂ O, F.W. 363.32 (354.31anhy), m.p. ca 208° dec., Merck 14,2142, EINECS 206-325-6, MDL MFCD00003862 | 1g 5g |
| | Application(s): An analog of caffeic acid | |
| |  | |
| J60457 | Chlorogenic acid [3-(3,4-Dihydroxycinnamoyl)quinic acid, 1,3,4,5-Tetrahydroxycyclohexanecarboxylic acid 3-(3,4-dihydroxycinnamate)] [327-97-9], C ₁₈ H ₁₆ O ₉ , F.W. 354.31, Powder, m.p. 210° dec., Merck 14,2142, EINECS 206-325-6, RTECS GU8480000, MDL MFCD00003862 | 250mg 1g 5g |
| | Application(s): An analog of caffeic acid | |
| | 6-Chloroguanine , see 2-Amino-6-chloropurine, A18195, p. 92 1-(3-Chloro-2-hydroxypropyl)-2-methyl-5-nitroimidazole , see Ornidazole, 99%, J63100, p. 308 7-Chloro-4-hydroxyquinoline-2-carboxylic acid , see 7-Chlorokynurenic acid, 99+%, J61359, p. 157 | |
| A18626 | 5-Chloroindole-2-carboxylic acid, 98% [10517-21-2], C ₈ H ₆ ClNO ₂ , F.W. 195.60, m.p. 287° dec., EINECS 234-050-1, RTECS NL5998400, BRN 153229, MDL MFCD00005613 | 1g 5g 25g |
| | ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Application(s): Potent antagonist at the glycine site of the NMDA receptor | |
| J61359 | 7-Chlorokynurenic acid, 99+% [7-Chloro-4-hydroxyquinoline-2-carboxylic acid] [18000-24-3], C ₁₀ H ₆ ClNO ₂ , F.W. 223.62, Powder, EINECS 241-913-6, MDL MFCD00069227 | 10mg 50mg |
| | Application(s): NMDA receptor antagonist at the glycine site | |
| J61283 | 7-Chlorokynurenic acid sodium salt, 99+% C ₁₀ H ₅ ClNNaO ₂ , F.W. 245.60, Powder, MDL MFCD12195840 | 10mg 50mg |
| | Application(s): NMDA receptor antagonist at the glycine site | |
| | 2 (3-Chloro-2-methylanilino)benzoic acid , see Tolfenamic acid, 99+%, J61256, p. 371 Chloromethylated styrene-divinylbenzene copolymer , see Merrifield Resin, L17027, p. 282 8-Chloro-11-(4-methyl-1-piperazinyloxy)-5H-dibenzo[b,e][1,4]-diazepine , see Clozapine, 98+%, J61583, p. 166 | |
| A11967 | Chloromethyl pivalate, 97% [Chloromethyl trimethylacetate, Pivaloyloxymethyl chloride] [18997-19-8], (CH ₃) ₃ CCO ₂ CH ₂ Cl, F.W. 150.60, b.p. 146-148°, f.p. 40°(104°F), d. 1.045, n _D ²⁰ 1.4170, UN2924, EINECS 242-735-1, BRN 1560838, MDL MFCD00008884, † | 25g 100g |
| | ! H:H314-H226, P:P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a | |
| | Reagent for the N-protection of amines, e.g. adenine in the presence of K ₂ CO ₃ in DMF, as pivaloyloxymethyl (Pom) derivatives, which have been found useful in the synthesis of sensitive nucleosides. The Pom group is cleaved in mild base, e.g. methanolic ammonia: <i>J. Am. Chem. Soc.</i> , 89 , 5439 (1967). | |
| | Chloromethyl trimethylacetate , see Chloromethyl pivalate, A11967, p. 157 Chloromycetin , see Chloramphenicol, B20841, p. 154 | |
| A14165 | 4-Chloro-7-nitrobenzofurazan, 99% [4-Chloro-7-nitrobenzo-2,1,3-oxadiazole, NBD chloride] [10199-89-0], C ₈ H ₄ ClN ₂ O ₃ , F.W. 199.56, m.p. 96-100°, EINECS 233-496-4, RTECS DF8002400, BRN 614212, MDL MFCD00005808, † | 5g 25g |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Fluorogenic reagent for amines and thiols: <i>Anal. Biochem.</i> , 53 , 290 (1973). Reagent for pre-column derivatization of amines: <i>Anal. Chim. Acta</i> , 130 , 377 (1981), 170 , 81 (1985); and of imino acids: <i>Anal. Biochem.</i> , 138 , 390 (1984), allowing detection after HPLC. | |
| | 4-Chloro-7-nitrobenzo-2,1,3-oxadiazole , see 4-Chloro-7-nitrobenzofurazan, A14165, p. 157 | |
| B21561 | 2-Chloro-4-nitrophenol, 97% [619-08-9], C ₆ H ₄ ClNO ₂ , F.W. 173.56, m.p. 108-112°, EINECS 210-578-8, RTECS SK5075000, BRN 2046372, MDL MFCD00043910, † | 10g 50g 250g |
| | ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| J64455 | 2-Chloro-5-nitro-N-4-pyridinylbenzamide ▲ [T0070907] [313516-66-4], C ₁₂ H ₈ ClN ₃ O ₃ , F.W. 277.66, Solid, MDL MFCD00121849 | 10mg 50mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| B21623 | Chlorophenol Red [3',3''-Dichlorophenolsulfonaphthalein] [4430-20-0], C ₁₉ H ₁₀ Cl ₂ O ₃ S, F.W. 432.28, EINECS 224-619-2, BRN 354053, MDL MFCD00005877, Note: Transition interval: pH 4.8 (yellow) to 6.4 (red), † | 5g 25g |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| |  | |


| Stock # | Description | Size |
|---------|---|---------------------------|
| L10364 | Chlorophenol Red sodium salt [Chlorophenol Red, water soluble] [123333-64-2], C ₁₆ H ₁₁ Cl ₂ NaO ₅ S, F.W. 445.26, m.p. ca 267° dec., EINECS 224-619-2, MDL MFCD00151199, Note: Transition interval: pH 4.8 (yellow) to 6.4 (red) | 5g |
| |  | |
| 38699 | Chlorophenol Red sodium salt, 0.04% w/v aq. soln. C ₁₆ H ₁₁ Cl ₂ NaO ₅ S, F.W. 445.26, Liquid, d. 0.990, MDL MFCD00151199, Note: Transition interval: pH 4.8 (yellow) to 6.4 (red), † | 100ml 500ml 6x100ml |
| | Chlorophenol Red, water soluble, see Chlorophenol Red sodium salt, L10364, p. 158 | |
| A17624 | 2-(4-Chlorophenoxy)isobutyric acid, 98% [2-(4-Chlorophenoxy)-2-methylpropionic acid, Clofibrac acid] [882-09-7], C ₉ H ₉ ClO ₃ , F.W. 214.65, m.p. 119-120°, Merck 14,2378, EINECS 212-925-9, RTECS UE9455000, BRN 1874067, MDL MFCD00004192 | 25g 100g |
| |  | |
| | ! H:H302, P:P264-P270-P301+P312-P330-P501a | |
| | Application(s): A drug used to reduce cholesterol levels in the blood | |
| | 2-(4-Chlorophenoxy)-2-methylpropionic acid, see 2-(4-Chlorophenoxy)isobutyric acid, A17624, p. 158 2-(4-Chlorophenoxy)-2-methylpropionic acid ethyl ester, see Clofibrate, 95+%, J60342, p. 165 | |
| H51982 | 4-Chloro-D-phenylalanine, 95% [(R)-2-Amino-3-(4-chlorophenyl)propionic acid, H-D-Phe(4-Cl)-OH] [14091-08-8], C ₉ H ₉ ClNO ₂ , F.W. 199.64, m.p. 260°, UN2811, BRN 2416151, MDL MFCD00079675 | 250mg 1g 5g |
| |  | |
| | ! H:H301-H317, P:P261-P301+P310-P302+P352-P321-P405-P501a | |
| B20355 | 1-(3-Chlorophenyl)biguanide hydrochloride, 97% ■ [2113-05-5], C ₈ H ₁₀ ClN ₅ HCl, F.W. 248.12, m.p. 191-194°, MDL MFCD00053019 | 1g 5g |
| |  | |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Application(s): Specific agonist for 5-HT receptor | |
| | 1-(3-Chlorophenyl)-2-[(1,1-dimethylethyl)amino]-1-propanone hydrochloride, see Bupropion hydrochloride, 99%, J61105, p. 140 1-[(2-Chlorophenyl)diphenylmethyl]-1H-imidazole, see Clotrimazole, J63895, p. 166 1-[(2-Chlorophenyl)diphenylmethyl]-1H-pyrazole, see TRAM 34, J60019, p. 372 4-(p-Chlorophenyl)-4-hydroxy-N,N-dimethyl-α,α-diphenyl-1-piperidinebutamide hydrochloride, see Loperamide hydrochloride, 98+%, J60168, p. 272 1-[2-(4-Chlorophenylmethoxy)-2-(2,4-dichlorophenyl)ethyl]-1H-imidazole nitrate, see Econazole nitrate, J63173, p. 204 [(4-Chlorophenyl)methyl]-3-(1H-imidazol-4-yl)propyl ester carbamimidothioic acid dihydrobromide, see Clobenpropit dihydrobromide, 99+%, J60807, p. 165 | |
| J60278 | 1-(4-Chlorophenyl)piperazine, 97% [38212-33-8], C ₁₀ H ₁₃ ClN ₂ , F.W. 196.70, Crystalline powder, m.p. 76-79°, b.p. 113°, MDL MFCD00044823 | 1g 5g 25g |
| |  | |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): A 5-HT-1 serotonin receptor agonist | |
| A14057 | 1-(3-Chlorophenyl)piperazine monohydrochloride, 97% [13078-15-4], C ₁₀ H ₁₃ ClN ₂ HCl, F.W. 233.14, m.p. ca 214° dec., UN2811, EINECS 235-976-9, RTECS TL2833500, BRN 4768691, MDL MFCD00012764 | 10g 50g |
| |  | |
| | ! H:H301-H315-H319-H335, P:P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Application(s): 5-HT2C/2B receptor agonist/partial agonist | |
| B25283 | 1-(4-Chlorophenyl)piperazine dihydrochloride, 95% ■ [38869-46-4], C ₁₀ H ₁₃ ClN ₂ ·2HCl, F.W. 269.60, m.p. 275-278° dec., EINECS 254-165-0, MDL MFCD00012766 | 5g 25g 100g |
| |  | |
| | ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Application(s): 5-HT2C/2B receptor agonist/partial agonist | |
| A16155 | Chlorophyllin, coppered trisodium salt ▲ [11006-34-1], C ₅₅ H ₇₀ CuN ₄ Na ₃ O ₆ , F.W. 724.15, EINECS 234-242-5, RTECS GS2168866, MDL MFCD00012149, † | 5g 25g 100g |
| |  | |
| J64066 | 2-Chloro-11-(1-piperazinyl)dibenzo[b,f]-1,4-oxazepine, 98% [Amoxapine] [14028-44-5], C ₁₇ H ₁₆ ClN ₃ O, F.W. 313.78, Powder, EINECS 237-867-1, RTECS HQ4025500, MDL MFCD00069210 | 250mg 1g 5g |
| | ! H:H302, P:P264-P270-P301+P312-P330-P501 | |
| | Application(s): A tricyclic norepinephrine uptake inhibitor | |




| Stock # | Description | Size |
|---------------|---|---|
| A11202 | 6-Chloropurine, 99% [87-42-3], C ₄ H ₃ ClN ₄ , F.W. 154.56, m.p. >300° dec., Merck 14,2161 , EINECS 201-745-6, RTECS UO7520000, BRN 5774, MDL MFCD00075825 ! H:302, P:264-P270-P301+P312-P330-P501a |  1g 5g 25g |
| J64871 | 6-Chloropurine 2'-deoxyriboside, 97% [6-Chloro-9-(2-deoxy-β-D-ribofuranosyl)purine] [4594-45-0], C ₁₀ H ₁₁ ClN ₄ O ₃ , F.W. 270.67, Powder, MDL MFCD00083282 ! H:302-H315-H319-H335, P:261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| J64612 | 6-Chloropurine riboside, 98% [2004-06-0], C ₁₀ H ₁₁ ClN ₄ O ₄ , F.W. 286.67, Powder, m.p. 158-162°, EINECS 217-904-8, RTECS UO7520800, BRN 40573, MDL MFCD00005738 ! H:315-H319-H335, P:261-P305+P351+P338-P302+P352-P321-P405-P501 | 50g 100g 250g |
| J60350 | Chloropyramine hydrochloride [N-(4-Chlorobenzyl)-N',N'-dimethyl-N-(2-pyridyl)ethylenediamine] [6170-42-9], C ₁₆ H ₂₀ ClN ₅ ·HCl, F.W. 326.26, Crystalline powder, Merck 14,2162 , EINECS 228-216-2, MDL MFCD00079009 Application(s): Competitive reversible H-1 receptor antagonist | 1g |
| A15394 | 2-Chloropyrimidine, 98% ■ [1722-12-9], C ₄ H ₃ ClN ₂ , F.W. 114.54, m.p. 64-67°, b.p. 75-76°/10mm, f.p. 98°(208°F), UN2811, EINECS 217-020-2, BRN 107171, MDL MFCD00006060  ! H:301-H319-H317-H335, P:280h-P262-P305+P351+P338-P309-P310 Alkylation with 3-buten-1-ol, followed by intramolecular Diels-Alder reaction, leads to a fused pyridine system, by a sequence analogous to that shown for 2-Chloropyrazine, A10108: Tetrahedron , 45 , 803 (1989). For a similar sequence using the anion of an alkynylmalononitrile, see: <i>Tetrahedron</i> , 45 , 5151 (1989). For synthesis of a benzofuropyridine by the cyclization of a 2-(alkynylphenoxy)pyrimidine, see: <i>Tetrahedron</i> , 45 , 6511 (1989). Organolithium reagents add to the 1,6-imine bond, giving, after aromatization with DDQ, 6-substituted 2-chloropyrimidines: <i>J. Org. Chem.</i> , 53 , 4137 (1988). | 10g 25g 100g |
| J64459 | Chloroquine diphosphate salt, 98% [N-(7-Chloro-4-quinoliny)-N1,N1-dimethyl-1,4-pentanediamine diphosphate salt] [50-63-5], C ₁₆ H ₂₀ ClN ₅ ·2H ₃ PO ₄ , F.W. 515.87, Powder, m.p. 213-216°, Merck 14,2163 , EINECS 200-055-2, RTECS VB2450000, BRN 4223142, MDL MFCD00069852 ! H:302, P:264-P270-P301+P312-P330-P501 | 25g 100g |
| J64326 | 4-(7-Chloro-4-quinolinylamino)-2-(diethylaminomethyl)phenol dihydrochloride dihydrate, 98% [Amodiaquine dihydrochloride dihydrate] [6398-98-7], C ₂₀ H ₂₂ ClN ₅ O·2HCl·2H ₂ O, F.W. 464.82 (392.33anhy), Yellow powder, Merck 14,572 , EINECS 200-706-0, RTECS GO7300100, MDL MFCD00078857 Application(s): An anti-malarial quinoline derivative that acts as an histamine N-methyltransferase inhibitor | 5g 25g 100g |
| A10310 | N-Chlorosuccinimide, 98% ■ [NCS] [128-09-6], C ₄ H ₄ ClNO ₂ , F.W. 133.53, m.p. 146-150°, d. 1.65, Merck 14,2164 , Fieser 1,139 13,79 14,87 15,86 16,84 18,101 19,95 20,108 21,131 , UN3261, EINECS 204-878-8, RTECS UY1013500, BRN 113915, MDL MFCD00005511, t  ! H:314-H302, P:280-P305+P351+P338-P309-P310 Source of positive chlorine in chlorination and oxidation reactions. Methyl ketones may be monochlorinated via their Li enolates: <i>J. Org. Chem.</i> , 49 , 1286 (1984). For the α-chlorination of acid chlorides formed <i>in situ</i> , see: <i>Tetrahedron Lett.</i> , 3235 (1974). For chlorination of deactivated anilines, see: <i>Synthesis</i> , 669 (1985). In the presence of triphenylphosphine or triphenyl phosphite, converts alcohols to alkyl chlorides stereospecifically with inversion: <i>Tetrahedron Lett.</i> , 3937 (1973). For a review, see: <i>Org. React.</i> , 29 , 1 (1983). Amides have been prepared by treatment of a carboxylic acid with NCS/PPH ₃ followed by an amine: <i>Synth. Commun.</i> , 25 , 959 (1995). With dimethyl sulfide, forms the Corey-Kim reagent, a mild, selective oxidant for alcohols. For a review, see: <i>Synthesis</i> , 857 (1990); for tabulated examples, see: <i>Org. Synth. Coll.</i> , 6 , 220 (1988). Primary alcohols are oxidized cleanly to aldehydes using NCS and a catalytic amount of TEMPO, A12733 , under phase-transfer conditions: <i>J. Org. Chem.</i> , 61 , 7452 (1996). NCS in ether is a convenient alternative to hypochlorite for the conversion of amines to N-chloroamines, for use, e.g. in the Hofmann-Loeffler reaction, see: <i>Chem. Ber.</i> , 88 , 883 (1955). Application(s): Regioselective chlorination and oxidizing reagent | 50g 250g 1kg |
| | 6-Chloro-7-sulfamyl-3,4-dihydro-1,2,4-benzothiadiazine-1,1-dioxide , see Hydrochlorothiazide, B22093, p. 247 | |
| 87977 | Chlorosulfonic acid, typically 99% ■ [7790-94-5], HSO ₃ Cl, F.W. 116.52, Liquid, b.p. 158°, d. 1.753, n _D ²⁰ 1.433, Merck 14,2165 , UN1754, EINECS 232-234-6, RTECS FX5730000, MDL MFCD00011523, t ! H:314-H335-EUH014, P:260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 250g 1kg 3x1kg |
| | 7-Chlorotetracycline hydrochloride , see Chlortetracycline hydrochloride, J60095, p. 160 | |











| Stock # | Description | Size |
|---------|--|--------------------|
| A12408 | 8-Chlorotheophylline, 99% [8-Chloro-1,3-dimethyl-2,6-purinedione] [85-18-7], C ₇ H ₇ ClN ₂ O ₂ , F.W. 214.61, m.p. ca 290° dec., EINECS 201-590-4, RTECS XH5063000, BRN 203068, MDL MFCD00005581 ! H:H302, P:P264-P270-P301+P312-P330-P501a | 50g 250g 1kg |
| |  | |
| | 2-Chloro-N-[[[4-(trifluoromethoxy)phenyl]amino]carbonyl]benzamide , see Triflumuron, 98+%, J63112, p. 376 | |
| 44407 | 2-Chlorotrityl chloride on polystyrene, 1% cross-linked, 100-200 mesh, 1.0-1.4 mmol/g [42074-68-0], Powder, MDL MFCD00040399 | 2g 10g 50g |
| | 1-(o-Chlorotrityl)imidazole , see Clotrimazole, J63895, p. 166 4-Chlorouracil , see 6-Chlorouracil, L01875, p. 160 | |
| A11084 | 5-Chlorouracil, 98% [5-Chloro-2,4-dihydropyrimidine] [1820-81-1], C ₄ H ₃ ClN ₂ O ₂ , F.W. 146.53, m.p. >300°, EINECS 217-339-7, RTECS YQ9410000, BRN 127173, MDL MFCD00006019 | 5g 25g 100g |
| |  | |
| L01875 | 6-Chlorouracil, 98+% [6-Chloro-2,4-dihydropyrimidine, 4-Chlorouracil] [4270-27-3], C ₄ H ₃ ClN ₂ O ₂ , F.W. 146.53, m.p. ca 295° dec., EINECS 224-258-0, BRN 120492, MDL MFCD00014595 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 1g 5g |
| |  | |
| | 4-Chloro-3,5-xenolol , see 4-Chloro-3,5-dimethylphenol, B21964, p. 155 | |
| B25238 | Chlorpheniramine maleate, 99% [113-92-8], C ₂₀ H ₂₅ ClN ₂ O ₄ , F.W. 390.86, m.p. 130-135°, EINECS 204-037-5, RTECS US6503000, MDL MFCD00069225, † ! H:H302, P:P264-P270-P301+P312-P330-P501a | 5g 25g |
| |  | |
| | Application(s): An antihistaminic agent | |
| J63659 | Chlorpromazine hydrochloride, 98+% [Hebanil, Klorpromex] [69-09-0], C ₁₇ H ₁₉ ClN ₂ S·HCl, F.W. 355.30, Crystalline solid, m.p. 196°, Merck 14,2185, UN2811, EINECS 200-701-3, RTECS SO1750000, BRN 3779989, MDL MFCD00012654, † ! H:H301-H330, P:P301+P310-P304+P340-P320-P330-P405-P501a | 10g 25g 100g |
| | Application(s): Reported to be useful as a substitute for benzidine, o-dianisidine and o-tolidine in the determination of microquantities of hemoglobin and peroxidase. | |
| J64110 | Chlorpropamide [1-(4-Chlorobenzenesulfonyl)-3-n-propylurea] [94-20-2], C ₁₀ H ₁₃ ClN ₂ O ₂ S, F.W. 276.74, Powder, Merck 14,2186, EINECS 202-314-5, RTECS YS6650000, MDL MFCD00079004 ! H:H302-H312-H332-H351, P:P261-P280-P281-P302+P352-P405-P501 | 25g 100g |
| | Application(s): Bacteriostatic antibiotic active against gram positive and gram negative bacteria | |
| J60095 | Chlortetracycline hydrochloride ▲ [7-Chlorotetracycline hydrochloride, Aureomycin] [64-72-2], C ₂₂ H ₂₃ ClN ₂ O ₈ ·HCl, F.W. 515.34, Powder, m.p. 210-215° dec., Merck 14,2192, EINECS 200-591-7, RTECS QI7800000, BRN 3858364, MDL MFCD00082440 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 25g 100g |
| | Application(s): Bacteriostatic antibiotic active against gram positive and gram negative bacteria | |
| | Chlorzoxazone , see 5-Chloro-2(3H)-benzoxazolone, B24507, p. 155 3-[(3-Cholamidopropyl)dimethylammonio]-1-propanesulfonate , see CHAPS, B21927, p. 152 Cholecalciferol , see Vitamin D3, B22524, p. 392 | |
| L08624 | 5α-Cholestan-3β-ol, 98% [Dihydrocholesterol] [80-97-7], C ₂₇ H ₄₈ O, F.W. 388.68, m.p. 140-144°, [α] _D ²⁰ +24° (c=1 in chloroform), Merck 14,2200, EINECS 201-315-8, RTECS FZ6350000, BRN 2418594, MDL MFCD00066413, † | 5g 25g |
| |  | |
| L08726 | 5α-Cholestan-3-one, 97% [566-88-1], C ₂₇ H ₄₆ O, F.W. 386.66, m.p. 128-132°, [α] _D ²⁰ +43° (c=1 in chloroform), BRN 2625580, MDL MFCD00065901 | 1g 5g |
| |  | |





| Stock # | Description | Size |
|---------|--|-----------------------|
| A11470 | Cholesterol, 95% [5-Cholesten-3 β -ol] [57-88-5], C ₂₇ H ₄₆ O, F.W. 386.66, m.p. 147-150°, b.p. 360°, d. 1.067, [α] _D ²⁰ -36° (c=2 in dioxane), Merck 14,2201, Fieser 1,141, EINECS 200-353-2, RTECS FZ8400000, BRN 1915888, MDL MFCD00003646, † | 50g 250g 1kg |
| | Application(s): Component of all biological membranes. Appears to inhibit basal channel activity in the brain | |
| J64282 | Cholesterol Esterase, from porcine pancreas [EC 3.1.1.13, Sterol-ester acylhydrolase] [9026-00-0], F.W. 440kDa, Lyophilized powder, EINECS 232-808-6, MDL MFCD00071052, † | 100units 500units |
| A15052 | Cholesteryl acetate, 97+% [Acetic acid cholesteryl ester] [604-35-3], C ₂₉ H ₄₈ O ₂ , F.W. 428.70, m.p. 112-114°, [α] _D ²⁰ -43° (c=5 in chloroform), Merck 14,2201, EINECS 210-066-4, BRN 2064235, MDL MFCD00003636, † | 25g 100g 500g |
| L02857 | Cholesteryl nonanoate [Cholesteryl pelargonate, Nonanoic acid cholesteryl ester] [1182-66-7], C ₃₆ H ₆₂ O ₂ , F.W. 526.89, m.p. 75-79°, [α] _D ²⁰ -30° (c=5 in chloroform), EINECS 214-658-3, BRN 3179820, MDL MFCD00003643, † | 25g 100g |
| | Cholesteryl octadecanoate , see Cholesteryl stearate, A14771, p. 161 | |
| A11378 | Cholesteryl oleate [Oleic acid cholesteryl ester] [303-43-5], C ₄₂ H ₇₈ O ₂ , F.W. 651.12, m.p. 44-47°, [α] _D ²⁰ -24° (c=1 in chloroform), EINECS 206-142-1, BRN 2343071, MDL MFCD00003645, † | 5g 25g 100g |
| | Cholesteryl pelargonate , see Cholesteryl nonanoate, L02857, p. 161 | |
| A14771 | Cholesteryl stearate, 96% [Cholesteryl octadecanoate, Octadecanoic acid cholesteryl ester] [35602-69-8], C ₄₈ H ₈₀ O ₂ , F.W. 653.13, m.p. 76-79°, [α] _D ²⁰ -23° (c=5 in chloroform), EINECS 252-637-0, BRN 2068492, MDL MFCD00003639 | 5g 25g 250g |
| J62050 | Cholic acid sodium salt [206986-87-0], C ₂₄ H ₄₀ NaO ₆ , F.W. 430.60, Powder, BRN 3582354, MDL MFCD00150749, † H:H303, P:P312 | 25g 100g 250g |
| | Application(s): Biochemical solubilizing agent | |
| J64657 | Choline bitartrate, 98+% ■ [2-(Hydroxyethyl)trimethylammonium bitartrate] [87-67-2], C ₉ H ₁₉ NO ₇ , F.W. 253.25, Powder, m.p. 151-153°, EINECS 201-763-4, MDL MFCD00036332, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 250g 1kg 2.5kg |
| A15828 | Choline chloride, 98+% ■ [(2-Hydroxyethyl)trimethylammonium chloride] [67-48-1], HOCH ₂ CH ₂ N(CH ₃) ₃ Cl, F.W. 139.63, m.p. ca 305° dec., Merck 14,2206, EINECS 200-655-4, RTECS KH2975000, BRN 3563126, MDL MFCD00011721, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 100g 500g 2.5kg |
| | Application(s): An acyl group acceptor | |
| J60341 | Chondroitin sulfate, 90+% [9007-28-7], C ₁₃ H ₂₁ NO ₁₅ S, F.W. 463.37, Powder, Merck 14,2214, EINECS 232-696-9, † | 1g 5g 25g |
| | Application(s): A mucopolysaccharide with N-acetylchondrosine as a repeating unit and with one sulfate group per disaccharide unit; acts as the flexible connecting matrix between the tough protein filaments in cartilage to form a polymeric system.A naturocetic agent | |
| J62927 | Chromomycin A3, 98% [7059-24-7], C ₅₇ H ₈₂ O ₂₆ , F.W. 1183.30, Powder, m.p. 185° dec., Merck 14,2238, UN3462, EINECS 230-348-0, RTECS GB7875000, MDL MFCD00043151 ☠ H:H300-H360, P:P281-P301+P310-P321-P308+P313-P405-P501a | 10mg |
| | Application(s): An inhibitor of DNA and RNA polymerases. Serves as a fluorescent DNA stain | |
| | Chrysin , see 5,7-Dihydroxyflavone, L14178, p. 192 | |


















| Stock # | Description | Size |
|---------|---|---------------|
| J64999 | Chrysophenine sodium salt [C.I. 24895, Direct Yellow 12] [2870-32-8], C ₃₀ H ₂₆ N ₄ O ₆ Na ₂ S ₂ , F.W. 680.66, Powder, EINECS 220-698-2, MDL MFCD00007488, † | 50g |
| J63275 | Chymostatin [N-(N α -Carbonyl-Cpd-X-Phe-al)-Phe] [9076-44-2], C ₃₁ H ₄₄ N ₄ O ₆ , F.W. 604.90, Powder, m.p. 276-278°, RTECS GC3047700, MDL MFCD00071059 Application(s): A highly specific chymotrypsin inhibitor produced by actinomycetes | 5mg |
| J65266 | α-Chymotrypsin, from bovine pancreas [EC 3.4.21.1] [9004-07-3], F.W. 25kDa, Lyophilized powder, EINECS 232-671-2, RTECS GC3050000, MDL MFCD00130481, † !  H.H315-H319-H334-H335, P.P285-P305+P351+P338-P302+P352-P321-P405-P501 | 100micrograms |
| J64741 | Chymotrypsinogen A, from bovine pancreas [9035-75-0], F.W. 25.6kDa, Powder, EINECS 232-905-3, MDL MFCD00130483 | 1g 5g |
| J65561 | CI 994 Δ [N-Acetyldinaline, 4-Acetylamino-N-(2'-aminophenyl)benzamide] [112522-64-2], C ₁₈ H ₁₅ N ₃ O ₂ , F.W. 269.30, Powder, RTECS CU8702023, MDL MFCD00866266 ! H.H319, P.P280-P264-P305+P351+P338-P337+P313 | 25mg 100mg |
| | <p>CI-1033, see Canertinib, 99+%, J63403, p. 145</p> <p>CI-1033, see Canertinib dihydrochloride salt, 99+%, J63750, p. 145</p> <p>C.I. 10020, see Naphthol Green B, A18268, p. 298</p> <p>C.I. 10316, see Naphthol Yellow S, B20872, p. 298</p> <p>C.I. 11050, see Janus Green B, A17391, p. 262</p> <p>C.I. 12140, see Sudan II, A17613, p. 355</p> <p>C.I. 13020, see Methyl Red, A16690, p. 290</p> <p>C.I. 13025, see Methyl Orange, A17604, p. 289</p> <p>C.I. 13065, see Mentanil Yellow, A17527, p. 283</p> <p>C.I. 14030, see Alizarin Yellow R sodium salt, 38707, p. 89</p> <p>C.I. 14640, see Eriochrome[®] Blue Black B, J63396, p. 210</p> <p>C.I. 19140, see Tartrazine, A17682, p. 358</p> <p>C.I. 20470, see Amido Black 10B, A11374, p. 91</p> <p>C.I. 21000, see Bismarck Brown Y, A16674, p. 127</p> <p>C.I. 22120, see Congo Red, B24310, p. 168</p> <p>C.I. 23850, see Trypan Blue, A18600, p. 384</p> <p>C.I. 23860, see Evans Blue, A16774, p. 218</p> <p>C.I. 24410, see Chicago Sky Blue 6B, A14242, p. 153</p> <p>C.I. 26105, see Sudan IV, A12181, p. 355</p> <p>C.I. 26125, see Oil Red O, A12989, p. 307</p> <p>C.I. 30235, see Chlorazol Black E, A13259, p. 154</p> <p>C.I. 35780, see Direct Red 80, B21693, p. 199</p> <p>C.I. 37175, see Fast Blue BB salt, L09704, p. 218</p> <p>C.I. 42000, see Malachite Green oxalate, A16186, p. 275</p> <p>C.I. 42040, see Brilliant Green, A12801, p. 135</p> <p>C.I. 42053, see Fast Green FCF, A16520, p. 219</p> <p>C.I. 42095, see Light Green SF Yellowish, B23330, p. 270</p> <p>C.I. 42135, see Xylenecyanol FF, B21530, p. 394</p> <p>C.I. 42510, see Basic Fuchsin, A12952, p. 117</p> <p>C.I. 42555, see Crystal Violet, B21932, p. 170</p> <p>C.I. 42655, see Brilliant Blue G, 43318, p. 135</p> <p>C.I. 42685, see Acid Fuchsin sodium salt, B22222, p. 76</p> <p>C.I. 45100, see Kiton Red S, A14769, p. 264</p> <p>C.I. 45170, see Rhodamine B, A13572, p. 337</p> <p>C.I. 45350, see Fluorescein disodium salt hydrate, A11659, p. 223</p> <p>C.I. 45350.1, see Fluorescein, L13251, p. 222</p> <p>C.I. 45370, see 4',5'-Dibromofluorescein, A18226, p. 184</p> <p>C.I. 45380, see Eosin Yellowish, B24535, p. 208</p> <p>C.I. 45400, see Eosin B, A17377, p. 208</p> <p>C.I. 45430, see Erythrosin B, A14180, p. 210</p> <p>C.I. 46005, see Acridine Orange, L13159, p. 76</p> <p>C.I. 50040, see Neutral Red, J62643, p. 300</p> <p>C.I. 50085, see Azocarmine G, A12507, p. 116</p> <p>C.I. 50240, see Safranin O, B21674, p. 339</p> <p>C.I. 50420, see Nigrosin water soluble, A18147, p. 302</p> <p>C.I. 51180, see Nile Blue A, A17174, p. 302</p> <p>C.I. 52010, see Azure I, A17508, p. 116</p> <p>C.I. 52015, see Methylene Blue, A18174, p. 287</p> <p>C.I. 58005, see Alizarin Red S sodium salt, 42040, p. 89</p> <p>C.I. 58050, see 1, 4-Dihydroxyanthraquinone, A11010, p. 191</p> <p>C.I. 59040, see Pyranine, L11252, p. 332</p> <p>C.I. 73051, see Indigocarmine, A16052, p. 255</p> <p>C.I. 74180, see Solvent Blue 38, A15395, p. 349</p> <p>C.I. 75290, see Hematoxylin hydrate, A12431, p. 242</p> <p>C.I. 75300, see Curcumin, B21573, p. 170</p> <p>CIAP, see Alkaline Phosphatase, calf intestine, EIA Grade, J61037, p. 89</p> <p>Cichorigenin, see 6,7-Dihydroxycoumarin, A15393, p. 192</p> | |
| J64094 | CIL-102 [1-[4-(Furo[2,3-b]quinolin-4-ylamino)phenyl]ethanone] [479077-76-4], C ₁₈ H ₁₄ N ₂ O ₂ , F.W. 302.33, Powder, MDL MFCD08277043 | 10mg |

| Stock # | Description | Size |
|--|--|---|
| J65319 | Cilostamide [N-Cyclohexyl-N-methyl-4-(1,2-dihydro-2-oxo-6-quinolyloxy)butyramide, OPC 3689] [68550-75-4], C ₂₆ H ₂₆ N ₂ O ₃ , F.W. 342.43, Powder, MDL MFCD00673958 | 10mg |
| J65933 | Cilostamide, 98% [6-[3-(N-Cyclohexyl-N-methylcarbamoyl)propoxy]quinolin-2[1H]-one, OPC 3689] [68550-75-4], C ₂₆ H ₂₆ N ₂ O ₃ , F.W. 342.44, Powder, MDL MFCD00673958 | 5mg |
| J62301 | Cilostazol, 98% [OPC-13013] [73963-72-1], C ₂₀ H ₂₇ N ₅ O ₂ , F.W. 369.46, Solid, Merck 14,2277, RTECS VC8277500, MDL MFCD00866780 ⚠ H:361, P:P281-P201-P202-P308+P313-P405-P501 | 10mg 50mg |
| Application(s): An inhibitor of phosphodiesterase III | | |
| J60650 | Cimaterol [2-Amino-5-[1-hydroxy-2-[(1-methylethyl)amino]ethyl]benzotrile] [54239-37-1], C ₁₇ H ₁₇ N ₃ O, F.W. 219.29, Solid, m.p. 159-161°, Merck 14,2278, BRN 2418129, MDL MFCD00209815 | 10mg 50mg |
| Application(s): A β-adrenergic agonist | | |
| J62825 | Cimetidine, 98+% [N-Cyano-N'-methyl-N''-(2-[(5-methyl-1H-imidazol-4-yl)methyl]thio)ethyl)guanidine, SKF-92334] [51481-61-9], C ₁₀ H ₁₆ N ₆ S, F.W. 252.34, Powder, m.p. 141-143°, Merck 14,2279, EINECS 257-232-2, RTECS MF0035500, MDL MFCD00133296 ⚠ H:360, P:P281-P201-P202-P308+P313-P405-P501a | 5g 10g 25g |
| Application(s): H2 histamine receptor antagonist | | |
| J63370 | Cinanserin hydrochloride, 99+% [1166-34-3], C ₂₀ H ₂₄ N ₂ OS HCl, F.W. 376.94, Solid ! H:302, P:P264-P270-P301+P312-P330-P501 | 10mg 50mg |
| Application(s): A 5-HT antagonist | | |
| Cincomeric acid , see Pyridine-3,4-dicarboxylic acid, A14580, p. 332 | | |
| A18796 | (-)-Cinchonidine, 99% (total base), may cont. up to 5% quinine ▲ [485-71-2], C ₁₉ H ₂₈ N ₄ O, F.W. 294.39, m.p. 201-206°, Merck 14,2286, EINECS 207-622-3, RTECS GD3500000, BRN 89690, MDL MFCD00006783, † | 25g 100g |
| | |  |
| A17523 | (+)-Cinchonine, 98+%, cont. up to 3% quinidine/dihydroquinidine and 3% quinine/dihydroquinine ▲ [118-10-5], C ₁₉ H ₂₈ N ₄ O, F.W. 294.39, m.p. 253-258°, [α] _D ²⁰ +225° (c=0.5 in ethanol), Merck 14,2287, Fieser 6,501, EINECS 204-234-6, RTECS GD3500000, BRN 89689, MDL MFCD00064372, † ! H:302, P:P264-P270-P301+P312-P330-P501a Resolving agent for chiral acids. For practical details for use in the resolution of 1,1'-bi(2-naphthol) via the cyclic phosphate ester, see: <i>Org. Synth. Coll.</i> , 8, 50 (1993). | 25g 100g |
| | |  |
| A12269 | 1,8-Cineole, 99% [Eucalyptol, 1,3,3-Trimethyl-2-oxabicyclo[2.2.2]octane] [470-82-6], C ₁₅ H ₂₆ O, F.W. 154.24, m.p. 1.0°, b.p. 176-177°, f.p. 49° (120°F), d. 0.923, n _D ²⁰ 1.4555, Merck 14,3895, UN3271, EINECS 207-431-5, RTECS OS9275000, BRN 105109, MDL MFCD00167977, † 🔥 H:H226, P:P210-P241-P280-P240-P303+P361+P353-P501a | 100ml 500ml |
| | |  |
| J64568 | Cinnarizine [1-trans-Cinnamyl-4-diphenylmethyl)piperazine, 1-Benzhydryl-4-trans-cinnamyl)piperazine] [298-57-7], C ₂₆ H ₂₈ N ₂ , F.W. 368.52, Powder, m.p. 117-121°, Merck 14,2305, EINECS 206-064-8, RTECS TL3430000, MDL MFCD00056037 | 25g 100g |
| J61317 | Ciprofloxacin, 98% [85721-33-1], C ₁₇ H ₁₈ FN ₃ O ₃ , F.W. 331.30, Powder, m.p. 253-257°, Merck 14,2314, RTECS VB1993800, BRN 3568352, MDL MFCD00185755 | 5g 25g |
| Application(s): An anti-bacterial agent effective against anaerobic bacteria | | |
| J61970 | Ciprofloxacin hydrochloride [86393-32-0], C ₁₇ H ₁₈ FN ₃ O ₃ HCl, F.W. 367.80, Lyophilized powder, Merck 14,2314, RTECS VB1993800, MDL MFCD00242856 | 5g 25g |
| Application(s): An anti-bacterial agent effective against anaerobic bacteria | | |
| Cisplatin , see cis-Diamminedichloroplatinum(II), 10471, p. 184 | | |


| Stock # | Description | Size |
|---------|---|---------------------|
| L05238 | Citraconic anhydride, 98%  [3-Methyl-2,5-furandione, Methylmaleic anhydride] [616-02-4], C ₅ H ₄ O ₃ , F.W. 112.08, m.p. 7-8°, b.p. 213-214°, f.p. 101° (213°F), d. 1.243, n _D ²⁰ 1.4710, UN2810, EINECS 210-459-0, RTECS GE6825000, BRN 1835, MDL MFCD00005522, †  H: H311-H315-H319, P: P305+P351+P338-P361-P302+P352-P321-P405-P501a Reagent for the protection of amino groups: <i>Biochem. J.</i> , 109 , 312 (1968). | 25g 100g 500g |
| J63008 | Citrate, 0.5M buffer soln., pH 2.5 [6132-04-3], Liquid | 250ml 500ml |
| J61391 | Citrate, 0.5M buffer soln., pH 3.0 [6132-04-3], Liquid, † | 250ml 500ml |
| J61690 | Citrate, 0.5M buffer soln., pH 3.5 [6132-04-3], Liquid, † | 250ml 500ml |
| J61249 | Citrate, 0.5M buffer soln., pH 4.0 [6132-04-3], Liquid | 250ml 500ml |
| J60024 | Citrate, 0.5M buffer soln., pH 4.5 [6132-04-3], Liquid | 250ml 500ml |
| J60125 | Citrate, 0.5M buffer soln., pH 5.0 [6132-04-3], Liquid | 250ml 500ml |
| J60754 | Citrate, 0.5M buffer soln., pH 5.5 [6132-04-3], Liquid | 250ml 500ml |
| J63950 | Citrate, 0.5M buffer soln., pH 6.0 [6132-04-3], Liquid | 250ml 500ml |
| J60919 | Citrate, 0.5M buffer soln., pH 8.0 [6132-04-3], Liquid | 250ml 500ml |
| J63666 | Citrate-buffered saline (20X) <i>[SSC buffer, 20X, Saline-sodium citrate buffer, 20X]</i> [6132-04-3], Liquid, Note: 300mM sodium citrate, 3M sodium chloride, pH 7.0 | 1L 2L |
| A15461 | Citrazinic acid, 97% <i>[2,6-Dihydroxyisonicotinic acid, 2,6-Dihydroxypyridine-4-carboxylic acid]</i> [99-11-6], C ₆ H ₅ NO ₂ , F.W. 155.11, m.p. >300° dec., Merck 14,2325 , EINECS 202-731-2, RTECS NS1400000, BRN 383736, MDL MFCD00006274, †  H: H315-H319-H335, P: P280g-P305+P351+P338 | 50g 250g |
| 36665 | Citric acid monohydrate, ACS, 99.0-102.0%  [5949-29-1], C ₆ H ₈ O ₇ ·H ₂ O, F.W. 210.14 (192.13anhy), Solid, d. 1.542, Merck 14,2326 , EINECS 201-069-1, RTECS GE7810000, MDL MFCD00149972, † Maximum level of impurities: Insoluble matter 0.005%, Residue after ignition 0.02%, Cl 0.001%, C ₂ O ₄ P.T. (limit about 0.05%), PO ₄ 0.001%, SO ₄ 0.002%, Fe 3ppm, Pb 2ppm, Substances carbonizable by hot sulfuric acid (tartrates, etc.) P.T.  H: H318-H302-H335-H315, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 100g 500g 2kg |
| A10395 | Citric acid, 99+% [77-92-9], C ₆ H ₈ O ₇ , F.W. 192.13, m.p. 153-154°, d. 1.665, Merck 14,2326 , EINECS 201-069-1, RTECS GE7350000, BRN 782061, MDL MFCD00011669, †  H: H318-H335-H315, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250g 1kg 5kg |
| 36664 | Citric acid, anhydrous, ACS, 99.5+%  [77-92-9], HOC(=O)C(OH)(COOH)CH ₂ COOH, F.W. 192.13, Crystalline, m.p. 153-154°, d. 1.665, Merck 14,2326 , EINECS 201-069-1, RTECS GE7350000, BRN 782061, MDL MFCD00011669, † Maximum level of impurities: Insoluble matter 0.005%, Residue after ignition 0.02%, Cl 0.001%, C ₂ O ₄ P.T. (limit about 0.05%), PO ₄ 0.001%, SO ₄ 0.002%, Fe 3ppm, Pb 2ppm, Substances carbonizable by hot sulfuric acid (tartrates, etc.) P.T.  H: H318-H335-H315, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): Vitamin C | 100g 500g 2kg |
| J64322 | Citric acid, Electrophoresis Grade, 99.5+%  [77-92-9], C ₆ H ₈ O ₇ , F.W. 192.13, Powder, m.p. 153-154°, d. 1.665, Merck 14,2326 , EINECS 201-069-1, RTECS GE7350000, BRN 782061, MDL MFCD00011669, †  H: H315-H318-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | 100g 500g 2kg |














| Stock # | Description | Size |
|---------|---|-------------------------|
| J64007 | Citrinin, 98% [8-Hydroxy-3,4,5-trimethyl-6-oxo-4,6-dihydro-3H-isochromene-7-carboxylic acid] [518-75-2], C ₁₃ H ₁₆ O ₅ , F.W. 250.25, Powder, Merck 14,2327, UN3462, EINECS 208-257-2, RTECS DJ2275000, BRN 5282243, MDL MFCD00006912  H:H301-H311-H330-H351, P:P301+P310-P304+P340-P320-P330-P361-P405-P501 | 5mg 10mg |
| L15753 | (±)-Citronellal, 96% △ [(+/-)-3,7-Dimethyl-6-octenal] [106-23-0], C ₁₀ H ₁₈ O, F.W. 154.25, b.p. 206-208°, f.p. 75°(167°F), d. 0.860, n _D ²⁰ 1.4490, Merck 14,2329, EINECS 203-376-6, RTECS RH2140000, BRN 1720789, MDL MFCD00038090, † ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313  | 100ml 500ml |
| A13316 | L-Citrulline, 98% [L-(+)-2-Amino-5-ureidovaleric acid] [372-75-8], C ₈ H ₁₃ N ₃ O ₃ , F.W. 175.19, m.p. 212-214° dec., [α] _D ²⁰ +22° (c=2 in 1N HCl), Merck 14,2331, EINECS 206-759-6, BRN 6055157, MDL MFCD00064397, †  | 10g 50g |
| J65211 | CL 316243 disodium salt [151126-84-0], C ₂₀ H ₁₈ Cl ₂ Na ₂ O ₇ , F.W. 465.80, Powder Cleland's Reagent DTE , see 1,4-Dithioerythritol, A10138, p. 200 Cleland's Reagent DTT racemic , see 1,4-Dithio-DL-threitol, A15797, p. 200 | 10mg |
| J62260 | Clenbuterol hydrochloride [21898-19-1], C ₁₂ H ₁₆ Cl ₂ N ₂ O·HCl, F.W. 313.65, Powder, Merck 14,2347, UN2811, EINECS 244-643-7, RTECS DN3180000, MDL MFCD00083280  H:H301, P:P264-P270-P301+P310-P321-P405-P501a Application(s): A β- 2 adrenoceptor agonist | 100mg |
| | 1,6-Cleve's Acid , see 5-Aminonaphthalene-2-sulfonic acid, L03099, p. 97 | |
| J61409 | Clindamycin hydrochloride monohydrate [58207-19-5], C ₁₈ H ₃₃ ClN ₂ O ₅ S·HCl·H ₂ O, F.W. 479.46 (461.44anhy), Powder, Merck 14,2356, EINECS 244-398-6, RTECS GF2275000, BRN 4070786, MDL MFCD07793327 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): Antibiotic U-28508E, effective against gram-positive bacteria | 1g 5g |
| J63387 | Clindamycin phosphate [24729-96-2], C ₁₈ H ₃₃ ClN ₂ O ₅ P ₃ , F.W. 504.96, Solid, m.p. 114°, Merck 14,2356, EINECS 246-433-0, RTECS GF2625000, MDL MFCD07793328 ! H:H302, P:P264-P270-P301+P312-P330-P501 Application(s): Antibiotic U-28508E, effective against gram-positive bacteria | 20mg 100mg |
| J60807 | Clobenpropit dihydrobromide, 99+% [VUF 9153, [(4-Chlorophenyl)methyl]-3-(1H-imidazol-4-yl)propyl ester carbamidodithioic acid dihydrobromide] [145231-45-4], C ₁₄ H ₁₇ ClN ₂ S ₂ ·2HBr, F.W. 470.66, Powder, m.p. 215-216°, MDL MFCD00467655 Application(s): A specific H-3 histamine receptor | 10mg 50mg |
| | Clofarabine , see 2-Chloro-2'-arabino-fluoro-2'-deoxyadenosine, 99+%, J60927, p. 155 | |
| J60342 | Clofibrate, 95+% [Ethyl 2-(4-chlorophenoxy)isobutyrate, 2-(4-Chlorophenoxy)-2-methylpropionic acid ethyl ester] [637-07-0], C ₁₂ H ₁₆ ClO ₃ , F.W. 242.70, Liquid, b.p. 154-156°, f.p. 113°(235°F), d. 1.14, n _D ²⁰ 1.5, Merck 14,2377, UN3082, EINECS 211-277-4, RTECS UE9480000, BRN 1913459, MDL MFCD00000615  H:H318-H302-H335-H315-H411, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): Peroxisome proliferator-activated receptor-α agonist. Induces apoptosis in hepatoma cells | 1g 5g 25g 100g |
| | Clofibric acid , see 2-(4-Chlorophenoxy)isobutyric acid, A17624, p. 158 | |
| J63552 | Clofilium tosylate, 97+% [92953-10-1], C ₂₂ H ₃₇ ClN ₂ C ₇ H ₄ O ₃ S, F.W. 510.17, Powder, m.p. 98-99°, RTECS CY9040870, MDL MFCD00069233 ! H:H302, P:P264-P270-P301+P312-P330-P501 Application(s): A potassium channel blocker | 25mg 100mg 250mg |
| | Clomifene citrate , see Clomiphene citrate, J63663, p. 165 | |
| J63663 | Clomiphene citrate [Clomifene citrate] [50-41-9], C ₂₆ H ₂₈ ClNO ₆ ·C ₆ H ₈ O ₇ , F.W. 598.08, Crystalline powder, Merck 14,2386, EINECS 200-035-3, RTECS YE0875000, MDL MFCD00058322  H:H360, P:P281-P201-P202-P308+P313-P405-P501 Application(s): A selective estrogen receptor modulator | 2g 10g |
| J62485 | Clomipramine hydrochloride [Anafранил гидрохлориде, 3-Chloro-10, 11-dihydro-N,N-dimethyl-5H-dibenzo[b,f]azepine-5-propanamine hydrochloride] [17321-77-6], C ₁₉ H ₂₃ ClN ₂ ·HCl, F.W. 351.32, Powder, m.p. 189-190°, Merck 14,2387, EINECS 241-344-3, RTECS HN9055000, MDL MFCD00069234 !  H:H302-H312-332-H360, P:P261-P280-P281-P302+P352-P405-P501 Application(s): Potent, selective 5-HT uptake blocker | 1g 5g |

| Stock # | Description | Size |
|---------|---|---------------------|
| J63707 | Clonidine hydrochloride, 98+% [2-(2,6-Dichloroanilino)-2-imidazoline hydrochloride] [4205-91-8], C ₉ H ₉ Cl ₂ N ₃ HCl, F.W. 266.55, Powder, Merck 14,2390, UN2811, EINECS 224-121-5, RTECS NJ2490000, BRN 4163525, MDL MFCD00036705  | 1g 5g |
| | Application(s): α -2 adrenergic agonist | |
| H56409 | (±)-Clopidogrel hydrogen sulfate, 98+% [135046-48-9], C ₁₆ H ₁₆ ClNO ₂ S H ₂ SO ₄ , F.W. 419.90, Merck 14,2396, MDL MFCD05865229  | 25mg |
| J60577 | Cloprosteno sodium salt [55028-72-3], C ₂₂ H ₂₈ ClNaO ₆ , F.W. 446.90, Powder, m.p. 68-70°, Merck 14,2399, EINECS 259-439-3  | 1mg 5mg 10mg |
| | Application(s): A potent prostaglandin F receptor agonist | |
| | Clortetrin , see Demeclocycline hydrochloride, J63102, p. 176 Clostridiopeptidase b , see Clostripain, Clostridium histolyticum, J61362, p. 166 | |
| J61362 | Clostripain, Clostridium histolyticum [Endoproteinase-Arg-C, Clostridiopeptidase b] [9028-00-6], Powder, EINECS 232-822-2, Note: Minimum 50 units per mg dry weight. One unit hydrolyzes one micromole of N-benzoyl-L-arginine ethyl ester per minute at 25 degrees and pH 7.6 in the presence of dithiothreitol | 1mg 10mg |
| | Application(s): A protease that cleaves proteins on the carboxyl bond of arginine | |
| | Clotam , see Tolfenamic acid, 99+%, J61256, p. 371 | |
| J63895 | Clotrimazole [1-[(2-Chlorophenyl)diphenylmethyl]-1H-imidazole, 1-(o-Chlorotriptyl)imidazole] [23593-75-1], C ₂₂ H ₁₇ ClN ₂ , F.W. 344.84, Powder, m.p. 147-149°, Merck 14,2417, EINECS 245-764-8, RTECS NI4377000, MDL MFCD00057220  | 5g 25g |
| | Application(s): Specific inhibitor of calcium-activated potassium channels | |
| J64314 | Cloxacillin sodium salt [642-78-4], C ₁₈ H ₁₇ ClN ₃ NaO ₅ S, F.W. 457.86, Powder, m.p. 170°, Merck 14,2419, EINECS 211-390-9, RTECS XH8750000, BRN 4103180, MDL MFCD00063568 | 1g 5g 25g |
| J61583 | Clozapine, 98+% [8-Chloro-11-(4-methyl-1-piperazinyl)-5H-dibenzo[b,e][1,4]-diazepine] [5786-21-0], C ₁₈ H ₁₉ Cl ₄ , F.W. 326.83, Solid, m.p. 182-184°, Merck 14,2423, UN2811, EINECS 227-313-7, RTECS HP1750000, MDL MFCD00153785  | 25mg 100mg |
| | Application(s): Potent, selective muscarinic antagonist | |
| | 5'-CMP.2Na , see Cytidine-5'-monophosphate disodium salt, 99+%, J63376, p. 174 CNQX , see 6-Cyano-7-Nitroquinoxaline-2,3-dione, 99+%, J63472, p. 170 | |
| J63246 | Cobalt(II) chloride, 0.5M aq. soln. [7791-13-1], CoCl ₂ , F.W. 129.84, Liquid, UN3077, †  | 50ml 100ml |
| 36554 | Cobalt(II) chloride hexahydrate, ACS, 98.0-102.0% ■ [7791-13-1], CoCl ₂ ·6H ₂ O, F.W. 237.93 (129.84anhy), Crystalline, m.p. 87°, d. 1.924, Merck 14,2437, Fieser 1,155 6,127 10,101 14,99 15,97 18,107 19,104 20,115 21,142, Solubility: Soluble in water, alcohol, acetone, ether, glycerol, UN3077, EINECS 231-589-4, RTECS GG0200000, MDL MFCD00149652, Note: m.p. 52-56° -4H ₂ O, 100° -5H ₂ O, 120-140° -6H ₂ O, † Maximum level of impurities: Insoluble matter 0.01%, NO ₃ 0.01%, SO ₄ 0.01%, Ca 0.005%, Cu 0.002%, Fe 0.005%, Mg 0.005%, Ni 0.1%, K 0.01%, Na 0.05%, Zn 0.03%  | 100g 500g |
| B22031 | Cobalt(II) chloride, anhydrous, 97% ■ [7646-79-9], CoCl ₂ , F.W. 129.84, m.p. 735°, b.p. 1049°, d. 3.367, Merck 14,2437, UN3077, EINECS 231-589-4, RTECS GF9800000, MDL MFCD00010938, Note: d ₂₅ 3.367. Decomposes at 400° on long heating in air., †  | 25g 100g 500g |
| | Coban® 3M , see Monensin sodium salt, 90-95.5%, J61669, p. 294 Cobinamide , see Methylcobalamin hydrate, A11176, p. 286 Coccarboxylase , see Thiamine pyrophosphate chloride, 98%, J61483, p. 366 Coenzyme M sodium salt , see 2-Mercaptoethane sulfonic acid sodium salt, 96%, J63989, p. 281 | |
| J64535 | Cofactor Recycling Enzymes Kit - 8 variants Lyophilized powder, Note: Contains 100mg each of: Alcohol Dehydrogenase A36, Formate Dehydrogenase, Glucose Dehydrogenase A, Glucose Dehydrogenase B, Isocitrate Dehydrogenase A, Malic Decarboxylase A, Malic Decarboxylase B, and Phenylalanine Dehydrogenase | 1each |
| | Application(s): Reduction of NAP+ or NADP+ is coupled to co-factor dependent enzymatic reductions | |

| Stock # | Description | Size |
|--|---|------------------------|
| J63900 | Colcemid, 98+% ▲ ▲ [Demecolcine, N-Methyl-N-desacetylcolchicine] [477-30-5], C ₂₇ H ₂₅ NO ₅ , F.W. 371.43, Powder, m.p. 186°, Merck 14,2887, UN2811, EINECS 207-514-6, RTECS GH0800000, BRN 2822892, MDL MFCD00075459 ☠ H: H301-H361, P: P281-P301+P310-P321-P308+P313-P405-P501a | 50mg 100mg |
| Application(s): Microtubule modulator that depolymerizes microtubules and inactivates spindle fiber formation | | |
| J61072 | Colchicine, 98+% ▲ [64-86-8], C ₂₂ H ₂₅ NO ₅ , F.W. 399.44, Powder, m.p. ca 150° dec., Merck 14,2471, UN1544, EINECS 200-598-5, RTECS GH0700000, BRN 2228813, MDL MFCD00078484, † ☠ H: H300-H340, P: P281-P301+P310-P321-P308+P313-P405-P501a | 1g |
| Application(s): Microtubule disrupting agent, and induces apoptosis in human lymphoma cells | | |
| J60915 | Colistin sulfate [Polymyxin E] [1264-72-8], Powder, Merck 14,2479, UN2811, EINECS 215-034-3, RTECS TR1500000, MDL MFCD00146495 ☠ H: H301, P: P264-P270-P301+P310-P321-P405-P501a | 1g |
| Application(s): A cationic polypeptide antibiotic from the polymyxin family. Binds to lipids on the cell cytoplasmic membrane of Gram-negative bacteria and disrupts the cell wall integrity | | |
| J60218 | Collagen, bovine achilles tendon [9007-34-5], Powder, EINECS 232-697-4, MDL MFCD00130825, † | 1g 5g |
| Application(s): An attachment factor for primary cultures of epithelioid cells | | |
| J62406 | Collagenase, Type I, Clostridium histolyticum [9001-12-1], Powder, Merck 14,2481, EINECS 232-582-9, MDL MFCD00130830, Note: Minimum 125 units per mg protein. One unit releases one micromole of L-leucine equivalents from collagen in 5 hours at 37 degrees and pH 7.5 ☠ ! H: H334-H335-H315-H319-H317, P: P285-P305+P351+P338-P302+P352-P321-P405-P501a | 100mg 1g |
| Application(s): Isolated from Clostridium histolyticum. Degrades native helical collagen fibrils | | |
| A11058 | 2,4,6-Collidine, 99% [2,4,6-Trimethylpyridine] [108-75-8], C ₈ H ₁₁ N, F.W. 121.18, m.p. -43°, b.p. 171-172°, f.p. 54° (129°F), d. 0.916, n _D ²⁰ 1.4980, Merck 14,9718, Fieser 1,155, UN1992, EINECS 203-613-3, RTECS UU0970000, BRN 107283, MDL MFCD00006338, † ☠ ! H: H226-H302-H312-H315-H319-H335, P: P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a Hindered base. For use in the dehydrochlorination of α-chloroketones to enones, see: <i>Org. Synth. Coll.</i> , 4 , 162 (1963). For use in combination with Trifluoromethanesulfonic anhydride, A11767 , for the generation of ketenimines from olefins, see N,N-Dimethylacetamide, A10924 , p. 195. Superior base for peptide coupling reactions, causing less racemization than the more commonly used N-ethylidiisopropylamine or N-methylmorpholine: <i>J. Org. Chem.</i> , 59 , 695 (1994). For comparison with other hindered bases, see: <i>J. Org. Chem.</i> , 61 , 2460 (1996). Solvent for various O-alkyl cleavage reaction by Lil, including hindered esters: <i>J. Org. Chem.</i> , 28 , 2184 (1963), and methyl ethers of phenols: <i>Chem. Commun.</i> , 616 (1969). | 25ml 100ml 500ml |
| J65434 | Coenzyme A trilithium salt, 95% ■ [18439-24-2], C ₂₁ H ₃₃ Li ₃ N ₇ O ₁₆ P ₃ S, F.W. 785.33, Powder, EINECS 242-317-9, MDL MFCD00075848 | 25mg 100mg |
| J65137 | Coenzyme Q-10, 98+% ▲ [Ubiquinone-10, Q-10] [303-98-0], C ₅₉ H ₉₈ O ₄ , F.W. 863.36, Powder, m.p. 48-52°, Merck 14,9843, EINECS 206-147-9, RTECS DK3900000, BRN 1900141, MDL MFCD00042919, † | 1g 5g 25g |
| J65131 | Compound E ▲ [γ-Secretase Inhibitor XXI, Compound E] [209986-17-4], C ₂₇ H ₂₄ F ₂ N ₂ O ₃ , F.W. 490.50, Solid | 0.5mg |
| ConA, see Concanavalin A, J61221, p. 167 | | |
| J61221 | Concanavalin A [ConA] [11028-71-0], Lyophilized powder, Merck 14,2495, EINECS 234-258-2, RTECS GK6890000, MDL MFCD00071069 ☠ H: H334-H317, P: P285-P261-P280-P302+P352-P321-P501a | 100mg 250mg |
| Application(s): A plant lectin that is a T-cell mitogen, and induces apoptosis in human fibroblasts | | |
| J62617 | Conessine, 97% [Neriine, Roquessine] [546-06-5], C ₂₄ H ₄₀ N ₂ , F.W. 356.59, Powder, m.p. 125-127°, Merck 14,2497, EINECS 208-897-2, MDL MFCD00016752 | 100mg 250mg |
| Application(s): Selective histamine H-3 receptor antagonist | | |




| Stock # | Description | Size |
|---------|--|------|
| B24310 | Congo Red, indicator grade [C.I. 22120] [573-58-0], C ₂₂ H ₁₂ N ₄ Na ₂ O ₆ S ₂ , F.W. 696.67, m.p. >360°, Merck 14,2498, EINECS 209-358-4, RTECS QK1400000, BRN 3894858, MDL MFCD00004028, † | 25g |
| | | 100g |
| | 500g | |
| |  | |
| | H:H350-H361d, P:P281-P201-P202-P308+P313-P405-P501a | |
| | Contraceptive Tetrapeptide , see Kentsin, J61809, p. 263 | |
| | Coomassie Brilliant Blue G 250 , see Brilliant Blue G, 43318, p. 135 | |
| A16064 | Copper(II) chloride dihydrate, 99% [Cupric chloride dihydrate] [10125-13-0], CuCl ₂ ·2H ₂ O, F.W. 170.48 (134.45anhy), m.p. 100° dec., d. 2.510, Merck 14,2633, UN2802, EINECS 231-210-2, RTECS GL7030000, MDL MFCD00149674, † | 250g |
| | 1kg | |
| |  H:H314-H400-H410-H302, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P313-P405-P501a | |
| A11262 | Copper(II) sulfate pentahydrate, 99% [Cupric sulfate] [7758-99-8], CuSO ₄ ·5H ₂ O, F.W. 249.68 (159.60anhy), d. 2.270, Merck 14,2653, Fieser 1,164 2,89 5,162 6,141 10,107 19,111, UN3077, EINECS 231-847-6, RTECS GL8900000, MDL MFCD00149681, † | 1kg |
| | 5kg | |
| | 25kg | |
| |  H:H400-H410-H302-H315-H319, P:P260-P273-P501a | |
| 14178 | Copper(II) sulfate pentahydrate, ACS, 98.0-102.0% [7758-99-8], CuSO ₄ ·5H ₂ O, F.W. 249.68 (159.60anhy), Crystalline, d. 2.270, Merck 14,2653, Fieser 1,164 2,89 5,162 6,141 10,107 19,111, Solubility: Soluble in water, methanol, glycerol., UN3077, EINECS 231-847-6, RTECS GL8900000, MDL MFCD00149681, Note: m.p. 30° -2H ₂ O, 110° -4H ₂ O, 250° anhydrous; d ₄ ²⁰ 2.286, † Maximum level of impurities: Insoluble matter 0.005%, Cl 0.001%, Nitrogen compounds (as N) 0.002%, Ca 0.005%, Ni 0.005%, K 0.01%, Na 0.02%, Fe 0.003% | 500g |
| | 2kg | |
| |  H:H400-H410-H302-H315-H319, P:P260-P273-P501a | |
| | Corotrope , see Milirnone, 98+%, J62659, p. 292 | |
| J64182 | Cortisone [17 α ,21-Dihydroxy-4-pregnene-3,11,20-trione, 17 α -Hydroxy-11-dehydrocorticosterone] [53-06-5], C ₂₁ H ₂₈ O ₅ , F.W. 360.44, Powder, m.p. 223-228° dec., Merck 14,2539, EINECS 200-162-4, RTECS GM9020000, BRN 1356062, MDL MFCD00003610 | 1g |
| | 5g | |
| | 10g | |
| A15336 | Coumarin, 98% [1-Benzopyran-2-one] [91-64-5], C ₉ H ₆ O ₂ , F.W. 146.15, m.p. 68-71°, b.p. 297-299°, f.p. 162°(323°F), d. 0.935, Merck 14,2562, UN2811, EINECS 202-086-7, RTECS GN4200000, BRN 383644, MDL MFCD00006850, † | 250g |
| | 1kg | |
| | 5kg | |
| |  | |
| |  H:H301-H351, P:P281-P301+P310-P321-P308+P313-P405-P501a | |
| | Coumarin 120 , see 7-Amino-4-methylcoumarin, A15017, p. 97 | |
| L07133 | Coumarin-3-carboxylic acid, 98% [2-Oxo-2H-1-benzopyran-3-carboxylic acid] [531-81-7], C ₉ H ₆ O ₄ , F.W. 190.15, m.p. 190-193°, Merck 14,2563, UN2811, EINECS 208-518-0, RTECS DJ2490000, BRN 154276, MDL MFCD00006852 | 25g |
| | 100g | |
| |  | |
| | H:H301, P:P264-P270-P301+P310-P321-P405-P501a | |
| | CPT11 , see Irinotecan hydrochloride trihydrate, J62370, p. 259 | |
| J63028 | C-Reactive Protein [CRP] [9007-41-4], Solid, Merck 14,2603, MDL MFCD00130690 | 1mg |
| | Application(s): For immunological applications in the preparation of antisera | |
| B25009 | Creatine monohydrate, 99% [N-Amidinosarcosine monohydrate] [6020-87-7], C ₄ H ₉ N ₃ O ₂ ·H ₂ O, F.W. 149.15 (131.13anhy), m.p. ca 292° dec., Merck 14,2568, EINECS 200-306-6, BRN 907175, MDL MFCD00071582, † | 100g |
| | 500g | |
| | 2.5kg | |
| |  | |
| A15362 | Creatine phosphate disodium salt tetrahydrate, 98+% [Sodium creatine phosphate dibasic tetrahydrate] [71519-72-7], C ₄ H ₈ N ₃ Na ₂ O ₇ ·4H ₂ O, F.W. 327.14 (255.07anhy), EINECS 213-074-6, MDL MFCD00150192 | 1g |
| | 5g | |
| | 25g | |
| |  | |
| | Application(s): Substrate for creatine kinase determinations | |
| B23097 | Creatinine, 98% [2-Imino-1-methylimidazolidin-4-one] [60-27-5], C ₄ H ₇ N ₃ O, F.W. 113.12, m.p. ca 255° dec., Merck 14,2569, EINECS 200-466-7, BRN 112061, MDL MFCD00059730, † | 10g |
| | 50g | |
| | 250g | |
| |  | |
| | H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Reacts with aromatic aldehydes in a route to derivatives of N-methylphenylalanine: <i>Org. Synth. Coll.</i> , 3, 586 (1955): | |




J61755 Creatinine hydrochloride, 99+% **100g**
250g
 [2-Amino-1-methyl-2-imidazolin-4-one]
 [19230-81-0], C₄H₇N₃O·HCl, F.W. 149.60, Crystalline, EINECS 242-898-9, MDL MFCD00134958, †

Application(s): Break-down product of creatine phosphate in muscle

A12899 o-Cresolphthalein **10g**
50g
 [596-27-0], C₂₂H₁₆O₄, F.W. 346.39, m.p. 223-225°, Merck 14,2576, EINECS 209-881-8, RTECS SM8390000, BRN 310554, MDL MFCD00005912, Note: Transition interval pH 8.2 (colorless) to pH 9.8 (red), †




L03859 o-Cresolphthalein complexone, indicator grade **1g**
5g
25g
 [o-Cresolphthalexon, Phthalein complexone]
 [2411-89-4], C₂₈H₂₀N₂O₁₂, F.W. 636.62, m.p. ca 198° dec., EINECS 219-318-8, BRN 381994, MDL MFCD00005911, †
 Indicator for complexometric titration of Mg, Ca, Sr and Ba:
Helv. Chim. Acta, **72**, 113 (1954).




o-Cresolphthalexon, see o-Cresolphthalein complexone, L03859, p. 169

B24338 m-Cresol Purple **5g**
25g
 [m-Cresolsulfonephthalein]
 [2303-01-7], C₂₁H₁₇O₅S, F.W. 382.44, Merck 14,2577, EINECS 218-960-6, BRN 350314, MDL MFCD00005871, Note: Transition interval (acid): pH 1.2 (red) to pH 2.8 (yellow); (alkaline) pH 7.4 (yellow) to pH 9.0 (purple), †




38691 m-Cresol Purple sodium salt, 0.04% w/v aq. soln. **100ml**
500ml
6x100ml
 [62625-31-4], C₂₁H₁₇NaO₅S, F.W. 404.42, Liquid, EINECS 263-656-9, MDL MFCD00005871, Note: Transition interval (acid): pH 1.2 (red) to pH 2.8 (yellow); (alkaline) pH 7.4 (yellow) to pH 9.0 (purple), †

A18025 m-Cresol Purple sodium salt **5g**
25g
 [m-Cresol Purple, water soluble, m-Cresolsulfonephthalein sodium salt]
 [62625-31-4], C₂₁H₁₇NaO₅S, F.W. 404.42, EINECS 263-656-9, MDL MFCD00010177, †



B21361 Cresol Red sodium salt **5g**
25g
100g
 [o-Cresolsulfonephthalein sodium salt]
 [62625-29-0], C₂₁H₁₇NaO₅S, F.W. 404.42, m.p. ca 250° dec., EINECS 263-654-8, MDL MFCD00001618, Note: Transition interval (acid): pH 0.2 (red) to pH 1.8 (yellow); (alkaline) pH 7.2 (yellow) to pH 8.8 (red), †



m-Cresolsulfonephthalein, see m-Cresol Purple, B24338, p. 169

o-Cresolsulfonephthalein sodium salt, see Cresol Red sodium salt, B21361, p. 169

m-Cresolsulfonephthalein sodium salt, see m-Cresol Purple sodium salt, A18025, p. 169

J64318 Cresyl Violet acetate **10g**
 [9-Amino-5-imino-5H-benzo[a]phenoxazine acetate salt, Cresyl echt violet]
 [10510-54-0], C₁₈H₁₅N₃O₃, F.W. 321.33, Powder, m.p. 140-143°, EINECS 234-043-3, MDL MFCD00013151

J65122 Cromolyn sodium salt, 98% **1g**
5g
25g
 [Cromoglycate, Cromoglycic acid]
 [15826-37-6], C₂₃H₁₄Na₂O₁₁, F.W. 512.33, Powder, Merck 14,2590, EINECS 239-926-7, RTECS DJ2380000, MDL MFCD00057744

J62367 Croton oil **10g**
25g
100g
 [Croton resin, Oleum tiglii]
 [8001-28-3], Oil, f.p. 74° (165°F), RTECS GQ6300000, MDL MFCD00130880, †












! H:350-H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P405-P501a






Application(s): A natural source of phorbol, phorbol esters and glycerides of saturated fatty acids

Croton resin, see Croton oil, J62367, p. 169







CRP, see C-Reactive Protein, J63028, p. 168


Crustecdysone, see Ecdysterone, J63091, p. 204

| Stock # | Description | Size |
|---------------|---|----------------------|
| B21932 | Crystal Violet [Basic Violet 3, C.I. 42555] [548-62-9], C ₂₅ H ₃₀ ClN ₃ , F.W. 407.99, m.p. ca 215° dec., Merck 14.4395, UN3077, EINECS 208-953-6, RTECS BO9000000, BRN 4077708, MDL MFCD00011750, †  H: H318-H351-H400-H410-H302, P: P280-P281-P305+P351+P338-P310-P405-P501a | 25g 100g 500g |
| |  | |
| 22866 | Crystal Violet, ACS, 90+% [Basic Violet 3, C.I. 42555] [548-62-9], C ₂₅ H ₃₀ ClN ₃ , F.W. 407.99, Powder, m.p. ca 215° dec., Merck 14.4395, UN3077, EINECS 208-953-6, RTECS BO9000000, BRN 4077708, MDL MFCD00011750, † Specifications: Sensitivity as indicator P.T., Loss on drying ≤7.5%, Absorbance characteristics P.T.  H: H318-H351-H400-H410-H302, P: P280-P281-P305+P351+P338-P310-P405-P501a | 25g 100g |
| | CT53518 , see Tandutinib, 99%, J62004, p. 358 CTP , see Cytidine-5'-triphosphate disodium salt, 98+%, J62238, p. 174 | |
| A16551 | Cupferron, 97+% [N-Nitrosophenylhydroxylamine ammonium salt] [135-20-6], C ₈ H ₉ N ₂ O ₂ , F.W. 155.16, m.p. 154° dec., Merck 14.2622, UN2811, EINECS 205-183-2, RTECS NC4725000, MDL MFCD00078422, †  H: H301-H351-H315-H319-H317, P: P280h-P305+P351+P338-P309-P310 | 25g |
| |  | |
| | Application(s): Reagent for determination of Ce, Cu, Fe, Sn, and Ti | |
| | Cupral , see Sodium diethyldithiocarbamate trihydrate, A15898, p. 345 Cuproin , see 2,2'-Biquinoline, A10907, p. 126 | |
| B21573 | Curcumin, 95% (total curcuminoid content), from Turmeric rhizome [1,7-Bis(4-hydroxy-3-methoxyphenyl)-1,6-heptadiene-3,5-dione, C.I. 75300] [458-37-7], C ₂₁ H ₂₀ O ₆ , F.W. 368.39, m.p. 170-175°, Merck 14.2673, EINECS 207-280-5, RTECS MI5230000, BRN 2306965, MDL MFCD00008365, †  H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 10g 50g 250g |
| |  | |
| | Application(s): Natural Yellow 3. Inhibits lipoxygenase and cyclooxygenase | |
| | Cyanocobalamin , see Vitamin B12, A14894, p. 392 α-Cyano-(3,5-di-t-butyl-4-hydroxy)thiocinnamide , see AG-879, 99%, J62625, p. 81 (E)-2-Cyano-3-(3,4-dihydroxyphenyl)-N-(3-phenylpropyl)-2-propenamide , see Tyrphostin B46, 99+%, J61704, p. 387 (E)-2-Cyano-3-(3,4-dihydroxyphenyl)-2-propenamide , see Tyrphostin A46, 99%, J60482, p. 386 N-Cyanoguanidine , see Dicyandiamide, A10451, p. 187 N-Cyano-N'-methyl-N'-[2-[(5-methyl-1H-imidazol-4-yl)methyl]thio]ethyl]guanidine , see Cimetidine, 98+%, J62825, p. 163 | |
| J63472 | 6-Cyano-7-nitroquinoxaline-2,3-dione, 99+% [CNQX] [115066-14-3], C ₈ H ₄ N ₂ O ₄ , F.W. 232.16, Solid, m.p. >300°, MDL MFCD00069232 | 10mg 25mg 50mg |
| | Application(s): Potent, selective kainate/quisqualate (non-NMDA) receptor antagonist | |
| L03442 | Cyanuric chloride, 98% ▯ [TCT, 2,4,6-Trichloro-1,3,5-triazine] [108-77-0], C ₃ Cl ₃ N ₃ , F.W. 184.41, m.p. 145-149°, b.p. 192-194°, f.p. >190°(374°F), d. 1.920, Fieser 3.72 4.522 5.687 6.149 10.114 15.105 20.124, UN2670, EINECS 203-614-9, RTECS XZ1400000, BRN 124246, MDL MFCD00006046, †  H: H330-H314-H302-H317-EU014, P: P303+P361+P353-P304+P340-P305+P351+P338-P320-P330-P405-P501a | 50g 250g 1kg |
| |  | |
| | In the presence of triethylamine, carboxylic acids are converted to their acid chlorides, allowing <i>in situ</i> formation of esters, amides and peptides: <i>Tetrahedron Lett.</i> , 20 , 3037 (1979). Similarly, sulfonic acids are converted to sulfonyl chlorides: <i>Tetrahedron Lett.</i> , 44 , 1499 (2003). ω-Hydroxy acids are converted to their lactones: <i>Tetrahedron Lett.</i> , 21 , 1893 (1980). Mild reagent in β-lactam synthesis: <i>Synthesis</i> , 209 (1981). Carboxylic acids, including N-Boc, -Fmoc and -Cbz amino acids have been converted to alcohols in good yield by activation with cyanuric chloride and N-methylmorpholine (NMM), followed by reduction with aqueous NaBH ₄ : <i>Tetrahedron Lett.</i> , 40 , 4395 (1999). Hydroxamic acids can also be prepared in a simple one-flask method using hydroxylamine hydrochloride in the presence of NMM and DMAP: <i>Org. Lett.</i> , 5 , 2715 (2003). Effects deoxygenation of diaryl sulfoxides. Alkyl sulfoxides undergo α-chlorination, which can be avoided by using cyanuric fluoride: <i>Synthesis</i> , 221 (1980). For use, in combination with DMSO, in a mild and efficient alternative to the Swern oxidation of alcohols to aldehydes or ketones, see: <i>J. Org. Chem.</i> , 66 , 7907 (2001). Reagent for dehydration of aldoximes: <i>J. Chem. Soc., Chem. Commun.</i> , 1226 (1972), and primary carboxamides: <i>Synthesis</i> , 657 (1980) to nitriles. The Vilsmeier-type complex with DMF also converts aldoximes cleanly to nitriles; ketoximes undergo the Beckmann rearrangement at room temperature in high yield: <i>J. Org. Chem.</i> , 67 , 6272 (2002). The complex converts primary and secondary alcohols to alkyl chlorides in high yield; addition of NaBr affords mainly the alkyl bromide: <i>Org. Lett.</i> , 4 , 553 (2002); whereas with 4 eq. of LiF, primary alcohols are selectively formylated, providing a mild and convenient method for their protection: <i>J. Org. Chem.</i> , 67 , 5152 (2002). For a brief feature on uses of the reagent in synthesis, see: <i>Synlett</i> , 2156 (2006). | |
| | Application(s): Reagent for detection of glycine in presence of other amino acids | |
| | 3',5'-Cyclic AMP , see Adenosine-3',5'-monophosphoric acid free acid, 98%, J60936, p. 79 | |

| Stock # | Description | Size |
|---------|--|---|
| J65001 | Cyclic AMP Enzyme Immunoassay Kit Note: Contains reagents reagents and two coated 96-well strip ELISA plates to perform the ELISA either acetylated or unacetylated Application(s): For detection of cGMP. Detection range is 0.05pmol/ml | 1kit |
| | 3',5'-Cyclic AMP Na , see Adenosine-3',5'-cyclic monophosphate sodium salt, 99%, J62174, p. 79 | |
| J65422 | Cyclic GMP Enzyme Immunoassay Kit Note: Contains reagents reagents and two coated 96-well strip ELISA plates to perform the ELISA either acetylated or unacetylated Application(s): For detection of cAMP. Detection range is 0.05pmol/ml | 1kit |
| | 1,1-Cyclobutanedicarboxylatodiammineplatinum(II) , see Carboplatin, J60433, p. 148 | |
| J63845 | Cyclocytidine hydrochloride, 98+% [Ancitabine hydrochloride, O-2,2'-Cyclocytidine hydrochloride] [10212-25-6], C ₉ H ₁₁ N ₃ O ₄ ·HCl, F.W. 261.66, Powder, m.p. 248-250°, Merck 14,629, EINECS 233-515-6, RTECS LV2615000, MDL MFCD00012636 Application(s): Anti-tumor agent | 1g 5g |
| | O-2,2'-Cyclocytidine hydrochloride , see Cyclocytidine hydrochloride, 98+%, J63845, p. 171 | |
| J60687 | α-Cyclodextrin, 97+% [Schardinger α-dextrin, Cyclohexaamylose] [10016-20-3], C ₃₆ H ₆₀ O ₃₀ , F.W. 972.84, Powder, EINECS 233-007-4, MDL MFCD00078207, † Application(s): Useful for selective precipitation of enantiomeric, positional or structural isomers | 5g 25g 100g |
| J63161 | β-Cyclodextrin [7585-39-9], C ₄₂ H ₇₀ O ₃₅ , F.W. 1134.98, Powder, m.p. 290° dec., EINECS 231-493-2, RTECS GU2293000, BRN 78623, MDL MFCD00078139, † Application(s): Use to solubilize non-polar compounds such a fatty acids, lipids and cholesterol. Reported useful for the selective precipitation of enantiomeric, positional or structural isomers | 25g 100g |
| A14529 | β-Cyclodextrin hydrate [Schardinger β-dextrin, Cycloheptaamylose] [68168-23-0], C ₄₈ H ₇₀ O ₃₅ ·xH ₂ O, F.W. 1134.98(anhy), m.p. 288° dec., [α] _D ²⁰ +142° (c=1.5 in water), Merck 14,2718, Fieser 6,151 8,133 9,129 12,150 15,107 18,117 21,151, EINECS 231-493-2, RTECS GU2293000, BRN 5915513, MDL MFCD00150811, † Has been used to influence regioselectivity in Diels-Alder reactions: <i>J. Chem. Soc., Chem. Commun.</i> , 971 (1995); for reaction scheme, see 2,6-Dimethyl-p-benzoquinone, A11342 . Encapsulation of aniline and N-substituted anilines allows regioselective bromination: <i>Tetrahedron</i> , 52, 3487 (1996). Catalyzes the Boc protection of amines with Di-tert-butyl dicarbonate, A14708 , p. 184 under neutral, aqueous conditions: <i>Synlett</i> , 1110 (2006). For a brief of uses as a supramolecular catalyst in organic synthesis, see: <i>Synlett</i> , 175 (2007). |  5g 25g 100g |
| L11271 | γ-Cyclodextrin hydrate [Schardinger γ-dextrin] [91464-90-3], C ₅₈ H ₉₀ O ₄₀ ·xH ₂ O, F.W. 1297.15(anhy), m.p. ca 267° dec., [α] _D ²⁰ +177° (c=1 in water) on dry basis, Merck 14,2718, Fieser 9,129, EINECS 241-482-4, BRN 5725162, MDL MFCD00149574, † For general reviews on cyclodextrins see α-cyclodextrin. |  100mg 500mg |
| | Cycloheptaamylose , see β-Cyclodextrin hydrate, A14529, p. 171 Cyclohexaamylose , see α-Cyclodextrin, 97+%, J60687, p. 171 (1S,2S)-(+)-1,2-Diaminocyclohexane , see (1S,2S)-(+)-1,2-Diaminocyclohexane, L14072, p. 182 Cyclohexanone-4-carboxylic acid , see 4-Oxocyclohexanecarboxylic acid, H27294, p. 310 | |
| A15851 | Cyclohexylamine, 98+% Δ [Aminocyclohexane] [108-91-8], C ₆ H ₁₁ N, F.W. 99.18, m.p. -18°, b.p. 133-134°, f.p. 27° (81°F), d. 0.868, n _D ²⁰ 1.4585, Merck 14,2729, UN2357, EINECS 203-629-0, RTECS GX0700000, BRN 471175, MDL MFCD00001486, †  100ml 500ml 2.5L ⚠️ H: H314-H226-H361f-H302-H312, P: P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a For protection of an aldehyde as its cyclohexyl imine, see, e.g.: <i>Org. Synth. Coll.</i> , 8, 586 (1993). Cyclohexyl imines of aldehydes have found use in the directed aldol synthesis: reaction with a less reactive ketone takes place in preference to self-condensation of the aldehyde. See, e.g.: <i>Org. Synth. Coll.</i> , 6, 901 (1988):  | |
| | 2-(Cyclohexylamino)ethanesulfonic acid , see CHES, A18047, p. 153 3-Cyclohexylamino-2-hydroxy-1-propanesulfonic acid , see CAPSO, B21305, p. 146 3-Cyclohexylamino-2-hydroxy-1-propanesulfonic acid sodium salt , see CAPSO sodium salt, B25202, p. 146 3-Cyclohexylamino-1-propanesulfonic acid , see CAPS, A17037, p. 145 | |
| B23056 | N-Cyclohexylmaleimide, 97% [1631-25-0], C ₁₀ H ₁₃ NO ₂ , F.W. 179.22, m.p. 89-91°, EINECS 216-630-6, MDL MFCD00043904, † ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a  | 1g 5g 25g |
| | 1-Cyclohexyl-3-4-[2-(5-methylpyrazine-2-carboxamido)ethyl]phenylsulfonylurea , see Glipizide, J63398, p. 232 | |


| Stock # | Description | Size |
|---|---|--------------------------|
| J61528 | Cyclopamine, 99+% [4449-51-8], C ₂₇ H ₄₁ NO ₂ , F.W. 411.62, Powder, m.p. 234-237°, RTECS GY0750000 H: H341-H361, P: P281-P201-P202-P308+P313-P405-P501a | 25mg 50mg |
| Application(s): Inhibits hedgehog/smoothened signaling. A steroidal alkaloid | | |
| J61565 | 8-Cyclopentyl-1,3-dimethylxanthine [NSC 101806] [35873-49-5], C ₁₂ H ₁₈ N ₂ O ₂ , F.W. 248.28, Powder, m.p. 250-252°, RTECS XH5093600, MDL MFCD00055116 | 100mg |
| Application(s): A selective A1 adenosine receptor antagonist | | |
| L11508 | Cyclophosphamide monohydrate, 97+% [Bis(2-chloroethyl)phosphoramidic cyclic propanolamide ester, Cyclophosphane] [6055-19-2], C ₇ H ₁₀ Cl ₂ N ₂ O ₂ P·H ₂ O, F.W. 279.10 (261.09anhy), m.p. 51-53°, Merck 14,2747, UN3464, EINECS 200-015-4, RTECS RP6157750, BRN 8167897, MDL MFCD00149395, Note: Special handling precautions required. View MSDS prior to purchase. MSDS are available online at www.alfa.com H: H301-H340-H350-H360, P: P281-P301+P310-P321-P308+P313-P405-P501a | 1g 5g |
| Application(s): Cancer research tool that induces apoptosis in tumor cells | | |
| Cyclophosphane, see Cyclophosphamide monohydrate, L11508, p. 172 | | |
| J61594 | Cyclopiiazonic acid, 99+% [18172-33-3], C ₂₀ H ₂₀ N ₂ O ₃ , F.W. 336.39, Powder, UN2811, RTECS UY8587000, MDL MFCD00167445 | 10mg 50mg |
| Application(s): Inhibitor of the sarco/endoplasmic reticulum calcium pump, calcium-ATPase | | |
| 1-Cyclopropyl-7-(4-ethyl-1-piperazinyl)-6-fluoro-1,4-dihydro-4-oxoquinoline-3-carboxylic acid , see Enrofloxacin, J60023, p. 207 | | |
| A18000 | D-Cycloserine, 98+% [(R)-(+)-4-Amino-3-isoxazolidinone] [68-41-7], C ₅ H ₈ N ₂ O ₂ , F.W. 102.09, m.p. 137° dec., [α] _D ²⁰ +115° (c=2 in water), Merck 14,2751, Solubility: Soluble in water. Slightly soluble in methanol, propylene glycol., EINECS 200-688-4, RTECS NY2975000, BRN 80798, MDL MFCD00005353 | 1g 5g |
| Application(s): Inhibits bacterial cell wall biosynthesis. Prevents conversion of D-Alanine to L-Alanine | | |
| J63191 | Cyclosporin A, 99+% [Cyclosporine A, Antibiotic S 7481F1] [59865-13-3], C ₃₈ H ₆₄ N ₁₀ O ₁₂ , F.W. 1202.61, Crystalline solid, m.p. 146-151°, Merck 14,2752, RTECS GZ4120000, BRN 3647785, MDL MFCD00274558 H: H361-H302, P: P281-P264-P301+P312-P308+P313-P405-P501a | 1g 5g |
| Application(s): Immunosuppressant. Induces apoptosis and inhibits angiogenesis induced by VEGF | | |
| Cyclosporine A, see Cyclosporin A, 99+%, J63191, p. 172 | | |
| J65998 | Cypermethrin, 95% [α-Cyano-(3-phenoxyphenyl)methyl 3-(2,2-dichlorovinyl) -2,2-dimethylcyclopropanecarboxylate] [52315-07-8], C ₂₂ H ₁₉ Cl ₂ NO ₃ , F.W. 416.30, Oil or liquid, f.p. 100°(212°F), Merck 14,2767, UN2810, EINECS 257-842-9, RTECS GZ1250000, MDL MFCD00055328 H: H301-H335-H373-H410, P: P260-P261-P301+P310-P321-P405-P501 | 100mg 1g 5g 25g |
| J63142 | Cyproconazole [94361-06-5], C ₁₈ H ₁₈ ClN ₂ O, F.W. 291.78, Crystalline, m.p. 108°, b.p. >250°, f.p. >100°(212°F), Merck 14,2771, UN3077, RTECS XZ4803250, BRN 8396421, MDL MFCD01678672 H: H361d-H400-H410-H302, P: P281-P273-P301+P312-P308+P313-P405-P501a | 5g 10g |
| Application(s): Causes hepatocellular adenomas and carcinomas | | |
| H-DL-(Cys)2-OH, see DL-Cystine, J63564, p. 173 | | |
| B22873 | Cystamine dihydrochloride, 97+% ■ [Bis(2-aminoethyl) disulfide dihydrochloride] [56-17-7], (H ₂ NCH ₂ CH ₂ S) ₂ ·2HCl, F.W. 225.20, m.p. 217-220°, Merck 14,2776, EINECS 200-260-7, RTECS KR7260000, BRN 3616850, MDL MFCD00012905, † H: H302, P: P280f | 25g 100g |
| J62240 | Cystatin, 95% [81989-95-9], Powder, MDL MFCD00130887 | 1mg |
| Cysteamine hydrochloride, see 2-Mercaptoethylamine hydrochloride, A14377, p. 281 | | |
| H56126 | DL-Cysteine, 96% [DL-2-Amino-3-mercaptopropionic acid, H-DL-Cys-OH] [3374-22-9], C ₃ H ₇ NO ₂ S, F.W. 121.16, m.p. 225° dec., EINECS 222-160-2, RTECS HA1595000, BRN 1721406, MDL MFCD00004881 | 5g 25g 100g |
| A10435 | L-Cysteine, 98+% △ [L-2-Amino-3-mercaptopropionic acid, H-Cys-OH] [52-90-4], C ₃ H ₇ NO ₂ S, F.W. 121.16, m.p. ca 220° dec., [α] _D ²⁰ +7.6° (c=5 in 5N HCl), Merck 14,2781, EINECS 200-158-2, RTECS HA1600000, BRN 1721408, MDL MFCD00064306, † H: H302, P: P264-P270-P301+P312-P330-P501a | 50g 250g 1kg |



| Stock # | Description | Size |
|---------|---|--|
| J63745 | L-Cysteine, Cell Culture Reagent Δ [L-2-Amino-3-mercaptopropionic acid] [52-90-4], C ₃ H ₇ NO ₂ S, F.W. 121.16, Powder, m.p. ca 220° dec., Merck 14,2781, EINECS 200-158-2, RTECS HA1600000, BRN 1721408, MDL MFCD00064306, † ! H: H302, P: P264-P270-P301+P312-P330-P501a | 25g 100g |
| H27107 | D-Cysteine hydrochloride monohydrate, 99% [D-2-Amino-3-mercaptopropionic acid hydrochloride monohydrate, H-D-Cys-OH.HCl.H ₂ O] [207121-46-8], C ₃ H ₇ NO ₂ S.HCl.H ₂ O, F.W. 175.64 (157.62anhy), m.p. 184-186°, EINECS 251-043-9, MDL MFCD00150051 ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a |  1g 5g |
| A10389 | L-Cysteine hydrochloride monohydrate, 99% Δ [H-Cys-OH.HCl.H ₂ O] [7048-04-6], C ₃ H ₇ NO ₂ S.HCl.H ₂ O, F.W. 175.64 (157.62anhy), m.p. ca 175° dec., [α] _D ²⁰ +5.5° (c=5 in 5N HCl), Merck 14,2781, EINECS 200-157-7, RTECS HA2285000, BRN 5158059, MDL MFCD00065606, † ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a |  25g 100g 500g |
| L06328 | L-Cysteine hydrochloride, anhydrous, 98% Δ \blacksquare [H-Cys-OH.HCl] [52-89-1], C ₃ H ₇ NO ₂ S.HCl, F.W. 157.62, m.p. ca 180° dec., [α] _D ²⁰ +6.4° (c=5 in 5N HCl), Merck 14,2781, EINECS 200-157-7, RTECS HA2275000, BRN 3560277, MDL MFCD00064553, † ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a |  25g 100g |
| J64436 | L-Cysteine methyl ester hydrochloride [L-Cys-OMe HCl] [18598-63-5], C ₄ H ₉ NO ₂ S.HCl, F.W. 171.65, Crystalline powder, m.p. 142° dec., Merck 14,5785, EINECS 242-435-0, RTECS HA2460000, BRN 3685824, MDL MFCD00038998 | 25g 100g 250g |
| J63564 | DL-Cystine [H-DL-(Cys) ₂ -OH, (±)-3,3'-Dithiobis(2-aminopropionic acid)] [923-32-0], C ₆ H ₁₂ N ₂ O ₄ S ₂ , F.W. 240.30, Powder, m.p. 227° dec., Merck 14,2782, EINECS 213-094-5, BRN 1728095, MDL MFCD00084652 | 5g 25g 100g |
| L13772 | D-Cystine, 98% [H-D-(Cys) ₂ -OH, (+)-3,3'-Dithiobis(2-aminopropionic acid)] [349-46-2], C ₆ H ₁₂ N ₂ O ₄ S ₂ , F.W. 240.30, m.p. ca 250° dec., [α] _D ²⁰ +219° (c=1 in 1N HCl), Merck 14,2782, EINECS 206-486-2, BRN 1728093, MDL MFCD00002610 |  1g 5g |
| A13762 | L-Cystine, 99% [H-(Cys) ₂ -OH, (-)-3,3'-Dithiobis(2-aminopropionic acid)] [56-89-3], C ₆ H ₁₂ N ₂ O ₄ S ₂ , F.W. 240.30, m.p. >240° dec., d. 1.68, [α] _D ²⁰ -219° (c=1 in 1N HCl), Merck 14,2782, EINECS 200-296-3, RTECS HA2690000, BRN 1728094, MDL MFCD00064228, † |  50g 250g 1kg |
| J61651 | L-Cystine, Cell Culture Reagent [H-(Cys) ₂ -OH, (-)-3,3'-Dithiobis(2-aminopropionic acid)] [56-89-3], C ₆ H ₁₂ N ₂ O ₄ S ₂ , F.W. 240.30, Powder, m.p. >240° dec., d. 1.68, Merck 14,2782, EINECS 200-296-3, RTECS HA2690000, BRN 1728094, MDL MFCD00064228, † | 10g 100g 500g 1kg |
| J62292 | L-Cystine dihydrochloride, 99% [30925-07-6], C ₆ H ₁₂ N ₂ O ₄ S ₂ .2HCl, F.W. 313.22, Powder, m.p. 228-232°, EINECS 250-391-9, MDL MFCD00070399, † | 25g 100g 250g |
| J63717 | L-Cystine dihydrochloride, Cell Culture Reagent [30925-07-6], C ₆ H ₁₂ N ₂ O ₄ S ₂ .2HCl, F.W. 313.22, Powder, m.p. 228-232°, EINECS 250-391-9, MDL MFCD00070399, † | 250g 1kg |
| J63071 | L-Cystine disodium salt monohydrate, 98+% [199329-53-8], C ₆ H ₁₀ N ₂ Na ₂ O ₄ S ₂ .H ₂ O, F.W. 302.27 (284.26anhy), Powder, EINECS 265-025-3, † | 50g 250g |
| J62310 | L-Cystine disodium salt, 98+% [64704-23-0], C ₆ H ₁₀ N ₂ Na ₂ O ₄ S ₂ , F.W. 284.30, Powder, EINECS 265-025-3, † | 250g 1kg |
| A10261 | Cytidine, 99% \blacksquare [65-46-3], C ₉ H ₁₃ N ₃ O ₅ , F.W. 243.22, m.p. ca 215° dec., [α] _D ²⁰ +29° (c=9 in water), Merck 14,2786, EINECS 200-610-9, RTECS UW7370000, BRN 89173, MDL MFCD00006545, † |  10g 50g 250g |




| Stock # | Description | Size |
|--|--|-------------------|
| J64234 | Cytidine-5'-diphosphate disodium salt, 98% [CDP disodium salt] [54394-90-0], C ₉ H ₁₃ N ₃ Na ₂ O ₁₁ P ₂ , F.W. 447.10, Powder, MDL MFCD00084682 | 1g |
| J64350 | Cytidine-5'-diphosphate trisodium salt [CDP trisodium salt] [34393-59-4], C ₉ H ₁₂ N ₃ Na ₃ O ₁₁ P ₂ , F.W. 469.12, Crystalline powder, EINECS 251-990-8, MDL MFCD00065201 | 25mg 1g |
| J64161 | Cytidine-5'-diphosphocholine [Citicoline] [987-78-0], C ₁₄ H ₂₆ N ₄ O ₁₁ P ₂ , F.W. 488.32, Powder | 10g 25g 50g |
| J63376 | Cytidine-5'-monophosphate disodium salt, 99+% [5'-CMP.2Na] [6757-06-8], C ₉ H ₁₂ N ₃ Na ₂ O ₈ P, F.W. 367.16, Crystalline powder, MDL MFCD00064355 | 1g 5g 25g |
| J62238 | Cytidine-5'-triphosphate disodium salt, 98+% [CTP] [36051-68-0], C ₉ H ₁₄ N ₃ Na ₂ O ₁₄ P ₃ , F.W. 527.12, Powder, f.p. 113°(235°F), EINECS 252-849-3, MDL MFCD00078193 | 500mg 1g 2g |
| J60280 | Cytochalasin A ▲ [14110-64-6], C ₂₈ H ₃₅ NO ₅ , F.W. 477.60, Powder, Merck 14,2790, UN1544, EINECS 237-964-9, BRN 949521, MDL MFCD00005935 ⚠ ! H:H361-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 1mg 5mg |
| Application(s): An anti-cytoskeletal compound. Inhibits glucose transport, actin polymerization and blocks the formation of microtubules. Inhibits cell division. Inhibits HIV-1 protease | | |
| J65342 | Cytochalasin B [Phomin] [14930-96-2], C ₂₈ H ₃₇ NO ₅ , F.W. 479.61, Powder, m.p. 218-221°, Merck 14,2790, UN1544, EINECS 239-000-2, RTECS RO0205000, BRN 1096207, MDL MFCD00077704 ⚠ ! H:H300-H310-H330-H361, P:P301+P310-P304+P340-P320-P330-P361-P405-P501 | 5mg 10mg |
| J62122 | Cytochrome C, equine heart, 90+% [9007-43-6], Powder, Merck 14,2791, EINECS 232-700-9, RTECS HA5365000, MDL MFCD00130890, † | 1g |
| Application(s): A component of the electron transport chain in mitochondria | | |
| A14731 | Cytosine, 98+% [4-Amino-2-hydroxypyrimidine] [71-30-7], C ₄ H ₅ N ₃ O, F.W. 111.10, m.p. >300°, Merck 14,2795, EINECS 200-749-5, RTECS UW7350150, BRN 2637, MDL MFCD00006034, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 5g 25g 100g |
| |  | |
| J65671 | Cytosine-β-D-arabinofuranose hydrochloride [1-(β-D-Arabinofuranosyl)cytosine HCl, Cytarabine HCl] [69-74-9], C ₈ H ₁₃ N ₃ O ₅ ·HCl, F.W. 279.68, Powder, m.p. 197-198°, EINECS 200-713-9, RTECS HA5500000, MDL MFCD00012839 ! ⚠ H:H319-H317-H361, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g 5g 10g |
| Cytosine deoxyriboside hydrochloride, see 2'-Deoxycytidine hydrochloride, L14153, p. 178 2,4-D, see 2,4-Dichlorophenoxyacetic acid, A12467, p. 186 D609 potassium salt, see Tricyclodecan-9-yl xanthogenate potassium salt, 98+%, J63015, p. 376 | | |
| J65995 | D-64131 [(5-Methoxy-1H-indol-2-yl)phenylmethanone] [74588-78-6], C ₁₈ H ₁₃ NO ₂ , F.W. 251.28, Crystalline solid | 10mg |
| DAB tetrahydrochloride hydrate, see 3,3'-Diaminobenzidine tetrahydrochloride hydrate, J62216, p. 182 | | |
| J61023 | Dacarbazine [Dacatic, Deticene] [4342-03-4], C ₈ H ₁₀ N ₄ O, F.W. 182.18, Powder, m.p. 210-212°, Merck 14,2798, EINECS 224-396-1, RTECS NI3950000, MDL MFCD00057167 ! ⚠ H:H302-H312-H332-H315-H319-H340-H350-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 500mg 1g |
| Application(s): Used in treatment of malignant melanoma and sarcomas. Generates methyl adducts to purine bases in DNA | | |
| Dacatic, see Dacarbazine, J61023, p. 174 DACH, see (1S,2S)-(+)-1,2-Diaminocyclohexane, L14072, p. 182 Dactinomycin, see Actinomycin D, J60148, p. 78 | | |
| J60431 | DAGO [Tyr-D-Ala-Gly-N-Me-Phe-Gly-ol, DAMGO] [100929-53-1], C ₂₈ H ₃₈ N ₂ O ₆ , F.W. 513.59, Powder, MDL MFCD00133215 | 5mg |
| Application(s): Mu-opioid receptor-specific enkephalin analog Daidzein, see 4',7-Dihydroxyisoflavone, 98+%, J63763, p. 192 DAMGO, see DAGO, J60431, p. 174 | | |


| Stock # | Description | Size |
|---------|---|-------------------------------|
| | 4-DAMP methiodide , see 4-Diphenylacetoxy-N-methylpiperidine methiodide, J62298, p. 198 | |
| J62200 | Danazol [17230-88-5], C ₂₂ H ₂₇ NO ₂ , F.W. 337.46, Powder, Merck 14,2812, EINECS 241-270-1, RTECS TU4157070, MDL MFCD00056838 ! ⚠ H: H302-H312-H332-H361, P: P261-P280-P281-P302+P352-P405-P501 | 100mg 500mg |
| | Application(s): Danazol is a weak androgen. Also an anterior pituitary suppressant | |
| J62904 | Danofloxacin [112398-08-0], C ₁₉ H ₂₀ FN ₂ O ₃ , F.W. 357.38, Powder, m.p. 268-272°, Merck 14,2813, MDL MFCD00864910 | 500mg 1g |
| | Application(s): Synthetic fluoroquinolone with broad spectrum anti-bacterial activity | |
| A11449 | Dansyl amide, 98% [5-Dimethylamino-1-naphthalenesulfonamide, DNSA] [1431-39-6], C ₁₂ H ₁₄ N ₂ O ₂ S, F.W. 250.32, m.p. 218-221°, EINECS 215-854-1, BRN 2217203, MDL MFCD00040000 Active site probe for enzymes. | 1g 5g 25g |
| | Application(s): Active site probe for carbonic anhydrase | |
| A13828 | Dansyl chloride, 97+% ▽ [5-Dimethylaminonaphthalene-1-sulfonyl chloride, DNSCl] [605-65-2], C ₁₂ H ₉ ClNO ₂ S, F.W. 269.75, m.p. 69-75°, Merck 14,2814, UN3261, EINECS 210-092-6, RTECS QK3688000, BRN 2217205, MDL MFCD00003985, † ⚠ H: H314, P: P280-P303+P361+P353-P305+P351+P338-P310 Reagent for the preparation of fluorescent derivatives of amino acids and proteins: <i>Biochemistry</i> , 9, 3878 (1970); <i>Anal. Biochem.</i> , 53, 132 (1973); 66, 104 (1975). | 1g 5g 25g |
| | Application(s): Used for N terminal amino acid and peptide labeling | |
| J60887 | Dantrolene sodium salt [14663-23-1], C ₂₁ H ₁₉ NaO ₅ , F.W. 336.23, Crystalline powder, Merck 14,2816, EINECS 238-706-8, RTECS MU3875000, MDL MFCD00079130 ⚠ H: H360, P: P281-P201-P202-P308+P313-P405-P501 | 100mg |
| | Application(s): Inhibits intracellular calcium release from the sarcoplasmic reticulum | |
| J65864 | DAPT ▲ [LY-374973, N-[N-(3,5-Difluorophenacetyl)-L-alanyl]-S-phenylglycine tert-butyl ester] [208255-80-5], C ₂₃ H ₂₆ F ₂ N ₂ O ₄ , F.W. 432.50, Lyophilized, MDL MFCD04974585 | 10mg |
| J60621 | Dasatinib [BMS-354825] [302962-49-8], C ₂₂ H ₂₆ ClN ₂ O ₂ S, F.W. 488.01, Powder or granular, Merck 14,2829, RTECS XJ3466000 ⚠ ! H: H360-H373-H302, P: P260-P281-P301+P312-P308+P313-P405-P501a | 250mg 500mg 1g |
| | Application(s): Inhibitor of tyrosine kinases | |
| J62972 | Dasatinib monohydrate [863127-77-9], C ₂₂ H ₂₆ ClN ₂ O ₂ S·H ₂ O, F.W. 506.02 (488.01anhy), Crystalline powder ⚠ ! H: H360-H373-H302, P: P260-P281-P301+P312-P308+P313-P405-P501a | 100mg 500mg 1g |
| | Application(s): Tyrosine kinase inhibitor | |
| | Daunomycin , see Daunorubicin hydrochloride, J60224, p. 175 | |
| J60224 | Daunorubicin hydrochloride ▀ [Daunomycin, Leukaemomycin C] [23541-50-6], C ₂₇ H ₂₉ NO ₁₀ ·HCl, F.W. 563.98, Red powder, Merck 14,2832, UN2811, EINECS 245-723-4, RTECS HB7878000, BRN 4229221, MDL MFCD04974507 ☠ ⚠ H: H301-H334-H351-H317, P: P285-P301+P310-P302+P352-P321-P405-P501a | 10mg |
| | DCC , see N,N'-Dicyclohexylcarbodiimide, A10973, p. 187 | |
| | DCM , see Dichloromethane, L13089, p. 186 | |
| | DEAE-Dextran , see Diethylaminoethyl dextran, J63781, p. 188 | |
| J62821 | Deblock trichloroacetic acid soln., 3% w/w in dichloromethane [DEBLK soln.] Liquid, d. 1.325, UN2810, † ⚠ ! ⚠ H: H318-H351-H335+H336-H315-H411, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 200ml 450ml 2.5L |
| | Application(s): Solvent specially purified and analyzed for biotechnology applications, including peptide and oligonucleotide synthesis | |
| A13883 | Decahydronaphthalene, cis + trans, 98% [91-17-8], C ₁₀ H ₁₈ , F.W. 138.25, m.p. <45°, b.p. 189-191°, f.p. 57°(134°F), d. 0.88, n _D ²⁰ 1.4740, Merck 14,2846, UN 1147, EINECS 202-046-9, RTECS QJ3150000, BRN 878165, MDL MFCD00004130, † ☠ ⚠ H: H331-H226-H315-H319-H335-H411, P: P260-P280h-P273-P305+P351+P338-P309-P310 | 100ml 500ml 2.5L 10L |
| | Decamethylenediamine , see 1,10-Diaminodecane, 98%, J63821, p. 183 | |

| Stock # | Description | Size |
|---------|--|-----------------|
| A11656 | Decanal, 96% Δ [Capric aldehyde, Decyl aldehyde] [112-31-2], $\text{CH}_2(\text{CH}_2)_9\text{CHO}$, F.W. 156.27, m.p. -5°, b.p. 207-209°, f.p. 85° (185°F), d. 0.828, n_D^{20} 1.4280, EINECS 203-957-4, RTECS HD6000000, BRN 1362530, MDL MFCD00007031, † | 100ml 500ml |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | 1,10-Decanediamine , see 1,10-Diaminododecane, 98%, J63821, p. 183 1-Decanesulfonic acid sodium salt , see Sodium 1-decanesulfonate, A14638, p. 345 | |
| J60173 | N-Decanoyl-N-methylglucamine [MEGA-10, N-(D-Glucityl)-N-methyldecanamide] [85261-20-7], $\text{C}_{17}\text{H}_{33}\text{NO}_6$, F.W. 349.46, Powder, m.p. 91-93°, BRN 6974359, MDL MFCD00036801 | 1g 5g |
| | Application(s): Non-ionic detergent for solubilizing membrane proteins | |
| | Decyl aldehyde , see Decanal, A11656, p. 176 | |
| J65900 | (2S,5S)-8-Decylbenzolactam V [(2S,5S)-8-decyl-5-(hydroxymethyl)-2-isopropyl-1-methyl-1,2,5,6-tetrahydrobenzo[e][1,4]diazocin-3(4H)-one] $\text{C}_{25}\text{H}_{42}\text{N}_2\text{O}_2$, F.W. 402.61, Oil | 0.5mg |
| | n-Decyl methyl ketone , see 2-Dodecanone, A18862, p. 201 | |
| J63123 | (+)-Dehydroabietylamine hydrochloride [Leelamine hydrochloride] [1446-61-3], $\text{C}_{20}\text{H}_{31}\text{N}\cdot\text{HCl}$, F.W. 321.90, White solid, EINECS 215-899-7, RTECS TP8701000, BRN 3084620, MDL MFCD00213430, † | 10mg 50mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): Resolving agent for carboxylic acids | |
| | Dehydroacetic acid sodium salt , see Sodium dehydroacetate, B21060, p. 345 | |
| A19666 | Dehydrocholic acid, 99% [3,7,12-Trioxo-5 β -cholan-24-oic acid, 3,7,12-Triketocholanic acid] [81-23-2], $\text{C}_{24}\text{H}_{38}\text{O}_8$, F.W. 402.54, m.p. 235-238°, $[\alpha]_D^{20} +26^\circ$ (c=1 in ethanol), Merck 14,2868, EINECS 201-335-7, RTECS FZ2300000, BRN 3226734, MDL MFCD00066410, † | 50g 250g |
| | H:H303, P:P312 | |
| | Application(s): A bile acid generated from oxidation of cholic acid | |
| J63678 | Delicious Peptide, bovine [H-Lys-Gly-Asp-Glu-Glu-Ser-Leu-Ala-OH] [73984-05-1], $\text{C}_{24}\text{H}_{37}\text{N}_5\text{O}_{16}$, F.W. 847.88, Powder | 5mg |
| | Application(s): A peptide with delicious beefy taste; originally extracted from beef meat | |
| | Delphinidenolol 1575 , see Myricetin, 98%, J60450, p. 296 | |
| J63334 | Delta Sleep-Inducing Peptide [DSIP, Trp-Ala-Gly-Gly-Asp-Ala-Ser-Gly-Glu] [62568-57-4], $\text{C}_{35}\text{H}_{48}\text{N}_{10}\text{O}_{15}$, F.W. 848.81, Powder, Merck 14,3458, MDL MFCD00076883 | 1mg 5mg |
| | Delta Yellow , see Nitrazine Yellow, J60281, p. 303 Deltorphan B , see Deltorphan II, J62286, p. 176 Deltorphan C , see Deltorphan I, J60952, p. 176 | |
| J60952 | Deltorphan I [Tyr-D-Ala-Phe-Asp-Val-Val-Gly-NH ₂ , Deltorphan C] [122752-15-2], $\text{C}_{37}\text{H}_{52}\text{N}_6\text{O}_{10}$, F.W. 768.87, Powder | 1mg 5mg |
| | Application(s): Selective delta-opioid receptor agonist | |
| J62286 | Deltorphan II [Tyr-D-Ala-Phe-Glu-Val-Val-Gly amide, Deltorphan B] [122752-16-3], $\text{C}_{38}\text{H}_{54}\text{N}_6\text{O}_{10}$, F.W. 782.88, Powder, MDL MFCD00080072 | 1mg 5mg |
| | Application(s): Selective delta-2 opioid receptor agonist | |
| J63102 | Demeclocycline hydrochloride [Clortetrin, Mexocine] [64-73-3], $\text{C}_{21}\text{H}_{21}\text{ClN}_3\text{O}_3\cdot\text{HCl}$, F.W. 501.32, Powder, m.p. >245° dec., Merck 14,2886, EINECS 200-592-2, RTECS QI7700000, BRN 3849198, MDL MFCD00082371 | 1g |
| | ! H:H317, P:P261-P280-P302+P352-P321-P363-P501 | |
| | Demecolcine , see Colcemid, 98+%, J63900, p. 167 | |
| J61048 | Denatonium benzoate [Bitrex® MacFarlan Smith, A Johnson Matthey Co.] [3734-33-6], $\text{C}_{21}\text{H}_{23}\text{N}_3\text{O}_2\cdot\text{C}_7\text{H}_5\text{O}_2$, F.W. 446.59, Powder, m.p. 164-169°, Merck 14,2891, EINECS 223-095-2, RTECS BO6650000, BRN 8179408, MDL MFCD00031578, † | 1g 5g 25g |
| | ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Application(s): The bitterest compound known | |
| J62977 | Denatured calf thymus DNA, phenol extracted Liquid | 10mg 20mg |
| | Denatured salmon testes DNA, phenol extracted Liquid | 10mg |






| Stock # | Description | Size |
|---------|--|-----------------------|
| J60132 | Denaturing lysis buffer Liquid, Note: 50mM Tris-HCl with 2% SDS, pH 7.4, † | 250ml 500ml |
| J60370 | Denaturing solution Liquid, UN3266, Note: 1.5M NaCl with 0.5M NaOH H: H314, P: P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 500ml 1L |
| J63135 | Denhardt's solution (50X) Liquid, Note: 1% Ficoll (Type 400, Pharmacia), 1% polyvinylpyrrolidone, and 1% bovine serum albumin, † | 50ml 100ml |
| J62416 | Denhardt's solution (100X) Liquid, Note: 2% Ficoll (Type 400, Pharmacia), 2% polyvinylpyrrolidone and 2% bovine serum albumin, † | 50ml 100ml |
| A11166 | 2'-Deoxyadenosine monohydrate, 99% [Adenine deoxyriboside, 9-(2-Deoxy-β-D-ribofuranosyl)adenine] [16373-93-6], C ₁₀ H ₁₃ N ₅ O ₅ ·H ₂ O, F.W. 269.26 (251.24anh), m.p. 186-189°, [α] _D ²⁰ -25° (c=0.5 in water), EINECS 213-488-7, RTECS AU7358600, BRN 5191174, MDL MFCD00149364, † | 1g 5g 25g |
| |  | |
| J63886 | 2'-Deoxyadenosine, 99% [Adenine deoxyriboside, 9-(2-Deoxy-β-D-ribofuranosyl)adenine] [958-09-8], C ₁₀ H ₁₃ N ₅ O ₅ , F.W. 251.24, Powder, EINECS 213-488-7, RTECS AU7358650, MDL MFCD00056003, † | 50g 100g |
| J65366 | 3'-Deoxyadenosine, 98% [Cordycepin] [73-03-0], C ₁₀ H ₁₃ N ₅ O ₅ , F.W. 251.24, Powder, UN2811, EINECS 200-791-4, RTECS AU7358610, BRN 35194, MDL MFCD00037998 H: H301-H315-H319-H335, P: P301+P310-P305+P351+P338-P302+P352-P321-P405-P501 | 10mg 25mg 100mg |
| J65307 | 2'-Deoxyadenosine-5'-diphosphate trisodium salt, 98% [dADP] [72003-83-9], C ₁₀ H ₁₂ N ₅ Na ₃ O ₉ P ₂ , F.W. 477.15, Powder, EINECS 276-280-5, MDL MFCD00083610 H: H302-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | 25mg 100mg |
| J64402 | 2'-Deoxyadenosine-5'-monophosphate, 99% [2'-dAMP, 2'-Deoxyadenylic acid] [653-63-4], C ₁₀ H ₁₃ N ₅ O ₆ P, F.W. 331.22, Crystalline powder, EINECS 211-503-1, MDL MFCD00005753 | 1g 5g 25g |
| J65542 | 2'-Deoxyadenosine-5'-triphosphate disodium salt, 97% [dATP, 2'-Deoxyadenosine 5'-triphosphoric acid disodium salt] [1927-31-7], C ₁₀ H ₁₄ N ₅ Na ₂ O ₁₂ P ₃ , F.W. 535.14, Powder, EINECS 217-662-3, RTECS AU7358800, MDL MFCD00080335 | 500mg |
| J64045 | 2'-Deoxyadenosine-5'-triphosphate disodium salt, 98% [dATP-Na2] [74299-50-6], C ₁₀ H ₁₄ N ₅ Na ₂ O ₁₂ P ₃ , F.W. 535.14, Powder, EINECS 277-809-2, MDL MFCD00080335 | 10mg 25mg 100mg |
| J64578 | Deoxy-bigCHAP [N,N-Bis[3-(D-gluconamido)propyl]deoxycholamide] [86303-23-3], C ₄₂ H ₇₅ N ₃ O ₁₅ , F.W. 862.05, Powder, Merck 14,1214, MDL MFCD00161482 H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | 250mg 1g |
| B20061 | Deoxycholic acid, 99% [83-44-3], C ₂₆ H ₄₀ O ₄ , F.W. 392.58, m.p. 172-176°, [α] _D ²⁰ +54° (c=2 in ethanol), Merck 14,2899, EINECS 201-478-5, RTECS FZ2100000, BRN 3219882, MDL MFCD00003673, † H: H302, P: P264-P270-P301+P312-P330-P501a | 25g 100g 500g |
| |  | |
| J62288 | Deoxycholic acid sodium salt [7-Deoxycholic acid sodium salt] [302-95-4], C ₂₆ H ₃₉ NaO ₄ , F.W. 414.60, Powder, EINECS 206-132-7, RTECS FZ2250000, BRN 3581950, MDL MFCD00064139, † H: H302-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | 25g 100g 250g |
| | 7-Deoxycholic acid sodium salt , see Deoxycholic acid sodium salt, J62288, p. 177 | |
| J63062 | 2'-Deoxycytidine [951-77-9], C ₉ H ₁₃ N ₃ O ₄ , F.W. 227.22, Crystalline powder, m.p. 209-211°, EINECS 213-454-1, RTECS HA3800000, BRN 87567, MDL MFCD00006547, † | 1g 5g 25g |






| Stock # | Description | Size |
|---------|--|------------------|
| L14153 | 2'-Deoxycytidine hydrochloride, 99% ■ [Cytosine deoxyriboside hydrochloride, 1-(2-Deoxy-β-D-ribofuranosyl)cytosine hydrochloride] [3992-42-5], C ₉ H ₁₃ N ₃ O ₄ ·HCl, F.W. 263.68, m.p. ca 170° dec., [α] _D ²⁰ +57° (c=1 in water), EINECS 223-639-9, BRN 3576124, MDL MFCD00012840, † | 250mg 1g |
| |  | |
| J65408 | 2'-Deoxycytidine-5'-diphosphate trisodium salt, 98% [dCDP] [151151-32-5], C ₉ H ₁₂ N ₃ Na ₃ O ₁₀ P ₂ , F.W. 453.12, Powder, MDL MFCD00056068 ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 25mg 100mg |
| J65244 | 2'-Deoxycytidine-5'-monophosphate, 99% [Deoxycytidylic acid, dCMP] [1032-65-1], C ₉ H ₁₄ N ₃ O ₅ P, F.W. 307.20, Crystalline powder, EINECS 213-849-9, BRN 41062, MDL MFCD00006546 | 1g 5g |
| J65724 | 2'-Deoxycytidine-5'-monophosphate disodium salt [Deoxycytidylic acid disodium salt, dCMP disodium salt] [13085-50-2], C ₉ H ₁₂ N ₃ Na ₂ O ₅ P, F.W. 351.16, Powder, EINECS 235-995-2, MDL MFCD00069774 | 25mg 1g |
| J65686 | 2'-Deoxycytidine-5'-triphosphate disodium salt [5'-dCTP Na ₂ , 2'-Deoxy-5'-triphosphocytidine disodium salt] [102783-51-7], C ₉ H ₁₀ N ₃ Na ₂ O ₁₃ P ₃ , F.W. 511.12, Powder | 25mg 250mg |
| | Deoxyepinephrine hydrochloride , see N-Methyldopamine hydrochloride, 98+%, J60306, p. 287 2'-Deoxy-5-fluorouridine , see 5-Fluoro-2'-deoxyuridine, L16497, p. 224 | |
| J65482 | 2-Deoxy-D-galactose, 99% [2-Deoxy-D-lyxohexose, 2-Deoxy-D-galactopyranose] [1949-89-9], C ₆ H ₁₂ O ₅ , F.W. 164.16, Powder, m.p. 107-110°, EINECS 217-765-3, BRN 1723333, MDL MFCD00014649 | 2g 5g 10g |
| | 6-Deoxy-D-galactose , see D-(+)-Fucose, A18234, p. 228 6-Deoxy-L-galactose , see L-(-)-Fucose, A16789, p. 228 | |
| L07338 | 2-Deoxy-D-glucose, 98% [154-17-6], C ₆ H ₁₂ O ₅ , F.W. 164.16, m.p. 147-152°, [α] _D ²⁰ +47° (c=0.5 in water, 45h), Merck 14,2904, EINECS 205-823-0, RTECS MQ3325000, BRN 1723331, MDL MFCD00151328, † Application(s): A useful culture media component for molecular genetics | 1g 5g 25g |
| |  | |
| L14519 | 2'-Deoxyguanosine hydrate, 99% [9-(2-Deoxy-β-D-ribofuranosyl)guanine hydrate, Guanine-2'-deoxyriboside hydrate] [961-07-9], C ₁₀ H ₁₃ N ₅ O ₄ ·xH ₂ O, F.W. 267.25(anhy), [α] _D ²⁰ -32° (c=0.5 in water), EINECS 213-505-8, RTECS MF8760000, BRN 39814, MDL MFCD00150760, † | 100mg 500mg |
| |  | |
| J60741 | 2'-Deoxyguanosine [961-07-9], C ₁₀ H ₁₃ N ₅ O ₄ , F.W. 267.25, Crystalline powder, EINECS 213-505-8, † | 1g 5g 10g |
| J64490 | 2'-Deoxyguanosine-5'-diphosphate sodium salt [dGDP] [102783-74-4], C ₁₀ H ₁₃ N ₅ Na _x O ₁₀ P ₂ (x=1-3), F.W. 427.20 (free acid), Powder, MDL MFCD00057075 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 25mg |
| J65186 | 2'-Deoxyguanosine-5'-monophosphate disodium salt hydrate, 99% [2'-Deoxy-5'-guanylic acid disodium salt, 5'-dGMP disodium salt] [33430-61-4], C ₁₀ H ₁₂ N ₅ Na ₂ O ₇ ·xH ₂ O, F.W. 391.18 (anhy), Crystalline powder, m.p. 245° dec., MDL MFCD00080331 | 1g 5g 25g |
| J65179 | 2'-Deoxyguanosine-5'-triphosphate trisodium salt, 97% [5'-dGTP] [93919-41-6], C ₁₀ H ₁₁ N ₅ Na ₃ O ₁₃ P ₃ , F.W. 573.13, Powder, MDL MFCD00080337 | 25mg |
| J61411 | 2'-Deoxyinosine [9-(2-Deoxy-β-D-ribofuranosyl)hypoxanthine] [890-38-0], C ₁₀ H ₁₂ N ₄ O ₄ , F.W. 252.23, Crystalline powder, m.p. >250°, EINECS 212-964-1, BRN 33517, MDL MFCD00005762 | 1g 10g 25g |



| Stock # | Description | Size |
|---------|---|----------------------|
| H52292 | 2'-Deoxyinosine, 98+% [9-(2-Deoxy-β-D-ribofuranosyl)hypoxanthine] [890-38-0], C ₁₀ H ₁₂ N ₄ O ₄ , F.W. 252.23, EINECS 212-964-1, MDL MFCD00005762 | 250mg 1g 5g |
| |  | |
| J64271 | 2'-Deoxyinosine-5'-monophosphate disodium salt, 99% [2'-Deoxyinosine-5'-monophosphoric acid disodium salt] [14999-52-1], C ₁₀ H ₁₁ N ₄ Na ₂ O ₇ P, F.W. 376.17, Powder, EINECS 239-090-3, MDL MFCD00134874 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g 5g |
| J64174 | 2'-Deoxyinosine-5'-triphosphate trisodium salt, 98% [dITP] [95648-77-4], C ₁₀ H ₁₂ N ₄ Na ₃ O ₁₃ P ₃ , F.W. 558.11, Powder, EINECS 306-018-8, MDL MFCD00167408 | 100mg |
| J61277 | (+)-1-Deoxymannojirimycin hydrochloride [DMJ, 1,5-Dideoxy-1,5-imino-D-mannitol hydrochloride] [73465-43-7], C ₈ H ₁₃ NO ₄ ·HCl, F.W. 199.60, Powder, MDL MFCD00083611 | 5mg 10mg 25mg |
| | Application(s): Selective inhibitor of α-mannosidase | |
| | 6-Deoxy-L-mannose monohydrate, see L-(+)-Rhamnose monohydrate, A16166, p. 336 D-1-Deoxy-1-(methylamino)glucitol, see N-Methyl-D-glucamine, L14282, p. 288 | |
| J62602 | (+)-1-Deoxymannojirimycin [1,5-Dideoxy-1,5-imino-D-glucitol, (2R,3R,4R,5S)-2-(Hydroxymethyl)-3,4,5-piperidinetriol] [19130-96-2], C ₈ H ₁₃ NO ₄ , F.W. 163.17, Powder, m.p. 195-196°, Merck 14,2905, RTECS TN4350300 | 5mg 50mg 100mg |
| | Application(s): An α-glucosidase inhibitor. Interferes with normal processing of N-linked glycoproteins. | |
| | 9-(2-Deoxy-β-D-ribofuranosyl)adenine, see 2'-Deoxyadenosine, 99%, J63886, p. 177 1-(2-Deoxy-β-D-ribofuranosyl)cytosine hydrochloride, see 2'-Deoxycytidine hydrochloride, L14153, p. 178 9-(2-Deoxy-β-D-ribofuranosyl)guanine hydrate, see 2'-Deoxyguanosine hydrate, L14519, p. 178 9-(2-Deoxy-β-D-ribofuranosyl)hypoxanthine, see 2'-Deoxyinosine, J61411, p. 178 1-(2-Deoxy-β-D-ribofuranosyl)uracil, see 2'-Deoxyuridine, A16026, p. 180 | |
| J62229 | Deoxyribonuclease I, bovine pancreas [EC 3.1.21.1, DNase I] [9003-98-9], Lyophilized powder, 31 kDa, Merck 14,2906, EINECS 232-667-0, RTECS RF0750000, MDL MFCD00130918, Note: Minimum 2,000 units per mg dry weight. One unit causes an increase in absorbance at 260nm of 0.001 per minute per ml at 25 degrees when acting upon highly polymerized DNA at pH 5.0, † | 25mg 100mg 1g |
| J60027 | Deoxyribonuclease I, bovine pancreas, Molecular Biology Grade [EC 3.1.21.1, DNase I] [9003-98-9], Liquid, 31 kDa, Merck 14,2906, EINECS 232-667-0, RTECS RF0750000, MDL MFCD00130918, Note: One unit causes an increase in absorbance at 260nm of 0.001 per minute per ml at 25 degrees when acting upon highly polymerized DNA at pH 5.0. Minimum 2,000 units per ml. Solution at 1 mg/ml containing 50% glycerol and 1 mM calcium chloride., † | 100units 500units |
| | Application(s): Endonuclease that splits phosphodiester linkages, preferentially adjacent to a pyrimidine nucleotide | |
| J61061 | Deoxyribonuclease I, bovine pancreas, Purified [EC 3.1.21.1, DNase I] [9003-98-9], Lyophilized powder, 31 kDa, Merck 14,2906, EINECS 232-667-0, RTECS RF0750000, MDL MFCD00130918, Note: Minimum 2,000 units per mg protein. One unit causes an increase in absorbance at 260nm of 0.001 per minute per ml at 25 degrees when acting upon highly polymerized DNA at pH 5.0, † | 5mg 20mg 100mg |
| | Application(s): Chromatographically purified | |
| J63389 | Deoxyribonuclease II, porcine spleen [EC 3.1.22.1, DNase II] [9025-64-3], Lyophilized powder, 38 kDa, EINECS 232-801-8, MDL MFCD00130919, Note: Minimum 800 units per mg dry weight. One unit causes an increase in absorbance at 260 nm of 0.001 per minute at 25°C, pH 4.6 using highly polymerized DNA as substrate. Supplied as a dialyzed, lyophilized powder. Store at 2-8°C., † | 80kilounits |
| J61774 | Deoxyribonuclease II, porcine spleen, Purified [EC 3.1.22.1, DNase II] [9025-64-3], Lyophilized powder, 38 kDa, EINECS 232-801-8, MDL MFCD00130919, Note: Minimum 12,000 units per mg protein. One unit will increase absorbance at 260nm by 0.001 per min per mL at pH 4.6 and 25°C. Chromatographically purified. Supplied as a dialyzed, lyophilized powder., † | 20kilounits |
| | Application(s): Hydrolyzes deoxyribonucleotide linkages in native and denatured DNA yielding products with 3'-phosphates | |
| J60840 | Deoxyribonucleic acid, salmon testes [Deoxyribonucleic acid, salmon sperm] [9007-49-2], Lyophilized powder | 1g |
| | Deoxyribonucleic acid, salmon sperm, see Deoxyribonucleic acid, salmon testes, J60840, p. 179 | |
| J64400 | Deoxyribonucleic acid sodium salt, calf thymus [91080-16-9], Lyophilized powder, EINECS 293-507-3, MDL MFCD00151698 | 100mg 1g |













| Stock # | Description | Size |
|---------|---|-----------------------|
| J65753 | Deoxyribonucleic acid sodium salt, salmon testes [SS-DNA] [9007-49-2], Lyophilized powder, Merck 14,2907, RTECS HG1933000 | 1g 5g |
| A11990 | 2-Deoxy-D-ribose, 99% ■ [Thymine]ose [533-67-5], C ₅ H ₁₀ O ₄ , F.W. 134.13, m.p. 76-85°, [α] _D ²⁰ -56° (c=1 in water, 24h), Merck 14,2908, EINECS 208-573-0, RTECS SB7230000, BRN 1721978, MDL MFCD00135904, † Starting material for a free-radical coupling reaction (employing homolytic fission of a derivative with 2-Mercaptopyridine N-oxide, A14152) which provides a facile preparative method for C-nucleosides: <i>Chem. Lett.</i> , 1673 (1992). | 1g 5g 25g |
| J65765 | 3'-Deoxythymidine [2',3'-Dideoxythymidine, ddT] [3416-05-5], C ₁₀ H ₁₄ N ₂ O ₅ , F.W. 226.23, Powder, m.p. 155-156°, BRN 21884, MDL MFCD00010570 | 500mg 1g |
| J64938 | 2'-Deoxythymidine-5'-diphosphate trisodium salt, 98% [95648-78-5], C ₁₀ H ₁₃ N ₂ Na ₃ O ₁₁ P ₂ , F.W. 468.13, Powder ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 25mg 100mg |
| A16026 | 2'-Deoxyuridine, 99% △ [1-(2-Deoxy-β-D-ribofuranosyl)uracil, <i>Uracil deoxyriboside</i>] [951-78-0], C ₉ H ₁₂ N ₂ O ₅ , F.W. 228.21, m.p. 164-167°, [α] _D ²⁰ +52° (c=1.1 in 1N NaOH), Merck 14,2910, EINECS 213-455-7, RTECS YU7490000, BRN 24433, MDL MFCD00006527, † | 1g 5g 25g |
| J65531 | 3'-Deoxyuridine [3'-Deoxy-D-uridine] [7057-27-4], C ₉ H ₁₂ N ₂ O ₅ , F.W. 228.21, Powder, MDL MFCD00079153 | 10mg 25mg |
| J64627 | 2'-Deoxyuridine-5'-monophosphate disodium salt, 99% [2'-dUMP, 2'-Deoxyuridine-5'-monophosphoric acid disodium salt] [42155-08-8], C ₉ H ₁₁ N ₂ Na ₂ O ₈ P, F.W. 352.15, Powder, EINECS 255-687-1, MDL MFCD00065282 ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 250mg 1g |
| J64716 | 2'-Deoxyuridine-5'-triphosphate disodium salt, 95% [dUTP sodium salt] [102814-08-4], C ₉ H ₁₁ N ₂ Na ₂ O ₁₄ P ₃ , F.W. 514.12, Powder, MDL MFCD00084701 | 25mg 50mg 100mg |
| | DEPC , see Diethyl cyanophosphonate, L14107, p. 188 | |
| J61286 | (R)-(-)-Deprenyl hydrochloride [Selegiline] [14611-52-0], C ₁₃ H ₁₇ N·HCl, F.W. 223.74, Crystalline Powder, Merck 14,8428, RTECS DA0292500, MDL MFCD00069299 ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 Application(s): Selective MAO-B inhibitor; anti-Parkinsonian agent | 1g |
| J62019 | Dermorphin [Tyr-D-Ala-Phe-Gly-Tyr-Pro-Ser-NH ₂] [77614-16-5], C ₂₀ H ₃₀ N ₆ O ₁₀ , F.W. 802.90, Powder Application(s): A mu-opioid receptor agonist | 5mg |
| | [Des-Gly10, D-Leu6, Pro-NHET9]LHRH , see Leuprolide, human, synthetic, J62967, p. 269 Deticene , see Dacarbazine, J61023, p. 174 | |
| A17590 | Dexamethasone, 98% ▲ [50-02-2], C ₂₂ H ₂₉ FO ₅ , F.W. 392.47, m.p. ca 260° dec., Merck 14,2943, EINECS 200-003-9, RTECS TU3980000, BRN 2066651, MDL MFCD00064136, † ⚠ H:H361d, P:P280h Application(s): Anti-inflammatory glucocorticoid | 1g 5g 25g |
| J63691 | Dexamethasone acetate [1177-87-3], C ₂₄ H ₃₁ FO ₆ , F.W. 434.50, Powder, m.p. 240°, Merck 14,2943, EINECS 214-646-8, RTECS TU4050000, BRN 2342608, MDL MFCD00027407, † ! H:H317, P:P261-P280-P302+P352-P321-P363-P501 Application(s): Glucocorticoid anti-inflammatory | 1g 5g |
| J64083 | Dexamethasone 21-phosphate disodium salt, 98% [2392-39-4], C ₂₂ H ₃₆ FN ₂ O ₈ P, F.W. 516.40, Powder, m.p. 233-240°, Merck 14,2943, EINECS 219-243-0, RTECS TU4056000, BRN 6473066, MDL MFCD00079105, † ! ⚠ H:H302-H351-H361, P:P281-P264-P301+P312-P308+P313-P405-P501 | 1g 5g |
























| Stock # | Description | Size |
|---------|---|-----------------------------------|
| | Dexpanthenol , see D-Panthenol, A18499, p. 311 | |
| J62775 | Dextran, MW ca 6,000 [9004-54-0], (C ₆ H ₁₀ O ₅) _n , Powder, Merck 14,2948, EINECS 232-677-5, MDL MFCD00130935, Note: Biosynthesized by the non-pathogenic Leuconostoc mesenteroides, † | 10g 50g 100g 500g |
| J61216 | Dextran, MW ca 20,000 [9004-54-0], (C ₆ H ₁₀ O ₅) _n , Powder, Merck 14,2948, EINECS 232-677-5, MDL MFCD00130935, Note: Biosynthesized by the non-pathogenic Leuconostoc mesenteroides., † | 10g 50g 100g 500g |
| J63690 | Dextran, MW ca 40,000 [Dextran 40] [9004-54-0], (C ₆ H ₁₀ O ₅) _n , Powder, Merck 14,2948, EINECS 232-677-5, RTECS HH9246000, MDL MFCD00130935, Note: Biosynthesized by Leuconostoc mesenteroides., † | 10g 50g 100g 500g |
| J60989 | Dextran, MW ca 75,000 [9004-54-0], (C ₆ H ₁₀ O ₅) _n , Powder, Merck 14,2948, EINECS 232-677-5, MDL MFCD00130935, Note: Biosynthesized by Leuconostoc mesenteroides., † | 10g 50g 100g 500g |
| J63789 | Dextran, MW ca 150,000 [9004-54-0], (C ₆ H ₁₀ O ₅) _n , Powder, Merck 14,2948, EINECS 232-677-5, MDL MFCD00130935, Note: Biosynthesized by Leuconostoc mesenteroides., † | 10g 50g 100g 500g 1kg |
| J60200 | Dextran, MW ca 250,000 [9004-54-0], (C ₆ H ₁₀ O ₅) _n , Powder, Merck 14,2948, EINECS 232-677-5, MDL MFCD00130935, Note: Biosynthesized by Leuconostoc mesenteroides., † | 10g 50g 100g 500g |
| J63702 | Dextran, MW ca 500,000 [9004-54-0], (C ₆ H ₁₀ O ₅) _n , Powder, Merck 14,2948, EINECS 232-677-5, MDL MFCD00130935, Note: Biosynthesized by the non-pathogenic Leuconostoc mesenteroides., † | 10g 50g 100g 500g |
| | Dextran 40 , see Dextran, MW ca 40,000, J63690, p. 181 | |
| | Dextran sodium sulfate , see Dextran sulfate sodium salt | |
| J60938 | Dextran sulfate sodium salt solution, 50% w/v aq. soln. [9011-18-1], Powder, Merck 14,2951, MDL MFCD00081551, † | 100ml |
| J62101 | Dextran sulfate sodium salt, MW ca 8,000 [Dextran sodium sulfate, Sodium dextran sulfate] [9011-18-1], Powder, Merck 14,2951, RTECS HH9290000, MDL MFCD00081551, Note: Biosynthesized by Leuconostoc mesenteroides., † | 25g 100g 1kg |
| J63606 | Dextran sulfate sodium salt, MW ca 40,000 [Dextran sodium sulfate, Sodium dextran sulfate] [9011-18-1], Powder, Merck 14,2951, RTECS HH9290000, MDL MFCD00081551, Note: Biosynthesized by Leuconostoc mesenteroides., † | 25g 100g |
| J62787 | Dextran sulfate sodium salt, MW ca >500,000 [Dextran sodium sulfate, Sodium dextran sulfate] [9011-18-1], Powder, Merck 14,2951, RTECS HH9290000, MDL MFCD00081551, Note: Biosynthesized by Leuconostoc mesenteroides., † | 5g 50g 100g 1kg |
| A15717 | Dextrin, precipitated by alcohol ■ [9004-53-9], Merck 14,2953, EINECS 232-675-4, RTECS HH9450000, MDL MFCD00081554, † | 100g 500g |
| J61732 | Dextromethorphan hydrobromide [125-69-9], C ₁₈ H ₂₅ NO·HBr, F.W. 352.32, Solid, m.p. 125-127°, Merck 14,8091, EINECS 204-750-1, BRN 6453793, MDL MFCD02173901 ! H: H302, P: P264-P270-P301+P312-P330-P501a | 5g 10g 50g |
| | Dextrose , see D-(+)-Glucose, A16828, p. 233 | |
| | DHA , see 1,3-Dihydroxyacetone, J60592, p. 191 | |
| | DHEBA , see N,N'-(1,2-Dihydroxyethylene)bisacrylamide, L19211, p. 192 | |
| J63775 | Diacerein [13739-02-1], C ₁₈ H ₁₂ O ₈ , F.W. 368.29, Powder, m.p. 217-218°, Merck 14,2960, EINECS 237-310-2, RTECS CB8781000, MDL MFCD00468030 ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): Interleukin-1 inhibitor | 1g 5g |











| Stock # | Description | Size |
|---------------|--|---------------------|
| | 1,6-Diacetamidohexane , see N,N'-Diacetyl-1,6-diaminohexane, B22771, p. 182 | |
| B22771 | N,N'-Diacetyl-1,6-diaminohexane, 98+% [N,N'-Diacetyl-1,6-hexanediamine, N,N'-Hexamethylenebis(acetamide)] [3073-59-4], CH ₃ CONH(CH ₂) ₆ NHCOCH ₃ , F.W. 200.28, m.p. 126-129°, RTECS AC2976200, BRN 1775764, MDL MFCD00008684 | 10g 50g 250g |
| | Application(s): Induces apoptosis in various transformed cells | |
| | 2,6-Diacetyl-7,9-dihydroxy-8,9b-dimethylidibenzofuran-1,3(2H,9bH)-dione , see (+)-Usnic acid, H56612, p. 389 | |
| | N,N'-Diacetyl-1,6-hexanediamine , see N,N'-Diacetyl-1,6-diaminohexane, B22771, p. 182 | |
| | Diacetyl monoxime , see 2,3-Butanedione monoxime, A14339, p. 140 | |
| L15694 | 1,4-Diacryloylpiperazine, 97% [1,4-Bis(acryloyl)piperazine, Diacroyl piperazine] [6342-17-2], C ₁₀ H ₁₄ N ₂ O ₂ , F.W. 194.23, m.p. 91-95°, BRN 745431, MDL MFCD00077661 | 1g 5g 25g |
| | H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Cross-linker in polyacrylamide gels. | |
| | 5,3'-Diallyl-2,4'-dihydroxybiphenyl , see Honokiol, 98+%, J63434, p. 246 | |
| A12195 | N,N'-Diallyl-L-tartardiamide, 99% [58477-85-3], C ₁₀ H ₁₆ N ₂ O ₄ , F.W. 228.25, m.p. 184-186°, [α] _D ²⁰ +118° (c=3 in methanol), EINECS 261-277-3, BRN 1712934, MDL MFCD00008640, † | 50g 250g |
| | H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Application(s): Cross-linking co-monomer for the polymerization of soluble polyacrylamide gels | |
| J61029 | Dialysis tubing wash buffer (5X) Liquid, Note: 10% (w/v) sodium bicarbonate solution, with 50mM EDTA, pH 8.0 | 250ml 500ml |
| J64585 | Diamide, 96% [1,1'-Azobis(N,N-dimethylformamide), N,N,N',N'-Tetramethylazodicarboxamide] [10465-78-8], C ₈ H ₁₂ N ₄ O ₂ , F.W. 172.18, Powder, EINECS 233-951-7, RTECS LQ1041000, BRN 1910409, MDL MFCD00008318 | 1g 5g |
| | 1,8-Diamino-4-azaoctane , see Spermidine, A19096, p. 350 | |
| | 1,2-Diaminobenzene dihydrochloride , see o-Phenylenediamine dihydrochloride, 98+%, J60354, p. 316 | |
| J60972 | 3,3'-Diaminobenzidine, tablets [91-95-2], C ₁₂ H ₁₄ N ₄ , F.W. 214.27, Tablets, EINECS 202-110-6, RTECS DV8750000, BRN 1212988, MDL MFCD00007725, Note: Each tablet contains 5mg of DAB, each tablet weighs 240mg., † | 50each 100each |
| | H:H315-H319-H334-H317-H350-H335, P:P285-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): Widely used peroxidase substrate for immunoblotting and immunohistochemical staining techniques | |
| J62216 | 3,3'-Diaminobenzidine tetrahydrochloride hydrate [DAB tetrahydrochloride hydrate] [868272-85-9], C ₁₂ H ₁₄ N ₄ ·4HCl·xH ₂ O, F.W. 360.11(anhy), Powder, MDL MFCD08273058 | 5g 10g |
| | H:H315-H319-H351-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): Widely used peroxidase substrate for immunoblotting and immunohistochemical staining techniques | |
| A14075 | 3,5-Diaminobenzoic acid, 98%, may contain up to 3% moisture [535-87-5], C ₇ H ₈ N ₂ O ₂ , F.W. 152.15, m.p. ca 235° dec., f.p. 210°(410°F), Merck 14,2978, EINECS 208-621-0, RTECS DG6186000, BRN 2086484, MDL MFCD00007807, † | 50g 100g 500g |
| | H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| |  | |
| B21316 | 1,4-Diaminobutane, 98+%   [1,4-Butanediamine, Putrescine] [110-60-1], H ₂ N(CH ₂) ₄ NH ₂ , F.W. 88.15, m.p. 25-28°, b.p. 158-160°, f.p. 63°(145°F), d. 0.877, n _D ²⁰ 1.4569, Merck 14,7947, UN2928, EINECS 203-782-3, RTECS EJ6800000, BRN 605282, MDL MFCD00008235, † | 25g 100g 500g |
| | H:H331-H314-H302-H312, P:P280-P305+P351+P338-P309-P310 | |
| A18312 | 1,4-Diaminobutane dihydrochloride, 99%  [1,4-Butanediamine dihydrochloride, Putrescine dihydrochloride] [333-93-7], HCl·H ₂ N(CH ₂) ₄ NH ₂ ·HCl, F.W. 161.08, m.p. ca 280° dec., Merck 14,7947, EINECS 206-375-9, RTECS EJ7280000, BRN 3906680, MDL MFCD00012526, † | 25g 100g |
| | H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | (S)-2,6-Diaminocaproic acid, see L-Lysine, 98%, J62225, p. 273 | |
| L14072 | (1S,2S)-(+)-1,2-Diaminocyclohexane, 98%  [(1S)-trans-1,2-Cyclohexanediamine, DACH] [21436-03-3], C ₆ H ₁₄ N ₂ , F.W. 114.19, m.p. 43-45°, b.p. 104-110°/40mm, f.p. 70°(158°F), [α] _D ²⁰ +25.5° (c=5 in 1N HCl), Fieser 2,223 12,396, UN3259, BRN 2801645, MDL MFCD00062986 | 250mg 1g 5g |
| | H:H314-H317, P:P280-P262-P303+P361+P353-P305+P351+P338-P309-P310 | |
| | Application(s): For synthesis of optically active products | |



| Stock # | Description | Size |
|---------|---|------------------------|
| J63821 | 1,10-Diaminodecane, 98% [1,10-Decanediamine, Decamethylenediamine] [646-25-3], NH ₂ (CH ₂) ₁₀ NH ₂ , F.W. 172.31, Powder, m.p. 59-61°, b.p. 140°/12mm, UN3259, EINECS 211-471-9, RTECS HD7175000, BRN 1738591, MDL MFCD00008151, † ⚠ H: H314, P: P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 10g 50g |
| | Application(s): NMDA receptor inverse agonist | |
| J65748 | 2,2'-Diamino-2'-deoxyadenosine, 98% [9-(2-amino-2-deoxy-β-D-ribofuranosyl)-2,6-diaminopurine, 2,6-Diaminopurine 2'-amino-2'-deoxyriboside] [215943-79-6], C ₁₀ H ₁₃ N ₅ O ₃ , F.W. 281.27, Powder | 1g |
| | 1,4-Diamino-2,3-dicyano-1,4-bis(2-aminophenylthio)butadiene , see U0126, 99+%, J61246, p. 387 | |
| J65237 | 2,3'-Diamino-2',3'-dideoxyadenosine, 99% [9-(3-Amino-2,3-dideoxy-β-D-ribofuranosyl)-2,6-diaminopurine, 2,6-Diaminopurine 3'-amino-2',3'-dideoxyriboside] [915399-37-0], C ₁₀ H ₁₃ N ₅ O ₂ , F.W. 265.27, Powder, MDL MFCD09750829 | 1g |
| | 4,4'-Diamino-3,3'-dimethoxybiphenyl , see o-Dianisidine, A17150, p. 184 4,4'-Diamino-3,3'-dimethoxybiphenyl dihydrochloride , see o-Dianisidine dihydrochloride, A17175, p. 184 3,7-Diamino-2,8-dimethyl-5-phenylphenazinium chloride , see Safranin O, B21674, p. 339 1,2-Diaminoethane , see Ethylenediamine, A12132, p. 215 3,8-Diamino-5-ethyl-6-phenylphenanthridinium bromide , see Ethidium bromide soln., 10mg/ml, J62282, p. 214 | |
| H55402 | 2,7-Diaminofluorene, 97+% [2,7-Fluorenediamine] [525-64-4], C ₁₃ H ₁₂ N ₂ , F.W. 196.25, m.p. 160-162°, Merck 14,4156, EINECS 208-377-5, RTECS LL6980000, BRN 2099859, MDL MFCD00001128 | 250mg 1g 5g |
| | (+/-)-2,6-Diaminohexanoic acid monohydrochloride, see DL-Lysine monohydrochloride, A11066, p. 273 (R)-2,6-Diaminohexanoic acid monohydrochloride, see D-Lysine monohydrochloride, L07710, p. 273 (S)-2,6-Diaminohexanoic acid monohydrochloride, see L-Lysine monohydrochloride, Cell Culture Reagent, J62099, p. 273 (S)-2,6-Diaminohexanoic acid methyl ester dihydrochloride, see L-Lysine methyl ester dihydrochloride, A18157, p. 273 3,6-Diamino-10-methylacridinium chloride hydrochloride, see Acriflavine hydrochloride, J60048, p. 76 3,8-Diamino-5-methyl-6-phenylphenanthridinium bromide, see Dimidium bromide, B24818, p. 197 | |
| A12993 | 2,3-Diaminonaphthalene, 97% [2,3-Naphthalenediamine] [771-97-1], C ₁₀ H ₈ N ₂ , F.W. 158.20, m.p. 193-196°, d. 1.096, Solubility: Slightly soluble in water, EINECS 212-241-0, BRN 2206394, MDL MFCD00004116, † ⚠ H: H302-H312-H332-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 1g 5g 25g |
| |  | |
| B23039 | 1,5-Diaminopentane, 98% △ ■ [1,5-Pentanediamine, Cadavarine] [462-94-2], H ₂ N(CH ₂) ₃ NH ₂ , F.W. 102.18, m.p. 9°, b.p. 178-180°, d. 0.873, n _D ²⁰ 1.4563, Merck 14,1609, UN2735, EINECS 207-329-0, MDL MFCD00008239 ⚠ H: H314, P: P280-P305+P351+P338-P309-P310 | 5g 25g |
| | (+/-)-2,5-Diaminopentanoic acid hydrochloride, see DL-Ornithine monohydrochloride, A18173, p. 308 (R)-(-)-2,5-Diaminopentanoic acid hydrochloride, see D-Ornithine hydrochloride, L00793, p. 308 (S)-(+)-2,5-Diaminopentanoic acid hydrochloride, see L-Ornithine hydrochloride, Cell Culture Reagent, J60241, p. 309 | |
| A11932 | 1,3-Diaminopropane, 98% △ ■ [1,3-Propanediamine, Trimethylenediamine] [109-76-2], H ₂ N(CH ₂) ₃ NH ₂ , F.W. 74.13, m.p. -12°, b.p. 134-136°, f.p. 48° (118°F), d. 0.888, n _D ²⁰ 1.4573, Fieser 13,160, UN2734, EINECS 203-702-7, RTECS TX6825000, BRN 605277, MDL MFCD00008228, † ⚠ H: H310-H314-H226-H302, P: P280-P305+P351+P338-P309-P310 | 100ml 500ml 2.5L |
| | The potassium derivative (KAPA) is a very strong base, valuable for its ability to cause the migration of acetylenic unsaturation to the terminal positions of alkynes (known as the "zip" reaction). In the presence of excess amine, reaction occurs within seconds; the driving force is the formation of a stable acetylide anion: <i>J. Am. Chem. Soc.</i> , 97 , 891 (1975). For example, with acetylenic carbinols: <i>J. Chem. Soc., Chem. Commun.</i> , 959 (1976); <i>Tetrahedron Lett.</i> , 2565 (1976); <i>Can. J. Chem.</i> , 62 , 1333 (1984). For a further example (2- to 9-decynol), using a combination of Potassium tert-butoxide , A13947 , and Li 3-aminopropanamide, see: <i>Org. Synth. Coll.</i> , 8 , 146 (1993). This technique avoids the use of KH. For the use of KAPA for the isomerization of β-pinene to the thermodynamically-more stable α-pinene, see: <i>Org. Synth. Coll.</i> , 8 , 553 (1993). For procedures for the generation of Na or K 3-amino-propylamides from the metals by ultrasound irradiation or in the presence of Fe(NO ₃) ₃ , see: <i>J. Org. Chem.</i> , 49 , 2494 (1984). | |
| B22775 | 4,4'-Diamino-3,3',5,5'-tetramethylbiphenyl , see 3,3',5,5'-Tetramethylbenzidine, A13868, p. 364 3,5-Diamino-1,2,4-triazole, 98+% [Guanazole, 1H-1,2,4-Triazole-3,5-diamine] [1455-77-2], C ₂ H ₃ N ₅ , F.W. 99.10, m.p. ca 205° dec., EINECS 215-937-2, RTECS XZ4535000, BRN 112467, MDL MFCD00005233, † | 5g 25g 100g |
| |  | |
| | Application(s): Inhibitor of DNA synthesis | |
| | 2,4-Diamino-5-(3,4,5-trimethoxybenzyl)pyrimidine , see Trimethoprim, J63053, p. 378 cis-Diammine(1,1-cyclobutanedicarboxylato) platinum , see Carboplatin, J60433, p. 148 | |

| Stock # | Description | Size |
|---------|--|---------------------|
| 10471 | cis-Diamminedichloroplatinum(II), Pt 64.5% min [Cisplatin] [15663-27-1], PtCl ₂ (NH ₃) ₂ , F.W. 300.06, Micro Crystals, m.p. 270° dec., Merck 14,2317, Solubility: Soluble in DMF. Insoluble in most common solvents, UN3288, EINECS 239-733-8, RTECS TP2450000, MDL MFCD00011623, Note: Special handling precautions required. View MSDS prior to purchase. MSDS are available online at www.alfa.com , †  | 250mg 1g 5g |
| | H:H300-H334-H350-H315-H319-H317-H335, P:P201-P301+P310-P308+P313 | |
| | Application(s): Potent anticancer agent that blocks DNA synthesis | |
| A17150 | o-Dianisidine, 98+% [4,4'-Diamino-3,3'-dimethoxybiphenyl, 3,3'-Dimethoxybenzidine] [119-90-4], C ₁₆ H ₁₆ N ₂ O ₂ , F.W. 244.30, m.p. 134-138°, f.p. 206°(402°F), Merck 14,2991, EINECS 204-355-4, RTECS DD0875000, BRN 1879884, MDL MFCD00008372, †  | 5g 25g 100g |
| |  H:H350-H302, P:P281-P264-P301+P312-P308+P313-P405-P501a Redox indicator. | |
| A17175 | o-Dianisidine dihydrochloride, 99% [4,4'-Diamino-3,3'-dimethoxybiphenyl dihydrochloride, 3,3'-Dimethoxybenzidine dihydrochloride] [20325-40-0], C ₁₆ H ₁₆ N ₂ O ₂ ·2HCl, F.W. 317.21, m.p. 268° dec., EINECS 243-737-5, RTECS DD1050000, BRN 3917996, MDL MFCD00012488, †  | 1g 5g |
| |  H:H350-H302, P:P281-P264-P301+P312-P308+P313-P405-P501a | |
| J65207 | Diarylpropionitrile [DPN, 2,3-Bis(4-hydroxyphenyl)-propionitrile] [1428-67-7], C ₁₅ H ₁₃ NO ₂ , F.W. 239.27, Powder, RTECS UG0900000 | 10mg |
| J63444 | Diatrizoic acid [Amidotrizoic acid] [117-96-4], C ₁₁ H ₉ I ₃ N ₃ O ₄ , F.W. 613.90, Powder, EINECS 204-223-6, RTECS DG5950000, MDL MFCD00069960 | 5g 25g 100g |
| | Application(s): A high-osmolality radiocontrast agent | |
| J64863 | 1,11-Diazo-3,6,9-trioxaundecane [Azido(bis)-PEG3] [101187-39-7], C ₈ H ₁₆ N ₆ O ₃ , F.W. 244.25, Viscous liquid  | 100mg |
| | H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J64904 | Dibenzazepine [γ-Secretase Inhibitor XX, Deshydroxy LY 411575] [209984-56-5], C ₂₆ H ₂₃ F ₂ N ₃ O ₃ , F.W. 463.48, Solid | 10mg |
| | 5H-Dibenz[b,f]azepine-5-carboxamide, see Carbamazepine, 98%, J62590, p. 146 Dibenzoylmethane, see 1,3-Diphenyl-1,3-propanedione, A13450, p. 199 4,5-Dibromo-2,7-dinitrofluorescein disodium salt, see Eosin B, A17377, p. 208 | |
| A12766 | 1,2-Dibromoethane, 99% ▲ [Ethylene dibromide] [106-93-4], BrCH ₂ CH ₂ Br, F.W. 187.87, m.p. 9-10°, b.p. 132°, f.p. None, d. 2.179, n _D ²⁰ 1.5385, Merck 14,3796, UN1605, EINECS 203-444-5, RTECS KH9275000, MDL MFCD00000233, Note: Special handling precautions required. View MSDS prior to purchase. MSDS are available online at www.alfa.com , †  | 1kg 5kg |
| | H:H301-H311-H331-H350-H315-H319-H335-H411, P:P301+P310-P305+P351+P338-P361-P302+P352-P405-P501a | |
| A18226 | 4',5'-Dibromofluorescein, 98% [C.I. 45370] [596-03-2], C ₂₀ H ₁₀ Br ₂ O ₃ , F.W. 490.12, m.p. 270-273°, Merck 14,3022, EINECS 209-876-0, RTECS LM5200000, BRN 57189, MDL MFCD00005042, †  | 50g 250g |
| |  H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| J62804 | Dibucaine hydrochloride [2-Butoxy-N-(2-diethylaminoethyl)-4-quinolinecarboxamide hydrochloride] [61-12-1], C ₂₀ H ₂₈ N ₃ O ₂ ·HCl, F.W. 379.92, Crystalline powder, Merck 14,3031, EINECS 200-498-1, RTECS GD3325000, MDL MFCD00012735  | 5g 25g |
| | H:H302-H318, P:P280-P264-P305+P351+P338-P310-P301+P312-P501 | |
| | Application(s): Potent, long-acting local anesthetic | |
| | 2,6-Di-tert-butyl-p-cresol, see 2,6-Di-tert-butyl-4-methylphenol, A16863, p. 185 | |
| A14708 | Di-tert-butyl dicarbonate, 97+% ▽ [Boc anhydride, Di-tert-butyl pyrocarbonate] [24424-99-5], C ₁₀ H ₁₈ O ₅ , F.W. 218.25, m.p. 21-24°, b.p. 56-57°/0.5mm, f.p. 37°(99°F), d. 0.950, n _D ²⁰ 1.4090, Fieser 4,128 7,91 8,145 10,122 13,94 15,113 19,117 20,133 21,162, UN2930, EINECS 246-240-1, RTECS HT0230000, BRN 1911173, MDL MFCD00008805, †  | 25g 100g 500g |
| |  H:H330-H318-H228-H315-H317-H335, P:P280-P305+P351+P338-P302+P352-P304+P340-P310 Reagent for amino group protection on the <i>tert</i> -butyl carbamate (<i>tert</i> -butoxycarbonyl, Boc derivatives), in high yield under mild conditions, widely used in peptide chemistry. For practical details, literature references and | |


| Stock # | Description | Size | |
|---------------|--|--|---|
| | <p>tabulated results, see: <i>Org. Synth. Coll.</i>, 7, 70 (1990). For further examples see: <i>Synthesis</i>, 223 (1987); <i>Org. Synth. Coll.</i>, 9, 124, 300 (1998). Benzyl carbamates (Cbz, Z) may be transformed into Boc in a one pot procedure catalyzed by Pd/C: <i>Tetrahedron Lett.</i>, 33, 3167 (1992).</p> <p>Rapid and efficient formation of Boc derivatives of amines, catalyzed by Copper(II) tetrafluoroborate hexahydrate, 26127, has been described: <i>Tetrahedron Lett.</i>, 47, 1087 (2006).</p> <p>For Boc protection of phenols, alcohols, thiols etc. under phase-transfer conditions, see: <i>Can. J. Chem.</i>, 63, 153 (1985). Amides can be protected in the presence of a catalytic quantity of DMAP (4-(Dimethylamino)pyridine, A13016): <i>J. Org. Chem.</i>, 48, 2424 (1983); <i>Acta Chem. Scand. B</i>, 40, 745 (1986); the amide link of the product undergoes facile alkaline hydrolysis or methanolysis. The nitrogen function of indoles and pyrroles can also be protected under similar conditions: <i>J. Chem. Soc., Chem. Commun.</i>, 1699 (1984); <i>Org. Synth. Coll.</i>, 9, 121 (1998). 1-Boc indoles may be synthesized from N-Boc 2-alkylanilines: <i>Synthesis</i>, 871 (1991).</p> <p>The Boc group is readily cleaved with acid, most often Trifluoroacetic acid, L06374.</p> <p>In the presence of 1 equivalent of DMAP in acetonitrile, arylamines are converted to isocyanates, generally in high yield; the dicarbonate here behaves as a convenient phosgene replacement: <i>Angew. Chem. Int. Ed.</i>, 34, 2497 (1995). The same reagent system has also been applied to nitroalkanes for the ambient temperature generation of nitrile oxides which were trapped <i>in situ</i> with dipolarophiles: <i>Synthesis</i>, 309 (1997). Carboxylic acids can be esterified in the presence of a catalytic amount of DMAP: <i>Synlett</i>, 263 (2004).</p> <p>Carboxylic acids have also been converted to Boc-protected amines, via a one-pot Curtius rearrangement, using the reagent in the presence of sodium azide, with catalytic amounts of TBAB and zinc triflate: <i>Org. Lett.</i>, 7, 4107 (2005). For a brief feature on uses of the reagent in synthesis, see: <i>Synlett</i>, 1995 (2001).</p> | | |
| | Application(s): Reagent for the introduction of the Boc protecting group | | |
| A14606 | <p>2,5-Di-tert-butylhydroquinone, 98+% [88-58-4], C₁₆H₂₂O₂, F.W. 222.33, m.p. 214-218°, b.p. 321°, f.p. >200°(392°F), d. 1.070, EINECS 201-841-8, RTECS MX516000, BRN 2049542, MDL MFCD00008825, †</p> <p>! H: H302-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a</p> |  | <p>250g 1kg</p> |
| A16863 | <p>2,6-Di-tert-butyl-4-methylphenol, 99% [BHT, <i>Butylated hydroxytoluene</i>] [128-37-0], C₁₅H₂₀O, F.W. 220.36, m.p. 69-72°, b.p. 264-265°, f.p. 127°(260°F), d. 1.048, Merck 14,1548, Fieser 15,113, UN3077, EINECS 204-881-4, RTECS GO7875000, BRN 1911640, MDL MFCD00011644, †</p> <p>! H: H302-H319-H411, P: P273-P305+P351+P338</p> <p>Radical inhibitor and antioxidant, readily soluble in nonpolar media. Finds widespread use in the inhibition of peroxide formation in ether solvents and also as a preservative/ antioxidant for unsaturated oils and fats in the food, synthetic rubber and paint industries.</p> <p>Source of t-butyl group in aromatic substitution reactions. For reviews of the use of t-butyl as a positional protecting group for aromatic substitution reactions, readily removable with, e.g. AlCl₃ in toluene, see: <i>Org. Prep. Proced. Int.</i>, 8, 51 (1976); <i>Synthesis</i>, 921 (1979).</p> |  | <p>250g 1kg</p> |
| | Application(s): Antioxidant | | |
| A13257 | <p>Di-n-butyl phthalate, 99% [Benzene-1,2-dicarboxylic acid di-n-butylester, <i>Phthalic acid di-n-butyl ester</i>] [84-74-2], C₁₈H₂₂O₄, F.W. 278.35, m.p. -35°, b.p. 339-340°, f.p. 171°(340°F), d. 1.045, n_D²⁰ 1.4920, Merck 14,3035, UN3082, EINECS 201-557-4, RTECS TI0875000, BRN 1914064, MDL MFCD00009441, †</p> <p>⚠ H: H360Df-H400, P: P281-P273-P308+P313-P391-P405-P501a</p> |  | <p>500g 2.5kg 10kg</p> |
| | <p>Di-tert-butyl pyrocarbonate, see Di-tert-butyl dicarbonate, A14708, p. 184</p> <p>2-(2,6-Dichloroanilino)-2-imidazoline hydrochloride, see Clonidine hydrochloride, 98+%, J63707, p. 166</p> | | |
| J64870 | <p>5,6-Dichlorobenzimidazole riboside, 98% [DBR, <i>5,6-Dichloro-1-β-D-ribofuranosylbenzimidazole</i>] [53-85-0], C₁₂H₁₂Cl₂N₂O₄, F.W. 319.14, Powder, RTECS DD7310000, BRN 39123, MDL MFCD00036785</p> | | <p>50mg 100mg 250mg</p> |
| J65324 | <p>7,8-Dichloro-1,4-dihydro-4-oxo-3-quinolinecarboxylic acid [CAY10577] [300675-28-9], C₁₀H₆Cl₂NO₃, F.W. 258.06, Crystalline solid</p> | | 5mg |
| | 2,5-Dichloro-3,6-dihydroxy-1,4-benzoquinone , see Chloranilic acid, A10493, p. 154 | | |
| 39121 | <p>1,2-Dichloroethane, ACS, 99+% [EDC, <i>Ethylene chloride</i>] [107-06-2], C₂H₄Cl₂, F.W. 98.96, Liquid, m.p. -35°, b.p. 83°, f.p. 15°(59°F), d. 1.256, n_D²⁰ 1.4448, Merck 14,3797, UN1184, EINECS 203-458-1, RTECS KI0525000, BRN 605264, MDL MFCD00000963, †</p> <p>Maximum level of impurities: Color (APHA) 10, Evaporation residue 0.002%, Titratable acid 0.0003meq/g, H₂O 0.03%</p> <p>⚠ H: H225-H350-H302-H315-H319-H335, P: P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a</p> | | <p>500ml 1L 4L 4x1L</p> |
| | Application(s): Suitable for ascorbic acid determination | | |
| A10107 | <p>2,6-Dichloroindophenol sodium salt hydrate ▲ [2,6-Dichlorophenolindophenol sodium salt hydrate, <i>Sodium 2,5-dichloroindophenoxide hydrate</i>] [620-45-1], C₁₂H₆Cl₂NNaO₂·xH₂O, F.W. 290.08(anhy), m.p. >300°, Merck 14,3068, EINECS 210-640-4, RTECS GU5495000, BRN 3641229, MDL MFCD00150014, †</p> <p>! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a</p> <p>Redox indicator: <i>Anal. Biochem.</i>, 101, 421 (1980).</p> |  | <p>5g 25g 100g</p> |



| Stock # | Description | Size |
|---|--|--------------------------|
| J65198 | 3,4-Dichloroisocoumarin, 99% [3,4-Dichloro-2-benzopyran-1-one, 3,4-DCI] [51050-59-0], C ₉ H ₆ Cl ₂ O ₂ , F.W. 215.03, Powder, UN2811, BRN 6802625, MDL MFCD00036960  | 10mg |
| J61138 | 5,7-Dichlorokynurenic acid [5,7-Dichloro-4-hydroxyquinoline-2-carboxylic acid] [131123-76-7], C ₁₀ H ₆ Cl ₂ NO ₃ , F.W. 240.06, Solid  | 10mg 50mg 100mg |
| J61567 | 5,7-Dichlorokynurenic acid sodium salt [131123-76-7], C ₁₀ H ₄ Cl ₂ NNaO ₃ , F.W. 258.10, Solid  | 10mg 50mg |
| Application(s): Potent NMDA receptor glycine site antagonist | | |
| L13089 | Dichloromethane, 99+%, stab. with ca. 50ppm 2-methyl-2-butene [DCM, Methylene chloride] [75-09-2], CH ₂ Cl ₂ , F.W. 84.93, m.p. -95°, b.p. 39-40°, d. 1.325, n _D ²⁰ 1.4244, Merck 14,6063, Fieser 1,676 2,273 4,337 7,239 18,131, UN1593, EINECS 200-838-9, RTECS PA8050000, BRN 1730800, MDL MFCD00000881, †  | 500ml 1L 2.5L |
| (2,3-Dichloro-4-[2-methylenebutyl]phenoxy)acetic acid, see Ethacrynic acid, J63684, p. 213 2-[(2,6-Dichloro-3-methylphenyl)amino]benzoic acid, see Meclofenamic acid sodium salt, 99+%, J60484, p. 279 | | |
| A14411 | 2,6-Dichlorophenol, 99% [87-65-0], C ₆ H ₃ Cl ₂ O, F.W. 163.00, m.p. 65-68°, b.p. 218-220°, Merck 14,3073, UN2020, EINECS 201-761-3, RTECS SK8750000, BRN 1447806, MDL MFCD00002176, †   | 25g 100g 500g |
| 2,6-Dichlorophenolindophenol sodium salt hydrate, see 2,6-Dichloroindophenol sodium salt hydrate, A10107, p. 185 3',3''-Dichlorophenolsulfonaphthalein, see Chlorophenol Red, B21623, p. 157 | | |
| A13231 | 2,3-Dichlorophenoxyacetic acid, 97% [2976-74-1], C ₈ H ₆ Cl ₂ O ₃ , F.W. 221.04, m.p. 173-175°, EINECS 221-022-9, BRN 1963475, MDL MFCD00004299   | 5g 25g |
| A12467 | 2,4-Dichlorophenoxyacetic acid, 98% [2,4-D] [94-75-7], C ₈ H ₆ Cl ₂ O ₃ , F.W. 221.04, m.p. 136-140°, b.p. 160°/0.4mm, d. 1.42, Merck 14,2796, EINECS 202-361-1, RTECS AG6825000, BRN 1214242, MDL MFCD00004300, †   | 50g 250g 1kg |
| J64981 | 2-(3-(2,3-Dichlorophenoxy)propylamino)ethanol hydrochloride [2,3-DCPE hydrochloride] [418788-90-6], C ₁₁ H ₁₅ Cl ₂ NO ₂ ·HCl, F.W. 300.61, Powder | 5mg 10mg |
| 2-[(2,6-Dichlorophenyl)amino]benzeneacetic acid sodium salt, see Diclofenac sodium salt, J62609, p. 186 4-(2,3-Dichlorophenyl)-1,4-dihydro-2,6-dimethyl-3,5-pyridinecarboxylic acid ethyl methyl ester, see Felodipine, J61195, p. 219 | | |
| A15131 | 2,4-Dichloropyrimidine, 98+%  [3934-20-1], C ₄ H ₂ Cl ₂ N ₂ , F.W. 148.98, m.p. 57-62°, b.p. 101°/23mm, EINECS 223-508-6, BRN 110911, MDL MFCD00006061, †   | 5g 10g 50g 250g |
| L13212 | 4,6-Dichloropyrimidine, 98% [1193-21-1], C ₄ H ₂ Cl ₂ N ₂ , F.W. 148.98, m.p. 64-68°, b.p. 176°, UN3261, EINECS 214-770-2, BRN 111195, MDL MFCD00006109   | 5g 25g |
| J62609 | Diclofenac sodium salt [2-[(2,6-Dichlorophenyl)amino]benzeneacetic acid sodium salt, Sodium 2-(2,6-dichloroanilino)phenylacetate] [15307-79-6], C ₁₆ H ₁₀ Cl ₂ NNaO ₃ , F.W. 318.14, Powder, m.p. 283-285°, Merck 14,3081, UN2811, EINECS 239-346-4, RTECS AG6330000, MDL MFCD00082251  | 5g 25g 100g |
| Application(s): Standard NSAID and cyclooxygenase (COX) inhibitor | | |
| J61581 | Dicloxacinilium sodium salt [13412-64-1], C ₁₆ H ₁₆ Cl ₂ N ₃ NaO ₃ S, F.W. 492.33, Powder, m.p. 222-225°, Merck 14,3084, RTECS XH8925000, MDL MFCD00056865  | 1g 5g |
| Application(s): An antibiotic used in the treatment of staphylococci bacteria that are resistant to penicillin G Dicoumarol, see Dicoumarol, J63634, p. 187 | | |








| Stock # | Description | Size |
|--|---|--|
| J63634 | Dicumarol [Dicoumarol, 3,3'-Methylenebis(4-hydroxycoumarin)] [66-76-2], C ₁₈ H ₁₂ O ₆ , F.W. 336.30, Powder, m.p. 286-289°, Merck 14,3090, UN2811, EINECS 200-632-9, RTECS GN7875000, MDL MFCD00006857, †  H: H372-H302-H411, P: P260-P273-P264-P270-P301+P312-P501a | 5g 25g |
| Application(s): Vitamin K reductase inhibitor possessing anticoagulant properties | | |
| A10451 | Dicyandiamide, 99% [N-Cyanoguanidine] [461-58-5], C ₂ H ₄ N ₄ , F.W. 84.08, m.p. 208-211°, d. 1.400, Merck 14,3092, Fieser 1,229, EINECS 207-312-8, RTECS ME9950000, BRN 605637, MDL MFCD00008066, † Reacts with aromatic nitriles in the presence of base to give 6-aryl-1,3,5-triazines (benzguanamines); see, e.g.: <i>Org. Synth. Coll.</i> , 4, 78 (1963). |  250g 500g 2.5kg |
| Dicyanomethane , see Malononitrile, A15046, p. 276 | | |
| A15671 | Dicyclohexylamine, 98% Δ [101-83-7], C ₁₂ H ₂₂ N, F.W. 181.32, m.p. -2°, b.p. 256°, f.p. 99°(210°F), d. 0.913, n _D ²⁰ 1.4842, Merck 14,3095, Fieser 1,231, UN2565, EINECS 202-980-7, RTECS HY4025000, BRN 605923, MDL MFCD00011658, †  H: H314-H400-H410-H302, P: P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a Forms highly crystalline salts with N-protected amino acids: <i>Liebigs Ann. Chem.</i> , 640, 157 (1961). Reacts with n-BuLi to give a hindered strong base; cf LDA (see Diisopropylamine, A10280), which has been used to promote, e.g. the α -carboethoxylation of ketones; see Diethyl dicarbonate, B22753 , p. 189. |  100ml 500ml 2.5L |
| A10973 | N,N'-Dicyclohexylcarbodiimide, 99% \blacktriangleleft [DCC] [538-75-0], C ₁₂ H ₂₂ N ₂ , F.W. 206.33, m.p. 33-36°, b.p. 154-156°/11mm, f.p. 138°(280°F), Merck 14,3096, Fieser 1,231 11,173 13,107 14,131 15,131 16,128 18,133 21,169, UN2811, EINECS 208-704-1, RTECS FF2160000, BRN 610662, MDL MFCD00011659, †  H: H311-H318-H302-H317, P: P305+P351+P338-P361-P302+P352-P321-P405-P501a Promotes a variety of acylation reactions between carboxylic acids and nucleophiles; the dicyclohexylurea by-product is almost insoluble in most solvents:  |  25g 100g 500g |
| In peptide coupling reactions, various auxiliary reagents have been used to suppress racemization. See, e.g., N-Hydroxysuccinimide, A10312 , p. 251, N-Hydroxyphthalimide, A13862 , and endo-N-Hydroxy-5-norbornene-2,3-dicarboximide, A13205 . For use of CuCl ₂ , see: <i>Tetrahedron Lett.</i> , 25, 771 (1984); <i>J. Chem. Soc., Chem. Commun.</i> , 419 (1988). For ester or thioester formation from an acid and an alcohol, the rate is greatly increased by addition of 4-(Dimethylamino)pyridine, A13016 : <i>Angew. Chem. Int. Ed.</i> , 17, 522 (1978). For t-butyl esters, see: <i>Org. Prep. Proced. Int.</i> , 20, 180 (1988); <i>Org. Synth. Coll.</i> , 7, 93 (1990). The same combination has been found useful in macrolactonization reactions: <i>J. Org. Chem.</i> , 50, 2394 (1985); and in formation of propynoic esters under mild conditions: <i>Tetrahedron Lett.</i> , 30, 4575 (1989). DCC-coupling is frequently used to prepare active esters, e.g. of 4-Nitrophenol, A14376 , or Pentafluorophenol, A15574 , for peptide coupling. DCC has also been used in dehydrations, e.g. carboxylic acids to anhydrides: <i>J. Am. Chem. Soc.</i> , 85, 1997 (1963); <i>J. Org. Chem.</i> , 54, 1922 (1989); primary amides: <i>J. Org. Chem.</i> , 26, 3356 (1961), and aldoximes: <i>Synth. Commun.</i> , 3, 101 (1973); 12, 25 (1982) to nitriles; dialkylacetic acids to ketenes (where stable): <i>Synthesis</i> , 568 (1989). The combination with Dimethyl sulfoxide, A13280 , is used in the Pfitzner-Moffatt oxidation of alcohols to carbonyl compounds under mild conditions: <i>J. Am. Chem. Soc.</i> , 85, 3027 (1963); 87, 5661, 5670 (1965); <i>Org. Synth. Coll.</i> , 5, 242 (1973); review: <i>Synthesis</i> , 857 (1990). In the presence of H ₂ SO ₄ or AlCl ₃ , Friedel-Crafts cyclohexylation of arenes has been reported: <i>Tetrahedron Lett.</i> , 35, 903 (1994). For reviews of advances in the chemistry of carbodiimides, see: <i>Chem. Rev.</i> , 67, 107 (1967), 81, 589 (1981); <i>Tetrahedron</i> , 37, 233 (1981). | | |
| Application(s): Carboxy group activating reagent for peptide synthesis | | |
| J61422 | Dicyclomine hydrochloride [67-92-5], C ₁₆ H ₂₅ NO ₂ ·HCl, F.W. 345.95, Solid, m.p. 164-166°, Merck 14,3097, EINECS 200-671-1, RTECS DT7350000, MDL MFCD00079158, †  H: H302-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10g 50g |
| Application(s): An anticholinergic that blocks muscarinic receptors | | |
| Di(cyclopentadienyl)iron , see Ferrocene, 87202, p. 219 | | |
| J64573 | 2',3'-Dideoxyadenosine, 98% [ddA] [4097-22-7], C ₁₀ H ₁₃ N ₅ O ₂ , F.W. 235.24, Powder, m.p. 181-184°, Merck 14,3101, EINECS 223-853-2, RTECS AU7358900, BRN 619924, MDL MFCD00010534 | 25mg 50mg 100mg |
| L10619 | 2',3'-Dideoxycytidine, 98+% [Zalcitabine] [7481-89-2], C ₈ H ₁₀ N ₃ O ₃ , F.W. 211.22, m.p. 216-220°, [α] _D ²⁰ +90° (c=0.5 in water), Merck 14,10109, RTECS HA3870000, BRN 654956, MDL MFCD00012188  H: H351-H361, P: P281-P201-P202-P308+P313-P405-P501a |  50mg 250mg |

















| Stock # | Description | Size |
|---------|---|-----------------------|
| J65810 | 2',3'-Dideoxyguanosine, 90+% [85326-06-3], C ₁₀ H ₁₃ N ₅ O ₈ , F.W. 251.24, Powder, MDL MFCD00057074 | 25mg 50mg 100mg |
| | 1,5-Dideoxy-1,5-imino-D-glucitol , see (+)-1-Deoxynojirimycin, J62602, p. 179 1,5-Dideoxy-1,5-imino-D-mannitol, hydrochloride , see (+)-1-Deoxymannojirimycin hydrochloride, J61277, p. 179 | |
| J64833 | 2',3'-Dideoxyinosine, 98% [ddl, ddIno] [69655-05-6], C ₁₀ H ₁₂ N ₄ O ₈ , F.W. 236.23, Powder, Merck 14,3098, RTECS NM7460700, BRN 3619529, MDL MFCD0007728 | 250mg 500mg 1g |
| | 4-(Diethylamino)azobenzene-2'-carboxylic Acid , see Ethyl Red, J63446, p. 217 | |
| A17485 | 2-Diethylaminoethyl 4-aminobenzoate hydrochloride, 99% ▲ [Procaine hydrochloride] [51-05-8], C ₁₃ H ₂₀ N ₂ O ₂ ·HCl, F.W. 272.78, m.p. 155-157°, b.p. 195-196°/17mm, Merck 14,7757, UN2811, EINECS 200-077-2, MDL MFCD00013000, †  H: H301, P: P264-P270-P301+P310-P321-P405-P501a | 50g 250g |
| | Application(s): A sodium channel blocker | |
| J63781 | Diethylaminoethyl dextran [DEAE-Dextran] [9015-73-0], Powder, Merck 14,2936 | 25g 100g |
| | N,N-Diethylaminoethyl 2,2-diphenylvalerate , see Proadifen hydrochloride, J63833, p. 328 | |
| J62528 | 8-(Diethylamino)octyl 3,4,5-trimethoxybenzoate hydrochloride, 97% [3,4,5-Trimethoxybenzoic acid 8-(diethylamino)octyl ester hydrochloride, TMB-8 hydrochloride] [53464-72-5], C ₂₂ H ₃₇ NO ₈ ·HCl, F.W. 432.00, Powder, m.p. 92-97°, EINECS 258-574-5, BRN 5466611, MDL MFCD00012502 | 50mg 250mg |
| | Application(s): Inhibits intracellular calcium mobilization | |
| | 4-(4-Diethylaminophenylazo)benzene-sulfonic acid sodium salt , see Ethyl Orange sodium salt, J62863, p. 217 | |
| L09919 | Diethyl chlorophosphite, 97% ▣ [Diethyl phosphorochloridite] [589-57-1], C ₄ H ₁₀ ClO ₂ P, F.W. 156.55, b.p. 153-155°, f.p. 25°(77°F), d. 1.082, n _D ²⁰ 1.4375, Merck 14,3841, Fieser 1,248 20,142, UN2920, EINECS 209-652-2, BRN 1098392, MDL MFCD00009074, †  | 5g 25g |
| | H: H314-H226-EU014, P: P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a Reacts readily with nucleophiles, e.g. amines, alcohols or organometallic species, with the introduction of a phosphorus substituent. The phosphorylation of OH groups has been brought about by treatment with the reagent followed by oxidation of the P(III) product to P(V) with, e.g. iodine: <i>Synth. Commun.</i> , 12 , 821 (1982); <i>Synthesis</i> , 572 (1986). The chlorophosphite has the advantage of greater reactivity over one-step phosphorylation reagents, e.g. Diphenyl phosphorochloridate, A13546 . Reagent for peptide coupling: <i>J. Am. Chem. Soc.</i> , 74 , 5304, 5309 (1952). Also useful, in the presence of TMS-OTf, in glycosidic couplings: <i>Tetrahedron Lett.</i> , 33 , 6123 (1992). In the presence of N-ethyl-diisopropylamine, reduces both aryl and alkyl nitro compounds to amines: <i>J. Org. Chem.</i> , 63 , 393 (1998). The reagent also effects dehydration of aldoximes to nitriles, deoxygenation of N-oxides and sulfoxides, and conversion of epoxides to chlorohydrins can also be effected: <i>J. Org. Chem.</i> , 67 , 711 (2002). | |
| L14107 | Diethyl cyanophosphonate, tech. 90% ▣ [DEPC, Diethyl phosphorocyanidate] [2942-58-7], C ₄ H ₁₀ NO ₂ P, F.W. 163.11, b.p. 104-105°/19mm, f.p. 80°(176°F), d. 1.075, n _D ²⁰ 1.4010, Fieser 5,217 6,192 7,107 10,145 20,143, UN2922, EINECS 220-936-5, RTECS TD2500000, BRN 1768938, MDL MFCD00010256  | 5g 25g |
| | H: H300-H310-H330-H314, P: P280-P305+P351+P338-P302+P352-P304+P340-P309-P310 Strecker reaction with aldehydes or ketones in the presence of amines or ammonia gives good yields of α-amino nitriles: <i>Tetrahedron Lett.</i> , 4663 (1979). Pre-formed enamines give the same products: <i>Synthesis</i> , 716 (1979). Phosphorylating agent for phenols: <i>Synth. Commun.</i> , 27 , 3035 (1997). Activates carboxylic acids towards nucleophiles: Promotes the formation of amides and esters from amines or alcohols in the presence of, e.g. triethylamine: <i>Tetrahedron</i> , 32 , 2211 (1976). The reaction is applicable to peptide synthesis, since little racemization has been observed: <i>J. Am. Chem. Soc.</i> , 97 , 7174 (1975). The extent of racemization in comparison with other methods has been studied: <i>Chem. Pharm. Bull.</i> , 30 , 3147 (1982). With 2 equivalents of reagent in the absence of a nucleophile, an intermediate 1-(1,1-dicyano)phosphite is formed, leading, on treatment with acid, to the homologated α-hydroxy acid: <i>Tetrahedron Lett.</i> , 39 , 9209 (1998). Thiol esters can be formed under similar conditions: <i>J. Org. Chem.</i> , 39 , 3302 (1974). Can also be used to activate carboxylic acids for the C-acylation of active methylene compounds: <i>J. Org. Chem.</i> , 43 , 3631 (1978). In the presence of Lewis acids, active methylene compounds such as dimethyl malonate react with the cyanophosphonate itself. The product can be converted to a uracil derivative by reaction with phenyl isocyanate: <i>Chem. Pharm. Bull.</i> , 42 , 1919 (1994):  | |









| Stock # | Description | Size | | | | | | | | | | | | |
|---|--|-------------------------------|--------|------|------|-----|-----|-----|---|------|------|------|------|------|
| J65918 | 1,3-Diethyl-5,6-diaminouracil ■ [5,6-Diamino-1,3-diethylpyrimidine-2,4(1H,3H)-dione] [52998-22-8], C ₈ H ₁₄ N ₄ O ₂ , F.W. 198.22, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 250mg | | | | | | | | | | | | |
| B22753 | Diethyl dicarbonate, 97% ▣ [Diethyl oxydiformate, Diethyl pyrocarbonate] [1609-47-8], C ₈ H ₁₀ O ₅ , F.W. 162.14, b.p. 93-94°/18mm, f.p. 69°(156°F), d. 1.101, n _D ²⁰ 1.3980, Merck 14,7998, Fieser 13,110, EINECS 216-542-8, RTECS LQ9350000, BRN 637031, MDL MFCD00009106, † ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a In the presence of the hindered base lithium dicyclohexylamide (from Dicyclohexylamine, A15671 , p. 187), α-ethoxycarbonylation of ketones occurs to give β-keto esters: <i>Synthesis</i> , 1014 (1984). Application(s): Ribonuclease inhibitor | 5g 25g 100g | | | | | | | | | | | | |
| A14728 | Diethylene glycol, 99% ■ [Bis(2-hydroxyethyl) ether, Digol] [111-46-6], (HOCH ₂ CH ₂) ₂ O, F.W. 106.12, m.p. -10°, b.p. 245-246°, f.p. 143°(289°F), d. 1.118, n _D ²⁰ 1.4470, Merck 14,3119, EINECS 203-872-2, RTECS ID5950000, BRN 969209, MDL MFCD00002882, † ! H:H302, P:P264-P270-P301+P312-P330-P501a High-boiling solvent which is widely used in the Huang Minlon modification of the Wolff-Kishner reaction for the reduction of carbonyl groups to methylenes; see Hydrazine monohydrate, A14005 . | 250g 500g 2.5kg 10kg | | | | | | | | | | | | |
| A17478 | Diethylene glycol diethyl ether, 99% [2-Ethoxyethyl ether, Bis(2-ethoxyethyl) ether] [112-36-7], (CH ₃ CH ₂ OCH ₂ CH ₂) ₂ O, F.W. 162.23, m.p. -44°, b.p. 188-190°, f.p. 71°(160°F), d. 0.909, n _D ²⁰ 1.4120, Merck 14,3118, EINECS 203-963-7, RTECS KN3160000, BRN 1699259, MDL MFCD00009254, † ! H:H319-EUH019, P:P280-P264-P305+P351+P338-P337+P313 | 100ml 500ml 2.5L | | | | | | | | | | | | |
| 43464 | Diethylene glycol diethyl ether, HPLC Grade, 99+% [2-Ethoxyethyl ether] [112-36-7], (CH ₃ CH ₂ OCH ₂ CH ₂) ₂ O, F.W. 162.23, Liquid, m.p. -44°, b.p. 188-190°, f.p. 71°(160°F), d. 0.909, n _D ²⁰ 1.4120, Merck 14,3118, EINECS 203-963-7, RTECS KN3160000, BRN 1699259, MDL MFCD00009254, Note: Filtered through 0.2μm filter, † ! H:H319-EUH019, P:P280-P264-P305+P351+P338-P337+P313 | 250ml | | | | | | | | | | | | |
| UV absorption - 1cm cell vs H₂O | | | | | | | | | | | | | | |
| <table border="1"> <thead> <tr> <th>λ (nm)</th> <th>400</th> <th>350</th> <th>320</th> <th>300</th> <th>260</th> </tr> </thead> <tbody> <tr> <td>A</td> <td>0.01</td> <td>0.01</td> <td>0.04</td> <td>0.10</td> <td>1.00</td> </tr> </tbody> </table> | | | λ (nm) | 400 | 350 | 320 | 300 | 260 | A | 0.01 | 0.01 | 0.04 | 0.10 | 1.00 |
| λ (nm) | 400 | 350 | 320 | 300 | 260 | | | | | | | | | |
| A | 0.01 | 0.01 | 0.04 | 0.10 | 1.00 | | | | | | | | | |
| A13397 | Diethylene glycol dimethyl ether, 99%, stab. with 100ppm BHT ■ [Bis(2-methoxyethyl) ether, Diglyme] [111-96-6], (CH ₃ OCH ₂ CH ₂) ₂ O, F.W. 134.18, m.p. -64°, b.p. 161-162°, f.p. 51°(124°F), d. 0.944, n _D ²⁰ 1.4080, Merck 14,3165, Fieser 1,255, UN3271, EINECS 203-924-4, RTECS KN3339000, BRN 1736101, MDL MFCD00008503, † ⚠ H:H360FD-H226-EUH019, P:P210-P241-P280-P303+P361+P353-P405-P501a Aprotic solvent which has useful solvent power, e.g. for Sodium borohydride, 35788 and hence has been widely used for <i>in situ</i> generation of diborane and for many other hydride reactions. For use in the hydroboration of olefins with borane-triethylamine complex, see: <i>Org. Synth. Coll.</i> , 7, 427 (1990). | 500ml 2.5L | | | | | | | | | | | | |
| A14670 | Diethylene glycol monoethyl ether, 98% ■ [2-(2-Ethoxyethoxy)ethanol, Ethyl digol] [111-90-0], HOCH ₂ CH ₂ OCH ₂ CH ₂ OCH ₂ CH ₃ , F.W. 134.18, m.p. -80°, b.p. 201-202°, f.p. 96°(204°F), d. 0.989, n _D ²⁰ 1.4280, Merck 14,1800, EINECS 203-919-7, RTECS KK8750000, BRN 1736441, MDL MFCD00002872, † ! H:H319, P:P305+P351+P338 | 500g 2.5kg 10kg | | | | | | | | | | | | |
| L13446 | Diethylene glycol monoethyl ether acetate, 99% [2-(2-Ethoxyethoxy)ethyl acetate] [112-15-2], CH ₃ CO ₂ (CH ₂ CH ₂ O) ₂ C ₂ H ₅ , F.W. 176.21, m.p. -25°, b.p. 218-219°, f.p. 95°(203°F), d. 1.012, n _D ²⁰ 1.4210, Merck 14,1800, EINECS 203-940-1, RTECS KK8925000, BRN 1764643, MDL MFCD00041928, † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 100ml 500ml 2.5L | | | | | | | | | | | | |
| A10926 | Diethylenetriaminepentacetic acid, 98+% [DTPA, Pentetic acid] [67-43-6], C ₁₄ H ₂₃ N ₃ O ₁₀ , F.W. 393.35, m.p. ca 220° dec., d. 1.56, Merck 14,7125, EINECS 200-652-8, RTECS MB8205000, BRN 1810219, MDL MFCD00004289, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Chelating agent. | 50g 250g 1kg 5kg | | | | | | | | | | | | |
| 4,4'-(1,2-Diethylethylene)diphenol, see Hexestrol, 98+%, J60889, p. 245 | | | | | | | | | | | | | | |
| L04503 | N,N-Diethylformamide, 99% [617-84-5], HCON(CH ₂ CH ₃) ₂ , F.W. 101.15, b.p. 178°, f.p. 65°(149°F), d. 0.910, n _D ²⁰ 1.4340, EINECS 210-533-2, RTECS LQ1925000, BRN 1209392, MDL MFCD00003287, † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 Dipolar aprotic solvent, compare N,N-Dimethylformamide, A13547 . | 100g 500g | | | | | | | | | | | | |





| Stock # | Description | Size |
|---------------|---|---------------------|
| | 3,3'-Diethyl-9-methyl-4,5,4',5'-dibenzothiacarbocyanine , see Stains-All, H32127, p. 352 | |
| | N,N-Diethyl-N-methyl-2-([3-methyl-1-oxo-2-phenylpentyl]oxy)ethan ammonium bromide , see Valetamate bromide, 99%, J62622, p. 390 | |
| | Diethyl oxydiformate , see Diethyl dicarbonate, B22753, p. 189 | |
| | Diethyl phosphorochloridite , see Diethyl chlorophosphite, L09919, p. 188 | |
| | Diethyl phosphorocyanidate , see Diethyl cyanophosphonate, L14107, p. 188 | |
| | Diethyl phosphoryl cyanide , see Diethyl cyanophosphonate, L14107, p. 188 | |
| | Diethyl pyrocarbonate , see Diethyl dicarbonate, B22753, p. 189 | |
| J63754 | Difloxacin hydrochloride [98106-17-3], C ₂₁ H ₁₉ F ₂ N ₃ O ₃ ·HCl, F.W. 435.85, White powder, Merck 14,3141, MDL MFCD03840489 | 5g 25g |
| | Application(s): A quinolone antibacterial compound. Structurally related to norfloxacin | |
| | Digitalin , see Digitoxin, J61736, p. 190 | |
| J61736 | Digitoxin [Digitalin] [71-63-6], C ₄₁ H ₆₄ O ₁₃ , F.W. 764.94, Crystalline powder, m.p. 240°, Merck 14,3163, UN2811, EINECS 200-760-5, RTECS IH2275000, BRN 76678, MDL MFCD0003686, † ☠ H: H301-H331-H373, P: P260-P261-P301+P310-P321-P405-P501a | 100mg |
| | Application(s): A cardiac glycoside | |
| | Diglycine , see Glycylglycine, A10523, p. 237 | |
| | Diglyme , see Diethylene glycol dimethyl ether, A13397, p. 189 | |
| | Digol , see Diethylene glycol, A14728, p. 189 | |
| B21902 | Digoxin, 96% [20830-75-5], C ₄₁ H ₆₄ O ₁₄ , F.W. 780.95, m.p. ca 250° dec., Merck 14,3167, UN2811, EINECS 244-068-1, MDL MFCD00003674, † ☠ H: H301, P: P264-P270-P301+P310-P321-P405-P501a | 1g 5g |
| | Application(s): A cardiac glycoside and substrate for Pgp; upregulates Pgp expression | |
| |  | |
| | 1,4-Diguandinobutane sulfate salt , see Arcaine sulfate salt, J63277, p. 109 | |
| | 22,23-Dihydroavermectin B1 , see Ivermectin, J62777, p. 262 | |
| | Dihydrocholesterol , see 5α-Cholestan-3β-ol, L08624, p. 160 | |
| | 3,7-Dihydro-1,3-dimethyl-1H-purine-2,6-dione , see Theophylline, J60203, p. 366 | |
| | 3,7-Dihydro-1,3-dimethylpurine-2,6-dione, complex with 1,2-ethanediamine (2:1) , see Aminophylline, anhydrous, 98%, J60705, p. 98 | |
| J60638 | Dihydrogocristine methanesulfonate [24730-10-7], C ₂₈ H ₄₈ N ₄ O ₅ S, F.W. 707.80, Powder, Merck 14,3653, EINECS 246-434-6, RTECS KE7600000, MDL MFCD00153792 | 200mg 1g |
| | Application(s): 5-HT receptor antagonist; partial agonist at adrenergic and dopaminergic receptors | |
| J63840 | Dihydroergotamine methanesulfonate [6190-39-2], C ₃₃ H ₄₃ N ₃ O ₅ ·CH ₃ SO ₃ S, F.W. 679.78, Powder, m.p. 230-235°, Merck 14,3174, EINECS 228-235-6, RTECS KE7920000, MDL MFCD00058615 ! H: H312-H332, P: P261-P280-P302+P352-P304+P340-P322-P501a | 100mg 1g |
| | Application(s): Agonist at vascular serotonin receptors; partial agonist at α-adrenergic and dopamine D2 receptors | |
| J65759 | Dihydrofluorescein diacetate, 97% [Diacetyldihydrofluorescein, DADF] [35340-49-9], C ₂₄ H ₁₈ O ₇ , F.W. 418.39, Powder, m.p. 213-215°, BRN 364167, MDL MFCD00005056 | 1g |
| | Application(s): Agonist at vascular serotonin receptors; partial agonist at α-adrenergic and dopamine D2 receptors | |
| B20575 | 2,3-Dihydrofuran, 98+% [1191-99-7], C ₄ H ₆ O, F.W. 70.09, b.p. 54-55°, f.p. -24°(-11°F), d. 0.927, n _D ²⁰ 1.4245, UN3271, EINECS 214-747-7, BRN 103168, MDL MFCD00003205, † ☠ H: H225-EU H019-H302-H319, P: P210-P241-P280-P303+P361+P353-P305+P351+P338-P501a | 25g 100g 500g |
| | For lithiation at the 5-position, see: <i>Tetrahedron Lett.</i> , 4187 (1977); <i>Org. Synth. Coll.</i> , 9, 530 (1998). For alkylation by active methylene compounds, catalyzed by trans-Dichlorobis(triphenylphosphine)palladium(II), 10491 , see: <i>J. Org. Chem.</i> , 47, 2812 (1982). For catalytic asymmetric arylation, see: <i>J. Am. Chem. Soc.</i> , 113, 1417 (1991); <i>Pure Appl. Chem.</i> , 64, 421 (1992). Forms tetrahydrofuranal esters (acyl hemiacetals) with carboxylic acids. These react with Grignard reagents to give good yields of ketones with minimal enolization or double addition (tertiary alcohol formation). The utility of other acyl hemiacetals as ketone precursors has also been studied: <i>J. Org. Chem.</i> , 61, 6071 (1996): | |
| |  | |
| | Dihydro-2,5-furandione , see Succinic anhydride, A12245, p. 354 | |
| | Dihydroharmine , see Harmaline, 98+%, J61699, p. 241 | |



| Stock # | Description | Size |
|---------|--|---|
| L01996 | 5,6-Dihydro-5-methyluracil, 98+% [5-Methyl-5,6-dihydrouracil] [696-04-8], C ₅ H ₈ N ₂ O ₂ , F.W. 128.13, m.p. 263-265°, EINECS 211-787-7, BRN 81983, MDL MFCD00023159 |  5g 25g |
| | 1,4-Dihydro-4-oxo-2,6-pyridinedicarboxylic acid hydrate, see Chelidamic acid hydrate, L00782, p. 153 1,4-Dihydro-5-(2-propoxyphenyl)-7H-1,2,3-triazolo(4,5-d)pyrimidin-7-one, see Zaprinast, 98+%, J63326, p. 395 2,3-Dihydropyran, see 3,4-Dihydro-2H-pyran, L02731, p. 191 | |
| L02731 | 3,4-Dihydro-2H-pyran, 99% [2,3-Dihydropyran] [110-87-2], C ₆ H ₈ O, F.W. 84.12, m.p. -70°, b.p. 85-86°, f.p. -15°(5°F), d. 0.926, n _D ²⁰ 1.4420, Fieser 1,256 3,99 5,220 7,109 10,147, UN2376, EINECS 203-810-4, BRN 103493, MDL MFCD00006558, † |  25ml 100ml 500ml |
| |  H:H225-H315-H319-H335, P:P210-P261-P280g-P305+P351+P338-P403+P233 Protects OH groups as their tetrahydropyranyl, (THP) ethers, stable to bases, Grignard or organolithium reagents, metal hydrides, etc., but readily removed by mild acid. Introduction (acetal formation) generally employs an acid catalyst, often <i>p</i> -TsOH. For example of protection, reaction with Grignard, and deprotection, see: <i>Org. Synth. Coll.</i> , 7, 334 (1990). For alternative catalysts for THP ether formations, see: Pyridinium <i>p</i>-toluenesulfonate, A15708, Triphenylphosphine hydrobromide, L14290, Boron trifluoride diethyl etherate, A15275, Amberlyst® 15(H), 89079 , p. 90, Montmorillonite K10, L15160, Acetonitrilphenylphosphonium bromide, B22434, Indium(III) trifluoromethanesulfonate, 40131 , Sulfuric acid/silica gel: <i>Synth. Commun.</i> , 22, 159 (1992), allows the catalyst to be removed by simple filtration. POCl ₃ , described for the protection of diethyl hydroxymethylphosphonate, permits use in the Horner-Wadsworth-Emmons reaction: <i>Org. Synth. Coll.</i> , 7, 160 (1990). See also iodotrimethylsilane, A12902 , providing non-acidic conditions; cf also Tetrahydropyran, A13392 . For selective monotetrahydropyranylation of symmetrical diols, catalyzed by acidic ion-exchange resin, Dowex® 50WX2 50-100 (H), L13943 , see: <i>J. Org. Chem.</i> , 63, 8183 (1998). For selective deprotection of THP ethers under non-acidic conditions with LiCl in wet DMSO, see: <i>J. Org. Chem.</i> , 61, 6038 (1996). The lithio-derivative, formed with <i>tert</i> -BuLi, reacts with, e.g. alkyl iodides or carbonyl compounds: <i>Tetrahedron Lett.</i> , 4187 (1977). Acetals and ortho esters, in the presence of Lewis acid catalysts, add readily to the vinyl ether system: <i>Chem. Lett.</i> , 1101 (1988). | |
| | Application(s): Widely used hydroxyl-protecting reagent | |
| | 1,5-Dihydro-4H-pyrazolo[3,4-d]pyrimidin-4-one, see 4-Hydroxy-1H-pyrazolo[3,4-d]pyrimidine, A16974, p. 251 | |
| J62103 | DL-erythro-Dihydrosphingosine [DL-Sphinganine, (2 <i>R</i> *,3 <i>S</i> *)-(±)-2-Aminooctadecane-1,3-diol] [3102-56-5], C ₁₈ H ₃₅ NO ₂ , F.W. 301.51, Powder, BRN 1724234, MDL MFCD00079141 | 10mg 50mg |
| | Application(s): Protein kinase C inhibitor. Precursor to sphingosine | |
| J60495 | Dihydrostreptomycin sesquisulfate [5490-27-7], C ₂₂ H ₄₁ N ₇ O ₁₂ ·1.5H ₂ SO ₄ , F.W. 730.71, Powder, Merck 14,3179, EINECS 226-823-7, RTECS WK2236000, BRN 3894221, MDL MFCD00070252, † | 100g |
| | 3,7-Dihydro-1,3,7-trimethyl-1H-purine-2,6-dione, see Caffeine, A10431, p. 142 | |
| L01918 | 5,6-Dihydrouracil, 99% [504-07-4], C ₄ H ₆ N ₂ O ₂ , F.W. 114.10, m.p. 278-280°, EINECS 207-982-1, BRN 112496, MDL MFCD00006029, † |  1g 5g |
| J60592 | 1,3-Dihydroxyacetone dimer [DHA, 1,2-Dihydroxy-2-propanone] [96-26-4], C ₆ H ₈ O ₅ , F.W. 90.08, Powder, m.p. 75-80°, Merck 14,3182, EINECS 202-494-5, RTECS UC1645000, † | 5g |
| | 1,2-Dihydroxyanthraquinone, see Alizarin, A14404, p. 89 | |
| A11010 | 1,4-Dihydroxyanthraquinone, 96% [C.I. 58050, Quinizarin] [81-64-1], C ₁₄ H ₈ O ₄ , F.W. 240.21, m.p. 195-198°, b.p. ca 450°, f.p. 222°(431°F), Merck 14,8064, EINECS 201-368-7, RTECS CB6600000, BRN 1914036, MDL MFCD00001209, † |  250g 1kg 5kg |
| | 1,2-Dihydroxybenzene, see Catechol, A10164, p. 150 1,3-Dihydroxybenzene, see Resorcinol, 36248, p. 336 1,4-Dihydroxybenzene, see Hydroquinone, A11411, p. 248 | |
| A11459 | 2,5-Dihydroxybenzoic acid, 99% [Gentic acid] [490-79-9], C ₇ H ₆ O ₅ , F.W. 154.12, m.p. ca 206° dec., Merck 14,4398, EINECS 207-718-5, RTECS LY3850000, BRN 2209119, MDL MFCD00002460, † |  25g 100g |
| |  H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Application(s): Aspirin metabolite and antioxidant excipient | |
| | 2-(3,4-Dihydroxybutylidene)malononitrile, see Tyrphostin A23, 99%, J60308, p. 386 2,3-Dihydroxybutanedioic acid, see L-(+)-Tartaric acid, 36405, p. 358 (<i>R</i> -(<i>R'</i>))-2,3-Dihydroxybutanedionate Tylosin (salt), see Tylosin tartrate, 98+%, J62633, p. 386 | |

| Stock # | Description | | Size |
|---------|--|--|----------------------|
| A15950 | 3,4-Dihydroxycinnamic acid, predominantly trans, 99% [Caffeic acid] [331-39-5], C ₉ H ₈ O ₄ , F.W. 180.16, m.p. ca 202° dec., Merck 14,1635, EINECS 206-361-2, RTECS GD8950000, BRN 2210883, MDL MFCD00004392 |  | 10g 50g |
| |  ! H:H351-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): Inhibitor of ornithine decarboxylase and protein tyrosine kinase | | |
| | 3,4-Dihydroxycinnamic acid phenylethyl ester , see Phenylethyl 3,4-dihydroxycinnamate, 99+%, J61386, p. 316 3-(3,4-Dihydroxycinnamoyl)quinic acid , see Chlorogenic acid, J60457, p. 157 | | |
| A15393 | 6,7-Dihydroxycoumarin, 98+% [Cichorigenin, Esculetin] [305-01-1], C ₉ H ₆ O ₄ , F.W. 178.15, m.p. ca 270° dec., Merck 14,3697, EINECS 206-161-5, RTECS GN6382500, BRN 152788, MDL MFCD00006874 |  | 1g 5g |
| |  ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Ultraviolet absorber. Application(s): A lipoxygenase inhibitor | | |
| | 6,7-Dihydroxycoumarin-6-glucoside , see Esculin sesquihydrate, J63114, p. 210 3,4-Dihydroxy-9,10-dioxo-2-anthracenesulfonic acid sodium salt , see Alizarin Red S sodium salt, 42040, p. 89 1,2-Dihydroxyethane , see Ethylene glycol, A11591, p. 216 N,N'-(1,2-Dihydroxy-1,2-ethanediy)bisacrylamide , see N,N'-(1,2-Dihydroxyethylene)bisacrylamide, L19211, p. 192 | | |
| L19211 | N,N'-(1,2-Dihydroxyethylene)bisacrylamide, 97% [1,2-Bis(acrylamido)ethylene glycol, DHEBA] [868-63-3], C ₈ H ₁₂ N ₂ O ₄ , F.W. 200.20, m.p. 141-143°, EINECS 212-780-1, BRN 1941875, MDL MFCD00008624, † |  | 5g 25g 100g |
| |  ! H:H340-H350-H302, P:P281-P264-P301+P312-P308+P313-P405-P501a Application(s): A cross-linking reagent for the recovery of separated biomolecules | | |
| L14178 | 5,7-Dihydroxyflavone, 98% [Chrysin] [480-40-0], C ₁₅ H ₁₀ O ₄ , F.W. 254.24, m.p. 284-289°, Merck 14,2256, EINECS 207-549-7, RTECS LK8329050, BRN 233276, MDL MFCD00006834 |  | 5g 25g |
| | 1,8-Dihydroxy-10-(β-D-glucopyranosyl)-3-(hydroxymethyl)-9(10H)-anthracenone , see Aloin, J62153, p. 90 (±)-3,4-Dihydroxy-N-[3-(4-hydroxyphenyl)-1-methylpropyl]-Δ-phenethylamine hydrochloride , see Dobutamine hydrochloride, J61333, p. 201 2,2-Dihydroxy-1,3-indanedione , see Ninhydrin, 43846, p. 303 | | |
| B22877 | 4',7-Dihydroxyisoflavone, 97% [Daidzein] [486-66-8], C ₁₅ H ₁₀ O ₄ , F.W. 254.24, m.p. 328-332° dec., Merck 14,2801, EINECS 207-635-4, RTECS DJ3100040, BRN 231523, MDL MFCD00016954 |  | 1g 5g 25g |
| |  ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | | |
| J63763 | 4',7-Dihydroxyisoflavone, 98+% [Daidzein] [486-66-8], C ₁₅ H ₁₀ O ₄ , F.W. 254.24, Powder, m.p. 328-332° dec., Merck 14,2801, EINECS 207-635-4, RTECS DJ3100040, BRN 231523, MDL MFCD00016954 | | 100mg 500mg 1g |
| |  ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): Analog of genistein and an agonist at estrogen receptors | | |
| | 2,6-Dihydroxyisonicotinic acid , see Citrazinic acid, A15461, p. 164 | | |
| A12681 | 4,6-Dihydroxy-2-mercaptopyrimidine, 98% [2-Thiobarbituric acid, 2-Mercaptopyrimidine-4,6-dione] [504-17-6], C ₄ H ₄ N ₂ O ₂ S, F.W. 144.15, m.p. >300°, EINECS 207-985-8, RTECS CQ7700000, BRN 120663, MDL MFCD00006674, † |  | 25g 100g 500g |
| |  ! H:H315-H319-H335, P:P280g-P305+P351+P338 Application(s): Used in a neuraminidase activity and inhibition assay | | |
| | 3,4-Dihydroxy-α-(methylaminomethyl)benzyl alcohol , see DL-Adrenaline, J63005, p. 80 2,4-Dihydroxy-5-methylpyrimidine , see Thymine, A15879, p. 369 2,4-Dihydroxy-6-methylpyrimidine , see 6-Methyluracil, B24191, p. 291 | | |
| A17739 | 1,3-Dihydroxynaphthalene, 98% ▲ [1,3-Naphthalenediol, Naphthoresorcinol] [132-86-5], C ₁₀ H ₈ O ₂ , F.W. 160.17, m.p. 123-126°, Merck 14,6396, EINECS 205-079-7, RTECS QJ4725000, BRN 2044002, MDL MFCD00003965, † |  | 1g 5g |
| |  ! H:H341-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | | |
| A17297 | 4,5-Dihydroxynaphthalene-2,7-disulfonic acid disodium salt dihydrate, 98% [Chromotropic acid disodium salt dihydrate] [5808-22-0], C ₁₀ H ₆ Na ₂ O ₆ S ₂ ·2H ₂ O, F.W. 400.29 (364.26anhy), m.p. >300°, Merck 14,2241, EINECS 204-972-9, BRN 3647189, MDL MFCD00150612, † |  | 10g 50g |
| |  ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | | |


| Stock # | Description | | Size |
|---------------|--|---|--|
| A15893 | 3,4-Dihydroxyphenylacetic acid, 98+% [Homoprotocatechuic acid] [102-32-9], C ₈ H ₈ O ₄ , F.W. 168.15, m.p. 128-130°, EINECS 203-024-1, RTECS AH0590000, BRN 2211017, MDL MFCD00004338 ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a |  | 1g 5g 25g |
| 41535 | 3,4-Dihydroxy-DL-phenylalanine, 98% [DL-DOPA, 3-Hydroxy-DL-tyrosine] [63-84-3], C ₉ H ₉ NO ₄ , F.W. 197.19, Crystalline, m.p. 290° dec., Merck 14,3420, EINECS 200-566-0, RTECS AY5250000, MDL MFCD00063060 ! H: H302, P: P264-P270-P301+P312-P330-P501a |  | 5g 25g 100g |
| A11311 | 3,4-Dihydroxy-L-phenylalanine, 98+% ▲ [L-DOPA, 3-Hydroxy-L-tyrosine] [59-92-7], C ₉ H ₉ NO ₄ , F.W. 197.19, m.p. ca 295° dec., Merck 14,5464, EINECS 200-445-2, RTECS AY5600000, BRN 2215169, MDL MFCD00002598, † ! H: H302, P: P264-P270-P301+P312-P330-P501a |  | 5g 25g 100g |
| | (-)-cis-2-(3,4-Dihydroxyphenyl)-3,4-dihydro-1(2H)-benzopyran-3,5,7-triol 3-gallate, see (-)-Epicatechin gallate, J60814, p. 208 2-(3,4-Dihydroxyphenyl)ethylamine hydrochloride, see Dopamine hydrochloride, A11136, p. 201 1,2-Dihydroxypropane, see 1,2-Propanediol, 30948, p. 329 1,2-Dihydroxy-2-propanone, see 1,3-Dihydroxyacetone, J60592, p. 191 7-[2,3-Dihydroxypropyl]-theophylline, see Dyphylline, J63167, p. 203 2,6-Dihydroxypurine, see Xanthine, A11077, p. 393 2,6-Dihydroxypyridine-4-carboxylic acid, see Citrazinic acid, A15461, p. 164 | | |
| L07160 | 4,6-Dihydroxy-1H-pyrazolo[3,4-d]pyrimidine, 98+% [Oxypurinol, 1H-Pyrazolo[3,4-d]pyrimidine-4,6(5H,7H)-dione] [2465-59-0], C ₅ H ₄ N ₄ O ₂ , F.W. 152.11, m.p. >300°, EINECS 219-570-9, BRN 139956, MDL MFCD00056934 Application(s): An inhibitor of xanthine oxidase 2,4-Dihydroxypyrimidine, see Uracil, A15570, p. 388 |  | 250mg 1g 5g |
| A15688 | 4,6-Dihydroxypyrimidine, 98% [4,6-Pyrimidinediol] [1193-24-4], C ₄ H ₄ N ₂ O ₂ , F.W. 112.09, m.p. >300°, EINECS 214-772-3, RTECS UW7523000, BRN 606433, MDL MFCD00016733, † ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a |  | 25g 100g 500g |
| L18567 | 3,5-Dihydroxytoluene, 99% △ [5-Methylresorcinol, Orcinol] [504-15-4], C ₇ H ₈ O ₂ , F.W. 124.14, m.p. 106-108°, b.p. 287-290°, Merck 14,6864, EINECS 207-984-2, RTECS VH2100000, BRN 1071903, MDL MFCD00002291, † ! H: H302-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): Used in production of orcein |  | 5g 25g |
| A16554 | Diiodofluorescein ▲ [C.I. 45425] [31395-16-1], C ₂₀ H ₁₀ I ₂ O ₅ , F.W. 584.11, m.p. 239-241° dec., MDL MFCD00036461 |  | 10g 50g |
| L06841 | 2,6-Diisopropylphenol, 97% [Propofol] [2078-54-8], C ₁₂ H ₁₈ O, F.W. 178.28, m.p. 17-18°, b.p. 254-256°, f.p. 113° (235°F), d. 0.962, n _D ²⁰ 1.5140, Merck 14,7834, EINECS 218-206-6, RTECS SL0810000, BRN 1866484, MDL MFCD00008885, † ! H: H302-H315-H319, P: P280-P305+P351+P338-P302+P352-P321-P362-P501a Application(s): An anesthetic that exhibits direct activation of the GABA-A receptor 2,5-Diketopiperazine, see Glycine anhydride, A18822, p. 237 |  | 25g 100g 500g |
| J62459 | Dilazep dihydrochloride [35898-87-4], C ₂₁ H ₂₄ N ₄ O ₁₀ ·2HCl, F.W. 677.62, Powder, Merck 14,3200, RTECS DI0250000, MDL MFCD00133267 ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): Inhibits adenosine uptake and platelet aggregation; coronary vasodilator | | 50mg |
| J65568 | Dil-Lipoprotein, very low density, human plasma [Dil-VLDL, 3,3'-Dioctadecylindocarbocyanine- very low density lipoprotein] | | 1each |
| J65330 | Dil-Lipoprotein, low density, human plasma [3,3'-Dioctadecylindocarbocyanine-low density lipoprotein, Dil-LDL] | | 200micrograms |
| J65597 | Dil-Lipoprotein, low density, acetylated, human plasma [3,3'-Dioctadecyloxycarbocyanine-acetylated low density lipoprotein, Dil-Ac-LDL] | | 200micrograms |


| Stock # | Description | Size |
|---|--|---------------------|
| J64164 | Dil-Lipoprotein, low density, oxidized, human plasma [3,3'-Dioctadecyloxycarbocyanine-oxidized low density lipoprotein, Dil-Oxidized LDL] | 1each |
| J65503 | Dil-Lipoprotein, high density, human plasma [3,3'-Dioctadecylindocarbocyanine-high density lipoprotein, Hil-HDL] | 1each |
| J63245 | (+)-cis-Diltiazem hydrochloride [33286-22-5], C ₂₂ H ₂₆ N ₂ O ₄ S HCl, F.W. 450.98, Powder, m.p. 207-212°, Merck 14,3202, EINECS 251-443-3, RTECS DL0310000, BRN 4228706, MDL MFCD00069252 !  H:H302-H312-H332-H361, P:P261-P280-P281-P302+P352-P405-P501 | 5g 10g 25g |
| Application(s): An L-type calcium channel blocker | | |
| J61079 | Dimaprit dihydrochloride [(S)-(-3-Dimethylaminopropyl)isothiourea dihydrochloride] [23256-33-9], C ₆ H ₁₅ N ₃ S 2HCl, F.W. 234.19, Powder, RTECS UM3850000, MDL MFCD00069260 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 100mg |
| Application(s): Selective histamine H2 agonist | | |
| A10140 | Dimedone, 98% [5,5-Dimethyl-1,3-cyclohexanedione] [126-81-8], C ₈ H ₁₂ O ₂ , F.W. 140.18, m.p. 146-150°, Merck 14,3242, Fieser 1,266, EINECS 204-804-4, RTECS GV0345000, BRN 471489, MDL MFCD00001588, † Classical reagent for the identification and isolation of aldehydes: <i>J. Org. Chem.</i> , 11 , 95 (1946). For conditions leading to exclusive 2-monomethylation, see: <i>Synth. Commun.</i> , 3 , 347 (1973). For direct nitration at the 2-position, see review on α-nitroketones: <i>Synthesis</i> , 261 (1980). Undergoes an example of an oxidative addition of 1,3-dicarbonyl compounds, mediated by CAN (Cerium(IV) ammonium nitrate, A12882), to give an alkene, e.g. with 2-methyl-2-pentene, the product is a fused dihydrofuran derivative: <i>J. Chem. Soc., Perkin 1</i> , 187 (1995):  | 25g 100g 500g |
| A comparative study has shown that CAN is superior to Mn(OAc) ₃ for this type of reaction: <i>J. Chem. Soc., Perkin 1</i> , 1487 (1996). | | |
| Application(s): Reagent used in synthesis of fused 3-methylfurans | | |
| J63718 | Dimenhydrinate [Amosyl] [523-87-5], C ₁₇ H ₂₁ NO ₇ , F.W. 469.96, Powder, m.p. 102-107°, Merck 14,3207, EINECS 208-350-8, RTECS XH5082000, MDL MFCD00054265, † ! H:H302, P:P264-P270-P301+P312-P330-P501 | 25g |
| Application(s): A histamine H1 antagonist | | |
| Dimercaprol , see 2,3-Dimercaptopropanol, L03953, p. 194 erythro-1,4-Dimercapto-2,3-butanediol , see 1,4-Dithioerythritol, A10138, p. 200 (±)-threo-1,4-Dimercapto-2,3-butanediol , see 1,4-Dithio-DL-threitol, A15797, p. 200 1,2-Dimercaptoethane , see Ethambutol dihydrochloride, J60695, p. 213 | | |
| L03953 | 2,3-Dimercaptopropanol, 97% Δ [BAL, Dimercaprol] [59-52-9], C ₃ H ₆ OS ₂ , F.W. 124.22, b.p. 120°/15mm, f.p. >110°(230°F), d. 1.244, n _D ²⁰ 1.5740, Merck 14,3209, UN2810, EINECS 200-433-7, RTECS UB2625000, BRN 1732058, MDL MFCD00004864, † ! H:H302-H315-H319-H317, P:P261-P280-P305+P351+P338-P302+P352-P321-P501a | 1g 5g 25g |
| Application(s): British Anti-Lewisite. A chelator that inhibits sugar nucleotide degradation. | | |
| 3,3'-Dimethoxybenzidine , see o-Dianisidine, A17150, p. 184 3,3'-Dimethoxybenzidine dihydrochloride , see o-Dianisidine dihydrochloride, A17175, p. 184 1-(3,4-Dimethoxybenzyl)-6,7-dimethoxyisoquinoline hydrochloride , see Papaverine hydrochloride, B25412, p. 312 10,11-Dimethoxystrychnine , see Brucine, J61178, p. 138 | | |
| J65540 | cis-5-(3,5-Dimethoxystyryl)-2-methoxyphenol [5-[(1Z)-2-(3,5-Dimethoxyphenyl)ethenyl]-2-methoxyphenol, cis-3,4',5'-Trimethoxy-3'-hydroxystilbene] [586410-08-4], C ₁₇ H ₁₈ O ₄ , F.W. 286.32, Oil | 10mg |
| J65136 | 5'-O-(4,4'-Dimethoxytrityl)-2'-deoxyinosine, 98% [2'-Deoxy-5'-O-DMT-inosine, 5'-O-DMT-2'-deoxyinosine] [93778-57-5], C ₃₁ H ₃₀ N ₄ O ₆ , F.W. 554.59, Powder, MDL MFCD00080301 | 1g |
| J64050 | 5'-O-(4,4'-Dimethoxytrityl)-2'-deoxyinosine-3'-CE-phosphoramidite, 98% C ₄₀ H ₄₇ N ₄ O ₇ P, F.W. 754.81, Powder ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| J65960 | 5'-O-(4,4'-Dimethoxytrityl)-2'-deoxyuridine, 98% [5'-O-DMT-dU, 5'-O-DMT-2'-deoxyuridine] [23669-79-6], C ₃₀ H ₃₀ N ₂ O ₇ , F.W. 530.57, Powder, EINECS 245-814-9, MDL MFCD00063410 | 1g |



| Stock # | Description | Size |
|---------|--|------------------------|
| J65478 | 5'-O-(4,4'-Dimethoxytrityl)-2'-deoxyuridine-3'-CE-phosphoramidite, 98% C ₃₀ H ₄₇ N ₇ O ₉ P, F.W. 730.78, Powder ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| J65936 | 5'-O-(4,4'-Dimethoxytrityl)-N₂-dimethylformamidinyl-2'-fluoro-2'-deoxyguanosine, 98% C ₃₄ H ₃₅ FN ₆ O ₆ , F.W. 642.68, Powder | 1g |
| J65536 | 5'-O-(4,4'-Dimethoxytrityl)-N₂-dimethylformamidinyl-2'-fluoro-2'-deoxyguanosine-3'-CE-phosphoramidite, 98% C ₄₃ H ₅₂ FN ₈ O ₇ P, F.W. 842.89, Powder ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| J65794 | 5'-O-(4,4'-Dimethoxytrityl)-N₂-dimethylformamidinyl-2'-O-methylguanosine, 98% C ₃₅ H ₃₈ N ₆ O ₇ , F.W. 654.71, Powder | 1g |
| J65699 | 5'-O-(4,4'-Dimethoxytrityl)-N₂-dimethylformamidinyl-2'-O-methylguanosine-3'-CE-phosphoramidite, 98% C ₄₄ H ₅₅ N ₆ O ₉ P, F.W. 854.93, Powder ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| J65008 | 5'-O-(4,4'-Dimethoxytrityl)-2'-fluoro-2'-deoxyinosine, 98% [2'-Deoxy-5'-O-DMT-2'-fluorinosine] C ₃₁ H ₂₉ FN ₄ O ₆ , F.W. 572.58, Powder | 1g |
| J64217 | 5'-O-(4,4'-Dimethoxytrityl)-2'-fluoro-2'-deoxyuridine, 98% [2'-Deoxy-5'-O-DMT-2'-fluorouridine, 2'-Fluoro-5'-O-DMT-uridine] [146954-74-7], C ₃₀ H ₂₉ N ₂ O ₇ F, F.W. 548.56, Powder | 5g |
| J65350 | 5'-O-(4,4'-Dimethoxytrityl)-2'-fluoro-2'-deoxyuridine-3'-CE-phosphoramidite, 98% C ₃₀ H ₄₅ FN ₇ O ₉ P, F.W. 748.77, Powder ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| J64232 | 5'-O-(4,4'-Dimethoxytrityl)-2'-fluoro-N₂-isobutryryl-2'-deoxyguanosine, 98% C ₃₅ H ₃₅ FN ₆ O ₇ , F.W. 657.69, Powder | 1g |
| J65817 | 5'-O-(4,4'-Dimethoxytrityl)-2'-fluoro-N₂-Isobutryryl-2'-deoxyguanosine-3'-CE-phosphoramidite, 98% C ₄₄ H ₅₃ FN ₇ O ₉ P, F.W. 857.90, Powder ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| J65583 | 5'-O-(4,4'-Dimethoxytrityl)-N₂-isobutryryl-2'-O-methylguanosine, 98% C ₃₈ H ₃₉ N ₅ O ₈ , F.W. 669.72, Powder | 1g |
| J65100 | 5'-O-(4,4'-Dimethoxytrityl)-N₂-isobutryryl-2'-O-methylguanosine-3'-CE-phosphoramidite, 98% C ₄₅ H ₅₆ N ₇ O ₉ P, F.W. 869.94, Powder ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| J65498 | 5'-O-(4,4'-Dimethoxytrityl)-N₆-methyl-2'-deoxyadenosine, 98% C ₃₂ H ₃₃ N ₅ O ₈ , F.W. 567.63, Powder | 1g |
| J64825 | 5'-O-(4,4'-Dimethoxytrityl)-2'-O-methylinosine, 98% C ₃₂ H ₃₂ N ₄ O ₇ , F.W. 584.62, Powder | 1g |
| J64880 | 5'-O-(4,4'-Dimethoxytrityl)-2'-O-methyluridine, 98% C ₃₁ H ₃₂ N ₂ O ₈ , F.W. 560.59, Powder | 1g |
| J65508 | 5'-O-(4,4'-Dimethoxytrityl)-2'-O-methyluridine-3'-CE-phosphoramidite, 98% C ₄₀ H ₄₉ N ₄ O ₉ P, F.W. 760.81, Powder ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| A10924 | N,N-Dimethylacetamide, 99% [DMA] [127-19-5], CH ₃ CON(CH ₃) ₂ , F.W. 87.12, m.p. -20°, b.p. 165-166°, f.p. 70°(158°F), d. 0.940, n _D ²⁰ 1.4385, Merck 14,3227, Fieser 1,270 2,144 4,165, EINECS 204-826-4, RTECS AB7700000, BRN 1737614, MDL MFCD00008686, † ! H:H360D-H312-H332, P:P261-P280-P281-P302+P352-P405-P501a Dipolar aprotic solvent, cf N,N-Dimethylformamide, A13547 , Dimethyl sulfoxide, A13280 , 1-Methyl-2-pyrrolidinone, A12260 . See also Sodium hydride, 13431 , for warning. Useful solvent in halox fluorinations of chloroarenes; compare Sulfolane, A13466 . Undergoes Vilsmeier-type reactions (compare DMF), with reactive substrates, introducing an acetyl group: <i>Chem. Ber.</i> , 97 , 616 (1964). | 250ml 500ml 2.5L |




| Stock # | Description | Size |
|---------------|---|--|
| | <p>Reacts with alkyl and aryl Grignard reagents to give methyl ketones in good yields: <i>Synthesis</i>, 228 (1984). In the presence of triflic anhydride and 2,4,6-collidine, forms a highly-reactive kateniumion triflate, which undergoes a [2+2] cycloaddition reaction with terminal alkenes to give, after hydrolysis a 3-alkylcyclobutanone: <i>J. Am. Chem. Soc.</i>, 107, 2192 (1985); <i>Org. Synth. Coll.</i>, 8, 306 (1993):</p> $\text{CH}_3\text{CON}(\text{CH}_3)_2 + \text{CH}_3(\text{CH}_2)_k\text{CH}=\text{CH}_2 \xrightarrow[\text{(CH}_2\text{)}_2]{\text{(CF}_3\text{SO}_2)_2\text{O, 2,4,6-collidine}} \left[\text{CH}_3(\text{CH}_2)_k \text{---} \text{C}^+\text{---} \text{NMe}_2 \right] \text{CF}_3\text{SO}_3^- \xrightarrow{\text{H}_2\text{O}} \text{CH}_3(\text{CH}_2)_k \text{---} \text{C}=\text{O} \quad 59\%$ | |
| B21174 | <p>Dimethyl adipate, 99% <i>[Adipic acid dimethyl ester, Hexanedioic acid dimethyl ester]</i> [627-93-0], $\text{C}_8\text{H}_{16}\text{O}_4(\text{CH}_3)_2$, $\text{CO}_2\text{C}_2\text{H}_5$, F.W. 174.20, m.p. 8°, b.p. 109-110°/14mm, f.p. 107°(224°F), d. 1.063, n_D^{20} 1.4280, Merck 14,162, EINECS 211-020-6, RTECS AV1645000, BRN 1707443, MDL MFCD00008469, †</p> | <p>50g 250g 1kg</p> |
| | <p>cis-1-(4-Dimethylaminoethoxyphenyl)-1,2-diphenyl-1-butene, see Tamoxifen, 98+%, J63509, p. 357 cis-1-(4-Dimethylaminoethoxyphenyl)-1,2-diphenyl-1-butene citrate, see Tamoxifen citrate, J60955, p. 357 2-(Dimethylamino)ethyl 4-(n-butylamino)benzoate hydrochloride, see Tetracaine hydrochloride, J63272, p. 361 (S)-4-(3-[2-(Dimethylamino)ethyl]-5-indolylmethyl)oxazolidin-2-one, see Zolmitriptan, J60616, p. 397</p> | |
| J65367 | <p>4-(Dimethylamino)-N-[6-(hydroxyamino)-6-oxohexyl]-benzamide $\text{C}_{18}\text{H}_{23}\text{N}_3\text{O}_5$, F.W. 293.36, Crystalline solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501</p> | 10mg |
| | <p>5-Dimethylamino-1-naphthalenesulfonamide, see Dansyl amide, A11449, p. 175 5-Dimethylamino-1-naphthalenesulfonyl chloride, see Dansyl chloride, A13828, p. 175 2-[4-(Dimethylamino)phenyl]azobenzoic acid, see Methyl Red hydrochloride, 36668, p. 290 2-[4-(Dimethylamino)phenyl]azobenzoic acid sodium salt, see Methyl Red sodium salt, 36667, p. 290</p> | |
| A10807 | <p>1-(3-Dimethylaminopropyl)-3-ethylcarbodiimide hydrochloride, 98+%  <i>[EDAC, EDCI]</i> [25952-53-8], $\text{CH}_3\text{CH}_2\text{N}=\text{C}=\text{N}(\text{CH}_2)_3\text{N}(\text{CH}_3)_2\text{HCl}$, F.W. 191.70, m.p. ca 113°, Fieser 1,371 2,196 12,199, EINECS 247-361-2, RTECS FF2200000, BRN 5764110, MDL MFCD00012503, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 'Water-soluble carbodiimide', widely used for peptide coupling, with the major advantage that excess reagent and the urea by-product can be easily removed by washing with dilute acid or water: <i>J. Org. Chem.</i>, 26, 2525 (1961); <i>J. Am. Chem. Soc.</i>, 87, 2492 (1965). For discussion of the mechanism of peptide coupling with this reagent, see: <i>J. Am. Chem. Soc.</i>, 103, 7090 (1981). Often used in conjunction with an additive such as HOBt (1-hydroxybenzotriazole hydrate) to suppress racemization; see, for example: <i>Bull. Chem. Soc. Jpn.</i>, 55, 2165 (1982). A two-phase solvent system (dichloromethane-water or isopropyl acetate-water) has been found to give superior results in this type of peptide coupling: <i>J. Org. Chem.</i>, 60, 3569 (1995). In a comparative study, submolar quantities HOBt in DMF-water gave good results: <i>Chem. Lett.</i>, 1 (1997). For use in the synthesis of cyclic derivatives of 3'-amino-3'-deoxyadenosine-5'-di- and triphosphates, see: <i>Angew. Chem. Int. Ed.</i>, 33, 1394 (1994). Promotes various other N-acylation reactions such as the formation of N-acylsulfonamides from primary sulfonamides and N-protected amino acids in the presence of DMAP: <i>Synlett</i>, 1141 (1995). For use in the acylation of phosphoranes, see (Cyanomethyl)triphenylphosphonium chloride, A13096.</p> | <p>1g 5g 25g</p> |
| J65596 | <p>5-[3-(Dimethylamino)propylidene]dibenzosuberane hydrochloride, 98% <i>[Amitriptyline hydrochloride, 5-(10,11-Dihydro-5H-dibenzo[a,d]cycloheptene)-N,N-dimethylpropan-1-amine hydrochloride]</i> [549-18-8], $\text{C}_{20}\text{H}_{22}\text{N}\text{HCl}$, F.W. 313.86, Powder, m.p. 196-197°, Merck 14,487, UN2811, EINECS 208-964-6, RTECS HO9450000, MDL MFCD00012537, †  H:H301-H311-H330-H315-H319-H334-H317-H361-H335, P:P301+P310-P304+P340-P305+P351+P338-P320-P330-P361-P405-P501</p> | <p>25g 100g</p> |
| | <p>Application(s): A tricyclic serotonin reuptake inhibitor</p> | |
| | <p>11-(3-Dimethylaminopropylidene)-6,11-dihydrodibenz[b,e]oxepine hydrochloride, see Doxepin hydrochloride, J62579, p. 201 (S)-(3-Dimethylaminopropyl)isothioureia dihydrochloride, see Dimaprit dihydrochloride, J61079, p. 194 Dimethylarsinic acid sodium salt trihydrate, see Cacodylic acid sodium salt trihydrate, A18139, p. 141</p> | |
| J63361 | <p>1,1-Dimethylbiguanide hydrochloride <i>[Metformin hydrochloride]</i> [1115-70-4], $\text{NH}_2\text{C}(\text{=NH})\text{NHC}(\text{=NH})\text{N}(\text{CH}_3)_2\text{HCl}$, F.W. 165.62, Powder, m.p. 218-226°, Merck 14,5938, EINECS 214-230-6, RTECS DU1800000, MDL MFCD00012582 ! H:H302-H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P501a</p> | <p>5g 25g 100g</p> |
| | <p>Application(s): An antidiabetic agent</p> | |
| | <p>Dimethyl butane-1,4-dicarboxylate, see Dimethyl adipate, B21174, p. 196 5,5-Dimethyl-1,3-cyclohexanedione, see Dimezone, A10140, p. 194</p> | |
| J61050 | <p>(S)-(+)-2,2-Dimethylcyclopropanecarboxamide [75885-58-4], $\text{C}_8\text{H}_{15}\text{NO}$, F.W. 113.16, Crystalline powder, EINECS 278-334-3, MDL MFCD00216614 ! H:H302-H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P501</p> | 1g |
| | <p>Application(s): For synthesis of optically active products</p> | |
| | <p>3,3-Dimethyl-DL-cysteine, see DL-Penicillamine, B24710, p. 313 3,3-Dimethyl-D-cysteine, see D-(-)-Penicillamine, A11446, p. 313 (±)-2,2-Dimethyl-1,3-dioxolane-4-methanol, see Solketal, L02814, p. 349 2,9-Dimethyl-4,7-diphenyl-1,10-phenanthroline, see Bathocuproin, B22841, p. 117 2,9-Dimethyl-4,7-diphenyl-1,10-phenanthroline disulfonic acid disodium salt, see Bathocuproin sulfonate disodium salt hydrate, B22550, p. 118</p> | |









| Stock # | Description | Size |
|---------|---|---|
| 39117 | N,N-Dimethylformamide, ACS, 99.8+% [68-12-2], HCON(CH ₂) ₂ , F.W. 73.09, m.p. -61°, b.p. 153°, f.p. 57° (135°F), d. 0.944, n _D ²⁰ 1.4310, Merck 14,3243, Fieser 1,273 9,182 11,198 12,203 14,148 16,144 18,146 19,137 21,178 , UN2265, EINECS 200-679-5, RTECS LQ2100000, BRN 605365, MDL MFCD00003284, † Maximum level of impurities: Appearance Clear, Color (APHA) 15, Evaporation residue 0.005%, Titratable base 0.003meq/g, Titratable acid 0.0005meq/g, H ₂ O 0.15% ⚠️ ! H:360D-H226-H312-H332-H319, P:P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a | 500ml 1L 4L 4x1L 4x4L |
| J64577 | N₂-Dimethylformamidinyl-2'-O-methylguanosine, 98% C ₁₄ H ₂₀ N ₆ O ₅ , F.W. 352.35, Powder | 1g |
| A11398 | N-(1,1-Dimethyl-2-hydroxyethyl)-3-amino-2-hydroxypropanesulfonic acid , see AMPSO, 98+%, J62378, p. 103 3,7-Dimethyl-2,6-octadienyl bromide , see Geranyl bromide, A14093, p. 231 (+/-)-3,7-Dimethyl-6-octenal , see (±)-Citronellal, L15753, p. 165 | |
| A11398 | 2,9-Dimethyl-1,10-phenanthroline hemihydrate, 98+% [Neocuproine] [34302-69-7], C ₁₄ H ₁₂ N ₂ ·0.5H ₂ O, F.W. 217.27 (208.26anhy), m.p. 160-164°, Merck 14,6449, EINECS 207-601-9, BRN 153179, MDL MFCD00149306, † ! H:315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Reagent for copper: <i>Anal. Chem.</i> , 46 , 692 (1974). Complexing agent for Cu(I) in the formation of aryl-sulfur bonds by reaction of aryl iodides with aryl and alkyl thiols: <i>Org. Lett.</i> , 4 , 2803 (2002). Co-catalyst in the Pd-catalyzed oxidation of alcohols: <i>Adv. Synth. Catal.</i> , 345 , 1341 (2003). |  5g 25g 100g |
| J63698 | 2,9-Dimethyl-1,10-phenanthroline, 98% [Neocuproine] [484-11-7], C ₁₄ H ₁₂ N ₂ , F.W. 208.26, Powder, m.p. 159-164°, Merck 14,6449, Solubility: Soluble in methanol, EINECS 207-601-9, RTECS SF8380000, MDL MFCD00004973, † ! H:315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 5g 25g |
| 43244 | Dimethylsuberimidate dihydrochloride  [34490-86-3], C ₁₈ H ₂₀ N ₂ O ₂ ·2HCl, F.W. 273.20, Crystalline, m.p. 213-214°, Solubility: Soluble in water, EINECS 252-060-4, MDL MFCD00012574, † ! H:315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 2g 10g |
| 36480 | Dimethyl sulfoxide, ACS, 99.9% min  [67-68-5], (CH ₃) ₂ SO, F.W. 78.13, Clear, colorless Liquid, m.p. 18.4°, b.p. 189°, f.p. 87° (189°F), d. 1.101, n _D ²⁰ 1.4790, Merck 14,3259, Fieser 1,296 14,150 15,146 16,149 17,127 18,149 20,154 21,180 , EINECS 200-664-3, RTECS PV6210000, BRN 506008, MDL MFCD00002089, † Maximum level of impurities: Evaporation residue 0.01%, Titratable acid 0.001meq/g, H ₂ O 0.1% H:H227, P:P210-P280-P370+P378a-P403+P235-P501a | 500ml 1L 4L 4x1L 4x4L |
| L19664 | 1,3-Dimethyluracil, 99% [874-14-6], C ₆ H ₈ N ₂ O ₂ , F.W. 140.14, m.p. 119-122°, EINECS 212-856-4, BRN 124074, MDL MFCD00038065, † |  1g 5g |
| B24818 | Dimidium bromide, 95% [3,8-Diamino-5-methyl-6-phenylphenanthridinium bromide] [518-67-2], C ₂₀ H ₁₈ BrN ₃ , F.W. 380.31, m.p. 230° dec., EINECS 208-256-7, RTECS SF7960500, MDL MFCD00011757 ! H:315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a |  250mg 1g |
| B21430 | 2,4-Dinitrobenzenesulfonic acid hydrate, 98% [89-02-1], C ₆ H ₄ N ₂ O ₅ ·xH ₂ O, F.W. 248.17(anhy), m.p. 107-109°, UN2585, EINECS 201-876-9, RTECS DB6500000, MDL MFCD00150961, † ⚠️ H:314, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a |  25g 100g |
| | Application(s): Used to prepare ether-soluble 2,4-dinitrophenyl derivatives of amino alcohols 2,4-Dinitrochlorobenzene , see 1-Chloro-2,4-dinitrobenzene, A13774, p. 155 | |

| Stock # | Description | Size |
|---------|---|-----------------------|
| | 5,7-Dinitro-8-hydroxy-2-naphthalenesulfonic acid disodium salt , see Naphthol Yellow S, B20872, p. 298 | |
| J60911 | 6,7-Dinitroquinoxaline-2,3-dione [DNXQ] [2379-57-9], C ₈ H ₄ N ₄ O ₆ , F.W. 252.14, Powder, m.p. >300°, MDL MFCD00069257 | 10mg 50mg |
| | Application(s): Potent competitive non-NMDA glutamate receptor antagonist | |
| J64267 | DiO-Lipoprotein, low density, human plasma [3,3'-Dioctadecyloxycarbocyanine-low density lipoprotein, DiO-LDL] | 1each |
| J64029 | DiO-Lipoprotein, low density, acetylated, human plasma [3,3'-Dioctadecyloxycarbocyanine-acetylated low density lipoprotein, DiO-Ac-LDL] | 200micrograms |
| J60976 | Diosgenin [3-β-Hydroxy-5-spirostene, Nitogenin] [512-04-9], C ₂₇ H ₄₂ O ₅ , F.W. 414.63, Powder, m.p. 200-206°, Merck 14,3295, EINECS 208-134-3, RTECS WH1450000, BRN 94582, MDL MFCD00016887 | 5g 25g 100g |
| | Application(s): Useful for synthesis of steroid products. Can be converted to pregnenolone and progesterone | |
| J62073 | Diosmin [3',5',7-Trihydroxy-4'-methoxyflavone 7-rutinoside] [520-27-4], C ₂₈ H ₃₂ O ₁₅ , F.W. 608.50, Powder, m.p. 274°, Merck 14,3297, EINECS 208-289-7, MDL MFCD00009772 | 5g 25g 100g |
| | Application(s): Natural flavanoid with anti-inflammatory effects | |
| | 2,5-Dioxo-3-pyrroline , see Maleimide, A13135, p. 275 β-(3,5-Dioxo-1,2,4-oxadiazolidin-2-yl)-L-alanine , see (+)-Quisqualic acid, 99+%, J61591, p. 334 3-(3,5-Dioxo-1,2,4-oxadiazolidin-2-yl)-L-alanine , see (+)-Quisqualic acid, 99+%, J61591, p. 334 2,6-Dioxo-1,2,3,6-tetrahydropyrimidine-4-carboxylic acid , see Orotic acid hydrate, A18594, p. 309 | |
| A10136 | Diphenhydramine hydrochloride, 99% ▲ [147-24-0], (C ₁₆ H ₁₉) ₂ CHOCH ₂ CH ₂ N(CH ₃) ₂ HCl, F.W. 291.82, m.p. 168-169°, UN2811, EINECS 205-687-2, MDL MFCD00012479 | 50g 250g 1kg |
| | ⚠ H.H351-H361-H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Application(s): A histamine H1 receptor antagonist | |
| | Diphenyl , see Biphenyl, A10265, p. 125 | |
| L02404 | Diphenylacetonitrile, 99% [86-29-3], C ₁₄ H ₁₁ N, F.W. 193.25, m.p. 72-76°, b.p. 181°/12mm, f.p. 120°(248°F), Merck 14,3316, EINECS 201-662-5, RTECS AL9800000, BRN 1911160, MDL MFCD0001862, † | 100g 500g |
| | ⚠ H.H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a In the presence of a phase-transfer catalyst, undergoes an unusual addition reaction with acetylene and other alkynes: <i>Org. Synth. Coll.</i> , 6, 940 (1988): | |
| |  | |
| J62298 | 4-Diphenylacetoxy-N-methylpiperidine methiodide [4-DAMP methiodide] [1952-15-4], C ₂₁ H ₂₈ INO ₂ , F.W. 451.40, Powder, m.p. 211-213°, MDL MFCD00078564 | 25mg 100mg |
| | Di-L-Phenylalanine , see L-Phenylalanyl-L-phenylalanine, J60043, p. 316 1-(α,4-Diphenylbenzyl)imidazole , see Bifonazole, 99%, J63253, p. 125 | |
| J64838 | Diphenyleneiodonium chloride [DPI chloride, Dibenziodolum chloride] [4673-26-1], C ₁₂ H ₈ I.Cl, F.W. 314.55, Powder, MDL MFCD00214165 | 25mg 50mg 100mg |
| | cis-1,2-Diphenylethylene , see cis-Stilbene, A11924, p. 352 Diphenyl ketone , see Benzophenone, A10739, p. 120 1-[2-(Diphenylmethoxy)ethyl]-4-(3-phenylpropyl)piperazine dihydrochloride , see GBR 12935 dihydrochloride, J62991, p. 230 | |
| L19398 | α,α-Diphenyl-N-methyl-D-prolinol, 97%, ee 99+% [(R)-α,α-Diphenyl-1-methylpyrrolidine-2-methanol] [144119-12-0], C ₁₈ H ₂₁ NO, F.W. 267.37, m.p. 68-71°, [α] _D ²⁰ -52° (c=1 in chloroform), BRN 1535407, MDL MFCD00145217 | 250mg 1g |
| | ⚠ H.H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| L19399 | α,α-Diphenyl-N-methyl-L-prolinol, 97%, ee 99+% [(S)-α,α-Diphenyl-1-methylpyrrolidine-2-methanol] [110529-22-1], C ₁₈ H ₂₁ NO, F.W. 267.37, m.p. 66-69°, [α] _D ²⁰ +52° (c=1 in chloroform), Fieser 17,131, BRN 4749387, MDL MFCD00145245 | 250mg 1g |
| | ⚠ H.H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| J61001 | (R)-(+)-2-(Diphenylmethyl)pyrrolidine [22348-31-8], C ₁₇ H ₁₉ N, F.W. 237.34, Liquid, MDL MFCD01861800 | Call |
| | ⚠ H.H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): For synthesis of optically active products | |
| | (R)-α,α-Diphenyl-1-methylpyrrolidine-2-methanol , see α,α-Diphenyl-N-methyl-D-prolinol, L19398, p. 198 | |




| Stock # | Description | Size |
|---------|--|---------------------|
| | (S)- α,α -Diphenyl-1-methylpyrrolidine-2-methanol, see α,α -Diphenyl-N-methyl-L-prolinol, L19399, p. 198 4,7-Diphenyl-1,10-phenanthroline, see Bathophenanthroline, A14258, p. 118 | |
| A13450 | 1,3-Diphenyl-1,3-propanedione, 98+% [Dibenzoylmethane, Dppd-H] [120-46-7], C ₁₅ H ₁₂ O ₂ , F.W. 224.26, m.p. 76-80°, b.p. 219-221°/18mm, Merck 14,3009, EINECS 204-398-9, RTECS TZ1930000, BRN 514910, MDL MFCD00003085, † Chelating ligand, e.g. for metal extraction. Reagent for uranium: <i>Anal. Chim. Acta</i> , 108 , 437 (1979). | 25g 100g 500g |
| J63641 | (R)-1,1-Diphenyl-2-propanol [52199-85-6], C ₁₅ H ₁₆ O, F.W. 176.26, Crystalline solid, MDL MFCD06762638 | 5mg 10mg |
| J63320 | (S)-1,1-Diphenyl-2-propanol [41997-47-1], C ₁₅ H ₁₆ O, F.W. 176.26, Crystalline solid, MDL MFCD06762637 | Call |
| | Application(s): For synthesis of optically active products | |
| | 1,3-Diphenyl-2-propen-1-one , see trans-Chalcone, A14734, p. 152 N-[3,3-Diphenylpropyl]-α-methylbenzylamine , see Fendiline hydrochloride, J63254, p. 219 | |
| J64676 | 2,3-Diphospho-D-glyceric acid pentasodium salt ■ [Sodium 3-hydroxy-3-phosphonato-2-(phosphonatooxy)propanoate, D-Glycerate 2,3-diphosphate pentasodium salt] [102783-53-9], C ₃ H ₅ O ₁₀ P ₂ Na ₅ , F.W. 375.95, Powder, MDL MFCD00070074 | 100mg |
| | Dipotassium phosphate , see Potassium hydrogen phosphate, 11593, p. 326 Diprophylline , see Dyphylline, J63167, p. 203 4-(Di-n-propylaminosulfonyl)benzoic acid , see Probenecid, B20010, p. 328 | |
| J63554 | 1,3-Dipropyl-8-phenylxanthine [85872-53-3], C ₁₇ H ₂₀ N ₄ O ₂ , F.W. 312.37, Powder, RTECS UO8430880 | 10mg 50mg |
| | Application(s): Selective A1 adenosine antagonist | |
| | 4-(Di-n-propylsulfamoyl)benzoic acid , see Probenecid, B20010, p. 328 | |
| J60369 | Diprotin A [H-Ile-Pro-Ile-OH, L-Isoleucyl-L-prolyl-L-isoleucine] [90614-48-5], C ₁₇ H ₃₁ N ₃ O ₄ , F.W. 341.25, Powder, RTECS NR4737000, MDL MFCD00038707 | 50mg 250mg |
| | Application(s): An inhibitor of dipeptidyl aminopeptidase IV | |
| J63321 | Diprotin B [H-Val-Pro-Leu-OH] [90614-49-6], C ₁₆ H ₂₉ N ₃ O ₄ , F.W. 327.40, Powder | 50mg 250mg |
| | Application(s): An inhibitor of dipeptidyl aminopeptidase IV | |
| J62498 | DIPSO, 0.2M buffer soln., pH 7.0 [102783-62-0], Liquid | 100ml 250ml |
| J63097 | DIPSO, 0.2M buffer soln., pH 7.5 [102783-62-0], Liquid | 100ml 250ml |
| J61388 | DIPSO, 0.2M buffer soln., pH 8.0 [102783-62-0], Liquid | 100ml 250ml |
| J62629 | DIPSO, 0.2M buffer soln., pH 8.5 [102783-62-0], Liquid | 100ml 250ml |
| J63329 | Dipyridamole [58-32-2], C ₂₀ H ₁₀ NaO ₄ , F.W. 504.63, Powder, m.p. 165-167°, Merck 14,3346, EINECS 200-374-7, RTECS KK7450000, MDL MFCD00010555 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 5g 25g |
| | Application(s): An inhibitor of adenosine transport and phosphodiesterase | |
| | 2,2'-Diquinoyl , see 2,2'-Biquinoline, A10907, p. 126 Direct Blue 1 , see Chicago Sky Blue 6B, A14242, p. 153 Direct Blue 14 , see Trypan Blue, A18600, p. 384 | |
| B21693 | Direct Red 80 [C.I. 35780, Sirius Red] [2610-10-8], C ₂₈ H ₂₈ N ₁₀ Na ₈ O ₂₁ S ₈ , F.W. 1373.09, EINECS 220-027-3, MDL MFCD00054389, † | 5g 25g 100g |
| |  | |
| | Direct Blue 86 , see Solvent Blue 38, A15395, p. 349 Disodium 3-iodoxyl phosphate , see 3-Iodoxy phosphate disodium salt, J60552, p. 256 Disodium malonate , see Malonic acid disodium salt, 44841, p. 276 Disodium 1-naphthyl phosphate hydrate , see 1-Naphthyl phosphate disodium salt hydrate, B22866, p. 298 Disodium 4-nitrophenyl phosphate , see 4-Nitrophenyl phosphate disodium salt hexahydrate, 5mg tablets, J61401, p. 304 Disodium phosphate , see Sodium hydrogen phosphate heptahydrate, 11592, p. 346 Disulfiram , see Tetraethylthiuram disulfide, B20721, p. 362 Disulfo copper phthalocyanine amine salt , see Solvent Blue 38, A15395, p. 349 (+/-)-3,3'-Dithiobis(2-aminopropionic acid) , see DL-Cystine, J63564, p. 173 | |


| Stock # | Description | Size |
|---------|---|--|
| | (+)-3,3'-Dithiobis(2-aminopropionic acid) , see D-Cystine, L13772, p. 173 (-)-3,3'-Dithiobis(2-aminopropionic acid) , see L-Cystine, A13762, p. 173 | |
| A14331 | 5,5'-Dithiobis(2-nitrobenzoic acid), 99% [<i>Bis(3-carboxy-4-nitrophenyl) disulfide, 3-Carboxy-4-nitrophenyl disulfide</i>] [69-78-3], C ₁₄ H ₈ N ₂ O ₆ S ₂ , F.W. 396.36, m.p. ca 240° dec., Fieser 1,351, EINECS 200-714-4, RTECS DG9650000, BRN 1896821, MDL MFCD00007140, t ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Reacts with free thiol groups to form a highly colored (yellow) thiolate anion: <i>Arch. Biochem. Biophys.</i> , 82 , 70 (1959); used for quantitative determination of thiols. Also used in chromogenic assay of acetylcholinesterase: <i>Enzyme Assays</i> , R. Eisenthal and M. J. Danson, Eds., OUP, Oxford (1992), p81. |  1g 5g 25g |
| | Application(s): Reagent for determination of sulfhydryl groups | |
| | Dithiocarb sodium , see Sodium diethylthiocarbamate trihydrate, A15898, p. 345 | |
| A10138 | 1,4-Dithioerythritol, 99% [<i>Cleland's Reagent DTE, erythro-1,4-Dimercapto-2,3-butanediol</i>] [6892-68-8], C ₆ H ₁₀ O ₂ S ₂ , F.W. 154.25, m.p. 82-84°, EINECS 229-998-8, RTECS KF2410000, BRN 1719756, MDL MFCD00063750, t ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Protective agent for preventing oxidation of thiol groups and reagent for reduction of disulfide groups in proteins: <i>Biochemistry</i> , 3 , 480 (1964); 11 , 2939 (1972); <i>J. Biol. Chem.</i> , 243 , 716 (1968); compare 1,4-Dithio-DL-threitol , A15797 , p. 200. |  1g 5g 25g |
| | Application(s): Reagent for maintaining thiols in reduced state. | |
| J64656 | 1,4-Dithioerythritol, Electrophoresis Grade, 99% [<i>Cleland's Reagent DTE, erythro-1,4-Dimercapto-2,3-butanediol</i>] [6892-68-8], C ₆ H ₁₀ O ₂ S ₂ , F.W. 154.25, Powder, m.p. 82-84°, EINECS 229-998-8, RTECS KF2410000, BRN 1719756, MDL MFCD00063750, t ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g 5g 25g |
| | 1,2-Dithiolane-3-valeric acid , see DL-Thioctic acid, L04711, p. 366 DL-6,8-Dithiooctanoic acid , see DL-Thioctic acid, L04711, p. 366 | |
| J65818 | 1,4-Dithio-DL-threitol, 100mM aq. soln. 250microliters [<i>DTT racemic, (±)-threo-1,4-Dimercapto-2,3-butanediol</i>] [3483-12-3], Liquid, Merck 14,3376 , EINECS 222-468-7, BRN 1719757, MDL MFCD00004877 | |
| | Application(s): For use with T7 RNA Polymerase, product no. J65896 | |
| A15797 | 1,4-Dithio-DL-threitol, 99% Δ [<i>Cleland's Reagent DTT racemic, (+/-)-threo-1,4-Dimercapto-2,3-butanediol</i>] [3483-12-3], C ₆ H ₁₀ O ₂ S ₂ , F.W. 154.25, m.p. 40-43°, b.p. 125-130°/12mm, f.p. >110°(230°F), Merck 14,3376 , EINECS 222-468-7, RTECS EK1610000, BRN 1719757, MDL MFCD00004877 ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Protective agent for preventing oxidation of thiol groups and reagent for reduction of disulfide groups in proteins: <i>Biochemistry</i> , 3 , 480 (1964); 11 , 2939 (1972); <i>J. Biol. Chem.</i> , 243 , 716 (1968); <i>Methods Enzymol.</i> , 25 , 185 (1967); 143 , 246 (1987). |  1g 5g 25g |
| | Application(s): Useful for stabilizing sulfhydryl-containing enzymes | |
| J64545 | 1,4-Dithio-DL-threitol, Electrophoresis Grade, 99% Δ [<i>Cleland's Reagent DTT racemic, (±)-threo-1,4-Dimercapto-2,3-butanediol</i>] [3483-12-3], C ₆ H ₁₀ O ₂ S ₂ , F.W. 154.25, Powder, m.p. 40-43°, b.p. 125-130°/12mm, f.p. >110°(230°F), Merck 14,3376 , EINECS 222-468-7, RTECS EK1610000, BRN 1719757, MDL MFCD00004877 ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g 5g 25g |
| | Dithranol , see 1,8,9-Trihydroxyanthracene, B20303, p. 377 | |
| J63917 | Dizocilpine maleate, 99+% [<i>(+)-MK 801 maleate, (5S,10R)-(+)-5-Methyl-10,11-dihydro-5H-dibenzo[a,d]cyclohepten-5,10-imine maleate</i>] [77086-22-7], C ₁₆ H ₁₅ N.C ₄ H ₄ O ₄ , F.W. 337.37, Crystalline powder, Merck 14,3386 , EINECS 278-614-5, RTECS HP1093575, MDL MFCD00082465 | 10mg 50mg |
| | Application(s): NMDA receptor antagonist that prevents calcium flux | |
| | DMA , see N,N-Dimethylacetamide, A10924, p. 195 DMJ , see (+)-1-Deoxymannojirimycin hydrochloride, J61277, p. 179 | |
| J62291 | DNA marker, broad range 1ml Liquid, Note: From 250-5,000 base pairs: 5 bands from 125-1,000bp; Four bands from 1,500-5,000bp 2ml | |
| J63178 | DNA marker, high range, 1,000 Base Pair Ladder 1ml Liquid, Note: Contains 8 bands from 1,000-10,000 base pairs: 1000bp increments from 1,000-6,000bp, 8,000 and 10,000bp. 2ml | |
| J63973 | DNA marker, low range, 250 Base Pair Ladder 1ml Liquid, Note: Contains seven bands from 200-3,000 base pairs: 250bp increments from 250 -1000bp, 1500, 2000 and 3000bp. 2ml | |
| J64630 | DNA Methyltransferase Inhibitor \blacktriangle 10mg [<i>RG108, N-Phthalyl-L-tryptophan</i>] [48208-26-0], C ₁₉ H ₁₄ N ₂ O ₄ , F.W. 334.32, Solid | |


| Stock # | Description | Size |
|---------------|---|------------------------|
| | DNase I , see Deoxyribonuclease I, bovine pancreas, J62229, p. 179 DNase II , see Deoxyribonuclease II, porcine spleen, J63389, p. 179 | |
| J60637 | DNAzol® Reagent Liquid, Note: DNAzol is a registered trademark of Molecular Research Center, Inc. ! H:H302+EUH032-H312-H332, P:P261-P280-P302+P352-P304+P340-P322-P501 | 50ml 100ml 200ml |
| | Application(s): Complete and ready to use reagent for the isolation of genomic DNA from solid and liquid samples of animal and plant origin | |
| | DNSA , see Dansyl amide, A11449, p. 175 DNSCl , see Dansyl chloride, A13828, p. 175 DNXQ , see 6,7-Dinitroquinoxaline-2,3-dione, J60911, p. 198 | |
| J61333 | Dobutamine hydrochloride [(±)-3,4-Dihydroxy-N-[3-(4-hydroxyphenyl)-1-methylpropyl]-β-phenethylamine hydrochloride] [49745-95-1], C ₁₈ H ₂₃ NO ₅ ·HCl, F.W. 337.85, Off-white solid, m.p. 184-186°, Merck 14,3395, EINECS 256-464-1, MDL MFCD00153795 ! H:H361-H302-H312-H332, P:P261-P280-P281-P302+P352-P405-P501a | 1g |
| | Application(s): A β-1 adrenoceptor agonist with weak β-2 adrenoceptor activity and some action at the α-1 adrenoceptor | |
| J60174 | Docetaxel [114977-28-5], C ₄₃ H ₅₃ NO ₁₄ , F.W. 807.88, Powder, m.p. 186-192°, Merck 14,3397, RTECS DA4172750, MDL MFCD00800737 | 100mg 500mg 1g |
| | Application(s): A second-generation cytotoxic antimicrotubule agent | |
| | Docosanoic acid , see Behenic acid, A12850, p. 118 | |
| A18862 | 2-Dodecanone, 98+% [n-Decyl methyl ketone] [6175-49-1], C ₁₂ H ₂₄ O, F.W. 184.32, m.p. 17-20°, b.p. 247°, f.p. 110°(230°F), d. 0.820, n _D ²⁰ 1.4330, EINECS 228-222-5, BRN 1703135, MDL MFCD00015064, † | 10g 50g |
| |  | |
| | N-Dodecanoyl-N-methylglycine sodium salt , see N-Lauroylsarcosine sodium salt, J60040, p. 266 | |
| L06233 | n-Dodecyl gallate, 98% ▲ [n-Dodecyl 3,4,5-trihydroxybenzoate, Gallic acid n-dodecyl ester] [1166-52-5], C ₁₉ H ₃₀ O ₅ , F.W. 338.45, m.p. 95-98°, EINECS 214-620-6, RTECS DH9100000, BRN 2701981, MDL MFCD00002195, † ! H:H317, P:P261-P280-P302+P352-P321-P363-P501a | 50g 250g |
| |  | |
| | n-Dodecyl sulfate sodium salt , see Sodium n-dodecyl sulfate, A11183, p. 346 n-Dodecyl 3,4,5-trihydroxybenzoate , see n-Dodecyl gallate, L06233, p. 201 | |
| J61608 | Domoic acid [14277-97-5], C ₁₅ H ₂₁ NO ₆ , F.W. 311.30, Crystalline powder, m.p. 213-217°, Merck 14,3417, RTECS UX9665100, BRN 4229251, MDL MFCD06795841 ! H:H302-H312-H332, P:P261-P280-P302+P352-P304+P340-P322-P501 | 5mg |
| | Application(s): Reported to be a potent glutamate agonist | |
| J63681 | Domperidone [57808-66-9], C ₂₂ H ₂₆ ClN ₂ O ₂ , F.W. 425.91, Crystalline powder, m.p. 243°, Merck 14,3418, EINECS 260-968-7, RTECS DE2275900, MDL MFCD00069256 ! H:H361, P:P281-P201-P202-P308+P313-P405-P501 | 25mg 100mg 500mg |
| | Application(s): Peripheral dopamine receptor antagonist that does not cross the blood-brain barrier | |
| | DL-DOPA , see 3,4-Dihydroxy-DL-phenylalanine, 41535, p. 193 L-Dopa , see L-3-(3,4-Dihydroxyphenyl)alanine, A11311, p. 193 | |
| A11136 | Dopamine hydrochloride, 99% ▲ ■ [2-(3,4-Dihydroxyphenyl)ethylamine hydrochloride, 3-Hydroxytyramine hydrochloride] [62-31-7], C ₈ H ₁₁ NO ₂ ·HCl, F.W. 189.64, m.p. 243-250°, Merck 14,3421, EINECS 200-527-8, RTECS UX1092000, BRN 3656720, MDL MFCD00012898, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 5g 25g 100g |
| |  | |
| | Application(s): A neurotransmitter and vasopressor that modulates cortical activation | |
| J61776 | Dovitinib [CHIR-258] [405169-16-6], C ₂₁ H ₂₇ FN ₃ O, F.W. 392.43, Powder, m.p. 285-310°, BRN 5702728 | 10mg 25mg 50mg |
| | Application(s): Multitargeted small-molecule tyrosine kinase receptor inhibitor | |
| J62579 | Doxepin hydrochloride [11-(3-Dimethylaminopropylidene)-6,11-dihydrodibenz[b,e]oxepine hydrochloride] [1229-29-4], C ₁₉ H ₂₁ NO·HCl, F.W. 315.84, Powder, m.p. 187-189°, Merck 14,3435, UN2811, EINECS 214-966-8, RTECS HQ4375000, MDL MFCD00079135 ! H:H301-H361, P:P281-P301+P310-P321-P308+P313-P405-P501a | 5g 25g |
| | Application(s): Potent H1-histamine receptor antagonist and a 5-HT receptor antagonist | |
| J60575 | Doxofylline [Ansimar, Maxivent] [69975-86-6], C ₁₁ H ₁₄ N ₂ O ₄ , F.W. 266.25, Crystalline powder, m.p. 144-146°, Merck 14,3438, EINECS 274-239-6 ! H:H302, P:P264-P270-P301+P312-P330-P501 | 5g |
| | Application(s): Xanthine bronchodilator that inhibits phosphodiesterase activity | |

| Stock # | Description | Size |
|---------|---|---------------------|
| J64000 | Doxorubicin hydrochloride [14-Hydroxydaunomycin] [25316-40-9], C ₂₂ H ₂₉ NO ₇ ·HCl, F.W. 579.99, Solid, m.p. 216° dec., Merck 14,3439, EINECS 246-818-3, RTECS QI9295900, BRN 4229251, MDL MFCD00077757 | 10mg 50mg |
| |  H: H350-H302, P: P281-P264-P301+P312-P308+P313-P405-P501a Application(s): Antitumor antibiotic agent that inhibits DNA topoisomerase II | |
| J63805 | Doxycycline monohydrate [Doxycycline] [17086-28-1], C ₂₂ H ₂₄ N ₂ O ₈ ·H ₂ O, F.W. 462.46 (444.44anhy), Powder, m.p. 167-168°, Merck 14,3440, MDL MFCD02682958 | 5g 25g |
| |  H: H302, P: P264-P270-P301+P312-P330-P501 Application(s): Inhibits angiogenesis and reduces lung metastases by inhibiting matrix metalloproteinases Doxycycline, see Doxycycline monohydrate, J63805, p. 202 | |
| J60579 | Doxycycline hyclate [Hydramycin, Doxycycline hydrochloride hemiethanolate hemihydrate] [24390-14-5], C ₂₂ H ₂₄ N ₂ O ₈ ·HCl·0.5H ₂ O·0.5C ₂ H ₆ O, F.W. 512.94 (503.94anhy), Powder, Merck 14,3440, RTECS QI8925000, MDL MFCD07357237 | 25g 100g |
| |  H: H302-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): Inhibits matrix metalloproteinases at subantimicrobial doses | |
| J60422 | Doxycycline hydrochloride [10592-13-9], C ₂₂ H ₂₄ N ₂ O ₈ ·HCl, F.W. 480.90, Crystalline powder, m.p. 195-201°, EINECS 234-198-7, MDL MFCD03427564 | 5g 25g |
| |  H: H302-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): Inhibits angiogenesis and reduces lung metastases by inhibiting matrix metalloproteinases Doxycycline hydrochloride hemiethanolate hemihydrate, see Doxycycline hyclate, J60579, p. 202 | |
| J64090 | Dp44mT ▲ [2-(Di(pyridin-2-yl)methylene)-N,N-dimethylhydrazinecarbothioamide, Di-2-pyridyl-ketone-4,4'-dimethyl-3-thiosemicarbazone] [152095-12-0], C ₁₄ H ₁₆ N ₆ S, F.W. 285.37, Powder, UN2811, MDL MFCD20527329 | 25mg |
| |  H: H301, P: P264-P270-P301+P310-P321-P405-P501 Dppd-H, see Dibenzoylmethane, A13450, p. 199 DSIP, see Delta Sleep-Inducing Peptide, J63334, p. 176 DTE, see 1,4-Dithioerythritol, A10138, p. 200 DTPA, see Diethylenetriaminepentaacetic acid, A10926, p. 189 DTT, see 1,4-Dithio-DL-threitol, A15797, p. 200 | |
| A18402 | Dulcitol, 97% ■ [Galactitol] [608-66-2], C ₆ H ₁₄ O ₆ , F.W. 182.17, m.p. 187-191°, b.p. 275-280°/1mm, d. 1.47, Merck 14,4332, EINECS 210-165-2, BRN 1721903, MDL MFCD00064288, † | 25g 100g 500g |
| |  Application(s): Useful reagent in bacteriology | |
| J63206 | Dulcitol, 99% ■ [Galactitol] [608-66-2], C ₆ H ₁₄ O ₆ , F.W. 182.17, Powder, m.p. 187-191°, b.p. 275-280°/1mm, d. 1.47, Merck 14,4332, EINECS 210-165-2, BRN 1721903, MDL MFCD00064288, † | 250g 500g |
| | Application(s): Useful reagent in bacteriology Durapatite, see Hydroxylapatite Durapatite, see Hydroxylapatite, fast flow, J60076, p. 249 | |
| J65171 | DY 131 [N-(4-(Diethylaminobenzylidene)-N'-(4-hydroxybenzoyl)-hydrazine] [95167-41-2], C ₁₈ H ₂₁ N ₃ O ₂ , F.W. 311.38, Solid, MDL MFCD00715585 | 10mg |
| |  H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J61330 | Dyclonine hydrochloride [1-(4-Butoxyphenyl)-3-(1-piperidinyl)-1-propanone] [536-43-6], C ₁₈ H ₂₇ NO ₂ ·HCl, F.W. 325.88, Crystalline powder, m.p. 173-178°, Merck 14,3473, EINECS 208-633-6, RTECS UG8750000, MDL MFCD00035386 | 25g 100g |
| |  H: H301-H318-H315-H335, P: P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a Dynorphin A (1-5), see Leu-Enkephalin, J61408, p. 207 | |
| J62646 | Dynorphin A (1-6), porcine [H-Tyr-Gly-Gly-Phe-Leu-Arg-OH] [75106-70-6], C ₃₄ H ₄₉ N ₅ O ₈ , F.W. 711.80, Lyophilized powder | 1mg 5mg |
| | Application(s): Biologically active fragment of dynorphin A. kappa opioid receptor agonist | |





| Stock # | Description | Size |
|---|--|---------------------|
| J63897 | Dynorphin A (1-7), porcine [H-Tyr-Gly-Gly-Phe-Leu-Arg-Arg-OH] [77101-32-7], C ₄₆ H ₆₁ N ₁₃ O ₉ , F.W. 868.00, Lyophilized powder | 1mg 5mg |
| Application(s): A biologically active fragment of dynorphin, and an opioid receptor agonist | | |
| J64636 | Dynorphin A (1-8), porcine [Tyr-Gly-Gly-Phe-Leu-Arg-Arg-Ile] [75790-53-3], C ₄₈ H ₇₂ N ₁₄ O ₁₀ , F.W. 981.15, Solid, MDL MFCD00076357 | 1mg |
| J64418 | Dynorphin A (1-9), porcine [Tyr-Gly-Gly-Phe-Leu-Arg-Arg-Ile-Arg] C ₅₂ H ₈₄ N ₁₆ O ₁₁ , F.W. 1137.33, Solid | 1mg |
| J64015 | Dynorphin A (1-13), porcine [Tyr-Gly-Gly-Phe-Leu-Arg-Arg-Ile-Arg-Pro-Lys-Leu-Lys] [72957-38-1], C ₇₅ H ₁₂₆ N ₂₄ O ₁₅ , F.W. 1603.95, Solid, RTECS JV7436666 | 1mg 5mg |
| J65394 | Dynorphin A (1-17), porcine [Prodynorphin (209-225), porcine, Tyr-Gly-Gly-Phe-Leu-Arg-Arg-Ile-Arg-Pro-Lys-Leu-Lys-Trp-Asp-Asn-Gln] C ₉₈ H ₁₅₅ N ₃₁ O ₂₃ , F.W. 2147.48, Solid | 1mg |
| J64002 | Dynorphin A (2-17), porcine [Gly-Gly-Phe-Leu-Arg-Arg-Ile-Arg-Pro-Lys-Leu-Lys-Trp-Asp-Asn-Gln] C ₉₀ H ₁₄₇ N ₂₅ O ₂₀ , F.W. 1983.32, Solid | 1mg |
| J65126 | Dynorphin A (3-17), porcine [Gly-Phe-Leu-Arg-Arg-Ile-Arg-Pro-Lys-Leu-Lys-Trp-Asp-Asn-Gln] C ₈₈ H ₁₄₃ N ₂₃ O ₂₀ , F.W. 1927.25, Solid | 1mg |
| J65986 | Dynorphin A (6-17), porcine [Arg-Arg-Ile-Arg-Pro-Lys-Leu-Lys-Trp-Asp-Asn-Gln] C ₇₁ H ₁₂₀ N ₂₆ O ₁₇ , F.W. 1609.87, Solid | 1mg |
| J64991 | Dynorphin A (13-17), porcine [Lys-Trp-Asp-Asn-Gln] C ₃₀ H ₄₃ N ₉ O ₁₀ , F.W. 689.72, Solid | 10mg 25mg |
| J65474 | [Phe7] Dynorphin A (1-7), porcine [Tyr-Gly-Gly-Phe-Leu-Arg-Phe] C ₄₃ H ₅₈ N ₁₀ O ₉ , F.W. 858.98, Solid | 10mg 25mg |
| J65622 | Dynorphin A amide, porcine [Tyr-Gly-Gly-Phe-Leu-Arg-Arg-Ile-Arg-Pro-Lys-Leu-Lys-Trp-Asp-Asn-Gln-NH2] [80448-90-4], C ₉₉ H ₁₅₆ N ₃₂ O ₂₂ , F.W. 2146.49, Solid, MDL MFCD00076351 | 1mg |
| J64409 | Dynorphin A (1-13) amide, porcine [Tyr-Gly-Gly-Phe-Leu-Arg-Arg-Ile-Arg-Pro-Lys-Leu-Lys-NH2] C ₇₅ H ₁₂₇ N ₂₅ O ₁₄ , F.W. 1602.96, Solid | 1mg 5mg |
| J65159 | Dynorphin A (2-17) amide, porcine [Gly-Gly-Phe-Leu-Arg-Arg-Ile-Arg-Pro-Lys-Leu-Lys-Trp-Asp-Asn-Gln-NH2] C ₉₀ H ₁₄₇ N ₂₅ O ₂₀ , F.W. 1983.32, Solid | 1mg |
| J64089 | Dynorphin B, porcine [Prodynorphin (228-240), Tyr-Gly-Gly-Phe-Leu-Arg-Arg-Gln-Phe-Lys-Val-Val-Thr] [85006-82-2], C ₇₄ H ₁₁₅ N ₂₁ O ₁₇ , F.W. 1570.83, Solid, MDL MFCD00076372 | 1mg |
| J64774 | Dynorphin B (1-9), porcine [Tyr-Gly-Gly-Phe-Leu-Arg-Arg-Gln-Phe] C ₅₄ H ₇₈ N ₁₆ O ₁₂ , F.W. 1143.29, Solid | 1mg |
| J64335 | Dynorphin B 29, porcine [Prodynorphin (228-256), porcine, Leumorphin, porcine] C ₁₆₁ H ₂₃₆ N ₄₂ O ₄₈ , F.W. 3527.84, Solid | 0.5mg 1mg |
| J63167 | Dyphylline [7-[2,3-Dihydroxypropyl]-theophylline, Diprophylline] [479-18-5], C ₁₀ H ₁₄ N ₄ O ₄ , F.W. 254.24, Powder, m.p. 161-162°, Merck 14,3479, EINECS 207-526-1, RTECS XH5100000, BRN 284563, MDL MFCD00005759, † ! H: H302, P: P264-P270-P301+P312-P330-P501 | 100g 500g 1kg |
| Application(s): An adenosine receptor antagonist, phosphodiesterase inhibitor and vasodilator | | |
| J62933 | E-64 [trans-Epoxy succinyl-leucylamido- [4-guanidino]butane] [66701-25-5], C ₁₅ H ₂₇ N ₅ O ₅ , F.W. 357.40, Powder, RTECS RR0390000, BRN 1405664, MDL MFCD00080261 | 5mg 25mg |
| Application(s): Selective and irreversible cysteine protease inhibitor | | |

| Stock # | Description | Size |
|---------------|---|--------------------|
| | EACA , see 6-Aminocaproic acid, A14719, p. 95 | |
| J63088 | Ebastine [90729-43-4], C ₂₂ H ₃₉ NO ₂ , F.W. 469.66, Powder, m.p. 84-87°, Merck 14,3484, RTECS EL8140000, MDL MFCD00865661 | 1g 5g |
| | Application(s): A histamine H1 receptor antagonist | |
| J64858 | EBPC [Ethyl 1-benzyl-3-hydroxy-2(5H)-oxopyrrole-4-carboxylate, CP-10668] [57056-57-2], C ₁₈ H ₁₅ NO ₄ , F.W. 261.27, Solid, MDL MFCD00179167 | 10mg |
| |  H:H302-H318, P:P280-P264-P305+P351+P338-P310-P301+P312-P501 | |
| J63190 | Ebselen [60940-34-3], C ₁₂ H ₈ NOSe, F.W. 274.20, Powder, m.p. 180-181°, Merck 14,3486, UN3283, RTECS DE4140750, MDL MFCD00210937 | 5mg 25mg |
| |  H:H330-H373-H400-H410, P:P260-P284-P304+P340-P320-P405-P501a | |
| | Application(s): Seleno-organic compound that inhibits nitric oxide-induced apoptosis. Potent antioxidant. Protects calcium influx blockage | |
| | Eburnamenine-14-carboxylic acid ethyl ester , see Vinpocetine, 98%, J61000, p. 392 | |
| J63091 | Ecdysterone [20-Hydroxyecdysone, Crustecdysone] [5289-74-7], C ₂₇ H ₄₄ O ₇ , F.W. 480.64, Powder, m.p. 242-244°, Merck 14,3491, RTECS FZ8060000, BRN 1917578, MDL MFCD00036740 | 10mg 50mg |
| | Application(s): An insect steroid hormone that induces apoptosis | |
| | ECG , see (-)-Epicatechin gallate, J60814, p. 208 | |
| J63402 | E. coli lysis buffer Liquid, Note: This buffer contains: 50mM Tris-HCl (pH 8.0), 1% Triton X-100, 1mM EDTA, and 10mM beta-mercaptoethanol. | 250ml 500ml |
| J62613 | E. coli lysis buffer-II Liquid, Note: This buffer contains: 10mM sodium phosphate (pH 7.4) with 2.7mM KCl, 140mM NaCl, and 1% Triton X-100. | 250ml 500ml |
| J63289 | E. coli sample buffer Liquid, Note: This buffer contains: 100mM magnesium chloride 64mM Tris HCL(pH 6.8), 2% SDS, 10% glycerol, 2% beta-mercaptoethanol, and 0.01% Bromophenol blue | 25ml 50ml |
| J63173 | Econazole nitrate [Ecostatin, 1-[2-(4-Chlorophenylmethoxy)-2-(2,4-dichlorophenyl)ethyl]-1H-imidazole nitrate] [24169-02-6], C ₁₈ H ₁₅ Cl ₃ N ₂ O·HNO ₃ , F.W. 444.70, Powder, m.p. 162°, Merck 14,3502, EINECS 246-053-5, RTECS NI4450000, MDL MFCD00058160 | 5g 25g |
| |  H:H302-H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P501 | |
| | Ecostatin , see Econazole nitrate, J63173, p. 204 | |
| | EDAC , see 1-(3-Dimethylaminopropyl)-3-ethylcarbodiimide hydrochloride, A10807, p. 196 | |
| | EDCI , see 1-(3-Dimethylaminopropyl)-3-ethylcarbodiimide hydrochloride, A10807, p. 196 | |
| | EDDA , see Ethylenediamine-N,N'-diacetic acid, J63570, p. 215 | |
| | Edetic acid , see Ethylenediaminetetraacetic acid, 11931, p. 215 | |
| | EDF , see Extracellular Death Factor trifluoroacetate salt, J61052, p. 218 | |
| | EDTA , see Ethylenediaminetetraacetic acid, Cell Culture Reagent, J62948, p. 215 | |
| | EDTA tetrasodium salt , see Ethylenediaminetetraacetic acid tetrasodium salt hydrate, A17385, p. 216 | |
| | EGCG , see (-)-Epigallocatechin gallate, J61745, p. 209 | |
| | EGFR Peptide (985-996) , see Epidermal Growth Factor Receptor Peptide (985-996), J64705, p. 209 | |
| | EGTA , see Ethylene glycol-O,O'-bis(2-aminoethyl)-N,N',N'-tetraacetic acid, A16086, p. 216 | |
| J61624 | 5,8,11,14-Eicosatetraynoic acid [ETYA, Octadecahydroarachidonic acid] [1191-85-1], C ₂₀ H ₂₈ O ₂ , F.W. 296.40, Solid, m.p. 81-82°, BRN 1798411, MDL MFCD00036967 | 20mg 100mg |
| | Application(s): A cyclooxygenase, lipoxigenase and cytochrome P450 inhibitor | |
| J63870 | cis-5,8,11-Eicosatrienoic acid [cis,cis,cis-5,8,11-Eicosatrienoic acid, MEAD acid] [20590-32-3], C ₂₀ H ₃₄ O ₂ , F.W. 306.50, Oil, MDL MFCD00065719, Note: Supplied as a 10mg/ml solution in ethanol | 1mg 5mg 10mg |
| | Application(s): Omega-3- fatty acid, with immunomodulatory activity | |
| | cis,cis,cis-5,8,11-Eicosatrienoic acid , see cis-5,8,11-Eicosatrienoic acid, J63870, p. 204 | |
| J60414 | 5,8,11,-Eicosatriynoic acid [ETI] [13488-22-7], C ₂₀ H ₂₈ O ₂ , F.W. 300.40, Solid, m.p. 68-69°, MDL MFCD00077343 | 1mg |
| | Application(s): Immunomodulatory and anti-inflammatory activity; a lipoxigenase inhibitor | |


| Stock # | Description | Size |
|---------|---|----------------------|
| A14832 | Elaidic acid, 98% [<i>trans</i> -9-Octadecenoic acid, <i>trans</i> -Oleic acid] [112-79-8], C ₁₈ H ₃₄ O ₂ , F.W. 282.47, m.p. 41-45°, b.p. 288°/100mm, i.p. >110°(230°F), Merck 14,3533, EINECS 204-006-6, RTECS JX6125000, BRN 1726543, MDL MFCD00063954 | 1g |
| | | 5g |
| | | 25g |
| | ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| |  | |
| J64441 | Elastase Inhibitor I ▲ ▲ [Boc-AAA-NHO-Bz, PPE Inhibitor] C ₂₁ H ₃₀ N ₄ O ₇ , F.W. 450.50, Solid | 1mg |
| J65641 | Elastase Inhibitor II ▲ [HNE Inhibitor, MeOSuc-AAPA-CMK] C ₂₀ H ₃₁ ClN ₄ O ₇ , F.W. 474.90, Solid | 5mg 10mg |
| J65894 | Elastase Inhibitor III ▲ [HLE Inhibitor, MeOSuc-AAPV-CMK] C ₂₃ H ₃₅ ClN ₅ O ₇ , F.W. 503.00, Solid | 5mg 10mg |
| J61753 | Elastase, porcine pancreas aqueous suspension [E.C. 3.4.21.36, Pancreatopeptidase E] [39445-21-1], Suspension, MW 25000, Merck 14,3535, EINECS 254-453-6, RTECS TS5052000, MDL MFCD00130998, Note: Minimum 3 units per mg protein. One unit cleaves one micromole of N-succinyl-L-alanyl-L-alanyl-L-alanine-p-nitroanilide per minute at 25 degrees and pH 8.0. 2X crystallized. Supplied as an aqueous suspension. This preparation must be diluted to dissolve t | 25mg 100mg |
| | ! ↓ H: H315-H319-H334-H335, P: P265-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): A serine protease that acts on elastin. Suitable for the isolation of Type II lung cells | |
| J61874 | Elastase, porcine pancreas [E.C. 3.4.21.36, Pancreatopeptidase E] [39445-21-1], Lyophilized powder, MW 25000, Merck 14,3535, EINECS 254-453-6, RTECS TS5052000, MDL MFCD00130998, Note: Minimum 3 units per mg protein. One unit cleaves one micromole of N-succinyl-L-alanyl-L-alanyl-L-alanine-p-nitroanilide per minute at 25 degrees and pH 8.0 | 25mg 100mg 1g |
| | ! ↓ H: H334-H335-H315-H319, P: P265-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Application(s): A serine protease that acts on elastin | |
| J60093 | Elastase Substrate V [MeOSuc-AAPV-AMC, Neutrophil elastase substrate, fluorogenic] [72252-90-5], C ₃₁ H ₄₁ N ₅ O ₉ , F.W. 627.70, Powder, MDL MFCD00077135, † | 25mg |
| | Application(s): Fluorogenic substrate for quantification of human leukocyte and porcine pancreatic elastase | |
| J61120 | Elastatinal [51798-45-9], C ₂₁ H ₃₆ N ₆ O ₇ , F.W. 512.60, Powder, EINECS 257-426-7, RTECS LZ9600000, BRN 873543 | 5mg 25mg |
| | Application(s): Irreversible elastase inhibitor | |
| J60596 | Eleodoisin [pGlu-Pro-Ser-Lys-Asp-Ala-Phe-Ile-Gly-Leu-Met-NH2] [69-25-0], C ₆₄ H ₈₅ N ₁₃ O ₁₅ S, F.W. 1188.44, Powder, Merck 14,3539 | 1mg 2mg 5mg |
| | Application(s): A potent vasodilating peptide that increases vascular permeability | |
| J62110 | Eleodoisin Related Peptide [H-Lys-Phe-Ile-Gly-Leu-Met-NHO, KFIGLM] [2990-43-4], C ₆₄ H ₈₅ N ₁₃ O ₁₅ S, F.W. 706.96, Powder | 5mg |
| | Application(s): Tachykinin receptor ligand; analog of substance P | |
| A15722 | Ellagic acid hydrate, 97%, may cont. up to 12% water ▲ ▲ [4,4',5,5',6,6'-Hexahydroxydiphenic acid 2,6,2',6'-dilactone hydrate] [476-66-4], C ₁₄ H ₆ O ₈ ·xH ₂ O, F.W. 302.20(anhy), m.p. 450° dec., Merck 14,3547, EINECS 207-508-3, RTECS DJ2620000, BRN 47549, MDL MFCD00149494 | 5g 25g 100g |
| | ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Application(s): Selective, ATP-competitive inhibitor of casein kinase 2. Exhibits antitumor and anticarcinogenic activity and inhibits glutathione S-transferase | |
| J61558 | Elution buffer, pH 8.0 Liquid, Note: This buffer contains: 50mM sodium phosphate, 300mM NaCl, and 250mM imidazole at pH 8.0. | 250ml |
| | Application(s): For elution of His-tag proteins from nickel resins and columns | |
| J64074 | Embelin ▲ [Apoptosis Activator III, 2,5-Dihydroxy-3-undecyl-2,5-cyclohexadiene-1,4-dione] [550-24-3], C ₁₇ H ₂₈ O ₄ , F.W. 294.40, Solid, Merck 14,3555, EINECS 208-979-8, RTECS DK4230000, MDL MFCD00016369 | 10mg 50mg |
| | Embonic acid , see Pamoic acid, A15207, p. 311 | |
| J61600 | Emodin [518-82-1], C ₁₅ H ₁₀ O ₅ , F.W. 270.24, Powder, Merck 14,3561, EINECS 208-258-8, RTECS CB7920600, BRN 1888141, MDL MFCD00001207 | 100mg 250mg 1g |
| | ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): A protein tyrosine kinase inhibitor | |





| Stock # | Description | Size |
|---------|---|-----------------|
| J60750 | Enalapril [75847-73-3], C ₂₀ H ₂₈ N ₂ O ₅ , F.W. 376.45, Powder, m.p. 142-147°, Merck 14,3567, RTECS TW3665500 | 1g 5g |
| | Application(s): Long-acting ACE inhibitor and antihypertensive | |
| J63392 | Enalaprilat [Enalaprillic acid] [76420-72-9], C ₁₈ H ₂₈ N ₂ O ₇ , F.W. 384.42, Crystalline solid, m.p. 148-151°, Merck 14,3568, EINECS 278-459-3 | 10mg 50mg |
| | Application(s): The active metabolite of enalapril | |
| | Enalaprillic acid , see Enalaprilat, J63392, p. 206 | |
| J63932 | Enalapril maleate salt [76095-16-4], C ₂₆ H ₃₈ N ₂ O ₅ ·C ₄ H ₄ O ₄ , F.W. 492.52, Powder, m.p. 143-145°, Merck 14,3567, EINECS 278-375-7, RTECS TW3666000, MDL MFCD00133304 | 5g |
| | Application(s): Long-acting ACE inhibitor and antihypertensive | |
| | Endoproteinase-Arg-C , see Clostripain, Clostridium histolyticum, J61362, p. 166 | |
| J63462 | α-Endorphin, human [H-Tyr-Gly-Gly-Phe-Met-Thr-Ser-Glu-Lys-Ser-Gln-Thr-Pro-Leu-Val-Thr-OH, β-Lipotropin (61-76)] [59004-96-5], C ₇₇ H ₁₂₀ N ₁₆ O ₂₆ S, F.W. 1745.98, Powder, MDL MFCD00076381 | 1mg |
| | Application(s): An opioid peptide and substrate for transglutaminase | |
| J62140 | α-Endorphin, human [59004-96-5], C ₁₃₈ H ₂₅₁ N ₃₈ O ₄₆ S, F.W. 3465.06, Powder | 1mg |
| J61230 | β-Endorphin, camel [59887-17-1], C ₁₅₅ H ₂₆₀ N ₄₂ O ₄₄ S, F.W. 3438.00, Powder, MDL MFCD00151072 | 1mg |
| | Application(s): An endogenous opioid peptide neurotransmitter found in the neurons of both the central and peripheral nervous system | |
| J62374 | β-Endorphin, human [61214-51-5], C ₁₃₈ H ₂₅₁ N ₃₈ O ₄₆ S, F.W. 3465.06, Powder, MDL MFCD00076383 | 1mg |
| | Application(s): An endogenous opioid peptide neurotransmitter found in the neurons of both the central and peripheral nervous system | |
| J62875 | β-Endorphin, rat [77367-63-6], C ₁₅₇ H ₂₅₄ N ₄₂ O ₄₄ S, F.W. 3466.09, Powder, MDL MFCD00133129 | 1mg |
| | Application(s): An endogenous opioid peptide neurotransmitter found in the neurons of both the central and peripheral nervous system | |
| J64685 | [Des-Tyr1]-β-Endorphin, human [Gly-Gly-Phe-Met-Thr-Ser-Glu-Lys-Ser-Gln-Thr-Pro-Leu-Val-Thr-Leu-Phe-Lys-Asn-Ala-Ile-Ile-Lys-Asn-Ala-Tyr-Lys-Lys-Gly-Glu] C ₁₄₉ H ₂₄₂ N ₃₈ O ₄₄ S, F.W. 3301.8, Solid | 1mg |
| J60948 | Endothall [7-Oxabicyclo [2.2.1] heptane-2,3-dicarboxylic acid] [145-73-3], C ₈ H ₁₀ O ₅ , F.W. 186.20, Powder, Merck 14,3575, UN2811, EINECS 205-660-5, RTECS RN7875000  H: H301-H312-H315-H319-H335, P: P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a | 20mg 100mg |
| | Application(s): A moderately potent inhibitor of protein phosphatase 2A | |
| J64516 | Endothelial Cell Growth Supplement, bovine hypothalamus [Endothelial Mitogen, ECGS] Note: Suitable for cell culture. Supplied partially purified as an aseptically lyophilized powder. Optimum concentration for endothelial cell culture media is 25-200 micrograms/ml. This product does not contain streptomycin which may be toxic to cells. | 50mg 10x50mg |
| J63502 | Endotoxin Inhibitor [H-Lys-Thr-Lys-Cys-Lys-Phe-Leu-Lys-Lys-Cys-OH, Lys-Thr-Lys-Cys-Lys-Phe-Leu-Lys-Lys-Cys, Disulfide Bridge: Cys4-Cys10] [147396-10-9], C ₅₃ H ₈₇ N ₁₃ O ₁₂ S ₂ , F.W. 1224.60, Powder | 1mg |
| | Application(s): Useful in the prophylaxis and treatment of LPS-mediated diseases; binds to and neutralizes endotoxin from gram-negative bacteria | |
| J62862 | Endotoxin Substrate [Boc-Leu-Gly-Arg-pNA] [68223-96-1], C ₂₅ H ₄₀ N ₆ O ₇ , F.W. 564.64, Powder | 50mg |
| | Application(s): Chromogenic substrate for horseshoe crab clotting enzyme, which is used in quantitative assays of endotoxin | |
| J64291 | Ene Reductase Kit - 8 variants (ENR1 through ENR8) [EC 1.3.1.44] Lyophilized powder, Note: Contains 100mg of each variant | 1each |
| | Application(s): These enzymes perform stereoselective reduction of activated alkenes | |

| Stock # | Description | Size |
|--|---|-----------------------|
| J64706 | Ene Reductase ENR1 [EC 1.3.1.44] Lyophilized powder | 250mg 500mg 1g |
| J65356 | Ene Reductase ENR2 [EC 1.3.1.44] Lyophilized powder | 250mg 500mg 1g |
| J64993 | Ene Reductase ENR3 [EC 1.3.1.44] Lyophilized powder | 250mg 500mg 1g |
| J65028 | Ene Reductase ENR4 [EC 1.3.1.44] Lyophilized powder | 250mg 500mg 1g |
| J64840 | Ene Reductase ENR5 [EC 1.3.1.44] Lyophilized powder | 250mg 500mg 1g |
| J64848 | Ene Reductase ENR6 [EC 1.3.1.44] Lyophilized powder | 250mg 500mg 1g |
| J65955 | Ene Reductase ENR7 [EC 1.3.1.44] Lyophilized powder | 250mg 500mg 1g |
| J64249 | Ene Reductase ENR8 [EC 1.3.1.44] Lyophilized powder | 250mg 500mg 1g |
| J61408 | Leu-Enkephalin [<i>H-Tyr-Gly-Gly-Phe-Leu-OH</i> , Dynorphin A (1-5)] [81678-16-2], C ₂₈ H ₃₇ N ₅ O ₇ , F.W. 555.70, Lyophilized powder Application(s): Endogenous opioid neurotransmitter that is an agonist at mu- and delta-opioid receptors | 25mg |
| J63207 | (Ala³)-Leu-Enkephalin [<i>Tyr-Ala-Gly-Phe-Leu</i>] [60284-47-1], C ₂₈ H ₃₉ N ₅ O ₇ , F.W. 569.66, Lyophilized powder Application(s): An opioid peptide | 25mg 100mg |
| J61859 | (D-Ala³)-Leu-Enkephalin [<i>Tyr-D-Ala-Gly-Phe-Leu</i>] [64963-01-5], C ₂₈ H ₃₉ N ₅ O ₇ , F.W. 569.66, Lyophilized powder, EINECS 265-291-0, MDL MFCD00076409 Application(s): An opioid peptide | 25mg 100mg |
| J60677 | (Des-Tyr¹)-Leu-Enkephalin [<i>Gly-Gly-Phe-Leu</i>] [60254-83-3], C ₁₇ H ₂₈ N ₄ O ₅ , F.W. 392.46, Lyophilized powder Application(s): An enkephalinase inhibitor | 100mg 500mg |
| J61684 | (Des-Tyr¹)-Met-Enkephalin [<i>H-Gly-Gly-Phe-Met-OH</i>] [61370-88-5], C ₁₈ H ₂₆ N ₄ O ₅ S, F.W. 410.49, Powder Application(s): An enkephalinase inhibitor | 5mg |
| J61154 | Met-Enkephalin [<i>H-Tyr-Gly-Gly-Phe-Met-OH</i>] [58569-55-4], C ₂₇ H ₃₅ N ₅ O ₅ S, F.W. 573.67, Powder, EINECS 261-335-8 Application(s): Endogenous opioid peptide that also functions as a growth factor on many cell types at a receptor that is distinct from the neuronal opioid receptors | 25mg 50mg 125mg |
| J61912 | Enoxacin [<i>Penetrex</i> ® The Clorox Company, <i>Bactidan</i>] [74011-58-8], C ₁₉ H ₁₇ FN ₃ O ₃ , F.W. 320.32, Crystalline powder, m.p. 220-224°, Merck 14,3587, RTECS QN2800000, MDL MFCD00133308 Application(s): A quinolone antibacterial agent which acts on DNA gyrase | 1g 5g 25g |
| J60023 | Enrofloxacin [<i>1-Cyclopropyl-7-(4-ethyl-1-piperazinyl)-6-fluoro-1,4-dihydro-4-oxoquinoline-3-carboxylic acid</i>] [93106-60-6], C ₁₉ H ₂₂ FN ₃ O ₃ , F.W. 359.39, Powder, m.p. 221-226°, Merck 14,3592, RTECS VB1993650, BRN 5307824, MDL MFCD00792463 | 5g 25g 100g |
| Enzymatic Digest of Lactalbumin , see Lactalbumin hydrolysate, J63215, p. 264 | | |

| Stock # | Description | Size |
|---|---|-----------------------|
| J63115 | Enzyme storage buffer in PBS and glycerol, autoclaved Liquid, Note: This buffer contains 50% Glycerol in PBS. ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 Application(s): For frozen storage of enzymes. | 125ml 250ml |
| J63264 | Enzyme storage buffer in TBS and glycerol, autoclaved Liquid, Note: This buffer contains 50% Glycerol in TBS. ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 Application(s): For frozen storage of enzymes | 125ml 250ml |
| A17377 | Eosin B [C.I. 45400, 4,5-Dibromo-2,7-dinitrofluorescein disodium salt] [548-24-3], C ₂₀ H ₆ Br ₂ N ₂ Na ₂ O ₈ , F.W. 624.08, EINECS 208-943-1, MDL MFCD00005041, t  Application(s): A counterstain for collagen | 25g 100g |
| Eosin-Methylene Blue , see Jenner's Stain, J61077, p. 262 | | |
| J62018 | Eosinophilotactic Tetrapeptide (AGSE) [Ala-Gly-Ser-Glu] [61756-28-3], C ₁₃ H ₂₂ N ₄ O ₈ , F.W. 362.40, Powder Application(s): A chemotactic for eosinophils | 5mg |
| J61884 | Eosinophilotactic Tetrapeptide (VGDE) [H-Val-Gly-Asp-Glu-OH] [99624-52-9], C ₁₆ H ₂₆ N ₄ O ₈ , F.W. 418.40, Powder Application(s): A chemotactic for eosinophils | 250mg |
| J61494 | Eosinophilotactic Tetrapeptide (VGSE) [H-Val-Gly-Ser-Glu-OH] [61756-22-7], C ₁₅ H ₂₆ N ₄ O ₈ , F.W. 390.40, Powder Application(s): A chemotactic for eosinophils | 5mg |
| B24535 | Eosin Yellowish [Acid Red 87, C.I. 45380] [17372-87-1], C ₂₀ H ₆ Br ₂ Na ₂ O ₈ , F.W. 691.86, Merck 14,3603, Solubility: Soluble in water, fairly soluble in alcohol, insoluble in ether, EINECS 241-409-6, RTECS LM5850000, BRN 3586809, MDL MFCD00133309, t ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 Adsorption and fluorescence indicator.  Application(s): Fluorescent stain for cytoplasm and collagen | 50g 250g |
| Epiadriamycin , see Epirubicin hydrochloride, J60411, p. 209 | | |
| J61218 | (-)-Epicatechin [(-)-cis-3,3',4',5,7-Pentahydroxyflavane, Epicatechol] [490-46-0], C ₁₅ H ₁₁ O ₆ , F.W. 290.27, Crystalline powder, m.p. 240°dec, EINECS 207-710-1, RTECS KB3745000, BRN 92760, MDL MFCD00075648 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): An antioxidant and natural product from green tea | 20mg |
| J60814 | (-)-Epicatechin gallate [(-)-cis-2-(3,4-Dihydroxyphenyl)-3,4-dihydro-1(2H)-benzopyran-3,5,7-triol 3-gallate, ECG] [1257-08-5], C ₂₂ H ₁₈ O ₁₀ , F.W. 442.37, Powder, RTECS DH9030000, MDL MFCD00075936 Application(s): A natural product from green tea that induces apoptosis | 10mg 20mg |
| Epicatechol , see (-)-Epicatechin, J61218, p. 208 | | |
| A15823 | (±)-Epichlorohydrin, 99% [(±)-1-Chloro-2,3-epoxypropane] [106-89-8], C ₃ H ₅ ClO, F.W. 92.53, m.p. -57°, b.p. 115-117°, f.p. 32°(90°F), d. 1.182, n _D ²⁰ 1.4380, Merck 14,3611, Fieser 1,355 4,222 5,290, UN2023, EINECS 203-439-8, RTECS TX4900000, BRN 79785, MDL MFCD00005132, t   H:H301-H311-H331-H350-H314-H226-H317, P:P301+P310-P303+P361+P353-P305+P351+P338-P361-P405-P501a For use as an acid scavenger in bromination reactions, see: <i>J. Am. Chem. Soc.</i> , 95 , 4419 (1973). The preparation of glycidyl ethers, often carried out in two steps, via the ring-opened chlorohydrin ether and subsequent ring-closure with base, can be achieved as a single step, under phase-transfer conditions: <i>Synthesis</i> , 117 (1983). For extension to diglycidyl ethers of diols, see: <i>Synthesis</i> , 649 (1985). Reaction with primary amines provides a one-step route to 3-azetidino: <i>J. Org. Chem.</i> , 55 , 2920 (1990): | 100g 500g 2.5kg |
| Application(s): A cyclodextrin cross-linking reagent | | |
| J64012 | Epidermal Growth Factor, human, 99% [EGF, human] Note: Recombinantly expressed in E. Coli. Receptor Grade. Suitable for cell culture and radioimmunoassays. Supplied as an aseptically lyophilized powder. | 50micrograms |

| Stock # | Description | Size |
|---------|---|-----------------------------------|
| J65329 | Epidermal Growth Factor, mouse submaxillary gland, 99% [EGF, mouse] Note: Receptor Grade. Suitable for cell culture and radioimmunoassays. Supplied as an aseptically lyophilized powder. | 100micrograms 10x100micrograms |
| J64798 | Epidermal Growth Factor, rat, 99% [EGF, rat] Note: Receptor Grade. Suitable for cell culture and radioimmunoassays. Supplied as an aseptically lyophilized powder. | 10micrograms |
| J64705 | Epidermal Growth Factor Receptor Peptide (985-996) [EGFR Peptide (985-996), Asp-Val-Val-Asp-Ala-Asp-Glu-Tyr-Leu-Ile-Pro-Gln] C ₆₁ H ₉₃ N ₁₃ O ₂₃ , F.W. 1376.46, Solid | 1mg |
| | Epidosin , see Valethamate bromide, 99%, J62622, p. 390 | |
| J61630 | (-)-Epigallocatechin [970-74-1], C ₁₅ H ₁₄ O ₇ , F.W. 306.27, Powder, RTECS KB100000, MDL MFCD00075939 Application(s): A natural product from green tea that induces apoptosis | 10mg |
| J61745 | (-)-Epigallocatechin gallate [EGCG, 3-O-gallate] [989-51-5], C ₂₂ H ₁₆ O ₁₁ , F.W. 458.40, Powder, m.p. 216-218°, Merck 14,3526, RTECS KB520000, MDL MFCD00075940 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5mg 10mg 50mg |
| | Application(s): An antioxidant that acts as an anti-promoter of carcinogenesis, inhibits angiogenesis and induces apoptosis | |
| | DL-Epinephrine , see DL-Adrenaline, J63005, p. 80 L-Epinephrine , see L-Adrenaline, L04911, p. 80 Epinine hydrochloride , see N-Methyldopamine hydrochloride, 98+%, J60306, p. 287 | |
| J60411 | Epirubicin hydrochloride [Epiadriamycin] [56390-09-1], C ₂₇ H ₂₉ NO ₁₁ ·HCl, F.W. 579.98, Solid, m.p. 185°, Merck 14,3623, EINECS 260-145-2, RTECS QI9295750 ! ↓ H:H302-H361, P:P281-P264-P301+P312-P308+P313-P405-P501 | 10mg 100mg |
| | Application(s): Cell-permeable anthracycline anti-tumor antibiotic | |
| | trans-Epoxy succinyl-leucylamido- [4-guanidino]butane , see E-64, J62933, p. 203 | |
| J61538 | EPPS, 0.2M buffer soln., pH 7.0 [HEPPS] [16052-06-5], Liquid, † | 100ml 250ml |
| J60511 | EPPS, 0.2M buffer soln., pH 7.5 [HEPPS] [16052-06-5], Liquid, † | 100ml 250ml |
| J61296 | EPPS, 0.2M buffer soln., pH 8.0 [HEPPS] [16052-06-5], Liquid, † | 100ml 250ml |
| J61476 | EPPS, 0.2M buffer soln., pH 8.5 [HEPPS] [16052-06-5], Liquid, † | 100ml 250ml |
| | Epsom salt , see Magnesium sulfate heptahydrate, Cell Culture Grade, J61839, p. 275 | |
| J61383 | (R,S)-Equol [4',7'-Isoflavandiol] [94105-90-5], C ₁₆ H ₁₄ O ₃ , F.W. 242.27, Crystalline powder, m.p. 151-153°, Merck 14,3644, BRN 87752, MDL MFCD00016662 Application(s): Urinary metabolite of daidzein, produced by humans and horses | 100mg 500mg |
| J61612 | Erbstatin analog [Methyl 2,5-dihydroxycinnamate] [63177-57-1], C ₁₀ H ₁₀ O ₄ , F.W. 194.19, Powder, MDL MFCD00132932 ☠ H:H301-H311-H330-H315-H319-H335, P:P301+P310-P304+P340-P305+P351+P338-P320-P330-P361-P405-P501 | 1mg 5mg 10mg |
| | Application(s): An inhibitor of the EGF receptor associated tyrosine kinase | |
| | Ergocalciferol , see Calciferol, J61610, p. 142 | |
| B23840 | Ergosterol hydrate, 96% (dry wt.), cont. up to ca 6% water [Provitamin D ₂] [57-87-4], C ₂₈ H ₄₄ O·xH ₂ O, F.W. 396.65(anhy), m.p. 154-160°, Merck 14,3659, UN2811, EINECS 200-352-7, MDL MFCD00003623 ☠ H:H300, P:P264-P270-P301+P310-P321-P405-P501a | 5g 25g |
| | Application(s): A membrane lipid found almost exclusively in fungi. It is used as an indicator of living fungal biomass | |










| Stock # | Description | Size |
|---------|---|--------------|
| J63396 | Eriochrome® Blue Black B [C.I. 14640, Mordant Black 3] [3564-14-5], C ₂₈ H ₁₁ N ₃ O ₅ S, F.W. 416.39, Powder, EINECS 222-639-6, RTECS QK2195000, MDL MFCD00003934, Note: Eriochrome is a registered trademark of Ciba Specialty Chemicals Corp., † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 100g |
| | | 500g |
| J61780 | Erioglaucine sodium salt [C.I. 42090, Acid Blue 9] [3844-45-9], C ₂₃ H ₂₂ N ₂ Na ₂ O ₆ S ₃ , F.W. 792.86, Powder, m.p. 283°, Merck 14,1373, EINECS 223-339-8, RTECS BQ4725000, MDL MFCD00012141, Note: Dye content: approx 60%, † | 5g |
| | | 25g |
| J61633 | Erlotinib hydrochloride [183319-69-9], C ₂₂ H ₂₃ N ₃ O ₄ ·HCl, F.W. 429.90, Powder, Merck 14,3672, MDL MFCD07781272 Application(s): A selective inhibitor for EGFR tyrosine kinases | 1g |
| | | 2g |
| | | 5g |
| | Erythorbic acid , see D-(-)-Isoascorbic acid, 36366, p. 260 | |
| J60146 | Erythrina Christagalli Agglutinin (ECA) Powder, MDL MFCD00163567 Application(s): Naturally occurring lectin with affinity for D-galactose and D-galactosides | 10mg |
| A15813 | meso-Erythritol, 99% [149-32-6], C ₄ H ₈ O ₄ , F.W. 122.12, m.p. 119-124°, b.p. 329-331°, Merck 14,3675, EINECS 205-737-3, RTECS KF2000000, BRN 1719753, MDL MFCD00004710, † | 25g |
| | | 100g |
| |  | |
| J62279 | Erythromycin, Cell Culture Grade [114-07-8], C ₂₇ H ₄₃ NO ₁₃ , F.W. 733.93, Crystalline powder, Merck 14,3681, EINECS 204-040-1, RTECS KF4375000, BRN 75279, MDL MFCD00084654 Application(s): Macrolide antibiotic that inhibits bacterial protein synthesis | 10g |
| | | 25g |
| B21093 | D-Erythrose, syrup, ca 70% w/v, >75% dry wt. basis ■ [583-50-6], C ₄ H ₈ O ₄ , F.W. 120.10, n _D ²⁰ 1.4980, [α] _D ²⁰ -33° (c=2 in water, 72H), Merck 14,3690, EINECS 209-505-2, BRN 1721698, MDL MFCD00006970 | 250mg 1g |
| |  | |
| A14180 | Erythrosin B ▲ ■ [C.I. 45430, Tetraiodofluorescein sodium salt] [568-63-8], C ₂₀ H ₆ I ₄ Na ₂ O ₇ , F.W. 879.87, EINECS 240-046-0, RTECS LM5950000, MDL MFCD00144257, † ! H:H302, P:P264-P270-P301+P312-P330-P501a Application(s): Acid Red 51 | 25g |
| | | 100g 500g |
| |  | |
| J62619 | Erythrosin B, spirit soluble [C.I. 45430:2, Solvent Red 140] [15905-32-5], C ₂₀ H ₆ I ₄ O ₇ , F.W. 835.89, Powder, EINECS 240-046-0, RTECS LM5950000, MDL MFCD00005044, † | 5g |
| | | 25g |
| | | 100g |
| | Esculetin , see 6,7-Dihydroxycoumarin, A15393, p. 192 | |
| J63114 | Esculin sesquihydrate [6,7-Dihydroxycoumarin-6-glucoside] [66778-17-4], C ₁₈ H ₁₆ O ₉ ·1.5H ₂ O, F.W. 367.31 (340.29anhy), Powder, m.p. 202-210°, Merck 14,3698, EINECS 208-517-5, RTECS DJ3085000, MDL MFCD00149492, † | 5g |
| | | 25g 100g |
| | Application(s): A naturally occurring antioxidant | |
| A11624 | Esculin sesquihydrate, 97% [6,7-Dihydroxycoumarin 6-glucoside sesquihydrate] [66778-17-4], C ₁₈ H ₁₆ O ₉ ·1.5H ₂ O, F.W. 367.31 (340.28anhy), m.p. 203-205°, [α] _D ²⁰ -41° (c=5 in pyridine), Merck 14,3698, EINECS 208-517-5, BRN 95387, MDL MFCD00149492, † Ultraviolet absorbent. Reversible inhibitor of phenylalanine hydroxylase. | 5g |
| | | 25g 100g |
| |  | |
| | Application(s): Inhibits chemically induced carcinogenesis in mouse skin and kidney | |
| J61477 | Eserine ▲ △ [Physostigmine] [57-47-6], C ₁₀ H ₁₅ N ₃ O ₂ , F.W. 275.35, Powder, m.p. 102-104°, Merck 14,7384, UN1544, EINECS 200-332-8, RTECS TJ2100000, BRN 91230, MDL MFCD00151090, † ☠ H:H300-H330, P:P301+P310-P304+P340-P320-P330-P405-P501a Application(s): Inhibitor of acetylcholinesterase that crosses the blood-brain barrier | 100mg |
| J64957 | Esterase Kit - 30 variants (E1 through E30) Lyophilized powder, Note: Contains 100mg of each variant Application(s): Enzymes perform enantioselective hydrolysis on esters of primary, secondary and tertiary alcohols. Useful in the resolution of racemic mixtures of alcohols or carboxylic acids | 1each |

| Stock # | Description | Size |
|---------------|---|-------------------------------|
| J65256 | Esterase Kit - 50 variants (E1 through E50) Lyophilized powder, Note: Contains 100mg of each variant | 1each |
| | Application(s): Enzymes perform enantioselective hydrolysis on esters of primary, secondary and tertiary alcohols. Useful in the resolution of racemic mixtures of alcohols or carboxylic acids | |
| J64051 | Esterase E1 Lyophilized powder | 250mg 500mg 1g |
| J64600 | Esterase E2 Lyophilized powder | 250mg 500mg 1g |
| J64099 | Esterase E3 Lyophilized powder | 250mg 500mg 1g |
| J64204 | Esterase E4 Lyophilized powder | 250mg 500mg 1g |
| J64799 | Esterase E5 Lyophilized powder | 250mg 500mg 1g |
| J65545 | Esterase E6 Lyophilized powder | 250mg 500mg 1g |
| J64561 | Esterase E7 Lyophilized powder | 250mg 500mg 1g |
| J65370 | Esterase E8 Lyophilized powder | 250mg 500mg 1g |
| J65259 | Esterase E9 Lyophilized powder | 250mg 500mg 1g |
| J64621 | Esterase E10 Lyophilized powder | 250mg 500mg 1g |
| J64909 | Esterase E11 Lyophilized powder | 250mg 500mg 1g |
| J65558 | Esterase E12 Lyophilized powder | 250mg 500mg 1g |
| J64470 | Esterase E13 Lyophilized powder | 250mg 500mg 1g |
| J65303 | Esterase E14 Lyophilized powder | 250mg 500mg 1g |
| J64246 | Esterase E15 Lyophilized powder | 250mg 500mg 1g |
| J65461 | Esterase E16 Lyophilized powder | 250mg 500mg 1g |
| J64745 | Esterase E17 Lyophilized powder | 250mg 500mg 1g |
| J65471 | Esterase E18 Lyophilized powder | 250mg 500mg 1g |


| Stock # | Description | Size |
|----------------|---|----------------------|
| J65011 | Esterase E19 Lyophilized powder | 250mg 500mg 1g |
| J65827 | Esterase E20 Lyophilized powder | 250mg 500mg 1g |
| J65920 | Esterase E21 Lyophilized powder | 250mg 500mg 1g |
| J65381 | Esterase E22 Lyophilized powder | 250mg 500mg 1g |
| J65877 | Esterase E23 Lyophilized powder | 250mg 500mg 1g |
| J65574 | Esterase E24 Lyophilized powder | 250mg 500mg 1g |
| J65095 | Esterase E25 Lyophilized powder | 250mg 500mg 1g |
| J65305 | Esterase E26 Lyophilized powder | 250mg 500mg 1g |
| J64649 | Esterase E27 Lyophilized powder | 250mg 500mg 1g |
| J64423 | Esterase E28 Lyophilized powder | 250mg 500mg 1g |
| J64114 | Esterase E29 Lyophilized powder | 250mg 500mg 1g |
| J65629 | Esterase E30 Lyophilized powder | 250mg 500mg 1g |
| J65947 | Esterase E31 Lyophilized powder | 250mg 500mg 1g |
| J64648 | Esterase E32 Lyophilized powder | 250mg 500mg 1g |
| J64873 | Esterase E33 Lyophilized powder | 250mg 500mg 1g |
| J64918 | Esterase E34 Lyophilized powder | 250mg 500mg 1g |
| J65872 | Esterase E35 Lyophilized powder | 250mg 500mg 1g |
| J64294 | Esterase E36 Lyophilized powder | 250mg 500mg 1g |
| J65979 | Esterase E37 Lyophilized powder | 250mg 500mg 1g |


| Stock # | Description | Size |
|---------|---|-----------------------|
| J64625 | Esterase E38 Lyophilized powder | 250mg 500mg 1g |
| J64309 | Esterase E39 Lyophilized powder | 250mg 500mg 1g |
| J65606 | Esterase E40 Lyophilized powder | 250mg 500mg 1g |
| J64195 | Esterase E41 Lyophilized powder | 250mg 500mg 1g |
| J65327 | Esterase E42 Lyophilized powder | 250mg 500mg 1g |
| J65708 | Esterase E43 Lyophilized powder | 250mg 500mg 1g |
| J65401 | Esterase E44 Lyophilized powder | 250mg 500mg 1g |
| J65797 | Esterase E45 Lyophilized powder | 250mg 500mg 1g |
| J64480 | Esterase E46 Lyophilized powder | 250mg 500mg 1g |
| J65296 | Esterase E47 Lyophilized powder | 250mg 500mg 1g |
| J64021 | Esterase E48 Lyophilized powder | 250mg 500mg 1g |
| J65278 | Esterase E49 Lyophilized powder | 250mg 500mg 1g |
| J64298 | Esterase E50 Lyophilized powder | 250mg 500mg 1g |
| J63684 | Ethacrynic acid [[2,3-Dichloro-4-[2-methylenebutyryl]phenoxy]acetic acid] [58-54-8], C ₁₃ H ₁₂ Cl ₂ O ₄ , F.W. 303.14, Crystalline powder, Merck 14,3717, EINECS 200-384-1, RTECS AG6600000, MDL MFCD00056693 ! H: H302-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): Diuretic that acts by inhibiting sodium-potassium-chloride cotransport | 1g |
| J60695 | Ethambutol dihydrochloride [2,2'-(1,2-Ethanediyldiimino)bis-1-butanol dihydrochloride, 1,2-Dimercaptoethane] [1070-11-7], C ₁₀ H ₂₀ N ₂ O ₂ , F.W. 204.31, Powder, Merck 14,3720, EINECS 213-970-7, RTECS EL3854000, MDL MFCD00216025 ⚠ H: H360, P: P281-P201-P202-P308+P313-P405-P501 Application(s): An antibacterial agent | 25g |
| | 1,2-Ethanediamine , see Ethylenediamine, A12132, p. 215 1,2-Ethandiol , see Ethylene glycol, A11591, p. 216 | |
| A11697 | Ethanolamine, 98+% Δ \blacksquare [2-Aminoethanol, 2-Hydroxyethylamine] [141-43-5], HOCH ₂ CH ₂ NH ₂ , F.W. 61.08, m.p. 10°, b.p. 169-170°, f.p. 93°(199°F), d. 1.012, n _D ²⁰ 1.4540, Merck 14,3727, Fieser 1,357 2,189 4,222 16,162, UN2491, EINECS 205-483-3, RTECS KJ5775000, BRN 505944, MDL MFCD00008183, † ⚠ H: H314-H302-H312-H332, P: P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a Reagent for the demethylation of quaternary ammonium salts formed by the exhaustive methylation of aromatic amines, providing a route to N,N-dimethyl arylamines: <i>Org. Synth. Coll.</i> , 5, 1018 (1973). Base for the cleavage of Fmoc protecting groups: <i>J. Am. Chem. Soc.</i> , 92, 5748 (1970); <i>J. Org. Chem.</i> , 37, 3404 (1972). | 250g 500g 2.5kg |





| Stock # | Description | Size |
|---------------|--|---|
| | Ethanoyl chloride , see Acetyl chloride, 43262, p. 71 | |
| J62029 | Ethidium bromide soln., 0.625mg/ml [1239-45-8], C ₂₁ H ₂₆ BrN ₃ , F.W. 394.31, Dropper bottle, Merck 14,4731, UN2810, EINECS 214-984-6, RTECS SF7950000, Note: 0.625 mg/ml ethidium bromide solution H: H341, P: P281-P201-P202-P308+P313-P405-P501a Application(s): For visualization of DNA in gel electrophoresis | 5ml |
| J62282 | Ethidium bromide soln., 10mg/ml [1239-45-8], C ₂₁ H ₂₆ BrN ₃ , F.W. 394.32, Dropper bottle, Merck 14,4731, UN2810, EINECS 214-984-6, RTECS SF7950000, MDL MFCD00011724 H: H341, P: P281-P201-P202-P308+P313-P405-P501a Application(s): For visualization of DNA in gel electrophoresis | 10ml |
| L07482 | Ethidium bromide, 98% (dry wt.) [3,8-Diamino-5-ethyl-6-phenylphenanthridinium bromide, Homidium bromide] [1239-45-8], C ₂₁ H ₂₆ BrN ₃ , F.W. 394.32, m.p. ca 261° dec., Merck 14,4731, UN2811, EINECS 214-984-6, RTECS SF7950000, BRN 3642536, MDL MFCD00011724, Note: Special handling precautions required. View MSDS prior to purchase. MSDS are available online at www.alfa.com H: H330-H341-H302, P: P260-P304+P340-P320-P330-P405-P501a Intercalation agent for DNA. Reviews: J.-B. Le Pecq, <i>Methods of Biochemical Analysis</i> , vol. 20, Wiley, N.Y. (1971), p41; M. Waring, <i>Antibiotics</i> , vol. 3, Springer-Verlag (1975), p141. Application(s): For DNA isolation and visualization | 1g 5g |
| |  | |
| J62931 | Ethidium bromide de-staining bags | 25each |
| J63580 | Ethisterone, 98% [Lutocyclin, 17 α -Ethinyltestosterone] [434-03-7], C ₂₇ H ₃₈ O ₂ , F.W. 312.45, Powder, m.p. 263-269°, Merck 14,3741, EINECS 207-096-5, RTECS TU5570250, BRN 1889895, MDL MFCD00003656 H: H351, P: P281-P201-P202-P308+P313-P405-P501 Application(s): A progestogen that counteracts the estrogenic proliferative effect on the endometrium | 5g 25g |
| L09327 | N(α)-Ethoxycarbonyl-L-asparagine, 97% [N(alpha)-Carboethoxy-L-asparagine, N(alpha)-Carboethoxy-L-asparagine] [16639-91-1], C ₁₁ H ₁₂ N ₂ O ₅ , F.W. 204.18, m.p. ca 166° dec., BRN 1712104, MDL MFCD00082761 | 1g 5g |
| |  | |
| A16100 | 2-Ethoxyethanol, 99% [Cellosolve, Ethylene glycol monoethyl ether] [110-80-5], CH ₃ CH ₂ OCH ₂ CH ₂ OH, F.W. 90.12, m.p. -90°, b.p. 134-135°, f.p. 44°(111°F), d. 0.931, n _D ²⁰ 1.4085, Merck 14,3750, UN1171, EINECS 203-804-1, RTECS KK8050000, BRN 1098271, MDL MFCD00002869, † H: H360FD-H226-H302-H312-H332, P: P210-P241-P303+P313-P302+P352-P405-P501a Application(s): A widely used solvent for nitrocelluloses and dyes | 500ml 2.5L |
| | 2-(2-Ethoxyethoxy)ethanol , see Diethylene glycol monoethyl ether, A14670, p. 189 2-(2-Ethoxyethoxy)ethyl acetate , see Diethylene glycol monoethyl ether acetate, L13446, p. 189 2-Ethoxyethyl ether , see Diethylene glycol diethyl ether, 43464, p. 189 7-Ethoxy-3H-phenoxazin-3-one , see 7-Ethoxyresorufin, J62987, p. 214 | |
| J62987 | 7-Ethoxyresorufin [Resorufin ethyl ether, 7-Ethoxy-3H-phenoxazin-3-one] [5725-91-7], C ₁₄ H ₁₁ NO ₃ , F.W. 241.24, Powder, m.p. 237-240°, BRN 225973, MDL MFCD00037661 Application(s): Fluorimetric substrate for detection of cytochrome P450 linked enzymes | 5mg |
| A12754 | Ethyl 4-aminobenzoate, 98% [H-4-Abz-OEt, 4-Aminobenzoic acid ethyl ester] [94-09-7], C ₉ H ₁₁ NO ₂ , F.W. 165.19, m.p. 88-92°, b.p. 310°, f.p. >110°(230°F), Merck 14,1086, EINECS 202-303-5, RTECS DG2450000, BRN 638434, MDL MFCD00007892, † H: H319-H317, P: P261-P280-P305+P351+P338-P302+P352-P321-P501a | 250g 1kg 5kg |
| |  | |
| | (R)-(+)-α-Ethylbenzyl alcohol , see (R)-(+)-1-Phenyl-1-propanol, L05681, p. 318 (S)-(-)-α-Ethylbenzyl alcohol , see (S)-(-)-1-Phenyl-1-propanol, L06608, p. 318 (R)-(+)-α-Ethylbenzylamine , see (R)-(+)-1-Phenylpropylamine, L16319, p. 318 (S)-(-)-α-Ethylbenzylamine , see (S)-(-)-1-Phenylpropylamine, L16320, p. 318 | |
| J60862 | Ethyl (R)-4-bromo-3-hydroxybutyrate [(R)-4-Bromo-3-hydroxybutyric acid ethyl ester] [95310-48-8], C ₈ H ₁₁ BrO ₃ , F.W. 211.06, Liquid Application(s): For synthesis of optically active products | Call |
| J62782 | Ethyl (S)-4-bromo-3-hydroxybutyrate [(S)-4-Bromo-3-hydroxybutyric acid ethyl ester] [95537-36-3], C ₈ H ₁₁ BrO ₃ , F.W. 211.06, Liquid Application(s): For synthesis of optically active products | 1g |

| Stock # | Description | Size |
|---------------|--|---|
| J60405 | 5'-N-Ethylcarboxamidoadenosine [NECA] [35920-39-9], C ₁₀ H ₁₆ N ₆ O ₄ , F.W. 308.29, Powder, m.p. 229-231°, UN2811, RTECS VJ2232000, MDL MFCD00069195  | 10mg 50mg |
| | Application(s): Potent adenosine receptor agonist with some affinity at A1 and A2 receptors | |
| H27621 | Ethyl cellulose [9004-57-3], d. 1.14, n _D ²⁰ 1.47, RTECS FJ5950500, MDL MFCD00131037, † | 250mg |
| | Ethyl 2-(4-chlorophenoxy)isobutyrate , see Clofibrate, 95+%, J60342, p. 165 Ethyl digol , see Diethylene glycol monoethyl ether, A14670, p. 189 1-Ethyl-1,4-dihydro-7-methyl-4-oxo-1,8-naphthyridine-3-carboxylic acid , see Nalidixic acid, B25096, p. 297 N-Ethyl-N'-(3-dimethylaminopropyl)carbodiimide hydrochloride , see 1-(3-Dimethylaminopropyl)-3-ethylcarbodiimide hydrochloride, A10807, p. 196 Ethylenebis(oxyethylenitrilo)tetraacetic acid , see Ethylene glycol-O,O'-bis(2-aminoethyl)-N,N,N',N'-tetraacetic acid, A16086, p. 216 Ethylene chloride , see 1,2-Dichloroethane, 39121, p. 185 | |
| A12132 | Ethylenediamine, 99%  [1,2-Diaminoethane, 1,2-Ethanediamine] [107-15-3], H ₂ NCH ₂ CH ₂ NH ₂ , F.W. 60.10, m.p. 8-11°, b.p. 117-118°, f.p. 38°(100°F), d. 0.899, n _D ²⁰ 1.4565, Merck 14,3795, Fieser 1,372 4,231 13,157, Solubility: Soluble in water, alcohol. Slightly soluble in ether, UN1604, EINECS 203-468-6, RTECS KH8575000, BRN 605263, MDL MFCD00008204, †  The Li derivative in excess amine is a strong base for the rearrangement of primary allylic alcohols to the isomeric aldehydes in high yield: <i>J. Chem. Soc., Chem. Commun.</i> , 812 (1985). At high temperatures, reduces nitroarenes to azo-compounds. Reaction does not occur for nitro-compounds with o-substituents or p-amino-substituents: <i>J. Org. Chem.</i> , 49, 1215 (1984). The ethylenediamine complex of Cr ²⁺ reduces aryl bromides to the hydrocarbons. For an example, see: <i>Org. Synth. Coll.</i> , 6, 821 (1988). | 100ml 500ml 2.5L 10L |
| | Application(s): Strongly basic amine useful as a building block in chemical synthesis | |
| J63570 | Ethylenediamine-N,N'-diacetic acid [N,N'-Ethylenediglycine, EDDA] [5657-17-0], HOOCCH ₂ NHCH ₂ CH ₂ NHCH ₂ COOH, F.W. 176.17, Powder, m.p. 224°, EINECS 227-105-6, BRN 1778355, MDL MFCD00004281, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 5g 25g |
| | Application(s): Acts as a chelating agent | |
| J62786 | Ethylenediaminetetraacetic acid, 0.5M aq. soln, pH 8.0 [EDTA] [60-00-4], (HO ₂ CCH ₂) ₂ NCH ₂ CH ₂ N(CH ₂ CO ₂ H) ₂ , F.W. 292.24, Liquid, † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 250ml 500ml |
| J60292 | Ethylenediaminetetraacetic acid, 0.5M aq. soln., pH 8.0, autoclaved [EDTA] [60-00-4], (HO ₂ CCH ₂) ₂ NCH ₂ CH ₂ N(CH ₂ CO ₂ H) ₂ , F.W. 292.24, Liquid, †  | 250ml 500ml |
| A10713 | Ethylenediaminetetraacetic acid, 99% [Edetic acid, EDTA] [60-00-4], (HO ₂ CCH ₂) ₂ NCH ₂ CH ₂ N(CH ₂ CO ₂ H) ₂ , F.W. 292.24, m.p. ca 245° dec., Merck 14,3517, Fieser 1,373, EINECS 200-449-4, RTECS AH4025000, BRN 1716295, MDL MFCD00003541, † ! H:H319, P:P305+P351+P338 Widely-used complexing agent for many cations. | 500g 1kg 5kg |
| 11931 | Ethylenediaminetetraacetic acid, ACS, 99.4+% [Edetic acid, EDTA] [60-00-4], (HO ₂ CCH ₂) ₂ NCH ₂ CH ₂ N(CH ₂ CO ₂ H) ₂ , F.W. 292.24, Powder, m.p. ca 245° dec., Merck 14,3517, Fieser 1,373, EINECS 200-449-4, RTECS AH4025000, BRN 1716295, MDL MFCD00003541, † Maximum level of impurities: Insoluble in dilute ammonium hydroxide 0.005%, Residue after ignition 0.2%, [(HOCOCH ₂) ₂ N] 0.1%, Ca 0.001%, Heavy Metals (as Pb) 0.001%, Fe 0.005%, Mg 5ppm ! H:H319, P:P305+P351+P338 | 100g 500g 2.5kg |
| | Application(s): Chelating agent | |
| J65585 | Ethylenediaminetetraacetic acid, Electrophoresis Grade, 99.4+% [Edetic acid, EDTA] [60-00-4], C ₁₀ H ₁₆ N ₂ O ₈ , F.W. 292.24, Powder, m.p. ca 245° dec., Merck 14,3517, EINECS 200-449-4, RTECS AH4025000, BRN 1716295, MDL MFCD00003541, † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 100g 500g 2.5kg |
| J62948 | Ethylenediaminetetraacetic acid, Cell Culture Reagent [EDTA] [60-00-4], C ₁₀ H ₁₆ N ₂ O ₈ , F.W. 292.24, Powder, Merck 14,3517, EINECS 200-449-4, RTECS AH4025000, BRN 1716295, MDL MFCD00003541, † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 500g 1kg |


| Stock # | Description | Size |
|--|--|---------------|
| 33312 | Ethylenediaminetetraacetic acid disodium salt dihydrate, ACS, 99.0-101.0% [EDTA disodium salt dihydrate] [6381-92-6], (NaO ₂ CCH ₂) ₂ NCH ₂ CH ₂ N(CH ₂ CO ₂ H) ₂ ·2H ₂ O, F.W. 372.24 (336.22anhy), Powder, m.p. 248° dec., Fieser 1,373, EINECS 205-358-3, RTECS AH4375000, BRN 3900609, MDL MFCD00150037, † Maximum level of impurities: Insoluble matter 0.005%, pH of a 5% solution 4.0-6.0 at 25°, [(HOCOCH ₂) ₃ N] 0.1%, Heavy Metals (as Pb) 0.005%, Fe 0.01% | 100g |
| | | 500g |
| A17385 | Ethylenediaminetetraacetic acid tetrasodium salt hydrate, 98% [EDTA tetrasodium salt hydrate] [194491-31-1], C ₁₀ H ₁₂ N ₂ Na ₄ O ₈ ·xH ₂ O, F.W. 380.17(anhy), m.p. >300°, EINECS 200-573-9, RTECS AH5075000, BRN 3828865, MDL MFCD00150025, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Complexing agent for many cations. | 250g |
| | | 1kg |
| | | 5kg |
| H56165 | Ethylenediaminetetraacetic acid trisodium salt hydrate, 99% [EDTA trisodium salt hydrate] [85715-60-2], C ₁₀ H ₁₃ N ₂ Na ₃ O ₈ ·xH ₂ O, F.W. 358.19, m.p. >300°, EINECS 205-758-8, MDL MFCD00149675 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250g |
| | | 500g |
| | | 5kg |
| Ethylene dibromide , see 1,2-Dibromoethane, A12766, p. 184 | | |
| N,N'-Ethylenediglycine , see Ethylenediamine-N,N'-diacetic acid, J63570, p. 215 | | |
| A11591 | Ethylene glycol, 99% ■ [1,2-Dihydroxyethane, 1,2-Ethanediol] [107-21-1], HOCH ₂ CH ₂ OH, F.W. 62.07, m.p. -13°, b.p. 196-198°, f.p. 119°(246°F), d. 1.113, n _D ²⁰ 1.4310, Merck 14,3798, Fieser 1,375 5,296 9,217 15,156 18,157, EINECS 203-473-3, RTECS KW2975000, BRN 505945, MDL MFCD00002885, † ! H:H302, P:P264-P270-P301+P312-P330-P501a For examples of use in acetal (1,3-dioxolane) formation, catalyzed by tosic acid with azeotropic water removal, see: <i>Org. Synth. Coll.</i> , 6 , 567 (1988); 7 , 241, 271 (1990). A mild dehydrating agent, e.g. triethyl orthoformate may be used as an alternative: <i>J. Org. Chem.</i> , 48 , 2122 (1983). PPTS (Pyridinium p-toluenesulfonate, A15708) has been recommended as a catalyst for the formation and cleavage of ethylene acetals, being less likely to cause acid-catalyzed rearrangements than tosic acid itself: <i>Synthesis</i> , 724 (1979). For acetalization of α,β-enals, tartaric acid in the presence of anhydrous MgSO ₄ gives good results: <i>J. Org. Chem.</i> , 60 , 2931 (1995). Review of the preparation of acetals: <i>Synthesis</i> , 501 (1981). See also 2,2-Dimethyl-1,3-dioxolane, L00482 . In combination with TMS chloride, α,β-enones are converted to β-chloro acetals in one step: <i>Tetrahedron Lett.</i> , 25 , 3805 (1984). | 250g |
| | | 500g |
| | | 2.5kg |
| | | 10kg |
| J60767 | Ethylene glycol-O,O'-bis(2-aminoethyl)-N,N,N',N'-tetraacetic acid, 0.5M aq. soln., pH 8.0 [EGTA] [67-42-5], C ₁₄ H ₂₄ N ₂ O ₁₀ , F.W. 380.35, Liquid, † | 50ml 100ml |
| J61721 | Ethylene glycol-O,O'-bis(2-aminoethyl)-N,N,N',N'-tetraacetic acid, 0.5M aq. soln., pH 8.0, autoclaved [EGTA] [67-42-5], C ₁₄ H ₂₄ N ₂ O ₁₀ , F.W. 380.35, Liquid, † | 50ml 100ml |
| A16086 | Ethylene glycol-O,O'-bis(2-aminoethyl)-N,N,N',N'-tetraacetic acid, 97% [EGTA, Ethylenebis(oxyethylenetriolo)tetraacetic acid] [67-42-5], C ₁₄ H ₂₄ N ₂ O ₁₀ , F.W. 380.35, m.p. ca 242° dec., Merck 14,3529, EINECS 200-651-2, RTECS AH3760000, BRN 1717370, MDL MFCD00004291, † Reagent for complexometry. | 10g |
| | | 50g |
| | | 250g |
| Ethylene glycol methyl ether , see 2-Ethoxyethanol, A16100, p. 214 | | |
| Ethylene glycol monoethyl ether , see 2-Ethoxyethanol, A16100, p. 214 | | |
| 1-Ethyl-2-[(E)-3-(1-ethylnaphtho[1,2-d]thiazolin-2-ylidene)-2-methylpropenyl]naphtho[1,2-d]thiazolium bromide , see Stains-All, H32127, p. 352 | | |
| Ethyl glycol , see 2-Ethoxyethanol, A16100, p. 214 | | |
| (±)-N-[4-(4-[Ethyl(n-heptyl)amino]-1-hydroxybutyl)phenyl]methanesulfonamide hemifumarate salt , see Ibutilide hemifumarate salt, H56358, p. 253 | | |
| A13172 | Ethyl 4-hydroxybenzoate, 99% [Ethylparaben, 4-Hydroxybenzoic acid ethyl ester] [120-47-8], C ₉ H ₁₀ O ₃ , F.W. 166.18, m.p. 116-118°, b.p. 297-298° dec., Merck 14,3837, EINECS 204-399-4, RTECS DH2190000, BRN 1101972, MDL MFCD00002353, † H:H303, P:P312 | 250g |
| | | 1kg 5kg |
| J63400 | Ethyl (R)-(-)-3-hydroxybutyrate [(R)-(-)-3-Hydroxybutyric acid ethyl ester] [24915-95-5], C ₈ H ₁₂ O ₅ , F.W. 132.16, Liquid, MDL MFCD00075386 Application(s): For synthesis of optically active products | 1g 5g |
| | | |
| J63184 | Ethyl (S)-(-)-3-hydroxybutyrate [(S)-(-)-3-Hydroxybutyric acid ethyl ester] [56816-01-4], C ₈ H ₁₂ O ₅ , F.W. 132.16, Liquid, EINECS 260-393-1 H:H227, P:P210-P280-P370+P378a-P403+P235-P501a Application(s): For synthesis of optically active products | 1g 5g |
| | | |



| Stock # | Description | Size |
|---------|--|--------------------|
| L00355 | N-Ethylmaleimide, 98+% [1-Ethyl-1H-pyrrole-2,5-dione, NEM] [128-53-0], C ₆ H ₇ NO ₂ , F.W. 125.13, m.p. 43-46°, b.p. 209-211°, f.p. 73°(163°F), Merck 14,3822, UN2928, EINECS 204-892-4, RTECS UX9625000, BRN 112448, MDL MFCD00005509, †  H: H300-H311-H314-H317, P: P280-P305+P351+P338-P302+P352-P309-P310 Reactive dienophile and dipolarophile. Reagent for modification of sulfhydryl groups of cysteine residues in proteins: <i>Methods Enzymol.</i> , 25 , 449 (1972); <i>Eur. J. Biochem.</i> , 145 , 245 (1984). | 10g 50g |
| | Application(s): Cysteine alkylating agent | |
| | 2-(Ethylmercuriomercapto)benzoic acid sodium salt , see Thimerosal, J61799, p. 366 | |
| L08218 | Ethyl 3-methyl-2-thionoimidazoline-1-carboxylate, 97% ▲ [Carbimazole, 3-Methyl-2-thionoimidazoline-1-carboxylic acid ethyl ester] [22232-54-8], C ₇ H ₁₀ N ₂ O ₂ S, F.W. 186.24, m.p. 122-126°, Merck 14,1798, EINECS 244-854-4, RTECS NJ2441000, BRN 144339, MDL MFCD00027421 ! H: H302-H319-H317, P: P261-P280-P305+P351+P338-P302+P352-P321-P501a | 5g 25g 100g |
| | Application(s): A thyroid inhibitor | |
| J62863 | Ethyl Orange sodium salt [4-(4-Diethylaminophenylazo)benzene-sulfonic acid sodium salt] [62758-12-7], (C ₁₆ H ₁₅) ₂ NC ₆ H ₄ N=NC ₆ H ₄ SO ₃ Na, F.W. 355.39, Powder, EINECS 263-716-4, BRN 3821641, MDL MFCD00007503, † ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | 100g 500g |
| | Application(s): Indicator: pH 3.0 (red) to pH 4.5 (yellow) | |
| | Ethylparaben , see Ethyl 4-hydroxybenzoate, A13172, p. 216 | |
| A14156 | Ethyl phenoxycetate, 99% [Phenoxyacetic acid ethyl ester] [2555-49-9], C ₈ H ₈ OCH ₂ CO ₂ CH ₂ CH ₃ , F.W. 180.20, b.p. 251-253°, f.p. >110°(230°F), d. 1.108, n _D ²⁰ 1.5055, EINECS 219-867-3, BRN 1871712, MDL MFCD00026895, † | 10g 50g 250g |
| J61826 | 2-Ethyl-5-phenylisoxazolium-3'-sulfonate [Woodward's Reagent K, NEPIS] [4156-16-5], C ₁₁ H ₁₁ NO ₃ S, F.W. 253.30, Powder, Merck 14,10050, EINECS 223-988-7 | 250mg 1g |
| | Application(s): Used to modify carboxyl groups of enzymes | |
| | N-Ethyl-2-phenyl-N-(4-pyridylmethyl)hydracrylamide , see Tropicamide, 99+%, J61132, p. 383 | |
| | 1-Ethyl-1H-pyrrole-2,5-dione , see N-Ethylmaleimide, L00355, p. 217 | |
| J63446 | Ethyl Red [4-(Diethylamino)azobenzene-2'-carboxylic Acid] [76058-33-8], C ₁₇ H ₁₉ N ₃ O ₂ , F.W. 297.36, Powder, m.p. ca 135° dec, BRN 3366056, MDL MFCD00002427 ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 25g 100g |
| | Application(s): Indicator: pH 4.5 (red) to pH 6.5 (yellow) | |
| J63951 | Ethyl Violet [C.I. 42600, Basic Violet 4] [2390-59-2], C ₁₅ H ₁₄ ClN ₃ , F.W. 492.15, Powder, EINECS 219-231-5, RTECS KH2682000, BRN 4117566, MDL MFCD00011765, Note: Dye content approx. 80%, † | 25g 100g |
| | 17a-Ethynyltestosterone , see Ethisterone, 98%, J63580, p. 214 | |
| | ETI , see 5,8,11,-Eicosatriynoic acid, J60414, p. 204 | |
| J62381 | Etidronate disodium [Etidronic acid, disodium salt] [7414-83-7], C ₈ H ₆ Na ₂ O ₇ P ₂ , F.W. 249.99, Crystalline solid, m.p. >300°, Merck 14,3863, EINECS 231-025-7, MDL MFCD00152567, † ! H: H302, P: P264-P270-P301+P312-P330-P501 | 1g |
| | Application(s): A bisphosphonate bone resorption inhibitor | |
| | Etidronic acid, disodium salt , see Etidronate disodium, J62381, p. 217 | |
| J63651 | Etoposide [33419-42-0], C ₂₃ H ₃₂ O ₁₃ , F.W. 588.56, Powder, m.p. 236-251°, Merck 14,3886, EINECS 251-509-1, RTECS KC0190000, MDL MFCD00869325 ! ⚠ H: H302-H350, P: P281-P264-P301+P312-P308+P313-P405-P501 | 25mg 100mg |
| | Application(s): Topoisomerase inhibitor and inducer of apoptosis | |
| | ETYA , see 5,8,11,14-Eicosatetraynoic acid, J61624, p. 204 | |
| | Eucalyptol , see 1,8-Cineole, A12269, p. 163 | |
| | Euflavine , see Acriflavine hydrochloride, J60048, p. 76 | |
| A14332 | Eugenol, 99% [4-Allyl-2-methoxyphenol, 4-Allylguaiacol] [97-53-0], C ₁₀ H ₁₂ O ₂ , F.W. 164.21, m.p. -10°, b.p. 252-253°, f.p. 127°(260°F), d. 1.068, n _D ²⁰ 1.5410, Merck 14,3898, EINECS 202-589-1, RTECS SJ4375000, BRN 1366759, MDL MFCD00008654, † ! H: H302-H315-H319-H317, P: P261-P280-P305+P351+P338-P302+P352-P321-P501a | 100g 500g |
| | Application(s): Internal standard in GC assays for presence of thymol in biological samples | |


| Stock # | Description | Size |
|---------------|---|---|
| A16774 | Evans Blue [C.I. 23860] [314-13-6], C ₃₃ H ₂₂ N ₂ Na ₂ O ₇ S ₂ , F.W. 960.82, Merck 14,3905, EINECS 206-242-5, MDL MFCD00004021, Note: Dye content: approx. 85%., † H.H351, P:P281-P201-P202-P308+P313-P405-P501a |  10g 50g |
| | Application(s): Direct Blue 53. Inhibits L-glutamate uptake, and AMPA and kainate receptor currents | |
| J60139 | Everolimus [159351-69-6], C ₅₃ H ₈₃ NO ₁₄ , F.W. 958.22, Powder, Merck 14,3907, MDL MFCD07785165 H.H372, P:P260-P264-P270-P314-P501 | 5mg 10mg 25mg |
| | Application(s): A rapamycin analog | |
| J62771 | Evodiamine [518-17-2], C ₁₈ H ₁₇ N ₃ O, F.W. 303.40, Solid, Merck 14,3908 | 10mg 50mg |
| | Application(s): A vanilloid receptor agonist that induces apoptosis in leukemia U937 cells | |
| J64753 | EX 527 [6-Chloro-2,3,4,9-tetrahydro-1H-carbazole-1-carboxamide] [49843-98-3], C ₁₃ H ₁₃ ClN ₂ O, F.W. 248.71, Powder, MDL MFCD03009471 ! H.H302-H319, P:P280-P264-P305+P351+P338-P301+P312-P337+P313-P501 | 50mg |
| J61478 | Experimental Allergic Encephalitogenic Peptide, human [Phe-Ser-Trp-Gly-Ala-Glu-Gly-Gln-Arg] [29705-92-8], C ₈₈ H ₆₄ N ₁₄ O ₁₄ , F.W. 1037.20, Lyophilized powder | 1mg 5mg |
| | Application(s): Active fragment of the myelin basic protein. Induces experimental allergic encephalomyelitis | |
| J61052 | Extracellular Death Factor trifluoroacetate salt [EDF, H-Asn-Asn-Trp-Asn-Asn-OH] [960129-66-2], C ₂₇ H ₃₈ N ₁₀ O ₁₀ ·C ₂ HF ₃ O ₂ , F.W. 774.66, Lyophilized powder | 5mg |
| | Application(s): Useful to study mediated bacterial cell death | |
| | Factor I , see Fibrinogen, bovine, J63276, p. 220 Factor IIa , see Thrombin, bovine plasma, J63383, p. 368 | |
| J63878 | Factor XA protease digestion buffer Liquid, Note: 20mM Tris-HCl, 50mM NaCl and 1mM calcium chloride, pH 8.0 | 250ml |
| | Application(s): For His-tag protein purification from mammalian cells | |
| | FAD-Na2 , see Flavin adenine dinucleotide disodium salt hydrate, A14495, p. 221 | |
| J63165 | Famotidine, 98+% [76824-35-6], C ₈ H ₁₅ N ₅ O ₂ S ₃ , F.W. 337.45, Powder, m.p. 166-168°, Merck 14,3930, RTECS UA2300000, MDL MFCD00079297 | 1g 5g 25g |
| | Application(s): A competitive histamine H2 receptor antagonist | |
| | Fampridine , see 4-Aminopyridine, 99+%, J61470, p. 99 | |
| A19316 | Farnesol, mixture of isomers, 96% ▲ [3,7,11-Trimethyl-2,6,10-dodecatrien-1-ol] [4602-84-0], C ₁₅ H ₂₆ O, F.W. 222.37, b.p. 159-160°/10mm, f.p. 146° (295°F), d. 0.887, n _D ²⁰ 1.4890, Merck 14,3937, EINECS 225-004-1, RTECS JR4979000, BRN 1763926, MDL MFCD00002918, † ! H.H319, P:P305+P351+P338 |  5g 25g 100g |
| | Application(s): Induces apoptosis in cell cultures | |
| A19778 | Farnesyl acetate, mixture of isomers, 96% [29548-30-9], C ₁₇ H ₂₈ O ₂ , F.W. 264.41, f.p. 95° (203°F), d. 0.91, n _D ²⁰ 1.477, EINECS 249-689-1, BRN 1784823, MDL MFCD00036516, † |  25g 100g |
| J62456 | Fast Blue BB base [C.I. 37175, 4'-Amino-2',5'-diethoxybenzanilide] [120-00-3], C ₁₇ H ₂₀ N ₂ O ₂ , F.W. 300.35, Powder, m.p. 98-100°, EINECS 204-363-8, BRN 3416889, MDL MFCD00009091, † ! H.H315-H318-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 25g 100g |
| | Application(s): C.I. 37175 | |
| L09704 | Fast Blue BB salt ▲ [4-Benzamido-2,5-diethoxybenzene diazonium chloride hemi zinc salt, C.I. 37175] [5486-84-0], C ₂₀ H ₁₈ Cl ₂ N ₂ O ₂ Zn, F.W. 831.89, m.p. ca 157° dec., EINECS 226-817-4, BRN 1845288, MDL MFCD00074765, † |  1g 5g 25g |
| J60574 | Fast Garnet GBC base [C.I. 11160, Solvent Yellow 3] [97-56-3], CH ₃ C ₆ H ₄ N=NC ₆ H ₃ (CH ₃)NH ₂ , F.W. 225.29, Powder, m.p. 101-102°, Merck 14,420, EINECS 202-591-2, RTECS XU8800000, BRN 6506005, MDL MFCD00007733, † ! H.H317-H350, P:P261-P280-P302+P352-P321-P405-P501 | 100g 500g |
| | Application(s): C.I. 11160 | |

| Stock # | Description | Size |
|---------|--|------------------------|
| A16520 | Fast Green FCF ■ [C.I. 42053] [2353-45-9], C ₃₇ H ₃₄ N ₂ Na ₂ O ₁₀ S ₃ , F.W. 808.86, m.p. ca 290° dec., Merck 14,3941, EINECS 219-091-5, RTECS BQ4425000, BRN 5718212, MDL MFCD00013053, † ↓ H:H341, P:P281-P201-P202-P308+P313-P405-P501a | 5g 25g 100g |
| | Application(s): Stain for showing collagen, muscle, cytoplasm and cells in mammalian tissues | |
| J63525 | Fasudil, 98+% [HA-1077] [103745-39-7], C ₁₄ H ₁₇ N ₃ O ₂ S, F.W. 327.83, Crystalline powder, Merck 14,3942 | 10mg 50mg |
| | Application(s): A potent Rho-kinase inhibitor with antivasospastic properties; inhibits vascular smooth muscle contraction by acting as an intracellular calcium antagonist | |
| J60594 | Fasudil dihydrochloride, 99+% [HA-1077 dihydrochloride] [203911-27-7], C ₁₄ H ₁₇ N ₃ O ₂ S·2HCl, F.W. 364.29, Powder, Merck 14,3942, RTECS HM4031166, MDL MFCD00153805 | 250mg 500mg 1g |
| | Application(s): A vasodilator agent which inhibits vascular smooth muscle contraction by acting as an intracellular calcium antagonist | |
| J60751 | Fasudil monohydrochloride, 99+% [HA-1077 hydrochloride] [105628-07-7], C ₁₄ H ₁₇ N ₃ O ₂ S·HCl, F.W. 327.83, Powder, Merck 14,3942, RTECS HM4031166 ! H:H302, P:P264-P270-P301+P312-P330-P501 | 250mg 500mg 1g |
| | Application(s): A vasodilator agent which inhibits vascular smooth muscle contraction by acting as an intracellular calcium antagonist | |
| J65298 | FBPase-1 Inhibitor ▲ [F16BPase Inhibitor] [883973-99-7], C ₁₃ H ₇ Cl ₃ N ₃ O ₃ S, F.W. 377.60, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10mg 50mg |
| | Application(s): A vasodilator agent which inhibits vascular smooth muscle contraction by acting as an intracellular calcium antagonist | |
| J63160 | FCS blocking buffer in PBS Liquid, Note: 10% Fetal calf serum in PBS | 250ml 500ml |
| | Application(s): For blocking excess solid surface in ELISA assays | |
| J61327 | FCS blocking buffer in TBS Liquid, Note: 10% Fetal calf serum in TBS | 250ml 500ml |
| | Application(s): For blocking excess solid surface in ELISA | |
| J61195 | Felodipine [Plendil, 4-(2,3-Dichlorophenyl)-1,4-dihydro-2,6-dimethyl-3,5-pyridinecarboxylic acid ethyl methyl ester] [72509-76-3], C ₁₈ H ₁₈ NO ₄ Cl ₂ , F.W. 384.25, Powder, Merck 14,3953, RTECS US7968700, MDL MFCD00868316 ! ↓ H:H302-H361, P:P281-P264-P301+P312-P308+P313-P405-P501 | 50mg 100mg 250mg |
| | Application(s): A dihydropyridine calcium channel blocker | |
| J63254 | Fendiline hydrochloride [N-[3,3-Diphenylpropyl]-α-methylbenzylamine] [13636-18-5], C ₂₃ H ₂₈ N·HCl, F.W. 351.92, Powder, m.p. 204-205°, Merck 14,3970, EINECS 237-121-5, RTECS DP4790000, MDL MFCD00079301 ! H:H302, P:P264-P270-P301+P312-P330-P501a | 5g |
| | Application(s): A calcium channel blocker | |
| J63562 | Fenvalerate, 99% [51630-58-1], C ₂₅ H ₄₂ ClNO ₃ , F.W. 419.91, Waxy solid, m.p. 54-59°, Merck 14,4010, UN2811, EINECS 257-326-3, RTECS CY1576350, BRN 2025982, MDL MFCD00055324 ☠ H:H301-H400-H410-H315-H319-H335, P:P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a | 25mg 100mg |
| | Application(s): Type II pyrethrin and a potent inhibitor of calcineurin (protein phosphatase 2B) | |
| | Ferric ammonium sulfate , see Ammonium iron(III) sulfate dodecahydrate, 39391, p. 101 Ferric citrate , see Iron(III) citrate hydrate, A10276, p. 259 Ferriprotoporphyrin IX chloride , see Hemin, A11165, p. 242 | |
| 87202 | Ferrocene, 99% ▲ ▽ [Bis(cyclopentadienyl)iron, Di(cyclopentadienyl)iron] [102-54-5], C ₁₀ H ₁₀ Fe, F.W. 186.04, Powder, Packaged under argon, m.p. 173-174°, b.p. 249°, Merck 14,4037, UN1325, EINECS 203-039-3, RTECS LK0700000, MDL MFCD00001427, † ☠ ! ↓ H:H228-H302-H411, P:P210-P241-P280-P240-P301+P312-P501a | 50g 250g 1kg |
| | Readily undergoes electrophilic substitution reactions such as acylation, formylation, Mannich reaction, etc. For a review, see: <i>Org. React.</i> , 17, 1 (1969). For Mannich reaction using tetramethylmethylenediamine as the source of the Mannich intermediate, see: <i>Org. Synth. Coll.</i> , 5, 434 (1973). Reacts with chlorobenzenes to give ferrocenium salts, which can be used to arylate diethyl malonate: <i>Synth. Commun.</i> , 18, 291 (1988); <i>J. Chem. Soc., Perkin 1</i> , 469 (1989). Promotes the Pschorr cyclization of stilbene derivatives in acetone to give phenanthrenes: <i>J. Org. Chem.</i> , 60, 196 (1995). In combination with TFA anhydride, reduces sulfoxides to sulfides at room temperature: <i>Chem. Lett.</i> , 400 (2000). | |







| Stock # | Description | Size |
|---------|--|------------------------------|
| | Ferrocenyl methyl ketone , see 1-Acetylferrocene, A13078, p. 72 | |
| | Ferrous ammonium sulfate , see Ammonium iron(II) sulfate hexahydrate, 13448, p. 101 | |
| | Ferulic acid , see trans-4-Hydroxy-3-methoxycinnamic acid, A13890, p. 250 | |
| J60437 | Fetuin I, fetal bovine serum [9014-81-7], Powder, EINECS 232-762-7, MDL MFCD00131055 | 100mg 250mg |
| | Application(s): A glycoprotein recovered from the globulin fraction of calf serum | 1g |
| J63262 | Fexofenadine hydrochloride [MDL 16455 hydrochloride, Terfenidine carboxylate hydrochloride] [153439-40-8], C ₂₀ H ₂₉ NO ₂ ·HCl, F.W. 538.12, Crystalline powder, m.p. 148-150°, Merck 14,4068, RTECS CY1633377, MDL MFCD00865710 | 25mg 100mg 500mg |
| | Application(s): H-1 receptor antagonist | |
| J63276 | Fibrinogen, bovine [Factor I] [9001-32-5], Powder, Merck 14,4071, EINECS 232-598-6, MDL MFCD00163624, Note: Greater than 75% clottable protein., † | 1g 5g 10g 25g |
| | Application(s): A soluble plasma glycoprotein, produced by the liver, that is converted by thrombin into fibrin during the blood coagulation process | |
| | Fibrinogen γ-chain dodecapeptide , see Fibrinogen-Binding Inhibitor Peptide, J60863, p. 220 | |
| J60863 | Fibrinogen-Binding Inhibitor Peptide [H-His-His-Leu-Gly-Gly-Ala-Lys-Gln-Ala-Gly-Asp-Val-OH, Fibrinogen γ-chain dodecapeptide] [89105-94-2], C ₂₀ H ₃₀ N ₁₀ O ₁₀ , F.W. 1189.30, Solid, MDL MFCD00167528 | 1mg 5mg |
| | Application(s): Inhibits the binding of fibrinogen and fibronectin | |
| J61540 | Fibrinogen-Binding Peptide [H-Glu-His-Ile-Pro-Ala-OH] [137235-80-4], C ₂₃ H ₃₉ N ₅ O ₈ , F.W. 565.63, Powder | 5mg 25mg |
| | Application(s): Antithrombotic agent | |
| J60967 | Fibrinolysis Inhibiting Factor [H-Gly-Pro-Arg-Pro-OH] C ₁₈ H ₃₁ N ₅ O ₅ , F.W. 425.48, Powder | 1mg 5mg |
| J65635 | Fibroblast Growth Factor, acidic, bovine, 90% [FGF1, human, aFGF, human] Note: Recombinantly expressed in E. Coli. Receptor Grade. Suitable for cell culture and radioimmunoassays. Supplied as an aseptically lyophilized powder. | 10micrograms 50micrograms |
| J64035 | Fibroblast Growth Factor, acidic, human, 95% [FGF1, bovine, aFGF, bovine] Note: Recombinantly expressed in E. Coli. Suitable for cell culture. Supplied as an aseptically lyophilized powder. | 5micrograms 25micrograms |
| J65713 | Fibroblast Growth Factor, basic, bovine, 95% [FGF2, bovine, bFGF, bovine] Note: Receptor Grade. Suitable for cell culture and radioimmunoassays. Supplied as an aseptically lyophilized powder. | 5micrograms 25micrograms |
| J64811 | Fibroblast Growth Factor, basic, human, 95% [FGF2, human, bFGF, human] Note: Recombinantly expressed in E. Coli. Receptor Grade. Suitable for cell culture and radioimmunoassays. Supplied as an aseptically lyophilized powder. | 10micrograms 50micrograms |
| J65662 | Fibroblast Growth Factor Basic Fragment (1-24), bovine [FGF2, Pro-Ala-Leu-Pro-Glu-Asp-Gly-Gly-Ser-Gly-Ala-Phe-Pro-Pro-Gly-His-Phe-Lys-Asp-Pro-Lys-Arg-Leu-Tyr] [62031-54-3], C ₁₁₈ H ₁₇₃ N ₃₁ O ₃₃ , F.W. 2553.82, Powder, Merck 14,4072, RTECS LK3641300, MDL MFCD00133317 | 0.5mg 1mg |
| J62380 | Fibronectin, bovine plasma [86088-83-7], Powder, EINECS 289-149-2, MDL MFCD00131062 | 5mg |
| | Application(s): High molecular weight extracellular glycoprotein | |
| J64560 | Fibronectin, human, 95% [HFN] | 1mg 10x1mg |
| J64390 | Fibronectin, rat, 95% | 1mg |
| J65696 | Fibronectin, stabilized soln., bovine | 5mg |
| J64738 | Fibronectin, stabilized soln., human | 1mg 10x1mg |
| J65555 | Fibronectin, stabilized soln., rat | 1mg |





| Stock # | Description | Size |
|---------|--|----------------------------|
| J64057 | Fibronectin, human, Enzyme Immunoassay Kit Note: One kit contains sufficient reagents and precoated 96-well strips to perform an ELISA for fibronectin Application(s): For detection of fibronectin. Detection range is 25-200ng/ml | 1kit |
| J60136 | Ficin, fig tree latex [EC 3.4.22.3] [9001-33-6], Lyophilized powder, Merck 14,4077, EINECS 232-599-1, RTECS LK3675000, MDL MFCD00081597, † ! ⚠ H:H315-H319-H334-H335, P:P285-P305+P351+P338-P302+P352-P321-P405-P501 | 25g |
| B22095 | Ficoll® 400 [Polysucrose 400] [26873-85-8], F.W. ca 400,000, EINECS 200-334-9, MDL MFCD00081599, † Application(s): Co-polymer of sucrose and epichlorohydrin used to make density gradients for lymphocyte separation | 10g 50g |
| A18577 | Field's Stain A MDL MFCD00146924, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 10g 50g |
| A18578 | Field's Stain B [17372-87-1], MDL MFCD00146926, Note: Contains Eosin Yellowish, with sodium hydrogen phosphate and potassium hydrogen phosphate for buffering., † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 10g 50g |
| L14552 | Filter Aid, Celite® AW Standard Supercel® [Celite® 521AW, filter aid] [61790-53-2], Merck 14,4973, EINECS 319-127-6, RTECS VV7311000, MDL MFCD00132803, † ⚠ ! H:H350-H373-H319-H335, P:P260-P261-P280-P305+P351+P338-P405-P501a Celite is a registered trademark of Celite Corp. Acid-washed grade for general filtrations. | 500g |
| B21983 | Filter aid, Celite® Standard Super-cel [61790-53-2], Merck 14,4973, EINECS 319-127-6, RTECS VV7311000, MDL MFCD00132803, † ⚠ ! H:H350-H373-H319-H335, P:P260-P261-P280-P305+P351+P338-P405-P501a | 500g 2.5kg |
| J63454 | Finasteride [98319-26-7], C ₂₂ H ₃₆ N ₂ O ₂ , F.W. 372.54, Powder, Merck 14,4082, RTECS CL5245000, MDL MFCD00869737 ! ⚠ H:H302-H360, P:P281-P264-P301+P312-P308+P313-P405-P501 | 100mg 500mg 1g 5g |
| A14495 | Flavin adenine dinucleotide disodium salt hydrate, 94% (dry wt.), water <10% [FAD-Na2, Riboflavin 5'-adenosine diphosphate disodium salt] [84366-81-4], C ₂₇ H ₃₁ N ₉ Na ₂ O ₁₅ P ₂ ·xH ₂ O, F.W. 829.52, EINECS 282-733-8, MDL MFCD00151217 | 100mg 500mg |
| J63527 | Flecainide acetate, 98% [N-(2-Piperidylmethyl)-2,5-bis-(2,2,2-trifluoroethoxy)benzamide acetate salt] [54143-56-5], C ₁₇ H ₂₀ F ₆ N ₂ O ₃ ·C ₂ H ₄ O ₂ , F.W. 474.40, Powder, m.p. 145-147°, Merck 14,4098, EINECS 258-997-5, RTECS CV5792550, MDL MFCD00214290 ⚠ ⚠ H:H300-H361-H315-H319-H335, P:P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a | 100mg 1g |
| J64484 | Flt-3 Inhibitor ▲ [2-[(3,4-Dimethoxybenzoyl)amino]-4,5,6,7-benzo[b]thiophene-3-carboxamide] [301305-73-7], C ₁₈ H ₂₀ N ₂ O ₄ S, F.W. 360.43, Powder, MDL MFCD00617269 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10mg 50mg |
| J62015 | Fluconazole, 99% [86386-73-4], C ₁₂ H ₁₂ F ₂ N ₄ O, F.W. 306.27, Crystalline powder, m.p. 138-140°, d. 1.05, Merck 14,4122, RTECS XZ4810000, MDL MFCD00274549 ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 1g 5g 25g |
| | Flucytosine, see 5-Fluorocytosine, L16496, p. 223 | |



| Stock # | Description | Size |
|---|--|------------------------|
| B23583 | Flufenamic acid, 97% ▲ [N-(3-Trifluoromethylphenyl)anthranilic acid] [530-78-9], C ₁₆ H ₁₀ F ₃ NO ₂ , F.W. 281.23, m.p. 133-135°, Merck 14,4132, UN2811, EINECS 208-494-1, RTECS CB4375000, BRN 1996069, MDL MFCD00002422 ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 10g 50g 250g |
| Application(s): An NSAID found to be a reversible gap junction blocker | | |
| J62537 | Flumazenil, 98% [Ro 15-1788] [78755-81-4], C ₁₅ H ₁₄ FN ₃ O ₃ , F.W. 303.29, Powder, Merck 14,4135, RTECS NI2922170, MDL MFCD00242764 | 100mg 500mg |
| Application(s): Benzodiazepine antagonist | | |
| J62969 | Flunarizine dihydrochloride, 99+% [1-[Bis(4-fluorophenyl)methyl]-4-(3-phenyl-2-propenyl)piperazine dihydrochloride] [30484-77-6], C ₂₈ H ₂₆ F ₂ N ₂ ·2HCl, F.W. 477.40, Powder, Merck 14,4144, EINECS 250-216-6, RTECS TK9187000, BRN 4284243, MDL MFCD00058198 ! H:H302, P:P264-P270-P301+P312-P330-P501 | 1g |
| Application(s): A dual sodium/calcium channel blocker; a cerebral and peripheral vasodilator | | |
| J63388 | Fiuo 3-AM [121714-22-5], C ₅₁ H ₈₀ Cl ₂ N ₂ O ₂₃ , F.W. 1129.86, Crystalline powder, MDL MFCD00083336 | 1mg |
| Application(s): Fluorescent indicator for intracellular calcium | | |
| J63996 | Fluocinolone acetonide [6-α-Fluorotriamcinolone acetonide] [67-73-2], C ₂₄ H ₃₅ F ₃ O ₆ , F.W. 452.49, Crystalline powder, m.p. 267-269°, Merck 14,4150, EINECS 200-668-5, RTECS TU3830000, MDL MFCD00010525 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 100mg 1g |
| Application(s): A glucocorticoid with anti-inflammatory properties | | |
| 2-Fluorenamine, see 2-Aminofluorene, B22769, p. 94 2-Fluorenylamine, see 2-Aminofluorene, B22769, p. 94 N-(9-Fluorenylmethoxycarbonyl) products, see Fmoc, B21107, p. 225 | | |
| A11683 | 9-Fluorenylmethyl chloroformate, 98% ▣ [Chloroformic acid 9-fluorenylmethyl ester, Fmoc-Cl] [28920-43-6], C ₁₅ H ₁₁ ClO ₂ , F.W. 258.70, m.p. 60-64°, Fieser 3,145 4,237 5,308 21,188, UN2923, EINECS 249-313-6, RTECS LQ6250000, BRN 2279177, MDL MFCD00001138 ! H:H314-H302-H332, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a Reagent for the protection of amino groups in peptide synthesis as their 9-fluorenylmethoxycarbonyl (Fmoc) derivatives: <i>J. Org. Chem.</i> , 37 , 3404 (1972); <i>J. Am. Chem. Soc.</i> , 96 , 4987 (1974); 99 , 7363 (1977). Review: <i>Acc. Chem. Res.</i> , 20 , 401 (1987). They are particularly applicable in solid-phase peptide synthesis. The stability of Fmoc-protected amino acids to acidic conditions permits their conversion in many cases to the acid chlorides as active intermediates for peptide coupling, resistant to racemization, in contrast to other protected amino acid chlorides. For a review of peptide synthesis via amino acid halides, see: <i>Acc. Chem. Res.</i> , 29 , 268 (1996). In the presence of triethylamine, reacts with Pentafluorophenol , A15574 , to give the PFP carbonate, a useful active ester for the preparation of Fmoc-amino acids. Moreover, the active PFP ester of the protected amino acid can be obtained by <i>in situ</i> DCC coupling with the liberated PFP: <i>Synthesis</i> , 303 (1986). Cleavage of the Fmoc group occurs under mildly basic conditions: Ethanolamine: <i>J. Am. Chem. Soc.</i> , 92 , 5748 (1970); <i>J. Org. Chem.</i> , 37 , 3404 (1972). Piperidine: <i>J. Org. Chem.</i> , 52 , 1197 (1987); applicable to solid-phase peptide synthesis. TBAF in DMF; rapid reaction at room temperature: <i>Tetrahedron Lett.</i> , 28 , 6617 (1987). For both the deblocking of Fmoc-protected amino acids and for the removal of excess reagent during the protection step, 4-(Aminomethyl)piperidine , L11577 , has been recommended: <i>J. Org. Chem.</i> , 51 , 3732 (1986); 55 , 721 (1990), particularly in conjunction with Fmoc-protected acid chlorides as the active species. Even better results have been obtained with Tris(2-aminoethyl)-amine , B21789 , in this type of chemistry: <i>J. Org. Chem.</i> , 55 , 1673 (1990). Limited use has also been made in the protection of alcohols as 9-fluorenylmethyl carbonates, rapidly cleaved by triethylamine: <i>J. Chem. Soc., Chem. Commun.</i> , 672 (1982). | 1g 5g 25g |
| Application(s): Base sensitive amino protecting group for solid-phase peptide synthesis | | |
| 43749 | Fluorescamine [38183-12-9], C ₁₇ H ₁₀ O ₄ , F.W. 278.27, Powder, m.p. 155-158°, Merck 14,4158, EINECS 253-814-5, MDL MFCD00005928 | 25mg 100mg 500mg |
| Application(s): For fluorescent detection of amino acids, peptides and proteins | | |
| L13251 | Fluorescein, 90+% [C.I. 45350.1, Solvent Yellow 94] [2321-07-5], C ₂₀ H ₁₂ O ₅ , F.W. 332.32, m.p. 320°, Merck 14,4159, EINECS 219-031-8, RTECS LM5075000, BRN 94324, MDL MFCD00005050, † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 Fluorescent agent. Adsorption indicator for halides. | 100g 500g |
| J62175 | Fluorescein amine isomer I, 96% [5-Aminofluorescein] [3326-34-9], C ₂₀ H ₁₃ NO ₅ , F.W. 347.32, Powder, m.p. 223° dec., EINECS 222-043-6, BRN 48395, MDL MFCD00005052, † ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g 5g |
| Application(s): A fluorescent labeling reagent | | |

























| Stock # | Description | Size |
|---|---|-----------------------|
| J60609 | Fluorescein amine isomer II, 95% [6-Aminofluorescein] [51649-83-3], C ₂₀ H ₁₃ NO ₅ , F.W. 347.32, Powder, m.p. 285° dec., EINECS 257-334-7, BRN 51708, MDL MFCD00005051 ! H:315-H319-H335, P:261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| Application(s): Fluorescent labeling reagent | | |
| B24466 | Fluorescein diacetate, 97% [596-09-8], C ₂₄ H ₁₆ O ₅ , F.W. 416.39, m.p. 200-203°, EINECS 209-877-6, BRN 62575, MDL MFCD00005062, † | 5g 25g 100g |
| Application(s): A substrate for esterases; used in studies on intracellular interactions and membrane permeability | | |
| J61549 | Fluorescein disodium salt [Acid Yellow 73, C.I. 45350] [518-47-8], C ₂₀ H ₁₀ Na ₂ O ₅ , F.W. 376.28, Powder, Merck 14,4159, EINECS 208-253-0, RTECS LM5425000, BRN 3833041, MDL MFCD00167039, † | 100g 500g |
| Application(s): A fluorophore commonly used in microscopy | | |
| A11659 | Fluorescein disodium salt hydrate [Acid Yellow 73, C.I. 45350] [518-47-8], C ₂₀ H ₁₀ Na ₂ O ₅ ·xH ₂ O, F.W. 376.28, m.p. >250°, Merck 14,4159, EINECS 208-253-0, RTECS LM5425000, BRN 3833041, MDL MFCD00167039, † Water-soluble form of fluorescein. | 100g 500g 2.5kg |
| L09319 | Fluorescein isothiocyanate, isomer 1, 95% ▽ [3326-32-7], C ₂₁ H ₁₁ NO ₅ S, F.W. 389.39, m.p. >360°, EINECS 222-042-0, BRN 1407295, MDL MFCD00005063, † ⚠ H:334-H317, P:260-P280g-P262-P309-P310 Reagent for fluorescent labelling of proteins: <i>Anal. Biochem.</i> , 20, 178 (1968). | 50mg 250mg 1g |
| Fluorexon, see Calcein sodium salt, L10255, p. 142 | | |
| J65562 | 2-Fluoro-9-β-D-arabinofuranosyladenine, 98% [Fludarabine, 2-F-araA] [21679-14-1], C ₁₀ H ₁₂ FN ₅ O ₄ , F.W. 285.23, Powder, Merck 14,4126, EINECS 244-525-5, RTECS AU6207000, BRN 1225932, MDL MFCD00132942 | 1g |
| 1-(4-Fluorobenzyl)-2-(1-[4-methoxyphenethyl]piperidin-4-yl)aminobenzimidazole, see Astemizole, 99+%, J60339, p. 111 | | |
| J60908 | 5-Fluorocytidine, 98% [2341-22-2], C ₈ H ₁₂ FN ₃ O ₃ , F.W. 261.21, Crystalline powder, m.p. 170-179°, RTECS HA3890000, MDL MFCD00210953 ! H:315-H319-H335, P:261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g 5g |
| L16496 | 5-Fluorocytosine, 98+% ▲ [Flucytosine] [2022-85-7], C ₈ H ₇ FN ₃ O, F.W. 129.09, m.p. ca 297° dec., Merck 14,4125, EINECS 217-968-7, RTECS HA6040000, BRN 127285, MDL MFCD00006035 ⚠ H:341, P:281-P201-P202-P308+P313-P405-P501a | 250mg 1g |
| J65441 | 2'-Fluoro-2'-deoxyadenosine, 99% [2'-Deoxy-2'-fluoroadenosine] [64183-27-3], C ₁₀ H ₁₂ FN ₅ O ₃ , F.W. 269.23, Powder | 1g |
| J65632 | 2'-Fluoro-2'-deoxycytidine, 99% [2'-Deoxy-2'-fluorocytidine] [10212-20-1], C ₉ H ₁₂ FN ₃ O ₄ , F.W. 245.21, Powder, MDL MFCD00057445 | 1g |
| J64055 | 2'-Fluoro-2'-deoxyguanosine, 99% [2'-Deoxy-2'-fluoroguanosine] [78842-13-4], C ₁₀ H ₁₂ FN ₅ O ₄ , F.W. 285.23, Powder ! H:302-H315-H319-H335, P:261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| J65208 | 2'-Fluoro-2'-deoxyinosine, 99% [2'-Deoxy-2'-fluoroinosine] [80049-87-2], C ₁₀ H ₁₁ FN ₅ O ₄ , F.W. 270.22, Powder | 1g |









| Stock # | Description | Size |
|---------|---|-------------------|
| J65948 | 2'-Fluoro-2'-deoxyuridine, 99% [1-(2-Fluoro-2-deoxy-β-D-ribofuranosyl)uracil] [784-71-4], C ₉ H ₁₁ FN ₂ O ₅ , F.W. 246.19, Powder, MDL MFCD01317293 | 1g 5g 25g |
| L16497 | 5-Fluoro-2'-deoxyuridine, 98+% [2'-Deoxy-5-fluorouridine, Floxuridine] [50-91-9], C ₉ H ₁₁ FN ₂ O ₅ , F.W. 246.20, m.p. 148-151°, Merck 14,4112, UN2811, EINECS 200-072-5, RTECS YU7535000, BRN 2645818, MDL MFCD00006530 ⚠ H: H360-H341-H302, P: P281-P264-P301+P312-P308+P313-P405-P501a | 100mg 500mg |
| H51972 | 4-Fluoro-N-Fmoc-L-phenylalanine, 95% [Fmoc-Phe(4-F)-OH] [169243-86-1], C ₂₄ H ₂₀ FNO ₄ , F.W. 405.42, BRN 8287377, MDL MFCD00191197 | 250mg 1g 5g |
| J65608 | 9α-Fluoro-16α-hydroxyprednisolone-16α,17α-acetonide , see Triamcinolone acetonide, 98+%, J63548, p. 374 | |
| J65608 | 2'-Fluoro-N2-isobutyryl-2'-deoxyguanosine, 98% C ₁₄ H ₁₈ FN ₅ O ₅ , F.W. 355.32, Powder | 1g |
| B22603 | 2-Fluoro-α-methyl-4-biphenylacetic acid, 99% [Flurbiprofen] [5104-49-4], C ₁₅ H ₁₃ FO ₂ , F.W. 244.27, m.p. 112-114°, Merck 14,4199, UN2811, EINECS 225-827-6, RTECS DU8341000, MDL MFCD00079303 ⚠ H: H301-H315-H319-H335, P: P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a | 1g 5g 25g |
| | Application(s): A cyclooxygenase inhibitor | |
| J64953 | (S)-(+)-α-Fluoromethylhistidine dihydrochloride [(S)-2-((Fluoromethyl)amino)-3-(1H-imidazol-4-yl)propanoic acid dihydrochloride] C ₇ H ₁₂ Cl ₂ FN ₃ O ₂ , F.W. 260.09, Solid | 10mg |
| | cis-5-Fluoro-2-methyl-1-[4-(methylsulfinyl)benzylidene]indene-3-acetic acid , see Sulindac, J61772, p. 356 | |
| J61336 | 4-Fluoro-7-nitrobenzofurozan [NBD-F, 4-Fluoro-7-nitro-2,1,3-benzoxadiazole] [29270-56-2], C ₈ H ₆ FN ₂ O ₃ , F.W. 183.10, Powder, m.p. 53-57°, f.p. 110°(230°F), BRN 1077571, MDL MFCD00010196 ⚠ H: H315-H319, P: P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | 100mg |
| | Application(s): Useful for amino acid and amine fluorescent labeling in HPLC | |
| | 4-Fluoro-7-nitro-2,1,3-benzoxadiazole , see 4-Fluoro-7-nitrobenzofurozan, J61336, p. 224 | |
| H51701 | 1-(4-Fluorophenyl)homopiperazine dihydrochloride, 98% [4-FPHP·2HCl] [263409-96-7], C ₁₁ H ₁₅ FN ₂ ·2HCl, F.W. 267.17, m.p. 219-223°, MDL MFCD08436121, Note: Sold in collaboration with Tosoh Organic Chemical Co., Ltd. ⚠ H: H315-H319-H335, P: P280g-P305+P351+P338 | 500mg |
| H51686 | 1-(3-Fluorophenyl)homopiperazine monohydrochloride, 98% [3-FPHP·HCl] [934991-99-8], C ₁₁ H ₁₅ FN ₂ ·HCl, F.W. 230.71, m.p. 187-191°, MDL MFCD09953903, Note: Sold in collaboration with Tosoh Organic Chemical Co., Ltd. | 500mg |
| | 4-(4-Fluorophenyl)-2-(4-hydroxyphenyl)-5-(4-pyridyl)imidazole , see SB 202190, 99+%, J60950, p. 340 | |
| | 4-(4-Fluorophenyl)-2-(4-methylsulfinylphenyl)-5-(4-pyridyl)imidazole , see SB 203580, 99%, J61482, p. 341 | |
| | 5-Fluoro-2,4(1H,3H)-pyrimidinedione , see 5-Fluorouracil, A13456, p. 224 | |
| | 6-α-Fluorotriamcinolone acetonide , see Fluciclonolone acetonide, J63996, p. 222 | |
| A13456 | 5-Fluorouracil, 99% ▲ [5-Fluoro-2,4(1H,3H)-pyrimidinedione, 5-FU] [51-21-8], C ₄ H ₄ FN ₂ O ₂ , F.W. 130.08, m.p. ca 282° dec., Merck 14,4181, UN2811, EINECS 200-085-6, RTECS YR0350000, BRN 127172, MDL MFCD00006018, † ⚠ H: H360-H341-H373-H302, P: P260-P281-P301+P312-P308+P313-P405-P501a Antineoplastic agent. Not for drug use. | 5g 25g 100g |
| J62083 | 5-Fluorouridine, 97% [316-46-1], C ₉ H ₁₁ FN ₂ O ₆ , F.W. 262.19, Powder, EINECS 206-260-3, RTECS YU8050000, BRN 33662, MDL MFCD00036832 ⚠ H: H341, P: P281-P201-P202-P308+P313-P405-P501a | 1g 5g |
| J61197 | Fluoxetine hydrochloride, 99% [LY-110,140 hydrochloride] [56296-78-7], C ₁₇ H ₁₈ F ₃ NO·HCl, F.W. 345.79, Powder, m.p. 158-159°, Merck 14,4185, EINECS 260-101-2, RTECS UI4050000, MDL MFCD00214288 ⚠ H: H302-H315-H318, P: P280-P305+P351+P338-P302+P352-P321-P310-P501 | 50mg 250mg |
| | Application(s): A selective serotonin reuptake inhibitor | |

| Stock # | Description | Size |
|---------|---|---------------------|
| J61179 | Fluphenazine, 98+% [69-23-8], C ₂₂ H ₂₆ F ₃ N ₃ OS, F.W. 437.52, Powder, m.p. 268-274°, Merck 14,4189, UN2811, EINECS 200-702-9, RTECS TL9730000 H: H301, P: P264-P270-P301+P310-P321-P405-P501a | 1g 5g 25g |
| | Application(s): Dopamine D1 receptor antagonist | |
| B20848 | Fluphenazine dihydrochloride, 98% ■ [146-56-5], C ₂₂ H ₂₆ F ₃ N ₃ OS·2HCl, F.W. 510.44, UN2811, EINECS 205-674-1, MDL MFCD00055212 H: H302, P: P264-P270-P301+P312-P330-P501a | 25g 100g 500g |
| | Application(s): A dopamine D1 receptor antagonist | |
| | Flurbiprophen , see 2-Fluoro- α -methyl-4-biphenylacetic acid, B22603, p. 224 FMN-Na , see Riboflavin-5'-phosphate sodium salt dihydrate, A14545, p. 337 | |
| B21107 | N-Fmoc-L-alanine monohydrate, 98% [N-(9-Fluorenylmethoxycarbonyl)-L-alanine monohydrate, Fmoc-Ala-OH] [207291-76-7], C ₁₉ H ₁₇ NO ₄ ·H ₂ O, F.W. 329.36 (311.34anhy), m.p. ca 130°, $[\alpha]_D^{20}$ -19° (c=1 in DMF), EINECS 252-660-6, BRN 2225975, MDL MFCD00037139 | 5g 25g |
| | (S)-3-(Fmoc-amino)adipic acid 6-tert-butyl ester, see N-Fmoc-L- β -homoglutamic acid 6-tert-butyl ester, H52188, p. 225 | |
| H52828 | 4-(Fmoc-amino)benzoic acid, 97% [Fmoc-4-Abz-OH] [185116-43-2], C ₂₂ H ₁₇ NO ₄ , F.W. 359.38, BRN 7722986, MDL MFCD00144888 | 250mg 1g 5g |
| | (S)-3-(Fmoc-amino)-5-methylhexanoic acid, see N-Fmoc-L- β -homoleucine, H51976, p. 225 (R)-3-(Fmoc-amino)-4-methylpentanoic acid, see N-Fmoc-L- β -homovaline, H52182, p. 225 (S)-2-(Fmoc-amino)-4-pentynoic acid, see N-Fmoc-L-propargylglycine, H52171, p. 226 | |
| H52195 | L-3-(Fmoc-amino)-N-trityladipic acid 6-amide, 95% [Fmoc- β -Homoglu(N-Trt)-OH, N ϵ -Trityl-N- β -Fmoc-L-homoglutamine] [401915-55-7], C ₄₀ H ₃₈ N ₂ O ₆ , F.W. 624.73, m.p. 113-117°, BRN 9601212, MDL MFCD03427580 | 250mg 1g |
| B21008 | N(α)-Fmoc-L-asparagine, 98% [N(α)-9-Fluorenylmethoxycarbonyl-L-asparagine, Fmoc-Asn-OH] [71989-16-7], C ₂₆ H ₁₉ N ₃ O ₅ , F.W. 354.36, m.p. ca 188° dec., $[\alpha]_D^{20}$ -12/+1° (c=1 in DMF), EINECS 276-252-2, BRN 4335103, MDL MFCD00037132 | 5g 25g |
| | N α -Fmoc-N- γ -Boc-L-2,4-diaminobutyric acid, see (S)-4-(Boc-amino)-2-(Fmoc-amino)butyric acid, H51990, p. 129 Fmoc-Cl, see 9-Fluorenylmethyl chloroformate, A11683, p. 222 | |
| H52190 | N-Fmoc-L-β-glutamic acid 5-tert-butyl ester, 95% [Fmoc- β -Glu(OtBu)-OH, N-Fmoc- β -homoaspartic acid 5-tert-butyl ester] [209252-17-5], C ₂₄ H ₂₇ NO ₆ , F.W. 425.48, BRN 7952342, MDL MFCD01862860 | 250mg 1g |
| B21050 | N-Fmoc-glycine, 98% [N-(9-Fluorenylmethoxycarbonyl)-glycine, Fmoc-Gly-OH] [29022-11-5], FmocNHCH ₂ CO ₂ H, F.W. 297.32, m.p. 172-175°, EINECS 249-373-3, BRN 2163967, MDL MFCD00037140 | 1g 5g |
| H52178 | N-Fmoc-L-β-homoolanine, 95% [Fmoc- β -Homoala-OH] [193954-26-6], C ₁₉ H ₁₉ NO ₄ , F.W. 325.36, BRN 7719789, MDL MFCD00270346 | 250mg 1g |
| | N-Fmoc- β -homoaspartic acid 5-tert-butyl ester, see Fmoc-L- β -glutamic acid 5-tert-butyl ester, H52190, p. 225 | |
| H52188 | N-Fmoc-L-β-homoglutamic acid 6-tert-butyl ester, 95% [(S)-3-(Fmoc-amino)adipic acid 6-tert-butyl ester, Fmoc- β -Homoglu(OtBu)-OH] [203854-49-3], C ₂₅ H ₂₉ NO ₆ , F.W. 439.51, m.p. 115-120°, BRN 8019724, MDL MFCD01863053 | 250mg 1g |
| H51976 | N-Fmoc-L-β-homoleucine, 95% [(S)-3-(Fmoc-amino)-5-methylhexanoic acid, Fmoc- β -Homoleu-OH] [193887-44-4], C ₂₂ H ₂₉ NO ₄ , F.W. 367.44, BRN 7723942, MDL MFCD01863059 | 250mg 1g |
| H52060 | N-Fmoc-L-β-homoproline, 95% [(S)-2-(1-Fmoc-2-pyrrolidinyl)acetic acid, Fmoc- β -Homopro-OH] [193693-60-6], C ₂₁ H ₂₇ NO ₄ , F.W. 351.40, BRN 7798553, MDL MFCD01863058 | 250mg 1g |
| H52182 | N-Fmoc-L-β-homovaline, 95% [(R)-3-(Fmoc-amino)-4-methylpentanoic acid, Fmoc-L- β -Ieu-OH] [172695-33-9], C ₂₁ H ₂₉ NO ₄ , F.W. 353.42, BRN 7388393, MDL MFCD01862853 | 250mg 1g |

| Stock # | Description | Size |
|--|---|---|
| H52740 | trans-N-Fmoc-4-hydroxy-L-proline, 97% [Fmoc-Hyp-OH] [88050-17-3], C ₂₀ H ₁₉ NO ₅ , F.W. 353.37, m.p. 189-193°, MDL MFCD00151929 |  1g |
| | | 5g |
| B21154 | N-Fmoc-L-isoleucine, 98% [N-(9-Fluorenylmethoxycarbonyl)-L-isoleucine, Fmoc-Ile-OH] [71989-23-6], C ₂₁ H ₂₃ NO ₄ , F.W. 353.42, m.p. 146-148°, EINECS 276-255-9, BRN 4716717, MDL MFCD00037125 |  1g |
| | | 5g |
| | | 25g |
| H29041 | N-Fmoc-D-leucine, 98% [N-(9-Fluorenylmethoxy)carbonyl-D-leucine, Fmoc-D-Leu-OH] [114360-54-2], C ₂₁ H ₂₃ NO ₄ , F.W. 353.42, m.p. 151-154°, MDL MFCD00062957 |  1g |
| | | 5g |
| | | 25g |
| B21040 | N-Fmoc-L-leucine, 98% [N-(9-Fluorenylmethoxycarbonyl)-L-leucine, Fmoc-Leu-OH] [35661-60-0], C ₂₁ H ₂₃ NO ₄ , F.W. 353.42, m.p. 152-155°, [α] _D ²⁰ -25° (c=1 in DMF), EINECS 252-662-7, BRN 2178254, MDL MFCD00037133 |  5g |
| | | 25g |
| | | |
| B21220 | N-Fmoc-L-methionine, 98+% [N-(9-Fluorenylmethoxycarbonyl)-L-methionine, Fmoc-Met-OH] [71989-28-1], C ₂₀ H ₂₁ NO ₃ S, F.W. 371.46, m.p. 132-135°, [α] _D ²⁰ -30° (c=1 in DMF), EINECS 276-258-5, BRN 4300266, MDL MFCD00037134 |  5g |
| | | 25g |
| | | |
| H52117 | N-Fmoc-4-methoxy-L-phenylalanine, 95% [Fmoc-Tyr(Me)-OH, N-Fmoc-O-methyl-L-tyrosine] [77128-72-4], C ₂₃ H ₂₃ NO ₅ , F.W. 417.45, MDL MFCD00153368 |  250mg |
| | | 1g |
| | | 5g |
| N-Fmoc-O-methyl-L-tyrosine, see N-Fmoc-4-methoxy-L-phenylalanine, H52117, p. 226 | | |
| H51962 | N-Fmoc-4-nitro-L-phenylalanine, 98% [Fmoc-Phe(4-NO ₂)-OH] [95753-55-2], C ₂₃ H ₂₃ N ₃ O ₆ , F.W. 432.43, m.p. 213-223°, BRN 5178656, MDL MFCD00057810 |  1g |
| | | 5g |
| | | |
| B22475 | N-Fmoc-L-norleucine, 98% [N-(9-Fluorenylmethoxycarbonyl)-L-norleucine, Fmoc-Nle-OH] [77284-32-3], C ₂₁ H ₂₃ NO ₄ , F.W. 353.42, m.p. 140-142°, MDL MFCD00037537 |  1g |
| | | 5g |
| | | 25g |
| B21689 | N-Fmoc-D-phenylalanine, 98% [N-(9-Fluorenylmethoxycarbonyl)-D-phenylalanine, Fmoc-D-Phe-OH] [86123-10-6], C ₂₃ H ₂₁ NO ₃ , F.W. 387.44, m.p. 181-185°, MDL MFCD00062955 |  1g |
| | | 5g |
| | | 25g |
| B21210 | N-Fmoc-L-phenylalanine, 98+% [N-(9-Fluorenylmethoxycarbonyl)-L-phenylalanine, Fmoc-Phe-OH] [35661-40-6], C ₂₃ H ₂₁ NO ₃ , F.W. 387.44, m.p. 180-185°, [α] _D ²⁰ -40° (c=1 in DMF), EINECS 252-661-1, BRN 3597808, MDL MFCD00037128 |  5g |
| | | 25g |
| | | |
| H28500 | N-Fmoc-D-proline, 98+%, may cont. up to ca 5% water [N-(9-Fluorenylmethoxy)carbonyl-D-proline, Fmoc-D-Pro-OH] [101555-62-8], C ₂₀ H ₁₉ NO ₄ , F.W. 337.38, m.p. 110-116°, MDL MFCD00077067 |  1g |
| | | 5g |
| | | 25g |
| B21081 | N-Fmoc-L-proline, 98% [N-(9-Fluorenylmethoxycarbonyl)-L-proline, Fmoc-Pro-OH] [71989-31-6], C ₂₀ H ₁₉ NO ₄ , F.W. 337.38, m.p. 113-117°, [α] _D ²⁰ -40° (c=1 in ethyl acetate), EINECS 276-259-0, BRN 3596735, MDL MFCD00037122 |  5g |
| | | 25g |
| | | |
| H52171 | N-Fmoc-L-propargylglycine, 95% [(S)-2-(Fmoc-amino)-4-pentynoic acid, Fmoc-propargyl-Gly-OH] [198561-07-8], C ₂₀ H ₁₇ NO ₄ , F.W. 335.36, BRN 9151699, MDL MFCD01075095 |  250mg |
| | | 1g |
| | | 5g |
| H52193 | N-Fmoc-3-(4-pyridyl)-D-alanine, 95% [Fmoc-β-(4-pyridyl)-D-Ala-OH] [205528-30-9], C ₂₃ H ₂₀ N ₂ O ₄ , F.W. 388.42, MDL MFCD00672567 |  250mg |
| | | 1g |
| | | 5g |
| H52172 | N-Fmoc-3-(4-pyridyl)-L-alanine, 95% [Fmoc-β-(4-pyridyl)-L-Ala-OH] [169555-95-7], C ₂₃ H ₂₀ N ₂ O ₄ , F.W. 388.42, BRN 7316905, MDL MFCD00672566 |  250mg |
| | | 1g |
| | | 5g |
| (S)-2-(1-Fmoc-2-pyrrolidinyl)acetic acid, see N-Fmoc-L-β-homoproline, H52060, p. 225 | | |
| B21079 | N-Fmoc-L-serine, 97+% [N-(9-Fluorenylmethoxycarbonyl)-L-serine, Fmoc-Ser-OH] [73724-45-5], C ₁₈ H ₁₇ NO ₅ , F.W. 327.34, m.p. 102-106°, [α] _D ²⁰ +13.6° (c=1 in ethyl acetate), BRN 4715791, MDL MFCD00051928 |  1g |
| | | 5g |
| | | |

| Stock # | Description | | Size |
|---------|---|---|-----------------------------------|
| H51975 | (S)-N-Fmoc-1,2,3,4-tetrahydroisoquinoline-3-carboxylic acid, 95% [Fmoc-Tic-OH] [136030-33-6], C ₂₅ H ₂₁ NO ₄ , F.W. 399.45, BRN 4827574, MDL MFCD00144368 |  | 250mg 1g 5g |
| H27363 | N-Fmoc-S-trityl-L-cysteine, 95% [N-(9-Fluorenylmethoxycarbonyl)-S-trityl-L-cysteine, Fmoc-Cys(Trt)-OH] [103213-32-7], C ₃₇ H ₃₇ NO ₄ S, F.W. 585.71, m.p. 171-173°, MDL MFCD00038538 |  | 1g 5g 25g |
| B22022 | N(α)-Fmoc-D-tryptophan, 98% [N-(9-Fluorenylmethoxycarbonyl)-D-tryptophan, Fmoc-D-Trp-OH] [86123-11-7], C ₂₈ H ₂₂ N ₂ O ₄ , F.W. 426.48, m.p. 182-185°, MDL MFCD00062954 |  | 1g 5g 25g |
| B21130 | N(α)-Fmoc-L-tryptophan, 98% [N(α)-9-Fluorenylmethoxycarbonyl-L-tryptophan, Fmoc-Trp-OH] [35737-15-6], C ₂₈ H ₂₂ N ₂ O ₄ , F.W. 426.48, m.p. 182-185°, [α] _D ²⁰ -27° (c=1 in DMF), EINECS 252-706-5, BRN 4216624, MDL MFCD00037126 |  | 1g 5g 25g |
| J65446 | N-Fmoc-Tyr-Ala-diazomethyl ketone [B-3530] [205763-22-0], C ₂₈ H ₂₆ N ₄ O ₅ , F.W. 498.54, Powder | | 10mg |
| B21030 | N-Fmoc-L-valine, 98% [N-(9-Fluorenylmethoxycarbonyl)-L-valine, Fmoc-Val-OH] [68858-20-8], C ₂₀ H ₁₈ NO ₄ , F.W. 339.40, m.p. 142-145°, [α] _D ²⁰ -17° (c=1 in DMF), EINECS 272-515-0, BRN 2177443, MDL MFCD00037124 |  | 5g 25g |
| | FMRF amide , see Molluscan Cardioexcitatory Neuropeptide, J62389, p. 294 | | |
| A14300 | Folic acid dihydrate, 97% [Pteroylglutamic acid] [75708-92-8], C ₁₉ H ₁₉ N ₇ O ₆ ·2H ₂ O, F.W. 477.44 (441.40anhy), m.p. ca 250° dec., [α] _D ²⁰ +18° (c=0.5 in 0.1N NaOH), Merck 14,4221, EINECS 200-419-0, RTECS LP5425000, BRN 100781, MDL MFCD00079305, † |  | 25g 100g |
| | Application(s): Vitamin B9. A B-complex vitamin necessary for the body to produce red blood cells | | |
| J60833 | Folic acid, crystalline [Pteroyl-L-glutamic acid] [59-30-3], C ₁₉ H ₁₉ N ₇ O ₆ , F.W. 441.41, Crystalline, Merck 14,4221, EINECS 200-419-0, RTECS LP5425000, BRN 100781, MDL MFCD00079305, † | | 25g 100g |
| | Application(s): Vitamin B9. A B-complex vitamin necessary for the body to produce red blood cells | | |
| J62937 | Folic acid, Cell Culture Reagent [PteGlu, Pteroyl-L-glutamic acid] [59-30-3], C ₁₉ H ₁₉ N ₇ O ₆ , F.W. 441.41, Powder, Merck 14,4221, EINECS 200-419-0, RTECS LP5425000, BRN 100781, MDL MFCD00079305, † | | 5g 25g 100g |
| | Application(s): Vitamin B9. A B-complex vitamin necessary for the body to produce red blood cells | | |
| J60401 | Formaldehyde, 4% in PBS [50-00-0], Liquid, † ⚠ H: H351-H302-H332-H317, P: P261-P280-P302+P352-P321-P405-P501a | | 250ml 500ml |
| 33314 | Formaldehyde, 37% in aq. soln., ACS, 36.5-38.0%, stab. with 10-15% methanol [Formalin, Formol] [50-00-0], HCHO, F.W. 30.03, Liquid, m.p. -15°, b.p. 97°, f.p. 60°(140°F), d. 1.083, n _D ²⁰ 1.3765, Merck 14,4235, Fieser 1,397 11,240 12,232 13,136 14,168 15,161 16,171 21,193, UN1198, EINECS 200-001-8, RTECS LP8925000, BRN 1209228, MDL MFCD00003274, † Maximum level of impurities: Color (APHA) 10, Residue after ignition 0.005%, Titratable acid 0.006meq/g, Cl 5ppm, SO ₂ 0.002%, Heavy Metals (as Pb) 5ppm, Fe 5ppm ⚠ H: H301-H311-H331-H370-H351-H314-H226-H317, P: P301+P310-P303+P361+P353-P305+P351+P338-P361-P405-P501a | | 500ml 1L 4L 4x1L 4x4L |
| 14835 | Formamide, ACS, 99.5+% ■ [75-12-7], HCONH ₂ , F.W. 45.04, Liquid, m.p. 2°, b.p. 210°, f.p. 154°(310°F), d. 1.134, n _D ²⁰ 1.4475, Merck 14,4237, EINECS 200-842-0, MDL MFCD00007941, † Specifications: Color (APHA) 10, Freezing point 2.0-3.0° ⚠ H: H360, P: P281-P201-P202-P308+P313-P405-P501a | | 250g 1kg 4x1kg |
| J65016 | Formate Dehydrogenase [EC 1.2.1.2] Lyophilized powder, Note: Component in the Cofactor Recycling Enzymes Kit, item J64535 | | 250mg 500mg 1g |



| Stock # | Description | Size |
|--|--|-----------------------|
| 36617 | Formic acid, ACS, 96+% [64-18-6], HCOOH, F.W. 46.03, Liquid, m.p. 7-9°, b.p. 100-101°, f.p. 50°(156°F), d. 1.220, n _D ²⁰ 1.3710, Merck 14,4241 , Fieser 1,404 8,232 9,226 11,243 13,137 18,163 19,148 20,168 21,193 , UN1779, EINECS 200-579-1, RTECS LQ4900000, BRN 1209246, MDL MFCD00003297, † Maximum level of impurities: Color (APHA) 15, Dilution test P.T., Evaporation residue 0.003%, CH ₃ COOH 0.4%, NH ₃ 0.005%, Cl 0.001%, SO ₄ 0.003%, SO ₃ P.T., Heavy Metals (as Pb) 0.001%, Fe 0.001%  H:H331-H314-H226-H302, P:P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a | 500g 2kg 4x500g |
| A13285 | Formic acid, 97% ■ [64-18-6], HCOOH, F.W. 46.03, m.p. 7-9°, b.p. 100-101°, f.p. 50°(156°F), d. 1.220, n _D ²⁰ 1.3710, Merck 14,4241 , Fieser 1,404 8,232 9,226 11,243 13,137 18,163 19,148 20,168 21,193 , UN1779, EINECS 200-579-1, RTECS LQ4900000, BRN 1209246, MDL MFCD00003297, †  H:H331-H314-H226-H302, P:P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a Cleaves trityl groups selectively in the presence of benzylidene acetals or TBDMS ethers: <i>Tetrahedron Lett.</i> , 27 , 579 (1986). Instead of the unstable formic anhydride, formylations may be carried out with formic acid and acetic anhydride to generate the mixed acetic formic anhydride <i>in situ</i> . For a review, see: <i>Tetrahedron</i> , 46 , 1081 (1990). This reagent has been used for the sulfoxylation of tertiary amine oxides: <i>Chem. Lett.</i> , 1517 (1985). Dehydration with sulfuric acid can be used to generate CO <i>in situ</i> . Subsequent reaction with tertiary carbocations gives the corresponding carboxylic acid (the Koch-Haaf carboxylation). For examples, see: <i>Org. Synth. Coll.</i> , 5 , 20, 739 (1973); improved procedure: <i>Synth. Commun.</i> , 19 , 1945 (1989). 1,4-Diols in which one alcohol is tertiary give γ -lactones: <i>Chem. Lett.</i> , 1187 (1982). Used in combination with formaldehyde in the Eschweiler-Clarke reductive methylation of amines, the formic acid acting as a hydride donor. Review: <i>Org. React.</i> , 5 , 290 (1949). For an example, see: <i>Org. Synth. Coll.</i> , 3 , 723 (1955). In the presence of Raney nickel alloy, reduces aromatic nitriles to aldehydes in high yield: <i>J. Chem. Soc.</i> , 5775 (1965); for list of examples, see: <i>Org. Synth. Coll.</i> , 6 , 631 (1988). Hydrogen donor, in combination with Pd on carbon, in catalytic transfer hydrogenations; see, e.g.: Selective reduction of dinitroarenes to nitroanilines: <i>J. Org. Chem.</i> , 45 , 4992 (1980). Dehalogenation of aryl halides: <i>Synthesis</i> , 876 (1982). Hydrogenation of aromatic rings: <i>Tetrahedron Lett.</i> , 33 , 7477 (1992). See also Palladium, A12012, Cyclohexene, A11359 , and Ammonium formate, A10699 . For a comparative mechanistic study of formic acid and formate salts in hydrogenolysis of aryl chlorides, see: <i>J. Org. Chem.</i> , 60 , 1347 (1995). In combination with Selenium(IV) oxide, 12358 , improved results have been obtained in the allylic oxidation of sterically-hindered olefins: <i>Synth. Commun.</i> , 24 , 29213 (1994). | 500g 2.5kg 10kg |
| J63292 | Forskolin, 98+% [66575-29-9], C ₂₂ H ₃₄ O ₇ , F.W. 410.51, Solid, Merck 14,2476 , EINECS 266-410-9, RTECS QL6150000, BRN 1692716, MDL MFCD00082317 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 10mg 50mg 100mg |
| Application(s): An adenylcyclase activator | | |
| 3-FPHP HCl, see 1-(3-Fluorophenyl)homopiperazine monohydrochloride, H51686, p. 224 4-FPHP 2HCl, see 1-(4-Fluorophenyl)homopiperazine dihydrochloride, H51701, p. 224 Frozen storage buffer , see FSB buffer, J60262, p. 228 | | |
| A17718 | D-Fructose, 99% [D-Levulose] [57-48-7], C ₆ H ₁₂ O ₆ , F.W. 180.16, m.p. ca 105-110°, d. 1.59, [α] _D ²⁰ -89° (c=2 in water), Merck 14,4273 , EINECS 200-333-3, RTECS LS7120000, BRN 1239004, MDL MFCD00148910, † | 250g 1kg 5kg |
| J60262 | FSB buffer [Frozen storage buffer] Liquid, Note: Contains 10mM potassium acetate, 10mM calcium chloride, 100mM potassium chloride, 54.5mM manganese chloride, 3mM hexamine cobalt chloride and 10% glycerol | 125ml 250ml |
| Application(s): For frozen storage of competent cells | | |
| Fuchsin acid sodium salt , see Acid Fuchsin sodium salt, B22222, p. 76 Fuchsin basic , see Basic Fuchsin, A12952, p. 117 | | |
| A18234 | D-(+)-Fucose, 99% ■ [6-Deoxy-D-galactose, <i>Rhodoese</i>] [3615-37-0], C ₆ H ₁₂ O ₅ , F.W. 164.16, m.p. 135-141°, [α] _D ²⁰ +76° (c=10 in water, 24h), Merck 14,4278 , EINECS 222-792-9, BRN 1723320, MDL MFCD00135603, † | 1g 5g |
| A16789 | L-(-)-Fucose, 99% ■ [6-Deoxy-L-galactose] [2438-80-4], C ₆ H ₁₂ O ₅ , F.W. 164.16, m.p. 139-142°, [α] _D ²⁰ -75° (c=10 in water, 24h), Merck 14,4279 , EINECS 219-452-7, BRN 1422661, MDL MFCD00069812, † | 1g 5g |
| 5-FUDR, see 5-Fluoro-2'-deoxyuridine, L16497, p. 224 Fugimycin , see Tacrolimus, 99+%, J63571, p. 357 | | |
| A10976 | Fumaric acid, 99% [trans-2-Butenedioic acid] [110-17-8], HO ₂ CCH=CHCO ₂ H, F.W. 116.07, m.p. ca 299° subl., f.p. 273°(523°F), d. 1.625, Merck 14,4287 , Fieser 5,319 , EINECS 203-743-0, RTECS LS9625000, BRN 605763, MDL MFCD00002700, † ! H:H319, P:P305+P351+P338 | 500g 2.5kg 10kg |
| Fumaric acid disodium salt , see Sodium fumarate, A11276, p. 346 | | |






| Stock # | Description | Size |
|---------|---|---------------------|
| J63686 | FURA 2 pentasodium salt [113694-64-7], C ₂₉ H ₂₃ Na ₅ N ₃ O ₁₄ , F.W. 751.45, Powder, MDL MFCD00083328 | 1mg |
| | Application(s): A very sensitive fluorescent calcium chelator | |
| J62728 | FURA 2-AM [Fura-2 pentakis(acetoxymethyl) ester] [108964-32-5], C ₄₄ H ₄₇ N ₃ O ₂₄ , F.W. 1001.87, Powder, BRN 8183748, MDL MFCD00036976 | 1mg |
| | Application(s): A calcium indicator; derivative of Fura-2 used to load the chelator into cells | |
| | Furacil , see 5-Nitro-2-furfurylidene semicarbazone, A18593, p. 304 2,5-Furandione , see Maleic anhydride, A12178, p. 275 Fura-2 pentakis(acetoxymethyl) ester , see FURA 2-AM, J62728, p. 229 | |
| B20834 | Furazolidone, 98% ▲ [3-(5-Nitrofurfurylideneamino)-2-oxazolidinone] [67-45-8], C ₆ H ₇ N ₃ O ₅ , F.W. 225.16, m.p. 254-256° dec., EINECS 200-653-3, RTECS RQ3675000, MDL MFCD00010550, † | 25g 100g 500g |
| |  ↓ H: H341, P: P281-P201-P202-P308-P313-P405-P501a | |
| | Application(s): Monoamine oxidase inhibitor | |
| J61378 | Furegrelate sodium salt, 99+% [U-63557A, Sodium furegrelate] [85666-17-7], C ₁₅ H ₁₀ NNaO ₃ , F.W. 275.20, Crystalline solid | 5mg 10mg 50mg |
| | Application(s): Inhibitor of thromboxane synthetase | |
| | N⁶-Furfuryladenine , see Kinetin, A13720, p. 264 6-Furfurylamino purine , see Kinetin, A13720, p. 264 7H-Furo[3,2-g]benzopyran-7-one , see Psoralen, 97%, J60042, p. 331 Furo[3,2-g]coumarin , see Psoralen, 97%, J60042, p. 331 | |
| J61457 | Furosemide, 97+% [4-Chloro-N-furfuryl-5-sulfamoylanthranilic acid] [54-31-9], C ₁₂ H ₁₁ ClN ₂ O ₆ S, F.W. 330.74, Crystalline powder, m.p. 206-209°, Merck 14,4309, EINECS 200-203-6, RTECS CB2625000, MDL MFCD00010549 | 5g 10g 25g |
| | ↓ H: H360, P: P281-P201-P202-P308-P313-P405-P501a | |
| | Application(s): Loop diuretic that inhibits the Na+/2Cl-/K+ (NKCC) cotransporter | |
| J63871 | G418 disulfate, 50mg/ml solution [Geneticin] [108321-42-2], C ₂₀ H ₄₀ N ₄ O ₁₀ ·2H ₂ SO ₄ , F.W. 692.71, Liquid, MDL MFCD00058314 | 10ml 50ml |
| | Application(s): Aminoglycoside that is toxic to bacteria, yeast, protozoans and helminths | |
| J62671 | G418 disulfate, Cell Culture Reagent [Geneticin disulfate] [108321-42-2], C ₂₀ H ₄₀ N ₄ O ₁₀ ·2H ₂ SO ₄ , F.W. 692.71, Powder, MDL MFCD00058314 | 1g 5g 25g |
| | Application(s): Aminoglycoside that is toxic to bacteria, yeast, protozoans and helminths | |
| J64528 | G3335 ▲ [H-Trp-Glu-OH] [36099-95-3], C ₁₈ H ₁₉ N ₃ O ₅ , F.W. 333.34, Solid | 50mg 100mg |
| | G6PD , see Glucose-6-phosphate dehydrogenase, Leuconostoc mesenteroides, J60117, p. 234 GABA , see 4-Aminobutyric acid, 99+%, J61307, p. 92 Galactitol , see Dulcitol, 99%, J63206, p. 202 4-O-β-D-Galactopyranosyl-D-fructose , see Lactulose, 99%, J60160, p. 265 6-O-α-D-Galactopyranosyl-D-glucose , see α-D-(+)-Melibiose, J60439, p. 279 | |
| L07462 | D-Galactosamine hydrochloride, 98% ■ [1772-03-8], C ₆ H ₁₃ NO ₅ ·HCl, F.W. 215.64, m.p. ca 183° dec., [α] _D ²⁰ +97° (c=1 in water), Merck 14,4334, EINECS 217-198-1, RTECS LW5500000, BRN 3697825, MDL MFCD00135830, † | 250mg 1g |
| |  | |
| A12813 | D-(+)-Galactose, 98% [59-23-4], C ₆ H ₁₂ O ₆ , F.W. 180.16, m.p. 164-168°, d. 1.50, [α] _D ²⁰ +80° (c=5 in water, 24h), Merck 14,4335, EINECS 200-416-4, RTECS LW5490000, BRN 1724619, MDL MFCD00151230, † | 50g 250g 1kg |
| |  | |
| B21448 | L(-)-Galactose, 98% [15572-79-9], C ₆ H ₁₂ O ₆ , F.W. 180.16, m.p. 163-165°, EINECS 239-630-8, BRN 1724622, MDL MFCD00063833 | 100mg 500mg |
| |  | |
| | Galanin Message Associated Peptide Fragment (16-41) amide , see GMAP (16-14) amide, J64666, p. 238 Galanin Message Associated Peptide Fragment (25-41) amide , see GMAP (25-41) amide, J64644, p. 238 | |
| J62482 | Galanthamine hydrobromide [1953-04-4], C ₁₁ H ₁₅ NO ₅ ·HBr, F.W. 368.27, Powder, Merck 14,4340, UN2811, EINECS 217-780-5, RTECS DF8075000, MDL MFCD00067672 | 50mg 1g |
| | ↓ H: H300, P: P264-P270-P301+P310-P321-P405-P501a | |
| | Application(s): Centrally active and long-acting acetylcholinesterase inhibitor | |


| Stock # | Description | Size |
|---------|--|---------------------|
| | 3-O-Gallate , see (-)-Epigallocatechin gallate, J61745, p. 209 Gallic acid , see 3,4,5-Trihydroxybenzoic acid, B24887, p. 377 Gallic acid n-dodecyl ester , see n-Dodecyl gallate, L06233, p. 201 | |
| J60731 | (-)-Gallic acid [(2S,3R)-2-(3,4,5-Trihydroxyphenyl)-3,4-dihydro-1(2H)-benzopyran-3,5,7-triol] [3371-27-5], C ₁₅ H ₁₀ O ₇ , F.W. 306.27, Powder, MDL MFCD01632616 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): Polyphenolic compound from green tea. Possesses free-radical scavenging ability | 10mg |
| J62740 | (-)-Gallic acid gallate [(2S,3R)-2-(3,4,5-Trihydroxyphenyl)-3,4-dihydro-1(2H)-benzopyran-3,5,7-triol 3-(3,4,5-trihydroxybenzoate)] [4233-96-9], C ₂₂ H ₁₈ O ₁₁ , F.W. 458.38, Powder, RTECS DH9000000, MDL MFCD00214298 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): An antioxidant from green tea | 10mg |
| J64547 | GAP 26 [Val-Cys-Tyr-Asp-Lys-Ser-Phe-Pro-Ile-Ser-His-Val-Arg] [197250-15-0], C ₇₀ H ₁₀₇ N ₁₉ O ₁₉ S, F.W. 1550.87, Solid | 0.5mg 1mg |
| J64109 | GAP 27 [Ser-Arg-Pro-Thr-Glu-Lys-Thr-Ile-Phe-Ile-Ile] [198284-64-9], C ₆₀ H ₁₀₂ N ₁₅ O ₁₇ , F.W. 1305.54, Solid, MDL MFCD03456920 | 0.5mg 1mg |
| J63405 | GBR 12783 dihydrochloride [67469-57-2], C ₂₈ H ₃₂ N ₂ O 2HCl, F.W. 485.50, Powder Application(s): A very potent and selective inhibitor of dopamine uptake | 10mg 50mg |
| | Gentisic acid , see 2,5-Dihydroxybenzoic acid, A11459, p. 191 | |
| J60684 | GBR 12909 dihydrochloride [1-(2-[Bis(4-fluorophenyl)methoxy]ethyl)-4-(3-phenylpropyl)piperazine dihydrochloride] [67469-78-7], C ₂₈ H ₃₂ F ₂ N ₂ O 2HCl, F.W. 523.49, Powder, MDL MFCD00055193 Application(s): Dopamine uptake inhibitor | 10mg 50mg |
| J62991 | GBR 12935 dihydrochloride [1-[2-(Diphenylmethoxy)ethyl]-4-(3-phenylpropyl)piperazine dihydrochloride] [67469-81-2], C ₂₈ H ₃₄ N ₂ O 2HCl, F.W. 487.51, Powder, MDL MFCD00083175 Application(s): A very potent and selective inhibitor of dopamine uptake | 10mg 50mg |
| | GDP , see Guanosine-5'-diphosphate disodium salt, J61646, p. 240 | |
| J62699 | Gelatin, 10% soln. [9000-70-8], Liquid, † | 125ml 250ml |
| J61548 | Gelatin, type A, 175 Bloom [9000-70-8], Powder, Merck 14,4382, EINECS 232-554-6, RTECS LX8580000, MDL MFCD00081638, † | 100g 500g 1kg |
| J62755 | Gelatin blocking buffer, 1% in PBS Liquid, Note: 1% Gelatin in PBS, † | 500ml 1L |
| J63104 | Gelatin blocking buffer, 1% in PBS, with 0.02% sodium azide Liquid, Note: 1% Gelatin and 0.02% Sodium azide in PBS | 500ml 1L |
| J62966 | Gelatin blocking buffer, 1% in TBS Liquid, Note: 1% Gelatin in TBS | 500ml 1L |
| J60805 | Gelatin blocking buffer, 1% in TBS, with 0.02% sodium azide Liquid, Note: 1% Gelatin and 0.02% Sodium azide in TBS | 500ml 1L |
| J60939 | Gelatin and Tween 20 in PBS Liquid, Note: Contains 1% Gelatin and 0.05% Tween-20 in PBS. | 500ml 1L |
| J62479 | Gelatin and Tween 20 in PBS, with 0.02% sodium azide Liquid, Note: This buffer contains 1% Gelatin and 0.05% Tween-20 in PBS with 0.02% sodium azide. | 500ml 1L |
| J62272 | Gelatin and Tween 20 in TBS Liquid, Note: This buffer contains 1% Gelatin and 0.05% Tween-20 in TBS. | 500ml 1L |
| J61671 | Gelatin and Tween 20 in TBS, with 0.02% sodium azide Liquid, Note: This buffer contains 1% Gelatin and 0.05% Tween-20 in TBS with 0.02% sodium azide. | 500ml 1L |
| J63358 | Gelatin veronal buffer (GVB), 5mM barbital Liquid, Note: This buffer contains: 5mM barbital, 145mM NaCl 145 mM, and 0.1% gelatin at pH 7.2. | 250ml 500ml |





| Stock # | Description | Size |
|---------|--|------------------------|
| J62828 | Gelatin veronal buffer (GVB), 10mM barbital Liquid, Note: This buffer contains: 10mM barbital, 145mM NaCl 145 mM, and 0.1% gelatin at pH 7.2. | 250ml 500ml |
| J63725 | Gelatin veronal buffer with EDTA (GVBE), 5mM barbital Liquid, Note: This buffer contains: 5mM barbital, 145mM NaCl, 0.1% gelatin, 10mM EDTA at pH 7.2. | 250ml 500ml |
| J61085 | Gelatin veronal buffer with EDTA (GVBE), 10mM barbital Liquid, Note: This buffer contains: 10mM barbital, 145mM NaCl, 0.1% gelatin, 10mM EDTA at pH 7.2. | 250ml 500ml |
| J61909 | Gelatin veronal buffer with Mg and EDTA (GVBMG), 5mM barbital Liquid, Note: This buffer contains: 5mM barbital, 145mM sodium chloride, 0.1% gelatin, 0.5mM magnesium chloride and 10mM EDTA at pH 7.2. | 250ml 500ml |
| J60686 | Gelatin veronal buffer with Mg and EDTA (GVBMG), 10mM barbital Liquid, Note: This buffer contains: 10mM barbital, 145mM sodium chloride, 0.1% gelatin, 0.5mM magnesium chloride and 10mM EDTA at pH 7.2 | 250ml 500ml |
| J61165 | Gelatin veronal buffer with Mg and Ca (GVB++), 5mM barbital Viscous liquid, Note: This buffer contains barbital 5 mM, 145mM sodium chloride, 0.1% gelatin, 0.5mM magnesium chloride, and 0.15mM calcium chloride at pH 7.2 | 250ml 500ml |
| J61744 | Gelatin veronal buffer with Mg and Ca (GVB++), 10mM barbital Liquid, Note: This buffer contains 10mM barbital, 145mM sodium chloride, 0.1% gelatin, 0.5mM magnesium chloride, and 0.15mM calcium chloride at pH 7.2 | 250ml 500ml |
| J63397 | Geldanamycin, 99+% [NSC 122750, U-29135] [30562-34-6], C ₂₀ H ₄₀ N ₂ O ₉ , F.W. 560.64, Powder, RTECS LX8920000, MDL MFCD00274570 H:H303, P:P312 | 25mg 100mg 250mg |
| | Application(s): Benzoquinoid antibiotic that inhibits pp60src tyrosine kinase | |
| J63423 | Gellan Gum [Phytigel] [71010-52-1], Powder, Merck 14,4383, EINECS 275-117-5, MDL MFCD00131909, † | 250g 1kg |
| | Application(s): An agar substitute and gelling agent | |
| | Geneticin , see G418 disulfate, 50mg/ml solution, J63871, p. 229 Geneticin disulfate , see G418 disulfate, Cell Culture Reagent, J62671, p. 229 Genistein , see 4',5,7-Trihydroxyisoflavone, 99+%, J63241, p. 377 Genistein-7-β-O-Glucopyranoside , see Genistin, 99+%, J63445, p. 231 Genistein 7-O-glucoside , see Genistin, 99+%, J63445, p. 231 | |
| J63445 | Genistin, 99+% [Genistein 7-O-glucoside, Genistein-7-β-O-Glucopyranoside] [529-59-9], C ₂₁ H ₃₀ O ₁₀ , F.W. 432.38, Powder, m.p. 258-259°, Merck 14,4391, RTECS DJ3093000, BRN 64479, MDL MFCD00016883 | 25mg 100mg |
| | Application(s): Glucoside of genistein that inhibits protein tyrosine kinase | |
| J62834 | Gentamycin sulfate, 600 I.U./mg [1405-41-0], Powder, Merck 14,4392, EINECS 215-778-9, RTECS LY2625000, MDL MFCD00270181, Note: Composed of Gentamycin C1 and Gentamycin C2 | 1g 5g 10g |
| | H:H334-H317, P:P285-P261-P280-P302+P352-P321-P501a | |
| | Application(s): Bacterial antibiotic that inhibits protein synthesis | |
| | Gentian Violet , see Crystal Violet, B21932, p. 170 | |
| A19864 | Geranyl acetate, 98% [105-87-3], (CH ₃) ₂ C=CHCH ₂ CH ₂ C(CH ₃)=CHCH ₂ O ₂ CCH ₃ , F.W. 196.29, b.p. 137-139°/25mm, f.p. 104°(219°F), d. 0.91, n _D ²⁰ 1.461, EINECS 203-341-5, RTECS RG5920000, MDL MFCD00015037, † | 25g 100g |
| | H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | |
| A14093 | Geranyl bromide, 96% ▲ [3,7-Dimethyl-2,6-octadienyl bromide] [6138-90-5], C ₁₀ H ₁₇ Br, F.W. 217.16, b.p. 99-101°/10mm, f.p. 95°(203°F), d. 1.094, n _D ²⁰ 1.5040, EINECS 228-123-7, BRN 1422412, MDL MFCD00000243, † | 5g 25g 100g |
| | H:H318-H335-H315, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Terpene building block. The Horner reaction with Methyldiphenylphosphine oxide , A11484, provides a convenient access to the natural product (3Z,6E)-α-farnesene, greatly superior to earlier multistep approaches: <i>J. Org. Chem.</i> , 60 , 6211 (1995): | |
| | | |
| | Gerontine , see Spermine, L19562, p. 351 GF 109203X , see Bisindolylmaleimide 1, J63401, p. 127 | |

| Stock # | Description | Size |
|---------|--|--------------------|
| J65403 | GGTI-2133 [N-[[4-(Imidazol-4-yl)methylamino]-2-(1-naphthyl)benzoyl]leucine] C ₂₇ H ₃₀ N ₄ O ₃ , F.W. 458.55, Solid, MDL MFCD07776925 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1mg |
| J65022 | GGTI-2147 ■ [(S)-Methyl 2-(4-(((1H-imidazol-4-yl)methyl)amino)-2-(naphthalen-1-yl)benzamido)-4-methylpentanoate] [191102-87-1], C ₂₈ H ₃₂ N ₄ O ₃ , F.W. 472.58, Solid | 0.5mg |
| J64943 | Ghrelin, human [258279-04-8], C ₁₄₀ H ₂₄₀ N ₄₇ O ₄₂ , F.W. 3370.85, Solid | 1mg |
| J64669 | Ghrelin, rat [258338-12-4], C ₁₄₇ H ₂₄₅ N ₄₅ O ₄₂ , F.W. 3314.78, Lyophilized powder, RTECS LY8965000, MDL MFCD02687544 | 1mg |
| J64299 | Ghrelin, Ser(palmitoyl), rat [258338-12-4], C ₁₅₅ H ₂₆₁ N ₄₅ O ₄₂ , F.W. 3427, Solid, RTECS LY8965000 | 0.5mg 1mg |
| J65946 | (Des-octanoyl)-Ghrelin, human [313951-59-6], C ₁₄₁ H ₂₃₈ N ₄₇ O ₄₁ , F.W. 3244.66, Solid, RTECS LY8960000 | 0.5mg 1mg |
| | GHRF , see Growth Hormone Releasing Factor GHRF (1-29), human , see Growth Hormone Releasing Factor (GRF) (1-29) amide, human, J61111, p. 238 GHRF (1-40), human , see Growth Hormone Releasing Factor (GRF) (1-40), human, J61784, p. 238 GHRF (1-44), human , see Growth Hormone Releasing Factor (GRF) (1-44), human, J62895, p. 238 | |
| A17843 | Gibberellic acid, 90+% [77-06-5], C ₁₉ H ₂₂ O ₆ , F.W. 346.37, m.p. 222° dec., [α] _D ²⁰ +78° (c=2 in methanol), Merck 14,4419, EINECS 201-001-0, RTECS LY8990000, BRN 54346, MDL MFCD00079329, † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 Plant growth regulator. For an overview of the chemistry of gibberelins, see: <i>Chem. Rev.</i> , 92 , 573 (1992). | 1g 5g 25g |
| | Application(s): Plant growth hormone | |
| 45569 | Gibberellic acid, 98% [77-06-5], C ₁₉ H ₂₂ O ₆ , F.W. 346.37, Powder, m.p. 222° dec., Merck 14,4419, EINECS 201-001-0, RTECS LY8990000, BRN 54346, MDL MFCD00079329, † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 500mg 2g 10g |
| | Application(s): Plant growth hormone | |
| B21172 | Giemsa Stain [51811-82-6], m.p. ca 300°, EINECS 257-438-2, MDL MFCD00081642, † | 10g 50g |
| | Application(s): Used in histopathology as a stain specific for phosphate groups in DNA | |
| | Gindarine , see L-Tetrahydropalmitine, J63911, p. 363 | |
| J62384 | Ginkgolide A [15291-75-5], C ₂₀ H ₂₄ O ₉ , F.W. 408.41, Powder, Merck 14,4426, MDL MFCD00133365 | 20mg |
| | Application(s): Platelet-Activating Factor (PAF) antagonist | |
| J60646 | Ginkgolide B [BN-52021] [15291-77-7], C ₂₀ H ₂₄ O ₁₀ , F.W. 424.40, Powder, Merck 14,4426, MDL MFCD05662347 | 10mg 50mg |
| | Application(s): Platelet-Activating Factor (PAF) antagonist | |
| J63101 | Ginseng Tetrapeptide [H-Val-γ-D-Glu-D-Arg-Gly-OH] [178553-95-2], C ₁₈ H ₃₃ N ₇ O ₇ , F.W. 459.50, Solid | 5mg |
| | Application(s): Appears to stimulate the growth of epidermal fibroblasts | |
| | Glibenclamide , see Glybenzcyclamide, B21459, p. 235 | |
| J62032 | Glimepiride [93479-97-1], C ₂₀ H ₂₄ N ₄ O ₃ S, F.W. 490.62, Powder, m.p. 212-215°, Merck 14,4440, RTECS UX9363950, MDL MFCD00878417 | 100mg 1g |
| | Application(s): A sulfonylurea hypoglycemic agent and potent potassium channel blocker | |
| J63398 | Glipizide [1-Cyclohexyl-3-4-[2-(5-methylpyrazine-2-carboxamido)ethyl]phenylsulfonyleurea] [29094-61-9], C ₂₁ H ₂₇ N ₄ O ₃ S, F.W. 445.54, Powder, Merck 14,4442, EINECS 249-427-6, RTECS YS7640000, MDL MFCD00072159 | 1g 5g |
| | Application(s): An ATP-dependent potassium channel blocker | |
| | H-L-Gln-OH , see L-Glutamine, 99+%, J61560, p. 235 GLP-2 (1-33), human , see Glucagon Like Peptide-2 (1-33), human, J65432, p. 233 | |







| Stock # | Description | Size |
|---------|--|--|
| J60827 | Glucagon (1-29), human [16941-32-5], C ₁₅₃ H ₂₂₅ N ₄₃ O ₄₅ S, F.W. 3982.80, Powder | 0.5mg 1mg |
| | Application(s): A peptide hormone that plays a role in maintaining glucose homeostasis | |
| J63443 | Glucagon (19-29), human [Ala-Gln-Asp-Phe-Val-Gln-Trp-Leu-Met-Asn-Thr] [64790-15-4], C ₆₁ H ₈₉ N ₁₅ O ₁₈ S, F.W. 1352.50, Powder | 1mg 5mg |
| | Application(s): This fragment inhibits calcium activated ATPase activity | |
| J65432 | Glucagon Like Peptide-2 (1-33), human C ₁₆₅ H ₂₅₄ N ₄₄ O ₅₅ S, F.W. 3766.1, Solid | 1mg |
| J64460 | [Ser8] Glucagon Like Peptide-1 (7-36) amide, human [[Ser8]-GLP-1 (7-36)] [215777-46-1], C ₁₄₈ H ₂₂₅ N ₄₀ O ₄₆ , F.W. 3312.61, Solid | 0.5mg 1mg |
| | D-Glucitol, see D-Sorbitol, 36404, p. 350 N-(D-Glucityl)-N-methyldecanamide, see N-Decanoyl-N-methylglucamine, J60173, p. 176 N-(D-Glucityl)-N-methyloctanamide, see N-Octanoyl-N-methylglucamine, J63574, p. 306 α-1,6-Glucobiose, see Isomaltose, J60884, p. 261 D-(+)-Gluconic acid δ-lactone, see D-(+)-Glucono-1,5-lactone, A13105, p. 233 δ-Gluconolactone, see D-(+)-Glucono-1,5-lactone, A13105, p. 233 | |
| A13105 | D-(+)-Glucono-1,5-lactone, 99% [D-(+)-Gluconic acid δ-lactone, δ-Gluconolactone] [90-80-2], C ₆ H ₁₀ O ₆ , F.W. 178.14, m.p. 154-159° dec., [α] _D ²⁰ +65° (c=4 in water), Merck 14,4457, EINECS 202-016-5, RTECS LZ5184000, BRN 83286, MDL MFCD00006647, † |  250g 500g 2.5kg |
| | 3-O-α-D-Glucopyranosyl-D-fructose, see D-Turanose, B21224, p. 385 6-O-α-D-Glucopyranosyl-D-fructose, see Palatinose hydrate, 98+%, J60091, p. 311 α-D-Glucopyranosyl-α-D-glucopyranoside, see D-(+)-Trehalose dihydrate, A19434, p. 374 4-O-α-Glucopyranosyl-D-glucose monohydrate, see D-(+)-Maltose monohydrate, A16266, p. 277 4-O-β-Glucopyranosyl-D-glucose, see D-(+)-Cellobiose, A14553, p. 151 6-O-α-D-Glucopyranosyl-D-glucose, see Isomaltose, J60884, p. 261 4-O-β-Glucopyranosyl-D-glucose octaacetate, see D-Cellobiose octaacetate, L08780, p. 151 | |
| A15532 | D-Glucosamine hydrochloride, 98+% [66-84-2], C ₆ H ₁₃ NO ₅ ·HCl, F.W. 215.64, m.p. ca 192° dec., [α] _D ²⁰ +73° (c=1 in water, 20h), Merck 14,4458, EINECS 200-638-1, RTECS LZ6665000, BRN 4157370, MDL MFCD00067674, † |  50g 250g 1kg |
| L09020 | β-D-Glucosamine pentaacetate, 96% [2-Acetamido-2-deoxy-1,3,4,6-tetra-O-acetyl-β-D-glucopyranose] [7772-79-4], C ₁₈ H ₂₃ NO ₁₀ , F.W. 389.37, m.p. 184-189°, [α] _D ²⁰ +4° (c=10 in chloroform), EINECS 231-865-4, BRN 98835, MDL MFCD00006595 |  1g 5g |
| J60667 | D-(+)-Glucose, 1M aq. soln., sterile [50-99-7], C ₆ H ₁₂ O ₆ , F.W. 180.16, Liquid, † | 125ml 250ml |
| A11090 | D-(+)-Glucose monohydrate, 99% [14431-43-7], C ₆ H ₁₂ O ₆ ·H ₂ O, F.W. 198.18 (180.16anhy), m.p. ca 83°, EINECS 200-075-1, MDL MFCD00149450, † |  500g 2.5kg |
| A16828 | D-(+)-Glucose, anhydrous, 99% [Dextrose] [50-99-7], C ₆ H ₁₂ O ₆ , F.W. 180.16, m.p. 147-153°, [α] _D ²⁰ +53° (c=10 in water, 3h), Merck 14,4459, EINECS 200-075-1, RTECS LZ6600000, BRN 1281608, MDL MFCD00063774, † |  500g 2.5kg 10kg |
| J65272 | Glucose Dehydrogenase variant A [EC 1.1.1.118] Lyophilized powder, Note: Component in the Cofactor Recycling Enzymes Kit, item J64535 | 250mg 500mg 1g |
| J65832 | Glucose Dehydrogenase variant B [EC 1.1.1.118] Lyophilized powder, Note: Component in the Cofactor Recycling Enzymes Kit, item J64535 | 250mg 500mg 1g |
| J60385 | Glucose gelatin veronal buffer (GGVB) Liquid, Note: This buffer contains: 5mM barbital, 140 mM glucose, 71mM sodium chloride, 0.1% gelatin, 0.5mM magnesium chloride, and 0.15mM calcium chloride at pH 7.2. | 250ml 500ml |
| J61846 | Glucose gelatin veronal buffer with EDTA (GGVB) Liquid, Note: This buffer contains: 5mM barbital, 140mM glucose, 71mM NaCl, 0.1% gelatin, and 10mM EDTA 10 mM at pH 7.2 | 250ml 500ml |

| Stock # | Description | Size |
|--|--|----------------------------|
| J60117 | Glucose-6-phosphate dehydrogenase, <i>Leuconostoc mesenteroides</i> [G6PD] [9001-40-5], Lyophilized powder, EINECS 232-602-6, MDL MFCD00081656, Note: Minimum 200 NADP units per mg protein. One unit reduces one micromole of NAD per minute at 37 degrees and pH 7.8, using glucose-6-phosphate as substrate. † | 1kilounit 10kilounits |
| Application(s): Oxidizes glucose-6-phosphate in the presence of NADP+ to yield 6-phosphogluconate | | |
| J61181 | Glucose-6-phosphate dehydrogenase, yeast [EC 1.1.1.49, RP-87086] [9001-40-5], Lyophilized powder, EINECS 232-602-6, MDL MFCD00081656, Note: One unit reduces one micromole of NADP per minute at pH 7.6 and 25 degrees. Minimum 20 units per mg protein. † | 1kilounit |
| Application(s): Converts p-glucose-6-phosphate to p-glucono-d-lactone-6-phosphate in presence of NADP+ or NAD+ | | |
| J63656 | Glucose veronal buffer (GVB) Liquid, Note: This buffer contains: 5mM barbital, 140mM glucose, 71mM sodium chloride, 0.5m magnesium chloride, and 0.15mM calcium chloride at pH 7.2. | 250ml 500ml |
| J60787 | Glucose veronal buffer with EDTA (GVB) Liquid, Note: 5mM barbital, 140mM glucose, 71mM NaCl 10mM EDTA, pH 7.2 | 250ml 500ml |
| L14350 | D-Glucuronic acid, 98+% [6556-12-3], C ₆ H ₁₀ O ₇ , F.W. 194.14, m.p. ca 158° dec., [α] _D ²⁰ +35° (c=6 in water), Merck 14,4465, EINECS 229-486-4, RTECS LZ8836600, BRN 1727083, MDL MFCD00077778, † | 5g 25g |
| | | |
| A15861 | D-Glucurono-6,3-lactone, 99% [32449-92-6], C ₆ H ₈ O ₆ , F.W. 176.12, m.p. 174° dec., [α] _D ²⁰ +19° (c=8 in water), Merck 14,4467, EINECS 251-053-3, RTECS LZ8930000, BRN 83595, MDL MFCD00135622, † | 25g 100g 500g |
| | | |
| A14191 | D-Glutamic acid, 99+% [D-2-Aminoglutaric acid, H-D-Glu-OH] [6893-26-1], C ₅ H ₉ NO ₄ , F.W. 147.13, m.p. 199° dec., [α] _D ²⁰ -30° (c=10 in 2N HCl), Merck 14,4469, EINECS 230-000-8, BRN 1723800, MDL MFCD00063112, † | 5g 25g 100g |
| | | |
| A15031 | L-Glutamic acid, 99+% [L-2-Aminoglutaric acid, H-Glu-OH] [56-86-0], C ₅ H ₉ NO ₄ , F.W. 147.13, m.p. 189-192° dec., d. 1.525, [α] _D ²⁰ +31° (c=5 in 5N HCl), Merck 14,4469, EINECS 200-293-7, RTECS LZ9700000, BRN 1723801, MDL MFCD00002634, † For use as a chiral building-block in the synthesis of the (S)-isomer of γ-butyrolactone-4-carboxylic acid, see: <i>Org. Synth. Coll.</i> , 7, 99 (1990): | 250g 500g 1kg 5kg |
| | | |
| For the differential protection of the α-carboxyl group of N-protected glutamic acid by reaction with formaldehyde to form the cyclic 5-oxazolidinone, see: <i>Synthesis</i> , 542 (1989). | | |
| A17719 | DL-Glutamic acid monohydrate, 99% [DL-2-Aminoglutaric acid monohydrate, H-DL-Glu-OH.H ₂ O] [19285-83-7], C ₅ H ₉ NO ₄ .H ₂ O, F.W. 165.15 (147.13anhy), m.p. ca 200° dec., d. 1.460, Merck 14,4469, EINECS 210-522-2, RTECS LZ9648000, BRN 4155097, MDL MFCD00150703, † | 25g 100g 500g |
| | | |
| J63424 | L-Glutamic acid monosodium salt [Monosodium glutamate, (S)-2-Aminopentanedioic acid] [142-47-2], C ₅ H ₈ NNaO ₄ , F.W. 169.11, Powder, Merck 14,6254, EINECS 205-538-1, RTECS MA1578000, MDL MFCD00013074, † | 10g 25g |
| A12505 | L-Glutamic acid hydrochloride, 99% ■ [L-2-Aminoglutaric acid hydrochloride, H-Glu-OH.HCl] [138-15-8], C ₅ H ₉ NO ₄ .HCl, F.W. 183.59, m.p. 203° dec., d. 1.525, [α] _D ²⁰ +23° (c=6 in water), Merck 14,4469, EINECS 205-315-9, BRN 3565569, MDL MFCD00012619, †  H: H318-H335-H315, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250g 1kg |
| | | |
| D-Glutamic acid 5-amide, see D-Glutamine, 99+%, J60784, p. 235 | | |
| J64847 | L-Glutamic acid α-(7-amido-4-methylcoumarin) [H-Glu-AMC, Glutamic acid-AMC] [98516-76-8], C ₁₅ H ₁₆ N ₂ O ₅ , F.W. 304.30, Powder | 50mg |
| J64272 | L-Glutamic acid γ-(7-amido-4-methylcoumarin) [H-Glu(AMC)-OH] [72669-53-5], C ₁₅ H ₁₆ N ₂ O ₅ , F.W. 304.30, Powder, MDL MFCD00038085 | 50mg |



| Stock # | Description | Size |
|---------|--|---|
| B24859 | L-Glutamic acid 5-methyl ester, 99% [L-Glu(OMe)-OH, γ -Methyl L-glutamate] [1499-55-4], C ₈ H ₁₁ NO ₄ , F.W. 161.16, m.p. 182° dec., EINECS 216-110-9, MDL MFCD00002632 |  5g |
| | | 25g |
| | | 100g |
| J60044 | Glutamic oxalacetic transaminase, porcine heart [L-Aspartate: 2-oxoglutarate aminotransferase, Aspartate aminotransferase] [9000-97-9], Suspension, EINECS 232-571-9, MDL MFCD00131191, Note: Minimum 200 units per mg protein. One unit catalyzes the transamination of one micromole of L-aspartate per minute at 25°C and pH 7.5, † | 1kilounit |
| | Application(s): Converts L-aspartate and α -ketoglutarate to oxaloacetate and L-glutamate | |
| J62109 | Glutamic pyruvic transaminase, porcine heart [L-Alanine: 2-oxoglutarate aminotransferase, EC 2.6.1.2] [9000-86-6], Lyophilized powder, EINECS 232-561-4, BRN 3562140, MDL MFCD00131192, Note: Minimum 100 units/mg. One unit converts one micromole of alpha-ketoglutarate to L-glutamate, in potassium phosphate buffer, at pH 7.5 and 25 degrees C, † | 1kilounit |
| | Application(s): Converts L-alanine and α -ketoglutarate to pyruvic acid and L-glutamate | |
| J60784 | D-Glutamine, 99+% [D-2-Aminoglutaramic acid, D-Glutamic acid 5-amide] [5959-95-5], C ₈ H ₁₀ N ₂ O ₃ , F.W. 146.14, Powder, BRN 1723796, MDL MFCD00065607 | 1g |
| | | 5g |
| | | 25g |
| | Application(s): Kinase inhibitor; has antivasospastic properties | |
| J61560 | L-Glutamine, 99+% [L-Glutamic acid 5-amide, H-L-Gln-OH] [56-85-9], C ₈ H ₁₀ N ₂ O ₃ , F.W. 146.14, Powder, m.p. ca 185° dec., Merck 14,4471, EINECS 200-292-1, RTECS MA2275100, BRN 1723797, MDL MFCD00008044, † | 100g |
| | | 500g |
| | | 1kg |
| J60573 | L-Glutamine, Cell Culture Reagent [56-85-9], C ₈ H ₁₀ N ₂ O ₃ , F.W. 146.14, Crystalline powder, Merck 14,4471, EINECS 200-292-1, RTECS MA2275100, BRN 1723797, MDL MFCD00008044, † | 25g 100g 1kg |
| | γ -L-Glutamyl-L-cysteinylglycine, see L-Glutathione, reduced, 98+%, J62166, p. 235 | |
| A14442 | γ-L-Glutamyl-4-nitroanilide, 98+% [7300-59-6], C ₁₁ H ₁₃ N ₃ O ₅ , F.W. 267.24, m.p. 185-188°, EINECS 230-748-5, BRN 2818758, MDL MFCD00036218, † |  1g |
| | | 5g |
| | | 25g |
| | Application(s): Substrate for γ -glutamyl transpeptidase | |
| | Glutathiol, see L-Glutathione, oxidized, J63715, p. 235 | |
| J63715 | L-Glutathione, oxidized [Glutathiol, GSSG] [27025-41-8], C ₂₀ H ₃₂ N ₆ O ₁₂ S ₂ , F.W. 612.64, Powder, Merck 14,4475, EINECS 248-170-7, RTECS MC0556500, BRN 1718700, MDL MFCD00063106 | 1g |
| | | 5g |
| | | ! |
| | H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Application(s): Acts as hydrogen acceptor in enzymatic determination of NADP and NADPH | |
| A18014 | L-Glutathione, reduced, 97% [γ -L-Glutamyl-L-cysteinylglycine, GSH] [70-18-8], C ₁₀ H ₁₇ N ₃ O ₆ S, F.W. 307.33, m.p. ca 193° dec., [α] _D ²⁰ -17° (c=2 in water), Merck 14,4475, EINECS 200-725-4, RTECS MC0556000, BRN 1729812, MDL MFCD00065939, † |  5g |
| | | 25g |
| | | 100g |
| | H:H303, P:P312 | |
| J62166 | L-Glutathione, reduced, 98+% [γ -L-Glutamyl-L-cysteinylglycine, GSH] [70-18-8], C ₁₀ H ₁₇ N ₃ O ₆ S, F.W. 307.33, Crystalline powder, m.p. ca 193° dec., Merck 14,4475, EINECS 200-725-4, RTECS MC0556000, BRN 1729812, MDL MFCD00065939, † | 5g |
| | | 25g |
| | | 100g |
| | Application(s): A tripeptide used for reductive cleavage of disulfide bonds | |
| | H-Gly-OH, see Glycine, 99.5+%, Cell Culture Reagent, J62407, p. 237 | |
| B21459 | Glybenzcyclamide, 99% [Glibenclamide, Glyburide] [10238-21-8], C ₂₃ H ₂₈ ClN ₃ O ₅ S, F.W. 494.01, m.p. 171-174°, EINECS 233-570-6, MDL MFCD00056625 |  25g |
| | | 100g |
| | | H:H303, P:P312 |
| | Application(s): ATP-dependent potassium channel (KATP) and cystic fibrosis transmembrane conductance regulator (CFTR) chloride channel blocker | |
| | Glyburide, see Glybenzcyclamide, B21459, p. 235 | |
| | Glycerin, see Glycerol, Cell Culture Grade, J62399, p. 235 | |
| J62399 | Glycerol, Cell Culture Grade [1,2,3-Propanetriol, Glycerin] [56-81-5], C ₃ H ₈ O ₃ , F.W. 92.09, Viscous liquid, m.p. 18°, b.p. 182°/20mm, f.p. 160°(320°F), d. 1.26, n _D ²⁰ 1.4740, Merck 14,4484, EINECS 200-289-5, RTECS MA8050000, BRN 635685, MDL MFCD00004722, † | 100ml |
| | | 250ml |
| | | 500ml |
| | ! | |
| | H:H319, P:P280-P264-P305+P351+P338-P337+P313 | |
| | Application(s): Useful as a cryoprotectant | |

| Stock # | Description | Size | | | | | | | | | | | | | | |
|---------|--|------------------|------|------|------|------|-----|-----|---|------|------|------|------|------|------|--|
| J61059 | Glycerol, Molecular Biology Grade ■ [56-81-5], HOCH ₂ CH(OH)CH ₂ OH, F.W. 92.09, Liquid, m.p. 18°, b.p. 182°/20mm, f.p. 160°(320°F), d. 1.26, n _D ²⁰ 1.474, Merck 14,4484, EINECS 200-289-5, RTECS MA8050000, BRN 635685, MDL MFCD00004722, † | 100ml | | | | | | | | | | | | | | |
| | | 500ml 1L | | | | | | | | | | | | | | |
| | ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | | | | | | | | | | | | | | | |
| | Application(s): Useful as a cryoprotectant | | | | | | | | | | | | | | | |
| J64719 | Glycerol, ultrapure, 99.5+% ■ [56-81-5], C ₃ H ₈ O ₃ , F.W. 92.09, Viscous liquid, m.p. 18°, b.p. 182°/20mm, f.p. 160°(320°F), d. 1.260, n _D ²⁰ 1.4740, Merck 14,4484, EINECS 200-289-5, RTECS MA8050000, BRN 635685, MDL MFCD00004722, † | 100ml | | | | | | | | | | | | | | |
| | | 250ml 500ml | | | | | | | | | | | | | | |
| | ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | | | | | | | | | | | | | | | |
| 38988 | Glycerol, ultrapure, HPLC Grade ■ [56-81-5], HOCH ₂ CH(OH)CH ₂ OH, F.W. 92.09, Viscous liquid, m.p. 18°, b.p. 182°/20mm, f.p. 160°(320°F), d. 1.26, n _D ²⁰ 1.474, Merck 14,4484, EINECS 200-289-5, RTECS MA8050000, BRN 635685, MDL MFCD00004722, Note: Suitable for spectrophotometry, chromatography. Filtered through 0.2µ filters., † Maximum level of impurities: H ₂ O 0.05% | 500ml | | | | | | | | | | | | | | |
| | | 1L 4L 4x1L | | | | | | | | | | | | | | |
| | ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | | | | | | | | | | | | | | | |
| | UV absorption - 1cm cell vs H₂O | | | | | | | | | | | | | | | |
| | <table border="1"> <thead> <tr> <th>λ(nm)</th> <th>400</th> <th>320</th> <th>280</th> <th>225</th> <th>210</th> <th>205</th> </tr> </thead> <tbody> <tr> <td>A</td> <td>0.01</td> <td>0.02</td> <td>0.05</td> <td>0.10</td> <td>0.30</td> <td>1.00</td> </tr> </tbody> </table> | λ(nm) | 400 | 320 | 280 | 225 | 210 | 205 | A | 0.01 | 0.02 | 0.05 | 0.10 | 0.30 | 1.00 | |
| λ(nm) | 400 | 320 | 280 | 225 | 210 | 205 | | | | | | | | | | |
| A | 0.01 | 0.02 | 0.05 | 0.10 | 0.30 | 1.00 | | | | | | | | | | |
| 32450 | Glycerol, ultrapure, Spectrophotometric Grade ■ [56-81-5], HOCH ₂ CH(OH)CH ₂ OH, F.W. 92.09, Viscous liquid, m.p. 18°, b.p. 182°/20mm, f.p. 160°(320°F), d. 1.26, n _D ²⁰ 1.474, Merck 14,4484, EINECS 200-289-5, RTECS MA8050000, BRN 635685, MDL MFCD00004722, † Maximum level of impurities: H ₂ O 0.1% | 100ml | | | | | | | | | | | | | | |
| | | 1L 4L 4x1L | | | | | | | | | | | | | | |
| | ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | | | | | | | | | | | | | | | |
| | UV absorption - 1cm cell vs H₂O | | | | | | | | | | | | | | | |
| | <table border="1"> <thead> <tr> <th>λ(nm)</th> <th>400</th> <th>320</th> <th>280</th> <th>225</th> <th>210</th> <th>205</th> </tr> </thead> <tbody> <tr> <td>A</td> <td>0.01</td> <td>0.02</td> <td>0.05</td> <td>0.10</td> <td>0.30</td> <td>1.00</td> </tr> </tbody> </table> | λ(nm) | 400 | 320 | 280 | 225 | 210 | 205 | A | 0.01 | 0.02 | 0.05 | 0.10 | 0.30 | 1.00 | |
| λ(nm) | 400 | 320 | 280 | 225 | 210 | 205 | | | | | | | | | | |
| A | 0.01 | 0.02 | 0.05 | 0.10 | 0.30 | 1.00 | | | | | | | | | | |
| A17132 | Glycerol triacetate, 99% [Triacetin] [102-76-1], C ₉ H ₁₈ O ₆ , F.W. 218.21, m.p. 2-4°, b.p. 257-259°, f.p. 149°(300°F), d. 1.155, EINECS 203-051-9, MDL MFCD00008716, † | 500g | | | | | | | | | | | | | | |
| | | 2.5kg | | | | | | | | | | | | | | |
| | | | | | | | | | | | | | | | | |
| A11830 | Glycerol tributyrate, 98% [Tributyryn] [60-01-5], C ₂₇ H ₅₀ O ₆ , F.W. 302.37, m.p. -75°, b.p. 307-308°, f.p. 174°(345°F), d. 1.032, n _D ²⁰ 1.4358, Merck 14,9620, EINECS 200-451-5, RTECS ET7350000, BRN 1714746, MDL MFCD00009392, † | 50g | | | | | | | | | | | | | | |
| | | 250g 1kg | | | | | | | | | | | | | | |
| | | | | | | | | | | | | | | | | |
| | Application(s): A triglyceride that may inhibit cell growth and induce cell differentiation | | | | | | | | | | | | | | | |
| | Glycerol trioleate , see Triolein, J62419, p. 379 | | | | | | | | | | | | | | | |
| A10922 | Glycerol tripalmitate, 98% [Tripalmitin] [555-44-2], C ₅₁ H ₉₈ O ₆ , F.W. 807.34, m.p. 60-64°, EINECS 209-098-1, MDL MFCD00008995, † | 1g | | | | | | | | | | | | | | |
| | | 5g 25g | | | | | | | | | | | | | | |
| | | | | | | | | | | | | | | | | |
| J62121 | β-Glycerophosphate, 200mM soln. [819-83-0], C ₃ H ₇ Na ₂ O ₆ P, F.W. 216.04, Liquid, † | 50ml | | | | | | | | | | | | | | |
| | | 100ml | | | | | | | | | | | | | | |
| | Glyceryl tridodecanoate , see Trilaurin, J62962, p. 378 | | | | | | | | | | | | | | | |
| | Glyceryl trimethylristate , see Trimyrustin, 95%, J62819, p. 378 | | | | | | | | | | | | | | | |
| J61855 | Glycine, 0.2M buffer soln., pH 2.5 [56-40-6], Liquid, † | 250ml | | | | | | | | | | | | | | |
| | | 500ml | | | | | | | | | | | | | | |
| J62527 | Glycine, 0.2M buffer soln., pH 3.0 [56-40-6], Liquid, † | 250ml | | | | | | | | | | | | | | |
| | | 500ml | | | | | | | | | | | | | | |
| J60154 | Glycine, 0.2M buffer soln., pH 3.5 [56-40-6], Liquid, † | 250ml | | | | | | | | | | | | | | |
| | | 500ml | | | | | | | | | | | | | | |
| 43497 | Glycine, ACS, 98.5+% [Aminoacetic acid, H-Gly-OH] [56-40-6], NH ₂ CH ₂ CO ₂ H, F.W. 75.07, Crystalline, m.p. ca 245° dec., d. 1.595, Merck 14,4491, Fieser 1,412, EINECS 200-272-2, RTECS MB7600000, BRN 635782, MDL MFCD00008131, † Maximum level of impurities: Residue after ignition 0.1%, Heavy metals (as Pb) 0.002%, Cl 0.005%, SO ₄ 0.005%, NH ₄ 0.005%, Substances darkened by sulfuric acid P.T., Hydrolyzable substances P.T. | 100g | | | | | | | | | | | | | | |
| | | 500g | | | | | | | | | | | | | | |
| | | 3kg | | | | | | | | | | | | | | |
| | ⚠ H:H373, P:P260-P314-P501a | | | | | | | | | | | | | | | |



| Stock # | Description | Size |
|---------|---|-------|
| A13816 | Glycine, 99% [Aminoacetic acid, H-Gly-OH] [56-40-6], NH ₂ CH ₂ CO ₂ H, F.W. 75.07, m.p. ca 245° dec., d. 1.595, Merck 14,4491, Fieser 1,412, EINECS 200-272-2, RTECS MB7600000, BRN 635782, MDL MFCD00008131, † | 100g |
| | | 250g |
| | | 500g |
| | | 2.5kg |
| | | 10kg |
| 36435 | Glycine, 99.5+% [Aminoacetic acid, H-Gly-OH] [56-40-6], H ₂ NCH ₂ CO ₂ H, F.W. 75.07, Powder, m.p. ca 245° dec., d. 1.595, Merck 14,4491, Fieser 1,412, EINECS 200-272-2, RTECS MB7600000, BRN 635782, MDL MFCD00008131, † | 250g |
| | | 1kg |
| J62407 | Glycine, 99.5+%, Cell Culture Reagent [Aminoacetic acid, H-Gly-OH] [56-40-6], H ₂ NCH ₂ CO ₂ H, F.W. 75.07, Powder, m.p. ca 245° dec., d. 1.595, Merck 14,4491, EINECS 200-272-2, RTECS MB7600000, BRN 635782, MDL MFCD00008131, † | 100g |
| | | 500g |
| | | 1kg |
| J64365 | Glycine, Electrophoresis Grade, 99.5+% [Aminoacetic acid, H-Gly-OH] [56-40-6], H ₂ NCH ₂ CO ₂ H, F.W. 75.07, Powder, m.p. ca 245° dec., d. 1.595, Merck 14,4491, EINECS 200-272-2, RTECS MB7600000, BRN 635782, MDL MFCD00008131, † | 250g |
| | | 1kg |
| J65592 | L-Glycine-7-amido-4-methylcoumarin [L-Gly-AMC, L-G-AMC] C ₁₂ H ₁₂ N ₂ O ₃ , F.W. 232.23, Solid | 10mg |
| | | 25mg |
| J64033 | L-Glycine-7-amido-4-trifluoromethylcoumarin [Gly-AFC, G-AFC] C ₁₂ H ₉ F ₃ N ₂ O ₃ , F.W. 286.20, Solid | 10mg |
| | | 25mg |
| A18822 | Glycine anhydride, 99% [2,5-Piperazinedione, 2,5-Diketopiperazine] [106-57-0], C ₄ H ₆ N ₂ O ₂ , F.W. 114.10, m.p. ca 300° dec., Merck 14,7466, EINECS 203-411-5, RTECS TL6325250, BRN 112112, MDL MFCD00006009, † | 25g |
| | | 100g |
| |  | |
| | Glycine Soja , see Soybean oil, J61399, p. 350 | |
| A12511 | Glycolic acid, 98% ■ [Hydroxyacetic acid] [79-14-1], HOCH ₂ CO ₂ H, F.W. 76.05, m.p. 74-80°, d. 1.49, Merck 14,4498, UN3261, EINECS 201-180-5, RTECS MC5250000, BRN 1209322, MDL MFCD00004312, † | 100g |
| | | 500g |
| |  ! H:H314-H302, P:P280-P305+P351+P338-P309-P310 | |
| J64191 | Glyco-SNAP-2 ▲ [N-(2-Deoxy-α,β-D-glucopyranose-2-)-N -acetyl-S-nitroso-D,L-penicillaminamide] [188849-82-3], C ₁₃ H ₂₃ N ₃ O ₆ S, F.W. 381.40, Solid | 5mg |
| | | 10mg |
| J60282 | Glycylglycine, 0.2M buffer soln., pH 7.5 [556-50-3], Liquid | 100ml |
| | | 250ml |
| J62920 | Glycylglycine, 0.2M buffer soln., pH 8.0 [556-50-3], Liquid | 100ml |
| | | 250ml |
| J60717 | Glycylglycine, 0.2M buffer soln., pH 8.5 [556-50-3], Liquid | 100ml |
| | | 250ml |
| J62591 | Glycylglycine, 0.2M buffer soln., pH 9.0 [556-50-3], Liquid | 100ml |
| | | 250ml |
| A10523 | Glycylglycine, 99% [Diglycine, Gly-Gly] [556-50-3], H ₂ NCH ₂ CONHCH ₂ CO ₂ H, F.W. 132.12, m.p. ca 220° dec., Merck 14,4503, EINECS 209-127-8, BRN 1765223, MDL MFCD00008130, † | 25g |
| | | 100g |
| | | 500g |
| | Application(s): Buffer with a useful pH range 7.5 to 8.9 | |
| A13778 | Glycylglycylglycine, 99% [Gly-Gly-Gly, Triglycine] [556-33-2], H ₂ NCH ₂ (CONHCH ₂) ₂ CO ₂ H, F.W. 191.14, m.p. ca 240° dec., Merck 14,6579, EINECS 209-122-0, BRN 1711130, MDL MFCD00036223 | 1g |
| | | 5g |
| | | 25g |
| | Gly-Gly , see Glycylglycine, A10523, p. 237 | |
| | Gly-Gly-Gly , see Glycylglycylglycine, A13778, p. 237 | |
| | Glyoxal bisacrylamide , see N,N'-(1,2-Dihydroxyethylene)bisacrylamide, L19211, p. 192 | |
| | Glyoxaline , see Imidazole, A10221, p. 254 | |









| Stock # | Description | Size |
|---------|--|------------------------|
| B25149 | Glyoxylic acid, 50% w/w aq. soln. [298-12-4], OHCCO ₂ H, F.W. 74.04, m.p. -93°, b.p. 111°, d. 1.339, UN3265, EINECS 206-058-5, MDL MFCD00006958, † | 250g 1kg 5kg |
| | ! H: H314-H317, P: P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a For use in aqueous hetero Diels-Alder reactions, see: <i>Tetrahedron</i> , 50 , 10265 (1994). Reagent for the facile deprotection of oximes in aqueous medium: <i>Tetrahedron Lett.</i> , 45 , 3161 (2004). | |
| J64718 | Gly-Phe β-naphthylamide [Glycylphenylalanine 2-naphthylamide, (S)-2-(2-Aminoacetamido)-N-(naphthalen-2-yl)-3-phenylpropanamide] [21438-66-4], C ₂₁ H ₂₁ N ₃ O ₂ , F.W. 347.41, Crystalline, MDL MFCD00021597 | 100mg |
| | ☞ H: H351, P: P281-P201-P202-P308+P313-P405-P501 | |
| J64034 | GM 1489 [(R)-3-((S)-3-(1H-Indol-3-yl)-1-oxo-1-((S)-1-phenylethylamino)propan-2-ylcarbonyl)-5-methylhexanoic acid, N-((2R)-2-(Carboxymethyl)-4-methylpentanoyl]-L-tryptophan-(S)-methyl-benzylamide] [170905-75-6], C ₂₇ H ₃₃ N ₃ O ₄ , F.W. 463.60, Solid | 1mg 5mg |
| J65687 | GM 6001 ☐ [Galdarin, N-((2R)-2-(Hydroxamidocarbonylmethyl)-4-methylpentanoyl]-L-tryptophan methylamide] [142880-36-2], C ₂₀ H ₂₈ N ₄ O ₄ , F.W. 388.50, Solid, MDL MFCD03453614 | 1mg 5mg |
| J64386 | GM 6001, Negative Control ☐ [(N-t-Butoxycarbonyl-L-leucyl-L-tryptophan methylamide)] C ₂₃ H ₃₄ N ₄ O ₄ , F.W. 430.54, Solid | 1mg 5mg |
| J64666 | GMAP (16-41) amide [Galanin Message Associated Peptide Fragment (16-41) amide, Preprogalanin (80-105) amide] [129541-35-1], C ₁₃₄ H ₂₁₉ N ₃₅ O ₃₇ S, F.W. 2944.44, Solid | 0.5mg 1mg |
| J64644 | GMAP (25-41) amide [Galanin Message Associated Peptide Fragment (25-41) amide, Thr-Ile-Met-Glu-Phe-Leu-Ala-Phe-Leu-His-Leu-Lys-Glu-Ala-Leu-NH2] [132567-21-6], C ₉₀ H ₁₄₃ N ₂₁ O ₂₂ S, F.W. 1903.29, Solid | 0.5mg 1mg |
| | GMBS , see N-(γ-Maleimidobutyryloxy)succinimide, J61850, p. 276 | |
| J64301 | Goat Serum | 5ml |
| L02639 | DL-Goitrin, 98+% [5-Vinylloxazolidone-2-thione] [13190-34-6], C ₅ H ₇ NOS, F.W. 129.18, m.p. 62-66°, Merck 14,4513 , EINECS 236-145-3, BRN 80669, MDL MFCD00015467 The antithyroid factor of turnip root: <i>J. Biol. Chem.</i> , 181 , 121 (1949). | 100mg 500mg |
| |  | |
| J63767 | Gossypol, 98+% [Thespesin, 2,2'-bis(8-Formyl-1,6,7-trihydroxy-5-isopropyl-3-methylnaphthalene)] [303-45-7], C ₃₀ H ₃₀ O ₈ , F.W. 518.56, Powder, Merck 14,4528 , RTECS DU3100000, MDL MFCD00017352 | 25mg 100mg 250mg |
| | ☞ ! H: H341-H361-H302, P: P281-P264-P301+P312-P308+P313-P405-P501a Application(s): Lipophilic agent derived from cottonseed | |
| B23521 | (+)-Griseofulvin, 97% [126-07-8], C ₁₇ H ₁₇ ClO ₆ , F.W. 352.77, m.p. 218-220°, Merck 14,4549 , EINECS 204-767-4, RTECS WG9800000, BRN 95226, MDL MFCD00082343 | 5g 25g 100g |
| | ☞ ! H: H360-H351-H317, P: P261-P280-P302+P352-P321-P405-P501a Application(s): Interferes with microtubule formation | |
| |  | |
| J65580 | Growth Hormone Pro-Releasing Factor, human C ₁₅₃ H ₂₄₈ N ₄₄ O ₅₀ S ₂ , F.W. 3567.99, Solid | 1mg |
| J61111 | Growth Hormone Releasing Factor (GRF) (1-29) amide, human [GHRF (1-29), human, Sermorelin] [86168-78-7], C ₁₄₈ H ₂₆₆ N ₄₄ O ₄₂ S, F.W. 3357.90, Powder, Merck 14,8461 , MDL MFCD00076559 | 0.5mg 1mg |
| | Application(s): A peptide hormone that stimulates release of the growth hormone | |
| J61784 | Growth Hormone Releasing Factor (GRF) (1-40), human [GHRF (1-40), human] [84069-10-3], C ₁₉₄ H ₃₁₇ N ₆₁ O ₆₃ S, F.W. 4544.08, Powder, MDL MFCD00081669 | 0.5mg 1mg |
| | Application(s): A peptide hormone that stimulates release of the growth hormone | |
| J62895 | Growth Hormone Releasing Factor (GRF) (1-44), human [GHRF (1-44), human] [83930-13-6], C ₂₁₅ H ₃₆₈ N ₇₂ O ₆₆ S, F.W. 5039.71, Powder, Merck 14,8714 , MDL MFCD00081671 | 0.5mg 1mg |
| | Application(s): A peptide hormone that stimulates release of the growth hormone | |
| | GSH , see L-Glutathione, reduced, 98+%, J62166, p. 235 | |

| Stock # | Description | Size |
|---------|---|-----------------------|
| J65166 | GSK 4716 [4-Hydroxy-2-[(1E)-[4-(1-methylethyl)phenyl]methylene]hydrazide, GW4716] [101574-65-6], C ₁₇ H ₁₈ N ₂ O ₂ , F.W. 282.34, Solid, UN3077, MDL MFCD00567155 ! H:H410, P:P273-P391-P501 | 10mg 50mg |
| J64048 | GSK-3β Inhibitor I ▲ [TDZD-8, 4-Benzyl-2-methyl-1,2,4-thiadiazolidine-3,5-dione] C ₁₀ H ₁₀ N ₂ SO ₂ , F.W. 222.26, Solid ! H:H317, P:P261-P280-P302+P352-P321-P363-P501 | 5mg |
| J64336 | GSK-3β Inhibitor VI [2-Chloro-1-(4,5-dibromothiophen-2-yl)ethanone] [62673-69-2], C ₈ H ₅ Br ₂ ClOS, F.W. 318.41, Solid | 5mg |
| J64554 | GSK-3β Inhibitor VIII ▲ [AR-A014418] [487021-52-3], C ₁₂ H ₁₂ N ₂ O ₄ S, F.W. 308.31, Solid, MDL MFCD08277040 ! H:H302-H315-H318-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10mg |
| J64307 | GSK-3 Inhibitor IX, Control, MeBIO ▲ [1-Methyl-BIO] [710323-61-8], C ₁₇ H ₁₂ BrN ₂ O ₂ , F.W. 370.20, Solid | 1mg |
| J64659 | GSK-3 Inhibitor X ▲ [BIO-Acetoxime, (2Z,3'E)-6-Bromindirubin-3'-acetoxime] [740841-15-0], C ₁₉ H ₁₂ BrN ₂ O ₅ , F.W. 398.21, Solid ! H:H340-H350, P:P281-P201-P202-P308+P313-P405-P501 | 1mg 5mg |
| | GSSG , see L-Glutathione, oxidized, J63715, p. 235 | |
| J62597 | GTE buffer Liquid, Note: Contains 25mM Tris, 50mM glucose, and 10mM EDTA. Application(s): For miniprep and DNA purification | 100ml 250ml |
| | GTP, see Guanosine-5'-triphosphate disodium salt, J61414, p. 240 Guaiacol, see 2-Methoxyphenol, A16319, p. 285 Guaiacol glyceryl ether, see 3-(2-Methoxyphenoxy)-1,2-propanediol, A16827, p. 285 Guaifenesin, see 3-(2-Methoxyphenoxy)-1,2-propanediol, A16827, p. 285 Guanazole, see 3,5-Diamino-1,2,4-triazole, B22775, p. 183 | |
| A13543 | Guanidine hydrochloride, 98% ■ [50-01-1], CH ₅ N ₃ .HCl, F.W. 95.53, m.p. 178-185°, d. 1.344, Merck 14,4562, EINECS 200-002-3, RTECS MF4300000, BRN 3591990, MDL MFCD00013026, † ! H:H302-H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P501a | 250g 1kg 5kg |
| J60786 | Guanidine hydrochloride, 99+% ■ [50-01-1], CH ₅ N ₃ .HCl, F.W. 95.53, Powder, m.p. 185-188°, d. 1.344, Merck 14,4562, EINECS 200-002-3, RTECS MF4300000, BRN 3591990, MDL MFCD00013026, † ! H:H302-H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P501a | 100g 500g 1kg |
| J65661 | Guanidine hydrochloride, Molecular Biology Grade ■ [50-01-1], CH ₅ N ₃ .HCl, F.W. 95.53, Crystalline solid, m.p. 178-185°, d. 1.34, EINECS 200-002-3, RTECS MF4300000, BRN 3591990, MDL MFCD00013026, † ! H:H302-H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P501 | 100g 500g |
| | Application(s): A protein denaturant | |
| J65485 | Guanidine hydrochloride, ultrapure, 99% ■ [50-01-1], CH ₅ N ₃ .HCl, F.W. 95.53, Powder, m.p. 185-188°, d. 1.344, Merck 14,4562, EINECS 200-002-3, RTECS MF4300000, BRN 3591990, MDL MFCD00013026, † ! H:H302-H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P501 | 500g 1kg 10g |
| | Guanidine rhodanide , see Guanidine thiocyanate, B21250, p. 239 | |
| B21250 | Guanidine thiocyanate, 99% ▲ [Guanidine rhodanide] [593-84-0], C ₂ H ₅ N ₃ S, F.W. 118.16, m.p. 118-122°, d. 1.29, EINECS 209-812-1, RTECS XL1225000, BRN 3563461, MDL MFCD00013027, † ! H:H302-EUH032-H312-H332-H412, P:P261-P280-P302+P352-P304+P340-P322-P501a | 100g 500g 2.5kg |
| J65104 | Guanidine thiocyanate, Molecular Biology Grade ▲ [Guanidine rhodanide] [593-84-0], CH ₅ N ₃ .CHNS, F.W. 118.16, Crystalline solid, m.p. 118-122°, d. 1.29, EINECS 209-812-1, RTECS XL1225000, BRN 3563461, MDL MFCD00013027, † ! H:H302-EUH032-H312-H332-H412, P:P261-P280-P302+P352-P304+P340-P322-P501a | 50g 250g 500g |
| | Application(s): A protein denaturant | |







| Stock # | Description | Size |
|---------------|--|----------------------------|
| A12024 | Guanine, 98% [2-Amino-6-hydroxypurine] [73-40-5], C ₅ H ₄ N ₆ O, F.W. 151.13, m.p. >300°, Merck 14,4564, EINECS 200-799-8, RTECS MF8260000, BRN 9680, MDL MFCD00071533, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 25g 100g 500g |
| | Guanine-2'-deoxyribose hydrate , see 2'-Deoxyguanosine hydrate, L14519, p. 178 | |
| A11328 | Guanosine, 98+% [118-00-3], C ₁₀ H ₁₃ N ₅ O ₅ , F.W. 283.24, m.p. ca 250° dec., [α] _D ²⁰ -72° (c=1.5 in 0.1N NaOH), Merck 14,4566, EINECS 204-227-8, RTECS MF8750000, BRN 625911, MDL MFCD00010182, † | 25g 50g 100g 250g |
| J61646 | Guanosine-5'-diphosphate disodium salt [GDP] [7415-69-2], C ₁₀ H ₁₃ N ₅ Na ₂ O ₁₁ P ₂ , F.W. 487.17, Powder, EINECS 231-026-2, MDL MFCD00084665 | 100mg 500mg |
| J61414 | Guanosine-5'-triphosphate disodium salt [GTP] [56001-37-7], C ₁₀ H ₁₄ N ₅ Na ₂ O ₁₄ P ₃ , F.W. 567.15, Powder, EINECS 259-940-7, BRN 4113439, MDL MFCD00083629 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 250mg 500mg 1g |
| J64285 | Guanylin, human [Pro-Gly-Thr-Cys-Glu-Ile-Cys-Ala-Tyr-Ala-Ala-Cys-Thr-Gly-Cys (disulfide bridges: Cys4-Cys12, Cys7-Cys15)] C ₆₈ H ₈₇ N ₁₅ O ₂₁ S ₄ , F.W. 1458.66, Solid | 1mg |
| J65417 | Guanylin, rat, mouse [Pro-Asn-Thr-Cys-Glu-Ile-Cys-Ala-Tyr-Ala-Ala-Cys-Thr-Gly-Cys (Disulfide bridge: Cys4-Cys12, Cys7-Cys15)] [144940-98-7], C ₆₀ H ₈₀ N ₁₅ O ₂₂ S ₄ , F.W. 1515.71, Solid | 1mg |
| | Gum arabic , see Acacia, 36499, p. 69 Gum karaya from sterculia tree , see Karaya Gum, J61844, p. 262 Gum tragacanth , see Tragacanth powder, A18502, p. 372 | |
| J61083 | Guvacine hydrochloride, 99+% [498-96-4], C ₈ H ₈ NO ₂ ·HCl, F.W. 163.60, Powder, Merck 14,4584, MDL MFCD00055191 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): GABA uptake inhibitor | 100mg |
| J65634 | GW 9662 [2-Chloro-5-nitro-N-phenylbenzamide] [22978-25-2], C ₁₃ H ₁₀ N ₂ O ₃ Cl, F.W. 276.68, Powder, MDL MFCD01215270 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10mg 50mg |
| | GW-786034 , see Pazopanib, 99+%, J62470, p. 312 | |
| J61697 | H-7 dihydrochloride [1-(5-Isoquinolinesulfonyl)-2-methylpiperazine dihydrochloride, Isoquinoline-5-sulfonic 2-methyl-1-piperazine dihydrochloride] [108930-17-2], C ₁₄ H ₁₇ N ₃ O ₂ ·2HCl, F.W. 364.29, Powder, m.p. 191-193°, BRN 5840763, MDL MFCD00036961 Application(s): Protein kinase inhibitor. Inhibits cyclic nucleotide dependent protein kinase (PKA) and protein kinase C | 10mg 50mg |
| J63638 | H-9 dihydrochloride [N-(2-Aminoethyl)-5-isoquinolinesulfonamide hydrochloride] [84468-17-7], C ₁₁ H ₁₃ N ₃ O ₂ ·2HCl, F.W. 324.22, Powder, MDL MFCD00069286 Application(s): Protein kinase inhibitor. Most effective for cAMP and cGMP dependent protein kinases | 10mg 50mg |
| | HA-1077 , see Fasudil, 98+%, J63525, p. 219 HA-1077 dihydrochloride , see Fasudil dihydrochloride, 99+%, J60594, p. 219 HA-1077 hydrochloride , see Fasudil monohydrochloride, 99+%, J60751, p. 219 HABA , see 2-(p-Hydroxyphenylazo)benzoic acid, A10333, p. 250 Haematin , see Hematin, A18518, p. 241 Haematoporphyrin dihydrochloride , see Hematoporphyrin dihydrochloride, A18579, p. 241 Haematoxylin , see Hematoxylin hydrate, A12431, p. 242 Haemin , see Hemin, A11165, p. 242 | |
| J63728 | Haloenol Lactone Suicide Substrate, 98+% [HELSS, Bromoenol lactone] [88070-98-8], C ₁₆ H ₁₃ BrO ₂ , F.W. 317.18, Powder, m.p. 103-106°, MDL MFCD00270871 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): Irreversibly inhibits calcium-independent phospholipase A-2 | 5mg 10mg 25mg |







| Stock # | Description | Size |
|---------------|--|---|
| J61688 | Haloperidol [52-86-8], C ₂₁ H ₂₈ ClFNO ₂ , F.W. 375.86, Powder, Merck 14,4598, UN2811, EINECS 200-155-6, RTECS EU1575000, MDL MFCD00051423  | 5g 25g |
| | H:H301-H360-H315-H319-H317-H335, P:P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Application(s): An antagonist for D2, D3, and D4 dopamine receptors that induces apoptosis of neurons in the striatum of rats | |
| J60543 | Hamburger Pentapeptide [Asp-Ser-Asp-Pro-Arg, IgE Peptide III] [62087-72-3], C ₂₂ H ₃₈ N ₈ O ₁₁ , F.W. 588.60, Lyophilized powder, Merck 14,7128, MDL MFCD00081022 | 25mg |
| | Application(s): Potent inhibitor of IgE formation | |
| J61699 | Harmaline, 98+% [1-Methyl-7-methoxy-3,4-dihydro-β-carboline, Dihydroharmine] [304-21-2], C ₁₃ H ₁₄ N ₂ O, F.W. 214.27, Crystals, m.p. 239-241°, Merck 14,4613, EINECS 206-152-6, RTECS UU9800000, BRN 207310, MDL MFCD00004955  | 1g 5g |
| | H:H302, P:P264-P270-P301+P312-P330-P501a | |
| | Application(s): CNS stimulant; may act through NMDA receptors. Reversible inhibitor of MAO-A | |
| L19068 | Harmine, 98+% [6-Methoxyharmine, 7-Methoxy-1-methyl-9H-pyrido[3,4-b]indole] [442-51-3], C ₁₃ H ₁₂ N ₂ O, F.W. 212.25, m.p. 262-266°, Merck 14,4616, EINECS 207-131-4, RTECS UV0175000, BRN 178813, MDL MFCD00004958   | 250mg 1g |
| | H:H302-H332-H319, P:P280h-P305+P351+P338 | |
| | Application(s): A monoamine oxidase inhibitor | |
| J61135 | Harmol [487-03-6], C ₁₂ H ₁₀ N ₂ O, F.W. 198.22, Powder, m.p. 231°, EINECS 207-645-9, MDL MFCD00834164 | 1g 5g |
| | Application(s): Induces apoptosis by Caspase-8 activation | |
| J63827 | Harmol hydrochloride dihydrate, 98% [1-Methyl-9H-pyrido-[3,4-b]indole-7-ol] [149022-16-2], C ₁₂ H ₁₀ N ₂ O.HCl.2H ₂ O, F.W. 270.72 (234.69anhy), Powder, MDL MFCD00150058 | 1g 5g |
| | Application(s): Induces apoptosis by Caspase-8 activation | |
| | Harnal , see Tamsulosin hydrochloride, 98+%, J61999, p. 357 HBTU , see O-(1H-Benzotriazol-1-yl)-N,N,N',N'-tetramethyluronium hexafluorophosphate, B23597, p. 120 | |
| J60507 | HDBA, 98+% [Lavendustin, 2-Hydroxy-5-(2,5-dihydroxybenzylamino)benzoic acid] [125697-93-0], C ₁₄ H ₁₃ N ₂ O ₅ , F.W. 275.26, Powder, BRN 6657779, MDL MFCD00153955  | 1mg 5mg 10mg |
| | H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): Inhibits calcium/calmodulin-dependent protein kinase II | |
| | Hebanil , see Chlorpromazine hydrochloride, 98+%, J63659, p. 160 | |
| J65734 | Helodermin C ₁₇₆ H ₂₈₈ N ₄₇ O ₄₉ , F.W. 3843.42, Solid | 0.5mg 1mg |
| J65020 | Helospectin II C ₁₈₀ H ₂₈₈ N ₄₆ O ₅₇ , F.W. 4008.48, Solid | 1mg |
| | HELSS , see Haloenol Lactone Suicide Substrate, 98+%, J63728, p. 240 | |
| A18518 | Hematin, 97% [Haematin] [15489-90-4], C ₃₄ H ₃₂ FeN ₄ O ₅ , F.W. 633.51, Merck 14,4635, EINECS 239-518-9, RTECS NO6725000, MDL MFCD00011615  | 1g 5g 25g |
| | Application(s): Stimulates synthesis of globulin | |
| A18579 | Hematoporphyrin dihydrochloride [Haematoporphyrin dihydrochloride] [17696-69-4], C ₃₄ H ₃₈ N ₄ O ₅ .2HCl, F.W. 671.62, Merck 14,4636, EINECS 241-699-4, RTECS TS5505000, BRN 78957, MDL MFCD00013470, †  | 1g 5g 25g |
| | H:H302, P:P264-P270-P301+P312-P330-P501a | |
| | Application(s): Endogenous porphyrin formed by the acid hydrolysis of hemoglobin  | |






| Stock # | Description | Size |
|---------|---|----------------------|
| A12431 | Hematoxylin hydrate, 96% (dry wt.), water ca 6% ▲ [C.I. 75290, Natural Black 1] [517-28-2], C ₁₆ H ₁₄ O ₅ ·xH ₂ O, F.W. 302.29(anhy), m.p. ca 200° dec., Merck 14,4637, EINECS 208-237-3, RTECS MH7875000, BRN 91399, MDL MFCD00078111, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Biological stain. Acid-base indicator: pH 5.0 - 6.0. | 5g 25g 100g |
| | Application(s): Extracted from the bark of the logwood tree | |
| | Hemimellitic acid dihydrate , see 1,2,3-Benzenetricarboxylic acid dihydrate, A17491, p. 119 | |
| A11165 | Hemin (porcine), 98+% [Haemin, Ferriprotoporphyrin IX chloride] [16009-13-5], C ₃₄ H ₃₂ ClFeN ₄ O ₄ , F.W. 651.95, m.p. >300°, Merck 14,4644, EINECS 240-140-1, RTECS LJ8080000, BRN 5229914, MDL MFCD00010726, † | 1g 5g 25g |
| | Application(s): Stimulates synthesis of globulin | |
| | Hemin chloride , see Hemin, A11165, p. 242 | |
| J63838 | Hemoglobin, bovine [9008-02-0], Powder, 64.5 kDa, MDL MFCD00131282, † | 5g 25g 100g |
| | Application(s): Iron-containing oxygen-transport metalloprotein in red blood cells | |
| J65288 | HEMOKININ 1, human [HEK-1, human, Thr-Gly-Lys-Ala-Ser-Gln-Phe-Phe-Gly-Leu-Met-NH2] [491851-53-7], C ₅₄ H ₈₂ N ₁₄ O ₁₄ S, F.W. 1183.38, Solid, MDL MFCD06656083 | 5mg 10mg |
| A16198 | Heparin sodium salt, from porcine intestinal mucosa, IU>=100/mg [9041-08-1], Merck 14,4653, RTECS MI0850000, MDL MFCD00081689, † | 250mg 1g 5g |
| | Application(s): Blood anti-coagulant | |
| J60443 | Heparin Binding Peptide [125720-21-0], C ₄₇ H ₇₄ N ₁₆ O ₁₀ , F.W. 1023.21, Solid, MDL MFCD00237001 | 1mg |
| A14777 | HEPES, 99% [4-(2-Hydroxyethyl)-1-piperazineethanesulfonic acid] [7365-45-9], C ₈ H ₁₈ N ₂ O ₃ S, F.W. 238.31, m.p. ca 236° dec., Merck 14,4654, EINECS 230-907-9, RTECS TL6809000, BRN 883043, MDL MFCD00006158, † Biological buffer, pKa = 7.55 at 20°: <i>Biochemistry</i> , 5, 467 (1966). | 10g 50g 250g |
| | Application(s): A zwitterionic buffer | |
| J61830 | HEPES hemisodium salt [4-(2-Hydroxyethyl)-1-piperazineethanesulfonic acid sodium salt] [103404-87-1], (C ₈ H ₁₇ N ₂ O ₃ S) ₂ Na, F.W. 497.58, Crystalline powder, MDL MFCD00036463 | 100g 250g 500g |
| | Application(s): A zwitterionic buffer | |
| A16516 | HEPES sodium salt, 99% ■ [4-(2-Hydroxyethyl)-1-piperazineethanesulfonic acid sodium salt] [75277-39-3], C ₈ H ₁₇ N ₂ NaO ₃ S, F.W. 260.28, EINECS 278-169-7, MDL MFCD00036463, † | 25g 100g |
| J60463 | HEPES, 0.5M buffer soln., pH 6.5 [7365-45-9], Liquid, † | 100ml 250ml |
| J60064 | HEPES, 0.5M buffer soln., pH 7.0 [7365-45-9], Liquid, † | 100ml 250ml |
| J61275 | HEPES, 0.5M buffer soln., pH 7.5 [7365-45-9], Liquid, † | 100ml 250ml |
| J61047 | HEPES, 0.5M buffer soln., pH 7.6 [7365-45-9], Liquid, † | 100ml 250ml |
| J63002 | HEPES, 0.5M buffer soln., pH 8.0 [7365-45-9], Liquid, † | 100ml 250ml |
| J63218 | HEPES, 0.5M buffer soln., pH 8.5 [7365-45-9], Liquid, † | 100ml 250ml |
| J63614 | HEPES, 0.5M buffer soln., pH 9.0 [7365-45-9], Liquid, † | 100ml 250ml |
| J61017 | HEPES, 1.0M buffer soln., pH 6.5 [7365-45-9], Liquid, † | 250ml 500ml |









| Stock # | Description | Size |
|---|--|-------------------|
| J62688 | HEPES, 1.0M buffer soln., pH 7.0 [7365-45-9], Liquid, † | 250ml 500ml |
| J60712 | HEPES, 1.0M buffer soln., pH 7.5 [7365-45-9], Liquid, † | 250ml 500ml |
| J63578 | HEPES, 1.0M buffer soln., pH 8.0 [7365-45-9], Liquid, † | 250ml 500ml |
| J61360 | HEPES, 1.0M buffer soln., pH 8.5 [7365-45-9], Liquid, † | 250ml 500ml |
| J60440 | HEPES, 1.0M buffer soln., pH 9.0 [7365-45-9], Liquid, † | 250ml 500ml |
| J61239 | HEPES-buffered saline, pH 6.5 (5X) [7365-45-9], Liquid, Note: Contains 125mM HEPES and 750mM sodium chloride, pH 6.5, † | 250ml 500ml |
| J62623 | HEPES-buffered saline, pH 7.0 (2X for transfection) [7365-45-9], Liquid, Note: Contains 280mM sodium chloride, 10mM potassium chloride, 1.5mM sodium phosphate, 12mM dextrose and 50mM HEPES, pH 7.0, † | 250ml 500ml |
| J60753 | HEPES-buffered saline, pH 7.0 (5X) [7365-45-9], Liquid, Note: Contains 125mM HEPES and 750mM sodium chloride, at pH 7.0, † | 250ml 500ml |
| J62915 | HEPES lysis buffer with NP-40 Liquid, Note: This buffer contains 50mM HEPES, 150mM NaCl, 1% NP-40 and 5mM EDTA at pH 7.4. | 250ml 500ml |
| J63867 | HEPES lysis buffer with NP-40 (2X) Liquid, Note: This buffer contains 100mM HEPES, 300mM NaCl, 2% NP-40 and 10mM EDTA at pH 7.4. | 125ml 250ml |
| J63860 | HEPES lysis buffer with Triton® X-100 Liquid, Note: This buffer contains 25mM HEPES, 150mM NaCl, 1% Triton X-100 and 5mM EDTA at pH 7.4. | 250ml 500ml |
| J62809 | HEPES lysis buffer with Triton® X-100 (2X) Liquid, Note: This buffer contains 50mM HEPES, 300mM NaCl, 2% Triton X-100 and 10mM EDTA at pH 7.4. | 125ml 250ml |
| J63297 | HEPES protein extraction buffer (5X) Liquid, Note: This buffer contains 250mM HEPES and 10% calcium chloride at pH 7.4. Add protease inhibitors according to your protocol. | 250ml 500ml |
| J63043 | HEPES-Triton® X-100 extraction buffer [7365-45-9], Liquid, Note: Contains 50mM HEPES (pH 7.4) and 10% Triton X-100. Add protease inhibitors according to your protocol., †  H: H318, P: P280-P305+P351+P338-P310 | 250ml 500ml |
| J63877 | HEPPSO, 0.2M buffer soln., pH 7.0 [68399-78-0], Liquid, † | 100ml 250ml |
| J61640 | HEPPSO, 0.2M buffer soln., pH 7.5 [68399-78-0], Liquid, † | 100ml 250ml |
| J62529 | HEPPSO, 0.2M buffer soln., pH 8.0 [68399-78-0], Liquid, † | 100ml 250ml |
| J60760 | HEPPSO, 0.2M buffer soln., pH 8.5 [68399-78-0], Liquid, † | 100ml 250ml |
| 1-Heptanesulfonic acid sodium salt , see Sodium 1-heptanesulfonate, A10917, p. 346 | | |
| J61806 | (R)-2-Heptanol [6033-24-5], C ₇ H ₁₆ O, F.W. 116.20, Liquid, f.p. 64°(147°F), BRN 1719090, MDL MFCD00065956 ! H: H312-H319, P: P280-P305+P351+P338-P302+P352-P322-P312-P501 Application(s): For synthesis of optically active products | 1g 5g |
| 33795 | (S)-(+)-2-Heptanol, 98% [6033-23-4], C ₇ H ₁₆ O, F.W. 116.20, Liquid, b.p. 160-162°, f.p. 59°(138°F), d. 0.815, n _D ²⁰ 1.4210, UN1987, MDL MFCD00065003  H: H226-H312-H319, P: P210-P241-P303+P361+P353-P305+P351+P338-P302+P352-P501a  | 250mg 1g 5g |
| Hesperetin 7-rhamnoglucoside , see Hesperidin, 98+%, J62126, p. 244 | | |


| Stock # | Description | Size |
|---------|---|---------------------|
| J62126 | Hesperidin, 98+% [Hesperetin 7-rhamnoglucoside, Hesperitin-7-rutinoside] [520-26-3], C ₂₈ H ₃₆ O ₁₅ , F.W. 610.56, Powder, m.p. 250-255° dec., Merck 14,4671, EINECS 208-288-1, RTECS MK6650000, BRN 75140, MDL MFCD00075663, † | 25g 100g |
| | Application(s): Acts as an antioxidant | |
| | Hesperetin, see 3',5',7-Trihydroxy-4'-methoxyflavanone, B20528, p. 377 Hesperitin-7-rutinoside, see Hesperidin, 98+%, J62126, p. 244 Heterauxin, see Indole-3-acetic acid, A10556, p. 256 | |
| J60853 | 1,2,3,4,5,6-Hexabromocyclohexane [NSC 7908, Benzene hexabromide] [1837-91-8], C ₆ H ₆ Br ₆ , F.W. 557.50, Solid, MDL MFCD00059127, † | 1g 5g |
| | Application(s): Potently and directly inhibits JAK2 tyrosine kinase autophosphorylation Hexadecanoic acid, see Palmitic acid, B20322, p. 311 | |
| A11180 | 1-Hexadecanol, 98% [Cetyl alcohol, n-Hexadecyl alcohol] [36653-82-4], CH ₃ (CH ₂) ₁₅ OH, F.W. 242.45, m.p. 47-51°, b.p. 190°/15mm, f.p. 135°(275°F), d. 0.817, Merck 14,2028, Solubility: Soluble in alcohol, chloroform, ether, EINECS 253-149-0, RTECS MM0225000, BRN 1748475, MDL MFCD00004760, † | 500g 2.5kg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | n-Hexadecyl alcohol, see 1-Hexadecanol, A11180, p. 244 | |
| A13499 | (1-Hexadecyl)pyridinium chloride monohydrate, 98% [Cetylpyridinium chloride monohydrate] [6004-24-6], C ₂₁ H ₃₆ ClN.H ₂ O, F.W. 358.02 (339.99anhy), m.p. 83-86°, Merck 14,2032, Solubility: Soluble in water, alcohol, chloroform, UN2811, EINECS 204-593-9, RTECS UU5075000, BRN 3578606, MDL MFCD00149977, † | 25g 100g 500g |
| | ! H:H301-H330-H400-H410-H315-H319-H335, P:P301+P310-P304+P340-P305+P351+P338-P320-P330-P405-P501a Catalyst, used in combination with tungstophosphoric acid for the chemoselective oxidation of anilines to nitroso- or nitrobenzenes by hydrogen peroxide: <i>J. Org. Chem.</i> , 58, 3633 (1993). | |
| |  | |
| A15235 | (1-Hexadecyl)trimethylammonium bromide, 98% ■ [Cetrimonium bromide, Cetyltrimethylammonium bromide] [57-09-0], CH ₃ (CH ₂) ₁₅ N(CH ₃) ₃ Br, F.W. 364.46, m.p. ca 245° dec., Merck 14,2025, Fieser 15,77, UN3077, EINECS 200-311-3, RTECS BQ7875000, BRN 3598189, MDL MFCD00011772, † | 100g 500g 5kg |
| | ! H:H318-H400-H410-H302-H335-H315, P:P280-P273-P305+P351+P338-P337+P313-P391-P501a Surfactant-type catalyst with many applications: O-Alkylation of alcohols and phenols; see 2,6-Dimethylphenol, A11947. Surfactant-assisted permanganate oxidations: <i>Can. J. Chem.</i> , 67, 1381 (1989). Reduction of alkyl halides to alkanes using zinc powder in micelles: <i>Synth. Commun.</i> , 19, 1649 (1989). Control of ortho-para ratio in the bromination of anilines: <i>Tetrahedron Lett.</i> , 30, 6209 (1989). Also facilitates ligand-free palladium salt-catalyzed Heck and Suzuki cross-coupling reactions in water: <i>Tetrahedron Lett.</i> , 46, 3357 (2005). | |
| | Hexa-2,4-dienoic acid, see Sorbic acid, A16196, p. 349 2,2',3,3',3'-Hexahydroxy-2,2'-biindan-1,1'-dione, see Hydrindantin dihydrate, A12462, p. 247 Hexahydroxycyclohexane, see myo-Inositol, A13586, p. 257 4,4',5,5',7,7'-Hexahydroxy-2,2'-dimethylnaphthodianthrone, see Hypericin, H26425, p. 253 4,4',5,5',6,6'-Hexahydroxydiphenic acid 2,6,2',6'-dilactone hydrate, see Ellagic acid hydrate, A15722, p. 205 | |
| J60466 | Hexamethonium bromide, 98+% [Hexane-1,6-bis(trimethylammonium bromide), N,N,N,N',N',N'-Hexamethylhexamethylenediammonium dibromide] [55-97-0], (CH ₃) ₃ N(Br)(CH ₂) ₆ N(CH ₃) ₃ , F.W. 362.19, Powder, m.p. 282-285° dec., Merck 14,4688, EINECS 200-249-7, RTECS BQ8575000, BRN 3715749, MDL MFCD00011787, † | 25g 100g |
| | Application(s): Nicotinic acetyl choline receptor antagonist N,N'-Hexamethylenebis(acetamide), see N,N'-Diacetyl-1,6-diaminohexane, B22771, p. 182 | |
| 36462 | Hexamethylenetetramine, ACS, 99+% ■ [Hexamine, Methenamine] [100-97-0], C ₆ H ₁₂ N ₄ , F.W. 140.19, Solid, m.p. 280° subl., f.p. 250°(482°F), d. 1.33, Merck 14,5966, Fieser 1,427 2,208 4,243 9,234 18,178 19,164 20,185, UN1328, EINECS 202-905-8, RTECS MN4725000, BRN 2018, MDL MFCD00006895, † | 100g 500g 2kg |
| | Maximum level of impurities: Loss on drying 2.0%, Residue after ignition 0.1%, Heavy Metals (as Pb) 0.001% ! H:H228-H317, P:P210-P241-P261-P302+P352-P321-P501a | |
| | N,N,N,N',N',N'-Hexamethylhexamethylenediammonium dibromide, see Hexamethonium bromide, 98+%, J60466, p. 244 Hexamethylparosaniline chloride, see Crystal Violet, 22866, p. 170 2,6,10,15,19,23-Hexamethyl-2,6,10,14,18,22-tetracosahexaene, see Squalene, B20944, p. 351 | |
| H25929 | Hexanamide, 99% [Caproamide] [628-02-4], CH ₃ (CH ₂) ₄ CONH ₂ , F.W. 115.18, m.p. 100-102°, EINECS 211-024-8, RTECS MN7875000, MDL MFCD00008046, † | 1g 5g |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Hexane-1,6-bis(trimethylammonium bromide), see Hexamethonium bromide, 98+%, J60466, p. 244 Hexanedioic acid, see Adipic acid, A13705, p. 79 Hexanedioic acid dimethyl ester, see Dimethyl adipate, B21174, p. 196 Hexanedioyl dichloride, see Adipoyl chloride, A13168, p. 80 | |


| Stock # | Description | Size |
|---------|--|--------------------------|
| L10401 | (S)-(+)-2-Hexanol, 98% [52019-78-0], C ₆ H ₁₄ O, F.W. 102.18, b.p. 137-138°, f.p. 45° (113°F), d. 0.818, n _D ²⁰ 1.4140, [α] _D ²⁰ +10.5° (neat), UN2282, BRN 1718997, MDL MFCD00065955  H:H226-H302, P:P261-P280f | 250mg 1g |
| J60889 | Hexestrol, 98+% [4,4'-(1,2-Diethylethylene)diphenol, meso-3,4-Bis(4-hydroxyphenyl)hexane] [84-16-2], C ₁₈ H ₂₂ O ₂ , F.W. 270.37, Powder, m.p. 186°, Merck 14,4701, EINECS 201-518-1, RTECS SL0560850, BRN 3209460, MDL MFCD00068996 H:H350, P:P281-P201-P202-P308+P313-P405-P501 Application(s): Nonsteroidal synthetic estrogen | 1g 10g |
| J63795 | Hexokinase, yeast ■ [9001-51-8], Lyophilized powder, EINECS 232-611-5, MDL MFCD00131321, Note: Minimum 140 units/mg protein. One unit converts 1 micromole of D-glucose to glucose-6-phosphate per min at 25 degrees C and pH 7.5 in the presence of ATP, † H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 Application(s): Catalyzes the phosphorylation of D-hexose sugars at the C6 position utilizing ATP as a phosphate source. Used to determine glucose, fructose, mannose and ATP | 1kilounit 10kilounits |
| L13597 | 1-n-Hexyl-3,7-dimethylxanthine, see 1-n-Hexyltheobromine, L13597, p. 245 | |
| L13597 | 1-n-Hexyltheobromine, 98+% [1-Hexyl-3,7-dimethylxanthine, Pentifylline] [1028-33-7], C ₁₈ H ₂₈ N ₂ O ₂ , F.W. 264.33, m.p. 80-81°, Merck 14,7127, EINECS 213-842-0, RTECS UO8450000, BRN 270632, MDL MFCD00041424 H:H302, P:P264-P270-P301+P312-P330-P501a Application(s): A vasodilator | 250mg 1g |
| | 5-HIAA, see 5-Hydroxyindole-3-acetic acid, 98%, J61435, p. 249 Highlink® GB, see N,N'-(1,2-Dihydroxyethylene)bisacrylamide, L19211, p. 192 | |
| A12690 | Hippuric acid, 98% [N-Benzoylglycine] [495-69-2], C ₉ H ₉ CONHCH ₂ CO ₂ H, F.W. 179.18, m.p. 188-191°, d. 1.371, Merck 14,4716, Fieser 1,432, EINECS 207-806-3, RTECS MR8150000, BRN 1073987, MDL MFCD00002692, † Condensation with aldehydes gives azlactones, which are intermediates in a classical route to amino acids; see, e.g.: <i>Org. Synth. Coll.</i> , 2, 489 (1943). An alternative approach involves alkylation of the trianion of hippuric acid, prepared by LDA/TMEDA in THF: <i>Tetrahedron Lett.</i> , 2205 (1976). For cyclization with acetic anhydride to 2-phenyl-5-oxazolone, see: <i>Org. Synth. Coll.</i> , 5, 946 (1973). | 100g 500g 1kg |
| | Hismanal, see Astemizole, 99+%, J60339, p. 111 | |
| J61727 | Histamine [51-45-6], C ₄ H ₉ N ₃ , F.W. 111.15, Powder, Merck 14,4719, UN2811, EINECS 200-100-6, RTECS MS1050000, BRN 2012, MDL MFCD00005210, † H:H301-H334-H315-H319-H317-H335, P:P285-P301+P310-P305+P351+P338-P302+P352-P405-P501a Application(s): Endogenous H1 and H2 histamine receptor agonist; H1 activation mobilizes calcium; H2 activation stimulates adenylate cyclase activity in neurons; activates nitric oxide synthetase; potent vasodilator | 1g 5g |
| L09198 | Histamine dihydrochloride, 98+% [56-92-8], C ₄ H ₉ N ₃ ·2HCl, F.W. 184.07, m.p. 245-249°, Merck 14,4719, EINECS 200-298-4, RTECS MS1575000, BRN 3624116, MDL MFCD00012703, † H:H334-H335-H315-H319-H317, P:P285-P305+P351+P338-P302+P352-P321-P405-P501a | 5g 25g |
| J61088 | Histamine diphosphate, 99+% [51-74-1], C ₄ H ₉ N ₃ ·2H ₃ PO ₄ , F.W. 307.14, Powder, Merck 14,4719, EINECS 200-118-4, RTECS NI5425000, † H:H302-H315-H318-H334-H317-H335, P:P285-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): Endogenous H1 and H2 agonist | 5g 25g |
| J64792 | Histatin 5 [Asp-Ser-His-Ala-Lys-Arg-His-His-Gly-Tyr-Lys-Arg-Lys-Phe-His-Glu-Lys-His-His-Ser-His-Arg-Gly-Tyr] [104339-66-4], C ₁₃₈ H ₁₉₅ N ₅₁ O ₃₃ , F.W. 3036.29, Solid, MDL MFCD00210682 | 0.5mg 1mg |
| B21027 | D-Histidine, 99% [(R)-2-Amino-3-(4-imidazolyl)propionic acid, H-D-His-OH] [351-50-8], C ₆ H ₉ N ₃ O ₂ , F.W. 155.16, m.p. ca 285° dec., [α] _D ²⁰ +39° (c=5 in water), EINECS 206-513-8, BRN 84089, MDL MFCD00065963, †  | 5g 25g 100g |
| A10413 | L-Histidine, 98+% [(S)-2-Amino-3-(4-imidazolyl)propionic acid, H-His-OH] [71-00-1], C ₆ H ₉ N ₃ O ₂ , F.W. 155.16, m.p. ca 281° dec., [α] _D ²⁰ -39° (c=5 in water), Merck 14,4720, EINECS 200-745-3, RTECS MS3070000, BRN 4673585, MDL MFCD00064315, †  | 25g 100g 500g |









| Stock # | Description | Size |
|---------|---|---|
| J63065 | L-Histidine, Cell Culture Reagent [L-2-Amino-3-(4-imidazolyl)propionic acid] [71-00-1], C ₈ H ₉ N ₃ O ₂ , F.W. 155.16, Powder, m.p. ca 281° dec., Merck 14,4720, EINECS 200-745-3, RTECS MS3070000, BRN 84088, MDL MFCD00064315, † | 10g 100g 500g 1kg |
| A16165 | DL-Histidine monohydrochloride monohydrate, 99% [H-DL-His-OH.HCl.H ₂ O] [123333-71-1], C ₈ H ₉ N ₃ O ₂ ·HCl·H ₂ O, F.W. 209.63 (191.62anhy), m.p. ca 250° dec., MDL MFCD00151028, † |  5g 25g 100g |
| A17627 | L-Histidine monohydrochloride monohydrate, 99% [H-His-OH.HCl.H ₂ O] [5934-29-2], C ₈ H ₉ N ₃ O ₂ ·HCl·H ₂ O, F.W. 209.63 (191.62anhy), m.p. ca 240° dec., [α] _D ²⁰ +9.3° (c=5 in 5N HCl), Merck 14,4720, EINECS 211-438-9, RTECS MS3119000, BRN 4168261, MDL MFCD00151027, † |  50g 250g 500g |
| J61465 | L-Histidine monohydrochloride monohydrate, Cell Culture Reagent [L-2-Amino-3-(4-imidazolyl)propionic acid monohydrochloride monohydrate] [5934-29-2], C ₈ H ₉ N ₃ O ₂ ·HCl·H ₂ O, F.W. 209.63 (191.62anhy), Powder, m.p. ca 240° dec., Merck 14,4720, EINECS 211-438-9, RTECS MS3119000, BRN 4168261, MDL MFCD00151027 | 10g 100g 500g 1kg |
| J65939 | Histone Acetyltransferase Inhibitor IV, CPTH2 ▲ [HAT Inhibitor IV, Gcn5p Inhibitor] [357649-93-5], C ₁₄ H ₁₄ ClN ₃ S, F.W. 291.80, Solid, MDL MFCD02307488 | 5mg 10mg |
| J65479 | Histone Deacetylase Inhibitor II ▲ [m-Carboxy cinnamic acid bis-hydroxamide, CBHA] [174664-65-4], C ₁₀ H ₁₀ N ₂ O ₄ , F.W. 222.20, Powder ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5mg 10mg |
| J64940 | Histone Deacetylase Inhibitor III ▲ [M 344, 4-Dimethylamino-N-(6-hydroxycarbamoylhexyl) benzamide] [251456-60-7], C ₁₆ H ₂₅ N ₃ O ₃ , F.W. 307.39, Powder, MDL MFCD03453554 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5mg 10mg |
| | HL-725 , see Trequinsin hydrochloride, 98+%, J63999, p. 374 H M P resin , see Wang resin, L17028, p. 393 | |
| J64917 | HNHA ▲ [Histone Deacetylase Inhibitor VI] [926908-04-5], C ₁₇ H ₂₁ NO ₂ S, F.W. 303.42, Crystalline solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10mg |
| | HNMPA , see (Hydroxy-2-naphthylmethyl)phosphonic acid, 98%, J63913, p. 250 Hoechst 33342® , see bis-Benzimide H-33342 trihydrochloride trihydrate, 98%, J62134, p. 126 Homidium bromide , see Ethidium bromide soln., 10mg/ml, J62282, p. 214 | |
| H31749 | DL-β-Homoproline hydrochloride, 97% [71985-79-0], C ₆ H ₁₂ ClNO ₂ , F.W. 165.62, m.p. 171-174° |  250mg 1g |
| | Homoprotocatechuic acid , see 3,4-Dihydroxyphenylacetic acid, A15893, p. 193 | |
| A12441 | Homovanillic acid, 98+% [4-Hydroxy-3-methoxyphenylacetic acid] [306-08-1], C ₉ H ₁₀ O ₄ , F.W. 182.18, m.p. 140-145°, Merck 14,4740, EINECS 206-176-7, BRN 2213447, MDL MFCD00004350, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Reagent for the determination of enzymes: <i>Anal. Chem.</i> , 40 , 190 (1968), and amino acids: <i>Anal. Biochem.</i> , 26 , 1 (1968). Application(s): Fluorimetric reagent and major catecholamine metabolite |  1g 5g 25g |
| J63434 | Honokiol, 98+% [5,3'-Diallyl-2,4'-dihydroxybiphenyl] [35354-74-6], C ₁₈ H ₁₈ O ₂ , F.W. 266.34, Powder, m.p. 86°, Merck 14,4742, UN3077, MDL MFCD00016674  H:H318-H411, P:P280-P273-P305+P351+P338-P310-P391-P501a Application(s): Induces apoptosis in human squamous lung cancer cells | 10mg 25mg 100mg |
| J61851 | Horse serum Liquid, Note: 10% Horse serum, 0.02% sodium azide in PBS | 100ml 250ml |
| | HOSu , see N-Hydroxysuccinimide, A10312, p. 251 3-HPA HCl , see 1-(3-Methoxyphenyl)homopiperazine monohydrochloride, H51751, p. 285 4-HPA HCl , see 1-(4-Methoxyphenyl)homopiperazine monohydrochloride, H51703, p. 285 HRP , see Peroxidase, horseradish, J60026, p. 314 5-HT , see Serotonin hydrochloride, B21263, p. 342 HTF bovine native protein , see Transferrin (HOLO), bovine plasma, 98+%, J61046, p. 373 5-HTP , see L-5-Hydroxytryptophan hydrate, A13954, p. 252 Human C carcinoma , see Calcitonin, human, 97+%, J63192, p. 142 | |






| Stock # | Description | Size |
|---------|--|---|
| J65512 | Human Epidermal Growth Factor Enzyme Immunoassay Kit Note: One kit contains sufficient reagents and precoated 96-well strips to perform an ELISA assay for EGF Application(s): For detection of Epidermal Growth factor. Detection range is 0.5-100ng/ml | 1kit |
| J60566 | Hyaluronic acid, bovine vitreous humor [9004-61-9], (C ₁₄ H ₂₁ NaO ₁₁) _n , Lyophilized powder, Merck 14,4757, EINECS 232-678-0, † Application(s): A natural high-viscosity polymer of acetylglucosamine and glucuronic acid | 10mg 50mg 100mg |
| J64856 | Hybridoma Cell Growth Supplement | 2x25ml |
| J60455 | Hybridization solution in SSC Liquid, Note: 6X Saline-sodium citrate (SSC) with 5% Blotto, pH 7.0 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): For hybridization of probes to nucleic acids | 100ml 250ml |
| J61559 | Hybridization solution in SSPE Liquid, Note: Contains 6X saline-sodium phosphate-EDTA (SSPE) and 5% Blotto. Application(s): For hybridization of probes to nucleic acids | 100ml 250ml |
| A12486 | Hydantoin, 99% [2,4-Imidazolidinedione] [461-72-3], C ₄ H ₈ N ₂ O ₂ , F.W. 100.08, m.p. 221-223°, Merck 14,4761, EINECS 207-313-3, RTECS MT8210000, BRN 110598, MDL MFCD00005259, † |  100g 500g 2.5kg |
| | Hydralazine hydrochloride , see 1-Hydrazinophthalazine hydrochloride, B22995, p. 247 Hydramycin , see Doxycycline hyclate, J60579, p. 202 | |
| 40120 | Hydrazine sulfate, ACS, 99.0% min [10034-93-2], H ₂ NNH ₂ ·H ₂ SO ₄ , F.W. 130.12, Crystalline, m.p. ca 255° dec., d. 1.370, Merck 14,4772, Fieser 1,445, UN3288, EINECS 233-110-4, RTECS MV9625000, MDL MFCD00044873, Note: Special handling precautions required. View MSDS prior to purchase. MSDS are available online at www.alfa.com, † Maximum level of impurities: Insoluble matter 0.005%, Residue after ignition 0.05%, Cl 0.005%, Heavy Metals (as Pb) 0.002%, Fe 0.001%  H:H301-H311-H331-H350-H400-H410-H317, P:P301+P310-P361-P302+P352-P321-P405-P501a | 500g |
| B22995 | 1-Hydrazinophthalazine hydrochloride, 98% [Hydralazine hydrochloride, 1(2H)-Phthalazinone hydrazone] [304-20-1], C ₈ H ₈ N ₄ ·HCl, F.W. 196.64, m.p. ca 275° dec., Merck 14,4763, UN2811, EINECS 206-151-0, RTECS TH9000000, BRN 3568329, MDL MFCD00135998, †  H:H301-H351-H361, P:P281-P301+P310-P321-P308+P313-P405-P501a |  5g 25g |
| | Application(s): A monoamine oxidase inhibitor | |
| A12462 | Hydrindantin dihydrate, 98% [2,2',3,3',3'-Hexahydroxy-2,2'-biindan-1,1'-dione] [5950-69-6], C ₁₈ H ₁₀ O ₆ ·2H ₂ O, F.W. 358.30 (322.27anhy), m.p. ca 250° dec., Merck 14,4775, EINECS 227-713-1, RTECS DU2989000, BRN 1895666, MDL MFCD00149242, † Reagent for photometric determination of amino acids. |  25g 100g 500g |
| | Application(s): Used in amino acid determinations as a ninhydrin synergist | |
| 35640 | Hydrochloric acid, 1.0N Standardized Solution [7647-01-0], HCl, F.W. 36.46, Liquid, EINECS 231-595-7, RTECS MW4025000, MDL MFCD00011324, † | 1L 4L 20L |
| 33257 | Hydrochloric acid, ACS, HCl 36.5-38.0% [Muratic acid] [7647-01-0], HCl, F.W. 36.46, Liquid, b.p. 81.5-110°, d. 1.19, Merck 14,4780, Fieser 1,308 2,215 4,250 5,322 6,283 7,172 8,246 9,239, Solubility: Soluble in water, alcohol, ether and benzene, UN1789, EINECS 231-595-7, RTECS MW4025000, MDL MFCD00011324, Note: Free from suspended matter or sediment, † Maximum level of impurities: Color (APHA) 10, Residue after ignition 5ppm, Br 0.005%, SO ₄ 1ppm, SO ₃ 1ppm, Extractable organic substances 5ppm, Free chlorine (Cl) 1ppm, NH ₄ 3ppm, As 0.01ppm, Heavy Metals (as Pb) 1ppm, Fe 0.2ppm  ! H:H314-H335, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 6lb 6x6lb |
| | Application(s): Acidizing petroleum wells, chemical intermediate, ore reduction, food processing, pickling and metal cleaning, general cleaning, and laboratory reagent | |
| B22093 | Hydrochlorothiazide, 98% [6-Chloro-7-sulfamyl-3,4-dihydro-1,2,4-benzothiadiazine-1,1-dioxide] [58-93-5], C ₇ H ₈ ClN ₂ O ₄ S ₂ , F.W. 297.74, m.p. 266-272°, Merck 14,4781, EINECS 200-403-3, RTECS DK9100000, BRN 625101, MDL MFCD00051765, † ! H:H302, P:P264-P270-P301+P312-P330-P501a |  5g 25g 100g |
| | Application(s): A carbonic anhydrase inhibitor | |

| Stock # | Description | Size |
|---|--|--------------------|
| A16292 | Hydrocortisone, 98% [50-23-7], C ₂₁ H ₃₀ O ₅ , F.W. 362.47, m.p. 213-215°, Merck 14,4787, EINECS 200-020-1, RTECS GM8925000, BRN 1354819, MDL MFCD00011654, † H:H361, P:P281-P201-P202-P308+P313-P405-P501a | 1g 5g |
| Application(s): A natural corticosteroid and anti-inflammatory compound | | |
| A18089 | Hydrocortisone acetate, 97+% ▲ [50-03-3], C ₂₃ H ₃₂ O ₆ , F.W. 404.51, m.p. ca 220° dec., Merck 14,4787, EINECS 200-004-4, RTECS GM8960000, BRN 2066841, MDL MFCD00037714 H:H361, P:P281-P201-P202-P308+P313-P405-P501a | 1g 5g |
| A11411 | Hydroquinone, 99% [1,4-Dihydroxybenzene, Quinol] [123-31-9], C ₆ H ₄ O ₂ , F.W. 110.11, m.p. 170-172°, b.p. 285-287°, f.p. 165°(329°F), d. 1.320, Merck 14,4808, Fieser 5,341, UN3077, EINECS 204-617-8, RTECS MX3500000, BRN 605970, MDL MFCD00002339, † H:H318-H341-H351-H400-H302-H317, P:P280-P273-P305+P351+P338 Widely used as a radical trap to inhibit polymerization and peroxidation reactions. Forms inclusion compounds (clathrates) with three molecules of hydroquinone held together by H bonds to form a cage in which a single guest molecule can be accommodated. For a review, see: D. D. MacNicol in <i>Inclusion Compounds</i> , Vol. 2, J. L. Atwood <i>et al</i> , Eds., Academic Press, London (1984), p1. A stable 1:1 complex with hydrazine has been isolated and found to be a useful, safer replacement for anhydrous hydrazine, e.g. in the solid state reaction with esters to give hydrazides: <i>J. Chem. Soc., Chem. Commun.</i> , 1531 (1995). | 250g 1kg 5kg |
| Hydroquinone-glucose , see Arbutin, L14945, p. 109 (S)-(-)-Hydrosuccinic acid , see L-(-)-Malic acid, 99%, J63221, p. 276 4'-Hydroxyacetanilide , see 4-Acetamidophenol, A11240, p. 70 Hydroxyacetic acid , see Glycolic acid, A12511, p. 237 5-Hydroxyanthranilic acid , see 2-Amino-5-hydroxybenzoic acid, L08256, p. 95 2-Hydroxybenzaldehyde , see Salicylaldehyde, A13833, p. 340 2-Hydroxybenzoic acid , see Salicylic acid, 30782, p. 340 2-Hydroxybenzoic acid sodium salt , see Sodium salicylate, A17056, p. 348 4-Hydroxybenzoic acid ethyl ester , see Ethyl 4-hydroxybenzoate, A13172, p. 216 | | |
| A14410 | 2-Hydroxybenzyl alcohol, 99% [Salicyl alcohol, Saligenin] [90-01-7], C ₇ H ₈ O ₂ , F.W. 124.14, m.p. 83-87°, Merck 14,8325, EINECS 201-960-5, RTECS DO6430000, BRN 1907195, MDL MFCD00004617, † H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 50g 250g 1kg |
| Application(s): Acts as a local anesthetic | | |
| L04651 | 4-Hydroxybenzylidenemalononitrile, 98% [3785-90-8], C ₁₀ H ₈ N ₂ O, F.W. 170.17, m.p. 187-190°, UN3439, EINECS 223-253-0, RTECS OO4200000, BRN 2209079, MDL MFCD00020189 H:H302-H312-H332-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 10g 50g |
| Application(s): Inhibitor of transducin GTPase activity | | |
| J61434 | 5-Hydroxydecanoic acid sodium salt, 98% [Sodium 5-hydroxydecanoate] [624-00-0], C ₁₀ H ₁₉ NaO ₃ , F.W. 210.25, Powder, MDL MFCD00153808 | 100mg 500mg |
| Application(s): A potassium channel antagonist which blocks the postschismic effects of the potassium channel activator cromakalim | | |
| J64095 | 4'-Hydroxydiclofenac [[2-(2,6-Dichloro-4-hydroxy-phenylamino)phenyl]acetic acid, 4'-OHD] [64118-84-9], C ₁₄ H ₁₁ Cl ₂ NO ₃ , F.W. 312.15, Powder, UN2811, RTECS AG6542800, BRN 4198042, MDL MFCD01671980 H:H301-H315-H318-H335-H410, P:P301+P310-P305+P351+P338-P302+P352-P321-P405-P501 | 5mg |
| Application(s): Selective agonist for D3 dopamine | | |
| J61065 | 2-Hydroxy-5-(2,5-dihydroxybenzylamino)benzoic acid , see HDBA, 98+%, J60507, p. 241 (±)-7-Hydroxy-2-di-n-propylaminotetralin hydrobromide [7-Hydroxy-DPAT hydrobromide] [74938-11-7], C ₁₆ H ₂₅ NO·HBr, F.W. 329.29, Powder, m.p. 168-170°, MDL MFCD00153809 | 10mg 50mg |
| Application(s): Selective agonist for D3 dopamine | | |
| 7-Hydroxy-DPAT hydrobromide , see (+/-)-7-Hydroxy-2-di-n-propylaminotetralin hydrobromide, J61065, p. 248 20-Hydroxyecdysone , see Ecdysterone, J63091, p. 204 2-Hydroxyethanesulfonic acid sodium salt , see Isethionic acid sodium salt, A12054, p. 260 2-Hydroxyethanethiol , see 2-Mercaptoethanol, A15890, p. 281 2-Hydroxyethylamine , see Ethanolamine, A11697, p. 213 2-Hydroxyethyl ether , see Diethylene glycol, A14728, p. 189 3-(2-Hydroxyethyl)indole , see Tryptophol, L02555, p. 385 | | |



| Stock # | Description | Size |
|---------|---|------------------------------------|
| | 4-(2-Hydroxyethyl)-1-piperazineethanesulfonic acid , see HEPES, A14777, p. 242 4-(2-Hydroxyethyl)-1-piperazineethanesulfonic acid sodium salt , see HEPES hemisodium salt, J61830, p. 242 | |
| J62548 | (R)-2-(1-Hydroxyethyl)pyridine [27911-63-3], C ₇ H ₉ NO, F.W. 123.16, Solid, MDL MFCD04972322 ! H: H302-H315-H318-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| | Application(s): For synthesis of optically active products | |
| J60980 | (S)-2-(1-Hydroxyethyl)pyridine [59042-90-9], C ₇ H ₉ NO, F.W. 123.16, Solid, MDL MFCD06795465 ! H: H302-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| | Application(s): For synthesis of optically active products | |
| | (2-Hydroxyethyl)trimethylammonium chloride , see Choline chloride, A15828, p. 161 | |
| B25016 | 6-Hydroxyflavone, 98% [6665-83-4], C ₁₅ H ₁₀ O ₅ , F.W. 238.25, m.p. 234-236°, EINECS 229-704-8, BRN 15827, MDL MFCD00017329 ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 1g 5g 25g |
| |  | |
| J61354 | Hydroxyguanidine sulfate [6345-29-5], CH ₅ N ₃ O 0.5H ₂ SO ₄ , F.W. 124.11, Crystals, m.p. 132-134° dec., EINECS 228-749-0, MDL MFCD00042033, † | 50mg |
| | Application(s): Reacts with nitric oxide forming an adduct which is a potent and stable vasodilator | |
| | 5-Hydroxy-2-(hydroxymethyl)-4H-pyran-4-one , see Kojic acid, A10760, p. 264 | |
| J61435 | 5-Hydroxyindole-3-acetic acid, 98% ▲ [5-HIAA] [54-16-0], C ₁₀ H ₉ NO ₃ , F.W. 191.19, Crystalline powder, m.p. 161-164° dec., EINECS 200-195-4, RTECS NL3650000, BRN 168797, MDL MFCD00005639 | 500mg 1g |
| | Application(s): Metabolite of melatonin | |
| | N-[4-[1-Hydroxy-2-(isopropylamino)ethyl]phenyl]methanesulfonamide hydrochloride , see Sotalol hydrochloride, 98%, J63772, p. 350 | |
| A15398 | Hydroxylamine hydrochloride, 99% ■ [Hydroxylammonium chloride] [5470-11-1], NH ₂ OH·HCl, F.W. 69.49, m.p. 152° dec., d. 1.67 ¹⁷ , Merck 14,4828, Fieser 1,478 2,217 7,176 9,245 11,257 15,170 18,186 21,222, UN2923, EINECS 226-798-2, RTECS NC3675000, BRN 3539763, MDL MFCD00051089, † ! H: H351-H373-H290-H400-H302-H312-H317-H315-H319, P: P280h-P273-P406 | 100g 250g 500g 1kg 5kg |
| | For examples of preparation of oximes from carbonyl compounds, see: <i>Org. Synth. Coll.</i> , 2 , 70, 313 (1955); 7 , 149 (1990). Dehydration of aldoximes is a valuable route to nitriles. The preparation of an oxime, and dehydration with acetic anhydride, are exemplified for veratraldehyde: <i>Org. Synth. Coll.</i> , 2 , 622 (1943). For other methods of dehydrating oximes to nitriles, see Benzaldoxime, A12053 . Procedures for the one-pot conversion of aldehydes to nitriles, without isolation of the intermediate oxime, include: refluxing the aldehyde with hydroxylamine hydrochloride in formic acid/ sodium acetate: <i>J. Chem. Soc.</i> , 1564 (1965); formic acid alone: <i>Synthesis</i> , 112 (1979); in pyridine and toluene, with azeotropic water removal: <i>Synthesis</i> , 190 (1982); in DMF (reflux; aromatics only): <i>Z. Chem.</i> , 15 , 302 (1975); heating in NMP at 110-115°, effective for aromatic and aliphatic substrates; under these conditions, DMF gave only 20-30% conversion: <i>Synthesis</i> , 586 (1999). A more recent ambient temperature one-pot procedure utilizes DBU in combination with ethyl dichlorophosphate: <i>Synlett</i> , 1317 (2007). For a one-pot synthesis of pyrazoles from aldehydes by cyclization of the intermediate oxime in acidic medium with potassium dihydrogen phosphate, see: <i>Tetrahedron Lett.</i> , 47 , 43 (2006). For a brief feature on uses of this reagent in Organic synthesis, see: <i>Synlett</i> , 1326 (2007). | |
| | Application(s): A monoamine oxidase inhibitor | |
| 36416 | Hydroxylamine hydrochloride, ACS, 96+% ■ [Hydroxylammonium chloride] [5470-11-1], NH ₂ OH·HCl, F.W. 69.49, Solid, m.p. 152° dec., d. 1.67 ¹⁷ , Merck 14,4828, Fieser 1,478 2,217 7,176 9,245 11,257 15,170 18,186 21,222, Solubility: Soluble in water, alcohol, methanol, glycerol, UN2923, EINECS 226-798-2, RTECS NC3675000, BRN 3539763, MDL MFCD00051089, † Maximum level of impurities: Clarity of alcohol solution P.T., Residue after ignition 0.05%, Titratable free acid 0.25meq/g, NH ₄ P.T., Sulfur compounds (as SO ₄) 0.005%, Heavy Metals (as Pb) 5ppm, Fe 5ppm ! H: H351-H373-H290-H400-H302-H312-H317-H315-H319, P: P280h-P273-P406 | 100g 500g |
| | Application(s): A monoamine oxidase inhibitor; inhibits platelet aggregation | |
| | Hydroxylammonium chloride , see Hydroxylamine hydrochloride, 36416, p. 249 | |
| J60076 | Hydroxylapatite, fast flow [Calcium phosphate hydroxide, Durapatite] [1306-06-5], Ca ₅ (OH)(PO ₄) ₃ , F.W. 502.32, Powder, Merck 14,3467, EINECS 215-145-7, RTECS MY8434000, MDL MFCD00010904, † ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10g 50g |
| | Application(s): Used for fractionation and purification of proteins, enzymes, plasmids and nucleic acids | |









| Stock # | Description | Size |
|---------|--|--|
| J61818 | Hydroxylapatite, high resolution [Calcium phosphate hydroxide, Durapatite] [1306-06-5], Ca ₅ (OH)(PO ₃) ₃ , F.W. 502.32, Powder, Merck 14,3467, EINECS 215-145-7, RTECS MY8434000, MDL MFCD00010904, † | 10g |
| | | 25g |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): Used for fractionation and purification of proteins, enzymes, plasmids and nucleic acids | |
| | 4-Hydroxy-2-mercapto-6-methylpyrimidine, see 6-Methyl-2-thiouracil, A17982, p. 290 | |
| | 4-Hydroxy-2-mercaptopyrimidine, see 2-Thiouracil, A18119, p. 368 | |
| | 4-Hydroxy-3-methoxybenzaldehyde, see Vanillin, A11169, p. 390 | |
| | 4-Hydroxy-3-methoxybenzoic acid, see Vanillic acid, A12074, p. 390 | |
| A13890 | trans-4-Hydroxy-3-methoxycinnamic acid, 99% [Ferulic acid] [537-98-4], C ₁₀ H ₁₀ O ₄ , F.W. 194.19, m.p. 170-175°, Merck 14,4062, EINECS 208-679-7, RTECS UD3365500, BRN 1371483, MDL MFCD00004400, † |  25g 100g 500g |
| | | |
| | Application(s): A chemopreventive analogue of caffeic acid | |
| | 4-Hydroxy-3-methoxyphenylacetic acid, see Homovanillic acid, A12441, p. 246 | |
| | 6-[(E)-4-Hydroxy-3-methylbut-2-enylamino]purine, see trans-Zeatin, 97%, J61972, p. 395 | |
| | 6-[(E)-4-Hydroxy-3-methylbut-2-enylamino]-9Δ-D-ribofuranosylpurine, see trans-Zeatin-riboside, J63382, p. 396 | |
| | (S)-[2-(4-Hydroxy-1-methylethyl)carbamoyl]carbazole benzyl ester, see N-Benzoyloxycarbonyl-L-alanine, H27066, p. 123 | |
| | (2R,3R,4R,5S)-2-(Hydroxymethyl)-3,4,5-piperidinetriol, see (+)-1-Deoxynojirimycin, J62602, p. 179 | |
| L18358 | (R)-(-)-5-(Hydroxymethyl)-2-pyrrolidinone, 99% [D-Pyrroglutaminol, H-D-Pyr-ol] [66673-40-3], C ₅ H ₉ NO ₂ , F.W. 115.13, m.p. 83-85°, b.p. 147-149°/0.06m, [α] _D ²⁰ -30° (c=2 in ethanol), BRN 5728422, MDL MFCD00077791 |  1g 5g |
| | | |
| L18359 | (S)-(+)-5-(Hydroxymethyl)-2-pyrrolidinone, 98% [L-Pyrroglutaminol, H-Pyr-ol] [17342-08-4], C ₅ H ₉ NO ₂ , F.W. 115.13, m.p. 78-82°, b.p. 147-149°/0.06m, [α] _D ²⁰ +30° (c=2 in ethanol), BRN 4657914, MDL MFCD00077792 |  1g 5g |
| | | |
| | (R)-(-)-2-(Hydroxymethyl)tetrahydrofuran, see (R)-(-)-Tetrahydrofurfuryl alcohol, L19044, p. 363 | |
| | (S)-(+)-2-(Hydroxymethyl)tetrahydrofuran, see (S)-(+)-Tetrahydrofurfuryl alcohol, J62573, p. 363 | |
| | 1-Hydroxynaphthalene, see 1-Naphthol, A11862, p. 298 | |
| | 2-Hydroxynaphthalene, see 2-Naphthol, A14564, p. 298 | |
| J63913 | (Hydroxy-2-naphthylmethyl)phosphonic acid, 98% [HNMPA] [120943-99-9], C ₁₁ H ₁₁ O ₄ P, F.W. 238.18, Solid | 5mg 25mg |
| | | |
| | Application(s): A selective insulin receptor tyrosine kinase inhibitor | |
| A15802 | 6-Hydroxynicotinic acid, 98% [2-Hydroxypyridine-5-carboxylic acid, 6-Hydroxypyridine-3-carboxylic acid] [5006-66-6], C ₆ H ₆ NO ₂ , F.W. 139.11, m.p. 314-316°, EINECS 225-682-9, BRN 472182, MDL MFCD00006277, † |  5g 25g 100g |
| | | |
| | Application(s): Metabolite of nicotinamide. Stimulates adrenocortical secretion | |
| A10562 | 4-Hydroxy-3-nitrobenzoic acid, 98% [616-82-0], C ₇ H ₅ NO ₄ , F.W. 183.12, m.p. 182-184°, EINECS 210-494-1, BRN 2213134, MDL MFCD00007119 |  25g 100g |
| | | |
| | Application(s): Standard in chymotrypsin assays | |
| | N-Hydroxy-N-nitrosobenzeneamine ammonium salt, see Cupferron, 97+%, A16551, p. 170 | |
| | 4-Hydroxyphenethylamine hydrochloride, see Tyramine hydrochloride, A12220, p. 386 | |
| | 7-Hydroxy-3H-phenoxazin-3-one-10-oxide sodium salt, see Resazurin sodium salt, B21187, p. 335 | |
| | 2-Hydroxy-2-phenylacetophenone, see Benzoin, A10188, p. 120 | |
| | 3-(4-Hydroxyphenyl)-DL-alanine, see DL-Tyrosine, A13740, p. 386 | |
| | 3-(4-Hydroxyphenyl)-D-alanine, see D-Tyrosine, A17709, p. 386 | |
| | 3-(4-Hydroxyphenyl)-L-alanine, see L-Tyrosine, A11141, p. 386 | |
| A10333 | 2-(p-Hydroxyphenylazo)benzoic acid, 98+% [HABA] [1634-82-8], C ₁₃ H ₁₀ N ₂ O ₃ , F.W. 242.23, m.p. 205-207°, EINECS 216-655-2, BRN 1842696, MDL MFCD00002428, † |  10g 50g 250g |
| | | |
| | Application(s): Indicator used in determination of serum albumin | |
| | 2-(4-Hydroxyphenyl)ethylamine, see Tyramine, 98+%, J60990, p. 386 | |
| | 2-(4-Hydroxyphenyl)ethylamine hydrochloride, see Tyramine hydrochloride, A12220, p. 386 | |
| | 4-Hydroxyphenyl-β-D-glucopyranoside, see Arbutin, L14945, p. 109 | |

| Stock # | Description | Size |
|---------|---|--|
| L07190 | D(-)-4-Hydroxyphenylglycine, 98+% [(R)-(-)- α -Amino-(4-hydroxyphenyl)acetic acid, H-D-Phg(4-OH)-OH] [22818-40-2], C ₉ H ₉ NO ₃ , F.W. 167.16, m.p. ca 240° dec., $[\alpha]_D^{20}$ -156° (c=1 in 1N HCl), EINECS 245-247-7, BRN 2210998, MDL MFCD00004262, † ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a |  5g 25g |
| | DL-3-Hydroxy-2-phenylpropionic acid , see DL-Tropic acid, B22040, p. 383 2-Hydroxypropionic acid , see DL-Lactic acid, L14259, p. 265 (R)-2-Hydroxypropionic acid , see D-Lactic acid, J61871, p. 265 (S)-2-Hydroxypropionic acid , see L-Lactic acid, L13242, p. 265 6-Hydroxypurine , see Hypoxanthine, A11481, p. 253 | |
| A16974 | 4-Hydroxy-1H-pyrazolo[3,4-d]pyrimidine, 98% [Allopurinol, 1,5-Dihydro-4H-pyrazolo[3,4-d]pyrimidin-4-one] [315-30-0], C ₇ H ₇ N ₃ O, F.W. 136.11, m.p. >300°, UN2811, EINECS 206-250-9, MDL MFCD00599413, † ! H: H301-H317, P: P261-P301+P310-P302+P352-P321-P405-P501a |  5g 25g |
| | Application(s): Xanthine oxidase inhibitor; decreases uric acid production | |
| | 6-Hydroxy-1,3,8-pyrenetrisulfonic acid trisodium salt , see Pyranine, L11252, p. 332 2-Hydroxypyridine-5-carboxylic acid , see 6-Hydroxynicotinic acid, A15802, p. 250 6-Hydroxypyridine-3-carboxylic acid , see 6-Hydroxynicotinic acid, A15802, p. 250 4-Hydroxypyridine-2,6-dicarboxylic acid hydrate , see Chelidamic acid hydrate, L00782, p. 153 4-Hydroxypyrimidine , see 4(3H)-Pyrimidone, A10859, p. 332 | |
| L19499 | (R)-(+)-3-Hydroxypyrrolidine, 99%, ee 99% Δ ■ [(R)-(+)-3-Pyrrolidinol] [2799-21-5], C ₄ H ₉ NO, F.W. 87.12, m.p. 15°, b.p. 108-110°/8mm, f.p. >110°(230°F), d. 1.048, n _D ²⁰ 1.4900, $[\alpha]_D^{20}$ +6.5° (c=3.5 in methanol), BRN 5376132, MDL MFCD00145220 ! H: H315-H319, P: P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 Product of Toray Industries, Inc. |  1g 5g |
| L19498 | (S)-(-)-3-Hydroxypyrrolidine, 99%, ee 99% Δ ■ [(S)-(-)-3-Pyrrolidinol] [100243-39-8], C ₄ H ₉ NO, F.W. 87.12, m.p. 15°, b.p. 108-110°/8mm, f.p. >110°(230°F), d. 1.048, n _D ²⁰ 1.4900, $[\alpha]_D^{20}$ -6.5° (c=3.5 in methanol), BRN 4652606, MDL MFCD00192426 ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a Product of Toray Industries, Inc. |  250mg 1g 5g |
| | 1-Hydroxy-2,5-pyrrolidinedione , see N-Hydroxysuccinimide, A10312, p. 251 | |
| 41272 | 8-Hydroxyquinoline, ACS [8-Quinolinal, Oxine] [148-24-3], C ₈ H ₇ NO, F.W. 145.16, Granular, m.p. 72-74°, b.p. 267°, Merck 14,4843, Solubility: Almost insoluble in water and diethyl ether. Highly soluble in ethanol, acetone, chloroform, and benzene., EINECS 205-711-1, RTECS VC4200000, BRN 114512, MDL MFCD00006807, † Maximum level of impurities: Insoluble in alcohol 0.05%, Melting point 72.5-74.0°, Residue after ignition 0.05%, SO ₄ 0.02%, Suitability for magnesium determination P.T. ! H: H341-H302, P: P281-P264-P301+P312-P308+P313-P405-P501a |  50g 250g 1kg |
| | Application(s): A bacteriostatic and fungistatic agent. Also a chelating agent for metals | |
| A12602 | 4-Hydroxyquinoline-2-carboxylic acid hydrate, 98% [Kynurenic acid] [345909-35-5], C ₁₀ H ₇ NO ₃ ·xH ₂ O, F.W. 189.17(anhy), m.p. ca 275° dec., Merck 14,5327, EINECS 207-751-5, RTECS VB2080000, BRN 147451, MDL MFCD00006753 ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a |  1g 5g 25g |
| | Application(s): Broad spectrum excitatory amino acid antagonist | |
| | 3-Hydroxyquinuclidine , see 3-Quinuclidinol, B21503, p. 334 | |
| J63588 | 2-Hydroxysaclofen [3-Amino-2-(4-chlorophenyl)-2-hydroxypropanesulfonic acid] [117354-64-0], C ₉ H ₁₂ ClNO ₃ S, F.W. 265.71, Solid, m.p. 268-271°, UN1759, RTECS DA0359200, MDL MFCD00069282 ! H: H314, P: P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a |  10mg 50mg |
| | Application(s): Selective antagonist at GABA-B receptors | |
| | 3-β-Hydroxy-5-spirostene , see Diosgenin, J60976, p. 198 N-Hydroxysuccinimide , see (+)-Biotin N-hydroxysuccinimide ester, 44771, p. 125 (±)-Hydroxysuccinic acid , see DL-Malic acid, A17874, p. 276 (R)-(+)-Hydroxysuccinic acid , see D-(+)-Malic acid, A11688, p. 276 (S)-(-)-Hydroxysuccinic acid , see L-(-)-Malic acid, 99%, J63221, p. 276 | |
| A10312 | N-Hydroxysuccinimide, 98+% ■ [HOSu, 1-Hydroxy-2,5-pyrrolidinedione] [6066-82-6], C ₄ H ₅ NO ₃ , F.W. 115.09, m.p. 94-99°, Fieser 1,487 9,246, EINECS 228-001-3, BRN 113913, MDL MFCD00005516, † Reagent for the preparation of active N-hydroxysuccinimide esters for peptide coupling with minimum racemization: <i>J. Am. Chem. Soc.</i> , 86 , 1839 (1964), or as an additive in the DCC method (see N,N'-Dicyclohexylcarbodiimide , A10973, p. 187) to suppress racemization: <i>J. Am. Chem. Soc.</i> , 89 , 7151 (1967). For a study of the aminolysis of N-hydroxysuccinimide esters, see: <i>J. Org. Chem.</i> , 53 , 3583 (1988). |  25g 100g 500g |





| Stock # | Description | Size |
|--|---|----------------------|
| J60680 | Hydroxytacrine maleate salt [9-Amino-1,2,3,4-tetrahydro-1-acridinol (2Z)-2-butenedioate, Velnacrine maleate] [118909-22-1], C ₁₇ H ₁₈ N ₂ O ₅ , F.W. 330.34, Solid, m.p. 171-173° | 1g |
| Application(s): Cholinesterase inhibitor. Potential Alzheimer's disease therapeutic | | |
| A12497 | 4-Hydroxy-TEMPO, free radical, 98+% [4-Hydroxy-2,2,6,6-tetramethyl-1-piperidin-1-yloxy, free radical] [2226-96-2], C ₈ H ₁₅ NO ₂ , F.W. 172.25, m.p. 69-72°, f.p. 146°(295°F), Fieser 9,247, EINECS 218-760-9, RTECS TN8991000, BRN 1422990, MDL MFCD00006478, † | 1g 5g 25g |
|  | | |
| <p>! H:H318-H302-H335-H315, P:P280-P305+P351+P338-P310-P405-P403+P233 Reviews: Synthesis and reactions of stable nitroxyl radicals: <i>Synthesis</i>, 190, 401 (1971); Advances in the chemistry of nitroxide spin labels: <i>Chem. Rev.</i>, 78, 37 (1978); Recent advances in the chemistry of nitroxides and their applications in spin labelling: <i>J. Sci. Ind. Res.</i>, 54, 623 (1995). For a brief feature on derived oxoammonium salts, see: <i>Synlett</i>, 1757 (2003). Compare also 4-Acetamido-TEMPO, B23456, and TEMPO, A1273. Recommended as a stabilizer (antioxidant) for the protection of unsaturated fatty acids and their derivatives: <i>J. Am. Chem. Soc.</i>, 101, 6748 (1979).</p> | | |
| Application(s): Superoxide scavenger with neuroprotective, anti-inflammatory and analgesic effects | | |
| 4-Hydroxy-2,2,6,6-tetramethyl-1-piperidin-1-yloxy, free radical , see 4-Hydroxy-TEMPO, A12497, p. 252 (R)-(-)-3-Hydroxy-4-(trimethylammonio)butyrate , see L-Carnitine, A17618, p. 148 5-Hydroxytryptamine hydrochloride , see Serotonin hydrochloride, B21263, p. 342 | | |
| A12237 | DL-5-Hydroxytryptophan, 99% [DL-2-Amino-3-[3-(5-hydroxyindole)]propionic acid] [56-69-9], C ₁₁ H ₁₂ N ₂ O ₃ , F.W. 220.23, m.p. ca 298° dec., Merck 14,4847, EINECS 200-284-8, RTECS YN7100000, BRN 88199, MDL MFCD00005651, † | 1g 5g |
|  | | |
| A13954 | L-5-Hydroxytryptophan hydrate, 98% [L-2-Amino-3-[3-(5-hydroxyindole)]propionic acid, 5-HTP] [4350-09-8], C ₁₁ H ₁₂ N ₂ O ₃ · xH ₂ O, F.W. 220.23(anhy), m.p. 258° dec., [α] _D ²⁰ -33° (c=1 in water), Merck 14,4847, UN2811, EINECS 224-411-1, RTECS YN710000, BRN 88200, MDL MFCD00064341, † | 250mg 1g |
|  | | |
| <p>! H:H302, P:P264-P270-P301+P312-P330-P501a For routes to 2-bromo-5-hydroxytryptophan derivatives, see: <i>Synthesis</i>, 28 (1996).</p> | | |
| 3-Hydroxytyramine hydrochloride , see Dopamine hydrochloride, A11136, p. 201 3-Hydroxy-DL-tyrosine , see 3,4-Dihydroxy-DL-phenylalanine, 41535, p. 193 3-Hydroxy-L-tyrosine , see L-3-(3,4-Dihydroxyphenyl)alanine, A11311, p. 193 1-Hydroxyundecane , see 1-Undecanol, A17817, p. 387 | | |
| A10831 | Hydroxyurea, 98% [127-07-1], CH ₃ N ₂ O ₃ , F.W. 76.06, m.p. ca 140° dec., Merck 14,4848, EINECS 204-821-7, RTECS YT4900000, BRN 1741548, MDL MFCD00007943 | 1g 5g 25g |
|  | | |
| <p>H:H340-H360, P:P281-P201-P202-P308+P313-P405-P501a</p> | | |
| Application(s): An inhibitor of DNA synthesis and an anticancer agent | | |
| 9-Hydroxyxanthene , see Xanthinol, A13476, p. 394 17-Hydroxyyohimban-16-carboxylic acid methyl ester hydrochloride , see Yohimbine hydrochloride, 98+%, J60185, p. 395 17α-Hydroxy-20α-yohimban-16β-carboxylic acid methyl ester hydrochloride , see Rauwolfscine hydrochloride, 99%, J63198, p. 335 | | |
| J60681 | Hygromycin B [31282-04-9], C ₂₀ H ₃₇ N ₅ O ₁₃ , F.W. 527.53, Lyophilized powder, Merck 14,4852, UN3462, EINECS 250-545-5, RTECS WK2130000, MDL MFCD06795479 | 100mg 250mg 1g |
|  | | |
| <p>H:H300-H310-H330-H334-H318-H317, P:P301+P310-P304+P340-P305+P351+P338-P320-P330-P361-P405-P501a</p> | | |
| Application(s): An aminoglycoside antibiotic that kills bacteria by inhibiting protein synthesis | | |
| J65234 | Hypercalcemia Malignancy Factor (1-34) amide, human [pTH-Related Protein (1-34) amide] [112955-31-4], C ₁₈₀ H ₂₈₈ N ₅₈ O ₄₇ , F.W. 4016.56, Solid, MDL MFCD00166741 | 0.5mg 1mg |
| J64361 | Hypercalcemia Malignancy Factor (7-34), amide, human [Leu-Leu-His-Asp-Lys-Gly-Lys-Ser-Ile-Gln-Asp-Leu-Arg-Arg-Arg-Phe-Phe-Leu-His-His-Leu-Ile-Ala-Glu-Ile-His-Thr-Ala-NH ₂] C ₁₅₃ H ₂₄₇ N ₄₉ O ₃₇ , F.W. 3364.89, Solid | 1mg |
| J65499 | Hypercalcemia Malignancy Factor (1-34), human [112540-82-6], C ₁₈₀ H ₂₈₈ N ₅₇ O ₄₈ , F.W. 4017.55, Solid | 1mg |



| Stock # | Description | Size |
|---------------|--|---|
| H26425 | Hypericin, 98% [4,4',5,5',7,7'-Hexahydroxy-2,2'-dimethylnaphthodianthrone, <i>Hypericum red</i>] [548-04-9], C ₂₃ H ₁₆ O ₆ , F.W. 504.44, m.p. ca 320° dec., Merck 14,4863, EINECS 208-941-0, BRN 1917913, MDL MFCD00016683 ! H: H302, P: P264-P270-P301+P312-P330-P501a Inhibitor of protein kinase C: <i>Biochem Biophys. Res. Commun.</i> , 165 , 1207 (1989); <i>Photochem. Photobiol.</i> , 82 , 720 (2006). Antiviral and antitumour photosensitizer: <i>Photochem. Photobiol.</i> , 54 , 95 (1991); <i>Curr. Drug Targets</i> , 3 , 55 (2002). | 25mg 100mg |
| | Application(s): Inhibitor of protein kinase C; induces photosensitized apoptosis | |
| | Hypericum red , see Hypericin, H26425, p. 253 Hypertensin I , see Angiotensin I (human), J62102, p. 104 | |
| A11481 | Hypoxanthine, 99% [6-Hydroxypurine] [68-94-0], C ₅ H ₄ N ₂ O, F.W. 136.11, m.p. >300°, Merck 14,4869, EINECS 200-697-3, RTECS UP0791000, BRN 5811, MDL MFCD00005725, † | 5g 25g 100g |
| | Hypoxanthine-9-β-D-ribofuranoside , see Inosine, A14459, p. 256 | |
| J62443 | Ibandronate sodium, 98+% [138844-81-2], C ₁₆ H ₁₆ NNaO ₈ P ₂ , F.W. 359.23, Crystalline powder, Merck 14,4873, RTECS SZ8563300, MDL MFCD07197214 H: H400-H410, P: P273-P391-P501a | 100mg |
| | Application(s): A third generation bisphosphonate used as bone resorptive inhibitor. Inhibits farnesyl diphosphate synthase | |
| J60748 | Ibotenic acid hydrate, 98+% [α-Amino-3-hydroxy-5-isoxazoleacetic acid] [2552-55-8], C ₆ H ₈ N ₂ O ₃ ·xH ₂ O, F.W. 158.11(anhy), Powder, Merck 14,4877, UN3462, RTECS NY2100000, MDL MFCD00069294 H: H301, P: P264-P270-P301+P310-P321-P405-P501a | 1mg 5mg 25mg |
| | Application(s): Potent NMDA and glutamate receptor agonist | |
| | Ibuprofen , see 4-Isobutyl-α-methylphenylacetic acid, B20989, p. 260 | |
| H56358 | Ibutilide hemifumarate salt, 99% [(±)-N-[4-(4-[Ethyl(n-heptyl)amino]-1-hydroxybutyl)phenyl]methanesulfonamide hemifumarate salt] [122647-32-9], C ₂₀ H ₃₈ N ₂ O ₅ ·0.5C ₄ H ₄ O ₄ , F.W. 442.61, Merck 14,4883, RTECS PB0475700, MDL MFCD01715410 | 25mg 100mg |
| | IDC , see 5-Iodo-2'-deoxycytidine, 99%, J61356, p. 258 Idoxuridine , see (+)-5-Iodo-2'-deoxyuridine, A11542, p. 258 | |
| J63303 | IEF Anode buffer (50X) Liquid, Note: Contains 350mM phosphoric acid at pH 2.4. ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | 500ml 1L |
| | Application(s): For isoelectric focusing (IEF) | |
| J61903 | IEF Cathode buffer (10X) with lysine Liquid, Note: Contains 0.2M lysine (free base) pH 3-7 | 250ml 500ml |
| | Application(s): For isoelectric focusing (IEF) | |
| J62204 | IEF Cathode buffer (10X) with lysine and arginine Liquid, Note: Contains 0.2M arginine (free base) and 0.2mM lysine (free base) at pH 10.1 | 250ml 500ml |
| | Application(s): For isoelectric focusing | |
| J62241 | IEF Sample buffer (2X) pH 3-10 with lysine and arginine Liquid, Note: Contains 40mM arginine (free base), 40mM lysine (free base) and 30% glycerol. ! H: H319, P: P280-P264-P305+P351+P338-P337+P313 | 25ml 50ml |
| J63633 | IEF Sample buffer (4X) pH 3-7 with lysine Liquid, Note: Contains 80mM lysine (free base) and 60% glycerol. ! H: H319, P: P280-P264-P305+P351+P338-P337+P313 | 25ml 50ml |
| J60932 | Ifenprodil hemitartrate, 99% [23210-56-2], C ₂₁ H ₂₇ NO ₂ ·0.5C ₄ H ₆ O ₆ , F.W. 400.49, Powder, Merck 14,4895, EINECS 245-491-4 ! H: H302, P: P264-P270-P301+P312-P330-P501 | 10mg 50mg |
| | Application(s): NMDA receptor antagonist, acting at the polyamine site | |
| J61055 | IGEPAL® CA-630 [Octylphenyl-polyethylene glycol] [9036-19-5], (C ₈ H ₁₆ O)nC ₁₄ H ₂₂ O, Liquid, MDL MFCD00132505, Note: IGEPAL is a registered trademark of Rhodia Operations, † H: H318-H315, P: P280-P305+P351+P338-P302+P352-P321-P310-P362 | 100ml 500ml |
| | Application(s): Detergent, equivalent to Nonidet P-40. For solubilizing membrane proteins | |
| | IgE Peptide III , see Hamburger Pentapeptide, J60543, p. 241 | |










| Stock # | Description | Size |
|--|--|-----------------------|
| J65916 | IGF-1R Inhibitor, PPP ▲ [Insulin-like Growth Factor-1 Receptor Inhibitor, Picropodophyllin] [477-47-4], C ₂₂ H ₂₂ O ₆ , F.W. 414.40, Solid, Merck 14,7546, UN3462, RTECS LV2510000, MDL MFCD01742647  | 10mg |
| J65132 | IKK-2 Inhibitor V ▲ [N-(3,5-Bis-trifluoromethylphenyl)-5-chloro-2-hydroxybenzamide, IMD-0354] [978-62-1], C ₁₅ H ₈ ClF ₆ NO ₂ , F.W. 383.67, Powder, MDL MFCD00218820 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10mg |
| J65815 | IL-1R Antagonist [BB-loop Mimic, Hydrocinnamoyl-L-valyl pyrrolidine] [566914-00-9], C ₁₈ H ₂₆ N ₂ O ₂ , F.W. 302.41, Oil | 25mg |
| H:Ile-OH, see L-Isoleucine, Cell Culture Reagent, J63045, p. 260 | | |
| J62346 | Imetit dihydrobromide, 98% [(S)-[2-(4-Imidazolyl)ethyl]isothiourea dihydrobromide] [32385-58-3], C ₈ H ₁₀ N ₄ S·2HBr, F.W. 332.06, Powder, MDL MFCD00153816 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 25mg 50mg 100mg |
| Application(s): An extremely potent, high affinity agonist at H3 and H4 receptors | | |
| J61956 | Imidazole, 0.5M buffer soln., pH 6.0 [288-32-4], Liquid, †  | 100ml 250ml |
| J62207 | Imidazole, 0.5M buffer soln., pH 6.5 [288-32-4], Liquid, †  | 100ml 250ml |
| J62593 | Imidazole, 0.5M buffer soln., pH 7.0 [288-32-4], Liquid, †  | 100ml 250ml |
| J63496 | Imidazole, 0.5M buffer soln., pH 7.5 [288-32-4], Liquid, †  | 100ml 250ml |
| A10221 | Imidazole, 99% [Glyoxaline] [288-32-4], C ₃ H ₄ N ₂ , F.W. 68.08, m.p. 88-92°, b.p. 256°, f.p. 145°(293°F), d. 1.03, Merck 14,4912, Fieser 1,492 2,220 21,224, UN2923, EINECS 206-019-2, RTECS NI3325000, BRN 103853, MDL MFCD00005183, †  Nucleophilic catalyst for many acylation and silylation reactions, compare 4-(Dimethylamino)pyridine, A13016 . For use in: silylation of 1,3-diketones, see Hexamethylidisilazane, A15139 ; introduction of the TBDMS and TBDPS groups; see: tert-Butyldimethylchlorosilane, A13064 , and tert-Butyldiphenylchlorosilane, A12721 , respectively. In combination with triphenylphosphine and iodine, vic-diols are converted to alkenes: <i>Synthesis</i> , 469 (1979), and alcohols to alkyl iodides: <i>Synth. Commun.</i> , 20, 1473 (1990). With 2 moles of an aroyl halide gives, after hydrolysis, good yields of 2-arylimidazoles: <i>Synthesis</i> , 675 (1978). | 100g 500g 2.5kg |
| Application(s): Excellent for buffer use in pH range 6.2 - 7.8. Also an histamine antagonist | | |
| B22473 | Imidazole-4-acetic acid monohydrochloride, 97% [3251-69-2], C ₆ H ₈ N ₂ O ₂ ·HCl, F.W. 162.58, m.p. 221-224°, EINECS 221-840-6, BRN 3701591, MDL MFCD00012698  | 1g 5g |
| Application(s): A GABA _A antagonist | | |
| J63887 | Imidazole-buffered saline (5X) [288-32-4], Liquid, Note: Contains 50mM imidazole and 750mM sodium chloride at pH 7.0., †  | 250ml 500ml |
| 2-Imidazoethiol, see 2-Mercaptoimidazole, L01346, p. 281 2,4-Imidazolidinedione, see Hydantoin, A12486, p. 247 (S)-[2-(4-Imidazolyl)ethyl]isothiourea dihydrobromide, see Imetit dihydrobromide, 98%, J62346, p. 254 7H-Imidazo[4,5-d]pyrimidine, see Purine, 98%, J60999, p. 331 | | |
| A11510 | Iminodiacetic acid, 98+% [142-73-4], HN(CH ₂ CO ₂ H) ₂ , F.W. 133.10, m.p. ca 243° dec., Merck 14,4917, EINECS 205-555-4, RTECS AI2975000, BRN 878499, MDL MFCD00004280, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 100g 500g 2.5kg |
| Application(s): Inhibitor of bovine liver glutamate dehydrogenase | | |
| 43809 | Iminodiacetic acid disodium salt hydrate, 97% [Sodium iminodiacetate dibasic hydrate] [17593-73-6], HN(CH ₂ CO ₂ Na) ₂ ·xH ₂ O, F.W. 177.07(anhy), Crystalline, Merck 14,4917, MDL MFCD00150689, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 50g 250g |










| Stock # | Description | Size |
|---------|--|--------------------|
| | 2-Imino-1-methylimidazolidin-4-one , see Creatinine, B23097, p. 168 | |
| J60131 | 2-Iminothiolane hydrochloride [2-Thiolanimine hydrochloride, <i>Traut's reagent</i>] [4781-83-3], C ₄ H ₇ NS·HCl, F.W. 137.63, Powder, m.p. 190-195°, BRN 3620079, MDL MFCD00039013 | 250mg 1g |
| | Application(s): Protein modification and cross-linking reagent, cleavable by thiols | |
| J63723 | Imipramine hydrochloride [113-52-0], C ₁₉ H ₂₃ N ₂ ·HCl, F.W. 316.87, Crystalline powder, m.p. 174-175°, Merck 14,4920, EINECS 204-030-7, RTECS HO1925000, MDL MFCD00012669, † ! H:3302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5g 25g 100g |
| | Application(s): A serotonin uptake inhibitor | |
| J63990 | Imiquimod, 99% [99011-02-6], C ₁₀ H ₁₆ N ₄ , F.W. 240.31, Solid, m.p. 292-294°, Merck 14,4922, UN2811, MDL MFCD00866946 GHS H:3301-H315-H319-H335, P:P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a | 100mg 1g |
| | Application(s): A caspase 3 activator that acts as an immunomodulator and displays antiviral and antitumor activity | |
| J64212 | Immethridine dihydrobromide [4-(1 <i>H</i> -Imidazol-4-ylmethyl)pyridine dihydrobromide] [87976-03-2], C ₈ H ₈ N ₄ ·2HBr, F.W. 321.01, Solid, MDL MFCD07370139 ! H:3315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10mg 50mg |
| | IMP, see Inosine-5'-monophosphate disodium salt hydrate, J61959, p. 256 | |
| J60062 | Inactivation Gate Peptide [Ac-Lys-Ile-Phe-Met-Lys-NH ₂] [156162-44-6], C ₃₄ H ₅₈ N ₈ O ₆ S, F.W. 706.95, Lyophilized powder | 25mg |
| | Application(s): Binds and inactivates open sodium channels | |
| J63846 | Indapamide [26807-65-8], C ₁₅ H ₁₆ ClN ₃ O ₃ S, F.W. 365.83, Powder, m.p. 160-162°, Merck 14,4935, EINECS 248-012-7, MDL MFCD00079375 | 1g 5g |
| | Application(s): Used as an antihypertensive. Diuretic | |
| J61485 | Indatraline hydrochloride, 99% [Lu 19-005] [86939-10-8], C ₁₈ H ₁₅ Cl ₂ N·HCl, F.W. 328.67, Solid, m.p. 186-188° | 10mg 50mg |
| | Application(s): Potent inhibitor of dopamine, norepinephrine and serotonin uptake | |
| J61007 | India Ink [8046-52-4], Liquid, Note: A ready to use solution of 0.2% India Ink in PBS with 0.05% Tween-20 | 500ml 1L |
| A16052 | Indigo carmine [Indigo-5,5'-disulfonic acid disodium salt, C.I. 73051] [860-22-0], C ₁₆ H ₈ N ₂ Na ₂ O ₆ S ₂ , F.W. 466.36, m.p. >300°, Merck 14,4944, EINECS 212-728-8, RTECS DU3000000, BRN 4103904, MDL MFCD00005723, † ! H:3302, P:P264-P270-P301+P312-P330-P501a | 25g 100g |
| | Application(s): Useful in the staining of Negri bodies | |
| | Indigo-5,5'-disulfonic acid disodium salt , see Indigo carmine, A16052, p. 255 | |
| A14427 | Indole, 99% ▲ [120-72-9], C ₈ H ₇ N, F.W. 117.15, m.p. 50-54°, b.p. 253-254°, f.p. 121°(249°F), d. 1.220, Merck 14,4963, UN2811, EINECS 204-420-7, RTECS NL2450000, BRN 107693, MDL MFCD00005607, † GHS H:3311-H318-H400-H302, P:P280-P305+P351+P338-P361-P302+P352-P405-P501a Lithiation of N-protected indoles usually occurs at the 2-position, e.g. benzenesulfonation of the 1-lithio derivative, 2-lithiation with LDA and treatment with pyridine-3,4-dicarboxylic anhydride. This sequence has been reported in a synthetic route to ellipticine and olivacine: <i>J. Org. Chem.</i> , 57 , 5891 (1992). Regioselective synthesis of 3-substituted indoles has been described using a sequence of N-silylation, 3-bromination of the 1-TBDMS derivative with NBS, 3-lithiation, treatment with an electrophile to introduce the 3-substituent, and desilylation with TBAF. Good overall yields are obtained for a range of electrophiles: <i>J. Org. Chem.</i> , 59 , 10 (1994); <i>Org. Synth. Coll.</i> , 9 , 417 (1998). Treatment with EtMgI followed by ZnCl ₂ leads to an N-zinc derivative. This undergoes acylation at the 3-position: <i>Tetrahedron</i> , 46 , 6061 (1990). Halogenation in the 2-position has been effected via the Li 1-carbamate and subsequent 2-lithiation: <i>J. Org. Chem.</i> , 57 , 2495 (1992): | 50g 250g 1kg |
| | | |
| | Treatment of the carbamate with Tri-<i>n</i>-butyltin chloride, A10746 , followed by Stille coupling enables synthesis of 2-aryl- and 2-vinylindoles: <i>J. Org. Chem.</i> , 60 , 6218 (1995). | |

| Stock # | Description | Size |
|--|--|--|
| A10556 | Indole-3-acetic acid, 98+% ▲ [Heterauxin, Indolyl-3-acetic acid] [87-51-4], C ₁₀ H ₉ NO ₂ , F.W. 175.19, m.p. ca 167° dec., f.p. 171° (339°F), Merck 14,4964, EINECS 201-748-2, RTECS NL3150000, BRN 143358, MDL MFCD00005636, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a |  5g 25g 100g 500g |
| Application(s): Plant growth hormone | | |
| A15260 | Indole-3-butyric acid, 98% [4-(3-Indolyl)butyric acid] [133-32-4], C ₁₃ H ₁₃ NO ₂ , F.W. 203.24, m.p. 121-125°, Merck 14,4965, UN2811, EINECS 205-101-5, RTECS NL5250000, BRN 171120, MDL MFCD00005664, † ☠ H:H301-H315-H319-H335, P:P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a |  5g 25g 100g |
| J65215 | Indolicidin [Ile-Leu-Pro-Trp-Lys-Trp-Pro-Trp-Trp-Pro-Trp-Arg-Arg-NH2] [140896-21-5], C ₁₀₆ H ₁₃₂ N ₂₆ O ₁₃ , F.W. 1906.28, Powder, Merck 14,10224, RTECS NM1890250 | 0.5mg 1mg |
| 2,3-Indolinedione, see Isatin, A12468, p. 260 Indolyl acetate, see 3-Indoxyl acetate, L04932, p. 256 Indolyl-3-acetic acid, see Indole-3-acetic acid, A10556, p. 256 4-(3-Indolyl)butyric acid, see Indole-3-butyric acid, A15260, p. 256 2-(3-Indolyl)ethanol, see Tryptophol, L02555, p. 385 | | |
| J63255 | Indomethacin, 99+% ▲ [1-(4-Chlorobenzoyl)-5-methoxy-2-methyl-1H-indole-3-acetic acid] [53-86-1], C ₁₉ H ₁₆ ClNO ₂ , F.W. 357.80, Powder, m.p. 158-161°, Merck 14,4968, UN2811, EINECS 200-186-5, RTECS NL3500000, BRN 497341, MDL MFCD00057095, † ☠ H:H300-H341, P:P281-P301+P310-P321-P308+P313-P405-P501a | 1g 5g 25g |
| Application(s): Non-selective cyclooxygenase inhibitor | | |
| L04932 | 3-Indoxyl acetate, 97% [3-Acetoxyindole, Indolyl acetate] [608-08-2], C ₁₀ H ₉ NO ₂ , F.W. 175.19, m.p. 128-130°, EINECS 210-154-2, RTECS A13325000, BRN 143086, MDL MFCD00014561, † Substrate for enzyme assay: <i>Anal. Chem.</i> , 37 , 120 (1965). |  1g 5g |
| Application(s): Useful for detection of esterases | | |
| J60552 | 3-Indoxyl phosphate disodium salt [Disodium 3-indoxyl phosphate] [3318-43-2], C ₈ H ₆ NNa ₂ O ₆ P, F.W. 257.09, Powder, EINECS 222-014-8, MDL MFCD00040646, † | 250mg 1g |
| Application(s): A histochemical substrate for alkaline phosphatase | | |
| J60601 | Ingenol 3-angelate, 99% [75567-37-2], C ₂₈ H ₃₄ O ₆ , F.W. 348.40, Powder, MDL MFCD07784504 | 1mg |
| Application(s): Protein kinase C activator | | |
| Ingrain blue 1, see Alcian Blue 8GX, J63233, p. 134 | | |
| A14459 | Inosine, 98+% [Hypoxanthine-9-β-D-ribofuranoside] [58-63-9], C ₁₀ H ₁₂ N ₄ O ₆ , F.W. 268.23, m.p. 212-215° dec., [α] _D ²⁰ -52° (c=1 in water), Merck 14,4975, EINECS 200-390-4, RTECS NW7460000, BRN 624889, MDL MFCD00066770, † |  5g 25g 100g |
| Application(s): Suppresses the increase of glucose and insulin in the blood | | |
| J65397 | Inosine-5'-diphosphate disodium salt, 95% [IDP] [54735-61-4], C ₁₀ H ₁₂ N ₄ O ₁₁ P ₂ Na ₂ , F.W. 472.15, Powder, EINECS 259-312-2, MDL MFCD00211028 | 1g 5g 10g |
| J61959 | Inosine-5'-monophosphate disodium salt hydrate [IMP] [4691-65-0], C ₁₀ H ₁₁ N ₄ Na ₂ O ₆ P·xH ₂ O, F.W. 392.17(anhy), Crystalline powder, EINECS 225-146-4, RTECS NM7519500, MDL MFCD00036201, † | 5g 25g 100g |
| J65670 | Inosine-5'-triphosphate trisodium salt, 96% [35908-31-7], C ₁₀ H ₁₂ N ₄ Na ₃ O ₁₄ P ₃ , F.W. 574.11, Powder, MDL MFCD00084678 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| J60828 | myo-Inositol, 97+% [87-89-8], C ₆ H ₁₂ O ₆ , F.W. 180.16, Crystalline powder, m.p. 222-227°, Merck 14,4978, EINECS 201-781-2, RTECS NM7520800, BRN 1907329, MDL MFCD00077932, † | 100g 500g |
| Application(s): A lipotropic agent | | |






| Stock # | Description | Size |
|---------|---|-----------------------|
| A13586 | myo-Inositol, 98+% [Hexahydroxycyclohexane, Myoinositol] [87-89-8], C ₆ H ₁₂ O ₆ , F.W. 180.16, m.p. 224-227°, d. 1.75, Merck 14,4978, EINECS 201-781-2, RTECS NM7520800, BRN 1907329, MDL MFCD00077932, † | 100g 500g 2.5kg |
| | Application(s): A lipotropic agent | |
| |  | |
| J62886 | D-myo-Inositol, Cell Culture Grade [87-89-8], C ₆ H ₁₂ O ₆ , F.W. 180.16, Crystalline powder, m.p. 222-227°, Merck 14,4978, EINECS 201-781-2, RTECS NM7520800, BRN 1907329, MDL MFCD00077932, † | 50g 100g 250g |
| | Application(s): A lipotropic agent | |
| | | |
| J61170 | Insulin B (22-25) [H-Arg-Gly-Phe-Phe-OH] [34367-73-2], C ₂₆₈ H ₃₅ N ₇ O ₅ , F.W. 525.61, Powder | 25mg 100mg |
| | | |
| J61321 | Insulin, from porcine pancreas, 98+% [12584-58-6], C ₅₂₆₈ H ₇₃₈₁ N ₁₆₅ O ₁₆ S ₆ , F.W. 5777.59, Lyophilized powder, Merck 14,4980, EINECS 235-703-3, RTECS NM8895000, MDL MFCD00131380 | 25mg 250mg |
| | Application(s): A hormone that is central to regulating energy and glucose metabolism in the body | |
| J64081 | Insulin-like Growth Factor-I, human, 97% [IGF-I, human, Somatomedin C] Note: Recombinantly expressed in E. Coli. Receptor Grade. Suitable for cell culture and radioimmunoassays. Supplied as an aseptically lyophilized powder. | 10micrograms |
| | | |
| J65170 | Insulin-like Growth Factor-II, human, 97% [IGF-II, human] Note: Recombinantly expressed in E. Coli. Receptor Grade. Suitable for cell culture and radioimmunoassays. Supplied as an aseptically lyophilized powder. | 10micrograms |
| | | |
| | INT, see 2-(p-iodophenyl)-3-(p-nitrophenyl)-5-phenyltetrazolium chloride hydrate, B22301, p. 258 | |
| J65928 | β-Interleukin-I (163-171), human [Val-Gln-Gly-Glu-Glu-Ser-Asn-Asp-Lys] [106021-96-9], C ₉₉ H ₁₆₄ N ₁₂ O ₁₉ , F.W. 1004.99, Solid | 1mg |
| | | |
| J65203 | β-Interleukin II (44-56) [Ile-Leu-Asn-Gly-Ile-Asn-Asn-Tyr-Lys-Asn-Pro-Lys-Leu] C ₆₈ H ₁₁₃ N ₁₈ O ₁₉ , F.W. 1500.74, Solid | 1mg |
| | | |
| J61698 | Intrinsic Factor [9008-12-2], Lyophilized powder, MDL MFCD00131406 | 1kilounit |
| | Application(s): A glycoprotein necessary for the absorption of vitamin B-12 | |
| A18425 | Inulin [9005-80-5], Merck 14,5004, EINECS 232-684-3, MDL MFCD00131407, Note: Yields D-fructose and D-glucose after acid hydrolysis., † | 10g 50g 250g |
| | Application(s): Mixture of fructose polymers that serves as carbohydrate storage in plants | |
| | Invertose , see Invert sugar, J60273, p. 257 | |
| J60273 | Invert sugar [Invertose] [8013-17-0], Thick syrup, Merck 14,5006, EINECS 232-393-1, MDL MFCD00148911, Note: Mixture of about 50% glucose and 50% fructose obtained by hydrolysis of starch., † | 100g 1kg |
| | Application(s): Pure Syrup | |
| | | |
| J64994 | Involucrin, human, Enzyme Immunoassay Kit Note: Contains sufficient material for 2500 tests or 25-96 well plates. Kit components include: anti-human Involucrin antibody (from rabbit), human Involucrin and goat anti-rabbit IgG-alkaline phosphatase conjugate. | 1kit |
| | Application(s): For detection of involucrin. Detection range is 0.5-10ng/ml | |
| A14715 | 2-Iodoacetamide, 98%, stab. with ca 5-8% water ▲ [144-48-9], ICH ₂ CONH ₂ , F.W. 184.96, m.p. 92-95°(dried), Fieser 1,504, UN2811, EINECS 205-630-1, RTECS AC4200000, BRN 1739080, MDL MFCD00008028, † | 5g 25g 100g |
| |  H.H301-H315-H319-H317-H335, P.P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Application(s): Alkylating agent used in peptide mapping because it covalently binds with the thiols in cysteine to prevent disulfide bond formation | |
| | 5-Iodoanthranilic acid , see 2-Amino-5-iodobenzoic acid, A19838, p. 96 | |
| B24416 | 4-Iodobenzenesulfonyl chloride, 97% ▲▲ [Pipsyl chloride] [98-61-3], C ₆ H ₄ ClO ₂ S, F.W. 302.52, m.p. 79-84°, Merck 14,7486, UN3261, EINECS 202-686-9, BRN 2691661, MDL MFCD00007441, † | 5g 25g 100g |
| |  | |
| |  H.H314, P.P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | |







| Stock # | Description | Size |
|--|---|--|
| A10563 | 2-Iodobenzoic acid, 98+% ▲ [88-67-5], C ₇ H ₅ IO ₂ , F.W. 248.02, m.p. 160-164°, d. 2.250, Merck 14,5030, Fieser 1,506, EINECS 201-850-7, RTECS DH2975000, BRN 1861406, MDL MFCD00002419, † ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Can be used to protect alcohols as their 2-iodobenzoates by DCC coupling. The group is removed by oxidation with chlorine under basic conditions: <i>Tetrahedron Lett.</i> , 28 , 5005 (1987). In the presence of Tetrakis(triphenylphosphine)palladium(0) , 10548 , and zinc chloride, undergoes cyclization with terminal acetylenes to give isocoumarins: <i>J. Org. Chem.</i> , 60 , 3711 (1995): |  25g 100g 500g |
| |  | |
| | For related reactions, see 4,4-Dimethyl-2-pentyne , L10210 , 2-Iodoaniline , A13059 , and 2-Iodophenol , A13599 . | |
| Application(s): Reagent for detection of sulfhydryl groups in proteins | | |
| A10730 | 4-Iodobenzoic acid, 97% ▲ [619-58-9], C ₇ H ₅ IO ₂ , F.W. 248.02, m.p. ca 265° dec., d. 2.18, EINECS 210-603-2, RTECS DH2976000, BRN 1860232, MDL MFCD00002533, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a |  10g 50g 250g |
| J64698 | 5-Iodocytidine, 99% ▲ [1-β-D-Ribofuranosyl-5-iodocytosine] [1147-23-5], C ₉ H ₁₂ IN ₃ O ₅ , F.W. 369.11, Powder | 1g |
| J61356 | 5-Iodo-2'-deoxycytidine, 99% [IDC] [6111-53-0], C ₉ H ₁₂ IN ₃ O ₄ , F.W. 353.11, Powder, m.p. 180-183°, EINECS 210-269-8, MDL MFCD00038063 ! H:H302, P:P264-P270-P301+P312-P330-P501a | 1g 2g |
| A11542 | (+)-5-Iodo-2'-deoxyuridine, 98% ▲ [Iodoxuridine] [54-42-2], C ₉ H ₁₁ IN ₃ O ₅ , F.W. 354.10, m.p. ca 190° dec., Merck 14,4891, EINECS 200-207-8, RTECS YU7700000, BRN 30397, MDL MFCD00134656, † ! H:H351-H361, P:P281-P201-P202-P308+P313-P405-P501a |  1g 5g |
| J61498 | 2-Iodomelatonin, 98+% [N-Acetyl-2-iodo-5-methoxytryptamine] [9315-00-5], C ₁₈ H ₁₈ IN ₂ O ₂ , F.W. 358.18, Crystalline, RTECS AC4376000, MDL MFCD00055216 | 10mg 50mg |
| Application(s): Potent melatonin agonist | | |
| Iodonitrotetrazolium chloride , see Iodonitrotetrazolium violet, B22301, p. 258 | | |
| B22301 | Iodonitrotetrazolium violet, 95% ▲ [INT, Iodonitrotetrazolium chloride] [146-68-9], C ₁₉ H ₁₃ ClIN ₃ O ₂ ·xH ₂ O, F.W. 505.70(anhy), m.p. ca 231° dec., EINECS 205-676-2, BRN 4093224, MDL MFCD00149999, † ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Reagent for dehydrogenase determination: <i>Clin. Chem.</i> , 19 , 766 (1973); <i>J. Histochem. Cytochem.</i> , 28 , 408 (1980). |  1g 5g 25g |
| Application(s): Used for dehydrogenase determination | | |
| 2-(4-Iodophenyl)-3-(4-nitrophenyl)-5-phenyltetrazolium chloride hydrate , see Iodonitrotetrazolium violet, B22301, p. 258 | | |
| L15606 | 2-Iodosobenzoic acid, 97% ▲ [Iodosylbenzoic acid] [304-91-6], C ₇ H ₅ IO ₃ , F.W. 264.02, m.p. ca 230° dec., Fieser 1,509 12,259, EINECS 206-159-4, RTECS DH3056550, BRN 1939973, MDL MFCD00002401 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Probably exists as the cyclized form 1-Hydroxy-1,1-dihydro-1,2-benzodioxol-3(1H)-one; CAS registry no. [161-62-4]. Reagent for α-hydroxylation of ketones; the by-product benzoic acid is easily removed by base extraction: <i>Tetrahedron Lett.</i> , 25 , 691 (1984). For an example, see: <i>Org. Synth. Coll.</i> , 7 , 263 (1990). Catalyst for cleavage of toxic phosphates and reactive esters: <i>Tetrahedron Lett.</i> , 28 , 251 (1987); <i>J. Am. Chem. Soc.</i> , 108 , 788 (1986); 116 , 4471 (1994). For a review of polyvalent iodine compounds, see: <i>Chem. Rev.</i> , 96 , 1123 (1996). |  1g 5g |
| Application(s): Commonly used peptide reagent for cleavage at tryptophyl and tyrosyl residues | | |
| Iodosylbenzoic acid , see 2-Iodosobenzoic acid, L15606, p. 258 | | |
| A18994 | 5-Iodouracil, 97% ▲ [696-07-1], C ₄ H ₄ IN ₂ O ₂ , F.W. 237.99, m.p. 274-276°, EINECS 211-788-2, RTECS YR0525000, BRN 4891, MDL MFCD00006020, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a For a review of the use of uracils as starting materials in heterocyclic synthesis, see: <i>Adv. Het. Chem.</i> , 55 , 130 (1992). |  10g 50g 250g |



| Stock # | Description | Size |
|---------|---|---------------------------|
| J62259 | 5-Iodouridine, 96% [1024-99-3], C ₈ H ₁₁ N ₂ O ₆ , F.W. 370.10, Powder, EINECS 213-833-1, BRN 33665, MDL MFCD00006532 | 1g 5g |
| J62448 | Ionomycin, 98% [56092-81-0], C ₂₈ H ₇₂ O ₉ , F.W. 709.02, Solution in ethanol, RTECS NO0600000, BRN 3642126, MDL MFCD06798385 ! H: H302, P: P264-P270-P301+P312-P330-P501a Application(s): Highly selective and potent calcium ionophore | 1mg 5mg |
| J60628 | Ionomycin calcium salt, 99% ▲ [56092-82-1], C ₂₈ H ₇₀ CaO ₉ , F.W. 747.08, Crystalline powder, RTECS NO0650000, BRN 1416163, MDL MFCD00151183 ! H: H302, P: P264-P270-P301+P312-P330-P501a Application(s): Highly selective and potent calcium ionophore | 5mg |
| J60453 | Ipratropium bromide, 99% [22254-24-6], C ₂₀ H ₃₀ BrNO ₃ , F.W. 412.37, Powder, Merck 14,5073, EINECS 244-873-8 ! H: H302-H332-H319, P: P261-P280-P305+P351+P338-P304+P340-P301+P312-P501 Application(s): Muscarinic acetylcholine receptor antagonist and a bronchodilator IPTG, see Isopropyl-β-D-thiogalactoside, B21149, p. 261 | 100mg |
| J60743 | Irinotecan hydrochloride [100286-90-6], C ₃₃ H ₃₈ N ₄ O ₆ ·HCl, F.W. 623.14, Yellow powder, Merck 14,5091, RTECS DW1061000, MDL MFCD01862255 ! H: H302, P: P264-P270-P301+P312-P330-P501a Application(s): Topoisomerase I inhibitor | 50mg 250mg |
| J62370 | Irinotecan hydrochloride trihydrate [CPT11] [100286-90-6], C ₃₃ H ₃₈ N ₄ O ₆ ·HCl·3H ₂ O, F.W. 677.19 (623.15anhy), Crystalline powder, m.p. 256°, Merck 14,5091, RTECS DW1060750, MDL MFCD01862255 ! H: H302, P: P264-P270-P301+P312-P330-P501 Application(s): Topoisomerase I inhibitor | 100mg 250mg |
| | Iron alum , see Ammonium iron(III) sulfate dodecahydrate, 39391, p. 101 Iron(II) ammonium sulfate , see Ammonium iron(II) sulfate hexahydrate, 13448, p. 101 | |
| 12497 | Iron(III) chloride hexahydrate, ACS, 97.0-102.0% ■ [Ferric chloride hexahydrate] [10025-77-1], FeCl ₃ ·6H ₂ O, F.W. 270.30 (162.21anhy), Lump, m.p. 37°, b.p. 280-285°, d. 1.820, Merck 14,4019, Fieser 1,390 3,145 6,259 10,185 11,237 12,230 13,133 20,204 21,240, Solubility: Freely soluble in water, alcohol, ether, acetone., UN3260, EINECS 231-729-4, RTECS NO5425000, MDL MFCD00149712, Note: b.p. 280° -H ₂ O; 300° dec., † Maximum level of impurities: Insoluble matter 0.01%, NO ₃ 0.01%, Phosphorus compounds (as PO ₄) 0.01%, SO ₄ 0.01%, Ca 0.01%, Cu 0.003%, Mg 0.005%, K 0.005%, Na 0.05%, Ferrous iron (Fe ²⁺) P.T. (limit about 0.002%), Zn 0.003% ! H: H314-H302, P: P280-P305+P351+P338-P309-P310 | 25g 250g 1kg 5kg |
| A10276 | Iron(III) citrate hydrate, Fe(III) 16.5-20%; Fe(II) max 5% ▲ [Citric acid iron(III) salt, Ferric citrate] [334024-15-6], C ₆ H ₅ FeO ₇ ·xH ₂ O, F.W. 244.94(anhy), EINECS 222-536-6, MDL MFCD00149617  | 50g 250g 1kg |
| J62550 | Iron Dextran 10% Powder ! H: H334-H317-H351, P: P285-P261-P302+P352-P321-P405-P501 Application(s): Prevents and treats neonatal anemia in pigs. The least toxic iron preparation available for parenteral administration | 1kg |
| J62750 | Iron Dextran 20% Powder ! H: H334-H317-H351, P: P285-P261-P302+P352-P321-P405-P501 Application(s): Prevents and treats neonatal anemia in pigs. | 1kg |
| 33315 | Iron(III) nitrate nonahydrate, ACS, 98.0-101.0% [7782-61-8], Fe(NO ₃) ₃ ·9H ₂ O, F.W. 403.99 (241.86anhy), Crystalline, m.p. 47°, b.p. 125° dec., d. 1.684, Merck 14,4027, Solubility: Freely soluble in water, alcohol, acetone. Slightly soluble in cold and concentrated HNO ₃ , UN1466, EINECS 233-899-5, RTECS NO7175000, MDL MFCD00149708, † Maximum level of impurities: Insoluble matter 0.005%, Cl 5ppm, SO ₄ 0.01%, Ca 0.01%, Mg 0.005%, K 0.005%, Na 0.05% ! H: H272-H315-H319, P: P221-P210-P305+P351+P338-P302+P352-P321-P501a | 500g 2kg 5x2kg |

| Stock # | Description | Size |
|---------|--|----------------------------|
| A12468 | Isatin, 98% [2,3-Indolinedione] [91-56-5], C ₈ H ₅ NO ₂ , F.W. 147.13, m.p. ca 194° dec., f.p. 220°(428°F), Merck 14,5104, EINECS 202-077-8, RTECS NL7873000, BRN 383659, MDL MFCD00005718, † Isatins undergo a one-pot Wolff-Kishner like reduction with hydrazine hydrate, under surprisingly mild conditions, to give the corresponding oxindoles: <i>Synth. Commun.</i> , 24 , 2835 (1994). Reaction with acid anhydrides or condensation with 4-Methyl-2-pentanone , A11618 , results in the formation of quinoline-4-carboxylic acid derivatives; for examples, see: <i>J. Med. Chem.</i> , 35 , 4893 (1992); 36 , 617, 3286 (1993): | 100g 500g 2.5kg |
| |  | |
| | Application(s): Chromatographic spray reagent for amino acid detection | |
| A12054 | Isethionic acid sodium salt, 98% [Sodium isethionate, 2-Hydroxyethanesulfonic acid sodium salt] [1562-00-1], HO(CH ₂) ₂ SO ₃ Na, F.W. 148.11, m.p. 191-194°, EINECS 216-343-6, RTECS K17700000, BRN 3633992, MDL MFCD00007534, † | 1kg 5kg |
| | Application(s): A surfactant and skin and mucous membrane irritant | |
| 36366 | D-(-)-Isoascorbic acid, 99% [D-(-)-Araboascorbic acid, Erythorbic acid] [89-65-6], C ₆ H ₈ O ₆ , F.W. 176.12, Powder, m.p. 169-172° dec., Merck 14,5126, EINECS 201-928-0, MDL MFCD00005378, † | 100g 500g |
| |  | |
| | Isobutanolamine, see 2-Amino-2-methyl-1-propanol, A17814, p. 97 | |
| B20989 | 4-Isobutyl-α-methylphenylacetic acid, 99% [Ibuprofen] [15687-27-1], C ₁₃ H ₁₈ O ₂ , F.W. 206.29, m.p. 75-78°, b.p. 157°/4mm, Merck 14,4881, UN3077, EINECS 239-784-6, RTECS MU6640000, MDL MFCD00010393, †  H: H361-H302-H411, P: P281-P273-P301+P312-P308+P313-P405-P501a | 1g 5g 25g |
| |  | |
| | Application(s): NSAID that inhibits cyclooxygenase-1 and -2 | |
| J65249 | N₂-Isobutyryl-2'-O-methylguanosine, 98% C ₁₅ H ₂₁ N ₅ O ₈ , F.W. 367.36, Powder  H: H302-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| J65073 | Isocitrate Dehydrogenase [EC 1.1.1.42] Lyophilized powder, Note: Component in the Cofactor Recycling Enzymes Kit, item J64535 | 250mg 500mg 1g |
| H54228 | Isocytosine, 99% [2-Amino-4-hydroxypyrimidine] [108-53-2], C ₄ H ₅ N ₃ O, F.W. 111.10, EINECS 203-592-0, MDL MFCD00057557 | 1g 5g 25g |
| |  | |
| | 4',7-Isouflavandiol, see (R,S)-Equol, J61383, p. 209 | |
| J63243 | Isoguvacine hydrochloride, 99% [1,2,3,6-Tetrahydro-4-pyridinecarboxylic acid hydrochloride] [64603-90-3], C ₆ H ₉ NO ₂ ·HCl, F.W. 163.60, Powder | 100mg |
| | Application(s): Specific GABA agonist | |
| A17521 | DL-Isoleucine, 99% [(+/-)-2-Amino-3-methylpentanoic acid, H-DL-Ile-OH] [443-79-8], C ₆ H ₁₃ NO ₂ , F.W. 131.18, m.p. ca 280° dec., Merck 14,5179, EINECS 207-139-8, BRN 1721796, MDL MFCD00004268, † | 25g 100g |
| |  | |
| H27488 | D-Isoleucine, 98% [(2R,3R)-2-Amino-3-methylpentanoic acid, H-D-Ile-OH] [319-78-8], C ₆ H ₁₃ NO ₂ , F.W. 131.18, m.p. 265° subl., EINECS 206-269-2, RTECS NR4700000, MDL MFCD00064221 | 250mg 1g |
| |  | |
| A13699 | L-Isoleucine, 99% [(2S,3S)-2-Amino-3-methylpentanoic acid, H-Ile-OH] [73-32-5], C ₆ H ₁₃ NO ₂ , F.W. 131.18, m.p. ca 287° dec., [α] _D ²⁰ +40° (c=5 in 6N HCl), Merck 14,5179, EINECS 200-798-2, RTECS NR4705000, BRN 1721792, MDL MFCD00064222, † | 10g 50g 100g 250g |
| |  | |
| J63045 | L-Isoleucine, Cell Culture Reagent [(2S,3S)-2-Amino-3-methylpentanoic acid, H-Ile-OH] [73-32-5], C ₆ H ₁₃ NO ₂ , F.W. 131.18, Powder, m.p. ca 287° dec., Merck 14,5179, EINECS 200-798-2, RTECS NR4705000, BRN 1721792, MDL MFCD00064222, † | 25g 100g |

| Stock # | Description | Size |
|---------|---|----------------------------|
| J64087 | L-Isoleucine 7-amido-4- methylcoumarin trifluoroacetate salt [H-Ile-AMC TFA] [191723-68-9], C ₁₆ H ₂₀ N ₂ O ₅ , F.W. 402.36, Powder | 50mg |
| | L-Isoleucyl-L-prolyl-L-isoleucine , see Diprotin A , J60369, p. 199 | |
| J60884 | Isomaltose [6-O-α-D-Glucopyranosyl-D-glucose, α-1,6-Glucobiose] [499-40-1], C ₁₂ H ₂₂ O ₁₁ , F.W. 342.30, Powder, EINECS 207-879-1, BRN 93355, MDL MFCD00065373 | 1g |
| | Isomaltulose , see Palatinose hydrate, 98+%, J60091, p. 311 | |
| | Isoniazid , see Isonicotinic acid hydrazide, A10583, p. 261 | |
| A18109 | Isonicotinic acid, 99% [Pyridine-4-carboxylic acid] [55-22-1], C ₆ H ₅ NO ₂ , F.W. 123.11, m.p. ca 310° subl., b.p. 260°/15mm, Merck 14,5187, EINECS 200-228-2, RTECS NS1103000, BRN 109599, MDL MFCD00006429, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 100g 500g 2.5kg |
| A10583 | Isonicotinic acid hydrazide, 98+% [Isoniazid, Pyridine-4-carboxylic hydrazide] [54-85-3], C ₆ H ₇ N ₃ O, F.W. 137.14, m.p. 169-174°, Merck 14,5186, EINECS 200-214-6, RTECS NS1751850, BRN 119374, MDL MFCD00006426, † ! H:H351-H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 50g 100g 500g 1kg |
| | Application(s): Used for fluorescent HPLC detection of delta 4-3-ketosteroids | |
| A11795 | Isonipecotic acid, 98% [H-DL-Inp-OH, Piperidine-4-carboxylic acid] [498-94-2], C ₈ H ₁₁ NO ₂ , F.W. 129.16, m.p. >350°, Merck 14,5189, EINECS 207-872-3, RTECS NS5150000, BRN 112553, MDL MFCD00006004, † | 25g 100g |
| | Application(s): A GABA-A receptor partial agonist | |
| | (R)-(-)-Isopropanolamine, see (R)-(-)-1-Amino-2-propanol, L14101, p. 99 (S)-(+)-Isopropanolamine, see (S)-(+)-1-Amino-2-propanol, L14102, p. 99 (+)-1-(Isopropylamino)-3-[4-(β-methoxyethyl)phenoxy]-2-propanol (+)-tartrate salt, see Metoprolol tartrate, 98+%, J61920, p. 291 1-Isopropylamino-3-(1-naphthyl)-2-propanol hydrochloride, see (±)-Propranolol hydrochloride, H26645, p. 329 Isopropyl carbanilate, see Isopropyl N-phenylcarbamate, B24998, p. 261 (±)-1,2-O-Isopropylidene glycerol, see Solketal, L02814, p. 349 1-Isopropyl-4-methyl-1,3-cyclohexadiene, see α-Terpinene, J62871, p. 360 (±)-2-Isopropyl-5-methylcyclohexanol, see DL-Menthol, A18098, p. 280 (1R,2S,5R)-2-Isopropyl-5-methylcyclohexanol, see L-Menthol, A10474, p. 280 (1S,2R,5S)-2-Isopropyl-5-methylcyclohexanol, see D-Menthol, L06102, p. 280 2-Isopropyl-5-methylphenol, see Thymol, A14563, p. 369 N-Isopropyl-DL-noradrenaline hydrochloride, see DL-Isoproterenol hydrochloride, 99%, J61788, p. 261 | |
| B24998 | Isopropyl N-phenylcarbamate, 96% [Isopropyl carbanilate] [122-42-9], C ₁₀ H ₁₃ NO ₂ , F.W. 179.22, m.p. 86-89°, EINECS 204-542-0, RTECS FD9100000, MDL MFCD00026382, † ! H:H302, P:P264-P270-P301+P312-P330-P501a | 5g 25g 100g |
| | Application(s): Inhibitor of plant metabolism | |
| B21149 | Isopropyl-β-D-thiogalactoside, dioxane-free, 99% [IPTG] [367-93-1], C ₈ H ₁₆ O ₅ , F.W. 238.30, m.p. 109-115°, [α] _D ²⁰ -32° (c=1 in water), EINECS 206-703-0, BRN 4631, MDL MFCD00063273, † | 1g 5g |
| | Application(s): β-galactosidase inducer | |
| J61788 | DL-Isoproterenol hydrochloride, 99% [(±)-Isoproterenol hydrochloride, N-Isopropyl-DL-noradrenaline hydrochloride] [51-30-9], C ₁₁ H ₁₇ NO ₂ ·HCl, F.W. 247.72, Crystalline powder, m.p. 165-175° dec., EINECS 200-089-8, RTECS DO1925000, BRN 3917363, MDL MFCD00012603 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 25g |
| | Application(s): Standard selective β-adrenoceptor agonist | |
| | (+)-Isoproterenol hydrochloride, see DL-Isoproterenol hydrochloride, 99%, J61788, p. 261 1-isoquinoline-5-sulfonic 2-methyl-1-piperazine dihydrochloride, see H-7 dihydrochloride, J61697, p. 240 1-(5-isoquinolylsulfonyl)-2-methylpiperazine dihydrochloride, see H-7 dihydrochloride, J61697, p. 240 | |
| J63674 | Isosorbide mononitrate, 98+% [16051-77-7], C ₈ H ₉ NO ₃ , F.W. 191.14, Crystalline powder, m.p. 92°, Merck 14,5225, UN3251, EINECS 240-197-2, RTECS LZ4386500, MDL MFCD00143462 ! H:H228-H302, P:P210-P241-P280-P240-P301+P312-P501a | 5g 10g 25g |
| | Application(s): A coronary vasodilator that does not require hepatic biotransformation | |
| | Isotretinoin , see 13-cis-Retinoic acid, J61666, p. 336 | |
| J63920 | Isradipine, 98+% [PN 200-110] [75695-93-1], C ₁₈ H ₂₁ N ₃ O ₅ , F.W. 371.39, Crystalline powder, Merck 14,5240, MDL MFCD00153820 | 10mg 50mg |
| | Application(s): L-type calcium channel blocker | |

| Stock # | Description | Size |
|---------|---|---|
| A15566 | Itaconic acid, 99% ■ [Methylenebutanedioic acid, Methylene succinic acid] [97-65-4], C ₄ H ₄ O ₄ , F.W. 130.10, m.p. 165-169°, b.p. 268°, d. 1.630, Merck 14,5242, EINECS 202-599-6, BRN 1759501, MDL MFCD00004260, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a |  250g 1kg 5kg |
| J62777 | Ivermectin [22,23-Dihydroavermectin B1, MK-933] [70288-86-7], C ₃₈ H ₇₄ O ₁₄ , F.W. 875.11, Powder, Merck 14,5248, UN2811, EINECS 274-536-0, RTECS IH7891500, MDL MFCD00869511  H:H300-H360-H319, P:P280-P301+P310-P305+P351+P338-P321-P405-P501a Application(s): Antiparasitic and macrolide antibiotic. Modulates glutamate-GABA-activated chloride channels. Also activates the glycine receptor chloride channel | 1g |
| J65506 | JAK2 Inhibitor IV ▲ [4-(3-Amino-1H-indazol-4-yl)-N-(tert-butyl)benzenesulfonamide] [1110502-30-1], C ₁₇ H ₂₀ N ₄ O ₂ S, F.W. 344.40, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5mg |
| A17391 | Janus Green B [C.I. 11050] [2869-83-2], C ₂₃ H ₃ ClN ₆ , F.W. 511.07, Merck 14,5255, EINECS 220-695-6, RTECS SG1633000, MDL MFCD00011758, †  | 5g 25g |
| J61077 | Jenner's Stain [Eosin-Methylene Blue] [62851-42-7], Powder, MDL MFCD00081733 Application(s): For use in staining blood smears | 25g 100g |
| J65433 | JNJ 10191584 maleate [VUF 6002 maleate, 1-[(5-Chloro-1H-benzimidazol-2-yl)carbonyl]-4-methylpiperazine maleate] [869497-75-6], C ₁₃ H ₁₅ ClN ₄ O ₄ , F.W. 394.81, Powder, MDL MFCD09878266 ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10mg 50mg |
| J62245 | Josamycin, 98+% [Leucomycin A3] [16846-24-5], C ₂₂ H ₃₉ NO ₁₅ , F.W. 827.99, Powder, EINECS 240-871-6, RTECS OH4725810, MDL MFCD00211043 Application(s): Macrolide antibiotic K252a, see Protein Kinase Inhibitor, J61687, p. 331 | 100mg |
| J63090 | K252c, 99% [Staurosporinone, 6,7,12,13-Tetrahydro-5H-indolo[2,3-a]pyrrolo[3,4-c]carbazol-5-one] [85753-43-1], C ₂₀ H ₁₃ N ₅ O, F.W. 311.34, Crystalline solid Application(s): Inhibits protein kinase C | 1mg 5mg |
| J60373 | Kaempferol, 98+% [3,4',5,7-Tetrahydroxyflavone] [520-18-3], C ₁₅ H ₁₀ O ₆ , F.W. 286.24, Powder, m.p. 276-278°, Merck 14,5274, EINECS 208-287-6, RTECS LK9275200, BRN 3044401, MDL MFCD00016938 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): Inhibits topoisomerase I catalyzed DNA religation. Induces apoptosis and is cytotoxic to human leukemic cell lines Kallidin, see Lys-Bradykinin, J62067, p. 273 Kallidin, see Lys-Bradykinin acetate salt, J61171, p. 135 | 10mg 50mg |
| J61272 | Kanamycin monosulfate [Kanamycin A] [25389-94-0], C ₁₈ H ₃₆ N ₄ O ₁₁ ·H ₂ SO ₄ , F.W. 582.58, Powder, Merck 14,5281, EINECS 246-933-9, RTECS NZ3225030, MDL MFCD00070253  H:H334-H360-H317, P:P285-P261-P302+P352-P321-P405-P501a Application(s): Antibiotic. Inhibits translocation during protein biosynthesis Kanamycin A, see Kanamycin monosulfate, J61272, p. 262 | 10g 100g |
| J60668 | Kanamycin monosulfate, Cell Culture Grade [Kanamycin A] [25389-94-0], C ₁₈ H ₃₆ N ₄ O ₁₁ ·H ₂ SO ₄ , F.W. 582.58, Powder, Merck 14,5281, EINECS 246-933-9, RTECS NZ3225030, MDL MFCD00070253  H:H334-H360-H317, P:P285-P261-P302+P352-P321-P405-P501a | 1g 5g 10g |
| J61844 | Karaya Gum [Gum karaya from sterculia tree, Tragacanth Indian] [9000-36-6], Powder, Merck 14,5284, EINECS 232-539-4, MDL MFCD00131251, † Application(s): Used as a thickener and emulsifier | 500g |









| Stock # | Description | Size |
|---|---|-------|
| J60353 | Kassinin, 96% [<i>H-Asp-Val-Pro-Lys-Ser-Asp-Gln-Phe-Val-Gly-Leu-Met-NH2</i>] [63968-82-1], C ₅₉ H ₉₅ N ₁₃ O ₁₆ S, F.W. 1334.56, Powder | 1mg |
| | | 2mg |
| | | 5mg |
| Application(s): Peptide of the tachykinin family | | |
| J65495 | Katacalcin [<i>Asp-Met-Ser-Ser-Asp-Leu-Glu-Arg-Asp-His-Arg-Pro-His-Val-Ser-Met-Pro-Gln-Asn-Ala-Asn</i>] [85916-47-8], C ₉₇ H ₁₅₄ N ₃₄ O ₃₆ S ₂ , F.W. 2436.59, Solid | 0.5mg |
| | | 1mg |
| J65791 | kb NB 142-70 ▲ [<i>9-Hydroxy-3,4-dihydrobenzo[4,5]thieno[2,3-f][1,4]thiazepin-5(2H)-one</i>] C ₁₁ H ₉ NO ₂ S, F.W. 251.32, Solid | 10mg |
| J60591 | Kemptide [<i>Phosphate acceptor peptide, Leu-Arg-Arg-Ala-Ser-Leu-Gly</i>] [65189-71-1], C ₃₂ H ₆₁ N ₁₃ O ₉ , F.W. 771.91, Powder, BRN 6263936, MDL MFCD00076710 | 1mg |
| | | 5mg |
| Application(s): Synthetic peptide substrate for protein kinase A | | |
| J61809 | Kentsin [<i>Contraceptive Tetr peptide, H-Thr-Pro-Arg-Lys-OH</i>] [56767-30-7], C ₂₁ H ₄₀ N ₆ O ₆ , F.W. 500.60, Lyophilized powder | 25mg |
| | | 100mg |
| J62798 | Ketanserin tartrate, 98+% [R 41 468] [83846-83-7], C ₂₈ H ₂₇ FN ₃ O ₃ , F.W. 545.52, Powder, Merck 14,5296, UN2811, EINECS 281-062-8, RTECS VA1411195, MDL MFCD00084651 | 50mg |
| | | 250mg |
|  H: H301, P: P264-P270-P301+P310-P321-P405-P501a | | |
| Application(s): Selective 5-HT _{2A} serotonin receptor antagonist | | |
| J60090 | Kethoxal [<i>2-Keto-3-ethoxybutyraldehyde</i>] [27762-78-3], C ₆ H ₁₂ O ₄ , F.W. 148.16, Liquid, Merck 14,5299 | 5g |
| | | 10g |
| Application(s): Antiviral agent that reacts with 30S ribosomal subunits | | |
| J63367 | Ketoconazole, 98+% [65277-42-1], C ₂₈ H ₂₆ Cl ₂ N ₄ O, F.W. 531.43, Powder, Merck 14,5302, UN2811, EINECS 265-667-4, RTECS TK7912300, MDL MFCD00058579 | 5g |
| | | 25g |
|  H: H301-H360F-H373-H400-H410, P: P260-P281-P301+P310-P321-P405-P501a | | |
| Application(s): Potent inhibitor of cytochrome P450c17 | | |
| 2-Keto-3-ethoxybutyraldehyde, see Kethoxal, J60090, p. 263 | | |
| A10256 | 2-Ketoglutaric acid, 98% [<i>2-Oxoglutaric acid</i>] [328-50-7], C ₅ H ₇ O ₅ , F.W. 146.10, m.p. 113-117°, Merck 14,5303, Fieser 1,531, EINECS 206-330-3, BRN 1705689, MDL MFCD00004165, † | 25g |
| | | 100g |
|  | | 500g |
|  H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | | |
| J63154 | α-Ketoglutaric acid disodium salt dihydrate, 99% ■ [305-72-6], C ₅ H ₇ Na ₂ O ₅ ·2H ₂ O, F.W. 226.09 (190.06anhy), Powder, EINECS 206-167-8, RTECS SA0454700, MDL MFCD00150702 | 1g |
| | | 25g |
| | | 100g |
| 250g | | |
| J62702 | Ketoprofen [<i>(2-[3-Benzoylphenyl]propionic acid)</i>] [22071-15-4], C ₁₈ H ₁₅ O ₃ , F.W. 254.29, Powder, m.p. 92-97°, Merck 14,5305, UN2811, EINECS 244-759-8, RTECS UE7570000, MDL MFCD00055790, † | 5g |
| | | 25g |
|  H: H301-H315-H319-H335, P: P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a | | |
| Application(s): A non-steroidal anti-inflammatory drug (NSAID); also inhibits cyclooxygenases-1 and -2 | | |
| α-Ketopropionic acid sodium salt, see Sodium pyruvate, Cell Culture Grade, J61840, p. 348 | | |
| J63708 | Ketotifen fumarate, 99% [34580-14-8], C ₁₉ H ₁₉ NOS ₃ , F.W. 425.50, Powder, Merck 14,5307, EINECS 252-100-0, RTECS DE8260000, MDL MFCD00079394 | 250mg |
| | | 1g |
|  H: H302, P: P264-P270-P301+P312-P330-P501 | | |
| Application(s): A H ₁ -histamine receptor antagonist that inhibits the anaphylactic release of histamine | | |
| J61967 | Kinase buffer I (5X) Liquid, Note: This buffer contains: 100mM Tris-HCl 100, 50mM magnesium chloride, 5mM dithiothreitol, and 5mM sodium orthovanadate, pH 7.4. | 100ml |
| | | 250ml |
| J60269 | Kinase buffer II (5X) Liquid, Note: This buffer contains: 100mM MOPS, 50mM magnesium acetate, 5mM DTT 5, 5mM EDTA, 25mM beta glycerophosphate, and 5mM sodium orthovanadate, pH 7.4. | 100ml |
| | | 250ml |

| Stock # | Description | Size |
|---------|---|---|
| J61566 | Kinase buffer III (5X) Liquid, Note: This buffer contains: 100mM PIPES and 50mM manganese chloride at pH 8.0 | 100ml 250ml |
| J63665 | Kinase buffer IV (5X) Liquid, Note: This buffer contains: 200mM HEPES, 25 mM magnesium acetate, 10mM DTT, and 0.5mM EDTA, pH 8.0. | 100ml 250ml |
| J62045 | Kinase buffer V (5X) Liquid, Note: This buffer contains: 100mM MOPS, 50mM magnesium chloride, and 50mM manganese chloride, pH 7.4. | 100ml 250ml |
| J63719 | Kinase Storage Buffer Liquid, Note: This buffer contains: 10mM Tris, 50mM sodium chloride, 1mM magnesium chloride, and 50% glycerol, pH 7.5. ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 100ml 250ml |
| J63865 | Kinetensin <i>[Ile-Ala-Arg-Arg-His-Pro-Tyr-Phe-Leu, Neurotensin-related peptide]</i> [103131-69-7], C ₅₆ H ₈₅ N ₁₇ O ₁₁ , F.W. 1172.38, Powder Application(s): Increases vascular permeability | 1mg |
| A13720 | Kinetin, 99% <i>[N(6)-Furfuryladenine, 6-Furfurylamino-purine]</i> [525-79-1], C ₁₀ H ₉ N ₅ O, F.W. 215.22, m.p. ca 270° dec., Merck 14,5311, EINECS 208-382-2, RTECS AU6270000, BRN 21703, MDL MFCD00075757, † Enhances the rate of cell-division in plants: <i>Plant Physiol.</i> , 54 , 644 (1974). Application(s): Plant growth accelerator |  1g 5g 25g |
| J65487 | Kisspeptin-10 <i>[Metastin (45-54), amide, human, Tyr-Asn-Trp-Asn-Ser-Phe-Gly-Leu-Arg-Phe-NH2]</i> C ₆₃ H ₈₃ N ₁₇ O ₁₄ , F.W. 1302.44, Powder, MDL MFCD03452696 | 0.5mg 1mg |
| J64054 | Kisspeptin-13 <i>[Leu-Pro-Asn-Tyr-Asn-Trp-Asn-Ser-Phe-Gly-Leu-Arg-Phe-NH2]</i> [374675-18-0], C ₇₈ H ₁₀₇ N ₂₁ O ₁₈ , F.W. 1626.81, Solid | 0.5mg 1mg |
| A14769 | Kiton Red S <i>[C.I. 45100, Sulforhodamine B]</i> [3520-42-1], C ₂₇ H ₂₈ N ₂ NaO ₅ S ₂ , F.W. 580.66, EINECS 222-529-8, RTECS BP6750000, BRN 3886008, MDL MFCD00010180, † Application(s): Fluorescent dye which uses laser-induced fluorescence for quantification of cellular proteins | 5g 25g |
| J62444 | KN-62 [127191-97-3], NH ₂ (CH ₂) ₁₀ NH ₂ , F.W. 721.84, Powder, m.p. 65-67°, MDL MFCD00083180 Application(s): Potently and specifically inhibits calcium/calmodulin kinase II | 1mg 10mg |
| A10760 | Kojic acid, 99% <i>[5-Hydroxy-2-(hydroxymethyl)-4H-pyran-4-one]</i> [501-30-4], C ₆ H ₆ O ₄ , F.W. 142.11, m.p. 152-155°, Merck 14,5317, EINECS 207-922-4, RTECS UQ0875000, BRN 120895, MDL MFCD00006580 H:H351, P:P281-P201-P202-P308+P313-P405-P501a Application(s): A chelation agent that inhibits melanin production. Also a tyrosine kinase inhibitor |  5g 25g 100g |
| J60199 | L-Kynurenine <i>[β-Anthraniloyl-L-alanine, L-2-Amino-4-(2-aminophenyl)-4-oxobutanoic acid]</i> [2922-83-0], C ₁₀ H ₁₂ N ₂ O ₅ , F.W. 208.21, Crystalline, RTECS CY9049700, MDL MFCD00069912 Application(s): Intermediate in the breakdown of tryptophan | 50mg |
| J63771 | Kyotorphin <i>[H-Tyr-Arg-OH]</i> [70904-56-2], C ₁₅ H ₂₃ N ₃ O ₄ , F.W. 337.38, Powder Application(s): Analgesic opioid peptide that modulates the Na ⁺ /Cl ⁻ dependent opioid peptide transporter | 5mg |
| J63215 | Lactalbumin hydrolysate <i>[Enzymatic Digest of Lactalbumin]</i> [68458-87-7], Powder, EINECS 270-615-9, MDL MFCD00147378, † Application(s): A solubilized enzymatic digest of lactalbumin | 500g 1kg 2.5kg |

| Stock # | Description | Size |
|---------|---|----------------------|
| J63220 | Lactate dehydrogenase, rabbit muscle [E.C. 1.1.1.27, NAD oxidoreductase] [9001-60-9], Suspension, Merck 14,5334, EINECS 232-617-8, MDL MFCD00131466, Note: Minimum 400units/mg protein. One unit will reduce 1.0 micromole of pyruvate to L-lactate per min at pH 7.5 at 37 C, † Application(s): Catalyzes the interconversion of pyruvate and lactate with concomitant interconversion of NADH and NAD+ | 50kilounits |
| L14259 | DL-Lactic acid, 80-85% aq. soln. [2-Hydroxypropionic acid] [50-21-5], C ₃ H ₅ O ₃ , F.W. 90.08, b.p. 122°/15mm, f.p. >110°(230°F), d. 1.209, n _D ²⁰ 1.4230, Merck 14,5336, EINECS 200-018-0, RTECS OD2800000, BRN 1209341, MDL MFCD00004520, † H: H318-H315, P: P280b-P305+P351+P338-P310 | 250g 1kg 2.5kg |
| 36415 | Lactic acid, ACS, 85.0-90.0% aq. soln. [2-Hydroxypropionic acid] [50-21-5], C ₃ H ₅ O ₃ , F.W. 90.08, Liquid, m.p. 18°, b.p. 122°/15mm, f.p. >110°(230°F), d. 1.209, n _D ²⁰ 1.4270, Merck 14,5336, EINECS 200-018-0, RTECS OD2800000, BRN 1209341, MDL MFCD00004520, Note: Product is predominantly the L-isomer., † Maximum level of impurities: Residue after ignition 0.02%, Cl 0.001%, SO ₂ 0.002%, Heavy Metals (as Pb) 5ppm, Fe 5ppm, Substances darkened by sulfuric acid P.T. H: H318-H315, P: P280b-P305+P351+P338-P310 | 100g 500g 2kg |
| J61871 | D-Lactic acid [(R)-2-Hydroxypropionic acid, H-D-Lac-OH] [10326-41-7], C ₃ H ₅ O ₃ , F.W. 90.08, Powder, m.p. 52°, Merck 14,5335, EINECS 233-713-2, BRN 1720254, MDL MFCD00068313, † H: H318-H315, P: P280-P305+P351+P338-P302+P352-P321-P310-P362 | 250mg 1g |
| L13242 | L-Lactic acid, anhydrous, 98% ■ [(S)-2-Hydroxypropionic acid] [79-33-4], C ₃ H ₅ O ₃ , F.W. 90.08, m.p. 52-54°, b.p. 119°/12mm, f.p. >110°(230°F), d. 1.22, Merck 14,5337, Fieser 15,181, EINECS 201-196-2, RTECS OD3100000, BRN 1720251, MDL MFCD00064266, † H: H318-H315, P: P280b-P305+P351+P338-P337+P313 | 5g 25g 100g |
| 36218 | α-D-Lactose monohydrate, ACS [64044-51-5], C ₁₂ H ₂₂ O ₁₁ ·H ₂ O, F.W. 360.32 (342.30anhy), Crystalline, m.p. ca 218° dec., d. 1.525, Merck 14,5343, EINECS 200-559-2, RTECS OD9625000, BRN 3768231, MDL MFCD00150747, † Maximum level of impurities: Insoluble matter 0.005%, Residue after ignition 0.03%, Dextrose P.T., Sucrose P.T., Heavy Metals (as Pb) 5ppm, Fe 5ppm, H ₂ O 4.0-6.0% H: H318-H315, P: P280-P305+P351+P338-P337+P313 | 500g 2kg |
| J60160 | Lactulose, 99% [4-O-β-D-Galactopyranosyl-D-fructose] [4618-18-2], C ₁₂ H ₂₂ O ₁₁ , F.W. 324.30, Powder, m.p. 169°, d. 1.32, Merck 14,5346, EINECS 225-027-7, RTECS LS6965000, BRN 93773, MDL MFCD00151469, † | 25g 50g 100g |
| J63615 | Laemmli SDS sample buffer, non-reducing (4X) Liquid, Note: Contains 250mM Tris-HCl (pH 6.8), 8% SDS, 40% glycerol, and 0.02% bromophenol blue., † H: H319, P: P280-P264-P305+P351+P338-P337+P313 | 25ml 50ml |
| J60660 | Laemmli SDS sample buffer, non-reducing (6X) Liquid, Note: Contains 375mM Tris-HCl (pH 6.8), 9% SDS, 50% glycerol, and 0.03% bromophenol blue. H: H319, P: P280-P264-P305+P351+P338-P337+P313 | 25ml 50ml |
| J60015 | Laemmli SDS sample buffer, reducing (4X) Liquid, Note: Contains 250mM Tris-HCl(pH 6.8), 8% SDS, 40% glycerol, 8% β-mercaptoethanol, and 0.02% bromophenol blue., † H: H318-H315-H412, P: P280-P305+P351+P338-P302+P352-P321-P310-P501a | 25ml 50ml |
| J61337 | Laemmli SDS sample buffer, reducing (6X) Liquid, Note: Contains 375mM Tris-HCl (pH 6.8), 9% SDS, 50% glycerol, 9% beta-mercaptoethanol, 0.03% bromophenol blue, † H: H318-H302-H315-H412, P: P280-P305+P351+P338-P302+P352-P321-P310-P501a | 25ml 50ml |
| J61716 | Laemmli SDS sample buffer with pyronin Y, non-reducing (4X) Liquid, Note: Contains 250mM Tris-HCl (pH 6.8), 8% SDS, 40% glycerol and 0.02% pyronin Y H: H319, P: P280-P264-P305+P351+P338-P337+P313 | 25ml 50ml |
| | Application(s): For protein sample preparation to be used in the Laemmli SDS-PAGE system | |


| Stock # | Description | Size |
|---------|--|----------------------|
| J62115 | Laemmli SDS sample buffer with pyronin Y, reducing (4X) Liquid, Note: Contains 250mM Tris-HCl (pH 6.8), 8% SDS, 40% glycerol, 8% β-mercaptoethanol, and 0.02% pyronin Y ! H:H312-H319, P:P280-P305+P351+P338-P302+P352-P322-P312-P501 | 25ml 50ml |
| | Application(s): For protein sample preparation to be used in the Laemmli SDS-PAGE system | |
| J64340 | Laminin (925-933) [Cys-Asp-Pro-Gly-Tyr-Ile-Gly-Ser-Arg] [110590-60-8], C ₄₀ H ₆₂ N ₁₂ O ₁₄ S, F.W. 967.05, Solid, MDL MFCD00076474 | 0.5mg 1mg |
| J64127 | Laminin (929-933) [Laminin Pentapeptide, Tyr-Ile-Gly-Ser-Arg] [110590-64-2], C ₂₆ H ₄₂ N ₆ O ₈ , F.W. 594.66, Solid | 1mg |
| J65640 | Laminin A Chain (2091-2108) [Cys-Ser-Arg-Ala-Arg-Lys-Gln-Ala-Ala-Ser-Ile-Lys-Val-Ala-Val-Ser-Ala-Asp-Arg] C ₈₂ H ₁₄₈ N ₃₁ O ₂₆ S, F.W. 2016.30, Solid | 0.5mg 1mg |
| J64356 | Laminin Pentapeptide amide [Tyr-Ile-Gly-Ser-Arg-NH ₂] C ₂₆ H ₄₃ N ₆ O ₇ , F.W. 593.67, Solid | 1mg |
| A16902 | Lanolin [Wool fat] [8006-54-0], m.p. 38-44°, Merck 14,5358, EINECS 232-348-6, RTECS OE3201000, MDL MFCD00081740, † | 250g 1kg |
| J62008 | Lansoprazole, 98+% [AG-1749] [103577-45-3], C ₁₆ H ₁₄ F ₃ N ₃ O ₂ S, F.W. 369.36, Crystalline powder, m.p. 173-175°, Merck 14,5362, RTECS DD9487500, MDL MFCD00866873 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 500mg 1g 5g |
| | Application(s): A proton pump inhibitor | |
| J62299 | Lapatinib, 99+% [231277-92-2], C ₂₅ H ₂₆ ClFN ₂ O ₄ S, F.W. 581.06, Powder, m.p. >240°, Merck 14,5367, RTECS VA0952500 ↓ ! H:H361-H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P405-P501a | 100mg 200mg 1g |
| | Application(s): An EGFR and HER2/neu (ErbB-2) dual tyrosine kinase inhibitor | |
| J62401 | Lapatinib ditosylate, 99+% [388082-78-8], C ₂₅ H ₂₆ ClFN ₂ O ₄ S·2C ₇ H ₈ O ₃ S, F.W. 925.46, Powder, m.p. 245-249°, Merck 14,5367 | 100mg 500mg 1g |
| | Application(s): An EGFR and HER2/neu (ErbB-2) dual tyrosine kinase inhibitor | |
| | Larapam , see Piroxicam, J63239, p. 323 | |
| J60040 | N-Lauroylsarcosine sodium salt, 95% ■ [N-Dodecanoyl-N-methylglycine sodium salt, Sarkosyl NL] [137-16-6], CH ₃ (CH ₂) ₁₀ CON(CH ₃)CH ₂ COONa, F.W. 293.39, Powder, Merck 14,4368, EINECS 205-281-5, BRN 5322974, MDL MFCD00042728, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10g 50g |
| | Application(s): Used in the cell lysis step of RNA purification. Anionic detergent | |
| J64928 | N-Lauroylsarcosine sodium salt, ultrapure, 97% ■ [N-Dodecanoyl-N-methylglycine sodium salt, Sarkosyl NL] [137-16-6], C ₁₅ H ₂₉ NNaO ₃ , F.W. 293.39, Powder, Merck 14,4368, EINECS 205-281-5, BRN 5322974, MDL MFCD00042728, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | Call |
| | Lauryl gallate , see n-Dodecyl gallate, L06233, p. 201 | |
| | Lavendustin , see HDBA, 98+%, J60507, p. 241 | |
| J61525 | LB Agar plate, plain Solid | 20plates |
| J64986 | Lysozyme, human, Enzyme Immunoassay Kit Note: One kit contains sufficient reagents and 1 precoated 96-well strip plate to perform ELISA for human lysozyme | 1kit |
| | Application(s): For detection of lysozyme. Detection range of 0.78-50ng/ml. | |
| J63497 | LB Agar plate with 20µg/ml ampicillin Solid | 20plates |
| J61314 | LB Agar plate with 50µg/ml ampicillin Solid | 20plates |
| J63197 | LB Agar plate with 100µg/ml ampicillin Solid | 20plates |

| Stock # | Description | Size |
|---------|---|--------------|
| J61842 | LB Agar plate with 50µg/ml ampicillin + tetracycline Solid | 20plates |
| J62796 | LB Agar plate with 100µg/ml ampicillin + tetracycline Solid | 20plates |
| J60487 | LB Agar plate with 25µg/ml kanamycin Solid | 20plates |
| J60540 | LB Agar plate with 50µg/ml kanamycin Solid | 20plates |
| J63541 | LB Agar plate with 10µg/ml streptomycin Solid | 20plates |
| J62665 | LB Agar plate with 50µg/ml streptomycin Solid | 20plates |
| J62894 | LB Agar plate with 10µg/ml tetracycline Solid | 20plates |
| J60347 | LB Agar plate with 50µg/ml tetracycline Solid | 20plates |
| J61405 | LB Agar plate with 20µg/ml carbenicillin Solid | 20plates |
| J62338 | LB Agar plate with 50µg/ml carbenicillin Solid | 20plates |
| J62923 | LB Agar plate with 25µg/ml chloramphenicol Solid | 20plates |
| J61140 | LB Agar plate with 50µg/ml chloramphenicol Solid | 20plates |
| J63820 | LB Agar plate with 50µg/ml gentamycin Solid | 20plates |
| J63211 | LB Agar plate with 25µg/ml NZY-kanamycin Solid | 20plates |
| J63296 | LB Agar plate with 50µg/ml NZY-kanamycin Solid | 20plates |
| J63732 | LB Agar plate with 25µg/ml spectinomycin Solid | 20plates |
| J60541 | LB Agar plate with 50µg/ml spectinomycin Solid | 20plates |
| H26760 | LB Broth (Lennox) ▣ ▣ [Luria Bertani Broth (Lennox)] MDL MFCD00147395 | 100g 500g |
| H26676 | LB Broth (Miller's modification) ▣ MDL MFCD00240868 | 100g 500g |
| J63905 | LB Medium, Miller Liquid, Note: Ingredients (per liter amounts): 10g Bacto tryptone, 5g Bacto yeast extract, 10g NaCl | 500ml 1L |
| J64111 | Lck Inhibitor II ▲ [3-(2-(1H-Benzo[d]imidazol-1-yl)-6-(2-morpholinoethoxy)-pyrimidin-4-ylamino)-4-methylphenol] [918870-43-6], C ₂₄ H ₂₆ N ₆ O ₃ , F.W. 446.50, Solid | 5mg |
| J61894 | LDS-sample buffer (4X), non-reducing Liquid, Note: This buffer contains: 988mM Tris-HCl, 2.04mM EDTA, 8% LDS, 40% glycerol, 0.88% Coomassie blue and 0.7mM phenol red at pH 8.5., † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 25ml 50ml |
| J61942 | LDS-sample buffer (4X), reducing Liquid, Note: This buffer contains 988mM Tris-HCl, 2.04mM EDTA, 8% LDS, 40% glycerol, 0.88% Coomassie blue, and 0.7mM phenol red, and 8% mercaptoethanol at pH 7.5. ! H:H312-H315-H319-H412, P:P280-P305+P351+P338-P302+P352-P321-P322-P501 | 25ml 50ml |

| Stock # | Description | Size |
|---------|---|---|
| 14243 | Lead(II) nitrate, ACS, 99.0% min ■ [10099-74-8], Pb(NO ₃) ₂ , F.W. 331.20, Crystalline, m.p. 470° dec., d. 4.530, Merck 14,5414, Solubility: Freely soluble in water. Soluble in absolute alcohol, methanol. Insoluble in concentrated HNO ₃ , UN1469, EINECS 233-245-9, RTECS OG2100000, MDL MFCD00011153, Note: pH of 20% aqueous solution ≈ 3.0-4.0, † Maximum level of impurities: Insoluble matter 0.005%, Cl 0.001%, Ca 0.005%, Cu 0.002%, Fe 0.001%, K 0.005%, Na 0.02%  H:H272-H360-H373-H400-H410-H302-H332, P:P221-P210-P260-P220-P405-P501a | 500g 2kg |
| | Application(s): As an oxidizer in dye industry, in manufacturing of mother-of-pearl, as mordant in printing textile, as sensitizer in photography | |
| J60576 | Lecithin, 60%, egg [L- α -Phosphatidylcholine] [8002-43-5], Powder, Merck 14,5428, EINECS 232-307-2, RTECS OG7565000, BRN 5209585, † | 100g 250g 500g |
| | Application(s): Naturally occurring lipid that protects cells from oxidation. Useful as an emulsifier | |
| J61675 | Lecithin, 90%, soybean [L- α -Phosphatidylcholine] [8002-43-5], Solid, Merck 14,5428, EINECS 232-307-2, RTECS OG7565000, BRN 5209585, † | 50g 100g 250g |
| | Application(s): Naturally occurring lipid that protects cells from oxidation. Useful as an emulsifier | |
| | Lealamine hydrochloride , see (+)-Dehydroabietylamine, J63123, p. 176 | |
| J65917 | Leflunomide [5-Methylisoxazole-4-(4-trifluoromethylcarboxanilide), Leflunomida] [75706-12-6], C ₁₂ H ₈ F ₃ N ₂ O ₂ , F.W. 270.21, Crystalline solid, Merck 14,5432, UN2811, RTECS NY2354200, MDL MFCD00867593  H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 100mg 500mg |
| A11644 | Leishman Stain [12627-53-1], EINECS 235-732-1, MDL MFCD00131498 | 25g 100g |
| | Application(s): Used to stain blood smears to identify parasites, leukocytes and trypanosomas | |
| J62344 | LENOX medium Liquid, Note: Ingredients (per liter amounts): 10g Tryptone, 5g Yeast Extract, 5g sodium chloride, 15g agar | 500ml 1L |
| J63784 | Leptomycin B, 99+%, 1mM soln. in ethanol [87081-35-4], C ₂₈ H ₄₈ O ₈ , F.W. 540.73, Liquid, f.p. 11°(52°F), Merck 14,5444, UN1993, MDL MFCD06795848, Note: Supplied as a 1mM solution in ethanol.  H:H225, P:P210-P241-P280-P240-P303+P361+P353-P501a | 100micrograms |
| | Application(s): Potent, specific inhibitor of nuclear export signal (NES)-dependent protein export from the nucleus | |
| J60602 | Lestaurtinib, 99+% [KT-5555] [111358-88-4], C ₂₈ H ₂₇ N ₅ O ₄ , F.W. 439.47, Powder, MDL MFCD12828858 | 1mg 5mg |
| | Application(s): Potent inhibitor of several tyrosine kinases | |
| | H-L-Leu-OH , see L-Leucine, Cell Culture Reagent, J62824, p. 268 | |
| A10590 | DL-Leucine, 99% [(+/-)-2-Amino-4-methylpentanoic acid, H-DL-Leu-OH] [328-39-2], C ₆ H ₁₃ NO ₂ , F.W. 131.18, m.p. ca 294° subl., d. 1.293, Merck 14,5451, EINECS 206-328-2, BRN 636005, MDL MFCD00063087, † |  50g 250g 1kg |
| A14842 | D-Leucine, 99% [(R)-2-Amino-4-methylpentanoic acid, H-D-Leu-OH] [328-38-1], C ₆ H ₁₃ NO ₂ , F.W. 131.18, m.p. >300°, [α] _D ²⁰ -15° (c=5 in 5N HCl), EINECS 206-327-7, RTECS OH2840000, BRN 1721721, MDL MFCD00063088, † |  5g 25g 100g |
| A12311 | L-Leucine, 99% [(S)-2-Amino-4-methylpentanoic acid, H-Leu-OH] [61-90-5], C ₆ H ₁₃ NO ₂ , F.W. 131.18, m.p. >300°, d. 1.293, [α] _D ²⁰ +15.5° (c=2 in 5N HCl), Merck 14,5451, EINECS 200-522-0, RTECS OH2850000, BRN 1721722, MDL MFCD00002617, † |  100g 500g 2.5kg |
| J62824 | L-Leucine, Cell Culture Reagent [H-L-Leu-OH] [61-90-5], C ₆ H ₁₃ NO ₂ , F.W. 131.17, Powder, EINECS 200-522-0, RTECS OH2850000, BRN 1721722, MDL MFCD00002617, † | 100g 250g 500g |
| J64951 | L-Leucine 7-amido-4-methylcoumarin hydrate [H-Leu-AMC] [66447-31-2], C ₁₄ H ₂₀ N ₂ O ₃ ·xH ₂ O, F.W. 288.37 (anhy), Powder, EINECS 266-363-4 | 250mg |
| B23745 | L-Leucinol, 97% △ [(S)-2-Amino-4-methylpentanol, H-Leu-ol] [7533-40-6], C ₆ H ₁₃ NO, F.W. 117.19, b.p. 198-200°, f.p. 90°(194°F), d. 0.917, n _D ²⁰ 1.4510, [α] _D ²⁰ +1.1° (neat), EINECS 231-400-5, BRN 1719240, MDL MFCD00063676  H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 |  5g 25g |






| Stock # | Description | Size |
|---------|---|-------------------|
| | Leucomycin A3 , see Josamycin, 98+%, J62245, p. 262 Leukaemomycin C , see Daunorubicin hydrochloride, J60224, p. 175 | |
| J61188 | Leupeptin hemisulfate [103476-89-7], C ₂₀ H ₃₈ N ₆ O ₄ ·0.5H ₂ SO ₄ , F.W. 475.59, Powder, MDL MFCD00037012 | 25mg 100mg |
| | Application(s): Reversible protease inhibitor which inhibits cathepsin B, calpain and trypsin | |
| J62147 | Leuprolide [Leuporelin, [Des-Gly10, D-Leu6, Pro-NHET9]LH-RH] [53714-56-0], C ₅₉ H ₈₄ N ₁₆ O ₁₂ , F.W. 1209.41, Powder, Merck 14,5457, Note: Supplied as an acetate salt. Sequence: pGlu-His-Trp-Ser-Tyr-DLeu-Leu-Arg-Pro-NHET | 1mg 5mg |
| | Application(s): Highly active luteinizing hormone releasing hormone (LHRH) agonist | |
| J62967 | Leuprolide, human, synthetic [Leuporelin, [Des-Gly10, D-Leu6, Pro-NHET9]LH-RH] [53714-56-0], C ₅₉ H ₈₄ N ₁₆ O ₁₂ , F.W. 1209.41, Powder, Merck 14,5457 | 5mg 25mg |
| | Leupropelin , see Leuprolide, J62147, p. 269 | |
| J62880 | Levitide, 96% [pGlu-Gly-Met-Ile-Gly-Thr-Leu-Thr-Ser-Lys-Arg-Ile-Lys-Gln-NH2] [114281-19-5], C ₆₆ H ₁₁₉ N ₂₁ O ₁₉ S, F.W. 1542.85, Powder, MDL MFCD00076644 | 1mg |
| | Application(s): Neurohormone-like peptide found in the skin of <i>Xenopus laevis</i> | |
| | Levodopa , see L-3-(3,4-Dihydroxyphenyl)alanine, A11311, p. 193 D-Levulose , see D-Fructose, A17718, p. 228 LGD-1069 , see Bexarotene, 99+%, J63701, p. 124 | |
| J64141 | LH-RH (4-10) [Luteinizing Hormone Releasing Hormone (4-10), Ser-Tyr-Gly-Leu-Arg-Pro-Gly-NH2] C ₂₃ H ₃₃ N ₁₁ O ₉ , F.W. 747.84, Solid H: H360, P: P281-P201-P202-P308+P313-P405-P501 | 1mg |
| J64883 | LH-RH free acid [Luteinizing Hormone Releasing Hormone, free acid, Glp-His-Trp-Ser-Tyr-Gly-Leu-Arg-Pro-Gly] C ₅₅ H ₇₄ N ₁₅ O ₁₄ , F.W. 1183.27, Solid | 5mg |
| J65645 | LH-RH, human [Gonadoreline, Glp-His-Trp-Ser-Tyr-Gly-Leu-Arg-Pro-Gly-NH2] [71447-49-9], C ₅₅ H ₇₅ N ₁₇ O ₁₅ , F.W. 1182.29, Powder, RTECS OK6470000 H: H360, P: P281-P201-P202-P308+P313-P405-P501 | 5mg |
| J64173 | LH-RH, salmon [Luteinizing Hormone Releasing Hormone, salmon, Glp-His-Trp-Ser-Tyr-Gly-Trp-Leu-Pro-Gly-NH2] [86073-88-3], C ₆₀ H ₇₃ N ₁₅ O ₁₃ , F.W. 1212.31, Powder, MDL MFCD00133497 H: H360, P: P281-P201-P202-P308+P313-P405-P501 | 1mg |
| | [Des-Gly10, D-Leu6, Pro-NHET9]LH-RH, see Leuprolide, J62147, p. 269 | |
| J65648 | [Gln₆] LH-RH, chicken [Glp-His-Trp-Ser-Tyr-Gly-Leu-Gln-Pro-Gly-NH2] C ₅₄ H ₇₁ N ₁₅ O ₁₄ , F.W. 1154.23, Solid H: H360, P: P281-P201-P202-P308+P313-P405-P501 | 1mg |
| J65994 | [Hyp₆] LH-RH [[Hyp9] Luteinizing Hormone Releasing Hormone, pGlu-His-Trp-Ser-Tyr-Gly-Leu-Arg-Hyp-Gly-NH2] [67019-13-0], C ₅₅ H ₇₅ N ₁₇ O ₁₄ , F.W. 1198.29, Solid, MDL MFCD00214314 H: H360, P: P281-P201-P202-P308+P313-P405-P501 | 5mg |
| J65530 | [D-Trp₆] LH-RH amide [Triptorelin, Glp-His-Trp-Ser-Tyr-DTrp-Leu-Arg-Pro-Gly-NH2] [57773-63-4], C ₆₄ H ₈₂ N ₁₆ O ₁₃ , F.W. 1311.45, Powder, Merck 14,9748, RTECS OK6371950, MDL MFCD00167541 H: H360, P: P281-P201-P202-P308+P313-P405-P501 | 5mg |
| J64762 | [D-Trp₆] LH-RH ethylamide [Triptoreline ethyl amide, Glp-His-Trp-Ser-Tyr-DTrp-Leu-Arg-Pro-Gly-NHET] C ₆₈ H ₈₆ N ₁₆ O ₁₃ , F.W. 1339.5, Solid H: H360, P: P281-P201-P202-P308+P313-P405-P501 | 5mg |
| J63035 | Lidocaine hydrochloride monohydrate, 98% [6108-05-0], C ₁₄ H ₂₂ N ₂ O·HCl·H ₂ O, F.W. 288.82 (270.80anhy), Crystalline powder, m.p. 75-79°, Merck 14,5482, UN2811, RTECS AN7700000, MDL MFCD00150329, † H: H301, P: P264-P270-P301+P310-P321-P405-P501a | 5g 25g 100g |
| | Application(s): Anesthetic. Blocks voltage-gated sodium channels | |

| Stock # | Description | Size |
|--|---|----------------------|
| J60678 | Lidocaine N-ethyl bromide, 99+% [QX-314 bromide, N-(2,6-Dimethylphenylcarbonylmethyl)triethylammonium bromide] [21306-56-9], C ₁₆ H ₂₇ BrN ₃ O, F.W. 343.31, Crystalline solid, MDL MFCD00083182 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 50mg 100mg |
| Application(s): Blocker of voltage-activated sodium channels | | |
| B23330 | Light Green SF Yellowish [Acid Green 5, C.I. 42095] [5141-20-8], C ₂₇ H ₃₄ N ₂ Na ₂ O ₆ S ₃ , F.W. 792.86, m.p. ca 288° dec., Merck 14.5485, EINECS 225-906-5, RTECS BQ4900000, BRN 5717828, MDL MFCD00012121, † ! H:H351, P:P281-P201-P202-P308+P313-P405-P501a Biological stain. | 10g 50g |
| Application(s): Useful as a general plasma stain, as a histological stain, and a cytological counterstain | | |
| J61251 | Lincomycin hydrochloride [859-18-7], C ₁₈ H ₃₄ N ₂ O ₆ S HCl, F.W. 443.00, Crystalline powder, EINECS 212-726-7, RTECS RH6315000, BRN 4171650, MDL MFCD00058237 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g 5g 25g |
| Application(s): Lincosamide antibiotic active against gram-positive bacteria | | |
| L07949 | Linoleic acid, 97% Δ [9,12-Octadecadienoic acid] [60-33-3], CH ₃ (CH ₂)CH=CHCH ₂ CH=CH(CH ₂)CO ₂ H, F.W. 280.45, m.p. -12°, b.p. 230°/16mm, f.p. >110° (230°F), d. 0.902, n _D ²⁰ 1.4699, Merck 14,5505, EINECS 200-470-9, RTECS RF9990000, BRN 1727101, MDL MFCD00064241, † | 5g 25g 100g |
| Application(s): Unsaturated omega-6 fatty acid | | |
| J65453 | Linomide [1,2-Dihydro-4-hydroxy-N,N-dimethyl-2-oxo-N-phenyl-3-quinolinecarboxamide] [84088-42-6], C ₁₈ H ₁₆ N ₂ O ₃ , F.W. 308.33, Powder ! H:H302, P:P264-P270-P301+P312-P330-P501 | 10mg |
| Liothyronine sodium salt, see 3,3',5'-Triiodo-L-thyronine sodium salt, J63312, p. 378 | | |
| J62903 | Lipase, from porcine pancreas [PPL, Triacylglycerol acylhydrolase] [9001-62-1], Powder, Merck 14,5511, EINECS 232-619-9, RTECS TO9776500, MDL MFCD00131509, Note: Minimum 24 USP units per mg. One unit liberates 1 micromole of fatty acid per min from olive oil at 37 degrees C and pH 9.0., † | 500g |
| Application(s): Catalyzes hydrolysis of emulsified esters of glycerol and long chain fatty acids | | |
| J64732 | Lipase Kit - 12 variants (L1 through L12) [EC 3.1.1.3] Lyophilized powder, Note: Contains 100mg of each variant | 1each |
| Application(s): Catalyzes enantioselective hydrolysis and interesterification of esters of primary and secondary alcohols. Catalyzes enantioselective synthesis and hydrolysis of amides | | |
| J65152 | Lipase L1 [EC 3.1.1.3] Lyophilized powder | 250mg 500mg 1g |
| J64108 | Lipase L2 [EC 3.1.1.3] Lyophilized powder | 250mg 500mg 1g |
| J64010 | Lipase L3 [EC 3.1.1.3] Lyophilized powder | 250mg 500mg 1g |
| J64017 | Lipase L4 [EC 3.1.1.3] Lyophilized powder | 250mg 500mg 1g |
| J64113 | Lipase L5 [EC 3.1.1.3] Lyophilized powder | 250mg 500mg 1g |
| J65835 | Lipase L6 [EC 3.1.1.3] Lyophilized powder | 250mg 500mg 1g |
| J65293 | Lipase L7 [EC 3.1.1.3] Lyophilized powder | 250mg 500mg 1g |












| Stock # | Description | Size |
|--|--|----------------------|
| J64563 | Lipase L8 [EC 3.1.1.3] Lyophilized powder | 250mg 500mg 1g |
| J65421 | Lipase L9 [EC 3.1.1.3] Lyophilized powder | 250mg 500mg 1g |
| J65151 | Lipase L10 [EC 3.1.1.3] Lyophilized powder | 250mg 500mg 1g |
| J65838 | Lipase L11 [EC 3.1.1.3] Lyophilized powder | 250mg 500mg 1g |
| J65235 | Lipase L12 [EC 3.1.1.3] Lyophilized powder | 250mg 500mg 1g |
| α -Lipoic acid, see DL-Thioctic acid, L04711, p. 366 | | |
| J64606 | Lipoprotein(a), human plasma, 99% [Lp(a)] | 100micrograms |
| J65029 | Lipoprotein, low density, acetylated, human plasma, 99% [Ac-LDL, Acetylated LDL] | 2mg |
| J64426 | Lipoprotein, low density, carbamylated, human plasma, 99% [Carbamylated-LDL, Low density lipoprotein, carbamylated] | 1each |
| J65039 | Lipoprotein, low density, human plasma, 99% [LDL, human, Low density lipoprotein] | 5mg |
| J65591 | Lipoprotein, low density, oxidized, human plasma, 99% [Ox-LDL, Oxidized LDL] | 2mg |
| J65261 | Lipoprotein, low density, oxidized, human plasma, Hi-TBAR, 99% [Ox-LDL, Oxidized LDL] | 2mg |
| J64223 | Lipoprotein, low density, oxidized, human plasma, Low-TBAR, 99% [Ox-LDL, Oxidized LDL] | 1each |
| J64903 | Lipoprotein, high density, human plasma, 99% [HDL, human, High density lipoprotein] | 10mg |
| J65642 | Lipoprotein, very low density, human plasma, 99% [Very low density lipoprotein, VLDL] | 1mg |
| J65182 | Lipoprotein Deficient Serum, bovine [LPDS, Bovine Serum, lipoprotein deficient] Note: Typical protein concentration is 90-120mg protein/ml | 1each |
| J65516 | Lipoprotein Deficient Serum, human [h-LPDS, Human Serum, lipoprotein deficient] Note: Typical protein concentration is approximately 50mg protein/ml | 1each |
| β -Lipotropin (61-76), see α -Endorphin, J63462, p. 206 | | |
| J60087 | LiSorb Liquid, Note: Contains: 100mM Lithium acetate, 50mM Tris-HCl, 1mM EDTA and 1 mM Sorbitol, pH 8.0 Application(s): For transformation of competent cells | 250ml 500ml |
| Lithiophor , see Lithium sulfate monohydrate, 36216, p. 272 | | |
| 36225 | Lithium carbonate, ACS, 99.0% min [554-13-2], Li ₂ CO ₃ , F.W. 73.90, Powder, m.p. 723°, b.p. 1310°, d. 2.11, Merck 14.5527, EINECS 209-062-5, MDL MFCD00011084, t Maximum level of impurities: Insoluble in dilute hydrochloric acid 0.01%, Cl 0.005%, NO ₃ 5ppm, Sulfur compounds (as SO ₄) 0.2%, NH ₄ 5ppm, Heavy Metals (as Pb) 0.002%, Fe 0.002%, Ca 0.01%, K 0.01%, Na 0.1% | 500g 2kg |
| ! H:H318-H302-H335-H315, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | | |
| J62644 | Lithium chloride, 200mM aq. soln. [7447-41-8], LiCl, F.W. 42.39, Liquid, t | 100ml 250ml |
| J61895 | Lithium chloride, 1M aq. soln. [7447-41-8], LiCl, F.W. 42.39, Liquid, t | 50ml 100ml |
| ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | | |


| Stock # | Description | Size |
|---------|--|---------------------|
| 36217 | Lithium chloride, ACS, 99% min ■ [7447-41-8], LiCl, F.W. 42.39, Granular, m.p. 605°, b.p. 1325-1360°, d. 2.068, Merck 14,5528, Fieser 1,609 2,246 4,298 5,677 13,332 16,194 18,211 20,215 21,248, Solubility: Very soluble in water, alcohol, ether, pyridine, and nitrobenzene, EINECS 231-212-3, RTECS QJ5950000, MDL MFCD00011078, † Maximum level of impurities: Insoluble matter 0.01%, Titratable base 0.008meq/g, Loss on drying at 105° 1.0%, NO ₃ 0.001%, SO ₄ 0.01%, Ba 0.003%, Heavy Metals (as Pb) 0.002%, Fe 0.001%, Ca 0.01%, K 0.01%, Na 0.20% ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 500g 2kg |
| | Application(s): In air-conditioning, welding and soldering flux, dry batteries, heat-exchange media, salt baths, and desiccants | |
| 39328 | Lithium dodecylsulfate, 99+% [2044-56-6], CH ₃ (CH ₂) ₁₁ OSO ₃ Li, F.W. 272.33, Powder, EINECS 218-058-2, MDL MFCD00007467, † ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 10g 50g |
| | Application(s): Detergent for solubilizing proteins for electrophoresis which exhibits greater solubility than SDS at lower temperatures | |
| J65509 | Lithium dodecylsulfate, ultrapure, 99% [2044-56-6], CH ₃ (CH ₂) ₁₁ OSO ₃ Li, F.W. 272.33, Powder, EINECS 218-058-2, MDL MFCD00007467, † ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10g 50g |
| | Lithium-Duriles , see Lithium sulfate monohydrate, 36216, p. 272 | |
| A11818 | Lithium L-lactate, 97% ■ [L-Lactic acid lithium salt] [27848-80-2], CH ₃ CH(OH)CO ₂ Li, F.W. 96.01, m.p. 253-255°, [α] _D ²⁰ -14° (c=1 in water), EINECS 248-692-5, RTECS QJ6311000, BRN 3568332, MDL MFCD00065399, † H:H303, P:P312 | 50g 250g 1kg |
| | Application(s): Useful chiral synthon, building block for depsipeptides | |
| 36216 | Lithium sulfate monohydrate, ACS, 99.0% min [Lithiophor, Lithium-Duriles] [10102-25-7], Li ₂ SO ₄ ·H ₂ O, F.W. 127.96 (109.94anhy), Crystalline, m.p. 130° -H ₂ O, d. 2.06, Merck 14,5541, Solubility: Soluble in water, EINECS 233-820-4, MDL MFCD00149766, † Maximum level of impurities: Loss on drying at 150° 13.0-15.0%, Insoluble matter 0.01%, Cl 0.002%, NO ₃ 0.001%, Heavy Metals (as Pb) 0.001%, Fe 0.001%, K 0.05%, Na 0.05% ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 100g 500g 2kg |
| J60177 | Litorin [pGlu-Gln-Trp-Ala-Val-Gly-His-Phe-Met-NH ₂ , Pituitary adenylate cyclase activating fragment 21-38] [55749-97-8], C ₅₁ H ₆₈ N ₁₄ O ₁₁ S, F.W. 1085.25, Lyophilized powder, MDL MFCD00167519 | 1mg |
| | Application(s): Bombesin-like nonapeptide from the skin of poisonous frogs | |
| J60485 | Liver Cell Growth Factor [Gly-His-Lys, Glycyl-Histidyl-Lysine] [72957-37-0], C ₁₄ H ₂₄ N ₆ O ₄ , F.W. 340.38, Powder, EINECS 277-125-4, MDL MFCD00012699 | 5mg |
| | Application(s): Growth modulating tripeptide | |
| J64233 | Liver Cell Growth Factor acetate salt [GHK acetate salt, Gly-His-Lys-acetate salt] [72957-37-0], C ₁₄ H ₂₄ N ₆ O ₄ ·C ₂ H ₄ O ₂ , F.W. 400.43, Powder, EINECS 277-125-4, MDL MFCD00012699 | 250mg |
| J64425 | Locostatin [UIC-1005, (4S)-3-[(E)-But-2-enoyl]-4-benzyl-2-oxazolidinone] [133812-16-5], C ₁₄ H ₁₅ NO ₃ , F.W. 245.27, Powder, MDL MFCD00278769 | 10mg 50mg |
| J63960 | Lofexidine hydrochloride, 98+% [21498-08-8], C ₁₁ H ₁₂ Cl ₂ N ₂ O·HCl, F.W. 295.60, Crystalline powder, m.p. 225-232°, Merck 14,5558, UN2811 ☞ H:H301, P:P264-P270-P301+P310-P321-P405-P501a | 1g 5g |
| | Application(s): α-2 adrenergic agonist | |
| J60168 | Loperamide hydrochloride, 98+% [4-(p-Chlorophenyl)-4-hydroxy-N,N-dimethyl-α,α-diphenyl-1-piperidinebutyramide hydrochloride] [34552-83-5], C ₂₈ H ₃₅ ClN ₂ O ₂ ·HCl, F.W. 513.51, Powder, Merck 14,5571, UN2811, EINECS 252-082-4, RTECS TM4960000, MDL MFCD00058581 ☞ H:H301, P:P264-P270-P301+P310-P321-P405-P501a | 5g 25g |
| | Application(s): At nanomolar concentrations, binds to mu-opioid receptors. L-type calcium channel blocker | |
| J60190 | Loratadine, 98+% [79794-75-5], C ₂₂ H ₂₃ N ₂ O ₂ Cl, F.W. 382.88, Powder, m.p. 134°, Merck 14,5578, RTECS TM6129200, MDL MFCD00672869 | 500mg 1g 5g |
| | Application(s): A non-sedating-type histamine H1-receptor antagonist | |
| J61713 | Lorglumide sodium salt, 98+% [97964-56-2], C ₂₂ H ₃₁ Cl ₂ N ₂ NaO ₄ , F.W. 481.39, Powder, RTECS SA3680700, MDL MFCD00083183 | 25mg 100mg |
| | Application(s): Potent and specific non-peptide cholecystokinin (CCK) receptor antagonist | |

| Stock # | Description | Size |
|---------|--|---|
| H52792 | Lovastatin, 97% [Mevacor] [75330-75-5], C ₂₄ H ₃₆ O ₅ , F.W. 404.56, m.p. 175°, RTECS EK7907000, MDL MFCD00072164 ! H.H302-H315-H319-H335, P.P261-P305+P351+P338-P302+P352-P321-P405-P501a | 5g |
| | | 25g |
| |  | |
| J65822 | Loxistatin [EST, E-64d] [88321-09-9], C ₁₇ H ₃₀ N ₂ O ₅ , F.W. 342.43, Powder, RTECS RR0404300, MDL MFCD00132883 ! H.H315-H319-H335, P.P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1mg 5mg |
| | Ludiomil hydrochloride , see Maprotiline hydrochloride, 99%, J62321, p. 277 | |
| J61462 | Luminol and oxidizing solutions (each bottle) Liquid, Note: Mix equal amounts of luminol and oxidizing solution, then incubate the membrane for 1 min. Expose membrane to x-ray film for at least one minute. Adjust exposure as necessary. Application(s): For chemiluminescent detection of HRP-based Western blotting systems. | 250ml 500ml |
| | Luteinizing Hormone Releasing Hormone , see LH-RH Luteolin , see 3',4',5,7-Tetrahydroxyflavone, L14186, p. 363 Lutocyclin , see Ethisterone, 98%, J63580, p. 214 | |
| J61915 | Luzindole, 97% [N-[2-[2-(Phenylmethyl)-1H-indol-3-yl]ethyl]acetamide, N-Acetyl-2-benzyltryptamine] [117946-91-5], C ₁₉ H ₂₀ N ₂ O, F.W. 292.37, Powder, m.p. 44-46°, MDL MFCD00672498 Application(s): A melatonin receptor antagonist | 5mg 25mg |
| | | LY-110,140 hydrochloride , see Fluoxetine hydrochloride, 99%, J61197, p. 224 H-Lys-OH.HCl , see L-Lysine monohydrochloride, Cell Culture Reagent, J62099, p. 273 |
| J62067 | Lys-Bradykinin [Kallidin, Lys-Arg-Pro-Pro-Gly-Phe-Ser-Pro-Phe-Arg] [100900-38-7], C ₅₆ H ₈₅ N ₁₇ O ₁₂ , F.W. 1188.40, Powder Application(s): Endogenous bradykinin receptor agonist | 5mg 25mg |
| J62225 | L-Lysine, 98% [(S)-2,6-Diaminocaproic acid] [56-87-1], C ₆ H ₁₂ N ₂ O ₂ , F.W. 146.19, Powder, m.p. 215°, Merck 14,5636, EINECS 200-294-2, RTECS OL5540000, BRN 1722531, MDL MFCD00064433, † | 25g 100g 500g |
| A11066 | DL-Lysine monohydrochloride, 99% [(+/-)-2,6-Diaminohexanoic acid monohydrochloride] [70-53-1], C ₆ H ₁₄ N ₂ O ₂ .HCl, F.W. 182.65, m.p. 267° dec., EINECS 200-739-0, BRN 4711993, MDL MFCD00064563, † | 25g 100g |
| |  | |
| L07710 | D-Lysine monohydrochloride, 98% [(R)-2,6-Diaminohexanoic acid monohydrochloride, H-D-Lys-OH.HCl] [7274-88-6], C ₆ H ₁₄ N ₂ O ₂ .HCl, F.W. 182.65, m.p. ca 260° dec., [α] _D ²⁰ -20.5° (c=5 in 5N HCl), EINECS 230-691-6, RTECS OL5632500, BRN 4356907, MDL MFCD00012920, † | 1g 5g |
| |  | |
| A16249 | L-Lysine monohydrochloride, 99+% [(S)-2,6-Diaminohexanoic acid monohydrochloride, H-Lys-OH.HCl] [657-27-2], C ₆ H ₁₄ N ₂ O ₂ .HCl, F.W. 182.65, m.p. ca 260° dec., [α] _D ²⁰ +20.5° (c=5 in 5N HCl), Merck 14,5636, EINECS 211-519-9, RTECS OL5650000, BRN 3563889, MDL MFCD00064564, † | 50g 250g 1kg |
| |  | |
| J62099 | L-Lysine monohydrochloride, Cell Culture Reagent [657-27-2], C ₆ H ₁₄ N ₂ O ₂ .HCl, F.W. 182.65, Powder, Merck 14,5636, EINECS 211-519-9, RTECS OL5650000, BRN 3563889, MDL MFCD00064564, † | 100g 500g 1kg |
| A18157 | L-Lysine methyl ester dihydrochloride, 99% ■ [(S)-2,6-Diaminohexanoic acid methyl ester dihydrochloride, H-Lys-OMe.2HCl] [26348-70-9], C ₇ H ₁₆ N ₂ O ₂ .2HCl, F.W. 233.14, m.p. ca 200° dec., EINECS 247-625-7, BRN 5302183, MDL MFCD00039067 | 25g 100g 500g |
| |  | |
| J63892 | Lysis buffer, pH 8.0 Liquid, Note: This buffer contains: 50mM sodium phosphate, 300mM sodium chloride and 10mM imidazole at pH 8.0. Application(s): For isolation of His-tag proteins | 500ml |
| J61792 | Lysis buffer, 0.5% Tween 20, pH 8.0 Liquid, Note: Contains 50mM sodium phosphate, 300mM sodium chloride, 10mM imidazole and 0.5% Tween-20. Application(s): For isolation of His-tag proteins | 500ml |

| Stock # | Description | Size |
|---|---|-------|
| J60701 | Lysozyme, chicken egg white | 1g |
| | [E.C. 3.2.1.17, <i>Muramidase</i>] [12650-88-3], Powder, Merck 14,5640, EINECS 235-747-3, RTECS OL5989000, MDL MFCD00131557, | 5g |
| | Note: Minimum 23,500 units/mg. One unit is the amount of enzyme causing a decrease in absorbance at 450nm of 0.001 per minute at 25 C and pH 6.2 with <i>Micrococcous Lysodeikticus</i> as a substrate in a 2.6 mL reaction mixture (1 cm light path) | 25g |
| Application(s): Catalyzes the hydrolysis of peptidoglycans found in bacterial cell walls | | |
| Lyticase , see Yeast Lytic Enzyme, <i>Arthrobacter luteus</i> , J63195, p. 395 | | |
| J65036 | M50054 ▲ [2,2'-Methylenebis(1,3-cyclohexanedione)] [54135-60-3], C ₁₃ H ₁₆ O ₄ , F.W. 236.00, Solid, EINECS 258-989-1 | 10mg |
| J64242 | MAC 1753 [5-(3,5-Dichlorophenoxy)-N-4-pyridinyl-2-furancarboxamide] [685830-90-4], C ₁₆ H ₁₀ Cl ₂ N ₂ O ₃ , F.W. 349.17 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5mg |
| J60917 | α-2-Macroglobulin, human plasma | 0.2mg |
| | Lyophilized powder, 725 kDa | 1mg |
| Application(s): A large plasma protein found in the blood capable of inactivating many proteases | | |
| J63844 | Macrophage Inhibitory Peptide | 50mg |
| | [H-Thr-Lys-Pro-OH, <i>Tuftsia</i> (1-3)] [41961-56-2], C ₁₅ H ₂₈ N ₂ O ₅ , F.W. 344.41, Powder | 250mg |
| Application(s): A tripeptide of the second constant domain of human immunoglobulin G. Inhibitor of macrophage functions | | |
| J60301 | Magainin I | 0.5mg |
| | [H-Gly-Ile-Gly-Lys-Phe-Leu-His-Ser-Ala-Gly-Lys-Phe-Gly-Lys-Ala-Phe-Val-Gly-Glu-Ile-Met-Lys-Ser-OH] [108433-99-4], C ₁₁₂ H ₁₇₇ N ₂₅ O ₂₆ S, F.W. 2409.88, Powder, MDL MFCD00133521 | |
| Application(s): Peptide that demonstrates antibiotic activity | | |
| J61172 | Magainin II | 0.5mg |
| | [Gly-Ile-Gly-Lys-Phe-Leu-His-Ser-Ala-Lys-Lys-Phe-Gly-Lys-Ala-Phe-Val-Gly-Glu-Ile-Met-Asn-Ser] [108433-95-0], C ₁₁₄ H ₁₈₀ N ₃₀ O ₂₈ S, F.W. 2466.93, Powder, MDL MFCD00133522 | 1mg |
| | | 2.5mg |
| Application(s): Peptide with potent antibiotic properties | | |
| Magenta I , see Basic Fuchsin, A12952, p. 117 | | |
| J60041 | Magnesium acetate, 1M aq. soln. | 50ml |
| | [142-72-3], Mg(CH ₃ COO) ₂ , F.W. 142.39, Liquid, † ! H:H302, P:P264-P270-P301+P312-P330-P501a | 100ml |
| J62411 | Magnesium chloride, 1M aq. soln. | 50ml |
| | [7786-30-3], MgCl ₂ , F.W. 95.22, Liquid, † H:H303, P:P312 | 100ml |
| J61014 | Magnesium chloride, 1M aq. soln., sterile | 125ml |
| | [7786-30-3], MgCl ₂ , F.W. 95.22, Liquid, † H:H303, P:P312 | 250ml |
| 36226 | Magnesium chloride hexahydrate, ACS, 99.0-102.0% ■ | 500g |
| | [7791-18-6], MgCl ₂ ·6H ₂ O, F.W. 203.30 (95.22anhy), Crystalline, m.p. 117° dec., d. 1.570, Merck 14,5662, Fieser 10.251, EINECS 232-094-6, RTECS OM2975000, MDL MFCD00149781, † | 2kg |
| | Maximum level of impurities: Insoluble matter 0.005%, NO ₃ 0.001%, PO ₄ 5ppm, SO ₄ 0.002%, NH ₄ 0.002%, Ba 0.005%, Ca 0.01%, Heavy Metals (as Pb) 5ppm, Fe 5ppm, Mn 5ppm, K 0.0005%, Na 0.005%, Sr 0.005% | |
| J62575 | Magnesium chloride hexahydrate, Cell Culture Reagent | 250g |
| | [7791-18-6], MgCl ₂ ·6H ₂ O, F.W. 203.30 (95.22anhy), Powder, Merck 14,5662, EINECS 232-094-6, RTECS OM2975000, MDL MFCD00149781, † | 500g |
| | | 1kg |
| 40318 | Magnesium silicate monohydrate (Talc) | 100g |
| | [14807-96-6], 3MgO·4SiO ₂ ·H ₂ O, F.W. 379.28 (361.27anhy), Powder, d. 2.7, Merck 14,9037, Solubility: Insoluble in water, cold acids, alkalis, EINECS 238-877-9, RTECS WW2710000, MDL MFCD00792903, † | 500g |
| | ! H:H332, P:P261-P271-P304+P340-P312 | 2.5kg |
| | Application(s): Lubricant, filler, electric and heat insulator, in clarifying liquids by filtration | |
| J63953 | Magnesium sulfate, 1M aq. soln. | 50ml |
| | [7487-88-9], MgSO ₄ , F.W. 120.37, Liquid, † | 100ml |
| J61030 | Magnesium sulfate, 1M aq. soln., sterile | 125ml |
| | [7487-88-9], MgSO ₄ , F.W. 120.37, Liquid, † | 250ml |

| Stock # | Description | Size | |
|---------|---|---|--------------------------|
| 11596 | Magnesium sulfate heptahydrate, ACS, 98.0-102.0% [Epsom salt] [10034-99-8], MgSO ₄ ·7H ₂ O, F.W. 246.48 (120.37anhy), Crystalline, d. 1.68, Merck 14,5691, Fieser 1,634 5,421, Solubility: Soluble in water. Slightly soluble in alcohol, glycerol, EINECS 231-298-2, RTECS OM4508000, MDL MFCD00149785, Note: 150° -6H ₂ O, 200° -7H ₂ O, † Maximum level of impurities: Insoluble matter 0.005%, pH of a 5% solution 5.0-8.2 at 25°, Cl 5ppm, NO ₃ 0.002%, NH ₄ 0.002%, Ca 0.02%, Heavy Metals (as Pb) 5ppm, Fe 5ppm, Mn 5ppm, K 0.005%, Na 0.005%, Sr 0.005% | 100g 500g 2kg | |
| | Application(s): Fireproofing, textiles, catalyst carrier, ceramics | | |
| 33337 | Magnesium sulfate, anhydrous, 99.5% min ■ [7487-88-9], MgSO ₄ , F.W. 120.37, Powder, m.p. 1124° dec., d. 2.66, Merck 14,5691, EINECS 231-298-2, MDL MFCD00011110, † | 500g 2kg 10kg | |
| | Application(s): Suitable for sensitive molecular biology applications | | |
| J61839 | Magnesium sulfate heptahydrate, Cell Culture Reagent [Epsom salt] [10034-99-8], MgSO ₄ ·7H ₂ O, F.W. 246.48 (120.37anhy), Powder, d. 1.68, Merck 14,5691, EINECS 231-298-2, RTECS OM4508000, MDL MFCD00149785 | 500g 1kg | |
| | Magon sulfate , see Xylidyl Blue I sodium salt, L10863, p. 394 | | |
| A16186 | Malachite Green oxalate [C.I. 42000] [2437-29-8], C ₂₅ H ₂₆ N ₄ O ₁₂ , F.W. 927.02, m.p. 164° dec., Merck 14,5699, UN2811, EINECS 219-441-7, RTECS BQ1190000, BRN 3644550, MDL MFCD00011766 ! H: H302-H312, P: P280-P302+P352-P322-P301+P312-P312-P501a |  H ₂ C ₂ O ₄ 2HC ₂ O ₄ ⁻ | 25g 100g |
| | Application(s): Biological stain, dye reagent, acid base indicator: pH 0.0 yellow, 2.0 green; 11.6 green, 14 colorless | | |
| J62283 | Malantide [Arg-Thr-Lys-Arg-Ser-Gly-Ser-Val-Tyr-Glu-Pro-Leu-Lys-Ile] [86555-35-3], C ₇₂ H ₁₂₄ N ₂₂ O ₂₁ , F.W. 1633.91, Powder | 1mg 2mg 5mg | |
| | Application(s): Substrate for cAMP-dependent protein kinase | | |
| J60582 | Maleate, 0.2M buffer soln., pH 5.0 [676-46-0], Liquid | 250ml 500ml | |
| J62049 | Maleate, 0.2M buffer soln., pH 5.5 [676-46-0], Liquid | 250ml 500ml | |
| J62035 | Maleate, 0.2M buffer soln., pH 6.0 [676-46-0], Liquid | 250ml 500ml | |
| J61156 | Maleate, 0.2M buffer soln., pH 6.5 [676-46-0], Liquid | 250ml 500ml | |
| J61297 | Maleate, 0.2M buffer soln., pH 7.0 [676-46-0], Liquid | 250ml 500ml | |
| A14596 | Maleic acid, 98+% [cis-2-Butenedioic acid] [110-16-7], C ₄ H ₄ O ₄ , F.W. 116.07, m.p. 132-136°, f.p. 127°(260°F), d. 1.59, Merck 14,5703, EINECS 203-742-5, RTECS OM9625000, BRN 605762, MDL MFCD00063177, † ! H: H302-H315-H319-H317-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a |  COOH COOH | 250g 1kg 5kg |
| A12178 | Maleic anhydride, 98+% ■ [cis-Butenedioic anhydride, 2,5-Furandione] [108-31-6], C ₄ H ₂ O ₃ , F.W. 98.06, m.p. 52-56°, b.p. 202°, f.p. 103°(217°F), Merck 14,5704, Fieser 4,316 5,422, UN2215, EINECS 203-571-6, RTECS ON3675000, BRN 106909, MDL MFCD00005518, † ! H: H334-H314-H302-H317, P: P260-P285-P303+P361+P353-P305+P351+P338-P405-P501a Reactive dienophile. For a review of its Diels-Alder reactions, see: <i>Org. React.</i> , 4 , 1 (1948). For examples, see: <i>Org. Synth. Coll.</i> , 3 , 807 (1955); 4 , 890 (1963). For reaction with Danishefsky's diene (1-Methoxy-3-trimethylsiloxy-1,3-butadiene, L14672), see: <i>Org. Synth. Coll.</i> , 7 , 312 (1990). Also undergoes photochemical and thermal (2+2)-cycloadditions with alkenes. For reaction with 1-alkynes, see: <i>Chem. Ber.</i> , 102 , 3974 (1969). For thermal (2+2)-cycloaddition with allene at high temperature, see: <i>Org. Synth. Coll.</i> , 5 , 459 (1973). For use in combination with Urea hydrogen peroxide adduct, L13940 , to generate peroxyaleic acid in epoxidation and Baeyer-Villiger reactions, see: <i>Heterocycles</i> , 36 , 1075 (1993). Peroxyaleic acid can also be generated <i>in situ</i> from maleic anhydride and 30% H ₂ O ₂ in NMP, and has been found to be a very effective oxidant for conversion of sulfides to sulfoxides. For a study of stoichiometric and catalytic oxidations with this system, see: <i>J. Org. Chem.</i> , 61 , 5693 (1996). |  O O | 250g 1kg 5kg |
| A13135 | Maleimide, 98+% [2,5-Dioxo-3-pyrroline, 1H-Pyrrole-2,5-dione] [541-59-3], C ₄ H ₃ NO ₂ , F.W. 97.07, m.p. 90-94°, b.p. 97-103/5mm, d. 1.249, Solubility: Soluble in water, UN2923, EINECS 208-787-4, RTECS ON4800000, BRN 106910, MDL MFCD00005494, † ! H: H301-H314-H317, P: P260-P301+P310-P303+P361+P353-P305+P351+P338-P405-P501a |  O NH O | 5g 25g 50g 250g |

| Stock # | Description | Size |
|---------------|---|---|
| | Stereoselective Diels-Alder reaction with an exocyclic diene has been used in the synthesis of a cyclohexannulated [5.3.1]propellane as a precursor of an ABC ring analogue of paclitaxel (Taxol): <i>J. Chem. Soc., Chem. Commun.</i> , 1395 (1995). | |
| | Application(s): Reacts quantitatively with sulfhydryl groups | |
| | 3-Maleimidobenzoic acid N-hydroxysuccinimide ester , see N-Succinimidyl 3-maleimidobenzoate, J61410, p. 354 | |
| J61850 | N-(γ-Maleimidobutyryloxy)succinimide [GIBBS] [80307-12-6], C ₁₂ H ₁₂ N ₂ O ₆ , F.W. 280.23, Powder, m.p. 130-132°, BRN 6427689, MDL MFCD00036817 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 100mg |
| | Application(s): A heterobifunctional cross-linking reagent with amine and sulfhydryl reactivity. Useful in enzyme immunoassays | |
| A17874 | DL-Malic acid, 98% [(\pm)-Hydroxysuccinic acid] [6915-15-7], C ₄ H ₆ O ₅ , F.W. 134.09, m.p. 130-133°, f.p. 203°(397°F), d. 1.609, Merck 14,5707 , Solubility: Soluble in acetone, dioxane, water, methanol and ethanol. Insoluble in benzene., EINECS 210-514-9, RTECS ON7175000, BRN 1723539, MDL MFCD00064212, † ! H:H318-H335-H315, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a |  500g 2.5kg |
| A11688 | D-(+)-Malic acid, 98+% [(R)-(+)-Hydroxysuccinic acid] [636-61-3], C ₄ H ₆ O ₅ , F.W. 134.09, m.p. 100-104°, d. 1.60, [α] _D ²⁰ +27° (c=5.5 in pyridine), Merck 14,5707 , EINECS 211-262-2, RTECS ON7260000, BRN 1723540, MDL MFCD00004245 ! H:H318-H335-H315, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a |  1g 5g 25g |
| J63221 | L-(-)-Malic acid, 99% [(S)-(-)-Hydroxysuccinic acid, (S)-(-)-Hydrosuccinic acid] [97-67-6], C ₄ H ₆ O ₅ , F.W. 134.09, Crystalline powder, m.p. 100-106°, f.p. 220°(428°F), d. 1.6, Merck 14,5707 , EINECS 202-601-5, RTECS ON7175000, BRN 1723541, MDL MFCD00064213, † ! H:H318-H335-H315, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 100g 500g 2.5kg |
| J65970 | Malic decarboxylase variant A Lyophilized powder, Note: Component in the Cofactor Recycling Enzymes Kit, item J64535 | 250mg 500mg 1g |
| J64878 | Malic decarboxylase variant B Lyophilized powder, Note: Component in the Cofactor Recycling Enzymes Kit, item J64535 | 250mg 500mg 1g |
| A17939 | Malonamide, 98% [108-13-4], C ₃ H ₄ N ₂ O ₂ , F.W. 102.09, m.p. 167-171°, EINECS 203-553-8, RTECS ON9125000, BRN 1751401, MDL MFCD00008034, † Reagent for fluorimetric determination of reducing carbohydrates: <i>Anal. Chim. Acta</i> , 108 , 421 (1979). |  100g 500g 2.5kg |
| A11526 | Malonic acid, 99% [Propanedioic acid] [141-82-2], C ₃ H ₄ O ₄ , F.W. 104.06, m.p. 132-136° dec., f.p. 157°(314°F), d. 1.62, Merck 14,5710 , EINECS 205-503-0, RTECS OO0175000, BRN 1751370, MDL MFCD00002707, † ! H:H318-H302-H335-H315, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Knoevenagel condensation with aldehydes yields substituted acrylic (e.g. cinnamic) acids; review: <i>Org. React.</i> , 15 , 204 (1967). For an example of the Doebner modification, using pyridine as solvent/base, see: <i>Org. Synth. Coll.</i> , 3 , 425 (1955); a catalytic amount of piperidine often gives superior results; see, e.g.: <i>Org. Synth. Coll.</i> , 4 , 327 (1963). |  100g 500g 2.5kg |
| 31715 | Malonic acid, Reagent Grade, 99.5+% [Propanedioic acid] [141-82-2], H ₂ C(CO ₂ H) ₂ , F.W. 104.06, Crystalline, m.p. 132-136° dec., f.p. 157°(314°F), d. 1.62, Merck 14,5710 , Solubility: Soluble in water, alcohol. Moderately soluble in pyridine, ether, EINECS 205-503-0, RTECS OO8175000, BRN 1751370, MDL MFCD00002707, † ! H:H318-H302-H335-H315, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 100g 500g 2.5kg |
| 44841 | Malonic acid disodium salt, 99% [Disodium malonate] [141-95-7], CH ₂ (COONa) ₂ , F.W. 148.03, Powder, EINECS 205-514-0, RTECS OO1750000, MDL MFCD00002708, † | 25g 100g |
| | Malonoben , see Tyrphostin A9, 99%, J63058, p. 386 | |
| A15046 | Malononitrile, 99% [Dicyanomethane, Propanedinitrile] [109-77-3], C ₂ H ₂ N ₂ , F.W. 66.06, m.p. 30-34°, b.p. 220-222°, f.p. 112°(233°F), d. 1.049, n _D ²⁰ 1.4150, Merck 14,5711 , Fieser 4,317 18,228 , Solubility: Soluble in water, UN2647, EINECS 203-703-2, RTECS OO3150000, BRN 773697, MDL MFCD00001883, † ! H:H301-H311-H331-H400-H410, P:P301+P310-P361-P302+P352-P321-P405-P501a The Na derivative can be arylated by reaction with aryl halides with a Pd catalyst: <i>J. Chem. Soc., Chem. Commun.</i> , 932 (1984). In the presence of butadiene, an additional 4-carbon unit is introduced: <i>J. Chem. Soc., Perkin 1</i> , 647 (1990): |  100g 500g 2.5kg |




Ternary condensation with an aromatic aldehyde and a cycloalkanone in the presence of ammonium acetate can give a variety of products. With cyclohexanone, the 2-amino-4-aryl-5,6,7,8-tetrahydroquinoline-3-carbonitriles are the major products: *J. Chem. Res. (Synop.)*, 146 (1995).
Reviews of the chemistry of malononitrile: *Chem. Rev.*, **69**, 591 (1969); *Synthesis*, 165, 241 (1978); 925 (1981); *Synlett*, 2247 (2004).

Application(s): Crosslinking agent for modification of proteins via amidation

A16266 D-(+)-Maltose monohydrate, 95%

[4-O- α -Glucopyranosyl-D-glucose monohydrate]

[6363-53-7], C₁₂H₂₂O₁₁·H₂O, F.W. 360.32 (342.30anhy), m.p. ca 120° dec., $[\alpha]_D^{20} +130^\circ$ (c=2 in water, 24h), Merck 14,5714, Solubility: Soluble in water. Slightly soluble in alcohol. Insoluble in ether, EINECS 200-716-5, RTECS OO5250000, BRN 5784659, MDL MFCD00149343, †



100g

500g

D-Mandelonitrile- β -D-glucosido-6- β -D-glucoside, see D-Amygdalin, 98+%, J61472, p. 103

J63150 Manganese(II) chloride, 1M aq. soln.

[7773-01-5], MnCl₂, F.W. 125.84, Liquid, †

! H:H302, P:P264-P270-P301+P312-P330-P501a

50ml

100ml

36526 Manganese(II) chloride tetrahydrate, ACS, 98.0-101.0% ■

[13446-34-9], MnCl₂·4H₂O, F.W. 197.90 (125.84anhy), Crystalline, m.p. 58°, d. 2.010, Merck 14,5728, Solubility: Soluble in water, alcohol, EINECS 231-869-6, MDL MFCD00149792, †

Maximum level of impurities: Insoluble matter 0.005%, pH of a 5% solution 3.5-6.0 at 25°, SO₄ 0.005%, Ca 0.005%, K 0.01%, Na 0.05%, Heavy Metals (as Pb) 5ppm, Fe 5ppm, Zn 0.005%

! H:H302, P:P264-P270-P301+P312-P330-P501a

100g

500g

2kg

J63305 Manidipine

[89226-50-6], C₃₅H₃₈N₄O₆, F.W. 610.71, Crystalline powder, Merck 14,5743, UN2811

! H:H302, P:P264-P270-P301+P312-P330-P501a

100mg

1g

Application(s): A calcium channel blocker

J60496 Manidipine dihydrochloride

[89226-75-5], C₃₅H₃₈N₄O₆·2HCl, F.W. 683.63, Crystalline powder, Merck 14,5743, UN2811

! H:H301, P:P264-P270-P301+P310-P321-P405-P501a

25mg


100mg

250mg

Application(s): Calcium channel blocker

A14030 D-Mannitol, 99%

[69-65-8], C₆H₁₂O₆, F.W. 182.17, m.p. 167-169°, b.p. 290-295°/3.5mm, d. 1.489, $[\alpha]_D^{20} +24^\circ$ (in borax solution), Merck 14,5745, EINECS 200-711-8, RTECS OP2060000, BRN 1721898, MDL MFCD00064287, †



250g

1kg

5kg

33342 D-Mannitol, ACS

[69-65-8], HOCH₂(CHOH)₄CH₂OH, F.W. 182.17, Crystalline, m.p. 165-167°, b.p. 290-295°/3.5mm, d. 1.489, Merck 14,5745, Solubility: Soluble in water, alcohol, pyridine, aniline. Insoluble in ether, EINECS 200-711-8, RTECS OP2060000, BRN 1721898, MDL MFCD00064287, †

Maximum level of impurities: Insoluble matter 0.01%, Residue after ignition 0.01%, Titratable acid 0.0008meq/g, Reducing sugars P.T., Heavy Metals (as Pb) 5ppm, Specific rotation at 25° +23.3° to +24.3°


500g

2.5kg

A10842 D-(+)-Mannose, 99% ■

[3458-28-4], C₆H₁₂O₆, F.W. 180.16, m.p. 127-133°, d. 1.54, $[\alpha]_D^{20} +13.8^\circ$ (c=10 in water, 24h), Merck 14,5747, Solubility: Soluble in water, EINECS 222-392-4, BRN 1564373, MDL MFCD00064122, †

Chiral building block. For use in a 15-step synthesis of the macrocycle (+)-aspicilin, in which 3 of the 4 asymmetric centers come from mannose, see: *Helv. Chim. Acta*, **72**, 1753 (1989).




25g

100g

500g

A17722 L-(-)-Mannose, 99%

[10030-80-5], C₆H₁₂O₆, F.W. 180.16, m.p. 129-131°, EINECS 233-080-2, BRN 1724628, MDL MFCD00136021, †



250mg

1g

J62321 Maprotiline hydrochloride, 99%

[Ludiomil hydrochloride]

[10347-81-6], C₂₀H₂₃N·HCl, F.W. 313.87, Crystalline powder, m.p. 230-232°, Merck 14,5748, EINECS 233-758-8, RTECS KJ4555000, MDL MFCD00079464

! H:H302, P:P264-P270-P301+P312-P330-P501


1g

5g










Application(s): Selective norepinephrine uptake inhibitor

Marcaïne, see Bupivacaine hydrochloride, 98+%, J62835, p. 140





| Stock # | Description | Size |
|---------|--|--|
| J61103 | Margatoxin, 99+% [rMargatoxin, MgTx] [145808-47-5], C ₁₇₈ H ₂₈₆ N ₃₂ O ₅₀ S ₇ , F.W. 4178.95, Powder, Merck 14,5752 ! H:H302-H312-H332, P:P261-P280-P302+P352-P304+P340-P322-P501 | 0.1mg 5x5micrograms 5x10micrograms |
| | Application(s): Peptide that blocks voltage-dependent Kv1.3 potassium channels | |
| | rMargatoxin , see Margatoxin, 99+%, J61103, p. 278 | |
| J62588 | Masitinib, 99+% [790299-79-5], C ₂₆ H ₃₀ N ₆ O ₅ , F.W. 498.64, Crystalline solid ! H:H361-H319-H317, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 25mg 50mg |
| | Application(s): Protein tyrosine kinase inhibitor | |
| J63412 | Mast Cell Degranulating Peptide [H-Ile-Lys-Cys-Asn-Cys-Lys-Arg-His-Val-Ile-Lys-Pro-His-Ile-Cys-Arg-Lys-Ile-Cys-Gly-Lys-Asn-NH ₂ (Cys3-Cys15, Cys5-Cys19), MCD Peptide] [32908-73-9], C ₁₁₀ H ₁₉₂ N ₄₆ O ₂₄ S ₄ , F.W. 2587.22, Powder, RTECS OQ5980000, MDL MFCD00167557 | 0.5mg |
| | Application(s): Degranulates mast cells, initiating histamine release | |
| J63655 | Mast Cell Degranulating Peptide HR-1 [Ile-Asn-Leu-Lys-Ala-Ile-Ala-Ala-Leu-Val-Lys-Lys-Val-Leu-NH ₂] [80533-94-4], C ₇₁ H ₁₃₃ N ₁₉ O ₁₅ , F.W. 1492.96, Powder, MDL MFCD00133526 | 1mg 5mg |
| | Application(s): Degranulates mast cells, initiating histamine release | |
| J60447 | Mast Cell Degranulating Peptide HR-2 [Phe-Leu-Pro-Leu-Ile-Leu-Gly-Lys-Leu-Val-Lys-Gly-Leu-Leu-NH ₂] [80388-04-1], C ₇₇ H ₁₃₅ N ₁₇ O ₁₄ , F.W. 1523.02, Powder | 1mg 5mg |
| | Application(s): Degranulates mast cells, initiating histamine release | |
| J61662 | Mastoparan [Ile-Asn-Leu-Lys-Ala-Leu-Ala-Ala-Leu-Ala-Lys-Lys-Ile-Leu-NH ₂] [72093-21-1], C ₇₀ H ₁₃₁ N ₁₉ O ₁₅ , F.W. 1478.93, Powder, BRN 5491949, MDL MFCD00076865 | 1mg 5mg |
| | Application(s): A peptide toxin originally isolated from wasp venom; stimulates exocytosis | |
| J61173 | Mastoparan X [Ile-Asn-Trp-Lys-Gly-Ile-Ala-Ala-Met-Ala-Lys-Lys-Leu-Leu-NH ₂] [72093-22-2], C ₇₃ H ₁₃₆ N ₂₀ O ₁₅ S, F.W. 1555.97, Powder | 1mg |
| | Application(s): Has effects similar to mastoparan; binds with high affinity to calmodulin and inhibits sarcoplasmic reticulum calcium-ATPase | |
| J65221 | Matrix Metalloproteinase Inhibitor I [MMP Inhibitor I, 4-Abz-Gly-Pro-D-Leu-D-Ala-NHOH] C ₂₃ H ₃₄ N ₆ O ₆ , F.W. 490.55, Powder, MDL MFCD00237459 | 5mg |
| | Maxivent , see Doxofylline, J60575, p. 201 MBHA.HCl resin , see 4-Methylbenzhydrylamine resin bound, 44455, p. 286 MCD Peptide , see Mast Cell Degranulating Peptide, J63412, p. 278 MDL , see Calpain Inhibitor III, 95+%, J62919, p. 144 MDL 16455 hydrochloride , see Fexofenadine hydrochloride, J63262, p. 220 MDL-72222 , see 3-Tropanyl-3,5-dichlorobenzoate, 99+%, J62583, p. 383 | |
| J64692 | MDM2 Inhibitor ▲ [trans-4-Iodo-4'-boranyl-chalcone, (E)-4-(3-(4-Iodophenyl)acryloyl)phenylboronic acid] [562823-84-1], C ₁₅ H ₁₂ BrO ₃ , F.W. 377.97, Solid, MDL MFCD06798340 | 10mg |
| | MEAD acid , see cis-5,8,11-Eicosatrienoic acid, J63870, p. 204 | |
| H26694 | Meat Peptone ■ ■ [Peptones, meat] [73049-73-7], MDL MFCD00131829, † | 100g 500g |
| | Application(s): Peptone is used in nutrient media for growing bacteria and fungi | |
| J60257 | Mecamylamine hydrochloride [826-39-1], C ₁₁ H ₂₁ N HCl, F.W. 203.75, Powder, Merck 14,5774, UN2811, EINECS 212-555-8, RTECS RB6900000, MDL MFCD00151462 ! H:H301-H315-H319-H335, P:P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a | 5mg 25mg 100mg |
| | Application(s): Nicotiny acetylcholine receptor antagonist | |
| | Mechlorethamine hydrochloride , see Chloromethyl pivalate, A11967, p. 157 | |
| J62464 | Meclizine dihydrochloride monohydrate [31884-77-2], C ₂₅ H ₂₇ ClN ₂ ·2HCl·H ₂ O, F.W. 481.89 (463.88anhy), Powder, m.p. 210-213°, Merck 14,5777 ! H:H302-H361, P:P281-P264-P301+P312-P308+P313-P405-P501 | 1g 5g 10g |
| | Application(s): Antiemetic and H1-histamine receptor antagonist | |
| | Meclofenamate sodium , see Meclofenamic acid sodium salt, 99+%, J60484, p. 279 | |






| Stock # | Description | Size |
|---------|--|-----------------|
| J60484 | Meclofenamic acid sodium salt, 99+% [Meclofenamate sodium, 2-[(2,6-Dichloro-3-methylphenyl)-amino]benzoic acid] [6385-02-0], C ₁₇ H ₁₁ Cl ₂ NNaO ₂ , F.W. 318.13, Powder, EINECS 228-983-3, RTECS CB2975500, MDL MFCD00077376 | 1g 5g 25g |
| | Application(s): Inhibits 5-lipoxygenase and cyclooxygenase; NSAID | |
| | Mecobalamin , see Methylcobalamin hydrate, A11176, p. 286 Mefenacid , see Mefenamic acid, 98%, J62705, p. 279 | |
| J62705 | Mefenamic acid, 98% [2-[(2,3-Dimethylphenyl)amino]benzoic acid, Mefenacid] [61-68-7], C ₁₅ H ₁₃ NO ₂ , F.W. 214.29, Powder, Merck 14,5798, EINECS 200-513-1, RTECS CB4550000, MDL MFCD00051721 ! H: H302, P: P264-P270-P301+P312-P330-P501a | 25g 100g |
| | Application(s): An non-steroidal anti-inflammatory drug with antiproliferative activity against human colon cancer cells | |
| | MEGA-10 , see N-Decanoyl-N-methylglucamine, J60173, p. 176 MEGA-8 , see N-Octanoyl-N-methylglucamine, J63574, p. 306 Meglumine , see N-Methyl-D-glucamine, L14282, p. 288 | |
| J64424 | [Met 210] Melanocyte Protein PMEL 17 (209-217), human, mouse [Ile-Met-Asp-Gln-Val-Pro-Phe-Ser-Val] C ₄₁₇ H ₇₇₄ N ₁₀ O ₁₄ S, F.W. 1035.21, Solid, MDL MFCD03093433 | 1mg |
| J64310 | α-Melanocyte Stimulating Hormone amide [α-MSH amide] [581-05-5], C ₇₇ H ₁₀₉ N ₂₁ O ₁₉ S, F.W. 1664.88, Solid | 1mg 5mg |
| | | |
| J64142 | α-Melanocyte Stimulating Hormone free acid [α-MSH free acid] [10466-28-1], C ₇₇ H ₁₀₈ N ₂₀ O ₂₀ S, F.W. 1665.86, Solid | 1mg |
| J65192 | β-Melanocyte Stimulating Hormone, human [β-Melanotropin, human, Ala-Glu-Lys-Lys-Asp-Glu-Gly-Pro-Tyr-Arg-Met-Glu-His-Phe-Arg-Trp-Gly-Ser-Pro-Pro-Lys-Asp] [17908-57-5], C ₁₁₈ H ₁₇₇ N ₃₄ O ₃₅ S, F.W. 2660.91, Solid, MDL MFCD00167548 | 1mg |
| J65088 | [D-Trp8] γ-Melanocyte Stimulating Hormone [Tyr-Val-Met-Gly-His-Phe-Arg-D-Trp-Asp-Arg-Phe-Gly, D-Trp-γ-MSH] C ₇₄ H ₉₉ N ₂₁ O ₁₅ S, F.W. 1570.77, Solid | 1mg |
| J60045 | Melanocyte-Stimulating Hormone-Release Inhibiting Factor, synthetic [H-Pro-Leu-Gly-NH ₂ , MIF-I] [2002-44-0], C ₁₀₃ H ₂₀₄ N ₄ O ₃ , F.W. 284.36, Lyophilized powder, Merck 14,5813, EINECS 217-902-7, MDL MFCD00037866 | 250mg 1g |
| | Application(s): Blocks the release of α-melanocyte stimulating hormone, increases brain dopamine levels and antagonizes physiological and behavioral opioid effects in vivo | |
| J65115 | Melanotan II [[Acetyl-Nle4, Asp5, DPhe7, Lys10)-cyclo-α-MSH (4-10) amide, Ac-Nle-cf[Asp-His-DPhe-Arg-Trp-Lys]-NH ₂] [121062-08-6], C ₉₀ H ₁₀₉ N ₁₅ O ₂₄ , F.W. 1024.18, Solid, RTECS OL4225000, MDL MFCD06795842 | 1mg |
| J62452 | Melatonin, 99+% [Regulin, N-Acetyl-5-methoxytryptamine] [73-31-4], C ₁₃ H ₁₆ N ₂ O ₂ , F.W. 232.28, Powder, m.p. 116-120°, Merck 14,5816, EINECS 200-797-7, RTECS AC5955000, BRN 205542, MDL MFCD00005655 ⚠ H: H361, P: P281-P201-P202-P308+P313-P405-P501a | 5g 25g |
| | Application(s): A pineal gland hormone associated with sleep regulation. It induces apoptosis | |
| B22209 | D-(+)-Melezitose hydrate, 99% ■ [207511-10-2], C ₁₈ H ₃₂ O ₁₆ ·xH ₂ O, F.W. 504.46 (anhy), m.p. ca 160° dec., [α] _D ²⁰ +88° (c=4 in water), Merck 14,5819, EINECS 209-894-9, BRN 99539, MDL MFCD00149448, † | 10g 50g |
| |  | |
| J60439 | α-D-(+)-Melibiose [6-O-α-D-Galactopyranosyl-D-glucose] [585-99-9], C ₁₂ H ₂₂ O ₁₁ , F.W. 342.30, Crystalline powder, Merck 14,5820, EINECS 209-568-6, MDL MFCD00198188, † | 5g 25g |
| | Melitose pentahydrate , see D-(+)-Raffinose pentahydrate, A18313, p. 335 | |










| Stock # | Description | Size |
|---|---|--|
| J60635 | Meloxicam [MOBIC, Metacam] [71125-38-7], C ₁₄ H ₁₃ N ₃ O ₄ S ₂ , F.W. 351.39, Powder, m.p. 255°, Merck 14,5826, UN2811, RTECS DL0702000, MDL MFCD00868752 ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 5g 25g |
| Application(s): A NSAID with high inhibitory action against cyclooxygenase (COX-2) | | |
| J63830 | Memantine hydrochloride [41100-52-1], C ₁₇ H ₂₁ N HCl, F.W. 215.76, Powder, Merck 14,5829, EINECS 255-219-6, MDL MFCD00214336 | 50mg |
| Application(s): An NMDA receptor antagonist; stimulates dopamine release | | |
| Menadione , see 2-Methyl-1,4-naphthoquinone, A13593, p. 289 Menaphthone , see 2-Methyl-1,4-naphthoquinone, A13593, p. 289 p-Menth-1-en-8-ol , see α-Terpineol, 16285, p. 360 | | |
| A18098 | DL-Menthol, 98+% [(±)-2-Isopropyl-5-methylcyclohexanol] [89-78-1], C ₁₀ H ₁₈ O, F.W. 156.27, m.p. 33-36°, b.p. 212-216°, f.p. 93°(199°F), d. 0.890, n _D ²⁰ 1.4615, Merck 14,5837, Fieser 12,294 13,172, EINECS 201-939-0, RTECS OT0350000, BRN 3194263, MDL MFCD00001484, † ! H:H318-H335-H315, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a |  50g 100g 250g 1kg |
| Application(s): Has local anesthetic and counter-irritant effects; a weak kappa-opioid receptor agonist | | |
| L06102 | D-Menthol, 99% [(1S,2R,5S)-2-Isopropyl-5-methylcyclohexanol] [15356-60-2], C ₁₀ H ₁₈ O, F.W. 156.27, m.p. 41-44°, b.p. 104-105°/10mm, f.p. 91°(195°F), d. 0.890, [α] _D ²⁰ +49° (c=10 in ethanol), Fieser 12,294 13,172 16,203, EINECS 239-387-8, RTECS OT0350000, BRN 1902292, MDL MFCD00062983, † ! H:H318-H335-H315, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a |  25g 100g |
| A10474 | L-Menthol, 99% [(1R,2S,5R)-2-Isopropyl-5-methylcyclohexanol] [2216-51-5], C ₁₀ H ₁₈ O, F.W. 156.27, m.p. 42-45°, b.p. 212-216°, f.p. 93°(199°F), d. 0.89, [α] _D ²⁰ -50° (c=10 in ethanol), Merck 14,5837, Fieser 12,294 13,172 16,203, EINECS 218-690-9, RTECS OT0700000, BRN 1902293, MDL MFCD00062979, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a The L-menthyl ester of succinic acid has been used in a chiral synthesis of (1S,2S)-cyclopropanedicarboxylic acid: <i>Org. Synth. Coll.</i> , 8, 141 (1993):  |  50g 250g 1kg |
| One recrystallization gives the pure enantiomer. | | |
| Mepyramine maleate , see Pyrilamine maleate, J63247, p. 332 | | |
| B20391 | Mercaptoacetic acid, 97+% Δ [Thioglycolic acid] [68-11-1], HSCH ₂ CO ₂ H, F.W. 92.11, m.p. -12°, b.p. 220°, f.p. 119°(246°F), d. 1.295, n _D ²⁰ 1.5045, Merck 14,9336, Fieser 1,1153 7,366, UN1940, EINECS 200-677-4, RTECS A15950000, BRN 506166, MDL MFCD00004876, † ! H:H301-H311-H331-H314, P:P301+P310-P303+P361+P353-P305+P351+P338-P361-P405-P501a | 100g 500g 2.5kg |
| Application(s): Reagent that protects tryptophan in amino acid analysis | | |
| L14356 | Mercaptoacetic acid sodium salt, 97% Δ \blacksquare [Sodium mercaptoacetate, Sodium thioglycolate] [367-51-1], HSCH ₂ CO ₂ Na, F.W. 114.10, m.p. ca 305°, Merck 14,8692, UN3335, EINECS 206-696-4, RTECS A17700000, BRN 4569109, MDL MFCD00043386, † ! H:H302-H317, P:P261-P280-P302+P352-P321-P301+P312-P501a | 25g 100g 500g |
| Application(s): Reagent that protects tryptophan in amino acid analysis | | |
| J60290 | Mercaptoacetic acid sodium salt, 98% Δ \blacksquare [Sodium mercaptoacetate, Sodium thioglycolate] [367-51-1], HSCH ₂ CO ₂ Na, F.W. 114.10, Powder, m.p. ca 305°, Merck 14,8692, UN3335, EINECS 206-696-4, RTECS A17700000, BRN 4569109, MDL MFCD00043386, † ! H:H302-H317, P:P261-P280-P302+P352-P321-P301+P312-P501a | 25g 100g 1kg |
| Application(s): Reagent that protects tryptophan in amino acid analysis | | |
| 2-Mercaptobenzoic acid , see Thiosalicylic acid, A13401, p. 367 | | |
| A14086 | 2-Mercaptobenzothiazole, 97% Δ [Benzothiazole-2-thiol] [149-30-4], C ₇ H ₅ NS ₂ , F.W. 167.25, m.p. 178-182°, f.p. 243°(469°F), d. 1.420, Merck 14,5868, Solubility: Soluble in alkali and alkali carbonate solutions, UN3077, EINECS 205-736-8, RTECS DL6475000, BRN 119484, MDL MFCD00005781, † ! H:H400-H410-H317, P:P261-P280-P302+P352-P321-P363-P501a Reagent for determination of Ag, Au, Bu, Cd, Hg, Ir, Pt, Tl. |  10g 100g 500g 2.5kg |

| Stock # | Description | Size |
|--|---|---|
| J63989 | 2-Mercaptoethane sulfonic acid sodium salt, 96% [Coenzyme M sodium salt, MESNA] [19767-45-4], HSCH ₂ CH ₂ SO ₃ Na, F.W. 164.18, Powder, Merck 14,5909, EINECS 243-285-9, RTECS KI7968000, BRN 3657828, MDL MFCD00007535 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 10g 25g |
| Application(s): Water-soluble disulfide reducing agent. Cofactor in methyl transfer reactions | | |
| A15890 | 2-Mercaptoethanol, 98+% Δ \blacksquare [Thioethylene glycol, Thioglycol] [60-24-2], HSCH ₂ CH ₂ OH, F.W. 78.13, m.p. -100°, b.p. 156-158°, f.p. 73°(163°F), d. 1.114, n _D ²⁰ 1.500, Merck 14,5869, Fieser 1,643, UN2966, EINECS 200-464-6, RTECS KL5600000, BRN 773648, MDL MFCD00004890, \dagger  H:H301-H311-H330-H318-H400-H410-H315-H317-H335, P:P301+P310-P304+P340-P305+P351+P338-P320-P330-P361-P405-P501a Protective agent for preventing oxidation of thiol groups in proteins: <i>Enzyme Assays</i> , R. Eisenthal and M. J. Danson, Eds., OUP, Oxford (1992), p 265. In the presence of BF ₃ etherate, reacts with carbonyl compounds to give monothioacetals (1,3-oxathiolanes): <i>J. Org. Chem.</i> , 33 , 2133 (1968). Amberlyst 15 is also effective: <i>Synthesis</i> , 1826 (2001), as is In(OTf) ₃ : <i>Synlett</i> , 1535 (2002). 1,3-Oxathiolanes can be prepared from acid-sensitive aldehydes with LiBH ₄ as catalyst in acetonitrile: <i>Synlett</i> , 238 (2001). Cleavage can be effected, e.g. with chloramine-T: <i>Tetrahedron Lett.</i> , 3445 (1971), isoamyl nitrite: <i>Tetrahedron Lett.</i> , 3561 (1978), or periodic acid: <i>Tetrahedron Lett.</i> , 37 , 4331 (1996). Selective cleavage of oxathiolanes in the presence of dithiolanes has been achieved with triphenylcarbenium tetrafluoroborate: <i>J. Chem. Soc., Perkin 1</i> , 542 (1972), or 4-nitrobenzaldehyde catalyzed by TMS-OTf: <i>J. Chem. Soc. Chem. Commun.</i> , 1937 (1994). Compare 1,2-Ethanedithiol, L12865 . 2-Mercaptoethanol is a reagent for the specific cleavage of the N-dithiasuccinimide protecting group from amines. See Chlorocarbonylsulfonyl chloride, L06432 . | 250g 1kg 5kg |
| Application(s): Solubilizes proteins by reducing disulfide linkages | | |
| A14377 | 2-Mercaptoethylamine hydrochloride, 98+% \blacksquare [Aminoethanethiol hydrochloride, Cysteamine hydrochloride] [156-57-0], HSCH ₂ CH ₂ NH ₂ ·HCl, F.W. 113.61, m.p. 65-69°, Merck 14,2779, Solubility: Soluble in water and alcohol, EINECS 205-858-1, RTECS KJ0200000, BRN 3590083, MDL MFCD00012904, \dagger ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a For selective protection of nitrogen by silylation, see: <i>Synthesis</i> , 924 (1980). | 25g 100g 500g |
| Application(s): An inhibitor of DMBA-induced mammary tumors | | |
| L01346 | 2-Mercaptoimidazole, 98+% [2-Imidazolethiol] [872-35-5], C ₃ H ₄ N ₂ S, F.W. 100.14, m.p. 222-227°, EINECS 212-823-4, RTECS NI8515000, BRN 105775, MDL MFCD00005188, \dagger ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a |  1g 5g 25g |
| A13094 | 2-Mercapto-1-methylimidazole, 98% [Methimazole, 1-Methylimidazole-2-thiol] [60-56-0], C ₄ H ₆ N ₂ S, F.W. 114.17, m.p. 144-147°, b.p. 280° dec., Merck 14,5971, Solubility: Freely soluble in water. Soluble in alcohol, chloroform. Sparingly soluble in ether, benzene., EINECS 200-482-4, RTECS NI8615000, BRN 108646, MDL MFCD00179321, \dagger  ! H:H361-H317, P:P261-P280-P302+P352-P321-P405-P501a |  25g 100g |
| Application(s): Possesses antioxidant properties | | |
| N-[(S)-3-Mercapto-2-methylpropionyl]-L-proline , see Captopril, J63593, p. 146 | | |
| L10257 | 2-Mercaptopropionic acid, 97% [Thiolactic acid] [79-42-5], C ₃ H ₄ O ₂ S, F.W. 106.14, m.p. 10-14°, b.p. 217°, f.p. 107°(225°F), d. 1.196, n _D ²⁰ 1.4820, Merck 14,9340, UN2936, EINECS 201-206-5, RTECS UF5250000, BRN 506218, MDL MFCD00004862, \dagger  ! H:H314-H302-H332, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a |  10g 100g 500g |
| A12197 | 6-Mercaptopurine monohydrate, 98% [6-Purinethiol monohydrate] [6112-76-1], C ₅ H ₄ N ₄ S·H ₂ O, F.W. 170.19 (152.17anhy), m.p. ca 315° dec., Merck 14,5871, EINECS 200-037-4, RTECS UP0400000, BRN 4012091, MDL MFCD03854445  ! H:H341-H361-H302, P:P281-P264-P301+P312-P308+P313-P405-P501a |  1g 5g 25g |
| 2-Mercaptopyrimidine-4,6-dione , see 4,6-Dihydroxy-2-mercaptopyrimidine, A12681, p. 192 | | |
| B23301 | Mercaptosuccinic acid, 98% [Thiomalic acid] [70-49-5], C ₄ H ₆ O ₄ S, F.W. 150.15, m.p. 150-154°, Merck 14,9343, EINECS 200-736-4, RTECS WM8225000, BRN 1099858, MDL MFCD00004860, \dagger ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a |  25g 100g 500g |
| 3-Mercapto-DL-valine , see DL-Penicillamine, B24710, p. 313 | | |
| 3-Mercapto-D-valine , see D-(-)-Penicillamine, A11446, p. 313 | | |


| Stock # | Description | Size |
|--|---|--|
| J61250 | Mercurochrome [Mercury dibromofluorescein disodium salt] [129-16-8], C ₂₀ H ₈ Br ₂ HgNa ₂ O ₆ , F.W. 750.65, Crystalline powder, Merck 14,5867, UN2025, EINECS 204-933-6, RTECS LM5250000, MDL MFCD00013081  H:H300-H310-H330-H373-H400-H410, P:P301+P310-P304+P340-P320-P330-P361-P405-P501a | 25g 100g |
| Application(s): Merbromin. An organomercuric compound that is a topical antiseptic | | |
| Mercury dibromofluorescein disodium salt, see Mercurochrome, J61250, p. 282 | | |
| L17027 | Merrifield Resin, 1% crosslinked, 200-400 mesh, 1.0-1.3mmol/g [Chloromethyl polystyrene, Chloromethylated styrene-divinylbenzene copolymer] [55844-94-5], MDL MFCD00146406 Crosslinked with 1% divinylbenzene. Supporting resin for solid phase peptide synthesis |  5g 20g 100g |
| J63257 | MES, 0.2M buffer soln., pH 5.5 [145224-94-8], Liquid | 250ml 500ml |
| J60930 | MES, 0.2M buffer soln., pH 6.0 [145224-94-8], Liquid H:EUH210 | 250ml 500ml |
| J62081 | MES, 0.5M buffer soln., pH 5.0 [145224-94-8], Liquid | 100ml 250ml |
| J62534 | MES, 0.5M buffer soln., pH 5.5 [145224-94-8], Liquid | 100ml 250ml |
| J62574 | MES, 0.5M buffer soln., pH 6.0 [145224-94-8], Liquid | 100ml 250ml |
| J63778 | MES, 0.5M buffer soln., pH 6.5 [145224-94-8], Liquid | 100ml 250ml |
| J63089 | MES, 0.5M buffer soln., pH 7.0 [145224-94-8], Liquid | 100ml 250ml |
| J63706 | MES, 0.5M buffer soln., pH 7.5 [145224-94-8], Liquid | 100ml 250ml |
| J61665 | MES, 0.5M buffer soln., pH 8.0 [145224-94-8], Liquid | 100ml 250ml |
| J63944 | MES, 0.5M buffer soln., pH 8.5 [145224-94-8], Liquid | 100ml 250ml |
| J60031 | MES, 0.5M buffer soln., pH 9.0 [145224-94-8], Liquid | 100ml 250ml |
| J61960 | MES, 1.0M buffer soln., pH 5.0 [145224-94-8], Liquid, † ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | 250ml 500ml |
| J63341 | MES, 1.0M buffer soln., pH 5.5 [145224-94-8], Liquid | 250ml 500ml |
| J60763 | MES, 1.0M buffer soln., pH 6.0 [145224-94-8], Liquid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250ml 500ml |
| J61587 | MES, 1.0M buffer soln., pH 6.5 [145224-94-8], Liquid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250ml 500ml |
| J62231 | MES, 1.0M buffer soln., pH 7.0 [145224-94-8], Liquid | 250ml 500ml |
| J62752 | MES, 1.0M buffer soln., pH 7.5 [145224-94-8], Liquid | 250ml 500ml |
| J61556 | MES, 1.0M buffer soln., pH 8.0 [145224-94-8], Liquid | 250ml 500ml |



| Stock # | Description | Size |
|---------|--|--|
| J62720 | MES, 1.0M buffer soln., pH 8.5 [145224-94-8], Liquid | 250ml 500ml |
| J61656 | MES, 1.0M buffer soln., pH 9.0 [145224-94-8], Liquid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250ml 500ml |
| A16104 | MES monohydrate, 98% [4-Morpholineethanesulfonic acid monohydrate, 2-(4-Morpholinyl)ethanesulfonic acid monohydrate] [145224-94-8], C ₈ H ₁₃ NO ₃ S·H ₂ O, F.W. 213.26 (195.24anhy), m.p. ca 308° dec., Merck 14,5902, EINECS 224-632-3, RTECS QE3479500, BRN 141319, MDL MFCD00149409, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Biological buffer, pKa = 6.15 at 20°: <i>Biochemistry</i> , 5, 467 (1966). Application(s): Good's buffer |  25g 100g 500g |
| H56472 | MES hydrate, 99+% [2-(4-Morpholinyl)ethanesulfonic acid hydrate, 4-Morpholineethanesulfonic acid hydrate] [4432-31-9], C ₈ H ₁₃ NO ₃ S·xH ₂ O, F.W. 195.24(anhy), m.p. ca 308° dec., Merck 14,5902, EINECS 224-632-3, RTECS QE3479500, BRN 141319, MDL MFCD00149409, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a |  250g 500g |
| J61979 | MES-buffered saline (5X), pH 6.5 [145224-94-8], Liquid, Note: Contains 125mM MES and 750mM NaCl 7 at pH 6.5 H:EUH210 | 250ml 500ml |
| J61938 | MES-buffered saline (5X), pH 7.0 [145224-94-8], Liquid, Note: Contains 125mM MES and 750mM NaCl 7.0 at pH 7.0 | 250ml 500ml |
| J63411 | MES lysis buffer with NP-40 Liquid, Note: This buffer contains: 25mM MES, 150mM NaCl, 1% NP-40, and 5mM EDTA, pH 7.0. ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 250ml 500ml |
| J60244 | MES lysis buffer with NP-40 (2X) Liquid, Note: This buffer contains 50mM MES, 300mM sodium chloride, 1% NP-40, and 10mM EDTA at pH 7.0. ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 125ml 250ml |
| J62693 | MES lysis buffer with Triton® X-100 Liquid, Note: This buffer contains: 25mM MES, 150mM sodium chloride, 1% Triton X-100, and 5mM EDTA at pH 7.0. | 250ml 500ml |
| J63169 | MES lysis buffer with Triton® X-100 (2X) Liquid, Note: This buffer contains: 50mM MES, 300mM NaCl, 2% Triton X-100 and 10mM EDTA at pH 7.0. | 125ml 250ml |
| | MESNA , see 2-Mercaptoethane sulfonic acid sodium salt, 96%, J63989, p. 281 Mesoxalylurea monohydrate , see Alloxan monohydrate, A15324, p. 89 | |
| J62138 | MES-SDS running buffer (20X) Liquid, Note: This buffer contains: 1M MES, 1M Tris base, 2% SDS and 20mM EDTA at pH 7.3. | 500ml 1L |
| | H-L-Met-OH , see L-Methionine, Cell Culture Reagent, J61904, p. 284 L-Met-AFC , see L-Methionine-7-amido-4-trifluoromethylcoumarin, J65843, p. 284 Metacam , see Meloxicam, J60635, p. 280 | |
| A17527 | Metanil Yellow [C.I. 13065] [587-98-4], C ₁₈ H ₁₁ N ₃ NaO ₃ S, F.W. 375.38, Merck 14,5928, EINECS 209-608-2, RTECS DB7329500, BRN 3831568, MDL MFCD00007486, † ! H:H318-H412, P:P280-P273-P305+P351+P338-P310-P501a |  50g 250g |
| | Application(s): As indicator. Transition interval: pH: 1.2 (red) to 2.3 (yellow) | |
| | Metformin hydrochloride , see 1,1-Dimethylbiguanide hydrochloride, J63361, p. 196 | |
| 44571 | Methanol, Biograde, 99.8+% [67-56-1], CH ₃ OH, F.W. 32.04, Liquid, m.p. -98°, b.p. 64.7°, f.p. 11° (52°F), d. 0.791, n _D ²⁰ 1.3290, Merck 14,5957, UN1230, EINECS 200-659-6, RTECS PC1400000, BRN 1098229, MDL MFCD00004595, Note: Filtered through 0.2 μ filter, † ! H:H225-H301-H311-H331-H370, P:P210-P301+P310-P303+P361+P353-P361-P405-P501a | 4L 4x4L |
| | Application(s): In nucleic acid and peptide synthesis | |
| | Methimazole , see 2-Mercapto-1-methylimidazole, A13094, p. 281 | |
| A11457 | DL-Methionine, 99% [(+/-)-2-Amino-4-(methylthio)butyric acid, H-DL-Met-OH] [59-51-8], C ₅ H ₁₁ NO ₂ S, F.W. 149.21, m.p. ca 272° dec., d. 1.34, Merck 14,5975, EINECS 200-432-1, RTECS PD0456000, BRN 636185, MDL MFCD00063096, † Soft nucleophile, which acts as a methyl acceptor in the cleavage of methyl ethers of phenols by Methanesulfonic acid , A13565. |  250g 1kg 5kg |




| Stock # | Description | Size |
|--|---|--|
| B21213 | D-Methionine, 99% [(R)-2-Amino-4-(methylthio)butyric acid, H-D-Met-OH] [348-67-4], C ₅ H ₁₁ NO ₂ S, F.W. 149.21, m.p. ca 280° dec., [α] _D ²⁰ -23° (c=2 in 2N HCl), Merck 14,5975, EINECS 206-483-6, RTECS PD0455000, BRN 1722293, MDL MFCD00002622, † |  5g |
| | | 25g |
| | | 100g |
| A10318 | L-Methionine, 98+% [(S)-2-Amino-4-(methylthio)butyric acid, H-Met-OH] [63-68-3], C ₅ H ₁₁ NO ₂ S, F.W. 149.21, m.p. ca 280° dec., [α] _D ²⁰ +23° (c=2 in 2N HCl), Merck 14,5975, EINECS 200-562-9, RTECS PD0457000, BRN 1722294, MDL MFCD00063097, † |  100g |
| | | 500g |
| | | 2.5kg |
| J61904 | L-Methionine, Cell Culture Reagent [H-L-Met-OH] [63-68-3], C ₅ H ₁₁ NO ₂ S, F.W. 149.21, Powder, m.p. 284° dec., Merck 14,5975, EINECS 200-562-9, BRN 1722294, MDL MFCD00063097, † | 50g |
| | | 100g |
| | | 500g |
| J65843 | L-Methionine-7-amido-4-trifluoromethylcoumarin [L-Met-AFC, L-M-AFC] C ₁₅ H ₁₅ F ₃ N ₂ O ₃ S, F.W. 360.35, Powder | 10mg |
| | | 25mg |
| B25094 | DL-Methionine sulfone, 98% [H-DL-Met(O ₂)-OH] [820-10-0], C ₅ H ₁₁ NO ₃ S, F.W. 181.21, EINECS 212-466-4, MDL MFCD00025079, † |  1g |
| | | 5g |
| | | 25g |
| A17027 | L-Methionine sulfone, 99+% [H-Met(O ₂)-OH] [7314-32-1], C ₅ H ₁₁ NO ₃ S, F.W. 181.21, m.p. 254° dec., [α] _D ²⁰ +11.6° (c=0.69 in water), EINECS 230-774-7, BRN 1725510, MDL MFCD00066020 |  1g |
| | | 5g |
| | | 25g |
| A18081 | DL-Methionine sulfoxide, 98+% [H-DL-Met(O)-OH] [62697-73-8], C ₅ H ₁₁ NO ₂ S, F.W. 165.21, m.p. ca 230° dec., EINECS 263-700-7, MDL MFCD00002620, † |  5g |
| | | 25g |
| | | 100g |
| J62873 | L-Methionine sulfoxide [3226-65-1], C ₅ H ₁₁ NO ₂ S, F.W. 165.21, Powder, EINECS 221-758-0, BRN 4129939, MDL MFCD00063093 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| | | 5g |
| | | 25g |
| J63075 | Methotrexate ▲ ■ [59-05-2], C ₂₀ H ₂₅ N ₅ O ₆ , F.W. 472.45, Powder, UN1544, EINECS 200-413-8, RTECS MA1225000, MDL MFCD00150847, † ☠️ ⚠️ H:H301-H360-H315-H319, P:P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): Anti-inflammatory, cytotoxic drug that acts as a potent folic acid antagonist | 100mg |
| | | 1g |
| | | 25g |
| J64730 | 5-Methoxybenzoxazole-2-thiol ▲ ■ [2-Mercapto-5-methoxybenzo[d]oxazole, 5-Methoxy-2(3H)-benzoxazolethione] [49559-83-3], C ₈ H ₇ NO ₂ S, F.W. 181.21, Powder, m.p. 218-223°, MDL MFCD03030041 ☠️ ! H:H302-H315-H318-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| | | 25g |
| | | 100g |
| 1-(4-Methoxybenzoyl)-2-pyrrolidinone, see Aniracetam, J61661, p. 104 (2R,3S,4S)-2-(4-Methoxybenzyl)-3,4-pyrrolidinediol-3-acetate, see Anisomycin, 97+%, J62964, p. 104 | | |
| J63839 | Methoxychlor [72-43-5], C ₁₆ H ₁₅ ClO ₂ , F.W. 345.65, Crystalline powder, m.p. 87°, Merck 14,5990, UN3077, EINECS 200-779-9, RTECS KJ3675000, BRN 2057367, MDL MFCD00000803 ☠️ ! H:H351-H302-H312-H332, P:P261-P280-P281-P302+P352-P405-P501a Application(s): Molecule with estrogenic activity | 5g |
| | | 25g |
| | | 100g |
| J62475 | 7-Methoxycoumarin-4-acetic acid, 99% [7-Methoxy-2-oxo-2H-1-benzopyran-4-acetic acid] [62935-72-2], C ₁₂ H ₁₀ O ₅ , F.W. 234.21, Crystalline solid, m.p. 193°, f.p. 87° (189°F), MDL MFCD0009774 Application(s): Precursor to coumarin-type fluorescent reagents | 100mg |
| | | 250mg |
| | | 1g |
| A17459 | 2-Methoxyethanol, 99% [Ethylene glycol monomethyl ether, Methyl Cellosolve] [109-86-4], CH ₃ OCH ₂ CH ₂ OH, F.W. 76.10, m.p. -85°, b.p. 124-125°, f.p. 46° (115°F), d. 0.965, n _D ²⁰ 1.4025, Merck 14,6038, UN1188, EINECS 203-713-7, RTECS KL5775000, BRN 1731074, MDL MFCD00002867, † ☠️ ⚠️ ! H:H360FD-H226-H302-H312-H332, P:P210-P241-P303+P361+P353-P302+P352-P405-P501a Application(s): Solvent for ninhydrin color reagent | 500ml |
| | | 2.5L |
| | | 10L |
| 2-Methoxyethyl ether, see Diethylene glycol dimethyl ether, A13397, p. 189 6-Methoxyharmane, see Harmine, L19068, p. 241 | | |









| Stock # | Description | Size |
|---------|---|--------------------|
| | (+)-6-Methoxy-α-methyl-2-naphthaleneacetic acid , see (S)-(+)-2-(6-Methoxy-2-naphthyl)propionic acid, L09855, p. 285 | |
| | 7-Methoxy-1-methyl-9H-pyrido[3,4-b]indole , see Harmine, L19068, p. 241 | |
| | 4-(6-Methoxy-2-naphthyl)-2-butanone , see Nabumetone, J63072, p. 296 | |
| L09855 | (S)-(+)-2-(6-Methoxy-2-naphthyl)propionic acid, 99% <i>[(+)-6-Methoxy-α-methyl-2-naphthaleneacetic acid, Naproxen]</i> [22204-53-1], C ₁₇ H ₁₆ O ₃ , F.W. 230.27, m.p. 154-156°, [α] _D ²⁰ +66° (c=1 in chloroform), Merck 14,6417, UN2811, EINECS 244-838-7, RTECS UF5275000, BRN 3591067, MDL MFCD00010500  | 1g 5g |
| | H:H301-H315-H319-H335, P:P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | 7-Methoxy-2-oxo-2H-1-benzopyran-4-acetic acid , see 7-Methoxycoumarin-4-acetic acid, 99%, J62475, p. 284 | |
| A16319 | 2-Methoxyphenol, 98+% ▲△ <i>[Catechol monomethyl ether, Guaiacol]</i> [90-05-1], C ₈ H ₈ O ₂ , F.W. 124.14, m.p. 28-31°, b.p. 204-206°, f.p. 82°(179°F), d. 1.129, n _D ²⁰ 1.5430, Merck 14,4553, EINECS 201-964-7, RTECS SL7525000, BRN 508112, MDL MFCD00002185, †  ! H:H302-H315-H319, P:P305+P351+P338 | 250g 1kg 5kg |
| A16827 | 3-(2-Methoxyphenoxy)-1,2-propanediol, 99+% <i>[Guaiacol glyceryl ether, Guaifenesin]</i> [93-14-1], C ₁₂ H ₁₄ O ₄ , F.W. 198.22, m.p. 80-82°, b.p. 215°/19mm, Merck 14,4555, EINECS 202-222-5, RTECS TY8400000, BRN 2049375, MDL MFCD00016873, †  ! H:H302, P:P264-P270-P301+P312-P330-P501a | 50g 250g 1kg |
| | Application(s): Centrally acting muscle relaxant with expectorant properties | |
| H51751 | 1-(3-Methoxyphenyl)homopiperazine monohydrochloride, 98% <i>[3-HPA HCl]</i> C ₁₃ H ₁₈ N ₂ O·HCl, F.W. 242.74, m.p. 169-173°, MDL MFCD16172199, Note: Sold in collaboration with Tosoh Organic Chemical Co., Ltd.  | 500mg |
| | Application(s): Useful intermediate for synthesis | |
| H51703 | 1-(4-Methoxyphenyl)homopiperazine monohydrochloride, 98% <i>[4-HPA HCl]</i> [934992-02-6], C ₁₃ H ₁₈ N ₂ O·HCl, F.W. 242.74, m.p. 175-179°, MDL MFCD11501072, Note: Sold in collaboration with Tosoh Organic Chemical Co., Ltd.  ! H:H315-H319-H335, P:P280g-P305+P351+P338 | 500mg |
| | Application(s): Useful intermediate for synthesis | |
| | 1-[2-(4-Methoxyphenyl)-2-[3-(4-methoxyphenyl)propoxy]ethyl]imidazole , see SKF-96365 hydrochloride, 99+%, J60937, p. 342 | |
| | 4-(2-Methoxyphenyl)-α-[(1-naphthalenyloxy)methyl]-1-piperazineethanol hydrochloride , see Naftopidil hydrochloride, 98+%, J63249, p. 297 | |
| | 1-[4-(2-Methoxyphenyl)piperazinyl]-3-(1-naphthyl)propan-2-ol , see Naftopidil, 98+%, J60311, p. 297 | |
| | 6-[3-(4-(2-Methoxyphenyl)-1-piperazinyl)propylamino]-1,3-dimethyluracil hydrochloride , see Urapidil hydrochloride, 98+%, J63219, p. 388 | |
| J63467 | (R)-1-Methoxy-2-propanol [4984-22-9], C ₄ H ₈ O ₂ , F.W. 89.11, Liquid, m.p. 119-121°, f.p. 33°(91°F), d. 0.921, n _D ²⁰ 1.403, UN3092, BRN 1718941, MDL MFCD01632587  ! H:H226-H336, P:P210-P241-P261-P303+P361+P353-P405-P501 | Call |
| | Application(s): For synthesis of optically active products | |
| J62757 | (S)-1-Methoxy-2-propanol [26550-55-0], C ₄ H ₈ O ₂ , F.W. 89.11, Liquid, m.p. 119-121°, f.p. 33°(91°F), d. 0.921, n _D ²⁰ 1.403, UN3092, BRN 1718940, MDL MFCD01632588  ! H:H226-H336, P:P210-P241-P261-P303+P361+P353-P405-P501 | Call |
| | Application(s): For synthesis of optically active products | |
| | (E)-1-Methoxy-4-propenylbenzene , see trans-Anethole, A13482, p. 103 | |
| A17108 | 8-Methoxypsoralen, 99% ▲ <i>[Xanthotoxin]</i> [298-81-7], C ₁₂ H ₈ O ₄ , F.W. 216.20, m.p. 146-150°, Merck 14,5988, EINECS 206-066-9, RTECS LV1400000, BRN 196453, MDL MFCD00005009, †   ! H:H340-H350-H318-H302, P:P280-P281-P305+P351+P338-P310-P405-P501a | 1g 5g 25g |
| | Application(s): A naturally occurring photoreactive substance | |
| J64435 | N-Methoxysuccinyl-Phe-Leu-Phe-7-amino-4-trifluoromethylcoumarin <i>[MeOSuc-FLF-AFC]</i> C ₃₀ H ₄₁ F ₃ N ₃ O ₈ , F.W. 750.76, Solid, MDL MFCD03452969 | 10mg |
| | 4'-Methoxy-3',5,7-trihydroxyflavanone , see 3',5,7-Trihydroxy-4'-methoxyflavanone, B20528, p. 377 | |
| J64922 | 2'-O-Methyladenosine, 99% [2140-79-6], C ₁₁ H ₁₃ N ₅ O ₄ , F.W. 281.27, Powder, MDL MFCD00056002 | 1g |
| | 2-Methylalanine , see 2-Aminoisobutyric acid, A13021, p. 96 | |

| Stock # | Description | Size |
|---------|---|------------------------|
| A12291 | Methylamine hydrochloride, 99% ■ [593-51-1], CH ₅ NH ₂ ·HCl, F.W. 67.52, m.p. 230-234°, b.p. 225-230°/15mm, Merck 14,6014, Solubility: Soluble in water, absolute alcohol, EINECS 209-795-0, RTECS PA0603000, BRN 3588822, MDL MFCD00012849, † ! H:H302-H319, P:P280f-P305+P351+P338 | 100g 500g 2.5kg |
| | Methylaminoacetic acid , see Sarcosine, A14594, p. 340 Methylaminoacetic acid hydrochloride , see Sarcosine hydrochloride, B25536, p. 340 (R)-2-(Methylamino)succinic acid , see N-Methyl-D-aspartic acid, 98+%, J61361, p. 286 3-Methylanthranilic acid , see 2-Amino-3-methylbenzoic acid, B24230, p. 96 | |
| J62431 | N-Methyl-L-arginine [2480-28-6], C ₇ H ₁₆ N ₂ O ₂ , F.W. 188.23, Powder | 10mg 50mg |
| J60890 | N-(O)-Methyl-L-arginine acetate, 99+% [L-NMMA] [53308-83-1], C ₉ H ₂₀ N ₂ O ₄ , F.W. 248.28, Powder, Merck 14,6022, BRN 6674255, MDL MFCD00069311 Application(s): Nitric oxide synthase inhibitor | 10mg 50mg |
| J61361 | N-Methyl-D-aspartic acid, 98+% [NMDA, (R)-2-(Methylamino)succinic acid] [6384-92-5], C ₈ H ₉ NO ₄ , F.W. 147.13, Powder, m.p. 187-192°, Merck 14,6662, RTECS C19457000, BRN 1724431, MDL MFCD00004226 | 50mg 100mg 500mg |
| | 4-Methylbenzenesulfonic acid monohydrate , see p-Toluenesulfonic acid monohydrate, 36506, p. 371 | |
| 44455 | 4-Methylbenzhydramine hydrochloride resin bound [MBHA.HCl resin] Powder, MDL MFCD00801150, Note: Poly(styrene-divinylbenzene), 1% cross-linked, 100-200 mesh base resin, loading 0.5-1.0mmol/g ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 5g 25g |
| | (R)-(+)-α-Methylbenzyl alcohol , see (R)-(+)-1-Phenylethanol, L19296, p. 316 (S)-(-)-α-Methylbenzyl alcohol , see (S)-(-)-1-Phenylethanol, B21188, p. 316 | |
| J63786 | Methyl caffeate [Caffeic acid methyl ester] [3843-74-1], C ₁₀ H ₁₀ O ₄ , F.W. 194.19, Powder, m.p. 158-161°, MDL MFCD00210468 Application(s): Inhibitor of protein tyrosine kinase | 250mg 1g |
| | Methyl caprylate , see Methyl octanoate, A10991, p. 289 Methyl Cellosolve® , see 2-Methoxyethanol, A17459, p. 284 | |
| 45490 | Methyl cellulose, viscosity 15 cPs [9004-67-5], Powder, Merck 14,6040, MDL MFCD00081763, † | 100g 500g 2.5kg |
| 43147 | Methyl cellulose, viscosity 400 cPs [9004-67-5], Powder, Merck 14,6040, MDL MFCD00081763, Note: Viscosity: 300-560 cPs for a 2% aqueous solution at 20°C, † | 100g 500g 2.5kg |
| 43146 | Methyl cellulose, viscosity 1600 cPs [9004-67-5], Powder, Merck 14,6040, MDL MFCD00081763, Note: Viscosity: 1125-2100 cPs for a 2% aqueous solution at 20°C, † | 100g 500g 2.5kg |
| 43483 | Methyl cellulose, viscosity 8000 cPs [9004-67-5], Powder, Merck 14,6040, MDL MFCD00081763, Note: Viscosity 7000-10,000 cPs for a 2% aqueous solution at 20°C, † | 100g 500g |
| 36718 | Methyl cellulose, viscosity 4000 cPs [9004-67-5], Powder, Merck 14,6040, MDL MFCD00081763, Note: Viscosity 4000 cPs for a 2% aqueous solution at 20°C, † | 100g 500g |
| | 3-O-Methyl-D-chiro-inositol , see D-Pinitol, H56648, p. 321 | |
| A11176 | Methylcobalamin hydrate, 99% [Cobinamide, Mecobalamin] [13422-55-4], C ₆₃ H ₉₁ N ₁₃ O ₁₄ P·xH ₂ O, F.W. 1344.41(anhy), EINECS 236-535-3, RTECS GG3745000, MDL MFCD00149221 | 100mg 500mg |











| Stock # | Description | Size |
|---------|---|---------------------------|
| J65528 | 2'-O-Methylcytidine, 99% [2140-72-9], C ₁₀ H ₁₅ N ₃ O ₅ , F.W. 257.24, Powder, MDL MFCD00056067 | 1g |
| 43492 | 5-Methylcytosine, 97% [554-01-8], C ₈ H ₁₁ N ₃ O, F.W. 125.13, Crystalline, Merck 14,6050, EINECS 209-058-3, RTECS UW7362350, MDL MFCD00233537 | 100mg 500mg |
| |  | |
| J64961 | N₆-Methyl-2'-deoxyadenosine, 99% [2'-Deoxy-N6-methyladenosine] [2002-35-9], C ₁₁ H ₁₅ N ₅ O ₅ , F.W. 265.27, Powder, MDL MFCD00055999 | 1g |
| J65209 | 5-Methyl-2'-deoxycytidine, 99% [2'-Deoxy-5-methylcytidine] [838-07-3], C ₁₀ H ₁₅ N ₃ O ₄ , F.W. 241.24, Powder, EINECS 212-655-1, RTECS HA3860000, MDL MFCD00006549 | 1g |
| J60509 | N-Methyldeoxyojirimycin [69567-10-8], C ₇ H ₁₃ NO ₄ , F.W. 177.20, Powder, m.p. 126-128°, BRN 1524564, MDL MFCD00133609 | 5mg 10mg |
| | Application(s): α-1,6-glucosidase inhibitor | |
| | N-Methyl-N-desacetylcolchicine , see Colcemid, 98+%, J63900, p. 167 (5S,10R)-(+)-5-Methyl-10,11-dihydro-5H-dibenzo[a,d]cyclohepten-5,10-imine maleate , see Dizocilpine maleate, 99+%, J63917, p. 200 5-Methyl-5,6-dihydrouracil , see 5,6-Dihydro-5-methyluracil, L01996, p. 191 Methyl 2,5-dihydroxycinnamate , see Erbstatin analog, J61612, p. 209 | |
| J60306 | N-Methyldopamine hydrochloride, 98+% [Epinine hydrochloride, Deoxyepinephrine hydrochloride] [62-32-8], C ₈ H ₁₃ NO ₂ ·HCl, F.W. 203.67, Powder, EINECS 200-528-3 | 1g 5g |
| | Application(s): Dopamine agonist | |
| | Methylene Azure , see Azure I, A17508, p. 116 | |
| J63265 | N,N'-Methylenebisacrylamide, 2% soln. [Bis-acrylamide, BAC] [110-26-9], C ₇ H ₁₀ N ₂ O ₂ , F.W. 154.17, Liquid, EINECS 203-750-9, MDL MFCD00008625, † | 500ml 1L |
| 43701 | N,N'-Methylenebisacrylamide, 99+% [Bis-acrylamide, BAC] [110-26-9], C ₇ H ₁₀ N ₂ O ₂ , F.W. 154.17, Powder, m.p. >300°, d. 1.235, EINECS 203-750-9, RTECS AS3678000, BRN 1706297, MDL MFCD00008625, † ! H: H302, P: P264-P270-P301+P312-P330-P501a Crosslinking agent for the synthesis of polyacrylamide gels. | 25g 100g |
| |  | |
| | 3,3'-Methylenebis(4-hydroxycoumarin) , see Dicumarol, J63634, p. 187 4,4'-Methylenebis(3-hydroxy-2-naphthoic acid) , see Pamoic acid, A15207, p. 311 | |
| A18174 | Methylene Blue, high purity, biological stain [Basic Blue 9, C.I. 52015] [122965-43-9], C ₁₆ H ₁₈ ClN ₃ S·xH ₂ O, F.W. 319.86(anhy), m.p. ca 180° dec., Merck 14,6060, EINECS 200-515-2, RTECS SO5600000, BRN 3599847, MDL MFCD00150006 ! H: H302, P: P264-P270-P301+P312-P330-P501a | 5g 25g 100g 500g |
| | Application(s): Sensitive stain for RNA and ribonuclease | |
| J60823 | Methylene Blue trihydrate [C.I. 52015, Basic Blue 9] [7220-79-3], C ₁₆ H ₁₈ ClN ₃ S·3H ₂ O, F.W. 373.90 (319.86anhy), Green crystalline Powder, Merck 14,6060, EINECS 200-515-2, RTECS SP5740000, BRN 3599847, MDL MFCD00150008, † ! H: H302, P: P264-P270-P301+P312-P330-P501a | 25g 100g 250g |
| | Application(s): Sensitive stain for RNA and ribonuclease | |
| | Methylenebutanedioic acid , see Itaconic acid, A15566, p. 262 Methylene chloride , see Dichloromethane, L13089, p. 186 | |
| J61773 | (R)-2-(Methylenemethoxy)propane-1,2-diol C ₅ H ₁₂ O ₃ , F.W. 120.15, Solid | Call |
| | Application(s): For synthesis of optically active products | |
| J62190 | (S)-2-(Methylenemethoxy)propane-1,2-diol C ₅ H ₁₂ O ₃ , F.W. 120.15, Solid | Call |
| | Application(s): For synthesis of optically active products | |
| | Methylenesuccinic acid , see Itaconic acid, A15566, p. 262 3-Methyl-2,5-furandione , see Citraconic anhydride, L05238, p. 164 | |

| Stock # | Description | Size |
|---------|--|--|
| L14282 | N-Methyl-D-glucamine, 99% \triangle ■ [D-1-Deoxy-1-(methylamino)glucitol, Meglumine] [6284-40-8], C ₇ H ₁₇ NO ₅ , F.W. 195.22, m.p. 128-131°, [α] _D ²⁰ -16.5° (c=2 in water), Merck 14,6078, EINECS 228-506-9, BRN 385906, MDL MFCD00004707, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 50g |
| | | 250g |
| |  | |
| | γ-Methyl L-glutamate, see L-Glutamic acid 5-methyl ester, B24859, p. 235 N-Methylglycine, see Sarcosine, A14594, p. 340 N-Methylglycine hydrochloride, see Sarcosine hydrochloride, B25536, p. 340 Methyl glycol, see 2-Methoxyethanol, A17459, p. 284 | |
| 42747 | Methyl Green, 0.1% w/v aq. soln. C ₂₇ H ₃₅ BrClN ₃ , F.W. 516.95, Liquid, MDL MFCD00036449, Note: Transition interval: pH 0.2 (yellow) to pH 1.8 (blue), † | 100ml |
| J61509 | Methyl Green, zinc chloride [C.I. 42590] [7114-03-6], C ₂₇ H ₃₅ Cl ₂ N ₃ ZnCl ₂ , F.W. 653.24, Powder, m.p. >300°, EINECS 230-415-4, BRN 3914106, MDL MFCD00151094 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 25g |
| | | 100g |
| | Application(s): DNA stain useful as tracking dye in acid buffers for electrophoresis. Binds selectively to AT-rich regions of native DNA. | |
| J60033 | Methylguanidine hydrochloride, 98% [TMG hydrochloride] [22661-87-6], C ₂ H ₇ N ₃ HCl, F.W. 109.56, Crystalline Powder, EINECS 245-147-3, RTECS MF3990000, MDL MFCD00012576 ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5g 25g |
| J65770 | 2'-O-Methylguanosine, 99% [2140-71-8], C ₁₁ H ₁₅ N ₅ O ₅ , F.W. 297.27, Powder ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g |
| J61636 | (R)-(-)-α-Methylhistamine dihydrochloride [75614-89-0], C ₈ H ₁₁ N ₃ ·2HCl, F.W. 198.10, Powder, MDL MFCD00083176 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 100mg |
| J60865 | α-Methyl-DL-histidine dihydrochloride, 99% [H-α-Me-DL-His-OH·2HCl] [32381-18-3], C ₈ H ₁₁ N ₃ O ₂ ·2HCl, F.W. 242.11, Powder, MDL MFCD00055953 | 250mg 500mg |
| A12575 | 1-Methylimidazole, 99% ■ [616-47-7], C ₄ H ₆ N ₂ , F.W. 82.11, m.p. -6°, b.p. 195-197°, f.p. 92°(197°F), d. 1.031, n _D ²⁰ 1.4970, Fieser 5,447 18,239, UN2922, EINECS 210-484-7, RTECS NI7000000, BRN 105197, MDL MFCD00005292, † ! H:H314-H302-H312, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a Useful base for peptide coupling, etc. See, e.g.: <i>J. Chem. Soc., Chem. Commun.</i> , 2223 (1995). A Undergoes lithiation at the 2-position. Reaction of the Li derivative with ketones followed by dehydration with acetic anhydride is a good route to 2-alkylideneimidazoles: <i>Synthesis</i> , 78 (1990). Likewise, reaction with benzonitrile gives the 2-benzoyl derivative, the carbonyl group of which undergoes Wittig methylenation: <i>Synth. Commun.</i> , 20, 321 (1990). Reacts with acid chlorides, including chloroformates, to give N-acylimidazolium salts, which are useful reagents for the acylation of, for example, amino acids: <i>Bull. Soc. Chim. Fr.</i> , 1021 (1973). | 100g 500g 2kg |
| | | |
| | 1-Methylimidazole-2-thiol , see 2-Mercapto-1-methylimidazole, A13094, p. 281 | |
| L03890 | 3-Methylindole, 99% ▲ [Skatole] [83-34-1], C ₈ H ₈ N, F.W. 131.18, m.p. 94-97°, b.p. 265-268°, f.p. 132°(269°F), Merck 14,8560, EINECS 201-471-7, RTECS NM0350000, BRN 111296, MDL MFCD00005627, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a N-Protection as the lithium carbamate permits lithiation at the 2-position: <i>Synth. Commun.</i> , 18, 1151 (1988): | 5g 25g 50g |
| | |  |
| |  | |
| | See also Indole, A14427 , p. 255 for a similar procedure. | |
| J64748 | 2'-O-Methylinosine, 99% [3881-21-8], C ₁₁ H ₁₂ N ₄ O ₅ , F.W. 282.25, Powder | 1g |
| J63667 | 5-(N-Methyl-N-isobutyl)amiloride, 98+% [MIA] [96861-65-3], C ₁₇ H ₁₈ ClN ₂ O, F.W. 299.76, Powder, MDL MFCD00078567 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): Inhibitor of Na ⁺ /H ⁺ antiporter. Possible antitumor agent | 5mg |



| Stock # | Description | Size |
|---------|---|---|
| H27029 | 1-Methylisoquinoline, 97% [1721-93-3], C ₁₀ H ₉ N, F.W. 143.19, m.p. 10-12°, b.p. 126-128°/16mm, f.p. >110°(230°F), d. 1.078, n _D ²⁰ 1.6140, EINECS 217-017-6, MDL MFCD00006902 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a |  1g 5g |
| J64389 | 7-Methyl lumazine [NSC 160394] [13401-38-2], C ₇ H ₈ N ₂ O ₂ , F.W. 178.15, Powder | 25mg |
| | Methylmaleic anhydride , see Citraconic anhydride, L05238, p. 164 6-(Methylmercapto)purine , see 6-(Methylthio)purine, L01836, p. 290 1-Methyl-7-methoxy-3,4-dihydro-Δ-carboline , see Harmaline, 98+%, J61699, p. 241 Methyl-(3-methylphenyl)carbamothioic acid O-2-naphthyl ester , see Tolnaftate, J61834, p. 371 | |
| A13593 | 2-Methyl-1,4-naphthoquinone, 98% ▲ [Menadione, Vitamin K3] [58-27-5], C ₁₁ H ₈ O ₂ , F.W. 172.18, m.p. 104-107°, Merck 14,5831, EINECS 200-372-6, RTECS QL9100000, BRN 1908453, MDL MFCD00001681, † ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a |  10g 50g 250g |
| | (S)-(+)-Methyl n-propyl carbinol , see (S)-(+)-2-Pentanol, L09314, p. 313 Methyl 5-n-propylthio-2-benzimidazolecarbamate , see Albendazole, H25925, p. 83 | |
| A10991 | Methyl octanoate, 99% [Methyl caprylate, Octanoic acid methyl ester] [111-11-5], CH ₃ (CH ₂) ₇ CO ₂ CH ₃ , F.W. 158.24, m.p. -40°, b.p. 193-194°, f.p. 72°(161°F), d. 0.875, n _D ²⁰ 1.4170, EINECS 203-835-0, RTECS RH0778000, BRN 1752270, MDL MFCD00009551, † | 50g 250g 1kg |
| 38695 | Methyl Orange, 0.1% w/v aq. soln. C ₁₄ H ₁₄ N ₃ NaO ₃ S, F.W. 327.34, Liquid, d. 0.987, EINECS 208-925-3, MDL MFCD00007502, Note: Transition interval: pH 3.2 (pink or red) to pH 4.4 (yellow), † | 500ml |
| A17604 | Methyl Orange [Acid Orange 52, C.I. 13025] [547-58-0], C ₁₄ H ₁₄ N ₃ NaO ₃ S, F.W. 327.34, m.p. >300°, Merck 14,6105, UN3143, EINECS 208-925-3, RTECS DB6327000, BRN 4732884, MDL MFCD00007502, † H:H301, P:P264-P270-P301+P310-P321-P405-P501a Acid-base indicator: pH 3.2 - 4.4. |  25g 100g 500g |
| L18881 | (R)-(-)-4-Methyl-2-pentanol, 99% [16404-54-9], C ₆ H ₁₄ O, F.W. 102.18, b.p. 130-131°, f.p. 41°(105°F), d. 0.802, n _D ²⁰ 1.4110, [α] _D ²⁰ -21° (neat), UN2053, BRN 1718992, MDL MFCD03093077 ! H:H226-H335, P:P262 |  250mg 1g |
| | Application(s): For synthesis of optically active products | |
| L18882 | (S)-(+)-4-Methyl-2-pentanol, 99% [14898-80-7], C ₆ H ₁₄ O, F.W. 102.18, b.p. 130-131°, f.p. 41°(105°F), d. 0.802, n _D ²⁰ 1.4110, [α] _D ²⁰ +21° (neat), UN2053, BRN 1718991, MDL MFCD03093078 ! H:H226-H335, P:P262 |  250mg 1g |
| | Application(s): For synthesis of optically active products | |
| H51685 | 1-(2-Methylphenyl)homopiperazine monohydrochloride, 98% [2-MPHP-HCl] C ₁₂ H ₁₈ N ₂ HCl, F.W. 226.75, m.p. 184-188°, MDL MFCD09953904, Note: Sold in collaboration with Tosoh Organic Chemical Co., Ltd. |  500mg |
| | Application(s): Useful intermediate for synthesis | |
| H51700 | 1-(3-Methylphenyl)homopiperazine monohydrochloride, 98% [3-MPHP-HCl] [934991-97-6], C ₁₂ H ₁₈ N ₂ HCl, F.W. 226.75, m.p. 136-140°, MDL MFCD08436120, Note: Sold in collaboration with Tosoh Organic Chemical Co., Ltd. |  500mg |
| | Application(s): Useful intermediate for synthesis | |
| H51750 | 1-(4-Methylphenyl)homopiperazine monohydrochloride, 98% [4-MPHP-HCl] C ₁₂ H ₁₈ N ₂ HCl, F.W. 226.75, m.p. 177-181°, MDL MFCD16172201, Note: Sold in collaboration with Tosoh Organic Chemical Co., Ltd. |  500mg |
| | Application(s): Useful intermediate for synthesis | |
| | (R)-(-)-1-Methylpropylamine , see (R)-(-)-2-Aminobutane, L03889, p. 92 (S)-(+)-1-Methylpropylamine , see (S)-(+)-2-Aminobutane, L10069, p. 92 1-Methyl-9H-pyrido-[3,4-b]indole-7-ol , see Harmol hydrochloride dihydrate, 98%, J63827, p. 241 Methyl 2-pyridyl ketone , see 2-Acetylpyridine, A12688, p. 74 Methyl 3-pyridyl ketone , see 3-Acetylpyridine, A14246, p. 74 N(1)-(4-Methyl-2-pyrimidyl)sulfanilamide , see Sulfamerazine, L04194, p. 355 | |

| Stock # | Description | Size | | | | | | | | | | | | |
|---------|--|-----------------------------------|------|------|------|-----|-----|---|------|------|------|------|------|--|
| 43894 | 1-Methyl-2-pyrrolidinone, ACS grade, 99.0+% [872-50-4], C ₅ H ₉ NO, F.W. 99.13, Liquid, m.p. -24°, b.p. 204°, f.p. 86°(187°F), d. 1.033, n _D ²⁰ 1.4705, Merck 14,6117, Fieser 1,696 2,281 9,316, EINECS 212-828-1, RTECS UY5790000, BRN 106420, MDL MFCD00003193, † Maximum level of impurities: Color (APHA) 50, H ₂ O 0.05%, Free amines (as CH ₃ NH ₂) 0.01%, Cl 1ppm | 500ml 1L 4L 4x1L 4x4L | | | | | | | | | | | | |
| | H: H360D-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | | | | | | | | | | | | | |
| 44063 | 1-Methyl-2-pyrrolidinone, Biograde, 99.5% ■ [872-50-4], C ₅ H ₉ NO, F.W. 99.13, Liquid, packaged under Argon, m.p. -24°, b.p. 204°, f.p. 86°(187°F), d. 1.033, n _D ²⁰ 1.4705, Merck 14,6117, Fieser 1,696 2,281 9,316, EINECS 212-828-1, RTECS UY5790000, BRN 106420, MDL MFCD00003193, Note: Amines (as dimethylamine) <10ppm, H ₂ O 200ppm, † | 1L 4L 4x4L | | | | | | | | | | | | |
| | H: H360D-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | | | | | | | | | | | | | |
| | UV absorption - 1cm cell vs H₂O | | | | | | | | | | | | | |
| | <table border="1"> <thead> <tr> <th>λ (nm)</th> <th>400</th> <th>350</th> <th>325</th> <th>300</th> <th>285</th> </tr> </thead> <tbody> <tr> <td>A</td> <td>0.01</td> <td>0.03</td> <td>0.01</td> <td>0.50</td> <td>1.00</td> </tr> </tbody> </table> | λ (nm) | 400 | 350 | 325 | 300 | 285 | A | 0.01 | 0.03 | 0.01 | 0.50 | 1.00 | |
| λ (nm) | 400 | 350 | 325 | 300 | 285 | | | | | | | | | |
| A | 0.01 | 0.03 | 0.01 | 0.50 | 1.00 | | | | | | | | | |
| | Application(s): Suitable for Biotech applications | | | | | | | | | | | | | |
| | 2-Methylquinoline , see Quinaldine, A13412, p. 333 | | | | | | | | | | | | | |
| 38698 | Methyl Red, 0.1% w/v solution in ethanol (CH ₃) ₂ NC ₆ H ₄ N=NC ₆ H ₄ CO ₂ H, F.W. 269.30, Liquid, UN1170, MDL MFCD00002425, Note: Transition interval: pH 4.2 (pink) to pH 6.2 (yellow), † | 100ml 500ml | | | | | | | | | | | | |
| | H: H224, P: P210-P241-P280-P240-P303+P361+P353-P501a | | | | | | | | | | | | | |
| A16690 | Methyl Red [C.I. 13020] [493-52-7], C ₁₅ H ₁₅ N ₃ O ₂ , F.W. 269.30, m.p. 179-182°, Merck 14,6119, EINECS 207-776-1, RTECS DG8960000, BRN 750102, MDL MFCD00002425, † Acid-base indicator: pH 4.2 - 6.2. | 100g 500g | | | | | | | | | | | | |
| | | | | | | | | | | | | | | |
| 36682 | Methyl Red, ACS [C.I. 13020] [493-52-7], C ₁₅ H ₁₅ N ₃ O ₂ , F.W. 269.30, Crystalline, m.p. 179-182°, Merck 14,6119, Solubility: Practically insoluble in water. Soluble in alcohol, acetic acid, EINECS 207-776-1, RTECS DG8960000, BRN 750102, MDL MFCD00002425, † Specifications: Melting point (range) 179-182°, Clarity of alcohol solution P.T.: Visual transition interval from pH 4.2 (pink) to 6.2 (yellow) | 25g 100g | | | | | | | | | | | | |
| | H: H351-EUH070, P: P281-P201-P202-P308+P313-P405-P501a | | | | | | | | | | | | | |
| | Application(s): pH indicator in pH range 4.2 - 6.3 | | | | | | | | | | | | | |
| 36668 | Methyl Red hydrochloride, ACS [2-[4-(Dimethylamino)phenyl]azobenzoic acid] [63451-28-5], C ₁₅ H ₁₅ N ₃ O ₂ ·HCl, F.W. 305.77, Crystalline, m.p. 175° dec., EINECS 264-190-9, MDL MFCD00012614 Specifications: Clarity of alcohol solution P.T.: Visual transition interval from pH 4.2 (pink) to 6.2 (yellow) | 25g 100g | | | | | | | | | | | | |
| | H: H351, P: P281-P201-P202-P308+P313-P405-P501a | | | | | | | | | | | | | |
| 36667 | Methyl Red sodium salt, ACS [2-[4-(Dimethylamino)phenyl]azobenzoic acid sodium salt] [845-10-3], C ₁₅ H ₁₄ N ₃ NaO ₂ , F.W. 291.29, Crystalline, EINECS 212-682-9, BRN 4065488, MDL MFCD00002426, † Specifications: Clarity of alcohol solution P.T.: Clarity of aqueous solution P.T.: Visual transition interval from pH 4.2 (pink) to 6.2 (yellow) | 25g 100g | | | | | | | | | | | | |
| | H: H302, P: P264-P270-P301+P312-P330-P501a | | | | | | | | | | | | | |
| | 5-Methylresorcinol , see 3,5-Dihydroxytoluene, L18567, p. 193 Methylrosaniline chloride , see Crystal Violet, B21932, p. 170 Methyl sulfoxide , see Dimethyl sulfoxide, 36480, p. 197 3-Methyl-2-thionimidazole-1-carboxylic acid ethyl ester , see Ethyl 3-methyl-2-thionimidazole-1-carboxylate, L08218, p. 217 | | | | | | | | | | | | | |
| L01836 | 6-(Methylthio)purine, 97% [6-(Methylmercapto)purine] [50-66-8], C ₅ H ₆ N ₄ S, F.W. 166.20, m.p. 220-223°, EINECS 200-057-3, RTECS UO8976000, BRN 7695, MDL MFCD00005576 | 1g 5g | | | | | | | | | | | | |
| | | | | | | | | | | | | | | |
| A17982 | 6-Methyl-2-thiouracil, 98% [4-Hydroxy-2-mercapto-6-methylpyrimidine] [56-04-2], C ₅ H ₆ N ₂ OS, F.W. 142.18, m.p. ca 329° dec., Merck 14,6128, EINECS 200-252-3, RTECS YR0875000, BRN 115648, MDL MFCD00006040, † | 50g 250g 1kg | | | | | | | | | | | | |
| | H: H351-H302, P: P281-P264-P301+P312-P308+P313-P405-P501a | | | | | | | | | | | | | |
| | | | | | | | | | | | | | | |
| | 6-Methyl-1,2,4-triazine-3,5(2H,4H)-dione , see 6-Azathymine, L06762, p. 114 5-Methyluracil , see Thymine, A15879, p. 369 | | | | | | | | | | | | | |


| Stock # | Description | Size | |
|---------|---|--|-----------------------|
| B24191 | 6-Methyluracil, 97% [2,4-Dihydroxy-6-methylpyrimidine] [626-48-2], C ₅ H ₆ N ₂ O ₂ , F.W. 126.12, m.p. 317-320°, Merck 14,6133, EINECS 210-949-4, RTECS YR0700000, BRN 115647, MDL MFCD00006028, † |  | 100g 500g 2.5kg |
| | † H:361, P:P281-P201-P202-P308+P313-P405-P501a | | |
| J64897 | 2'-O-Methyluridine, 99% [2140-76-3], C ₁₀ H ₁₄ N ₂ O ₆ , F.W. 258.23, Powder | 1g | |
| | 8-Methyl-N-vanillyl-trans-6-nonenamide , see Capsaicin, J62865, p. 146 Methyl Violet 10B , see Crystal Violet, B21932, p. 170 | | |
| J61545 | Metoclopramide hydrochloride monohydrate [54143-57-6], C ₁₁ H ₂₂ ClN ₃ O ₂ ·HCl·H ₂ O, F.W. 354.28 (336.26anhy), Crystalline solid, Merck 14,6143 ! H:302, P:P264-P270-P301+P312-P330-P501 | 10g 25g 100g | |
| | Application(s): 5-HT ₃ serotonin antagonist; D ₂ dopamine antagonist | | |
| J61920 | Metoprolol tartrate, 98+% [(±)-1-(Isopropylamino)-3-[4-(β-methoxyethyl)phenoxy]-2-propanol (+)-tartrate salt] [56392-17-7], (C ₁₅ H ₂₅ NO ₃) ₂ ·C ₈ H ₈ O ₆ , F.W. 684.82, Powder, m.p. 120°, Merck 14,6151, EINECS 260-148-9, RTECS UB7450100, MDL MFCD00056257 | 5g 25g | |
| | Application(s): A β-adrenergic blocker Mevacor , see Lovastatin, H52792, p. 273 | | |
| J61357 | Mevastatin, 98% [73573-88-3], C ₂₃ H ₃₄ O ₅ , F.W. 390.52, Powder, Merck 14,6164, BRN 1269441, MDL MFCD05662341 | 5mg 10mg 25mg | |
| | Application(s): Inhibitor of HMG-CoA reductase. Induces apoptosis | | |
| | Mexocine , see Demeclocycline hydrochloride, J63102, p. 176 | | |
| J62440 | Mezerein, Daphne mezereum [34807-41-5], C ₃₈ H ₃₈ O ₁₀ , F.W. 654.71, 34807-41-5, RTECS HB5425500, BRN 1675867, MDL MFCD00135953 ! H:315, P:P280-P264-P302+P352-P321-P362-P332+P313 | 1mg | |
| | Application(s): Protein kinase C (PKC) activator. Inflammatory tumor promoter o-3M3FBS , see 2,4,6-Trimethyl-N-[2-(trifluoromethyl)phenyl]benzenesulfonamide, J65391, p. 378 m-3M3FBS , see 2,4,6-Trimethyl-N-[3-(trifluoromethyl)phenyl]benzenesulfonamide, J65999, p. 378 | | |
| J63250 | MG 132 [Z-Leu-Leu-Aldehyde] [133407-82-6], C ₂₆ H ₄₁ N ₃ O ₅ , F.W. 475.63, Crystalline solid, MDL MFCD00674886 | 1mg 5mg 10mg | |
| | Application(s): Inhibitor of calpain proteases MG-341 , see Bortezomib, 99%, J60378, p. 134 MIA , see 5-(N-Methyl-N-isobutyl)amiloride, 98+%, J63667, p. 288 | | |
| J61570 | Mianserin hydrochloride [21535-47-7], C ₁₈ H ₂₀ N ₂ ·HCl, F.W. 300.83, Powder, Merck 14,6172, EINECS 244-426-7, RTECS HP8780000, MDL MFCD00055072 ! H:302, P:P264-P270-P301+P312-P330-P501 | 100mg | |
| J60872 | Miconazole, 99% ▲ [22916-47-8], C ₁₁ H ₁₄ Cl ₂ N ₂ O, F.W. 416.13, Powder, m.p. 170°, Merck 14,6178, EINECS 245-324-5, RTECS NI4770000 ! H:302-H317, P:P261-P280-P302+P352-P321-P301+P312-P501a | 1g 5g 25g | |
| | Application(s): Inhibits cytochrome P450-dependent 14-α-demethylase | | |
| J60796 | (±)-Miconazole nitrate, 98+% [22832-87-7], C ₁₁ H ₁₄ Cl ₂ N ₂ O·HNO ₃ , F.W. 479.15, Powder, m.p. 170-185°, Merck 14,6178, EINECS 245-256-6, RTECS NI4771000, MDL MFCD00058161 ! H:302-H317, P:P261-P280-P302+P352-P321-P301+P312-P501 | 5g 25g | |
| | Application(s): Inhibits cytochrome P450-dependent 14α-demethylase | | |
| J62917 | Midostaurin [PKC412, 4'-N-Benzoylstauosporine] [120685-11-2], C ₃₅ H ₃₀ N ₂ O ₄ , F.W. 570.64, Powder, m.p. 235-260°, Merck 14,6185, MDL MFCD12828879 | 1mg 5mg | |
| | Application(s): Inhibits a variety of serine/threonine and tyrosine kinases including PKC | | |
| J64947 | MIF Antagonist, ISO-1 ▲ [(S,R)-3-(4-Hydroxyphenyl)-4,5-dihydro-5-isoxazole acetic acid, methyl ester, Macrophage Migration Inhibitory Factor Antagonist] [478336-92-4], C ₁₂ H ₁₃ NO ₄ , F.W. 235.24, Solid | 5mg 25mg | |
| | MIF-I , see Melanocyte-Stimulating Hormone-Release Inhibiting Factor, synthetic, J60045, p. 279 Milrila , see Milrinone, 98+%, J62659, p. 292 | | |






| Stock # | Description | Size |
|---------------|---|-----------------------|
| J62659 | Milrinone, 98+% [Corotrope, Milirila] [78415-72-2], C ₁₆ H ₁₅ N ₃ O, F.W. 211.22, Powder, m.p. 264°, Merck 14,6197, UN2811, EINECS 278-903-6, RTECS DW1762000, MDL MFCD00133539  | 10mg 50mg 100mg |
| | Application(s): Potent cAMP-specific phosphodiesterase inhibitor | |
| J62592 | Mineral oil, high purity [8042-47-5], Oily liquid, EINECS 232-455-8, RTECS PY8047000, MDL MFCD00131611, t | 100ml 500ml |
| | Application(s): Suitable for PCR applications | |
| J61803 | Minoxidil [38304-91-5], C ₉ H ₁₁ N ₃ O, F.W. 209.25, Crystalline powder, m.p. 248-265°, Merck 14,6203, EINECS 253-874-2, RTECS UV8200000, MDL MFCD00063409  | 1g 5g 25g |
| | Application(s): Stimulates ATP-activated potassium channels | |
| J65156 | MIRA-1 [1-[(1-Oxopropoxy)methyl]-1H-pyrrole 2,5-dione] [72835-26-8], C ₈ H ₉ NO ₄ , F.W. 183.16, Powder | 10mg |
| J63193 | Mitomycin C [50-07-7], C ₁₅ H ₁₉ N ₃ O ₅ , F.W. 334.33, Powder, m.p. 360°, Merck 14,6215, UN2811, EINECS 200-008-6, RTECS CN0700000, BRN 7231816, MDL MFCD00078109, t  | 1mg 5mg 10mg |
| | Application(s): Antineoplastic agent which inhibits DNA synthesis and induces apoptosis | |
| | MK-0457 , see Tozasertib, 99+%, J63232, p. 372 MK-217 , see Alendronate sodium trihydrate, 97%, J61397, p. 88 MK-231 , see Sulindac, J61772, p. 356 (+)-MK 801 maleate , see Dizocilpine maleate, 99+%, J63917, p. 200 MK-933 , see Ivermectin, J62777, p. 262 MLN518 , see Tandutinib, 99%, J62004, p. 358 MMLV RT , see Reverse Transcriptase, murine, Moloney Murine Leukemia Virus, J60167, p. 336 | |
| J65638 | MMP Inhibitor II [N-Hydroxy-1,3-bis(4-methoxyphenylsulfonyl)-5,5-dimethylhexahydropyrimidine-2-carboxamide] [203915-59-7], C ₂₁ H ₂₇ N ₅ O ₈ S ₂ , F.W. 513.58, Solid | 5mg 10mg |
| J65783 | MMP-3 Inhibitor ▲ [N-Hydroxy-2(R)-[(4-methoxyphenyl)sulfonyl]-[benzylamino]-4-methylpentanamide] C ₂₀ H ₂₆ N ₂ O ₅ S, F.W. 406.50, Solid | 5mg |
| J64823 | MMP-3 Inhibitor III ▲ [(S)-3-Phenyl-2-(3-(5-thioxo-4,5-dihydro-1,3,4-thiadiazol-2-yl)ureido)propanoic acid] C ₁₂ H ₁₂ N ₄ O ₅ S ₂ , F.W. 324.40, Solid | 2mg |
| J64368 | MMP-3 Inhibitor VIII ▲ [(R)-2-(N-benzyl-4-methoxyphenylsulfonamido)-N-hydroxy-4-methylpentanamide] [208663-26-7], C ₂₀ H ₂₆ N ₂ O ₅ S, F.W. 406.49, Solid  | 5mg |
| J64304 | MMP-9 Inhibitor I ▲ [2-(N-Benzyl-4-methoxyphenylsulfonamido)-5-((diethylamino)methyl)-N-hydroxy-3-methylbenzamide] [1177749-58-4], C ₂₇ H ₃₅ N ₅ O ₅ S, F.W. 511.63, Solid  | 5mg |
| J65620 | MMP-2/MMP-3 Inhibitor [N-[[[4,5-Dihydro-5-thioxo-1,3,4-thiadiazol-2-yl)amino]carbo nyl]-L-phenylalanine methyl ester] C ₁₅ H ₁₄ N ₄ O ₅ S ₂ , F.W. 338.40, Solid | 5mg |
| J64580 | MMP-9/MMP-13 Inhibitor I ▲ [N-Hydroxy-1-(4-methoxyphenyl)sulfonyl-4-(4-biphenylcarbonyl)piperazine-2-carboxamide] [204140-01-2], C ₂₈ H ₂₈ N ₆ O ₆ S, F.W. 459.55, Solid  | 1mg |
| J60690 | MNE buffer, pH 6.5 Liquid, Note: 20mM MES, 150mM NaCl, 5mM EDTA, pH 6.5 | 250ml 500ml |
| | MOBIC , see Meloxicam, J60635, p. 280 | |
| J61416 | MOBS, 0.2M buffer soln., pH 7.0 [4-(4-Morpholinyl)butanesulfonic acid] [115724-21-5], Liquid  | 100ml 250ml |















| Stock # | Description | Size |
|--|---|--------------------|
| J63519 | MOBS, 0.2M buffer soln., pH 7.5 [4-(4-Morpholinyl)butanesulfonic acid] [115724-21-5], Liquid | 100ml |
| | | 250ml |
| ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | | |
| J63594 | MOBS, 0.2M buffer soln., pH 8.0 [4-(4-Morpholinyl)butanesulfonic acid] [115724-21-5], Liquid | 100ml |
| | | 250ml |
| ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | | |
| J62203 | MOBS, 0.2M buffer soln., pH 8.5 [4-(4-Morpholinyl)butanesulfonic acid] [115724-21-5], Liquid | 100ml |
| | | 250ml |
| ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | | |
| L05383 | Molecular sieves, 3A, 0.4-0.8mm (0.02-0.03in) beads ■ [308080-99-1], MDL MFCD00131613 Molecular sieve of 3 Angstrom pore size useful where dynamic mass transfer needs to be maximized at the expense of physical strength and pressure drop. | 250g |
| | | 1kg |
| L05335 | Molecular sieves, 3A, 1-2mm (0.04-0.08in) beads ■ [308080-99-1], MDL MFCD00131613 Molecular sieve of 3 Angstrom pore size of particular use in the drying of liquids, especially methanol and ethanol. A detailed comparison has been made of the drying of various alcohols, using 3A or 4A powder or beads. In general, the powder form is more effective for ethanol, 2-butanol, t-butanol and ethylene glycol, but beads are better for methanol. In all cases studied, 3A sieves were more effective than 4A: <i>J. Org. Chem.</i> , 48 , 2420 (1983). Superior drying agent for acetonitrile: <i>J. Org. Chem.</i> , 49 , 3852 (1984). | 250g |
| | | 1kg |
| | | 5kg |
| 87957 | Molecular sieves, 3A, 1-2mm (0.04-0.08in) dia. pellets ■ [308080-99-1], Pellets, MDL MFCD00147627 | 1kg 5kg |
| 33530 | Molecular sieves, 3A, 3-4mm (0.12-0.16in) dia. pellets ■ [308080-99-1], Pellets, MDL MFCD00147627 | 1kg 5kg |
| L05359 | Molecular sieves, 3A, 3-5mm (0.12-0.20in) beads ■ [308080-99-1], MDL MFCD00131613 Molecular sieve of 3 Angstrom pore size suitable for the drying of small molecular gas streams or where it is essential to exclude large molecules from the micropores to prevent undesirable reactions. | 250g |
| | | 1kg |
| B21165 | Molecular sieves, 3A, powder ■ [308080-99-1], MDL MFCD00147627 | 250g |
| | | 1kg 5kg |
| ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | | |
| 32256 | Molecular sieves, 4A with indicator, -8+12 (ca 2mm) beads [70955-01-0], -8+12 Beads, MDL MFCD00147627 | 250g 1kg 5kg |
| L05512 | Molecular sieves, 4A, 0.4-0.8mm (0.02-0.03in) beads ■ [70955-01-0], MDL MFCD00131613 Molecular sieve of 4 Angstrom pore size useful where dynamic mass transfer needs to be maximized at the expense of physical strength and pressure drop. | 250g |
| | | 1kg |
| 87956 | Molecular sieves, 4A, 1-2mm (0.04-0.08in) dia. pellets ■ [70955-01-0], Pellets, MDL MFCD00131613 | 1kg 5kg |
| 88120 | Molecular sieves, 4A, 3-4mm (0.12-0.16in) dia. pellets ■ [70955-01-0], Pellets, MDL MFCD00131613 | 1kg 5kg |
| L05454 | Molecular sieves, 4A, 1-2mm (0.04-0.08in) beads ■ [70955-01-0], MDL MFCD00131613 Molecular sieve of 4 Angstrom pore size useful in general liquid and gas drying applications. | 250g |
| | | 1kg |
| | | 5kg |
| L05466 | Molecular sieves, 4A, 3-5mm (0.12-0.20in) beads ■ [70955-01-0], MDL MFCD00131613 Molecular sieve of 4 Angstrom pore size useful in general gas drying applications. | 250g |
| | | 1kg |
| | | 5kg |
| A11535 | Molecular sieves, 4A, powder ■ [70955-01-0], MDL MFCD00131613 | 250g |
| | | 1kg |
| | | 5kg |
| ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Unformed molecular sieve of 4 Angstrom pore size useful in homogeneous drying applications. | | |
| 87955 | Molecular sieves, 5A, 1-2mm (0.04-0.08in) dia. pellets ■ [69912-79-4], Pellets, MDL MFCD00147627 | 1kg |
| | | 5kg |


| Stock # | Description | Size |
|---------|---|---------------------|
| 33551 | Molecular sieves, 5A, 3-4mm (0.12-0.16in) dia. pellets ■ [69912-79-4], Pellets, MDL MFCD00147627 | 1kg 5kg |
| L05722 | Molecular sieves, 5A, 3-5mm (0.12-0.20in) beads ■ [69912-79-4], MDL MFCD00131613 | 250g 1kg |
| B21109 | Molecular sieves, 13X, 1.6-2.5mm (0.063-0.098in) beads ■ [63231-69-6], MDL MFCD00131613 Molecular sieve of 8.5 Angstrom pore size for removal of carbon dioxide, water and trace organic constituents in air pre-purification, LPG drying and sweetening, and various hydrocarbon separation processes. | 250g 1kg 5kg |
| 87954 | Molecular sieves, 13X, 1-2mm (0.04-0.08in) dia. pellets ■ [63231-69-6], 1/16in Pellets, MDL MFCD00131613 | 1kg 5kg |
| 33550 | Molecular sieves, 13X, 3-4mm (0.12-0.16in) dia. pellets ■ [63231-69-6], 1/8in Pellets, MDL MFCD00131613 | 1kg 5kg |
| L06085 | Molecular sieves, 13X, 3-5mm (0.12-0.20in) beads ■ [63231-69-6], MDL MFCD00131613 | 250g 1kg 5kg |
| A10378 | Molecular sieves, 13X, powder ■ [63231-69-6], MDL MFCD00131613 Unformed molecular sieve of 8.5 Angstrom pore size useful in homogeneous separation processes. | 250g 1kg 5kg |
| J62389 | Molluscan Cardioexcitatory Neuropeptide <i>[Phe-Met-Arg-Phe-NH₂, FMRF amide]</i> [64190-70-1], C ₂₈ H ₄₂ N ₆ O ₅ S, F.W. 598.76, Powder, MDL MFCD00076625 Application(s): A neuropeptide involved in neuronal nitric oxide production | 10mg |
| J61669 | Monensin sodium salt, 90-95.5% <i>[Coban[®] 3M, Rumensin]</i> [22373-78-0], C ₂₈ H ₄₆ NaO ₁₁ , F.W. 692.86, Powder, m.p. 267-269°, Merck 14,6246, UN3462, EINECS 244-941-7, RTECS JH2830000, BRN 4122200, MDL MFCD00077826  H:H300, P:P264-P270-P301+P310-P321-P405-P501a Application(s): Antibiotic that functions as a sodium ionophore. Induces apoptosis in HL-60 cells | 1g 5g |
| | Monochloroacetic acid , see Chloroacetic acid, A11482, p. 154 Monoethylene glycol , see Ethylene glycol, A11591, p. 216 Monosodium glutamate , see L-Glutamic acid monosodium salt, J63424, p. 234 Monosodium orthophosphate , see Sodium dihydrogen phosphate monohydrate, 11591, p. 345 | |
| A12914 | MOPS, 99% <i>[4-Morpholinepropanesulfonic acid, 3-(4-Morpholinyl)propanesulfonic acid]</i> [1132-61-2], C ₇ H ₁₃ NO ₃ S, F.W. 209.27, m.p. 277-280° dec., f.p. 110° (230°F), Merck 14,6265, EINECS 214-478-5, RTECS QE9104530, BRN 1106776, MDL MFCD00006183, †  ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Biological buffer, pK _a = 7.2 at 20°C: <i>Biochemistry</i> , 5, 467 (1966). Utilized to promote a mimetic of the transketolase reaction: <i>Eur. J. Org. Chem.</i> , 1121 (2006). Application(s): Good's buffer | 25g 100g 500g |
| J62477 | MOPS, 0.5M buffer soln., pH 5.5 [1132-61-2], Liquid, † ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | 100ml 250ml |
| J62476 | MOPS, 0.5M buffer soln., pH 6.0 [1132-61-2], Liquid, † ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | 100ml 250ml |
| J63369 | MOPS, 0.5M buffer soln., pH 6.5 [1132-61-2], Liquid, † ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | 100ml 250ml |
| J60328 | MOPS, 0.5M buffer soln., pH 7.0 [1132-61-2], Liquid, † ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | 100ml 250ml |
| J62839 | MOPS, 0.5M buffer soln., pH 7.5 [1132-61-2], Liquid, † ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | 100ml 250ml |
| J61236 | MOPS, 0.5M buffer soln., pH 8.0 [1132-61-2], Liquid, † ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | 100ml 250ml |

| Stock # | Description | Size |
|---|---|-------|
| J62368 | MOPS, 0.5M buffer soln., pH 8.5 [1132-61-2], Liquid, † ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | 100ml |
| | | 250ml |
| J60922 | MOPS, 0.5M buffer soln., pH 9.0 [1132-61-2], Liquid, † ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | 100ml |
| | | 250ml |
| J62261 | MOPS, 1.0M buffer soln., pH 5.5 [1132-61-2], Liquid, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250ml |
| | | 500ml |
| J62840 | MOPS, 1.0M buffer soln., pH 6.0 [1132-61-2], Liquid, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250ml |
| | | 500ml |
| J61797 | MOPS, 1.0M buffer soln., pH 6.5 [1132-61-2], Liquid, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250ml |
| | | 500ml |
| J61821 | MOPS, 1.0M buffer soln., pH 7.0 [1132-61-2], Liquid, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250ml |
| | | 500ml |
| J61843 | MOPS, 1.0M buffer soln., pH 7.5 [1132-61-2], Liquid, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250ml |
| | | 500ml |
| J61958 | MOPS, 1.0M buffer soln., pH 8.0 [1132-61-2], Liquid, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250ml |
| | | 500ml |
| J62682 | MOPS, 1.0M buffer soln., pH 8.5 [1132-61-2], Liquid, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250ml |
| | | 500ml |
| J60097 | MOPS, 1.0M buffer soln., pH 9.0 [1132-61-2], Liquid, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250ml |
| | | 500ml |
| J63986 | MOPS-buffered saline (5X), pH 7.0 [1132-61-2], Liquid, Note: 125mM MOPS and 750mM NaCl, pH 7.0., † | 250ml |
| | | 500ml |
| J60490 | MOPS-buffered saline (5X), pH 7.2 [1132-61-2], Liquid, Note: 125mM MOPS and 750mM NaCl, pH 7.2, † | 250ml |
| | | 500ml |
| J61616 | MOPS-buffered saline (5X), pH 7.5 [1132-61-2], Liquid, Note: 125mM MOPS and 750mM NaCl 750 mM, pH 7.5, † | 250ml |
| | | 500ml |
| J60184 | MOPS-EDTA-sodium acetate buffer (MESA) Liquid, Note: This buffer contains: 0.4M MOPS, 0.1M sodium acetate and 10mM EDTA at pH 7.0., † | 500ml |
| | | 1L |
| J60993 | MOPSO, 0.2M buffer soln., pH 6.0 [79803-73-9], Liquid | 100ml |
| | | 250ml |
| J61833 | MOPSO, 0.2M buffer soln., pH 6.5 [79803-73-9], Liquid | 100ml |
| | | 250ml |
| J61469 | MOPSO, 0.2M buffer soln., pH 7.0 [79803-73-9], Liquid | 100ml |
| | | 250ml |
| J60464 | MOPSO, 0.2M buffer soln., pH 7.5 [79803-73-9], Liquid | 100ml |
| | | 250ml |
| J62847 | MOPS-SDS running buffer (20X) Liquid, Note: This buffer contains: 1M MOPS, 1M Tris base, 2% SDS and 20mM EDTA at pH 7.7. | 500ml |
| | | 1L |
| Mordant Black 3 , see Eriochrome® Blue Black B ®Ciba Specialty Chemicals Corp., J63396, p. 210 | | |







| Stock # | Description | Size |
|--|---|----------------------|
| J61987 | Morphiceptin acetate [<i>β</i> -Casomorphin (1-4) amide (bovine)] [87777-29-5], C ₂₈ H ₃₅ N ₅ O ₅ , F.W. 521.61, Powder | 25mg 100mg |
| Application(s): Agonist for μ-opioid receptors | | |
| 4-Morpholineethanesulfonic acid monohydrate, see MES monohydrate, A16104, p. 283 | | |
| 4-Morpholinepropanesulfonic acid, see MOPS, A12914, p. 294 | | |
| 2-(4-Morpholinyl)ethanesulfonic acid monohydrate, see MES monohydrate, A16104, p. 283 | | |
| 3-(4-Morpholinyl)propanesulfonic acid, see MOPS, A12914, p. 294 | | |
| 2-MPHP HCl, see 1-(2-Methylphenyl)homopiperazine monohydrochloride, H51685, p. 289 | | |
| 3-MPHP HCl, see 1-(3-Methylphenyl)homopiperazine monohydrochloride, H51700, p. 289 | | |
| 4-MPHP HCl, see 1-(4-Methylphenyl)homopiperazine monohydrochloride, H51750, p. 289 | | |
| MRITC, see 5(6)-Tetramethylrhodamine isothiocyanate, J62258, p. 365 | | |
| MTT, see Thiazolyl Blue tetrazolium bromide, L11939, p. 366 | | |
| J63859 | Mucin, bovine submaxillary gland [84195-52-8], Powder, 400-4000 kDa, EINECS 282-357-4, MDL MFCD00131629 | 100mg 500mg |
| Application(s): Neuraminidase substrate | | |
| J65685 | Mu-Phe-HomoPhe-fluoromethyl ketone [<i>Mu-Phe-HomoPhe-FMK, N-Morpholineurea-phenylalanyl-homophenylalanylfluoromethyl ketone</i>] C ₂₅ H ₃₀ FN ₃ O ₄ , F.W. 455.52, Powder, MDL MFCD03452972 | 5mg 10mg |
| Muramidase, see Lysozyme, chicken egg white, J60701, p. 274 | | |
| Muramyl dipeptide, see Adjuvant Peptide, J62385, p. 80 | | |
| A17540 | Murexide [<i>Ammonium purpurate</i>] [3051-09-0], C ₈ H ₈ N ₄ O ₆ , F.W. 284.19, m.p. >300°, Merck 14,6306, EINECS 221-266-6, BRN 3582175, MDL MFCD00012777, † Indicator for complexometric titration. | 10g 50g 250g |
| Application(s): Indicator for calcium determinations | | |
| Muritic acid, see Hydrochloric acid, 33257, p. 247 | | |
| J61720 | Muscimol, 99+% [2763-96-4], C ₈ H ₈ N ₂ O ₂ , F.W. 114.10, Powder, Merck 14,6312, UN1544, EINECS 220-430-4, RTECS NY3325000, BRN 1618960, MDL MFCD00057894, †  H:H300, P:P264-P270-P301+P310-P321-P405-P501a | 5mg 10mg 50mg |
| Application(s): Selective GABAa agonist | | |
| Musculamine, see Spermine, L19562, p. 351 | | |
| J61905 | Mycophenolic acid, 99+% [24280-93-1], C ₁₇ H ₂₀ O ₅ , F.W. 320.34, Powder, m.p. 139-141°, Merck 14,6327, EINECS 246-119-3, RTECS MP8050000, BRN 1295848, MDL MFCD00036814 ! H:H302, P:P264-P270-P301+P312-P330-P501a | 1g 5g 10g |
| Application(s): Immunosuppressant agent. Blocks inosine monophosphate dehydrogenase in the guanosine monophosphate pathway | | |
| Mycosporan, see Bifonazole, 99%, J63253, p. 125 | | |
| Myoinositol, see myo-Inositol, A13586, p. 257 | | |
| J60450 | Myricetin, 98% [<i>Cannabiscetin, Delphidenolon 1575</i>] [529-44-2], C ₁₅ H ₁₀ O ₆ , F.W. 318.24, Crystalline solid, m.p. >300°, Merck 14,6332, EINECS 208-463-2, BRN 332331, MDL MFCD00006827 | 10mg 25mg 50mg |
| Application(s): Common flavanol in plants that inhibits phenolsulfotransferase. Strongly inhibits yeast α-glucosidase | | |
| Myristic acid, see Tetradecanoic acid, A12067, p. 362 | | |
| Myristyltrimethylammonium bromide, see (1-Tetradecyl)trimethylammonium bromide, L10294, p. 362 | | |
| Myristyltrimethylammonium chloride hydrate, see Benzylidimethyl-n-tetradecylammonium chloride hydrate, 98%, J63465, p. 122 | | |
| J63072 | Nabumetone [4-(6-Methoxy-2-naphthyl)-2-butanone] [42924-53-8], C ₁₈ H ₁₆ O ₂ , F.W. 228.29, Crystalline powder, m.p. 76-78°, Merck 14,6343, RTECS EL9085000, MDL MFCD00079518 | 5g 25g |
| Application(s): Anti-inflammatory, anti-bacterial. A non-steroidal anti-inflammatory drug (NSAID) that inhibits cyclooxygenase | | |
| β-NAD, see β-Nicotinamide adenine dinucleotide, 98+%, J62337, p. 301 | | |
| β-NADH disodium salt trihydrate, see β-Nicotinamide adenine dinucleotide reduced disodium salt trihydrate, 98%, J61461, p. 302 | | |
| β-NADH disodium salt, see β-Nicotinamide adenine dinucleotide reduced disodium salt, 98%, J61638, p. 302 | | |
| NAD oxidoreductase, see Lactate dehydrogenase, rabbit muscle, J63220, p. 265 | | |
| β-NADP monosodium salt, see β-Nicotinamide adenine dinucleotide phosphate sodium salt, 44126, p. 301 | | |
| β-NADP disodium salt, see β-Nicotinamide adenine dinucleotide phosphate disodium salt, 98+%, J62556, p. 301 | | |
| β-NADPH tetrasodium salt, see β-Nicotinamide adenine dinucleotide phosphate reduced tetrasodium salt, 98+%, J62089, p. 302 | | |
| β-NADPH tetrasodium salt tetrahydrate, see β-Nicotinamide adenine dinucleotide phosphate reduced tetrasodium salt tetrahydrate, 98+%, J60387, p. 301 | | |


| Stock # | Description | Size |
|--|--|---|
| J60311 | Naftopidil, 98+% [KT-611, 1-[4-(2-Methoxyphenyl)piperazinyl]-3-(1-naphthoxy)propan-2-ol] [57149-07-2], C ₂₆ H ₂₈ N ₂ O ₃ , F.W. 392.49, Powder, m.p. 127°, Merck 14,6356, RTECS TL9336500, MDL MFCD00242741 | 5g |
| Application(s): α1-adrenoceptor antagonist; antihypertensive | | |
| J63249 | Naftopidil hydrochloride, 98+% [KT-611 hydrochloride, 4-(2-Methoxyphenyl)-α-[(1-naphthalenyloxy)methyl]-1-piperazineethanol hydrochloride] C ₂₆ H ₂₈ N ₂ O ₃ ·HCl, F.W. 428.96, Powder, m.p. 116-118°, RTECS TL9336500 | 10mg 50mg |
| Application(s): An α1-adrenoceptor antagonist and antihypertensive | | |
| B25096 | Nalidixic acid, 99% [1,4-Dihydro-1-ethyl-7-methyl-4-oxo-1,8-naphthyridine-3-carboxylic acid, 1-Ethyl-1,4-dihydro-7-methyl-4-oxo-1,8-naphthyridine-3-carboxylic acid] [389-08-2], C ₁₉ H ₁₈ N ₂ O ₃ , F.W. 232.24, m.p. 228-230°, Merck 14,6359, EINECS 206-864-7, RTECS QN2885000, BRN 750515, MDL MFCD00006884 | 5g 25g 100g |
| ! H: H302, P: P264-P270-P301+P312-P330-P501a | |  |
| J63550 | Nalidixic acid sodium salt [3374-05-8], C ₁₉ H ₁₇ N ₂ NaO ₃ , F.W. 254.22, Powder, m.p. >280°, EINECS 222-159-7, RTECS QN2885000, BRN 3580062, MDL MFCD00064376 | 5g 25g 100g |
| ! H: H334-H317, P: P285-P261-P280-P302+P352-P321-P501a | | |
| Application(s): Inhibitor of bacterial DNA gyrase. An antibacterial agent | | |
| J60013 | Naloxone hydrochloride, 98% [357-08-4], C ₁₉ H ₂₁ NO ₂ ·HCl, F.W. 363.84, Crystalline powder, m.p. 200-205°, Merck 14,6362, EINECS 206-611-0, RTECS QD2275000, MDL MFCD00069322 | 100mg 500mg 1g |
| ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | | |
| Application(s): A specific opiate antagonist. Blocks the action of sigma-agonists at opioid sites | | |
| J60590 | Naltrexone hydrochloride ▲ [16676-29-2], C ₁₉ H ₂₁ NO ₂ ·HCl, F.W. 377.86, Powder, Merck 14,6363, EINECS 240-723-0, RTECS QD2160000, BRN 3580333, MDL MFCD00069324 | 250mg 1g |
| ! H: H302, P: P264-P270-P301+P312-P330-P501a | | |
| Application(s): A congener of naloxone and also an opioid antagonist | | |
| NANA , see N-(-)-Acetylneuraminic acid, L13950, p. 74 | | |
| Naphazoline nitrate , see 2-(1-Naphthylmethyl)-2-imidazoline nitrate, L12617, p. 298 | | |
| Naphthalene Black 10B , see Amido Black 10B, A11374, p. 91 | | |
| Naphthalene-1-carboxylic acid , see 1-Naphthoic acid, A10273, p. 297 | | |
| Naphthalene-2-carboxylic acid , see 2-Naphthoic acid, L05102, p. 297 | | |
| 2,3-Naphthalenediamine , see 2,3-Diaminonaphthalene, A12993, p. 183 | | |
| 1,3-Naphthalenediol , see 1,3-Dihydroxynaphthalene, A17739, p. 192 | | |
| 1-Naphthalenol , see 1-Naphthol, A11862, p. 298 | | |
| A18542 | α-Naphthoflavone, 97% [7,8-Benzoflavone] [604-59-1], C ₁₉ H ₁₂ O ₂ , F.W. 272.31, m.p. 156-159°, EINECS 210-071-1, RTECS QL6250000, BRN 210862, MDL MFCD00004985, t | 5g 25g |
| Application(s): An aryl hydrocarbon receptor antagonist | |  |
| A18543 | β-Naphthoflavone, 98+% [5,6-Benzoflavone] [6051-87-2], C ₁₉ H ₁₂ O ₂ , F.W. 272.31, m.p. 162-166°, EINECS 227-958-4, RTECS QL6200000, BRN 18991, MDL MFCD00004986 | 1g 5g |
| Application(s): Inhibitor of aryl hydrocarbon hydroxylase | |  |
| A10273 | 1-Naphthoic acid, 98% [Naphthalene-1-carboxylic acid] [86-55-5], C ₁₁ H ₈ O ₂ , F.W. 172.18, m.p. 160-162°, b.p. >300°, f.p. 195°(383°F), d. 1.398, Merck 14,6381, EINECS 201-681-9, RTECS QL0960000, BRN 1908896, MDL MFCD00004007, t | 25g 100g |
| ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | |  |
| The unprotected acid undergoes lithiation, e.g. with s-BuLi, by stereospecific 1,4-addition, providing a facile route to 1,1,2-trisubstituted 1,2-dihydronaphthalenes: <i>J. Org. Chem.</i> , 61 , 5206 (1996). | | |
| L05102 | 2-Naphthoic acid, 98+% [Naphthalene-2-carboxylic acid] [93-09-4], C ₁₁ H ₈ O ₂ , F.W. 172.18, m.p. 182-186°, f.p. 205°(401°F), d. 1.08, Merck 14,6382, EINECS 202-217-8, RTECS QL1050000, BRN 972039, MDL MFCD00004101, t | 5g 25g |
| ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | |  |
| The unprotected acid undergoes lithiation, e.g. with s-BuLi, by stereospecific 1,4-addition, providing a facile route to 1,2,2-trisubstituted 1,2-dihydronaphthalenes: <i>J. Org. Chem.</i> , 61 , 5206 (1996). | | |
| α-Naphthol, see 1-Naphthol, A11862, p. 298 | | |
| β-Naphthol, see 2-Naphthol, A14564, p. 298 | | |







| Stock # | Description | Size |
|---------|---|-----------------------|
| A11862 | 1-Naphthol, 99% ▲ △ <i>[α-Naphthol, 1-Hydroxynaphthalene]</i> [90-15-3], C ₁₀ H ₈ O, F.W. 144.17, m.p. 95-97°, b.p. 278-280°, f.p. 125°(257°F), d. 1.28, Merck 14.6383, Solubility: Soluble in alcohol, benzene, chloroform, ether, UN2811, EINECS 201-969-4, RTECS QL2800000, BRN 1817321, MDL MFCD00003930, †  | 100g 500g 2.5kg |
| |  H:H318-H302-H312-H335-H315, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| A14564 | 2-Naphthol, 98+% ▲ <i>[β-Naphthol, 2-Hydroxynaphthalene]</i> [135-19-3], C ₁₀ H ₈ O, F.W. 144.17, m.p. 120-124°, b.p. 285-286°, f.p. 153°(307°F), d. 1.280, Merck 14.6384, UN3077, EINECS 205-182-7, RTECS QL2975000, BRN 742134, MDL MFCD00004067, †  | 250g 1kg 5kg |
| |  H:H400-H302-H332, P:P261-P273-P304+P340-P301+P312-P312-P501a Application(s): Fluorescence indicator | |
| | Naphthol Blue Black , see Amido Black 10B, A11374, p. 91 | |
| A18268 | Naphthol Green B <i>[Acid Green 1, C.I. 10020]</i> [19381-50-1], C ₂₀ H ₁₃ FeN ₃ Na ₂ O ₁₅ S ₃ , F.W. 878.47, EINECS 243-010-2, RTECS LJ8930000, MDL MFCD00003886, †  | 25g 100g |
| | 2-Naphthol hydrogen sulfate potassium salt , see 2-Naphthyl sulfate potassium salt, 44061, p. 298 | |
| B20872 | Naphthol Yellow S <i>[C.I. 10316, 5,7-Dinitro-8-hydroxy-2-naphthalenesulfonic acid disodium salt]</i> [846-70-8], C ₁₀ H ₆ N ₂ Na ₂ O ₆ S, F.W. 358.20, m.p. >300°, Merck 14.6393, EINECS 212-690-2, RTECS QK1813000, BRN 2708476, MDL MFCD00003958, Note: C.I. 10316, †  | 50g 250g 1kg |
| | Naphthoresorcinol , see 1,3-Dihydroxynaphthalene, A17739, p. 192 | |
| | 1-Naphthylamine-6-sulfonic acid , see 5-Aminonaphthalene-2-sulfonic acid, L03099, p. 97 | |
| J63214 | N-(1-Naphthyl)ethylenediamine dihydrochloride, ACS ▲ ■ [1465-25-4], C ₁₂ H ₁₆ N ₂ ·2HCl, F.W. 259.18, Powder, m.p. ca 195°, Merck 14.6409, EINECS 215-981-2, RTECS KV5330000, BRN 3707471, MDL MFCD00012556, †  H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 5g 25g 100g |
| | Application(s): Used for colorimetric determination of sulfonamide in blood | |
| L12617 | 2-(1-Naphthylmethyl)-2-imidazoline nitrate, 99% ■ <i>[Naphazoline nitrate]</i> [5144-52-5], C ₁₄ H ₁₄ N ₂ ·HNO ₃ , F.W. 273.29, m.p. 168-170°, EINECS 225-915-4, RTECS NJ4376000, BRN 3779329, MDL MFCD00014316  | 25g 100g |
| |  H:H302, P:P264-P270-P301+P312-P330-P501a | |
| B22866 | 1-Naphthyl phosphate disodium salt hydrate, 99% <i>[Disodium 1-naphthyl phosphate hydrate]</i> [207569-06-0], C ₁₀ H ₇ Na ₂ O ₆ P·xH ₂ O, F.W. 268.12(anhy), m.p. >300°, EINECS 218-564-3, BRN 4895811, MDL MFCD00150614  | 1g 5g 25g |
| |  H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Substrate for phosphatases: <i>Methods of Enzymatic Analysis</i> , 3rd ed., H. U. Bergmeyer, Ed., Verlag Chemie, Weinheim (1984), vol. 4, p102. | |
| J63004 | 1-Naphthyl phosphate monosodium salt monohydrate, 97+% [81012-89-7], C ₁₀ H ₇ NaO ₆ P·H ₂ O, F.W. 264.15 (246.13anhy), Powder, BRN 1877764, MDL MFCD00150615  H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5g 25g |
| | Application(s): Substrate for determination of phosphatases | |
| J62097 | 1-(1-Naphthyl)piperazine hydrochloride [104113-71-5], C ₁₄ H ₁₈ N ₂ ·HCl, F.W. 248.75, Solid  H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g 5g |
| | Application(s): 5-HT1 serotonin receptor agonist. 5-HT2 serotonin receptor antagonist | |
| 44061 | 2-Naphthyl sulfate potassium salt, 98% <i>[2-Naphthol hydrogen sulfate potassium salt, Potassium 2-naphthyl sulfate]</i> [1733-89-7], C ₁₀ H ₇ KO ₄ S, F.W. 262.33, Powder, m.p. >300°, EINECS 217-072-6, MDL MFCD00004059, †  | 250mg 1g |
| | Naproxen , see (S)-(+)-2-(6-Methoxy-2-naphthyl)propionic acid, L09855, p. 285 | |
| J63103 | Naproxen sodium, 98% [26159-34-2], C ₁₄ H ₁₃ NaO ₃ , F.W. 252.24, Powder, m.p. 259-262°, Merck 14.6417, EINECS 247-486-2, RTECS QJ1047000, MDL MFCD00058507 | 5g 25g 100g |
| | Application(s): A cyclooxygenase inhibitor | |
| | Naringenin , see 4',5,7-Trihydroxyflavanone, L09834, p. 377 | |
| | Naringenin-7-rhamnoglucoside , see Naringin, J63166, p. 299 | |

| Stock # | Description | Size |
|--|---|--------------|
| J63166 | Naringin [Naringenin-7-rhamnoglucoside] [14259-46-2], C ₂₇ H ₃₂ O ₁₄ , F.W. 580.53, Powder, EINECS 238-138-0, RTECS QN6340000, BRN 102012, MDL MFCD00148888 | 25g 100g |
| Application(s): A citrus bioflavonoid that inhibits cytochrome P-450 monooxygenase activity | | |
| L10163 | Naringin hydrate, 98% [10236-47-2], C ₂₇ H ₃₂ O ₁₄ ·xH ₂ O, F.W. 580.55(anhy), m.p. ca 166° dec., [α] _D ²⁰ -90° (c=1 in ethanol), Merck 14,6424, EINECS 233-566-4, RTECS QN6340000, BRN 102012, MDL MFCD00149445, † Bitter principle of grapefruit. | 10g 50g |
| Application(s): A citrus bioflavonoid that inhibits cytochrome P450 monooxygenase activity | | |
|  | | |
| Natural Black 1 , see Hematoxylin hydrate, A12431, p. 242 Natural Yellow 18 , see Berberine chloride, J62311, p. 123 NBD chloride , see 4-Chloro-7-nitrobenzofurazan, A14165, p. 157 NBD-F , see 4-Fluoro-7-nitrobenzofurozan, J61336, p. 224 NBS , see N-Bromosuccinimide, A15922, p. 138 NCS , see N-Chlorosuccinimide, A10310, p. 159 NCS 382 sodium salt , see 6,7,8,9-Tetrahydro-5H-benzocycloheptene-5-ol-4-ylidene acetic acid, J63941, p. 362 NECA , see 5'-N-Ethylcarboxamidoadenosine, J60405, p. 215 | | |
| J64372 | Necrosis Inhibitor, IM-54 [1-Methyl-3-(1-methyl-1H-indol-3-yl)-4-(pentylamino)-1H-pyrrole-2,5-dione] [861891-50-1], C ₁₉ H ₂₃ N ₃ O ₂ , F.W. 325.40, Powder | 5mg |
| J65341 | Necrostatin-1 ▲ [Nec-1, Necroptotic Inhibitor] [4311-88-0], C ₁₃ H ₁₃ N ₃ OS, F.W. 259.33, Powder, MDL MFCD00056916 | 20mg |
| J64646 | Necrostatin-1, Inactive Control ▲ [Nec-1i, 5-(Indol-3-ylmethyl)-2-thiohydantoin] [64419-92-7], C ₁₂ H ₁₁ N ₃ OS, F.W. 245.30, Powder | 5mg |
| J62793 | Nefazodone hydrochloride, 98+% [BMV-13754] [82752-99-6], C ₂₃ H ₂₂ ClN ₂ O ₂ ·HCl, F.W. 506.47, Powder, m.p. 186-187°, Merck 14,6438, MDL MFCD00935760 | 1g 5g |
| Application(s): An antidepressant acts by modifying serotonin transmission. Mixed 5-HT2A serotonin receptor antagonist/serotonin uptake inhibitor | | |
| NEM , see N-Ethylmaleimide, L00355, p. 217 Neocuproine , see 2,9-Dimethyl-1,10-phenanthroline hemihydrate, A11398, p. 197 | | |
| J65680 | α-Neo-Endorphin (1-7) [Tyr-Gly-Gly-Phe-Leu-Arg-Lys] C ₄₀ H ₆₁ N ₁₁ O ₉ , F.W. 839.98, Solid | 10mg 25mg |
| J65819 | [Met5, Lys6] α-Neo-Endorphin (1-6) [Tyr-Gly-Gly-Phe-Met-Lys] C ₃₅ H ₄₇ N ₇ O ₈ , F.W. 701.83, Solid | 10mg 25mg |
| J64851 | [Met5, Lys6,7] α-Neo-Endorphin (1-7) [Tyr-Gly-Gly-Phe-Met-Lys-Lys] C ₃₉ H ₅₉ N ₉ O ₉ S, F.W. 830, Solid | 10mg 25mg |
| J62922 | Neohesperidin dihydrochalcone hydrate, 98+% [20702-77-6], C ₂₈ H ₃₆ O ₁₅ ·xH ₂ O, F.W. 612.58(anhy), Crystalline powder, Merck 14,6452, EINECS 243-978-6, RTECS LZ5785000, MDL MFCD03840557 | 5g 25g |
| Application(s): Artificial sweetener derived from citrus | | |
| J61499 | Neomycin sulfate hydrate [1405-10-3], C ₂₃ H ₄₆ N ₆ O ₁₃ ·3H ₂ SO ₄ ·xH ₂ O, F.W. 908.87(anhy), Powder, Merck 14,6454, EINECS 215-773-1, † H:H334-H317, P:P285-P261-P280-P302+P352-P321-P501 | 25g 100g |
| Application(s): An antibiotic. Acts as an inhibitor of protein biosynthesis | | |
| Neonicotine , see (±)-Anabasine, L12089, p. 103 | | |
| J62300 | Neostigmine bromide [114-80-7], C ₁₂ H ₁₆ BrN ₂ O ₂ , F.W. 303.20, Powder, m.p. 175-177°, Merck 14,6464, UN2811, EINECS 204-054-8, RTECS BR3150000, MDL MFCD00011795 H:H300-H310-H330-H334-H315-H319-H317-H335, P:P301+P310-P304+P340-P305+P351+P338-P320-P330-P361-P405-P501a | 250mg 1g |
| Application(s): A reversible acetylcholinesterase inhibitor | | |
| NEPIS , see 2-Ethyl-5-phenylisoxazolium-3'-sulfonate, J61826, p. 217 | | |
| Nerine , see Conessine, 97%, J62617, p. 167 | | |



| Stock # | Description | Size |
|---------|--|--------------------------------|
| J64864 | Nerve Growth Factor 2.5S, mouse submaxillary gland, 95% [NGF-2.5S] Note: Receptor Grade. Suitable for cell culture. Supplied as an aseptically lyophilized powder. | 10micrograms 5x10micrograms |
| J60711 | Neuraminidase, Clostridium perfringens, 50% w/w sucrose [Acyl-neuraminyl hydrolase, EC 3.2.1.18] [9001-67-6], Lyophilized powder, EINECS 232-624-6, RTECS QQ3450000, MDL MFCD00131711, Note: Minimum 10 units per mg protein. One unit releases one micromole of sialic acid per minute at 37°C and pH 5.0, from bovine submaxillary mucin, † Application(s): A hydrolytic enzyme that removes sialic acid from mucoproteins | 5units 10units |
| J63259 | Neuraminidase, Clostridium perfringens [Acyl-neuraminyl hydrolase, EC 3.2.1.18] [9001-67-6], Lyophilized powder, EINECS 232-624-6, RTECS QQ3450000, MDL MFCD00131711, Note: Minimum 0.5 units per mg dry weight. One unit releases one micromole of sialic acid per minute at 37°C and pH 5.0, from bovine submaxillary mucin, † Application(s): A hydrolytic enzyme that removes sialic acid from mucoproteins | 10mg |
| | Neuridine , see Spermine, L19562, p. 351 | |
| J63747 | Neuromedin N [Lys-Ile-Pro-Tyr-Ile-Leu] [92169-45-4], C ₂₈ H ₆₃ N ₇ O ₈ , F.W. 745.96, Lyophilized powder Application(s): Neurotensin-like peptide which can induce hypotension | 10mg |
| J63359 | Neurotensin [Glp-Leu-Tyr-Glu-Asn-Lys-Pro-Arg-Arg-Pro-Tyr-Ile-Leu] [55508-42-4], C ₇₈ H ₁₂₁ N ₂₁ O ₂ , F.W. 1672.92, Lyophilized powder Application(s): A neuromodulator of dopamine transmission and of anterior pituitary hormone secretion that exhibits a wide spectrum of pharmacological effects | 1mg 5mg |
| J62461 | Neurotensin (1-6) [Glp-Leu-Tyr-Glu-Asn-Lys] [87620-09-5], C ₃₅ H ₅₉ N ₉ O ₁₂ , F.W. 776.80, Lyophilized powder Application(s): Fragment of neurotensin | 1mg |
| J62253 | Neurotensin (1-8) [Glp-Leu-Tyr-Glu-Asn-Lys-Pro-Arg] [80887-44-1], C ₄₅ H ₇₁ N ₁₃ O ₁₄ , F.W. 1030.15, Lyophilized powder Application(s): Neurotensin fragment | 5mg 25mg |
| J63799 | Neurotensin (1-11) [Pyr-Leu-Tyr-Glu-Asn-Lys-Pro-Arg-Arg-Pro-Tyr-OH] [74032-89-6], C ₆₈ H ₉₉ N ₁₉ O ₁₈ , F.W. 1446.63, Lyophilized powder Application(s): Fragment of neurotensin | 1mg 5mg |
| J61112 | Neurotensin (8-13) [Arg-Arg-Pro-Tyr-Ile-Leu] [60482-95-3], C ₃₈ H ₆₄ N ₁₂ O ₈ , F.W. 817.00, Lyophilized powder Application(s): Shortest analog of neurotensin with full binding and pharmacological activities | 5mg |
| | Neurotensin-related peptide , see Kinetensin, J63865, p. 264 | |
| J60275 | Neutralization solution Liquid, Note: This solution contains: 1.5M NaCl and 1M Tris, pH range 7.0-7.2. | 250ml 500ml |
| J61379 | Neutral Red, 1% aq. solution, Ready-to-use [Basic Red 5, C.I. 50040] [553-24-2], C ₁₅ H ₁₇ ClN ₄ , F.W. 288.78, Liquid, Merck 14,6488, EINECS 209-035-8, MDL MFCD00012651, † Application(s): Nuclear counterstain useful in pH range 6.8 - 8.0 | 500ml 1L |
| J63054 | Neutral Red [Basic Red 5, C.I. 50040] [553-24-2], C ₁₅ H ₁₇ ClN ₄ , F.W. 288.78, Powder, m.p. 290° dec., Merck 14,6488, EINECS 209-035-8, RTECS SG1400000, BRN 3918740, MDL MFCD00012651, † Application(s): Nuclear counterstain useful in pH range 6.8 - 8.0 | 1g 5g 25g |
| J62643 | Neutral Red, ACS [Basic Red 5, C.I. 50040] [553-24-2], C ₁₅ H ₁₇ ClN ₄ , F.W. 288.78, Powder, m.p. 290° dec., Merck 14,6488, EINECS 209-035-8, RTECS SG1400000, BRN 3918740, MDL MFCD00012651, † Application(s): Nuclear counterstain useful in pH range 6.8 - 8.0 | 50g 250g |
| | Neutrophil elastase substrate, fluorogenic , see Elastase Substrate V, J60093, p. 205 | |
| J65706 | NF-kB Activation Inhibitor IV ▲ [(E)-2-Fluoro-4'-methoxystilbene] C ₁₅ H ₁₃ FO, F.W. 228.26, Solid ! H:H302, P:P264-P270-P301+P312-P330-P501 | 10mg |

| Stock # | Description | Size |
|---------|--|-----------------------|
| J64555 | NF-κB Activation Inhibitor VI, BOT-64 ▲ [(Z)-6,6-Dimethyl-2-(phenylimino)-6,7-dihydrobenzo[d][1,3]oxathiol-4(5H)-one] [113760-29-5], C ₁₅ H ₁₅ NO ₂ S, F.W. 273.40, Solid | 5mg 25mg |
| | Niacin , see Nicotinic acid, A12683, p. 302 Niacinamide , see Nicotinamide, A15970, p. 301 | |
| J61269 | Nicardipine hydrochloride, 98+% [54527-84-3], C ₂₀ H ₂₉ N ₃ O ₆ ·HCl, F.W. 515.99, Powder, Merck 14,6495, UN2811, EINECS 259-198-4, RTECS US7972100, MDL MFCD00057327  H: H301-H311-H330, P: P301+P310-P304+P340-P320-P330-P361-P405-P501a | 1g 5g |
| | Application(s): L-type calcium channel blocker | |
| J63295 | Nicergoline [5-Bromonicotinic acid 10-methoxy-1,6-dimethylergoline-8-methyl ester] [27848-84-6], C ₂₆ H ₂₆ BrN ₃ O ₃ , F.W. 484.39, Powder, Merck 14,6496, EINECS 248-694-6, RTECS KE6341000, MDL MFCD00869626 ! H: H302, P: P264-P270-P301+P312-P330-P501 | 100mg 1g |
| | Application(s): Cerebral and peripheral vasodilator | |
| J61204 | Nickel(II) chloride, 0.5M aq. soln. [7791-20-0], NiCl ₂ , F.W. 129.6, Liquid, † !  H: H312-H332-H341-H350-H360-H372-H411, P: P260-P261-P280-P302+P352-P405-P501 | 50ml 100ml |
| J61993 | Nickel(II) sulfate, 0.5M aq. soln. [10101-97-0], NiSO ₄ , F.W. 262.86, Liquid, †  H: H334-H350-H360D-H372-H341-H315-H317-H411, P: P260-P285-P302+P352-P321-P405-P501a | 50ml 100ml |
| 12514 | Nickel(II) sulfate hexahydrate, 98% [10101-97-0], NiSO ₄ ·6H ₂ O, F.W. 262.86 (154.77anhy), Crystalline, d. 2.070, Merck 14,6517, Solubility: Soluble in water. Slightly soluble in alcohol, methanol, UN3288, EINECS 232-104-9, RTECS QR9600000, MDL MFCD00149813, Note: m.p. 100° -5H ₂ O, 280° -6H ₂ O, †  H: H334-H350-H360D-H372-H341-H400-H410-H302-H332-H315-H317, P: P273-P201-P309+P311-P501a | 500g 2kg |
| | Application(s): In nickel plating, as mordant in dyeing and in printing textiles | |
| 36336 | Nickel(II) sulfate hexahydrate, ACS, 98.0% min [10101-97-0], NiSO ₄ ·6H ₂ O, F.W. 262.86 (154.77anhy), Powder, d. 2.070, Merck 14,6517, UN3288, EINECS 232-104-9, RTECS QR9600000, MDL MFCD00149813, Note: m.p. 100° -5H ₂ O, 280° -6H ₂ O, † Maximum level of impurities: Insoluble matter 0.005%, Cl 0.001%, Nitrogen compounds (as N) 0.002%, Co 0.002%, Mg 0.005%, Mn 0.002%, Na 0.01%, Na 0.05%, Cu 0.005%, Fe 0.001%, Ca 0.005%  H: H334-H350-H360D-H372-H341-H400-H410-H302-H332-H315-H317, P: P273-P201-P309+P311-P501a | 100g 500g 2.5kg |
| J60879 | Nicorandil, 98+% [2-(3-Pyridylcarbonylamino)ethyl nitrate] [65141-46-0], C ₈ H ₈ N ₂ O ₄ , F.W. 211.17, Powder, m.p. 92-93°, Merck 14,6521, EINECS 265-514-1, RTECS US4667600, MDL MFCD00186520  H: H302-H318, P: P280-P264-P305+P351+P338-P310-P301+P312-P501 | 250mg 1g |
| | Application(s): A vasodilator that activates ATP-sensitive potassium channels | |
| A15970 | Nicotinamide, 99% [Niacinamide, Pyridine-3-carboxamide] [98-92-0], C ₆ H ₆ N ₂ O, F.W. 122.13, m.p. 128-132°, f.p. 182°(360°F), d. 1.40, Merck 14,6523, EINECS 202-713-4, RTECS QS3675000, BRN 383619, MDL MFCD00006395, † ! H: H319, P: P280-P264-P305+P351+P338-P337+P313 | 100g 250g 1kg |
| | Application(s): The amide of nicotinic acid (vitamin B-3) | |
| J62337 | β-Nicotinamide adenine dinucleotide, 98+% [β-NAD] [53-84-9], C ₂₁ H ₂₇ N ₇ O ₁₄ P ₂ , F.W. 663.43, Powder, Merck 14,6344, EINECS 200-184-4, RTECS UU3450000, BRN 3584133, MDL MFCD00036253, † | 1g 5g 25g |
| 44126 | β-Nicotinamide adenine dinucleotide phosphate monosodium salt [β-NADP monosodium salt, Triphosphopyridine nucleotide monosodium salt] [1184-16-3], C ₂₁ H ₂₇ N ₇ NaO ₁₇ P ₃ , F.W. 765.40, Powder, EINECS 214-664-6, BRN 4779954, MDL MFCD00036973 ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250mg 1g |
| J62556 | β-Nicotinamide adenine dinucleotide phosphate disodium salt, 97% [β-NADP disodium salt] [24292-60-2], C ₂₁ H ₂₆ N ₇ Na ₂ O ₁₇ P ₃ , F.W. 787.37, Powder, EINECS 246-129-8, MDL MFCD00065390 | 250mg 1g |
| J60387 | β-Nicotinamide adenine dinucleotide phosphate reduced tetrasodium salt hydrate, 98+% [β-NADPH tetrasodium salt tetrahydrate] C ₂₁ H ₂₆ N ₇ Na ₄ O ₁₇ P ₃ ·xH ₂ O, F.W. 905.42 (833.35anhy), Powder | 100mg 500mg |











| Stock # | Description | Size |
|---------|---|--|
| J62089 | β-Nicotinamide adenine dinucleotide phosphate reduced tetrasodium salt, 95% ▲ [β-NADPH tetrasodium salt] [2646-71-1], C ₂₁ H ₂₆ N ₇ Na ₄ O ₁₄ P ₃ ·3H ₂ O, F.W. 833.35, Powder, EINECS 220-163-3, MDL MFCD00036263 | 100mg 500mg |
| J61461 | β-Nicotinamide adenine dinucleotide reduced disodium salt trihydrate, 98% [β-NADH disodium salt trihydrate] C ₂₁ H ₂₇ N ₇ Na ₂ O ₁₄ P ₂ ·3H ₂ O, F.W. 763.46 (709.41anhy), Powder | 1g 5g |
| J61638 | β-Nicotinamide adenine dinucleotide reduced disodium salt, 98% [β-NADH disodium salt] [606-68-8], C ₂₁ H ₂₇ N ₇ Na ₂ O ₁₄ P ₂ , F.W. 709.41, Powder, EINECS 210-123-3, BRN 5230241, MDL MFCD00036200, † | 1g 5g |
| A12398 | (S)-(-)-Nicotine, 99% ▲ ▲ ▲ [54-11-5], C ₁₀ H ₁₄ N ₂ , F.W. 162.24, m.p. -79°, b.p. 245-248°, f.p. 101°(213°F), d. 1.017, n _D ²⁰ 1.5265, [α] _D ²⁰ -168° (neat), Merck 14,6524, UN1654, EINECS 200-193-3, RTECS QS5250000, BRN 82109, MDL MFCD00006369, †  H: H301-H310-H411, P: P301+P310-P361-P302+P350-P321-P405-P501a |  25g 100g |
| A12683 | Nicotinic acid, 99% [Niacin, Pyridine-3-carboxylic acid] [59-67-6], C ₆ H ₅ NO ₂ , F.W. 123.11, m.p. 236-239°, f.p. 293°(559°F), d. 1.4, Merck 14,6525, EINECS 200-441-0, RTECS QT0525000, BRN 109591, MDL MFCD00006391, † ! H: H319, P: P280-P264-P305+P351+P338-P373+P313 Application(s): Vitamin of the B complex with hypolipidemic properties occurring in various animal and plant tissues. Required by the body for the formation of coenzymes NAD and NADP |  250g 1kg 5kg |
| J64759 | Nicotinic acid adenine dinucleotide phosphate tetrasodium salt [NAADP, NAADP tetrasodium salt] [5502-96-5], C ₂₁ H ₂₆ N ₈ Na ₄ O ₁₆ P ₃ , F.W. 832.32, Solid, MDL MFCD00274064 ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10mg |
| | Nicotinoyl-Gly-OH , see Nicotinuric acid, 98+%, J62215, p. 302 | |
| J62215 | Nicotinuric acid, 98+% [Nicotinylglycine, Nicotinoyl-Gly-OH] [583-08-4], C ₈ H ₈ N ₂ O ₃ , F.W. 180.16, Crystalline powder, EINECS 209-497-0, MDL MFCD00023578 Application(s): The major detoxification product of nicotinic acid. A nicotinic acid antagonist | 5g 25g |
| J62811 | Nifedipine, 98% [21829-25-4], C ₁₈ H ₁₈ N ₂ O ₆ , F.W. 346.33, Powder, m.p. 171-175°, Merck 14,6528, EINECS 244-598-3, RTECS US7975000, MDL MFCD00057326 ! H: H302, P: P264-P270-P301+P312-P330-P501a Application(s): L-type calcium channel blocker; induces apoptosis in human glioblastoma cells | 5g 25g 100g |
| J60489 | Niflumic acid, 99+% ▲ [2-[3-(Trifluoromethyl)anilino]nicotinic acid, 2-(α,α,α-Trifluoro-m-toluidino)nicotinic acid] [4394-00-7], C ₁₃ H ₈ F ₃ N ₂ O ₂ , F.W. 282.22, Crystalline powder, m.p. 203-204°, Merck 14,6531, UN2811, EINECS 224-516-2, RTECS QT2999100, MDL MFCD00010569  H: H301-H312-H332-H315-H319-H335, P: P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): Selective cyclooxygenase-2 (COX-2) inhibitor. A NSAID found to be a potent anion channel blocker | 5g 10g 50g |
| J61349 | Nigericin sodium salt, 98+% [Antibiotic K178 sodium salt] [28380-24-7], C ₃₈ H ₆₀ NaO ₁₁ , F.W. 746.94, Powder, Merck 14,6541, UN3462, RTECS QT6840000, BRN 3892398, MDL MFCD00036825  H: H301-H315-H319-H335, P: P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): A potassium ionophore | 10mg 50mg |
| J61186 | Nigrosin, alcohol soluble [Solvent Black 5, C.I. 50415] [11099-03-9], Powder, RTECS GE5800000, MDL MFCD00149005, † | 25g 100g 1kg |
| A18147 | Nigrosin water soluble [Acid Black 2, C.I. 50420] [8005-03-6], RTECS GC4762250, MDL MFCD00044681, † Application(s): Fairly common biological stain for tissues and cells | 25g 100g |
| A17174 | Nile Blue A [C.I. 51180, Basic Blue 12] [3625-57-8], C ₄₀ H ₄₀ N ₄ O ₆ S, F.W. 732.84, m.p. >300° dec., EINECS 222-832-5, RTECS DJ1931000, MDL MFCD00064529 |  5g 25g |










| Stock # | Description | Size |
|--|--|---------------------|
| J62578 | Nilotinib, 99+% [AMN107] [641571-10-0], C ₂₈ H ₂₂ F ₃ N ₆ O, F.W. 529.52, Powder, m.p. 230-242°, RTECS CV5581770 ! H: H360, P: P281-P201-P202-P308+P313-P405-P501a | 100mg 500mg |
| Application(s): Tyrosine kinase inhibitor specifically targeting Bcr-Abl | | |
| J63699 | Nimesulide [N-(4-Nitro-2-phenoxyphenyl)methanesulfonamide] [51803-78-2], C ₁₈ H ₁₂ N ₂ O ₅ S, F.W. 308.31, Needle-like crystals, m.p. 145-147°, Merck 14,6548, UN2811, EINECS 257-431-4, RTECS PB0970000, MDL MFCD00079470 ! H: H301, P: P264-P270-P301+P310-P321-P405-P501a | 5g 25g |
| Application(s): Highly selective cyclooxygenase-2 inhibitor which induces apoptosis | | |
| J61287 | Nimodipine, 98+% [66085-59-4], C ₂₃ H ₂₈ N ₂ O ₇ , F.W. 418.44, Powder, Merck 14,6551, EINECS 266-127-0, RTECS US7975500, MDL MFCD00153848 ! H: H302-H312-H332, P: P261-P280-P302+P352-P304+P340-P322-P501a | 500mg 1g 5g |
| Application(s): Potent L-type calcium channel antagonist | | |
| 43846 | Ninhydrin, ACS reagent ▲ [2,2-Dihydroxy-1,3-indanedione] [485-47-2], C ₉ H ₆ O ₃ , F.W. 178.14, Crystalline, m.p. 251° dec., Merck 14,6554, Fieser 1,732 4,356, Solubility: Soluble in water and alcohol, EINECS 207-618-1, RTECS NK5425000, BRN 1910963, MDL MFCD00003791, † Maximum level of impurities: Appearance White to brownish-white crystals, Identification and melting point P.T., Solubility P.T., Sensitivity to amino acids P.T. ! H: H302-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 25g 100g 500g |
| Application(s): Reagent for determination of amino acids and amine containing compounds, as an intermediate. | | |
| B24723 | Nipecotic acid, 98% [H-DL-Nip-OH, (+/-)-Piperidine-3-carboxylic acid] [498-95-3], C ₈ H ₁₁ NO ₂ , F.W. 129.16, m.p. ca 261° dec., Merck 14,6561, Solubility: Soluble in water, EINECS 207-873-9, RTECS TM6125380, BRN 81096, MDL MFCD00005992 ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 1g 5g 25g |
| Application(s): GABA reuptake inhibitor | | |
| Nitogenin , see Diosgenin, J60976, p. 198 | | |
| J60281 | Nitrazine Yellow [C.I. 14890, Delta Yellow] [5423-07-4], C ₁₆ H ₈ N ₄ Na ₂ O ₁₁ S ₂ , F.W. 542.36, Powder, MDL MFCD00003938, † | 1g 5g 25g |
| Application(s): pH indicator | | |
| J60841 | Nitrendipine [39562-70-4], C ₁₈ H ₂₀ N ₂ O ₆ , F.W. 360.36, Powder, EINECS 254-513-1, RTECS US5653000, MDL MFCD00082255 ! H: H302-H312-H332, P: P261-P280-P302+P352-P304+P340-P322-P501 | 100mg 1g |
| Application(s): L-type calcium channel blocker | | |
| 35624 | Nitric acid, 1.0N Standardized Solution [7697-37-2], HNO ₃ , F.W. 63.01, Liquid, UN3624, EINECS 231-714-2, MDL MFCD00011349, † ! H: H330-H314, P: P280-P303+P361+P353-P305+P351+P338-P310 | 500ml 1L |
| 36515 | Nitrilotriacetic acid, ACS, 98.0% min [Tris(carboxymethyl)amine, N,N-Bis(carboxymethyl)glycine] [139-13-9], N(CH ₂ CO ₂ H) ₃ , F.W. 191.14, Powder, m.p. 246° dec., Merck 14,6579, EINECS 205-355-7, RTECS AJ0175000, BRN 1710776, MDL MFCD00004287, Note: Clarity of solution passes test, † ! H: H351-H302-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 100g 500g |
| Application(s): Chelating and sequestering agent. Used in the manufacture of synthetic detergents | | |
| 2,2',2''-Nitrilotriethanol , see Triethanolamine, L04486, p. 376 | | |
| 2,2',2''-Nitrilotriethanol hydrochloride , see Triethanolamine hydrochloride, A15678, p. 376 | | |
| J60230 | Nitro Blue Tetrazolium chloride, 99% [Nitro BT, Nitrotetrazolium Blue chloride] [298-83-9], C ₄₀ H ₃₀ Cl ₂ N ₁₀ O ₆ , F.W. 817.65, Crystalline powder, m.p. ca 190° dec., EINECS 206-067-4, RTECS XF8045000, BRN 4115923, MDL MFCD00012159, † ! H: H302-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 1g 5g |
| Application(s): Intense blue dye used in histochemistry determinations | | |
| Nitro BT , see Nitro Blue Tetrazolium chloride, 99%, J60230, p. 303 | | |
| J62541 | Nitrocellulose stripping buffer (10X) Liquid, Note: This buffer contains 0.5X SSC and 100 mM EDTA at pH 8.0. To strip the membrane perform 2 to 3 changes (15 seconds each) of boiling hot stripping buffer., † | 250ml 500ml |





| Stock # | Description | Size |
|--|--|---------|
| A18593 | 5-Nitro-2-furaldehyde semicarbazone, 98+% ▲ [Furacin, Nitrofurazone] [59-87-0], C ₆ H ₅ N ₃ O ₄ , F.W. 198.14, m.p. ca 240° dec., Merck 14,6600, EINECS 200-443-1, RTECS LT7700000, BRN 86403, MDL MFCD00003225, † ☠ ! H:H341-H351-H361-H302, P:P281-P264-P301+P312-P308+P313-P405-P501a | 25g |
| | | 100g |
| | | 250g |
| Application(s): Bactericidal compound used as an antibiotic | | |
| B24079 | Nitrofurantoin, 98% ▲ ■ [N-(5-Nitro-2-furfurylidene)-1-aminohydantoin] [67-20-9], C ₈ H ₇ N ₃ O ₅ , F.W. 238.16, m.p. ca 265° dec., EINECS 200-646-5, MDL MFCD00003224, † ☠ ! H:H334-H341-H351-H361-H302-H317, P:P285-P261-P302+P352-P321-P405-P501a | 25g |
| | | 100g |
| | | 500g |
| Application(s): An antibiotic used to treat urinary tract infections | | |
| Nitrofurazone, see 5-Nitro-2-furfurylidene semicarbazone, A18593, p. 304 | | |
| 5-Nitrofurural semicarbazone, see 5-Nitro-2-furfurylidene semicarbazone, A18593, p. 304 | | |
| N-(5-Nitro-2-furfurylidene)-1-aminohydantoin, see Nitrofurantoin, B24079, p. 304 | | |
| 3-(5-Nitrofururylideneamino)-2-oxazolidinone, see Furazolidone, B20834, p. 229 | | |
| L07970 | 7-Nitro-1H-indazole, 98% [2942-42-9], C ₇ H ₅ N ₃ O ₂ , F.W. 163.14, m.p. 184-189°, EINECS 220-934-4, RTECS NK7962200, BRN 6809, MDL MFCD00022789 ☠ ! H:H341-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 1g |
| | | 5g |
| | | 25g |
| Application(s): Nitrix oxide synthase inhibitor | | |
| N-(4-Nitro-2-phenoxyphenyl)methanesulfonamide, see Nimesulide, J63699, p. 303 | | |
| J61401 | 4-Nitrophenyl phosphate disodium salt hexahydrate, 5mg tablets [pNPP disodium salt, Disodium 4-nitrophenyl phosphate] [4264-83-9], C ₆ H ₄ NNa ₂ O ₆ P 6H ₂ O, F.W. 371.15 (263.05anhy), Tablets, EINECS 224-246-5, BRN 5324661, MDL MFCD00066288, † | 100pcs |
| | | 1000pcs |
| | | |
| Application(s): Substrate for alkaline and acid phosphatase determinations | | |
| A12310 | 4-Nitrophenyl phosphate disodium salt hexahydrate, 98% [4264-83-9], C ₆ H ₄ NNa ₂ O ₆ P 6H ₂ O, F.W. 371.15 (253.06anhy), m.p. >300°, EINECS 224-246-5, BRN 5324661, MDL MFCD00007319, † Chromogenic substrate for phosphatases: <i>Methods of Enzymatic Analysis</i> , 3rd ed., H. U. Bergmeyer, Ed., Verlag Chemie, Weinheim (1984), vol. 4, p76. | 5g |
| | | 25g |
| | | 100g |
| Application(s): Substrate for alkaline and acid phosphatase determinations | | |
| N-Nitroso-N-phenylhydroxylamine ammonium salt, see Cupferron, 97+% , A16551, p. 170 | | |
| Nitrotetrazolium Blue chloride, see Nitro Blue Tetrazolium chloride, 99%, J60230, p. 303 | | |
| L-NMMA, see N ω -Methyl-L-arginine acetate, 99+% , J60890, p. 286 | | |
| Nonanoic acid cholesteryl ester, see Cholesteryl nonanoate, L02857, p. 161 | | |
| A19166 | (+)-Nootkatone, crystalline, 98+% [4674-50-4], C ₁₅ H ₂₂ O, F.W. 218.34, m.p. 34-36°, b.p. 125°/0.5mm, f.p. 99°(210°F), d. 0.997, [α] _D ²⁰ +185° (c=1 in chloroform), EINECS 225-124-4, BRN 4676969, MDL MFCD00036591, † | 1g |
| | | 5g |
| | | 25g |
| L08087 | L-Noradrenaline, 98% ▲ △ [L-Arterenol, L-Norepinephrine] [51-41-2], C ₈ H ₁₁ NO ₃ , F.W. 169.18, m.p. ca 220° dec., [α] _D ²⁰ -45° (c=5 in 0.5 N HCl), Merck 14,6695, UN2811, EINECS 200-096-6, RTECS DN5950000, BRN 4231961, MDL MFCD00025592 ☠ H:H300, P:P264-P270-P301+P310-P321-P405-P501a | 1g |
| | | |
| | | |
| L03149 | Nordihydroguaiaretic acid, 97% [1,4-Bis(3,4-dihydroxyphenyl)-2,3-dimethylbutane] [500-38-9], C ₁₈ H ₂₂ O ₄ , F.W. 302.37, m.p. 184-188°, Merck 14,6693, EINECS 207-903-0, RTECS UX1750000, BRN 2056825, MDL MFCD00002206 ! H:H302-H315-H319-H335, P:P280H-P305+P351+P338 Naturally-occurring antioxidant. | 1g |
| | | 5g |
| | | |
| Application(s): Naturally occurring antioxidant and inhibitor of lipoxygenase | | |
| L-Norepinephrine, see L-Noradrenaline, L08087, p. 304 | | |
| J62652 | Norfloxacin [Baccidal, Sebercim] [70458-96-7], C ₁₆ H ₁₈ FN ₃ O ₃ , F.W. 319.33, Powder, m.p. 220-221°, Merck 14,6700, EINECS 274-614-4, RTECS VB5005000, MDL MFCD00079532 | 1g |
| | | 5g |
| | | 25g |
| Application(s): A synthetic fluoroquinolone antibiotic | | |
| L08257 | D-(-)-Norleucine, 99% [(R)-(-)-2-Aminohexanoic acid, H-D-Nle-OH] [327-56-0], C ₆ H ₁₃ NO ₂ , F.W. 131.18, m.p. >300°, [α] _D ²⁰ -23° (c=5 in 5N HCl), Merck 14,6706, EINECS 206-320-9, BRN 1721749, MDL MFCD00008099 | 1g |
| | | 5g |
| | | |




| Stock # | Description | Size | |
|---------|--|---|----------------|
| L03913 | L-(+)-Norleucine, 99% [(S)-(+)-2-Aminohexanoic acid, H-Nle-OH] [327-57-1], C ₆ H ₁₃ NO ₂ , F.W. 131.18, m.p. >300°, [α] _D ²⁰ +23° (c=5 in 5N HCl), Merck 14,6706, EINECS 206-321-4, RTECS RC6308000, BRN 1721750, MDL MFCD00064423, † Internal standard for amino acid analysis: <i>Anal. Biochem.</i> , 150 , 174 (1985). |  | 1g |
| | | 5g | |
| | | 25g | |
| L10809 | DL-Nornicotine, 98% ■ [DL-2-(3-Pyridyl)pyrrolidine] [5746-86-1], C ₈ H ₁₂ N ₂ , F.W. 148.21, b.p. 107-108°/2mm, f.p. 101° (213°F), d. 1.074, n _D ²⁰ 1.5490, Merck 14,6712, UN2810, RTECS QS6350000, BRN 81968, MDL MFCD00016913 ! H:H302-H312-H332-H315-H319, P:P261-P280-P305+P351+P338-P302+P352-P321-P501a Application(s): Nicotinic acetylcholine receptor agonist. Tobacco alkaloid |  | 10mg |
| | | 50mg | |
| A15900 | DL-Norvaline, 98% [(+/-)-2-Aminopentanoic acid, DL-2-Aminovaleric acid] [760-78-1], C ₅ H ₁₁ NO ₂ , F.W. 117.15, m.p. >300°, Merck 14,6716, EINECS 212-082-7, BRN 1721163, MDL MFCD00064420, † |  | 100g 500g |
| B23444 | D-Norvaline, 99% [(R)-2-Aminopentanoic acid, D-2-Aminovaleric acid] [2013-12-9], C ₅ H ₁₁ NO ₂ , F.W. 117.15, m.p. >300°, [α] _D ²⁰ -25° (c=10 in 20% HCl), Merck 14,6716, EINECS 217-936-2, BRN 1721161, MDL MFCD00008097 |  | 1g |
| | | 5g | |
| | | 25g | |
| L08658 | L-Norvaline, 99% [(S)-2-Aminopentanoic acid, L-2-Aminovaleric acid] [6600-40-4], C ₅ H ₁₁ NO ₂ , F.W. 117.15, m.p. >300°, [α] _D ²⁰ +25° (c=10 in 20% HCl), Merck 14,6716, EINECS 229-543-3, BRN 1721162, MDL MFCD00064421 |  | 1g 5g |
| J60928 | Novobiocin sodium salt [1476-53-5], C ₃₁ H ₃₈ N ₈ NaO ₁₁ , F.W. 634.61, Powder, m.p. 215°, Merck 14,6722, EINECS 216-023-6, RTECS RD5425000, BRN 3892910 ! H:H319-H317, P:P261-P280-P305+P351+P338-P302+P352-P321-P501a Application(s): Topoisomerase II inhibitor | | 1g |
| | | | 5g |
| | | | 10g |
| J60766 | NP-40 lysis buffer Liquid, Note: This buffer contains: 50mM Tris-HCl (pH 7.4), 150mM NaCl, 1%NP-40 and 5mM EDTA., † | | 250ml 500ml |
| J62805 | NP-40 lysis buffer (2X) Liquid, Note: This buffer contains: 100mM Tris-HCl (pH 7.4), 300mM NaCl, 2% NP-40, and 10mM EDTA. | | 125ml 250ml |
| J61428 | NP-40 lysis buffer, high salt Liquid, Note: This buffer contains: 50mM Tris-HCl (pH 7.4), 500mM NaCl, 1% NP-40 and 5mM EDTA. | | 250ml 500ml |
| J60902 | NP-40 lysis buffer, low salt Liquid, Note: This buffer contains: 50mM Tris-HCl (pH 7.4), 1% NP-40, and 5mM EDTA. | | 250ml 500ml |
| J60143 | NP-40 lysis buffer with glycerol (2X) Liquid, Note: This buffer contains: 100mM Tris-HCl (pH 8.0), 300mM sodium chloride, 2% NP-40, 10mM EDTA, and 10% glycerol. | | 125ml 250ml |
| J60838 | NP-40 permeating solution in PBS (10X) Liquid, Note: 1% (v/v) NP-40 in 10X PBS., † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | | 250ml 500ml |
| J62410 | NP-40 permeating solution in TBS (10X) Liquid, Note: 1% (v/v) NP-40 in 10X TBS. | | 250ml 500ml |
| | NSC 7908 , see 1,2,3,4,5,6-Hexabromocyclohexane, J60853, p. 244 | | |
| J64979 | NSC 23766 ▲ ■ [Rac1 Inhibitor] [733767-34-5], C ₂₄ H ₃₅ N ₇ ·3HCl, F.W. 530.96, Powder | | 10mg |
| | NSC-85998 , see Streptozotocin, 98%, J61601, p. 352 NSC 122023 , see Valinomycin, 90+%, J62312, p. 390 NSC 101806 , see 8-Cyclopentyl-1,3-dimethylxanthine, J61565, p. 172 NSC 122750 , see Geldanamycin, 99+%, J63397, p. 231 NSC 339554 , see Bryostatin 2, J61551, p. 139 NTA , see Nitrilotriacetic acid, 36515, p. 303 | | |
| J62974 | Nylon membrane stripping buffer (10X) Liquid, Note: This buffer contains 10mM Tris-HCl (pH 8.0) and 10mM EDTA. To strip the membrane incubate for 2 hours in the stripping buffer at 75C. | | 250ml 500ml |
| J62486 | Nystatin [1400-61-9], C ₄₇ H ₇₂ NO ₁₇ , F.W. 926.09, Fine powder, m.p. 160°, Merck 14,6736, EINECS 215-749-0, RTECS RF5950000 Application(s): Increases the permeability of the cell membrane of sensitive fungi by binding to sterols | | 5g |
| | | | 10g |


| Stock # | Description | Size |
|---------|---|---|
| J60555 | NZCYM medium Liquid, Note: Ingredients (per liter amounts): 10g NZ amine, 5g NaCl, 5g Bacto yeast extract, 1g Casamino acids and 2g magnesium sulfate heptahydrate Application(s): NZCYM Medium is used for cultivating recombinant strains of Escherichia coli | 500ml 1L |
| J61680 | NZM medium Liquid, Note: Ingredients (per liter amounts): 10g NZ amine, 5g NaCl, and 2g magnesium sulfate heptahydrate Application(s): For the cultivation of recombinant strains of Escherichia coli. NZM medium is a modification of NZCYM medium | 500ml 1L |
| J60918 | NZYM medium Liquid, Note: Ingredients (per liter amounts): 10g NZ amine, 5g NaCl, 5g Bacto yeast extract, 2g magnesium sulfate heptahydrate Application(s): NZYM Medium is used for cultivating recombinant strains of Escherichia coli | 500ml 1L |
| | 3,4,5,6,3',5',3'',5'''-Octabromophenolsulfonphthalein , see Tetrabromophenol Blue, B20123, p. 361 Octadecanoic acid cholesteryl ester , see Cholesteryl stearate, A14771, p. 161 cis-9-Octadecenoic acid , see Oleic acid, 31997, p. 307 trans-9-Octadecenoic acid , see Elaidic acid, A14832, p. 205 Octadecylthioarachidonic acid , see 5,8,11,14-Eicosatetraynoic acid, J61624, p. 204 1-Octanesulfonic acid sodium salt , see Sodium 1-octanesulfonate, A14292, p. 347 Octanoic acid methyl ester , see Methyl caprylate, A10991, p. 289 | |
| L11502 | (R)-(-)-2-Octanol, 99% [5978-70-1], C ₈ H ₁₈ O, F.W. 130.23, b.p. 179-180°, f.p. 76°(169°F), d. 0.819, n _D ²⁰ 1.4260, [α] _D ²⁰ -10° (c=1 in ethanol), Merck 14,6752, EINECS 227-777-0, BRN 1719324, MDL MFCD00064284, t ! H:H319, P:P261-P305+P351+P338 |  1g 5g |
| L12425 | (S)-(+)-2-Octanol, 99% [6169-06-8], C ₈ H ₁₈ O, F.W. 130.23, b.p. 179-180°, f.p. 76°(169°F), d. 0.819, n _D ²⁰ 1.4260, [α] _D ²⁰ +10° (c=1 in ethanol), Merck 14,6752, EINECS 228-213-6, BRN 1719323, MDL MFCD00064283, t ! H:H319, P:P261-P305+P351+P338 |  1g 5g |
| J63574 | N-Octanoyl-N-methylglucamine [MEGA-8, N-(D-Glucityl)-N-methyloctanamide] [85316-98-9], C ₁₈ H ₃₁ NO ₆ , F.W. 321.41, Powder, m.p. 88-89°, BRN 5816747, MDL MFCD00134152 Application(s): Non-ionic detergent for solubilizing membrane proteins | 1g 5g |
| J60071 | (S)-1-Octen-3-ol [24587-53-9], C ₈ H ₁₆ O, F.W. 128.21, Liquid, MDL MFCD04972323 ! H:H302-H332-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): For synthesis of optically active products | Call |
| J61281 | (±)-Octopamine hydrochloride, 99% [α-(Aminomethyl)-4-hydroxybenzyl alcohol hydrochloride] [770-05-8], C ₈ H ₁₁ NO ₂ ·xHCl, F.W. 189.64, Powder, m.p. 170° dec., Merck 14,6759, EINECS 212-216-4, BRN 3915414, MDL MFCD00012881 ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): α-adrenoceptor agonist; invertebrate neurotransmitter and neuromodulator | 1g 5g 10g |
| | Octoxynol-9 , see Triton® X-100, A16046, p. 383 | |
| L13259 | n-Octyl-β-D-glucopyranoside [n-Octyl-β-D-glucoside, OGD] [29836-26-8], C ₁₈ H ₃₆ O ₆ , F.W. 292.37, m.p. 103-104°, [α] _D ²⁰ -31° (c=2 in methanol), EINECS 249-887-8, BRN 84118, MDL MFCD00063288 Nonionic dialyzable detergent. Application(s): Non-ionic detergent for membrane proteins |  250mg 1g |
| | n-Octyl-β-D-glucoside , see n-Octyl-β-D-glucopyranoside, L13259, p. 306 Octylphenyl-polyethylene glycol , see Igepal CA-630® Rhodia, J61055, p. 253 n-Octyltetraoxyethylene , see Tetraethylene glycol mono-octyl ether, J62496, p. 362 | |
| J61028 | n-Octyl-β-D-thioglucopyranoside, 98+% [Octyl thioglucoside] [85618-21-9], C ₁₈ H ₃₆ O ₅ S, F.W. 308.44, Crystalline powder, m.p. 128°, BRN 4182783, MDL MFCD00012189 Application(s): Non-ionic detergent used for the solubilization of membrane proteins | 2.5g 5g 10g |
| | Octyl thioglucoside , see n-Octyl-β-D-thioglucopyranoside, 98+%, J61028, p. 306 ODQ , see 1H-[1,2,4]Oxadiazolo[4,3-a]-quinoxalin-1-one, 99+%, J62250, p. 310 Oflocet , see Ofloxacin, J62080, p. 306 | |
| J62080 | Ofloxacin [Oflocet, Ofloxacin] [82419-36-1], C ₁₈ H ₂₀ FN ₃ O ₄ , F.W. 361.37, Crystalline powder, m.p. 270-275°, Merck 14,6771, RTECS UU8815500, MDL MFCD00226105 Application(s): Fluorinated nalidixic acid analog with broad-spectrum antibacterial activity | 1g 5g |
| | Ofloxacin , see Ofloxacin, J62080, p. 306 | |




| Stock # | Description | Size |
|---------------|--|---|
| | OGD , see n-Octyl-β-D-glucopyranoside, L13259, p. 306 | |
| A12989 | Oil Red O [C.I. 26125, Solvent Red 27] [1320-06-5], C ₂₆ H ₂₄ N ₂ O, F.W. 408.51, m.p. ca 166° dec., EINECS 215-295-3, BRN 3491382, MDL MFCD00003898, † | 25g 100g |
| | Application(s): Suitable as a lipid and lipoprotein stain on cellulose acetate |  |
| J60155 | Okadaic acid, 98% [78111-17-8], C ₄₄ H ₈₆ O ₁₃ , F.W. 805.02, Powder, Merck 14,6819, UN3462, RTECS AA8227800, MDL MFCD00083455 | 300micrograms |
| | Application(s): Potent inhibitor of serine/threonine-specific protein phosphatases 1 and 2A (PP1 and PP2A). Does not inhibit tyrosine or alkaline phosphatases |  |
| J61791 | Okadaic acid potassium salt, 98% [155751-72-7], C ₄₄ H ₈₆ KO ₁₃ , F.W. 843.11, Powder, UN3462, MDL MFCD00214356 | 300micrograms |
| | Application(s): Potent inhibitor of serine/threonine-specific protein phosphatases 1 and 2A (PP1 and PP2A). Does not inhibit tyrosine or alkaline phosphatases |  |
| J62463 | Okadaic acid sodium salt, 98% [209266-80-8], C ₄₄ H ₈₆ NaO ₁₃ , F.W. 827.00, Powder, UN3462, MDL MFCD00210208 | 300micrograms |
| | Application(s): Potent inhibitor of serine/threonine-specific protein phosphatases 1 and 2A (PP1 and PP2A). Does not inhibit tyrosine or alkaline phosphatases |  |
| A16663 | Oleic acid, tech. 90% ▲ [cis-9-Octadecenoic acid] [112-80-1], C ₁₈ H ₃₄ O ₂ , F.W. 282.47, m.p. 13-14°, b.p. 286°/100mm, d. 0.887, n _D ²⁰ 1.4610, Merck 14,6828, EINECS 204-007-1, RTECS RG2275000, BRN 1726542, MDL MFCD00064242, † | 1L 5L |
| | Application(s): Potent inhibitor of serine/threonine-specific protein phosphatases 1 and 2A (PP1 and PP2A). Does not inhibit tyrosine or alkaline phosphatases |  |
| 31997 | Oleic acid, 99% ▲ [cis-9-Octadecenoic acid] [112-80-1], C ₁₈ H ₃₄ O ₂ , F.W. 282.47, Liquid, m.p. 13-14°, b.p. 286°/100mm, d. 0.887, n _D ²⁰ 1.4610, Merck 14,6828, EINECS 204-007-1, RTECS RG2275000, BRN 1726542, MDL MFCD00064242, † | 5g 25g 100g |
| | Application(s): Potent inhibitor of serine/threonine-specific protein phosphatases 1 and 2A (PP1 and PP2A). Does not inhibit tyrosine or alkaline phosphatases |  |
| | trans-Oleic acid , see Elaidic acid, A14832, p. 205 Oleic acid cholesteryl ester , see Cholesteryl oleate, A11378, p. 161 Oleum tiglii , see Croton oil, J62367, p. 169 | |
| J61898 | Oligomycin [1404-19-9], C ₄₅ H ₇₄ O ₁₁ , F.W. 791.07, Powder, Merck 14,6833, EINECS 215-767-9, BRN 7615308 | 10mg |
| | Application(s): Inhibits respiration in mitochondria. Also inhibits ATP synthase |  |
| J60211 | Oligomycin A, 99+% [579-13-5], C ₄₅ H ₇₄ O ₁₁ , F.W. 791.07, Powder, Merck 14,6833, EINECS 209-437-3, RTECS RK3328000, BRN 5702132, MDL MFCD00065705 | 10mg 25mg |
| | Application(s): Inhibits growth of molds |  |
| J60388 | Olomoucine, 98% [101622-51-9], C ₁₅ H ₁₈ N ₆ O, F.W. 298.35, Crystalline powder, m.p. 120-130°, MDL MFCD00189360 | 5mg 25mg |
| | Application(s): Selective inhibitor of cdc2, cdk and other cyclin-related kinases | |
| J62860 | Omeprazole, 98% [73590-58-6], C ₁₇ H ₁₆ N ₂ O ₃ S, F.W. 345.42, Powder, m.p. 158-159°, Merck 14,6845, RTECS DD9087000, MDL MFCD00083192 | 1g 5g 25g |
| | Application(s): A proton pump inhibitor |  |
| J65767 | Omi/HtrA2 Protease Inhibitor ▲ [High Temperature Requirement A2 Inhibitor I, 5-((5-(2-Nitrophenyl)furan-2-yl)methyl-ene)-1,3-diphenyl-2-thioxodihydropyrimidine-4,6(1H,5H)-dione] C ₂₇ H ₁₇ N ₃ O ₅ S, F.W. 495.50, Solid | 10mg |
| | Application(s): A proton pump inhibitor | |
| J64018 | Oncrasin 1 ▲ [1-[(4-Chlorophenyl)methyl]-1H-indole-3-carboxaldehyde] [75629-57-1], C ₁₆ H ₁₂ ClNO, F.W. 269.73, Powder, MDL MFCD01051808 | 10mg |
| | Application(s): A proton pump inhibitor | |
| | OPC-13013 , see Cilostazol, 98%, J62301, p. 163 | |

| Stock # | Description | Size |
|---|---|------------------------|
| J62709 | Opiorphin [<i>H-Gln-Arg-Phe-Ser-Arg-OH</i>] [864084-88-8], C ₂₉ H ₄₈ N ₁₂ O ₆ , F.W. 692.78, Powder | 5mg 25mg |
| Application(s): Modulator of mood-related states and pain sensation | | |
| J62743 | Orange G, Electrophoresis Grade [<i>C.I. 16230, Acid Orange 10</i>] [1936-15-8], C ₁₆ H ₁₀ N ₂ Na ₂ O ₅ S, F.W. 452.38, Powder, EINECS 217-705-6, RTECS QJ6500000, BRN 4120705, MDL MFCD00012457, t | 25g 100g 1kg |
| Application(s): Collagen stain for connective tissue | | |
| J60562 | Orange G loading dye (6X), glycerol based Liquid, Note: Contains: 0.25% Orange-G and 30% glycerol in autoclaved DI water, t ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 25ml 50ml |
| J62098 | Orange G/blue dye (6X) Liquid, Note: Contains: 0.25% Orange-G, 0.25% bromophenol blue, 0.25% xylene cyanol FF, 30mM EDTA in autoclaved DI water | 10ml 25ml |
| J61877 | Orange G/blue loading dye (6X) Liquid, Note: Contains: 0.25% Orange-G, 0.25% bromophenol blue, 0.25% xylene cyanol FF, 15% Ficoll, 30mM EDTA in autoclaved DI water | 10ml 25ml |
| B20294 | Orcein, for analysis [1400-62-0], Merck 14,6863, EINECS 215-750-6, MDL MFCD00062310, t | 1g 5g |
| Application(s): Red in acidic pH and blue in alkaline pH | | |
| Orcinol, see 3,5-Dihydroxytoluene, L18567, p. 193 | | |
| J65378 | Orexin A, human C ₁₅₂ H ₂₄₃ N ₄₇ O ₄₄ S ₄ , F.W. 3561.09, Solid | 0.5mg |
| J65811 | Orexin B, canine [<i>Arg-Pro-Gly-Pro-Pro-Gly-Leu-Gln-Gly-Arg-Leu-Gln-Arg-Leu-Leu-Gln-Ala-Ser-Gly-Asn-His-Ala-Ala-Gly-Ile-Leu-Thr-Met-NH2</i>] C ₁₂₅ H ₂₁₃ N ₄₄ O ₃₄ S, F.W. 2908.36, Solid | 0.5mg 1mg |
| J65110 | Orexin B, human ▲ [<i>Arg-Ser-Gly-Pro-Pro-Gly-Leu-Gln-Gly-Arg-Leu-Gln-Arg-Leu-Leu-Gln-Ala-Ser-Gly-Asn-His-Ala-Ala-Gly-Ile-Leu-Thr-Met-NH2</i>] C ₁₂₃ H ₂₁₂ N ₄₄ O ₃₃ S, F.W. 2899.33, Lyophilized powder | 0.5mg 1mg |
| J65275 | Orexin B, mouse, rat [<i>Arg-Pro-Gly-Pro-Pro-Gly-Leu-Gln-Gly-Arg-Leu-Gln-Arg-Leu-Leu-Gln-Ala-Asn-Gly-Asn-His-Ala-Ala-Gly-Ile-Leu-Thr-Met-NH2</i>] [202801-92-1], C ₁₂₆ H ₂₁₄ N ₄₅ O ₃₄ S, F.W. 2935.38, Solid | 0.5mg 1mg |
| J64476 | [Ala₁₁, D-Leu₁₅] Orexin B, human [<i>Arg-Ser-Gly-Pro-Pro-Gly-Leu-Gln-Gly-Arg-Ala-Gln-Arg-Leu-DLeu-Gln-Ala-Ser-Gly-Asn-His-Ala-Ala-Gly-Ile-Leu-Thr-Met-NH2</i>] [532932-99-3], C ₁₂₀ H ₂₀₀ N ₄₄ O ₃₃ S, F.W. 2857.25, Solid | 1mg |
| J62999 | Orlistat, 98% [(-)-Tetrahydrolipstatin, Ro-18-0647] [96829-58-2], C ₂₉ H ₅₃ NO ₅ , F.W. 495.73, Solid, m.p. <50°, Merck 14,6869, RTECS OH3167600, MDL MFCD05662360 | 50mg 100mg 250mg |
| Application(s): Novel inhibitor of fatty acid synthase. Halts tumor cell proliferation and induces tumor cell apoptosis | | |
| H-Orn-OH.HCl, see L-Ornithine hydrochloride, Cell Culture Reagent, J60241, p. 309 | | |
| J63100 | Ornidazole, 99% [1-(3-Chloro-2-hydroxypropyl)-2-methyl-5-nitroimidazole] [16773-42-5], C ₇ H ₁₀ ClN ₃ O ₃ , F.W. 219.63, Powder, m.p. 84-86°, Merck 14,6872, EINECS 240-826-0, RTECS NI5460000, MDL MFCD00057960 ! H:H302, P:P264-P270-P301+P312-P330-P501 | 5g 25g |
| Application(s): Interferes with electron transport in metabolic pathways | | |
| A18173 | DL-Ornithine monohydrochloride, 99% [(+/-)-2,5-Diaminopentanoic acid hydrochloride, H-DL-Orn-OH.HCl] [1069-31-4], C ₅ H ₁₂ N ₂ O ₂ .HCl, F.W. 168.62, m.p. ca 225° dec., EINECS 213-956-0, BRN 4153338, MDL MFCD00065398, t | 5g 25g 50g |
| L00793 | D-Ornithine hydrochloride, 98+% [(R)-(-)-2,5-Diaminopentanoic acid hydrochloride, H-D-Orn-OH.HCl] [16682-12-5], C ₅ H ₁₂ N ₂ O ₂ .HCl, F.W. 168.62, m.p. 237° dec., [α] _D ²⁰ -23° (c=5 in 5N HCl), EINECS 240-729-3, BRN 4153339, MDL MFCD00012917 | 1g 5g |





| Stock # | Description | Size |
|---------|---|---|
| A12111 | L-Ornithine hydrochloride, 99% [(S)-(+)-2,5-Diaminopentanoic acid hydrochloride, H-Orn-OH.HCl] [3184-13-2], C ₅ H ₁₂ N ₂ O ₂ .HCl, F.W. 168.62, m.p. ca 238° dec., [α] _D ²⁰ +23° (c=5 in 5N HCl), Merck 14.6874, EINECS 221-678-6, RTECS RM2985000, BRN 3625847, MDL MFCD00064562, † | 25g |
| | | 100g |
| | | 500g |
| |  | |
| J60241 | L-Ornithine hydrochloride, Cell Culture Reagent [(S)-(+)-2,5-Diaminopentanoic acid hydrochloride, H-Orn-OH.HCl] [3184-13-2], C ₅ H ₁₂ N ₂ O ₂ .HCl, F.W. 168.62, White crystalline powder, m.p. ca 238° dec., Merck 14,6874, EINECS 221-678-6, RTECS RM2985000, BRN 3625847, MDL MFCD00064562, † | 50g |
| | | 100g |
| | | 250g |
| A18594 | Orotic acid hydrate, 98% [1,2,3,6-Tetrahydro-2,6-dioxypyrimidine-4-carboxylic acid hydrate, Uracil-4-carboxylic acid hydrate] [50887-69-9], C ₄ H ₄ N ₂ O ₄ .xH ₂ O, F.W. 156.10(anhy), m.p. >300°, Merck 14,6876, EINECS 200-619-8, BRN 383901, MDL MFCD00006027, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 50g |
| | | 250g |
| | |  |
| B25349 | Orotic acid, anhydrous, 97% [1,2,3,6-Tetrahydro-2,6-dioxypyrimidine-4-carboxylic acid, Uracil-4-carboxylic acid] [65-86-1], C ₄ H ₄ N ₂ O ₄ , F.W. 156.10, m.p. 344-347°, EINECS 200-619-8, RTECS RM3180000, MDL MFCD00006027, † ! H:H302-H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P501a | 100g |
| | | 500g |
| | |  |
| | Orthoboric acid , see Boric acid, 33253, p. 134 | |
| A18067 | Orthophosphoric acid, 85% aq. soln. [Phosphoric acid (ortho)] [7664-38-2], H ₃ PO ₄ , F.W. 98.00, m.p. 19-21°, d. 1.700, n _D ²⁰ 1.4310, Merck 14,7344, Fieser 1,860 4,387 7,255 10,317 15,266, UN1805, EINECS 231-633-2, RTECS TB6300000, MDL MFCD00011340, † H:H314, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 500ml |
| | | 2.5L |
| | | 10L |
| 33266 | Orthophosphoric acid, 85% w/w aq. soln., ACS [Phosphoric acid (ortho)] [7664-38-2], H ₃ PO ₄ , F.W. 98.00, Liquid, m.p. 19-21°, d. 1.70, Merck 14,7344, Fieser 1,860 4,387 7,255 10,317 15,266, UN1805, EINECS 231-633-2, RTECS TB6300000, MDL MFCD00011340, † Maximum level of impurities: Color (APHA) 10, Insoluble matter 0.001%, Cl 3ppm, NO ₂ 5ppm, SO ₂ 0.003%, Volatile acids (as CH ₃ COOH) 0.001%, Sb 0.002%, Ca 0.002%, Mg 0.002%, As 1ppm, Heavy Metals (as Pb) 0.001%, Fe 0.003%, Mn 0.5ppm, K 0.005%, Na 0.025%, Red H:H314, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 100g |
| | | 1kg |
| | | 4x1kg |
| J65012 | Osteocalcin (1-49), human C ₂₈₈ H ₃₇₉ N ₈₈ O ₈₁ S ₂ , F.W. 5925.41, Solid | 1mg |
| J65386 | Osteocalcin (7-19), human [Gly-Ala-Pro-Val-Pro-Tyr-Pro-Asp-Pro-Leu-Glu-Pro-Arg] [120944-72-1], C ₆₅ H ₈₈ N ₁₆ O ₁₉ , F.W. 1407.57, Solid, MDL MFCD00133727 | 1mg 5mg |
| J65959 | Osteocalcin (45-49), human [Phe-Tyr-Gly-Pro-Val] [85679-70-5], C ₂₀ H ₃₀ N ₅ O ₇ , F.W. 581.66, Solid, MDL MFCD00076322 | 10mg |
| | | 25mg |
| J64816 | Osteocalcin, human, intact, Enzyme Immunoassay Kit Note: One kit contains all the necessary reagents and a 96-well strip plate to perform an ELISA for intact human osteocalcin. Application(s): For detection of osteocalcin. Detection range is 1.0-50ng/ml | 1kit |
| J64764 | Osteocalcin, human, mid-tact, Enzyme Immunoassay Kit Note: One kit contains all the necessary reagents and a 96-well strip plate to perform an ELISA for mid-tact human osteocalcin. Application(s): For detection of osteocalcin. Detection range is 1.0-50ng/ml | 1kit |
| J65214 | Osteocalcin, rat, Enzyme Immunoassay Kit Note: One kit contains all the necessary reagents and a 96-well strip plate to perform an ELISA for rat osteocalcin. Application(s): For detection of rat osteocalcin. Detection range is 0.3-20ng/ml | 1kit |
| J64231 | Osteocalcin, rat, 99.9% | 10micrograms |
| J64239 | Osteocalcin, mouse, Enzyme Immunoassay Kit Note: One kit contains all the necessary reagents and a 96-well strip plate to perform an ELISA for mouse osteocalcin. Application(s): For detection of mouse osteocalcin. Detection range is 1.0-50ng/ml | 1kit |
| | Otercil potassium , see Oxonic acid potassium salt, J60400, p. 310 | |

| Stock # | Description | Size |
|--|---|--|
| J60724 | Ouabain octahydrate, 98% ▲ [<i>γ</i> -Strophanthin] [11018-89-6], C ₂₈ H ₄₄ O ₁₂ ·8H ₂ O, F.W. 728.78 (584.66anhy), Powder, UN1544, RTECS RN3675000, BRN 101712, MDL MFCD00149240  H:H301-H330-H373, P:P301+P310-P304+P340-P320-P330-P405-P501a | 1g 5g |
| Application(s): Inhibitor of sodium-potassium-dependent ATPase | | |
| 7-Oxabicyclo [2.2.1] heptane-2,3-dicarboxylic acid, see Endothal, J60948, p. 206 | | |
| J62250 | 1H-[1,2,4]Oxadiazolo[4,3-a]-quinoxalin-1-one, 99+% [ODQ] [41443-28-1], C ₈ H ₅ N ₃ O ₂ , F.W. 187.15, Powder, m.p. 160-170°, MDL MFCD00792620  H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10mg 50mg |
| Application(s): Selective inhibitor of nitric oxide-sensitive guanylyl cyclase | | |
| 33262 | Oxalic acid dihydrate, ACS, 99.5-102.5% [6153-56-6], HO ₂ CCO ₂ H·2H ₂ O, F.W. 126.07 (90.04anhy), Crystalline, m.p. 101-105°, d. 1.65, Merck 14,6911, Fieser 1,764, Solubility: Very soluble in water. Moderately soluble in ethanol. Sparingly soluble in ether, UN3261, EINECS 205-634-3, RTECS K11600000, BRN 3679436, MDL MFCD00149102, † Maximum level of impurities: Insoluble matter 0.005%, Residue after ignition 0.01%, Cl 0.002%, SO ₂ 0.005%, Ca 0.001%, Nitrogen compounds (as N) 0.001%, Heavy Metals (as Pb) 5ppm, Fe 2ppm, Substances darkened by hot sulfuric acid P.T.  H:H302-H312, P:P280-P302+P352-P322-P301+P312-P312-P501a | 50g 250g 1kg 5kg |
| Application(s): As an analytical reagent, in dye and paint industries, in polymers, in metal treatment, in cleaning and textile finishing, and as a reagent for dehydration and condensation | | |
| A12739 | Oxalacetic acid, 97% [2-Oxobutanedioic acid, 2-Oxosuccinic acid] [328-42-7], C ₄ H ₄ O ₅ , F.W. 132.07, m.p. 161° dec., f.p. 88° (190°F), Merck 14,6909, UN3261, EINECS 206-329-8, BRN 1705475, MDL MFCD00002592, †  H:H314, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a Substrate for citrate synthase. |  5g 25g 100g |
| 15789 | Oxalacetic acid, 98+% [328-42-7], C ₄ H ₄ O ₅ , F.W. 132.07, Powder, m.p. 161° dec., f.p. 88° (190°F), Merck 14,6909, UN3261, EINECS 206-329-8, BRN 1705475, MDL MFCD00002592, †  H:H314, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 2g 10g |
| 44410 | Oxalic acid, anhydrous, 98% [144-62-7], HO ₂ CCO ₂ H, F.W. 90.04, Crystalline, m.p. ca 185° dec., d. 1.9 ¹⁷ , Merck 14,6911, UN3261, EINECS 205-634-3, RTECS RO2450000, BRN 385686, MDL MFCD00002573, †  H:H302-H312, P:P280-P302+P352-P322-P301+P312-P312-P501a | 50g 250g |
| Oxalic acid sodium salt, see Sodium oxalate, A11648, p. 347 | | |
| Oxine, see 8-Hydroxyquinoline, A1272, p. 251 | | |
| 2-Oxo-2H-1-benzopyran-3-carboxylic acid, see Coumarin-3-carboxylic acid, L07133, p. 168 | | |
| 2-Oxobutanedioic acid, see Oxalacetic acid, A12739, p. 310 | | |
| H27294 | 4-Oxocyclohexanecarboxylic acid, 98% [Cyclohexanone-4-carboxylic acid] [874-61-3], C ₇ H ₁₀ O ₃ , F.W. 142.16, MDL MFCD00102035  H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a |  250mg 1g |
| 2-Oxoglutaric acid, see 2-Ketoglutaric acid, A10256, p. 263 | | |
| J60400 | Oxonic acid potassium salt [Allantoxanic acid potassium salt, Otercil potassium] [2207-75-2], C ₄ H ₂ KN ₃ O ₄ , F.W. 195.18, Powder, m.p. 300°, EINECS 218-627-5, RTECS RR4580000, MDL MFCD00010565 | 5g 25g 100g |
| Application(s): Inhibitor of uricase | | |
| 2-Oxopropionic acid, see Pyruvic acid, A13875, p. 333 | | |
| 2-Oxosuccinic acid, see Oxalacetic acid, A12739, p. 310 | | |
| L-(-)-2-Oxothiazolidine-4-carboxylic acid, see (R)-(-)-2-Oxothiazolidine-4-carboxylic acid, J62254, p. 310 | | |
| J62254 | (R)-(-)-2-Oxothiazolidine-4-carboxylic acid [L-(-)-Thiazolidin-2-one-4-carboxylic acid, L-(-)-2-Oxothiazolidine-4-carboxylic acid] [19771-63-2], C ₄ H ₅ NO ₃ S, F.W. 147.15, Powder, m.p. 174° dec., Merck 14,6950, RTECS XJ5426650, BRN 4179169, MDL MFCD00066092  H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1g 5g |
| Application(s): Reagent for hepatic glutathione studies. | | |
| 2,2'-Oxydiethanol, see Diethylene glycol, A14728, p. 189 | | |
| Oxypurinol, see 4,6-Dihydroxypyrazolo[3,4-d]pyrimidine, L07160, p. 193 | | |
| J62427 | Oxytetracycline, 98+% [79-57-2], C ₂₂ H ₂₄ N ₂ O ₉ , F.W. 460.43, Powder, m.p. 184-185°, Merck 14,6976, EINECS 201-212-8, RTECS Q17875000, MDL MFCD00003700, †  H:H301, P:P264-P270-P301+P310-P321-P405-P501a | 10g 50g 100g |
| Application(s): Impairs mitochondrial protein synthesis | | |


| Stock # | Description | Size |
|---------|---|-----------------------|
| J62489 | Oxytetracycline hydrochloride ▲ △ [2058-46-0], C ₂₂ H ₂₄ N ₂ O ₉ ·HCl, F.W. 496.90, Crystalline powder, m.p. 180°, Merck 14,6976, EINECS 218-161-2, RTECS Ql8225000, BRN 3853107, MDL MFCD00135815, † | 25g 100g |
| | Application(s): Impairs mitochondrial protein synthesis | |
| J63421 | Oxytocin, 96% [Cys-Tyr-Ile-Gln-Asn-Cys-Pro-Leu-Gly-NH ₂] [50-56-6], C ₄₃ H ₆₆ N ₁₂ O ₁₂ S ₂ , F.W. 1007.19, Lyophilized powder, Merck 14,6979, UN2811, EINECS 200-048-4, RTECS RS7534000 | 5mg 25mg |
| | ! H: H300-H361, P: P281-P301+P310-P321-P308+P313-P405-P501a | |
| | Application(s): Peptide hormone that acts predominantly as a neurotransmitter; stimulates uterine contraction and lactation | |
| J65848 | p21-Activated Kinase Inhibitor III, IPA-3 ▲ [PAK Inhibitor III, 1,1'-Disulfanediylbis(naphthalen-2-ol)] [42521-82-4], C ₂₀ H ₁₄ O ₂ S ₂ , F.W. 350.50, Solid, UN3077, MDL MFCD00388917 | 5mg 10mg |
| | ! H: H318-H410, P: P280-P273-P305+P351+P338-P310-P391-P501 | |
| | PABA , see 4-Aminobenzoic acid sodium salt, 99%, J63428, p. 92 | |
| J62734 | Paclitaxel, 99.5+% [33069-62-4], C ₄₇ H ₅₁ NO ₁₄ , F.W. 853.91, Crystalline solid, m.p. 213° dec., Merck 14,6982, RTECS DA8340700, BRN 1420457, MDL MFCD00869953, Note: Isolated from <i>Taxus brevifolia</i> | 100mg 500mg 1g |
| | ! H: H334-H341-H361-H318-H302-H312-H332-H335-H315-H317, P: P285-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Application(s): Promotes assembly and inhibits disassembly of microtubules (anti-cancer agent) | |
| J60091 | Palatinose hydrate, 98+% [6-O-α-D-Glucopyranosyl-D-fructose, Isomaltulose] [13718-94-0], C ₁₂ H ₂₂ O ₁₁ ·xH ₂ O, F.W. 342.30, Powder, m.p. 122-124°, Merck 14,5182, EINECS 237-282-1, RTECS LS7175420, BRN 1757215, MDL MFCD00076094 | 25g 100g |
| B20322 | Palmitic acid, 95% [Hexadecanoic acid] [57-10-3], CH ₃ (CH ₂) ₁₄ COOH, F.W. 256.43, m.p. 60-62°, b.p. 215°/15mm, f.p. 206°(402°F), d. 0.853, n _D ²⁰ 1.4273, Merck 14,6996, EINECS 200-312-9, RTECS RT4550000, BRN 607489, MDL MFCD00002747, † | 500g 2.5kg 10kg |
| | ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Application(s): A saturated fatty acid | |
| A15207 | Pamoic acid, 99% [Embonic acid, 4,4'-Methylenebis(3-hydroxy-2-naphthoic acid)] [130-85-8], C ₂₂ H ₁₆ O ₆ , F.W. 388.38, m.p. >300°, Merck 14,7005, Solubility: Soluble in nitrobenzene, pyridine, EINECS 204-998-0, RTECS QL2180000, BRN 901319, MDL MFCD00004079, † | 50g 250g |
| | ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Application(s): Used in preparation of repository derivatives of medicinal agents | |
| |  | |
| J62162 | Pancreatin, porcine pancreas [Pancreatin from porcine pancreas] [8049-47-6], Lyophilized powder, Merck 14,7006, EINECS 232-468-9, RTECS RT9033000, MDL MFCD00131789, Note: Pancreatin will convert not less than 25 times its weight of potato starch into soluble carbohydrates in 5 minutes in water at 40 °C, will digest not less than 25 times its weight of casein in 60 minutes at pH7.5 at 40 °C and will release not less than 2, † | 250g 1kg |
| | ! H: H334-H335-H315-H319, P: P285-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Application(s): Hydrolyzes starch into dextrins and sugar | |
| | Pancreatopeptidase E , see Elastase, porcine pancreas, J61874, p. 205 Pancreatopeptidase E , see Elastase, porcine pancreas aqueous suspension, J61753, p. 205 | |
| A18499 | D-Panthenol, 98+% ■ [Dexpanthenol, Provitamin B] [81-13-0], C ₈ H ₁₅ NO ₃ , F.W. 205.26, b.p. 118-120°/0.02m, f.p. 159°(318°F), d. 1.162, n _D ²⁰ 1.4990, [α] _D ²⁰ -30° (c=5 in water), Merck 14,2947, EINECS 201-327-3, RTECS ES4316000, BRN 1724947, MDL MFCD00065006, † | 100g 500g |
| |  | |
| A16609 | D-Pantothenic acid calcium salt hydrate, 98% ■ [Calcium D-pantothenate hydrate] [331748-07-3], C ₁₈ H ₃₂ CaN ₂ O ₁₀ ·xH ₂ O, F.W. 476.54(anhy), m.p. ca 138° dec., [α] _D ²⁰ +27° (c=5 in water), Merck 14,7015, EINECS 205-278-9, RTECS RU4375000, BRN 3769272, MDL MFCD00002766, † | 100g 500g |
| |  | |
| | Application(s): Vitamin B-5 | |
| | D-Panthenol , see D-Panthenol, A18499, p. 311 | |
| J61875 | Papain, Carica Papaya Latex [EC 3.4.22.2] [9001-73-4], Lyophilized powder, 23 kDa, Merck 14,7016, EINECS 232-627-2, RTECS RU4950000, MDL MFCD00131791, Note: Activates to at least 15 units per mg protein. One unit hydrolyzes one micromole of benzoyl-L-arginine ethyl ester per minute at 25°C and pH 6.2 after activation in a solution containing 1.1 mM EDTA, 0.067 mM mercaptoethanol and 5.5 mM cysteine-HCl for 30, † | 25mg 100mg 1g |
| | ! H: H315-H319-H334-H335, P: P285-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): A cysteine protease; breaks down intercellular matrix of cartilage | |

| Stock # | Description | Size |
|---------|--|-----------------------|
| L04152 | Papaverine, 97% ▲ [58-74-2], C ₂₀ H ₂₁ NO ₄ , F.W. 339.38, m.p. 146-147°, Merck 14,7019, EINECS 200-397-2, RTECS NW8450000, BRN 312930, MDL MFCD00024138 ! H:H302, P:P264-P270-P301+P312-P330-P501a | 5g 25g |
| | Application(s): A phosphodiesterase inhibitor | |
| B25412 | Papaverine hydrochloride, 99% ▲ [1-(3,4-Dimethoxybenzyl)-6,7-dimethoxyisoquinoline hydrochloride] [61-25-6], C ₂₀ H ₂₁ NO ₄ ·HCl, F.W. 375.85, m.p. ca 220° dec., Merck 14,7019, EINECS 200-502-1, RTECS NW8575000, MDL MFCD00012745, † ! H:H302, P:P264-P270-P301+P312-P330-P501a | 5g 25g |
| | Application(s): A phosphodiesterase inhibitor | |
| | Paracetamol , see 4-Acetamidophenol, A11240, p. 70 | |
| J61899 | Paraformaldehyde, 4% in PBS Liquid ! H:H318-H351-H317-H315, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250ml 500ml |
| J62478 | Paraformaldehyde, 4% in PBS + Mg + EGTA Liquid, Note: 4% Paraformaldehyde in PBS with 2mM magnesium chloride and 5mM EGTA ! H:H318-H351-H317-H315, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250ml 500ml |
| | Application(s): For histology. | |
| J61984 | Paraformaldehyde fixative solution Liquid, Note: Contains 3.7 % (w/v) paraformaldehyde and 3 % (w/v) sucrose in PBS, pH 7.4., † ! H:H351-H317, P:P261-P280-P302+P352-P321-P405-P501a | 250ml 500ml |
| J61274 | Paromomycin sulfate [1263-89-4], C ₂₃ H ₄₅ N ₅ O ₁₄ ·H ₂ SO ₄ , F.W. 713.71, White to off-white powder, Merck 14,7041, EINECS 215-031-7, RTECS WK2320000, BRN 5715182, MDL MFCD00079278 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 1g 5g 25g |
| | Application(s): Inhibits initiation and elongation during protein synthesis | |
| J64413 | PARP Inhibitor VIII, PJ34 ▲ ■ [2-Dimethylamino-N-(6-oxo-5,6-dihydrophenanthridin-2-yl)acetamide dihydrochloride] [344458-15-7], C ₁₇ H ₁₇ N ₃ O ₂ ·2HCl, F.W. 352.26, Solid | 5mg 25mg |
| J61341 | Paxilline, 97+% [57186-25-1], C ₂₇ H ₃₃ NO ₄ , F.W. 435.56, Powder, UN2811, RTECS DJ2830000, MDL MFCD00083464 ! H:H301-H311-H330-H318-H315-H335, P:P301+P310-P304+P340-P305+P351+P338-P320-P330-P361-P405-P501a | 5mg 25mg |
| | Application(s): Potent blocker of high-conductance calcium-activated potassium (BKCa) channels | |
| J62470 | Pazopanib, 99+% [GW-786034] [444731-52-6], C ₂₁ H ₂₃ N ₃ O ₃ S, F.W. 437.52, Powder, m.p. 309-311°, RTECS DB2356200 | 25mg 50mg 100mg |
| | Application(s): Second generation multi-targeted tyrosine kinase receptor inhibitor | |
| | PCMX , see 4-Chloro-3,5-dimethylphenol, B21964, p. 155 | |
| J60502 | PCO-400 [Potassium Channel Opener] [121055-10-5], C ₁₇ H ₁₇ NO ₄ , F.W. 299.33, Solid | 20mg 100mg |
| | Application(s): A potassium channel activator | |
| J65158 | PD 151746 ▲ [3-(5-Fluoro-3-indolyl)-2-mercapto-(Z)-2-propenoic acid] [179461-52-0], C ₁₁ H ₈ FNO ₂ , F.W. 237.30, Solid | 5mg |
| | PD-183805 , see Canertinib dihydrochloride salt, 99+%, J63750, p. 145 | |
| J61021 | Pectin Citrus [Poly-D-galacturonic acid methyl ester] [9000-69-5], Powder, Merck 14,7063, EINECS 232-553-0, RTECS RX4280000, MDL MFCD00081838, † | 100g 500g |
| J63408 | Pectinase, Aspergillus niger [EC 4.2.2.10] [9032-75-1], Powder, EINECS 232-885-6, Note: Minimum 20 units per mg dry weight. One unit releases 1 micromole of D-galacturonic acid from polygalacturonic acid per minute at 37°C and pH 5.0, † | 250mg 1g |
| | Pelargonic acid cholesteryl ester , see Cholesteryl nonanoate, L02857, p. 161 | |
| | Penetrex® The Clorox Company , see Enoxacin, J61912, p. 207 | |






| Stock # | Description | Size |
|---------|---|-------|
| B24710 | DL-Penicillamine, 97+% [3,3-Dimethyl-DL-cysteine, 3-Mercapto-DL-valine] [52-66-4], C ₈ H ₁₅ NO ₂ S, F.W. 149.21, m.p. ca 212° dec., Merck 14,7088, EINECS 200-147-2, RTECS YV9445000, BRN 2039817, MDL MFCD00004856 | 1g |
| | | 5g |
| | | 25g |
| | ! H:H302-H315-H319-H335, P:P280h-P305+P351+P338 Metal chelating agent. | |
| | Application(s): Heavy metal chelating agent | |
| A11446 | D(-)-Penicillamine, 99% [3,3-Dimethyl-D-cysteine, 3-Mercapto-D-valine] [52-67-5], C ₈ H ₁₅ NO ₂ S, F.W. 149.21, m.p. 202-204° dec., [α] _D ²⁰ -63° (c=1 in 1N NaOH), Merck 14,7088, EINECS 200-148-8, RTECS YV9425000, BRN 1722375, MDL MFCD00064302 | 5g |
| | | 25g |
| | | 100g |
| | ! H:H315-H319-H335, P:P280g-P305+P351+P338 | |
| | Application(s): Exogenous nitric oxide synthase (NOS) modulator. Physiological chelating agent for heavy metals | |
| J63901 | Penicillin G potassium salt [Benzylpenicillin potassium salt, Potassium benzylpenicillinate] [113-98-4], C ₁₆ H ₁₇ KN ₂ O ₆ S, F.W. 372.48, Powder, Merck 14,7094, EINECS 204-038-0, RTECS XH9700000, BRN 3832841, MDL MFCD00036193, † | 25g |
| | | 100g |
| | | |
| | ! H:H334-H302-H317, P:P285-P261-P280-P302+P352-P321-P501a | |
| | Application(s): Inhibits bacterial cell wall synthesis | |
| J63032 | Penicillin G sodium salt [Benzylpenicillin sodium salt] [69-57-8], C ₁₆ H ₁₇ N ₂ NaO ₆ S, F.W. 356.37, Powder, Merck 14,7094, EINECS 200-710-2, RTECS XH9800000, BRN 3834217, MDL MFCD00069666 | 5g |
| | | 25g |
| | | 100g |
| | ! H:H334-H317, P:P285-P261-P280-P302+P352-P321-P501a | |
| | Application(s): Inhibits bacterial cell wall synthesis | |
| J62442 | Penicillin V potassium salt [Phenoxymethylpenicillin acid potassium salt] [132-98-9], C ₁₆ H ₁₇ KN ₂ O ₆ S, F.W. 388.48, Powder, Merck 14,7100, EINECS 205-086-5, RTECS XH9275000, BRN 3899451, MDL MFCD00051771, † | 10g |
| | | 25g |
| | | 100g |
| | ! H:H302-H334-H317, P:P285-P261-P280-P302+P352-P501 | |
| | Application(s): Inhibits bacterial cell wall synthesis | |
| J61700 | (R)-3,3,4,4-Pentafluorobutanol C ₄ H ₄ F ₅ O, F.W. 164.07, Liquid | Call |
| | | |
| | | |
| | ! H:H226-H315-H319-H335, P:P210-P241-P303+P361+P353-P305+P351+P338-P405-501 | |
| | Application(s): For synthesis of optically active products | |
| J60988 | (S)-3,3,4,4-Pentafluorobutanol C ₄ H ₄ F ₅ O, F.W. 164.07, Liquid | Call |
| | | |
| | | |
| | ! H:H226-H315-H319-H335, P:P210-P241-P303+P361+P353-P305+P351+P338-P405-501 | |
| | Application(s): For synthesis of optically active products | |
| | (-)-cis-3,3',4',5,7-Pentahydroxyflavone, see (-)-Epicatechin, J61218, p. 208 3,3',4',5,7-Pentahydroxyflavone dihydrate, see Quercetin dihydrate, A15807, p. 333 1,5-Pentanediamine, see 1,5-Diaminopentane, B23039, p. 183 | |
| J63298 | (R)-(-)-2-Pentanol, 97% [31087-44-2], C ₅ H ₁₂ O, F.W. 88.15, Liquid, b.p. 119-120°, f.p. 34° (93°F), d. 0.81, n _D ²⁰ 1.406, UN1105, BRN 4652311, MDL MFCD00065953 | 250mg |
| | | 1g |
| | | |
| | ! H:H226-H332-H335-EUH066, P:P210-P241-P261-P303+P361+P353-P405-P501 | |
| | Application(s): For synthesis of optically active products | |
| L09314 | (S)-(+)-2-Pentanol, 97% [(S)-(+)-Methyl n-propyl carbinol] [26184-62-3], C ₅ H ₁₂ O, F.W. 88.15, b.p. 118-119°, f.p. 33° (91°F), d. 0.810, n _D ²⁰ 1.4060, [α] _D ²⁰ +13.7° (neat), UN1105, RTECS SA4900000, BRN 1718820, MDL MFCD00065952 | 250mg |
| | | 1g |
| | | |
| | ! H:H226-H332-H335-EUH066, P:P210-P241-P261-P303+P361+P353-P405-P501a | |
| | Pentanophenone, see Valerophenone, A10525, p. 390 Pentetic acid, see Diethylenetriaminepentaacetic acid, A10926, p. 189 Pentifylline, see 1-n-Hexylthiobromine, L13597, p. 245 | |
| J61679 | Pepsin, porcine stomach [EC 3.4.23.1, Pepsin A] [9001-75-6], Powder, Merck 14,7146, EINECS 232-629-3, RTECS SC6132000, Note: Minimum 2,500 units/mg. One unit increases absorbance at 280nm by 0.001 per minute at 37°C and pH 2.0, measured as TCA soluble products from denatured hemoglobin, † | 1g |
| | | 5g |
| | | 10g |
| | ! H:H334-H335-H315-H319, P:P285-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Pepsin A, see Pepsin, porcine stomach, J61679, p. 313 | |
















| Stock # | Description | Size |
|---------|---|---------------------|
| J60237 | Pepstatin A, 98% [26305-03-3], C ₂₈ H ₄₈ N ₆ O ₈ , F.W. 685.90, Powder, m.p. 233° dec., Merck 14,7147, EINECS 247-600-0, RTECS SC6155000, BRN 2201362, MDL MFCD00060740 Application(s): Protease inhibitor that acts on pepsin, renin and cathepsin D | 5mg 25mg |
| J60026 | Peroxidase, horseradish [EC 1.11.1.7, HRP] [9003-99-0], Lyophilized powder, EINECS 232-668-6, Note: Minimum 85 units/mg dry weight. One unit decomposes 1 micromole of hydrogen peroxide per minute at 25°C and pH 7.0 using aminoantipyrine and phenol, † | 100mg 1g |
| J65630 | P-Glycoprotein Inhibitor [trans-4-Chloro-N-(3-[3-(4-hydroxy-3-methoxyphenyl)acryloyl]phenyl)benzamide, Permeability Glycoprotein Inhibitor] C ₂₈ H ₁₈ ClNO ₄ , F.W. 407.85, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): Transports a variety of substrates across cellular membranes | 10mg |
| | Pharmasin , see Tylosin tartrate, 98+%, J62633, p. 386 (R)-(+)-sec-Phenethyl alcohol , see (R)-(+)-1-Phenylethanol, L19296, p. 316 (S)-(-)-sec-Phenethyl alcohol , see (S)-(-)-1-Phenylethanol, B21188, p. 316 | |
| 33213 | Phenol, ACS, 99+%, stab. △ [108-95-2], C ₆ H ₅ OH, F.W. 94.11, Crystalline, m.p. 40-43°, b.p. 181°, f.p. 79°(175°F), d. 1.071, Merck 14,7241, Fieser 1,828, UN1671, EINECS 203-632-7, RTECS SJ3325000, BRN 969616, MDL MFCD00002143, † Maximum level of impurities: Clarity of solution P.T., Evaporation residue 0.05%, H ₂ O 0.5%, Freezing point ≥ 40.5° ☞☞☞ H:H301-H311-H331-H314-H341-H373, P:P301+P310-P303+P361+P353-P305+P351+P338-P361-P405-P501a | 100g 500g 2kg |
| J64011 | Phenol, ultrapure, 99% △ [108-95-2], C ₆ H ₅ OH, F.W. 94.11, Crystalline, m.p. 40-43°, b.p. 181°, f.p. 79°(175°F), d. 1.071, Merck 14,7241, UN1671, EINECS 203-632-7, RTECS SJ3325000, BRN 969616, MDL MFCD00002143, † | 100g 500g |
| 44526 | Phenol, 99.5%, unstab. ■ [108-95-2], C ₆ H ₅ OH, F.W. 94.11, Solid melt, m.p. 40-43°, b.p. 181°, f.p. 79°(175°F), d. 1.071, Merck 14,7241, Fieser 1,828, UN1671, EINECS 203-632-7, RTECS SJ3325000, BRN 969616, MDL MFCD00002143, Note: Doubly distilled., † ☞☞☞ H:H301-H311-H331-H314-H341-H373, P:P301+P310-P303+P361+P353-P305+P351+P338-P361-P405-P501a Application(s): Molecular biology | 100g |
| J62336 | Phenol:Chloroform:Isoamyl alcohol 25:24:1, Ready-to-use saturated aq. soln., pH 5.2, with alkaline buffer [136112-00-0], Liquid, UN2922, MDL MFCD00133763 ☞☞☞ H:H331-H314-H341-H351-H373-H302-H312, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a Application(s): Useful for purifying RNA | 100ml 500ml |
| J60331 | Phenol:Chloroform:Isoamyl alcohol 25:24:1, Ready-to-use saturated aq. soln., pH 6.7, with alkaline buffer [136112-00-0], Liquid, UN2922, MDL MFCD00133763 ☞☞☞ H:H331-H314-H341-H351-H373-H302-H312, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a Application(s): Useful for purifying RNA | 100ml 400ml |
| J63452 | Phenol:Chloroform 1:1, Ready-to-use soln., pH 6.7, with alkaline buffer Liquid, UN2922 ☞☞☞ H:H331-H314-H341-H351-H373-H302-H312, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a Application(s): Useful for purifying RNA | 100ml 1L |
| A17135 | Phenolphthalein, 98% [77-09-8], C ₂₀ H ₁₄ O ₄ , F.W. 318.33, m.p. 258-262°, d. 1.299, Merck 14,7243, EINECS 201-004-7, RTECS SM8380000, BRN 284423, MDL MFCD00005913, † ☞ H:H350-H341-H361f, P:P281-P201-P202-P308+P313-P405-P501a Acid-base indicator: pH 8.0 - 10.0. | 50g 250g 1kg |
| 38705 | Phenolphthalein, ACS [77-09-8], C ₂₀ H ₁₄ O ₄ , F.W. 318.33, Powder, m.p. 258-262°, d. 1.299, Merck 14,7243, Solubility: Soluble in alcohol. Slightly soluble in ether, EINECS 201-004-7, RTECS SM8380000, BRN 284423, MDL MFCD00005913, † Specifications: Clarity of alcohol solution P.T., Visual transition interval from pH 8.0 (colorless) to 10.0 (red) ☞ H:H350-H341-H361f, P:P281-P201-P202-P308+P313-P405-P501a Application(s): Indicator | 100g 500g |











| Stock # | Description | Size |
|--|---|-----------------------------------|
| 38703 | Phenolphthalein, 0.5% w/v in alcohol [77-09-8], C ₂₀ H ₁₄ O ₄ , F.W. 318.33, Liquid, f.p. 24° (76°F), d. 0.918, UN1987, EINECS 201-004-7, MDL MFCD00005913, Note: Transition interval: pH 8.0 (colorless) to pH 10.0 (red), † ⚠️⚠️⚠️ H:H225-H350-H371-H302-H312-H332, P:P210-P241-P260-P303+P361+P353-P405-P501a | 500ml 1L |
| 38704 | Phenolphthalein, 1% w/v in alcohol [77-09-8], C ₂₀ H ₁₄ O ₄ , F.W. 318.33, Liquid, UN1986, EINECS 201-004-7, MDL MFCD00005913, Note: Transition interval: pH 8.0 (colorless) to pH 10.0 (red), † ⚠️⚠️⚠️ H:H225-H350-H370-H341, P:P210-P241-P260-P303+P361+P353-P405-P501a | 500ml |
| J61785 | Phenolphthalein, 2% soln. in 95% ethanol [77-09-8], C ₂₀ H ₁₄ O ₄ , F.W. 318.33, Liquid, Merck 14,7243, UN1987, EINECS 201-004-7, MDL MFCD00005913, † ⚠️⚠️⚠️ H:H225-H350-H341-H371, P:P210-P241-P260-P303+P361+P353-P405-P501a | 100ml 1L |
| Application(s): pH indicator | | |
| 16294 | Phenol Red, ACS [Phenolsulfonphthalein, Phenylsulfonephthalein] [143-74-8], C ₁₉ H ₁₃ O ₅ S, F.W. 354.38, Crystalline, m.p. >300°, Merck 14,7247, Solubility: Practically insoluble in chloroform, ether. Soluble in aqueous alkali hydroxides or carbonates with red color (removed by boiling with zinc dust). Solubility in water: approximately 1g/1300ml. Solubility in alcohol: approximately 1g/350ml, EINECS 205-609-7, RTECS SJ7490000, BRN 326470, MDL MFCD00003552, † Specifications: Clarity of solution P.T., Visual transition interval from pH 6.8 (yellow) to 8.2 (red) ⚠️ H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 5g 25g 100g |
| Application(s): pH indicator | | |
| 38702 | Phenol Red sodium salt, 0.02% w/v aq. soln. C ₁₉ H ₁₃ NaO ₅ S, F.W. 376.37, Liquid, d. 0.972, EINECS 252-057-8, MDL MFCD00066901, Note: Transition interval: pH 6.8 (yellow) to pH 8.2 (red), † | 100ml 500ml 6x100ml |
| 15987 | Phenol Red sodium salt, ACS [34487-61-1], C ₁₉ H ₁₃ NaO ₅ S, F.W. 376.37, Crystalline, m.p. 285° dec., Merck 14,7247, EINECS 252-057-8, BRN 6260026, MDL MFCD00066901, † Specifications: Clarity of solution P.T., Visual transition interval from pH 6.8 (yellow) to 8.2 (red) ⚠️ H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 5g 25g |
| Application(s): pH indicator | | |
| Phenolsulfonphthalein, see Phenol Red, 16294, p. 315 | | |
| A12517 | Phenothiazine, 98+% ▲ [92-84-2], C ₁₅ H ₉ NS, F.W. 199.28, m.p. 182-186°, b.p. 235°/21mm, Merck 14,7252, EINECS 202-196-5, RTECS SN5075000, BRN 143237, MDL MFCD00005015, † ⚠️ H:H319-H317-H412, P:P261-P280-P305+P351+P338-P302+P352-P321-P501a Lithiation in THF gives orange crystals of (phenothiazin-10-yl)lithium.3THF. Carboxylation and the orientation of a second lithiation have been studied: <i>Angew. Chem. Int. Ed.</i> , 34 , 921 (1995). | 250g 500g 5kg |
| Application(s): Acts on type I calcium/calmodulin dependent phosphodiesterase | | |
| Phenoxyacetic acid ethyl ester, see Ethyl phenoxyacetate, A14156, p. 217 | | |
| J61900 | Phenoxybenzamine hydrochloride [63-92-3], C ₁₆ H ₂₀ ClNO, F.W. 340.29, Powder, Merck 14,7256, EINECS 200-569-7, RTECS DP3750000, MDL MFCD00055152 ⚠️⚠️ H:H302-H351, P:P281-P264-P301+P312-P308+P313-P405-P501 | 250mg 1g |
| Application(s): Selective α adrenergic blocking agent. Irreversible calmodulin inhibitor | | |
| Phenoxymethylpenicillinic acid potassium salt, see Penicillin V potassium salt, J62442, p. 313 | | |
| 2-Phenylacetohydrazide, see N-Acetyl-N'-phenylhydrazine, A14446, p. 74 | | |
| A10132 | DL-Phenylalanine, 99% [(+/-)-2-Amino-3-phenylpropionic acid, H-DL-Phe-OH] [150-30-1], C ₉ H ₉ NO ₂ , F.W. 165.19, m.p. ca 266° dec., Merck 14,7271, EINECS 205-756-7, BRN 1910407, MDL MFCD00064225, † | 25g 100g 500g |
| A10572 | D-Phenylalanine, 99% [(R)-2-Amino-3-phenylpropionic acid, H-D-Phe-OH] [673-06-3], C ₉ H ₉ NO ₂ , F.W. 165.19, m.p. ca 275° dec., [α] _D ²⁰ +34° (c=2 in water), Merck 14,7271, EINECS 211-603-5, RTECS AY7533000, BRN 2804068, MDL MFCD00004270, † | 5g 25g 100g |
| A13238 | L-Phenylalanine, 99% [(S)-2-Amino-3-phenylpropionic acid, H-Phe-OH] [63-91-2], C ₉ H ₉ NO ₂ , F.W. 165.19, m.p. 227° dec., [α] _D ²⁰ -34° (c=2 in water), Merck 14,7271, EINECS 200-568-1, RTECS AY7535000, BRN 1910408, MDL MFCD00064227, † Other amino acids have been resolved by crystallization of their complexes with L-phenylalanine, and decomplexation with activated carbon: <i>Chem. Lett.</i> , 113 (1984). Formation of the N,N-dibenzyl benzyl ester by reaction with benzyl bromide and base, followed by LAH reduction and Swern oxidation, lead to the N,N-dibenzyl (S)-α-amino aldehyde, a useful chiral intermediate: <i>Org. Synth.</i> , 76 , 110 (1998). | 25g 50g 100g 500g 1kg |








| Stock # | Description | Size |
|--|--|----------------------|
| J63925 | L-Phenylalanine, Cell Culture Reagent [63-91-2], C ₉ H ₉ NO ₂ , F.W. 165.19, Powder, Merck 14,7271, EINECS 200-568-1, RTECS AY7535000, BRN 1910408, MDL MFCD00064227, † | 100g 250g 500g |
| J64524 | Phenylalanine Dehydrogenase [EC 1.4.1.20] Lyophilized powder, Note: Component in the Cofactor Recycling Enzymes Kit, item J64535 | 250mg 500mg 1g |
| L09697 | D-Phenylalaninol, 98% Δ [(R)-(+)-2-Amino-3-phenyl-1-propanol, H-D-Phe-ol] [5267-64-1], C ₉ H ₉ NO, F.W. 151.21, m.p. 89-94°, [α] _D ²⁰ +23° (c=5 in ethanol), UN3259, EINECS 226-086-1, BRN 4665408, MDL MFCD00064298  H: H314, P: P280-P303+P361+P353-P305+P351+P338-P310 Has been used as a chiral auxiliary for asymmetric Michael reactions: <i>J. Org. Chem.</i> , 50 , 3863 (1985). | 250mg 1g |
| A11586 | L-Phenylalaninol, 98% Δ [(S)-(-)-2-Amino-3-phenyl-1-propanol, H-Phe-ol] [3182-95-4], C ₉ H ₉ NO, F.W. 151.21, m.p. 89-94°, [α] _D ²⁰ -23° (c=5 in ethanol), UN3259, EINECS 221-674-4, RTECS UA6900000, BRN 2208238, MDL MFCD0004732  H: H314, P: P280-P303+P361+P353-P305+P351+P338-P310 | 1g 5g 25g |
| J60043 | L-Phenylalanyl-L-phenylalanine [H-Phe-Phe-OH, Di-L-Phenylalanine] [2577-40-4], C ₁₈ H ₂₀ N ₂ O ₃ , F.W. 312.37, Powder, EINECS 219-930-5, MDL MFCD00063154 | 1g 5g |
| Application(s): Plays a role in nanotube formation | | |
| J60063 | L-Phenylalanyl-L-proline [H-Phe-Pro-OH] [7669-65-0], C ₁₄ H ₁₈ N ₂ O ₃ , F.W. 262.31, Powder, MDL MFCD00020833 | 1g 5g |
| Application(s): Substrate for skin fibroblast prolidase | | |
| Phenylbenzene, see Biphenyl, A10265, p. 125 4-Phenylbenzoyl chloride, see 4-Biphenylcarbonyl chloride, A13956, p. 125 1-Phenyl-1,3-butanedione, see Benzoylacetone, A14537, p. 121 | | |
| L03449 | Phenylbutazone, 98% [4-Butyl-1,2-diphenyl-3,5-pyrazolidinedione] [50-33-9], C ₁₉ H ₂₀ N ₂ O ₂ , F.W. 308.38, m.p. 105-108°, Merck 14,7277, UN2811, EINECS 200-029-0, RTECS UQ8225000, BRN 290080, MDL MFCD00005500, †  H: H301-H351-H361d-H319, P: P280h-P305+P351+P338-P309-P310 | 25g 100g |
| Application(s): A non-steroidal anti-inflammatory drug | | |
| Phenyl dichlorophosphate, see Phenyl phosphorodichloridate, A10479, p. 317 | | |
| J60354 | o-Phenylenediamine dihydrochloride, 98+% [1,2-Diaminobenzene dihydrochloride] [615-28-1], C ₆ H ₈ N ₂ ·2HCl, F.W. 181.07, Powder, UN2811, EINECS 210-418-7, RTECS ST0175000, BRN 3912045, MDL MFCD00012966, †  | 25g 100g 500g |
| H: H301-H341-H351-H400-H410-H312-H332-H319-H317, P: P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a | | |
| Application(s): A peroxidase substrate for ELISA procedures | | |
| L19296 | (R)-(+)-1-Phenylethanol, ChiPros® 99%, ee 97+% [(R)-(+)-α-Methylbenzyl alcohol, (R)-(+)-sec-Phenethyl alcohol] [1517-69-7], C ₈ H ₁₀ O, F.W. 122.17, m.p. 9-11°, b.p. 88-89°/10mm, f.p. 85° (185°F), d. 1.012, n _D ²⁰ 1.5280, [α] _D ²⁰ +45° (c=5 in methanol), UN2937, BRN 2039798, MDL MFCD00064263  H: H318-H302-H335-H315, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 5g 25g |
| Application(s): For synthesis of optically active products | | |
| B21188 | (S)-(-)-1-Phenylethanol, 99% [(S)-(-)-α-Methylbenzyl alcohol, (S)-(-)-sec-Phenethyl alcohol] [1445-91-6], C ₈ H ₁₀ O, F.W. 122.17, m.p. 9-11°, b.p. 97-99°/20mm, f.p. 85° (185°F), n _D ²⁰ 1.5280, UN2937, BRN 2039797, MDL MFCD00064264  H: H318-H302-H335-H315, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 1g 5g |
| Application(s): For synthesis of optically active products | | |
| Phenylethyl caffeate, see Phenylethyl 3,4-dihydroxycinnamate, 99+%, J61386, p. 316 | | |
| J61386 | Phenylethyl 3,4-dihydroxycinnamate, 99+% [3,4-Dihydroxycinnamic acid phenylethyl ester, Phenylethyl caffeate] [104594-70-9], C ₁₇ H ₁₆ O ₄ , F.W. 284.31, Powder, RTECS UD3334375, MDL MFCD00866470 H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | 250mg 1g |
| Application(s): Inhibitor of protein tyrosine kinase, and is cytotoxic to cancer cell lines | | |
| J64722 | Phenylethyl 3-methylcaffeate [(E)-Phenethyl 3-(4-hydroxy-3-methoxyphenyl)acrylate, CCRIS 7791] [71835-85-3], C ₁₈ H ₁₈ O ₄ , F.W. 298.33, Solid, m.p. 80-81° | 50mg 100mg |



| Stock # | Description | Size |
|---------------|---|--|
| A14182 | N-Phenylglycine, 97% [103-01-5], (C ₈ H ₉)NHCH ₂ CO ₂ H, F.W. 151.17, m.p. 117-119°, Merck 14,7292, EINECS 203-070-2, BRN 509838, MDL MFCD00014009, † | 10g 50g |
| | Application(s): Pharmaceutical intermediate | |
| A15669 | D-(-)-2-Phenylglycine, 99% [D-(-)-α-Aminophenylacetic acid, H-D-Phg-OH] [875-74-1], C ₈ H ₉ NO ₂ , F.W. 151.17, m.p. 277° dec., [α] _D ²⁰ -154° (c=1 in 1N HCl), Merck 14,7291, EINECS 212-876-3, BRN 2208676, MDL MFCD00008061, † |  25g 100g 500g |
| A19360 | L-(+)-2-Phenylglycine, 98+% [(S)-(+)-α-Aminophenylacetic acid, H-Phg-OH] [2935-35-5], C ₈ H ₉ NO ₂ , F.W. 151.17, m.p. 288° dec., [α] _D ²⁰ +156° (c=1 in 1N HCl), Merck 14,7291, Fieser 17,278, EINECS 220-909-8, BRN 2208675, MDL MFCD00064403, † |  25g 100g 500g |
| A19030 | (R)-(-)-2-Phenylglycinol, 98% △ [(R)-(-)-2-Amino-2-phenylethanol, H-D-Phg-ol] [56613-80-0], C ₈ H ₉ NO, F.W. 137.18, m.p. 76-78°, [α] _D ²⁰ -30° (c=0.75 in 1N HCl), Fieser 15,256 17,279, EINECS 260-287-5, BRN 2935848, MDL MFCD00008062 ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a Condensation with glutaraldehyde gives a useful intermediate in asymmetric synthesis of alkaloids: <i>Org. Synth. Coll.</i> , 9 , 176 (1998): |  1g 5g 25g |
| |  Starting material for the enantioselective synthesis of 2,6-disubstituted piperazines: <i>Synthesis</i> , 833 (1996), and for chiral α-amino phosphonates: <i>Org. Synth.</i> , 75 , 19 (1997). | |
| L13265 | (S)-(+)-2-Phenylglycinol, 98+% △ [(S)-(+)-2-Amino-2-phenylethanol, H-Phg-ol] [20989-17-7], C ₈ H ₉ NO, F.W. 137.18, m.p. 76-78°, [α] _D ²⁰ +30° (c=0.75 in 1N HCl), Fieser 15,256, BRN 3196190, MDL MFCD00064404 ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a Reagent for the resolution of acids via the easily hydrolyzed amides: <i>J. Org. Chem.</i> , 51 , 4836 (1986). |  1g 5g 25g |
| | Phenylmethanephosphonic acid , see Benzylphosphonic acid, A13850, p. 123 Phenylmethanesulfonyl fluoride , see α-Toluenesulfonyl fluoride, B22146, p. 371 N-[2-[2-(Phenylmethyl)-1H-indol-3-yl]ethyl]acetamide , see Luzindole, 97%, J61915, p. 273 Phenylmethylsulfonyl fluoride , see α-Toluenesulfonyl fluoride, B22146, p. 371 | |
| A10592 | 2-Phenylphenol, 99% [Biphenyl-2-ol, 2-Hydroxybiphenyl] [90-43-7], C ₁₂ H ₁₀ O, F.W. 170.21, m.p. 54-58°, b.p. 152-154°/15mm, f.p. 124°(255°F), d. 1.293, Merck 14,7304, UN3077, EINECS 201-993-5, RTECS DV5775000, BRN 606907, MDL MFCD00002208, † ! H: H400-H302-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a |  250g 500g 2.5kg 10kg |
| 44711 | Phenyl phosphate disodium salt hydrate, 98% ■ [3279-54-7], C ₆ H ₅ OPO(ONa) ₂ ·xH ₂ O, F.W. 218.06(anhy), Crystalline, Merck 14,3357, EINECS 221-917-4, BRN 4167154, MDL MFCD00002133, † | 25g 100g |
| | Application(s): Used in phosphatase determinations | |
| A10479 | Phenyl phosphorodichloridate, 97% ■ [Phenyl dichlorophosphate] [770-12-7], C ₆ H ₅ Cl ₂ O ₂ P, F.W. 210.98, m.p. -1°, b.p. 241-243°, f.p. 112°(233°F), d. 1.415, n _D ²⁰ 1.5230, Fieser 1,84712,384 13,240 15,255, UN2922, EINECS 212-220-6, RTECS TD4393000, BRN 511863, MDL MFCD00002067, † ! H: H310-H314-H302, P: P260-P303+P361+P353-P305+P351+P338-P361-P405-P501a Reagent for the preparation of phosphate diesters. The phenyl group is removable by hydrogenolysis: <i>J. Am. Chem. Soc.</i> , 75 , 4510 (1953). Coupling reagent, e.g. in pyridine for the preparation of derivatives of sulfinic acids with alcohols, amines, thiols etc.: <i>Synthesis</i> , 937 (1980). Similarly, carboxylic acids in pyridine can be coupled with thiols to give thiocarboxylic acid S-esters: <i>Can. J. Chem.</i> , 58 , 2645 (1980), and with sodium azide in the presence of a phase-transfer catalyst to give acyl azides: <i>Synth. Commun.</i> , 13 , 289 (1983). Reacts with the Li enolates of β-diketones, in the presence of LiCl, to give β-chloro-α,β-enones: <i>Can. J. Chem.</i> , 64 , 520 (1986). In combination with NaI, cleaves dialkyl ethers to iodides in high yield: <i>Synth. Commun.</i> , 18 , 119 (1988), and 1,3-dithianes and other dithioacetals to carbonyl groups: <i>Tetrahedron Lett.</i> , 29 , 5471 (1988). In combination with Dimethyl sulfoxide , A13280, effects selective oxidation of alcohols to aldehydes or ketones with less α-chlorination than the more usual Swern (Oxalyl chloride , A18012) system: <i>J. Org. Chem.</i> , 52 , 5621 (1987). Similarly, benzylamines have been converted to benzaldehydes: <i>Synth. Commun.</i> , 19 , 3407 (1989). For a brief feature on uses of the reagent in synthesis, see: <i>Synlett</i> , 1651 (2004). |  25g 100g 500g |
| | Application(s): Reagent for preparation of phosphate diesters | |

| Stock # | Description | Size |
|---|---|---|
| L05681 | (R)-(+)-1-Phenyl-1-propanol, 99% [(R)-(+)- α -Ethylbenzyl alcohol] [1565-74-8], C ₉ H ₁₂ O, F.W. 136.19, b.p. 217-219°, f.p. 95°(203°F), d. 0.993, n _D ²⁰ 1.5200, [α] _D ²⁰ +47° (c=2.2 in hexane), RTECS DO5470000, BRN 2041555, MDL MFCD00064279 ! H.H302, P:P264-P270-P301+P312-P330-P501a |  100mg 500mg |
| Application(s): For synthesis of optically active products | | |
| L06608 | (S)-(-)-1-Phenyl-1-propanol, 99% [(S)-(-)- α -Ethylbenzyl alcohol] [613-87-6], C ₉ H ₁₂ O, F.W. 136.19, b.p. 217-219°, f.p. 95°(203°F), d. 0.993, n _D ²⁰ 1.5200, [α] _D ²⁰ -47° (c=2.2 in hexane), RTECS DO5470000, BRN 2041556, MDL MFCD00066207 ! H.H302, P:P264-P270-P301+P312-P330-P501a |  100mg 500mg |
| Application(s): For synthesis of optically active products | | |
| L13999 | (R)-(+)-2-Phenyl-1-propanol, 98+% [19141-40-3], C ₉ H ₁₂ O, F.W. 136.19, b.p. 220°, f.p. 108°(226°F), d. 0.975, n _D ²⁰ 1.5260, [α] _D ²⁰ +18° (neat), MDL MFCD00145206 ! H.H302, P:P280f |  250mg |
| Application(s): For synthesis of optically active products | | |
| L13988 | (S)-(-)-2-Phenyl-1-propanol, 98+% [37778-99-7], C ₉ H ₁₂ O, F.W. 136.19, b.p. 220°, f.p. 108°(226°F), d. 0.975, n _D ²⁰ 1.5260, [α] _D ²⁰ -18° (neat), MDL MFCD00145249 ! H.H302, P:P280f |  250mg 1g |
| Application(s): For synthesis of optically active products | | |
| J61693 | (R)-2-Phenylpropionamide [14182-57-1], C ₉ H ₁₁ NO, F.W. 149.19, Solid ! H.H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | Call |
| Application(s): For synthesis of optically active products | | |
| J60150 | (S)-2-Phenylpropionamide [13490-74-9], C ₉ H ₁₁ NO, F.W. 149.19, Solid ! H.H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | Call |
| Application(s): For synthesis of optically active products | | |
| L16319 | (R)-(+)-1-Phenylpropylamine, ChiPros® 99+%, ee 98% Δ [(R)-(+)-1-Amino-1-phenylpropane, (R)-(+)- α -Ethylbenzylamine] [3082-64-2], C ₉ H ₁₃ N, F.W. 135.21, m.p. -69°, b.p. 205°, f.p. 77°(170°F), d. 0.930, n _D ²⁰ 1.5200, [α] _D ²⁰ +20° (neat), UN2735, BRN 3029904, MDL MFCD00083057 ! H.H314-H302-H411, P:P280-P273-P305+P351+P338-P309-P310 |  1g 5g 25g |
| Application(s): For synthesis of optically active products | | |
| L16320 | (S)-(-)-1-Phenylpropylamine, ChiPros® 99+%, ee 99% Δ [(S)-(-)-1-Amino-1-phenylpropane, (S)-(-)- α -Ethylbenzylamine] [3789-59-1], C ₉ H ₁₃ N, F.W. 135.21, m.p. -69°, b.p. 205°, f.p. 77°(170°F), d. 0.930, n _D ²⁰ 1.5200, [α] _D ²⁰ -20° (neat), UN2735, BRN 2412016, MDL MFCD00082356 ! H.H314-H302-H411, P:P280-P273-P305+P351+P338-P309-P310 |  1g 5g 25g |
| Application(s): For synthesis of optically active products | | |
| Phenylsulfonephthalein, see Phenol Red, 16294, p. 315 | | |
| L10991 | Phloretin, 98% [2',4',6'-Trihydroxy-3-(4-hydroxyphenyl)propiophenone] [60-82-2], C ₁₅ H ₁₄ O ₅ , F.W. 274.28, m.p. ca 263° dec., Merck 14,7326, EINECS 200-488-7, BRN 1887240, MDL MFCD00002288 ! H.H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a |  25mg 100mg |
| Application(s): Topical antioxidant | | |
| B25502 | Phloroglucinol, anhydrous, 98% \blacktriangle [1,3,5-Trihydroxybenzene, 1,3,5-Benzenetriol, anhydrous] [108-73-6], C ₆ H ₆ O ₃ , F.W. 126.11, m.p. 215-220°, Merck 14,7328, EINECS 203-611-2, RTECS SY1050000, BRN 1341907, MDL MFCD00002286, † ! H.H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Reacts with mono- or dimethylamine in DMF-water, with displacement of one of the OH groups, to give 5-aminoresorcinols: <i>Helv. Chim. Acta</i> , 56 , 510 (1973). The electron-rich nucleus undergoes acylation with nitriles under mild Lewis acid catalysis, to give ketones (Houben-Hoesch reaction). Selective monobromination cannot be achieved conventionally. For bromination-debromination protocols for the preparation of the mono- and di-brominated derivatives, see: <i>Can. J. Chem.</i> , 67 , 335 (1989). |  50g 250g |
| Application(s): Reagent for pentoses, pentosans and aldehydes. Used as a bone decalcifier in microscopy specimens | | |

| Stock # | Description | Size |
|---------|---|----------------------------|
| J63916 | Phorbol 12-myristate 13-acetate, 99+% ▲ [PMA, TPA] [16561-29-8], C ₃₆ H ₅₆ O ₈ , F.W. 616.83, Film or powder, Merck 14,7332, RTECS QH4377000, BRN 2407201, MDL MFCD00036736 ! H:H315, P:P280-P264-P302+P352-P321-P362-P332+P313 | 1mg 5mg 10mg 25mg |
| | Application(s): Activates protein kinase C and promotes skin tumors in mice. | |
| J61099 | 4α-Phorbol 12-myristate 13-acetate, 99% ▲ [4 α -PMA] [63597-44-4], C ₃₆ H ₅₆ O ₈ , F.W. 616.83, Powder or film, Merck 14,7332, MDL MFCD00153860 | 1mg 5mg |
| | Application(s): Negative control for phorbol ester activation of protein kinase C | |
| J62267 | Phosphatase buffer 1 (5X) Liquid, Note: This buffer contains: 100mM Tris (pH 7.5) and 100mM magnesium chloride. | 100ml 250ml |
| J65354 | Phosphatase Inhibitor Cocktail A Liquid, Note: Contains 2.5mM (-)-p-Bromotetramisole oxalate, 500uM cantharidin and 500nM microcystin-LR | 1unit |
| | Application(s): For use with tissue and cell extracts, including extracts containing detergents | |
| J64651 | Phosphatase Inhibitor Cocktail B ■ Lyophilized solid, UN2811, Note: Reconstitute in 1ml water to make a solution with 200mM imidazole, 100mM sodium fluoride, 115mM sodium molybdate, 100mM sodium orthovanadate and 400mM sodium tartrate !! H:H302-H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P501 | 1unit |
| | Application(s): For the inhibition of protein tyrosine phosphatases, acid- and alkaline-phosphatases | |
| J64216 | Phosphatase Inhibitor Cocktail III ■ Lyophilized solid, Note: One unit contains 250mM sodium fluoride, 5mM sodium orthovanadate, 50mM sodium pyrophosphate and 50mM β -glycerophosphate when reconstituted in 1ml of water ! H:H302+EUH032-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1unit |
| J64084 | Phosphatase Inhibitor Cocktail IV Liquid, Note: 1ml in DMSO. Contains 2.5mM (-)-p-bromotetramisole oxalate, 500uM cantharidin and 1uM calyculin A, Discodermia calyx | 1ml |
| | Application(s): For inhibition of both serine/threonine and alkaline phosphatases | |
| J63907 | Phosphatase Inhibitor Cocktail I Liquid, Note: This cocktail will inhibit acid-, alkaline-, and tyrosine phosphatases and is suitable for cell and tissue lysis. Contains imidazole, sodium fluoride, sodium molybdate, sodium orthovanadate, sodium pyrophosphate, and tartrate. 100X concentrate. Store at -, † ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | 5ml |
| J61022 | Phosphatase Inhibitor Cocktail II Liquid, Note: This cocktail will inhibit broad spectrum of serine/theorine and tyrosine phosphatases and is suitable for cell and tissue lysis. Contains: sodium fluoride, sodium orthovanadate, sodium pyrophosphate, b-glycerophosphate. 100X concentrate. Store at -20 C., † ! H:H302, P:P264-P270-P301+P312-P330-P501a | 5ml |
| | Phosphate acceptor peptide , see Kemptide, J60591, p. 263 | |
| J60467 | Phosphate, 0.2M buffer soln., pH 4.4 [7558-80-7], Liquid, † | 500ml 1L |
| J60325 | Phosphate, 0.2M buffer soln., pH 6.8 [7558-80-7], Liquid, † | 500ml 1L |
| J60669 | Phosphate, 0.2M buffer soln., pH 7.0 [7558-80-7], Liquid, † | 500ml 1L |
| J62899 | Phosphate, 0.2M buffer soln., pH 7.2 [7558-80-7], Liquid, † | 500ml 1L |
| J60380 | Phosphate, 0.2M buffer soln., pH 7.4 [7558-80-7], Liquid, † | 500ml 1L |
| J61324 | Phosphate, 0.2M buffer soln., pH 7.5 [7558-80-7], Liquid, † | 500ml 1L |
| J61870 | Phosphate, 0.2M buffer soln., pH 7.6 [7558-80-7], Liquid, † | 500ml 1L |
| J60480 | Phosphate, 0.2M buffer soln., pH 8.0 [7558-80-7], Liquid, † | 500ml 1L |
| J61925 | Phosphate, 0.2M buffer soln., pH 8.5 [7558-80-7], Liquid, † | 500ml 1L |

| Stock # | Description | Size |
|---------|--|-------------------|
| J63581 | Phosphate, 0.2M buffer soln., pH 9.0 [7558-80-7], Liquid, † | 500ml 1L |
| J60819 | Phosphate, 0.2M buffer soln., pH 9.5 [7558-80-7], Liquid, † | 500ml 1L |
| J60845 | Phosphate, 0.5M buffer soln., pH 6.5 [7558-80-7], Liquid, † | 250ml 500ml |
| J62749 | Phosphate, 0.5M buffer soln., pH 7.0 [7558-80-7], Liquid, † | 250ml 500ml |
| J63974 | Phosphate, 0.5M buffer soln., pH 7.2 [7558-80-7], Liquid, † | 250ml 500ml |
| J60785 | Phosphate, 0.5M buffer soln., pH 7.4 [7558-80-7], Liquid, † | 250ml 500ml |
| J63349 | Phosphate, 0.5M buffer soln., pH 7.5 [7558-80-7], Liquid, † | 250ml 500ml |
| J60197 | Phosphate, 0.5M buffer soln., pH 7.6 [7558-80-7], Liquid, † | 250ml 500ml |
| J61722 | Phosphate, 0.5M buffer soln., pH 8.0 [7558-80-7], Liquid, † | 250ml 500ml |
| J61086 | Phosphate, 0.5M buffer soln., pH 8.5 [7558-80-7], Liquid, † | 250ml 500ml |
| J62345 | Phosphate, 0.5M buffer soln., pH 9.0 [7558-80-7], Liquid, † H:EUH210 | 250ml 500ml |
| J62025 | Phosphate, 0.5M buffer soln., pH 9.5 [7558-80-7], Liquid, † | 250ml 500ml |
| J62694 | Phosphate buffered RIPA Liquid, Note: This product contains: 10mM sodium phosphate (pH 7.2), 150mM sodium chloride, 1% Triton X-100 , 0.5% sodium deoxycholate and 0.1% SDS. | 250ml 500ml |
| J60780 | Phosphate buffered RIPA (2X) Liquid, Note: Contains: 20mM sodium phosphate, 300mM NaCl, 2% Triton X-100,1% sodium deoxycholate, and 0.2% SDS, pH 7.2., † | 125ml 250ml |
| J62939 | Phosphate buffered RIPA with glycerol (2X) Liquid, Note: Contains: 20mM sodium phosphate, 300mM NaCl, 2% Triton X-100,1% sodium deoxycholate, and 0.2% SDS, with 10% glycerol, pH 7.2. | 125ml 250ml |
| J62036 | Phosphate-buffered saline (PBS, 10X), pH 7.4 Liquid, Note: Contains 100mM phosphate buffer, 27mM potassium chloride, and 1.37M sodium chloride at pH 7.4, † | 1L 2L 4L |
| J60801 | Phosphate-buffered saline (PBS, 10X), pH 7.4, for Western blot Liquid, Note: Contains: 100mM phosphate and 1.5M NaCl at pH 7.4 Application(s): For western blot washing. | 1L 2L 4L |
| J62692 | Phosphate-buffered saline (PBS, 10X), pH 7.6 Liquid, Note: Contains 100mM phosphate, 27mM KCl and 1.37M NaCl, pH 7.6. | 1L 2L 4L |
| J62851 | Phosphate-buffered saline (PBS, 10X), RNase free Liquid, † | 250ml 500ml |
| J61917 | Phosphate-buffered saline (DPBS, 10X), Dulbecco's formula Liquid | 500ml 1L 2L |
| J61196 | Phosphate-buffered saline (PBS, 1X), sterile Liquid, Note: 137mM sodium chloride 2.7mM potassium chloride, 10mM Na ₂ HPO ₄ , and 1mM KH ₂ PO ₄ , pH 7.4, † | 500ml |
| J60893 | Phosphate-buffered saline (PBS, 5X), with EDTA Liquid, Note: 5X PBS with 50mM EDTA, pH 7.4 | 1L 2L |


| Stock # | Description | Size |
|---------|---|------------------------|
| J63521 | Phosphate-buffered saline (PBS, 10X), with Triton® X-100 Liquid, Note: 10X formulation with 1% Triton X-100. | 250ml 500ml |
| J60465 | Phosphate-buffered saline (PBS, 10X), no potassium Liquid, Note: Contains 80mM phosphate, 1.37 M NaCl, at pH range 7.4. H:EUH210 | 500ml 1L |
| J62982 | Phosphate-Citrate Buffer (5X) Liquid, Note: Contains 1M sodium phosphate and 0.5M sodium citrate. | 100ml 250ml |
| | L-a-Phosphatidylcholine , see Lecithin, 60%, egg, J60576, p. 268 | |
| J64598 | Phosphodiesterase Inhibitor (IBMX) | 100mg |
| J64453 | Phosphodiesterase 4 Inhibitor ▲ [Ethyl 3,5-dimethyl-1-(3-nitrophenyl)-1H-pyrazole-4-carboxylate] [346440-86-6], C ₁₄ H ₁₃ N ₃ O ₄ , F.W. 289.29, Solid | 5mg 25mg |
| | Phosphoenolpyruvate kinase , see Pyruvate Kinase, rabbit muscle, J61373, p. 333 | |
| J61943 | Phosphoenolpyruvic acid tricyclohexylammonium salt, 99+% [2-(Phosphonoxy)-2-propenoic acid tri(cyclohexylammonium) salt, PEP-tri] [35556-70-8], C ₂₁ H ₃₀ O ₆ P·3C ₆ H ₁₁ N, F.W. 465.58, Powder, EINECS 252-618-7, BRN 3752336, MDL MFCD00004258, † | 1g 5g 25g |
| | Application(s): Metabolic intermediate in many kinase reactions | |
| J63013 | Phosphoenolpyruvic acid trisodium salt heptahydrate, 98% [2-(Phosphonoxy)-2-propenoic acid trisodium salt, PEP-triNa] [5541-93-5], C ₃ H ₃ Na ₃ O ₆ ·7H ₂ O, F.W. 360.09, Powder, EINECS 226-906-8, MDL MFCD00150737, † | 1g 5g |
| | Application(s): When coupled with pyruvate kinase it completes an ATP-regenerating system | |
| | Phosphoenol transphosphorylase , see Pyruvate Kinase, rabbit muscle, J61373, p. 333 | |
| | 2-(Phosphonoxy)-2-propenoic acid tri(cyclohexylammonium) salt , see Phosphoenolpyruvic acid tricyclohexylammonium salt, 99+%, J61943, p. 321 | |
| | 2-(Phosphonoxy)-2-propenoic acid trisodium salt , see Phosphoenolpyruvic acid tricyclohexylammonium salt, 99+%, J63013, p. 321 | |
| J63456 | Phosphoramidon disodium salt, 97+% [119942-99-3], C ₂₃ H ₂₈ N ₃ Na ₂ O ₁₀ P, F.W. 587.47, Solid, BRN 8105669, MDL MFCD00077870 | 5mg |
| | Application(s): Inhibitor of thermolysin and collagenase | |
| | Phosphoric acid (ortho) , see Orthophosphoric acid, 33266, p. 309 | |
| | 1(2H)-Phthalazinone hydrazone , see 1-Hydrazinophthalazine hydrochloride, B22995, p. 247 | |
| | Phthalein complexone , see o-Cresolphthalein complexone, L03859, p. 169 | |
| | Phthalic acid di-n-butyl ester , see Di-n-butyl phthalate, A13257, p. 185 | |
| | Phylloquinone , see Vitamin K ₁ , L10575, p. 393 | |
| J62647 | Physalaemin [Glp-Ala-Asp-Pro-Asn-Lys-Phe-Tyr-Gly-Leu-Met-NH ₂] [2507-24-6], C ₂₈ H ₄₈ N ₄ O ₁₀ S, F.W. 1265.45, Powder, Merck 14,7381, MDL MFCD00076375 | 1mg 5mg |
| | Application(s): A vasodilator and hypotensive agent | |
| | Physostigmine , see Eserine, J61477, p. 210 | |
| | Phytigel , see Gellan Gum, J63423, p. 231 | |
| J64277 | Pifithrin-α, p-Nitro hydrobromide ▲ ■ [1-(4-Nitrophenyl)-2-(4,5,6,7-tetrahydro-2-imino-3(2H)-benzophthalazolyl)ethanone hydrobromide] [389850-21-9], C ₁₅ H ₁₆ BrN ₂ O ₃ S·HBr, F.W. 398.30, Solid | 5mg |
| B21410 | (+)-Piocarpine hydrochloride, 99% ▲ ■ [54-71-7], C ₁₁ H ₁₆ N ₂ O ₂ ·HCl, F.W. 244.72, m.p. 202-205°, Merck 14,7424, UN1544, EINECS 200-212-5, RTECS TK1450000, MDL MFCD00012722, †  | 1g 5g 25g |
| |  H:H300-H330, P:P301+P310-P304+P340-P320-P330-P405-P501a | |
| H56648 | D-Pinitol, 95% [3-O-Methyl-D-chiro-inositol] [10284-63-6], C ₇ H ₁₄ O ₆ , F.W. 194.18, m.p. 178-185°, Merck 14,10361, MDL MFCD00216659 | 250mg 1g 5g |
| |  | |
| | Piperazine-1,4-bis(ethanesulfonic acid) , see PIPES, A16090, p. 322 | |
| | Piperazine-1,4-bis(ethanesulfonic acid) monosodium salt , see PIPES monosodium salt, B21835, p. 322 | |
| | 2,5-Piperazinedione , see Glycine anhydride, A18822, p. 237 | |
| | 2-(1-Piperazinylo)quinoline maleate salt , see Quipazine dimaleate, 99+%, J61933, p. 334 | |
| A12442 | Piperidine, 99% △ [110-89-4], C ₅ H ₁₁ N, F.W. 85.15, m.p. -11°, b.p. 105-106°, f.p. 3°(37°F), d. 0.862, n _D ²⁰ 1.4520, Merck 14,7468, Fieser 1,886 2,332 4,393 6,472 7,293 19,272, UN2401, EINECS 203-813-0, RTECS TM3500000, BRN 102438, MDL MFCD00005979, †  | 100ml 500ml 2.5L |
| |  H:H225-H311-H331-H314, P:P210-P303+P361+P353-P305+P351+P338-P361-P405-P501a Base catalyst in the Doebner modification of the Knoevenagel condensation; see Malonic acid, A11526 , p. 276. Widely used for cleavage of Fmoc protecting groups: <i>J. Org. Chem.</i> , 52 , 1197 (1987); <i>Tetrahedron Lett.</i> , 34 , 6135 (1993). For preparation of the piperidine enamine of cyclooctanecarboxaldehyde, and its subsequent use in the synthesis of spirohexadienones, see: <i>Org. Synth. Coll.</i> , 7 , 473 (1990). | |


| Stock # | Description | Size |
|---------|---|---|
| | (±)-Piperidine-3-carboxylic acid, see Nipecotic acid, B24723, p. 303 Piperidine-4-carboxylic acid, see Isonipecotic acid, A11795, p. 261 N-(2-Piperidylmethyl)-2,5-bis-(2,2,2-trifluoroethoxy)benzamide acetate salt, see Flecainide acetate, 98%, J63527, p. 221 | |
| A16090 | PIPES, 98% [Piperazine-1,4-bis(ethanesulfonic acid)] [5625-37-6], C ₈ H ₁₈ N ₂ O ₆ S ₂ , F.W. 302.37, m.p. >300°, Merck 14,7479, EINECS 227-057-6, BRN 817713, MDL MFCD00006159, † Biological buffer, pKa = 6.8 at 20°: <i>Biochemistry</i> , 5, 467 (1966). |  25g 100g 500g |
| B21835 | PIPES monosodium salt hydrate, 99% [Piperazine-1,4-bis(ethanesulfonic acid) monosodium salt] [10010-67-0], C ₈ H ₁₇ N ₂ NaO ₆ S ₂ ·xH ₂ O, F.W. 324.34(anhy), m.p. >300°, Merck 14,7479, EINECS 233-005-3, MDL MFCD00065472, † |  25g 100g |
| J60891 | PIPES, 0.5M buffer soln., pH 5.5 [5625-37-6], Liquid, † | 100ml 250ml |
| J62224 | PIPES, 0.5M buffer soln., pH 6.0 [5625-37-6], Liquid, † | 100ml 250ml |
| J61224 | PIPES, 0.5M buffer soln., pH 6.5 [5625-37-6], Liquid, † | 100ml 250ml |
| J61786 | PIPES, 0.5M buffer soln., pH 6.8 [5625-37-6], Liquid, † | 100ml 250ml |
| J63234 | PIPES, 0.5M buffer soln., pH 7.0 [5625-37-6], Liquid, † | 100ml 250ml |
| J63617 | PIPES, 0.5M buffer soln., pH 7.5 [5625-37-6], Liquid, † | 100ml 250ml |
| J61406 | PIPES, 0.5M buffer soln., pH 8.0 [5625-37-6], Liquid, † | 100ml 250ml |
| J60611 | PIPES, 1.0M buffer soln., pH 6.0 [5625-37-6], Liquid, † | 250ml 500ml |
| J60659 | PIPES, 1.0M buffer soln., pH 6.5 [5625-37-6], Liquid, † | 250ml 500ml |
| J60300 | PIPES, 1.0M buffer soln., pH 6.8 [5625-37-6], Liquid, † | 250ml 500ml |
| J62195 | PIPES, 1.0M buffer soln., pH 7.0 [5625-37-6], Liquid, † | 250ml 500ml |
| J62494 | PIPES, 1.0M buffer soln., pH 7.5 [5625-37-6], Liquid, † | 250ml 500ml |
| J60618 | PIPES, 1.0M buffer soln., pH 8.0 [5625-37-6], Liquid, † | 250ml 500ml |
| J63152 | PIPES-buffered saline (5X), pH 6.5 [5625-37-6], Liquid, Note: Contains 50mM PIPES and 750mM NaCl, pH 6.5., † | 250ml 500ml |
| J60947 | PIPES-buffered saline (5X), pH 6.8 [5625-37-6], Liquid, Note: Contains 50mM PIPES, 750mM NaCl at pH 6.8., † | 250ml 500ml |
| J63543 | PIPES-buffered saline (5X), pH 7.0 [5625-37-6], Liquid, Note: Contains 50mM PIPES, 750mM NaCl at pH 7.0., † | 250ml 500ml |
| J62278 | PIPES lysis buffer with NP-40 Liquid, Note: Contains 25mM PIPES (pH 7.0), 150mM sodium chloride, 1% NP-40 and 5mM EDTA. | 250ml 500ml |
| J60568 | PIPES lysis buffer with NP-40 (2X) Liquid, Note: Contains 50mM PIPES (pH 7.0), 300mM NaCl, 2% NP-40 and 10mM EDTA. | 125ml 250ml |
| J62360 | PIPES lysis buffer with Triton® X-100 Liquid, Note: Contains 25mM PIPES (pH 7.0), 150mM NaCl, 1% Triton X-100 and 5mM EDTA. | 250ml 500ml |

| Stock # | Description | Size |
|---------|--|---------------------|
| J62068 | PIPES lysis buffer with Triton® X-100 (2X) Liquid, Note: Contains 50mM PIPES (pH 7.0), 300mM NaCl, 2% Triton X-100 and 10mM EDTA. | 125ml 250ml |
| | Pipsyl chloride , see 4-Iodobenzenesulfonyl chloride, B24416, p. 257 | |
| J62252 | Pirenzepine dihydrochloride, 99% ■ [29868-97-1], C ₁₅ H ₂₁ N ₃ O ₂ ·2HCl, F.W. 424.32, Powder, m.p. 192-198°, Merck 14,7491, EINECS 249-907-5, RTECS UU7883000, MDL MFCD00055214 | 100mg 1g 5g |
| | Application(s): A M1 muscarinic receptor antagonist | |
| J63239 | Piroxicam [Piroxicamum, <i>Larapam</i>] [36322-90-4], C ₁₅ H ₁₃ N ₃ O ₄ S, F.W. 331.35, Powder, Merck 14,7506, UN2811, EINECS 252-974-3, RTECS DL0705000, MDL MFCD00057317 | 1g 5g 10g |
| | H: H301, P: P264-P270-P301+P310-P321-P405-P501a | |
| | Application(s): A non-steroidal anti-inflammatory drug (NSAID) that is a highly selective inhibitor of cyclooxygenase-1 (COX-1) | |
| | Piroxicamum , see Piroxicam, J63239, p. 323 Pituitary adenylate cyclase activating fragment 21-38 , see Litorin, J60177, p. 272 Pivaloyloxymethyl chloride , see Chloromethyl pivalate, A11967, p. 157 | |
| J61263 | Plasmid DNA isolation solution I Liquid, Note: Contains 50mM glucose, 25mM Tris-HCl (pH 8.0) and EDTA | 250ml 500ml |
| J63486 | Plasmid DNA isolation solution II Liquid, Note: Contains 0.2M sodium hydroxide and 1% SDS. | 250ml 500ml |
| | H: H315-H319, P: P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | |
| J60196 | Plasmid DNA isolation solution III Liquid, Note: Contains 5M Potassium Acetate and 11.5ml glacial acetic acid in 28.5ml of water. The resulting solution is 3M with respect to potassium and 5M with respect to acetate. | 250ml 500ml |
| J64463 | Platelet-Derived Growth Factor-AA, human, Receptor Grade, 97% [PdGF-AA] Note: Recombinantly expressed in E. Coli. Receptor Grade. Suitable for use in cell culture. Supplied as an aseptically lyophilized powder | 5micrograms |
| J64812 | Platelet-Derived Growth Factor-BB, human, Receptor Grade, 97% [PdGF-BB] Note: Recombinantly expressed in E. Coli. Receptor Grade. Suitable for cell culture. Supplied as a lyophilized powder in silanized vial. | 1microgram |
| J64483 | Platelet-Poor Plasma Derived Serum, bovine [Bovine serum, from platelet poor plasma] | 10ml 100ml |
| | Plendil , see Felodipine, J61195, p. 219 PN 200-110 , see Isradipine, 98+%, J63920, p. 261 pNPP disodium salt , see 4-Nitrophenyl phosphate disodium salt hexahydrate, 5mg tablets, J61401, p. 304 | |
| J61495 | Polyethylene glycol (PEG), 50% soln. [25322-68-3], H(OCH ₂ CH ₂) _n OH, Liquid, Note: Contains 50% PEG 3350 in 1M Lithium Acetate solution, pH 4.9., t | 100ml 250ml |
| | H: H315-H319, P: P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | |
| B21918 | Polyethylene glycol 200 ■ [PEG 200] [25322-68-3], H(OCH ₂ CH ₂) _n OH, m.p. -55 to -40°, f.p. 171° (339°F), d. 1.127, n _D ²⁰ 1.4590, Merck 14,7568, Fieser 12,399, EINECS 203-473-3, RTECS TQ3600000, MDL MFCD01779596, t | 250g 500g 1kg |
| | A mixture of PEG200 with dichloromethane has been recommended as a solvent system for the Sandmeyer conversion of aromatic amines to halides, giving particularly good results for aryl chlorides: <i>J. Chem. Soc., Chem. Commun.</i> , 1523 (1984). For use of polyethylene glycols as phase-transfer catalysts, see Polyethylene glycol 400 , B21992, p. 323. | |
| B21992 | Polyethylene glycol 400 ■ [PEG 400] [25322-68-3], H(OCH ₂ CH ₂) _n OH, m.p. 4-8°, n _D ²⁰ 1.4660, Merck 14,7568, MDL MFCD01779601, t | 250g 1kg |
| | Polyethylene glycols can act as effective solvents and low-cost phase-transfer catalysts by complexing with cations Examples of reactions promoted by these species: Nucleophilic displacements of benzyl halides: <i>Synthesis</i> , 184 (1977). Permanganate oxidations: <i>J. Org. Chem.</i> , 43 , 1532 (1978); <i>Tetrahedron Lett.</i> , 3543 (1979). Dichromate oxidations: similar results to carcinogenic HMPA, and to crown ethers. Good solvent for borohydride reductions: <i>Tetrahedron Lett.</i> , 4581 (1979). Stereospecific reduction of alkynes to <i>cis</i> -alkenes using NaBH ₄ and a catalytic amount of PdCl ₂ in dichloromethane-PEG: <i>J. Chem. Soc., Chem. Commun.</i> , 515 (1982). Wacker oxidation of olefins to methyl ketones: <i>Tetrahedron Lett.</i> , 26 , 2263 (1985). Conversion of acids to peracids; see Potassium peroxydisulfate , A15310. Recyclable medium for rapid Baylis-Hillman reactions (see Ammonium bismuth citrate , A17003): <i>Tetrahedron Lett.</i> , 45 , 5865 (2004). | |

| Stock # | Description | Size |
|---------|--|-----------------------------|
| B21798 | Polyethylene glycol 600 [PEG 600] [25322-68-3], H(OCH ₂ CH ₂) _n OH, m.p. 17-23°, f.p. 252°(485°F), d. 1.120, n _D ²⁰ 1.4680, Merck 14,7568, Fieser 12,399, EINECS 500-038-2, RTECS TQ3800000, MDL MFCD00081839, † Catalyzes the reaction of potassium aryloxides with dichloromethane at room temperature to give good yields of diaryloxymethanes: <i>J. Chem. Res. (Synop.)</i> , 503 (1995). | 250g 1kg |
| B22134 | Polyethylene glycol 1,000 [PEG 1000] [25322-68-3], H(OCH ₂ CH ₂) _n OH, m.p. 35-40°, f.p. 260°(500°F), d. 1.101, Merck 14,7568, Fieser 12,399, RTECS TQ4025000, MDL MFCD01779605, † | 250g 1kg |
| A16241 | Polyethylene glycol 1,500 [PEG 1500] [25322-68-3], H(OCH ₂ CH ₂) _n OH, m.p. 44-48°, Merck 14,7568, EINECS 500-038-2, RTECS TQ4030000, MDL MFCD01779609, Note: M.W. range 1,300-1,600, † | 250g 1kg |
| B22181 | Polyethylene glycol 2,000 [PEG 2000] [25322-68-3], H(OCH ₂ CH ₂) _n OH, m.p. 53-55°, Merck 14,7568, RTECS TQ4041000, MDL MFCD01779611, † | 250g 1kg |
| A16151 | Polyethylene glycol 4,000 [PEG 4000] [25322-68-3], H(OCH ₂ CH ₂) _n OH, m.p. 58-62°, Merck 14,7568, RTECS TQ4050000, MDL MFCD01779612, Note: M.W. range 3,000-3,700, † | 250g 1kg 5kg |
| A17541 | Polyethylene glycol 6,000 [PEG 6000] [25322-68-3], H(OCH ₂ CH ₂) _n OH, m.p. 60-63°, Merck 14,7568, EINECS 203-473-3, RTECS TQ4100000, MDL MFCD01779614, † | 250g 1kg 5kg |
| 43443 | Polyethylene glycol 8,000 [PEG 8000] [25322-68-3], H(OCH ₂ CH ₂) _n OH, Powder, m.p. 60-63°, Merck 14,7568, MDL MFCD01779615, Note: M.W. range 7000 - 9000, † | 100g 500g 2kg 10kg |
| B21955 | Polyethylene glycol 10,000 [PEG 10000] [25322-68-3], H(OCH ₂ CH ₂) _n OH, m.p. 58-63°, f.p. 265°(509°F), d. 1.2, Merck 14,7568, EINECS 203-473-3, RTECS TQ4110000, MDL MFCD00081839, † | 250g 1kg |
| 42635 | Polyethylene glycol 12,000 [PEG 12000, Carbowax®] [25322-68-3], H(OCH ₂ CH ₂) _n OH, Powder, m.p. 64-65°, f.p. ≥240°(464°F), Merck 14,7568, MDL MFCD00081839, Note: M.W. range 11,000 - 13,000, † | 250g 1kg |
| A17925 | Polyethylene glycol 20,000 [PEG 20000] [25322-68-3], H(OCH ₂ CH ₂) _n OH, m.p. 63-66°, f.p. 260°(500°F), d. 1.20, Merck 14,7568, EINECS 203-473-3, MDL MFCD00081839, Note: M.W. ≈20,000, † | 250g 1kg |
| J62213 | Polyethylene glycol-lithium acetate soln. [PEG-LiOAc solution, PEG-lithium acetate solution] Liquid, Note: Contains 40% PEG 3350 in solution with 100mM lithium acetate, 10mM Tris-HCl, and 1mM EDTA, pH8.0. Application(s): Common solution for protein and DNA isolation from yeast | 250ml 500ml |
| | Polyethylene glycol tert-octylphenyl ether , see Triton® X-100, A16046, p. 383 | |
| J61270 | Polyethyleneimine, M.W. 60,000, 50% w/w aq. soln. [9002-98-6], -HN-[CH ₂ CH ₂ NH-] _n , Liquid, d. 1.07, MDL MFCD00084427, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 100g 250g |
| | Application(s): A protein precipitant used to purify proteins | |
| 40529 | Polyethyleneimine, branched, M.W. 70,000, 30% w/v aq. soln. [9002-98-6], (-NHCH ₂ CH ₂) _x (-N(CH ₂ CH ₂ NH ₂)CH ₂ CH ₂) _y , Liquid, MDL MFCD00803910, † ! H:H302, P:P264-P270-P301+P312-P330-P501a | 25g 100g 500g |
| | Application(s): A protein precipitant used to purify proteins | |
| | Poly-D-galacturonic acid methyl ester , see Pectin Citrus, J61021, p. 312 | |
| J65578 | Poly-D-lysine hydrobromide | 5mg |
| | Polymannuronic acid , see Alginate acid, A17582, p. 89 | |
| | Polymannuronic acid sodium salt , see Alginate acid sodium salt, A18565, p. 89 | |


| Stock # | Description | Size |
|---------|--|---------------|
| J63074 | Polymixin B sulfate | 1g |
| | [Aerosporin] [1405-20-5], C ₂₈ H ₅₈ N ₁₀ O ₁₃ ·2H ₂ SO ₄ , F.W. 1385.63, Powder, Merck 14,7573, EINECS 215-774-7, RTECS TR150000, MDL MFCD00131991 | 5g |
| | ! H: H302, P: P264-P270-P301+P312-P330-P501a | |
| | Application(s): Antibiotic for gram-negative bacteria | |
| J61763 | Polymixin B sulfate, Cell Culture Reagent | 1g |
| | [1405-20-5], C ₂₈ H ₅₈ N ₁₀ O ₁₃ ·2H ₂ SO ₄ , F.W. 1385.63, Powder, Merck 14,7573, EINECS 215-774-7, RTECS TR150000, MDL MFCD00131991 | 5g |
| | ! H: H302, P: P264-P270-P301+P312-P330-P501a | |
| | Application(s): Antibiotic for gram-negative bacteria | |
| | Polymyxin E , see Colistin sulfate, J60915, p. 167 | |
| | Polyoxyethylene sorbitan monolaurate , see Polysorbate 20, L15029, p. 325 | |
| | Polyoxyethylene sorbitan monooleate , see Polysorbate 80, L13315, p. 325 | |
| L15029 | Polysorbate 20 | 100ml |
| | [Polyoxyethylene sorbitan monolaurate] [9005-64-5], C ₆₈ H ₁₁₄ O ₂₆ , b.p. >100°, f.p. >110°(230°F), d. 1.105, n _D ²⁰ 1.4700, RTECS TR7400000, MDL MFCD00165986, † | 500ml |
| | Application(s): Used for solubilizing membrane proteins during isolation and purification | |
| L13315 | Polysorbate 80 | 100ml |
| | [Polyoxyethylene sorbitan monooleate] [9005-65-6], b.p. >100°, f.p. >149°(300°F), d. 1.064, n _D ²⁰ 1.4720, Merck 14,7582, RTECS WG2932500, MDL MFCD00082107, † | 500ml 2.5L |
| | Application(s): Used for solubilizing membrane proteins during isolation and purification | |
| | Polystyrene PHB , see Wang resin, L17028, p. 393 | |
| | Polysucrose 400 , see Ficoll® 400, B22095, p. 221 | |
| 41238 | Polyvinyl alcohol, 86-89% hydrolyzed, low molecular weight | 25g |
| | [9002-89-5], [-CH ₂ CH(OH)-] _n , MDL MFCD00081922, Note: Average MW: 10,000 to 26,000, † | 100g 500g |
| 41626 | Polyvinylpyrrolidone, M.W. 8,000 | 100g |
| | [PVP] [9003-39-8], (C ₆ H ₉ NO) _n , Powder, m.p. 130°, Merck 14,7697, MDL MFCD00149016, † | 500g |
| | Application(s): A cryoprotectant, also useful in plant cell culture research | |
| J60382 | Polyvinylpyrrolidone, M.W. 10,000 | 25g |
| | [PVP K15, Povidone] [9003-39-8], (C ₆ H ₉ NO) _n , Powder, Merck 14,7697, RTECS TR8370000, MDL MFCD00149016, † | 100g 500g |
| | Application(s): A cryoprotectant, also useful in plant cell culture research | |
| J62417 | Polyvinylpyrrolidone, M.W. 40,000 | 100g |
| | [PVP, Povidone] [9003-39-8], (C ₆ H ₉ NO) _n , Powder, Merck 14,7697, RTECS TR8370000, MDL MFCD00149016, † | 500g 1kg |
| | Application(s): A cryoprotectant, also useful in plant cell culture research | |
| A14315 | Polyvinylpyrrolidone, average M.W. 58,000 | 100g |
| | [PVP K-30] [9003-39-8], (C ₆ H ₉ NO) _n , Merck 14,7697, MDL MFCD00149016, † | 500g 2.5kg |
| | Application(s): A cryoprotectant, also useful in plant cell culture research | |
| J61381 | Polyvinylpyrrolidone, M.W. 360,000 | 250g |
| | [PVP K90, Povidone] [9003-39-8], (C ₆ H ₉ NO) _n , Powder, Merck 14,7697, RTECS TR8370000, MDL MFCD00149016, † | 500g 1kg |
| | Application(s): A cryoprotectant, also useful in plant cell culture research | |
| 43728 | Polyvinylpyrrolidone, M.W. 1,300,000 ■ | 50g |
| | [9003-39-8], (C ₆ H ₉ NO) _n , Powder, Merck 14,7697, MDL MFCD00149016, † | 250g 1kg |
| | POM-Cl, see Chloromethyl pivalate, A11967, p. 157 | |
| J63139 | Ponceau S, 0.2% v/v soln. in 5% acetic acid | 500ml |
| | [C.I. 27195, Acid Red 112] [6226-79-5], C ₂₂ H ₁₂ N ₄ Na ₂ O ₁₀ S ₄ , F.W. 760.56, Liquid, MDL MFCD00003892 | 1L |
| | ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J60744 | Ponceau S, Electrophoresis Grade | 10g |
| | [C.I. 27195] [6226-79-5], C ₂₂ H ₁₂ N ₄ Na ₂ O ₁₀ S ₄ , F.W. 760.58, Powder, EINECS 228-319-2, RTECS QJ6600000, MDL MFCD00003892, † | 50g 250g |
| | ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): Protein stain for electrophoresis | |
| | Pontamine Sky Blue 6BX , see Chicago Sky Blue 6B, A14242, p. 153 | |




| Stock # | Description | Size |
|---------|---|---------------------|
| J63333 | POPSO, 0.2M buffer soln., pH 7.0 [108321-07-9], Liquid | 100ml 250ml |
| J60869 | POPSO, 0.2M buffer soln., pH 7.5 [108321-07-9], Liquid | 100ml 250ml |
| J60085 | POPSO, 0.2M buffer soln., pH 8.0 [108321-07-9], Liquid | 100ml 250ml |
| J60623 | POPSO, 0.2M buffer soln., pH 8.5 [108321-07-9], Liquid | 100ml 250ml |
| J62817 | Potassium acetate, 1M aq. soln., pH 7.5 [127-08-2], CH ₃ CO ₂ K, F.W. 98.15, Liquid, † | 100ml 250ml |
| J60832 | Potassium acetate, 1M aq. soln., pH 7.5, RNAse free [127-08-2], CH ₃ CO ₂ K, F.W. 98.15, Liquid, † | 125ml 250ml |
| J63372 | Potassium acetate, 8M aq. soln. [127-08-2], CH ₃ CO ₂ K, F.W. 98.15, Liquid, † H:H303, P:P312 | 100ml 250ml |
| J62856 | Potassium acetate, 8M aq. soln., RNAse free [127-08-2], CH ₃ CO ₂ K, F.W. 98.15, Liquid, † H:H303, P:P312 | 125ml 250ml |
| | Potassium benzylpenicillinate , see Penicillin G potassium salt, J63901, p. 313 Potassium Channel Opener , see PCO-400, J60502, p. 312 | |
| J63739 | Potassium chloride, 1M aq. soln. [7447-40-7], KCl, F.W. 74.55, Liquid, † | 100ml 250ml |
| J60105 | Potassium chloride, 1M aq. soln., autoclaved [7447-40-7], KCl, F.W. 74.55, Liquid, † H:H303, P:P312 | 100ml 250ml |
| J62422 | Potassium chloride, 1M aq. soln., RNAse free [7447-40-7], KCl, F.W. 74.55, Liquid, † H:H303, P:P312 | 125ml 250ml |
| 11595 | Potassium chloride, ACS, 99.0-100.5% ■ [7447-40-7], KCl, F.W. 74.55, Crystalline, m.p. 773°, b.p. 1500° subl., d. 1.984, n _D ²⁰ 1.490, Merck 14,7621, Fieser 6,480, Solubility: Freely soluble in water. Soluble in glycerol, alcohol, EINECS 231-211-8, RTECS TS8050000, MDL MFCD00011360, † Maximum level of impurities: Insoluble matter 0.005%, pH of a 5% solution 5.4-8.6 at 25°, I 0.002%, Br 0.01%, NO ₃ 0.003%, PO ₄ 5ppm, SO ₄ 0.001%, Ba P.T. (limit about 0.001%), Ca 0.002%, Mg 0.001%, Heavy Metals (as Pb) 5ppm, Fe 3ppm, Na 0.005% ! H:H302, P:P264-P270-P301+P312-P330-P501a Application(s): In buffer solution, electrode cells, photography, lab reagent, fertilizer, spectroscopy | 1kg 5kg |
| J65093 | Potassium dihydrogen arsenate, 98% [Potassium arsenate, monobasic, Arsenic acid potassium salt] [7784-41-0], KH ₂ AsO ₄ , F.W. 180.03, Powder, m.p. 277-283°, Merck 14,7607, UN1677, EINECS 232-065-8, RTECS CG1100000, MDL MFCD00036296, †  H:H301-H330-H350-H410, P:P301+P310-P304+P340-P320-P330-P405-P501 | 25g 100g 500g |
| 11594 | Potassium dihydrogen phosphate, ACS, 99.0% min ■ [Potassium orthophosphate, Potassium phosphate, monobasic] [7778-77-0], KH ₂ PO ₄ , F.W. 136.09, Crystalline, m.p. 253°, d. 2.338, Merck 14,7659, Solubility: Slightly soluble in water. Insoluble in alcohol, EINECS 231-913-4, RTECS TC6615500, MDL MFCD00011401, Note: Loses H ₂ O at 400°, forming metaphosphate, † Maximum level of impurities: Insoluble matter 0.01%, Loss on drying at 105° 0.2%, pH of a 5% solution 4.1-4.5 at 25°, Cl 0.001%, SO ₄ 0.003%, Heavy Metals (as Pb) 0.001%, Fe 0.002%, Na 0.005% ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 Application(s): In buffers for pH determination. | 250g 500g 1kg |
| 11593 | Potassium hydrogen phosphate, ACS, 98.0% min ■ [Potassium phosphate, dibasic, Dipotassium phosphate] [7758-11-4], K ₂ HPO ₄ , F.W. 174.18, Powder, Merck 14,7658, Solubility: Soluble in water. Slightly soluble in alcohol, EINECS 231-834-5, RTECS TC5580000, MDL MFCD00011383, † Maximum level of impurities: Insoluble matter 0.01%, Loss on drying at 105° 1.0%, pH of a 5% solution 8.5-9.6 at 25°, Cl 0.003%, Nitrogen compounds (as N) 0.001%, SO ₄ 0.005%, Heavy Metals (as Pb) 5ppm, Fe 0.001%, Na 0.05% ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 250g 1kg 5kg |

| Stock # | Description | Size |
|---------|---|-------|
| A12428 | Potassium hydrogen sulfate, 97% ■ | 100g |
| | [Potassium bisulfate] | 500g |
| | [7646-93-7], KHSO ₄ , F.W. 136.17, m.p. 195-197° dec., d. 2.240, Merck 14,7613, Fieser 1,909, UN2509, EINECS 231-594-1, RTECS TS7200000, MDL MFCD00011404, † | 2.5kg |
| | ⚠ ! H: H314-H335, P: P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 10kg |
| 13451 | Potassium hydroxide, ACS, 85% min, K₂CO₃ 2.0% max △ ■ | 50g |
| | [1310-58-3], KOH, F.W. 56.11, Pellets, m.p. 360°, b.p. 1320-1324°, d. 2.044, Merck 14,7640, Fieser 1,935 4,409 5,557 6,486 7,303 8,415 9,387 11439, 21,360, Solubility: Soluble in water, alcohol, and glycerol. Slightly soluble in ether, UN1813, EINECS 215-181-3, RTECS TT2100000, MDL MFCD00003553, Note: Usually contains 10-15% water, † | 500g |
| | Maximum level of impurities: Cl 0.01%, Nitrogen compounds (as N) 0.001%, PO ₄ 5ppm, SO ₄ 0.003%, Heavy Metals (as Ag) 0.001%, Fe 0.001%, Ni 0.001%, Ca 0.005%, Mg 0.002%, Na 0.05% | 2kg |
| | ⚠ ! H: H314-H302, P: P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 10kg |
| | Application(s): In soap manufacture, in bleaching, as an electrolyte, as an absorbent, in dyestuffs, in liquid fertilizer, in electroplating, as a reagent | |
| | Potassium 2-naphthyl sulfate , see 2-Naphthyl sulfate potassium salt, 44061, p. 298 | |
| | Potassium orthophosphate , see Potassium dihydrogen phosphate, 11594, p. 326 | |
| 13145 | Potassium peroxydisulfate, ACS, 99.0% min | 250g |
| | [Potassium persulfate] | 1kg |
| | [7727-21-1], K ₂ S ₂ O ₈ , F.W. 270.33, Crystalline, m.p. 100° dec., d. 2.477, Merck 14,7656, Fieser 1,952 3,238 5,563 7,274 8,417 10,331 11,441 15,274 20,316, UN1492, EINECS 231-781-8, RTECS SE0400000, MDL MFCD00011386, † | |
| | Maximum level of impurities: Insoluble matter 0.005%, Chlorine compounds (as Cl) 0.001%, Heavy Metals (as Pb) 0.001%, Fe 5ppm, Mn 2ppm | |
| | ⚠ ! H: H334-H272-H302-H335-H315-H319-H317, P: P221-P210-P285-P305+P351+P338-P405-P501a | |
| | Application(s): A polymerization accelerant for PAGE gels | |
| | Potassium persulfate , see Potassium peroxydisulfate, 13145, p. 327 | |
| J61261 | Potassium phosphate, 0.2M buffer soln., pH 7.0 | 500ml |
| | [7778-77-0], Liquid, † | 1L |
| J60664 | Potassium phosphate, 0.2M buffer soln., pH 7.2 | 500ml |
| | [7778-77-0], Liquid, † | 1L |
| J62397 | Potassium phosphate, 0.2M buffer soln., pH 7.4 | 500ml |
| | [7778-77-0], Liquid, † | 1L |
| J62239 | Potassium phosphate, 0.2M buffer soln., pH 7.5 | 500ml |
| | [7778-77-0], Liquid, † | 1L |
| J63128 | Potassium phosphate, 0.2M buffer soln., pH 7.6 | 500ml |
| | [7778-77-0], Liquid, † | 1L |
| J60851 | Potassium phosphate, 0.2M buffer soln., pH 8.0 | 500ml |
| | [7778-77-0], Liquid, † | 1L |
| J60584 | Potassium phosphate, 0.5M buffer soln., pH 7.0 | 250ml |
| | [7778-77-0], Liquid, † | 500ml |
| J60326 | Potassium phosphate, 0.5M buffer soln., pH 7.2 | 250ml |
| | [7778-77-0], Liquid, † | 500ml |
| J61413 | Potassium phosphate, 0.5M buffer soln., pH 7.4 | 250ml |
| | [7778-77-0], Liquid, † | 500ml |
| J61553 | Potassium phosphate, 0.5M buffer soln., pH 7.5 | 250ml |
| | [7778-77-0], Liquid, † | 500ml |
| J63189 | Potassium phosphate, 0.5M buffer soln., pH 7.6 | 250ml |
| | [7778-77-0], Liquid, † | 500ml |
| | Potassium phosphate, dibasic , see Potassium hydrogen phosphate, 11593, p. 326 | |
| | Potassium phosphate, monobasic , see Potassium dihydrogen phosphate, 11594, p. 326 | |
| 33241 | Potassium sodium L-tartrate tetrahydrate, ACS, 99.0-102.0% | 100g |
| | [Rochelle Salt, Sodium potassium tartrate] | 500g |
| | [6381-59-5], C ₄ H ₄ KNaO ₆ ·4H ₂ O, F.W. 282.23 (210.29anhy), Crystalline, m.p. 70-80°, d. 1.77, Merck 14,7670, EINECS 206-156-8, BRN 6113568, MDL MFCD00150989, Note: Loses water of crystallization at 140° unstable above 225°, † | 2.5kg |
| | Maximum level of impurities: Insoluble matter 0.005%, Chloride (as Cl) 0.0015%, PO ₄ 0.002%, SO ₄ 0.005%, NH ₄ 0.002%, Ca 0.005%, Heavy Metals (as Pb) 5ppm, Fe 0.001%, pH of a 5% solution 6.0-8.5 at 25° | |








| Stock # | Description | Size |
|---------|---|-------------------|
| 14311 | Potassium sulfate, ACS, 99.0% min [7778-80-5], K ₂ SO ₄ , F.W. 174.27, Crystalline, m.p. 1069°, b.p. 1689°, d. 2.662, Merck 14,7674, Solubility: Soluble in water. Insoluble in alcohol, EINECS 231-915-5, RTECS TT5900000, MDL MFCD00011388, † Maximum level of impurities: Insoluble matter 0.01%, pH of a 5% solution 5.5-8.5 at 25°, Cl 0.001%, Nitrogen compounds (as N) 5ppm, Ca 0.01%, Mg 0.005%, Heavy Metals (as Pb) 5ppm, Fe 5ppm, Na 0.02% | 500g 2kg |
| | Potassium sulfocyanate , see Potassium thiocyanate, 14318, p. 328 | |
| 14318 | Potassium thiocyanate, ACS, 98.5% min ▲ ▽ [Potassium sulfocyanate] [333-20-0], KSCN, F.W. 97.18, Crystalline, m.p. 172-175°, b.p. 500° dec., d. 1.89, Merck 14,7691, Fieser 1,954, Solubility: Soluble in water, acetone, and alcohol. When dissolved in its own weight of water, the temperature drops ≈30°, EINECS 206-370-1, RTECS XL1925000, BRN 3594799, MDL MFCD00011413, † Maximum level of impurities: Insoluble in water 0.005%, pH of a 5% solution 5.3-8.7 at 25°, Cl 0.005%, SO ₄ 0.005%, NH ₄ 0.003%, Heavy Metals (as Pb) 5ppm, Fe 2ppm, Na 0.005%, Iodine-consuming substances P.T. ! H:H302-EU032-H312-H332-H412, P:P261-P280-P302+P352-P304+P340-P322-P501a | 100g 500g |
| | Povidone , see Polyvinylpyrrolidone, M.W. 360,000, J61381, p. 325 Povidone , see Polyvinylpyrrolidone, M.W. 40,000, J62417, p. 325 Povidone , see Polyvinylpyrrolidone, M.W. 10,000, J60382, p. 325 PPL , see Lipase, from porcine pancreas, J62903, p. 270 | |
| J64165 | PPM1D Phosphatase Inhibitor ▲ [2,5-Bis-(2-Thienylidene)cyclopentanone, CCT007093] [176957-55-4], C ₁₅ H ₁₂ OS ₂ , F.W. 272.40, Solid, MDL MFCD00121546 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10mg 50mg |
| J61712 | Prazosin hydrochloride [19237-84-4], C ₁₈ H ₁₅ N ₃ O ₂ ·HCl, F.W. 419.86, Powder, m.p. 285°, Merck 14,7717, EINECS 242-903-4, RTECS VA1350000, BRN 4303561, MDL MFCD00058177 ! H:H302-H315-H319-H361-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): An α adrenoceptor antagonist | 250mg 1g |
| J63618 | Prehybridization solutions in SSC Liquid, Note: Contains 6X SSC, 5X Denhardt's solution, 0.5% SDS, and 100ug/ml of denatured DNA from salmon testes. Application(s): For the hybridization of probes to nucleic acids in Northern and Southern blotting | 50ml 100ml |
| J61729 | Prehybridization solutions in SSPE Liquid, Note: Contains 6X SSPE, 5X Denhardt's solution, 0.5% SDS, and 100ug/ml of denatured DNA from salmon testes Application(s): For the hybridization of probes to nucleic acids in Northern and Southern Blotting | 50ml 100ml |
| | (Ile3)-Pressinoic acid , see Tocinoic acid, 96%, J62846, p. 370 | |
| J60648 | Prilocaine hydrochloride, 98% [1786-81-8], C ₁₃ H ₁₉ N ₃ O·HCl, F.W. 256.77, Powder, m.p. 167-168°, Merck 14,7743, EINECS 217-244-0, RTECS UG5775000, MDL MFCD00079279 Application(s): A local anesthetic | 1g 5g 10g |
| J64071 | Prima-1 ▲ [2,2-Bis(hydroxymethyl)quinuclidin-3-one] [5608-24-2], C ₉ H ₁₃ NO ₃ , F.W. 185.20, Solid, MDL MFCD04974196 ! H:H302-H317, P:P261-P280-P302+P352-P321-P301+P312-P501 | 10mg 50mg |
| J63833 | Proadifen hydrochloride [SKF-525A hydrochloride, N,N-Diethylaminoethyl 2,2-diphenylvalerate] [62-68-0], C ₂₃ H ₃₁ NO ₂ ·HCl, F.W. 389.97, Powder, m.p. 122-123°, RTECS YV7175000, MDL MFCD00055151 ! H:H302, P:P264-P270-P301+P312-P330-P501 Application(s): Inhibits cytochrome P-450, blocks glibenclamide-sensitive potassium channels. Also inhibits neuronal nitric oxide synthase | 500mg 1g 2g |
| B20010 | Probenecid, 98% [4-(Di-n-propylaminosulfonyl)benzoic acid, 4-(Di-n-propylsulfamoyl)benzoic acid] [57-66-9], C ₁₃ H ₁₉ NO ₂ S, F.W. 285.36, m.p. 198-199°, Merck 14,7754, EINECS 200-344-3, RTECS DG9400000, MDL MFCD00038402, † ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 2.5g 10g |
| | Procaine hydrochloride , see 2-Diethylaminoethyl 4-aminobenzoate hydrochloride, A17485, p. 188 | |
| J64824 | Procaspase-3 Activator ▲ [PAC-1, (4-Benzylpiperazino)acetic acid-(3-allyl-2-hydroxybenzylidene)hydrazide] [315183-21-2], C ₂₃ H ₂₈ N ₄ O ₂ , F.W. 392.49, Powder, UN3077, MDL MFCD03302441 ! H:H302-H315-H319-H335-H410, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 25mg 50mg |
| J60532 | Proctolin [Arg-Tyr-Leu-Pro-Thr] [57966-42-4], C ₃₀ H ₄₈ N ₈ O ₈ , F.W. 648.76, Powder Application(s): An insect neuropeptide | 1mg |



| Stock # | Description | Size |
|---------|--|---|
| L11109 | (R)-(-)-Prolinol, 98+% Δ ■ [<i>H-D-Pro-ol, (R)-(-)-2-Pyrrolidinemethanol</i>] [68832-13-3], C ₅ H ₁₁ NO, F.W. 101.15, m.p. 74-76°/2mm, f.p. 86°(186°F), d. 1.025, n _D ²⁰ 1.4849, [α] _D ²⁰ -31° (c=1 in toluene), BRN 1523669, MDL MFCD00064321 ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 |  1g 5g 25g |
| L09779 | (S)-(+)-Prolinol, 98% Δ ■ [<i>H-Pro-ol, (S)-(+)-2-Pyrrolidinemethanol</i>] [23356-96-9], C ₅ H ₁₁ NO, F.W. 101.15, m.p. 42-44°, b.p. 74-76°/2mm, f.p. 86°(186°F), d. 1.025, n _D ²⁰ 1.4853, [α] _D ²⁰ +31° (c=1 in toluene), Fieser 10,332 13,261, EINECS 245-605-2, BRN 79843, MDL MFCD00005255 ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 |  1g 5g 25g |
| J64533 | Prolyl Endopeptidase Inhibitor ▲ [<i>Z-PP-CHO</i>] [86925-97-5], C ₁₈ H ₂₂ N ₂ O ₄ , F.W. 330.40, Ol | 5mg |
| | Propanedinitrile , see Malononitrile, A15046, p. 276 Propanedioic acid , see Malonic acid, A11526, p. 276 | |
| 30948 | 1,2-Propanediol, ACS, 99.5% ■ [<i>(±)-Propylene glycol, 1,2-Dihydroxypropane</i>] [57-55-6], C ₃ H ₈ O ₂ , F.W. 76.10, Liquid, m.p. -60°, b.p. 186-188°, f.p. 107°(225°F), d. 1.036, n _D ²⁰ 1.4320, Merck 14,7855. Solubility: Miscible with water, acetone, chloroform. Soluble in ether, EINECS 200-338-0, RTECS TY2000000, BRN 1340498, MDL MFCD00064272, † Maximum level of impurities: Color (APHA) 10, Residue after ignition 0.005%, Titratable acid 0.0005meq/g, Cl 1ppm, H ₂ O 0.2% | 500ml 1L 4L 4x1L |
| | Application(s): As a substitute for ethylene glycol and glycerol. Good solvent for resins. Dissolves many essential oils, but immiscible with fixed oils. | |
| A11923 | 1,3-Propanesultone, 99% ■ [<i>3-Hydroxy-1-propanesulfonic acid γ-sultone</i>] [1120-71-4], C ₃ H ₆ O ₃ S, F.W. 122.14, m.p. 30-33°, b.p. 179-181°/30mm, f.p. >110°(230°F), d. 1.392, UN2811, EINECS 214-317-9, RTECS RP5425000, BRN 109782, MDL MFCD00005355, Note: Special handling precautions required. View MSDS prior to purchase. MSDS are available online at www.alfa.com, † ! H:H350-H302-H312, P:P280-P281-P302+P352-P322-P405-P501a For a review of the chemistry of sultones, see: <i>Tetrahedron</i> , 43, 1027 (1987). |  10g 50g 250g |
| | 1,2,3-Propanetriol , see Glycerol, Cell Culture Grade, J62399, p. 235 (1Z)-Propene-1,2,3-tricarboxylic acid , see cis-Aconitic acid, A16010, p. 76 1,2,3-Propanetricarboxylic acid , see trans-Aconitic acid, B20087, p. 76 trans-4-Propenylanisole , see trans-Anethole, A13482, p. 103 | |
| L04210 | Propionic acid, 99% [79-09-4], CH ₃ CH ₂ CO ₂ H, F.W. 74.08, m.p. -21°, b.p. 140-141°, f.p. 51°(123°F), d. 0.992, n _D ²⁰ 1.3870, Merck 14,7825, Fieser 12,415, UN3463, EINECS 201-176-3, RTECS UE5950000, BRN 506071, MDL MFCD00002756, †  H:H314-H226, P:P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a | 100g 1kg 2.5kg |
| | Propofol , see 2,6-Diisopropylphenol, L06841, p. 193 | |
| H26645 | (±)-Propranolol hydrochloride, 99% [<i>1-Isopropylamino-3-(1-naphthyloxy)-2-propanol hydrochloride</i>] [318-98-9], C ₁₈ H ₂₁ NO ₂ ·HCl, F.W. 295.80, m.p. 163-165°, Merck 14,7840, EINECS 206-268-7, MDL MFCD00012558 ! H:H302, P:P264-P270-P301+P312-P330-P501a |  5g 25g |
| | Application(s): A β-adrenergic blocker | |
| | (±)-Propylene glycol , see 1,2-Propanediol, 30948, p. 329 | |
| J60971 | Prostratin, 99+% [60857-08-1], C ₂₂ H ₃₀ O ₆ , F.W. 390.47, Powder, m.p. 216-219°, MDL MFCD00674138 | 1mg 5mg |
| | Application(s): 12-Deoxyphorbol 13-acetate; activator of protein kinase C. A weak mouse ear irritant, but lethal at 1ug per mouse | |
| J62926 | Protamine sulfate ■ [9009-65-8], Powder, RTECS UK9450000, † | 1g 5g 10g |
| | Application(s): Reverses the anticoagulant effects of heparin | |
| J64401 | Protease Inhibitor Cocktail I ■ Lyophilized solid, Note: Forms 100x solution when reconstituted in 1ml water. A 1x solution contains 500uM AEBSF.HCl, 150nM aprotinin, 1uM E-64, 0.5mM EDTA disodium salt, and 1uM leupeptin hemisulfate | 1unit |
| J65358 | Protease Inhibitor Cocktail I, Animal Free ■ Solid, Note: A 1x stock solution contains 500uM AEBSF.HCl, 150nM aprotinin, 1uM E-64, 0.5mM EDTA and 1uM leupeptin hemisulfate. Reconstitute each vial with 1ml water to obtain a 100X stock solution | 1unit |



| Stock # | Description | Size |
|---------|---|------------|
| J64963 | Protease Inhibitor Cocktail II ■ Lyophilized solid, Note: Reconstitute each vial with 1ml DMSO and 4ml H2O to obtain a 5ml stock solution containing 20 mM AEBSF.HCl, 1.7mM bestatin, 200uM E-64, 85mM EDTA, and 2mM pepstatin A Application(s): Inhibits aspartic, cysteine, serine, and metalloproteases, as well as aminopeptidases. Recommended for use with bacterial cell extracts | 1unit |
| J64283 | Protease Inhibitor Cocktail III Liquid, Note: 1ml in DMSO. One unit contains 100mM AEBSF.HCl, 80µM aprotinin, 5mM bestatin, 1.5mM E-64, 2mM leupeptin hemisulfate, and 1mM pepstatin A Application(s): For use with mammalian cell and tissue extracts | 1unit |
| J64156 | Protease Inhibitor Cocktail III, Animal-Free Liquid, Note: Each vial contains 100mM AEBSF.HCl, 80uM recombinant aprotinin, 5mM bestatin, 1.5mM E-64, 2mM leupeptin hemisulfate and 1mM pepstatin A Application(s): For use with mammalian cell and tissue extracts | 1ml |
| J64112 | Protease Inhibitor Cocktail III, Animal-Free, DMSO-Free ■ Lyophilized solid, Note: Will make a 1ml solution of 100mM AEBSF.HCl, 80uM recombinant aprotinin, 5mM bestatin, 1.5mM E-64, 2mM leupeptin hemisulfate and 1mM pepstatin A when reconstituted in water | 1unit |
| J65789 | Protease Inhibitor Cocktail IV Liquid, Note: One unit contains 100mM AEBSF.HCl, 1.5mM E-64, 2mM pepstatin A and 500mM 1,10-phenanthroline. 1ml in DMSO Application(s): For use with fungal and yeast extracts | 1unit |
| J65412 | Protease Inhibitor Cocktail V, EDTA-Free ■ Lyophilized solid, Note: A 1x stock solution contains 500uM AEBSF.HCl, 150nM aprotinin, 1uM E-64 and 1uM leupeptin hemisulfate | 1unit |
| J64920 | Protease Inhibitor Cocktail V, EDTA-Free, Animal-Free ■ Lyophilized solid, Note: Makes 100x stock solution with 1ml of water. A 1X stock solution contains 500 uM AEBSF.HCl, 150nM aprotinin, 1uM E-64 and 1uM leupeptin hemisulfate Application(s): For the inhibition of serine- and cysteine-proteases, but not metalloproteases. For applications that require animal-free reagents | 1unit |
| J65974 | Protease Inhibitor Cocktail VI, General Use ■ Lyophilized solid, Note: Reconstitute with 100ml water. The reconstituted cocktail solution contains 2mM AEBSF.HCl, 1mM EDTA disodium salt, 130 uM bestatin, 1uM E-64, 1uM leupeptin hemisulfate and 0.3uM aprotinin | 1unit |
| J64576 | Protease Inhibitor Cocktail VI, Plant Cells Liquid, UN2922, Note: 1ml solution in DMSO containing 200mM AEBSF.HCl, 10mM bestatin, 3mM E-64, 2mM leupeptin hemisulfate, 500mM o-phenanthroline and 2mM pepstatin A  H:H301-H314-H410, P:P260-P301+P310-P303+P631+P353-P305+P351+P338-P405-P501 | 1ml |
| J64016 | Protease Inhibitor Cocktail VII, for His Tag Sequences Liquid, Note: 1ml in DMSO. Contains 100mM AEBSF.HCl, 5 mM bestatin, 1.5mM E-64, 2mM pepstatin A and 200µM phosphoramidon disodium salt. | 1unit |
| J65553 | Protease Inhibitor Cocktail VII, for His Tag Sequences, DMSO-Free ■ Lyophilized solid, Note: When reconstituted to 1ml, 1 unit makes a solution containing 100 mM AEBSF.HCl, 5mM bestatin, 1.5mM E-64, 2mM pepstatin A and 200uM phosphoramidon disodium salt | 1unit |
| J65384 | Protease Inhibitor Cocktail VIII Liquid, Note: A 1ml DMSO solution containing 1.56mM ALLN, 500uM antipain and 1.5mM E-64 ! H:H302, P:P264-P270-P301+P312-P330-P501 Application(s): Has selective specificity for the inhibition of cysteine proteases, including calpains, cathepsins and papain | 1ml |
| J61852 | Protease Inhibitor Cocktail, for general use Liquid, Note: Contains AEBSF, Aprotinin, E-64, Bestatin, Leupeptin, and EDTA. 1 ml of 100X concentrate store at -20C | 1ml |
| J61473 | Protease Inhibitor Cocktail, for mammalian cells Liquid, Note: Contains AEBSF, Aprotinin, E-64, Bestatin and Leupeptin. 1 ml of 100X concentrate store at -20C | 1ml |
| J64973 | Proteasome Inhibitor II [Z-LLF-CHO, Z-Leu-Leu-Phe-CHO] C ₂₉ H ₃₉ N ₃ O ₅ , F.W. 509.64, Powder, MDL MFCD01862616 | 1mg 5mg |
| J64492 | Proteasome Substrate ▲ [Z-LLL-AMC, Z-Leu-Leu-Leu-AMC] C ₃₈ H ₄₈ N ₄ O ₇ , F.W. 648.79, Lyophilized powder, MDL MFCD01074988 | 1mg 5mg |
| J63404 | Protein A, Staph. aureus [SpA] Lyophilized powder, 47 kDa, MDL MFCD00081934 Application(s): Used to detect immunoglobins in immunochemical assays | 25mg |












| Stock # | Description | Size |
|---------|--|------------------------|
| J63377 | Protein coupling kit Liquid, Note: This kit contains 1L of: Gel swelling solution (1 mM HCl), Gel Coupling Solution (10mM sodium borate or citrate, 500mM sodium chloride, pH 9.3), Gel washing solution (100mM sodium acetate, 500mM sodium chloride, pH 4.0). Application(s): For protein coupling in affinity chromatography applications | 1kit |
| J61622 | Protein Kinase C Substrate [Val-Arg-Lys-Arg-Thr-Leu-Arg-Arg-Leu] C ₅₁ H ₁₀₀ N ₂₂ O ₁₁ , F.W. 1197.50, Lyophilized powder | 1mg 5mg |
| J61687 | Protein Kinase Inhibitor [K252a] [97161-97-2], C ₂₇ H ₂₁ N ₃ O ₅ , F.W. 467.47, Powder, RTECS NZ0550000, MDL MFCD00133989 | 1mg 5mg |
| J62051 | Proteinase K, Tritirachium album limber [39450-01-6], Lyophilized powder, 28.9 kDa, EINECS 254-457-8, MDL MFCD00132129, Note: Minimum 20 units per mg dry weight. One unit releases one micromole of Folin positive amino acids, measured as tyrosine, at 37°C and pH 7.5, using urea denatured hemoglobin as the substrate ! H: H315-H319-H334-H335, P: P285-P305+P351+P338-P302+P352-P321-P405-P501 | 25mg 100mg |
| J63710 | Proteinase K, Ready-to-use soln. [39450-01-6], Liquid, 28.9 kDa, EINECS 254-457-8, Note: Minimum 400 units per ml. One unit releases one micromole of Folin positive amino acids, measured as tyrosine, at 37°C and pH 7.5, using urea denatured hemoglobin as the substrate. ! H: H315-H319-H334-H335, P: P285-P305+P351+P338-P302+P352-P321-P405-P501 | 5ml 25ml |
| J60042 | Psoralen, 97% [7H-Furo[3,2-g]benzopyran-7-one, Furo[3,2-g]coumarin] [66-97-7], C ₁₁ H ₆ O ₃ , F.W. 186.16, Solid, m.p. 163-164°, Merck 14,7928, EINECS 200-639-7, RTECS LV0944000, BRN 152784, MDL MFCD00010520 ! H: H302-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | 100mg 500mg |
| J64512 | PTP1B Inhibitor ▲ [3-(3,5-Dibromo-4-hydroxy-benzoyl)-2-ethyl-benzofuran-6-sulfonicacid-(4-(thiazol-2-ylsulfamyl)-phenyl)-amide] [765317-72-4], C ₂₆ H ₁₈ Br ₂ N ₃ O ₅ S ₂ , F.W. 741.45, Solid | 5mg |
| J60999 | Purine, 98% [7H-Imidazo[4,5-d]pyrimidine] [120-73-0], C ₅ H ₄ N ₄ , F.W. 120.11, Crystals, m.p. 215-217°, Merck 14,7942, EINECS 204-421-2, RTECS UO7450000, BRN 3200, MDL MFCD00079221 | 1g 5g |
| J60175 | 6-Purinethiol monohydrate , see 6-Mercaptopurine monohydrate, A12197, p. 281 | |
| J60175 | Puromycin, 98+% [53-79-2], C ₂₂ H ₂₉ N ₇ O ₅ , F.W. 471.51, Powder, Merck 14,7943, UN2811, RTECS AU7350000, BRN 3853613, MDL MFCD00012691 H: H300, P: P264-P270-P301+P310-P321-P405-P501a | 10mg 25mg 100mg |
| J61278 | Puromycin dihydrochloride, 99+% [58-58-2], C ₂₂ H ₂₉ N ₇ O ₅ ·2HCl, F.W. 544.44, Powder, m.p. 168-170°, Merck 14,7943, EINECS 200-387-8, RTECS AU355000, BRN 3853613, MDL MFCD00012691 ! H: H302, P: P264-P270-P301+P312-P330-P501a | 25mg 100mg 500mg |
| | Putrescine , see 1,4-Diaminobutane, B21316, p. 182 Putrescine dihydrochloride , see 1,4-Diaminobutane dihydrochloride, A18312, p. 182 PVP , see Polyvinylpyrrolidone, M.W. 40,000, J62417, p. 325 PVP K15 , see Polyvinylpyrrolidone, M.W. 10,000, J60382, p. 325 PVP K-30 , see Polyvinylpyrrolidone, average M.W. 58,000, A14315, p. 325 PVP K90 , see Polyvinylpyrrolidone, M.W. 360,000, J61381, p. 325 | |




| Stock # | Description | Size |
|---------|--|------|
| L11252 | Pyranine <i>[C.I. 59040, 6-Hydroxy-1,3,8-pyrenetrisulfonic acid trisodium salt]</i> [6358-69-6], C ₁₆ H ₈ Na ₃ O ₁₀ S ₃ , F.W. 524.39, EINECS 228-783-6, RTECS UR2700000, BRN 4107272, MDL MFCD00037575, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 5g |
| | | 25g |
| |  | |
| | 1H-Pyrazolo[3,4-d]pyrimidine-4,6(5H,7H)-dione , see 4,6-Dihydroxy-1H-pyrazolo[3,4-d]pyrimidine, L07160, p. 193 4-Pyridinamine , see 4-Aminopyridine, 99+%, J61470, p. 99 Pyridine-3-carboxamide , see Nicotinamide, A15970, p. 301 Pyridine-3-carboxylic acid , see Nicotinic acid, A12683, p. 302 Pyridine-4-carboxylic acid , see Isonicotinic acid, A18109, p. 261 Pyridine-4-carboxylic hydrazide , see Isonicotinic acid hydrazide, A10583, p. 261 | |
| A11414 | Pyridine-2,3-dicarboxylic acid, 99% <i>[Quinolinic acid]</i> [89-00-9], C ₆ H ₄ NO ₄ , F.W. 167.12, m.p. ca 188° dec., Merck 14,8073, EINECS 201-874-8, RTECS US7967250, BRN 137110, MDL MFCD00006295, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): Endogenous NMDA agonist | 25g |
| | | 100g |
| |  | |
| A14580 | Pyridine-3,4-dicarboxylic acid, 98% <i>[Cinchomeronic acid]</i> [490-11-9], C ₆ H ₄ NO ₄ , F.W. 167.12, m.p. ca 255° dec., Merck 14,2283, EINECS 207-705-4, BRN 137242, MDL MFCD00006392 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 10g |
| | | 50g |
| |  | |
| | Pyridine-3-thiocarboxamide , see Thionicotinamide, A11144, p. 367 | |
| A12323 | Pyridoxal-5-phosphate monohydrate, 98% ▲ [41468-25-1], C ₈ H ₁₀ NO ₆ P·H ₂ O, F.W. 265.17 (247.15anhy), m.p. 140-143°, Merck 14,7979, MDL MFCD00149414, † Application(s): Active form of Vitamin B-6 | 1g |
| | | 5g |
| |  | 25g |
| J62679 | Pyridoxamine dihydrochloride, Cell Culture Reagent <i>[4-(Aminomethyl)-5-hydroxy-6-methyl-3-pyridinemethanol dihydrochloride]</i> [524-36-7], C ₈ H ₁₂ N ₂ O ₂ ·2HCl, F.W. 241.12, Solid, m.p. 220-224°, Merck 14,7980, EINECS 208-357-6, RTECS UV1230000, BRN 3632748, MDL MFCD00012808 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 2.5g |
| | | 5g |
| |  | 10g |
| | Application(s): A vitamin in the Vitamin B-6 family | |
| | 2-(3-Pyridylcarbonylamino)ethyl nitrate , see Nicorandil, 98+%, J60879, p. 301 2-(3-Pyridyl)piperidine , see (±)-Anabasin, L12089, p. 103 DL-2-(3-Pyridyl)pyrrolidine , see DL-Nornicotine, L10809, p. 305 | |
| J63247 | Pyrilamine maleate <i>[Mepyramine maleate]</i> [59-33-6], C ₁₇ H ₂₃ N ₃ O ₄ ·C ₄ H ₄ O ₄ , F.W. 401.46, Powder, Merck 14,7984, EINECS 200-422-7, RTECS UT1225000, MDL MFCD00069333, † ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 25g |
| | | 100g |
| | Application(s): Selective inverse agonist for the H ₁ -histamine receptor | |
| | 2-Pyrimidinamine , see 2-Aminopyrimidine, B24594, p. 99 4,6-Pyrimidinediol , see 4,6-Dihydroxypyrimidine, A15688, p. 193 2,4,5,6(1H,3H)-Pyrimidinetetrone , see Alloxan monohydrate, A15324, p. 89 4-Pyrimidinol , see 4(3H)-Pyrimidone, A10859, p. 332 | |
| A10859 | 4(3H)-Pyrimidone, 98+% <i>[4-Hydroxypyrimidine, 4-Pyrimidinol]</i> [51953-17-4], C ₄ H ₄ N ₂ O, F.W. 96.09, m.p. 164-167°, EINECS 257-545-4, RTECS UW7350000, BRN 106975, MDL MFCD00167178, † | 1g |
| | | 5g |
| |  | |
| | 4-Pyrimidone , see 4(3H)-Pyrimidone, A10859, p. 332 Pyrocatechol , see Catechol, A10164, p. 150 DL-Pyroglutamic acid , see (±)-2-Pyrrolidinone-5-carboxylic acid, L09424, p. 333 D-Pyroglutaminol , see (R)-(-)-5-(Hydroxymethyl)-2-pyrrolidinone, L18358, p. 250 L-Pyroglutaminol , see (S)-(+)-5-(Hydroxymethyl)-2-pyrrolidinone, L18359, p. 250 Pyronin G , see Pyronin Y, J61068, p. 332 | |
| J61068 | Pyronin Y <i>[C.I. 45005, Pyronin G]</i> [92-32-0], C ₁₇ H ₁₅ ClNO, F.W. 302.80, Crystalline powder, m.p. 250-260°, Merck 14,8007, EINECS 202-147-8, RTECS BQ1450000, BRN 3795789, MDL MFCD00011725, † Application(s): Marker dye for RNA useful in acid buffer systems | 1g |
| | | 5g |
| |  | 10g |
| J60505 | Pyronin Y, 0.2% w/v aq. soln. <i>[C.I. 45005, Pyronin G]</i> [92-32-0], C ₁₇ H ₁₅ ClNO, F.W. 302.80, Liquid, Merck 14,8007, BRN 3795789, MDL MFCD00011725, † | 10ml |
| | | 25ml |
| | 1H-Pyrrole-2,5-dione , see Maleimide, A13135, p. 275 | |




| Stock # | Description | Size |
|---------|--|--|
| | (+/-)- Pyrrrolidine-2-acetic acid hydrochloride , see DL-▲-Homoproline hydrochloride, H31749, p. 246 | |
| B23731 | 1-Pyrrrolidinedithiocarbamic acid ammonium salt, 98% ■ [Ammonium pyrrrolidinedithiocarbamate, APDC] [5108-96-3], C ₄ H ₁₂ N ₂ S ₂ , F.W. 164.29, m.p. 150-155°, EINECS 225-834-4, BRN 3730472, MDL MFCD00012720, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Chelating ligand useful for the extraction of many metals from aqueous solution. | 25g 100g  |
| | 2.5-Pyrrrolidinedione , see Succinimide, A13503, p. 354 (R)-(-)-2-Pyrrrolidinemethanol , see (R)-(-)-Prolinol, L11109, p. 329 (S)-(+)-2-Pyrrrolidinemethanol , see (S)-(+)-Prolinol, L09779, p. 329 (R)-(+)-3-Pyrrrolidinol , see (R)-(+)-3-Hydroxypyrrrolidine, L19499, p. 251 (S)-(-)-3-Pyrrrolidinol , see (S)-(-)-3-Hydroxypyrrrolidine, L19498, p. 251 | |
| L09424 | (±)-2-Pyrrrolidinone-5-carboxylic acid, 99% [DL-Pyrrrolidone-5-carboxylic acid, H-DL-Pyr-OH] [149-87-1], C ₅ H ₇ NO ₃ , F.W. 129.12, m.p. 183-185°, EINECS 205-748-3, BRN 82131, MDL MFCD00064322 ! H:H318-H335-H315, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 50g 250g  |
| | DL-2-Pyrrrolidone-5-carboxylic acid , see (±)-2-Pyrrrolidinone-5-carboxylic acid, L09424, p. 333 1H-Pyrrrolo[2,3-b]pyridine , see 7-Azaindole, L07983, p. 114 | |
| J61373 | Pyruvate Kinase, rabbit muscle [Phosphoenolpyruvate kinase, Phosphoenol transphosphorylase] [9001-59-6], Lyophilized powder, EINECS 232-616-2, MDL MFCD00081946, Note: Minimum 375 units per mg solid; 500 units per mg protein. One unit liberates 1 micromole pyruvate per minute from PEP in the presence of ADP at 30 C and pH 7.6., † | 50kilounits |
| A13875 | Pyruvic acid, 98% [2-Oxopropionic acid] [127-17-3], C ₃ H ₄ O ₃ , F.W. 88.06, m.p. 11-12°, b.p. 164-166°, f.p. 83°(181°F), d. 1.267, n _D ²⁰ 1.4295, Merck 14,8021, Fieser 1,974, UN3265, EINECS 204-824-3, RTECS UZ0829800, BRN 506211, MDL MFCD00002585, † ! H:H314, P:P260-P305+P351+P338-P309-P310 | 100g 500g 2.5kg  |
| | Pyruvic acid sodium salt , see Sodium pyruvate, Cell Culture Grade, J61840, p. 348 | |
| A15807 | Quercetin dihydrate, 97% [3,3',4',5',7-Pentahydroxyflavone dihydrate, Quercetin hydrate] [6151-25-3], C ₁₅ H ₁₀ O ₇ ·2H ₂ O, F.W. 338.28 (302.25anhy), m.p. 310-315°, Merck 14,8034, UN2811, EINECS 204-187-1, RTECS LK8950000, BRN 317313, MDL MFCD00149487, † ! H:H301-H341, P:P281-P301+P310-P321-P308+P313-P405-P501a | 25g 100g 500g  |
| | Application(s): Inhibitor of protein tyrosine kinase | |
| | Quercetin hydrate , see Quercetin dihydrate, A15807, p. 333 | |
| J61919 | Quin 2 [73630-23-6], C ₂₆ H ₂₃ K ₄ N ₃ O ₁₀ , F.W. 693.87, Powder, Merck 14,8042, BRN 5374262, MDL MFCD00065487 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 100mg |
| | Application(s): A highly specific fluorescent calcium indicator | |
| A13412 | Quinaldine, 97+% ▲ ▲ [2-Methylquinoline] [91-63-4], C ₁₀ H ₉ N, F.W. 143.19, m.p. -2°, b.p. 247-248°, f.p. 79°(174°F), d. 1.058, n _D ²⁰ 1.6120, Merck 14,8047, EINECS 202-085-1, RTECS UZ9625000, BRN 110309, MDL MFCD00006756, † ! H:H302-H312-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 25g 100g 500g  |
| | Application(s): Used in preparation of oil-soluble dyes | |
| J61913 | Quinapril hydrochloride, 98% [82586-55-8], C ₂₈ H ₃₀ N ₂ O ₅ ·HCl, F.W. 474.99, Solid, m.p. 120-130°, Merck 14,8051, RTECS NW7176000, MDL MFCD00889215 | 100mg 1g 5g |
| | Application(s): Angiotensin-converting enzyme inhibitor | |
| B24094 | Quinazoline, 98% [253-82-7], C ₈ H ₆ N ₂ , F.W. 130.15, m.p. 45-48°, b.p. 243°, f.p. 106°(224°F), Merck 14,8053, EINECS 205-965-3, MDL MFCD00006712 | 1g 5g  |
| | Application(s): Anti-malarial agent | |
| A12559 | (+)-Quinidine ▲ [56-54-2], C ₂₀ H ₂₄ N ₂ O ₂ , F.W. 324.42, m.p. 171-173°, [α] _D ²⁰ +260° (c=1 in ethanol), Merck 14,8060, Fieser 15,277, EINECS 200-279-0, RTECS VA4725000, BRN 91866, MDL MFCD00135581, † ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 1g 5g 25g  |
| | Application(s): Antiarrhythmic agent that blocks the inward sodium channel | |



| Stock # | Description | Size |
|--|--|-----------------------|
| J60426 | Quinidine sulfate dihydrate, 98+% [6591-63-5], C ₂₀ H ₂₆ N ₂ O ₄ ·H ₂ O·S ₂ H ₂ O, F.W. 782.94, Powder, m.p. 212-214°, Merck 14,8060, RTECS VA5605000, MDL MFCD00149346 ! H:H302, P:P264-P270-P301+P312-P330-P501 | 5g 25g |
| Application(s): A sodium channel blocker, and to a lesser extent also blocks potassium channels | | |
| A10459 | Quinine, anhydrous, 99% (total base), may cont. up to 5% dihydroquinine ▲ [130-95-0], C ₂₀ H ₂₄ N ₂ O ₂ , F.W. 324.42, m.p. ca 177° dec., [α] _D ²⁰ -166° (c=1 in ethanol), Merck 14,8061, Fieser 6,501 7,311 8,430 9,403 10,338 11,456 15,277, EINECS 205-003-2, RTECS VA6020000, BRN 91867, MDL MFCD00198096, † ! H:H334-H302-H335-H315-H319-H317, P:P285-P305+P351+P338-P302+P352-P321-P405-P501a Resolving agent for chiral acids. For a review of resolutions, see: <i>Topics Stereochem.</i> , 6, 107 (1977). | 10g 50g 250g |
| Application(s): A potassium channel blocker | | |
| A17036 | Quinine hemisulfate monohydrate, 99% ▲ [Quinine sulfate dihydrate] [6119-70-6], C ₂₀ H ₂₄ N ₂ O ₂ ·0.5H ₂ SO ₄ ·H ₂ O, F.W. 391.47 (373.46anhy), m.p. 217-218° dec., [α] _D ²⁰ -230° (c=2 in 0.1M HCl), Merck 14,8061, EINECS 212-359-2, RTECS VA8440000, BRN 6113937, MDL MFCD00150792, † ! H:H334-H302-H317, P:P285-P261-P280-P302+P352-P321-P501a | 10g 50g 250g |
| Application(s): A potassium channel blocker | | |
| Quinine sulfate dihydrate , see Quinine hemisulfate monohydrate, A17036, p. 334 Quinizarin , see 1,4-Dihydroxyanthraquinone, A11010, p. 191 Quinol , see Hydroquinone, A11411, p. 248 Quinolinic acid , see Pyridine-2,3-dicarboxylic acid, A11414, p. 332 8-Quinolol , see 8-Hydroxyquinoline, 41272, p. 251 | | |
| J65627 | N-(2-Quinolyl)valyl-aspartyl-(2,6-difluorophenoxy)methyl ketone hydrate ▲ ■ [Q-VD-OPH hydrate, Q-Val-Asp-CH2-OPh] [1135695-98-5], C ₂₆ H ₂₅ F ₂ N ₃ O ₆ ·xH ₂ O, F.W. 513.49 (anhy), Powder, MDL MFCD20527311 | 5mg |
| A14055 | Quinoxaline, 98+% [91-19-0], C ₈ H ₆ N ₂ , F.W. 130.15, m.p. 27-32°, b.p. 220-223°, f.p. 98°(208°F), d. 1.124, Merck 14,8078, EINECS 202-047-4, RTECS VD1225000, BRN 109351, MDL MFCD00006719, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 100g 500g 2.5kg |
| Application(s): Used as dyes, pharmaceuticals and antibiotics intermediate | | |
| B21503 | 3-Quinuclidinol, 98+% ▲ [1-Azabicyclo[2.2.2]octan-3-ol, 3-Hydroxyquinuclidine] [1619-34-7], C ₇ H ₁₃ NO, F.W. 127.19, m.p. 217-224°, Merck 14,8082, Fieser 6,501, UN3263, EINECS 216-578-4, RTECS VD6191700, BRN 104327, MDL MFCD00151326, † ! H:H314, P:P260-P303+P361+P353-P305+P351+P338-P301+P330-P331-P405-P501a Reagent for selective cleavage of β-keto esters to ketones in high yield: <i>Synth. Commun.</i> , 5, 341 (1975). Geminal diesters are converted to monoesters in high yield under similar conditions: <i>J. Org. Chem.</i> , 41, 208 (1976). Superior catalyst for the Baylis-Hillman reaction: the addition of acrylic esters to aldehydes, often very slow (4-7 days) with the usual catalyst 1,4-Diazabicyclo[2.2.2]octane, A14003 , is much faster (<1 day) in the presence of quinuclidinol: <i>Synth. Commun.</i> , 18, 495 (1988); <i>Tetrahedron Lett.</i> , 32, 5611 (1991). For more recent discussion and methodology, see: <i>J. Org. Chem.</i> , 67, 510 (2002); 68, 692 (2003). For reviews of the Baylis-Hillman reaction, see: <i>Tetrahedron</i> , 44, 4653 (1988); 52, 8001 (1996). The rate of addition of enones to aldehydes is similarly enhanced: <i>Synth. Commun.</i> , 18, 495 (1988); 19, 959 (1989). | 5g 25g 100g |
| A13320 | 3-Quinuclidinone hydrochloride, 98+% ■ [1-Azabicyclo[2.2.2]octan-3-one hydrochloride] [1193-65-3], C ₇ H ₁₁ NO·HCl, F.W. 161.63, m.p. ca 300° dec., EINECS 214-776-5, BRN 3695039, MDL MFCD00137391, † | 5g 25g 100g |
| J61933 | Quipazine dimaleate, 99+% [2-(1-Piperaziny)quinoline maleate salt] [5786-68-5], C ₁₃ H ₁₅ N ₃ ·2C ₄ H ₄ O ₄ , F.W. 445.43, Solid, m.p. 151-154°, UN2811, EINECS 227-314-2, RTECS VC2515000, MDL MFCD00133796 ! H:H301, P:P264-P270-P301+P310-P321-P405-P501a | 100mg |
| Application(s): Selective 5-HT-3 receptor agonist | | |
| J61591 | (+)-Quisqualic acid, 99+% [β-(3,5-Dioxo-1,2,4-oxadiazolidin-2-yl)-L-alanine, 3-(3,5-Dioxo-1,2,4-oxadiazolidin-2-yl)-L-alanine] [52809-07-1], C ₅ H ₇ N ₃ O ₅ , F.W. 189.13, Powder, m.p. 185-187°, Merck 14,8085, BRN 1078734, MDL MFCD00069337 ! H:H302-H312-H332, P:P261-P280-P302+P352-P304+P340-P322-P501 | 5mg 10mg 50mg |
| Application(s): Group I mGlu receptor agonist. AMPA agonist | | |
| QX-314 bromide , see Lidocaine N-ethyl bromide, 99+%, J60678, p. 270 R 41 468 , see Ketanserin tartrate, 98+%, J62798, p. 263 | | |
| J65639 | R5C3 [5-Methyl-N-(2-phenoxybenzoyl)-1-[(phenylmethoxy)carbonyl]-D/L-tryptophan] [753504-14-2], C ₃₃ H ₂₈ N ₂ O ₆ , F.W. 548.58, Powder, MDL MFCD08705330 | 10mg |


| Stock # | Description | Size |
|---------|---|------------------------|
| J65195 | Rabbit Serum | 5ml |
| A18313 | D-(+)-Raffinose pentahydrate, 99% ■ [<i>Melitose pentahydrate</i>] [17629-30-0], C ₁₈ H ₃₂ O ₁₆ ·5H ₂ O, F.W. 594.52 (504.45anhy), m.p. 78-82°, [α] _D ²⁰ +105° (c=10 in water), Merck 14,8096, EINECS 208-146-9, RTECS LZ5851200, BRN 4285763, MDL MFCD00071590, Note: [α] _D ²⁰ =+105.2°(C=4), † | 10g 50g |
| |  | |
| | RAMP , see (R)-(+)-1-Amino-2-(methoxymethyl)pyrrolidine, J60524, p. 96 | |
| J61334 | Ranatensin, 96% [<i>Glp-Val-Pro-Gln-Trp-Ala-Val-Gly-His-Phe-Met-NH2</i>] [29451-71-6], C ₆₁ H ₈₄ N ₁₀ O ₁₅ S, F.W. 1281.48, Powder, MDL MFCD00167518 | 2mg |
| | Application(s): Demonstrates various blood pressure effects | |
| B22260 | Ranitidine hydrochloride, 99% [66357-59-3], C ₁₃ H ₂₂ N ₂ O ₃ S·HCl, F.W. 350.86, m.p. ca 134° dec., Merck 14,8110, EINECS 266-333-0, MDL MFCD00069339 | 5g 25g |
| | ! H:H302, P:P264-P270-P301+P312-P330-P501a | |
| | Application(s): An H-2 histamine receptor antagonist | |
| J62473 | Rapamycin, 99+% [<i>Sirolimus, AY-22989</i>] [53123-88-9], C ₃₁ H ₇₉ NO ₁₃ , F.W. 914.17, Powder, Merck 14,8114, RTECS VE6250000, MDL MFCD00867594, Note: Store at -20 | 50mg 100mg 200mg |
| | Application(s): Blocks cytokine-mediated signal transduction pathways | |
| J61347 | Rapid stain G-250 | 500ml 1L |
| | Liquid | |
| J61969 | Rapid stain R-250 | 500ml 1L |
| | Liquid | |
| J63198 | Rauwolscine hydrochloride, 99% ▲ [<i>α-Yohimbine hydrochloride, 17α-Hydroxy-20α-yohimban-16β-carboxylic acid methyl ester hydrochloride</i>] [6211-32-1], C ₂₁ H ₂₆ N ₂ O ₃ ·HCl, F.W. 390.91, Powder, UN1544, EINECS 228-279-6, RTECS ZG1035000, MDL MFCD06668052 | 100mg |
| | ! H:H301-H311-H330, P:P301+P310-P304+P340-P320-P330-P361-P405-P501a | |
| | Application(s): Standard α-2 adrenergic antagonist | |
| J62990 | RBC lysis buffer for human | 250ml 500ml |
| | Liquid, Note: Contains 150mM ammonium chloride, 10mM potassium bicarbonate, 0.1mM EDTA at pH 7.2-7.4., † | |
| | Application(s): For lysis of human red blood cells. | |
| J62150 | RBC lysis buffer for mouse | 250ml 500ml |
| | Liquid, Note: Contains 10mM Tris-HCl, 150mM ammonium chloride at pH 7.2-7.4., † | |
| | Application(s): For lysis of mouse red blood cells | |
| | RC-160 , see Vapreotide, J61096, p. 391 | |
| | Regulin , see Melatonin, 99+%, J62452, p. 279 | |
| | Reinecke salt , see Ammonium diamminetetrahydrocyanatochromate(III) monohydrate, 87777, p. 101 | |
| B21187 | Resazurin sodium salt [<i>7-Hydroxy-3H-phenoxazin-3-one-10-oxide sodium salt</i>] [62758-13-8], C ₉ H ₆ NNaO ₃ , F.W. 251.18, Merck 14,8141, EINECS 263-718-5, RTECS SP7700000, BRN 3794971, MDL MFCD00005036, † | 1g 5g |
| | ! H:H315-H319-H335, P:P280g-P305+P351+P338 | |
| | Application(s): As indicator pH 3.8 (orange) to 6.5 (dark violet) | |
| L03506 | Reserpine, 99% [50-55-5], C ₃₃ H ₄₀ N ₂ O ₉ , F.W. 608.69, m.p. ca 265°, [α] _D ²⁰ -122° (c=1 in chloroform), Merck 14,8145, EINECS 200-047-9, RTECS ZG0350000, BRN 102014, MDL MFCD00005091, † | 1g 5g |
| | ! H:H360-H351-H302, P:P281-P264-P301+P312-P308+P313-P405-P501a | |
| | Application(s): Inhibits vesicular uptake of catecholamines and serotonin | |
| |  | |

| Stock # | Description | Size |
|--|--|---|
| J62458 | Resiniferatoxin, 99+% [57444-62-9], C ₃₃ H ₄₀ O ₉ , F.W. 628.71, Solid, UN2811, RTECS CY1633700, BRN 5371150, MDL MFCD00135927  H:H301-H315-H319-H335, P:P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a | 1mg 5mg 10mg |
| Application(s): Diterpene ester related to phorbol but apparently not tumorigenic; activates protein kinase C | | |
| A13080 | Resorcinol, 99% ▲ ▲ [1,3-Dihydroxybenzene, 1,3-Benzenediol] [108-46-3], C ₆ H ₆ O ₂ , F.W. 110.11, m.p. 109-112°, b.p. 280-281°, f.p. 171°(339°F), d. 1.272, Merck 14,8155, UN2876, EINECS 203-585-2, RTECS VG9625000, BRN 906905, MDL MFCD00002269, †   | 50g 250g 1kg 5kg |
| 36248 | Resorcinol, ACS, 99.0-100.5% ▲ ▲ [1,3-Dihydroxybenzene, 1,3-Benzenediol] [108-46-3], C ₆ H ₆ O ₂ , F.W. 110.11, m.p. 109-112°, b.p. 280-281°, f.p. 171°(339°F), d. 1.272, Merck 14,8155, Solubility: Soluble in water, alcohol, ether, and glycerol, UN2876, EINECS 203-585-2, RTECS VG9625000, BRN 906905, MDL MFCD00002269, † Maximum level of impurities: Melting point 110-112°, Insoluble matter 0.005%, Residue after ignition 0.01%, Titratable acid 0.004meq/g  | 25g 100g 500g |
| Resorufin ethyl ether, see 7-Ethoxyresorufin, J62987, p. 214 | | |
| J60790 | Resveratrol, 98% [501-36-0], C ₁₆ H ₁₂ O ₅ , F.W. 228.24, Powder, Merck 14,8158, RTECS CZ8987000, MDL MFCD00133799  | 500mg |
| Application(s): A phytoestrogen with antitumor, antioxidant, antiplatelet, anti-inflammatory effects. Inhibits cytochrome P450 1A1 (IC ₅₀ = 23 d ₁ μM) and displays mixed agonist/antagonist actions at ER-α and ER-β estrogen receptors | | |
| J62219 | 9-cis-Retinoic acid [5300-03-8], C ₂₀ H ₂₈ O ₂ , F.W. 300.44, Powder, Merck 14,249, RTECS VH6450000, MDL MFCD00270072  | 5mg |
| Application(s): A high affinity ligand for the retinoid X receptor | | |
| J61666 | 13-cis-Retinoic acid [Isotretinoin] [4759-48-2], C ₂₀ H ₂₈ O ₂ , F.W. 300.44, Powder, m.p. 172-175°, Merck 14,5228, EINECS 225-296-0, RTECS VH6440000, MDL MFCD00079542, †  | 500mg |
| Application(s): A vitamin A analog that inhibits cell proliferation and induces cell differentiation | | |
| 44540 | Retinoic acid, 98% ▲ [Vitamin A acid] [302-79-4], C ₂₀ H ₂₈ O ₂ , F.W. 300.44, Crystalline, m.p. 180-182°, Merck 14,8165, EINECS 206-129-0, RTECS VH6475000, BRN 2057223, MDL MFCD00001551, †   | 100mg 500mg 2g |
| J62079 | Retinol, 98%, synthetic ▲ ▯ [Vitamin A alcohol] [68-26-8], C ₂₀ H ₃₀ O, F.W. 286.46, Crystalline solid, Merck 14,10013, EINECS 200-683-7, RTECS VH6750000, BRN 403040, MDL MFCD00001552, †  | 1g 5g |
| Retinol acetate, see Vitamin A acetate in gelatin, A16237, p. 392 Retinol palmitate, see Retinol palmitate, 98+%, J63022, p. 392 Retinyl acetate, see Vitamin A acetate in gelatin, A16237, p. 392 Retinyl palmitate, see Vitamin A Palmitate, 98+%, J63022, p. 392 | | |
| J65829 | Reverse Transcriptase, Avian Myeloblastosis Virus in phosphate buffer [EC 2.7.7.49] Liquid | 1kilounit |
| Application(s): Synthesizes DNA complements to RNA transcripts | | |
| J60167 | Reverse Transcriptase, murine, Moloney Murine Leukemia Virus [MMLV RT] [9068-38-6], Liquid, EINECS 232-964-5, MDL MFCD00283754, Note: One unit is the amount of enzyme required to catalyze the transfer of 1 nmol of deoxynucleotide into acid-precipitable material in 10 minutes at 37°C. 200,000 units/ml in 20 mM Tris-HCl (pH 7.5), 200 mM NaCl, 1 mM DTT, 0.01% NP-40, 0.1 mM EDTA, 50% glycerol | 10kilounits |
| Application(s): Synthesizes a complementary DNA strand using single-stranded RNA or DNA in the presence of a primer | | |
| A16166 | L-(+)-Rhamnose monohydrate, 99% [6-Deoxy-L-mannose monohydrate] [10030-85-0], C ₈ H ₁₂ O ₅ ·H ₂ O, F.W. 182.19 (164.17anhy), m.p. 89-94°, d. 1.47, [α] _D ²⁰ +8° (c=10 in water, 20h), Merck 14,8172, EINECS 222-793-4, BRN 5988592, MDL MFCD00149363, †  | 5g 25g 100g |




| Stock # | Description | Size |
|--|--|------------------------------|
| J62315 | Rhodamine 6G [Basic Red 1, C.I. 45160] [989-38-8], C ₂₈ H ₃₁ ClN ₂ O ₃ , F.W. 479.02, Powder, EINECS 213-584-9, RTECS DH0175000, BRN 3900071, MDL MFCD00012665, † ! H:302, P:264-P270-P301+P312-P330-P501a | 25g 100g |
| Application(s): Suitable for fluorescent labelling | | |
| A13572 | Rhodamine B [Basic Violet 10, C.I. 45170] [81-88-9], C ₂₈ H ₃₁ ClN ₂ O ₃ , F.W. 479.02, m.p. ca 210° dec., d. 1.31, Merck 14,8183, EINECS 201-383-9, RTECS BP3675000, BRN 4119648, MDL MFCD00011931, †  ! H:318-H351-H302, P:280-P281-P305+P351+P338-P310-P405-P501a Biological stain. Reagent for determination of Cd and Zn: <i>Anal. Chem.</i> , 176 , 285 (1960); also for various other metals. | 50g 250g 1kg |
| Application(s): Suitable for fluorescent labelling | | |
| A13622 | Rhodanile Blue [14969-56-3], C ₄₈ H ₄₆ ClN ₅ O ₅ , F.W. 778.40, EINECS 239-040-0, MDL MFCD00011937 ! H:351-H319, P:280-P281-P305+P351+P338-P308+P313-P405-P501a | 1g 5g 25g |
| Application(s): Complex of Rhodamine B and Nile Blue. | | |
| Rhodeose , see D-(+)-Fucose, A18234, p. 228 Ribitol , see Adonitol, L03253, p. 80 | | |
| A11764 | Riboflavin, 98% ▲ [Vitamin B ₂] [83-88-5], C ₁₇ H ₂₀ N ₄ O ₆ , F.W. 376.37, m.p. >300°, Merck 14,8200, EINECS 201-507-1, MDL MFCD00005022, †  | 25g 100g |
| Application(s): Photoinitiator of polymerization for PAGE gels | | |
| Riboflavin 5'-adenosine diphosphate disodium salt , see Flavin adenine dinucleotide disodium salt hydrate, A14495, p. 221 | | |
| A14545 | Riboflavin-5'-phosphate sodium salt dihydrate [FMN-Na] [6184-17-4], C ₁₇ H ₂₀ N ₄ NaO ₉ P·2H ₂ O, F.W. 514.36 (478.34anhy), m.p. >300°, Merck 14,8201, EINECS 204-988-6, BRN 4106529, MDL MFCD00150993, †  | 10g 50g |
| Application(s): Photoinitiator of polymerization for PAGE gels | | |
| 2-β-D-Ribofuranosyl-1,2,4-triazine-3,5(2H,4H)-dione , see 6-Azauridine, J61309, p. 114 | | |
| J62952 | Ribonuclease, bovine pancreas Lyophilized powder, Note: 0.22 micron filtered; sterile. Minimum 2,500 units per mg. One unit causes an increase in absorbance of 1.0 at 260nm at 37 C and pH 5.0 when yeast ribosomal RNA is hydrolyzed to acid soluble oligonucleotides. | 100mg |
| J62232 | Ribonuclease A, bovine pancreas, Molecular Biology Grade ▣ [EC 3.1.27.5, <i>Rnase A</i>] [9001-99-4], Lyophilized powder, Merck 14,8202, EINECS 232-646-6, RTECS RF0760000, MDL MFCD00132181, Note: Minimum 2500 units/mg dry wt. Chromatographically purified. One unit causes an increase in absorbance of 1.0 at 260nm at 37°C and pH 5.0 when yeast ribosomal RNA is hydrolyzed to acid soluble oligonucleotides., † | 200mg 1g |
| J61996 | Ribonuclease A, bovine pancreas, purified ▣ [EC 3.1.27.5, <i>Rnase A</i>] [9001-99-4], Lyophilized powder, Merck 14,8202, EINECS 232-646-6, RTECS RF0760000, MDL MFCD00132181, Note: Chromatographically purified. Unsuitable for heat treatment. Minimum 3000 units/mg dry wt. One unit causes an increase in absorbance of 1.0 at 260nm at 37°C and pH 5.0 when yeast ribosomal RNA is hydrolyzed to acid soluble oligonucleotides., † | 25mg 100mg |
| J62334 | Ribonuclease B, bovine pancreas ▣ [EC 3.1.4.22, <i>RNase B</i>] [9001-99-4], Lyophilized powder, Merck 14,8202, EINECS 232-646-6, RTECS RF0760000, MDL MFCD00132181, Note: Minimum 1000 units/mg dry wt. One unit causes an increase in absorbance of 1.0 at 260nm at 37°C and pH 5.0 when yeast ribosomal RNA is hydrolyzed to acid soluble oligonucleotides, † | 100mg |
| J61644 | Ribonuclease T1, Aspergillus oryzae in 2.8M ammonium sulfate [9026-12-4], Liquid, MDL MFCD00132191, Note: One unit causes an increase in absorbance of 1.0 at 260nm at 37°C, pH 7.5 in 15 minutes. Minimum 300,000 units/mg protein. | 100kilounits 500kilounits |
| J61215 | Ribonucleic acid from Baker's yeast [63231-63-0], Powder, MDL MFCD00132195, Note: Primarily ribosomal RNA. Suitable substrate for ribonuclease assays, † | 100mg 1g |

| Stock # | Description | Size |
|---------|--|---|
| A17894 | D-(-)-Ribose, 98% ■ [50-69-1], C ₅ H ₁₀ O ₅ , F.W. 150.13, m.p. 82-86°, [α] _D ²⁰ -20° (c=10 in water, 28h), Merck 14,8204, EINECS 200-059-4, RTECS VJ2275000, BRN 1723081, MDL MFCD00135453, † For an evaluation of the potential of D-ribose as an enantiopure building block for construction of the C-ring of taxol, see: <i>J. Org. Chem.</i> , 60 , 7849 (1995). |  10g 50g 250g |
| B21117 | L-(+)-Ribose, 99% ■ [24259-59-4], C ₅ H ₁₀ O ₅ , F.W. 150.13, m.p. 85-88°, EINECS 246-110-4, MDL MFCD00167010 |  250mg 1g 5g |
| J60836 | Rifampin, Molecular Biology Grade [Rifampicin] [13292-46-1], C ₄₃ H ₅₈ N ₂ O ₁₂ , F.W. 822.94, Powder, m.p. 183-188°, Merck 14,8216, EINECS 236-312-0, RTECS VJ7000000, BRN 5723476, MDL MFCD00151389 ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 1g 5g 25g |
| J63095 | Rifamycin SV sodium, 98+% [14897-39-3], C ₃₇ H ₄₆ NNaO ₁₂ , F.W. 719.45, Powder, Merck 14,8218, EINECS 238-965-7 | 1g 5g |
| J63099 | Rigin, 96% [Gly-Gln-Pro-Arg] [77727-17-4], C ₁₈ H ₃₂ N ₆ O ₆ , F.W. 456.51, Powder | 5mg |
| J63306 | RIPA buffer Liquid, Note: 50mM Tris-HCl (pH 7.4), 150mM NaCl 1% NP-40, 0.5% sodium deoxycholate and 0.1% SDS, † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 250ml 500ml |
| J63324 | RIPA buffer (2X) Liquid, Note: Contains: 100mM Tris-HCl (pH 7.4) 300 mM NaCl, 2% NP-40, 1% sodium deoxycholate and 0.2% SDS., † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 125ml 250ml |
| J62524 | RIPA buffer (5X) Liquid, Note: 250mM Tris-HCl (pH 7.4), 750mM NaCl, 5% NP-40, 2.5% sodium deoxycholate, 0.5% SDS., †  H:H318, P:P280-P305+P351+P338-P310 | 50ml 100ml |
| J61529 | RIPA buffer with EDTA Liquid, Note: 50mM Tris-HCl (pH 7.4), 150mM NaCl 1% NP-40, 0.5% sodium deoxycholate and 0.1% SDS with 5mM EDTA. | 250ml 500ml |
| J60645 | RIPA buffer with EDTA + EGTA Liquid, Note: 50mM Tris-HCl (pH 7.4), 150mM NaCl 1% NP-40, 0.5% sodium deoxycholate and 0.1% SDS with 5mM EDTA and 1mM EGTA. | 250ml 500ml |
| J61951 | RIPA buffer with EGTA Liquid, Note: 50mM Tris-HCl (pH 7.4), 150mM NaCl 1% NP-40, 0.5% sodium deoxycholate and 0.1% SDS with 1mM EGTA. | 250ml 500ml |
| J61734 | RIPA with glycerol (2X) Liquid | 125ml 250ml |
| J62725 | RIPA buffer with Triton® X-100 (1X) Liquid, Note: 50mM Tris-HCl (pH 7.4), 150 mM NaCl, 1% Triton X-100, 0.5% sodium deoxycholate, 0.1% SDS. | 250ml 500ml |
| J60488 | RIPA buffer with Triton® X-100 (2X) Liquid, Note: 100mM Tris-HCl (pH 7.4), 300 mM NaCl, 2% Triton X-100, 1.0% sodium deoxycholate, 0.2% SDS. | 125ml 250ml |
| J62885 | RIPA buffer with Triton® X-100 (5X) Liquid, Note: 250mM Tris-HCl (pH 7.4), 750 mM NaCl, 5% Triton X-100, 2.5% sodium deoxycholate, 0.5% SDS. | 50ml 100ml |
| J60423 | RIPA buffer with Triton® X-100 + 10% glycerol (2X) Liquid, Note: 100mM Tris-HCl (pH 7.4) 300mM NaCl, 2% Triton X-100, 1% sodium deoxycholate, 0.2% SDS, 10% glycerol. | 125ml 250ml |
| J62189 | RIPA buffer-2 Liquid, Note: 50mM Tris-HCl (pH 8.0), 150mM NaCl, 1% NP-40 0.5% sodium deoxycholate, 0.1% SDS. | 250ml 500ml |
| J60629 | RIPA buffer-2 (2X) Liquid, Note: 100mM Tris-HCl (pH 8.0), 300mM NaCl, 2% NP-40, 1.0% sodium deoxycholate, 0.2% SDS. | 125ml 250ml |


| Stock # | Description | Size |
|---------|--|-----------------|
| J65379 | RITA, p53 inhibitor III ▲ [5,5'-(2,5-Furandiyl)bis-2-thiophenemethanol, NSC 652287] [213261-59-7], C ₁₄ H ₁₂ O ₃ S ₂ , F.W. 292.40, Crystalline solid | 1mg 10mg |
| J62832 | RNA sample loading buffer Liquid, Note: 62.5% Formamide, 1.14M Formaldehyde, 50ug/mL ethidium bromide in 1.25X MOPS buffer, ! ⚠ H:H317-H351-H360, P:P261-P280-P302+P352-P321-P405-P501 | 1ml 2ml |
| J62468 | RNA sample loading buffer (6X) Liquid, Note: Contains 50% glycerol, 1mM EDTA, 0.25% bromophenol blue and 0.25% xylene cyanol FF | 1ml 2ml |
| J61937 | RNA sample loading buffer, no ethidium bromide Liquid, Note: 62.5% formamide, 1.14M formaldehyde in MOPS buffer. 1.25X concentrate. ! ⚠ H:H317-H351-H360, P:P261-P280-P302+P352-P321-P405-P501 Application(s): Formulated for electrophoresis of RNA on formaldehyde-agarose gels with or without ethidium bromide | 1ml 2ml |
| | Rnase A , see Ribonuclease A, bovine pancreas, Molecular Biology Grade, J62232, p. 337 Rnase A , see Ribonuclease A, bovine pancreas, purified, J61996, p. 337 RNase B , see Ribonuclease B, bovine pancreas, J62334, p. 337 | |
| J61574 | RNase Removal Reagent Liquid, d. 1.00, Note: Supplied in a spray bottle Application(s): Destroys RNases and DNases on contact | 475ml |
| | Ro 1-7683 , see Tropicamide, 99+%, J61132, p. 383 Ro-18-0647 , see Orlistat, 98%, J62999, p. 308 Ro 15-1788 , see Flumazenil, 98%, J62537, p. 222 Romemsin , see Monensin sodium salt, 90-95.5%, J61669, p. 294 Roquessine , see Conessine, 97%, J62617, p. 167 Rosaniline hydrochloride , see Basic Fuchsin, A12952, p. 117 Rotundine , see L-Tetrahydropalmatine, J63911, p. 363 RP-87086 , see Glucose-6-phosphate dehydrogenase, yeast, J61181, p. 234 Saccharin , see o-Benzoic sulfimide, B23938, p. 119 Saccharin sodium hydrate , see o-Benzoic sulfimide sodium salt hydrate, A15530, p. 119 D-(+)-Saccharose , see Sucrose, 36508, p. 354 | |
| J63345 | Saclofen, 99+% [β-(Aminomethyl)-4-chlorobenzeneethanesulfonic acid] [125464-42-8], C ₉ H ₁₂ ClNO ₃ S, F.W. 249.71, Solid, MDL MFCD00216817 ! ⚠ H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): Selective antagonist at GABA-B receptors. An analog of baclofen | 10mg 50mg |
| J63982 | Safflower oil, Carthamus tinctorius [Carthamus tinctorius oil] [8001-23-8], Oil, f.p. >113°(235°F), d. 0.921, n _D ²⁰ 1.476, EINECS 232-276-5, RTECS VN2230000, MDL MFCD00132216, † | 500ml 1L |
| B21674 | Safranin O [C.I. 50240, 3,7-Diamino-2,8-dimethyl-5-phenylphenazinium chloride] [477-73-6], C ₂₀ H ₁₆ ClN ₄ , F.W. 350.85, EINECS 207-518-8, RTECS SG1623000, BRN 3924099, MDL MFCD00011759, † ! ⚠ H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Biological stain. Application(s): Redox and adsorption indicator. Biological stain used in histology, cytology, bacteriology | 10g 50g |
| |  | |
| J65248 | SAG ▲ [3-Chloro-N-[trans-4-(methylamino)cyclohexyl]-N-[[3-(4-pyridinyl)phenyl]methyl]-benzo[b]thiophene-2-carboxamide] [912545-86-9], C ₂₈ H ₂₈ ClN ₃ OS, F.W. 490.06, Oil | 1mg |
| J63741 | Salbutamol, 99% [Albuterol] [18559-94-9], C ₁₃ H ₂₁ NO ₃ , F.W. 239.31, Powder, m.p. 157-158°, Merck 14,216, EINECS 242-424-0, RTECS ZE4400000, BRN 6405698, MDL MFCD00148978 ! ⚠ H:H302, P:P264-P270-P301+P312-P330-P501 Application(s): A β-adrenergic agonist | 1g 5g 25g |
| A18544 | Salbutamol sulfate, 99% ▲ [Albuterol sulfate, α-[(tert-Butylamino)methyl]-4-hydroxy-1,3-benzenedimethanol sulfate] [51022-70-9], C ₂₀ H ₄₂ N ₂ O ₆ ·H ₂ SO ₄ , F.W. 576.70, EINECS 256-916-8, RTECS CZ6430100, MDL MFCD00055200 ! ⚠ H:H302, P:P264-P270-P301+P312-P330-P501a Application(s): A β-adrenergic agonist | 1g 5g 25g |
| |  | |

| Stock # | Description | Size |
|--|--|---|
| A16524 | D-(-)-Salicin, 99% [138-52-3], C ₁₃ H ₁₈ O ₇ , F.W. 286.28, m.p. 200-203°, [α] _D ²⁰ -62.5° (c=3 in water), Merck 14,8324, EINECS 205-331-6, RTECS LZ5901700, BRN 89593, MDL MFCD00006590, † Substrate for β-glucosidase. |  5g 25g 100g |
| Application(s): An analgesic and antipyretic. Substrate for β-glucosidase | | |
| Salicyl alcohol, see 2-Hydroxybenzyl alcohol, A14410, p. 248 | | |
| A13833 | Salicylaldehyde, 99% ▲ ▲ [2-Hydroxybenzaldehyde] [90-02-8], C ₇ H ₆ O ₂ , F.W. 122.12, m.p. -7°, b.p. 197°, f.p. 76°(168°F), d. 1.168, n _D ²⁰ 1.5730, Merck 14,8326, EINECS 201-961-0, RTECS VN5250000, BRN 471388, MDL MFCD00003317, † |  100g 500g 2.5kg |
| ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a A convenient method for the racemization of amino acids consists in heating in acetic acid with 0.05 equivalents of an aldehyde, such as salicylaldehyde: <i>J. Org. Chem.</i> , 48 , 843 (1983). For a review of the use of circular dichroism studies of salicylidene derivatives of chiral amines, to establish their absolute configurations using the "salicylidene chirality rule", see: <i>Chem. Rev.</i> , 83 , 359 (1983). | | |
| Application(s): Precursor to a variety of chelating agents | | |
| A12253 | Salicylic acid, 99% ▲ [2-Hydroxybenzoic acid] [69-72-7], C ₇ H ₆ O ₃ , F.W. 138.12, m.p. 158-160°, b.p. 211°/20mm, f.p. 157°(315°F), d. 1.443, Merck 14,8332, EINECS 200-712-3, RTECS VO0525000, BRN 774890, MDL MFCD00002439, † |  250g 500g 2.5kg |
| ! H:H318-H302-H335-H315, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | | |
| 30782 | Salicylic acid, ACS, 99+% [2-Hydroxybenzoic acid] [69-72-7], C ₇ H ₆ O ₃ , F.W. 138.12, Powder, m.p. 158-160°, b.p. 211°/20mm, f.p. 157°(315°F), d. 1.443, Merck 14,8332, Solubility: Soluble in alcohol, acetone, ether. Slightly soluble in cold water. More soluble in boiling water. Water solubility increased by Na ₃ PO ₄ , alkali acetates or alkali citrates, EINECS 200-712-3, RTECS VO0525000, BRN 774890, MDL MFCD00002439, † Maximum level of impurities: Melting point 158.0-161.0°, Residue after ignition 0.01%, Cl 0.001%, SO _x 0.003%, Heavy Metals (as Pb) 5ppm, Fe 2ppm, Substances darkened by sulfuric acid P.T. | 100g 500g 2.5kg |
| ! H:H318-H302-H335-H315, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | | |
| Salicylic acid sodium salt, see Sodium salicylate, A17056, p. 348 | | |
| Saligenin, see 2-Hydroxybenzyl alcohol, A14410, p. 248 | | |
| J64192 | Salubrinol ▲ [eIF-2α Inhibitor, SAL] [405060-95-9], C ₂₁ H ₁₇ Cl ₃ N ₃ OS, F.W. 479.81, Powder | 5mg 10mg |
| SAMP, see (S)-(-)-1-Amino-2-(methoxymethyl)pyrrolidine, J61723, p. 96 | | |
| J65294 | SANT-1 ▲ ▲ [(4-Benzyl-piperazin-1-yl)-(3,5-dimethyl-1-phenyl-1H-pyrazol-4-yl)methylene]-amine] [304909-07-7], C ₂₃ H ₂₇ N ₅ , F.W. 373.49, Solid, MDL MFCD01827306 | 10mg 50mg |
| A18820 | Saponin [8047-15-2], m.p. 158° dec., Merck 14,8365, EINECS 232-462-6, RTECS VQ1400000, MDL MFCD00081981, † | 25g 100g |
| ! H:H319-H335, P:P261-P280-P305+P351+P338-P304+P340-P405-P501a | | |
| Application(s): A glycoside used to permeabilize cellular membranes | | |
| J63209 | Saponin permeating solution, 0.5% w/v soln. in PBS (5X) Liquid H:EUH210 | 125ml 250ml |
| Application(s): Cell permeabilizing agent | | |
| H-Sar-OH, see Sarcosine, A14594, p. 340 | | |
| A14594 | Sarcosine, 98% ■ [Methylaminoacetic acid, N-Methylglycine] [107-97-1], CH ₃ NHCH ₂ CO ₂ H, F.W. 89.09, m.p. ca 208° dec., Merck 14,8373, EINECS 203-538-6, RTECS VQ2897000, BRN 1699442, MDL MFCD00004279, † | 100g 500g 2.5kg |
| Application(s): A type 1 glycine transporter inhibitor | | |
| B25536 | Sarcosine hydrochloride, 99% [Methylaminoacetic acid hydrochloride, N-Methylglycine hydrochloride] [637-96-7], CH ₃ NHCH ₂ CO ₂ H HCl, F.W. 125.56, m.p. ca 173° dec., Merck 14,8373, EINECS 211-310-2, MDL MFCD00012609, † | 25g 100g |
| Application(s): A type 1 glycine transporter inhibitor | | |
| Sarkosyl NL, see N-Lauroylsarcosine sodium salt, J60040, p. 266 | | |
| J60950 | SB 202190, 99+% [4-(4-Fluorophenyl)-2-(4-hydroxyphenyl)-5-(4-pyridyl)imidazole] [152121-30-7], C ₂₀ H ₁₄ FN ₃ O, F.W. 331.35, Powder, m.p. 240-243°, MDL MFCD00941964 | 25mg 50mg 100mg |
| ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | | |
| Application(s): Inhibits p38 kinase activity in vivo through competition with ATP | | |

| Stock # | Description | Size |
|--|---|--|
| J61482 | SB 203580, 99% [4-(4-Fluorophenyl)-2-(4-methylsulfinylphenyl)-5-(4-pyridyl)imidazole] [152121-47-6], C ₂₁ H ₁₆ FN ₃ OS, F.W. 377.44, Powder, m.p. 235-247°, MDL MFCD00922198 ! H:H302-H318, P:P280-P264-P305+P351+P338-P310-P301+P312-P501 | 25mg 50mg 100mg |
| Application(s): Highly specific new inhibitor of p38 kinase and MAP Kinase homologues | | |
| J65387 | SB 225002 [1-(2-Bromophenyl)-3-(2-hydroxy-4-nitrophenyl)urea] [182498-32-4], C ₁₃ H ₁₀ BrN ₂ O ₃ , F.W. 352.10, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 5mg 10mg |
| Scarlet Red , see Sudan IV, A12181, p. 355 | | |
| Schardinger α-dextrin , see α-Cyclodextrin, J60687, p. 171 | | |
| Schardinger β-dextrin , see β-Cyclodextrin hydrate, A14529, p. 171 | | |
| Schardinger γ-dextrin , see γ-Cyclodextrin hydrate, L11271, p. 171 | | |
| J62171 | Schiff's Reagent Liquid, † | 500ml |
| Application(s): Used for detection of glycoproteins in polyacrylamide gels | | |
| Sebercim , see Norfloxacin, J62652, p. 304 | | |
| J64068 | γ-Secretase Inhibitor I [Z-Leu-Leu-Nle-CHO (Nle = Norleucine)] [133407-83-7], C ₂₆ H ₄₁ N ₃ O ₅ , F.W. 475.62, Solid | 5mg |
| J64828 | γ-Secretase Inhibitor II [MW167] C ₂₆ H ₃₀ N ₂ O ₄ , F.W. 362.47, Solid | 1mg 5mg |
| Secreted Frizzled Related Protein-1 Inhibitor , see sFRP-1 Inhibitor, J65910, p. 342 | | |
| Selegiline , see (R)-(-)-Deprenyl hydrochloride, J61286, p. 180 | | |
| J63664 | Semi dry blot transfer buffer (10X) Liquid, Note: 480mM Tris base, 390mM glycine, 0.375% SDS. Add methanol according to your protocol. | 1L 2L |
| J60181 | Separating or resolving buffer (4X) Liquid, Note: 1.5M Tris-HCl and 0.4% SDS, pH 8.8. ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 500ml 1L |
| H-L-Ser-OH , see L-Serine, Cell Culture Reagent, J62187, p. 341 | | |
| A15184 | DL-Serine, 99% [(+/-)-2-Amino-3-hydroxypropionic acid, H-DL-Ser-OH] [302-84-1], C ₃ H ₇ NO ₃ , F.W. 105.09, m.p. ca 240° dec., Merck 14,8460, EINECS 206-130-6, BRN 1721402, MDL MFCD00064223, † |  100g 500g |
| A11353 | D-Serine, 99% [(R)-2-Amino-3-hydroxypropionic acid, H-D-Ser-OH] [312-84-5], C ₃ H ₇ NO ₃ , F.W. 105.09, m.p. 218-220° dec., [α] _D ²⁰ -13° (c=5 in 5N HCl), Merck 14,8460, Fieser 14,282, EINECS 206-229-4, RTECS VT8200000, BRN 1721403, MDL MFCD00004269, † |  5g 25g 100g |
| A11179 | L-Serine, 99% [(S)-2-Amino-3-hydroxypropionic acid, H-Ser-OH] [56-45-1], C ₃ H ₇ NO ₃ , F.W. 105.09, m.p. 214-224° dec., [α] _D ²⁰ +14.5° (c=9 in 1N HCl), Merck 14,8460, Fieser 12,430 14,282, EINECS 200-274-3, RTECS VT8100000, BRN 1721404, † Has been used in a synthesis of D-amino acids. The configuration is inverted by conversion of the carboxyl group to the new alkyl chain by reaction with an organolithium reagent to give the ketone, which is deoxygenated by Raney nickel desulfurization of the thioketal, the hydroxymethyl group becoming the new carboxyl group by oxidation with oxygen over a Pt catalyst: <i>J. Am. Chem. Soc.</i> , 106 , 1095 (1984): |  25g 100g 500g |
| $ \begin{array}{c} \text{HO} \quad \text{COOH} \\ \quad \\ \text{CH}_2 \quad \text{C} \\ \\ \text{NH}_2 \\ \text{NHSO}_2\text{Ph} \end{array} \xrightarrow[\text{ii) RMgBr}]{\text{i) 2n-BuLi}} \begin{array}{c} \text{HO} \quad \text{COR} \\ \quad \\ \text{CH}_2 \quad \text{C} \\ \\ \text{NH}_2 \\ \text{NHSO}_2\text{Ph} \end{array} \xrightarrow[\text{iii) O}_2, \text{ Pt}]{\begin{array}{l} \text{i) HSCH}_2\text{CH}_2\text{CH}_2\text{SH} \\ \text{ii) Raney nickel} \end{array}} \begin{array}{c} \text{HOOC} \quad \text{CH}_2\text{R} \\ \quad \\ \text{CH}_2 \quad \text{C} \\ \\ \text{NH}_2 \\ \text{NHSO}_2\text{Ph} \end{array} $ | | |
| J62187 | L-Serine, Cell Culture Reagent [H-L-Ser-OH] [56-45-1], C ₃ H ₇ NO ₃ , F.W. 105.09, Powder, m.p. 222°, Merck 14,8460, EINECS 200-274-3, RTECS VT8100000, BRN 1721404, MDL MFCD00064224, † | 10g 100g 500g 1kg |
| J64695 | Serine Protease Inhibitor Cocktail I Lyophilized solid, Note: Makes a 100X stock solution in 1ml of water. A 1x solution contains 500uM AEBSF.HCl, 420nM aprotinin, 20uM elastatinal and 1uM GGACK | 1unit |
| Sermorelin , see Growth Hormone Releasing Factor (GRF) (1-29) amide, human, J61111, p. 238 | | |
| H-DL-Ser-OH , see DL-Serine, A15184, p. 341 | | |
| H-D-Ser-OH , see D-Serine, A11353, p. 341 | | |
| H-Ser-OH , see L-Serine, A11179, p. 341 | | |





| Stock # | Description | Size |
|---------------|--|--------------------------------------|
| B21263 | Serotonin hydrochloride, 99% ▲ ■ [3-(2-Aminoethyl)-5-hydroxyindole hydrochloride, 5-HT] [153-98-0], C ₁₀ H ₁₂ N ₂ O·HCl, F.W. 212.68, m.p. 167-172°, Merck 14,8463 , UN2811, EINECS 244-464-4, RTECS NM2571000, BRN 3570963, MDL MFCD00012686  H.H301, P:P264-P270-P301+P310-P321-P405-P501a | 1g 5g 10g |
| J65910 | sFRP-1 Inhibitor ▲ [Secreted Frizzled Related Protein-1 Inhibitor] [915754-88-0], C ₁₉ H ₂₈ N ₂ O ₄ S ₂ , F.W. 410.60, Oil | 5mg 25mg |
| L04848 | (-)-Shikimic acid, 98% ■ [3,4,5-Trihydroxy-1-cyclohexene-1-carboxylic acid] [138-59-0], C ₇ H ₁₀ O ₅ , F.W. 174.16, m.p. 184-188°, [α] _D ²⁰ -175° (c=2 in water), Merck 14,8480 , EINECS 205-334-2, RTECS GW4600000, BRN 4782717, MDL MFCD00066278 Key intermediate in the biosynthesis of aromatic amino acids. Monograph: E. Haslam, <i>Shikimic Acid</i> , Wiley, Chichester (1993). Reviews: <i>Chem. Rev.</i> , 65 , 435 (1965); <i>Tetrahedron</i> , 34 , 3353 (1978); <i>Biosynthesis</i> , 6 , 40 (1980); <i>Natural Prod. Rep.</i> , 10 , 233 (1993); <i>Synthesis</i> , 179 (1993). Application(s): Inhibits rapamycin biosynthesis | 250mg 1g |
| 11660 | Silver acetate, anhydrous, 99% ▲ [563-63-3], AgOOCCH ₃ , F.W. 166.92, Crystalline, m.p. dec., d. 3.26, Merck 14,8505 , Solubility: Soluble in dilute HNO ₃ . Water solubility increases with temperature, UN3077, EINECS 209-254-9, RTECS AJ4100000, MDL MFCD00012446, †  H.H400-H410-H315, P:P280-P273-P302+P352-P321-P362-P501a | 25g 100g |
| 20835 | Silver lactate ▲ [128-00-7], CH ₃ CH(OH)CO ₂ Ag, F.W. 196.94, Powder, m.p. 120-122°, Merck 14,8517 , UN3077, RTECS UA2465550, MDL MFCD00043279  H.H400-H315-H319-H335, P:P280g-P273-P305+P351+P338 | 10g 50g |
| J64486 | Sirtinol [(E)-2-((2-Hydroxynaphthalen-1-yl)methyl)amino)-N-(1-phenylethyl)benzamide] [410536-97-9], C ₂₆ H ₂₂ N ₂ O ₂ , F.W. 394.46, Crystals ! H.H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10mg 50mg |
| J64980 | SJA 6017 ▲ [N-(4-Fluorophenylsulfonyl)-L-valyl-L-leucinal] [190274-53-4], C ₁₇ H ₂₅ FN ₂ O ₃ S, F.W. 372.50, Lyophilized solid Skatole, see 3-Methylindole, L03890, p. 288 SKF-525A hydrochloride, see Proadifen hydrochloride, J63833, p. 328 SKF-92334, see Cimetidine, 98+% , J62825, p. 163 | 1mg 5mg |
| J60937 | SKF-96365 hydrochloride, 99+% [1-[2-(4-Methoxyphenyl)-2-[3-(4-methoxyphenyl)propoxy]ethyl]imidazole] [130495-35-1], C ₂₂ H ₂₆ N ₂ O ₃ ·HCl, F.W. 402.92, Powder, RTECS NI6823500, MDL MFCD00236407 ! H.H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): Inhibits receptor-mediated calcium influx | 10mg 50mg |
| J61367 | SM buffer, pH 7.5 Liquid, Note: 50mM Tris-HCl, 8mM magnesium sulfate, 100mM sodium chloride, and 0.01% gelatin, pH7.5 Application(s): Phage diluent and storage buffer. Used for routine manipulation of phage suspensions. | 100ml 250ml |
| J64726 | Smoothened Agonist dihydrochloride dihydrate ▲ ■ [SAG1.3 HCl] [364590-63-6], C ₂₈ H ₂₈ ClN ₃ OS·2HCl·2H ₂ O, F.W. 599.00, Solid | 1mg 5mg |
| J62210 | SOB medium Liquid, Note: Contains 0.5% Yeast Extract, 2% Tryptone, 10mM NaCl, 2.5mM KCl, 10mM magnesium chloride and 10mM magnesium sulfate Application(s): For cultivating recombinant strains of Escherichia coli | 100ml 250ml |
| J60255 | SOC medium Liquid, Note: Contains 0.5% Yeast Extract, 2% Tryptone, 10mM NaCl, 2.5mM KCl, 10mM magnesium chloride, 10mM magnesium sulfate and 20mM glucose Application(s): for cultivating recombinant strains of Escherichia coli | 100ml 250ml |
| J63669 | SOD , see Superoxide Dismutase, bovine erythrocytes, J63003, p. 356 Sodium acetate, 1M aq. soln., pH 4.5, RNase free [127-09-3], NaOOCCH ₃ , F.W. 82.03, Liquid, † | 125ml 250ml |

| Stock # | Description | Size |
|---|--|-------------------------------|
| J61288 | Sodium acetate, 3M aq. soln., pH 4.5, autoclaved [127-09-3], NaOOCCH ₃ , F.W. 82.03, Liquid, † | 125ml 250ml |
| J63560 | Sodium acetate, 3M aq. soln., pH 5.2, autoclaved [127-09-3], NaOOCCH ₃ , F.W. 82.03, Liquid, † | 125ml 250ml |
| J61928 | Sodium acetate, 3M aq. soln., pH 5.2, RNase free [127-09-3], NaOOCCH ₃ , F.W. 82.03, Liquid, † | 125ml 250ml |
| J60899 | Sodium acetate, 3M aq. soln., pH 7.0, autoclaved [127-09-3], NaOOCCH ₃ , F.W. 82.03, Liquid, † | 125ml 250ml |
| J61934 | Sodium acetate, 3M aq. soln., pH 7.0, RNase free [127-09-3], NaOOCCH ₃ , F.W. 82.03, Liquid, † | 125ml 250ml |
| A16230 | Sodium acetate trihydrate, 99% [Acetic acid sodium salt trihydrate] [6131-90-4], NaOOCCH ₃ ·3H ₂ O, F.W. 136.08 (82.03anhy), m.p. 62-64°, d. 1.45, Merck 14,8571, Fieser 1,1024 5,59, EINECS 204-823-8, RTECS AJ4580000, BRN 3732037, MDL MFCD00071557, Note: -3H ₂ O @ 120°, † | 500g 2.5kg 10kg |
| 11553 | Sodium acetate trihydrate, ACS, 99.0%-100.5% [Acetic acid sodium salt trihydrate] [6131-90-4], NaOOCCH ₃ ·3H ₂ O, F.W. 136.08 (82.03anhy), Crystalline, m.p. 62-64°, d. 1.45, Merck 14,8571, Fieser 1,1024 5,59, Solubility: Freely soluble in alcohol, EINECS 204-823-8, RTECS AJ4580000, BRN 3732037, MDL MFCD00071557, Note: 120° -3H ₂ O, † Maximum level of impurities: Insoluble matter 0.005%, pH of a 5% solution 7.5-9.2 at 25°, Cl 0.001%, PO ₄ 5ppm, SO ₄ 0.002%, Ca 0.005%, Mg 0.002%, Heavy Metals (as Pb) 5ppm, Fe 5ppm, Substances reducing permanganate P.T., K 0.005% | 500g 2kg |
| Application(s): In photography, analytical laboratory as buffer, pharmaceutical | | |
| 11554 | Sodium acetate, anhydrous, ACS, 99.0% min ■ [Acetic acid sodium salt] [127-09-3], NaOOCCH ₃ , F.W. 82.03, Crystalline, m.p. 324°, d. 1.528, Merck 14,8571, Fieser 1,1024 5,59, EINECS 204-823-8, RTECS AJ4300010, BRN 3595639, MDL MFCD00012459, † Maximum level of impurities: Insoluble matter 0.01%, Loss on drying at 120° 1.0%, pH of a 5% solution 7.5-9.2 at 25°, Cl 0.002%, PO ₄ 0.001%, SO ₄ 0.003%, Ca 0.005%, Mg 0.002%, Heavy Metals (as Pb) 0.001%, Fe 0.001% H:H303, P:P312 | 250g 1kg 5kg |
| Sodium alginate , see Alginic acid sodium salt, high viscosity, J61887, p. 89 | | |
| Sodium 4-aminobenzoate , see 4-Aminobenzoic acid sodium salt, 99%, J63428, p. 92 | | |
| J64449 | Sodium 4-aminosalicylate dihydrate, 98% ▲ △ [4-Amino-2-hydroxybenzoic acid sodium salt, 4-Aminosalicylic acid sodium salt dihydrate] [6018-19-5], C ₇ H ₇ NNaO ₃ ·2H ₂ O, F.W. 211.14 (175.12ahy), Powder, m.p. 250°, EINECS 205-091-2, RTECS VO1700000, MDL MFCD00151044, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 25g 100g 500g |
| Sodium L-aspartate monohydrate , see L-Aspartic acid monosodium salt monohydrate, B22321, p. 111 | | |
| 14314 | Sodium azide, 99% △ [26628-22-8], NaN ₃ , F.W. 65.01, Powder or Granular, m.p. ca 275° dec, d. 1.846, Merck 14,8581, Solubility: Soluble in water and liquid ammonia. Slightly soluble in alcohol, UN1687, EINECS 247-852-1, RTECS VY8050000, MDL MFCD00003536, †  H:H300-EUH032-H400-H410, P:P273-P284-P301+P310-P321-P405-P501a The reaction of alkyl halides with the highly-nucleophilic azide anion gives alkyl azides which, because of their facile reduction by hydrogenation, SnCl ₂ , P(III) reagents, etc., provide an excellent, mild route to primary amines. For a review of the preparation and synthetic uses of azides, see: <i>Chem. Rev.</i> , 88 , 297 (1988). The preparation of alkyl azides is ideally suited to phase-transfer methods: <i>Synthesis</i> , 823 (1979); <i>Tetrahedron Lett.</i> , 3107 (1978); 30 , 1245 (1989). The use of ultrasound has also been found to be effective: <i>Acta Chem. Scand. B</i> , 38 , 895 (1984). For a one-pot conversion of alkyl bromides to amines using the Staudinger reaction, see Triethyl phosphite, L00339 ; see also Triphenylphosphine, L02502 . For reviews, see: <i>Tetrahedron</i> , 37 , 437 (1981); 48 , 1353 (1992). Reaction with acyl halides or mixed anhydrides gives acyl azides. These undergo the Curtius rearrangement to isocyanates, which can be isolated, or hydrolyzed <i>in situ</i> to the primary amine. For examples, see: <i>Org. Synth. Coll.</i> , 6 , 95, 910 (1988). Reagent for selective cleavage of methyl(diphenyl)silyl ethers; see Chloro(methyl)diphenylsilane, L04162 . For a brief feature on uses of this reagent in Organic synthesis, see: <i>Synlett</i> , 505 (2007). | 10g 100g 500g |
| Application(s): In airbag inflation, as a preservative in diagnostic medicinals | | |
| Sodium bentonite , see Bentonite, A15795, p. 118 | | |
| A15946 | Sodium benzoate, 99% [Benzoic acid sodium salt] [532-32-1], C ₇ H ₅ NaO ₂ , F.W. 144.11, m.p. >300°, Merck 14,8582, Fieser 1,1044 2,377, Solubility: Soluble in water, alcohol, EINECS 208-534-8, RTECS DH6650000, BRN 3572467, MDL MFCD00012463, † ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | 250g 500g 2.5kg 10kg |
| Sodium o-benzosulfimide hydrate , see o-Benzoic sulfimide sodium salt hydrate, A15530, p. 119 | | |
| Sodium bicarbonate , see Sodium hydrogen carbonate, 14707, p. 346 | | |
| J62495 | Sodium bicarbonate, 1M buffer soln., pH 8.0 [144-55-8], Liquid, † | 500ml 1L |










| Stock # | Description | Size |
|---|---|----------------------|
| J60408 | Sodium bicarbonate, 1M buffer soln., pH 8.5 [144-55-8], Liquid, † | 250ml 500ml 1L |
| J60066 | Sodium bicarbonate, 1M buffer soln., pH 9.0 [144-55-8], Liquid, † | 250ml 500ml 1L |
| J62808 | Sodium bicarbonate, 1M buffer soln., pH 9.4 [144-55-8], Liquid, † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 250ml 500ml |
| J63025 | Sodium bicarbonate, 1M buffer soln., pH 10.0 [144-55-8], Liquid, † ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 250ml 500ml |
| J60068 | Sodium borate, 0.5M buffer soln., pH 8.0 [1330-43-4], Liquid, † H:H360FD, P:P281-P201-P202-P308+P313-P405-P501a | 250ml 500ml |
| J62902 | Sodium borate, 0.5M buffer soln., pH 8.5 [1330-43-4], Liquid, † H:H360, P:P281-P201-P202-P308+P313-P405-P501 | 250ml 500ml |
| J63637 | Sodium borate, 0.5M buffer soln., pH 9.0 [1330-43-4], Liquid, † H:H360FD, P:P281-P201-P202-P308+P313-P405-P501a | 250ml 500ml |
| Sodium borate (tetra) decahydrate , see Sodium tetraborate decahydrate, 40114, p. 349 | | |
| A11079 | Sodium butyrate, 98+% ■ [Butyric acid sodium salt] [156-54-7], CH ₃ (CH ₂) ₂ CO ₂ Na, F.W. 110.09, m.p. >300°, EINECS 205-857-6, RTECS ET6400000, BRN 3629439, MDL MFCD00002816, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): Decreases calcium release from intracellular stores. Inhibits histone deacetylase | 5g 100g 500g |
| J60367 | Sodium cacodylate, 0.1M buffer soln., pH 6.5 [6131-99-3], Liquid | 100ml 250ml |
| J62202 | Sodium cacodylate, 0.1M buffer soln., pH 6.8 [6131-99-3], Liquid | 100ml 250ml |
| J60344 | Sodium cacodylate, 0.1M buffer soln., pH 7.0 [6131-99-3], Liquid, † H:H412, P:P273-P501a | 125ml 250ml |
| Sodium cacodylate trihydrate , see Cacodylic acid sodium salt trihydrate, A18139, p. 141 | | |
| 11552 | Sodium carbonate, anhydrous, ACS, 99.5% min ■ [497-19-8], Na ₂ CO ₃ , F.W. 105.99, Granular, d. 2.53, n _D ²⁰ 1.535, Merck 14.8596, Fieser 7,332, Solubility: Soluble in water. Insoluble in alcohol, EINECS 207-838-8, RTECS VZ4050000, BRN 4154566, MDL MFCD00003494, Note: m.p. 851° (begins to lose CO ₂ at 400°), † Note: m.p. 851° (begins to lose CO ₂ at 400°), † Maximum level of impurities: Insoluble matter 0.01%, Loss on heating at 285° 1.0%, Cl 0.001%, PO ₄ 0.001%, SiO ₂ 0.005%, Sulfur compounds (as SO ₂) 0.003%, Ca 0.03%, Mg 0.005%, Heavy Metals (as Pb) 5ppm, Fe 5ppm, K 0.005% ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 50g 500g 2kg |
| 33377 | Sodium carbonate, ACS primary standard, 99.95-100.05% (dried basis) ■ [497-19-8], Na ₂ CO ₃ , F.W. 105.99, Granular, d. 2.53, n _D ²⁰ 1.535, Merck 14.8596, Fieser 7,332, EINECS 207-838-8, RTECS VZ4050000, BRN 4154566, MDL MFCD00003494, Note: m.p. 851° (begins to lose CO ₂ at 400°). For use as an alkalimetric standard, material should be heated at 285° for 2 hrs., † Maximum level of impurities: Insoluble matter 0.01%, Loss on drying at 285° 1.0%, Cl 0.001%, Nitrogen compounds (as N) 0.001%, PO ₄ 0.001%, SiO ₂ 0.005%, Sulfur compounds (as SO ₂) 0.003%, Ammonium hydroxide precipitate 0.01%, Ca 0.02%, Mg 0.004%, Heavy Meta ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 100g 500g |
| J61807 | Sodium chloride, 5M aq. soln., pH 8.0, autoclaved [7647-14-5], NaCl, F.W. 58.44, Liquid, † H:H303, P:P312 | 250ml 500ml |
| J61890 | Sodium chloride, 5M aq. soln., autoclaved [7647-14-5], NaCl, F.W. 58.44, Liquid, † | 250ml 500ml |


| Stock # | Description | Size |
|---------|---|-----------------------|
| J60434 | Sodium chloride, 5M aq. soln., RNase free [7647-14-5], NaCl, F.W. 58.44, Liquid, † H:H303, P:P312 | 125ml 250ml |
| 12314 | Sodium chloride, ACS, 99.0% min ■ [7647-14-5], NaCl, F.W. 58.44, Crystalline, m.p. 801°, b.p. 1413°, d. 2.165, n _D ²⁰ 1.5442, Merck 14,8599, Fieser 6,285, Solubility: Soluble in water, glycerol. Very slightly soluble in alcohol, EINECS 231-598-3, RTECS VZ4725000, MDL MFCD00003477, † Maximum level of impurities: Insoluble matter 0.005%, pH of a 5% solution 5.0-9.0 at 25°, I 0.002%, Br 0.01%, Chlorate and nitrate (as NO ₃) 0.003%, PO ₄ 5ppm, SO ₄ 0.004%, Ba P.T., Ca 0.002%, Mg 0.001%, Heavy Metals (as Pb) 5ppm, Fe 2ppm, K 0.005% H:H303, P:P312 | 500g 2kg 10kg |
| A17074 | Sodium cholate hydrate, 99% [Cholic acid sodium salt hydrate] [206986-87-0], C ₂₄ H ₃₈ NaO ₇ ·xH ₂ O, F.W. 430.56(anhy), RTECS FZ9600000, BRN 3582354, MDL MFCD00064138, † H:H303, P:P312 | 10g 50g |
| | Application(s): Biochemical solubilizing agent | |
| J62918 | Sodium citrate, 0.5M buffer soln., pH 5.0 Liquid | 250ml 500ml |
| J63199 | Sodium citrate, 0.5M buffer soln., pH 5.5 Liquid | 250ml 500ml |
| J61815 | Sodium citrate, 0.5M buffer soln., pH 6.0 Liquid ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 250ml 500ml |
| J63888 | Sodium citrate, 0.5M buffer soln., pH 6.5 Liquid | 250ml 500ml |
| | Sodium creatine phosphate dibasic tetrahydrate , see Creatine phosphate disodium salt tetrahydrate, A15362, p. 168 | |
| A14638 | Sodium 1-decanesulfonate, 99% (dry wt.), water <1.5% [1-Decanesulfonic acid sodium salt] [13419-61-9], CH ₃ (CH ₂) ₉ SO ₃ Na, F.W. 244.33, m.p. >300°, EINECS 236-525-9, BRN 3918920, MDL MFCD00007526 | 5g 25g 100g |
| | Application(s): Ion-associating reagent for HPLC, useful for analysis of peptides and proteins. | |
| B21060 | Sodium dehydroacetate, 97% [3-Acetyl-4-hydroxy-6-methyl-2-pyrone sodium salt, Dehydroacetic acid sodium salt] [4418-26-2], C ₈ H ₇ NaO ₄ , F.W. 190.13, m.p. ca 295° dec., EINECS 224-580-1, RTECS UP8225000, MDL MFCD00040583, † ! H:H302, P:P264-P270-P301+P312-P330-P501a | 100g 500g 2.5kg |
| B20759 | Sodium deoxycholate monohydrate, 98% [Deoxycholic acid sodium salt monohydrate] [145224-92-6], C ₂₄ H ₃₈ NaO ₇ ·H ₂ O, F.W. 432.58 (414.58anhy), m.p. >300°, [α] _D ²⁰ +44° (c=2 in water), Merck 14,2899, EINECS 206-132-7, RTECS FZ2250000, BRN 3643164, MDL MFCD00150750, † ! H:H302-H335, P:P261-P304+P340-P301+P312-P312-P405-P501a | 25g 100g 500g |
| | Sodium dextran sulfate , see Dextran sulfate sodium salt Sodium 2-(4,6-dichloroanilino)phenylacetate , see Diclofenac sodium salt, J62609, p. 186 Sodium 2,5-dichloroindophenoxide hydrate , see 2,6-Dichloroindophenol sodium salt hydrate, A10107, p. 185 | |
| A15898 | Sodium diethyldithiocarbamate trihydrate, 98% ■ [Diethyldithiocarbamic acid sodium salt trihydrate, Dithiocarb sodium] [20624-25-3], C ₅ H ₁₀ NNaS ₂ ·3H ₂ O, F.W. 225.31 (171.28anhy), m.p. 94-102°, Merck 14,3378, EINECS 205-710-6, RTECS EZ6550000, BRN 3920507, MDL MFCD00150617, † ! H:H302, P:P264-P270-P301+P312-P330-P501a Reagent for extraction of heavy metals: <i>Anal. Chem.</i> , 54, 2536 (1982). | 100g 500g |
| 11591 | Sodium dihydrogen phosphate monohydrate, ACS, 98.0-102.0% ■ [Monosodium orthophosphate, Sodium phosphate, monobasic] [10049-21-5], NaH ₂ PO ₄ ·H ₂ O, F.W. 137.99 (119.98anhy), Crystalline, m.p. 100° -H ₂ O, Merck 14,8660, Fieser 1,395, EINECS 231-449-2, RTECS WA1900000, MDL MFCD00149208, † Maximum level of impurities: Insoluble matter 0.01%, pH of a 5% solution 4.1-4.5 at 25%, Cl 5ppm, SO ₄ 0.003%, Ca 0.005%, K 0.01%, As 0.5ppm, Heavy Metals (as Pb) 0.001%, Fe 0.001% ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250g 1kg 5kg |
| J63394 | Sodium n-dodecyl sulfate (SDS), 20% aq. soln. [151-21-3], CH ₃ (CH ₂) ₁₁ OSO ₃ Na, F.W. 288.38, Liquid, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250ml 500ml |






| Stock # | Description | Size |
|---------|---|-----------------------------|
| A11183 | Sodium n-dodecyl sulfate, 99% (dry wt.), water <1.5% [n-Dodecyl sulfate sodium salt, Sodium lauryl sulfate] [151-21-3], CH ₃ (CH ₂) ₁₁ OSO ₃ Na, F.W. 288.38, m.p. ca 206°, Merck 14,8636, Fieser 13,281, EINECS 205-788-1, RTECS WT1050000, BRN 3599286, MDL MFCD00036175, † | 25g |
| | | 100g 500g |
| | ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a The reaction rate and endo:exo ratio in the Diels-Alder cycloadditions of acrylic acid derivatives to cyclopentadiene is increased in the presence of this surfactant: <i>Tetrahedron Lett.</i> , 27 , 1285 (1986). | |
| | Application(s): Denatures and solubilizes proteins for electrophoresis | |
| J64241 | Sodium n-dodecyl sulfate, ultrapure, 99% [n-Dodecyl sulfate sodium salt, Sodium lauryl sulfate] [151-21-3], CH ₃ (CH ₂) ₁₁ OSO ₃ Na, F.W. 288.38, Powder, m.p. ca 206°, Merck 14,8636, EINECS 205-788-1, RTECS WT1050000, BRN 3599286, MDL MFCD00036175, † | 25g |
| | | 100g 500g |
| | ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J60251 | Sodium fluoride, 200mM aq. soln. [7681-49-4], NaF, F.W. 41.99, Liquid, † | 100ml |
| | | 250ml |
| | H:H303, P:P312 | |
| A11276 | Sodium fumarate, 98% ■ [Fumaric acid disodium salt] [17013-01-3], C ₄ H ₂ Na ₂ O ₄ , F.W. 160.04, EINECS 241-087-7, RTECS LT1830000, MDL MFCD00064567 | 100g |
| | | 500g 2.5kg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| |  | |
| | Sodium furegrelate, see Furegrelate sodium salt, 99+%, J61378, p. 229 | |
| A10464 | Sodium D-gluconate, 97% [D-Gluconic acid sodium salt] [527-07-1], C ₆ H ₁₁ NaO ₇ , F.W. 218.14, m.p. ca 206° dec., [α] _D ²⁰ +12° (c=20 in water), Merck 14,4456, EINECS 208-407-7, RTECS LZ5235000, BRN 3919651, MDL MFCD00064210, † | 2.5kg |
| | | 10kg |
| |  | |
| A10917 | Sodium 1-heptanesulfonate, 99% (dry wt.), water <2% [1-Heptanesulfonic acid sodium salt] [22767-50-6], CH ₃ (CH ₂) ₆ SO ₃ Na, F.W. 202.24, m.p. >300°, EINECS 245-210-5, BRN 3731762, MDL MFCD00007543, † | 5g |
| | | 25g 100g |
| | Application(s): HPLC reagent used for ion-association in analyses of peptides and proteins | |
| 14707 | Sodium hydrogen carbonate, ACS, 99.7-100.3% [Sodium bicarbonate] [144-55-8], NaHCO ₃ , F.W. 84.01, Granular, d. 2.159, n _D ²⁰ 1.500, Merck 14,8583, Fieser 3,260 5,595, Solubility: Soluble in water. Insoluble in alcohol, EINECS 205-633-8, RTECS VZ0950000, BRN 4153970, MDL MFCD00003528, Note: m.p. ≈50°, begins to lose CO ₂ ≈100°, converts to Na ₂ CO ₃ . Aqueous solutions begin to decompose into CO ₂ and Na ₂ CO ₃ at ≈20°. Completely decomposed upon boiling, † | 500g |
| | | 2kg 10kg |
| | Maximum level of impurities: Insoluble matter 0.015%, Cl 0.003%, PO ₄ 0.001%, SO ₄ 0.003%, NH ₄ 5ppm, Ca 0.02%, Mg 0.005%, Heavy Metals (as Pb) 5ppm, Fe 0.001%, K 0.005% | |
| | H:H303, P:P312 | |
| | Application(s): As a source of CO ₂ , in making sodium salts, baking powder, cleaning compounds | |
| 11592 | Sodium hydrogen phosphate heptahydrate, ACS, 98.0-102.0% [Disodium phosphate, Sodium phosphate, dibasic] [7782-85-6], Na ₂ HPO ₄ ·7H ₂ O, F.W. 268.07 (141.98anhy), Crystalline, m.p. 48.1°-5H ₂ O, d. 1.7, Merck 14,8659, EINECS 231-448-7, RTECS WC4600000, MDL MFCD00149180, † | 500g |
| | | 2kg |
| | Maximum level of impurities: pH of a 5% solution 8.7-9.3 at 25°, Insoluble matter 0.005%, Cl 0.001%, SO ₄ 0.005%, Heavy Metals (as Pb) 0.001%, Fe 0.001% | |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| 13437 | Sodium hydrogen phosphate, anhydrous, ACS, 99.0% min ■ [Disodium phosphate, Sodium phosphate, dibasic] [7558-79-4], Na ₂ HPO ₄ , F.W. 141.98, Granular, Merck 14,8659, EINECS 231-448-7, RTECS WC4500000, MDL MFCD00003496, Note: Suitable for buffer solutions, † | 250g |
| | | 1kg 5kg |
| | Maximum level of impurities: Insoluble matter 0.01%, Loss on drying at 105° 0.2%, pH of a 5% solution 8.7-9.3 at 25°, Cl 0.002%, SO ₄ 0.005%, Heavy Metals (as Pb) 0.001%, Fe 0.002% | |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| J63736 | Sodium hydroxide, 10N aq. soln. [1310-73-2], NaOH, F.W. 40.00, Liquid, UN1824, † | 100ml |
| | | 250ml |
| |  H:H314, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | |
| 13455 | Sodium hydroxide (low chloride), ACS, 97.0% min △ ■ [1310-73-2], NaOH, F.W. 40.00, Pellets, m.p. 318°, b.p. 1390°, d. 2.13, Merck 14,8627, Fieser 5,616 7,336 8,460 18,334, Solubility: Soluble in water, alcohol and glycerol, UN1823, EINECS 215-185-5, RTECS WB4900000, MDL MFCD00003548, † | 2.5g |
| | | 100g 500g 2kg 10kg |
| | Maximum level of impurities: Cl 0.005%, N 0.001%, PO ₄ 0.001%, SO ₄ 0.003%, Heavy Metals (as Ag) 0.002%, Fe 0.001%, Hg 0.1ppm, Ca 0.005%, Mg 0.002%, Ni 0.001%, K 0.02%, Na ₂ CO ₃ 1.0% | |
| |  H:H314, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | |
| | Application(s): In chemical manufacture, rayon and cellophane, as a neutralizing agent in petroleum refining, in pulp, paper detergents and textiles, and as a lab reagent. NaOH solutions precipitate most metals as hydroxides from aqueous solutions of the metal salts | 2x12.5kg |


| Stock # | Description | Size |
|---------|--|-----------------------|
| J60415 | Sodium hydroxide and β-mercaptoethanol buffer Liquid, UN2922, Note: Solution contains: 1.85M sodium hydroxide and 7.5% β -mercaptoethanol.  H:H318-H315-H412, P:P280-P305+P351+P338-P302+P352-P321-P310-P501a | 250ml 500ml |
| | Application(s): Common solution for protein and DNA isolation from yeast. | |
| | Sodium 2-hydroxybenzoate , see Sodium salicylate, A17056, p. 348 Sodium 5-hydroxydecanoate , see 5-Hydroxydecanoic acid sodium salt, 98%, J61434, p. 248 Sodium iminodiacetate dibasic hydrate , see Iminodiacetic acid disodium salt hydrate, 43809, p. 254 Sodium isethionate , see Isethionic acid sodium salt, A12054, p. 260 | |
| 41529 | Sodium DL-lactate, 60% w/w aq. soln. <i>[DL-Lactic acid sodium salt]</i> [72-17-3], $\text{CH}_3\text{CH}(\text{OH})\text{CO}_2\text{Na}$, F.W. 112.06, Liquid, d. 1.326, Merck 14,8635, EINECS 200-772-0, RTECS OD5680000, BRN 4332999, MDL MFCD00065400, †  H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250ml 1L |
| | Application(s): Useful chiral synthon; building block for depsipeptides | |
| | Sodium lauryl sulfate , see Sodium n-dodecyl sulfate, A11183, p. 346 Sodium mercaptoacetate , see Mercaptoacetic acid sodium salt, 98%, J60290, p. 280 Sodium nitroferricyanide(III) , see Sodium pentacyanonitrosylferrate(III) dihydrate, 87683, p. 347 Sodium nitroprusside , see Sodium pentacyanonitrosylferrate(III) dihydrate, 87683, p. 347 | |
| A14292 | Sodium 1-octanesulfonate, 99% <i>[1-Octanesulfonic acid sodium salt]</i> [5324-84-5], $\text{CH}_3(\text{CH}_2)_7\text{SO}_3\text{Na}$, F.W. 216.28, m.p. >300°, EINECS 226-195-4, BRN 3574241, MDL MFCD00007544, † | 5g 25g 100g |
| | Application(s): Reagent for HPLC analysis of peptides and proteins | |
| 81104 | Sodium orthovanadate, 99.9% (metals basis) <i>[Sodium vanadate (ortho), Sodium vanadium oxide]</i> [13721-39-6], Na_3VO_4 , F.W. 183.94, Granular, m.p. 850-866°, EINECS 237-287-9, RTECS YW1120000, MDL MFCD00003511, †  H:H302-H332-H315-H319-H335, P:P280h-P305+P351+P338 | 25g 100g 500g |
| | Application(s): Inhibitor of protein tyrosine phosphatase and alkaline phosphatase | |
| J60191 | Sodium orthovanadate, 100mM aq. soln. [13721-39-6], Na_3VO_4 , F.W. 183.94, Liquid, † H:EUH210 | 50ml 100ml |
| A11648 | Sodium oxalate, 99% ■ <i>[Oxalic acid sodium salt]</i> [62-76-0], $\text{Na}_2\text{C}_2\text{O}_4$, F.W. 134.00, m.p. ca 250-270° dec., d. 2.340, Merck 14,8650, EINECS 200-550-3, RTECS K11750000, BRN 3631622, MDL MFCD00012465, †  H:H302-H312, P:P280-P302+P352-P322-P301+P312-P312-P501a | 100g 500g 2.5kg |
| 87683 | Sodium pentacyanonitrosylferrate(III) dihydrate, ACS, 99.0-102.0% <i>[Sodium nitroprusside, Sodium nitroferricyanide(III)]</i> [13755-38-9], $\text{Na}_2[\text{Fe}(\text{CN})_5\text{NO}] \cdot 2\text{H}_2\text{O}$, F.W. 297.95 (261.92anhy), Crystalline, d. 1.72, Merck 14,8649, Fieser 18,337, UN1588, EINECS 238-373-9, RTECS LJ8925000, MDL MFCD00149192, † Maximum level of impurities: Insoluble matter 0.01%, Cl 0.02%, SO_4 P.T. (limit about 0.01%)  H:H301-H312-H332, P:P261-P301+P310-P302+P352-P321-P405-P501a | 50g 250g |
| | Application(s): For chromatographic detection of peptides | |
| A15713 | Sodium phosphate dodecahydrate, 97% <i>[Sodium phosphate, tribasic dodecahydrate, Trisodium phosphate dodecahydrate]</i> [10101-89-0], $\text{Na}_3\text{PO}_4 \cdot 12\text{H}_2\text{O}$, F.W. 380.12 (163.94anhy), m.p. ca 75° dec., d. 1.62, Merck 14,8662, UN3262, EINECS 231-509-8, RTECS TC9575000, MDL MFCD00149198, †  H:H314, P:P280-P305+P351+P338-P309-P310 | 500g 2.5kg 10kg |
| 13438 | Sodium phosphate, tribasic, anhydrous, tech. ■ <i>[Trisodium phosphate]</i> [7601-54-9], Na_3PO_4 , F.W. 163.94, -100 Mesh Powder, Merck 14,8662, UN3262, EINECS 231-509-8, RTECS TC9490000, MDL MFCD00003510, †  H:H314, P:P280-P305+P351+P338-P309-P310 | 1kg 5kg |
| J63482 | Sodium phosphate, 0.2M buffer soln., pH 7.0 Liquid, † | 500ml 1L |
| J63816 | Sodium phosphate, 0.2M buffer soln., pH 7.2 Liquid, † | 500ml 1L |
| J62152 | Sodium phosphate, 0.2M buffer soln., pH 7.4 Liquid, † | 500ml 1L |

| Stock # | Description | Size |
|---------|---|---------------------|
| J62041 | Sodium phosphate, 0.2M buffer soln., pH 7.5 Liquid, † | 500ml 1L |
| J62815 | Sodium phosphate, 0.2M buffer soln., pH 7.6 Liquid, † | 500ml 1L |
| J62733 | Sodium phosphate, 0.2M buffer soln., pH 8.0 Liquid, † | 500ml 1L |
| J61372 | Sodium phosphate, 0.2M buffer soln., pH 8.5 Liquid, † | 500ml 1L |
| J60565 | Sodium phosphate, 0.2M buffer soln., pH 9.0 Liquid, † | 500ml 1L |
| J63159 | Sodium phosphate, 0.2M buffer soln., pH 9.5 Liquid, † | 500ml 1L |
| J63791 | Sodium phosphate, 0.5M buffer soln., pH 7.0 Liquid, † | 250ml 500ml |
| J61561 | Sodium phosphate, 0.5M buffer soln., pH 7.5 Liquid, † | 250ml 500ml |
| J60158 | Sodium phosphate, 0.5M buffer soln., pH 7.6 Liquid, † | 250ml 500ml |
| J60825 | Sodium phosphate, 0.5M buffer soln., pH 8.0 Liquid, † | 250ml 500ml |
| J61151 | Sodium phosphate, 0.5M buffer soln., pH 8.5 Liquid, † | 250ml 500ml |
| J60651 | Sodium phosphate, 0.5M buffer soln., pH 9.0 Liquid, † | 250ml 500ml |
| J61456 | Sodium phosphate, 0.5M buffer soln., pH 9.5 Liquid, † | 250ml 500ml |
| | Sodium phosphate, dibasic , see Sodium hydrogen phosphate heptahydrate, 11592, p. 346 Sodium phosphate, monobasic , see Sodium dihydrogen phosphate monohydrate, 11591, p. 345 Sodium potassium tartrate , see Potassium sodium L-tartrate tetrahydrate, 33241, p. 327 | |
| A17440 | Sodium propionate, 99% ■ [Propionic acid sodium salt] [137-40-6], CH ₃ CH ₂ CO ₂ Na, F.W. 96.06, m.p. 285-291°, Merck 14,8669, EINECS 205-290-4, RTECS UF7525000, MDL MFCD00002759, † ! H: H312, P: P280-P302+P352-P322-P312-P363-P501a | 500g 2.5kg |
| J62052 | Sodium pyrophosphate, 200mM buffer soln. [7758-16-9], Liquid, † | 100ml 250ml |
| A11148 | Sodium pyruvate, 99% [Pyruvic acid sodium salt] [113-24-6], C ₃ H ₃ NaO ₃ , F.W. 110.04, m.p. >300°, EINECS 204-024-4, BRN 3568341, MDL MFCD00002586, † | 50g 250g 500g |
| J61840 | Sodium pyruvate, Cell Culture Grade [Pyruvic acid sodium salt, α-Ketopropionic acid sodium salt] [113-24-6], CH ₃ COCOONa, F.W. 110.04, Powder, EINECS 204-024-4, BRN 3568341, MDL MFCD00002586, † | 50g 100g 500g |
| | Sodium saccharin , see o-Benzoic sulfimide sodium salt hydrate, A15530, p. 119 | |
| A17056 | Sodium salicylate, 99% ▲ [Salicylic acid sodium salt, Sodium 2-hydroxybenzoate] [54-21-7], C ₇ H ₅ NaO ₃ , F.W. 160.11, m.p. >300°, Merck 14,8332, EINECS 200-198-0, RTECS VO5075000, BRN 3732792, MDL MFCD00002440, † ! H: H302-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250g 1kg |
| 12585 | Sodium selenite, anhydrous, 99% min, typically 99.75% min (metals basis) ■ [Selenious acid disodium salt] [10102-18-8], Na ₂ SeO ₃ , F.W. 172.94, Powder, m.p. >350°, Merck 14,8673, Solubility: Freely soluble in water. Insoluble in alcohol, UN2630, EINECS 233-267-9, RTECS VS7350000, MDL MFCD00003489, † ☞ H: H300-EUH031-H331-H317-H411, P: P261-P301+P310-P302+P352-P321-P405-P501a | 100g 500g |
| | Application(s): In glass manufacturing | |





| Stock # | Description | Size |
|--|--|----------------------------|
| 11560 | Sodium sulfate, ACS, 99.0% min ■ [7757-82-6], Na ₂ SO ₄ , F.W. 142.04, Granular, m.p. 884°, d. 2.680, n _D ²⁰ 1.484, Merck 14,8680, Fieser 1,1103, Solubility: Soluble in water. Insoluble in alcohol, EINECS 231-820-9, RTECS WE1650000, MDL MFCD00003504, † Maximum level of impurities: Insoluble matter 0.01%, Loss on ignition 0.5%, Cl 0.001%, N 5ppm, PO ₄ 0.001%, Heavy Metals (as Pb) 5ppm, Fe 0.001%, Ca 0.01%, Mg 0.005%, K 0.01%, pH of a 5% solution 5.2-9.2 at 25° | 500g 2kg 10kg |
| Application(s): In drying organic liquids, in Kjeldahl nitrogen determination, in manufacturing of glass | | |
| A18346 | Sodium taurocholate hydrate, 97% [Taurocholic acid sodium salt] [145-42-6], C ₂₆ H ₄₄ NNaO ₇ S xH ₂ O, F.W. 537.73(anhy), [α] _D ²⁰ +23.0° (c=3 in water), Merck 14,9075, EINECS 205-653-7, MDL MFCD00150819, † | 1g 5g 25g |
|  | | |
| 40114 | Sodium tetraborate decahydrate, ACS, 99.5-105.0% [Borax, Sodium borate (tetra) decahydrate] [1303-96-4], Na ₂ B ₄ O ₇ ·10H ₂ O, F.W. 381.37 (201.22anhy), Powder, m.p. 75°, d. 1.73, Merck 14,8590, Solubility: Soluble in water, glycerol. Insoluble in alcohol, EINECS 215-540-4, RTECS VZ2275000, MDL MFCD00149193, Note: 100° -5H ₂ O, 150° -9H ₂ O, 320° -10H ₂ O, † Maximum level of impurities: Insoluble matter 0.005%, Cl 0.001%, PO ₄ 0.001%, SO ₄ 0.005%, Ca 0.005%, Heavy Metals (as Pb) 0.001%, Fe 5ppm, pH of a 0.01M solution 9.15-9.20 at 25° | 500g |
| ↓ H: H360FD, P: P201-P308+P313 | | |
| Sodium thioglycolate, see Mercaptoacetic acid sodium salt, 98%, J60290, p. 280 | | |
| A17629 | Sodium thiosulfate, anhydrous, 99% ■ [7772-98-7], Na ₂ S ₂ O ₃ , F.W. 158.11, d. 1.667, Merck 14,8694, EINECS 231-867-5, RTECS XN6476000, MDL MFCD00003499, † | 500g 2.5kg |
| 36489 | Sodium tungsten oxide dihydrate, ACS, 99.0-101.0% [10213-10-2], Na ₂ WO ₄ ·2H ₂ O, F.W. 329.86 (293.83anhy), Powder, m.p. 100° -2H ₂ O, d. 3.250, Merck 14,8698, Fieser 13,145 15,295, EINECS 236-743-4, RTECS YO7900000, MDL MFCD00149190, † Maximum level of impurities: Insoluble matter 0.01%, Titratable free base 0.02meq/g, Cl 0.005%, Mo 0.001%, SO ₄ 0.01%, Heavy metals and iron (as Pb) 0.001% | 100g 500g |
| ! H: H302-H319, P: P280-P264-P305+P351+P338-P301+P312-P337+P313-P501a | | |
| Sodium vanadate (ortho), see Sodium orthovanadate, 81104, p. 347 | | |
| Sodium vanadium oxide, see Sodium orthovanadate, 81104, p. 347 | | |
| L02814 | Solketal, 97% [(+/-)-2,2-Dimethyl-1,3-dioxolane-4-methanol, (+/-)-2,3-O-Isopropylidenedeglycerol] [100-79-8], C ₈ H ₁₆ O ₃ , F.W. 132.16, m.p. -27°, b.p. 188-190°, f.p. 80° (176°F), d. 1.064, n _D ²⁰ 1.4340, Merck 14,5213, EINECS 202-888-7, RTECS JI0400000, BRN 104465, MDL MFCD00063238, † H: H227 | 100g 500g 2.5kg |
| Application(s): Useful for synthesis of mono-, di- and triglycerides | | |
| Solvent Black 3, see Sudan Black B, J62268, p. 355 | | |
| Solvent Black 5, see Nigrosin, alcohol soluble, J61186, p. 302 | | |
| A15395 | Solvent Blue 38 [C.I. 74180, Direct Blue 86] [1328-51-4], m.p. ca 235° dec., EINECS 215-523-1, MDL MFCD00071424 | 25g 100g |
| Solvent Orange 7, see Sudan II, A17613, p. 355 | | |
| Solvent Red 24, see Sudan IV, A12181, p. 355 | | |
| Solvent Red 27, see Oil Red O, A12989, p. 307 | | |
| Solvent Red 140, see Erythrosin B, spirit soluble, J62619, p. 210 | | |
| Solvent Yellow 3, see Fast Garnet GBC base, J60574, p. 218 | | |
| Solvent Yellow 94, see Fluorescein, L13251, p. 222 | | |
| J62984 | Sorafenib, 99+% [BAY 43-9006] [284461-73-0], C ₂₁ H ₁₆ ClF ₃ N ₄ O ₃ , F.W. 464.83, Crystalline powder, Merck 14,8720 | 1g 2g 5g |
| Application(s): An inhibitor of Raf kinase, PDGF, VEGF receptor 2&3 kinases | | |
| A16196 | Sorbic acid, 99% [Hexa-2,4-dienoic acid] [110-44-1], CH ₃ CH=CHCH=CHCO ₂ H, F.W. 112.13, m.p. 132-135°, b.p. 228° dec., f.p. 127° (260°F), d. 1.205, Merck 14,8721, Fieser 15,296, EINECS 203-768-7, RTECS WG2100000, BRN 1741831, MDL MFCD00002703, † | 250g 500g 1kg 5kg |
| ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | | |
| Sorbitan mono-octadecanoate, see Sorbitan monostearate, L11435, p. 350 | | |
| J62576 | Sorbitan monooleate [Span® 80] [1338-43-8], C ₂₄ H ₄₄ O ₆ , F.W. 428.61, Viscous liquid, f.p. 113° (235°F), Merck 14,8724, EINECS 215-665-4, RTECS WG2932400, MDL MFCD00080948, † | 1L |
| Application(s): An emulsifier | | |

| Stock # | Description | Size |
|--|--|--|
| L11435 | Sorbitan monostearate <i>[Sorbitan monoostadecanoate, Span® 60]</i> [1338-41-6], C ₂₈ H ₄₈ O ₆ , F.W. 430.63, m.p. 53-57°, f.p. >149°(300°F), d. 1.00, Merck 14,8724, EINECS 215-664-9, RTECS WG2933500, MDL MFCD00005366, † Span® is a registered trademark of ICI Group. Nonionic surfactant. |  250g 1kg |
| Application(s): Emulsifier used in cosmetics, pharmaceuticals and food preparation | | |
| J62648 | Sorbitan sesquioleate <i>[Arlacel® 83, Span® 83]</i> [8007-43-0], C ₄₂ H ₇₆ O ₇ , F.W. 693.06, Viscous liquid, f.p. 113°(235°F), d. 0.989, n _D ²⁰ 1.478, EINECS 232-360-1, RTECS WG2934330, MDL MFCD00151568, † | 500ml 1L |
| Application(s): An emulsifier | | |
| 36404 | D-Sorbitol, 98% ■ <i>[D-Glucitol]</i> [50-70-4], C ₆ H ₁₄ O ₆ , F.W. 182.17, Powder, m.p. 98-100°, Merck 14,8725, Solubility: Soluble in water, methanol, acetone, DMF, EINECS 200-061-5, RTECS LZ4290000, BRN 1721899, MDL MFCD00004708, † |  500g 2kg |
| B21208 | D-Sorbose, 98% [3615-56-3], C ₆ H ₁₂ O ₆ , F.W. 180.16, m.p. 163-165°, EINECS 222-796-0, MDL MFCD00151095 |  100mg 500mg |
| J63772 | Sotalol hydrochloride, 98% <i>[N-[4-[1-Hydroxy-2-(isopropylamino)ethyl]phenyl]methanesulfonamide hydrochloride]</i> [959-24-0], C ₁₂ H ₂₀ N ₂ O ₃ S HCl, F.W. 308.82, Powder, Merck 14,8728, EINECS 213-496-0, RTECS PB0826000, MDL MFCD00242937 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 100mg 1g 5g |
| Application(s): Potent β adrenergic antagonist | | |
| J61399 | Soybean oil <i>[Glycine Soja]</i> [8001-22-7], Oil, f.p. >113°(235°F), d. 0.92, n _D ²⁰ 1.4743, EINECS 232-274-4, RTECS WG4862000, MDL MFCD00132356, † | 500ml 1L |
| J65573 | SP6 RNA Polymerase in potassium phosphate buffer <i>[RNA Polymerase from Salmonella enterica serotype typhimurium, SP6-infected]</i> [9014-24-8], Liquid, MDL MFCD00132197, † | 1kilounit 5kilounits |
| Application(s): Transcribes RNA from DNA sequences | | |
| J65792 | SP6 RNA Polymerase in Tris buffer <i>[RNA Polymerase from Salmonella enterica serotype typhimurium, SP6-infected]</i> [9014-24-8], Liquid, MDL MFCD00132197, † | 2kilounits 10kilounits |
| Application(s): Transcribes RNA from DNA sequences | | |
| J64124 | SP6 RNA Polymerase 10X Reaction Buffer Liquid | 6ml |
| Application(s): For use with SP6 RNA Polymerase product no. J65792 | | |
| J65092 | SP6 RNA Polymerase 5X Transcription Optimized Buffer Liquid | 200microliters |
| Application(s): For use with SP6 RNA Polymerase product no. J65573 | | |
| SpA , see Protein A, Staph. aureus, J63404, p. 330 Span® 60 , see Sorbitan monostearate, L11435, p. 350 Span® 80 , see Sorbitan monooleate, J62576, p. 349 Span® 83 , see Sorbitan sesquioleate, J62648, p. 350 | | |
| J61820 | Spectinomycin dihydrochloride pentahydrate, Cell Culture Grade <i>[Spectinomycin dihydrochloride]</i> [22189-32-8], C ₁₈ H ₂₈ N ₂ O ₇ ·2HCl·5H ₂ O, F.W. 495.35 (405.28anhy), Powder, EINECS 244-554-3, RTECS WG7400000, MDL MFCD00150886, Note: Greater than 600 micrograms per milligram | 5g 25g |
| Application(s): An aminocyclitol antibiotic that binds to the 30S ribosomal subunit of bacteria and interrupts protein synthesis | | |
| Spectinomycin dihydrochloride, see Spectinomycin dihydrochloride pentahydrate, Cell Culture Grade, J61820, p. 350 | | |
| A19096 | Spermidine, 99% △ <i>[N-(3-Aminopropyl)-1,4-diaminobutane, 1,8-Diamino-4-azaoctane]</i> [124-20-9], H ₂ N(CH ₂) ₂ NH(CH ₂) ₄ NH ₂ , F.W. 145.25, m.p. 22-25°, b.p. 128-130°/14mm, f.p. >110°(230°F), d. 0.925, n _D ²⁰ 1.4790, Merck 14,8742, UN2735, EINECS 204-689-0, RTECS EJ7000000, BRN 1698591, MDL MFCD00008229, † ! H:H314, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 1g 5g 25g 100g |
| Application(s): Binds to the polyamine modulatory site of NMDA | | |



| Stock # | Description | Size |
|---|--|-----------------|
| J61595 | Spermidine trihydrochloride, 99+% [N-(3-Aminopropyl)-1,4-butanediamine trihydrochloride] [334-50-9], NH ₂ (CH ₂) ₃ NH(CH ₂) ₄ NH ₂ ·3HCl, F.W. 254.63, Powder, m.p. 250° dec., Merck 14,8742, EINECS 206-379-0, RTECS EJ7023000, BRN 3552356, MDL MFCD00012918, † ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | 100mg |
| Application(s): Binds and precipitates DNA; may be used for purification of DNA binding proteins | | |
| L19562 | Spermine, 97% ▲ ■ [Neuridine, Musculamine] [71-44-3], C ₁₀ H ₂₆ N ₄ , F.W. 202.35, m.p. 28-30°, b.p. 150°/5mm, f.p. >110°(230°F), Merck 14,8743, UN3259, EINECS 200-754-2, RTECS EJ7175000, BRN 1751791, MDL MFCD00008215, † ! H: H314, P: P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 1g 5g |
| Application(s): Binds to the polyamine modulatory site of NMDA | | |
| J63060 | Spermine tetrahydrochloride, 99% [N,N'-Bis(3-aminopropyl)-1,4-butanediamine tetrahydrochloride] [306-67-2], C ₁₀ H ₂₆ N ₄ ·4HCl, F.W. 348.19, Powder, EINECS 206-189-8, RTECS EJ7230000, BRN 3911771, MDL MFCD00012914, † ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 1g 5g 25g |
| Application(s): Binds to the polyamine modulatory site of NMDA | | |
| DL-Sphinganine , see DL-erythro-Dihydrosphingosine, J62103, p. 191 4-Sphingenine , see D-erythro-Sphingosine, 99+%, J63584, p. 351 | | |
| J63584 | D-erythro-Sphingosine, 99+% [4-Sphingenine, trans-D-erythro-2-Amino-4-octadecene-1,3-diol] [123-78-4], C ₁₈ H ₃₇ NO ₂ , F.W. 299.50, Powder, Merck 14,8747, EINECS 204-651-3, BRN 1727294, MDL MFCD00036751 | 5mg 25mg |
| Application(s): Inhibits protein kinase C and calmodulin-dependent enzymes. Induces apoptosis. A constituent of cell membranes | | |
| H52427 | D-erythro-Sphingosine hydrochloride, 97% [trans-D-erythro-2-Amino-4-octadecene-1,3-diol hydrochloride] [2673-72-5], C ₁₈ H ₃₇ NO ₂ ·HCl, F.W. 335.96 | 100mg 500mg |
| Application(s): Inhibitor of protein kinase C and calmodulin-dependent enzymes, but may stimulate mast cells by activation of protein kinase C | | |
| J60119 | Spirolactone [52-01-7], C ₂₂ H ₃₂ O ₅ , F.W. 416.58, Powder, m.p. 207-208°, Merck 14,8760, EINECS 200-133-6, RTECS TU4725000, MDL MFCD00082250, † ! H: H360, P: P281-P201-P202-P308+P313-P405-P501 | 1g 5g 10g |
| Application(s): Antihypertensive potassium sparing diuretic; aldosterone receptor antagonist | | |
| B20944 | Squalene, 98% ▲ ▲ [2,6,10,15,19,23-Hexamethyl-2,6,10,14,18,22-tetracosahexaene] [111-02-4], C ₃₀ H ₅₀ , F.W. 410.73, m.p. -75°, b.p. 285°/25mm, f.p. 218°(424°F), d. 0.855, n _D ²⁰ 1.4955, Merck 14,8768, EINECS 203-826-1, MDL MFCD00008912, † | 100g 500g |
| Application(s): Biosynthetic precursor to all steroids | | |
| J60839 | SSC buffer (20X) Liquid, Note: 0.3M sodium citrate, 3.0M sodium chloride, pH 7.0. | 1L 2L 4L |
| J60561 | SSC (20X), RNase free Liquid, Note: 0.3M sodium citrate, 3.0M sodium chloride, pH 7.0. | 250ml 500ml |
| J61214 | SSPE (20X) Liquid, Note: 0.2M sodium phosphate, 3.0M sodium chloride, 20mM EDTA, pH approx. 7.4 | 1L 2L 4L |
| J60783 | SSPE (20X), RNase free Liquid, Note: 0.2M sodium phosphate, 3.0M sodium chloride, 20mM EDTA. | 250ml 500ml |
| J63450 | Stacking buffer (4X) Liquid, Note: Contains 0.5M Tris-HCl, 0.4% SDS, pH 6.8. | 500ml 1L |
| J62630 | Stains-All, 95% ▲ [7423-31-6], C ₃₀ F ₁₂ BrN ₂ S ₂ , F.W. 559.58, Powder, EINECS 231-047-7, BRN 3865213, MDL MFCD00078788, † ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 1g 5g |
| Application(s): Cationic carbocyanine dye used in electrophoresis to stain proteins and nucleic acids | | |


| Stock # | Description | Size |
|---------|---|--------------------|
| H32127 | Stains-All, 96% [1-Ethyl-2-[(E)-3-(1-ethylnaphtho[1,2-d]thiazolin-2-ylidene)-2-methylpropenyl-naphtho[1,2-d]thiazolium bromide, 3,3'-Diethyl-9-methyl-4,5,4',5'-dibenzothiacarbocyanine] [7423-31-6], C ₃₀ H ₂₇ BrN ₂ S ₂ , F.W. 559.58, EINECS 231-047-7, BRN 3865213, MDL MFCD00078788, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 1g 5g |
| | Application(s): General protein and nucleic acid stain, which stains different colors on bands of RNA (bluish purple), DNA (blue) and proteins (red) | |
| 36703 | Starch, soluble, ACS (for iodometry) [Amylodextrin] [9005-84-9], Powder, m.p. 256-258° dec., Merck 14,8799, Solubility: Soluble in hot water, EINECS 232-686-4, MDL MFCD00082026, † Maximum level of impurities: Solubility P.T., pH of a 2% solution 5.0-7.0 at 25°, Residue after ignition 0.4%, Sensitivity P.T. | 50g 250g 1kg |
| J65749 | STAT5 Inhibitor ▲ [(E)-N'-((4-Oxo-4H-chromen-3-yl)methylene)nicotinohydrazide] C ₁₆ H ₁₁ N ₃ O ₃ , F.W. 293.30, Solid | 10mg |
| J62837 | Staurosporine, 99+% [Antibiotic AM-2282] [62996-74-1], C ₂₈ H ₂₆ N ₂ O ₃ , F.W. 466.54, Powder, m.p. 240-243°, Merck 14,8802, RTECS KD5084000, BRN 1060573, MDL MFCD00077402 ! H:H350, P:P281-P201-P202-P308+P313-P405-P501a | 1mg 5mg 10mg |
| | Application(s): Broad spectrum protein kinase inhibitor | |
| | Staurosporinone , see K252c, 99%, J63090, p. 262 | |
| J60265 | STE buffer soln. Liquid, Note: Contains 100mM NaCl, 10mM Tris-HCl, 1mM EDTA, pH 8.0. | 1L 2L |
| A12244 | Stearic acid, 98% [Octadecanoic acid] [57-11-4], CH ₃ (CH ₂) ₁₆ CO ₂ H, F.W. 284.48, m.p. 69-72°, b.p. 232°/15mm, f.p. 196°(384°F), d. 0.941, Merck 14,8804, EINECS 200-313-4, RTECS WI2800000, BRN 608585, MDL MFCD00002752, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 5g 25g 100g |
| | Application(s): A saturated fatty acid | |
| | Stearic acid cholesteryl ester , see Cholesteryl stearate, A14771, p. 161 | |
| J65114 | Stem-Cell Factor/c-Kit Inhibitor ▲ [SCF/c-Kit Signaling Inhibitor, ISCK03] [945526-43-2], C ₁₈ H ₁₇ N ₃ O ₃ S, F.W. 355.50, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10mg 50mg |
| J60563 | STET Liquid, Note: 100mM NaCl, 10mM Tris-HCl (pH 8.0), 1mM EDTA, 5% Triton X-100. | 500ml 1L |
| A11924 | cis-Stilbene, 97% ▲ [cis-1,2-Diphenylethylene] [645-49-8], C ₁₄ H ₁₂ , F.W. 180.25, m.p. 1-2°, b.p. 307°, f.p. >110°(230°F), d. 1.04, n _D ²⁰ 1.6220, Merck 14,8817, EINECS 211-445-7, RTECS DA0513600, BRN 1616739, MDL MFCD00004788 ! H:H319, P:P305+P351+P338 | 1g 5g 25g |
| |  | |
| | D-Streptamine , see Apramycin, 98+%, J63874, p. 108 | |
| J62428 | Streptavidin, Streptomyces avidinii, 96% [9013-20-1], Lyophilized powder, 13.5 kDa, MDL MFCD00082035 | 2mg 10mg |
| | Application(s): A protein with high affinity for biotin | |
| J61299 | Streptomycin sulfate, Cell Culture Reagent [3810-74-0], C ₂₁ H ₃₈ N ₂ O ₁₂ · 1.5H ₂ SO ₄ , F.W. 728.69, Powder, Merck 14,8826, EINECS 223-286-0, RTECS WK4990000, BRN 3894995, MDL MFCD00037023, † ! H:H302, P:P264-P270-P301+P312-P330-P501 | 50g 100g |
| | Application(s): Inhibits initiation and causes misreading of rRNA in protein synthesis | |
| J61601 | Streptozotocin, 97+% ■ [NSC-85998, U-9889] [18883-66-4], C ₈ H ₁₃ N ₃ O ₃ , F.W. 265.22, Powder, m.p. 121°, Merck 14,8832, EINECS 242-646-8, RTECS LZ5775000, BRN 2060675, MDL MFCD00006607 ! H:H351, P:P281-P201-P202-P308+P313-P405-P501a | 500mg 1g |
| | Application(s): Antibiotic and antitumor agent. Potent methylating agent for DNA | |
| J60925 | Stripping buffer (4X) Liquid, Note: 150mM Tris-HCl, 8% SDS, pH 6.8. Add mercaptoethanol according to your protocol. ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 250ml 500ml |





| Stock # | Description | Size |
|---|---|--------------------|
| J62023 | Stripping buffer-2 (4X) Liquid, Note: 0.2M Glycine, pH 2.5. | 250ml 500ml |
| J60810 | Stripping buffer-3 (4X) Liquid, Note: 0.4M Glycine, 0.2% SDS, 2% Tween-20, pH 2.5. | 250ml 500ml |
| γ-Strophanthin, see Oubain octahydrate, 98%, J60724, p. 310 | | |
| J61534 | SU buffer, SDS + Urea Liquid, Note: 5% SDS, 8M Urea, 50mM Tris-HCl and 0.05% bromophenol blue, pH 6.8 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 50ml 100ml |
| J63489 | Substance P [Arg-Pro-Lys-Pro-Gln-Gln-Phe-Phe-Gly-Leu-Met-NH2] [33507-63-0], C ₆₃ H ₉₈ N ₁₆ O ₁₃ S, F.W. 1347.64, Powder, EINECS 251-545-8, MDL MFCD00076780 Application(s): A neurokinin NK-1 receptor agonist | 1mg 5mg 25mg |
| J61828 | Substance P free acid [H-Arg-Pro-Lys-Pro-Gln-Gln-Phe-Phe-Gly-Leu-Met-OH] [71977-09-8], C ₆₃ H ₉₇ N ₁₇ O ₁₄ S, F.W. 1348.63, Powder Application(s): A neurokinin NK-1 receptor agonist | 5mg |
| J62756 | Substance P (1-4) [Arg-Pro-Lys-Pro] [57468-16-3], C ₂₂ H ₄₀ N ₃ O ₅ , F.W. 496.61, Powder Application(s): Active fragment of Substance P | 5mg |
| J60018 | Substance P (1-7), 96% [Arg-Pro-Lys-Pro-Gln-Gln-Phe] [68060-49-1], C ₄₁ H ₆₅ N ₁₃ O ₁₀ S, F.W. 900.05, Powder, MDL MFCD00076789 Application(s): Active fragment of Substance P | 2mg 5mg |
| J61891 | Substance P (4-11) [Octa-Substance P, Pro-Gln-Gln-Phe-Phe-Gly-Leu-Met-NH2] [53749-60-3], C ₄₈ H ₆₇ N ₁₁ O ₁₀ S, F.W. 966.17, Powder Application(s): Active fragment of Substance P | 5mg 25mg |
| J63228 | Substance P (6-11) [Hexa-Substance P, Gln-Phe-Phe-Gly-Leu-Met-NH2] [51165-09-4], C ₄₁ H ₆₀ N ₁₀ O ₉ S, F.W. 869.05, Powder Application(s): Active fragment of Substance P | 5mg 25mg |
| J63619 | Succinate, 0.2M buffer soln., pH 4.0 [110-15-6], Liquid, † H:H303, P:P312 | 250ml 500ml |
| J63881 | Succinate, 0.2M buffer soln., pH 4.5 [110-15-6], Liquid, † H:H303, P:P312 | 250ml 500ml |
| J63863 | Succinate, 0.2M buffer soln., pH 5.0 [110-15-6], Liquid, † H:H303, P:P312 | 250ml 500ml |
| J61100 | Succinate, 0.2M buffer soln., pH 5.5 [110-15-6], Liquid, † H:H303, P:P312 | 250ml 500ml |
| J61853 | Succinate, 0.2M buffer soln., pH 6.0 [110-15-6], Liquid, † H:H303, P:P312 | 250ml 500ml |
| J62078 | Succinate, 0.2M buffer soln., pH 6.5 [110-15-6], Liquid, † H:H303, P:P312 | 250ml 500ml |
| 33272 | Succinic acid, ACS, 99.0% min [Butanedioic acid] [110-15-6], HO ₂ CCH ₂ CH ₂ CO ₂ H, F.W. 118.09, Crystalline, m.p. 186-188°, b.p. 235°, f.p. 206°(402°F), d. 1.56, Merck 14,8869, Solubility: Soluble in water (increasing with temperature). Soluble in alcohol, methanol, EINECS 203-740-4, RTECS WM4900000, BRN 1754069, MDL MFCD00002789, † Maximum level of impurities: Insoluble matter 0.01%, Residue after ignition 0.02%, Cl 0.001%, PO ₄ 0.001%, SO ₄ 0.003%, Nitrogen compounds (as N) 0.001%, Heavy Metals (as Pb) 5ppm, Fe 5ppm, Melting point 185.0°-191.0° ! H:H318-H335-H315, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 500g 2kg |

| Stock # | Description | Size |
|---------|---|---|
| A12245 | Succinic anhydride, 99% ▲ <i>[Butanedioic anhydride, Dihydro-2,5-furandione]</i> [108-30-5], C ₄ H ₄ O ₃ , F.W. 100.07, m.p. 118-121°, b.p. 261°, f.p. 157°(314°F), d. 1.572, Merck 14,8870, Fieser 4,468, Solubility: Soluble in chloroform, EINECS 203-570-0, RTECS WN0875000, BRN 108441, MDL MFCD00005525, † |  250g 500g 1kg 5kg |
| | † H:H302-H319-H335, P:P261-P280-P305+P351+P338-P304+P340-P405-P501a Friedel-Crafts reaction with arenes gives 3-aryloxypropionic acids: <i>Org. Synth. Coll.</i> , 2 , 81 (1943). For a review of the Friedel-Crafts reactions of the anhydrides of dibasic acids, see: <i>Org. React.</i> , 5 , 229 (1949). For reaction with phosphoranes, in a route to 2,2-disubstituted cyclopentane-1,3-diones, see (1-Ethoxycarbonyl)ethylidene)triphenylphosphorane, A15619 . A method for protecting both H atoms of a primary amine consists of formation of the succinimide, followed by enolsilylation with Triisopropylsilyl trifluoromethanesulfonate, B21127 , to form the 2,5-bis(triisopropylsiloxy)pyrroles. Deprotection can be effected by desilylation with dilute HCl, followed by hydrazinolysis: <i>Tetrahedron Lett.</i> , 38 , 2617 (1997). | |
| A13503 | Succinimide, 98+% <i>[Butanimide, 2,5-Pyrrolidinedione]</i> [123-56-8], C ₄ H ₅ NO ₂ , F.W. 99.09, m.p. 121-126°, b.p. 287-288°, f.p. 201°(393°F), d. 1.410, Merck 14,8871, EINECS 204-635-6, RTECS WN2200000, BRN 108440, MDL MFCD00005495, † With the cycloalkenylation agent (1-Ethoxycarbonylcyclopropyl)triphenylphosphonium tetrafluoroborate, A18305 , gives a bridgehead lactam (pyrrolizone) which is an intermediate in a diastereoselective synthesis of (±)-isoretrocanol: <i>Liebigs Ann. Chem.</i> , 521 (1983): |  250g 1kg 5kg |
| |  | |
| J64834 | N-Succinimidyl 15-azido-4,7,10,13-tetraoxapentadecanoate <i>[Azido-PEG4-NHS ester]</i> C ₁₅ H ₂₄ N ₄ O ₈ , F.W. 308.37, Liquid | 25mg 100mg 1g |
| | † H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J61410 | N-Succinimidyl 3-maleimidobenzoate, 98+% ▲▲ <i>[3-Maleimidobenzoic acid N-hydroxysuccinimide ester]</i> [58626-38-3], C ₁₅ H ₁₀ N ₂ O ₆ , F.W. 314.26, Powder, m.p. 175-177°, EINECS 261-368-8, BRN 1505254, MDL MFCD00005514 | 250mg 1g 5g |
| | † H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): A heterobifunctional coupling reagent useful for forming enzyme immunoconjugates | |
| J64496 | N-Succinimidyl 3-(propargyloxy)propionate <i>[Acetylene-PEG-NHS ester]</i> C ₁₀ H ₁₁ NO ₅ , F.W. 225.20, Solid | 100mg |
| | † H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J64902 | N-Succinimidyl 4,7,10,13-tetraoxahexadec-15-ynoate <i>[Acetylene-PEG4-NHS ester]</i> C ₁₈ H ₂₃ NO ₆ , F.W. 357.36, Viscous liquid | 25mg 100mg |
| | † H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J65375 | N-Succinyl-Gly-Gly-Phe-p-nitroanilide ▲ <i>[Suc-Gly-Gly-Phe-pNA, Chymotrypsin Substrate I, Colorimetric]</i> [68982-90-1], C ₂₃ H ₂₅ N ₃ O ₈ , F.W. 499.47, Solid, EINECS 273-486-7, MDL MFCD00038721 | 5mg 50mg |
| A15583 | Sucrose, 99% <i>[D-(+)-Saccharose]</i> [57-50-1], C ₁₂ H ₂₂ O ₁₁ , F.W. 342.30, m.p. 186-190°, d. 1.580, [α] _D ²⁰ +66.5° (c=10 in water), Merck 14,8881, EINECS 200-334-9, RTECS WN6500000, BRN 90825, MDL MFCD00006626, † | 500g 2.5kg 10kg |
| | Application(s): Used for protein purification in sucrose density gradient studies | |
| 36508 | Sucrose, ACS <i>[D-(+)-Saccharose]</i> [57-50-1], C ₁₂ H ₂₂ O ₁₁ , F.W. 342.30, Crystalline, m.p. 185-187°, d. 1.58, Merck 14,8881, Solubility: Soluble in water. Slightly soluble in alcohol, methanol, EINECS 200-334-9, RTECS WN6500000, BRN 90825, MDL MFCD00006626, † Maximum level of impurities: Specific rotation [α] _D ²⁵ +66.3° to +66.8°, Insoluble matter 0.005%, Loss on drying at 105° 0.03%, Residue after ignition 0.01%, Titratable acid 0.0008meq/g, Cl 0.005%, Sulfate and sulfite (as SO ₄) 0.005%, Heavy Metals (as Pb) 5ppm, |  250g 1kg |
| J65148 | Sucrose, Molecular Biology Grade <i>[D-(+)-Saccharose]</i> [57-50-1], C ₁₂ H ₂₂ O ₁₁ , F.W. 342.30, Crystalline solid, m.p. 185-187°, d. 1.58, EINECS 200-334-9, RTECS WN6500000, BRN 90825, MDL MFCD00006626, † | 100g 500g 1kg |
| | Application(s): For protein purification by sucrose density gradients | |


| Stock # | Description | Size |
|---|--|-----------------------|
| J64270 | Sucrose, ultrapure, 99% [D-(-)-Saccharose] [57-50-1], C ₁₂ H ₂₂ O ₁₁ , F.W. 342.30, Crystalline, m.p. 185-187°, d. 1.58, Merck 14,8881 , EINECS 200-334-9, RTECS WN6500000, BRN 90825, MDL MFCD00006626, † | 100g 500g 1kg |
| J63662 | Sucrose, 1.2M aq. soln. [57-50-1], C ₁₂ H ₂₂ O ₁₁ , F.W. 342.30, Liquid, † | 500ml 1L |
| J60720 | Sucrose, 80%, in MNE buffer, MES + NaCl + EDTA Liquid | 250ml 500ml |
| J63979 | Sucrose gelatin veronal buffer (SGVB), pH 7.2 Liquid, Note: Contains 5mM barbital, 30mM NaCl, 227mM sucrose, 0.1% gelatin, 0.5mM magnesium chloride, 0.15mM calcium chloride, pH 7.2. | 250ml 500ml |
| J62587 | Sucrose gelatin veronal buffer with EDTA (SGVBE), pH 7.2 Liquid, Note: Contains 5mM barbital, 30mM NaCl, 227mM sucrose, 0.1% gelatin, 10mM EDTA, pH 7.2. | 250ml 500ml |
| A17613 | Sudan II [C.I. 12140, Solvent Orange 7] [3118-97-6], C ₁₈ H ₁₆ N ₂ O, F.W. 276.34, m.p. 156-160°, EINECS 221-490-4, MDL MFCD00003896, † ⚠ ! H:H351-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 25g 100g |
| A18318 | Sudan III [C.I. 26100, Solvent Red 23] [85-86-9], C ₂₂ H ₁₆ N ₂ O, F.W. 352.40, m.p. ca 200° dec., Merck 14,8884 , EINECS 201-638-4, RTECS QK4250000, BRN 931185, MDL MFCD00003905, † ⚠ ! H:H341-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 25g 100g 500g |
| A12181 | Sudan IV [C.I. 26105, Scarlet Red] [85-83-6], C ₂₄ H ₂₀ N ₂ O, F.W. 380.45, m.p. ca 185° dec., Merck 14,8393 , EINECS 201-635-8, MDL MFCD00003893, † ⚠ ! H:H341-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 25g 100g |
| Application(s): Useful as a stain for fat in animal tissue | | |
| J62268 | Sudan Black B [C.I. 26150, Solvent Black 3] [4197-25-5], C ₂₀ H ₁₂ N ₂ , F.W. 456.55, Powder, m.p. 118-126°, Merck 14,8885 , EINECS 224-087-1, RTECS SD4431500, BRN 723248, MDL MFCD00006919, † | 10g 25g 100g |
| Application(s): Histochemical stain for chromosomes | | |
| A19836 | Sulfacetamide, 98% [N-(4-Aminobenzene-sulfonyl)acetamide, N-Sulfanilylacetamide] [144-80-9], C ₉ H ₁₀ N ₂ O ₂ S, F.W. 214.24, m.p. 182-184°, Merck 14,8899 , EINECS 205-640-6, RTECS AC8450000, BRN 981718, MDL MFCD00066501, † ⚠ H:H341, P:P281-P201-P202-P308+P313-P405-P501a | 50g 250g |
| Application(s): Sulfonamide antibiotic with antibacterial activity, especially against acne | | |
| Sulfadimidine, see Sulfamethazine, A19276, p. 355 | | |
| L04194 | Sulfamerazine, 98+% [N(1)-(4-Methyl-2-pyrimidinyl)sulfanilamide, 2-Sulfanilamido-4-methylpyrimidine] [127-79-7], C ₁₁ H ₁₂ N ₄ O ₂ S, F.W. 264.30, m.p. 234-238°, Merck 14,8913 , EINECS 204-866-2, RTECS WP0750000, BRN 249133, MDL MFCD00023212, † | 25g 100g |
| A19276 | Sulfamethazine, 99% [N(1)-(4,6-Dimethyl-2-pyrimidinyl)sulfanilamide, Sulfadimidine] [57-68-1], C ₁₃ H ₁₄ N ₄ O ₂ S, F.W. 278.34, m.p. 198-201°, EINECS 200-346-4, MDL MFCD00006066, † | 25g 100g |
| Application(s): Sulfonamide antibacterial | | |
| Sulfamic acid, see Amidosulfonic acid, 33233, p. 91 | | |
| A13001 | Sulfanilamide, 98% [4-Aminobenzene-sulfonamide] [63-74-1], C ₆ H ₇ N ₂ O ₂ S, F.W. 172.21, m.p. 163-168°, d. 1.08, Merck 14,8925 , EINECS 200-563-4, RTECS WO8400000, BRN 511852, MDL MFCD00007939, † ! H:H302, P:P264-P270-P301+P312-P330-P501a Intermediate for preparation of 2,6-disubstituted anilines, by electrophilic substitution followed by removal of the sulfonamide blocking group by desulfonation with sulfuric acid. See, e.g.: <i>Org. Synth. Coll.</i> , 3 , 262 (1955). | 100g 500g 2.5kg |
| Application(s): Sulfonamide antibacterial | | |
| 2-Sulfanilamido-4-methylpyrimidine, see Sulfamerazine, L04194, p. 355 | | |



| Stock # | Description | Size |
|--|--|----------------------|
| 41540 | Sulfanilic acid, ACS, 98.0-102.0% [121-57-3], C ₆ H ₇ NO ₃ S, F.W. 173.19, Powder, m.p. ca 365°, Merck 14,8926, EINECS 204-482-5, RTECS WP3895500, BRN 908765, MDL MFCD00007886, † Maximum level of impurities: Residue after ignition 0.01%, Insoluble in sodium carbonate 0.02%, Cl 0.002%, NO _x 0.5ppm, SO _x 0.01% ! H:H315-H319-H317, P:P261-P280-P305+P351+P338-P302+P352-P321-P501a | 50g 250g |
| Application(s): Reagent for chromatographic detection of histidine | | |
| N-Sulfanilylacetamide, see Sulfacetamide, A19836, p. 355 | | |
| 410727 | Sulfathiazole, 99% [N(1)-(2-Thiazolyl)sulfanilamide] [72-14-0], C ₈ H ₈ N ₂ O ₂ S ₂ , F.W. 255.32, m.p. 200-203°, Merck 14,8943, EINECS 200-771-5, MDL MFCD00005319, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 100g 500g |
|  | | |
| 410486 | Sulfonazo III tetrasodium salt [68504-35-8], C ₂₂ H ₁₂ N ₄ Na ₄ O ₁₄ S ₄ , F.W. 776.57, m.p. ≈300°, EINECS 270-924-9, MDL MFCD00003942 Indicator for determination of sulfates and sulfur: <i>Anal. Chem.</i> 37, 1159 (1965). Spectrophotometric reagent for alkaline earth metals. Application(s): Spectrophotometric reagent for alkaline earth metals and indicator for sulfate titrations | 5g 25g |
|  | | |
| J60581 | Sulforhodamine 101 acid chloride [Texas Red®, Sulforhodamine 101 sulfonyl chloride] [82354-19-6], C ₃₁ H ₂₆ ClN ₄ O ₆ S ₂ , F.W. 625.15, Powder, BRN 8667894, MDL MFCD00012406 ! H:H302-H351-H373, P:P260-P281-P301+P312-P308+P313-P405-P501 | 10mg |
| Application(s): Fluorescent labeling compound | | |
| Sulforhodamine 101 sulfonyl chloride, see Sulforhodamine 101 acid chloride, J60581, p. 356 | | |
| Sulforhodamine B, see Kiton Red S, A14769, p. 264 | | |
| 43144 | 5-Sulfosalicylic acid dihydrate, ACS, 99+% [2-Hydroxy-5-sulfobenzoic acid dihydrate] [5965-83-3], C ₇ H ₆ O ₆ S 2H ₂ O, F.W. 254.22 (218.19anhy), Powder, m.p. 103-112°, Merck 14,8964, Fieser 1,1118, UN2585, EINECS 202-555-6, RTECS VO650000, BRN 650741, MDL MFCD00007508, † Maximum level of impurities: Insoluble matter 0.02%, Residue after ignition 0.1%, Cl 0.001%, HOC ₆ H ₄ COOH 0.04%, SO _x 0.02%, Pb 0.002%, Fe 0.001% ! H:H314-H302, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 25g 100g 500g |
| Application(s): Reagent for precipitation of proteins | | |
| J61772 | Sulindac [cis-5-Fluoro-2-methyl-1-[4-(methylsulfinyl)benzylidene]indene-3-acetic acid, MK-231] [38194-50-2], C ₂₀ H ₁₇ FO ₃ S, F.W. 356.41, Powder, m.p. 182-185°, Merck 14,8982, UN2811, EINECS 253-819-2, RTECS NK8226000, MDL MFCD00599589 ! H:H301-H334-H361-H317, P:P285-P301+P310-P302+P352-P321-P405-P501a | 5g 25g |
| Application(s): A non-steroidal anti-inflammatory drug (NSAID) that inhibits cyclooxygenase-1 and induces apoptosis in HT-29 cells | | |
| J62104 | Sulindac sulfide [32004-67-4], C ₂₀ H ₁₇ FO ₂ S, F.W. 340.41, Powder, m.p. 189-191°, EINECS 250-892-2, MDL MFCD00869764 ! H:H302-H334-H317-H361, P:P285-P261-P302+P352-P321-P405-P501 | 100mg |
| Application(s): Active metabolite of sulindac; inhibits cyclooxygenase-1 | | |
| Sunsorb® 770, see 2-Deoxy-D-ribose, A11990, p. 180 | | |
| J63003 | Superoxide Dismutase, bovine erythrocytes [EC 1.15.1.1, SOD] [9054-89-1], Lyophilized powder, Merck 14,9002, EINECS 232-943-0, MDL MFCD00132404, Note: Minimum 1,400 units/mg dry wt. One unit inhibits by 50% the maximum reduction of nitro blue tetrazolium under the specified conditions Application(s): Catalyzes the dismutation of superoxide radicals to hydrogen peroxide and molecular oxygen | 2mg 10mg |
| J64422 | Suptopin-2 [(E)-4-Hydroxy-3-(3-(4-hydroxy-3,5-dimethoxyphenyl)acryloyl)-6-methyl-2H-pyran-2-one] [331852-66-5], C ₁₇ H ₁₆ O ₇ , F.W. 332.30, Powder, MDL MFCD00810236 | 10mg |
| J61707 | Suramin hexasodium salt, 98+% [129-46-4], C ₆₁ H ₂₆ N ₆ Na ₆ O ₂₃ S ₆ , F.W. 1429.16, Powder, Merck 14,9006, EINECS 204-949-3, RTECS QM7000000, BRN 3694087, MDL MFCD00210217 Application(s): An antitumor and antiparasitic compound. Inhibits reverse transcriptase | 250mg 500mg 1g |
| J64281 | Syk Inhibitor ▲ [Spleen Tyrosine Kinase Inhibitor] [622387-85-3], C ₁₈ H ₁₃ N ₃ O ₃ S, F.W. 353.40, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1mg 5mg |

| Stock # | Description | Size |
|---------|---|-------------------------|
| J62843 | Syntide 2, 96% [Pro-Leu-Ala-Arg-Thr-Leu-Ser-Val-Ala-Gly-Leu-Pro-Gly-Lys-Lys] [108334-68-5], C ₆₈ H ₁₂₂ N ₂₀ O ₁₈ , F.W. 1507.84, Lyophilized powder | 1mg 5mg |
| | Application(s): Selective substrate for calmodulin-dependent protein kinase II | |
| J65312 | T4 DNA Ligase, in 20mM Tris HCl and 50mM KCl [EC 6.5.1.1] [9015-85-4], F.W. 62kDa, Liquid, EINECS 232-770-0, MDL MFCD00163508, † | 1kilounit 5kilounits |
| | Application(s): Seals nicks in double stranded DNA and RNA and also in DNA/RNA hybrids. For ligation of blunt ended or cohesive DNA fragments | |
| J65133 | T4 DNA Ligase, 99+%, in 10mM Tris HCl and 50mM NaCl [EC 6.5.1.1] [9015-85-4], F.W. 55.3kDa, Liquid, EINECS 232-770-0, MDL MFCD00163508, † | 150kilounits |
| | Application(s): Forms an energy dependent phosphodiester linkage between the termini of adjacent polynucleotides of duplex DNA. For ligation of cloning vector and restriction insert fragments | |
| J65896 | T7 RNA Polymerase, in 20mM potassium phosphate and 10mM DTT [EC 2.7.7.6] [9014-24-8], Liquid, EINECS 232-756-4, † | 1kilounit 5kilounits |
| | Application(s): For synthesis of RNA transcripts, biologically active mRNA and antisense RNA | |
| J60070 | Tacrine hydrochloride hydrate, 98+% [9-Amino-1,2,3,4-tetrahydroacridine hydrochloride, THA hydrochloride] [1684-40-8], C ₁₃ H ₁₄ N ₂ HCl·xH ₂ O, F.W. 234.73(anhy), Powder, m.p. 283-284°, Merck 14,9024, UN2811, EINECS 216-867-5, RTECS AR9532500, MDL MFCD00150067 | 500mg 1g 5g |
| | ! H:H302-H332-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): A potent centrally acting anticholinesterase | |
| J63571 | Tacrolimus, 99+% [FK-506, Fugimycin] [104987-11-3], C ₄₄ H ₆₈ NO ₁₂ , F.W. 804.02, Powder, m.p. 120-125°, Merck 14,9025, UN2811, RTECS KD4200000, MDL MFCD11045918 | 50mg 100mg 500mg |
| | H:H301, P:P264-P270-P301+P310-P321-P405-P501a | |
| | Application(s): Interacts with the immunophilins cyclophilin and FKBP-12 | |
| J63677 | TAE (10X), TRIS + acetate + EDTA Liquid, Note: 0.4M Tris base, 0.4M acetate, 10mM EDTA, pH 8.0., † | 1L 2L 4L |
| J63931 | TAE (50X), TRIS + acetate + EDTA Liquid, Note: 2M Tris base, 1M acetate, 50mM EDTA, pH 8.0., † | 1L 2L 4L |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| B21192 | D-Tagatose, 99% [87-81-0], C ₆ H ₁₂ O ₆ , F.W. 180.16, m.p. 129-135°, [α] _D ²⁰ -4.7° (c=1 in water), Merck 14,9030, EINECS 201-772-3, BRN 1724555, MDL MFCD00134449 | 250mg 1g 5g |
| |  | |
| J64028 | Tamibarotene [AM 80] [94497-51-5], C ₂₂ H ₂₆ NO ₃ , F.W. 351.44, Solid, Merck 14,9047, RTECS DH6940000, MDL MFCD00866188 | 10mg 50mg |
| J64893 | Tamm Horsfall Glycoprotein, human, 99% [Uromodulin] | 100micrograms |
| J63509 | Tamoxifen, 98+% [cis-1-(4-Dimethylaminoethoxyphenyl)-1,2-diphenyl-1-butene] [10540-29-1], C ₂₆ H ₂₉ NO, F.W. 371.52, Powder, Merck 14,9048, EINECS 234-118-0, RTECS KR5919600, MDL MFCD00010454 | 500mg 1g 5g |
| | H:H350-H360+H362, P:P263-P260-P281-P308+P313-P405-P501 | |
| | Application(s): Inhibitor of protein kinase C and induces apoptosis in cancer cells | |
| J60955 | Tamoxifen citrate ▲ ■ [cis-1-(4-Dimethylaminoethoxyphenyl)-1,2-diphenyl-1-butene citrate] [54965-24-1], C ₂₈ H ₂₉ NO ₃ ·C ₆ H ₈ O ₇ , F.W. 563.65, White to off-white powder, Merck 14,9048, EINECS 259-415-2, RTECS KH2387000, MDL MFCD00058321 | 1g 5g |
| | ! H:H350-H360+H362-H302, P:P263-P260-P281-P301+P312-P405-P501a | |
| | Application(s): Inhibitor of protein kinase C and induces apoptosis in cancer cells | |
| J61999 | Tamsulosin hydrochloride, 98+% [Hamal] [106463-17-6], C ₂₀ H ₂₈ N ₂ O ₂ S·HCl, F.W. 444.97, Powder, m.p. 228-230°, Merck 14,9049, RTECS DB2430000, MDL MFCD00922997 | 10mg 25mg 100mg |
| | ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): An α-1 adrenoceptor antagonist | |



| Stock # | Description | Size |
|--|---|--|
| J62004 | Tandutinib, 99% [MLN518, CT53518] [387867-13-2], C ₃₁ H ₄₂ N ₆ O ₄ , F.W. 562.71, Powder, m.p. 177-178° | 25mg 50mg 100mg |
| Application(s): Tyrosine kinase receptor inhibitor with antineoplastic activity | | |
| A17022 | Tannic acid ▲ △ [1401-55-4], C ₇₆ H ₅₂ O ₄₆ , F.W. 1701.23, m.p. ca 218° dec., Merck 14,9052, EINECS 215-753-2, RTECS WW5075000, BRN 8186396, MDL MFCD00066397, † H:H303, P:P312 | 250g 1kg |
| Application(s): Used for enzyme immobilization and protein adsorption | | |
| J64330 | TAPI-2 ▲ ■ [TNF-β Protease Inhibitor-2] [187034-31-7], C ₁₉ H ₂₇ N ₅ O ₅ , F.W. 415.53, Solid | 1mg |
| A17754 | TAPS, 99% [3-[Tris(hydroxymethyl)methyl]amino-1-propanesulfonic acid] [29915-38-6], (HOCH ₂) ₃ CNH(CH ₂) ₃ SO ₃ H, F.W. 243.28, m.p. 239-241° dec., EINECS 249-954-1, MDL MFCD00007538, † | 25g 100g |
| Application(s): A zwitterionic Good's Buffer | | |
| J60322 | TAPS, 0.2M buffer soln., pH 8.0 [91000-53-2], Liquid | 100ml 250ml |
| J63268 | TAPS, 0.2M buffer soln., pH 8.5 [91000-53-2], Liquid | 100ml 250ml |
| J61189 | TAPS sodium salt, 98% [91000-53-2], (HOCH ₂) ₃ CNH(CH ₂) ₃ SO ₃ Na, F.W. 265.26, Powder, MDL MFCD00069903 | 25g 100g |
| Application(s): Zwitterionic buffer | | |
| J64594 | Taq DNA Polymerase [EC 2.7.7.7] [9012-90-2], Liquid, EINECS 232-741-2, † | 400units |
| Application(s): Catalyzes polymeration of deoxyribonucleotides into DNA strands. Suitable for PCR and automated sequencing reactions | | |
| J64587 | Taq DNA Polymerase Standard 10X Reaction Buffer Liquid | 6ml |
| Application(s): For use with Taq DNA Polymerase product no. J64594 | | |
| Targretin , see Bexarotene, 99+%, J63701, p. 124 | | |
| A10683 | DL-Tartaric acid, 99% [133-37-9], C ₄ H ₆ O ₆ , F.W. 150.09, m.p. 210-212° dec., Merck 14,9069, EINECS 205-105-7, BRN 1725148, MDL MFCD00071626, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a |  250g 500g 1kg |
| A11264 | D-(-)-Tartaric acid, 99% [147-71-7], C ₄ H ₆ O ₆ , F.W. 150.09, m.p. 166-170°, f.p. 210° (410°F), [α] _D ²⁰ -13° (c=10 in water), Merck 14,9068, Fieser 16,312 17,321, EINECS 205-695-6, BRN 1725145, MDL MFCD00004238, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a |  25g 100g 500g |
| Application(s): Useful as a resolving agent | | |
| 36405 | L-(+)-Tartaric acid, ACS [2,3-Dihydroxybutanedioic acid] [87-69-4], C ₄ H ₆ O ₆ , F.W. 150.09, Granular, m.p. 168-170°, d. 1.760, Merck 14,9070, Solubility: Soluble in water, methanol, ethanol, glycerol, EINECS 201-766-0, RTECS WW7875000, BRN 1725147, MDL MFCD00064207, † Maximum level of impurities: Insoluble matter 0.005%, Residue after ignition 0.02%, Cl 0.001%, C ₂ O ₃ P. T. (limit about 0.1%), PO ₄ 0.001%, Sulfur compounds (as S) 0.002%, Heavy Metals (as Pb) 5ppm, Fe 5ppm ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a |  100g 500g 2kg |
| Application(s): Useful as a resolving agent | | |
| L-(+)-Tartaric acid diammonium salt , see Ammonium L-(+)-tartrate, 17658, p. 102 | | |
| A17682 | Tartrazine [Acid Yellow 23, C.I. 19140] [1934-21-0], C ₁₆ H ₁₀ N ₄ Na ₂ O ₆ S ₂ , F.W. 534.37, Merck 14,9072, EINECS 217-699-5, MDL MFCD00148908, † ! H:H334-H317, P:P285-P261-P280-P302+P352-P321-P501a |  25g 100g 500g |

| Stock # | Description | Size |
|---------|--|---------------------|
| A12403 | Taurine, 99% | 100g |
| | [2-Aminoethanesulfonic acid] [107-35-7], H ₂ NCH ₂ CH ₂ SO ₃ H, F.W. 125.15, m.p. >300°, Merck 14,9074, EINECS 203-483-8, RTECS WX0175000, BRN 1751215, MDL MFCD00008197, † | 500g |
| | ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a For a monograph, see: <i>Taurine</i> , R. Huxtable, A. Barbeau, Eds., Raven Press, N.Y., (1975). | 2.5kg |
| J62308 | Taurine, Cell Culture Grade [107-35-7], NH ₂ CH ₂ CH ₂ SO ₃ H, F.W. 125.15, Powder, m.p. >300° dec., Merck 14,9074, EINECS 203-483-8, RTECS WX0175000, BRN 1751215, MDL MFCD00008197, † | 100g 500g 1kg |
| | Taurocholic acid sodium salt , see Sodium taurocholate hydrate, A18346, p. 349 | |
| J62568 | TB Solution-I Liquid, Note: 250mM potassium chloride, 15mM calcium chloride, 10mM PIPES, 55mM manganese chloride, pH 6.5. | 125ml 250ml |
| | Application(s): For transformation of competent cells. | |
| J60028 | TB Solution-II Liquid, Note: 250mM potassium chloride, 15mM calcium chloride, 10mM HEPES, 55mM manganese chloride, pH 6.5. | 125ml 250ml |
| | Application(s): For transformation of competent cells. | |
| J63410 | TB Solution-III Liquid, Note: 30mM potassium acetate, 150mM calcium chloride, 50mM manganese chloride, 10 mM rubidium chloride, 15% glycerol. | 125ml 250ml |
| | Application(s): For transformation of competent cells. | |
| J63318 | TB Solution-IV Liquid, Note: Contains 10mM MOPS, 10mM rubidium chloride and 15% glycerol | 125ml 250ml |
| | Application(s): For transformation of competent cells | |
| | TBAC , see Tetra-n-butylammonium chloride (up to ca 15% bromide), A15186, p. 361 | |
| J63487 | TBE (5X), TRIS + borate + EDTA Liquid, Note: 0.45M Tris base, 0.45M boric acid, 10mM EDTA. | 2L 4L |
| | ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J62449 | TBE (10X), TRIS + borate + EDTA Liquid, Note: 0.9M Tris base, 0.9M boric acid, 20mM EDTA | 1L 2L 4L |
| | ! ↓ H: H315-H319-H360-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J60357 | TBE sample buffer (6X) Liquid, Note: 270mM Tris base, 270mM boric acid, 6mM EDTA, 36% glycerol, 0.03% bromophenol blue, 0.03% xylene cyanol. | 25ml 50ml |
| | ! ↓ H: H315-H319-H360-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J62788 | TBE running buffer (10X) Liquid, Note: 0.89M Tris base, 0.89 boric acid, 20mM EDTA, pH 8.3. | 1L 2L 4L |
| | ! ↓ H: H315-H319-H360-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J60186 | TBE urea sample buffer (2X) Liquid, Note: Contains 90mM Tris base, 90mM boric acid, 2mM EDTA, 12% Ficoll, 7M urea, 0.03% bromophenol blue, 0.03% xylene cyanol. | 10ml 25ml |
| | ! ↓ H: H315-H319-H360-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | TBTU , see O-(1H-Benzotriazol-1-yl)-N,N,N',N'-tetramethyluronium tetrafluoroborate, L13470, p. 120 | |
| | TCA , see Trichloroacetic acid, 10% w/v aq. soln., J62355, p. 374 | |
| | TCA , see Trichloroacetic acid, 5% w/v aq. soln., J62366, p. 374 | |
| | TCT , see Cyanuric chloride, L03442, p. 170 | |
| J60738 | TE buffer, (20X), pH 7.4, autoclaved Liquid, Note: 200mM Tris-HCl, 20mM EDTA. | 250ml 500ml |
| J61110 | TE buffer, (20X), pH 7.6, autoclaved Liquid | 250ml 500ml |
| J62388 | TE buffer, (20X), pH 8.0, autoclaved Liquid | 250ml 500ml |
| J60234 | TE buffer, pH 7.4, RNase free Liquid, Note: 200mM Tris-HCl with 20mM EDTA | 125ml 250ml |
| J62285 | TE buffer, pH 7.6, RNase free Liquid, Note: 200mM Tris-HCl with 20mM EDTA . | 125ml 250ml |



| Stock # | Description | Size |
|---------|--|-----------------------|
| J62745 | TE buffer, pH 8.1, RNase free Liquid, Note: 200mM Tris-HCl with 20mM EDTA | 125ml 250ml |
| J61546 | TEA, 0.2M buffer soln., pH 7.0 [102-71-6], Liquid, † | 250ml 500ml |
| J61319 | TEA, 0.2M buffer soln., pH 7.5 [102-71-6], Liquid, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250ml 500ml |
| J63793 | TEA, 0.2M buffer soln., pH 8.0 [102-71-6], Liquid, † H:EUH210 | 250ml 500ml |
| J61668 | TEA, 0.2M buffer soln., pH 8.5 [102-71-6], Liquid, † | 250ml 500ml |
| | TEAC , see Tetraethylammonium chloride, J62507, p. 362 TEA chloride , see Tetraethylammonium chloride, J62507, p. 362 | |
| J61441 | Telmisartan, 99% [BIBR 277, 4'-[(1,4'-Dimethyl-2'-n-propyl[2,6'-bi-1H-benzimidazol]-1'-yl)methyl]biphenyl-2-carboxylic acid] [144701-48-4], C ₃₃ H ₃₀ N ₄ O ₃ , F.W. 514.62, Powder, m.p. 261-263°, Merck 14,9129, RTECS DV2037500, MDL MFCD00918125 Application(s): An angiotensin II receptor antagonist | 250mg 1g |
| | TEMED , see N,N,N',N'-Tetramethylethylenediamine, Electrophoresis Grade, J63734, p. 365 | |
| J63654 | Temsirolimus, 99+% [162635-04-3], C ₅₆ H ₈₇ NO ₁₆ , F.W. 1030.29, Powder, Merck 14,9142 ! ☠ H:H302-H373, P:P260-P264-P270-P301+P312-P314-P501 | 25mg 50mg 100mg |
| | Application(s): A Rapamycin derivative with anti-cancer activity that inhibits mTOR | |
| J62055 | Terazosin hydrochloride, 99+% [63074-08-8], C ₁₉ H ₂₅ N ₃ O ₄ ·HCl, F.W. 423.90, Powder, RTECS TK8044925, MDL MFCD00467965 Application(s): α-1 adrenoceptor antagonist | 50mg |
| J61936 | Terfenadine [50679-08-8], C ₂₂ H ₄₁ NO ₂ , F.W. 471.67, Powder, m.p. 145-152°, Merck 14,9163, EINECS 256-710-8, RTECS TM4969000, MDL MFCD00079622 Application(s): An antihistamine | 100mg |
| | Terfenidine carboxylate hydrochloride , see Fexofenadine hydrochloride, J63262, p. 220 | |
| J62871 | α-Terpinene [α-Terpinene, 1-Isopropyl-4-methyl-1,3-cyclohexadiene] [99-86-5], C ₁₀ H ₁₆ , F.W. 136.23, Liquid, b.p. 173-175°, f.p. 50°(122°F), d. 0.837, n _D ²⁰ 1.4780, Merck 14,9170, UN2319, EINECS 202-795-1, RTECS OS8060000, BRN 1853379, MDL MFCD00001534, † ☠ ! ☠ H:H226-H302-H315-H319-H335-H411, P:P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a | 100ml 500ml |
| 16285 | α-Terpineol, 96% [α,α,4-Trimethyl-3-cyclohexene-1-methanol, p-Menth-1-en-8-ol] [98-55-5], C ₁₀ H ₁₈ O, F.W. 154.24, Liquid, m.p. 31-32°, b.p. 210-219°, f.p. 90°(194°F), d. 0.930, n _D ²⁰ 1.4830, Merck 14,9171, EINECS 202-680-6, RTECS WZ6700000, MDL MFCD00001557, † ! H:H315, P:P280-P264-P302+P352-P321-P362-P332+P313 Application(s): A naturally-occurring monoterpene alcohol | 25g 100g 500g |
| |  | |
| H26824 | Terrific Broth <input checked="" type="checkbox"/> <input checked="" type="checkbox"/> MDL MFCD00243264 | 100g 500g |
| J63379 | TES, 0.2M buffer soln., pH 7.0 [70331-82-7], Liquid, † | 100ml 250ml |
| J61350 | TES, 0.2M buffer soln., pH 7.5 [70331-82-7], Liquid, † | 100ml 250ml |
| J61889 | TES, 0.2M buffer soln., pH 8.0 [70331-82-7], Liquid, † | 100ml 250ml |
| B21819 | TES, 99% [2-((Tris(hydroxymethyl)methyl)amino)ethane-1-sulfonic acid] [7365-44-8], (HOCH ₂) ₃ CNHCH ₂ CH ₂ SO ₃ H, F.W. 229.25, m.p. ca 225° dec., Merck 14,9176, EINECS 230-906-3, BRN 1957061, MDL MFCD00007532, † Biological buffer useful in pH range 7.0 - 8.0: <i>Biochemistry</i> , 5, 467 (1966). Application(s): A zwitterionic Good's Buffer | 10g 50g 250g |

| Stock # | Description | Size |
|---------|---|-----------------------|
| J62706 | TES sodium salt [2-((Tris(hydroxymethyl)methyl)amino)ethane-1-sulfonic acid sodium salt] [70331-82-7], C ₆ H ₁₁ NNaO ₆ S, F.W. 251.23, Powder, Merck 14,9176, BRN 1957061, MDL MFCD00065482, † | 25g 250g 1kg |
| | Application(s): A zwitterionic Good's Buffer | |
| | 2',4',5',7'-Tetrabromofluorescein disodium salt, see Eosin Yellowish, B24535, p. 208 | |
| B20123 | Tetrabromophenol Blue [3,4,5,6,3',5',3'',5''-Octabromophenolsulfonphthalein] [4430-25-5], C ₂₀ H ₂ Br ₈ O ₅ S, F.W. 985.55, m.p. 203-205° dec., EINECS 224-622-9, BRN 378438, MDL MFCD00005876, † Acid-base indicator: pH 3.0 - 4.6. | 1g 5g 25g |
| | Application(s): Phase transfer catalyst | |
| |  | |
| A10249 | Tetra-n-butylammonium bromide, 98+% ■ [TBAB, Aliquat® 100] [1643-19-2], [CH ₃ (CH ₂) ₃] ₄ NBr, F.W. 322.38, m.p. 101-105°, d. 1.15, Fieser 4,477 5,644 7,353 18,286 20,356 21,407, EINECS 216-699-2, BRN 3570983, MDL MFCD00011633, † | 100g 500g 2.5kg |
| | ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Phase-transfer catalyst of wide application. Some illustrative examples are given below. K salts of α-bromocarboxylic acids can be cyclized to lactones under effectively "high-dilution" conditions by extracting into toluene in the presence of a small amount of catalyst. The 16-membered ring lactone was formed in 92% yield: <i>J. Org. Chem.</i> , 48 , 1533 (1983). Primary alkyl chlorides can be converted to alcohols in excellent yield by phase-transfer reaction with sodium formate and hydrolysis of the resulting formate esters: <i>Synthesis</i> , 763 (1986). β-Lactones are formed by the cyclization of β-bromoacids under phase-transfer conditions: <i>Chem. Pharm. Bull.</i> , 29 , 1063 (1981). An improved procedure for the Curtius rearrangement involves reaction of acid chlorides with azide ion under phase-transfer conditions: <i>Synthesis</i> , 38 (1983). Aromatic carboxamides undergo N-alkylation with alkyl halides using KOH under solvent-free conditions: <i>Synth. Commun.</i> , 22 , 1661 (1992). Has been used as an "ionic liquid" in the regioselective O-alkylation of ambident nucleophiles: <i>Tetrahedron Lett.</i> , 33 , 4435 (1992). A method is described whereby the "solvent" can be recovered quantitatively. A semi-molten mixture with KF or CsF has been found to be an effective system for fluorodehalogenation of, e.g., benzyl bromide: <i>J. Fluorine Chem.</i> , 73 , 185 (1995). Effective catalyst for amination reactions of alkyl or activated aryl halides, by increasing the solubility of ammonia in organic media: <i>J. Chem. Soc., Chem. Commun.</i> , 267 (1987). Application(s): Phase transfer catalyst | |
| A15186 | Tetra-n-butylammonium chloride (up to ca 15% bromide), 95% ex total halide ■ [TBAC] [1112-67-0], [CH ₃ (CH ₂) ₃] ₄ NCl, F.W. 277.92, m.p. ca 70°, Fieser 20,356, EINECS 214-195-7, BRN 3571227, MDL MFCD00011635, † | 5g 25g 100g |
| | ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Phase-transfer catalyst used in the N-alkylation of ureas: <i>Monatsh.</i> , 123 , 599 (1994). For improved phase-transfer alkylation of ethyl acetate and diethyl malonate using toluene-water, see: <i>Org. Prep. Proced. Int.</i> , 26 , 469 (1994). Application(s): Phase transfer catalyst | |
| A14047 | Tetra-n-butylammonium hydrogen sulfate, 97% ■ [32503-27-8], [CH ₃ (CH ₂) ₃] ₄ NHSO ₄ , F.W. 339.54, m.p. 168-172°, Fieser 6,565 7,354 18,286, EINECS 251-068-5, MDL MFCD00011637, † | 50g 250g 1kg |
| | ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Widely used phase-transfer catalyst. Some illustrative applications are given below: Benzanilides have been N-alkylated in the presence of NaOH and K ₂ CO ₃ : <i>Synth. Commun.</i> , 18 , 2011 (1988). It was the most effective catalyst studied for the cyclization of β-amino acids to β-lactams by methanesulfonyl chloride and KHCO ₃ : <i>Chem. Lett.</i> , 443 (1981). In the dehydrohalogenation of aryl 2-haloethyl ethers to give vinyl ethers, this catalyst was found much more effective than the corresponding halides or benzyltriethylammonium salts: <i>Synthesis</i> , 688 (1979). For use in the permanganate oxidation of benzylic positions, see Potassium permanganate, A12170 . The oxidation of primary alcohols to aldehydes by potassium chromate under phase-transfer conditions is better for higher homologues, where solubility in the aqueous phase is limited: <i>Synthesis</i> , 134 (1979). For phase-transfer catalyzed dichromate oxidation of secondary alcohols to ketones, see: <i>Tetrahedron Lett.</i> , 1601 (1978). For phase-transfer catalyzed conversion of nitriles to amides by alkaline H ₂ O ₂ , see: <i>Synthesis</i> , 243 (1980). Application(s): Phase transfer catalyst | |
| J63272 | Tetracaine hydrochloride [2-(Dimethylamino)ethyl 4-(n-butylamino)benzoate hydrochloride] [136-47-0], C ₁₅ H ₂₄ N ₂ O ₂ ·HCl, F.W. 300.82, Powder, Merck 14,9188, UN2811, EINECS 205-248-5, RTECS DG4900000, MDL MFCD00038912 | 25g 100g |
| |  H:H301-H334-H319-H317, P:P285-P301+P310-P305+P351+P338-P302+P352-P405-P501a Application(s): A potent topical local anesthetic | |
| J61714 | Tetracycline [60-54-8], C ₂₂ H ₃₂ N ₂ O ₆ , F.W. 444.43, Crystalline powder, m.p. 172-174°, Merck 14,9196, EINECS 200-481-9, RTECS Q18750000, BRN 2230417, MDL MFCD00151232 | 5g 25g 100g |
| | ! H:H302, P:P264-P270-P301+P312-P330-P501a Application(s): Can induce apoptosis in osteoclasts | |


| Stock # | Description | Size |
|---------------|---|----------------------------|
| B21408 | Tetracycline hydrochloride, 98% ▲ △ [64-75-5], C ₂₂ H ₂₄ N ₂ O ₈ ·HCl, F.W. 480.91, m.p. 220-223°, Merck 14,9196, EINECS 200-593-8, MDL MFCD00078142, † H: H361, P: P281-P201-P202-P308+P313-P405-P501a | 25g 100g |
| | Application(s): Can induce apoptosis in osteoclasts | |
| A12067 | Tetradecanoic acid, 98% [Myristic acid] [544-63-8], CH ₃ (CH ₂) ₁₂ CO ₂ H, F.W. 228.38, m.p. 53-56°, b.p. 326°, f.p. 175°(347°F), d. 0.862, Merck 14,6333, EINECS 208-875-2, RTECS QH4375000, BRN 508624, MDL MFCD00002744, † H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 250g 500g 2.5kg |
| | n-Tetradecylbenzyltrimethylammonium chloride hydrate, see Benzyltrimethyl-n-tetradecylammonium chloride hydrate, 98%, J63465, p. 122 | |
| L10294 | (1-Tetradecyl)trimethylammonium bromide, 98% [Myristyltrimethylammonium bromide, Trimethyl-n-tetradecylammonium bromide] [1119-97-7], CH ₃ (CH ₂) ₁₃ N(CH ₃) ₃ Br, F.W. 336.40, m.p. 245-250°, Merck 14,6336, UN1759, EINECS 214-291-9, RTECS BS5776000, BRN 3633227, MDL MFCD00011770, † H: H314-H411, P: P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 25g 100g 500g |
| | Application(s): Phase transfer catalyst | |
| A13835 | Tetraethylammonium bromide, 98% ■ [71-91-0], (CH ₃ CH ₂) ₄ NBr, F.W. 210.16, m.p. ca 285° dec., d. 1.397, Merck 14,9199, Fieser 6,568 10,305, EINECS 200-769-4, RTECS BS5950000, BRN 3563430, MDL MFCD00011825, † H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a Phase-transfer catalyst. For use in combination with anhydrous HBr as a reagent for selective monohydrobromination of an alkyne, see: <i>Org. Synth.</i> , 76, 263 (1998). | 250g 1kg 5kg |
| | Application(s): Phase transfer catalyst | |
| J62507 | Tetraethylammonium chloride ■ [TEA chloride, TEAC] [56-34-8], (CH ₃ CH ₂) ₄ NCl, F.W. 165.71, Powder, Merck 14,9200, EINECS 200-267-5, RTECS BS6125000, BRN 3563247, MDL MFCD00011828, † H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 25g 100g |
| | Application(s): Phase transfer catalyst | |
| 30818 | Tetraethylammonium chloride monohydrate, 98+% [68696-18-4], (C ₂ H ₅) ₄ NCl·H ₂ O, F.W. 183.72 (165.71anhy), Crystalline, m.p. ca 110°, d. 1.0801, Merck 14,9200, Fieser 1,1137, EINECS 200-267-5, RTECS BS6125000, BRN 3563247, MDL MFCD00149992, † H: H302-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 50g 250g |
| | Application(s): Phase transfer catalyst | |
| B23880 | Tetraethylene glycol, 99% [Tetraglycol] [112-60-7], O(CH ₂ CH ₂ OCH ₂ CH ₂ OH) ₂ , F.W. 194.23, m.p. -4°, b.p. 313-314°, f.p. 193°(379°F), d. 1.125, n _D ²⁰ 1.4590, EINECS 203-989-9, RTECS XC2100000, BRN 1634320, MDL MFCD00002879, † | 500ml 2.5L |
| | Application(s): Used as a solvent to dissolve water-insoluble compounds | |
| J62496 | Tetraethylene glycol monoethyl ether [n-Octyltetraoxyethylene] [19327-39-0], CH ₃ (CH ₂) ₇ (OCH ₂ CH ₂) ₄ OH, F.W. 306.44, Solid, BRN 1781226, MDL MFCD00043033, † H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 1g 5g |
| | Application(s): Reagent for solubilizing membrane proteins | |
| | Tetraethylrhodamine , see Rhodamine B, A13572, p. 337 | |
| B20721 | Tetraethylthiuram disulfide, 97% [Disulfiram] [97-77-8], C ₁₀ H ₂₀ N ₂ S ₄ , F.W. 296.54, m.p. 69-72°, b.p. 117°/17mm, d. 1.300, Merck 14,3364, Fieser 6,569, UN3077, EINECS 202-607-8, RTECS JO1225000, BRN 1712560, MDL MFCD00009048, † H: H373-H400-H410-H302-H317, P: P260-P261-P280-P302+P352-P321-P501a | 100g 250g 1kg 5kg |
| | Application(s): Dopamine β-hydroxylase inhibitor | |
| | Tetraglycol , see Tetraethylene glycol, B23880, p. 362 | |
| J63941 | 6,7,8,9-Tetrahydro-5H-benzocycloheptene-5-ol-4-ylidene acetic acid [NCS 382 sodium salt] [131733-92-1], C ₁₃ H ₁₃ NaO ₃ , F.W. 240.23, Powder, m.p. 141-143°, RTECS MA0600800, MDL MFCD11046018 | 100mg |
| | Application(s): γ-Hydroxybutyrate (GHB) receptor antagonist | |
| | 1,2,3,6-Tetrahydro-2,6-dioxypyrimidine-4-carboxylic acid , see Orotic acid, B25349, p. 309 | |
| | 1,2,3,6-Tetrahydro-2,6-dioxypyrimidine-4-carboxylic acid hydrate , see Orotic acid hydrate, A18594, p. 309 | |












| Stock # | Description | Size | | | | | | | | | | |
|---------|--|---------------------------|------|------|-----|-----|---|------|------|------|------|--|
| 44505 | Tetrahydrofuran, Biograde, 99.8%, unstab. [109-99-9], C ₄ H ₈ O, F.W. 72.11, Liquid, m.p. -108°, b.p. 66°, f.p. -17°(1°F), d. 0.889, n _D ²⁰ 1.4070, Merck 14,9211, Fieser 1,1140 2,398 3,278 5,649 6,570, UN2056, EINECS 203-726-8, RTECS LU5950000, BRN 102391, MDL MFCD00005356, Note: Water <100ppm, † Maximum level of impurities: Color (APHA) 10, Peroxide (as H ₂ O ₂) 0.015%, Residue after evaporation 5 ppm H ₂ O 0.01% ! H:H225-EUH019-H319-H335, P:P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a | 1L 4L 4x1L | | | | | | | | | | |
| | UV absorption - 1cm cell vs H₂O | | | | | | | | | | | |
| | <table border="1"> <thead> <tr> <th>λ(nm)</th> <th>300</th> <th>250</th> <th>225</th> <th>212</th> </tr> </thead> <tbody> <tr> <td>A</td> <td>0.01</td> <td>0.17</td> <td>0.50</td> <td>1.00</td> </tr> </tbody> </table> | λ(nm) | 300 | 250 | 225 | 212 | A | 0.01 | 0.17 | 0.50 | 1.00 | |
| λ(nm) | 300 | 250 | 225 | 212 | | | | | | | | |
| A | 0.01 | 0.17 | 0.50 | 1.00 | | | | | | | | |
| | Application(s): Nucleic acid and peptide synthesis | | | | | | | | | | | |
| 32468 | Tetrahydrofuran, Spectrophotometric Grade, 99.7+%, unstab. [109-99-9], C ₄ H ₈ O, F.W. 72.11, Liquid, distilled in glass, m.p. -108°, b.p. 66°, f.p. -17°(1°F), d. 0.889, n _D ²⁰ 1.4070, Merck 14,9211, Fieser 1,1140 2,398 3,278 5,649 6,570, UN2056, EINECS 203-726-8, RTECS LU5950000, BRN 102391, MDL MFCD00005356, Note: Filtered through 0.2μ filters. Suitable for spectrophotometry, † Maximum level of impurities: Evaporation residue 5ppm, H ₂ O 0.03%, Acidity (CH ₃ COOH) 0.005%, Peroxides (as H ₂ O ₂) 0.03% ! H:H225-EUH019-H319-H335, P:P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a | 100ml 1L 4L 4x1L | | | | | | | | | | |
| | UV absorption - 1cm cell vs H₂O | | | | | | | | | | | |
| | <table border="1"> <thead> <tr> <th>λ(nm)</th> <th>300</th> <th>250</th> <th>225</th> <th>212</th> </tr> </thead> <tbody> <tr> <td>A</td> <td>0.01</td> <td>0.18</td> <td>0.50</td> <td>1.00</td> </tr> </tbody> </table> | λ(nm) | 300 | 250 | 225 | 212 | A | 0.01 | 0.18 | 0.50 | 1.00 | |
| λ(nm) | 300 | 250 | 225 | 212 | | | | | | | | |
| A | 0.01 | 0.18 | 0.50 | 1.00 | | | | | | | | |
| J62007 | (R)-Tetrahydrofuran-2-carboxamide [539820-25-2], C ₅ H ₉ NO ₂ , F.W. 115.13, Solid | Call | | | | | | | | | | |
| | Application(s): For synthesis of optically active products | | | | | | | | | | | |
| J60420 | (S)-Tetrahydrofuran-2-carboxamide [498573-81-2], C ₅ H ₉ NO ₂ , F.W. 115.13, Solid, MDL MFCD04039924 | Call | | | | | | | | | | |
| | Application(s): For synthesis of optically active products | | | | | | | | | | | |
| L19044 | (R)-(-)-Tetrahydrofurfuryl alcohol, 98+% [(R)-(-)-2-(Hydroxymethyl)tetrahydrofuran] [22415-59-4], C ₅ H ₁₀ O ₂ , F.W. 102.13, b.p. 173-175°, f.p. 75°(167°F), d. 1.053, n _D ²⁰ 1.4520, [α] _D ²⁰ -2.3° (neat), BRN 79846, MDL MFCD03093085 ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 250mg 1g | | | | | | | | | | |
| | Application(s): For synthesis of optically active products | | | | | | | | | | | |
| J62573 | (S)-(+)-Tetrahydrofurfuryl alcohol [(S)-(+)-2-(Hydroxymethyl)tetrahydrofuran] [72074-94-3], C ₅ H ₁₀ O ₂ , F.W. 102.13, Liquid ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | Call | | | | | | | | | | |
| | Application(s): For synthesis of optically active products | | | | | | | | | | | |
| | (-)-Tetrahydrolipstatin, see Orlistat, 98%, J62999, p. 308 | | | | | | | | | | | |
| J63911 | L-Tetrahydropalmatine [Gindarine, Rotundine] [10097-84-4], C ₂₁ H ₂₅ NO ₄ , F.W. 355.43, Powder, m.p. 147°, Merck 14,9215 | 1g 25g | | | | | | | | | | |
| | Application(s): Voltage dependent L-type calcium channel inhibitor | | | | | | | | | | | |
| J63328 | Tetrahydropalmatine, 98% [THP] [2934-97-6], C ₂₁ H ₂₅ NO ₄ , F.W. 355.43, Powder, m.p. 155°, MDL MFCD00214191 ! H:H302, P:P264-P270-P301+P312-P330-P501 | 1g 5g | | | | | | | | | | |
| | 1,2,3,6-Tetrahydro-4-pyridinecarboxylic acid hydrochloride, see Isoguvacine hydrochloride, 99%, J63243, p. 260 Tetrahydrothiazole, see Thiazolidine, H26427, p. 366 1,3,4,5-Tetrahydroxycyclohexanecarboxylic acid 3-(3,4-dihydroxycinnamate), see Chlorogenic acid, J60457, p. 157 | | | | | | | | | | | |
| L14186 | 3',4',5,7-Tetrahydroxyflavone, 97% [Luteolin] [491-70-3], C ₁₅ H ₁₀ O ₆ , F.W. 286.24, m.p. >300°, Merck 14,5614, EINECS 207-741-0, RTECS LK9275210, BRN 292084, MDL MFCD00017309 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Anti-oxidant and radical scavenger in biological systems: <i>Methods Enzymol.</i> , 234, 420 (1994). | 100mg 500mg | | | | | | | | | | |
| | Application(s): An apoptosis inducer | | | | | | | | | | | |
| | 3,4',5,7-Tetrahydroxyflavone, see Kaempferol, 98+%, J60373, p. 262 (1S,6S,7R,8R,8aR)-1,6,7,8-Tetrahydroxyoctahydroindolizidine, see Castanospermine, 99%, J61071, p. 150 | | | | | | | | | | | |










| Stock # | Description | Size |
|--|---|------------------------|
| J64414 | 2-(4,5,6,7-Tetraiodo-1,3-dioxoisindolin-2-yl)acetic acid [CAY10578] [19231-60-8], C ₁₀ H ₅ I ₄ NO ₄ , F.W. 708.75, Powder | 10mg |
| | Tetraiodofluorescein sodium salt , see Erythrosin B, A14180, p. 210 3,3',5,5'-Tetraiodo-L-thyronine , see L-Thyroxine, 98%, J62606, p. 370 | |
| J64206 | N,N,N',N'-Tetrakis-(2-pyridylmethyl)ethylenediamine [TPEN, TPEDA] [16858-02-9], C ₂₈ H ₂₈ N ₆ , F.W. 424.54, Powder, m.p. 110-112°, BRN 4211982, MDL MFCD00036918 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 100mg 300mg |
| A13288 | Tetramethylammonium chloride, 97%, may cont. ca 3% silica as anticaking agent ■ [75-57-0], (CH ₃) ₄ NCl, F.W. 109.60, m.p. >300°, d. 1.17, UN2811, EINECS 200-880-8, RTECS BS7700000, BRN 2496575, MDL MFCD00011628, † H:H301-H311-H315-H319-H335, P:P280h-P305+P351+P338-P309-P310 Thermally-stable phase-transfer catalyst which has been used in nucleophilic displacement reactions of aryl nitro groups with KF in tetramethylene sulfone: <i>J. Org. Chem.</i> , 56 , 6406 (1991). A detailed study of the halix Cl /F ⁻ exchange reaction of activated aryl chlorides, for example the conversion of 1,2-dichloro-4-nitrobenzene to 2-chloro-1-fluoro-4-nitrobenzene in DMSO at 120°C showed tetramethylammonium chloride to be superior to other common phase-transfer catalysts. It was necessary to pre-dry the catalyst to <0.2% water to avoid competition from hydrolytic displacement: <i>Chem. Commun.</i> , 297 (1996). Compare also Tetraphenylphosphonium bromide , A15860, and Tetraphenylphosphonium chloride , A10575. | 250g 1kg 5kg |
| Application(s): Phase transfer catalyst | | |
| J61325 | 3,3',5,5'-Tetramethylbenzidine soln., Ready-to-Use, high sensitivity [TMB soluble reagent, high sensitivity] [54827-17-7], C ₁₆ H ₂₀ N ₂ , F.W. 240.35, Liquid, EINECS 259-364-6, BRN 2808541, MDL MFCD00007748, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 125ml 500ml 1L |
| Application(s): Excellent colorimetric substrate for detection of horseradish peroxidase labelled probes and is used with peroxidase and peroxidase coupled systems, particularly in ELISA techniques, blue result | | |
| J60461 | 3,3',5,5'-Tetramethylbenzidine soln., Ready-to-Use, precipitating, standard sensitivity [TMB reagent, standard sensitivity] [54827-17-7], C ₁₆ H ₂₀ N ₂ , F.W. 240.35, Liquid, EINECS 259-364-6, BRN 2808541, MDL MFCD00007748, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 125ml 500ml 1L |
| Application(s): Excellent colorimetric substrate for detection of horseradish peroxidase labelled probes and is used with peroxidase and peroxidase coupled systems, particularly in ELISA techniques, blue result | | |
| J60808 | 3,3',5,5'-Tetramethylbenzidine aq. soln. [TMB soluble reagent, aq. soln.] [54827-17-7], C ₁₆ H ₂₀ N ₂ , F.W. 240.35, Liquid, EINECS 259-364-6, BRN 2808541, MDL MFCD00007748, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 125ml 500ml 1L |
| Application(s): Excellent colorimetric substrate for detection of horseradish peroxidase labelled probes and is used with peroxidase and peroxidase coupled systems, particularly in ELISA techniques, blue result | | |
| A13868 | 3,3',5,5'-Tetramethylbenzidine, 98% ▲ [4,4'-Diamino-3,3',5,5'-tetramethylbiphenyl] [54827-17-7], C ₁₆ H ₂₀ N ₂ , F.W. 240.35, m.p. 168-171°, EINECS 259-364-6, RTECS DV2300000, BRN 2808541, MDL MFCD00007748, † ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 1g 5g 25g |
| Application(s): Excellent colorimetric substrate for detection of horseradish peroxidase labelled probes; particularly useful in ELISA techniques, blue result can be read spectrophotometrically at 370 or 650 nm | | |
| J60332 | 3,3',5,5'-Tetramethylbenzidine dihydrochloride hydrate, 99+% ▲ ▽ [TMB dihydrochloride hydrate] [207738-08-7], C ₁₆ H ₂₀ N ₂ ·2HCl·xH ₂ O, F.W. 313.27(anhy), Powder, MDL MFCD00150104 ! H:H341-H302-H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P405-P501a | 1g 2.5g 5g |
| Application(s): Excellent colorimetric substrate for detection of horseradish peroxidase labelled probes and is used with peroxidase and peroxidase coupled systems, particularly in ELISA techniques, blue result | | |
| A12536 | N,N,N',N'-Tetramethylethylenediamine, 99% ▲ ▽ ■ [1,2-Bis(dimethylamino)ethane, TMEDA] [110-18-9], (CH ₃) ₂ NCH ₂ CH ₂ N(CH ₃) ₂ , F.W. 116.21, m.p. -55°, b.p. 120-122°, f.p. 18°(62°F), d. 0.775, n _D ²⁰ 1.4180, Fieser 2,403 3,284 4,485 5,652 6,576 7,358 12,477 13,57, UN2372, EINECS 203-744-6, RTECS KV7175000, BRN 1732991, MDL MFCD00008335, † ! H:H225-H314-H302-H332, P:P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a Widely used complexing agent in lithiation reactions, often giving enhanced reactivity in otherwise difficult metallations: <i>J. Am. Chem. Soc.</i> , 92 , 4664 (1970). Subsequent work by Collum and others indicated that the situation may be much less straightforward than was previously thought, but the effect of TMEDA is likely to be most pronounced in the absence of strong donor solvents such as THF. For a discussion of the factors involved, see: <i>Acc. Chem. Res.</i> , 25 , 448 (1992). Under some conditions also, TMEDA itself may undergo lithiation: <i>Organometallics</i> , 13 , 5173 (1994). Used in combination with alkylolithiums in the <i>ortho</i> -metallation of aromatics; see, e.g.: <i>Org. Synth. Coll.</i> , 6 , 478 (1988); <i>Org. Synth. Coll.</i> , 9 , 559 (1998). For discussion of the dramatic acceleration of the rate of <i>ortho</i> -lithiation of anisole in the presence of TMEDA, effective also in sub-stoichiometric amounts, see: <i>Tetrahedron Lett.</i> , 35 , 385 (1994). See also <i>Tetrahedron Lett.</i> , 35 , 401 (1994), <i>J. Org. Chem.</i> , 62 , 3024 (1997) for further discussion of the role of TMEDA in <i>ortho</i> -metallation. | 100ml 500ml 2.5L |









| Stock # | Description | Size |
|---------|--|------------------------|
| | <p>The oxidative coupling of terminal acetylenes to diynes, by O₂ in the presence of CuCl, is improved by addition of TMEDA as a complexing agent: <i>J. Org. Chem.</i>, 27, 3320 (1962). For example and discussion, see: <i>Org. Synth. Coll.</i>, 8, 63 (1993):</p> $\text{Me}_3\text{SiC}\equiv\text{CH} \xrightarrow[\text{Me}_2\text{CO}]{\text{O}_2, \text{CuCl, TMEDA}} \text{Me}_3\text{SiC}\equiv\text{C}-\text{C}\equiv\text{CSiMe}_3 \quad 66\text{-}76\%$ <p>In catalytic amounts, produces up to a 20-fold increase in reaction rate in aqueous Michael additions catalyzed by ytterbium triflate: <i>J. Org. Chem.</i>, 71, 352 (2006).</p> | |
| J63734 | <p>N,N,N',N'-Tetramethylethylenediamine, Electrophoresis Grade ■ [TEMED] [110-18-9], (CH₃)₂NCH₂CH₂N(CH₃)₂, F.W. 116.21, Liquid, m.p. -55°, b.p. 120-122°, f.p. 18°(154°F), d. 0.775, n_D²⁰ 1.4180, Merck 14,9134, UN2372, EINECS 203-744-6, RTECS KV7175000, BRN 1732991, MDL MFCD00008335, †</p> <p>! H: H225-H314-H302-H332, P: P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a</p> | 25ml 100ml |
| J62258 | <p>5(6)-Tetramethylrhodamine isothiocyanate [TRITC, MRITC] [95197-95-8], C₂₅H₂₁N₃O₃S, F.W. 443.52, Powder</p> <p>! H: H315-H319-H334-H335, P: P285-P305+P351+P338-P302+P352-P321-P405-P501</p> <p>Application(s): Reagent for fluorescent labelling of proteins</p> | 10mg |
| J61080 | <p>Tetranitro blue tetrazolium chloride, 97% [TNBT] [1184-43-6], C₄₀H₂₈Cl₂N₁₂O₁₀·2C₂H₆O, F.W. 999.78, Powder, EINECS 214-665-1, BRN 3897475, MDL MFCD00036338, †</p> <p>H: H350, P: P281-P201-P202-P308+P313-P405-P501</p> <p>Application(s): Redox indicator for enzymes</p> | 100mg 1g |
| J61034 | <p>1H-Tetrazole, 0.45M in acetonitrile [288-94-8], CH₂N₄, F.W. 70.05, Liquid, d. 0.798, Merck 14,2786, UN1648, EINECS 206-023-4, RTECS UW7370000, BRN 105799, MDL MFCD00005247</p> <p>! H: H225-H302-H312-H332-H319, P: P210-P241-P303+P361+P353-P305+P351+P338-P302+P352-P501a</p> <p>Application(s): Coupling reagent for preparation of polynucleotides</p> <p>Tetrazolium Blue chloride, see Blue Tetrazolium chloride, A12502, p. 129 Texas Red[®], see Sulforhodamine 101 acid chloride, J60581, p. 356 THA hydrochloride, see Tacrine hydrochloride hydrate, 98+%, J60070, p. 357</p> | 200ml 450ml |
| J60271 | <p>Thalidomide [50-35-1], C₁₅H₁₀N₂O₄, F.W. 258.23, Powder, Merck 14,9255, UN2811, EINECS 200-031-1, RTECS TI4375000</p> <p>H: H301-H340-H360-H312, P: P280-P301+P310-P302+P352-P321-P405-P501a</p> <p>Application(s): Teratogenic compound found to inhibit HIV-1 replication and FGF-induced angiogenesis</p> | 100mg |
| J62266 | <p>(±)-Thalidomide, 99+% [50-35-1], C₁₅H₁₀N₂O₄, F.W. 258.23, Powder, Merck 14,9255, UN2811, EINECS 200-031-1, RTECS TI4375000, MDL MFCD00153873</p> <p>H: H301-H340-H360-H312, P: P280-P301+P310-P302+P352-P321-P405-P501a</p> <p>Application(s): Teratogenic compound found to inhibit HIV-1 replication and FGF-induced angiogenesis</p> | 100mg |
| J62866 | <p>Thapsigargin, 95% ▲ [67526-95-8], C₃₁H₅₀O₁₂, F.W. 650.75, Solid film, Merck 14,9272, RTECS RH0325700, MDL MFCD00083511</p> <p>H: H334-H335-H315-H319, P: P285-P305+P351+P338-P302+P352-P321-P405-P501a</p> <p>Application(s): Cell permeable sesquiterpene lactone tumor promoter. Inhibits endoplasmic reticulum calcium-ATPase</p> | 1mg 5mg 10mg |
| J63668 | <p>Thaumatococcus daniellii [53850-34-3], Powder, Merck 14,9273, EINECS 258-822-2</p> <p>Application(s): A mixture of the intensely sweet proteins thaumatococcosin I and thaumatococcosin II</p> | 25mg 100mg 250mg |
| A11861 | <p>Theobromine, 99% [3,7-Dimethylxanthine] [83-67-0], C₇H₈N₂O₂, F.W. 180.17, m.p. 345-350°, d. 1.50, Merck 14,9282, EINECS 201-494-2, RTECS XH2275000, BRN 16464, MDL MFCD00022830, †</p> <p>! H: H302, P: P264-P270-P301+P312-P330-P501a</p> <p>Application(s): Phosphodiesterase inhibitor</p> | 50g 100g 250g |
| A15997 | <p>Theophylline monohydrate, 99% [1,3-Dimethylxanthine monohydrate] [5967-84-0], C₇H₈N₂O₂·H₂O, F.W. 198.18 (180.16anhy), m.p. 270-274°, Merck 14,9285, UN2811, EINECS 200-385-7, RTECS XH3850000, BRN 13463, MDL MFCD00151659, †</p> <p>H: H301, P: P264-P270-P301+P310-P321-P405-P501a</p> <p>Application(s): Dimethylxanthine. A methylxanthine drug used in therapy for respiratory diseases such as COPD and asthma</p> | 50g 250g 1kg |

| Stock # | Description | Size |
|---------|--|---------------------|
| J60203 | Theophylline [1,3-Dimethylxanthine, 3,7-Dihydro-1,3-dimethyl-1H-purine-2,6-dione] [58-55-9], C ₇ H ₈ N ₄ O ₂ , F.W. 180.16, Powder, m.p. 270-274°, Merck 14,9285, UN2811, EINECS 200-385-7, RTECS XH3850000, BRN 13463, MDL MFCD00079619, † | 11b 51b |
| |  H: H301, P: P264-P270-P301+P310-P321-P405-P501a Application(s): Phosphodiesterase inhibitor; diuretic; cardiac stimulant; muscle relaxant; asthma medication. A methylxanthine drug used in therapy for respiratory diseases such as COPD and asthma | |
| | Theophylline hemi(ethylenediamine) complex , see Aminophylline, anhydrous, 98%, J60705, p. 98 Thespesin , see Gossypol, 98+%, J63767, p. 238 | |
| J60009 | Thiabendazole, 98+% [2-(4-Thiazolyl)benzimidazole] [148-79-8], C ₁₀ H ₇ N ₃ S, F.W. 201.25, Powder, m.p. 304-305°, Merck 14,9289, UN3077, EINECS 205-725-8, RTECS DE0700000, BRN 611403, MDL MFCD00005587, † | 10g 100g 500g |
| |  H: H400-H410, P: P273-P391-P501a | |
| | Thiactin , see Thiostrepton, Streptomyces laurentii, 98%, J62332, p. 368 | |
| A19560 | Thiamine hydrochloride, 99% (dry wt.), may cont. up to 5% water ▲ ■ [Vitamin B1 hydrochloride, Aneurine hydrochloride] [67-03-8], C ₁₂ H ₁₇ ClN ₄ OS HCl, F.W. 337.28, m.p. ca 250° dec., Merck 14,9295, EINECS 200-641-8, RTECS XI7350000, BRN 3851771, MDL MFCD00012780, † | 100g 250g 1kg |
| |  H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| J60014 | Thiamine nitrate [Vitamin B, nitrate] [532-43-4], C ₁₂ H ₁₇ N ₄ O ₆ S, F.W. 327.36, Powder, m.p. 190°, Merck 14,9295, EINECS 208-537-4, RTECS XI7400000, MDL MFCD00036330, † | 10g 25g |
| J61483 | Thiamine pyrophosphate chloride, 98% [Aneurinepyrophosphoric acid, Cocarboxylase] [154-87-0], C ₁₂ H ₁₆ ClN ₄ O ₇ P ₂ S, F.W. 460.77, Powder, Merck 14,9296, EINECS 205-836-1, RTECS XI7552000, BRN 3875902, MDL MFCD00038740, † | 5g 25g |
| | Application(s): Cocarboxylase, a form of Vitamin B-1 | |
| J63575 | Thiamphenicol [15318-45-3], C ₁₂ H ₁₅ Cl ₂ NO ₂ S, F.W. 356.22, Powder, Merck 14,9301, EINECS 239-355-3, RTECS AB6680000, BRN 2819542, MDL MFCD00467983 | 1g 5g 25g |
| | Application(s): The methyl-sulfonyl analogue of chloramphenicol | |
| H26427 | Thiazolidine, 97% [Tetrahydrothiazole] [504-78-9], C ₃ H ₇ NS, F.W. 89.16, b.p. 165°, f.p. 56°(133°F), d. 1.131, n _D ²⁰ 1.5545, UN1993, EINECS 208-002-5, RTECS XJ5123700, MDL MFCD00005211 | 1g 5g |
| |   H: H226-H315-H319-H335, P: P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a | |
| | L(-)-Thiazolidin-2-one-4-carboxylic acid , see L(-)-2-Oxothiazolidine-4-carboxylic acid, J62254, p. 310 2-(4-Thiazolyl)benzimidazole , see Thiabendazole, 98+%, J60009, p. 366 | |
| L11939 | Thiazolyl Blue tetrazolium bromide, 98% ▲ [3-(4,5-Dimethyl-2-thiazolyl)-2,5-diphenyl-2H-tetrazolium bromide, MTT] [298-93-1], C ₁₈ H ₁₆ BrN ₅ S, F.W. 414.33, m.p. ca 195° dec., EINECS 206-069-5, RTECS XF8060000, BRN 3825277, MDL MFCD00011964, † | 1g 5g |
| |  Application(s): Used in measurement of cell proliferation. Produces a yellowish solution that is converted to dark blue, water-insoluble MTT formazan by mitochondrial dehydrogenases of living cells | |
| | N(1)-(2-Thiazolyl)sulfanilamide , see Sulfathiazole, A10727, p. 356 | |
| J61799 | Thimerosal [2-(Ethylmercuriomercurio)benzoic acid sodium salt] [54-64-8], C ₈ H ₈ HgNaO ₂ S, F.W. 404.81, Powder, m.p. 234-237°, f.p. 250°(482°F), Merck 14,9317, UN2025, EINECS 200-210-4, RTECS OV8400000, BRN 8169555, MDL MFCD00013062, † | 10g 25g |
| |  H: H301-H310-H330-H373-H400-H410, P: P301+P310-P304+P340-P320-P330-P361-P405-P501a Application(s): A bacteriostatic and fungistatic mercurial agent | |
| | 2-Thiobarbituric acid , see 4,6-Dihydroxy-2-mercaptopyrimidine, A12681, p. 192 Thiocarbamide , see Thiourea, A12828, p. 368 Thioconazole , see Tioconazole, 98+%, J60459, p. 370 | |
| L04711 | DL-Thioctic acid, 98% [1,2-Dithiolane-3-valeric acid, DL-6,8-Dithiooctanoic acid] [1077-28-7], C ₈ H ₁₄ O ₂ S ₂ , F.W. 206.33, m.p. 59-63°, b.p. 160-165°, Merck 14,9326, EINECS 214-071-2, RTECS JP1192000, BRN 81853, MDL MFCD00005474 | 5g 25g |
| |   H: H302-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a Application(s): α Lipoic acid. A hydrogen transferrin cofactor | |



| Stock # | Description | Size |
|---------|---|-----------------------|
| A17002 | 2,2'-Thiodiethanol, 99% [Bis(2-hydroxyethyl) sulfide, Thiodiglycol] [111-48-8], S(CH ₂ CH ₂ OH) ₂ , F.W. 122.19, m.p. -16°, b.p. 164-166°/20mm, f.p. 160°(320°F), d. 1.221, n _D ²⁰ 1.5210, Merck 14,9330, EINECS 203-874-3, RTECS XR1700000, BRN 1236325, MDL MFCD00002910, † ! H: H319, P: P280-P264-P305+P351+P338-P337+P313 | 100g 500g 2.5kg |
| | Application(s): Useful antioxidant in amino acid determinations Thiodiglycol , see 2,2'-Thiodiethanol, A17002, p. 367 Thioethanolamine hydrochloride , see 2-Mercaptoethylamine hydrochloride, A14377, p. 281 Thioethylene glycol , see 2-Mercaptoethanol, A15890, p. 281 | |
| J61043 | Thioflavine T, tech. 75% [Basic Yellow 1, C.I. 49005] [2390-54-7], C ₁₇ H ₁₅ ClN ₂ S, F.W. 318.86, Powder, EINECS 219-228-9, BRN 3922452, MDL MFCD00011944, † | 5g 25g |
| | Application(s): A dye used to visualize β-amyloid plaques, like those associated with Alzheimer's Disease | |
| J63621 | 5-Thio-D-glucose, 97+% [20408-97-3], C ₆ H ₁₂ O ₅ S, F.W. 196.22, Powder, m.p. 135-138°, Merck 14,9334, EINECS 243-798-8, RTECS LZ7500000, BRN 1865193, MDL MFCD00006663 | 5mg 10mg 25mg |
| | Thioglycol , see 2-Mercaptoethanol, A15890, p. 281 Thioglycolic acid , see Mercaptoacetic acid, B20391, p. 280 Thioglycolic acid sodium salt , see Mercaptoacetic acid sodium salt, L14356, p. 280 | |
| B21280 | 6-Thioguanine, 98% [2-Amino-6-mercaptapurine, 2-Amino-6-purinethiol] [154-42-7], C ₅ H ₆ N ₆ S, F.W. 167.19, m.p. >360°, Merck 14,9337, UN2811, EINECS 205-827-2, RTECS UP0740000, BRN 157765, MDL MFCD00233553 ☠ H: H301-H341, P: P281-P301+P310-P321-P308+P313-P405-P501a | 1g 5g |
| |  | |
| B24934 | 2-Thiohydantoin, 99% [503-87-7], C ₄ H ₆ N ₂ OS, F.W. 116.14, m.p. 229-231° dec., EINECS 207-977-4, RTECS MU4200000, MDL MFCD00005277, † ! H: H302, P: P264-P270-P301+P312-P330-P501a | 5g 25g 100g |
| |  Thiolactic acid , see 2-Mercaptopropionic acid, L10257, p. 281 Thiolaniline hydrochloride , see 2-Iminothiolane hydrochloride, J60131, p. 255 Thiomalic acid , see Mercaptosuccinic acid, B23301, p. 281 | |
| A11144 | Thionicotinamide, 98% [Pyridine-3-thiocarboxamide] [4621-66-3], C ₆ H ₆ N ₂ S, F.W. 138.19, m.p. ca 190° dec., f.p. 160°(320°F), EINECS 225-036-6, RTECS QS4488000, BRN 109593, MDL MFCD00006399, † ! H: H302-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 25g 100g |
| |  | |
| A12514 | Thiophene-2-carboxylic acid, 99% [2-Thenoic acid] [527-72-0], C ₅ H ₄ O ₂ S, F.W. 128.15, m.p. 126-130°, b.p. 259-261°, d. 1.42, Merck 14,9354, EINECS 208-423-4, RTECS XM8330200, BRN 110150, MDL MFCD00005437, † ! H: H302-H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 25g 100g 500g |
| |  Application(s): A hypoglycemic, anti-lipolytic agent | |
| J60895 | Thioridazine hydrochloride ▲ ■ [130-61-0], C ₂₁ H ₂₆ N ₂ S ₂ ·HCl, F.W. 407.03, Powder, m.p. 161-163°, Merck 14,9359, UN3077, EINECS 204-992-8, RTECS SP2275000, MDL MFCD00012655 ☠ H: H301-H400-H410-H315-H319-H335, P: P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a | 5g |
| |  Application(s): An anti-psychotic that blocks neurotransmission at dopaminergic synapses | |
| J62557 | DL-Thiorphan [76721-89-6], C ₁₂ H ₁₅ NOS, F.W. 253.32, Powder, m.p. 124-126°, BRN 4872101, MDL MFCD00058435 | 25mg |
| | Application(s): Potent and specific inhibitor of enkephalinase with antinociceptive activity. Substrate for peptidylglycine α-amidating monooxygenase. | |
| A13401 | Thiosalicylic acid, 98% ▲ ▲ [2-Mercaptobenzoic acid] [147-93-3], C ₇ H ₆ O ₂ S, F.W. 154.19, m.p. 165-168°, d. 1.49, Merck 14,9360, EINECS 205-704-3, RTECS DH3325000, BRN 508507, MDL MFCD00004836, † ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | 50g 250g 1kg |
| |  | |
| A14630 | Thiosemicarbazide, 99% [79-19-6], CH ₃ N ₃ S, F.W. 91.14, m.p. ca 180° dec., Merck 14,9361, Fieser 1,1164, UN2811, EINECS 201-184-7, RTECS VT4200000, BRN 506320, MDL MFCD00007620, † ☠ H: H300, P: P264-P270-P301+P310-P321-P405-P501a | 100g 500g 2.5kg |
| |  Application(s): Used in TLC to stain α-keto acids | |

| Stock # | Description | Size |
|---|---|-------------------------------|
| J62332 | Thiostrepton, Streptomyces laurentii, 90+% [Bryamycin, Thiactin] [1393-48-2], C ₇₂ H ₈₂ O ₁₈ N ₁₉ S ₅ , F.W. 1664.89, Powder, Merck 14,9364, EINECS 215-734-9, RTECS XN6300100, MDL MFCD00135828 | 1g 5g |
| Application(s): Natural cyclic oligopeptide antibiotic | | |
| A18119 | 2-Thiouracil, 98% [4-Hydroxy-2-mercaptopyrimidine] [141-90-2], C ₄ H ₄ N ₂ OS, F.W. 128.15, m.p. >300°, Merck 14,9366, EINECS 205-508-8, RTECS YR1575000, BRN 112227, MDL MFCD00006039, † ☠ H:351, P:P281-P201-P202-P308+P313-P405-P501a | 25g 100g 500g |
| A12828 | Thiourea, 99% [Thiocarbamide] [62-56-6], CH ₄ N ₂ S, F.W. 76.12, m.p. 172-178°, d. 1.405, Merck 14,9367, Fieser 1,1164 2,412 3,290 6,586 11,519 15,308 19,336 20,371 21,421, UN3077, EINECS 200-543-5, RTECS YU2800000, BRN 605327, MDL MFCD00008067, † ☠ ! ☠ H:351-H361d-H302-H411, P:P280h-P273 | 100g 500g 2.5kg 10kg |
| Reagent for the conversion of alkyl halides to thiols by base hydrolysis of the isothiuronium salts; see also N-Acetylthiourea, B21198 . Cleavage of isothiuronium salts with base and alkylation of the resulting thiolate has been used as a convenient synthesis of unsymmetrical sulfides: <i>Synth. Commun.</i> , 14 , 209 (1984). Epoxides are converted to episulfides: <i>J. Org. Chem.</i> , 26 , 3467 (1961). The 2,3-epoxy alcohols resulting from the Sharpless enantioselective epoxidation can be converted to the corresponding episulfides with retention at both centers, using Ti(O-i-Pr) ₄ as mediator: <i>J. Org. Chem.</i> , 53 , 4114 (1988). Widely used in heterocyclic syntheses, e.g. of thiazoles and pyrimidines. Has been used in a convenient synthesis of isothiocyanates from oximes via the nitrile oxide: <i>Tetrahedron Lett.</i> , 34 , 8283 (1993); see also Benzaldoxime, A12053 : | | |
| | | |
| Application(s): Reagent for organic synthesis | | |
| 36609 | Thiourea, ACS, 99% min. [Thiocarbamide] [62-56-6], H ₂ NCSNH ₂ , F.W. 76.12, Crystalline, m.p. 175-178°, d. 1.405, Merck 14,9367, Fieser 1,1164 2,412 3,290 6,586 11,519 15,308 19,336 20,371 21,421, UN3077, EINECS 200-543-5, RTECS YU2800000, BRN 605327, MDL MFCD00008067, † Maximum level of impurities: Solubility in water P.T., Residue after ignition 0.1%, Loss on drying 0.5%, Melting point 174-177° ☠ ! ☠ H:351-H361d-H302-H411, P:P281-P273-P301+P312-P308+P313-P405-P501a | 50g 250g 1kg |
| Application(s): Reagent for organic synthesis | | |
| J60679 | 4-Thiouridine, 98+% [13957-31-8], C ₈ H ₁₂ N ₂ O ₃ S, F.W. 260.27, Crystalline, EINECS 237-735-3, MDL MFCD00006538 | 5mg 25mg 100mg |
| Thiouridine, see 4-Thiouridine, 98+%, J60679, p. 368 THP, see Tetrahydropalmitate, 98%, J63328, p. 363 | | |
| A10606 | DL-Threonine, 99% [(+/-)-2-Amino-3-hydroxybutyric acid, H-DL-Thr-OH] [80-68-2], C ₄ H ₉ NO ₃ , F.W. 119.12, m.p. ca 244° dec., Merck 14,9380, EINECS 201-300-6, BRN 1721647, MDL MFCD00063722, † | 25g 100g 500g |
| B21177 | D-Threonine, 99% [(2R,3S)-2-Amino-3-hydroxybutyric acid, H-D-Thr-OH] [632-20-2], C ₄ H ₉ NO ₃ , F.W. 119.12, m.p. ca 274° dec., [α] _D ²⁰ +29° (c=5 in water), EINECS 211-171-8, RTECS XO8580000, BRN 1721643, MDL MFCD00064269 For conversion to enantiomerically pure 1,3-butanediol, see: <i>Synth. Commun.</i> , 21 , 2295 (1991). | 5g 25g 100g |
| A16851 | L-Threonine, 98+% [(2S,3R)-2-Amino-3-hydroxybutyric acid, H-Thr-OH] [72-19-5], C ₄ H ₉ NO ₃ , F.W. 119.12, m.p. 255° dec., [α] _D ²⁰ -28° (c=5 in water), Merck 14,9380, EINECS 200-774-1, RTECS XO8590000, BRN 1721646, MDL MFCD00064270, † | 25g 100g 500g |
| J63709 | L-Threonine, Cell Culture Reagent [(2S,3R)-2-Amino-3-hydroxybutyric acid] [72-19-5], C ₄ H ₉ NO ₃ , F.W. 119.12, Powder, m.p. 256° dec., Merck 14,9380, EINECS 200-774-1, RTECS XO8590000, BRN 1721646, MDL MFCD00064270, † | 250g 1kg |
| J63383 | Thrombin, bovine plasma [Factor IIa, EC 3.4.21.5] [9002-04-4], Powder, Merck 14,9383, EINECS 232-648-7, RTECS XO8950000, MDL MFCD00166053 | 100kilounits 500kilounits |
| J63240 | Thrombin buffer, pH 8.0 Liquid, Note: 50mM Tris-HCl (pH 8.0), 150mM NaCl, 2mM calcium chloride. | 250ml 500ml |

| Stock # | Description | Size | |
|---------|--|--|-------|
| A11493 | Thymidine, 99% [50-89-5], C ₁₀ H ₁₄ N ₂ O ₅ , F.W. 242.23, m.p. 186-190°, [α] _D ²⁰ +19° (c=1 in water), Merck 14,9397, EINECS 200-070-4, RTECS XP2071000, BRN 89285, MDL MFCD00006537, † |  | 5g |
| | | 25g | |
| | | 100g | |
| | | | |
| J60747 | Thymidine-5'-monophosphate disodium salt [TMP] [33430-62-5], C ₁₀ H ₁₃ N ₂ Na ₂ O ₈ P, F.W. 366.18, Powder, EINECS 251-518-0, BRN 4086927, MDL MFCD09039259 | | 100mg |
| | | 250mg | |
| | | 1g | |
| | | 5g | |
| A15879 | Thymine, 97% [2,4-Dihydroxy-5-methylpyrimidine, 5-Methyluracil] [89-83-8], C ₅ H ₆ N ₂ O ₂ , F.W. 126.12, m.p. 316-317°, Merck 14,9398, EINECS 200-616-1, RTECS XP2100000, BRN 607626, MDL MFCD00006026, † |  | 25g |
| | | 100g | |
| | | 500g | |
| | | | |
| A14563 | Thymol, 98+% [2-Isopropyl-5-methylphenol] [89-83-8], C ₁₀ H ₁₄ O, F.W. 150.22, m.p. 49-52°, b.p. 231-233°, f.p. 102°(215°F), d. 0.970, Merck 14,9399, UN2430, EINECS 201-944-8, RTECS XP2275000, BRN 1907135, MDL MFCD00002309, † |  | 100g |
| | | 250g | |
| | | 500g | |
| | | | |
| | ! H: H314-H302-H411, P: P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | | |
| | Application(s): Has strong antiseptic properties | | |
| B21370 | Thymol Blue [76-61-9], C ₂₇ H ₃₀ O ₅ S, F.W. 466.60, m.p. 223° dec., Merck 14,9400, EINECS 200-973-3, RTECS XP2575000, MDL MFCD00005869, † |  | 10g |
| | | 50g | |
| | | | |
| | | | |
| 16272 | Thymol Blue, ACS [Thymolsulfonphthalein] [76-61-9], C ₂₇ H ₃₀ O ₅ S, F.W. 466.60, Crystalline, m.p. 223° dec., Merck 14,9400, Solubility: Insoluble in water. Soluble in alcohol, dilute alkali solutions, EINECS 200-973-3, RTECS XP2575000, MDL MFCD00005869, † Specifications: Clarity of solution P.T., Visual transition interval (acid range) pH 1.2 (red) to 2.8 (yellow), Visual transition range (alkaline range) pH 8.0 (yellow) to 9.2 (blue) |  | 2g |
| | | 10g | |
| | | 50g | |
| | | | |
| | Application(s): pH indicator: 1.2 (red) to 2.8 (yellow) to 9.6 (blue) | | |
| 38692 | Thymol Blue sodium salt, 0.04% w/v aq. soln. [62625-21-2], C ₂₇ H ₂₉ NaO ₅ S, F.W. 488.58, Liquid, d. 0.979, EINECS 200-973-3, MDL MFCD00151093, Note: Transition interval: pH 1.2 (red) to pH 2.8 (yellow); pH 8.0 (yellow) to pH 9.2 (blue), † | | 100ml |
| | | 500ml | |
| | | 6x100ml | |
| | | | |
| 42785 | Thymol Blue sodium salt, ACS [62625-21-2], C ₂₇ H ₂₉ NaO ₅ S, F.W. 488.58, Crystalline, m.p. ca 284° dec., Solubility: Soluble in water, EINECS 263-650-6, BRN 3861515, MDL MFCD00151093, Note: Thymolsulfonphthalein, † Specifications: Clarity of solution P.T., Visual transition interval (acid range) pH 1.2 (red) to pH 2.8 (yellow), Visual transition interval (alkaline range) pH 8.0 (yellow) to pH 9.2 (blue) | | 2g |
| | | 10g | |
| | | | |
| | | | |
| | Application(s): Water soluble pH indicator | | |
| 38706 | Thymolphthalein, 0.05% w/v solution in ethanol [125-20-2], C ₂₈ H ₃₀ O ₄ , F.W. 430.55, Liquid, f.p. 11°(52°F), d. 0.920, Merck 14,9401, UN1170, BRN 359413, MDL MFCD00005909, Note: Transition interval: pH 8.8 (colorless) to pH 10.5 (blue), † |  | 100ml |
| | | 500ml | |
| | | | |
| | | | |
| | ! H: H225-H371, P: P210-P241-P260-P303+P361+P353-P405-P501a | | |
| 16245 | Thymolphthalein, ACS [125-20-2], C ₂₈ H ₃₀ O ₄ , F.W. 430.55, Crystalline, m.p. 251-253°, Merck 14,9401, Solubility: Insoluble in water. Soluble in alcohol, acetone, dilute alkalis (blue color), H ₂ SO ₄ (red color), EINECS 204-729-7, BRN 359413, MDL MFCD00005909, † Maximum level of impurities: Clarity of solution P.T., Visual transition interval from pH 8.8 (colorless) to 10.5 (blue) | | 5g |
| | | 25g | |
| | | | |
| | | | |
| | Application(s): pH indicator; colorless below pH 9.3, blue above pH 10.5 | | |
| | Thymolsulfonphthalein , see Thymol Blue, 16272, p. 369 | | |
| J61431 | Thymopentin, 99+% [Arg-Lys-Asp-Val-Tyr, TP-5] [69558-55-0], C ₃₀ H ₄₉ N ₉ O ₉ , F.W. 679.77, Powder, Merck 14,9403, MDL MFCD00214200 | | 25mg |
| | | 100mg | |
| | | | |
| | | | |
| | Application(s): Reduces endocrine responses | | |










| Stock # | Description | Size |
|---------|---|--------------------|
| J62120 | Thyrotropin-Releasing Hormone [TRH, Pyr-His-Pro-NH2] [24305-27-9], C ₁₈ H ₂₂ N ₄ O ₄ , F.W. 362.38, Powder, Merck 14,9588, EINECS 246-143-4, RTECS TW3580000, BRN 770238, MDL MFCD00038640 | 50mg |
| | Application(s): Two-chain glycoprotein hormone. Activates adenylate cyclase in the thyroid gland, stimulating iodine uptake, thyroxine synthesis and release | |
| J62606 | L-Thyroxine, 98% [3,3',5,5'-Tetraiodo-L-thyronine] [51-48-9], C ₁₅ H ₁₁ I ₄ NO ₄ , F.W. 776.87, Crystalline powder, m.p. 223° dec., Merck 14,9415, EINECS 200-101-1, RTECS YP2833500, BRN 2228515, MDL MFCD00002595, † | 1g 5g |
| J63971 | Ticlopidine hydrochloride [5-(2-Chlorobenzyl)-4,5,6,7-tetrahydrothieno[3,2-c]pyridine hydrochloride] [53885-35-1], C ₁₆ H ₁₄ ClNS·HCl, F.W. 300.25, Powder, Merck 14,9429, EINECS 258-837-4, RTECS XJ9089100, MDL MFCD00079606 | 5g 25g |
| | ! H:H302, P:P264-P270-P301+P312-P330-P501 | |
| | Application(s): Platelet aggregation inhibitor capable of inducing apoptosis in various cancer cell lines | |
| J60459 | Tioconazole, 98+% [Tioconazole] [65899-73-2], C ₁₈ H ₁₃ Cl ₃ N ₂ OS, F.W. 387.71, Powder, Merck 14,9452, EINECS 265-973-8, RTECS NI4480000, MDL MFCD00057276 | 1g 5g 25g |
| | ! H:H302-H413, P:P273-P264-P270-P301+P312-P330-P501a | |
| | Application(s): Potent inhibitor of cytochrome-P450 | |
| | TIS, see Triisopropylsilane, L09585, p. 378 TLCK, see Nα-(p-Toluenesulfonyl)-L-Lysine chloromethyl ketone hydrochloride, J60120, p. 371 TLCK, see Nα-(p-Toluenesulfonyl)-DL-Lysine chloromethyl ketone hydrochloride, 98%, J63959, p. 371 | |
| J63355 | TM media, TRIS + MgSO₄·7H₂O | 100ml 250ml |
| | Liquid, Note: 5.5mM Tris-HCl, 8mM magnesium sulfate, pH 7.5. | |
| | TMB-8 hydrochloride, see 8-(Diethylamino)octyl 3,4,5-trimethoxybenzoate hydrochloride, 97%, J62528, p. 188 TMB dihydrochloride hydrate, see 3,3',5,5'-Tetramethylbenzidine dihydrochloride hydrate, 99+%, J60332, p. 364 TMB soluble reagent, aq. soln., see 3,3',5,5'-Tetramethylbenzidine aq. soln., J60808, p. 364 TMB soluble reagent, high sensitivity, see 3,3',5,5'-Tetramethylbenzidine soln., Ready-to-Use, high sensitivity, J61325, p. 364 TMB reagent, standard sensitivity, see 3,3',5,5'-Tetramethylbenzidine soln., Ready-to-Use, precipitating, standard sensitivity, J60461, p. 364 TMEDA, see N,N,N',N'-Tetramethylethylenediamine, A12536, p. 364 TMG hydrochloride, see Methylguanidine hydrochloride, 98%, J60033, p. 288 TMP, see Thymidine-5'-monophosphate disodium salt, J60747, p. 369 TMP, see 4,5',8-Trimethylpsoralen, 99%, J63226, p. 378 | |
| J63985 | TN buffer soln. [TRIS NaCl buffer soln] Liquid, Note: 10mM Tris-HCl, 150mM sodium chloride, pH 8.0. | 500ml 1L |
| | TNBT, see Tetranitro Blue Tetrazolium chloride, 97%, J61080, p. 365 TNBT, see Tetranitro Blue tetrazolium chloride, J61080, p. 365 | |
| J60622 | TNT buffer soln. [TRIS NaCl Tween 20 buffer soln.] Liquid, Note: 10mM Tris-HCl, 150mM NaCl, 0.05% Tween-20, pH 8.0. | 1L 2L |
| J62995 | Tobramycin sulfate [79645-27-5], (C ₁₈ H ₃₇ N ₅ O ₉) ₂ ·5H ₂ SO ₄ , F.W. 1425.41, Powder, Merck 14,9490, RTECS WK2110000, MDL MFCD00133864 | 100mg 1g |
| | ! H:H302-H312-332-H360, P:P261-P280-P281-P302+P352-P405-P501 | |
| | Application(s): A water-soluble aminoglycoside antibiotic | |
| J62846 | Tocinoic acid, 96% [(Ile3)-Pressinoic acid, H-Cys-Tyr-Ile-Gln-Asn-Cys-OH] [34330-23-9], C ₃₀ H ₄₄ N ₆ O ₁₀ S ₂ , F.W. 740.86, Powder, MDL MFCD00076737 | 25mg |
| | Application(s): A ring-structured analog of oxytocin that decreases locomotor activity | |
| A17039 | DL-α-Tocopherol, 97+% ▲ ▲ [Vitamin E] [10191-41-0], C ₂₉ H ₅₀ O ₂ , F.W. 430.72, m.p. 2-4°, b.p. 200-220°/0.1mm, f.p. 240°(464°F), d. 0.950, n _D ²⁰ 1.5050, Merck 14,10021, EINECS 233-466-0, RTECS GA8746000, BRN 94012, MDL MFCD00072051, † | 50g 250g 1kg |
| |  | |
| | DL-α-Tocopheryl acetate, see Vitamin E acetate, A14505, p. 393 Toddaline, see Chelerythrine chloride, 99+%, J62906, p. 153 Tolazoline hydrochloride, see 2-Benzyl-2-imidazoline hydrochloride, B21764, p. 122 | |



| Stock # | Description | Size |
|---------|---|-------|
| B21698 | Tolbutamide, 98% [1- <i>n</i> -Butyl-3-(<i>p</i> -tolylsulfonyl)urea] [64-77-7], C ₁₆ H ₁₈ N ₂ O ₃ S, F.W. 270.35, m.p. 128-130°, Merck 14,9507, EINECS 200-594-3, RTECS YS4550000, BRN 1984428, MDL MFCD00027169, † | 10g |
| | | 50g |
| | 250g | |
| | ! H: H302-H317, P: P261-P280-P302+P352-P321-P301+P312-P501a | |
| | Application(s): A first-generation potassium channel blocker | |
| J61256 | Tolfenamic acid, 99+% [2 (3-Chloro-2-methylanilino)benzoic acid, Clotam] [13710-19-5], C ₁₇ H ₁₂ ClNO ₂ , F.W. 261.70, Crystalline powder, Merck 14,9513, UN2811, EINECS 237-264-3, RTECS CB2687500, MDL MFCD00133865 | 5g |
| | | 10g |
| | 25g | |
| | ! H: H301, P: P264-P270-P301+P310-P321-P405-P501a | |
| | Application(s): NSAID that activates calcium-activated potassium channels | |
| J62663 | Tolmetin sodium salt dihydrate, 98+% [64490-92-2], C ₁₅ H ₁₄ NNaO ₃ ·2H ₂ O, F.W. 315.30 (279.27anhy), Powder, Merck 14,9518, RTECS UX9280000, MDL MFCD00150761 | 1g |
| | | 5g |
| | 25g | |
| | ! H: H302-H315, P: P280-P302+P352-P321-P362-P301+P312-P501 | |
| | Application(s): An NSAID compound | |
| J61834 | Tolnaftate [Methyl-(3-methylphenyl)carbamothioic acid O-2-naphthyl ester, Carbamothioic acid] [2398-96-1], C ₁₉ H ₁₇ NOS, F.W. 307.41, Powder, m.p. 110-113°, Merck 14,9519, EINECS 219-266-6, MDL MFCD00056611, † | 1g |
| | | 5g |
| | 25g | |
| | Application(s): Antifungal agent | |
| | α-Toluenephosphonic acid, see Benzylphosphonic acid, A13850, p. 123 | |
| 36506 | p-Toluenesulfonic acid monohydrate, 97% [4-Methylbenzenesulfonic acid monohydrate] [6192-52-5], CH ₃ C ₆ H ₄ SO ₃ H·H ₂ O, F.W. 190.22 (172.20anhy), Solid, m.p. 103-106°, b.p. 140°/20mm, f.p. 150°(302°F), d. 1.24, Merck 14,9533, Fieser 1,1172 4,508 5,673 6,597 7,374 8,488 9,471 11,535 12,507, UN2585, EINECS 203-180-0, RTECS XT6300000, BRN 3568023, MDL MFCD00142137, † | 25g |
| | | 100g |
| | 500g | |
| | ! H: H315-H319-H335, P: P280-P305+P351+P338-P309-P510 | |
| B22146 | α-Toluenesulfonyl fluoride, 99% ☑ [Phenylmethanesulfonyl fluoride, Phenylmethylsulfonyl fluoride] [329-98-6], C ₇ H ₇ FO ₂ S, F.W. 174.19, m.p. 92-94°, UN2923, EINECS 206-350-2, RTECS XT8040000, BRN 2088311, MDL MFCD00007424, † | 1g |
| | | 5g |
| | 25g | |
| | ! H: H301-H314, P: P260-P301+P310-P303+P361+P353-P305+P351+P338-P405-P501a | |
| | Application(s): A powerful protease inhibitor | |
| J63959 | N-α-(p-Toluenesulfonyl)-DL-lysine chloromethyl ketone hydrochloride, 98% [TLCK, N-α-p-Tosyl-DL-lysine chloromethyl ketone hydrochloride] [4238-41-9], C ₁₈ H ₂₇ ClN ₂ O ₆ S HCl, F.W. 369.31, Powder, EINECS 224-199-0, RTECS XT5160000 | 50mg |
| | | 100mg |
| | 250mg | |
| | ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): Inhibitor of papain and trypsin | |
| J60120 | N-α-(p-Toluenesulfonyl)-L-lysine chloromethyl ketone hydrochloride [TLCK, N-α-p-Tosyl-L-lysine chloromethyl ketone hydrochloride] [4272-74-6], C ₁₈ H ₂₇ ClN ₂ O ₆ S HCl, F.W. 369.31, Powder, EINECS 224-266-4, RTECS XT5160000, BRN 7106867, MDL MFCD00065395 | 500mg |
| | | 1g |
| | ! H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): Inhibitor of papain and trypsin | |
| J60639 | N-(p-Toluenesulfonyl)-L-phenylalanine chloromethyl ketone [TPCK, N-p-Tosyl-L-phenylalanine chloromethyl ketone] [402-71-1], C ₁₇ H ₁₈ ClNO ₂ S, F.W. 351.85, Powder, EINECS 206-954-6, RTECS XT5613500, BRN 2895215, MDL MFCD00000935, † | 1g |
| | | 5g |
| | ! H: H315-H318-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): Enzyme inhibitor that inactivates chymotrypsin but not trypsin | |
| J63803 | Toremifene, 98+% [Toremifene base, 2-(4-[(1Z)-4-Chloro-1,2-diphenyl-1-butenyl]phenoxy)-N,N-dimethylethanamine] [89778-26-7], C ₂₈ H ₂₈ ClNO, F.W. 405.96, Powder, m.p. 108-110°, Merck 14,9550, UN3077 | 500mg |
| | | 1g |
| | 5g | |
| | ! H: H318-H400-H410-H302, P: P280-P273-P305+P351+P338-P310-P301+P312-P501a | |
| | Application(s): A chlorinated tamoxifen analogue, that induces apoptosis in some cells | |
| | N-α-p-Tosyl-L-lysine chloromethyl ketone hydrochloride, see N-α-(p-Toluenesulfonyl)-L-lysine chloromethyl ketone hydrochloride, J60120, p. 371 | |
| | N-p-Tosyl-L-phenylalanine chloromethyl ketone, see N-(p-Toluenesulfonyl)-L-phenylalanine chloromethyl ketone, J60639, p. 371 | |



| Stock # | Description | Size |
|---------|--|----------|
| J63232 | Tozasertib, 99+% | 10mg |
| | [VX-680, MK-0457] [639089-54-6], C ₂₃ H ₂₈ N ₆ OS, F.W. 464.59, Powder, m.p. 245-260° | 25mg |
| | ! H:H360, P:P281-P201-P202-P308+P313-P405-P501 | 50mg |
| | Application(s): Important inhibitor of all aurora kinases. Induces apoptosis and blocks tumor growth in varieties of leukemia, colon and pancreatic tumors | |
| | TP-5, see Thymopentin, 99+%, J61431, p. 369 | |
| | TPCK, see N-(p-Toluenesulfonyl)-L-phenylalanine chloromethyl ketone, J60639, p. 371 | |
| J60233 | TPE (10X), TRIS + phosphate + EDTA | 1L |
| | Liquid, Note: 0.9M Tris base, 0.9M phosphate, 200mM EDTA. | 2L |
| | ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | 4L |
| J65162 | T4 Polynucleotide Kinase [EC 2.7.1.78, <i>Polynucleotide Kinase from T4-infected Escherichia coli</i>] [37211-65-7], Liquid, EINECS 253-400-4, † | 500units |
| | Application(s): Transfers the γ -phosphate of ATP to the 5' hydroxyl terminus of single- and double-stranded nucleic acids and 3'-nucleoside monophosphates. Used in the 5' phosphorylation of oligonucleotides | |
| A18502 | Tragacanth powder | 100g |
| | [<i>Gum tragacanth</i>] [9000-65-1], Merck 14,4581, EINECS 232-552-5, RTECS XW7750000, MDL MFCD00131255, † | 500g |
| | Tragacanth Indian, see Karaya Gum, J61844, p. 262 | |
| J60019 | TRAM 34 | 25mg |
| | [1-[(2-Chlorophenyl)diphenylmethyl]-1H-pyrazole] [289905-88-0], C ₂₂ H ₁₇ ClN ₂ , F.W. 344.84, Powder, m.p. 145-147°, MDL MFCD09842562 | |
| | ! H:H302, P:P264-P270-P301+P312-P330-P501 | |
| | Application(s): TRAM-34 is a potent inhibitor of the intermediate-conductance calcium-activated potassium channel | |
| J64941 | Transaminase Kit - 12 variants (TA1 through TA12) | 1each |
| | Lyophilized powder, Note: Contains 100mg of each variant | |
| | Application(s): Enzymes catalyze the synthesis of chiral amines from prochiral ketones by asymmetric amino transfer | |
| J64306 | Transaminase Kit - 20 variants (TA1 through TA20) | 1each |
| | Lyophilized powder, Note: Contains 100mg of each variant | |
| | Application(s): Catalyze synthesis of chiral amines from prochiral ketones by asymmetric amino transfer | |
| J64836 | Transaminase TA1 | 250mg |
| | Lyophilized powder | 500mg |
| | | 1g |
| J65711 | Transaminase TA2 | 250mg |
| | Lyophilized powder | 500mg |
| | | 1g |
| J64914 | Transaminase TA3 | 250mg |
| | Lyophilized powder | 500mg |
| | | 1g |
| J64900 | Transaminase TA4 | 250mg |
| | Lyophilized powder | 500mg |
| | | 1g |
| J64513 | Transaminase TA5 | 250mg |
| | Lyophilized powder | 500mg |
| | | 1g |
| J64473 | Transaminase TA6 | 250mg |
| | Lyophilized powder | 500mg |
| | | 1g |
| J64783 | Transaminase TA7 | 250mg |
| | Lyophilized powder | 500mg |
| | | 1g |
| J64699 | Transaminase TA8 | 250mg |
| | Lyophilized powder | 500mg |
| | | 1g |
| J64060 | Transaminase TA9 | 250mg |
| | Lyophilized powder | 500mg |
| | | 1g |


| Stock # | Description | Size |
|---------|---|----------------------|
| J64092 | Transaminase TA10 Lyophilized powder | 250mg 500mg 1g |
| J65720 | Transaminase TA11 Lyophilized powder | 250mg 500mg 1g |
| J64376 | Transaminase TA12 Lyophilized powder | 250mg 500mg 1g |
| J65452 | Transaminase TA13 Lyophilized powder | 250mg 500mg 1g |
| J64756 | Transaminase TA14 Lyophilized powder | 250mg 500mg 1g |
| J65834 | Transaminase TA15 Lyophilized powder | 250mg 500mg 1g |
| J64791 | Transaminase TA16 Lyophilized powder | 250mg 500mg 1g |
| J64260 | Transaminase TA17 Lyophilized powder | 250mg 500mg 1g |
| J65905 | Transaminase TA18 Lyophilized powder | 250mg 500mg 1g |
| J64421 | Transaminase TA19 Lyophilized powder | 250mg 500mg 1g |
| J65112 | Transaminase TA20 Lyophilized powder | 250mg 500mg 1g |
| J63037 | Transfer or electro blotting buffer (10X), pH 8.5 Liquid, Note: 0.25M Tris base, 1.92M glycine, pH 8.5. Add methanol according to your protocol. | 1L 2L 4L |
| J61626 | Transferrin (Apo), bovine plasma, 98+% <i>[Apo Transferrin]</i> [11096-37-0], Lyophilized powder, Merck 14,9571, EINECS 234-318-8, MDL MFCD00130536, † Application(s): Blood plasma protein for iron delivery. Apo-transferrin is iron-free | 50mg 500mg 1g |
| J61046 | Transferrin (Holo), bovine plasma, 98+% <i>[Siderophilin, iron-saturated, HTF bovine native protein]</i> [11096-37-0], Lyophilized powder, Merck 14,9571, EINECS 234-318-8, MDL MFCD00131337, † Application(s): Blood plasma protein for iron delivery. HOLO-transferrin has iron bound at the N-terminus | 50mg 500mg 1g |
| J63244 | Transformation buffer-1, pH 7.5 Liquid, Note: Contains 30mM potassium-acetate, 150mM calcium chloride, 10mM PIPES, 100mM potassium chloride, 50mM manganese chloride and 15% glycerol, pH 7.5 | 125ml 250ml |
| J63293 | Transformation buffer-2, pH 7.5 Liquid, Note: Contains 10mM MOPS, 75mM calcium chloride, 10mM potassium chloride, and 15% glycerol, pH 7.5 | 125ml 250ml |
| J64478 | Transforming Growth Factor-α, human, 98% <i>[TGF-α]</i> Note: Recombinantly expressed in E. Coli. Receptor Grade. Suitable for radioimmunoassays. Supplied as a lyophilized powder | 2micrograms |
| J65773 | Transforming Growth Factor-β 1, human platelets, 97% <i>[TGF-β1]</i> Note: Receptor Grade. Suitable for use in cell culture. Supplied as a lyophilized powder with BSA. | 0.5micrograms |

| Stock # | Description | Size |
|---|--|---------------------|
| J65044 | Transforming Growth Factor-β 1, human platelets, carrier free, 97% [TGF-beta 1] Note: Receptor Grade. Suitable for use in cell culture. Supplied as 5ug in TFA and acetonitrile. | 5micrograms |
| J65173 | Transforming Growth Factor-β 1, human platelets, lyophilized with BSA, 97% [TGF-beta 1] Note: Receptor Grade. Suitable for use in cell culture. Supplied as a lyophilized powder with BSA. | 5micrograms |
| Traut's reagent , see 2-Iminothiolane hydrochloride, J60131, p. 255 | | |
| J63070 | Trazodone hydrochloride [25332-39-2], C ₁₈ H ₂₂ ClN ₂ O·HCl, F.W. 408.33, Powder, m.p. 222-227°, Merck 14,9579, EINECS 246-855-5, RTECS XZ5660000, MDL MFCD00079603  H:H302-H351, P:P281-P264-P301+P312-P308+P313-P405-P501 | 1g 5g 25g |
| Application(s): A serotonin uptake inhibitor | | |
| A19434 | D-(+)-Trehalose dihydrate, 99% ■ [α-D-Glucopyranosyl-α-D-glucopyranoside] [6138-23-4], C ₁₂ H ₂₂ O ₁₁ ·2H ₂ O, F.W. 378.33 (342.29anhy), m.p. 97-99°, [α] _D ²⁰ +179° (c=2 in water), Merck 14,9580, EINECS 202-739-6, BRN 5322018, MDL MFCD00071594, †  | 5g 25g 100g |
| J63999 | Trequinsin hydrochloride, 98+% [HL-725] [78416-81-6], C ₂₄ H ₂₇ N ₃ O ₃ ·HCl, F.W. 441.95, Powder, RTECS UW7727000, MDL MFCD01076563 | 10mg |
| Application(s): Anti-hypertensive agent, inhibitor of cGMP-inhibited phosphodiesterase | | |
| TRH , see Thyrotropin-Releasing Hormone, J62120, p. 370 | | |
| Triacetin , see Glycerol triacetate, A17132, p. 236 | | |
| Triacylglycerol acylhydrolase , see Lipase, from porcine pancreas, J62903, p. 270 | | |
| J63548 | Triamcinolone acetonide, 98+% [9α-Fluoro-16α-hydroxyprednisolone-16α,17α-acetonide] [76-25-5], C ₂₈ H ₃₁ FO ₆ , F.W. 434.50, Powder, m.p. 274-278°, Merck 14,9596, EINECS 200-948-7, RTECS TU3920000, MDL MFCD00056834, †  H:H360-H302, P:P281-P264-P301+P312-P308+P313-P405-P501a | 1g |
| Application(s): A glucocorticoid, antiasthmatic (inhalant); antiallergic (nasal) | | |
| B20044 | 2,4,7-Triamino-6-phenylpteridine, 98% [Triamterene] [396-01-0], C ₁₀ H ₇ N ₅ , F.W. 253.27, m.p. >300°, Merck 14,9599, EINECS 206-904-3, RTECS UO3470000, BRN 266723, MDL MFCD00006708   H:H301-H315-H319-H335, P:P301+P310-P305+P351+P338-P302+P352-P321-P405-P501a | 5g 25g 100g |
| Application(s): Weak diuretic with potassium sparing properties that blocks sodium reuptake in the kidneys | | |
| Triamterene , see 2,4,7-Triamino-6-phenylpteridine, B20044, p. 374 | | |
| 1,2,4-Triazine-3,5(2H,4H)-dione , see 6-Azauracil, A14389, p. 114 | | |
| A11597 | 1,2,4-Triazole, 99% [288-88-0], C ₂ H ₃ N ₃ , F.W. 69.07, m.p. 118-122°, b.p. 260°, f.p. 158°(316°F), Merck 14,9605, Fieser 1,1188 2,423, EINECS 206-022-9, RTECS XZ3806000, BRN 104767, MDL MFCD00005228, †   H:H361d-H302-H319, P:P280-P281-P305+P351+P338-P301+P312-P405-P501a | 25g 100g 500g |
| Bifunctional acylation catalyst, often superior to Imidazole , A10221 , p. 254, for esterification, amidation, etc. Has found limited use as a catalyst for low-racemization peptide bond formation: <i>Proc. Chem. Soc.</i> , 266 (1963); <i>Rec. Trav. Chim.</i> , 84 , 213 (1965); <i>Liebigs Ann. Chem.</i> , 691 , 212 (1966). In a comparative study of 1- vs 4-alkylation using different bases it was found that the best yields of the 1-substituted regioisomers were obtained with DBU: <i>Tetrahedron Lett.</i> , 41 , 1297 (2000). | | |
| Application(s): Useful as an antifungal compound | | |
| 1H-1,2,4-Triazole-3,5-diamine , see 3,5-Diamino-1,2,4-triazole, B22775, p. 183 | | |
| Tributyrin , see Glycerol tributyrate, A11830, p. 236 | | |
| J62366 | Trichloroacetic acid, 5% w/v aq. soln. [TCA] [76-03-9], Cl ₃ CCO ₂ H, F.W. 163.39, Liquid, Merck 14,9627, UN2564, EINECS 200-927-2, BRN 970119, MDL MFCD00004177, †  H:H314-H335+H336-H411, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 500ml 1L |
| Application(s): Protein precipitation reagent | | |
| J62355 | Trichloroacetic acid, 10% w/v aq. soln. [TCA] [76-03-9], Cl ₃ CCO ₂ H, F.W. 163.39, Liquid, Merck 14,9627, UN2564, EINECS 200-927-2, RTECS AJ7875000, BRN 970119, MDL MFCD00004177, †  H:H314-H335+H336-H411, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 500ml |
| Application(s): Protein precipitation reagent | | |

| Stock # | Description | Size |
|---------------|---|--|
| A11156 | Trichloroacetic acid, 99% ■ [TCA] [76-03-9], Cl ₃ CCO ₂ H, F.W. 163.39, m.p. 54-58°, b.p. 196°, d. 1.629, Merck 14,9627 , Fieser 1,1194 2,425 4,520 , UN1839, EINECS 200-927-2, RTECS AJ7875000, BRN 970119, MDL MFCD00004177, †  H: H314-H400-H410, P: P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a Trihaloacetic acids react with aldehydes in DMSO at room temperature to give trihalomethyl carbinols: <i>J. Chem. Soc., Perkin 2</i> , 1247 (1984): $\text{ArCHO} + \text{X}_3\text{CCOOH} \xrightarrow[\text{-CO}_2]{\text{DMSO, room temp.}} \text{ArCHX}_3 \begin{matrix} \\ \text{OH} \end{matrix} \quad \text{X} = \text{Cl, Br} \quad 50-80\%$ | 250g 500g 1kg 5kg |
| | The acid and its Na salt (1:1) in DMF are also effective: <i>Tetrahedron Lett.</i> , 33 , 3435 (1992). Use of HMPA or DMI extends the scope to less reactive aldehydes: <i>Synthesis</i> , 327 (1990). Application(s): Protein precipitation reagent | |
| 22156 | Trichloroacetic acid, ACS, 99% ■ [TCA] [76-03-9], CCl ₃ CO ₂ H, F.W. 163.39, Crystalline, m.p. 54-58°, b.p. 196°, d. 1.629, Merck 14,9627 , Fieser 1,1194 2,425 4,520 , UN1839, EINECS 200-927-2, RTECS AJ7875000, BRN 970119, MDL MFCD00004177, † Maximum level of impurities: Clarity of solution P.T. Insoluble matter 0.01%, Residue after ignition 0.03%, Cl 0.002%, NO _x 0.002%, PO _x 5ppm, SO _x 0.02%, Heavy Metals (as Pb) 0.002%, Fe 0.001%, Substances darkened by sulfuric acid P.T.  H: H314-H400-H410, P: P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 50g 250g 1kg |
| | Application(s): Protein precipitation reagent 1,2-O-(2,2,2-Trichloroethylidene)-α-D-glucufuranose , see α-Chloralose, A11492, p. 153 Trichloromethane , see Chloroform, 32614, p. 156 2,4,6-Trichloro-1,3,5-triazine , see Cyanuric chloride, L03442, p. 170 | |
| A14695 | Tricine, 98+% [N-(Trishydroxymethylmethyl)glycine] [5704-04-1], (HOCH ₂) ₃ CNHCH ₂ CO ₂ H, F.W. 179.17, m.p. ca 183° dec., Merck 14,9651 , EINECS 227-193-6, BRN 1937804, MDL MFCD00004277, Note: pH range: 7.8-8.8, † Biological buffer, pKa = 8.15 at 20°: <i>Biochemistry</i> , 5 , 467 (1966). | 25g 100g 500g |
| | Application(s): Good's buffers | |
| J60107 | Tricine, 0.5M buffer soln., pH 6.5 [5704-04-1], Liquid | 100ml 250ml |
| J62234 | Tricine, 0.5M buffer soln., pH 7.0 [5704-04-1], Liquid | 100ml 250ml |
| J62672 | Tricine, 0.5M buffer soln., pH 7.5 [5704-04-1], Liquid | 100ml 250ml |
| J62983 | Tricine, 0.5M buffer soln., pH 8.0 [5704-04-1], Liquid | 100ml 250ml |
| J63108 | Tricine, 0.5M buffer soln., pH 8.5 [5704-04-1], Liquid | 100ml 250ml |
| J63880 | Tricine, 0.5M buffer soln., pH 9.0 [5704-04-1], Liquid | 100ml 250ml |
| J60811 | Tricine-buffered saline (5X), pH 7.0 [5704-04-1], Liquid, Note: 50mM tricine and 750mM NaCl, pH 7.0 | 250ml 500ml |
| J63294 | Tricine-buffered saline (5X), pH 7.5 [5704-04-1], Liquid, Note: 50mM Tricine and 750mM NaCl, pH 7.5 | 250ml 500ml |
| J60745 | Tricine-buffered saline (5X), pH 8.0 [5704-04-1], Liquid, Note: 50mM Tricine and 750mM NaCl, pH 8.0 | 250ml 500ml |
| J64437 | Tricine, Electrophoresis Grade, 99% [N-(Trishydroxymethylmethyl)glycine] [5704-04-1], (HOCH ₂) ₃ CNHCH ₂ CO ₂ H, F.W. 179.17, Powder, m.p. ca 183° dec., Merck 14,9651 , EINECS 227-193-6, BRN 1937804, MDL MFCD00004277, † | Call |
| J62677 | Tricine-SDS Sample Buffer (2X), non-reducing Liquid, Note: Contains: 900mM Tris-HCl (pH 8.45), 8% SDS, 20% glycerol, 0.01% Coomassie blue, 0.01% Phenol Red | 25ml 50ml |
| J61042 | Tricine-SDS Sample Buffer (2X), reducing Liquid, Note: Contains 900mM Tris-HCl (pH 8.45), 8% SDS, 20% glycerol, 0.01% Coomassie blue, 0.01% Phenol Red, 4% mercaptoethanol. | 25ml 50ml |
| | Tricosaethylene glycol mono-n-dodecyl ether , see Brij® L23, A15809, p. 135 | |


| Stock # | Description | Size |
|--|--|--|
| J63015 | Tricyclodecan-9-yl xanthogenate potassium salt, 98+% [D609 potassium salt, O-Tricyclo[5.2.1.0 ⁶] ⁶ dec-9-yl dithiocarbonate potassium salt] [83373-60-8], C ₁₁ H ₁₅ KOS ₂ , F.W. 266.46, Powder, EINECS 280-379-9, MDL MFCD00171401 ! H:H302, P:P264-P270-P301+P312-P330-P501 | 5mg 25mg |
| Application(s): Inhibitor of phosphatidylcholine-specific phospholipase C | | |
| O-Tricyclo[5.2.1.0⁶]⁶dec-9-yl dithiocarbonate potassium salt, 98+% , J63015, p. 376 1,2,3-Tridodecanoylglycerol , see Trilaurin, J62962, p. 378 | | |
| L04486 | Triethanolamine, 98+%   [2,2',2''-Nitrilotriethanol, Tris(2-hydroxyethyl)amine] [102-71-6], (HOCH ₂ CH ₂) ₃ N, F.W. 149.19, m.p. 19-21°, b.p. 206-207°/15mm, f.p. 185°(365°F), d. 1.124, n _D ²⁰ 1.4850, Merck 14,9665 , Fieser 1,1196 , EINECS 203-049-8, RTECS KL9275000, BRN 1699263, MDL MFCD00002855, † ! H:H315-H319, P:P260-P305+P351+P338-P302+P352-P321-P362-P332+P313 Reacts with N-alkylanilines in dioxane (autoclave) in the presence of Dichlorotris(triphenylphosphine)ruthenium(II), L00373 , to give 1-alkyl indoles in good yield: <i>Synth. Commun.</i> , 26 , 1349 (1996). | 100g 500g 2.5kg |
| Application(s): Protein purification reagent | | |
| A15678 | Triethanolamine hydrochloride, 99+%  [2,2',2''-Nitrilotriethanol hydrochloride, Tris(2-hydroxyethyl)amine hydrochloride] [637-39-8], (HOCH ₂ CH ₂) ₃ N·HCl, F.W. 185.65, m.p. 177-179°, Merck 14,9665 , EINECS 211-284-2, RTECS KL9346500, BRN 3909940, MDL MFCD00012596, † | 250g 1kg 5kg |
| Application(s): Protein purification reagent | | |
| A17318 | Triethylamine hydrochloride, 98%  [Triethylammonium chloride] [554-68-7], (CH ₃ CH ₂) ₃ N·HCl, F.W. 137.65, m.p. ca 260° dec., d. 1.07, EINECS 209-067-2, RTECS YE2111500, BRN 3906409, MDL MFCD00012500, † ! H:H302-H315-H319-H335, P:P280H-P305+P351+P338 | 250g 1kg |
| Application(s): Protein purification reagent | | |
| Triethylammonium chloride , see Triethylamine hydrochloride, A17318, p. 376 | | |
| L04128 | Triethylene glycol dimethyl ether, 99%  [Triglyme] [112-49-2], CH ₃ O(CH ₂ CH ₂ O) ₂ CH ₃ , F.W. 178.23, m.p. -45°, b.p. 215-216°, f.p. 113°(235°F), d. 0.986, n _D ²⁰ 1.4230, Merck 14,9692 , EINECS 203-977-3, RTECS XF0665000, BRN 1700630, MDL MFCD00008504, †  H:H360Df-EUHO19, P:P281-P201-P202-P308+P313-P405-P501a Useful aprotic solvent with chelating properties. Has been used as solvent in a simplified Wittig synthesis, with anhydrous K ₂ CO ₃ as base and the phosphonium salt, such as Methyltriphenylphosphonium bromide, A15878 , acting as both reactant and phase-transfer catalyst: <i>Synth. Commun.</i> , 22 , 513 (1992). | 100g 500g 2.5kg |
| A16128 | Triethylenetetramine, tech. 60%, balance branched and cyclic triethylenetetramines  [112-24-3], H ₂ NCH ₂ CH ₂ (NHCH ₂ CH ₂) ₂ NH ₂ , F.W. 146.24, m.p. ca -35°, b.p. ca 267°, f.p. 122°(252°F), d. 0.982, n _D ²⁰ 1.4980, Merck 14,9663 , UN2259, EINECS 203-950-6, RTECS YE6650000, BRN 6054448, MDL MFCD00008169, †  ! H:H314-H312-H317-H412, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 500ml 2.5L |
| Application(s): Catalyzes the hydrolysis of N-terminal peptide bonds | | |
| J63112 | Triflumuron, 98+% [Trifluron, 2-Chloro-N-[[[4-(trifluoromethoxy)phenyl]amino]carbonyl]benzamide] [64628-44-0], C ₁₅ H ₁₀ ClF ₃ N ₂ O ₅ , F.W. 358.70, Solid, m.p. 198°, Merck 14,9678 , EINECS 264-980-3, RTECS CV2474000, BRN 2776684, MDL MFCD00072496 | 10g 25g 100g |
| Application(s): Inhibits uridine incorporation into RNA | | |
| A14365 | Trifluoroacetic acid, biochemical grade, 99.5+%  [76-05-1], CF ₃ CO ₂ H, F.W. 114.02, m.p. -15°, b.p. 72-73°, d. 1.480, n _D ²⁰ 1.2840, Merck 14,9681 , Fieser 1,1219 , 6,613 11,557, 15,338 17,369 18,375 20,395 21,446 , UN2699, EINECS 200-929-3, RTECS AJ9625000, BRN 742035, MDL MFCD00004169, †  ! H:H314-H332-H412, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 50g 250g 1kg |
| Application(s): Used to cleave peptide blocking groups | | |
| A10788 | 2,2,2-Trifluoroethanol, 99+% [Trifluoroethyl alcohol] [75-89-8], CF ₃ CH ₂ OH, F.W. 100.04, m.p. -44°, b.p. 74-75°, f.p. 29°(84°F), d. 1.391, n _D ²⁰ 1.2900, UN2929, EINECS 200-913-6, RTECS KM5250000, BRN 1733203, MDL MFCD00004672, †    H:H301-H311-H331-H318-H226-H361F-H315-H335, P:P260-P280-P305+P351+P338-P304+P340-P310 Useful ionizing solvent, see: <i>Tetrahedron Lett.</i> , 2335 (1974), and references therein. Good solvent for oligopeptides with potential as a cosolvent along with proton acceptors such as DMF for peptide coupling reactions: <i>Tetrahedron Lett.</i> , 33 , 7007 (1992). Compare 1,1,1,3,3,3-Hexafluoro-2-propanol, A12747 . Effective solvent for uncatalyzed epoxidations of alkenes with hydrogen peroxide (caution! 60%): <i>Synlett</i> , 248 (2001). For a review of fluorinated alcohols as solvents for selective and clean reactions, see: <i>Synlett</i> , 18 (2004). Trifluoroethyl esters have also found use as active esters in peptide coupling; see, for example: <i>J. Chem. Soc., Perkin 1</i> , 2867 (1996). Reacts with triphenylphosphine dibromide to give the bis(trifluoroethoxy)phosphorane, which converts alcohols to trifluoroethyl ethers, carboxylic acids to trifluoroethyl esters and aldehydes to bis(trifluoroethyl) acetals: <i>J. Org. Chem.</i> , 45 , 5052 (1980). | 50g 100g 500g 1kg |

The stereodirecting effect of the MEM group (see **2-Methoxyethoxymethyl chloride, L01050**) has been exploited by Percy *et al* in the formation of a new fluorine-containing acyl anion equivalent: **Tetrahedron, 51, 9201 (1995)**:



Claisen or Wittig rearrangements of the derived difluoroallyl alcohols can be used in routes to molecules containing a CF₂ group: **Tetrahedron, 51, 11327 (1995)**; *J. Org. Chem.*, **61, 166 (1996)**, or to monofluorinated vinylic compounds: **Tetrahedron Lett.**, **37, 5183 (1996)**.

Trifluoroethyl alcohol, see **2,2,2-Trifluoroethanol, A10788**, p. 376
2-[3-(Trifluoromethyl)anilino]nicotinic acid, see **Niflumic acid, 99+%**, J60489, p. 302
N-[3-(Trifluoromethyl)phenyl]anthranilic acid, see **Flufenamic acid, B23583**, p. 222

| | | | |
|---------------|--|---|-----------|
| L10465 | 1-(2-(Trifluoromethyl)phenyl)imidazole, 98+% ▲ <i>[TRIM]</i> [25371-96-4], C ₁₀ H ₇ F ₃ N ₂ , F.W. 212.18, m.p. 50-53°, b.p. 75°/0.025mm, BRN 3955637, MDL MFCD00041206 |  | 1g |
|---------------|--|---|-----------|

! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a


Application(s): Potent nitric oxide synthase inhibitor

2-(α,α,α-Trifluoro-m-toluidino)nicotinic acid, see **Niflumic acid, 99+%**, J60489, p. 302

Trifluron, see **Triflumuron, 98+%**, J63112, p. 376

Triglycine, see **Glycylglycylglycine, A13778**, p. 237


Triglyme, see **Triethylene glycol dimethyl ether, L04128**, p. 376

| | | | |
|---------------|--|---|--------------------------------------|
| B20303 | 1,8,9-Trihydroxyanthracene, 97% <i>[Dithranol]</i> [1143-38-0], C ₁₄ H ₁₀ O ₃ , F.W. 226.23, m.p. 177-181°, Merck 14,684 , EINECS 214-538-0, RTECS CB1225000, BRN 2054360, MDL MFCD00001250 |  | 1g 5g 25g |
|---------------|--|---|--------------------------------------|

! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a

Application(s): Inhibits leukotriene biosynthesis

1,3,5-Trihydroxybenzene, see **Phloroglucinol, B25502**, p. 318


| | | | |
|---------------|--|---|---|
| B24887 | 3,4,5-Trihydroxybenzoic acid, anhydrous, 99% ▲ ■ <i>[Gallic acid]</i> [149-91-7], C ₇ H ₆ O ₅ , F.W. 170.12, m.p. ca 251° dec., d. 1.694, Merck 14,4345 , EINECS 205-749-9, RTECS LW7525000, BRN 2050274, MDL MFCD00002510, † |  | 250g 1kg 5kg |
|---------------|--|---|---|

! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a


Application(s): Organic acid used as a standard for determining phenols in the Folin-Ciocalteu assay

2-(3,4,5-Trihydroxybenzylidene)malononitrile, see **Tyrphostin A25, 99+%**, J62936, p. 386

3,4,5-Trihydroxy-1-cyclohexene-1-carboxylic acid, see (-)-**Shikimic acid, L04848**, p. 342

| | | | |
|---------------|--|---|-------------------------|
| L09834 | 4',5,7-Trihydroxyflavanone, 97% <i>[Naringenin]</i> [67604-48-2], C ₁₅ H ₁₂ O ₅ , F.W. 272.26, m.p. 248-251°, Merck 14,6424 , EINECS 266-769-1, RTECS DJ2981530, MDL MFCD00006844 |  | 2g 10g |
|---------------|--|---|-------------------------|


! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a


| | | | |
|---------------|---|--|-----------------------------|
| L15041 | 4',5,7-Trihydroxyflavone, 97% <i>[Apigenin]</i> [520-36-5], C ₁₅ H ₁₀ O ₅ , F.W. 270.24, m.p. ca 315° dec., Merck 14,730 , EINECS 208-292-3, RTECS LK9276000, BRN 262620, MDL MFCD00006831 |  | 25mg 100mg |
|---------------|---|--|-----------------------------|

! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a


Application(s): Nonmutagenic flavonoid shown to inhibit cell proliferation, angiogenesis, and protein kinase. Also induces apoptosis in breast cancer cells

2',4',6'-Trihydroxy-3-(4-hydroxyphenyl)propiophenone, see **Phloretin, L10991**, p. 318

| | | | |
|---------------|---|--|------------------------------|
| L14171 | 4',5,7-Trihydroxyisoflavone, 97% <i>[Genistein]</i> [446-72-0], C ₁₅ H ₁₀ O ₅ , F.W. 270.24, m.p. ca 300°, Merck 14,4391 , EINECS 207-174-9, RTECS NR2392000, BRN 263823, MDL MFCD00016952, † Tyrosine kinase inhibitor: <i>J. Biol. Chem.</i> , 262, 5592 (1987) . |  | 100mg 500mg |
|---------------|---|--|------------------------------|

| | | | |
|---------------|---|--|---|
| J63241 | 4',5,7-Trihydroxyisoflavone, 99+% <i>[Genistein]</i> [446-72-0], C ₁₅ H ₁₀ O ₅ , F.W. 270.24, Powder, m.p. ca 300°, Merck 14,4391 , EINECS 207-174-9, RTECS NR2392000, BRN 263823, MDL MFCD00016952, † |  | 100mg 1g 10g |
|---------------|---|--|---|



Application(s): Inhibitor of tyrosine protein kinase

| | | | |
|---------------|---|--|--------------------------------------|
| B20528 | 3',5,7-Trihydroxy-4'-methoxyflavanone, 97% <i>[Hesperetin, 4'-Methoxy-3',5,7-trihydroxyflavanone]</i> [520-33-2], C ₁₆ H ₁₄ O ₆ , F.W. 302.30, m.p. 227-232°, Merck 14,4670 , EINECS 208-290-2, BRN 309850, MDL MFCD00075646 |  | 1g 5g 25g |
|---------------|---|--|--------------------------------------|

! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a

| Stock # | Description | Size |
|---------------|---|--|
| | 3',5,7-Trihydroxy-4'-methoxyflavone 7-rutinoside , see Diosmin, J62073, p. 198 (2S,3R)-2-(3,4,5-Trihydroxyphenyl)-3,4-dihydro-1(2H)-benzopyran-3,5,7-triol , see (-)-Gallicocatechin, J60731, p. 230 (2S,3R)-2-(3,4,5-Trihydroxyphenyl)-3,4-dihydro-1(2H)-benzopyran-3,5,7-triol 3-(3,4,5-trihydroxybenzoate) , see (-)-Gallicocatechin gallate, J62740, p. 230 | |
| J63312 | 3,3',5'-Triiodo-L-thyronine sodium salt [Liothyronine sodium salt] [55-06-1], C ₁₅ H ₁₁ I ₃ NNaO ₄ , F.W. 672.96, Powder, m.p. 205°, Merck 14,5510, EINECS 200-223-5, RTECS YP2836500, BRN 8179867, MDL MFCD00002594 ! H:H302-H312-H332, P:P261-P280-P302+P352-P304+P340-P322-P501a | 500mg 1g |
| L09585 | Triisopropylsilane, 98% [TIS] [6485-79-6], [(CH ₃) ₂ CH] ₃ SiH, F.W. 158.36, b.p. 166°, f.p. 35°(95°F), d. 0.773, n _D ²⁰ 1.4340, UN1993, BRN 1733718, MDL MFCD00009657 ! H:H226-H315-H319-H335, P:P210-P241-P303+P361+P353-P305+P351+P338-P405-P501a Selective silylation of primary OH groups in the presence of secondary has been carried out with this reagent in combination with CsF and imidazole: <i>J. Organomet. Chem.</i> , 282 , 155 (1985). Triethylsilane and triisopropylsilane have been studied as cation scavengers in the deprotection of peptides with TFA, and were found to give good results, with triisopropylsilane being particularly effective in trapping trityl cations in the TFA deprotection of cysteine containing peptides. The use of triisopropylsilane minimizes the risk of reduction of the indole nucleus in tryptophan-containing peptides: <i>Tetrahedron Lett.</i> , 30 , 2739 (1989). | 5g 25g 100g |
| | 3,7,12-Triketocholic acid , see Dehydrocholic acid, A19666, p. 176 | |
| J62962 | Trilaurin [Glyceryl tridodecanoate, 1,2,3-Tridodecanoylglycerol] [538-24-9], [C ₁₃ (CH ₂) ₁₀ COOCH ₂] ₃ CHOCO(CH ₂) ₁₀ CH ₃ , F.W. 639.01, Powder, m.p. 47°, EINECS 208-687-0, BRN 1730452, MDL MFCD00026559, † | 25g |
| | TRIM , see 1-(2-Trifluoromethylphenyl)imidazole, L10465, p. 377 | |
| J63053 | Trimethoprim [2,4-Diamino-5-(3,4,5-trimethoxybenzyl)pyrimidine] [738-70-5], C ₁₆ H ₁₈ N ₄ O ₃ , F.W. 290.32, Powder, m.p. 199-203°, Merck 14,9709, EINECS 212-006-2, RTECS UV8225000, BRN 625127, MDL MFCD00036761 | 1g 5g 25g |
| | Application(s): An antibacterial and inhibitor of formylation. Dihydrofolate reductase inhibitor with selectivity for the prokaryote enzyme | |
| J65567 | cis-3,4',5-Trimethoxy-3'-aminostilbene [(Z)-5-(3,5-Dimethoxystyryl)-2-methoxyaniline] [586410-12-0], C ₁₇ H ₁₉ NO ₃ , F.W. 285.34, Oil ! H:H302, P:P264-P270-P301+P312-P330-P501 | 10mg |
| | 3,4,5-Trimethoxybenzoic acid 8-(diethylamino)octyl ester hydrochloride , see 8-(Diethylamino)octyl 3,4,5-trimethoxybenzoate hydrochloride, 97%, J62528, p. 188 α,α,4-Trimethyl-3-cyclohexene-1-methanol , see α-Terpineol, 16285, p. 360 3,7,11-Trimethyl-2,6,10-dodecatrien-1-ol , see Farnesol, A19316, p. 218 Trimethylenediamine , see 1,3-Diaminopropane, A11932, p. 183 1,3,3-Trimethyl-2-oxabicyclo[2.2.2]octane , see 1,8-Cineole, A12269, p. 163 | |
| J63226 | 4,5',8-Trimethylpsoralen, 99% [Trioxsalen, TMP] [3902-71-4], C ₁₄ H ₁₀ O ₃ , F.W. 228.25, Powder, m.p. 229-231°, Merck 14,9735, UN1759, EINECS 223-459-0, RTECS LV1576000, BRN 221723, MDL MFCD00005010, † ! H:H314-H351, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 1g 5g |
| | Application(s): Photochemical crosslinker of DNA. Useful for treatment of psoriasis | |
| | 2,4,6-Trimethylpyridine , see 2,4,6-Collidine, A11058, p. 167 Trimethyl-n-tetradecylammonium bromide , see (1-Tetradecyl)trimethylammonium bromide, L10294, p. 362 | |
| J65391 | 2,4,6-Trimethyl-N-[2-(trifluoromethyl)phenyl]benzenesulfonamide [o-3M3FBS] [313981-55-4], C ₁₆ H ₁₆ F ₃ NO ₂ S, F.W. 343.36, Powder ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10mg 50mg |
| J65999 | 2,4,6-Trimethyl-N-[3-(trifluoromethyl)phenyl]benzenesulfonamide [m-3M3FBS] [200933-14-8], C ₁₆ H ₁₆ F ₃ NO ₂ S, F.W. 343.36, Powder, MDL MFCD00095824 ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10mg 50mg |
| | 1,3,7-Trimethylxanthine , see Caffeine, A10431, p. 142 | |
| J62819 | Trimyrustin, 95% [Glyceryl trimyristrate, 1,2,3-Tritetradecanoylglycerol] [555-45-3], [C ₁₄ (CH ₂) ₁₂ COOCH ₂] ₃ CHOCO(CH ₂) ₁₂ CH ₃ , F.W. 723.16, Powder, m.p. 56-57°, Merck 14,9724, EINECS 209-099-7, BRN 1718242, MDL MFCD00036229, † | 25g |
| | 1,2,3-Tri(cis-9-octadecenyl)glycerol , see Triolein, J62419, p. 379 | |

| Stock # | Description | Size |
|---------|--|--------------------|
| J62419 | Triolein [1,2,3-Tri(cis-9-octadecenoyl)glycerol, Glycerol trioleate] [122-32-7], (C ₅₇ H ₁₀₄ COOCH ₂) ₃ CHOCOC ₁₇ H ₃₃ , F.W. 885.45, Liquid, b.p. 235-240°/18mm, f.p. 330°(626°F), d. 0.91, n _D ²⁰ 1.468, Merck 14,9732, EINECS 204-534-7, RTECS RG1936500, BRN 1718692, MDL MFCD00137563, † | 25g 100g |
| | 3,7,12-Trioxo-5β-cholan-24-oic acid , see Dehydrocholic acid, A19666, p. 176 Trioxsalen , see 4,5',8-Trimethylpsoralen, 99%, J63226, p. 378 Tripalmitin , see Glycerol tripalmitate, A10922, p. 236 | |
| J64760 | Tripeptidylpeptidase Inhibitor ▲ [H-AAF-CMK, TPPII Inhibitor] [184901-82-4], C ₁₆ H ₂₂ ClN ₃ O ₃ , F.W. 453.90, Solid | 5mg 10mg |
| | N-(Triphenylmethyl)glycine , see N-Tritylglycine, L09095, p. 383 | |
| A10870 | 2,3,5-Triphenyl-2H-tetrazolium chloride, 98% ▲■ [TTC] [298-96-4], C ₁₉ H ₁₅ ClN ₄ , F.W. 334.81, m.p. ca 250° dec., Merck 14,9744, EINECS 206-071-6, RTECS XF8100000, BRN 3923356, MDL MFCD00011963, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Reagent for detection of reducing sugars. Oxidizing agent, reduced to the colored formazan, capable of introducing a -hydroxyl substituent into steroidal enones: <i>J. Chem. Soc., Perkin 1</i> , 2687 (1988). | 10g 50g 250g |
| | Application(s): Useful indicator for reducing substances | |
| | Triphosphopyridine nucleotide monosodium salt , see β-Nicotinamide adenine dinucleotide phosphate monosodium salt, 44126, p. 301 2,4,6-Tri(2-pyridyl)-s-triazine , see 2,4,6-Tri(2-pyridyl)-1,3,5-triazine, A17201, p. 379 | |
| A17201 | 2,4,6-Tri(2-pyridyl)-1,3,5-triazine, 98% [2,4,6-Tri(2-pyridyl)-s-triazine] [3682-35-7], C ₁₈ H ₁₂ N ₆ , F.W. 312.34, m.p. 248-252°, Merck 14,9750, EINECS 222-965-9, RTECS XZ2050000, BRN 282581, MDL MFCD00006045, † ! H:H315-H319-H335, P:P261-P305-P351+P338-P302+P352-P321-P405-P501a Reagent for determination of Fe: <i>Anal. Chem.</i> , 31 , 1862 (1959). | 5g 25g 100g |
| | Application(s): Reagent for the colorimetric determination of iron | |
| | TRIS , see Tris(hydroxymethyl)aminomethane, Electrophoresis Grade, 99.5%, J61016, p. 382 | |
| J61787 | TRIS, 0.5M buffer soln., pH 6.5 [77-86-1], Liquid, † | 500ml 1L |
| J63735 | TRIS, 0.5M buffer soln., pH 6.8 [77-86-1], Liquid, † | 500ml 1L |
| J61213 | TRIS, 0.5M buffer soln., pH 7.0 [77-86-1], Liquid, † | 500ml 1L |
| J61009 | TRIS, 0.5M buffer soln., pH 7.2 [77-86-1], Liquid, † | 500ml 1L |
| J62778 | TRIS, 0.5M buffer soln., pH 7.4 [77-86-1], Liquid, † | 500ml 1L |
| J61141 | TRIS, 0.5M buffer soln., pH 7.5 [77-86-1], Liquid, † | 500ml 1L |
| J62736 | TRIS, 0.5M buffer soln., pH 7.6 [77-86-1], Liquid, † | 500ml 1L |
| J61944 | TRIS, 0.5M buffer soln., pH 7.8 [77-86-1], Liquid, † | 500ml 1L |
| J62552 | TRIS, 0.5M buffer soln., pH 8.0 [77-86-1], Liquid, † | 500ml 1L |
| J62944 | TRIS, 0.5M buffer soln., pH 8.2 [77-86-1], Liquid, † | 500ml 1L |
| J61537 | TRIS, 0.5M buffer soln., pH 8.4 [77-86-1], Liquid, † | 500ml 1L |
| J62131 | TRIS, 0.5M buffer soln., pH 8.5 [77-86-1], Liquid, † | 500ml 1L |
| J62287 | TRIS, 0.5M buffer soln., pH 8.6 [77-86-1], Liquid, † | 500ml 1L |










| Stock # | Description | Size |
|---------|---|-------------|
| J61144 | TRIS, 0.5M buffer soln., pH 8.8 [77-86-1], Liquid, † | 500ml 1L |
| J62551 | TRIS, 0.5M buffer soln., pH 9.0 [77-86-1], Liquid, † | 500ml 1L |
| J63134 | TRIS, 0.5M buffer soln., pH 9.5 [77-86-1], Liquid, † | 500ml 1L |
| J60381 | TRIS, 1.0M buffer soln., pH 6.5 [77-86-1], Liquid, † | 1L |
| J62264 | TRIS, 1.0M buffer soln., pH 6.5, 0.2 micron filtered [77-86-1], Liquid, † | 500ml |
| J63831 | TRIS, 1.0M buffer soln., pH 6.8 [77-86-1], Liquid, † ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | 1L |
| J62657 | TRIS, 1.0M buffer soln., pH 7.0 [77-86-1], Liquid, † | 1L |
| J60822 | TRIS, 1.0M buffer soln., pH 7.0, 0.2 micron filtered [77-86-1], Liquid, † | 500ml |
| J62186 | TRIS, 1.0M buffer soln., pH 7.2 [77-86-1], Liquid, † | 1L |
| J60202 | TRIS, 1.0M buffer soln., pH 7.4 [77-86-1], Liquid, † | 1L |
| J60636 | TRIS, 1.0M buffer soln., pH 7.5 [77-86-1], Liquid, † ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | 1L |
| J62993 | TRIS, 1.0M buffer soln., pH 7.5, 0.2 micron filtered [77-86-1], Liquid, † | 500ml |
| J61036 | TRIS, 1.0M buffer soln., pH 7.6 [77-86-1], Liquid, † | 1L |
| J61579 | TRIS, 1.0M buffer soln., pH 7.8 [77-86-1], Liquid, † | 1L |
| J62726 | TRIS, 1.0M buffer soln., pH 8.0 [77-86-1], Liquid, † | 1L |
| J61429 | TRIS, 1.0M buffer soln., pH 8.0, 0.2 micron filtered [77-86-1], Liquid, † | 500ml |
| J61798 | TRIS, 1.0M buffer soln., pH 8.2 [77-86-1], Liquid, † | 1L |
| J62577 | TRIS, 1.0M buffer soln., pH 8.4 [77-86-1], Liquid, † ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | 1L |
| J61038 | TRIS, 1.0M buffer soln., pH 8.5, 0.2 micron filtered [77-86-1], Liquid, † | 500ml |
| J61066 | TRIS, 1.0M buffer soln., pH 8.6 [77-86-1], Liquid, † ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | 1L |
| J60452 | TRIS, 1.0M buffer soln., pH 8.8 [77-86-1], Liquid, † | 1L |
| J62085 | TRIS, 1.0M buffer soln., pH 9.0 [77-86-1], Liquid, † | 1L |
| J60707 | TRIS, 1.0M buffer soln., pH 9.0, 0.2 micron filtered [77-86-1], Liquid, † ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | 500ml |







| Stock # | Description | Size |
|---------|--|-------------------|
| J62084 | TRIS, 1.0M buffer soln., pH 9.5 [77-86-1], Liquid, † ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | 1L |
| | TRIS hydrochloride , see Tris(hydroxymethyl)aminomethane hydrochloride, A11379, p. 382 | |
| J62560 | TRIS-acetate-SDS running buffer (10X), pH 8.3 Liquid, Note: 500mM Tris base, 500mM Tricine, 3.5mM SDS, pH 8.3. Application(s): Running buffer for TRIS-acetate gels | 500ml 1L |
| J62664 | TRIS-buffered saline (TBS, 10X, high salt) pH 7.4 [77-86-1], Liquid, Note: Contains 250mM Tris, 5M NaCl, pH 7.4., † | 500ml 1L 2L |
| J60102 | TRIS-buffered saline (TBS, 10X, low salt) pH 8.0 [77-86-1], Liquid, Note: 250mM Tris, 0.5M NaCl, pH 8.0., † | 1L 2L 4L |
| J62938 | TRIS-buffered saline (TBS, 10X) pH 7.4, for Western blot [77-86-1], Liquid, Note: 250mM Tris, 1.5M NaCl, pH 7.4., † Application(s): For Western blot washing. | 1L 2L 4L |
| J60764 | TRIS-buffered saline (TBS, 10X) pH 7.4 Liquid, Note: 250mM Tris, 27mM potassium chloride, 1.37M sodium chloride, pH 7.4., † | 1L 2L 4L |
| J60877 | TRIS-buffered saline (TBS, 20X) pH 7.4 [77-86-1], Liquid, Note: Contains: 0.5M Tris, 54mM KCl, and 2.74M NaCl, pH 7.4, † | 1L 2L |
| J62662 | TRIS-buffered saline (TBS, 10X) pH 7.6 [77-86-1], Liquid, Note: 250mM Tris, 27mM potassium chloride, 1.37M sodium chloride, pH 7.6., † | 2L 4L |
| J62780 | TRIS-buffered saline (TBS, 10X) pH 8.0 [77-86-1], Liquid, Note: 250mM Tris, 27mM KCl, 1.37M NaCl, pH 8.0., † | 1L 2L 4L |
| J63692 | TRIS-buffered saline (TBS, 5X), with EDTA Liquid, Note: 125mM Tris, 14mM KCl, 0.68M NaCl, pH 7.4, with 50mM EDTA | 1L 2L |
| J62533 | TRIS-buffered saline (TBS, 10X), with 1% Triton® X-100 Liquid, Note: 250mM Tris, 27mM KCl, 1.37M NaCl, pH 7.4 with 1% Triton X-100 | 500ml 1L |
| J60448 | TRIS-buffered saline (TBS, 10X), with 0.5% Tween 20 Liquid, Note: 250mM Tris, 27mM KCl, 1.37M NaCl, pH 7.4 with 0.5% Tween 20 | 500ml 1L 2L |
| J63682 | TRIS-buffered saline (TBS, 20X), with 0.5% Tween 20 Liquid | 1L 2L |
| J62955 | TRIS-buffered saline (TBS, 10X), with 1% Tween 20 Liquid, Note: 250mM Tris, 27mM KCl, 1.37M NaCl, pH 7.4, with 1% Tween 20 | 500ml 1L 2L |
| J60497 | TRIS-buffered saline (TBS, 20X), with 1% Tween 20 Liquid, Note: 500mM Tris-HCl, 54mM KCl, 2.74M NaCl, pH 7.4 with 1% Tween-20 | 1L 2L |
| J61339 | TRIS-CAPS buffer (10X) Liquid, Note: Contains: 0.6M Tris, and 0.4M CAPS. pH 9.6 Anode, pH 9.5 Cathode., † Application(s): For blot transfer Tris(carboxymethyl)amine, see Nitrilotriacetic acid, 36515, p. 303 | 500ml 1L |
| J62914 | TRIS-glycine-native running buffer (10X), pH 8.5 Liquid, Note: 0.25M Tris base, 1.92M glycine, pH 8.5. ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 | 1L 2L 4L |
| J61006 | TRIS-glycine-SDS running buffer (10X), pH 8.3 Liquid, Note: 0.25M Tris base, 1.92M glycine, 1% SDS, pH 8.3., † | 1L 2L 4L |
| J61864 | TRIS-glycine native sample buffer (4X), pH 8.6 Liquid, Note: 400mM Tris HCl (pH 8.6), 40% glycerol, 0.02% bromophenol blue. ! H:H319, P:P280-P264-P305+P351+P338-P337+P313 Application(s): For preparation of protein samples for native gel electrophoresis | 25ml 50ml |

| Stock # | Description | Size |
|---------|---|---------------------|
| J62737 | TRIS-HEPES-native running buffer (10X), pH 8.0 Liquid, Note: 1M Tris base, 1M HEPES, pH 8.0. | 500ml 1L 2L |
| J61789 | TRIS-HEPES-SDS running buffer (10X), pH 8.0 Liquid, Note: 1M Tris base, 1M HEPES, 30mM SDS, pH 8.0., † ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | 500ml 1L 2L |
| | Tris(2-hydroxyethyl)amine , see Triethanolamine, L04486, p. 376 Tris(2-hydroxyethyl)amine hydrochloride , see Triethanolamine hydrochloride, A15678, p. 376 | |
| 31801 | Tris(hydroxymethyl)aminomethane, ACS, 99.8-100.1% (Assay, dried basis) ■ [2-Amino-2-hydroxymethyl-1,3-propanediol, TRIS] [77-86-1], (HOCH ₂) ₃ CNH ₂ , F.W. 121.14, Crystalline, m.p. 171-172°, b.p. 219-220°/10mm, d. 1.353, Merck 14,9772, EINECS 201-064-4, RTECS TY2900000, BRN 741883, MDL MFCD00004679, † Maximum level of impurities: Absorbance P.T., H ₂ O 2.0%, Insoluble matter 0.005%, Heavy Metals (as Pb) 5ppm, Fe 5ppm ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 50g 250g 1kg |
| J61016 | Tris(hydroxymethyl)aminomethane, Electrophoresis Grade, 99.5% [TRIS] [77-86-1], C ₃ H ₇ NO ₃ , F.W. 121.14, Crystalline powder, Merck 14,9772, EINECS 201-064-4, RTECS TY2900000, BRN 741883, MDL MFCD00004679, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | 100g 500g |
| J62569 | Tris(hydroxymethyl)aminomethane, Electrophoresis Grade, 99.9% [TRIS] [77-86-1], C ₃ H ₇ NO ₃ , F.W. 121.14, Crystalline powder, Merck 14,9772, EINECS 201-064-4, RTECS TY2900000, BRN 741883, MDL MFCD00004679, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 100g 500g 5kg |
| J61062 | Tris(hydroxymethyl)aminomethane, Molecular Biology Grade, 99.9% [TRIS] [77-86-1], C ₃ H ₇ NO ₃ , F.W. 121.14, Crystalline powder, Merck 14,9772, EINECS 201-064-4, RTECS TY2900000, BRN 741883, MDL MFCD00004679, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 100g 500g |
| J65594 | Tris(hydroxymethyl)aminomethane, ultrapure, 99.9% ■ [TRIS] [77-86-1], C ₃ H ₇ NO ₃ , F.W. 121.14, Crystalline powder, m.p. 167-172°, b.p. 219-220°, d. 1.35, Merck 14,9772, EINECS 201-064-4, RTECS TY2900000, BRN 741883, MDL MFCD00004679, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1kg 5kg |
| J63636 | Tris(hydroxymethyl)aminomethane hydrochloride, 1M stock soln, pH 8.0 [TRIS-HCl] [1185-53-1], Liquid | 1L |
| J62848 | Tris(hydroxymethyl)aminomethane hydrochloride, 1M soln., pH 7,4, RNase free [TRIS-HCl] [1185-53-1], Liquid, Note: 1M TRIS-HCl, † | 250ml |
| J60080 | Tris(hydroxymethyl)aminomethane hydrochloride, 1M soln., pH 8.0, RNase free [Tris-HCl] [1185-53-1], Liquid, Note: 1M TRIS-HCl, † | 250ml |
| A11379 | Tris(hydroxymethyl)aminomethane hydrochloride, 99+% ■ [2-Amino-2-hydroxymethyl-1,3-propanediol hydrochloride, TRIS hydrochloride] [1185-53-1], (HOCH ₂) ₃ CNH ₂ ·HCl, F.W. 157.60, m.p. ca 152° dec., EINECS 214-684-5, BRN 3675235, MDL MFCD00012590, † Biological buffer. | 50g 250g 1kg |
| | Tris(hydroxymethyl)methylamine hydrochloride , see Tris(hydroxymethyl)aminomethane hydrochloride, A11379, p. 382 N-[Tris(hydroxymethyl)methyl]-2-aminoethanesulfonic acid , see TES, B21819, p. 360 N-[Tris(hydroxymethyl)methyl]-2-aminoethanesulfonic acid sodium salt , see TES sodium salt, J62706, p. 361 3-[Tris(hydroxymethyl)methyl]amino-1-propanesulfonic acid , see TAPS, A17754, p. 358 N-(Tris(hydroxymethyl)methyl)glycine , see Tricine, A14695, p. 375 | |
| 36439 | Trisodium citrate dihydrate, ACS, 99.0% min [6132-04-3], Na ₃ C ₆ H ₅ O ₇ ·2H ₂ O, F.W. 294.10 (258.07anhy), Crystalline, m.p. 150° -2H ₂ O, Merck 14,8602, Solubility: Soluble in water. Insoluble in alcohol, EINECS 200-675-3, BRN 6104939, MDL MFCD00150031, † Maximum level of impurities: pH of a 5% solution 7.0-9.0 at 25°, Insoluble matter 0.005%, Cl 0.003%, SO ₄ 0.005%, NH ₃ 0.003%, Ca 0.005%, Heavy Metals (as Pb) 5ppm, Fe 5ppm | 500g 2kg |
| | Application(s): Sequestering agent, buffer, photography | |
| | Trisodium phosphate , see Sodium phosphate, tribasic, 13438, p. 347 Trisodium phosphate dodecahydrate , see Sodium phosphate dodecahydrate, A15713, p. 347 | |





| Stock # | Description | Size |
|---------|---|------------------------|
| J63948 | TRIS-Tricine-SDS kit (10X) Liquid, Note: Contains one each of Tris anode buffer and Tris-Tricine-SDS cathode buffer for PAGE. | 500ml 1L |
| J63375 | TRIS-Tricine-SDS running buffer (10X), anode buffer, pH 8.9 Liquid, Note: 2M Tris-HCl, pH 8.9. ! H:H302-H319, P:P280-P264-P305+P351+P338-P301+P312-P337+P313-P501 Application(s): For TRIS-Tricine gel electrophoresis | 500ml 1L |
| J60992 | TRIS-Tricine-SDS running buffer (10X), cathode buffer, pH 8.3 Liquid, Note: 1M Tris base, 1M Tricine, 1% SDS, pH 8.3. Application(s): For TRIS-Tricine SDS gel electrophoresis TRITC, see 5(6)-Tetramethylrhodamine isothiocyanate, J62258, p. 365 1,2,3-Tritetradecanoylglycerol, see Trimyristin, 95%, J62819, p. 378 Triton® B, see Benzyltrimethylammonium hydroxide, A14927, p. 123 | 500ml 1L |
| A16046 | Triton® X-100 [Octoxynol-9, Polyethylene glycol tert-octylphenyl ether] [9002-93-1], F.W. ca. 625, m.p. ca 5°, b.p. >250°, f.p. 180°(356°F), d. 1.061, n _D ²⁰ 1.4900, Merck 14,6761, RTECS MD0907600, MDL MFCD00132505, † ! H:H302-H319-H412, P:P280d-P305+P351+P338-P337+P313 Nonionic detergent and emulsifier. Application(s): Detergent, equivalent to Nonidet P-40 | 100ml 500ml 2.5L |
| J62289 | Triton® X-100 lysis buffer, pH 7.4 Liquid, Note: Contains 50mM Tris-HCl (pH 7.4), 150mM NaCl, 1% Triton X-100, and 5mM EDTA., † | 250ml 500ml |
| J63653 | Triton® X-100 lysis buffer (2X), pH 7.4 Liquid, Note: 100mM Tris-HCl (pH 7.4), 300mM NaCl, 2% Triton X-100, 10mM EDTA. | 125ml 250ml |
| J62526 | Triton® X-100 lysis buffer-2, pH 8.0 Liquid, Note: 50mM Tris-HCl (pH 8.0), 150mM NaCl, 1% Triton X-100, 5mM EDTA., † | 250ml 500ml |
| J63866 | Triton® X-100 lysis buffer with glycerol (2X), pH 7.4 Liquid, Note: Contains 100mM Tris-HCl (pH 7.4), 300mM NaCl, 2% Triton X-100, 10mM EDTA, and 10% glycerol. | 125ml 250ml |
| L09095 | N_ε-Trityl-Nβ-Fmoc-L-homoglutamine , see L-3-(Fmoc-amino)-N-trityladipic acid 6-amide, H52195, p. 225 N-Tritylglycine, 97% [N-(Triphenylmethyl)glycine, Trt-Gly-OH] [5893-05-0], (C ₂₆ H ₂₅) ₃ CNHCH ₂ CO ₂ H, F.W. 317.39, m.p. 170-174° dec., BRN 1998718, MDL MFCD00004276 | 5g 25g 100g |
| J64810 | TrkA Inhibitor ▲ [(Z)-4-(((2-Oxoindolin-3-ylidene)methyl)amino)benzenesulfonamide] [388626-12-8], C ₁₅ H ₁₃ N ₃ O ₂ S, F.W. 315.40, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1mg 5mg |
| J62583 | Tromethamine hydrochloride , see Tris(hydroxymethyl)aminomethane hydrochloride, A11379, p. 382 3-Tropanyl-3,5-dichlorobenzoate, 99+% [MDL-72222, Bemesepron] [40796-97-2], C ₁₅ H ₁₇ Cl ₂ NO ₂ , F.W. 314.21, Powder, RTECS DG7580000 Application(s): 5-HT ₃ serotonin antagonist | 50mg |
| J62807 | 3-Tropanylindole-3-carboxylate hydrochloride [Tropisetron hydrochloride] [105826-92-4], C ₁₇ H ₂₀ N ₂ O ₂ ·HCl, F.W. 320.82, Powder, Merck 14,9783, MDL MFCD00210221 Application(s): A selective 5-HT ₃ serotonin receptor antagonist | 100mg 1g |
| B22040 | DL-Tropic acid, 99% [DL-3-Hydroxy-2-phenylpropionic acid] [552-63-6], C ₉ H ₁₀ O ₃ , F.W. 166.18, m.p. 117-119°, Merck 14,9779, EINECS 208-465-3, BRN 2209199, MDL MFCD00004255, † | 10g 50g |
| J61132 | Tropicamide, 99+% [N-Ethyl-2-phenyl-N-(4-pyridylmethyl)hydracrylamide, Ro 1-7683] [1508-75-4], C ₁₇ H ₂₀ N ₂ O ₂ , F.W. 284.35, Powder, m.p. 98°, Merck 14,9780, EINECS 216-140-2, RTECS CY1487860, MDL MFCD00058580 ! ⚠ H:H302-H312-H332-H315-H319-H334-H317-H335, P:P285-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): A muscarinic antagonist | 1g |
| J64677 | Tropine DL-tropate, 99% ▲ [DL-Hyoscyamine, Atropine] [51-55-8], C ₁₇ H ₂₃ NO ₃ , F.W. 289.37, Powder, Merck 14,875, UN1544, EINECS 200-104-8, RTECS CK0700000, BRN 91260, MDL MFCD00022622, † ⚠ H:H300-H330, P:P301+P310-P304+P340-P320-P330-P405-P501 Application(s): Reduces brain levels of acetylcholine | 1g 5g 25g |





| Stock # | Description | Size |
|---------------|--|---|
| | Tropisetron hydrochloride , see 3-Tropanylindole-3-carboxylate hydrochloride, J62807, p. 383 | |
| A11299 | Tropolone, 98% ■ [2-Hydroxy-2,4,6-cycloheptatrien-1-one] [533-75-5], C ₇ H ₆ O ₂ , F.W. 122.12, m.p. 50-55°, b.p. 115°/12mm, f.p. >110°(230°F), EINECS 208-577-2, RTECS GU4075000, BRN 1904978, MDL MFCD00004158 Reagent for Rh: <i>Mikrochim. Acta</i> , 459 (1972). Non-benzenoid aromatic system, analogous to phenol. For a review of 7-membered conjugated cyclic systems, see: <i>Chem. Rev.</i> , 73 , 293 (1973). For a study of the role of chelation and resonance in the intrinsic acidity and basicity of tropolone, see: <i>J. Org. Chem.</i> , 62 , 3200 (1997). |  1g 5g 25g |
| | Application(s): A non-benzenoid aromatic compound | |
| A18600 | Trypan Blue, dye content >60% [C.I. 23850, Direct Blue 14] [72-57-1], C ₂₄ H ₂₄ N ₈ Na ₄ O ₁₁ S ₄ , F.W. 960.82, m.p. >300° Merck 14.9792 , EINECS 200-786-7, RTECS QJ6475000, MDL MFCD00003969, † H:H350-H361, P:P281-P201-P202-P308+P313-P405-P501a |  25g 100g 500g |
| | Application(s): Used in dye exclusion studies in cell culture | |
| J63688 | Trypsin, bovine pancreas [EC 3.4.21.4, Peptidyl peptide hydrolase] [9002-07-7], Powder, Merck 14,9795 , EINECS 232-650-8, RTECS YN5075000, MDL MFCD00082094, Note: Minimum 2500 USP units/mg. One unit causes a decrease in absorbance at 253nm of 0.003 per minute at 25 C., † H:H334-H335-H315-H319, P:P285-P305+P351+P338-P302+P352-P321-P405-P501a | 1g 10g |
| | Application(s): A pancreatic serine protease | |
| J63993 | Trypsin 1:250, porcine pancreas [EC 3.4.21.4] [9002-07-7], Powder, Merck 14,9795 , EINECS 232-650-8, RTECS YN5075000, Note: Low endotoxin. Minimum 225 units/mg. One unit causes a decrease in absorbance at 253 nm of 0.003 per minute at 25C., † H:H334-H335-H315-H319, P:P285-P305+P351+P338-P302+P352-P321-P405-P501a | 10g 50g |
| | Application(s): A pancreatic serine protease | |
| J60402 | Trypsin, porcine pancreas [EC 3.4.21.4, Trypsin IV porcine] [9002-07-7], Lyophilized Powder, 23.8 kDa, Merck 14,9795 , EINECS 232-650-8, RTECS YN5075000, MDL MFCD00082094, Note: Minimum 250 units/mg. One unit causes a decrease in absorbance at 253nm of 0.003 per minute at 25C., † H:H334-H335-H315-H319, P:P285-P305+P351+P338-P302+P352-P321-P405-P501a | 10g 50g |
| | Application(s): A pancreatic serine protease | |
| J63927 | Trypsin inhibitor, chicken egg whites [Trypsin inhibitor, ovomucoid] [9035-81-8], Powder, EINECS 232-906-9, MDL MFCD00082102 H:H334-H317, P:P285-P261-P280-P302+P352-P321-P501 | 500mg 1g 2g |
| | Application(s): Inhibits the pancreatic enzyme trypsin | |
| J60982 | Trypsin inhibitor, soybeans [9035-81-8], Powder, EINECS 232-906-9, MDL MFCD00082103 H:H334-H317, P:P285-P261-P280-P302+P352-P321-P501a | 100mg 1g |
| | Application(s): Inhibits the pancreatic enzyme trypsin | |
| L05936 | DL-Tryptophan, 99% [(+/-)-2-Amino-3-(3-indolyl)propionic acid, H-DL-Trp-OH] [54-12-6], C ₁₁ H ₁₂ N ₂ O ₂ , F.W. 204.23, m.p. ca 280° dec., [α] _D ²⁰ +31.5° (c=1 in water), RTECS YN6129200, BRN 86196, MDL MFCD00064339, † |  5g 25g 100g |
| A18426 | D-Tryptophan, 99% [(R)-2-Amino-3-(3-indolyl)propionic acid, H-D-Trp-OH] [153-94-6], C ₁₁ H ₁₂ N ₂ O ₂ , F.W. 204.23, m.p. 273° dec., [α] _D ²⁰ +31.5° (c=1 in water), EINECS 205-819-9, RTECS YN6129000, BRN 86198, MDL MFCD00005647, † |  5g 25g 100g |
| A10230 | L-Tryptophan, 99% [(S)-2-Amino-3-(3-indolyl)propionic acid, H-Trp-OH] [73-22-3], C ₁₁ H ₁₂ N ₂ O ₂ , F.W. 204.23, m.p. 280° 285°, [α] _D ²⁰ -31.5° (c=1 in water), Merck 14.9797 , EINECS 200-795-6, RTECS YN6130000, BRN 86197, MDL MFCD00064340, † |  25g 100g 500g |
| J62508 | L-Tryptophan, Cell Culture Reagent [73-22-3], C ₁₁ H ₁₂ N ₂ O ₂ , F.W. 204.23, Powder, m.p. 280-285°, Merck 14,9797 , EINECS 200-795-6, RTECS YN6130000, BRN 86197, MDL MFCD00064340, † | 10g 100g 1kg |






| Stock # | Description | Size |
|---------|--|---|
| L02555 | Tryptophol, 97% [3-(2-Hydroxyethyl)indole, 2-(3-Indolyl)ethanol] [526-55-6], C ₁₀ H ₁₁ NO, F.W. 161.20, m.p. 56-59°, b.p. 174°/2mm, f.p. 255°(491°F), Merck 14,9798, EINECS 208-393-2, RTECS KL3685000, BRN 125553, MDL MFCD00005659, † |  1g 5g |
| J62318 | TSS (Transformation & Storage Soln.), pH 6.5 Liquid, Note: Contains 85% LB medium, 10% (w/v) PEG MW 8000, 5% (v/v) DMSO, 50mM magnesium chloride, pH 6.5, sterile filtered. | 125ml 250ml |
| | Application(s): Enables preparation of competent E. coli in a single step and allows transformation of cells without heat-shock | |
| | TTC, see 2,3,5-Triphenyl-2H-tetrazolium chloride, A10870, p. 379 | |
| J60222 | D-Tubocurarine chloride △ [57-94-3], C ₂₇ H ₄₁ ClN ₂ O ₈ ·HCl, F.W. 681.65, Powder, Merck 14,9807, UN1544, EINECS 200-356-9 | 10mg 50mg |
| |  H: H300, P: P264-P270-P301+P310-P321-P405-P501a | |
| | Application(s): Competitive, non-selective nicotinic acetylcholine receptor antagonist | |
| J63904 | Tuftsins, 96% [Thr-Lys-Pro-Arg] [72103-53-8], C ₂₁ H ₄₀ N ₆ O ₈ , F.W. 500.60, Powder | 5mg |
| | Application(s): An immunomodulating peptide | |
| | Tuftsins (1-3), see Macrophage Inhibitory Peptide, J63844, p. 274 | |
| J63975 | Tulobuterol [41570-61-0], C ₁₂ H ₁₈ ClNO, F.W. 227.73, White to off-white crystalline powder, m.p. 159-163°, Merck 14,9811, RTECS DA4734170 | 1g 5g |
| |  H: H302, P: P264-P270-P301+P312-P330-P501a | |
| | Application(s): β-2-adrenergic receptor agonist | |
| J61448 | Tulobuterol hydrochloride, 98% ■ [56776-01-3], C ₁₂ H ₁₈ ClNO·HCl, F.W. 264.19, Powder, m.p. 159-163°, Merck 14,9811, RTECS DN8785000, MDL MFCD00214398 | 1g 5g |
| |  H: H302, P: P264-P270-P301+P312-P330-P501a | |
| | Application(s): β-2-adrenergic receptor agonist | |
| J62217 | Tunicamycin, 95% ▲ ▽ [11089-65-9], C ₃₈ H ₆₄ N ₄ O ₁₆ , F.W. 844.95, Powder, Merck 14,9819, UN3462, RTECS YO7980200, BRN 6888090, MDL MFCD00065709 | 10mg |
| |  H: H300-H330-H373, P: P301+P310-P304+P340-P320-P330-P405-P501a | |
| | Application(s): A mixture of homologous nucleoside antibiotics | |
| B21224 | D-Turanose, 98% [3-O-α-D-glucopyranosyl-D-fructose] [547-25-1], C ₁₂ H ₂₂ O ₁₁ , F.W. 342.30, m.p. ca 170° dec., Merck 14,9821, EINECS 208-918-5, BRN 93771, MDL MFCD00006606, † |  1g 5g |
| | Application(s): Sucrose analog not metabolized by higher plants. Carbon source for fungi and bacteria | |
| | Tween®, see Polysorbate, L15029, p. 325 | |
| J61544 | Tween 20 blocking buffer, 1% in PBS (10X) Liquid | 500ml 1L 2L |
| J60304 | Tween 20 blocking buffer, 0.5% in PBS (10X) Liquid | 500ml 1L 2L |
| J63314 | Tween 20 washing buffer, 1% in PBS (10X) Liquid | 500ml 1L 2L |
| J63596 | Tween 20 washing buffer, 0.5% in PBS (10X) Liquid | 500ml 1L 2L |
| J61419 | Tween 20 washing buffer, 1% in PBS (20X) Liquid | 1L 2L |
| J62844 | Tween 20 washing buffer, 0.5% in PBS (20X) Liquid | 1L 2L |

| Stock # | Description | Size |
|--|--|-------|
| J62633 | Tylosin tartrate, 98+% [Pharmasin, (R-(R'))-2,3-dihydroxybutanedionate Tylosin (salt)] [1405-54-5], C ₄₆ H ₇₇ NO ₁₇ ·C ₈ H ₆ O ₆ , F.W. 1066.20, Powder, EINECS 215-781-5 | 1g |
| | | 5g |
| | | 10g |
| H:H334-H317, P:P285-P261-P280-P302+P352-P321-P501 | | |
| Application(s): Macrolide antibiotic | | |
| H-L-Tyr-OH , see L-Tyrosine, Cell Culture Reagent, J63511, p. 386 | | |
| J60990 | Tyramine, 98+% [2-(4-Hydroxyphenyl)ethylamine, 4-(2-Aminoethyl)phenol] [51-67-2], C ₈ H ₁₁ NO, F.W. 137.18, Powder, m.p. 160-162°, b.p. 175-181°, Merck 14,9835, EINECS 200-115-8, RTECS SJ5950000, BRN 1099914, MDL MFCD00008193 | 1g |
| | | 5g |
| | | 25g |
| H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | | |
| Application(s): Reagent for fluorescence enzyme immunoassay | | |
| A12220 | Tyramine hydrochloride, 98% [4-Hydroxyphenethylamine hydrochloride, 2-(4-Hydroxyphenyl)ethylamine hydrochloride] [60-19-5], C ₈ H ₁₁ NO·HCl, F.W. 173.65, m.p. 271-274°, Merck 14,9835, EINECS 200-462-5, RTECS SJ6050000, BRN 3627058, MDL MFCD00012901, † | 5g |
| | | 100g |
| | | |
| H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | | |
| Application(s): Reagent for fluorescence enzyme immunoassay | | |
| A13740 | DL-Tyrosine, 98% [3-(4-Hydroxyphenyl)-DL-alanine, H-D-Tyr-OH] [556-03-6], C ₉ H ₉ NO ₃ , F.W. 181.19, m.p. ca 325° dec., Merck 14,9839, EINECS 209-113-1, BRN 515881, MDL MFCD00063074, † | 10g |
| | | 50g |
| | | 250g |
| H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | | |
| A17709 | D-Tyrosine, 99% [3-(4-Hydroxyphenyl)-D-alanine, H-D-Tyr-OH] [556-02-5], C ₉ H ₉ NO ₃ , F.W. 181.19, m.p. 310-314°, [α] _D ²⁰ +11° (c=4 in 1N HCl), Merck 14,9839, EINECS 209-112-6, BRN 2212157, MDL MFCD00063073, † | 1g |
| | | 5g |
| | | 25g |
| H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | | |
| A11141 | L-Tyrosine, 99% [3-(4-Hydroxyphenyl)-L-alanine, H-Tyr-OH] [60-18-4], C ₉ H ₉ NO ₃ , F.W. 181.19, m.p. >300°, d. 1.46, [α] _D ²⁰ -11° (c=4 in 1N HCl), Merck 14,9839, EINECS 200-460-4, RTECS YP2275600, BRN 392441, MDL MFCD00002606, † | 50g |
| | | 100g |
| | | 1kg |
| H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | | |
| J63511 | L-Tyrosine, Cell Culture Reagent [H-L-Tyr-OH] [60-18-4], C ₉ H ₉ NO ₃ , F.W. 181.19, Powder, m.p. >300°, Merck 14,9839, EINECS 200-460-4, RTECS YP2275600, BRN 392441, MDL MFCD00002606, † | 10g |
| | | 100g |
| | | 500g |
| 1kg | | |
| J61770 | L-Tyrosine disodium salt dihydrate, 99% [122666-87-9], C ₉ H ₉ NNa ₂ O ₃ ·2H ₂ O, F.W. 265.47 (225.15anhy), Powder | 100g |
| | | 500g |
| | | 1kg |
| H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | | |
| J63058 | Tyrphostin A9, 99% [Tyrphostin AG-17, Malonoben] [10537-47-0], C ₁₈ H ₂₂ N ₂ O, F.W. 282.39, Powder, UN2811, RTECS OO3737000, MDL MFCD00209853 | 50mg |
| | | 100mg |
| | | |
| H:H301-H311-H330, P:P301+P310-P304+P340-P320-P330-P361-P405-P501a | | |
| Application(s): Selective inhibitor of PDGF receptor tyrosine kinase | | |
| J60308 | Tyrphostin A23, 99% [Tyrphostin AG-18, 2-(3,4,5-Trihydroxybenzylidene)malononitrile] [118409-57-7], C ₁₆ H ₈ N ₂ O ₂ , F.W. 186.17, Powder, MDL MFCD00133899 | 5mg |
| | | 10mg |
| | | 25mg |
| Application(s): Potent inhibitor of EGF receptor kinase activity | | |
| J62936 | Tyrphostin A25, 99+% [Tyrphostin AG-82, 2-(3,4,5-Trihydroxybenzylidene)malononitrile] [118409-58-8], C ₁₆ H ₈ N ₂ O ₂ , F.W. 202.14, Crystalline powder, m.p. 245° | 5mg |
| | | 10mg |
| | | 25mg |
| Application(s): Potent inhibitor of EGF receptor kinase activity | | |
| J60482 | Tyrphostin A46, 99% [Tyrphostin AG-99, (E)-2-Cyano-3-(3,4-dihydroxyphenyl)-2-propenamide] [122520-85-8], C ₁₆ H ₈ N ₂ O ₃ , F.W. 204.19, Powder | 5mg |
| | | 10mg |
| | | 25mg |
| Application(s): Inhibitor of EGF receptor kinase activity | | |
| Tyrphostin AG-17 , see Tyrphostin A9, 99%, J63058, p. 386 | | |
| Tyrphostin AG-18 , see Tyrphostin A23, 99%, J60308, p. 386 | | |
| Tyrphostin AG-82 , see Tyrphostin A25, 99+%, J62936, p. 386 | | |
| Tyrphostin AG-99 , see Tyrphostin A46, 99%, J60482, p. 386 | | |
| Tyrphostin AG-370 , see Tyrphostin B7, 95%, cis + trans, J63126, p. 387 | | |












| Stock # | Description | Size |
|---------|---|------------------------|
| | Tyrphostin AG-490 , see Tyrphostin B42, 99+%, J61715, p. 387 | |
| J65263 | Tyrphostin AG 537 ▲ [Bis-Tyrphostin] C ₂₃ H ₂₀ N ₄ O ₈ , F.W. 448.43, Powder | 10mg 100mg |
| | Tyrphostin AG-555 , see Tyrphostin B46, 99+%, J61704, p. 387 | |
| | Tyrphostin AG 879 , see AG-879, 99%, J62625, p. 81 | |
| J63126 | Tyrphostin B7, 95%, cis + trans [Tyrphostin AG-370, 2-Amino-4-(5-indolyl)-1,1,3-tricyanobuta-1,3-diene] [134036-53-6], C ₁₅ H ₉ N ₅ , F.W. 259.27, Powder, MDL MFCD00236449 | 1mg 5mg 10mg |
| | Application(s): A protein kinase inhibitor | |
| J61715 | Tyrphostin B42, 99+% [Tyrphostin AG-490, N-Benzyl-2-(3,4-dihydroxybenzylidene)cyanacetamide] [134036-52-5], C ₁₇ H ₁₁ N ₃ O ₃ , F.W. 294.31, Powder, MDL MFCD00236452 | 25mg 100mg |
| | Application(s): A protein kinase inhibitor | |
| J61704 | Tyrphostin B46, 98+% [Tyrphostin AG-555, (E)-2-Cyano-3-(3,4-dihydroxyphenyl)-N-(3-phenylpropyl)-2-propenamide] [133550-34-2], C ₁₉ H ₁₈ N ₂ O ₃ , F.W. 322.36, Powder, MDL MFCD00209865 | 10mg 50mg |
| | Application(s): Inhibitor of EGF receptor kinase activity | |
| J65227 | Tyrphostin C15 ▲ [AG 825, Tyrphostin AG-825] [149092-50-2], C ₁₉ H ₁₅ N ₃ O ₃ S ₂ , F.W. 397.47, Powder, MDL MFCD01074971 | 10mg |
| J61246 | U0126, 99+% [1,4-Diamino-2,3-dicyano-1,4-bis(2-aminophenylthio)butadiene] [109511-58-2], C ₁₈ H ₁₆ N ₆ S ₂ , F.W. 380.49, Powder | 25mg 100mg 300mg |
| | Application(s): Selective inhibitor of mitogen-activated protein kinases MEK-1 and MEK-2 | |
| | U-9889 , see Streptozotocin, 98%, J61601, p. 352 | |
| | U-22324 , see Alamehithin, J63829, p. 82 | |
| | U-29135 , see Geldanamycin, 99+%, J63397, p. 231 | |
| | U-6357A , see Furegrelate sodium salt, 99+%, J61378, p. 229 | |
| J62898 | U-73122, 99+% [1-[6-(((17β)-3-Methoxyestra-1,3,5[10]-trien-17-yl)amino)hexyl]pyrrole-2,5-dione] [112648-68-7], C ₂₉ H ₄₀ N ₂ O ₃ , F.W. 464.65, Crystalline solid | 1mg 5mg 10mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): Inhibitor of phospholipase C activation and inhibits the down regulation of muscarinic receptors | |
| J62719 | U-73343, 98% [1-[6-(((17β)-3-Methoxyestra-1,3,5[10]-trien-17-yl)amino)hexyl]pyrrolidine-2,5-dione] [142878-12-4], C ₂₉ H ₄₂ N ₂ O ₃ , F.W. 466.66, Powder, m.p. 136-138°, MDL MFCD00211221 | 5mg 25mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| | Application(s): Inactive analog of U-73122 | |
| | Ubenimex , see Bestatin, J61106, p. 124 | |
| J65388 | Ubiquitin E1 Inhibitor, PYR-41 ▲ [Ubiquitin-Activating Enzyme E1 Inhibitor, PYR-41] [418805-02-4], C ₁₇ H ₁₃ N ₃ O ₇ ·3H ₂ O, F.W. 425.40, Solid | 25mg 100mg |
| | ! H:H302-H317, P:P261-P280-P302+P352-P321-P301+P312-P501 | |
| | UCN-1028c , see Calphostin C, 99+%, J60647, p. 144 | |
| | UDP sodium salt , see Uridine-5'-diphosphate sodium salt, 98+%, J60141, p. 389 | |
| | UK-48340 , see Amlodipine, 98+%, J62242, p. 100 | |
| A16101 | Undecanal, 97% △ [n-Undecyl aldehyde, Undecylic aldehyde] [112-44-7], CH ₃ (CH ₂) ₉ CHO, F.W. 170.30, m.p. -2°, b.p. 110-112°/12mm, f.p. 95°(203°F), d. 0.827, n _D ²⁰ 1.4340, EINECS 203-972-6, RTECS YQ1500000, BRN 1753213, MDL MFCD00007016, † | 25g 100g |
| | H:H227, P:P210-P280-P370+P378a-P403+P235-P501a | |
| A11244 | Undecanoic acid, 98% [112-37-8], CH ₃ (CH ₂) ₉ CO ₂ H, F.W. 186.30, m.p. 26-29°, b.p. 283-285°, f.p. >110°(230°F), EINECS 203-964-2, RTECS YQ2275000, BRN 1759287, MDL MFCD00002730, † | 50g 250g 1kg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Application(s): An unsaturated fatty acid | |
| A17817 | 1-Undecanol, 98% [n-Undecyl alcohol, 1-Hydroxyundecane] [112-42-5], CH ₃ (CH ₂) ₁₀ OH, F.W. 172.31, m.p. 13-15°, b.p. 243°, f.p. 113°(235°F), d. 0.831, n _D ²⁰ 1.4400, UN3082, EINECS 203-970-5, RTECS YQ3155000, BRN 1698334, MDL MFCD00004751, † | 100g 500g |
| | !  H:H315-H319-H411, P:P280g-P273-P305+P351+P338 | |








| Stock # | Description | Size |
|---------|--|---|
| A19122 | 10-Undecenoic acid, 99% [Undecylenic acid] [112-38-9], C ₁₁ H ₂₀ O ₂ , F.W. 184.28, m.p. 22-25°, b.p. 126-128°/1mm, f.p. 160°(320°F), d. 0.910, n _D ²⁰ 1.4493, Merck 14,9848, EINECS 203-965-8, RTECS YQ2975000, BRN 1762631, MDL MFCD00004442, † ! H.H315-H319-H335, P.P261-P305+P351+P338-P302+P352-P321-P405-P501a |  250g 1kg |
| | n-Undecyl alcohol , see 1-Undecanol, A17817, p. 387 n-Undecyl aldehyde , see Undecanal, A16101, p. 387 Undecylenic acid , see 10-Undecenoic acid, A19122, p. 388 Undecylic aldehyde , see Undecanal, A16101, p. 387 | |
| J64874 | uPA Inhibitor II, UK122 ▲ C ₁₇ H ₁₃ N ₃ O ₂ .CF ₃ CO ₂ H, F.W. 405.30, Solid | 5mg 25mg |
| A15570 | Uracil, 99+% [2,4-Dihydroxypyrimidine] [66-22-8], C ₄ H ₄ N ₂ O ₂ , F.W. 112.09, m.p. ca 330°, Merck 14,9850, EINECS 200-621-9, RTECS YQ8650000, BRN 606623, MDL MFCD00006016, † For a review of the use of uracils as starting materials in heterocyclic synthesis, see: <i>Adv. Het. Chem.</i> , 55 , 130 (1992). |  50g 250g 1kg |
| | Uracil-4-carboxylic acid hydrate , see Orotic acid hydrate, A18594, p. 309 Uracil deoxyriboside , see 2'-Deoxyuridine, A16026, p. 180 | |
| J63219 | Urapidil hydrochloride, 98+% [6-(3-[4-(2-Methoxyphenyl)-1-piperazinyl]propylamino)-1,3-dimethyluracil hydrochloride] [64887-14-5], C ₂₈ H ₂₉ N ₅ O ₃ .HCl, F.W. 423.93, Powder, RTECS YQ9862000, MDL MFCD00078601 ! H.H302, P.P264-P270-P301+P312-P330-P501 | 500mg 1g 5g |
| | Application(s): α-1-Adrenoceptor antagonist and 5-HT1A receptor agonist | |
| A12360 | Urea, 98+% [Carbamide] [57-13-6], NH ₂ CONH ₂ , F.W. 60.06, m.p. 130-135°, d. 1.335, Merck 14,9867, Fieser 1,1262 2,455, EINECS 200-315-5, RTECS YR6250000, BRN 635724, MDL MFCD00008022, † Widely used in diazotization reactions for the destruction of excess HNO ₃ . For the one-pot conversion of carboxylic acids to nitriles, by heating with urea in the presence of 1.5-2.0 moles of sulfamic acid, see: <i>Chimia</i> , 25 , 94 (1971). For a procedure for conversion of carboxylic acids to primary amides by heating with urea, see: <i>Org. Synth. Coll.</i> , 3 , 768 (1955); 4 , 513 (1963). Reacts with alcohols on prolonged heating to give alkyl carbamates; see, e.g.: <i>Org. Synth. Coll.</i> , 1 , 140 (1941). | 500g 2.5kg 10kg |
| | Application(s): Used as a protein denaturant | |
| 36428 | Urea, ACS, 99.0-100.5% [Carbamide] [57-13-6], NH ₂ CONH ₂ , F.W. 60.06, Crystalline, m.p. 132-135°, d. 1.335, Merck 14,9867, Fieser 1,1262 2,455, Solubility: Soluble in water, alcohol, methanol, glycerol, benzene, and conc. HCl. Practically insoluble in chloroform, ether, EINECS 200-315-5, RTECS YR6250000, BRN 635724, MDL MFCD00008022, † Maximum level of impurities: Insoluble matter 0.01%, Residue after ignition 0.01%, Cl 5ppm, SO ₄ 0.001%, Heavy Metals (as Pb) 0.001%, Fe 0.001%, Melting point 132-135° | 100g 500g 2kg |
| | Application(s): Used as a protein denaturant | |
| J64769 | Urea, Molecular Biology Grade [Carbamide] [57-13-6], NH ₂ CONH ₂ , F.W. 60.06, Powder, m.p. 132-134°, d. 1.34, EINECS 200-315-5, RTECS YR6250000, BRN 635724, MDL MFCD00008022, † | 500g 1kg 2.5kg |
| | Application(s): A protein denaturant | |
| J65769 | Urea, ultrapure, 99% [Carbamide] [57-13-6], NH ₂ CONH ₂ , F.W. 60.06, Crystalline, m.p. 132-135°, d. 1.335, Merck 14,9867, EINECS 200-315-5, RTECS YR6250000, BRN 635724, MDL MFCD00008022, † | 100g 500g 2.5kg |
| J60844 | Urea, 8M buffer soln., pH 7.5 Liquid | 250ml 500ml |
| | Urea amidohydrolase , see Urease, Jack Beans, J61455, p. 388 | |
| J61455 | Urease, Jack Beans [EC 3.5.1.5, Urea amidohydrolase] [9002-13-5], Lyophilized powder, 480 kDa, Merck 14,9870, EINECS 232-656-0, RTECS YU1700000, MDL MFCD00070858, Note: Min 45 units/mg dry wt. One unit oxidizes one micromole of NADH per minute at 25 C and pH 7.6. The hydrolysis of urea is measured by coupling ammonia production to a glutamate dehydrogenase reaction., † ! H.H334-H335-H315-H319, P.P285-P305+P351+P338-P302+P352-P321-P405-P501a | 250mg 1g 10g |
| | Application(s): Catalyzes hydrolysis of urea | |
| | 5-Ureidohydantoin , see Allantoin, A15571, p. 89 | |






| Stock # | Description | Size |
|---------------|---|--|
| A13346 | Uric acid, 99% [69-93-2], C ₅ H ₄ N ₂ O ₃ , F.W. 168.11, m.p. >300°, d. 1.89, Merck 14,9875 , EINECS 200-720-7, RTECS YU7050080, BRN 156158, MDL MFCD00005712, † | 25g 100g 500g |
| |  | |
| J60875 | Uricase, Candida utilis [EC 1.7.3.3] [9002-12-4], Lyophilized powder, Merck 14,9876 , EINECS 232-655-5, MDL MFCD00082126, Note: Minimum 2 units per mg dry weight. One unit oxidizes one micromole of uric acid per minute | 100units |
| | Application(s): Oxidizes uric acid | |
| A15227 | Uridine, 99% [58-96-8], C ₉ H ₁₂ N ₂ O ₆ , F.W. 244.20, m.p. 166-169°, [α] _D ²⁰ +9.5° (c=2 in water), Merck 14,9877 , EINECS 200-407-5, RTECS YR1450000, BRN 754904, MDL MFCD00006526, † | 5g 25g 100g |
| |  | |
| J64329 | Uridine-5'-diphosphate disodium salt, 98% <input checked="" type="checkbox"/> [27821-45-0], C ₉ H ₁₂ N ₂ Na ₂ O ₁₂ P ₂ , F.W. 448.13, Powder, EINECS 248-678-9, BRN 8817400, MDL MFCD00149253 | 1g 5g |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | |
| J60141 | Uridine-5'-diphosphate sodium salt, 98+% [UDP sodium salt] [21931-53-3], C ₉ H ₁₂ N ₂ Na ₂ O ₁₂ P ₂ , F.W. 448.12, Powder | 100mg 500mg |
| | ! ⚠ H:H302-H371, P:P260-P264-P309+P311-P301+P312-P405-P501 | |
| A18601 | Uridine-5'-monophosphate disodium salt, 99% [5'-Uridylic acid disodium salt] [3387-36-8], C ₉ H ₁₁ N ₂ Na ₂ O ₆ P, F.W. 368.15, m.p. ca 209° dec., EINECS 222-211-9, RTECS YU7975000, BRN 3582885, MDL MFCD00006525 | 5g 25g 100g |
| |  | |
| J63427 | Uridine-5'-triphosphate trisodium salt, 98+% [UTP-Na3] [19817-92-6], C ₉ H ₁₂ N ₂ Na ₃ O ₁₃ P ₃ , F.W. 550.09, Powder, EINECS 243-347-5, BRN 3585234, MDL MFCD00044310 | 100mg 250mg |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | 5'-Uridylic acid disodium salt, see Uridine-5'-monophosphate disodium salt, A18601, p. 389 | |
| J64679 | cis-Urocanic acid ▲ [cis-3-(1H-Imidazol-4-yl)-2-propenoic acid, cis-UCA] [7699-35-6], C ₈ H ₈ N ₂ O ₂ , F.W. 138.12, Solid, MDL MFCD11045310 | 10mg 100mg |
| J65601 | Uroguanylin, human [Asn-Asp-Asp-Cys-Glu-Leu-Cys-Val-Asn-Val-Ala-Cys-Thr- Gly-Cys-Leu (disulfide bridges: Cys4-Cys12, Cys7-Cys15)] C ₆₄ H ₁₀₂ N ₁₈ O ₂₆ S ₄ , F.W. 1667.86, Solid | 1mg |
| J60553 | Urokinase, human urine [EC 3.4.21.73] [9039-53-6], Lyophilized powder, 54 kDa, Merck 14,9887 , EINECS 232-917-9, RTECS OB8900000, MDL MFCD00132566, Note: 83,700IU/mg. 1nM UK will cause a change in absorbance of 0.001 at 405nm in 1 minute at R/T in 100 ul 0.05M Tris-HCl, 0.1M NaCl, pH 7.4, using S2444 (0.6mM) as the substrate, † | 100micrograms 1mg 5mg |
| | Application(s): A serine protease; biological plasminogen activator | |
| B20490 | Ursodeoxycholic acid, 99% [128-13-2], C ₂₃ H ₄₀ O ₄ , F.W. 392.56, m.p. 201-204°, Merck 14,9889 , EINECS 204-879-3, RTECS FZ2000000, MDL MFCD00003680 | 1g 5g 25g |
| | H:H303, P:P312 | |
| | Application(s): A secondary bile acid | |
| |  | |
| H56612 | (+)-Usnic acid, 98% [2,6-Diacetyl-7,9-dihydroxy-8,9b-dimethyldibenzofuran-1,3(2H,9bH)-dione] [7562-61-0], C ₁₈ H ₁₆ O ₇ , F.W. 344.32, m.p. 201-203°, EINECS 231-456-0, RTECS HP5295050, BRN 96698, MDL MFCD00016878 | 5g 25g |
| |  | |










UTP-Na3, see Uridine-5'-triphosphate trisodium salt, 98+%, J63427, p. 389


| Stock # | Description | | Size |
|---------------|--|--|--------------------------------|
| | H-L-Val-OH , see L-Valine, Cell Culture Reagent, J62943, p. 390 | | |
| A10525 | Valerophenone, 99% [<i>n</i> -Butyl phenyl ketone, <i>Pentanophenone</i>] [1009-14-9], C ₁₁ H ₁₄ O, F.W. 162.23, m.p. -9°, b.p. 244-245°, f.p. 102°(215°F), d. 0.978, n _D ²⁰ 1.5143, EINECS 213-767-3, BRN 1907717, MDL MFCD00009480, † |  | 25g 100g 500g |
| J62622 | Valethamate bromide, 99% [<i>Epidosin</i> , <i>N,N</i> -Diethyl- <i>N</i> -methyl-2-((3-methyl-1-oxo-2-phenylpentyl)oxy)ethan ammonium bromide] [90-22-2], C ₁₉ H ₃₂ BrNO ₂ , F.W. 386.37, Powder, m.p. 120-127°, Merck 14,9906, EINECS 201-977-8, RTECS BP7600000, MDL MFCD00031617 | | 5g 25g |
| | ! H:H302-H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | | |
| A16756 | DL-Valine, 99% [<i>DL</i> -2-Aminoisovaleric acid, (+/-)-2-Amino-3-methylbutyric acid] [516-06-3], C ₆ H ₁₁ NO ₂ , F.W. 117.15, m.p. ca 296° subl., Merck 14,9909, EINECS 208-220-0, BRN 506689, MDL MFCD00004267, † |  | 100g 500g 2.5kg |
| A18894 | D-Valine, 98+% [<i>D</i> -2-Aminoisovaleric acid, (<i>R</i>)-(-)-2-Amino-3-methylbutyric acid] [640-68-6], C ₆ H ₁₁ NO ₂ , F.W. 117.15, m.p. 295° dec., [α] _D ²⁰ -27° (c=5 in 5N HCl), EINECS 211-368-9, RTECS YV9360000, BRN 1721135, MDL MFCD00064219, † |  | 5g 25g 100g |
| A12720 | L-Valine, 99% [<i>L</i> -2-Aminoisovaleric acid, (<i>S</i>)-(+)-2-Amino-3-methylbutyric acid] [72-18-4], C ₆ H ₁₁ NO ₂ , F.W. 117.15, m.p. ca 315°, d. 1.23, [α] _D ²⁰ +27° (c=5 in 5N HCl), Merck 14,9909, EINECS 200-773-6, RTECS YV9361000, BRN 1721136, MDL MFCD00064220, † |  | 25g 100g 500g |
| J62943 | L-Valine, Cell Culture Reagent [<i>H</i> -L-Val-OH] [72-18-4], C ₆ H ₁₁ NO ₂ , F.W. 117.15, Powder, Merck 14,9909, EINECS 200-773-6, RTECS YV9361000, BRN 1721136, MDL MFCD00064220, † | | 1g 5g 25g 100g 1kg |
| L14166 | D-(-)-Valinol, 98% △ [(<i>R</i>)-(-)-2-Amino-3-methyl-1-butanol, <i>H</i> -D-Val-ol] [4276-09-9], C ₆ H ₁₃ NO, F.W. 103.17, m.p. 30-34°, b.p. 189-190°, f.p. 78°(172°F), d. 0.931, n _D ²⁰ 1.4550, [α] _D ²⁰ -11° (c=10 in water), BRN 1719138, MDL MFCD00064297 |  | 1g 5g |
| | ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 | | |
| L11300 | L-(+)-Valinol, 97% △ [(<i>S</i>)-(+)-2-Amino-3-methyl-1-butanol, <i>H</i> -Val-ol] [2026-48-4], C ₆ H ₁₃ NO, F.W. 103.17, m.p. 30-35°, b.p. 80-81°/8mm, f.p. 78°(172°F), d. 0.926, n _D ²⁰ 1.4548, [α] _D ²⁰ +17° (c=10 in ethanol), Fieser 12,563 13,341 16,380, EINECS 217-975-5, BRN 1719137, MDL MFCD00064296 |  | 1g 5g 25g |
| | ! H:H315-H319, P:P280-P305+P351+P338-P302+P352-P321-P362-P332+P313 Chiral auxiliary and building block. See also (4S)-(-)-Isopropyl-2-oxazolidinone, A14029 , for derived reagents. | | |
| J62312 | Valinomycin, 90+% [<i>NSC 122023</i>] [2001-95-8], C ₅₄ H ₈₀ N ₆ O ₁₈ , F.W. 1111.34, Crystalline powder, Merck 14,9910, UN2811, EINECS 217-896-6, RTECS YV9468000, BRN 78657, MDL MFCD00005114, † | | 100mg |
| | Application(s): Potassium-selective ionophoric cyclodepsipeptide; inhibitor of mitochondrial action | | |
| J65255 | D-Val-Leu-Lys-7-amino-4-methylcoumarin [<i>D</i> -VLK-AMC] C ₂₇ H ₄₁ N ₃ O ₅ , F.W. 515.64, Solid, MDL MFCD00038828 | | 10mg |
| J62790 | Vancomycin hydrochloride, Molecular Biology Grade ■ [1404-93-9], C ₆₆ H ₇₅ Cl ₂ N ₉ O ₂₄ ·HCl, F.W. 1485.73, Powder, Merck 14,9929, RTECS YW4380000, BRN 3704657 | | 1g 5g |
| | ! H:H317, P:P261-P280-P302+P352-P321-P363-P501a | | |
| | Application(s): Inhibits bacterial mucopeptide synthesis | | |
| A12074 | Vanillic acid, 98% [4-Hydroxy-3-methoxybenzoic acid] [121-34-6], C ₈ H ₈ O ₄ , F.W. 168.15, m.p. 210-218°, Merck 14,9931, EINECS 204-466-8, RTECS YW5300000, BRN 2208364, MDL MFCD00002551, † |  | 25g 100g 500g |
| | ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a | | |
| A11169 | Vanillin, 99% ▲ △ [4-Hydroxy-3-methoxybenzaldehyde] [121-33-5], C ₈ H ₈ O ₃ , F.W. 152.15, m.p. 81-83°, b.p. 170°/15mm, f.p. 153°(307°F), d. 1.06, Merck 14,9932, EINECS 204-465-2, RTECS YW5775000, BRN 472792, MDL MFCD00006942, † |  | 100g 500g 2.5kg |
| | ! H:H302-H332, P:P261-P264-P304+P340-P301+P312-P312-P501a | | |





| Stock # | Description | Size |
|--|---|----------------------|
| J61096 | Vapreotide [RC-160, DPhe-Cys-Tyr-DTrp-Lys-Val-Cys-Trp-NH2] [103222-11-3], C ₅₇ H ₇₀ N ₁₂ O ₈ S ₂ , F.W. 1131.38, Lyophilized powder, Merck 14,9934 | 1mg 5mg |
| Application(s): Analog of somatostatin shown to inhibit tumor growth | | |
| J63082 | Vargatef, 99+% [BIBF 1120, Intedanib] [928326-83-4], C ₃₁ H ₃₃ N ₅ O ₄ , F.W. 539.63, Crystalline solid or powder | 5mg 10mg 25mg |
| Application(s): Indolinone derivative that inhibits VEGFR, PDGFR and FGFR | | |
| J64375 | Vascular Endothelial Cell Growth Factor, 98% [VEGF] Note: Recombinantly expressed in E. Coli. Receptor Grade. Suitable for use in cell culture. Supplied as an aseptically lyophilized powder. | 10micrograms |
| J63980 | Vasoactive Intestinal Peptide, human, porcine, rat [VIP, His-Ser-Asp-Ala-Leu-Phe-Thr-Asp-Thr-Tyr-Thr-Arg-Leu-Arg-Lys-Gln-Met-Ala-Met-Lys-Lys-Tyr-Leu-Asn-Ser-Val-Leu-Asn-NH2] [40077-57-4], C ₄₄ H ₇₃ N ₁₅ O ₁₂ S ₂ , F.W. 3325.84, Powder, MDL MFCD00167535 | 0.5mg 1mg |
| Application(s): Demonstrates vasoconstrictor activity | | |
| J61248 | Vasopressin, 98+% [Cys-Tyr-Phe-Gln-Asn-Cys-Pro-Arg-Gly-NH2, AVP peptide] [11000-17-2], C ₄₆ H ₆₅ N ₁₅ O ₁₂ S ₂ , F.W. 1084.24, Lyophilized powder, EINECS 234-236-2 | 5mg 25mg 100mg |
| Application(s): Has antidiuretic activity and plays a role in water balance in animals | | |
| Veinacrine maleate , see Hydroxytacrine maleate salt, J60680, p. 252 | | |
| J61535 | (±)-Verapamil hydrochloride, 99+% [Arpamy] [152-11-4], C ₂₇ H ₃₈ N ₂ O ₄ ·HCl, F.W. 491.07, Powder, m.p. 138-141°, Merck 14,9950, UN2811, EINECS 205-800-5, RTECS YV8320000, BRN 3647093, MDL MFCD00055208 | 1g |
| H: H301-H311-H330, P: P301+P310-P304+P340-P320-P330-P361-P405-P501a | | |
| Application(s): A calcium channel blocker with a chemopreventive character | | |
| J62324 | Veratridine, 97+% [3-Veratroylveracevine] [71-62-5], C ₃₈ H ₅₂ NO ₁₁ , F.W. 673.80, Powder, Merck 14,9954, UN1544, EINECS 200-758-4, RTECS YX5600000, BRN 78875, MDL MFCD00082515 | 10mg 50mg |
| H: H300-H310-H330-H315-H319-H335, P: P301+P310-P304+P340-P305+P351+P338-P320-P330-P361-P405-P501a | | |
| Application(s): Activates sodium ion channels | | |
| A11985 | Veratrole, 99% [Catechol dimethyl ether, 1,2-Dimethoxybenzene] [91-16-7], C ₈ H ₁₀ O ₂ , F.W. 138.17, m.p. 21-23°, b.p. 206-207°, f.p. 87°(188°F), d. 1.084, n _D ²⁰ 1.5330, Merck 14,9956, EINECS 202-045-3, RTECS CZ6475000, BRN 1364621, MDL MFCD00008357,  | 250g 1kg 5kg |
| H: H302, P: P264-P270-P301+P312-P330-P501a | | |
| In contrast to 1,3-Dimethoxybenzene, A13380 , direct dilithiation with n-BuLi + TMEDA is feasible, giving, after reaction with TMS chloride, the 3,6-disilyl derivative as the major product in 50-60% yield: <i>J. Org. Chem.</i> , 49 , 4657 (1984). | | |
| 3-Veratroylveracevine , see Veratridine, 97+%, J62324, p. 391 | | |
| J61371 | Veronal-buffered saline (VBS), 5mM buffer soln., pH 7.0 | 250ml 500ml |
| Liquid, Note: 5mM barbital, 145mM NaCl, pH 7.0. | | |
| J61611 | Veronal-buffered saline (VBS), 10mM buffer soln., pH 7.0 | 250ml 500ml |
| Liquid, Note: 10mM barbital, 145mM NaCl, pH 7.0. | | |
| J63779 | Veronal-buffered saline (VBS), 10mM buffer soln., pH 7.4 | 250ml 500ml |
| Liquid, Note: 10mM barbital, 145mM NaCl | | |
| J60003 | Veronal-buffered saline with MG + CA (VBS++), 5mM buffer soln., pH 7.2 | 250ml 500ml |
| Liquid, Note: 5mM barbital, 145mM sodium chloride, 0.5mM magnesium chloride 15mM calcium chloride, pH 7.2. | | |
| J63853 | Veronal-buffered saline with MG + CA (VBS++), 10mM buffer soln., pH 7.2 | 250ml 500ml |
| Liquid, Note: 10mM barbital, 145mM sodium chloride, 0.5mM magnesium chloride 15mM calcium chloride, pH 7.2. | | |
| J62759 | Veronal-buffered saline with EDTA (VBSE), 5mM buffer soln., pH 7.2 | 250ml 500ml |
| Liquid, Note: 5mM barbital. 145mM NaCl 10mM EDTA, pH 7.2. | | |
| J63338 | Veronal-buffered saline with EDTA (VBSE), 10mM buffer soln., pH 7.2 | 250ml 500ml |
| Liquid, Note: 10mM barbital, 145mM NaCl, 10mM EDTA, pH 7.2. | | |

| Stock # | Description | Size |
|---------|---|---------------------|
| J60535 | Veronal-buffered saline with MG + EGTA (VBSMG), 5mM buffer soln., pH 7.2 Liquid, Note: 5mM barbital, 145mM sodium chloride, 0.5mM magnesium chloride, 5mM EGTA, pH 7.2. | 250ml 500ml |
| J63417 | Veronal-buffered saline with MG + EGTA (VBSMG), 10mM buffer soln., pH 7.2 Liquid, Note: 10mM barbital, 145mM sodium chloride, 0.5mM magnesium chloride, 5mM EGTA, pH 7.2. | 250ml 500ml |
| J63598 | Vinblastine sulfate, 98% [<i>Vincalculblastine sulfate</i>] [143-67-9], C ₂₁ H ₂₆ N ₂ O ₈ S, F.W. 909.06, Powder, m.p. 267°, Merck 14,9982, EINECS 205-606-0, RTECS YY8400000, BRN 3659812, MDL MFCD00082457  H:H302-H315-H318-H360-H373, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 Application(s): Anticancer agent; microtubule disrupter; Induces apoptosis Vincalculblastine sulfate , see Vinblastine sulfate, 98%, J63598, p. 392 | 10mg 50mg |
| J60545 | Vincamine, 98% [1617-90-9], C ₂₁ H ₂₆ N ₂ O ₃ , F.W. 354.45, Powder, m.p. 232°, Merck 14,9983, EINECS 216-576-3, RTECS YY8575000, MDL MFCD00078054 ! H:H302, P:P264-P270-P301+P312-P330-P501 Application(s): A vasodilator | 1g 5g |
| J60907 | Vincristine sulfate, 98+% [2068-78-2], C ₄₆ H ₅₈ N ₄ O ₁₄ S, F.W. 923.04, Powder, m.p. >300°, b.p. 273-281°, Merck 14,9986, UN2811, EINECS 218-190-0, RTECS OH6340000, BRN 3924631, MDL MFCD00084729  H:H360-H341, P:P281-P201-P202-P308+P313-P405-P501a Application(s): An anti-tumor alkaloid used in cancer research | 5mg 25mg |
| J61000 | Vinpocetine, 98% [<i>Eburnamenine-14-carboxylic acid ethyl ester</i>] [42971-09-5], C ₂₂ H ₂₆ N ₂ O ₂ , F.W. 350.46, Powder, m.p. 147-149°, Merck 14,9991, EINECS 256-028-0, RTECS JW4792000, MDL MFCD00211233 ! H:H302, P:P264-P270-P301+P312-P330-P501 Application(s): Specific calcium-calmodulin-dependent phosphodiesterase inhibitor | 20mg 100mg |
| | 5-Vinyloxazolidone-2-thione , see DL-Goitrin, L02639, p. 238 VIP , see Vasoactive Intestinal Peptide, human, porcine, rat, J63980, p. 391 | |
| A16237 | Vitamin A acetate in gelatin, powder, 500,000 I.U/g [<i>Retinol acetate, Retinyl acetate</i>] [127-47-9], Merck 14,10013, EINECS 204-844-2, RTECS VH6825000, BRN 1915439, MDL MFCD00019413, †  H:H361, P:P281-P201-P202-P308+P313-P405-P501a  | 25g 100g 500g |
| | Vitamin A acid , see Retinoic acid, 44540, p. 336 Vitamin A alcohol , see Retinol, 98%, synthetic, J62079, p. 336 | |
| J63022 | Vitamin A palmitate, 98+% [<i>Retinyl palmitate, Retinol palmitate</i>] [79-81-2], C ₅₈ H ₁₀₀ O ₂ , F.W. 524.87, Solid, m.p. 28-29°, Merck 14,10013, EINECS 201-228-5, RTECS VH6860000, BRN 1917366, MDL MFCD00019414, †  H:H361, P:P281-P201-P202-P308+P313-P405-P501a | 25g 100g |
| | Vitamin B1 hydrochloride , see Thiamine hydrochloride, A19560, p. 366 Vitamin B, Nitrate , see Thiamine nitrate, J60014, p. 366 Vitamin B2 , see Riboflavin, A11764, p. 337 | |
| A14894 | Vitamin B12, 98+% (dry wt basis) ■ [<i>Cyanocobalamin</i>] [68-19-9], C ₆₃ H ₈₈ CoN ₁₄ O ₁₄ P, F.W. 1355.38, Merck 14,10014, EINECS 200-680-0, RTECS GG3750000, BRN 4122889, MDL MFCD00151092, † For monographs, see: <i>B₁₂</i> (2 vols), D. Dolphon, Ed., Wiley-Interscience, N.Y. (1982); <i>B₁₂ and B₁₂-Proteins</i> , B. Kraeutler, T. Golding, Eds., Wiley-VCH, Weinheim (1998). For a review, see: <i>Vitamins</i> , W. Friedrich, Ed., de Gruyter, Berlin (1988), pp 837-928. For review of biosynthesis, see: <i>Angew. Chem. Int. Ed.</i> , 32 , 1223 (1993). | 1g 5g 25g |
| | Vitamin BT , see L-Carnitine, A17618, p. 148 Vitamin C , see L-(+)-Ascorbic acid, 36237, p. 110 Vitamin C sodium salt , see L-Ascorbic acid sodium salt, A17759, p. 110 Vitamin D2 , see Calciferol, J61610, p. 142 | |
| B22524 | Vitamin D3, 99% ▲ △ [<i>Cholecalciferol</i>] [67-97-0], C ₂₇ H ₄₄ O, F.W. 384.65, m.p. 83-87°, Merck 14,10019, UN2811, EINECS 200-673-2, RTECS VS2900000, BRN 2339331, MDL MFCD00078131, †  H:H301-H311-H330-H372, P:P301+P310-P304+P340-P320-P330-P361-P405-P501a  | 1g 5g |
| | Vitamin E , see DL- α -Tocopherol, A17039, p. 370 | |

| Stock # | Description | Size |
|---------------|---|---|
| A14505 | Vitamin E acetate, 97% ▲ △ [DL- α -Tocopheryl acetate] [7695-91-2], C ₃₁ H ₅₂ O ₃ , F.W. 472.76, m.p. -28°, b.p. >300°, f.p. 210°(410°F), d. 0.960, n _D ²⁰ 1.4960, Merck 14.9495 , EINECS 231-710-0, RTECS GA8747000, BRN 97512, MDL MFCD00072042, † | 25g 100g 500g |
| |  | |
| | Vitamin H , see D-(+)-Biotin, A14207, p. 125 | |
| L10575 | Vitamin K₁ ▲ [Phylloquinone] [84-80-0], C ₃₁ H ₄₆ O ₂ , m.p. ca -20°, b.p. ca 140°/0.001m, f.p. >110°(230°F), d. 0.984, n _D ²⁰ 1.5260, Merck 14.7380 , EINECS 201-564-2, RTECS QJ5800000, BRN 2568816, MDL MFCD00214063, † | 1g 5g |
| |  | |
| | Vitamin K₃ , see 2-Methyl-1,4-naphthoquinone, A13593, p. 289 VUF 9153 , see Clobenpropit dihydrobromide, 99+%, J60807, p. 165 W-7 hydrochloride , see N-(6-Aminoheptyl)-5-chloro-1-naphthalenesulfonamide hydrochloride, J63012, p. 95 | |
| L17028 | Wang resin, 1% cross-linked, 0.8-1.1mmol/g, 200-400 mesh [4-Benzyloxybenzyl alcohol, polymer supported, Polystyrene PHB] MDL MFCD00131778, Note: Polystyrene-1% divinylbenzene resin, 200-400 mesh Supporting resin for solid phase synthesis. | 5g 25g |
| |  | |
| J61918 | Wash buffer, pH 8.0 Liquid, Note: 50mM sodium dihydrogen phosphate, 300 mM sodium chloride, 20mM imidazole, pH 8.0. | 500ml |
| | Application(s): For His-tag protein purification | |
| J60428 | Wash buffer, 1.0% Triton® X-100, pH 8.0 Liquid, Note: 50mM Tris-HCl, 500mM NaCl, 1% Triton X-100 | 250ml 500ml |
| | Application(s): For GST-fusion protein purification | |
| J60165 | Wash buffer, 0.5% Tween 20, pH 8.0 Liquid, Note: 50mM sodium dihydrogen phosphate, 300 mM sodium chloride, and 20mM imidazole with 0.5% Tween-20, pH 8.0. | 500ml |
| | Application(s): For His-tag protein purification | |
| J62087 | Water, DEPC-Treated [7732-18-5], H ₂ O, F.W. 18.02, Liquid, b.p. 100°, d. 1.000, Merck 14.10039 , EINECS 231-791-2, RTECS ZC0110000, BRN 2050024, MDL MFCD00011332 | 250ml 1L |
| J65589 | Water, Endotoxin-free [7732-18-5], H ₂ O, F.W. 18.02, Liquid, b.p. 100°, d. 1.00, n _D ²⁰ 1.34, Merck 14.10039 , EINECS 231-791-2, RTECS ZC0110000, BRN 2050024, MDL MFCD00011332, † | 500ml 1L |
| J60610 | Water, RNase, DNase-free [7732-18-5], H ₂ O, F.W. 18.02, Liquid, b.p. 100°, d. 1.000, Merck 14.10039 , EINECS 231-791-2, RTECS ZC0110000, BRN 2050024, MDL MFCD00011332, † | 3.8L |
| J63969 | Wheat Germ Oil [8006-95-9], Oil | 5kg 10kg 15kg |
| | Application(s): A natural source of vitamin E | |
| | Woodward's Reagent K , see 2-Ethyl-5-phenylisoxazolium-3'-sulfonate, J61826, p. 217 Wool fat , see Lanolin, A16902, p. 266 | |
| J63983 | Wortmannin, Penicillium funiculosum, 99+% ▲ [KY 12420] [19545-26-7], C ₂₃ H ₂₈ O ₆ , F.W. 428.44, Powder, Merck 14.10053 , UN3462, RTECS CB9641000, BRN 67676, MDL MFCD00133927  H:H300-H310-H330, P:P301+P310-P304+P340-P320-P330-P361-P405-P501a | 10mg 25mg 50mg |
| | Application(s): Inhibitor of phosphatidylinositol 3-kinase | |
| A17903 | Wright's Stain [68988-92-1], EINECS 273-541-5, MDL MFCD00082143, † Biological stain. | 25g 100g |
| | Application(s): Useful stain for blood and for bone marrow films | |
| | WSC , see 1-(3-Dimethylaminopropyl)-3-ethylcarbodiimide hydrochloride, A10807, p. 196 9-Xanthenol , see 9-Hydroxyxanthene, A13476, p. 394 Xanthen-9-one , see Xanthone, A14812, p. 394 | |
| A11077 | Xanthine, 99% [2,6-Dihydroxypurine] [69-89-6], C ₅ H ₄ N ₂ O ₆ , F.W. 152.11, m.p. >300°, Merck 14.10059 , EINECS 200-718-6, RTECS ZD7700000, BRN 8733, MDL MFCD00078453, † | 25g 100g |
| |  | |

| Stock # | Description | Size |
|---------------|---|---|
| A14812 | Xanthone, 99% [Xanthen-9-one] [90-47-1], C ₁₃ H ₈ O ₂ , F.W. 196.21, m.p. 174-178°, b.p. 350-351°, Merck 14 ,10062, EINECS 201-997-7, RTECS ZD5711000, BRN 140443, MDL MFCD00005060, † |  25g 100g 500g |
| | Xanthotoxin , see 8-Methoxypsoralen, A17108, p. 285 | |
| A13476 | Xanthrol, 98+% ▲ [9-Hydroxyxanthen, 9-Xanthenol] [90-46-0], C ₁₃ H ₁₀ O ₂ , F.W. 198.22, m.p. 122-126°, EINECS 201-996-1, RTECS ZD5710000, BRN 10395, MDL MFCD00005057, † Used in the protection of thiols as their S-xanthenyl (Xan) thioethers, by reaction in the presence of TFA. The Xan group can also be cleaved using TFA in dichloromethane in the presence of triethylsilane as a cation scavenger, or with iodine in acetic acid: <i>J. Org. Chem.</i> , 62 , 3841 (1997). |  5g 25g 100g |
| | Application(s): Useful in tests for urea | |
| J61481 | Xenopsin [Glp-Gly-Lys-Arg-Pro-Trp-Ile-Leu] [51827-01-1], C ₆₇ H ₇₃ N ₁₃ O ₁₀ , F.W. 980.18, Powder | 1mg 5mg |
| | Application(s): Multifunctional neuropeptide isolated from frog skin | |
| | X-α-Gal , see 5-Bromo-4-chloro-3-indolyl-a-D-galactoside, J60151, p. 136 | |
| J61726 | XTT sodium salt [2,3-Bis(2-methoxy-4-nitro-5-sulfonylphenyl)-2H-tetrazolium-5-carboxanilide inner salt] [111072-31-2], C ₂₂ H ₁₆ N ₄ NaO ₁₅ S ₂ , F.W. 673.52, Powder, MDL MFCD00083517 | 250mg |
| | Application(s): Tetrazolium derivative useful in cancer research | |
| J61430 | Xylazine [2-(2,6-Dimethylphenylamino)-5,6-dihydro-4H-thiazine hydrochloride] [7361-61-7], C ₁₂ H ₁₆ N ₂ S, F.W. 220.33, Powder, Merck 14 ,10080, UN2811, EINECS 230-902-1, RTECS XJ0776300, MDL MFCD00057908  | 1g 5g 25g |
| J62394 | Xylazine hydrochloride [23076-35-9], C ₁₂ H ₁₆ N ₂ SHCl, F.W. 256.79, Powder, Merck 14 ,10080, UN2811, EINECS 245-417-0, RTECS XJ0776350, BRN 6448471, MDL MFCD00058196  | 5g 25g |
| | Application(s): Agonist at the α-2 adrenergic receptor | |
| B21530 | Xylenecyanol FF, dye content 70% [Acid blue 147, C.I. 42135] [2650-17-1], C ₂₅ H ₂₇ N ₃ NaO ₅ S ₂ , F.W. 538.61, m.p. ca 295° dec., EINECS 220-167-5, MDL MFCD00019481, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a |  10g 50g |
| | Application(s): A tracking dye for DNA sequencing | |
| A17457 | Xylenol Blue [p-Xylenolsulfonephthalein] [125-31-5], C ₂₀ H ₂₂ O ₃ S, F.W. 410.49, m.p. ca 212° dec., Merck 14 ,10083, EINECS 204-736-5, BRN 363132, MDL MFCD00005870, † ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501a Acid-base indicator: pH 1.2 - 2.8; 8.0 - 9.6. |  1g 5g |
| | Application(s): pH Indicator: pH 1.2 (red) -pH 2.8 (yellow); pH 8.0 (yellow)-pH 9.6 (blue) | |
| | p-Xylenolsulfonephthalein , see Xylenol Blue, A17457, p. 394 | |
| L10863 | Xylidyl Blue I sodium salt [Magon sulfate] [14936-97-1], C ₂₅ H ₂₀ N ₂ NaO ₅ S, F.W. 513.51, EINECS 239-012-8, MDL MFCD00003890 Complexometric reagent for Mg. |  1g 5g |
| | Application(s): Used in the colorimetric determination of Mg | |
| A16944 | Xylitol, 99% ■ [87-99-0], C ₅ H ₁₂ O ₅ , F.W. 152.15, m.p. 92-96°, d. 1.515, Merck 14 ,10085, EINECS 201-788-0, RTECS ZF0800000, BRN 1720523, MDL MFCD00064292, † |  100g 500g |
| A10643 | D-(+)-Xylose, 98+% ■ [58-86-6], C ₅ H ₁₀ O ₅ , F.W. 150.13, m.p. 147-151°, f.p. > 100° (212°F), d. 1.525, [α] _D ²⁰ +20° (c=10 in water, 10h), Merck 14 ,10087, EINECS 200-400-7, RTECS ZF2285000, BRN 1562108, MDL MFCD00151475, † For conversion to the useful chiral synthon (2S,4S)-2,4,5-trihydroxypentanoic acid 4,5-acetonide methyl ester, see: <i>Org. Synth. Coll.</i> , 9 , 717 (1998). |  100g 500g 2.5kg |

| Stock # | Description | Size |
|---------|---|------------------------|
| B21622 | L(-)-Xylose, 99% ■ [609-06-3], C ₅ H ₁₀ O ₅ , F.W. 150.13, m.p. 147-151°, d. 1.525, [α] _D ²⁰ -20° (c=10 in water, 10h), EINECS 210-174-1, BRN 1723080, MDL MFCD00151096, † | 5g 25g 100g |
| |  | |
| | Y-acetate, see 3-Indoxyl acetate, L04932, p. 256 | |
| J60287 | Yeast extract [8013-01-2], Powder, EINECS 232-387-9, RTECS ZF6610000, MDL MFCD00132599 | 1kg 5kg |
| | Application(s): Microbial media | |
| J61459 | Yeast lysis solution for DNA isolation Liquid, Note: 0,5M lithium chloride, 50mM Tris-HC, 1% Triton X-100 6.25mM EDTA, pH 8.0 | 250ml 500ml |
| | Yeast Lytic Enzyme, Arthrobacter luteus [Lyticase, Zymolyase 20T] [37340-57-1], Lyophilized powder, MDL MFCD00131560, Note: 20 units/mg. One unit decreases absorbance at 800nm by 30% after 2 hour assay at 25 C using brewer's yeast as a substrate. | 250mg 500mg 1g |
| | ⚠ H: H334, P: P285-P261-P342+P311-P304+P341-P501a | |
| | Application(s): Hydrolyzes linear glucose polymers with β-1,3-linkages | |
| H26271 | Yeast Nitrogen Base MDL MFCD00217952 | 100g 500g |
| | Yohimbine hydrochloride, 98+% ▲ [17-Hydroxyyohimban-16-carboxylic acid methyl ester hydrochloride] [65-19-0], C ₂₁ H ₂₈ N ₂ O ₃ ·HCl, F.W. 390.91, Powder, m.p. 288-290°, Merck 14,10102, UN1544, EINECS 200-600-4, RTECS ZG1015000, MDL MFCD00012674, † | 1g 5g |
| | ⚠ H: H300-H311-H330, P: P301+P310-P304+P340-P320-P330-P361-P405-P501a | |
| | Application(s): Standard α-2-adrenergic antagonist | |
| | α-Yohimbine hydrochloride, see Rauwolscine hydrochloride, 99%, J63198, p. 335 | |
| J61512 | YPAD Agar plates Liquid, Note: Agar plates prepared with 10g Bacto Yeast extract, 20g Peptone, 20g dextrose, 40mg adenine sulfate and 20g agar in 1L of water. | 20plates |
| | YP Base Medium ■■ MDL MFCD01636187, Note: Ingredients (per liter amounts): 20g tryptone and 10g yeast extract. Final pH of 7.0 at 25C | 100g 500g |
| | Application(s): For maintaining and developing yeast in molecular microbiology procedures | |
| J63227 | 2X YT Microbial medium Liquid, Note: Ingredients (per liter amounts): 16g tryptone (pancreatic digest of casein), 10g yeast extract, 5g NaCl | 500ml 1L |
| | Application(s): Growth medium for culturing Escherichia coli, particularly laboratory or recombinant strains. | |
| J64905 | Z-Ala-Glu(OMe)-Val-Asp(OMe)-fluoromethyl ketone [Z-AEVD-FMK, Z-A-E(OMe)-V-Asp(OMe)-FMK] C ₂₈ H ₃₉ N ₅ O ₁₀ F, F.W. 610.63, Powder, MDL MFCD03453601 | 1mg |
| | Zalcitabine, see 2',3'-Dideoxycytidine, L10619, p. 187 | |
| J63326 | Zaprinast, 98+% [1,4-Dihydro-5-(2-propoxyphenyl)-7H-1,2,3-triazolo(4,5-d)pyrimidin-7-one] [37762-06-4], C ₁₃ H ₁₃ N ₅ O ₂ , F.W. 271.28, Powder, EINECS 253-655-1, RTECS XZ6157358, MDL MFCD00214073 | 10mg 50mg 100mg |
| | ⚠ H: H315-H319-H335, P: P261-P305+P351+P338-P302+P352-P321-P405-P501a | |
| | Application(s): Phosphodiesterase inhibitor | |
| J64569 | Z-Asp-Glu-Val-Asp-7-amido-4-trifluoromethylcoumarin [Z-DEVD-AFC, Z-Asp-Glu-Val-Asp-AFC] C ₃₈ H ₃₈ F ₃ N ₅ O ₁₄ , F.W. 821.71, Powder | 5mg |
| | Z-Asp(O-Me)-Glu(O-Me)-Val-Asp(O-Me)-fluoromethyl ketone [Z-DEVD-FMK] C ₃₀ H ₄₁ N ₄ O ₁₂ F, F.W. 668.66, Powder | 5mg |
| J65068 | Z-Asp(OMe)-Gln-Met-Asp(OMe)-fluoromethyl ketone [Z-Asp(OMe)-Gln-Met-Asp(OMe)-FMK, Z-D(OMe)QMD(OMe)-FMK] C ₂₈ H ₄₀ FN ₅ O ₁₁ S, F.W. 685.72, Powder, MDL MFCD03452876 | 1mg 5mg |
| | trans-Zeatin, 97% [6-[(E)-4-Hydroxy-3-methylbut-2-enylamino]purine] [1637-39-4], C ₁₀ H ₁₃ N ₅ O, F.W. 219.25, Powder, m.p. 208-210°, Merck 14,10117, RTECS EM9506000, BRN 616241, MDL MFCD00213654 | 50mg 100mg 250mg |
| | Application(s): Plant growth hormone that stimulates cell division | |

| Stock # | Description | Size |
|---------|--|-----------------------|
| J63382 | trans-Zeatin-riboside [6-[(E)-4-Hydroxy-3-methylbut-2-enylamino]-9β-D-ribofuranosyl]purine [6025-53-2], C ₁₅ H ₂₂ N ₆ O ₅ , F.W. 351.36, Powder, BRN 5460894, MDL MFCD00036809 | 25mg 50mg 100mg |
| | Application(s): Main effects in tissue culture systems include control of shoot growth and formation, cell division and inhibition of leaf senescence | |
| J65890 | Z-Glu-Asp-Val-Glu-p-nitroanilide ▾ [Z-DEVD-pNA, Z-DEVD-pNA colorimetric substrate] C ₃₂ H ₃₈ N ₆ O ₁₄ , F.W. 730.67, Powder | 5mg |
| J64796 | Z-Gly-Gly-Leu-7-amido-4-methylcoumarin ▲ [Z-Gly-Gly-Leu-AMC, Z-GGL-AMC] C ₂₈ H ₃₂ N ₂ O ₇ , F.W. 536.57, Powder | 5mg 50mg |
| J65721 | Z-Gly-Leu-Phe-chloromethyl ketone [Z-GLF-CMK, Z-Gly-Leu-Phe-CMK] C ₂₈ H ₃₂ ClN ₂ O ₅ , F.W. 502.00, Solid, MDL MFCD03452908 | 10mg 25mg |
| J65505 | Z-Ile-Glu(O-ME)-Thr-Asp(O-Me) fluoromethyl ketone ▾ [Z-IETD-FMK, Caspase-8 inhibitor] C ₃₃ H ₄₃ FN ₃ O ₁₁ , F.W. 654.68, Powder, MDL MFCD01861686 | 5mg |
| A12909 | Zinc acetate dihydrate, 97+% [Acetic acid zinc salt] [5970-45-6], Zn(OOCH ₃) ₂ ·2H ₂ O, F.W. 219.48 (183.45anhy), m.p. 237°, d. 1.735, Merck 14,10128, UN3077, EINECS 209-170-2, RTECS ZG8750000, BRN 3732513, MDL MFCD00066961, †  ! H:H400-H410-H319, P:P280-P273-P264-P305+P351+P338-P337+P313-P501a | 100g 500g 2.5kg |
| J62160 | Zinc chloride, 25mM aq. soln. [7646-85-7], ZnCl ₂ , F.W. 136.28, Liquid, † | 50ml 100ml |
| 12307 | Zinc chloride, ACS, 97% ■ [7646-85-7], ZnCl ₂ , F.W. 136.28, Lump, m.p. 290°, b.p. 732°, d. 2.91, Merck 14,10132, Fieser 1,1289 13,349 15,368 16,391 18,410 19,409 20,439 21,493, Solubility: Freely soluble in water, dilute HCl, alcohol, glycerol, acetone, ether. Zinc oxychloride forms with much water, UN2331, EINECS 231-592-0, RTECS ZH1400000, MDL MFCD00011295, † Maximum level of impurities: Oxychloride P.T., Insoluble matter 0.005%, Ca 0.06%, Mg 0.01%, NO ₃ 0.003%, SO ₄ 0.01%, NH ₄ 0.005%, Fe 0.001%, Pb 0.005%, K 0.02%, Na 0.05%  ! H:H314-H400-H410-H302, P:P260-P303+P361+P353-P305+P351+P338-P301+P330+P331-P405-P501a | 250g 1kg 5kg |
| | Application(s): Catalyst, dehydrating and condensing agent, soldering flux, metal etchant | |
| B23022 | Zinc gluconate hydrate, 97% [Gluconic acid zinc salt] [4468-02-4], C ₁₂ H ₂₂ O ₁₄ Zn·xH ₂ O, F.W. 455.69(anhy), Merck 14,4456, EINECS 224-736-9, RTECS ZH3750000, MDL MFCD00868110, † ! H:H302, P:P264-P270-P301+P312-P330-P501a | 100g 500g |
| |  | |
| J60963 | Zinc sulfate, 100mM aq. soln. [7733-02-0], ZnSO ₄ , F.W. 161.43, Liquid, † ! H:H319-H412, P:P280-P273-P264-P305+P351+P338-P337+P313-P501a | 50ml 100ml |
| 33399 | Zinc sulfate heptahydrate, ACS, 99.0-103.0% [7446-20-0], ZnSO ₄ ·7H ₂ O, F.W. 287.54 (161.43anhy), Lump, m.p. 100°, d. 1.97, Merck 14,10159, Solubility: Soluble in water, glycerol, UN3077, EINECS 231-793-3, RTECS ZH5300000, MDL MFCD00149894, Note: 280° -7H ₂ O, † Maximum level of impurities: Insoluble matter 0.01%, pH of a 5% solution 4.4-6.0 at 25°, Cl 5ppm, NO ₃ 0.002%, NH ₄ 0.001%, Fe 0.001%, Pb 0.003%, Mn 3ppm, Ca 0.005%, Mg 0.005%, K 0.01%, Na 0.05%  ! H:H318-H400-H410-H302, P:P280-P273-P305+P351+P338-P310-P301+P312-P501a | 100g 500g 2.5kg |
| J64557 | ZJ-43 [(S)-2-(3-((S)-1-carboxy-3-methylbutyl)ureido)pentanedioic acid] [723331-20-2], C ₁₂ H ₂₀ N ₂ O ₇ , F.W. 304.30, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 10mg 50mg |
| J64966 | Z-Leu-Glu(O-Me)-His-Asp(O-Me) fluoromethyl ketone trifluoroacetate salt hydrate [Z-LEHD-FMK] C ₃₂ H ₄₃ FN ₃ O ⁺ ·O ⁻ ·C ₂ F ₃ HF ₂ O ₂ ·yH ₂ O · ¹ H ₄₂ O ₃ PD ₂ .CHGaC ₃₂ H ₄₃ FN, F.W. 690.71 (free base), Powder, MDL MFCD01862609 | 1mg 10mg |
| J64613 | Z-Leu-Leu-Glu-7-amido-4-methylcoumarin ▲ [BML-ZW9345, Z-LLE-AMC] C ₃₅ H ₄₄ N ₂ O ₈ , F.W. 664.75, Lyophilized powder, MDL MFCD01074989 | 5mg 50mg |

| Stock # | Description | Size |
|---------|---|---------------|
| J64731 | Z-Leu-Val-Gly-diazomethyl ketone [C-3455] [119670-30-3], C ₂₂ H ₃₁ N ₅ O ₅ , F.W. 445.52, Powder | 25mg 100mg |
| J65730 | ZM 336372 ▲ [N-[5-(3-Dimethylaminobenzamido)-2-methylphenyl]-4-hydroxybenzamide] [208260-29-1], C ₂₃ H ₂₃ N ₃ O ₃ , F.W. 389.45, Solid ! H:H315-H319-H335, P:P261-P305+P351+P338-P302+P352-P321-P405-P501 | 1mg 5mg |
| J60616 | Zolmitriptan [(S)-4-(3-[2-(Dimethylamino)ethyl]-5-indolylmethyl)oxazolidin-2-one] [139264-17-8], C ₁₆ H ₂₁ N ₃ O ₂ , F.W. 287.36, Crystalline powder, m.p. 136-141°, Merck 14,10189, MDL MFCD00871503 Application(s): A serotonin 5HT1D-receptor agonist | 100mg 1g |
| J65795 | Z-Phe-Ala fluoromethyl ketone [Z-FA-FMK, Z-Phe-Ala-FMK] [105637-38-5], C ₂₁ H ₂₃ N ₂ O ₄ F, F.W. 386.42, Powder, MDL MFCD00883668 | 5mg 50mg |
| J64479 | Z-Phe-Arg-7-amido-4-trifluoromethylcoumarin [Z-Phe-Arg-AFC, Z-FR-AFC] C ₃₃ H ₃₃ F ₃ N ₅ O ₆ , F.W. 666.64, Lyophilized powder | 10mg |
| J65856 | Z-Phe-Phe-fluoromethyl ketone [Z-Phe-Phe-FMK, Z-FF-FMK] C ₂₇ H ₂₇ FN ₂ O ₄ , F.W. 462.51, Powder, MDL MFCD03453604 | 1mg 5mg |
| J65523 | Z-Tyr-Val-Ala-Asp(OMe)-fluoromethyl ketone [Z-YVAD-FMK, Z-YVAD(OMe)-FMK] C ₃₁ H ₃₉ FN ₃ O ₆ , F.W. 630.66, Powder | 1mg 5mg |
| J65345 | Z-Val-Ala-Asp(OMe)-fluoromethyl ketone [Z-VAD(OMe)-FMK, Methyl 5-fluoro-3-[2-[[3-methyl-2-(phenylmethoxycarbonylamino)butanoyl]amino]propanoyl- amino]-4-oxopentanoate] [187389-52-2], C ₂₂ H ₃₀ FN ₃ O ₇ , F.W. 467.49, Powder | 5mg 50mg |
| J65419 | Z-Val-Asp(OMe)-Val-Ala-Asp(OMe)-fluoromethyl ketone [Z-VDVAD-FMK, Z-VD(OMe)VAD(OMe)-FMK] C ₃₂ H ₄₆ FN ₅ O ₁₁ , F.W. 695.73, Powder, MDL MFCD03452881 | 5mg 50mg |
| J65892 | Z-Val-Glu(OMe)-Ile-Asp(OMe)-fluoromethyl ketone [Z-VEID-FMK, Z-VE(OMe)ID(OMe)-FMK] C ₃₁ H ₄₅ FN ₄ O ₁₀ , F.W. 652.71, Powder, MDL MFCD03452882 | 1mg 5mg |
| J65339 | Z-Val-Lys(biotin)-Asp(OMe)-fluoromethyl ketone [Z-Val-Lys(biotin)-Asp(OMe)-FMK, Z-VL(biotin)D(OMe)-FMK] C ₃₅ H ₅₁ FN ₆ O ₉ S, F.W. 750.87, Solid | 1mg 5mg |
| J64544 | Z-Val-Val-Nle-diazomethyl ketone [C-3890, Z-Val-Val-Nle-DMK] [155026-49-6], C ₂₅ H ₃₇ N ₅ O ₅ , F.W. 487.60, Powder | 50mg 250mg |
| J61375 | Zymogram developing buffer (10X), pH 7.45 Liquid, Note: 0.5M Tris-HCl, (pH 7.45), 2.0M sodium chloride, 50mM calcium chloride, 0.2% Brij 35. | 500ml 1L |
| J63137 | Zymogram renaturation buffer (10X) Liquid, Note: 27% (w/v) Triton X-100 in DI water. ! H:H302-H318-H412, P:P280-P273-P305+P351+P338-P310-P301+P312-P501 | 500ml 1L |
| J62774 | Zymogram sample buffer, pH 6.6 Liquid, Note: 63mM Tris HCl (pH 6.8), 2% SDS, 10% glycerol, 2% β-mercaptoethanol, 0.005% Bromophenol blue. H:H412, P:P273-P501 | 25ml 50ml |
| | Zymolyase 20T , see Yeast Lytic Enzyme, <i>Arthro bacter luteus</i> , J63195, p. 395 | |
| J62876 | Zymosan, <i>Saccharomyces cerevisiae</i> [58856-93-2], Powder, Merck 14,10200, RTECS Z12750000, MDL MFCD00082157 Application(s): An insoluble preparation of yeast cell, has been shown to activate macrophages via toll-like receptor 2 | 50mg 1g |

Trademarks










Bitrex® is a trademark of Macfarlan Smith, a Johnson Matthey Company.

The following trademarks are acknowledged and are accurate to the best of our knowledge at the time of printing.

| | |
|----------------|----------------------------------|
| Aliquat® | General Mills, Inc. |
| Amberlite® | Rohm & Haas Company |
| Amberlyst® | Rohm & Haas Company |
| Arlacel 83® | Croda International PLC |
| Brij® | Uniqema Americas LLC |
| Carbowax® | Dow Chemical Co. |
| Celite® | Celite Corp. |
| ChiPros® | BASF |
| Coban® | 3M Company |
| DNAzol® | Molecular Research Center, Inc. |
| Eriochrome® | Huntsman International LLC Corp. |
| Ficoll® | GE Healthcare Bio-Sciences |
| Hoechst 33342® | Invitrogen Corporation |
| IGEPAL® | Rhodia Operations |
| Penetrex® | The Clorox Company |
| Span™ | Croda International PLC |
| Texas Red® | Molecular Probes, Inc. |
| Triton® | Dow Chemical Co. |

Precautionary & Hazard Statements

GHS Hazard Symbols - Pictograms

| | | | | |
|---|---|---|---|---|
|  |  |  |  |  |
| Explosive | Oxidizing | Flammable | Toxic | Harmful or Irritant |
|  |  |  |  | |
| Corrosive | Dangerous for the Environment | Health Hazard | Gases | |

GHS Precautionary and Hazard Statements

Hazardous products listed in this catalogue are marked with P and H numbers as assigned to the Precautionary and Hazard statements under UN legislation.

Precautionary Statements

General precautionary statements

- P101 If medical advice is needed, have product container or label at hand
 P102 Keep out of reach of children
 P103 Read label before use

Prevention precautionary statements

- P201 Obtain special instructions before use
 P202 Do not handle until all safety precautions have been read and understood
 P210 Keep away from heat/sparks/open flames/hot surfaces – No smoking
 P211 Do not spray on an open flame or other ignition source
 P220 Keep/Store away from clothing/.../combustible materials
 P221 Take any precaution to avoid mixing with combustibles
 P222 Do not allow contact with air
 P223 Keep away from any possible contact with water, because of violent reaction and possible flash fire
 P230 Keep wetted with ...
 P231 Handle under inert gas
 P232 Protect from moisture
 P233 Keep container tightly closed
 P234 Keep only in original container

- P235 Keep cool
 P240 Ground/bond container and receiving equipment
 P241 Use explosion-proof electrical/ventilating/light/.../equipment
 P242 Use only non-sparking tools
 P243 Take precautionary measures against static discharge
 P244 Keep reduction valves free from grease and oil
 P250 Do not subject to grinding/shock/.../friction
 P251 Pressurized container – Do not pierce or burn, even after use
 P260 Do not breathe dust/fume/gas/mist/vapours/spray
 P261 Avoid breathing dust/fume/gas/mist/vapours/spray
 P262 Do not get in eyes, on skin, or on clothing
 P263 Avoid contact during pregnancy/while nursing
 P264 Wash ... thoroughly after handling
 P270 Do not eat, drink or smoke when using this product
 P271 Use only outdoors or in a well-ventilated area
 P272 Contaminated work clothing should not be allowed out of the workplace
 P273 Avoid release to the environment
 P280 Wear protective gloves/protective clothing/eye protection/face protection
 P281 Use personal protective equipment as required
 P282 Wear cold insulating gloves/face shield/eye protection
 P283 Wear fire/flame resistant/retardant clothing

- P284 Wear respiratory protection
 P285 In case of inadequate ventilation wear respiratory protection
 P231+232 Handle under inert gas. Protect from moisture
 P235+410 Keep cool. Protect from sunlight

Response precautionary statements

- P301 IF SWALLOWED:
 P302 IF ON SKIN:
 P303 IF ON SKIN (or hair):
 P304 IF INHALED:
 P305 IF IN EYES:
 P306 IF ON CLOTHING:
 P307 IF exposed:
 P308 IF exposed or concerned:
 P309 IF exposed or you feel unwell:
 P310 Immediately call a POISON CENTER or doctor/physician
 P311 Call a POISON CENTER or doctor/physician
 P312 Call a POISON CENTER or doctor/physician if you feel unwell
 P313 Get medical advice/attention
 P314 Get Medical advice/attention if you feel unwell
 P315 Get immediate medical advice/attention
 P320 Specific treatment is urgent (see ... on this label)
 P321 Specific treatment (see ... on this label)
 P322 Specific measures (see ... on this label)
 P330 Rinse mouth
 P331 Do NOT induce vomiting
 P332 If skin irritation occurs:
 P333 If skin irritation or a rash occurs:
 P334 Immerse in cool water/wrap in wet bandages
 P335 Brush off loose particles from skin
 P336 Thaw frosted parts with lukewarm water. Do not rub affected area
 P337 If eye irritation persists:
 P338 Remove contact lenses if present and easy to do. Continue rinsing
 P340 Remove victim to fresh air and keep at rest in a position comfortable for breathing
 P341 If breathing is difficult, remove victim to fresh air and keep at rest in a position comfortable for breathing
 P342 If experiencing respiratory symptoms:
 P350 Gently wash with plenty of soap and water
 P351 Rinse continuously with water for several minutes
 P352 Wash with plenty of soap and water
 P353 Rinse skin with water/shower
 P360 Rinse immediately contaminated clothing and skin with plenty of water before removing clothes
 P361 Remove/Take off immediately all contaminated clothing
 P362 Take off contaminated clothing and wash before reuse
 P363 Wash contaminated clothing before reuse
 P370 In case of fire:
 P371 In case of major fire and large quantities:
 P372 Explosion risk in case of fire
 P373 DO NOT fight fire when fire reaches explosives
 P374 Fight fire with normal precautions from a reasonable distance
 P375 Fight fire remotely due to the risk of explosion
 P376 Stop leak if safe to do so
 P377 Leaking gas fire – do not extinguish, unless leak can be stopped safely
 P378 Use ... for extinction

- P380 Evacuate area
 P381 Eliminate all ignition sources if safe to do so
 P390 Absorb spillage to prevent material damage
 P391 Collect spillage
 P301+310 IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician
 P301+312 IF SWALLOWED: Call a POISON CENTER or doctor/physician if you feel unwell
 P301+330+331 IF SWALLOWED: Rinse mouth. Do NOT induce vomiting
 P302+334 IF ON SKIN: Immerse in cool water/wrap in wet bandages
 P302+350 IF ON SKIN: Gently wash with plenty of soap and water
 P302+352 IF ON SKIN: Wash with plenty of soap and water
 P303+361+353 IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower
 P304+312 IF INHALED: Call a POISON CENTER or doctor/physician if you feel unwell
 P304+340 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing
 P304+341 IF INHALED: If breathing is difficult, remove victim to fresh air and keep at rest in a position comfortable for breathing
 P305+351+338 IF IN EYES: Rinse continuously with water for several minutes. Remove contact lenses if present and easy to do – continue rinsing
 P306+360 IF ON CLOTHING: Rinse immediately contaminated clothing and skin with plenty of water before removing clothes
 P307+311 IF exposed: Call a POISON CENTER or doctor/physician
 P308+313 IF exposed or concerned: Get medical advice/attention
 P309+311 IF exposed or you feel unwell: Call a POISON CENTER or doctor/physician
 P332+313 If skin irritation occurs: Get medical advice/attention
 P333+313 If skin irritation or a rash occurs: Get medical advice/attention
 P335+334 Brush off loose particles from skin. Immerse in cool water/wrap in wet bandages
 P337+313 If eye irritation persists: Get medical advice/attention
 P342+311 If experiencing respiratory symptoms: Call a POISON CENTER or doctor/physician
 P370+376 In case of fire: Stop leak if safe to do so
 P370+378 In case of fire: Use ... for extinction
 P370+380 In case of fire: Evacuate area
 P370+380+375 In case of fire: Evacuate area. Fight fire remotely due to the risk of explosion
 P371+380+375 In case of major fire and large quantities: Evacuate area. Fight fire remotely due to the risk of explosion

Storage precautionary statements

- P401 Store ...
 P402 Store in a dry place
 P403 Store in a well ventilated place
 P404 Store in a closed container
 P405 Store locked up
 P406 Store in a corrosive resistant/... container with a resistant inner liner
 P407 Maintain air gap between stacks/pallets
 P410 Protect from sunlight

| | |
|----------|--|
| P411 | Store at temperatures not exceeding ... °C/... °F |
| P412 | Do not expose to temperatures exceeding 50 °C/122 °F |
| P413 | Store bulk masses greater than ... kg/ ... lbs at temperatures not exceeding ... °C/... °F |
| P420 | Store away from other materials |
| P422 | Store contents under ... |
| P402+404 | Store in a dry place. Store in a closed container |
| P403+233 | Store in a well ventilated place. Keep container tightly closed |
| P403+235 | Store in a well ventilated place. Keep cool |
| P410+403 | Protect from sunlight. Store in a well ventilated place |
| P410+412 | Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F |
| P411+235 | Store at temperatures not exceeding... °C/... °F. Keep cool |

Disposal precautionary statements

| | |
|------|--------------------------------------|
| P501 | Dispose of contents/container to ... |
|------|--------------------------------------|

Hazard Statements

Physical hazards

| | |
|------|---|
| H200 | Unstable explosive |
| H201 | Explosive; mass explosion hazard |
| H202 | Explosive; severe projection hazard |
| H203 | Explosive; fire, blast or projection hazard |
| H204 | Fire or projection hazard |
| H205 | May mass explode in fire |
| H220 | Extremely flammable gas |
| H221 | Flammable gas |
| H222 | Extremely flammable material |
| H223 | Flammable material |
| H224 | Extremely flammable liquid and vapour |
| H225 | Highly flammable liquid and vapour |
| H226 | Flammable liquid and vapour |
| H227 | Combustible liquid |
| H228 | Flammable solid |
| H240 | Heating may cause an explosion |
| H241 | Heating may cause a fire or explosion |
| H242 | Heating may cause a fire |
| H250 | Catches fire spontaneously if exposed to air |
| H251 | Self-heating; may catch fire |
| H252 | Self-heating in large quantities; may catch fire |
| H260 | In contact with water releases flammable gases which may ignite spontaneously |
| H261 | In contact with water releases flammable gas |
| H270 | May cause or intensify fire; oxidizer |
| H271 | May cause fire or explosion; strong oxidizer |
| H272 | May intensify fire; oxidizer |
| H280 | Contains gas under pressure; may explode if heated |
| H281 | Contains refrigerated gas; may cause cryogenic burns or injury |
| H290 | May be corrosive to metals |

Health hazards

| | |
|------|---|
| H300 | Fatal if swallowed |
| H301 | Toxic if swallowed |
| H302 | Harmful if swallowed |
| H303 | May be harmful if swallowed |
| H304 | May be fatal if swallowed and enters airways |
| H305 | May be harmful if swallowed and enters airways |
| H310 | Fatal in contact with skin |
| H311 | Toxic in contact with skin |
| H312 | Harmful in contact with skin |
| H313 | May be harmful in contact with skin |
| H314 | Causes severe skin burns and eye damage |
| H315 | Causes skin irritation |
| H316 | Causes mild skin irritation |
| H317 | May cause an allergic skin reaction |
| H318 | Causes serious eye damage |
| H319 | Causes serious eye irritation |
| H320 | Causes eye irritation |
| H330 | Fatal if inhaled |
| H331 | Toxic if inhaled |
| H332 | Harmful if inhaled |
| H333 | May be harmful if inhaled |
| H334 | May cause allergy or asthma symptoms or breathing difficulties if inhaled |
| H335 | May cause respiratory irritation |
| H336 | May cause drowsiness or dizziness |
| H340 | May cause genetic defects |
| H341 | Suspected of causing genetic defects |
| H350 | May cause cancer |
| H351 | Suspected of causing cancer |
| H360 | May damage fertility or the unborn child |
| H361 | Suspected of damaging fertility or the unborn child |
| H362 | May cause harm to breast-fed children |
| H370 | Causes damage to organs |
| H371 | May cause damage to organs |
| H372 | Causes damage to organs through prolonged or repeated exposure |
| H373 | May cause damage to organs through prolonged or repeated exposure |

Environmental hazards

| | |
|------|--|
| H400 | Very toxic to aquatic life |
| H401 | Toxic to aquatic life |
| H402 | Harmful to aquatic life |
| H410 | Very toxic to aquatic life with long lasting effects |
| H411 | Toxic to aquatic life with long lasting effects |
| H412 | Harmful to aquatic life with long lasting effects |
| H413 | May cause long lasting harmful effects to aquatic life |

EUH Statements

All H statements listed before are internationally valid. The following EUH statements are only valid in all countries within the EU.

- EUH001 Explosive when dry.
- EUH006 Explosive with or without contact with air.
- EUH014 Reacts violently with water.
- EUH018 In use may form flammable/explosive vapour/air mixture.
- EUH019 May form explosive peroxides.
- EUH044 Risk of explosion if heated under confinement.
- EUH029 Contact with water liberates toxic gas.
- EUH031 Contact with acids liberates toxic gas.
- EUH032 Contact with acids liberates very toxic gas.
- EUH066 Repeated exposure may cause skin dryness/cracking.
- EUH070 Toxic by eye contact.
- EUH071 Corrosive to the respiratory tract.
- EUH059 Hazardous to the ozone layer.
- EUH201 Contains lead. Should not be used on surfaces liable to being chewed or sucked.
- EUH201A Warning! Contains lead.
- EUH202 Cryanoacrylate. Danger. Bonds skin and eyes in seconds. Keep out of the reach of children.
- EUH203 Contains chromium (VI). May produce an allergic reaction.
- EUH204 Contains isocyanates. May produce an allergic reaction.
- EUH205 Contains epoxy constituents.
- EUH206 Warning! Do not use together with other products. May release dangerous gases (chlorine).
- EUH207 Warning! Contains cadmium. Dangerous fumes are formed during use. See information supplied by the manufacturer. Comply with the safety instructions.
- EUH208 Contains <name of sensitising substance>. May produce an allergic reaction.
- EUH209 Can become highly flammable in use.
- EUH209A Can become flammable in use.
- EUH210 Safety data sheet available on request.
- EUH401 To avoid risks to human health and the environment, comply with the instructions for use.

Alfa Aesar

Visit Our Website at
www.alfa.com

| | | | | | |
|---|---|--|--|--|--|
| 13 | 14 | 15 | 16 | 17 | 18 |
| B Boron [B] 10.811 mp: 2072°C bp: 2551°C d: 2.48 g/cc | C Carbon [C] 12.0107 mp: 3500°C bp: 4827°C d: 2.26 g/cc | N Nitrogen [N] 14.0067 mp: -210°C bp: -196°C d: 1.25 g/l | O Oxygen [O] 15.9994 mp: -218°C bp: -183°C d: 1.43 g/l | F Fluorine [F] 18.998423 mp: -220°C bp: -188°C d: 1.68 g/l | He Helium [He] 4.002602 mp: -272°C bp: -269°C d: 0.179 g/l |

Periodic Table of Elements

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|---|--|--|---|---|---|--|--|--|--|---|---|---|--|--|---|--|--|--|--|--|--|--|---|--|--|---|---|--|---|--|---|---|---|---|--|--|---|---|---|---|--|--|--|--|---|--|---|--|--|---|---|--|---|---|---|---|--|
| 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| H Hydrogen [H] 1.00794 mp: -252.87°C bp: -252.87°C d: 0.089 g/l | He Helium [He] 4.002602 mp: -272°C bp: -269°C d: 0.179 g/l | Li Lithium [Li] 6.941 mp: 180.5°C bp: 1342°C d: 0.535 g/cc | Be Beryllium [Be] 9.01224 mp: 2970°C bp: 2970°C d: 1.848 g/cc | B Boron [B] 10.811 mp: 2072°C bp: 2551°C d: 2.48 g/cc | C Carbon [C] 12.0107 mp: 3500°C bp: 4827°C d: 2.26 g/cc | N Nitrogen [N] 14.0067 mp: -210°C bp: -196°C d: 1.25 g/l | O Oxygen [O] 15.9994 mp: -218°C bp: -183°C d: 1.43 g/l | F Fluorine [F] 18.998423 mp: -220°C bp: -188°C d: 1.68 g/l | Ne Neon [Ne] 20.1797 mp: -248.6°C bp: -248.6°C d: 0.9002 g/l | Na Sodium [Na] 22.98976928 mp: 97.8°C bp: 883°C d: 0.968 g/cc | Mg Magnesium [Mg] 24.304 mp: 650°C bp: 1090°C d: 1.738 g/cc | Al Aluminum [Al] 26.9815386 mp: 933°C bp: 2542°C d: 2.70 g/cc | Si Silicon [Si] 28.0855 mp: 1414°C bp: 2355°C d: 2.33 g/cc | P Phosphorus [P] 30.973762 mp: 44°C bp: 280°C d: 1.82 g/cc | S Sulfur [S] 32.06 mp: 115°C bp: 444°C d: 1.96 g/cc | Cl Chlorine [Cl] 35.453 mp: -101°C bp: -34°C d: 3.12 g/l | Ar Argon [Ar] 39.948 mp: -182°C bp: -186°C d: 1.78 g/l | K Potassium [K] 39.0983 mp: 63.5°C bp: 770°C d: 0.862 g/cc | Ca Calcium [Ca] 40.078 mp: 842°C bp: 1484°C d: 1.55 g/cc | Sc Scandium [Sc] 44.955912 mp: 1539°C bp: 2835°C d: 2.836 g/cc | Ti Titanium [Ti] 47.88 mp: 1668°C bp: 3287°C d: 4.507 g/cc | V Vanadium [V] 50.9415 mp: 1910°C bp: 3407°C d: 6.118 g/cc | Cr Chromium [Cr] 51.9961 mp: 2135°C bp: 2672°C d: 7.19 g/cc | Mn Manganese [Mn] 54.938044 mp: 1246°C bp: 2061°C d: 7.47 g/cc | Fe Iron [Fe] 55.845 mp: 1538°C bp: 2861°C d: 7.87 g/cc | Co Cobalt [Co] 58.933195 mp: 1495°C bp: 2709°C d: 8.86 g/cc | Ni Nickel [Ni] 58.6934 mp: 1455°C bp: 2730°C d: 8.90 g/cc | Cu Copper [Cu] 63.546 mp: 1085°C bp: 2567°C d: 8.93 g/cc | Zn Zinc [Zn] 65.38 mp: 419.5°C bp: 907°C d: 7.14 g/cc | Ga Gallium [Ga] 69.723 mp: 29.76°C bp: 2403°C d: 5.91 g/cc | Ge Germanium [Ge] 72.64 mp: 937.4°C bp: 2833°C d: 5.32 g/cc | As Arsenic [As] 74.9216 mp: 817°C bp: 2875°C d: 5.73 g/cc | Se Selenium [Se] 78.96 mp: 221°C bp: 685°C d: 4.82 g/cc | Br Bromine [Br] 79.904 mp: -7.4°C bp: 58.8°C d: 3.12 g/cc | Kr Krypton [Kr] 83.798 mp: -153°C bp: -153°C d: 3.71 g/l | Rb Rubidium [Rb] 85.4678 mp: 39°C bp: 688°C d: 1.53 g/cc | Sr Strontium [Sr] 87.62 mp: 777°C bp: 1382°C d: 2.54 g/cc | Y Yttrium [Y] 88.90584 mp: 1522°C bp: 2770°C d: 4.67 g/cc | Zr Zirconium [Zr] 91.224 mp: 1852°C bp: 3550°C d: 6.52 g/cc | Nb Niobium [Nb] 92.90638 mp: 2477°C bp: 4947°C d: 8.47 g/cc | Mo Molybdenum [Mo] 95.94 mp: 2623°C bp: 5563°C d: 10.22 g/cc | Tc Technetium [Tc] 98 mp: 2477°C bp: 4947°C d: 11.5 g/cc | Ru Ruthenium [Ru] 101.07 mp: 2250°C bp: 4423°C d: 12.37 g/cc | Rh Rhodium [Rh] 102.9055 mp: 2237°C bp: 4495°C d: 12.41 g/cc | Ir Iridium [Ir] 192.222 mp: 2446°C bp: 4471°C d: 22.56 g/cc | Pt Platinum [Pt] 195.084 mp: 1768°C bp: 3825°C d: 21.45 g/cc | Ag Silver [Ag] 107.8682 mp: 961.78°C bp: 2162°C d: 10.49 g/cc | Cd Cadmium [Cd] 112.411 mp: 321°C bp: 942°C d: 8.65 g/cc | In Indium [In] 114.818 mp: 156.6°C bp: 2071°C d: 7.31 g/cc | Sn Tin [Sn] 118.710 mp: 231.9°C bp: 2260°C d: 7.31 g/cc | Pb Lead [Pb] 207.2 mp: 327.3°C bp: 1749°C d: 11.34 g/cc | Tl Thallium [Tl] 204.3833 mp: 304°C bp: 1740°C d: 11.85 g/cc | Po Polonium [Po] 209 mp: 254°C bp: 337°C d: 9.19 g/cc | Bi Bismuth [Bi] 208.9804 mp: 271°C bp: 630°C d: 9.78 g/cc | Po Polonium [Po] 209 mp: 254°C bp: 337°C d: 9.19 g/cc | At Astatine [At] 210 mp: 302°C bp: 575°C d: 9.37 g/cc | Rn Radon [Rn] 222 mp: -210°C bp: -62°C d: 9.73 g/l |

key

- H** - Hydrogen
- Density**
- Melting Point**
- Boiling Point**
- Electron Configuration**
- Symbol**
- Atomic Weight**
- Atomic Number**

| | | | | | | | | | | | | | | | | | |
|--|--|---|--|---|---|---|--|--|--|--|--|---|--|---|--|--|---|
| 19 | 20 | 21 | 22 | 23 | 24 | 25 | 26 | 27 | 28 | 29 | 30 | 31 | 32 | 33 | 34 | 35 | 36 |
| Fr Francium [Fr] 223 mp: 27°C bp: 670°C d: 1.88 g/cc | Ra Radium [Ra] 226 mp: 700°C bp: 1350°C d: 5.50 g/cc | Ac Actinium [Ac] 227 mp: 1050°C bp: 3290°C d: 6.09 g/cc | La Lanthanum [La] 138.90547 mp: 920°C bp: 3500°C d: 6.918 g/cc | Ce Cerium [Ce] 140.12 mp: 799°C bp: 3443°C d: 6.99 g/cc | Pr Praseodymium [Pr] 140.90766 mp: 935°C bp: 3273°C d: 6.773 g/cc | Nd Neodymium [Nd] 144.24 mp: 1024°C bp: 3273°C d: 6.99 g/cc | Pm Promethium [Pm] 145 mp: 914°C bp: 2800°C d: 7.26 g/cc | Sm Samarium [Sm] 150.36 mp: 1072°C bp: 3273°C d: 7.54 g/cc | Eu Europium [Eu] 151.964 mp: 822°C bp: 1597°C d: 5.20 g/cc | Gd Gadolinium [Gd] 157.25 mp: 1313°C bp: 3273°C d: 7.90 g/cc | Tb Terbium [Tb] 158.92534 mp: 1362°C bp: 3273°C d: 8.23 g/cc | Dy Dysprosium [Dy] 162.50031 mp: 1412°C bp: 3273°C d: 8.55 g/cc | Ho Holmium [Ho] 164.93032 mp: 1472°C bp: 3273°C d: 8.79 g/cc | Er Erbium [Er] 167.259 mp: 1527°C bp: 3273°C d: 9.05 g/cc | Tm Thulium [Tm] 168.93002 mp: 1545°C bp: 3273°C d: 9.32 g/cc | Yb Ytterbium [Yb] 173.045 mp: 1069°C bp: 3273°C d: 9.67 g/cc | Lu Lutetium [Lu] 174.967 mp: 1323°C bp: 3273°C d: 9.84 g/cc |

| | | | | | | | | | | | | | | | | | |
|---|---|--|---|---|--|--|---|---|--|---|---|---|---|---|---|---|---|
| 37 | 38 | 39 | 40 | 41 | 42 | 43 | 44 | 45 | 46 | 47 | 48 | 49 | 50 | 51 | 52 | 53 | 54 |
| Rf Rutherfordium [Rf] 261 mp: 1537°C bp: 2900°C d: 13.27 g/cc | Db Dubnium [Db] 262 mp: 1537°C bp: 2900°C d: 13.27 g/cc | Sg Seaborgium [Sg] 266 mp: 1537°C bp: 2900°C d: 13.27 g/cc | Bh Bohrium [Bh] 264 mp: 1537°C bp: 2900°C d: 13.27 g/cc | Hs Hassium [Hs] 277 mp: 1537°C bp: 2900°C d: 13.27 g/cc | Mt Meitnerium [Mt] 288 mp: 1537°C bp: 2900°C d: 13.27 g/cc | Ds Darmstadtium [Ds] 289 mp: 1537°C bp: 2900°C d: 13.27 g/cc | Rg Roentgenium [Rg] 291 mp: 1537°C bp: 2900°C d: 13.27 g/cc | Cn Copernicium [Cn] 285 mp: 1537°C bp: 2900°C d: 13.27 g/cc | Nh Nihonium [Nh] 286 mp: 1537°C bp: 2900°C d: 13.27 g/cc | Fl Flerovium [Fl] 289 mp: 1537°C bp: 2900°C d: 13.27 g/cc | Uuq Ununquadium [Uuq] 294 mp: 1537°C bp: 2900°C d: 13.27 g/cc | Uup Ununpentium [Uup] 295 mp: 1537°C bp: 2900°C d: 13.27 g/cc | Uuq Ununquadium [Uuq] 294 mp: 1537°C bp: 2900°C d: 13.27 g/cc | Uup Ununpentium [Uup] 295 mp: 1537°C bp: 2900°C d: 13.27 g/cc | Uuq Ununquadium [Uuq] 294 mp: 1537°C bp: 2900°C d: 13.27 g/cc | Uup Ununpentium [Uup] 295 mp: 1537°C bp: 2900°C d: 13.27 g/cc | Uuq Ununquadium [Uuq] 294 mp: 1537°C bp: 2900°C d: 13.27 g/cc |

| | | | | | | | | | | | | | | | | |
|--|--|--|---|---|---|--|--|--|--|--|---|--|---|--|--|---|
| 55 | 56 | 57 | 58 | 59 | 60 | 61 | 62 | 63 | 64 | 65 | 66 | 67 | 68 | 69 | 70 | 71 |
| Cs Cesium [Cs] 132.9054519 mp: 28.5°C bp: 688°C d: 1.88 g/cc | Ba Barium [Ba] 137.327 mp: 727°C bp: 1640°C d: 3.51 g/cc | La Lanthanum [La] 138.90547 mp: 920°C bp: 3500°C d: 6.918 g/cc | Ce Cerium [Ce] 140.12 mp: 799°C bp: 3443°C d: 6.99 g/cc | Pr Praseodymium [Pr] 140.90766 mp: 935°C bp: 3273°C d: 6.773 g/cc | Nd Neodymium [Nd] 144.24 mp: 1024°C bp: 3273°C d: 6.99 g/cc | Pm Promethium [Pm] 145 mp: 914°C bp: 2800°C d: 7.26 g/cc | Sm Samarium [Sm] 150.36 mp: 1072°C bp: 3273°C d: 7.54 g/cc | Eu Europium [Eu] 151.964 mp: 822°C bp: 1597°C d: 5.20 g/cc | Gd Gadolinium [Gd] 157.25 mp: 1313°C bp: 3273°C d: 7.90 g/cc | Tb Terbium [Tb] 158.92534 mp: 1362°C bp: 3273°C d: 8.23 g/cc | Dy Dysprosium [Dy] 162.50031 mp: 1412°C bp: 3273°C d: 8.55 g/cc | Ho Holmium [Ho] 164.93032 mp: 1472°C bp: 3273°C d: 8.79 g/cc | Er Erbium [Er] 167.259 mp: 1527°C bp: 3273°C d: 9.05 g/cc | Tm Thulium [Tm] 168.93002 mp: 1545°C bp: 3273°C d: 9.32 g/cc | Yb Ytterbium [Yb] 173.045 mp: 1069°C bp: 3273°C d: 9.67 g/cc | Lu Lutetium [Lu] 174.967 mp: 1323°C bp: 3273°C d: 9.84 g/cc |

| | | | | | | | | | | | | | | | | |
|--|--|---|---|---|---|--|---|---|--|---|---|---|---|--|--|----|
| 72 | 73 | 74 | 75 | 76 | 77 | 78 | 79 | 80 | 81 | 82 | 83 | 84 | 85 | 86 | 87 | 88 |
| Hf Hafnium [Hf] 178.49 mp: 2204°C bp: 5027°C d: 13.31 g/cc | Ta Tantalum [Ta] 180.94788 mp: 2996°C bp: 5424°C d: 15.65 g/cc | W Tungsten [W] 183.84 mp: 3410°C bp: 5620°C d: 19.35 g/cc | Re Rhenium [Re] 186.207 mp: 3180°C bp: 5620°C d: 21.03 g/cc | Os Osmium [Os] 192.22 mp: 3047°C bp: 5540°C d: 22.57 g/cc | Ir Iridium [Ir] 192.222 mp: 2446°C bp: 4471°C d: 22.56 g/cc | Pt Platinum [Pt] 195.084 mp: 1768°C bp: 3825°C d: 21.45 g/cc | Au Gold [Au] 196.966569 mp: 1063°C bp: 2835°C d: 19.30 g/cc | Hg Mercury [Hg] 200.59 mp: -38.83°C bp: 357°C d: 13.55 g/cc | Tl Thallium [Tl] 204.3833 mp: 304°C bp: 1740°C d: 11.85 g/cc | Pb Lead [Pb] 207.2 mp: 327.3°C bp: 1749°C d: 11.34 g/cc | Bi Bismuth [Bi] 208.9804 mp: 271°C bp: 630°C d: 9.78 g/cc | Po Polonium [Po] 209 mp: 254°C bp: 337°C d: 9.19 g/cc | At Astatine [At] 210 mp: 302°C bp: 575°C d: 9.37 g/cc | Rn Radon [Rn] 222 mp: -210°C bp: -62°C d: 9.73 g/l | Fr Francium [Fr] 223 mp: 27°C bp: 670°C d: 1.88 g/cc | |

| | | | | | | | | | | | | | | | | |
|--|---|--|---|---|---|--|--|--|--|--|---|--|---|--|--|---|
| 89 | 90 | 91 | 92 | 93 | 94 | 95 | 96 | 97 | 98 | 99 | 100 | 101 | 102 | 103 | 104 | 105 |
| Ra Radium [Ra] 226 mp: 700°C bp: 1350°C d: 5.50 g/cc | Ac Actinium [Ac] 227 mp: 1050°C bp: 3290°C d: 6.09 g/cc | La Lanthanum [La] 138.90547 mp: 920°C bp: 3500°C d: 6.918 g/cc | Ce Cerium [Ce] 140.12 mp: 799°C bp: 3443°C d: 6.99 g/cc | Pr Praseodymium [Pr] 140.90766 mp: 935°C bp: 3273°C d: 6.773 g/cc | Nd Neodymium [Nd] 144.24 mp: 1024°C bp: 3273°C d: 6.99 g/cc | Pm Promethium [Pm] 145 mp: 914°C bp: 2800°C d: 7.26 g/cc | Sm Samarium [Sm] 150.36 mp: 1072°C bp: 3273°C d: 7.54 g/cc | Eu Europium [Eu] 151.964 mp: 822°C bp: 1597°C d: 5.20 g/cc | Gd Gadolinium [Gd] 157.25 mp: 1313°C bp: 3273°C d: 7.90 g/cc | Tb Terbium [Tb] 158.92534 mp: 1362°C bp: 3273°C d: 8.23 g/cc | Dy Dysprosium [Dy] 162.50031 mp: 1412°C bp: 3273°C d: 8.55 g/cc | Ho Holmium [Ho] 164.93032 mp: 1472°C bp: 3273°C d: 8.79 g/cc | Er Erbium [Er] 167.259 mp: 1527°C bp: 3273°C d: 9.05 g/cc | Tm Thulium [Tm] 168.93002 mp: 1545°C bp: 3273°C d: 9.32 g/cc | Yb Ytterbium [Yb] 173.045 mp: 1069°C bp: 3273°C d: 9.67 g/cc | Lu Lutetium [Lu] 174.967 mp: 1323°C bp: 3273°C d: 9.84 g/cc |

| | | | | | | | | | | | | | | | | |
|---|--|---|---|---|---|--|--|--|---|--|---|---|---|--|--|--|
| 106 | 107 | 108 | 109 | 110 | 111 | 112 | 113 | 114 | 115 | 116 | 117 | 118 | 119 | 120 | 121 | 122 |
| Hg Mercury [Hg] 200.59 mp: -38.83°C bp: 357°C d: 13.55 g/cc | Tl Thallium [Tl] 204.3833 mp: 304°C bp: 1740°C d: 11.85 g/cc | Pb Lead [Pb] 207.2 mp: 327.3°C bp: 1749°C d: 11.34 g/cc | Bi Bismuth [Bi] 208.9804 mp: 271°C bp: 630°C d: 9.78 g/cc | Po Polonium [Po] 209 mp: 254°C bp: 337°C d: 9.19 g/cc | At Astatine [At] 210 mp: 302°C bp: 575°C d: 9.37 g/cc | Rn Radon [Rn] 222 mp: -210°C bp: -62°C d: 9.73 g/l | Fr Francium [Fr] 223 mp: 27°C bp: 670°C d: 1.88 g/cc | Ra Radium [Ra] 226 mp: 700°C bp: 1350°C d: 5.50 g/cc | Ac Actinium [Ac] 227 mp: 1050°C bp: 3290°C d: 6.09 g/cc | La Lanthanum [La] 138.90547 mp: 920°C bp: 3500°C d: 6.918 g/cc | Ce Cerium [Ce] 140.12 mp: 799°C bp: 3443°C d: 6.99 g/cc | Pr Praseodymium [Pr] 140.90766 mp: 935°C bp: 3273°C d: 6.773 g/cc | Nd Neodymium [Nd] 144.24 mp: 1024°C bp: 3273°C d: 6.99 g/cc | Pm Promethium [Pm] 145 mp: 914°C bp: 2800°C d: 7.26 g/cc | Sm Samarium [Sm] 150.36 mp: 1072°C bp: 3273°C d: 7.54 g/cc | Eu Europium [Eu] 151.964 mp: 822°C bp: 1597°C d: 5.20 g/cc |

| | | | | | | | | | | | | | | | | |
|---|--|--|---|--|---|---|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 123 | 124 | 125 | 126 | 127 | 128 | 129 | 130 | 131 | 132 | 133 | 134 | 135 | 136 | 137 | 138 | 139 |
| U Uranium [U] 238.02891 mp: 1132°C bp: 4084°C d: 19.05 g/cc | Np Neptunium [Np] 237 mp: 640°C bp: 2712°C d: 20.25 g/cc | Pu Plutonium [Pu] 239.04688 mp: 912°C bp: 3273°C d: 19.84 g/cc | Am Americium [Am] 243 mp: 1362°C bp: 2712°C d: 13.67 g/cc | Cm Curium [Cm] 247 mp: 1362°C bp: 2712°C d: 13.67 g/cc | Bk Berkelium [Bk] 247 mp: 1362°C bp: 2712°C d: 13.67 g/cc | Cf Californium [Cf] 251 mp: 1362°C bp: | | | | | | | | | | |

Access the Latest Information www.alfa.com

**Looking for new
products?**

**Want to check
product availability?**

Need more information?

**Visit
www.alfa.com**

**Our website provides easy
access to the following:**

- Material Safety Data Sheets (MSDS)
- Certificates of Analysis
- Up-to-date product availability
- Current pricing and ability to request pricing quotations
- Structure/substructure search

**Other enhancements to the
site include:**

- Improved search function
- Easy online shopping
- Order tracking and history
- Complete technical information and literature references



Alfa Aesar

Alfa Aesar

